

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027024

Luminaire Tested: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027024
REPORT IS A COMBINATION OF REPORTS P1002608 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5791.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	100	96	92	89	93	90	86	83	78	76	73	68	66	64	58	56	55
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	38	35
5	70	59	51	45	65	55	48	42	49	43	38	43	38	34	37	33	30
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	31	27	24
8	56	43	36	30	52	41	34	29	36	31	26	32	27	24	28	24	21
9	52	40	32	27	49	37	31	26	33	28	24	29	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7813	7813	7813	7813
5°	7819	8863	7826	6724
10°	7771	10102	7758	5772
15°	7714	10954	7666	5215
20°	7617	12003	7547	4761
25°	7530	13753	7393	4492
30°	7406	14510	7278	4249
35°	7209	11631	7058	4053
40°	6903	8039	6801	3846
45°	6515	5985	6442	3674
50°	6072	4927	5972	3537
55°	5593	4202	5549	3417
60°	5124	3597	5035	3324
65°	4617	3106	4543	3189
70°	4083	2579	4028	2955
75°	3516	1995	3469	2564
80°	2776	1349	2676	1885
85°	1778	676	1715	962

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11933 cd/sqm

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.4	2.0
10°-20°	349.6	6.0
20°-30°	567.8	9.8
30°-40°	694.0	12.0
40°-50°	629.5	10.9
50°-60°	501.4	8.7
60°-70°	349.2	6.0
70°-80°	186.0	3.2
80°-90°	47.3	0.8
90°-100°	26.0	0.4
100°-110°	172.6	3.0
110°-120°	310.8	5.4
120°-130°	398.9	6.9
130°-140°	429.0	7.4
140°-150°	402.7	7.0
150°-160°	325.7	5.6
160°-170°	210.6	3.6
170°-180°	72.6	1.3
0°-30°	1034.8	17.9
0°-40°	1728.7	29.9
0°-60°	2859.6	49.4
0°-90°	3442.1	59.4
90°-120°	509.3	8.8
90°-150°	1739.8	30.0
90°-180°	2349.0	40.6
0°-180°	5791.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1407	1219	1067	1218	116
15°	1171	1757	1164	836	1171	330
25°	1078	2161	1058	706	1078	496
35°	938	1735	918	604	938	586
45°	737	818	729	502	737	568
55°	519	504	514	410	519	464
65°	321	310	316	318	321	318
75°	155	152	153	196	155	165
85°	31	34	30	49	31	37
90°	1	14	1	14	1	4
95°	32	12	32	12	32	40
105°	167	168	167	168	167	177
115°	313	311	313	311	313	310
125°	445	445	445	445	445	397
135°	555	553	555	553	555	428
145°	643	642	643	642	643	402
155°	708	703	708	703	708	326
165°	748	744	748	744	748	211
175°	765	761	765	761	765	73
180°	765	765	765	765	765	

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1221.5	1228.7	1237.0	1243.2	1253.6	1256.7	1261.9	1265.0	1268.1	1271.2	1273.2
5°	1218.4	1236.0	1251.5	1262.9	1282.6	1289.8	1299.1	1310.5	1324.0	1335.3	1342.6
7.5°	1210.1	1238.0	1258.7	1281.5	1308.4	1326.0	1335.3	1359.2	1380.9	1397.5	1419.2
10°	1199.7	1232.9	1265.0	1299.1	1337.4	1357.1	1375.7	1408.8	1438.9	1465.8	1487.5
12.5°	1188.4	1228.7	1267.0	1311.5	1363.3	1387.1	1399.5	1456.5	1493.7	1508.2	1550.7
15°	1170.8	1218.4	1273.2	1328.1	1371.6	1399.5	1433.7	1479.2	1516.5	1548.6	1582.7
17.5°	1154.2	1206.0	1261.9	1322.9	1386.1	1422.3	1448.2	1488.6	1528.9	1570.3	1602.4
20°	1127.3	1194.6	1251.5	1316.7	1391.2	1417.1	1444.0	1491.7	1535.1	1579.6	1620.0
22.5°	1105.5	1169.7	1247.4	1309.5	1372.6	1398.5	1431.6	1481.3	1533.1	1583.8	1642.8
25°	1077.6	1149.0	1216.3	1282.6	1347.8	1375.7	1405.7	1469.9	1523.7	1589.0	1654.2
27.5°	1047.6	1121.1	1188.4	1248.4	1309.5	1347.8	1379.9	1447.1	1518.6	1590.0	1674.9
30°	1015.5	1084.8	1149.0	1208.0	1275.3	1314.6	1346.7	1425.4	1505.1	1596.2	1697.7
32.5°	981.3	1046.5	1101.4	1161.4	1232.9	1269.1	1312.6	1398.5	1492.7	1601.4	1728.7
35°	937.8	1000.0	1048.6	1109.7	1181.1	1227.7	1273.2	1369.5	1479.2	1600.3	1746.3
37.5°	894.4	943.0	989.6	1054.8	1137.6	1180.1	1227.7	1333.3	1458.5	1597.2	1753.5
40°	842.6	890.2	930.6	996.9	1083.8	1132.5	1182.1	1292.9	1434.7	1585.9	1727.7
42.5°	790.9	831.2	875.7	945.1	1028.9	1080.7	1133.5	1256.7	1403.7	1552.7	1656.2
45°	737.0	768.1	816.7	879.9	968.9	1018.6	1078.6	1212.2	1360.2	1492.7	1544.4
47.5°	681.1	712.2	757.7	818.8	906.8	965.8	1022.7	1156.3	1305.3	1407.8	1407.8
50°	627.3	652.1	696.7	757.7	846.8	900.6	958.6	1100.4	1220.4	1296.0	1228.7
52.5°	569.3	597.3	634.5	698.7	786.7	835.4	898.5	1019.6	1133.5	1164.5	1061.0
55°	518.6	541.4	576.6	637.7	719.4	770.2	824.0	939.9	1036.2	1034.1	923.4
57.5°	465.8	484.5	521.7	577.6	653.2	698.7	752.6	853.0	931.6	903.7	799.1
60°	417.2	430.6	466.9	512.4	584.9	627.3	679.1	760.8	820.9	781.5	676.0
62.5°	366.4	382.0	411.0	455.5	519.6	553.8	592.1	674.9	713.2	678.0	570.4
65°	320.9	333.3	359.2	396.5	454.4	485.5	518.6	586.9	623.2	572.4	483.4
67.5°	275.4	289.8	308.5	341.6	387.1	416.1	445.1	504.1	520.7	475.1	400.6
70°	232.9	245.3	262.9	286.7	325.0	350.9	372.7	421.3	432.7	390.3	331.2
72.5°	191.5	199.8	214.3	233.9	269.1	283.6	306.4	339.5	354.0	315.7	273.3
75°	155.3	161.5	170.8	185.3	209.1	224.6	243.3	274.3	273.3	246.4	216.3
77.5°	120.1	121.1	131.5	144.9	159.4	172.9	182.2	203.9	206.0	189.4	164.6
80°	85.9	89.0	93.2	103.5	115.9	121.1	132.5	146.0	148.0	135.6	119.0
82.5°	54.9	56.9	60.0	66.2	74.5	80.7	87.0	92.1	97.3	90.1	76.6
85°	31.1	32.1	35.2	37.3	41.4	44.5	49.7	54.9	53.8	48.7	44.5
87.5°	15.5	15.5	15.5	17.6	19.7	19.7	21.7	22.8	23.8	21.7	19.7
90°	0.6	1.6	2.6	3.6	4.6	5.1	5.5	6.4	7.3	8.2	9.1
92.5°	10.8	9.7	8.5	7.4	6.3	5.7	6.1	6.8	7.6	8.3	9.1
95°	32.3	31.9	31.5	31.2	30.8	30.6	28.2	23.4	18.7	13.9	9.1
97.5°	60.7	61.5	62.2	63.0	63.7	64.1	58.1	46.1	34.2	22.2	10.2
100°	94.7	95.1	95.5	95.8	96.2	96.4	96.6	97.1	97.6	98.1	98.6
102.5°	129.2	129.7	130.2	130.7	131.2	131.5	131.6	131.9	132.1	132.4	132.6
105°	166.6	167.1	167.6	168.1	168.6	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.2	205.2	205.2	205.2	205.2	205.2	205.3	205.6	205.8	206.1	206.3
110°	242.6	242.6	242.6	242.6	242.6	242.6	242.7	243.0	243.2	243.5	243.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	277.7	278.1	278.5	278.8	279.2	279.4	279.5	279.6	279.7	279.9	280.0
115°	312.9	313.5	314.1	314.8	315.4	315.7	315.8	315.9	316.0	316.2	316.3
117.5°	349.7	349.7	349.7	349.7	349.7	349.7	350.0	350.5	351.0	351.5	352.0
120°	383.7	383.6	383.5	383.4	383.3	383.2	383.4	383.8	384.1	384.5	384.9
122.5°	413.8	414.4	415.0	415.7	416.3	416.6	416.7	416.8	416.9	417.1	417.2
125°	445.0	445.9	446.7	447.6	448.5	448.9	448.9	448.9	448.9	448.9	448.9
127.5°	475.0	475.6	476.2	476.9	477.5	477.8	477.7	477.6	477.5	477.4	477.3
130°	502.2	502.8	503.4	504.1	504.7	505.0	505.1	505.2	505.3	505.5	505.6
132.5°	529.4	530.2	530.9	531.7	532.4	532.8	532.6	532.2	531.9	531.5	531.1
135°	554.9	555.7	556.4	557.2	557.9	558.3	558.2	557.9	557.7	557.4	557.2
137.5°	578.7	579.5	580.2	581.0	581.7	582.1	582.0	581.7	581.5	581.2	581.0
140°	602.0	602.2	602.5	602.7	603.0	603.1	603.0	602.9	602.8	602.6	602.5
142.5°	622.9	623.0	623.2	623.3	623.4	623.5	623.6	623.9	624.1	624.4	624.6
145°	643.4	643.6	643.9	644.1	644.4	644.5	644.5	644.5	644.5	644.5	644.5
147.5°	661.5	661.5	661.5	661.5	661.5	661.5	661.6	661.7	661.8	662.0	662.1
150°	678.5	678.3	678.0	677.8	677.5	677.4	677.5	677.8	678.0	678.3	678.5
152.5°	694.9	694.3	693.7	693.0	692.4	692.1	692.2	692.5	692.7	693.0	693.2
155°	708.5	707.7	707.0	706.2	705.5	705.1	705.2	705.5	705.8	706.0	706.3
157.5°	719.3	718.9	718.5	718.2	717.8	717.6	717.6	717.6	717.6	717.6	717.6
160°	730.6	729.8	729.1	728.3	727.6	727.2	727.3	727.4	727.5	727.7	727.8
162.5°	739.7	738.9	738.2	737.4	736.7	736.3	736.4	736.5	736.6	736.8	736.9
165°	747.7	746.9	746.2	745.4	744.7	744.3	744.4	744.5	744.6	744.7	744.8
167.5°	753.9	753.1	752.4	751.6	750.9	750.5	750.6	750.7	750.8	751.0	751.1
170°	759.0	758.1	757.2	756.3	755.4	755.0	755.1	755.2	755.3	755.5	755.6
172.5°	762.4	761.5	760.6	759.7	758.8	758.4	758.5	758.8	759.1	759.3	759.6
175°	764.7	763.9	763.2	762.4	761.7	761.3	761.4	761.5	761.6	761.7	761.8
177.5°	766.4	765.6	764.9	764.1	763.4	763.0	763.1	763.2	763.3	763.4	763.5
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1275.3	1282.6	1288.8	1293.9	1298.1	1304.3	1300.2	1301.2	1303.3	1307.4	1307.4
5°	1358.1	1369.5	1375.7	1396.4	1401.6	1400.6	1397.5	1414.0	1413.0	1406.8	1405.7
7.5°	1438.9	1458.5	1476.1	1492.7	1497.9	1511.3	1514.4	1521.7	1519.6	1530.0	1524.8
10°	1512.4	1543.4	1560.0	1584.8	1591.0	1597.2	1605.5	1609.7	1619.0	1617.9	1617.9
12.5°	1569.3	1606.6	1628.3	1634.5	1658.3	1665.6	1672.8	1686.3	1683.2	1684.2	1690.4
15°	1613.8	1650.0	1668.7	1697.7	1714.2	1722.5	1734.9	1749.4	1747.3	1756.7	1754.6
17.5°	1646.9	1681.1	1715.2	1758.7	1759.8	1781.5	1810.5	1816.7	1830.2	1820.8	1820.8
20°	1673.8	1719.4	1768.0	1823.9	1830.2	1843.6	1878.8	1902.6	1918.1	1913.0	1916.1
22.5°	1702.8	1768.0	1825.0	1880.9	1910.9	1934.7	1968.9	2006.1	2019.6	2027.9	2025.8
25°	1740.1	1808.4	1892.3	1969.9	2001.0	2046.5	2092.0	2128.3	2138.6	2161.4	2140.7
27.5°	1778.4	1874.7	1979.2	2070.3	2109.6	2146.9	2201.8	2228.7	2242.1	2252.5	2245.2
30°	1810.5	1943.0	2056.8	2140.7	2168.6	2190.4	2221.4	2227.6	2222.5	2230.8	2241.1
32.5°	1860.2	1989.6	2085.8	2126.2	2123.1	2122.1	2098.3	2065.1	2057.9	2038.2	2065.1
35°	1887.1	1990.6	2027.9	1974.0	1952.3	1913.0	1837.4	1787.7	1744.2	1734.9	1737.0
37.5°	1871.6	1911.9	1867.4	1725.6	1690.4	1630.4	1530.0	1459.6	1427.5	1402.6	1434.7
40°	1787.7	1743.2	1621.0	1448.2	1397.5	1340.5	1246.3	1208.0	1162.5	1153.2	1195.6
42.5°	1649.0	1513.4	1340.5	1207.0	1154.2	1122.1	1043.4	1007.2	975.1	960.6	984.4
45°	1460.6	1296.0	1122.1	1012.4	967.9	929.6	883.0	844.7	824.0	817.8	837.4
47.5°	1266.0	1092.1	953.4	871.6	825.0	796.0	752.6	730.8	714.3	716.3	719.4
50°	1079.7	921.3	814.7	732.9	710.1	687.3	658.4	639.7	631.4	634.5	632.5
52.5°	919.2	790.9	700.8	637.7	627.3	605.6	581.8	566.2	563.1	564.2	567.3
55°	778.4	678.0	606.6	561.1	549.7	534.1	519.6	509.3	501.0	504.1	503.1
57.5°	671.8	583.8	529.0	491.7	483.4	474.1	460.6	455.5	452.4	446.2	451.3
60°	577.6	506.2	458.6	435.8	428.6	422.3	407.9	401.6	399.6	396.5	404.7
62.5°	488.6	437.9	401.6	380.9	373.7	367.5	360.2	355.1	356.1	352.0	356.1
65°	418.2	376.8	350.9	332.3	323.0	318.8	317.8	309.5	308.5	309.5	310.5
67.5°	353.0	317.8	298.1	286.7	279.5	275.4	272.2	267.1	271.2	268.1	270.2
70°	294.0	270.2	249.5	238.1	235.0	236.0	230.8	228.8	229.8	227.7	229.8
72.5°	237.1	217.4	209.1	200.8	196.7	195.6	192.5	189.4	192.5	191.5	191.5
75°	189.4	174.9	165.6	160.4	160.4	158.4	153.2	153.2	153.2	152.2	153.2
77.5°	146.0	133.5	129.4	124.2	124.2	121.1	120.1	120.1	118.0	121.1	119.0
80°	108.7	99.4	93.2	90.1	90.1	89.0	87.0	85.9	87.0	85.9	85.9
82.5°	70.4	66.2	63.1	60.0	59.0	60.0	59.0	56.9	58.0	56.9	59.0
85°	40.4	36.2	36.2	34.2	35.2	33.1	34.2	32.1	31.1	34.2	32.1
87.5°	17.6	16.6	16.6	14.5	14.5	14.5	13.5	14.5	13.5	12.4	13.5
90°	9.7	10.3	11.0	11.6	11.9	12.1	12.5	12.8	13.2	13.6	13.2
92.5°	9.7	10.3	11.0	11.6	11.9	12.0	12.1	12.2	12.4	12.5	12.4
95°	9.7	10.3	11.0	11.6	11.9	11.9	11.9	11.9	11.9	11.9	11.9
97.5°	10.4	10.7	10.9	11.2	11.3	11.4	11.5	11.6	11.8	11.9	11.8
100°	79.8	61.1	42.3	23.6	14.2	13.9	13.4	12.9	12.4	11.9	12.4
102.5°	132.9	133.1	133.4	133.7	133.8	128.5	117.9	107.4	96.8	86.2	96.8
105°	168.9	168.9	168.9	168.9	168.9	168.8	168.7	168.6	168.4	168.3	168.4
107.5°	206.4	206.6	206.7	206.8	206.9	206.6	206.1	205.6	205.1	204.6	205.1
110°	243.3	242.9	242.6	242.2	242.0	242.1	242.2	242.3	242.5	242.6	242.5

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	279.5	279.0	278.5	278.0	277.7	277.6	277.3	277.1	276.8	276.6	276.8
115°	315.8	315.3	314.8	314.3	314.0	313.6	312.9	312.1	311.4	310.6	311.4
117.5°	351.2	350.5	349.7	349.0	348.6	348.5	348.2	348.0	347.7	347.5	347.7
120°	384.6	384.4	384.1	383.8	383.7	383.4	382.8	382.1	381.5	380.9	381.5
122.5°	417.0	416.7	416.5	416.2	416.1	415.7	415.0	414.2	413.5	412.7	413.5
125°	448.4	447.9	447.4	446.9	446.7	446.5	446.1	445.8	445.4	445.0	445.4
127.5°	477.0	476.8	476.5	476.2	476.1	475.6	474.6	473.6	472.6	471.6	472.6
130°	505.2	504.8	504.5	504.1	503.9	503.6	503.0	502.3	501.7	501.1	501.7
132.5°	531.1	531.1	531.1	531.1	531.1	530.8	530.2	529.5	528.9	528.3	528.9
135°	557.0	556.7	556.5	556.2	556.1	555.7	555.0	554.2	553.5	552.7	553.5
137.5°	581.0	581.0	581.0	581.0	581.0	580.7	580.1	579.4	578.8	578.2	578.8
140°	602.8	603.0	603.3	603.6	603.7	603.3	602.6	601.8	601.1	600.3	601.1
142.5°	624.6	624.6	624.6	624.6	624.6	624.2	623.5	622.7	622.0	621.2	622.0
145°	644.6	644.8	644.9	645.0	645.1	644.7	644.0	643.2	642.5	641.7	642.5
147.5°	662.2	662.3	662.4	662.5	662.6	662.2	661.3	660.4	659.6	658.7	659.6
150°	678.7	679.0	679.2	679.5	679.6	679.1	678.1	677.1	676.1	675.1	676.1
152.5°	693.5	693.7	694.0	694.3	694.4	694.0	693.1	692.2	691.3	690.4	691.3
155°	706.7	707.1	707.4	707.8	708.0	707.5	706.5	705.4	704.4	703.4	704.4
157.5°	718.0	718.4	718.7	719.1	719.3	718.8	717.8	716.8	715.8	714.8	715.8
160°	728.3	728.8	729.3	729.8	730.1	729.6	728.6	727.5	726.5	725.5	726.5
162.5°	737.7	738.4	739.2	739.9	740.3	739.7	738.6	737.5	736.3	735.2	736.3
165°	745.6	746.3	747.1	747.8	748.2	747.7	746.7	745.7	744.7	743.7	744.7
167.5°	752.0	752.8	753.7	754.6	755.0	754.4	753.3	752.2	751.0	749.9	751.0
170°	756.6	757.6	758.6	759.6	760.1	759.5	758.4	757.3	756.1	755.0	756.1
172.5°	760.5	761.3	762.2	763.1	763.5	762.9	761.8	760.7	759.5	758.4	759.5
175°	762.8	763.8	764.9	765.9	766.4	765.8	764.7	763.6	762.4	761.3	762.4
177.5°	764.4	765.3	766.2	767.1	767.5	767.0	766.0	765.0	764.0	763.0	764.0
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1305.3	1298.1	1300.2	1298.1	1292.9	1289.8	1281.5	1271.2	1267.0	1261.9	1258.7
5°	1409.9	1404.7	1403.7	1395.4	1393.3	1380.9	1360.2	1349.8	1337.4	1325.0	1312.6
7.5°	1523.7	1517.5	1496.8	1493.7	1495.8	1480.3	1453.4	1432.7	1406.8	1389.2	1365.4
10°	1617.9	1605.5	1587.9	1589.0	1581.7	1561.0	1534.1	1512.4	1475.1	1452.3	1418.2
12.5°	1674.9	1664.5	1662.5	1652.1	1645.9	1619.0	1586.9	1558.9	1531.0	1499.9	1474.1
15°	1744.2	1730.8	1721.5	1707.0	1702.8	1674.9	1639.7	1607.6	1575.5	1546.5	1491.7
17.5°	1820.8	1806.3	1771.1	1768.0	1743.2	1716.3	1682.1	1634.5	1600.3	1558.9	1518.6
20°	1907.8	1887.1	1841.5	1830.2	1810.5	1766.0	1719.4	1666.6	1611.7	1569.3	1521.7
22.5°	2005.1	1968.9	1935.7	1899.5	1885.0	1830.2	1766.0	1701.8	1635.5	1577.6	1520.6
25°	2131.4	2083.8	2037.2	2001.0	1976.1	1904.7	1818.8	1733.9	1657.3	1581.7	1507.2
27.5°	2230.8	2189.3	2138.6	2091.0	2058.9	1974.0	1875.7	1766.0	1670.7	1578.6	1498.9
30°	2238.0	2225.6	2194.5	2168.6	2133.5	2042.4	1933.7	1809.4	1691.4	1579.6	1482.3
32.5°	2102.4	2127.2	2140.7	2144.8	2137.6	2084.8	1985.4	1848.8	1710.1	1570.3	1467.8
35°	1810.5	1876.7	1958.5	1989.6	2019.6	2047.5	1995.8	1876.7	1716.3	1568.3	1445.1
37.5°	1490.6	1550.7	1686.3	1748.4	1783.6	1894.3	1936.8	1872.6	1728.7	1570.3	1423.3
40°	1202.8	1298.1	1395.4	1479.2	1534.1	1658.3	1789.8	1804.3	1711.1	1550.7	1395.4
42.5°	1012.4	1068.3	1141.8	1219.4	1268.1	1415.1	1593.1	1697.7	1656.2	1518.6	1361.2
45°	862.3	903.7	973.0	998.9	1061.0	1201.8	1390.2	1541.3	1562.0	1467.8	1321.9
47.5°	740.1	775.3	819.8	851.9	901.6	1007.2	1166.6	1333.3	1432.7	1398.5	1267.0
50°	652.1	681.1	718.4	737.0	769.1	864.4	984.4	1150.1	1283.6	1295.0	1195.6
52.5°	578.7	595.2	624.2	644.9	670.8	728.7	837.4	974.1	1124.2	1186.3	1107.6
55°	514.5	527.9	553.8	567.3	580.7	630.4	715.3	839.5	980.3	1062.1	1017.6
57.5°	456.5	467.9	489.6	502.0	509.3	556.9	622.1	719.4	845.7	945.1	920.3
60°	408.9	419.2	431.7	441.0	449.3	488.6	534.1	612.8	725.6	821.9	815.7
62.5°	358.2	367.5	380.9	390.3	397.5	422.3	460.6	520.7	617.0	706.0	723.6
65°	313.7	320.9	330.2	334.4	343.7	362.3	393.4	447.2	525.9	605.6	618.0
67.5°	273.3	275.4	281.6	290.9	292.9	309.5	337.5	377.8	438.9	504.1	523.8
70°	229.8	232.9	238.1	245.3	249.5	259.8	283.6	310.5	363.3	420.3	434.8
72.5°	191.5	195.6	197.7	201.9	203.9	220.5	230.8	257.8	294.0	341.6	357.1
75°	155.3	159.4	160.4	162.5	164.6	171.8	186.3	202.9	232.9	264.0	284.7
77.5°	123.2	122.1	124.2	127.3	126.3	132.5	141.8	156.3	176.0	201.9	215.3
80°	87.0	87.0	90.1	93.2	92.1	98.3	101.4	111.8	128.4	144.9	150.1
82.5°	58.0	58.0	61.1	61.1	63.1	64.2	68.3	73.5	87.0	95.2	98.3
85°	33.1	33.1	34.2	34.2	34.2	36.2	39.3	41.4	45.5	50.7	52.8
87.5°	13.5	14.5	14.5	14.5	14.5	16.6	16.6	18.6	19.7	21.7	21.7
90°	12.8	12.5	12.1	11.9	11.6	11.0	10.3	9.7	9.1	8.2	7.3
92.5°	12.2	12.1	12.0	11.9	11.6	11.0	10.3	9.7	9.1	8.3	7.6
95°	11.9	11.9	11.9	11.9	11.6	11.0	10.3	9.7	9.1	13.9	18.7
97.5°	11.6	11.5	11.4	11.3	11.2	10.9	10.7	10.4	10.2	22.2	34.2
100°	12.9	13.4	13.9	14.2	23.6	42.3	61.1	79.8	98.6	98.1	97.6
102.5°	107.4	117.9	128.5	133.8	133.7	133.4	133.1	132.9	132.6	132.4	132.1
105°	168.6	168.7	168.8	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.6	206.1	206.6	206.9	206.8	206.7	206.6	206.4	206.3	206.1	205.8
110°	242.3	242.2	242.1	242.0	242.2	242.6	242.9	243.3	243.7	243.5	243.2

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	277.1	277.3	277.6	277.7	278.0	278.5	279.0	279.5	280.0	279.9	279.7
115°	312.1	312.9	313.6	314.0	314.3	314.8	315.3	315.8	316.3	316.2	316.0
117.5°	348.0	348.2	348.5	348.6	349.0	349.7	350.5	351.2	352.0	351.5	351.0
120°	382.1	382.8	383.4	383.7	383.8	384.1	384.4	384.6	384.9	384.5	384.1
122.5°	414.2	415.0	415.7	416.1	416.2	416.5	416.7	417.0	417.2	417.1	416.9
125°	445.8	446.1	446.5	446.7	446.9	447.4	447.9	448.4	448.9	448.9	448.9
127.5°	473.6	474.6	475.6	476.1	476.2	476.5	476.8	477.0	477.3	477.4	477.5
130°	502.3	503.0	503.6	503.9	504.1	504.5	504.8	505.2	505.6	505.5	505.3
132.5°	529.5	530.2	530.8	531.1	531.1	531.1	531.1	531.1	531.1	531.5	531.9
135°	554.2	555.0	555.7	556.1	556.2	556.5	556.7	557.0	557.2	557.4	557.7
137.5°	579.4	580.1	580.7	581.0	581.0	581.0	581.0	581.0	581.0	581.2	581.5
140°	601.8	602.6	603.3	603.7	603.6	603.3	603.0	602.8	602.5	602.6	602.8
142.5°	622.7	623.5	624.2	624.6	624.6	624.6	624.6	624.6	624.6	624.4	624.1
145°	643.2	644.0	644.7	645.1	645.0	644.9	644.8	644.6	644.5	644.5	644.5
147.5°	660.4	661.3	662.2	662.6	662.5	662.4	662.3	662.2	662.1	662.0	661.8
150°	677.1	678.1	679.1	679.6	679.5	679.2	679.0	678.7	678.5	678.3	678.0
152.5°	692.2	693.1	694.0	694.4	694.3	694.0	693.7	693.5	693.2	693.0	692.7
155°	705.4	706.5	707.5	708.0	707.8	707.4	707.1	706.7	706.3	706.0	705.8
157.5°	716.8	717.8	718.8	719.3	719.1	718.7	718.4	718.0	717.6	717.6	717.6
160°	727.5	728.6	729.6	730.1	729.8	729.3	728.8	728.3	727.8	727.7	727.5
162.5°	737.5	738.6	739.7	740.3	739.9	739.2	738.4	737.7	736.9	736.8	736.6
165°	745.7	746.7	747.7	748.2	747.8	747.1	746.3	745.6	744.8	744.7	744.6
167.5°	752.2	753.3	754.4	755.0	754.6	753.7	752.8	752.0	751.1	751.0	750.8
170°	757.3	758.4	759.5	760.1	759.6	758.6	757.6	756.6	755.6	755.5	755.3
172.5°	760.7	761.8	762.9	763.5	763.1	762.2	761.3	760.5	759.6	759.3	759.1
175°	763.6	764.7	765.8	766.4	765.9	764.9	763.8	762.8	761.8	761.7	761.6
177.5°	765.0	766.0	767.0	767.5	767.1	766.2	765.3	764.4	763.5	763.4	763.3
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1254.6	1249.4	1243.2	1243.2	1236.0	1232.9	1226.7	1224.6	1219.4	1211.1	1204.9
5°	1299.1	1285.7	1277.4	1270.1	1254.6	1243.2	1231.8	1219.4	1207.0	1192.5	1175.9
7.5°	1342.6	1317.8	1306.4	1293.9	1271.2	1247.4	1224.6	1208.0	1191.5	1168.7	1148.0
10°	1388.1	1357.1	1336.4	1319.8	1284.6	1254.6	1221.5	1197.7	1171.8	1142.8	1115.9
12.5°	1426.4	1386.1	1368.5	1337.4	1297.0	1260.8	1219.4	1183.2	1149.0	1114.9	1081.7
15°	1458.5	1420.2	1376.8	1364.3	1308.4	1256.7	1210.1	1163.5	1121.1	1086.9	1048.6
17.5°	1468.9	1420.2	1398.5	1368.5	1302.2	1248.4	1189.4	1138.7	1098.3	1047.6	1017.6
20°	1472.0	1425.4	1395.4	1367.4	1308.4	1237.0	1179.0	1116.9	1068.3	1017.6	969.9
22.5°	1463.7	1408.8	1379.9	1352.9	1286.7	1225.6	1158.3	1090.0	1033.1	986.5	938.9
25°	1448.2	1384.0	1356.1	1327.1	1263.9	1196.6	1123.1	1057.9	1005.1	949.2	902.7
27.5°	1427.5	1354.0	1321.9	1291.9	1229.8	1166.6	1097.3	1030.0	971.0	912.0	868.5
30°	1401.6	1316.7	1287.7	1248.4	1188.4	1128.3	1065.2	997.9	931.6	875.7	828.1
32.5°	1368.5	1279.4	1241.1	1203.9	1138.7	1083.8	1023.8	960.6	896.4	841.6	791.9
35°	1338.5	1237.0	1194.6	1157.3	1084.8	1026.9	977.2	918.2	861.2	804.3	759.8
37.5°	1298.1	1194.6	1143.8	1105.5	1032.0	973.0	926.5	880.9	820.9	766.0	724.6
40°	1255.6	1141.8	1094.2	1055.9	979.3	915.1	870.6	830.2	781.5	730.8	687.3
42.5°	1217.3	1091.1	1040.3	993.7	916.1	859.2	813.6	782.6	738.1	692.5	653.2
45°	1168.7	1037.2	982.4	933.7	859.2	797.1	753.6	728.7	695.6	651.1	617.0
47.5°	1119.0	979.3	922.3	874.7	794.0	739.1	696.7	672.8	650.1	614.9	580.7
50°	1053.8	918.2	866.4	811.6	731.9	676.0	640.8	617.0	599.4	574.5	545.5
52.5°	982.4	855.0	799.1	751.5	672.8	622.1	581.8	568.3	550.7	532.1	507.2
55°	906.8	786.7	732.9	686.3	613.8	562.1	529.0	514.5	501.0	486.5	470.0
57.5°	831.2	715.3	664.6	623.2	555.9	506.2	479.3	459.6	450.3	442.0	428.6
60°	737.0	638.7	599.4	562.1	495.8	450.3	424.4	409.9	401.6	397.5	391.3
62.5°	654.2	573.5	530.0	493.8	441.0	400.6	375.8	364.4	357.1	355.1	347.8
65°	566.2	496.9	462.7	431.7	386.1	349.9	329.2	315.7	310.5	309.5	309.5
67.5°	483.4	427.5	393.4	371.6	332.3	300.2	280.5	275.4	272.2	268.1	267.1
70°	405.8	361.3	331.2	312.6	277.4	253.6	238.1	229.8	229.8	226.7	224.6
72.5°	337.5	292.9	273.3	257.8	228.8	208.1	196.7	194.6	187.4	186.3	186.3
75°	264.0	230.8	217.4	203.9	182.2	167.7	158.4	153.2	149.1	149.1	150.1
77.5°	198.7	176.0	163.6	153.2	137.7	128.4	121.1	119.0	114.9	114.9	114.9
80°	140.8	128.4	119.0	110.8	99.4	91.1	87.0	82.8	82.8	81.8	82.8
82.5°	91.1	80.7	75.6	74.5	64.2	61.1	55.9	56.9	53.8	52.8	54.9
85°	52.8	47.6	41.4	39.3	35.2	31.1	29.0	30.0	29.0	27.9	29.0
87.5°	20.7	17.6	16.6	16.6	13.5	12.4	11.4	12.4	10.4	10.4	11.4
90°	6.4	5.5	5.1	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	6.8	6.1	5.7	6.3	7.4	8.5	9.7	10.8	9.7	8.5	7.4
95°	23.4	28.2	30.6	30.8	31.2	31.5	31.9	32.3	31.9	31.5	31.2
97.5°	46.1	58.1	64.1	63.7	63.0	62.2	61.5	60.7	61.5	62.2	63.0
100°	97.1	96.6	96.4	96.2	95.8	95.5	95.1	94.7	95.1	95.5	95.8
102.5°	131.9	131.6	131.5	131.2	130.7	130.2	129.7	129.2	129.7	130.2	130.7
105°	168.9	168.9	168.9	168.6	168.1	167.6	167.1	166.6	167.1	167.6	168.1
107.5°	205.6	205.3	205.2	205.2	205.2	205.2	205.2	205.2	205.2	205.2	205.2
110°	243.0	242.7	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	279.6	279.5	279.4	279.2	278.8	278.5	278.1	277.7	278.1	278.5	278.8
115°	315.9	315.8	315.7	315.4	314.8	314.1	313.5	312.9	313.5	314.1	314.8
117.5°	350.5	350.0	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7
120°	383.8	383.4	383.2	383.3	383.4	383.5	383.6	383.7	383.6	383.5	383.4
122.5°	416.8	416.7	416.6	416.3	415.7	415.0	414.4	413.8	414.4	415.0	415.7
125°	448.9	448.9	448.9	448.5	447.6	446.7	445.9	445.0	445.9	446.7	447.6
127.5°	477.6	477.7	477.8	477.5	476.9	476.2	475.6	475.0	475.6	476.2	476.9
130°	505.2	505.1	505.0	504.7	504.1	503.4	502.8	502.2	502.8	503.4	504.1
132.5°	532.2	532.6	532.8	532.4	531.7	530.9	530.2	529.4	530.2	530.9	531.7
135°	557.9	558.2	558.3	557.9	557.2	556.4	555.7	554.9	555.7	556.4	557.2
137.5°	581.7	582.0	582.1	581.7	581.0	580.2	579.5	578.7	579.5	580.2	581.0
140°	602.9	603.0	603.1	603.0	602.7	602.5	602.2	602.0	602.2	602.5	602.7
142.5°	623.9	623.6	623.5	623.4	623.3	623.2	623.0	622.9	623.0	623.2	623.3
145°	644.5	644.5	644.5	644.4	644.1	643.9	643.6	643.4	643.6	643.9	644.1
147.5°	661.7	661.6	661.5	661.5	661.5	661.5	661.5	661.5	661.5	661.5	661.5
150°	677.8	677.5	677.4	677.5	677.8	678.0	678.3	678.5	678.3	678.0	677.8
152.5°	692.5	692.2	692.1	692.4	693.0	693.7	694.3	694.9	694.3	693.7	693.0
155°	705.5	705.2	705.1	705.5	706.2	707.0	707.7	708.5	707.7	707.0	706.2
157.5°	717.6	717.6	717.6	717.8	718.2	718.5	718.9	719.3	718.9	718.5	718.2
160°	727.4	727.3	727.2	727.6	728.3	729.1	729.8	730.6	729.8	729.1	728.3
162.5°	736.5	736.4	736.3	736.7	737.4	738.2	738.9	739.7	738.9	738.2	737.4
165°	744.5	744.4	744.3	744.7	745.4	746.2	746.9	747.7	746.9	746.2	745.4
167.5°	750.7	750.6	750.5	750.9	751.6	752.4	753.1	753.9	753.1	752.4	751.6
170°	755.2	755.1	755.0	755.4	756.3	757.2	758.1	759.0	758.1	757.2	756.3
172.5°	758.8	758.5	758.4	758.8	759.7	760.6	761.5	762.4	761.5	760.6	759.7
175°	761.5	761.4	761.3	761.7	762.4	763.2	763.9	764.7	763.9	763.2	762.4
177.5°	763.2	763.1	763.0	763.4	764.1	764.9	765.6	766.4	765.6	764.9	764.1
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1202.8	1200.8	1195.6	1192.5	1182.1	1169.7	1165.6	1155.2	1159.4	1152.1	1152.1
5°	1170.8	1161.4	1155.2	1145.9	1126.2	1112.8	1098.3	1091.1	1086.9	1081.7	1077.6
7.5°	1129.4	1122.1	1115.9	1098.3	1076.6	1057.9	1040.3	1033.1	1019.6	1010.3	1006.2
10°	1093.1	1082.8	1068.3	1047.6	1024.8	1001.0	985.5	969.9	959.6	954.4	943.0
12.5°	1055.9	1043.4	1027.9	997.9	973.0	958.6	930.6	916.1	910.9	906.8	893.3
15°	1017.6	1004.1	985.5	957.5	935.8	901.6	885.1	873.7	861.2	860.2	849.9
17.5°	983.4	966.8	951.3	917.1	890.2	860.2	850.9	838.5	827.1	814.7	809.5
20°	939.9	924.4	913.0	875.7	845.7	827.1	811.6	801.2	794.0	781.5	779.5
22.5°	900.6	884.0	868.5	840.5	814.7	790.9	772.2	760.8	757.7	752.6	743.2
25°	862.3	845.7	827.1	801.2	774.3	757.7	741.2	733.9	727.7	719.4	712.2
27.5°	830.2	814.7	797.1	765.0	742.2	729.8	712.2	703.9	695.6	691.5	688.4
30°	791.9	774.3	760.8	736.0	711.2	694.6	682.2	674.9	667.7	663.5	661.5
32.5°	754.6	738.1	728.7	701.8	682.2	662.5	653.2	648.0	643.9	639.7	635.6
35°	724.6	708.0	693.6	668.7	649.0	635.6	628.3	620.1	617.0	612.8	612.8
37.5°	687.3	674.9	660.4	636.6	619.0	608.7	602.5	592.1	591.1	589.0	585.9
40°	655.3	642.8	629.4	608.7	593.1	580.7	572.4	567.3	564.2	562.1	560.0
42.5°	621.1	607.6	601.4	577.6	564.2	551.7	547.6	542.4	541.4	537.2	532.1
45°	588.0	576.6	564.2	546.6	535.2	524.8	518.6	514.5	509.3	508.3	505.2
47.5°	559.0	545.5	534.1	517.6	505.2	496.9	491.7	486.5	482.4	479.3	476.2
50°	521.7	511.4	502.0	484.5	474.1	465.8	458.6	454.4	450.3	450.3	450.3
52.5°	485.5	476.2	467.9	455.5	443.0	435.8	427.5	424.4	422.3	419.2	422.3
55°	450.3	441.0	432.7	423.4	408.9	402.7	394.4	391.3	392.3	392.3	395.4
57.5°	413.0	405.8	400.6	389.2	375.8	369.5	364.4	361.3	361.3	365.4	366.4
60°	376.8	369.5	360.2	349.9	341.6	334.4	331.2	332.3	332.3	334.4	339.5
62.5°	336.4	332.3	327.1	312.6	307.4	302.3	298.1	301.2	300.2	305.4	312.6
65°	299.2	295.0	287.8	280.5	274.3	269.1	268.1	269.1	271.2	276.4	284.7
67.5°	257.8	257.8	251.5	245.3	240.2	235.0	236.0	237.1	239.1	245.3	257.8
70°	223.6	219.5	213.2	209.1	205.0	202.9	200.8	205.0	211.2	215.3	224.6
72.5°	186.3	183.2	178.0	173.9	172.9	170.8	169.8	171.8	178.0	185.3	195.6
75°	147.0	148.0	144.9	141.8	141.8	138.7	140.8	140.8	147.0	154.2	162.5
77.5°	113.9	112.8	111.8	109.7	108.7	108.7	108.7	110.8	117.0	121.1	129.4
80°	80.7	81.8	78.7	79.7	78.7	79.7	79.7	83.8	87.0	92.1	98.3
82.5°	53.8	53.8	51.8	52.8	52.8	52.8	53.8	55.9	60.0	64.2	68.3
85°	30.0	31.1	29.0	31.1	31.1	31.1	32.1	33.1	36.2	37.3	41.4
87.5°	11.4	13.5	13.5	11.4	12.4	13.5	14.5	13.5	15.5	17.6	18.6
90°	4.6	5.1	5.5	6.4	7.3	8.2	9.1	9.7	10.3	11.0	11.6
92.5°	6.3	5.7	6.1	6.8	7.6	8.3	9.1	9.7	10.3	11.0	11.6
95°	30.8	30.6	28.2	23.4	18.7	13.9	9.1	9.7	10.3	11.0	11.6
97.5°	63.7	64.1	58.1	46.1	34.2	22.2	10.2	10.4	10.7	10.9	11.2
100°	96.2	96.4	96.6	97.1	97.6	98.1	98.6	79.8	61.1	42.3	23.6
102.5°	131.2	131.5	131.6	131.9	132.1	132.4	132.6	132.9	133.1	133.4	133.7
105°	168.6	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.2	205.2	205.3	205.6	205.8	206.1	206.3	206.4	206.6	206.7	206.8
110°	242.6	242.6	242.7	243.0	243.2	243.5	243.7	243.3	242.9	242.6	242.2

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	279.2	279.4	279.5	279.6	279.7	279.9	280.0	279.5	279.0	278.5	278.0
115°	315.4	315.7	315.8	315.9	316.0	316.2	316.3	315.8	315.3	314.8	314.3
117.5°	349.7	349.7	350.0	350.5	351.0	351.5	352.0	351.2	350.5	349.7	349.0
120°	383.3	383.2	383.4	383.8	384.1	384.5	384.9	384.6	384.4	384.1	383.8
122.5°	416.3	416.6	416.7	416.8	416.9	417.1	417.2	417.0	416.7	416.5	416.2
125°	448.5	448.9	448.9	448.9	448.9	448.9	448.9	448.4	447.9	447.4	446.9
127.5°	477.5	477.8	477.7	477.6	477.5	477.4	477.3	477.0	476.8	476.5	476.2
130°	504.7	505.0	505.1	505.2	505.3	505.5	505.6	505.2	504.8	504.5	504.1
132.5°	532.4	532.8	532.6	532.2	531.9	531.5	531.1	531.1	531.1	531.1	531.1
135°	557.9	558.3	558.2	557.9	557.7	557.4	557.2	557.0	556.7	556.5	556.2
137.5°	581.7	582.1	582.0	581.7	581.5	581.2	581.0	581.0	581.0	581.0	581.0
140°	603.0	603.1	603.0	602.9	602.8	602.6	602.5	602.8	603.0	603.3	603.6
142.5°	623.4	623.5	623.6	623.9	624.1	624.4	624.6	624.6	624.6	624.6	624.6
145°	644.4	644.5	644.5	644.5	644.5	644.5	644.5	644.6	644.8	644.9	645.0
147.5°	661.5	661.5	661.6	661.7	661.8	662.0	662.1	662.2	662.3	662.4	662.5
150°	677.5	677.4	677.5	677.8	678.0	678.3	678.5	678.7	679.0	679.2	679.5
152.5°	692.4	692.1	692.2	692.5	692.7	693.0	693.2	693.5	693.7	694.0	694.3
155°	705.5	705.1	705.2	705.5	705.8	706.0	706.3	706.7	707.1	707.4	707.8
157.5°	717.8	717.6	717.6	717.6	717.6	717.6	717.6	718.0	718.4	718.7	719.1
160°	727.6	727.2	727.3	727.4	727.5	727.7	727.8	728.3	728.8	729.3	729.8
162.5°	736.7	736.3	736.4	736.5	736.6	736.8	736.9	737.7	738.4	739.2	739.9
165°	744.7	744.3	744.4	744.5	744.6	744.7	744.8	745.6	746.3	747.1	747.8
167.5°	750.9	750.5	750.6	750.7	750.8	751.0	751.1	752.0	752.8	753.7	754.6
170°	755.4	755.0	755.1	755.2	755.3	755.5	755.6	756.6	757.6	758.6	759.6
172.5°	758.8	758.4	758.5	758.8	759.1	759.3	759.6	760.5	761.3	762.2	763.1
175°	761.7	761.3	761.4	761.5	761.6	761.7	761.8	762.8	763.8	764.9	765.9
177.5°	763.4	763.0	763.1	763.2	763.3	763.4	763.5	764.4	765.3	766.2	767.1
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1156.3	1149.0	1148.0	1150.1	1145.9	1152.1	1150.1	1152.1	1146.9	1152.1	1149.0
5°	1076.6	1074.5	1070.3	1065.2	1066.2	1067.2	1072.4	1067.2	1071.4	1072.4	1077.6
7.5°	1002.0	997.9	1001.0	998.9	989.6	987.5	989.6	992.7	998.9	1003.1	1006.2
10°	942.0	939.9	935.8	932.7	927.5	924.4	928.5	924.4	932.7	939.9	939.9
12.5°	896.4	888.2	883.0	882.0	870.6	872.6	876.8	879.9	889.2	893.3	893.3
15°	848.8	842.6	840.5	836.4	832.3	836.4	834.3	837.4	841.6	845.7	847.8
17.5°	807.4	806.4	807.4	797.1	800.2	795.0	796.0	801.2	798.1	801.2	807.4
20°	770.2	772.2	769.1	765.0	765.0	758.8	766.0	763.9	765.0	771.2	780.5
22.5°	742.2	741.2	738.1	735.0	730.8	731.9	732.9	730.8	739.1	744.3	745.3
25°	712.2	710.1	709.1	706.0	701.8	706.0	704.9	706.0	708.0	716.3	710.1
27.5°	684.2	680.1	682.2	679.1	678.0	679.1	679.1	680.1	682.2	683.2	684.2
30°	660.4	656.3	655.3	653.2	652.1	653.2	655.3	653.2	661.5	660.4	660.4
32.5°	634.5	631.4	629.4	629.4	628.3	627.3	628.3	629.4	635.6	631.4	635.6
35°	609.7	607.6	607.6	605.6	604.5	604.5	604.5	608.7	606.6	609.7	609.7
37.5°	585.9	585.9	584.9	582.8	581.8	582.8	581.8	583.8	582.8	583.8	584.9
40°	561.1	559.0	557.9	557.9	554.8	551.7	554.8	554.8	555.9	559.0	560.0
42.5°	531.0	532.1	532.1	527.9	527.9	527.9	529.0	530.0	530.0	532.1	532.1
45°	505.2	503.1	503.1	503.1	501.0	502.0	504.1	504.1	504.1	504.1	502.0
47.5°	476.2	476.2	477.2	477.2	480.3	479.3	479.3	478.2	476.2	476.2	477.2
50°	449.3	452.4	453.4	453.4	454.4	455.5	455.5	453.4	452.4	449.3	449.3
52.5°	423.4	425.4	427.5	430.6	432.7	431.7	431.7	429.6	425.4	424.4	423.4
55°	395.4	398.5	402.7	405.8	408.9	409.9	409.9	405.8	401.6	396.5	396.5
57.5°	369.5	372.7	379.9	383.0	387.1	387.1	385.1	382.0	375.8	371.6	368.5
60°	343.7	348.8	354.0	360.2	365.4	366.4	363.3	359.2	352.0	346.8	342.6
62.5°	315.7	320.9	331.2	337.5	341.6	341.6	341.6	336.4	327.1	319.9	313.7
65°	288.8	294.0	303.3	311.6	314.7	317.8	314.7	309.5	302.3	294.0	287.8
67.5°	260.9	267.1	276.4	282.6	286.7	289.8	287.8	283.6	274.3	262.9	258.8
70°	229.8	232.9	246.4	252.6	258.8	260.9	258.8	252.6	243.3	230.8	226.7
72.5°	200.8	203.9	216.3	221.5	226.7	228.8	225.7	221.5	213.2	201.9	196.7
75°	167.7	172.9	179.1	187.4	193.6	195.6	192.5	189.4	179.1	171.8	167.7
77.5°	132.5	137.7	146.0	153.2	159.4	158.4	154.2	155.3	143.9	135.6	132.5
80°	100.4	104.6	110.8	117.0	120.1	120.1	119.0	114.9	110.8	104.6	99.4
82.5°	69.4	74.5	79.7	83.8	83.8	84.9	82.8	81.8	77.6	72.5	71.4
85°	41.4	42.4	46.6	46.6	50.7	48.7	47.6	50.7	46.6	43.5	42.4
87.5°	18.6	17.6	18.6	18.6	17.6	19.7	19.7	18.6	19.7	18.6	18.6
90°	11.9	12.1	12.5	12.8	13.2	13.6	13.2	12.8	12.5	12.1	11.9
92.5°	11.9	12.0	12.1	12.2	12.4	12.5	12.4	12.2	12.1	12.0	11.9
95°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
97.5°	11.3	11.4	11.5	11.6	11.8	11.9	11.8	11.6	11.5	11.4	11.3
100°	14.2	13.9	13.4	12.9	12.4	11.9	12.4	12.9	13.4	13.9	14.2
102.5°	133.8	128.5	117.9	107.4	96.8	86.2	96.8	107.4	117.9	128.5	133.8
105°	168.9	168.8	168.7	168.6	168.4	168.3	168.4	168.6	168.7	168.8	168.9
107.5°	206.9	206.6	206.1	205.6	205.1	204.6	205.1	205.6	206.1	206.6	206.9
110°	242.0	242.1	242.2	242.3	242.5	242.6	242.5	242.3	242.2	242.1	242.0

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	277.7	277.6	277.3	277.1	276.8	276.6	276.8	277.1	277.3	277.6	277.7
115°	314.0	313.6	312.9	312.1	311.4	310.6	311.4	312.1	312.9	313.6	314.0
117.5°	348.6	348.5	348.2	348.0	347.7	347.5	347.7	348.0	348.2	348.5	348.6
120°	383.7	383.4	382.8	382.1	381.5	380.9	381.5	382.1	382.8	383.4	383.7
122.5°	416.1	415.7	415.0	414.2	413.5	412.7	413.5	414.2	415.0	415.7	416.1
125°	446.7	446.5	446.1	445.8	445.4	445.0	445.4	445.8	446.1	446.5	446.7
127.5°	476.1	475.6	474.6	473.6	472.6	471.6	472.6	473.6	474.6	475.6	476.1
130°	503.9	503.6	503.0	502.3	501.7	501.1	501.7	502.3	503.0	503.6	503.9
132.5°	531.1	530.8	530.2	529.5	528.9	528.3	528.9	529.5	530.2	530.8	531.1
135°	556.1	555.7	555.0	554.2	553.5	552.7	553.5	554.2	555.0	555.7	556.1
137.5°	581.0	580.7	580.1	579.4	578.8	578.2	578.8	579.4	580.1	580.7	581.0
140°	603.7	603.3	602.6	601.8	601.1	600.3	601.1	601.8	602.6	603.3	603.7
142.5°	624.6	624.2	623.5	622.7	622.0	621.2	622.0	622.7	623.5	624.2	624.6
145°	645.1	644.7	644.0	643.2	642.5	641.7	642.5	643.2	644.0	644.7	645.1
147.5°	662.6	662.2	661.3	660.4	659.6	658.7	659.6	660.4	661.3	662.2	662.6
150°	679.6	679.1	678.1	677.1	676.1	675.1	676.1	677.1	678.1	679.1	679.6
152.5°	694.4	694.0	693.1	692.2	691.3	690.4	691.3	692.2	693.1	694.0	694.4
155°	708.0	707.5	706.5	705.4	704.4	703.4	704.4	705.4	706.5	707.5	708.0
157.5°	719.3	718.8	717.8	716.8	715.8	714.8	715.8	716.8	717.8	718.8	719.3
160°	730.1	729.6	728.6	727.5	726.5	725.5	726.5	727.5	728.6	729.6	730.1
162.5°	740.3	739.7	738.6	737.5	736.3	735.2	736.3	737.5	738.6	739.7	740.3
165°	748.2	747.7	746.7	745.7	744.7	743.7	744.7	745.7	746.7	747.7	748.2
167.5°	755.0	754.4	753.3	752.2	751.0	749.9	751.0	752.2	753.3	754.4	755.0
170°	760.1	759.5	758.4	757.3	756.1	755.0	756.1	757.3	758.4	759.5	760.1
172.5°	763.5	762.9	761.8	760.7	759.5	758.4	759.5	760.7	761.8	762.9	763.5
175°	766.4	765.8	764.7	763.6	762.4	761.3	762.4	763.6	764.7	765.8	766.4
177.5°	767.5	767.0	766.0	765.0	764.0	763.0	764.0	765.0	766.0	767.0	767.5
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4	1219.4
2.5°	1158.3	1152.1	1159.4	1150.1	1152.1	1163.5	1162.5	1172.8	1179.0	1178.0	1183.2
5°	1081.7	1081.7	1084.8	1083.8	1094.2	1103.5	1115.9	1126.2	1137.6	1143.8	1151.1
7.5°	1006.2	1016.5	1018.6	1023.8	1036.2	1051.7	1064.1	1079.7	1096.2	1107.6	1115.9
10°	944.1	952.3	960.6	964.8	978.2	998.9	1016.5	1041.4	1062.1	1074.5	1085.9
12.5°	889.2	898.5	902.7	921.3	930.6	944.1	968.9	995.8	1018.6	1032.0	1041.4
15°	849.9	855.0	864.4	875.7	885.1	901.6	922.3	952.3	974.1	985.5	1017.6
17.5°	816.7	822.9	828.1	833.3	847.8	865.4	885.1	910.9	938.9	958.6	975.1
20°	782.6	785.7	791.9	800.2	810.5	827.1	844.7	871.6	896.4	912.0	933.7
22.5°	742.2	751.5	757.7	763.9	775.3	794.0	810.5	830.2	861.2	878.8	901.6
25°	718.4	722.5	726.7	733.9	742.2	758.8	777.4	798.1	822.9	841.6	861.2
27.5°	687.3	693.6	698.7	708.0	713.2	726.7	744.3	765.0	795.0	810.5	827.1
30°	661.5	667.7	671.8	676.0	683.2	697.7	714.3	730.8	758.8	778.4	795.0
32.5°	635.6	641.8	647.0	650.1	657.3	666.6	680.1	700.8	724.6	738.1	759.8
35°	612.8	612.8	619.0	623.2	629.4	637.7	650.1	665.6	690.4	708.0	727.7
37.5°	586.9	588.0	593.1	596.2	602.5	610.7	623.2	637.7	658.4	671.8	691.5
40°	560.0	563.1	565.2	570.4	577.6	580.7	593.1	609.7	630.4	642.8	659.4
42.5°	533.1	535.2	540.3	544.5	550.7	555.9	564.2	579.7	595.2	613.8	627.3
45°	503.1	508.3	511.4	518.6	521.7	526.9	535.2	547.6	566.2	577.6	593.1
47.5°	477.2	479.3	481.3	490.7	496.9	500.0	508.3	515.5	535.2	545.5	560.0
50°	449.3	449.3	452.4	456.5	463.7	470.0	477.2	485.5	501.0	511.4	525.9
52.5°	423.4	420.3	422.3	424.4	431.7	437.9	445.1	456.5	471.0	477.2	489.6
55°	395.4	390.3	393.4	396.5	398.5	406.8	415.1	422.3	433.7	443.0	454.4
57.5°	365.4	364.4	362.3	363.3	368.5	373.7	379.9	389.2	402.7	409.9	416.1
60°	338.5	332.3	330.2	332.3	335.4	338.5	346.8	355.1	366.4	373.7	380.9
62.5°	310.5	304.3	300.2	297.1	300.2	307.4	312.6	318.8	328.1	336.4	342.6
65°	283.6	274.3	270.2	268.1	267.1	272.2	276.4	284.7	292.9	296.1	303.3
67.5°	253.6	245.3	240.2	237.1	237.1	237.1	241.2	249.5	257.8	258.8	266.0
70°	223.6	214.3	209.1	205.0	202.9	205.0	210.1	211.2	218.4	220.5	224.6
72.5°	191.5	183.2	177.0	171.8	172.9	174.9	174.9	177.0	181.2	186.3	186.3
75°	161.5	150.1	147.0	142.9	140.8	140.8	140.8	144.9	148.0	152.2	151.1
77.5°	127.3	121.1	114.9	112.8	109.7	108.7	110.8	110.8	112.8	115.9	117.0
80°	98.3	91.1	87.0	84.9	80.7	79.7	80.7	80.7	83.8	82.8	83.8
82.5°	68.3	63.1	60.0	56.9	54.9	55.9	54.9	54.9	55.9	54.9	54.9
85°	39.3	38.3	36.2	35.2	34.2	32.1	34.2	33.1	32.1	31.1	33.1
87.5°	18.6	17.6	17.6	15.5	15.5	14.5	15.5	15.5	14.5	14.5	14.5
90°	11.6	11.0	10.3	9.7	9.1	8.2	7.3	6.4	5.5	5.1	4.6
92.5°	11.6	11.0	10.3	9.7	9.1	8.3	7.6	6.8	6.1	5.7	6.3
95°	11.6	11.0	10.3	9.7	9.1	13.9	18.7	23.4	28.2	30.6	30.8
97.5°	11.2	10.9	10.7	10.4	10.2	22.2	34.2	46.1	58.1	64.1	63.7
100°	23.6	42.3	61.1	79.8	98.6	98.1	97.6	97.1	96.6	96.4	96.2
102.5°	133.7	133.4	133.1	132.9	132.6	132.4	132.1	131.9	131.6	131.5	131.2
105°	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.6
107.5°	206.8	206.7	206.6	206.4	206.3	206.1	205.8	205.6	205.3	205.2	205.2
110°	242.2	242.6	242.9	243.3	243.7	243.5	243.2	243.0	242.7	242.6	242.6

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	278.0	278.5	279.0	279.5	280.0	279.9	279.7	279.6	279.5	279.4	279.2
115°	314.3	314.8	315.3	315.8	316.3	316.2	316.0	315.9	315.8	315.7	315.4
117.5°	349.0	349.7	350.5	351.2	352.0	351.5	351.0	350.5	350.0	349.7	349.7
120°	383.8	384.1	384.4	384.6	384.9	384.5	384.1	383.8	383.4	383.2	383.3
122.5°	416.2	416.5	416.7	417.0	417.2	417.1	416.9	416.8	416.7	416.6	416.3
125°	446.9	447.4	447.9	448.4	448.9	448.9	448.9	448.9	448.9	448.9	448.5
127.5°	476.2	476.5	476.8	477.0	477.3	477.4	477.5	477.6	477.7	477.8	477.5
130°	504.1	504.5	504.8	505.2	505.6	505.5	505.3	505.2	505.1	505.0	504.7
132.5°	531.1	531.1	531.1	531.1	531.1	531.5	531.9	532.2	532.6	532.8	532.4
135°	556.2	556.5	556.7	557.0	557.2	557.4	557.7	557.9	558.2	558.3	557.9
137.5°	581.0	581.0	581.0	581.0	581.0	581.2	581.5	581.7	582.0	582.1	581.7
140°	603.6	603.3	603.0	602.8	602.5	602.6	602.8	602.9	603.0	603.1	603.0
142.5°	624.6	624.6	624.6	624.6	624.6	624.4	624.1	623.9	623.6	623.5	623.4
145°	645.0	644.9	644.8	644.6	644.5	644.5	644.5	644.5	644.5	644.5	644.4
147.5°	662.5	662.4	662.3	662.2	662.1	662.0	661.8	661.7	661.6	661.5	661.5
150°	679.5	679.2	679.0	678.7	678.5	678.3	678.0	677.8	677.5	677.4	677.5
152.5°	694.3	694.0	693.7	693.5	693.2	693.0	692.7	692.5	692.2	692.1	692.4
155°	707.8	707.4	707.1	706.7	706.3	706.0	705.8	705.5	705.2	705.1	705.5
157.5°	719.1	718.7	718.4	718.0	717.6	717.6	717.6	717.6	717.6	717.6	717.8
160°	729.8	729.3	728.8	728.3	727.8	727.7	727.5	727.4	727.3	727.2	727.6
162.5°	739.9	739.2	738.4	737.7	736.9	736.8	736.6	736.5	736.4	736.3	736.7
165°	747.8	747.1	746.3	745.6	744.8	744.7	744.6	744.5	744.4	744.3	744.7
167.5°	754.6	753.7	752.8	752.0	751.1	751.0	750.8	750.7	750.6	750.5	750.9
170°	759.6	758.6	757.6	756.6	755.6	755.5	755.3	755.2	755.1	755.0	755.4
172.5°	763.1	762.2	761.3	760.5	759.6	759.3	759.1	758.8	758.5	758.4	758.8
175°	765.9	764.9	763.8	762.8	761.8	761.7	761.6	761.5	761.4	761.3	761.7
177.5°	767.1	766.2	765.3	764.4	763.5	763.4	763.3	763.2	763.1	763.0	763.4
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1219.4	1219.4	1219.4	1219.4
2.5°	1190.4	1200.8	1208.0	1221.5
5°	1163.5	1182.1	1199.7	1218.4
7.5°	1136.6	1158.3	1186.3	1210.1
10°	1106.6	1134.5	1167.7	1199.7
12.5°	1076.6	1109.7	1145.9	1188.4
15°	1040.3	1082.8	1125.2	1170.8
17.5°	1008.2	1051.7	1097.3	1154.2
20°	972.0	1019.6	1069.3	1127.3
22.5°	939.9	992.7	1044.5	1105.5
25°	903.7	955.4	1012.4	1077.6
27.5°	873.7	921.3	977.2	1047.6
30°	837.4	889.2	945.1	1015.5
32.5°	803.3	853.0	912.0	981.3
35°	768.1	818.8	871.6	937.8
37.5°	735.0	778.4	831.2	894.4
40°	697.7	745.3	792.9	842.6
42.5°	663.5	707.0	751.5	790.9
45°	625.2	662.5	704.9	737.0
47.5°	590.0	623.2	656.3	681.1
50°	554.8	580.7	605.6	627.3
52.5°	513.4	542.4	555.9	569.3
55°	476.2	492.7	505.2	518.6
57.5°	439.9	447.2	453.4	465.8
60°	392.3	400.6	407.9	417.2
62.5°	350.9	355.1	357.1	366.4
65°	311.6	310.5	315.7	320.9
67.5°	269.1	268.1	273.3	275.4
70°	227.7	226.7	227.7	232.9
72.5°	188.4	188.4	189.4	191.5
75°	152.2	152.2	153.2	155.3
77.5°	114.9	117.0	115.9	120.1
80°	83.8	81.8	83.8	85.9
82.5°	54.9	56.9	56.9	54.9
85°	31.1	31.1	31.1	31.1
87.5°	13.5	13.5	14.5	15.5
90°	3.6	2.6	1.6	0.6
92.5°	7.4	8.5	9.7	10.8
95°	31.2	31.5	31.9	32.3
97.5°	63.0	62.2	61.5	60.7
100°	95.8	95.5	95.1	94.7
102.5°	130.7	130.2	129.7	129.2
105°	168.1	167.6	167.1	166.6
107.5°	205.2	205.2	205.2	205.2
110°	242.6	242.6	242.6	242.6

TEST NUMBER: P1027024

CATALOG NUMBER: S125DIP-B850D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	278.8	278.5	278.1	277.7
115°	314.8	314.1	313.5	312.9
117.5°	349.7	349.7	349.7	349.7
120°	383.4	383.5	383.6	383.7
122.5°	415.7	415.0	414.4	413.8
125°	447.6	446.7	445.9	445.0
127.5°	476.9	476.2	475.6	475.0
130°	504.1	503.4	502.8	502.2
132.5°	531.7	530.9	530.2	529.4
135°	557.2	556.4	555.7	554.9
137.5°	581.0	580.2	579.5	578.7
140°	602.7	602.5	602.2	602.0
142.5°	623.3	623.2	623.0	622.9
145°	644.1	643.9	643.6	643.4
147.5°	661.5	661.5	661.5	661.5
150°	677.8	678.0	678.3	678.5
152.5°	693.0	693.7	694.3	694.9
155°	706.2	707.0	707.7	708.5
157.5°	718.2	718.5	718.9	719.3
160°	728.3	729.1	729.8	730.6
162.5°	737.4	738.2	738.9	739.7
165°	745.4	746.2	746.9	747.7
167.5°	751.6	752.4	753.1	753.9
170°	756.3	757.2	758.1	759.0
172.5°	759.7	760.6	761.5	762.4
175°	762.4	763.2	763.9	764.7
177.5°	764.1	764.9	765.6	766.4
180°	764.7	764.7	764.7	764.7

(END OF REPORT)