

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027058

Luminaire Tested: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027058
REPORT IS A COMBINATION OF REPORTS P1004929 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8012.1 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	44	42
3	82	73	66	60	76	68	62	57	58	53	50	49	46	43	41	38	36
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	34	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	49	41	36	42	36	32	36	31	28	30	27	24
7	59	47	39	34	55	44	37	32	38	33	28	33	28	25	27	24	22
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10061	11349	10061	8723
10°	10005	12754	9972	7541
15°	9897	13493	9829	6566
20°	9766	14566	9678	5935
25°	9594	16487	9486	5386
30°	9420	17525	9279	4994
35°	9195	14412	9066	4628
40°	8795	9787	8721	4300
45°	8270	7036	8259	3976
50°	7732	5410	7769	3677
55°	7126	4400	7112	3389
60°	6561	3605	6529	3008
65°	5905	3005	5941	2422
70°	5360	2411	5338	2017
75°	4529	1827	4529	1658
80°	3671	1115	3629	1115
85°	2584	587	2510	664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14334 cd/sqm

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	1.9
10°-20°	441.9	5.5
20°-30°	700.6	8.7
30°-40°	846.6	10.6
40°-50°	753.8	9.4
50°-60°	578.0	7.2
60°-70°	375.4	4.7
70°-80°	182.2	2.3
80°-90°	44.8	0.6
90°-100°	43.5	0.5
100°-110°	289.3	3.6
110°-120°	521.0	6.5
120°-130°	668.8	8.3
130°-140°	719.3	9.0
140°-150°	675.1	8.4
150°-160°	546.1	6.8
160°-170°	353.2	4.4
170°-180°	121.8	1.5
0°-30°	1293.2	16.1
0°-40°	2139.8	26.7
0°-60°	3471.6	43.3
0°-90°	4073.9	50.8
90°-120°	853.9	10.7
90°-150°	2917.1	36.4
90°-180°	3938.0	49.2
0°-180°	8012.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1568	1801	1568	1385	1568	149
15°	1502	2164	1492	1053	1502	424
25°	1373	2591	1358	846	1373	633
35°	1196	2150	1179	690	1196	745
45°	936	961	934	543	936	722
55°	661	528	659	406	661	592
65°	410	299	413	241	410	410
75°	200	139	200	126	200	214
85°	45	30	44	34	45	51
90°	1	23	1	23	1	6
95°	54	20	54	20	54	66
105°	279	282	279	282	279	296
115°	525	521	525	521	525	520
125°	746	746	746	746	746	666
135°	930	927	930	927	930	717
145°	1079	1076	1079	1076	1079	675
155°	1188	1179	1188	1179	1188	547
165°	1254	1247	1254	1247	1254	354
175°	1282	1276	1282	1276	1282	122
180°	1282	1282	1282	1282	1282	

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1573.0	1585.9	1589.8	1600.1	1611.7	1614.3	1620.8	1629.8	1634.9	1633.7	1633.7
5°	1567.8	1589.8	1605.3	1623.3	1645.3	1654.3	1662.0	1681.4	1696.9	1705.9	1721.4
7.5°	1558.8	1591.1	1616.9	1644.0	1677.5	1693.0	1709.8	1736.9	1765.3	1783.3	1800.1
10°	1544.6	1585.9	1622.0	1662.0	1707.2	1730.4	1751.1	1792.4	1827.2	1850.4	1889.2
12.5°	1524.0	1575.6	1625.9	1678.8	1735.6	1760.1	1788.5	1833.7	1882.7	1916.3	1948.5
15°	1502.0	1564.0	1618.2	1681.4	1749.8	1787.2	1823.3	1871.1	1915.0	1952.4	1989.8
17.5°	1476.2	1542.0	1609.1	1681.4	1758.8	1796.3	1827.2	1884.0	1930.5	1967.9	2001.4
20°	1445.3	1518.8	1594.9	1675.0	1753.7	1788.5	1818.2	1880.1	1921.4	1961.4	2009.2
22.5°	1411.7	1491.7	1573.0	1651.7	1729.1	1766.6	1801.4	1855.6	1900.8	1955.0	2016.9
25°	1373.0	1460.7	1543.3	1622.0	1695.6	1730.4	1761.4	1820.8	1884.0	1952.4	2022.1
27.5°	1334.3	1419.5	1499.5	1571.7	1651.7	1684.0	1715.0	1789.8	1864.6	1936.9	2032.4
30°	1291.7	1378.2	1447.8	1514.9	1592.4	1625.9	1664.6	1749.8	1835.0	1933.0	2049.2
32.5°	1244.0	1322.7	1387.2	1456.9	1526.6	1567.8	1616.9	1709.8	1807.9	1925.3	2073.7
35°	1196.2	1259.4	1318.8	1384.6	1468.5	1512.4	1560.1	1658.2	1780.8	1921.4	2094.3
37.5°	1135.6	1196.2	1242.7	1309.8	1396.2	1447.8	1495.6	1609.1	1748.5	1912.4	2093.0
40°	1073.6	1125.2	1169.1	1238.8	1333.0	1380.7	1432.4	1556.2	1715.0	1886.6	2062.1
42.5°	1006.5	1050.4	1098.1	1165.2	1256.9	1303.3	1362.7	1507.2	1668.5	1850.4	1982.1
45°	935.5	978.1	1018.1	1087.8	1179.4	1229.8	1294.3	1442.7	1611.7	1774.3	1853.0
47.5°	865.9	903.3	945.9	1006.5	1099.4	1154.9	1220.7	1379.4	1535.6	1672.4	1678.8
50°	798.8	828.4	864.6	926.5	1023.3	1076.2	1144.6	1293.0	1445.3	1539.5	1476.2
52.5°	729.1	756.2	793.6	847.8	938.1	1000.1	1059.4	1207.8	1335.6	1398.8	1282.7
55°	660.7	683.9	722.6	783.3	862.0	909.7	970.4	1108.5	1220.7	1222.0	1095.6
57.5°	593.6	614.2	646.5	700.7	774.2	829.7	885.2	1005.2	1081.4	1059.4	918.8
60°	534.2	547.1	576.8	629.7	698.1	738.1	797.5	898.1	948.5	908.4	757.5
62.5°	472.3	485.2	508.4	551.0	615.5	658.1	695.5	778.1	813.0	752.3	628.4
65°	410.4	425.8	442.6	476.2	536.8	565.2	598.8	659.4	692.9	622.0	514.9
67.5°	356.2	363.9	380.7	415.5	458.1	483.9	507.1	548.4	554.9	498.1	410.4
70°	305.8	308.4	323.9	344.5	376.8	392.3	411.6	436.2	436.2	389.7	320.0
72.5°	249.0	252.9	264.5	286.5	305.8	313.6	320.0	335.5	332.9	290.3	242.6
75°	200.0	202.6	211.6	222.0	229.7	243.9	249.0	246.5	245.2	209.0	181.9
77.5°	154.8	156.1	162.6	171.6	172.9	178.1	174.2	174.2	162.6	141.9	127.8
80°	113.6	114.8	117.4	120.0	120.0	120.0	120.0	113.6	105.8	92.9	89.0
82.5°	76.1	76.1	77.4	80.0	78.7	76.1	73.6	67.1	61.9	58.1	55.5
85°	45.2	45.2	46.5	45.2	40.0	38.7	36.1	34.8	33.6	32.3	32.3
87.5°	21.9	20.6	18.1	15.5	15.5	15.5	15.5	15.5	15.5	14.2	14.2
90°	1.0	2.7	4.4	6.1	7.8	8.6	9.3	10.8	12.3	13.7	15.2
92.5°	18.1	16.2	14.3	12.4	10.5	9.5	10.1	11.4	12.7	13.9	15.2
95°	54.2	53.6	52.9	52.3	51.6	51.3	47.3	39.3	31.2	23.2	15.2
97.5°	101.7	103.0	104.2	105.5	106.8	107.4	97.4	77.3	57.2	37.2	17.1
100°	158.7	159.3	160.0	160.6	161.3	161.6	162.0	162.9	163.7	164.6	165.4
102.5°	216.7	217.5	218.4	219.2	220.1	220.5	220.7	221.1	221.6	222.0	222.4
105°	279.4	280.2	281.1	281.9	282.8	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.0	344.0	344.0	344.0	344.0	344.0	344.2	344.6	345.1	345.5	345.9
110°	406.7	406.7	406.7	406.7	406.7	406.7	406.9	407.4	407.8	408.3	408.7

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	465.7	466.3	466.9	467.6	468.2	468.5	468.6	468.8	469.1	469.3	469.5
115°	524.6	525.6	526.7	527.7	528.8	529.3	529.4	529.6	529.9	530.1	530.3
117.5°	586.4	586.4	586.4	586.4	586.4	586.4	586.8	587.7	588.5	589.4	590.2
120°	643.4	643.2	643.0	642.7	642.5	642.4	642.7	643.4	644.0	644.7	645.3
122.5°	693.8	694.8	695.9	696.9	698.0	698.5	698.6	698.8	699.1	699.3	699.5
125°	746.0	747.5	749.0	750.5	752.0	752.7	752.7	752.7	752.7	752.7	752.7
127.5°	796.4	797.4	798.5	799.5	800.6	801.1	801.0	800.8	800.6	800.4	800.2
130°	842.0	843.1	844.1	845.2	846.3	846.8	846.9	847.1	847.3	847.5	847.7
132.5°	887.6	888.9	890.1	891.4	892.7	893.3	893.0	892.4	891.7	891.1	890.5
135°	930.4	931.7	932.9	934.2	935.5	936.1	935.9	935.5	935.0	934.6	934.2
137.5°	970.3	971.6	972.8	974.1	975.4	976.0	975.8	975.4	974.9	974.5	974.1
140°	1009.3	1009.7	1010.1	1010.6	1011.0	1011.2	1011.1	1010.9	1010.6	1010.4	1010.2
142.5°	1044.4	1044.6	1044.8	1045.1	1045.3	1045.4	1045.6	1046.0	1046.5	1046.9	1047.3
145°	1078.6	1079.0	1079.4	1079.9	1080.3	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5
147.5°	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.2	1109.4	1109.6	1109.8	1110.0
150°	1137.6	1137.2	1136.8	1136.3	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6
152.5°	1165.1	1164.1	1163.0	1162.0	1160.9	1160.4	1160.6	1161.0	1161.5	1161.9	1162.3
155°	1187.9	1186.6	1185.4	1184.1	1182.8	1182.2	1182.4	1182.8	1183.3	1183.7	1184.1
157.5°	1206.0	1205.4	1204.7	1204.1	1203.4	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1
160°	1225.0	1223.7	1222.5	1221.2	1219.9	1219.3	1219.4	1219.6	1219.8	1220.0	1220.2
162.5°	1240.2	1238.9	1237.7	1236.4	1235.1	1234.5	1234.6	1234.8	1235.1	1235.3	1235.5
165°	1253.5	1252.2	1251.0	1249.7	1248.4	1247.8	1247.9	1248.1	1248.4	1248.6	1248.8
167.5°	1264.0	1262.7	1261.5	1260.2	1258.9	1258.3	1258.4	1258.6	1258.8	1259.0	1259.2
170°	1272.5	1271.0	1269.6	1268.1	1266.6	1265.9	1266.0	1266.2	1266.4	1266.6	1266.8
172.5°	1278.2	1276.7	1275.3	1273.8	1272.3	1271.6	1271.8	1272.2	1272.7	1273.1	1273.5
175°	1282.0	1280.7	1279.5	1278.2	1276.9	1276.3	1276.4	1276.6	1276.9	1277.1	1277.3
177.5°	1284.9	1283.6	1282.4	1281.1	1279.8	1279.2	1279.3	1279.5	1279.7	1279.9	1280.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1640.1	1649.1	1656.9	1653.0	1668.5	1667.2	1669.8	1675.0	1676.2	1673.7	1668.5
5°	1729.1	1742.1	1764.0	1775.6	1773.0	1783.3	1788.5	1796.3	1804.0	1801.4	1801.4
7.5°	1828.5	1846.6	1868.5	1898.2	1902.1	1911.1	1926.6	1926.6	1935.6	1931.7	1930.5
10°	1915.0	1936.9	1971.7	1995.0	2005.3	2010.5	2025.9	2031.1	2041.4	2042.7	2042.7
12.5°	1985.9	2024.7	2047.9	2071.1	2076.3	2084.0	2095.6	2103.4	2107.2	2107.2	2103.4
15°	2023.4	2054.3	2081.4	2105.9	2120.1	2126.6	2138.2	2147.2	2152.4	2164.0	2166.6
17.5°	2038.8	2076.3	2120.1	2155.0	2179.5	2186.0	2209.2	2216.9	2227.2	2232.4	2238.9
20°	2060.8	2115.0	2167.9	2210.5	2233.7	2250.5	2275.0	2311.1	2321.4	2321.4	2317.6
22.5°	2080.1	2149.8	2222.1	2290.5	2309.8	2343.4	2388.5	2427.3	2442.7	2449.2	2444.0
25°	2103.4	2198.9	2293.1	2378.2	2431.1	2455.6	2516.3	2562.8	2580.8	2591.1	2593.7
27.5°	2143.4	2263.4	2383.4	2491.8	2546.0	2574.4	2637.6	2677.6	2699.5	2708.6	2702.1
30°	2188.5	2335.6	2475.0	2571.8	2607.9	2642.8	2684.1	2699.5	2694.4	2694.4	2713.7
32.5°	2235.0	2387.3	2511.1	2574.4	2587.3	2582.1	2565.3	2518.9	2491.8	2491.8	2508.6
35°	2260.8	2392.4	2455.6	2435.0	2384.7	2355.0	2263.4	2211.8	2153.7	2149.8	2169.2
37.5°	2246.6	2303.4	2277.6	2142.1	2073.7	2016.9	1873.7	1816.9	1774.3	1715.0	1806.6
40°	2147.2	2127.9	1993.7	1798.8	1722.7	1642.7	1529.1	1472.4	1413.0	1404.0	1425.9
42.5°	1979.5	1864.6	1668.5	1480.1	1402.7	1345.9	1259.4	1204.0	1166.5	1151.0	1176.9
45°	1770.4	1589.8	1393.6	1244.0	1158.8	1129.1	1050.4	1001.4	973.0	961.4	979.4
47.5°	1514.9	1333.0	1147.2	1020.7	970.4	940.7	887.8	845.2	820.7	813.0	820.7
50°	1286.5	1099.4	943.3	862.0	816.8	792.3	748.4	721.3	702.0	696.8	709.7
52.5°	1089.1	918.8	800.1	727.8	698.1	677.5	646.5	623.3	611.7	606.5	615.5
55°	912.3	774.2	678.8	616.8	594.9	582.0	554.9	542.0	529.1	527.8	536.8
57.5°	756.2	660.7	572.9	529.1	522.6	503.3	480.0	468.4	462.0	460.7	464.5
60°	629.7	544.6	491.6	452.9	443.9	428.4	415.5	407.8	400.0	397.4	400.0
62.5°	523.9	456.8	414.2	388.4	375.5	371.6	357.4	348.4	347.1	347.1	349.7
65°	432.3	375.5	348.4	327.8	318.7	314.9	304.5	298.1	299.4	299.4	300.7
67.5°	352.3	311.0	286.5	276.1	268.4	267.1	256.8	254.2	251.6	251.6	254.2
70°	280.0	254.2	236.1	231.0	229.7	220.7	216.8	215.5	211.6	212.9	212.9
72.5°	219.4	202.6	192.3	184.5	185.8	180.7	175.5	175.5	172.9	176.8	176.8
75°	162.6	154.8	147.1	144.5	147.1	144.5	140.7	139.4	140.7	139.4	139.4
77.5°	120.0	116.1	113.6	112.3	112.3	107.1	104.5	107.1	101.9	104.5	104.5
80°	83.9	78.7	77.4	74.8	76.1	72.3	73.6	71.0	71.0	71.0	71.0
82.5°	52.9	51.6	51.6	51.6	50.3	50.3	50.3	50.3	50.3	50.3	49.0
85°	32.3	31.0	31.0	31.0	29.7	29.7	29.7	29.7	29.7	29.7	29.7
87.5°	12.9	14.2	14.2	15.5	14.2	12.9	12.9	12.9	14.2	14.2	12.9
90°	16.3	17.3	18.4	19.5	20.0	20.3	20.9	21.6	22.2	22.8	22.2
92.5°	16.3	17.3	18.4	19.5	20.0	20.1	20.3	20.5	20.7	20.9	20.7
95°	16.3	17.3	18.4	19.5	20.0	20.0	20.0	20.0	20.0	20.0	20.0
97.5°	17.5	17.9	18.4	18.8	19.0	19.1	19.3	19.6	19.8	20.0	19.8
100°	133.9	102.5	71.0	39.5	23.8	23.4	22.5	21.7	20.8	20.0	20.8
102.5°	222.8	223.2	223.7	224.1	224.3	215.4	197.7	180.0	162.2	144.5	162.2
105°	283.2	283.2	283.2	283.2	283.2	283.1	282.9	282.7	282.5	282.3	282.5
107.5°	346.1	346.3	346.6	346.8	346.9	346.5	345.6	344.8	343.9	343.1	343.9
110°	408.1	407.4	406.8	406.1	405.8	405.9	406.1	406.3	406.5	406.7	406.5

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	468.7	467.8	467.0	466.1	465.7	465.5	465.1	464.6	464.2	463.8	464.2
115°	529.5	528.6	527.8	526.9	526.5	525.9	524.6	523.3	522.1	520.8	522.1
117.5°	588.9	587.7	586.4	585.1	584.5	584.3	583.9	583.4	583.0	582.6	583.0
120°	644.9	644.5	644.0	643.6	643.4	642.9	641.8	640.7	639.7	638.6	639.7
122.5°	699.1	698.7	698.2	697.8	697.6	697.0	695.7	694.4	693.2	691.9	693.2
125°	751.9	751.0	750.2	749.3	748.9	748.6	747.9	747.3	746.6	746.0	746.6
127.5°	799.8	799.4	798.9	798.5	798.3	797.5	795.8	794.1	792.4	790.7	792.4
130°	847.1	846.5	845.8	845.2	844.9	844.4	843.3	842.2	841.2	840.1	841.2
132.5°	890.5	890.5	890.5	890.5	890.5	890.0	888.9	887.8	886.8	885.7	886.8
135°	933.8	933.4	932.9	932.5	932.3	931.7	930.4	929.1	927.9	926.6	927.9
137.5°	974.1	974.1	974.1	974.1	974.1	973.6	972.5	971.5	970.4	969.4	970.4
140°	1010.6	1011.0	1011.5	1011.9	1012.1	1011.5	1010.2	1008.9	1007.7	1006.4	1007.7
142.5°	1047.3	1047.3	1047.3	1047.3	1047.3	1046.7	1045.4	1044.1	1042.9	1041.6	1042.9
145°	1080.7	1080.9	1081.2	1081.4	1081.5	1080.9	1079.6	1078.3	1077.1	1075.8	1077.1
147.5°	1110.2	1110.4	1110.7	1110.9	1111.0	1110.3	1108.8	1107.3	1105.8	1104.3	1105.8
150°	1138.0	1138.4	1138.9	1139.3	1139.5	1138.7	1137.0	1135.3	1133.6	1131.9	1133.6
152.5°	1162.7	1163.1	1163.6	1164.0	1164.2	1163.5	1162.0	1160.5	1159.0	1157.5	1159.0
155°	1184.7	1185.4	1186.0	1186.7	1187.0	1186.2	1184.5	1182.8	1181.1	1179.4	1181.1
157.5°	1203.7	1204.4	1205.0	1205.7	1206.0	1205.2	1203.5	1201.8	1200.1	1198.4	1200.1
160°	1221.1	1221.9	1222.8	1223.7	1224.1	1223.2	1221.5	1219.8	1218.1	1216.4	1218.1
162.5°	1236.8	1238.0	1239.3	1240.6	1241.2	1240.2	1238.3	1236.4	1234.5	1232.6	1234.5
165°	1250.1	1251.3	1252.6	1253.9	1254.5	1253.7	1252.0	1250.3	1248.6	1246.9	1248.6
167.5°	1260.7	1262.2	1263.7	1265.2	1265.9	1264.9	1263.0	1261.1	1259.2	1257.3	1259.2
170°	1268.5	1270.2	1271.9	1273.6	1274.4	1273.5	1271.6	1269.7	1267.8	1265.9	1267.8
172.5°	1275.0	1276.4	1277.9	1279.4	1280.1	1279.2	1277.3	1275.4	1273.5	1271.6	1273.5
175°	1279.0	1280.7	1282.4	1284.1	1284.9	1283.9	1282.0	1280.1	1278.2	1276.3	1278.2
177.5°	1281.6	1283.1	1284.6	1286.1	1286.8	1286.0	1284.3	1282.6	1280.9	1279.2	1280.9
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1675.0	1665.9	1669.8	1665.9	1662.0	1658.2	1649.1	1636.2	1625.9	1618.2	1616.9
5°	1804.0	1792.4	1784.6	1780.8	1773.0	1762.7	1745.9	1726.6	1703.3	1694.3	1676.2
7.5°	1922.7	1918.8	1900.8	1898.2	1893.0	1873.7	1845.3	1819.5	1789.8	1765.3	1742.1
10°	2035.0	2025.9	2013.0	1995.0	1992.4	1967.9	1940.8	1904.6	1865.9	1842.7	1801.4
12.5°	2104.7	2094.3	2080.1	2068.5	2062.1	2046.6	2009.2	1973.0	1938.2	1895.6	1859.5
15°	2155.0	2142.1	2116.3	2107.2	2099.5	2078.8	2051.8	2014.3	1967.9	1938.2	1886.6
17.5°	2223.4	2207.9	2182.1	2165.3	2151.1	2118.9	2080.1	2029.8	1985.9	1952.4	1905.9
20°	2302.1	2278.9	2245.3	2223.4	2202.7	2165.3	2111.1	2051.8	1988.5	1947.2	1899.5
22.5°	2432.4	2388.5	2335.6	2304.7	2276.3	2211.8	2147.2	2073.7	2002.7	1940.8	1882.7
25°	2558.9	2515.0	2449.2	2406.6	2362.7	2287.9	2202.7	2100.8	2010.5	1938.2	1862.1
27.5°	2676.3	2631.1	2570.5	2518.9	2476.3	2364.0	2251.8	2136.9	2022.1	1922.7	1845.3
30°	2703.4	2684.1	2637.6	2592.4	2553.7	2450.5	2320.2	2174.3	2036.3	1908.5	1822.1
32.5°	2539.5	2587.3	2598.9	2592.4	2567.9	2494.4	2374.4	2220.8	2056.9	1902.1	1783.3
35°	2198.9	2285.3	2374.4	2422.1	2445.3	2455.6	2384.7	2244.0	2071.1	1891.7	1757.5
37.5°	1823.3	1907.2	2047.9	2118.9	2197.6	2300.8	2329.2	2238.9	2064.7	1884.0	1716.2
40°	1498.2	1605.3	1721.4	1785.9	1854.3	2040.1	2180.8	2170.5	2044.0	1855.6	1684.0
42.5°	1219.4	1286.5	1388.5	1459.5	1543.3	1751.1	1939.5	2032.4	1982.1	1820.8	1642.7
45°	1016.8	1068.5	1140.7	1213.0	1264.6	1453.0	1676.2	1828.5	1876.3	1758.8	1579.5
47.5°	856.8	895.5	958.8	1003.9	1059.4	1207.8	1401.4	1615.6	1716.2	1671.1	1512.4
50°	734.2	765.2	815.5	843.9	893.0	1020.7	1167.8	1392.4	1544.6	1549.8	1423.3
52.5°	627.1	658.1	700.7	725.2	754.9	841.3	989.7	1179.4	1354.9	1419.5	1321.4
55°	545.8	563.9	598.8	618.1	645.2	729.1	823.3	984.6	1167.8	1273.6	1211.7
57.5°	471.0	490.4	512.3	527.8	547.1	614.2	699.4	820.7	1002.6	1117.5	1096.8
60°	410.4	422.0	442.6	454.2	472.3	516.2	575.5	696.8	841.3	949.7	961.4
62.5°	353.6	363.9	378.1	388.4	400.0	434.9	478.7	565.2	691.7	809.1	824.6
65°	304.5	313.6	321.3	330.3	339.4	361.3	398.7	465.8	563.9	673.6	707.1
67.5°	260.7	263.2	274.9	276.1	281.3	298.1	325.2	379.4	450.4	538.1	582.0
70°	218.1	223.2	225.8	229.7	234.9	246.5	268.4	296.8	349.7	420.7	462.0
72.5°	176.8	178.1	181.9	184.5	189.7	198.7	209.0	231.0	264.5	316.2	353.6
75°	140.7	141.9	144.5	145.8	149.7	152.3	157.4	172.9	196.1	227.1	254.2
77.5°	105.8	108.4	111.0	111.0	112.3	114.8	117.4	122.6	134.2	154.8	178.1
80°	72.3	73.6	73.6	74.8	73.6	77.4	81.3	87.7	92.9	99.4	111.0
82.5°	50.3	50.3	50.3	51.6	51.6	52.9	52.9	54.2	55.5	59.4	64.5
85°	31.0	31.0	32.3	29.7	31.0	32.3	32.3	31.0	32.3	33.6	34.8
87.5°	12.9	12.9	14.2	14.2	14.2	14.2	12.9	14.2	12.9	14.2	14.2
90°	21.6	20.9	20.3	20.0	19.5	18.4	17.3	16.3	15.2	13.7	12.3
92.5°	20.5	20.3	20.1	20.0	19.5	18.4	17.3	16.3	15.2	13.9	12.7
95°	20.0	20.0	20.0	20.0	19.5	18.4	17.3	16.3	15.2	23.2	31.2
97.5°	19.6	19.3	19.1	19.0	18.8	18.4	17.9	17.5	17.1	37.2	57.2
100°	21.7	22.5	23.4	23.8	39.5	71.0	102.5	133.9	165.4	164.6	163.7
102.5°	180.0	197.7	215.4	224.3	224.1	223.7	223.2	222.8	222.4	222.0	221.6
105°	282.7	282.9	283.1	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.8	345.6	346.5	346.9	346.8	346.6	346.3	346.1	345.9	345.5	345.1
110°	406.3	406.1	405.9	405.8	406.1	406.8	407.4	408.1	408.7	408.3	407.8

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	464.6	465.1	465.5	465.7	466.1	467.0	467.8	468.7	469.5	469.3	469.1
115°	523.3	524.6	525.9	526.5	526.9	527.8	528.6	529.5	530.3	530.1	529.9
117.5°	583.4	583.9	584.3	584.5	585.1	586.4	587.7	588.9	590.2	589.4	588.5
120°	640.7	641.8	642.9	643.4	643.6	644.0	644.5	644.9	645.3	644.7	644.0
122.5°	694.4	695.7	697.0	697.6	697.8	698.2	698.7	699.1	699.5	699.3	699.1
125°	747.3	747.9	748.6	748.9	749.3	750.2	751.0	751.9	752.7	752.7	752.7
127.5°	794.1	795.8	797.5	798.3	798.5	798.9	799.4	799.8	800.2	800.4	800.6
130°	842.2	843.3	844.4	844.9	845.2	845.8	846.5	847.1	847.7	847.5	847.3
132.5°	887.8	888.9	890.0	890.5	890.5	890.5	890.5	890.5	890.5	891.1	891.7
135°	929.1	930.4	931.7	932.3	932.5	932.9	933.4	933.8	934.2	934.6	935.0
137.5°	971.5	972.5	973.6	974.1	974.1	974.1	974.1	974.1	974.1	974.5	974.9
140°	1008.9	1010.2	1011.5	1012.1	1011.9	1011.5	1011.0	1010.6	1010.2	1010.4	1010.6
142.5°	1044.1	1045.4	1046.7	1047.3	1047.3	1047.3	1047.3	1047.3	1047.3	1046.9	1046.5
145°	1078.3	1079.6	1080.9	1081.5	1081.4	1081.2	1080.9	1080.7	1080.5	1080.5	1080.5
147.5°	1107.3	1108.8	1110.3	1111.0	1110.9	1110.7	1110.4	1110.2	1110.0	1109.8	1109.6
150°	1135.3	1137.0	1138.7	1139.5	1139.3	1138.9	1138.4	1138.0	1137.6	1137.2	1136.8
152.5°	1160.5	1162.0	1163.5	1164.2	1164.0	1163.6	1163.1	1162.7	1162.3	1161.9	1161.5
155°	1182.8	1184.5	1186.2	1187.0	1186.7	1186.0	1185.4	1184.7	1184.1	1183.7	1183.3
157.5°	1201.8	1203.5	1205.2	1206.0	1205.7	1205.0	1204.4	1203.7	1203.1	1203.1	1203.1
160°	1219.8	1221.5	1223.2	1224.1	1223.7	1222.8	1221.9	1221.1	1220.2	1220.0	1219.8
162.5°	1236.4	1238.3	1240.2	1241.2	1240.6	1239.3	1238.0	1236.8	1235.5	1235.3	1235.1
165°	1250.3	1252.0	1253.7	1254.5	1253.9	1252.6	1251.3	1250.1	1248.8	1248.6	1248.4
167.5°	1261.1	1263.0	1264.9	1265.9	1265.2	1263.7	1262.2	1260.7	1259.2	1259.0	1258.8
170°	1269.7	1271.6	1273.5	1274.4	1273.6	1271.9	1270.2	1268.5	1266.8	1266.6	1266.4
172.5°	1275.4	1277.3	1279.2	1280.1	1279.4	1277.9	1276.4	1275.0	1273.5	1273.1	1272.7
175°	1280.1	1282.0	1283.9	1284.9	1284.1	1282.4	1280.7	1279.0	1277.3	1277.1	1276.9
177.5°	1282.6	1284.3	1286.0	1286.8	1286.1	1284.6	1283.1	1281.6	1280.1	1279.9	1279.7
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1613.0	1605.3	1600.1	1598.8	1591.1	1584.6	1576.9	1575.6	1571.7	1561.4	1554.9
5°	1663.3	1645.3	1641.4	1629.8	1610.4	1596.2	1578.2	1567.8	1556.2	1536.9	1521.4
7.5°	1715.0	1690.4	1672.4	1655.6	1628.5	1602.7	1576.9	1556.2	1535.6	1507.2	1484.0
10°	1765.3	1727.9	1705.9	1681.4	1644.0	1605.3	1569.1	1539.5	1505.9	1472.4	1438.8
12.5°	1811.7	1764.0	1731.7	1696.9	1650.4	1602.7	1556.2	1514.9	1480.1	1434.9	1397.5
15°	1840.1	1787.2	1755.0	1721.4	1651.7	1598.8	1544.6	1491.7	1445.3	1397.5	1362.7
17.5°	1856.9	1797.5	1761.4	1730.4	1659.5	1587.2	1517.5	1460.7	1410.4	1353.6	1307.2
20°	1849.2	1791.1	1757.5	1727.9	1645.3	1573.0	1498.2	1432.4	1369.1	1311.1	1262.0
22.5°	1832.4	1771.7	1734.3	1707.2	1633.7	1548.5	1465.9	1394.9	1329.1	1271.1	1215.6
25°	1796.3	1736.9	1704.6	1671.1	1598.8	1517.5	1433.6	1357.5	1287.8	1225.9	1163.9
27.5°	1764.0	1691.7	1658.2	1628.5	1552.4	1480.1	1397.5	1313.6	1242.7	1178.1	1116.2
30°	1726.6	1645.3	1609.1	1569.1	1500.7	1432.4	1349.8	1272.3	1198.8	1130.4	1071.0
32.5°	1686.6	1592.4	1551.1	1505.9	1436.2	1371.7	1302.0	1225.9	1152.3	1085.2	1023.3
35°	1634.9	1534.3	1486.6	1444.0	1371.7	1307.2	1242.7	1179.4	1105.9	1034.9	975.5
37.5°	1585.9	1474.9	1424.6	1375.6	1299.4	1237.5	1184.6	1125.2	1054.3	985.9	929.1
40°	1530.4	1402.7	1351.1	1305.9	1227.2	1158.8	1111.0	1064.6	1002.6	936.8	874.9
42.5°	1480.1	1335.6	1281.4	1234.9	1152.3	1087.8	1042.7	1003.9	949.7	889.1	825.9
45°	1410.4	1263.3	1207.8	1158.8	1074.9	1014.3	967.8	934.3	891.7	834.9	778.1
47.5°	1345.9	1193.6	1133.0	1073.6	997.5	935.5	893.0	867.2	838.8	788.4	730.4
50°	1267.2	1113.6	1051.7	1002.6	916.2	863.3	820.7	802.6	776.8	729.1	682.6
52.5°	1182.0	1036.2	978.1	918.8	838.8	787.1	749.7	729.1	708.4	673.6	629.7
55°	1082.7	949.7	895.5	842.6	762.6	714.9	681.3	659.4	647.8	615.5	583.3
57.5°	987.2	862.0	811.7	762.6	692.9	638.8	616.8	597.5	580.7	557.5	530.4
60°	890.4	776.8	722.6	678.8	618.1	569.1	551.0	531.6	518.7	500.7	481.3
62.5°	779.4	682.6	641.3	600.0	548.4	509.7	489.1	473.6	456.8	445.2	428.4
65°	662.0	593.6	553.6	522.6	473.6	438.7	423.3	412.9	398.7	387.1	374.2
67.5°	552.3	498.1	481.3	447.8	410.4	379.4	367.8	354.9	343.2	336.8	325.2
70°	446.5	407.8	391.0	382.0	340.7	320.0	309.7	304.5	290.3	283.9	276.1
72.5°	345.8	331.6	320.0	308.4	281.3	268.4	256.8	251.6	241.3	236.1	233.6
75°	255.5	246.5	240.0	238.7	227.1	214.2	202.6	200.0	192.3	187.1	184.5
77.5°	179.4	176.8	175.5	176.8	169.0	161.3	158.7	156.1	147.1	145.8	145.8
80°	117.4	123.9	123.9	122.6	120.0	118.7	114.8	112.3	107.1	105.8	107.1
82.5°	72.3	76.1	77.4	80.0	78.7	77.4	74.8	73.6	74.8	72.3	73.6
85°	36.1	38.7	43.9	43.9	45.2	45.2	45.2	43.9	41.3	42.6	41.3
87.5°	14.2	15.5	15.5	15.5	14.2	18.1	19.4	19.4	19.4	16.8	16.8
90°	10.8	9.3	8.6	7.8	6.1	4.4	2.7	1.0	2.7	4.4	6.1
92.5°	11.4	10.1	9.5	10.5	12.4	14.3	16.2	18.1	16.2	14.3	12.4
95°	39.3	47.3	51.3	51.6	52.3	52.9	53.6	54.2	53.6	52.9	52.3
97.5°	77.3	97.4	107.4	106.8	105.5	104.2	103.0	101.7	103.0	104.2	105.5
100°	162.9	162.0	161.6	161.3	160.6	160.0	159.3	158.7	159.3	160.0	160.6
102.5°	221.1	220.7	220.5	220.1	219.2	218.4	217.5	216.7	217.5	218.4	219.2
105°	283.2	283.2	283.2	282.8	281.9	281.1	280.2	279.4	280.2	281.1	281.9
107.5°	344.6	344.2	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0	344.0
110°	407.4	406.9	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	468.8	468.6	468.5	468.2	467.6	466.9	466.3	465.7	466.3	466.9	467.6
115°	529.6	529.4	529.3	528.8	527.7	526.7	525.6	524.6	525.6	526.7	527.7
117.5°	587.7	586.8	586.4	586.4	586.4	586.4	586.4	586.4	586.4	586.4	586.4
120°	643.4	642.7	642.4	642.5	642.7	643.0	643.2	643.4	643.2	643.0	642.7
122.5°	698.8	698.6	698.5	698.0	696.9	695.9	694.8	693.8	694.8	695.9	696.9
125°	752.7	752.7	752.7	752.0	750.5	749.0	747.5	746.0	747.5	749.0	750.5
127.5°	800.8	801.0	801.1	800.6	799.5	798.5	797.4	796.4	797.4	798.5	799.5
130°	847.1	846.9	846.8	846.3	845.2	844.1	843.1	842.0	843.1	844.1	845.2
132.5°	892.4	893.0	893.3	892.7	891.4	890.1	888.9	887.6	888.9	890.1	891.4
135°	935.5	935.9	936.1	935.5	934.2	932.9	931.7	930.4	931.7	932.9	934.2
137.5°	975.4	975.8	976.0	975.4	974.1	972.8	971.6	970.3	971.6	972.8	974.1
140°	1010.9	1011.1	1011.2	1011.0	1010.6	1010.1	1009.7	1009.3	1009.7	1010.1	1010.6
142.5°	1046.0	1045.6	1045.4	1045.3	1045.1	1044.8	1044.6	1044.4	1044.6	1044.8	1045.1
145°	1080.5	1080.5	1080.5	1080.3	1079.9	1079.4	1079.0	1078.6	1079.0	1079.4	1079.9
147.5°	1109.4	1109.2	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1	1109.1
150°	1136.3	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6	1137.2	1136.8	1136.3
152.5°	1161.0	1160.6	1160.4	1160.9	1162.0	1163.0	1164.1	1165.1	1164.1	1163.0	1162.0
155°	1182.8	1182.4	1182.2	1182.8	1184.1	1185.4	1186.6	1187.9	1186.6	1185.4	1184.1
157.5°	1203.1	1203.1	1203.1	1203.4	1204.1	1204.7	1205.4	1206.0	1205.4	1204.7	1204.1
160°	1219.6	1219.4	1219.3	1219.9	1221.2	1222.5	1223.7	1225.0	1223.7	1222.5	1221.2
162.5°	1234.8	1234.6	1234.5	1235.1	1236.4	1237.7	1238.9	1240.2	1238.9	1237.7	1236.4
165°	1248.1	1247.9	1247.8	1248.4	1249.7	1251.0	1252.2	1253.5	1252.2	1251.0	1249.7
167.5°	1258.6	1258.4	1258.3	1258.9	1260.2	1261.5	1262.7	1264.0	1262.7	1261.5	1260.2
170°	1266.2	1266.0	1265.9	1266.6	1268.1	1269.6	1271.0	1272.5	1271.0	1269.6	1268.1
172.5°	1272.2	1271.8	1271.6	1272.3	1273.8	1275.3	1276.7	1278.2	1276.7	1275.3	1273.8
175°	1276.6	1276.4	1276.3	1276.9	1278.2	1279.5	1280.7	1282.0	1280.7	1279.5	1278.2
177.5°	1279.5	1279.3	1279.2	1279.8	1281.1	1282.4	1283.6	1284.9	1283.6	1282.4	1281.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1551.1	1545.9	1542.0	1538.2	1521.4	1503.3	1500.7	1496.9	1489.1	1498.2	1494.3
5°	1511.1	1499.5	1493.0	1476.2	1455.6	1440.1	1427.2	1411.7	1405.3	1400.1	1398.8
7.5°	1462.0	1451.7	1440.1	1423.3	1397.5	1371.7	1352.3	1336.9	1324.0	1317.5	1317.5
10°	1414.3	1401.4	1385.9	1357.5	1333.0	1300.7	1280.1	1264.6	1246.5	1236.2	1227.2
12.5°	1365.3	1351.1	1336.9	1300.7	1272.3	1238.8	1209.1	1189.8	1180.7	1169.1	1153.6
15°	1316.2	1294.3	1280.1	1244.0	1207.8	1174.3	1154.9	1134.3	1113.6	1102.0	1096.8
17.5°	1264.6	1249.1	1225.9	1187.2	1147.2	1117.5	1089.1	1069.7	1045.2	1033.6	1022.0
20°	1218.1	1194.9	1171.7	1133.0	1094.3	1054.3	1025.9	1002.6	987.2	978.1	967.8
22.5°	1162.7	1140.7	1121.4	1080.1	1037.5	1000.1	969.1	954.9	939.4	925.2	914.9
25°	1114.9	1093.0	1073.6	1028.5	982.0	947.2	923.9	905.9	889.1	882.6	872.3
27.5°	1064.6	1043.9	1018.1	973.0	931.7	902.0	877.5	860.7	847.8	834.9	827.2
30°	1016.8	993.6	970.4	921.4	887.8	858.1	834.9	814.2	803.9	797.5	784.6
32.5°	970.4	940.7	921.4	876.2	843.9	815.5	796.2	778.1	765.2	753.6	743.3
35°	920.1	887.8	868.4	831.0	797.5	769.1	752.3	739.4	723.9	713.6	708.4
37.5°	872.3	845.2	825.9	787.1	753.6	730.4	712.3	695.5	689.1	674.9	672.3
40°	820.7	797.5	779.4	742.0	711.0	692.9	673.6	658.1	646.5	640.0	631.0
42.5°	774.2	754.9	735.5	700.7	671.0	649.1	634.9	620.7	610.4	600.0	593.6
45°	731.7	711.0	692.9	659.4	629.7	610.4	596.2	579.4	576.8	562.6	556.2
47.5°	686.5	668.4	652.9	618.1	591.0	571.7	554.9	543.3	531.6	526.5	517.5
50°	642.6	624.6	606.5	575.5	551.0	531.6	514.9	502.0	495.5	487.8	480.0
52.5°	594.9	580.7	566.5	534.2	509.7	492.9	478.7	462.0	455.5	449.1	443.9
55°	554.9	534.2	518.7	491.6	469.7	451.6	436.2	423.3	416.8	411.6	405.2
57.5°	500.7	487.8	474.9	450.4	429.7	411.6	396.2	385.8	378.1	374.2	375.5
60°	454.2	440.0	432.3	406.5	385.8	371.6	357.4	347.1	339.4	335.5	334.2
62.5°	405.2	394.9	380.7	362.6	342.0	329.1	318.7	311.0	298.1	296.8	292.9
65°	357.4	349.7	336.8	320.0	303.2	291.6	280.0	269.7	264.5	258.1	254.2
67.5°	311.0	303.2	291.6	277.4	265.8	254.2	243.9	233.6	224.5	219.4	216.8
70°	265.8	259.4	251.6	234.9	220.7	211.6	203.9	197.4	188.4	185.8	184.5
72.5°	222.0	215.5	211.6	197.4	184.5	176.8	169.0	162.6	158.7	157.4	153.6
75°	181.9	175.5	170.3	157.4	149.7	144.5	136.8	134.2	130.3	129.0	127.8
77.5°	141.9	135.5	134.2	125.2	116.1	113.6	111.0	105.8	105.8	105.8	103.2
80°	101.9	100.7	99.4	90.3	86.5	83.9	82.6	78.7	76.1	73.6	72.3
82.5°	68.4	67.1	65.8	61.9	58.1	56.8	55.5	52.9	52.9	54.2	51.6
85°	41.3	38.7	37.4	36.1	33.6	33.6	34.8	33.6	33.6	33.6	32.3
87.5°	15.5	15.5	15.5	15.5	16.8	14.2	15.5	15.5	14.2	14.2	12.9
90°	7.8	8.6	9.3	10.8	12.3	13.7	15.2	16.3	17.3	18.4	19.5
92.5°	10.5	9.5	10.1	11.4	12.7	13.9	15.2	16.3	17.3	18.4	19.5
95°	51.6	51.3	47.3	39.3	31.2	23.2	15.2	16.3	17.3	18.4	19.5
97.5°	106.8	107.4	97.4	77.3	57.2	37.2	17.1	17.5	17.9	18.4	18.8
100°	161.3	161.6	162.0	162.9	163.7	164.6	165.4	133.9	102.5	71.0	39.5
102.5°	220.1	220.5	220.7	221.1	221.6	222.0	222.4	222.8	223.2	223.7	224.1
105°	282.8	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2
107.5°	344.0	344.0	344.2	344.6	345.1	345.5	345.9	346.1	346.3	346.6	346.8
110°	406.7	406.7	406.9	407.4	407.8	408.3	408.7	408.1	407.4	406.8	406.1

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	468.2	468.5	468.6	468.8	469.1	469.3	469.5	468.7	467.8	467.0	466.1
115°	528.8	529.3	529.4	529.6	529.9	530.1	530.3	529.5	528.6	527.8	526.9
117.5°	586.4	586.4	586.8	587.7	588.5	589.4	590.2	588.9	587.7	586.4	585.1
120°	642.5	642.4	642.7	643.4	644.0	644.7	645.3	644.9	644.5	644.0	643.6
122.5°	698.0	698.5	698.6	698.8	699.1	699.3	699.5	699.1	698.7	698.2	697.8
125°	752.0	752.7	752.7	752.7	752.7	752.7	752.7	751.9	751.0	750.2	749.3
127.5°	800.6	801.1	801.0	800.8	800.6	800.4	800.2	799.8	799.4	798.9	798.5
130°	846.3	846.8	846.9	847.1	847.3	847.5	847.7	847.1	846.5	845.8	845.2
132.5°	892.7	893.3	893.0	892.4	891.7	891.1	890.5	890.5	890.5	890.5	890.5
135°	935.5	936.1	935.9	935.5	935.0	934.6	934.2	933.8	933.4	932.9	932.5
137.5°	975.4	976.0	975.8	975.4	974.9	974.5	974.1	974.1	974.1	974.1	974.1
140°	1011.0	1011.2	1011.1	1010.9	1010.6	1010.4	1010.2	1010.6	1011.0	1011.5	1011.9
142.5°	1045.3	1045.4	1045.6	1046.0	1046.5	1046.9	1047.3	1047.3	1047.3	1047.3	1047.3
145°	1080.3	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.7	1080.9	1081.2	1081.4
147.5°	1109.1	1109.1	1109.2	1109.4	1109.6	1109.8	1110.0	1110.2	1110.4	1110.7	1110.9
150°	1135.9	1135.7	1135.9	1136.3	1136.8	1137.2	1137.6	1138.0	1138.4	1138.9	1139.3
152.5°	1160.9	1160.4	1160.6	1161.0	1161.5	1161.9	1162.3	1162.7	1163.1	1163.6	1164.0
155°	1182.8	1182.2	1182.4	1182.8	1183.3	1183.7	1184.1	1184.7	1185.4	1186.0	1186.7
157.5°	1203.4	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1	1203.7	1204.4	1205.0	1205.7
160°	1219.9	1219.3	1219.4	1219.6	1219.8	1220.0	1220.2	1221.1	1221.9	1222.8	1223.7
162.5°	1235.1	1234.5	1234.6	1234.8	1235.1	1235.3	1235.5	1236.8	1238.0	1239.3	1240.6
165°	1248.4	1247.8	1247.9	1248.1	1248.4	1248.6	1248.8	1250.1	1251.3	1252.6	1253.9
167.5°	1258.9	1258.3	1258.4	1258.6	1258.8	1259.0	1259.2	1260.7	1262.2	1263.7	1265.2
170°	1266.6	1265.9	1266.0	1266.2	1266.4	1266.6	1266.8	1268.5	1270.2	1271.9	1273.6
172.5°	1272.3	1271.6	1271.8	1272.2	1272.7	1273.1	1273.5	1275.0	1276.4	1277.9	1279.4
175°	1276.9	1276.3	1276.4	1276.6	1276.9	1277.1	1277.3	1279.0	1280.7	1282.4	1284.1
177.5°	1279.8	1279.2	1279.3	1279.5	1279.7	1279.9	1280.1	1281.6	1283.1	1284.6	1286.1
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1487.8	1490.4	1484.0	1481.4	1476.2	1482.7	1484.0	1482.7	1494.3	1489.1	1491.7
5°	1401.4	1396.2	1392.4	1383.3	1383.3	1384.6	1388.5	1382.0	1385.9	1394.9	1393.6
7.5°	1305.9	1303.3	1304.6	1294.3	1286.5	1289.1	1286.5	1298.2	1304.6	1302.0	1307.2
10°	1219.4	1224.6	1213.0	1207.8	1202.7	1207.8	1206.5	1209.1	1216.9	1222.0	1231.1
12.5°	1149.8	1148.5	1142.0	1136.9	1127.8	1130.4	1138.1	1135.6	1136.9	1148.5	1147.2
15°	1083.9	1076.2	1071.0	1059.4	1062.0	1053.0	1060.7	1069.7	1073.6	1083.9	1090.4
17.5°	1018.1	1016.8	1010.4	1009.1	994.9	991.0	998.8	1001.4	1005.2	1010.4	1019.4
20°	962.6	961.4	952.3	949.7	938.1	945.9	943.3	948.5	951.0	961.4	965.2
22.5°	912.3	905.9	903.3	899.4	895.5	894.3	899.4	898.1	907.2	911.0	912.3
25°	865.9	860.7	859.4	853.0	850.4	846.5	850.4	854.3	864.6	868.4	873.6
27.5°	823.3	819.4	816.8	811.7	807.8	807.8	810.4	815.5	819.4	822.0	824.6
30°	784.6	782.0	774.2	771.7	767.8	767.8	767.8	770.4	776.8	784.6	788.4
32.5°	744.6	739.4	734.2	734.2	730.4	730.4	731.7	734.2	740.7	742.0	748.4
35°	705.9	700.7	696.8	694.2	695.5	690.4	692.9	696.8	704.6	707.1	711.0
37.5°	668.4	667.1	659.4	655.5	658.1	658.1	656.8	659.4	664.6	669.7	672.3
40°	627.1	624.6	624.6	620.7	622.0	616.8	620.7	623.3	625.8	631.0	634.9
42.5°	591.0	588.4	583.3	584.6	580.7	580.7	583.3	584.6	588.4	594.9	597.5
45°	552.3	552.3	549.7	545.8	547.1	543.3	545.8	547.1	552.3	558.7	556.2
47.5°	514.9	513.6	513.6	508.4	511.0	507.1	511.0	512.3	514.9	518.7	517.5
50°	478.7	474.9	476.2	474.9	473.6	473.6	476.2	476.2	478.7	478.7	482.6
52.5°	441.3	441.3	438.7	440.0	442.6	440.0	443.9	440.0	442.6	443.9	446.5
55°	407.8	405.2	406.5	405.2	410.4	406.5	410.4	407.8	410.4	409.1	411.6
57.5°	371.6	367.8	369.1	367.8	371.6	370.3	374.2	370.3	371.6	372.9	376.8
60°	330.3	330.3	330.3	327.8	331.6	331.6	330.3	330.3	335.5	338.1	336.8
62.5°	291.6	290.3	286.5	285.2	286.5	283.9	289.1	287.8	290.3	292.9	295.5
65°	249.0	246.5	245.2	242.6	242.6	241.3	242.6	247.8	249.0	250.3	256.8
67.5°	214.2	212.9	211.6	207.8	207.8	210.3	210.3	210.3	218.1	214.2	219.4
70°	183.2	180.7	178.1	176.8	176.8	178.1	179.4	180.7	179.4	184.5	185.8
72.5°	153.6	154.8	152.3	152.3	152.3	151.0	151.0	153.6	154.8	153.6	154.8
75°	127.8	127.8	126.5	127.8	127.8	126.5	126.5	129.0	129.0	127.8	131.6
77.5°	103.2	101.9	99.4	96.8	98.1	96.8	98.1	96.8	100.7	104.5	101.9
80°	72.3	71.0	71.0	71.0	72.3	71.0	73.6	71.0	72.3	72.3	73.6
82.5°	51.6	52.9	52.9	51.6	52.9	51.6	52.9	52.9	52.9	51.6	52.9
85°	33.6	33.6	33.6	33.6	32.3	33.6	33.6	33.6	34.8	33.6	34.8
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	15.5	14.2	15.5
90°	20.0	20.3	20.9	21.6	22.2	22.8	22.2	21.6	20.9	20.3	20.0
92.5°	20.0	20.1	20.3	20.5	20.7	20.9	20.7	20.5	20.3	20.1	20.0
95°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
97.5°	19.0	19.1	19.3	19.6	19.8	20.0	19.8	19.6	19.3	19.1	19.0
100°	23.8	23.4	22.5	21.7	20.8	20.0	20.8	21.7	22.5	23.4	23.8
102.5°	224.3	215.4	197.7	180.0	162.2	144.5	162.2	180.0	197.7	215.4	224.3
105°	283.2	283.1	282.9	282.7	282.5	282.3	282.5	282.7	282.9	283.1	283.2
107.5°	346.9	346.5	345.6	344.8	343.9	343.1	343.9	344.8	345.6	346.5	346.9
110°	405.8	405.9	406.1	406.3	406.5	406.7	406.5	406.3	406.1	405.9	405.8

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	465.7	465.5	465.1	464.6	464.2	463.8	464.2	464.6	465.1	465.5	465.7
115°	526.5	525.9	524.6	523.3	522.1	520.8	522.1	523.3	524.6	525.9	526.5
117.5°	584.5	584.3	583.9	583.4	583.0	582.6	583.0	583.4	583.9	584.3	584.5
120°	643.4	642.9	641.8	640.7	639.7	638.6	639.7	640.7	641.8	642.9	643.4
122.5°	697.6	697.0	695.7	694.4	693.2	691.9	693.2	694.4	695.7	697.0	697.6
125°	748.9	748.6	747.9	747.3	746.6	746.0	746.6	747.3	747.9	748.6	748.9
127.5°	798.3	797.5	795.8	794.1	792.4	790.7	792.4	794.1	795.8	797.5	798.3
130°	844.9	844.4	843.3	842.2	841.2	840.1	841.2	842.2	843.3	844.4	844.9
132.5°	890.5	890.0	888.9	887.8	886.8	885.7	886.8	887.8	888.9	890.0	890.5
135°	932.3	931.7	930.4	929.1	927.9	926.6	927.9	929.1	930.4	931.7	932.3
137.5°	974.1	973.6	972.5	971.5	970.4	969.4	970.4	971.5	972.5	973.6	974.1
140°	1012.1	1011.5	1010.2	1008.9	1007.7	1006.4	1007.7	1008.9	1010.2	1011.5	1012.1
142.5°	1047.3	1046.7	1045.4	1044.1	1042.9	1041.6	1042.9	1044.1	1045.4	1046.7	1047.3
145°	1081.5	1080.9	1079.6	1078.3	1077.1	1075.8	1077.1	1078.3	1079.6	1080.9	1081.5
147.5°	1111.0	1110.3	1108.8	1107.3	1105.8	1104.3	1105.8	1107.3	1108.8	1110.3	1111.0
150°	1139.5	1138.7	1137.0	1135.3	1133.6	1131.9	1133.6	1135.3	1137.0	1138.7	1139.5
152.5°	1164.2	1163.5	1162.0	1160.5	1159.0	1157.5	1159.0	1160.5	1162.0	1163.5	1164.2
155°	1187.0	1186.2	1184.5	1182.8	1181.1	1179.4	1181.1	1182.8	1184.5	1186.2	1187.0
157.5°	1206.0	1205.2	1203.5	1201.8	1200.1	1198.4	1200.1	1201.8	1203.5	1205.2	1206.0
160°	1224.1	1223.2	1221.5	1219.8	1218.1	1216.4	1218.1	1219.8	1221.5	1223.2	1224.1
162.5°	1241.2	1240.2	1238.3	1236.4	1234.5	1232.6	1234.5	1236.4	1238.3	1240.2	1241.2
165°	1254.5	1253.7	1252.0	1250.3	1248.6	1246.9	1248.6	1250.3	1252.0	1253.7	1254.5
167.5°	1265.9	1264.9	1263.0	1261.1	1259.2	1257.3	1259.2	1261.1	1263.0	1264.9	1265.9
170°	1274.4	1273.5	1271.6	1269.7	1267.8	1265.9	1267.8	1269.7	1271.6	1273.5	1274.4
172.5°	1280.1	1279.2	1277.3	1275.4	1273.5	1271.6	1273.5	1275.4	1277.3	1279.2	1280.1
175°	1284.9	1283.9	1282.0	1280.1	1278.2	1276.3	1278.2	1280.1	1282.0	1283.9	1284.9
177.5°	1286.8	1286.0	1284.3	1282.6	1280.9	1279.2	1280.9	1282.6	1284.3	1286.0	1286.8
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1486.6	1493.0	1487.8	1484.0	1494.3	1499.5	1499.5	1508.5	1517.5	1525.3	1526.6
5°	1394.9	1405.3	1407.8	1406.5	1422.0	1429.8	1446.5	1455.6	1468.5	1477.5	1487.8
7.5°	1311.1	1325.3	1326.5	1329.1	1352.3	1365.3	1379.4	1402.7	1420.7	1433.6	1445.3
10°	1227.2	1236.2	1245.2	1256.9	1280.1	1302.0	1322.7	1347.2	1370.4	1383.3	1400.1
12.5°	1163.9	1170.4	1180.7	1188.5	1213.0	1232.3	1259.4	1293.0	1326.5	1336.9	1357.5
15°	1098.1	1102.0	1122.7	1130.4	1151.0	1183.3	1200.1	1232.3	1268.5	1287.8	1311.1
17.5°	1022.0	1045.2	1058.1	1067.2	1093.0	1118.8	1145.9	1179.4	1225.9	1244.0	1260.7
20°	967.8	984.6	998.8	1010.4	1033.6	1072.3	1096.8	1123.9	1167.8	1188.5	1213.0
22.5°	920.1	934.3	947.2	960.1	975.5	1010.4	1038.8	1076.2	1120.1	1139.4	1167.8
25°	874.9	889.1	896.8	912.3	933.0	957.5	991.0	1024.6	1068.5	1090.4	1117.5
27.5°	831.0	845.2	859.4	872.3	886.5	909.7	933.0	975.5	1020.7	1046.5	1069.7
30°	793.6	800.1	813.0	827.2	841.3	863.3	890.4	920.1	971.7	994.9	1023.3
32.5°	752.3	763.9	773.0	783.3	801.3	819.4	843.9	881.3	922.6	944.6	975.5
35°	713.6	723.9	730.4	748.4	760.1	779.4	803.9	837.5	872.3	896.8	923.9
37.5°	676.2	686.5	694.2	704.6	720.0	736.8	762.6	787.1	828.4	849.1	880.1
40°	637.5	646.5	655.5	667.1	681.3	702.0	717.5	748.4	782.0	805.2	828.4
42.5°	600.0	605.2	615.5	628.4	642.6	660.7	682.6	707.1	740.7	761.3	782.0
45°	560.0	569.1	580.7	589.7	602.6	620.7	640.0	662.0	695.5	716.2	738.1
47.5°	522.6	529.1	536.8	551.0	567.8	580.7	601.3	622.0	652.9	672.3	692.9
50°	483.9	490.4	502.0	511.0	523.9	540.7	560.0	582.0	611.7	624.6	645.2
52.5°	447.8	450.4	462.0	471.0	483.9	503.3	518.7	538.1	566.5	580.7	601.3
55°	411.6	414.2	420.7	429.7	443.9	459.4	476.2	498.1	522.6	535.5	554.9
57.5°	374.2	376.8	383.3	389.7	403.9	418.1	437.4	455.5	480.0	491.6	509.7
60°	336.8	336.8	343.2	352.3	362.6	375.5	392.3	414.2	432.3	446.5	459.4
62.5°	296.8	300.7	304.5	311.0	322.6	338.1	352.3	367.8	389.7	400.0	411.6
65°	256.8	260.7	268.4	274.9	283.9	294.2	312.3	325.2	342.0	353.6	363.9
67.5°	222.0	225.8	231.0	238.7	245.2	256.8	269.7	282.6	300.7	308.4	316.2
70°	185.8	189.7	193.6	203.9	210.3	219.4	228.4	241.3	256.8	262.0	268.4
72.5°	157.4	158.7	163.9	166.5	175.5	183.2	193.6	201.3	212.9	219.4	224.5
75°	132.9	132.9	134.2	136.8	141.9	147.1	154.8	162.6	172.9	176.8	183.2
77.5°	104.5	108.4	107.1	109.7	112.3	114.8	121.3	126.5	136.8	139.4	141.9
80°	74.8	76.1	80.0	83.9	83.9	87.7	91.6	92.9	99.4	103.2	103.2
82.5°	54.2	55.5	54.2	55.5	56.8	58.1	61.9	67.1	67.1	68.4	71.0
85°	33.6	33.6	34.8	36.1	36.1	34.8	37.4	36.1	37.4	40.0	40.0
87.5°	16.8	15.5	15.5	15.5	15.5	15.5	16.8	15.5	16.8	16.8	16.8
90°	19.5	18.4	17.3	16.3	15.2	13.7	12.3	10.8	9.3	8.6	7.8
92.5°	19.5	18.4	17.3	16.3	15.2	13.9	12.7	11.4	10.1	9.5	10.5
95°	19.5	18.4	17.3	16.3	15.2	23.2	31.2	39.3	47.3	51.3	51.6
97.5°	18.8	18.4	17.9	17.5	17.1	37.2	57.2	77.3	97.4	107.4	106.8
100°	39.5	71.0	102.5	133.9	165.4	164.6	163.7	162.9	162.0	161.6	161.3
102.5°	224.1	223.7	223.2	222.8	222.4	222.0	221.6	221.1	220.7	220.5	220.1
105°	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	283.2	282.8
107.5°	346.8	346.6	346.3	346.1	345.9	345.5	345.1	344.6	344.2	344.0	344.0
110°	406.1	406.8	407.4	408.1	408.7	408.3	407.8	407.4	406.9	406.7	406.7

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	466.1	467.0	467.8	468.7	469.5	469.3	469.1	468.8	468.6	468.5	468.2
115°	526.9	527.8	528.6	529.5	530.3	530.1	529.9	529.6	529.4	529.3	528.8
117.5°	585.1	586.4	587.7	588.9	590.2	589.4	588.5	587.7	586.8	586.4	586.4
120°	643.6	644.0	644.5	644.9	645.3	644.7	644.0	643.4	642.7	642.4	642.5
122.5°	697.8	698.2	698.7	699.1	699.5	699.3	699.1	698.8	698.6	698.5	698.0
125°	749.3	750.2	751.0	751.9	752.7	752.7	752.7	752.7	752.7	752.7	752.0
127.5°	798.5	798.9	799.4	799.8	800.2	800.4	800.6	800.8	801.0	801.1	800.6
130°	845.2	845.8	846.5	847.1	847.7	847.5	847.3	847.1	846.9	846.8	846.3
132.5°	890.5	890.5	890.5	890.5	890.5	891.1	891.7	892.4	893.0	893.3	892.7
135°	932.5	932.9	933.4	933.8	934.2	934.6	935.0	935.5	935.9	936.1	935.5
137.5°	974.1	974.1	974.1	974.1	974.1	974.5	974.9	975.4	975.8	976.0	975.4
140°	1011.9	1011.5	1011.0	1010.6	1010.2	1010.4	1010.6	1010.9	1011.1	1011.2	1011.0
142.5°	1047.3	1047.3	1047.3	1047.3	1047.3	1046.9	1046.5	1046.0	1045.6	1045.4	1045.3
145°	1081.4	1081.2	1080.9	1080.7	1080.5	1080.5	1080.5	1080.5	1080.5	1080.5	1080.3
147.5°	1110.9	1110.7	1110.4	1110.2	1110.0	1109.8	1109.6	1109.4	1109.2	1109.1	1109.1
150°	1139.3	1138.9	1138.4	1138.0	1137.6	1137.2	1136.8	1136.3	1135.9	1135.7	1135.9
152.5°	1164.0	1163.6	1163.1	1162.7	1162.3	1161.9	1161.5	1161.0	1160.6	1160.4	1160.9
155°	1186.7	1186.0	1185.4	1184.7	1184.1	1183.7	1183.3	1182.8	1182.4	1182.2	1182.8
157.5°	1205.7	1205.0	1204.4	1203.7	1203.1	1203.1	1203.1	1203.1	1203.1	1203.1	1203.4
160°	1223.7	1222.8	1221.9	1221.1	1220.2	1220.0	1219.8	1219.6	1219.4	1219.3	1219.9
162.5°	1240.6	1239.3	1238.0	1236.8	1235.5	1235.3	1235.1	1234.8	1234.6	1234.5	1235.1
165°	1253.9	1252.6	1251.3	1250.1	1248.8	1248.6	1248.4	1248.1	1247.9	1247.8	1248.4
167.5°	1265.2	1263.7	1262.2	1260.7	1259.2	1259.0	1258.8	1258.6	1258.4	1258.3	1258.9
170°	1273.6	1271.9	1270.2	1268.5	1266.8	1266.6	1266.4	1266.2	1266.0	1265.9	1266.6
172.5°	1279.4	1277.9	1276.4	1275.0	1273.5	1273.1	1272.7	1272.2	1271.8	1271.6	1272.3
175°	1284.1	1282.4	1280.7	1279.0	1277.3	1277.1	1276.9	1276.6	1276.4	1276.3	1276.9
177.5°	1286.1	1284.6	1283.1	1281.6	1280.1	1279.9	1279.7	1279.5	1279.3	1279.2	1279.8
180°	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0	1282.0

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1535.6	1547.2	1558.8	1573.0
5°	1504.6	1525.3	1547.2	1567.8
7.5°	1471.1	1500.7	1529.1	1558.8
10°	1433.6	1471.1	1503.3	1544.6
12.5°	1392.4	1432.4	1477.5	1524.0
15°	1351.1	1401.4	1449.1	1502.0
17.5°	1312.3	1360.1	1413.0	1476.2
20°	1265.9	1318.8	1378.2	1445.3
22.5°	1216.9	1274.9	1339.4	1411.7
25°	1175.6	1234.9	1296.9	1373.0
27.5°	1130.4	1192.3	1253.0	1334.3
30°	1078.8	1145.9	1207.8	1291.7
32.5°	1029.7	1096.8	1165.2	1244.0
35°	982.0	1047.8	1116.2	1196.2
37.5°	936.8	996.2	1063.3	1135.6
40°	894.3	948.5	1007.8	1073.6
42.5°	840.1	903.3	958.8	1006.5
45°	793.6	845.2	896.8	935.5
47.5°	739.4	791.0	834.9	865.9
50°	694.2	735.5	771.7	798.8
52.5°	640.0	678.8	708.4	729.1
55°	587.1	620.7	646.5	660.7
57.5°	539.4	561.3	580.7	593.6
60°	486.5	503.3	520.0	534.2
62.5°	429.7	447.8	456.8	472.3
65°	379.4	391.0	405.2	410.4
67.5°	330.3	336.8	345.8	356.2
70°	278.7	282.6	291.6	305.8
72.5°	233.6	237.4	243.9	249.0
75°	185.8	189.7	194.9	200.0
77.5°	145.8	147.1	149.7	154.8
80°	105.8	109.7	112.3	113.6
82.5°	73.6	74.8	74.8	76.1
85°	46.5	43.9	43.9	45.2
87.5°	16.8	19.4	19.4	21.9
90°	6.1	4.4	2.7	1.0
92.5°	12.4	14.3	16.2	18.1
95°	52.3	52.9	53.6	54.2
97.5°	105.5	104.2	103.0	101.7
100°	160.6	160.0	159.3	158.7
102.5°	219.2	218.4	217.5	216.7
105°	281.9	281.1	280.2	279.4
107.5°	344.0	344.0	344.0	344.0
110°	406.7	406.7	406.7	406.7

TEST NUMBER: P1027058

CATALOG NUMBER: S125RDIP-B1090D1090UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	467.6	466.9	466.3	465.7
115°	527.7	526.7	525.6	524.6
117.5°	586.4	586.4	586.4	586.4
120°	642.7	643.0	643.2	643.4
122.5°	696.9	695.9	694.8	693.8
125°	750.5	749.0	747.5	746.0
127.5°	799.5	798.5	797.4	796.4
130°	845.2	844.1	843.1	842.0
132.5°	891.4	890.1	888.9	887.6
135°	934.2	932.9	931.7	930.4
137.5°	974.1	972.8	971.6	970.3
140°	1010.6	1010.1	1009.7	1009.3
142.5°	1045.1	1044.8	1044.6	1044.4
145°	1079.9	1079.4	1079.0	1078.6
147.5°	1109.1	1109.1	1109.1	1109.1
150°	1136.3	1136.8	1137.2	1137.6
152.5°	1162.0	1163.0	1164.1	1165.1
155°	1184.1	1185.4	1186.6	1187.9
157.5°	1204.1	1204.7	1205.4	1206.0
160°	1221.2	1222.5	1223.7	1225.0
162.5°	1236.4	1237.7	1238.9	1240.2
165°	1249.7	1251.0	1252.2	1253.5
167.5°	1260.2	1261.5	1262.7	1264.0
170°	1268.1	1269.6	1271.0	1272.5
172.5°	1273.8	1275.3	1276.7	1278.2
175°	1278.2	1279.5	1280.7	1282.0
177.5°	1281.1	1282.4	1283.6	1284.9
180°	1282.0	1282.0	1282.0	1282.0

(END OF REPORT)