

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027144

Luminaire Tested: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027144
REPORT IS A COMBINATION OF REPORTS P1005285 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8027.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	57	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	45
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42	42	42	38
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	42	39	36	36	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	32	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	23
8	57	44	36	31	53	42	35	30	37	32	27	33	29	25	29	26	23	23	23	20
9	53	40	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21	21	21	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12088	12088	12088	12088
5°	12078	13624	12078	10472
10°	12010	15310	11970	9053
15°	11880	16197	11798	7881
20°	11722	17485	11618	7124
25°	11517	19791	11387	6465
30°	11308	21036	11139	5995
35°	11038	17300	10883	5556
40°	10558	11748	10469	5161
45°	9927	8446	9914	4772
50°	9280	6495	9326	4414
55°	8554	5281	8537	4067
60°	7877	4329	7839	3612
65°	7088	3607	7133	2907
70°	6435	2895	6409	2421
75°	5436	2193	5436	1990
80°	4405	1338	4356	1338
85°	3099	703	3013	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17206 cd/sqm

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.9	2.3
10°-20°	530.4	6.6
20°-30°	841.0	10.5
30°-40°	1016.3	12.7
40°-50°	904.8	11.3
50°-60°	693.8	8.6
60°-70°	450.6	5.6
70°-80°	218.7	2.7
80°-90°	52.9	0.7
90°-100°	34.7	0.4
100°-110°	230.5	2.9
110°-120°	415.1	5.2
120°-130°	532.8	6.6
130°-140°	573.1	7.1
140°-150°	537.9	6.7
150°-160°	435.1	5.4
160°-170°	281.4	3.5
170°-180°	97.0	1.2
0°-30°	1552.4	19.3
0°-40°	2568.6	32.0
0°-60°	4167.3	51.9
0°-90°	4889.5	60.9
90°-120°	680.3	8.5
90°-150°	2324.0	29.0
90°-180°	3137.0	39.1
0°-180°	8027.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1887	1887	1887	1887	1887	
5°	1882	2162	1882	1662	1882	179
15°	1803	2598	1791	1264	1803	508
25°	1648	3110	1630	1016	1648	760
35°	1436	2581	1416	829	1436	894
45°	1123	1154	1122	652	1123	867
55°	793	634	792	488	793	711
65°	493	359	496	290	493	492
75°	240	167	240	152	240	257
85°	54	36	53	40	54	62
90°	1	18	1	18	1	6
95°	43	16	43	16	43	53
105°	223	225	223	225	223	236
115°	418	415	418	415	418	414
125°	594	594	594	594	594	531
135°	741	738	741	738	741	571
145°	859	857	859	857	859	537
155°	946	940	946	940	946	436
165°	999	993	999	993	999	282
175°	1021	1017	1021	1017	1021	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1888.2	1903.7	1908.4	1920.8	1934.7	1937.8	1945.5	1956.4	1962.6	1961.0	1961.0
5°	1882.0	1908.4	1927.0	1948.6	1975.0	1985.8	1995.1	2018.3	2036.9	2047.8	2066.4
7.5°	1871.2	1909.9	1940.9	1973.4	2013.7	2032.3	2052.4	2085.0	2119.0	2140.7	2160.9
10°	1854.2	1903.7	1947.1	1995.1	2049.3	2077.2	2102.0	2151.6	2193.4	2221.3	2267.7
12.5°	1829.4	1891.3	1951.7	2015.2	2083.4	2112.8	2146.9	2201.1	2260.0	2300.3	2339.0
15°	1803.0	1877.4	1942.4	2018.3	2100.4	2145.4	2188.7	2246.0	2298.7	2343.6	2388.6
17.5°	1772.1	1851.1	1931.6	2018.3	2111.3	2156.2	2193.4	2261.5	2317.3	2362.2	2402.5
20°	1734.9	1823.2	1914.6	2010.6	2105.1	2146.9	2182.5	2256.9	2306.5	2354.5	2411.8
22.5°	1694.6	1790.6	1888.2	1982.7	2075.7	2120.6	2162.4	2227.5	2281.7	2346.7	2421.1
25°	1648.1	1753.5	1852.6	1947.1	2035.4	2077.2	2114.4	2185.6	2261.5	2343.6	2427.3
27.5°	1601.7	1703.9	1799.9	1886.7	1982.7	2021.4	2058.6	2148.5	2238.3	2325.0	2439.7
30°	1550.5	1654.3	1738.0	1818.5	1911.5	1951.7	1998.2	2100.4	2202.7	2320.4	2459.8
32.5°	1493.2	1587.7	1665.2	1748.8	1832.5	1882.0	1940.9	2052.4	2170.1	2311.1	2489.2
35°	1435.9	1511.8	1583.1	1662.1	1762.8	1815.4	1872.7	1990.5	2137.6	2306.5	2514.0
37.5°	1363.1	1435.9	1491.7	1572.2	1676.0	1738.0	1795.3	1931.6	2098.9	2295.6	2512.5
40°	1288.8	1350.7	1403.4	1487.0	1600.1	1657.4	1719.4	1868.1	2058.6	2264.6	2475.3
42.5°	1208.2	1260.9	1318.2	1398.7	1508.7	1564.5	1635.7	1809.2	2002.9	2221.3	2379.3
45°	1123.0	1174.1	1222.2	1305.8	1415.8	1476.2	1553.6	1731.8	1934.7	2129.9	2224.4
47.5°	1039.4	1084.3	1135.4	1208.2	1319.7	1386.4	1465.4	1655.9	1843.3	2007.5	2015.2
50°	958.8	994.5	1037.8	1112.2	1228.4	1291.9	1374.0	1552.1	1734.9	1848.0	1772.1
52.5°	875.2	907.7	952.6	1017.7	1126.1	1200.5	1271.7	1449.9	1603.2	1679.1	1539.7
55°	793.1	821.0	867.4	940.2	1034.7	1092.0	1164.8	1330.6	1465.4	1466.9	1315.1
57.5°	712.5	737.3	776.0	841.1	929.4	996.0	1062.6	1206.7	1298.1	1271.7	1102.9
60°	641.3	656.8	692.4	755.9	838.0	886.0	957.3	1078.1	1138.5	1090.5	909.3
62.5°	566.9	582.4	610.3	661.4	738.9	790.0	834.9	934.0	975.9	903.1	754.4
65°	492.6	511.2	531.3	571.6	644.4	678.5	718.7	791.5	831.8	746.6	618.1
67.5°	427.5	436.8	457.0	498.8	549.9	580.9	608.8	658.3	666.1	597.9	492.6
70°	367.1	370.2	388.8	413.6	452.3	470.9	494.1	523.6	523.6	467.8	384.2
72.5°	299.0	303.6	317.5	343.9	367.1	376.4	384.2	402.7	399.6	348.5	291.2
75°	240.1	243.2	254.0	266.4	275.7	292.8	299.0	295.9	294.3	250.9	218.4
77.5°	185.9	187.4	195.2	206.0	207.6	213.8	209.1	209.1	195.2	170.4	153.4
80°	136.3	137.9	141.0	144.1	144.1	144.1	144.1	136.3	127.0	111.5	106.9
82.5°	91.4	91.4	92.9	96.0	94.5	91.4	88.3	80.5	74.4	69.7	66.6
85°	54.2	54.2	55.8	54.2	48.0	46.5	43.4	41.8	40.3	38.7	38.7
87.5°	26.3	24.8	21.7	18.6	18.6	18.6	18.6	18.6	18.6	17.0	17.0
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.6	9.7	10.9	12.1
92.5°	14.4	12.9	11.4	9.9	8.4	7.6	8.1	9.1	10.1	11.1	12.1
95°	43.2	42.7	42.2	41.7	41.2	40.9	37.7	31.3	24.9	18.5	12.1
97.5°	81.0	82.0	83.0	84.1	85.1	85.6	77.6	61.6	45.6	29.6	13.6
100°	126.4	126.9	127.4	127.9	128.4	128.7	129.0	129.7	130.4	131.0	131.7
102.5°	172.6	173.3	174.0	174.7	175.4	175.7	175.9	176.2	176.5	176.9	177.2
105°	222.6	223.3	223.9	224.6	225.3	225.6	225.6	225.6	225.6	225.6	225.6
107.5°	274.1	274.1	274.1	274.1	274.1	274.1	274.3	274.6	274.9	275.3	275.6
110°	324.1	324.1	324.1	324.1	324.1	324.1	324.3	324.6	324.9	325.3	325.6

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	371.0	371.5	372.0	372.5	373.0	373.3	373.4	373.5	373.7	373.8	374.0
115°	417.9	418.7	419.6	420.4	421.3	421.7	421.8	422.0	422.1	422.3	422.5
117.5°	467.2	467.2	467.2	467.2	467.2	467.2	467.5	468.2	468.9	469.5	470.2
120°	512.6	512.4	512.2	512.1	511.9	511.8	512.1	512.6	513.1	513.6	514.1
122.5°	552.7	553.5	554.4	555.2	556.1	556.5	556.6	556.8	556.9	557.1	557.3
125°	594.4	595.6	596.8	597.9	599.1	599.7	599.7	599.7	599.7	599.7	599.7
127.5°	634.5	635.3	636.2	637.0	637.9	638.3	638.2	638.0	637.9	637.7	637.5
130°	670.8	671.6	672.5	673.3	674.2	674.6	674.7	674.9	675.0	675.2	675.4
132.5°	707.2	708.2	709.2	710.2	711.2	711.7	711.4	710.9	710.4	709.9	709.4
135°	741.2	742.2	743.2	744.3	745.3	745.8	745.6	745.3	745.0	744.6	744.3
137.5°	773.0	774.0	775.0	776.1	777.1	777.6	777.4	777.1	776.8	776.4	776.1
140°	804.1	804.4	804.8	805.1	805.4	805.6	805.5	805.3	805.2	805.0	804.8
142.5°	832.1	832.3	832.5	832.6	832.8	832.9	833.1	833.4	833.7	834.1	834.4
145°	859.4	859.7	860.1	860.4	860.7	860.9	860.9	860.9	860.9	860.9	860.9
147.5°	883.6	883.6	883.6	883.6	883.6	883.6	883.7	883.8	884.0	884.1	884.3
150°	906.3	906.0	905.6	905.3	905.0	904.8	905.0	905.3	905.6	906.0	906.3
152.5°	928.3	927.5	926.6	925.8	924.9	924.5	924.7	925.0	925.3	925.7	926.0
155°	946.4	945.4	944.4	943.4	942.4	941.9	942.1	942.4	942.7	943.1	943.4
157.5°	960.8	960.3	959.8	959.3	958.8	958.5	958.5	958.5	958.5	958.5	958.5
160°	976.0	975.0	974.0	972.9	971.9	971.4	971.5	971.7	971.8	972.0	972.2
162.5°	988.1	987.1	986.1	985.0	984.0	983.5	983.6	983.8	983.9	984.1	984.3
165°	998.7	997.7	996.7	995.6	994.6	994.1	994.2	994.4	994.5	994.7	994.9
167.5°	1007.0	1006.0	1005.0	1004.0	1003.0	1002.5	1002.6	1002.7	1002.9	1003.0	1003.2
170°	1013.8	1012.6	1011.4	1010.3	1009.1	1008.5	1008.6	1008.8	1008.9	1009.1	1009.3
172.5°	1018.4	1017.2	1016.0	1014.9	1013.7	1013.1	1013.3	1013.6	1013.9	1014.3	1014.6
175°	1021.4	1020.4	1019.4	1018.3	1017.3	1016.8	1016.9	1017.1	1017.2	1017.4	1017.6
177.5°	1023.7	1022.7	1021.7	1020.6	1019.6	1019.1	1019.2	1019.4	1019.5	1019.7	1019.9
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1968.8	1979.6	1988.9	1984.3	2002.9	2001.3	2004.4	2010.6	2012.1	2009.1	2002.9
5°	2075.7	2091.1	2117.5	2131.4	2128.3	2140.7	2146.9	2156.2	2165.5	2162.4	2162.4
7.5°	2194.9	2216.6	2242.9	2278.6	2283.2	2294.1	2312.7	2312.7	2323.5	2318.9	2317.3
10°	2298.7	2325.0	2366.9	2394.8	2407.1	2413.3	2431.9	2438.1	2450.5	2452.1	2452.1
12.5°	2383.9	2430.4	2458.3	2486.1	2492.3	2501.6	2515.6	2524.9	2529.5	2529.5	2524.9
15°	2428.8	2466.0	2498.5	2528.0	2545.0	2552.7	2566.7	2577.5	2583.7	2597.7	2600.8
17.5°	2447.4	2492.3	2545.0	2586.8	2616.3	2624.0	2651.9	2661.2	2673.6	2679.8	2687.5
20°	2473.8	2538.8	2602.3	2653.4	2681.3	2701.5	2730.9	2774.3	2786.6	2786.6	2782.0
22.5°	2497.0	2580.6	2667.4	2749.5	2772.7	2813.0	2867.2	2913.7	2932.3	2940.0	2933.8
25°	2524.9	2639.5	2752.6	2854.8	2918.3	2947.7	3020.5	3076.3	3098.0	3110.4	3113.5
27.5°	2572.9	2716.9	2861.0	2991.1	3056.2	3090.3	3166.2	3214.2	3240.5	3251.3	3243.6
30°	2627.1	2803.7	2971.0	3087.2	3130.5	3172.3	3221.9	3240.5	3234.3	3234.3	3257.5
32.5°	2682.9	2865.6	3014.4	3090.3	3105.7	3099.5	3079.4	3023.6	2991.1	2991.1	3011.3
35°	2713.8	2871.8	2947.7	2923.0	2862.5	2826.9	2716.9	2655.0	2585.3	2580.6	2603.9
37.5°	2696.8	2765.0	2734.0	2571.3	2489.2	2421.1	2249.1	2181.0	2129.9	2058.6	2168.6
40°	2577.5	2554.3	2393.2	2159.3	2067.9	1971.9	1835.6	1767.4	1696.2	1685.3	1711.6
42.5°	2376.2	2238.3	2002.9	1776.7	1683.8	1615.6	1511.8	1445.2	1400.3	1381.7	1412.7
45°	2125.2	1908.4	1672.9	1493.2	1391.0	1355.4	1260.9	1202.0	1167.9	1154.0	1175.7
47.5°	1818.5	1600.1	1377.1	1225.3	1164.8	1129.2	1065.7	1014.6	985.2	975.9	985.2
50°	1544.4	1319.7	1132.3	1034.7	980.5	951.1	898.4	865.9	842.7	836.5	851.9
52.5°	1307.4	1102.9	960.4	873.6	838.0	813.2	776.0	748.2	734.2	728.0	738.9
55°	1095.1	929.4	814.8	740.4	714.1	698.6	666.1	650.6	635.1	633.5	644.4
57.5°	907.7	793.1	687.8	635.1	627.3	604.1	576.2	562.3	554.5	553.0	557.6
60°	755.9	653.7	590.2	543.7	532.9	514.3	498.8	489.5	480.2	477.1	480.2
62.5°	628.9	548.3	497.2	466.2	450.8	446.1	429.1	418.2	416.7	416.7	419.8
65°	518.9	450.8	418.2	393.4	382.6	378.0	365.6	357.8	359.4	359.4	360.9
67.5°	422.9	373.3	343.9	331.5	322.2	320.6	308.3	305.2	302.1	302.1	305.2
70°	336.1	305.2	283.5	277.3	275.7	264.9	260.2	258.7	254.0	255.6	255.6
72.5°	263.3	243.2	230.8	221.5	223.1	216.9	210.7	210.7	207.6	212.2	212.2
75°	195.2	185.9	176.6	173.5	176.6	173.5	168.8	167.3	168.8	167.3	167.3
77.5°	144.1	139.4	136.3	134.8	134.8	128.6	125.5	128.6	122.4	125.5	125.5
80°	100.7	94.5	92.9	89.8	91.4	86.7	88.3	85.2	85.2	85.2	85.2
82.5°	63.5	62.0	62.0	62.0	60.4	60.4	60.4	60.4	60.4	60.4	58.9
85°	38.7	37.2	37.2	37.2	35.6	35.6	35.6	35.6	35.6	35.6	35.6
87.5°	15.5	17.0	17.0	18.6	17.0	15.5	15.5	15.5	17.0	17.0	15.5
90°	12.9	13.8	14.6	15.5	15.9	16.2	16.7	17.2	17.7	18.2	17.7
92.5°	12.9	13.8	14.6	15.5	15.9	16.0	16.2	16.3	16.5	16.7	16.5
95°	12.9	13.8	14.6	15.5	15.9	15.9	15.9	15.9	15.9	15.9	15.9
97.5°	13.9	14.3	14.6	14.9	15.1	15.2	15.4	15.5	15.7	15.9	15.7
100°	106.6	81.6	56.5	31.4	18.9	18.6	17.9	17.2	16.6	15.9	16.6
102.5°	177.5	177.9	178.2	178.5	178.7	171.6	157.5	143.4	129.2	115.1	129.2
105°	225.6	225.6	225.6	225.6	225.6	225.5	225.4	225.2	225.1	224.9	225.1
107.5°	275.8	276.0	276.1	276.3	276.4	276.1	275.4	274.7	274.0	273.3	274.0
110°	325.1	324.6	324.1	323.6	323.3	323.4	323.6	323.7	323.9	324.1	323.9



TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	373.3	372.7	372.0	371.3	371.0	370.8	370.5	370.2	369.8	369.5	369.8
115°	421.8	421.2	420.5	419.8	419.5	419.0	418.0	416.9	415.9	414.9	415.9
117.5°	469.2	468.2	467.1	466.1	465.6	465.4	465.1	464.8	464.4	464.1	464.4
120°	513.8	513.4	513.1	512.8	512.6	512.2	511.3	510.5	509.6	508.8	509.6
122.5°	556.9	556.6	556.2	555.9	555.7	555.2	554.2	553.2	552.2	551.2	552.2
125°	599.0	598.3	597.6	596.9	596.6	596.4	595.9	595.4	594.9	594.4	594.9
127.5°	637.2	636.8	636.5	636.2	636.0	635.3	634.0	632.6	631.3	629.9	631.3
130°	674.9	674.4	673.9	673.4	673.1	672.7	671.8	671.0	670.1	669.3	670.1
132.5°	709.4	709.4	709.4	709.4	709.4	709.0	708.2	707.3	706.5	705.7	706.5
135°	744.0	743.6	743.3	743.0	742.8	742.3	741.3	740.2	739.2	738.2	739.2
137.5°	776.1	776.1	776.1	776.1	776.1	775.7	774.8	774.0	773.1	772.3	773.1
140°	805.2	805.5	805.9	806.2	806.4	805.9	804.9	803.8	802.8	801.8	802.8
142.5°	834.4	834.4	834.4	834.4	834.4	833.9	832.9	831.8	830.8	829.8	830.8
145°	861.1	861.2	861.4	861.5	861.6	861.1	860.1	859.1	858.1	857.1	858.1
147.5°	884.5	884.7	884.8	885.0	885.1	884.5	883.3	882.2	881.0	879.8	881.0
150°	906.6	907.0	907.3	907.6	907.8	907.1	905.8	904.5	903.1	901.8	903.1
152.5°	926.3	926.7	927.0	927.3	927.5	926.9	925.7	924.6	923.4	922.2	923.4
155°	943.9	944.4	944.9	945.4	945.7	945.0	943.7	942.3	941.0	939.6	941.0
157.5°	959.0	959.5	960.0	960.5	960.8	960.1	958.8	957.5	956.1	954.8	956.1
160°	972.9	973.5	974.2	974.9	975.2	974.5	973.2	971.8	970.5	969.1	970.5
162.5°	985.3	986.3	987.3	988.3	988.8	988.0	986.5	985.0	983.5	982.0	983.5
165°	995.9	996.9	997.9	998.9	999.4	998.7	997.4	996.1	994.7	993.4	994.7
167.5°	1004.4	1005.6	1006.7	1007.9	1008.5	1007.7	1006.2	1004.7	1003.2	1001.7	1003.2
170°	1010.6	1012.0	1013.3	1014.6	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0
172.5°	1015.8	1017.0	1018.1	1019.3	1019.9	1019.1	1017.6	1016.1	1014.6	1013.1	1014.6
175°	1019.0	1020.3	1021.7	1023.0	1023.7	1022.9	1021.4	1019.9	1018.3	1016.8	1018.3
177.5°	1021.1	1022.3	1023.4	1024.6	1025.2	1024.5	1023.2	1021.8	1020.5	1019.1	1020.5
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	2010.6	1999.8	2004.4	1999.8	1995.1	1990.5	1979.6	1964.1	1951.7	1942.4	1940.9
5°	2165.5	2151.6	2142.3	2137.6	2128.3	2115.9	2095.8	2072.6	2044.7	2033.8	2012.1
7.5°	2308.0	2303.4	2281.7	2278.6	2272.4	2249.1	2215.1	2184.1	2148.5	2119.0	2091.1
10°	2442.8	2431.9	2416.4	2394.8	2391.7	2362.2	2329.7	2286.3	2239.9	2212.0	2162.4
12.5°	2526.4	2514.0	2497.0	2483.0	2475.3	2456.7	2411.8	2368.4	2326.6	2275.5	2232.1
15°	2586.8	2571.3	2540.4	2529.5	2520.2	2495.4	2462.9	2418.0	2362.2	2326.6	2264.6
17.5°	2668.9	2650.3	2619.4	2599.2	2582.2	2543.5	2497.0	2436.6	2383.9	2343.6	2287.9
20°	2763.4	2735.5	2695.3	2668.9	2644.1	2599.2	2534.2	2462.9	2387.0	2337.4	2280.1
22.5°	2919.9	2867.2	2803.7	2766.5	2732.4	2655.0	2577.5	2489.2	2404.0	2329.7	2260.0
25°	3071.7	3019.0	2940.0	2888.9	2836.2	2746.4	2644.1	2521.8	2413.3	2326.6	2235.2
27.5°	3212.6	3158.4	3085.6	3023.6	2972.5	2837.8	2703.0	2565.1	2427.3	2308.0	2215.1
30°	3245.2	3221.9	3166.2	3111.9	3065.5	2941.5	2785.1	2610.1	2444.3	2291.0	2187.2
32.5°	3048.4	3105.7	3119.7	3111.9	3082.5	2994.2	2850.2	2665.8	2469.1	2283.2	2140.7
35°	2639.5	2743.3	2850.2	2907.5	2935.4	2947.7	2862.5	2693.7	2486.1	2270.8	2109.7
37.5°	2188.7	2289.4	2458.3	2543.5	2637.9	2761.9	2795.9	2687.5	2478.4	2261.5	2060.2
40°	1798.4	1927.0	2066.4	2143.8	2225.9	2449.0	2617.8	2605.4	2453.6	2227.5	2021.4
42.5°	1463.8	1544.4	1666.7	1751.9	1852.6	2102.0	2328.1	2439.7	2379.3	2185.6	1971.9
45°	1220.6	1282.6	1369.3	1456.1	1518.0	1744.2	2012.1	2194.9	2252.2	2111.3	1896.0
47.5°	1028.5	1075.0	1150.9	1205.1	1271.7	1449.9	1682.2	1939.3	2060.2	2006.0	1815.4
50°	881.4	918.6	979.0	1013.0	1071.9	1225.3	1401.8	1671.4	1854.2	1860.3	1708.5
52.5°	752.8	790.0	841.1	870.5	906.2	1009.9	1188.1	1415.8	1626.4	1703.9	1586.2
55°	655.2	676.9	718.7	742.0	774.5	875.2	988.3	1181.9	1401.8	1528.9	1454.5
57.5°	565.4	588.6	615.0	633.5	656.8	737.3	839.6	985.2	1203.6	1341.4	1316.6
60°	492.6	506.5	531.3	545.2	566.9	619.6	690.9	836.5	1009.9	1140.1	1154.0
62.5°	424.4	436.8	453.9	466.2	480.2	522.0	574.7	678.5	830.3	971.2	989.8
65°	365.6	376.4	385.7	396.5	407.4	433.7	478.6	559.2	676.9	808.6	848.9
67.5°	312.9	316.0	329.9	331.5	337.7	357.8	390.3	455.4	540.6	645.9	698.6
70°	261.8	268.0	271.1	275.7	281.9	295.9	322.2	356.3	419.8	505.0	554.5
72.5°	212.2	213.8	218.4	221.5	227.7	238.5	250.9	277.3	317.5	379.5	424.4
75°	168.8	170.4	173.5	175.0	179.7	182.8	189.0	207.6	235.4	272.6	305.2
77.5°	127.0	130.1	133.2	133.2	134.8	137.9	141.0	147.2	161.1	185.9	213.8
80°	86.7	88.3	88.3	89.8	88.3	92.9	97.6	105.3	111.5	119.3	133.2
82.5°	60.4	60.4	60.4	62.0	62.0	63.5	63.5	65.1	66.6	71.3	77.4
85°	37.2	37.2	38.7	35.6	37.2	38.7	38.7	37.2	38.7	40.3	41.8
87.5°	15.5	15.5	17.0	17.0	17.0	17.0	15.5	17.0	15.5	17.0	17.0
90°	17.2	16.7	16.2	15.9	15.5	14.6	13.8	12.9	12.1	10.9	9.7
92.5°	16.3	16.2	16.0	15.9	15.5	14.6	13.8	12.9	12.1	11.1	10.1
95°	15.9	15.9	15.9	15.9	15.5	14.6	13.8	12.9	12.1	18.5	24.9
97.5°	15.5	15.4	15.2	15.1	14.9	14.6	14.3	13.9	13.6	29.6	45.6
100°	17.2	17.9	18.6	18.9	31.4	56.5	81.6	106.6	131.7	131.0	130.4
102.5°	143.4	157.5	171.6	178.7	178.5	178.2	177.9	177.5	177.2	176.9	176.5
105°	225.2	225.4	225.5	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6
107.5°	274.7	275.4	276.1	276.4	276.3	276.1	276.0	275.8	275.6	275.3	274.9
110°	323.7	323.6	323.4	323.3	323.6	324.1	324.6	325.1	325.6	325.3	324.9

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	370.2	370.5	370.8	371.0	371.3	372.0	372.7	373.3	374.0	373.8	373.7
115°	416.9	418.0	419.0	419.5	419.8	420.5	421.2	421.8	422.5	422.3	422.1
117.5°	464.8	465.1	465.4	465.6	466.1	467.1	468.2	469.2	470.2	469.5	468.9
120°	510.5	511.3	512.2	512.6	512.8	513.1	513.4	513.8	514.1	513.6	513.1
122.5°	553.2	554.2	555.2	555.7	555.9	556.2	556.6	556.9	557.3	557.1	556.9
125°	595.4	595.9	596.4	596.6	596.9	597.6	598.3	599.0	599.7	599.7	599.7
127.5°	632.6	634.0	635.3	636.0	636.2	636.5	636.8	637.2	637.5	637.7	637.9
130°	671.0	671.8	672.7	673.1	673.4	673.9	674.4	674.9	675.4	675.2	675.0
132.5°	707.3	708.2	709.0	709.4	709.4	709.4	709.4	709.4	709.4	709.9	710.4
135°	740.2	741.3	742.3	742.8	743.0	743.3	743.6	744.0	744.3	744.6	745.0
137.5°	774.0	774.8	775.7	776.1	776.1	776.1	776.1	776.1	776.1	776.4	776.8
140°	803.8	804.9	805.9	806.4	806.2	805.9	805.5	805.2	804.8	805.0	805.2
142.5°	831.8	832.9	833.9	834.4	834.4	834.4	834.4	834.4	834.4	834.1	833.7
145°	859.1	860.1	861.1	861.6	861.5	861.4	861.2	861.1	860.9	860.9	860.9
147.5°	882.2	883.3	884.5	885.1	885.0	884.8	884.7	884.5	884.3	884.1	884.0
150°	904.5	905.8	907.1	907.8	907.6	907.3	907.0	906.6	906.3	906.0	905.6
152.5°	924.6	925.7	926.9	927.5	927.3	927.0	926.7	926.3	926.0	925.7	925.3
155°	942.3	943.7	945.0	945.7	945.4	944.9	944.4	943.9	943.4	943.1	942.7
157.5°	957.5	958.8	960.1	960.8	960.5	960.0	959.5	959.0	958.5	958.5	958.5
160°	971.8	973.2	974.5	975.2	974.9	974.2	973.5	972.9	972.2	972.0	971.8
162.5°	985.0	986.5	988.0	988.8	988.3	987.3	986.3	985.3	984.3	984.1	983.9
165°	996.1	997.4	998.7	999.4	998.9	997.9	996.9	995.9	994.9	994.7	994.5
167.5°	1004.7	1006.2	1007.7	1008.5	1007.9	1006.7	1005.6	1004.4	1003.2	1003.0	1002.9
170°	1011.5	1013.0	1014.5	1015.3	1014.6	1013.3	1012.0	1010.6	1009.3	1009.1	1008.9
172.5°	1016.1	1017.6	1019.1	1019.9	1019.3	1018.1	1017.0	1015.8	1014.6	1014.3	1013.9
175°	1019.9	1021.4	1022.9	1023.7	1023.0	1021.7	1020.3	1019.0	1017.6	1017.4	1017.2
177.5°	1021.8	1023.2	1024.5	1025.2	1024.6	1023.4	1022.3	1021.1	1019.9	1019.7	1019.5
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1936.2	1927.0	1920.8	1919.2	1909.9	1902.2	1892.9	1891.3	1886.7	1874.3	1866.5
5°	1996.7	1975.0	1970.3	1956.4	1933.2	1916.1	1894.4	1882.0	1868.1	1844.9	1826.3
7.5°	2058.6	2029.2	2007.5	1987.4	1954.8	1923.9	1892.9	1868.1	1843.3	1809.2	1781.3
10°	2119.0	2074.1	2047.8	2018.3	1973.4	1927.0	1883.6	1848.0	1807.7	1767.4	1727.1
12.5°	2174.8	2117.5	2078.8	2036.9	1981.2	1923.9	1868.1	1818.5	1776.7	1722.5	1677.6
15°	2208.9	2145.4	2106.6	2066.4	1982.7	1919.2	1854.2	1790.6	1734.9	1677.6	1635.7
17.5°	2229.0	2157.8	2114.4	2077.2	1992.0	1905.3	1821.6	1753.5	1693.1	1624.9	1569.1
20°	2219.7	2150.0	2109.7	2074.1	1975.0	1888.2	1798.4	1719.4	1643.5	1573.8	1514.9
22.5°	2199.6	2126.8	2081.9	2049.3	1961.0	1858.8	1759.7	1674.5	1595.5	1525.8	1459.2
25°	2156.2	2085.0	2046.2	2006.0	1919.2	1821.6	1720.9	1629.5	1545.9	1471.5	1397.2
27.5°	2117.5	2030.7	1990.5	1954.8	1863.4	1776.7	1677.6	1576.9	1491.7	1414.2	1339.9
30°	2072.6	1975.0	1931.6	1883.6	1801.5	1719.4	1620.3	1527.3	1439.0	1356.9	1285.7
32.5°	2024.5	1911.5	1861.9	1807.7	1724.0	1646.6	1562.9	1471.5	1383.3	1302.7	1228.4
35°	1962.6	1841.8	1784.4	1733.3	1646.6	1569.1	1491.7	1415.8	1327.5	1242.3	1171.0
37.5°	1903.7	1770.5	1710.1	1651.2	1559.8	1485.5	1422.0	1350.7	1265.5	1183.4	1115.3
40°	1837.1	1683.8	1621.8	1567.6	1473.1	1391.0	1333.7	1277.9	1203.6	1124.6	1050.2
42.5°	1776.7	1603.2	1538.2	1482.4	1383.3	1305.8	1251.6	1205.1	1140.1	1067.3	991.4
45°	1693.1	1516.5	1449.9	1391.0	1290.3	1217.5	1161.7	1121.5	1070.4	1002.2	934.0
47.5°	1615.6	1432.8	1360.0	1288.8	1197.4	1123.0	1071.9	1040.9	1006.8	946.4	876.7
50°	1521.1	1336.8	1262.4	1203.6	1099.8	1036.3	985.2	963.5	932.5	875.2	819.4
52.5°	1418.9	1243.8	1174.1	1102.9	1006.8	944.9	900.0	875.2	850.4	808.6	755.9
55°	1299.6	1140.1	1075.0	1011.5	915.5	858.1	817.9	791.5	777.6	738.9	700.1
57.5°	1185.0	1034.7	974.3	915.5	831.8	766.8	740.4	717.2	697.0	669.2	636.6
60°	1068.8	932.5	867.4	814.8	742.0	683.1	661.4	638.2	622.7	601.0	577.8
62.5°	935.6	819.4	769.9	720.3	658.3	611.9	587.1	568.5	548.3	534.4	514.3
65°	794.6	712.5	664.5	627.3	568.5	526.7	508.1	495.7	478.6	464.7	449.2
67.5°	663.0	597.9	577.8	537.5	492.6	455.4	441.5	426.0	412.0	404.3	390.3
70°	536.0	489.5	469.3	458.5	408.9	384.2	371.8	365.6	348.5	340.8	331.5
72.5°	415.1	398.1	384.2	370.2	337.7	322.2	308.3	302.1	289.7	283.5	280.4
75°	306.7	295.9	288.1	286.6	272.6	257.1	243.2	240.1	230.8	224.6	221.5
77.5°	215.3	212.2	210.7	212.2	202.9	193.6	190.5	187.4	176.6	175.0	175.0
80°	141.0	148.7	148.7	147.2	144.1	142.5	137.9	134.8	128.6	127.0	128.6
82.5°	86.7	91.4	92.9	96.0	94.5	92.9	89.8	88.3	89.8	86.7	88.3
85°	43.4	46.5	52.7	52.7	54.2	54.2	54.2	52.7	49.6	51.1	49.6
87.5°	17.0	18.6	18.6	18.6	17.0	21.7	23.2	23.2	23.2	20.1	20.1
90°	8.6	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	9.1	8.1	7.6	8.4	9.9	11.4	12.9	14.4	12.9	11.4	9.9
95°	31.3	37.7	40.9	41.2	41.7	42.2	42.7	43.2	42.7	42.2	41.7
97.5°	61.6	77.6	85.6	85.1	84.1	83.0	82.0	81.0	82.0	83.0	84.1
100°	129.7	129.0	128.7	128.4	127.9	127.4	126.9	126.4	126.9	127.4	127.9
102.5°	176.2	175.9	175.7	175.4	174.7	174.0	173.3	172.6	173.3	174.0	174.7
105°	225.6	225.6	225.6	225.3	224.6	223.9	223.3	222.6	223.3	223.9	224.6
107.5°	274.6	274.3	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1
110°	324.6	324.3	324.1	324.1	324.1	324.1	324.1	324.1	324.1	324.1	324.1

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	373.5	373.4	373.3	373.0	372.5	372.0	371.5	371.0	371.5	372.0	372.5
115°	422.0	421.8	421.7	421.3	420.4	419.6	418.7	417.9	418.7	419.6	420.4
117.5°	468.2	467.5	467.2	467.2	467.2	467.2	467.2	467.2	467.2	467.2	467.2
120°	512.6	512.1	511.8	511.9	512.1	512.2	512.4	512.6	512.4	512.2	512.1
122.5°	556.8	556.6	556.5	556.1	555.2	554.4	553.5	552.7	553.5	554.4	555.2
125°	599.7	599.7	599.7	599.1	597.9	596.8	595.6	594.4	595.6	596.8	597.9
127.5°	638.0	638.2	638.3	637.9	637.0	636.2	635.3	634.5	635.3	636.2	637.0
130°	674.9	674.7	674.6	674.2	673.3	672.5	671.6	670.8	671.6	672.5	673.3
132.5°	710.9	711.4	711.7	711.2	710.2	709.2	708.2	707.2	708.2	709.2	710.2
135°	745.3	745.6	745.8	745.3	744.3	743.2	742.2	741.2	742.2	743.2	744.3
137.5°	777.1	777.4	777.6	777.1	776.1	775.0	774.0	773.0	774.0	775.0	776.1
140°	805.3	805.5	805.6	805.4	805.1	804.8	804.4	804.1	804.4	804.8	805.1
142.5°	833.4	833.1	832.9	832.8	832.6	832.5	832.3	832.1	832.3	832.5	832.6
145°	860.9	860.9	860.9	860.7	860.4	860.1	859.7	859.4	859.7	860.1	860.4
147.5°	883.8	883.7	883.6	883.6	883.6	883.6	883.6	883.6	883.6	883.6	883.6
150°	905.3	905.0	904.8	905.0	905.3	905.6	906.0	906.3	906.0	905.6	905.3
152.5°	925.0	924.7	924.5	924.9	925.8	926.6	927.5	928.3	927.5	926.6	925.8
155°	942.4	942.1	941.9	942.4	943.4	944.4	945.4	946.4	945.4	944.4	943.4
157.5°	958.5	958.5	958.5	958.8	959.3	959.8	960.3	960.8	960.3	959.8	959.3
160°	971.7	971.5	971.4	971.9	972.9	974.0	975.0	976.0	975.0	974.0	972.9
162.5°	983.8	983.6	983.5	984.0	985.0	986.1	987.1	988.1	987.1	986.1	985.0
165°	994.4	994.2	994.1	994.6	995.6	996.7	997.7	998.7	997.7	996.7	995.6
167.5°	1002.7	1002.6	1002.5	1003.0	1004.0	1005.0	1006.0	1007.0	1006.0	1005.0	1004.0
170°	1008.8	1008.6	1008.5	1009.1	1010.3	1011.4	1012.6	1013.8	1012.6	1011.4	1010.3
172.5°	1013.6	1013.3	1013.1	1013.7	1014.9	1016.0	1017.2	1018.4	1017.2	1016.0	1014.9
175°	1017.1	1016.9	1016.8	1017.3	1018.3	1019.4	1020.4	1021.4	1020.4	1019.4	1018.3
177.5°	1019.4	1019.2	1019.1	1019.6	1020.6	1021.7	1022.7	1023.7	1022.7	1021.7	1020.6
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1861.9	1855.7	1851.1	1846.4	1826.3	1804.6	1801.5	1796.8	1787.5	1798.4	1793.7
5°	1813.9	1799.9	1792.2	1772.1	1747.3	1728.7	1713.2	1694.6	1686.9	1680.7	1679.1
7.5°	1755.0	1742.6	1728.7	1708.5	1677.6	1646.6	1623.4	1604.8	1589.3	1581.5	1581.5
10°	1697.7	1682.2	1663.6	1629.5	1600.1	1561.4	1536.6	1518.0	1496.3	1483.9	1473.1
12.5°	1638.8	1621.8	1604.8	1561.4	1527.3	1487.0	1451.4	1428.2	1417.3	1403.4	1384.8
15°	1580.0	1553.6	1536.6	1493.2	1449.9	1409.6	1386.4	1361.6	1336.8	1322.8	1316.6
17.5°	1518.0	1499.4	1471.5	1425.1	1377.1	1341.4	1307.4	1284.1	1254.7	1240.7	1226.8
20°	1462.3	1434.4	1406.5	1360.0	1313.6	1265.5	1231.5	1203.6	1185.0	1174.1	1161.7
22.5°	1395.6	1369.3	1346.1	1296.5	1245.4	1200.5	1163.3	1146.3	1127.7	1110.6	1098.2
25°	1338.3	1312.0	1288.8	1234.6	1178.8	1137.0	1109.1	1087.4	1067.3	1059.5	1047.1
27.5°	1277.9	1253.1	1222.2	1167.9	1118.4	1082.7	1053.3	1033.2	1017.7	1002.2	992.9
30°	1220.6	1192.7	1164.8	1106.0	1065.7	1030.1	1002.2	977.4	965.0	957.3	941.8
32.5°	1164.8	1129.2	1106.0	1051.8	1013.0	979.0	955.7	934.0	918.6	904.6	892.2
35°	1104.4	1065.7	1042.5	997.6	957.3	923.2	903.1	887.6	869.0	856.6	850.4
37.5°	1047.1	1014.6	991.4	944.9	904.6	876.7	855.0	834.9	827.2	810.1	807.0
40°	985.2	957.3	935.6	890.7	853.5	831.8	808.6	790.0	776.0	768.3	757.5
42.5°	929.4	906.2	882.9	841.1	805.5	779.1	762.1	745.1	732.7	720.3	712.5
45°	878.3	853.5	831.8	791.5	755.9	732.7	715.6	695.5	692.4	675.4	667.6
47.5°	824.1	802.4	783.8	742.0	709.4	686.2	666.1	652.1	638.2	632.0	621.1
50°	771.4	749.7	728.0	690.9	661.4	638.2	618.1	602.6	594.8	585.5	576.2
52.5°	714.1	697.0	680.0	641.3	611.9	591.7	574.7	554.5	546.8	539.1	532.9
55°	666.1	641.3	622.7	590.2	563.8	542.1	523.6	508.1	500.3	494.1	486.4
57.5°	601.0	585.5	570.0	540.6	515.8	494.1	475.5	463.2	453.9	449.2	450.8
60°	545.2	528.2	518.9	487.9	463.2	446.1	429.1	416.7	407.4	402.7	401.2
62.5°	486.4	474.0	457.0	435.3	410.5	395.0	382.6	373.3	357.8	356.3	351.6
65°	429.1	419.8	404.3	384.2	364.0	350.1	336.1	323.7	317.5	309.8	305.2
67.5°	373.3	364.0	350.1	333.0	319.1	305.2	292.8	280.4	269.5	263.3	260.2
70°	319.1	311.3	302.1	281.9	264.9	254.0	244.7	237.0	226.2	223.1	221.5
72.5°	266.4	258.7	254.0	237.0	221.5	212.2	202.9	195.2	190.5	189.0	184.3
75°	218.4	210.7	204.5	189.0	179.7	173.5	164.2	161.1	156.4	154.9	153.4
77.5°	170.4	162.6	161.1	150.3	139.4	136.3	133.2	127.0	127.0	127.0	123.9
80°	122.4	120.8	119.3	108.4	103.8	100.7	99.1	94.5	91.4	88.3	86.7
82.5°	82.1	80.5	79.0	74.4	69.7	68.2	66.6	63.5	63.5	65.1	62.0
85°	49.6	46.5	44.9	43.4	40.3	40.3	41.8	40.3	40.3	40.3	38.7
87.5°	18.6	18.6	18.6	18.6	20.1	17.0	18.6	18.6	17.0	17.0	15.5
90°	6.1	6.8	7.4	8.6	9.7	10.9	12.1	12.9	13.8	14.6	15.5
92.5°	8.4	7.6	8.1	9.1	10.1	11.1	12.1	12.9	13.8	14.6	15.5
95°	41.2	40.9	37.7	31.3	24.9	18.5	12.1	12.9	13.8	14.6	15.5
97.5°	85.1	85.6	77.6	61.6	45.6	29.6	13.6	13.9	14.3	14.6	14.9
100°	128.4	128.7	129.0	129.7	130.4	131.0	131.7	106.6	81.6	56.5	31.4
102.5°	175.4	175.7	175.9	176.2	176.5	176.9	177.2	177.5	177.9	178.2	178.5
105°	225.3	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6
107.5°	274.1	274.1	274.3	274.6	274.9	275.3	275.6	275.8	276.0	276.1	276.3
110°	324.1	324.1	324.3	324.6	324.9	325.3	325.6	325.1	324.6	324.1	323.6

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	373.0	373.3	373.4	373.5	373.7	373.8	374.0	373.3	372.7	372.0	371.3
115°	421.3	421.7	421.8	422.0	422.1	422.3	422.5	421.8	421.2	420.5	419.8
117.5°	467.2	467.2	467.5	468.2	468.9	469.5	470.2	469.2	468.2	467.1	466.1
120°	511.9	511.8	512.1	512.6	513.1	513.6	514.1	513.8	513.4	513.1	512.8
122.5°	556.1	556.5	556.6	556.8	556.9	557.1	557.3	556.9	556.6	556.2	555.9
125°	599.1	599.7	599.7	599.7	599.7	599.7	599.7	599.0	598.3	597.6	596.9
127.5°	637.9	638.3	638.2	638.0	637.9	637.7	637.5	637.2	636.8	636.5	636.2
130°	674.2	674.6	674.7	674.9	675.0	675.2	675.4	674.9	674.4	673.9	673.4
132.5°	711.2	711.7	711.4	710.9	710.4	709.9	709.4	709.4	709.4	709.4	709.4
135°	745.3	745.8	745.6	745.3	745.0	744.6	744.3	744.0	743.6	743.3	743.0
137.5°	777.1	777.6	777.4	777.1	776.8	776.4	776.1	776.1	776.1	776.1	776.1
140°	805.4	805.6	805.5	805.3	805.2	805.0	804.8	805.2	805.5	805.9	806.2
142.5°	832.8	832.9	833.1	833.4	833.7	834.1	834.4	834.4	834.4	834.4	834.4
145°	860.7	860.9	860.9	860.9	860.9	860.9	860.9	861.1	861.2	861.4	861.5
147.5°	883.6	883.6	883.7	883.8	884.0	884.1	884.3	884.5	884.7	884.8	885.0
150°	905.0	904.8	905.0	905.3	905.6	906.0	906.3	906.6	907.0	907.3	907.6
152.5°	924.9	924.5	924.7	925.0	925.3	925.7	926.0	926.3	926.7	927.0	927.3
155°	942.4	941.9	942.1	942.4	942.7	943.1	943.4	943.9	944.4	944.9	945.4
157.5°	958.8	958.5	958.5	958.5	958.5	958.5	958.5	959.0	959.5	960.0	960.5
160°	971.9	971.4	971.5	971.7	971.8	972.0	972.2	972.9	973.5	974.2	974.9
162.5°	984.0	983.5	983.6	983.8	983.9	984.1	984.3	985.3	986.3	987.3	988.3
165°	994.6	994.1	994.2	994.4	994.5	994.7	994.9	995.9	996.9	997.9	998.9
167.5°	1003.0	1002.5	1002.6	1002.7	1002.9	1003.0	1003.2	1004.4	1005.6	1006.7	1007.9
170°	1009.1	1008.5	1008.6	1008.8	1008.9	1009.1	1009.3	1010.6	1012.0	1013.3	1014.6
172.5°	1013.7	1013.1	1013.3	1013.6	1013.9	1014.3	1014.6	1015.8	1017.0	1018.1	1019.3
175°	1017.3	1016.8	1016.9	1017.1	1017.2	1017.4	1017.6	1019.0	1020.3	1021.7	1023.0
177.5°	1019.6	1019.1	1019.2	1019.4	1019.5	1019.7	1019.9	1021.1	1022.3	1023.4	1024.6
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1786.0	1789.1	1781.3	1778.3	1772.1	1779.8	1781.3	1779.8	1793.7	1787.5	1790.6
5°	1682.2	1676.0	1671.4	1660.5	1660.5	1662.1	1666.7	1659.0	1663.6	1674.5	1672.9
7.5°	1567.6	1564.5	1566.0	1553.6	1544.4	1547.4	1544.4	1558.3	1566.0	1562.9	1569.1
10°	1463.8	1470.0	1456.1	1449.9	1443.7	1449.9	1448.3	1451.4	1460.7	1466.9	1477.7
12.5°	1380.2	1378.6	1370.9	1364.7	1353.8	1356.9	1366.2	1363.1	1364.7	1378.6	1377.1
15°	1301.2	1291.9	1285.7	1271.7	1274.8	1264.0	1273.3	1284.1	1288.8	1301.2	1308.9
17.5°	1222.2	1220.6	1212.9	1211.3	1194.3	1189.6	1198.9	1202.0	1206.7	1212.9	1223.7
20°	1155.6	1154.0	1143.2	1140.1	1126.1	1135.4	1132.3	1138.5	1141.6	1154.0	1158.7
22.5°	1095.1	1087.4	1084.3	1079.7	1075.0	1073.5	1079.7	1078.1	1088.9	1093.6	1095.1
25°	1039.4	1033.2	1031.6	1023.9	1020.8	1016.1	1020.8	1025.4	1037.8	1042.5	1048.7
27.5°	988.3	983.6	980.5	974.3	969.7	969.7	972.8	979.0	983.6	986.7	989.8
30°	941.8	938.7	929.4	926.3	921.7	921.7	921.7	924.8	932.5	941.8	946.4
32.5°	893.8	887.6	881.4	881.4	876.7	876.7	878.3	881.4	889.1	890.7	898.4
35°	847.3	841.1	836.5	833.4	834.9	828.7	831.8	836.5	845.8	848.9	853.5
37.5°	802.4	800.8	791.5	786.9	790.0	790.0	788.4	791.5	797.7	803.9	807.0
40°	752.8	749.7	749.7	745.1	746.6	740.4	745.1	748.2	751.3	757.5	762.1
42.5°	709.4	706.3	700.1	701.7	697.0	697.0	700.1	701.7	706.3	714.1	717.2
45°	663.0	663.0	659.9	655.2	656.8	652.1	655.2	656.8	663.0	670.7	667.6
47.5°	618.1	616.5	616.5	610.3	613.4	608.8	613.4	615.0	618.1	622.7	621.1
50°	574.7	570.0	571.6	570.0	568.5	568.5	571.6	571.6	574.7	574.7	579.3
52.5°	529.8	529.8	526.7	528.2	531.3	528.2	532.9	528.2	531.3	532.9	536.0
55°	489.5	486.4	487.9	486.4	492.6	487.9	492.6	489.5	492.6	491.0	494.1
57.5°	446.1	441.5	443.0	441.5	446.1	444.6	449.2	444.6	446.1	447.7	452.3
60°	396.5	396.5	396.5	393.4	398.1	398.1	396.5	396.5	402.7	405.8	404.3
62.5°	350.1	348.5	343.9	342.3	343.9	340.8	347.0	345.4	348.5	351.6	354.7
65°	299.0	295.9	294.3	291.2	291.2	289.7	291.2	297.4	299.0	300.5	308.3
67.5°	257.1	255.6	254.0	249.4	249.4	252.5	252.5	252.5	261.8	257.1	263.3
70°	220.0	216.9	213.8	212.2	212.2	213.8	215.3	216.9	215.3	221.5	223.1
72.5°	184.3	185.9	182.8	182.8	182.8	181.2	181.2	184.3	185.9	184.3	185.9
75°	153.4	153.4	151.8	153.4	153.4	151.8	151.8	154.9	154.9	153.4	158.0
77.5°	123.9	122.4	119.3	116.2	117.7	116.2	117.7	116.2	120.8	125.5	122.4
80°	86.7	85.2	85.2	85.2	86.7	85.2	88.3	85.2	86.7	86.7	88.3
82.5°	62.0	63.5	63.5	62.0	63.5	62.0	63.5	63.5	63.5	62.0	63.5
85°	40.3	40.3	40.3	40.3	38.7	40.3	40.3	40.3	41.8	40.3	41.8
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	18.6	17.0	18.6
90°	15.9	16.2	16.7	17.2	17.7	18.2	17.7	17.2	16.7	16.2	15.9
92.5°	15.9	16.0	16.2	16.3	16.5	16.7	16.5	16.3	16.2	16.0	15.9
95°	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9	15.9
97.5°	15.1	15.2	15.4	15.5	15.7	15.9	15.7	15.5	15.4	15.2	15.1
100°	18.9	18.6	17.9	17.2	16.6	15.9	16.6	17.2	17.9	18.6	18.9
102.5°	178.7	171.6	157.5	143.4	129.2	115.1	129.2	143.4	157.5	171.6	178.7
105°	225.6	225.5	225.4	225.2	225.1	224.9	225.1	225.2	225.4	225.5	225.6
107.5°	276.4	276.1	275.4	274.7	274.0	273.3	274.0	274.7	275.4	276.1	276.4
110°	323.3	323.4	323.6	323.7	323.9	324.1	323.9	323.7	323.6	323.4	323.3

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	371.0	370.8	370.5	370.2	369.8	369.5	369.8	370.2	370.5	370.8	371.0
115°	419.5	419.0	418.0	416.9	415.9	414.9	415.9	416.9	418.0	419.0	419.5
117.5°	465.6	465.4	465.1	464.8	464.4	464.1	464.4	464.8	465.1	465.4	465.6
120°	512.6	512.2	511.3	510.5	509.6	508.8	509.6	510.5	511.3	512.2	512.6
122.5°	555.7	555.2	554.2	553.2	552.2	551.2	552.2	553.2	554.2	555.2	555.7
125°	596.6	596.4	595.9	595.4	594.9	594.4	594.9	595.4	595.9	596.4	596.6
127.5°	636.0	635.3	634.0	632.6	631.3	629.9	631.3	632.6	634.0	635.3	636.0
130°	673.1	672.7	671.8	671.0	670.1	669.3	670.1	671.0	671.8	672.7	673.1
132.5°	709.4	709.0	708.2	707.3	706.5	705.7	706.5	707.3	708.2	709.0	709.4
135°	742.8	742.3	741.3	740.2	739.2	738.2	739.2	740.2	741.3	742.3	742.8
137.5°	776.1	775.7	774.8	774.0	773.1	772.3	773.1	774.0	774.8	775.7	776.1
140°	806.4	805.9	804.9	803.8	802.8	801.8	802.8	803.8	804.9	805.9	806.4
142.5°	834.4	833.9	832.9	831.8	830.8	829.8	830.8	831.8	832.9	833.9	834.4
145°	861.6	861.1	860.1	859.1	858.1	857.1	858.1	859.1	860.1	861.1	861.6
147.5°	885.1	884.5	883.3	882.2	881.0	879.8	881.0	882.2	883.3	884.5	885.1
150°	907.8	907.1	905.8	904.5	903.1	901.8	903.1	904.5	905.8	907.1	907.8
152.5°	927.5	926.9	925.7	924.6	923.4	922.2	923.4	924.6	925.7	926.9	927.5
155°	945.7	945.0	943.7	942.3	941.0	939.6	941.0	942.3	943.7	945.0	945.7
157.5°	960.8	960.1	958.8	957.5	956.1	954.8	956.1	957.5	958.8	960.1	960.8
160°	975.2	974.5	973.2	971.8	970.5	969.1	970.5	971.8	973.2	974.5	975.2
162.5°	988.8	988.0	986.5	985.0	983.5	982.0	983.5	985.0	986.5	988.0	988.8
165°	999.4	998.7	997.4	996.1	994.7	993.4	994.7	996.1	997.4	998.7	999.4
167.5°	1008.5	1007.7	1006.2	1004.7	1003.2	1001.7	1003.2	1004.7	1006.2	1007.7	1008.5
170°	1015.3	1014.5	1013.0	1011.5	1010.0	1008.5	1010.0	1011.5	1013.0	1014.5	1015.3
172.5°	1019.9	1019.1	1017.6	1016.1	1014.6	1013.1	1014.6	1016.1	1017.6	1019.1	1019.9
175°	1023.7	1022.9	1021.4	1019.9	1018.3	1016.8	1018.3	1019.9	1021.4	1022.9	1023.7
177.5°	1025.2	1024.5	1023.2	1021.8	1020.5	1019.1	1020.5	1021.8	1023.2	1024.5	1025.2
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1784.4	1792.2	1786.0	1781.3	1793.7	1799.9	1799.9	1810.8	1821.6	1830.9	1832.5
5°	1674.5	1686.9	1690.0	1688.4	1707.0	1716.3	1736.4	1747.3	1762.8	1773.6	1786.0
7.5°	1573.8	1590.8	1592.4	1595.5	1623.4	1638.8	1655.9	1683.8	1705.4	1720.9	1734.9
10°	1473.1	1483.9	1494.8	1508.7	1536.6	1562.9	1587.7	1617.2	1645.0	1660.5	1680.7
12.5°	1397.2	1404.9	1417.3	1426.6	1456.1	1479.3	1511.8	1552.1	1592.4	1604.8	1629.5
15°	1318.2	1322.8	1347.6	1356.9	1381.7	1420.4	1440.6	1479.3	1522.7	1545.9	1573.8
17.5°	1226.8	1254.7	1270.2	1281.0	1312.0	1343.0	1375.5	1415.8	1471.5	1493.2	1513.4
20°	1161.7	1181.9	1198.9	1212.9	1240.7	1287.2	1316.6	1349.2	1401.8	1426.6	1456.1
22.5°	1104.4	1121.5	1137.0	1152.5	1171.0	1212.9	1246.9	1291.9	1344.5	1367.8	1401.8
25°	1050.2	1067.3	1076.6	1095.1	1119.9	1149.4	1189.6	1229.9	1282.6	1308.9	1341.4
27.5°	997.6	1014.6	1031.6	1047.1	1064.2	1092.0	1119.9	1171.0	1225.3	1256.2	1284.1
30°	952.6	960.4	975.9	992.9	1009.9	1036.3	1068.8	1104.4	1166.4	1194.3	1228.4
32.5°	903.1	917.0	927.9	940.2	961.9	983.6	1013.0	1058.0	1107.5	1133.9	1171.0
35°	856.6	869.0	876.7	898.4	912.4	935.6	965.0	1005.3	1047.1	1076.6	1109.1
37.5°	811.7	824.1	833.4	845.8	864.3	884.5	915.5	944.9	994.5	1019.2	1056.4
40°	765.2	776.0	786.9	800.8	817.9	842.7	861.2	898.4	938.7	966.6	994.5
42.5°	720.3	726.5	738.9	754.4	771.4	793.1	819.4	848.9	889.1	913.9	938.7
45°	672.3	683.1	697.0	707.9	723.4	745.1	768.3	794.6	834.9	859.7	886.0
47.5°	627.3	635.1	644.4	661.4	681.6	697.0	721.8	746.6	783.8	807.0	831.8
50°	580.9	588.6	602.6	613.4	628.9	649.0	672.3	698.6	734.2	749.7	774.5
52.5°	537.5	540.6	554.5	565.4	580.9	604.1	622.7	645.9	680.0	697.0	721.8
55°	494.1	497.2	505.0	515.8	532.9	551.4	571.6	597.9	627.3	642.8	666.1
57.5°	449.2	452.3	460.1	467.8	484.8	501.9	525.1	546.8	576.2	590.2	611.9
60°	404.3	404.3	412.0	422.9	435.3	450.8	470.9	497.2	518.9	536.0	551.4
62.5°	356.3	360.9	365.6	373.3	387.2	405.8	422.9	441.5	467.8	480.2	494.1
65°	308.3	312.9	322.2	329.9	340.8	353.2	374.9	390.3	410.5	424.4	436.8
67.5°	266.4	271.1	277.3	286.6	294.3	308.3	323.7	339.2	360.9	370.2	379.5
70°	223.1	227.7	232.3	244.7	252.5	263.3	274.2	289.7	308.3	314.4	322.2
72.5°	189.0	190.5	196.7	199.8	210.7	220.0	232.3	241.6	255.6	263.3	269.5
75°	159.5	159.5	161.1	164.2	170.4	176.6	185.9	195.2	207.6	212.2	220.0
77.5°	125.5	130.1	128.6	131.7	134.8	137.9	145.6	151.8	164.2	167.3	170.4
80°	89.8	91.4	96.0	100.7	100.7	105.3	110.0	111.5	119.3	123.9	123.9
82.5°	65.1	66.6	65.1	66.6	68.2	69.7	74.4	80.5	80.5	82.1	85.2
85°	40.3	40.3	41.8	43.4	43.4	41.8	44.9	43.4	44.9	48.0	48.0
87.5°	20.1	18.6	18.6	18.6	18.6	18.6	20.1	18.6	20.1	20.1	20.1
90°	15.5	14.6	13.8	12.9	12.1	10.9	9.7	8.6	7.4	6.8	6.1
92.5°	15.5	14.6	13.8	12.9	12.1	11.1	10.1	9.1	8.1	7.6	8.4
95°	15.5	14.6	13.8	12.9	12.1	18.5	24.9	31.3	37.7	40.9	41.2
97.5°	14.9	14.6	14.3	13.9	13.6	29.6	45.6	61.6	77.6	85.6	85.1
100°	31.4	56.5	81.6	106.6	131.7	131.0	130.4	129.7	129.0	128.7	128.4
102.5°	178.5	178.2	177.9	177.5	177.2	176.9	176.5	176.2	175.9	175.7	175.4
105°	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.6	225.3
107.5°	276.3	276.1	276.0	275.8	275.6	275.3	274.9	274.6	274.3	274.1	274.1
110°	323.6	324.1	324.6	325.1	325.6	325.3	324.9	324.6	324.3	324.1	324.1

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	371.3	372.0	372.7	373.3	374.0	373.8	373.7	373.5	373.4	373.3	373.0
115°	419.8	420.5	421.2	421.8	422.5	422.3	422.1	422.0	421.8	421.7	421.3
117.5°	466.1	467.1	468.2	469.2	470.2	469.5	468.9	468.2	467.5	467.2	467.2
120°	512.8	513.1	513.4	513.8	514.1	513.6	513.1	512.6	512.1	511.8	511.9
122.5°	555.9	556.2	556.6	556.9	557.3	557.1	556.9	556.8	556.6	556.5	556.1
125°	596.9	597.6	598.3	599.0	599.7	599.7	599.7	599.7	599.7	599.7	599.1
127.5°	636.2	636.5	636.8	637.2	637.5	637.7	637.9	638.0	638.2	638.3	637.9
130°	673.4	673.9	674.4	674.9	675.4	675.2	675.0	674.9	674.7	674.6	674.2
132.5°	709.4	709.4	709.4	709.4	709.4	709.9	710.4	710.9	711.4	711.7	711.2
135°	743.0	743.3	743.6	744.0	744.3	744.6	745.0	745.3	745.6	745.8	745.3
137.5°	776.1	776.1	776.1	776.1	776.1	776.4	776.8	777.1	777.4	777.6	777.1
140°	806.2	805.9	805.5	805.2	804.8	805.0	805.2	805.3	805.5	805.6	805.4
142.5°	834.4	834.4	834.4	834.4	834.4	834.1	833.7	833.4	833.1	832.9	832.8
145°	861.5	861.4	861.2	861.1	860.9	860.9	860.9	860.9	860.9	860.9	860.7
147.5°	885.0	884.8	884.7	884.5	884.3	884.1	884.0	883.8	883.7	883.6	883.6
150°	907.6	907.3	907.0	906.6	906.3	906.0	905.6	905.3	905.0	904.8	905.0
152.5°	927.3	927.0	926.7	926.3	926.0	925.7	925.3	925.0	924.7	924.5	924.9
155°	945.4	944.9	944.4	943.9	943.4	943.1	942.7	942.4	942.1	941.9	942.4
157.5°	960.5	960.0	959.5	959.0	958.5	958.5	958.5	958.5	958.5	958.5	958.8
160°	974.9	974.2	973.5	972.9	972.2	972.0	971.8	971.7	971.5	971.4	971.9
162.5°	988.3	987.3	986.3	985.3	984.3	984.1	983.9	983.8	983.6	983.5	984.0
165°	998.9	997.9	996.9	995.9	994.9	994.7	994.5	994.4	994.2	994.1	994.6
167.5°	1007.9	1006.7	1005.6	1004.4	1003.2	1003.0	1002.9	1002.7	1002.6	1002.5	1003.0
170°	1014.6	1013.3	1012.0	1010.6	1009.3	1009.1	1008.9	1008.8	1008.6	1008.5	1009.1
172.5°	1019.3	1018.1	1017.0	1015.8	1014.6	1014.3	1013.9	1013.6	1013.3	1013.1	1013.7
175°	1023.0	1021.7	1020.3	1019.0	1017.6	1017.4	1017.2	1017.1	1016.9	1016.8	1017.3
177.5°	1024.6	1023.4	1022.3	1021.1	1019.9	1019.7	1019.5	1019.4	1019.2	1019.1	1019.6
180°	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4	1021.4

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1886.7	1886.7	1886.7	1886.7
2.5°	1843.3	1857.2	1871.2	1888.2
5°	1806.1	1830.9	1857.2	1882.0
7.5°	1765.9	1801.5	1835.6	1871.2
10°	1720.9	1765.9	1804.6	1854.2
12.5°	1671.4	1719.4	1773.6	1829.4
15°	1621.8	1682.2	1739.5	1803.0
17.5°	1575.3	1632.6	1696.2	1772.1
20°	1519.6	1583.1	1654.3	1734.9
22.5°	1460.7	1530.4	1607.9	1694.6
25°	1411.1	1482.4	1556.7	1648.1
27.5°	1356.9	1431.3	1504.1	1601.7
30°	1295.0	1375.5	1449.9	1550.5
32.5°	1236.1	1316.6	1398.7	1493.2
35°	1178.8	1257.8	1339.9	1435.9
37.5°	1124.6	1195.8	1276.4	1363.1
40°	1073.5	1138.5	1209.8	1288.8
42.5°	1008.4	1084.3	1150.9	1208.2
45°	952.6	1014.6	1076.6	1123.0
47.5°	887.6	949.5	1002.2	1039.4
50°	833.4	882.9	926.3	958.8
52.5°	768.3	814.8	850.4	875.2
55°	704.8	745.1	776.0	793.1
57.5°	647.5	673.8	697.0	712.5
60°	584.0	604.1	624.2	641.3
62.5°	515.8	537.5	548.3	566.9
65°	455.4	469.3	486.4	492.6
67.5°	396.5	404.3	415.1	427.5
70°	334.6	339.2	350.1	367.1
72.5°	280.4	285.0	292.8	299.0
75°	223.1	227.7	233.9	240.1
77.5°	175.0	176.6	179.7	185.9
80°	127.0	131.7	134.8	136.3
82.5°	88.3	89.8	89.8	91.4
85°	55.8	52.7	52.7	54.2
87.5°	20.1	23.2	23.2	26.3
90°	4.8	3.5	2.1	0.8
92.5°	9.9	11.4	12.9	14.4
95°	41.7	42.2	42.7	43.2
97.5°	84.1	83.0	82.0	81.0
100°	127.9	127.4	126.9	126.4
102.5°	174.7	174.0	173.3	172.6
105°	224.6	223.9	223.3	222.6
107.5°	274.1	274.1	274.1	274.1
110°	324.1	324.1	324.1	324.1

TEST NUMBER: P1027144

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	372.5	372.0	371.5	371.0
115°	420.4	419.6	418.7	417.9
117.5°	467.2	467.2	467.2	467.2
120°	512.1	512.2	512.4	512.6
122.5°	555.2	554.4	553.5	552.7
125°	597.9	596.8	595.6	594.4
127.5°	637.0	636.2	635.3	634.5
130°	673.3	672.5	671.6	670.8
132.5°	710.2	709.2	708.2	707.2
135°	744.3	743.2	742.2	741.2
137.5°	776.1	775.0	774.0	773.0
140°	805.1	804.8	804.4	804.1
142.5°	832.6	832.5	832.3	832.1
145°	860.4	860.1	859.7	859.4
147.5°	883.6	883.6	883.6	883.6
150°	905.3	905.6	906.0	906.3
152.5°	925.8	926.6	927.5	928.3
155°	943.4	944.4	945.4	946.4
157.5°	959.3	959.8	960.3	960.8
160°	972.9	974.0	975.0	976.0
162.5°	985.0	986.1	987.1	988.1
165°	995.6	996.7	997.7	998.7
167.5°	1004.0	1005.0	1006.0	1007.0
170°	1010.3	1011.4	1012.6	1013.8
172.5°	1014.9	1016.0	1017.2	1018.4
175°	1018.3	1019.4	1020.4	1021.4
177.5°	1020.6	1021.7	1022.7	1023.7
180°	1021.4	1021.4	1021.4	1021.4

(END OF REPORT)