

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027148

Luminaire Tested: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027148
REPORT IS A COMBINATION OF REPORTS P1005289 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7786.0 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	61
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	57	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	49	49	45
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42	42	42	38
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	42	39	36	36	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	32	32	29
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28	28	28	26
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25	25	25	23
8	57	44	36	31	53	42	35	30	37	32	27	33	29	25	29	26	23	23	23	20
9	53	40	33	28	49	38	32	27	34	29	25	31	26	23	27	23	21	21	21	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	25	21	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11724	11724	11724	11724
5°	11715	13214	11715	10157
10°	11649	14850	11610	8781
15°	11523	15710	11444	7644
20°	11370	16959	11268	6910
25°	11171	19196	11045	6271
30°	10968	20404	10804	5814
35°	10706	16780	10556	5389
40°	10240	11395	10154	5007
45°	9629	8192	9615	4629
50°	9002	6299	9045	4281
55°	8296	5122	8280	3945
60°	7640	4198	7603	3503
65°	6875	3499	6918	2820
70°	6242	2807	6216	2348
75°	5273	2127	5273	1929
80°	4272	1297	4224	1297
85°	3007	683	2922	772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 16689 cd/sqm

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.5	2.3
10°-20°	514.5	6.6
20°-30°	815.7	10.5
30°-40°	985.7	12.7
40°-50°	877.6	11.3
50°-60°	673.0	8.6
60°-70°	437.1	5.6
70°-80°	212.1	2.7
80°-90°	51.4	0.7
90°-100°	33.6	0.4
100°-110°	223.6	2.9
110°-120°	402.7	5.2
120°-130°	516.9	6.6
130°-140°	555.9	7.1
140°-150°	521.7	6.7
150°-160°	422.0	5.4
160°-170°	272.9	3.5
170°-180°	94.1	1.2
0°-30°	1505.7	19.3
0°-40°	2491.4	32.0
0°-60°	4041.9	51.9
0°-90°	4742.5	60.9
90°-120°	659.9	8.5
90°-150°	2254.4	29.0
90°-180°	3044.0	39.1
0°-180°	7786.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1825	2097	1825	1612	1825	173
15°	1749	2520	1737	1226	1749	493
25°	1599	3017	1580	986	1599	737
35°	1393	2503	1373	804	1393	867
45°	1089	1119	1088	632	1089	841
55°	769	614	768	473	769	689
65°	478	349	481	281	478	478
75°	233	162	233	147	233	250
85°	53	35	51	39	53	60
90°	1	18	1	18	1	6
95°	42	15	42	15	42	51
105°	216	218	216	218	216	229
115°	405	402	405	402	405	402
125°	577	577	577	577	577	515
135°	719	716	719	716	719	554
145°	834	831	834	831	834	521
155°	918	912	918	912	918	423
165°	969	964	969	964	969	274
175°	991	986	991	986	991	94
180°	991	991	991	991	991	

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1831.4	1846.5	1851.0	1863.0	1876.5	1879.5	1887.0	1897.5	1903.6	1902.1	1902.1
5°	1825.4	1851.0	1869.0	1890.0	1915.6	1926.1	1935.1	1957.6	1975.7	1986.2	2004.2
7.5°	1814.9	1852.5	1882.5	1914.1	1953.1	1971.2	1990.7	2022.2	2055.3	2076.3	2095.9
10°	1798.4	1846.5	1888.5	1935.1	1987.7	2014.7	2038.8	2086.9	2127.4	2154.5	2199.5
12.5°	1774.4	1834.4	1893.0	1954.6	2020.7	2049.3	2082.3	2134.9	2192.0	2231.1	2268.6
15°	1748.8	1820.9	1884.0	1957.6	2037.3	2080.8	2122.9	2178.5	2229.6	2273.2	2316.7
17.5°	1718.8	1795.4	1873.5	1957.6	2047.8	2091.4	2127.4	2193.5	2247.6	2291.2	2330.2
20°	1682.7	1768.3	1857.0	1950.1	2041.8	2082.3	2116.9	2189.0	2237.1	2283.7	2339.3
22.5°	1643.6	1736.8	1831.4	1923.1	2013.2	2056.8	2097.4	2160.5	2213.1	2276.2	2348.3
25°	1598.6	1700.7	1796.9	1888.5	1974.2	2014.7	2050.8	2119.9	2193.5	2273.2	2354.3
27.5°	1553.5	1652.7	1745.8	1829.9	1923.1	1960.7	1996.7	2083.8	2171.0	2255.1	2366.3
30°	1503.9	1604.6	1685.7	1763.8	1854.0	1893.0	1938.1	2037.3	2136.4	2250.6	2385.8
32.5°	1448.3	1540.0	1615.1	1696.2	1777.4	1825.4	1882.5	1990.7	2104.9	2241.6	2414.4
35°	1392.7	1466.4	1535.5	1612.1	1709.7	1760.8	1816.4	1930.6	2073.3	2237.1	2438.4
37.5°	1322.1	1392.7	1446.8	1525.0	1625.6	1685.7	1741.3	1873.5	2035.8	2226.6	2436.9
40°	1250.0	1310.1	1361.2	1442.3	1552.0	1607.6	1667.7	1811.9	1996.7	2196.5	2400.9
42.5°	1171.9	1223.0	1278.6	1356.7	1463.4	1517.4	1586.5	1754.8	1942.6	2154.5	2307.7
45°	1089.3	1138.8	1185.4	1266.5	1373.2	1431.8	1506.9	1679.7	1876.5	2065.8	2157.5
47.5°	1008.1	1051.7	1101.3	1171.9	1280.1	1344.7	1421.3	1606.1	1787.9	1947.1	1954.6
50°	930.0	964.6	1006.6	1078.7	1191.4	1253.0	1332.6	1505.4	1682.7	1792.4	1718.8
52.5°	848.9	880.4	924.0	987.1	1092.3	1164.4	1233.5	1406.3	1555.0	1628.6	1493.4
55°	769.2	796.3	841.4	912.0	1003.6	1059.2	1129.8	1290.6	1421.3	1422.8	1275.5
57.5°	691.1	715.1	752.7	815.8	901.4	966.1	1030.7	1170.4	1259.0	1233.5	1069.7
60°	622.0	637.0	671.6	733.2	812.8	859.4	928.5	1045.7	1104.3	1057.7	881.9
62.5°	549.9	564.9	592.0	641.5	716.7	766.2	809.8	906.0	946.5	875.9	731.7
65°	477.8	495.8	515.3	554.4	625.0	658.1	697.1	767.7	806.8	724.2	599.5
67.5°	414.7	423.7	443.2	483.8	533.4	563.4	590.4	638.5	646.0	579.9	477.8
70°	356.1	359.1	377.1	401.1	438.7	456.7	479.3	507.8	507.8	453.7	372.6
72.5°	290.0	294.5	308.0	333.5	356.1	365.1	372.6	390.6	387.6	338.0	282.5
75°	232.9	235.9	246.4	258.4	267.4	284.0	290.0	287.0	285.5	243.4	211.8
77.5°	180.3	181.8	189.3	199.8	201.3	207.3	202.8	202.8	189.3	165.3	148.7
80°	132.2	133.7	136.7	139.7	139.7	139.7	139.7	132.2	123.2	108.2	103.7
82.5°	88.6	88.6	90.1	93.1	91.6	88.6	85.6	78.1	72.1	67.6	64.6
85°	52.6	52.6	54.1	52.6	46.6	45.1	42.1	40.6	39.1	37.6	37.6
87.5°	25.5	24.0	21.0	18.0	18.0	18.0	18.0	18.0	18.0	16.5	16.5
90°	0.7	2.0	3.3	4.6	5.9	6.6	7.2	8.3	9.5	10.6	11.8
92.5°	14.0	12.5	11.0	9.5	8.0	7.3	7.8	8.8	9.8	10.8	11.8
95°	41.9	41.4	40.9	40.4	39.9	39.7	36.6	30.4	24.2	18.0	11.8
97.5°	78.6	79.6	80.6	81.5	82.5	83.0	75.2	59.7	44.2	28.7	13.2
100°	122.7	123.2	123.7	124.2	124.7	124.9	125.2	125.9	126.5	127.2	127.8
102.5°	167.5	168.1	168.8	169.4	170.1	170.4	170.6	170.9	171.2	171.6	171.9
105°	215.9	216.6	217.2	217.9	218.6	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	265.9	265.9	265.9	265.9	265.9	265.9	266.1	266.4	266.7	267.0	267.3
110°	314.4	314.4	314.4	314.4	314.4	314.4	314.6	314.9	315.2	315.5	315.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	359.9	360.4	360.9	361.4	361.9	362.1	362.2	362.3	362.5	362.6	362.8
115°	405.4	406.2	407.0	407.9	408.7	409.1	409.2	409.3	409.5	409.6	409.8
117.5°	453.2	453.2	453.2	453.2	453.2	453.2	453.5	454.2	454.8	455.5	456.1
120°	497.2	497.0	496.9	496.7	496.6	496.5	496.7	497.2	497.7	498.2	498.7
122.5°	536.2	537.0	537.8	538.6	539.4	539.8	539.9	540.1	540.2	540.4	540.6
125°	576.6	577.7	578.9	580.0	581.1	581.7	581.7	581.7	581.7	581.7	581.7
127.5°	615.5	616.3	617.1	618.0	618.8	619.2	619.1	618.9	618.8	618.6	618.4
130°	650.7	651.5	652.3	653.2	654.0	654.4	654.5	654.6	654.8	654.9	655.1
132.5°	686.0	687.0	688.0	688.9	689.9	690.4	690.2	689.7	689.2	688.7	688.2
135°	719.0	720.0	721.0	722.0	723.0	723.5	723.3	723.0	722.7	722.3	722.0
137.5°	749.9	750.9	751.9	752.8	753.8	754.3	754.1	753.8	753.5	753.1	752.8
140°	780.0	780.3	780.7	781.0	781.3	781.5	781.4	781.2	781.1	780.9	780.7
142.5°	807.2	807.4	807.5	807.7	807.8	807.9	808.1	808.4	808.7	809.1	809.4
145°	833.6	833.9	834.3	834.6	834.9	835.1	835.1	835.1	835.1	835.1	835.1
147.5°	857.1	857.1	857.1	857.1	857.1	857.1	857.2	857.4	857.5	857.7	857.9
150°	879.2	878.9	878.5	878.2	877.9	877.7	877.9	878.2	878.5	878.9	879.2
152.5°	900.5	899.7	898.9	898.0	897.2	896.8	897.0	897.3	897.6	898.0	898.3
155°	918.1	917.1	916.1	915.2	914.2	913.7	913.9	914.2	914.5	914.9	915.2
157.5°	932.0	931.5	931.0	930.5	930.0	929.8	929.8	929.8	929.8	929.8	929.8
160°	946.7	945.7	944.7	943.8	942.8	942.3	942.4	942.6	942.7	942.9	943.1
162.5°	958.5	957.5	956.5	955.6	954.6	954.1	954.2	954.3	954.5	954.6	954.8
165°	968.8	967.8	966.8	965.9	964.9	964.4	964.5	964.6	964.8	964.9	965.1
167.5°	976.8	975.8	974.8	973.9	972.9	972.4	972.5	972.7	972.8	973.0	973.2
170°	983.5	982.3	981.2	980.0	978.9	978.3	978.4	978.5	978.7	978.8	979.0
172.5°	987.9	986.7	985.6	984.4	983.3	982.7	982.9	983.2	983.5	983.9	984.2
175°	990.8	989.8	988.8	987.9	986.9	986.4	986.5	986.6	986.8	986.9	987.1
177.5°	993.0	992.0	991.0	990.1	989.1	988.6	988.7	988.8	989.0	989.1	989.3
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1909.6	1920.1	1929.1	1924.6	1942.6	1941.1	1944.1	1950.1	1951.6	1948.6	1942.6
5°	2013.2	2028.3	2053.8	2067.3	2064.3	2076.3	2082.3	2091.4	2100.4	2097.4	2097.4
7.5°	2128.9	2150.0	2175.5	2210.1	2214.6	2225.1	2243.1	2243.1	2253.6	2249.1	2247.6
10°	2229.6	2255.1	2295.7	2322.7	2334.8	2340.8	2358.8	2364.8	2376.8	2378.3	2378.3
12.5°	2312.2	2357.3	2384.3	2411.4	2417.4	2426.4	2439.9	2448.9	2453.4	2453.4	2448.9
15°	2355.8	2391.8	2423.4	2451.9	2468.5	2476.0	2489.5	2500.0	2506.0	2519.5	2522.6
17.5°	2373.8	2417.4	2468.5	2509.0	2537.6	2545.1	2572.1	2581.1	2593.2	2599.2	2606.7
20°	2399.4	2462.5	2524.1	2573.6	2600.7	2620.2	2648.8	2690.8	2702.8	2702.8	2698.3
22.5°	2421.9	2503.0	2587.2	2666.8	2689.3	2728.4	2781.0	2826.0	2844.1	2851.6	2845.6
25°	2448.9	2560.1	2669.8	2768.9	2830.5	2859.1	2929.7	2983.8	3004.8	3016.8	3019.9
27.5°	2495.5	2635.2	2775.0	2901.2	2964.3	2997.3	3070.9	3117.5	3143.1	3153.6	3146.1
30°	2548.1	2719.4	2881.6	2994.3	3036.4	3076.9	3125.0	3143.1	3137.0	3137.0	3159.6
32.5°	2602.2	2779.5	2923.7	2997.3	3012.3	3006.3	2986.8	2932.7	2901.2	2901.2	2920.7
35°	2632.2	2785.5	2859.1	2835.1	2776.5	2741.9	2635.2	2575.1	2507.5	2503.0	2525.6
37.5°	2615.7	2681.8	2651.8	2494.0	2414.4	2348.3	2181.5	2115.4	2065.8	1996.7	2103.4
40°	2500.0	2477.5	2321.2	2094.4	2005.7	1912.6	1780.4	1714.3	1645.1	1634.6	1660.2
42.5°	2304.7	2171.0	1942.6	1723.3	1633.1	1567.0	1466.4	1401.8	1358.2	1340.2	1370.2
45°	2061.3	1851.0	1622.6	1448.3	1349.2	1314.6	1223.0	1165.9	1132.8	1119.3	1140.3
47.5°	1763.8	1552.0	1335.6	1188.4	1129.8	1095.3	1033.7	984.1	955.5	946.5	955.5
50°	1497.9	1280.1	1098.3	1003.6	951.0	922.5	871.4	839.8	817.3	811.3	826.3
52.5°	1268.0	1069.7	931.5	847.4	812.8	788.8	752.7	725.7	712.1	706.1	716.7
55°	1062.2	901.4	790.3	718.2	692.6	677.6	646.0	631.0	616.0	614.5	625.0
57.5°	880.4	769.2	667.1	616.0	608.5	585.9	558.9	545.4	537.9	536.4	540.9
60°	733.2	634.0	572.4	527.3	516.8	498.8	483.8	474.8	465.7	462.7	465.7
62.5°	610.0	531.9	482.3	452.2	437.2	432.7	416.2	405.7	404.1	404.1	407.2
65°	503.3	437.2	405.7	381.6	371.1	366.6	354.6	347.1	348.6	348.6	350.1
67.5°	410.2	362.1	333.5	321.5	312.5	311.0	299.0	296.0	293.0	293.0	296.0
70°	326.0	296.0	274.9	268.9	267.4	256.9	252.4	250.9	246.4	247.9	247.9
72.5°	255.4	235.9	223.9	214.8	216.3	210.3	204.3	204.3	201.3	205.8	205.8
75°	189.3	180.3	171.3	168.3	171.3	168.3	163.8	162.3	163.8	162.3	162.3
77.5°	139.7	135.2	132.2	130.7	130.7	124.7	121.7	124.7	118.7	121.7	121.7
80°	97.7	91.6	90.1	87.1	88.6	84.1	85.6	82.6	82.6	82.6	82.6
82.5°	61.6	60.1	60.1	60.1	58.6	58.6	58.6	58.6	58.6	58.6	57.1
85°	37.6	36.1	36.1	36.1	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	15.0	16.5	16.5	18.0	16.5	15.0	15.0	15.0	16.5	16.5	15.0
90°	12.6	13.4	14.2	15.0	15.4	15.6	16.1	16.6	17.1	17.6	17.1
92.5°	12.6	13.4	14.2	15.0	15.4	15.5	15.7	15.8	16.0	16.2	16.0
95°	12.6	13.4	14.2	15.0	15.4	15.4	15.4	15.4	15.4	15.4	15.4
97.5°	13.5	13.9	14.2	14.5	14.7	14.8	14.9	15.1	15.2	15.4	15.2
100°	103.5	79.2	54.9	30.6	18.4	18.1	17.4	16.7	16.1	15.4	16.1
102.5°	172.2	172.5	172.8	173.1	173.3	166.4	152.7	139.0	125.3	111.6	125.3
105°	218.9	218.9	218.9	218.9	218.9	218.8	218.6	218.5	218.3	218.1	218.3
107.5°	267.5	267.7	267.8	268.0	268.1	267.8	267.1	266.4	265.8	265.1	265.8
110°	315.3	314.8	314.3	313.8	313.6	313.7	313.9	314.0	314.2	314.4	314.2

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	362.2	361.5	360.9	360.2	359.9	359.7	359.4	359.1	358.7	358.4	358.7
115°	409.2	408.5	407.9	407.2	406.9	406.4	405.4	404.5	403.5	402.5	403.5
117.5°	455.1	454.1	453.2	452.2	451.7	451.5	451.2	450.9	450.5	450.2	450.5
120°	498.4	498.0	497.7	497.4	497.2	496.8	496.0	495.2	494.4	493.6	494.4
122.5°	540.3	539.9	539.6	539.3	539.1	538.6	537.6	536.7	535.7	534.7	535.7
125°	581.1	580.4	579.8	579.1	578.8	578.6	578.1	577.6	577.1	576.6	577.1
127.5°	618.1	617.8	617.5	617.2	617.0	616.3	615.0	613.7	612.4	611.1	612.4
130°	654.6	654.1	653.6	653.1	652.9	652.5	651.7	650.9	650.1	649.3	650.1
132.5°	688.2	688.2	688.2	688.2	688.2	687.8	687.0	686.1	685.3	684.5	685.3
135°	721.7	721.3	721.0	720.7	720.5	720.0	719.0	718.1	717.1	716.1	717.1
137.5°	752.8	752.8	752.8	752.8	752.8	752.4	751.6	750.8	750.0	749.2	750.0
140°	781.0	781.4	781.7	782.0	782.2	781.7	780.7	779.8	778.8	777.8	778.8
142.5°	809.4	809.4	809.4	809.4	809.4	808.9	807.9	807.0	806.0	805.0	806.0
145°	835.3	835.4	835.6	835.7	835.8	835.3	834.3	833.4	832.4	831.4	832.4
147.5°	858.1	858.2	858.4	858.5	858.6	858.0	856.9	855.8	854.6	853.5	854.6
150°	879.5	879.8	880.1	880.4	880.6	880.0	878.7	877.4	876.1	874.8	876.1
152.5°	898.6	898.9	899.2	899.5	899.7	899.1	898.0	896.9	895.7	894.6	895.7
155°	915.7	916.2	916.7	917.2	917.4	916.7	915.4	914.1	912.8	911.5	912.8
157.5°	930.3	930.8	931.3	931.8	932.0	931.4	930.1	928.8	927.5	926.2	927.5
160°	943.7	944.4	945.0	945.7	946.0	945.3	944.0	942.7	941.4	940.1	941.4
162.5°	955.8	956.8	957.7	958.7	959.2	958.5	957.0	955.5	954.1	952.6	954.1
165°	966.1	967.1	968.0	969.0	969.5	968.8	967.5	966.2	964.9	963.6	964.9
167.5°	974.3	975.5	976.6	977.7	978.3	977.6	976.1	974.6	973.2	971.7	973.2
170°	980.3	981.6	982.9	984.2	984.9	984.2	982.7	981.2	979.8	978.3	979.8
172.5°	985.3	986.5	987.6	988.7	989.3	988.6	987.1	985.6	984.2	982.7	984.2
175°	988.4	989.7	991.0	992.3	993.0	992.3	990.8	989.3	987.9	986.4	987.9
177.5°	990.5	991.6	992.8	993.9	994.5	993.8	992.5	991.2	989.9	988.6	989.9
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1950.1	1939.6	1944.1	1939.6	1935.1	1930.6	1920.1	1905.1	1893.0	1884.0	1882.5
5°	2100.4	2086.9	2077.8	2073.3	2064.3	2052.3	2032.8	2010.2	1983.2	1972.7	1951.6
7.5°	2238.6	2234.1	2213.1	2210.1	2204.0	2181.5	2148.5	2118.4	2083.8	2055.3	2028.3
10°	2369.3	2358.8	2343.8	2322.7	2319.7	2291.2	2259.6	2217.6	2172.5	2145.4	2097.4
12.5°	2450.4	2438.4	2421.9	2408.4	2400.9	2382.8	2339.3	2297.2	2256.6	2207.0	2165.0
15°	2509.0	2494.0	2464.0	2453.4	2444.4	2420.4	2388.8	2345.3	2291.2	2256.6	2196.5
17.5°	2588.7	2570.6	2540.6	2521.1	2504.5	2467.0	2421.9	2363.3	2312.2	2273.2	2219.1
20°	2680.3	2653.3	2614.2	2588.7	2564.6	2521.1	2458.0	2388.8	2315.2	2267.1	2211.6
22.5°	2832.1	2781.0	2719.4	2683.3	2650.3	2575.1	2500.0	2414.4	2331.7	2259.6	2192.0
25°	2979.3	2928.2	2851.6	2802.0	2750.9	2663.8	2564.6	2445.9	2340.8	2256.6	2168.0
27.5°	3116.0	3063.4	2992.8	2932.7	2883.1	2752.4	2621.7	2488.0	2354.3	2238.6	2148.5
30°	3147.6	3125.0	3070.9	3018.4	2973.3	2853.1	2701.3	2531.6	2370.8	2222.1	2121.4
32.5°	2956.8	3012.3	3025.9	3018.4	2989.8	2904.2	2764.4	2585.7	2394.8	2214.6	2076.3
35°	2560.1	2660.8	2764.4	2820.0	2847.1	2859.1	2776.5	2612.7	2411.4	2202.5	2046.3
37.5°	2122.9	2220.6	2384.3	2467.0	2558.6	2678.8	2711.9	2606.7	2403.9	2193.5	1998.2
40°	1744.3	1869.0	2004.2	2079.3	2159.0	2375.3	2539.1	2527.1	2379.8	2160.5	1960.7
42.5°	1419.8	1497.9	1616.6	1699.2	1796.9	2038.8	2258.1	2366.3	2307.7	2119.9	1912.6
45°	1183.9	1244.0	1328.1	1412.3	1472.4	1691.7	1951.6	2128.9	2184.5	2047.8	1839.0
47.5°	997.6	1042.7	1116.3	1168.9	1233.5	1406.3	1631.6	1881.0	1998.2	1945.6	1760.8
50°	854.9	890.9	949.5	982.6	1039.7	1188.4	1359.7	1621.1	1798.4	1804.4	1657.2
52.5°	730.2	766.2	815.8	844.4	878.9	979.6	1152.4	1373.2	1577.5	1652.7	1538.5
55°	635.5	656.6	697.1	719.7	751.2	848.9	958.5	1146.3	1359.7	1482.9	1410.8
57.5°	548.4	570.9	596.5	614.5	637.0	715.1	814.3	955.5	1167.4	1301.1	1277.1
60°	477.8	491.3	515.3	528.8	549.9	601.0	670.1	811.3	979.6	1105.8	1119.3
62.5°	411.7	423.7	440.2	452.2	465.7	506.3	557.4	658.1	805.3	942.0	960.0
65°	354.6	365.1	374.1	384.6	395.1	420.7	464.2	542.4	656.6	784.3	823.3
67.5°	303.5	306.5	320.0	321.5	327.5	347.1	378.6	441.7	524.3	626.5	677.6
70°	253.9	259.9	262.9	267.4	273.4	287.0	312.5	345.6	407.2	489.8	537.9
72.5°	205.8	207.3	211.8	214.8	220.9	231.4	243.4	268.9	308.0	368.1	411.7
75°	163.8	165.3	168.3	169.8	174.3	177.3	183.3	201.3	228.4	264.4	296.0
77.5°	123.2	126.2	129.2	129.2	130.7	133.7	136.7	142.7	156.3	180.3	207.3
80°	84.1	85.6	85.6	87.1	85.6	90.1	94.7	102.2	108.2	115.7	129.2
82.5°	58.6	58.6	58.6	60.1	60.1	61.6	61.6	63.1	64.6	69.1	75.1
85°	36.1	36.1	37.6	34.6	36.1	37.6	37.6	36.1	37.6	39.1	40.6
87.5°	15.0	15.0	16.5	16.5	16.5	16.5	15.0	16.5	15.0	16.5	16.5
90°	16.6	16.1	15.6	15.4	15.0	14.2	13.4	12.6	11.8	10.6	9.5
92.5°	15.8	15.7	15.5	15.4	15.0	14.2	13.4	12.6	11.8	10.8	9.8
95°	15.4	15.4	15.4	15.4	15.0	14.2	13.4	12.6	11.8	18.0	24.2
97.5°	15.1	14.9	14.8	14.7	14.5	14.2	13.9	13.5	13.2	28.7	44.2
100°	16.7	17.4	18.1	18.4	30.6	54.9	79.2	103.5	127.8	127.2	126.5
102.5°	139.0	152.7	166.4	173.3	173.1	172.8	172.5	172.2	171.9	171.6	171.2
105°	218.5	218.6	218.8	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	266.4	267.1	267.8	268.1	268.0	267.8	267.7	267.5	267.3	267.0	266.7
110°	314.0	313.9	313.7	313.6	313.8	314.3	314.8	315.3	315.8	315.5	315.2

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	359.1	359.4	359.7	359.9	360.2	360.9	361.5	362.2	362.8	362.6	362.5
115°	404.5	405.4	406.4	406.9	407.2	407.9	408.5	409.2	409.8	409.6	409.5
117.5°	450.9	451.2	451.5	451.7	452.2	453.2	454.1	455.1	456.1	455.5	454.8
120°	495.2	496.0	496.8	497.2	497.4	497.7	498.0	498.4	498.7	498.2	497.7
122.5°	536.7	537.6	538.6	539.1	539.3	539.6	539.9	540.3	540.6	540.4	540.2
125°	577.6	578.1	578.6	578.8	579.1	579.8	580.4	581.1	581.7	581.7	581.7
127.5°	613.7	615.0	616.3	617.0	617.2	617.5	617.8	618.1	618.4	618.6	618.8
130°	650.9	651.7	652.5	652.9	653.1	653.6	654.1	654.6	655.1	654.9	654.8
132.5°	686.1	687.0	687.8	688.2	688.2	688.2	688.2	688.2	688.2	688.7	689.2
135°	718.1	719.0	720.0	720.5	720.7	721.0	721.3	721.7	722.0	722.3	722.7
137.5°	750.8	751.6	752.4	752.8	752.8	752.8	752.8	752.8	752.8	753.1	753.5
140°	779.8	780.7	781.7	782.2	782.0	781.7	781.4	781.0	780.7	780.9	781.1
142.5°	807.0	807.9	808.9	809.4	809.4	809.4	809.4	809.4	809.4	809.1	808.7
145°	833.4	834.3	835.3	835.8	835.7	835.6	835.4	835.3	835.1	835.1	835.1
147.5°	855.8	856.9	858.0	858.6	858.5	858.4	858.2	858.1	857.9	857.7	857.5
150°	877.4	878.7	880.0	880.6	880.4	880.1	879.8	879.5	879.2	878.9	878.5
152.5°	896.9	898.0	899.1	899.7	899.5	899.2	898.9	898.6	898.3	898.0	897.6
155°	914.1	915.4	916.7	917.4	917.2	916.7	916.2	915.7	915.2	914.9	914.5
157.5°	928.8	930.1	931.4	932.0	931.8	931.3	930.8	930.3	929.8	929.8	929.8
160°	942.7	944.0	945.3	946.0	945.7	945.0	944.4	943.7	943.1	942.9	942.7
162.5°	955.5	957.0	958.5	959.2	958.7	957.7	956.8	955.8	954.8	954.6	954.5
165°	966.2	967.5	968.8	969.5	969.0	968.0	967.1	966.1	965.1	964.9	964.8
167.5°	974.6	976.1	977.6	978.3	977.7	976.6	975.5	974.3	973.2	973.0	972.8
170°	981.2	982.7	984.2	984.9	984.2	982.9	981.6	980.3	979.0	978.8	978.7
172.5°	985.6	987.1	988.6	989.3	988.7	987.6	986.5	985.3	984.2	983.9	983.5
175°	989.3	990.8	992.3	993.0	992.3	991.0	989.7	988.4	987.1	986.9	986.8
177.5°	991.2	992.5	993.8	994.5	993.9	992.8	991.6	990.5	989.3	989.1	989.0
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1878.0	1869.0	1863.0	1861.5	1852.5	1845.0	1836.0	1834.4	1829.9	1817.9	1810.4
5°	1936.6	1915.6	1911.1	1897.5	1875.0	1858.5	1837.5	1825.4	1811.9	1789.4	1771.3
7.5°	1996.7	1968.2	1947.1	1927.6	1896.0	1866.0	1836.0	1811.9	1787.9	1754.8	1727.8
10°	2055.3	2011.7	1986.2	1957.6	1914.1	1869.0	1826.9	1792.4	1753.3	1714.3	1675.2
12.5°	2109.4	2053.8	2016.2	1975.7	1921.6	1866.0	1811.9	1763.8	1723.3	1670.7	1627.1
15°	2142.4	2080.8	2043.3	2004.2	1923.1	1861.5	1798.4	1736.8	1682.7	1627.1	1586.5
17.5°	2162.0	2092.9	2050.8	2014.7	1932.1	1848.0	1766.8	1700.7	1642.1	1576.0	1521.9
20°	2153.0	2085.4	2046.3	2011.7	1915.6	1831.4	1744.3	1667.7	1594.1	1526.5	1469.4
22.5°	2133.4	2062.8	2019.2	1987.7	1902.1	1802.9	1706.7	1624.1	1547.5	1479.9	1415.3
25°	2091.4	2022.2	1984.7	1945.6	1861.5	1766.8	1669.2	1580.5	1499.4	1427.3	1355.2
27.5°	2053.8	1969.7	1930.6	1896.0	1807.4	1723.3	1627.1	1529.5	1446.8	1371.7	1299.6
30°	2010.2	1915.6	1873.5	1826.9	1747.3	1667.7	1571.5	1481.4	1395.7	1316.1	1247.0
32.5°	1963.7	1854.0	1805.9	1753.3	1672.2	1597.1	1515.9	1427.3	1341.7	1263.5	1191.4
35°	1903.6	1786.4	1730.8	1681.2	1597.1	1521.9	1446.8	1373.2	1287.6	1204.9	1135.8
37.5°	1846.5	1717.3	1658.7	1601.6	1512.9	1440.8	1379.2	1310.1	1227.5	1147.8	1081.7
40°	1781.9	1633.1	1573.0	1520.4	1428.8	1349.2	1293.6	1239.5	1167.4	1090.8	1018.6
42.5°	1723.3	1555.0	1491.9	1437.8	1341.7	1266.5	1214.0	1168.9	1105.8	1035.2	961.5
45°	1642.1	1470.9	1406.3	1349.2	1251.5	1180.9	1126.8	1087.7	1038.2	972.1	906.0
47.5°	1567.0	1389.7	1319.1	1250.0	1161.4	1089.3	1039.7	1009.6	976.6	918.0	850.4
50°	1475.4	1296.6	1224.5	1167.4	1066.7	1005.1	955.5	934.5	904.5	848.9	794.8
52.5°	1376.2	1206.4	1138.8	1069.7	976.6	916.5	872.9	848.9	824.8	784.3	733.2
55°	1260.5	1105.8	1042.7	981.1	887.9	832.3	793.3	767.7	754.2	716.7	679.1
57.5°	1149.3	1003.6	945.0	887.9	806.8	743.7	718.2	695.6	676.1	649.0	617.5
60°	1036.7	904.5	841.4	790.3	719.7	662.6	641.5	619.0	604.0	582.9	560.4
62.5°	907.5	794.8	746.7	698.6	638.5	593.5	569.4	551.4	531.9	518.3	498.8
65°	770.7	691.1	644.5	608.5	551.4	510.8	492.8	480.8	464.2	450.7	435.7
67.5°	643.0	579.9	560.4	521.3	477.8	441.7	428.2	413.2	399.6	392.1	378.6
70°	519.8	474.8	455.2	444.7	396.6	372.6	360.6	354.6	338.0	330.5	321.5
72.5°	402.6	386.1	372.6	359.1	327.5	312.5	299.0	293.0	281.0	274.9	271.9
75°	297.5	287.0	279.4	277.9	264.4	249.4	235.9	232.9	223.9	217.9	214.8
77.5°	208.8	205.8	204.3	205.8	196.8	187.8	184.8	181.8	171.3	169.8	169.8
80°	136.7	144.2	144.2	142.7	139.7	138.2	133.7	130.7	124.7	123.2	124.7
82.5°	84.1	88.6	90.1	93.1	91.6	90.1	87.1	85.6	87.1	84.1	85.6
85°	42.1	45.1	51.1	51.1	52.6	52.6	52.6	51.1	48.1	49.6	48.1
87.5°	16.5	18.0	18.0	18.0	16.5	21.0	22.5	22.5	22.5	19.5	19.5
90°	8.3	7.2	6.6	5.9	4.6	3.3	2.0	0.7	2.0	3.3	4.6
92.5°	8.8	7.8	7.3	8.0	9.5	11.0	12.5	14.0	12.5	11.0	9.5
95°	30.4	36.6	39.7	39.9	40.4	40.9	41.4	41.9	41.4	40.9	40.4
97.5°	59.7	75.2	83.0	82.5	81.5	80.6	79.6	78.6	79.6	80.6	81.5
100°	125.9	125.2	124.9	124.7	124.2	123.7	123.2	122.7	123.2	123.7	124.2
102.5°	170.9	170.6	170.4	170.1	169.4	168.8	168.1	167.5	168.1	168.8	169.4
105°	218.9	218.9	218.9	218.6	217.9	217.2	216.6	215.9	216.6	217.2	217.9
107.5°	266.4	266.1	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9	265.9
110°	314.9	314.6	314.4	314.4	314.4	314.4	314.4	314.4	314.4	314.4	314.4

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	362.3	362.2	362.1	361.9	361.4	360.9	360.4	359.9	360.4	360.9	361.4
115°	409.3	409.2	409.1	408.7	407.9	407.0	406.2	405.4	406.2	407.0	407.9
117.5°	454.2	453.5	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2	453.2
120°	497.2	496.7	496.5	496.6	496.7	496.9	497.0	497.2	497.0	496.9	496.7
122.5°	540.1	539.9	539.8	539.4	538.6	537.8	537.0	536.2	537.0	537.8	538.6
125°	581.7	581.7	581.7	581.1	580.0	578.9	577.7	576.6	577.7	578.9	580.0
127.5°	618.9	619.1	619.2	618.8	618.0	617.1	616.3	615.5	616.3	617.1	618.0
130°	654.6	654.5	654.4	654.0	653.2	652.3	651.5	650.7	651.5	652.3	653.2
132.5°	689.7	690.2	690.4	689.9	688.9	688.0	687.0	686.0	687.0	688.0	688.9
135°	723.0	723.3	723.5	723.0	722.0	721.0	720.0	719.0	720.0	721.0	722.0
137.5°	753.8	754.1	754.3	753.8	752.8	751.9	750.9	749.9	750.9	751.9	752.8
140°	781.2	781.4	781.5	781.3	781.0	780.7	780.3	780.0	780.3	780.7	781.0
142.5°	808.4	808.1	807.9	807.8	807.7	807.5	807.4	807.2	807.4	807.5	807.7
145°	835.1	835.1	835.1	834.9	834.6	834.3	833.9	833.6	833.9	834.3	834.6
147.5°	857.4	857.2	857.1	857.1	857.1	857.1	857.1	857.1	857.1	857.1	857.1
150°	878.2	877.9	877.7	877.9	878.2	878.5	878.9	879.2	878.9	878.5	878.2
152.5°	897.3	897.0	896.8	897.2	898.0	898.9	899.7	900.5	899.7	898.9	898.0
155°	914.2	913.9	913.7	914.2	915.2	916.1	917.1	918.1	917.1	916.1	915.2
157.5°	929.8	929.8	929.8	930.0	930.5	931.0	931.5	932.0	931.5	931.0	930.5
160°	942.6	942.4	942.3	942.8	943.8	944.7	945.7	946.7	945.7	944.7	943.8
162.5°	954.3	954.2	954.1	954.6	955.6	956.5	957.5	958.5	957.5	956.5	955.6
165°	964.6	964.5	964.4	964.9	965.9	966.8	967.8	968.8	967.8	966.8	965.9
167.5°	972.7	972.5	972.4	972.9	973.9	974.8	975.8	976.8	975.8	974.8	973.9
170°	978.5	978.4	978.3	978.9	980.0	981.2	982.3	983.5	982.3	981.2	980.0
172.5°	983.2	982.9	982.7	983.3	984.4	985.6	986.7	987.9	986.7	985.6	984.4
175°	986.6	986.5	986.4	986.9	987.9	988.8	989.8	990.8	989.8	988.8	987.9
177.5°	988.8	988.7	988.6	989.1	990.1	991.0	992.0	993.0	992.0	991.0	990.1
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1805.9	1799.9	1795.4	1790.9	1771.3	1750.3	1747.3	1742.8	1733.8	1744.3	1739.8
5°	1759.3	1745.8	1738.3	1718.8	1694.7	1676.7	1661.7	1643.6	1636.1	1630.1	1628.6
7.5°	1702.2	1690.2	1676.7	1657.2	1627.1	1597.1	1574.5	1556.5	1541.5	1534.0	1534.0
10°	1646.6	1631.6	1613.6	1580.5	1552.0	1514.4	1490.4	1472.4	1451.3	1439.3	1428.8
12.5°	1589.6	1573.0	1556.5	1514.4	1481.4	1442.3	1407.8	1385.2	1374.7	1361.2	1343.2
15°	1532.5	1506.9	1490.4	1448.3	1406.3	1367.2	1344.7	1320.6	1296.6	1283.1	1277.1
17.5°	1472.4	1454.3	1427.3	1382.2	1335.6	1301.1	1268.0	1245.5	1217.0	1203.4	1189.9
20°	1418.3	1391.2	1364.2	1319.1	1274.0	1227.5	1194.4	1167.4	1149.3	1138.8	1126.8
22.5°	1353.7	1328.1	1305.6	1257.5	1207.9	1164.4	1128.3	1111.8	1093.8	1077.2	1065.2
25°	1298.1	1272.5	1250.0	1197.4	1143.3	1102.8	1075.7	1054.7	1035.2	1027.7	1015.6
27.5°	1239.5	1215.5	1185.4	1132.8	1084.7	1050.2	1021.6	1002.1	987.1	972.1	963.0
30°	1183.9	1156.9	1129.8	1072.7	1033.7	999.1	972.1	948.0	936.0	928.5	913.5
32.5°	1129.8	1095.3	1072.7	1020.1	982.6	949.5	927.0	906.0	890.9	877.4	865.4
35°	1071.2	1033.7	1011.1	967.6	928.5	895.4	875.9	860.9	842.9	830.8	824.8
37.5°	1015.6	984.1	961.5	916.5	877.4	850.4	829.3	809.8	802.3	785.8	782.8
40°	955.5	928.5	907.5	863.9	827.8	806.8	784.3	766.2	752.7	745.2	734.7
42.5°	901.4	878.9	856.4	815.8	781.3	755.7	739.2	722.7	710.6	698.6	691.1
45°	851.9	827.8	806.8	767.7	733.2	710.6	694.1	674.6	671.6	655.1	647.5
47.5°	799.3	778.3	760.2	719.7	688.1	665.6	646.0	632.5	619.0	613.0	602.5
50°	748.2	727.2	706.1	670.1	641.5	619.0	599.5	584.4	576.9	567.9	558.9
52.5°	692.6	676.1	659.6	622.0	593.5	573.9	557.4	537.9	530.4	522.8	516.8
55°	646.0	622.0	604.0	572.4	546.9	525.8	507.8	492.8	485.3	479.3	471.8
57.5°	582.9	567.9	552.9	524.3	500.3	479.3	461.2	449.2	440.2	435.7	437.2
60°	528.8	512.3	503.3	473.3	449.2	432.7	416.2	404.1	395.1	390.6	389.1
62.5°	471.8	459.7	443.2	422.2	398.1	383.1	371.1	362.1	347.1	345.6	341.0
65°	416.2	407.2	392.1	372.6	353.1	339.5	326.0	314.0	308.0	300.5	296.0
67.5°	362.1	353.1	339.5	323.0	309.5	296.0	284.0	271.9	261.4	255.4	252.4
70°	309.5	302.0	293.0	273.4	256.9	246.4	237.4	229.9	219.4	216.3	214.8
72.5°	258.4	250.9	246.4	229.9	214.8	205.8	196.8	189.3	184.8	183.3	178.8
75°	211.8	204.3	198.3	183.3	174.3	168.3	159.3	156.3	151.7	150.2	148.7
77.5°	165.3	157.8	156.3	145.7	135.2	132.2	129.2	123.2	123.2	123.2	120.2
80°	118.7	117.2	115.7	105.2	100.7	97.7	96.2	91.6	88.6	85.6	84.1
82.5°	79.6	78.1	76.6	72.1	67.6	66.1	64.6	61.6	61.6	63.1	60.1
85°	48.1	45.1	43.6	42.1	39.1	39.1	40.6	39.1	39.1	39.1	37.6
87.5°	18.0	18.0	18.0	18.0	19.5	16.5	18.0	18.0	16.5	16.5	15.0
90°	5.9	6.6	7.2	8.3	9.5	10.6	11.8	12.6	13.4	14.2	15.0
92.5°	8.0	7.3	7.8	8.8	9.8	10.8	11.8	12.6	13.4	14.2	15.0
95°	39.9	39.7	36.6	30.4	24.2	18.0	11.8	12.6	13.4	14.2	15.0
97.5°	82.5	83.0	75.2	59.7	44.2	28.7	13.2	13.5	13.9	14.2	14.5
100°	124.7	124.9	125.2	125.9	126.5	127.2	127.8	103.5	79.2	54.9	30.6
102.5°	170.1	170.4	170.6	170.9	171.2	171.6	171.9	172.2	172.5	172.8	173.1
105°	218.6	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9
107.5°	265.9	265.9	266.1	266.4	266.7	267.0	267.3	267.5	267.7	267.8	268.0
110°	314.4	314.4	314.6	314.9	315.2	315.5	315.8	315.3	314.8	314.3	313.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	361.9	362.1	362.2	362.3	362.5	362.6	362.8	362.2	361.5	360.9	360.2
115°	408.7	409.1	409.2	409.3	409.5	409.6	409.8	409.2	408.5	407.9	407.2
117.5°	453.2	453.2	453.5	454.2	454.8	455.5	456.1	455.1	454.1	453.2	452.2
120°	496.6	496.5	496.7	497.2	497.7	498.2	498.7	498.4	498.0	497.7	497.4
122.5°	539.4	539.8	539.9	540.1	540.2	540.4	540.6	540.3	539.9	539.6	539.3
125°	581.1	581.7	581.7	581.7	581.7	581.7	581.7	581.1	580.4	579.8	579.1
127.5°	618.8	619.2	619.1	618.9	618.8	618.6	618.4	618.1	617.8	617.5	617.2
130°	654.0	654.4	654.5	654.6	654.8	654.9	655.1	654.6	654.1	653.6	653.1
132.5°	689.9	690.4	690.2	689.7	689.2	688.7	688.2	688.2	688.2	688.2	688.2
135°	723.0	723.5	723.3	723.0	722.7	722.3	722.0	721.7	721.3	721.0	720.7
137.5°	753.8	754.3	754.1	753.8	753.5	753.1	752.8	752.8	752.8	752.8	752.8
140°	781.3	781.5	781.4	781.2	781.1	780.9	780.7	781.0	781.4	781.7	782.0
142.5°	807.8	807.9	808.1	808.4	808.7	809.1	809.4	809.4	809.4	809.4	809.4
145°	834.9	835.1	835.1	835.1	835.1	835.1	835.1	835.3	835.4	835.6	835.7
147.5°	857.1	857.1	857.2	857.4	857.5	857.7	857.9	858.1	858.2	858.4	858.5
150°	877.9	877.7	877.9	878.2	878.5	878.9	879.2	879.5	879.8	880.1	880.4
152.5°	897.2	896.8	897.0	897.3	897.6	898.0	898.3	898.6	898.9	899.2	899.5
155°	914.2	913.7	913.9	914.2	914.5	914.9	915.2	915.7	916.2	916.7	917.2
157.5°	930.0	929.8	929.8	929.8	929.8	929.8	929.8	930.3	930.8	931.3	931.8
160°	942.8	942.3	942.4	942.6	942.7	942.9	943.1	943.7	944.4	945.0	945.7
162.5°	954.6	954.1	954.2	954.3	954.5	954.6	954.8	955.8	956.8	957.7	958.7
165°	964.9	964.4	964.5	964.6	964.8	964.9	965.1	966.1	967.1	968.0	969.0
167.5°	972.9	972.4	972.5	972.7	972.8	973.0	973.2	974.3	975.5	976.6	977.7
170°	978.9	978.3	978.4	978.5	978.7	978.8	979.0	980.3	981.6	982.9	984.2
172.5°	983.3	982.7	982.9	983.2	983.5	983.9	984.2	985.3	986.5	987.6	988.7
175°	986.9	986.4	986.5	986.6	986.8	986.9	987.1	988.4	989.7	991.0	992.3
177.5°	989.1	988.6	988.7	988.8	989.0	989.1	989.3	990.5	991.6	992.8	993.9
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1732.3	1735.3	1727.8	1724.8	1718.8	1726.3	1727.8	1726.3	1739.8	1733.8	1736.8
5°	1631.6	1625.6	1621.1	1610.6	1610.6	1612.1	1616.6	1609.1	1613.6	1624.1	1622.6
7.5°	1520.4	1517.4	1518.9	1506.9	1497.9	1500.9	1497.9	1511.4	1518.9	1515.9	1521.9
10°	1419.8	1425.8	1412.3	1406.3	1400.3	1406.3	1404.8	1407.8	1416.8	1422.8	1433.3
12.5°	1338.7	1337.1	1329.6	1323.6	1313.1	1316.1	1325.1	1322.1	1323.6	1337.1	1335.6
15°	1262.0	1253.0	1247.0	1233.5	1236.5	1226.0	1235.0	1245.5	1250.0	1262.0	1269.5
17.5°	1185.4	1183.9	1176.4	1174.9	1158.4	1153.9	1162.9	1165.9	1170.4	1176.4	1186.9
20°	1120.8	1119.3	1108.8	1105.8	1092.3	1101.3	1098.3	1104.3	1107.3	1119.3	1123.8
22.5°	1062.2	1054.7	1051.7	1047.2	1042.7	1041.2	1047.2	1045.7	1056.2	1060.7	1062.2
25°	1008.1	1002.1	1000.6	993.1	990.1	985.6	990.1	994.6	1006.6	1011.1	1017.1
27.5°	958.5	954.0	951.0	945.0	940.5	940.5	943.5	949.5	954.0	957.0	960.0
30°	913.5	910.5	901.4	898.4	893.9	893.9	893.9	896.9	904.5	913.5	918.0
32.5°	866.9	860.9	854.9	854.9	850.4	850.4	851.9	854.9	862.4	863.9	871.4
35°	821.8	815.8	811.3	808.3	809.8	803.8	806.8	811.3	820.3	823.3	827.8
37.5°	778.3	776.7	767.7	763.2	766.2	766.2	764.7	767.7	773.7	779.8	782.8
40°	730.2	727.2	727.2	722.7	724.2	718.2	722.7	725.7	728.7	734.7	739.2
42.5°	688.1	685.1	679.1	680.6	676.1	676.1	679.1	680.6	685.1	692.6	695.6
45°	643.0	643.0	640.0	635.5	637.0	632.5	635.5	637.0	643.0	650.5	647.5
47.5°	599.5	598.0	598.0	592.0	595.0	590.4	595.0	596.5	599.5	604.0	602.5
50°	557.4	552.9	554.4	552.9	551.4	551.4	554.4	554.4	557.4	557.4	561.9
52.5°	513.8	513.8	510.8	512.3	515.3	512.3	516.8	512.3	515.3	516.8	519.8
55°	474.8	471.8	473.3	471.8	477.8	473.3	477.8	474.8	477.8	476.3	479.3
57.5°	432.7	428.2	429.7	428.2	432.7	431.2	435.7	431.2	432.7	434.2	438.7
60°	384.6	384.6	384.6	381.6	386.1	386.1	384.6	384.6	390.6	393.6	392.1
62.5°	339.5	338.0	333.5	332.0	333.5	330.5	336.5	335.0	338.0	341.0	344.1
65°	290.0	287.0	285.5	282.5	282.5	281.0	282.5	288.5	290.0	291.5	299.0
67.5°	249.4	247.9	246.4	241.9	241.9	244.9	244.9	244.9	253.9	249.4	255.4
70°	213.3	210.3	207.3	205.8	205.8	207.3	208.8	210.3	208.8	214.8	216.3
72.5°	178.8	180.3	177.3	177.3	177.3	175.8	175.8	178.8	180.3	178.8	180.3
75°	148.7	148.7	147.2	148.7	148.7	147.2	147.2	150.2	150.2	148.7	153.2
77.5°	120.2	118.7	115.7	112.7	114.2	112.7	114.2	112.7	117.2	121.7	118.7
80°	84.1	82.6	82.6	82.6	84.1	82.6	85.6	82.6	84.1	84.1	85.6
82.5°	60.1	61.6	61.6	60.1	61.6	60.1	61.6	61.6	61.6	60.1	61.6
85°	39.1	39.1	39.1	39.1	37.6	39.1	39.1	39.1	40.6	39.1	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	18.0	16.5	18.0
90°	15.4	15.6	16.1	16.6	17.1	17.6	17.1	16.6	16.1	15.6	15.4
92.5°	15.4	15.5	15.7	15.8	16.0	16.2	16.0	15.8	15.7	15.5	15.4
95°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
97.5°	14.7	14.8	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.7
100°	18.4	18.1	17.4	16.7	16.1	15.4	16.1	16.7	17.4	18.1	18.4
102.5°	173.3	166.4	152.7	139.0	125.3	111.6	125.3	139.0	152.7	166.4	173.3
105°	218.9	218.8	218.6	218.5	218.3	218.1	218.3	218.5	218.6	218.8	218.9
107.5°	268.1	267.8	267.1	266.4	265.8	265.1	265.8	266.4	267.1	267.8	268.1
110°	313.6	313.7	313.9	314.0	314.2	314.4	314.2	314.0	313.9	313.7	313.6

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	359.9	359.7	359.4	359.1	358.7	358.4	358.7	359.1	359.4	359.7	359.9
115°	406.9	406.4	405.4	404.5	403.5	402.5	403.5	404.5	405.4	406.4	406.9
117.5°	451.7	451.5	451.2	450.9	450.5	450.2	450.5	450.9	451.2	451.5	451.7
120°	497.2	496.8	496.0	495.2	494.4	493.6	494.4	495.2	496.0	496.8	497.2
122.5°	539.1	538.6	537.6	536.7	535.7	534.7	535.7	536.7	537.6	538.6	539.1
125°	578.8	578.6	578.1	577.6	577.1	576.6	577.1	577.6	578.1	578.6	578.8
127.5°	617.0	616.3	615.0	613.7	612.4	611.1	612.4	613.7	615.0	616.3	617.0
130°	652.9	652.5	651.7	650.9	650.1	649.3	650.1	650.9	651.7	652.5	652.9
132.5°	688.2	687.8	687.0	686.1	685.3	684.5	685.3	686.1	687.0	687.8	688.2
135°	720.5	720.0	719.0	718.1	717.1	716.1	717.1	718.1	719.0	720.0	720.5
137.5°	752.8	752.4	751.6	750.8	750.0	749.2	750.0	750.8	751.6	752.4	752.8
140°	782.2	781.7	780.7	779.8	778.8	777.8	778.8	779.8	780.7	781.7	782.2
142.5°	809.4	808.9	807.9	807.0	806.0	805.0	806.0	807.0	807.9	808.9	809.4
145°	835.8	835.3	834.3	833.4	832.4	831.4	832.4	833.4	834.3	835.3	835.8
147.5°	858.6	858.0	856.9	855.8	854.6	853.5	854.6	855.8	856.9	858.0	858.6
150°	880.6	880.0	878.7	877.4	876.1	874.8	876.1	877.4	878.7	880.0	880.6
152.5°	899.7	899.1	898.0	896.9	895.7	894.6	895.7	896.9	898.0	899.1	899.7
155°	917.4	916.7	915.4	914.1	912.8	911.5	912.8	914.1	915.4	916.7	917.4
157.5°	932.0	931.4	930.1	928.8	927.5	926.2	927.5	928.8	930.1	931.4	932.0
160°	946.0	945.3	944.0	942.7	941.4	940.1	941.4	942.7	944.0	945.3	946.0
162.5°	959.2	958.5	957.0	955.5	954.1	952.6	954.1	955.5	957.0	958.5	959.2
165°	969.5	968.8	967.5	966.2	964.9	963.6	964.9	966.2	967.5	968.8	969.5
167.5°	978.3	977.6	976.1	974.6	973.2	971.7	973.2	974.6	976.1	977.6	978.3
170°	984.9	984.2	982.7	981.2	979.8	978.3	979.8	981.2	982.7	984.2	984.9
172.5°	989.3	988.6	987.1	985.6	984.2	982.7	984.2	985.6	987.1	988.6	989.3
175°	993.0	992.3	990.8	989.3	987.9	986.4	987.9	989.3	990.8	992.3	993.0
177.5°	994.5	993.8	992.5	991.2	989.9	988.6	989.9	991.2	992.5	993.8	994.5
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1730.8	1738.3	1732.3	1727.8	1739.8	1745.8	1745.8	1756.3	1766.8	1775.9	1777.4
5°	1624.1	1636.1	1639.1	1637.6	1655.7	1664.7	1684.2	1694.7	1709.7	1720.3	1732.3
7.5°	1526.5	1543.0	1544.5	1547.5	1574.5	1589.6	1606.1	1633.1	1654.2	1669.2	1682.7
10°	1428.8	1439.3	1449.8	1463.4	1490.4	1515.9	1540.0	1568.5	1595.6	1610.6	1630.1
12.5°	1355.2	1362.7	1374.7	1383.7	1412.3	1434.8	1466.4	1505.4	1544.5	1556.5	1580.5
15°	1278.6	1283.1	1307.1	1316.1	1340.2	1377.7	1397.2	1434.8	1476.9	1499.4	1526.5
17.5°	1189.9	1217.0	1232.0	1242.5	1272.5	1302.6	1334.1	1373.2	1427.3	1448.3	1467.9
20°	1126.8	1146.3	1162.9	1176.4	1203.4	1248.5	1277.1	1308.6	1359.7	1383.7	1412.3
22.5°	1071.2	1087.7	1102.8	1117.8	1135.8	1176.4	1209.4	1253.0	1304.1	1326.6	1359.7
25°	1018.6	1035.2	1044.2	1062.2	1086.2	1114.8	1153.9	1192.9	1244.0	1269.5	1301.1
27.5°	967.6	984.1	1000.6	1015.6	1032.2	1059.2	1086.2	1135.8	1188.4	1218.5	1245.5
30°	924.0	931.5	946.5	963.0	979.6	1005.1	1036.7	1071.2	1131.3	1158.4	1191.4
32.5°	875.9	889.4	899.9	912.0	933.0	954.0	982.6	1026.1	1074.2	1099.8	1135.8
35°	830.8	842.9	850.4	871.4	884.9	907.5	936.0	975.1	1015.6	1044.2	1075.7
37.5°	787.3	799.3	808.3	820.3	838.3	857.9	887.9	916.5	964.6	988.6	1024.6
40°	742.2	752.7	763.2	776.7	793.3	817.3	835.3	871.4	910.5	937.5	964.6
42.5°	698.6	704.6	716.7	731.7	748.2	769.2	794.8	823.3	862.4	886.4	910.5
45°	652.0	662.6	676.1	686.6	701.6	722.7	745.2	770.7	809.8	833.8	859.4
47.5°	608.5	616.0	625.0	641.5	661.1	676.1	700.1	724.2	760.2	782.8	806.8
50°	563.4	570.9	584.4	595.0	610.0	629.5	652.0	677.6	712.1	727.2	751.2
52.5°	521.3	524.3	537.9	548.4	563.4	585.9	604.0	626.5	659.6	676.1	700.1
55°	479.3	482.3	489.8	500.3	516.8	534.9	554.4	579.9	608.5	623.5	646.0
57.5°	435.7	438.7	446.2	453.7	470.3	486.8	509.3	530.4	558.9	572.4	593.5
60°	392.1	392.1	399.6	410.2	422.2	437.2	456.7	482.3	503.3	519.8	534.9
62.5°	345.6	350.1	354.6	362.1	375.6	393.6	410.2	428.2	453.7	465.7	479.3
65°	299.0	303.5	312.5	320.0	330.5	342.6	363.6	378.6	398.1	411.7	423.7
67.5°	258.4	262.9	268.9	277.9	285.5	299.0	314.0	329.0	350.1	359.1	368.1
70°	216.3	220.9	225.4	237.4	244.9	255.4	265.9	281.0	299.0	305.0	312.5
72.5°	183.3	184.8	190.8	193.8	204.3	213.3	225.4	234.4	247.9	255.4	261.4
75°	154.7	154.7	156.3	159.3	165.3	171.3	180.3	189.3	201.3	205.8	213.3
77.5°	121.7	126.2	124.7	127.7	130.7	133.7	141.2	147.2	159.3	162.3	165.3
80°	87.1	88.6	93.1	97.7	97.7	102.2	106.7	108.2	115.7	120.2	120.2
82.5°	63.1	64.6	63.1	64.6	66.1	67.6	72.1	78.1	78.1	79.6	82.6
85°	39.1	39.1	40.6	42.1	42.1	40.6	43.6	42.1	43.6	46.6	46.6
87.5°	19.5	18.0	18.0	18.0	18.0	18.0	19.5	18.0	19.5	19.5	19.5
90°	15.0	14.2	13.4	12.6	11.8	10.6	9.5	8.3	7.2	6.6	5.9
92.5°	15.0	14.2	13.4	12.6	11.8	10.8	9.8	8.8	7.8	7.3	8.0
95°	15.0	14.2	13.4	12.6	11.8	18.0	24.2	30.4	36.6	39.7	39.9
97.5°	14.5	14.2	13.9	13.5	13.2	28.7	44.2	59.7	75.2	83.0	82.5
100°	30.6	54.9	79.2	103.5	127.8	127.2	126.5	125.9	125.2	124.9	124.7
102.5°	173.1	172.8	172.5	172.2	171.9	171.6	171.2	170.9	170.6	170.4	170.1
105°	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.9	218.6
107.5°	268.0	267.8	267.7	267.5	267.3	267.0	266.7	266.4	266.1	265.9	265.9
110°	313.8	314.3	314.8	315.3	315.8	315.5	315.2	314.9	314.6	314.4	314.4

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	360.2	360.9	361.5	362.2	362.8	362.6	362.5	362.3	362.2	362.1	361.9
115°	407.2	407.9	408.5	409.2	409.8	409.6	409.5	409.3	409.2	409.1	408.7
117.5°	452.2	453.2	454.1	455.1	456.1	455.5	454.8	454.2	453.5	453.2	453.2
120°	497.4	497.7	498.0	498.4	498.7	498.2	497.7	497.2	496.7	496.5	496.6
122.5°	539.3	539.6	539.9	540.3	540.6	540.4	540.2	540.1	539.9	539.8	539.4
125°	579.1	579.8	580.4	581.1	581.7	581.7	581.7	581.7	581.7	581.7	581.1
127.5°	617.2	617.5	617.8	618.1	618.4	618.6	618.8	618.9	619.1	619.2	618.8
130°	653.1	653.6	654.1	654.6	655.1	654.9	654.8	654.6	654.5	654.4	654.0
132.5°	688.2	688.2	688.2	688.2	688.2	688.7	689.2	689.7	690.2	690.4	689.9
135°	720.7	721.0	721.3	721.7	722.0	722.3	722.7	723.0	723.3	723.5	723.0
137.5°	752.8	752.8	752.8	752.8	752.8	753.1	753.5	753.8	754.1	754.3	753.8
140°	782.0	781.7	781.4	781.0	780.7	780.9	781.1	781.2	781.4	781.5	781.3
142.5°	809.4	809.4	809.4	809.4	809.4	809.1	808.7	808.4	808.1	807.9	807.8
145°	835.7	835.6	835.4	835.3	835.1	835.1	835.1	835.1	835.1	835.1	834.9
147.5°	858.5	858.4	858.2	858.1	857.9	857.7	857.5	857.4	857.2	857.1	857.1
150°	880.4	880.1	879.8	879.5	879.2	878.9	878.5	878.2	877.9	877.7	877.9
152.5°	899.5	899.2	898.9	898.6	898.3	898.0	897.6	897.3	897.0	896.8	897.2
155°	917.2	916.7	916.2	915.7	915.2	914.9	914.5	914.2	913.9	913.7	914.2
157.5°	931.8	931.3	930.8	930.3	929.8	929.8	929.8	929.8	929.8	929.8	930.0
160°	945.7	945.0	944.4	943.7	943.1	942.9	942.7	942.6	942.4	942.3	942.8
162.5°	958.7	957.7	956.8	955.8	954.8	954.6	954.5	954.3	954.2	954.1	954.6
165°	969.0	968.0	967.1	966.1	965.1	964.9	964.8	964.6	964.5	964.4	964.9
167.5°	977.7	976.6	975.5	974.3	973.2	973.0	972.8	972.7	972.5	972.4	972.9
170°	984.2	982.9	981.6	980.3	979.0	978.8	978.7	978.5	978.4	978.3	978.9
172.5°	988.7	987.6	986.5	985.3	984.2	983.9	983.5	983.2	982.9	982.7	983.3
175°	992.3	991.0	989.7	988.4	987.1	986.9	986.8	986.6	986.5	986.4	986.9
177.5°	993.9	992.8	991.6	990.5	989.3	989.1	989.0	988.8	988.7	988.6	989.1
180°	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8	990.8

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1829.9	1829.9	1829.9	1829.9
2.5°	1787.9	1801.4	1814.9	1831.4
5°	1751.8	1775.9	1801.4	1825.4
7.5°	1712.8	1747.3	1780.4	1814.9
10°	1669.2	1712.8	1750.3	1798.4
12.5°	1621.1	1667.7	1720.3	1774.4
15°	1573.0	1631.6	1687.2	1748.8
17.5°	1528.0	1583.5	1645.1	1718.8
20°	1473.9	1535.5	1604.6	1682.7
22.5°	1416.8	1484.4	1559.5	1643.6
25°	1368.7	1437.8	1509.9	1598.6
27.5°	1316.1	1388.2	1458.8	1553.5
30°	1256.0	1334.1	1406.3	1503.9
32.5°	1198.9	1277.1	1356.7	1448.3
35°	1143.3	1220.0	1299.6	1392.7
37.5°	1090.8	1159.9	1238.0	1322.1
40°	1041.2	1104.3	1173.4	1250.0
42.5°	978.1	1051.7	1116.3	1171.9
45°	924.0	984.1	1044.2	1089.3
47.5°	860.9	921.0	972.1	1008.1
50°	808.3	856.4	898.4	930.0
52.5°	745.2	790.3	824.8	848.9
55°	683.6	722.7	752.7	769.2
57.5°	628.0	653.6	676.1	691.1
60°	566.4	585.9	605.5	622.0
62.5°	500.3	521.3	531.9	549.9
65°	441.7	455.2	471.8	477.8
67.5°	384.6	392.1	402.6	414.7
70°	324.5	329.0	339.5	356.1
72.5°	271.9	276.4	284.0	290.0
75°	216.3	220.9	226.9	232.9
77.5°	169.8	171.3	174.3	180.3
80°	123.2	127.7	130.7	132.2
82.5°	85.6	87.1	87.1	88.6
85°	54.1	51.1	51.1	52.6
87.5°	19.5	22.5	22.5	25.5
90°	4.6	3.3	2.0	0.7
92.5°	9.5	11.0	12.5	14.0
95°	40.4	40.9	41.4	41.9
97.5°	81.5	80.6	79.6	78.6
100°	124.2	123.7	123.2	122.7
102.5°	169.4	168.8	168.1	167.5
105°	217.9	217.2	216.6	215.9
107.5°	265.9	265.9	265.9	265.9
110°	314.4	314.4	314.4	314.4

TEST NUMBER: P1027148

CATALOG NUMBER: S125RDIP-B1270D850UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	361.4	360.9	360.4	359.9
115°	407.9	407.0	406.2	405.4
117.5°	453.2	453.2	453.2	453.2
120°	496.7	496.9	497.0	497.2
122.5°	538.6	537.8	537.0	536.2
125°	580.0	578.9	577.7	576.6
127.5°	618.0	617.1	616.3	615.5
130°	653.2	652.3	651.5	650.7
132.5°	688.9	688.0	687.0	686.0
135°	722.0	721.0	720.0	719.0
137.5°	752.8	751.9	750.9	749.9
140°	781.0	780.7	780.3	780.0
142.5°	807.7	807.5	807.4	807.2
145°	834.6	834.3	833.9	833.6
147.5°	857.1	857.1	857.1	857.1
150°	878.2	878.5	878.9	879.2
152.5°	898.0	898.9	899.7	900.5
155°	915.2	916.1	917.1	918.1
157.5°	930.5	931.0	931.5	932.0
160°	943.8	944.7	945.7	946.7
162.5°	955.6	956.5	957.5	958.5
165°	965.9	966.8	967.8	968.8
167.5°	973.9	974.8	975.8	976.8
170°	980.0	981.2	982.3	983.5
172.5°	984.4	985.6	986.7	987.9
175°	987.9	988.8	989.8	990.8
177.5°	990.1	991.0	992.0	993.0
180°	990.8	990.8	990.8	990.8

(END OF REPORT)