

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027154

Luminaire Tested: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027154
REPORT IS A COMBINATION OF REPORTS P1005325 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5470.0 lumens
Efficiency: N/A
Efficacy: 131.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	93	89	85	82	82	79	76	73	61	59	58	45	44	43	30	30	29
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	56	68	61	55	51	48	44	40	35	33	31	24	22	21
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	21	20	18
5	65	54	46	40	57	48	42	37	38	33	30	28	25	23	19	18	16
6	59	48	40	35	53	43	37	32	34	29	26	26	22	20	18	16	14
7	55	43	36	30	49	39	32	28	31	26	23	23	20	18	16	14	13
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	15	13	11
9	47	36	28	24	42	32	26	22	26	21	18	19	16	14	14	12	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3480	3480	3480	3480
5°	3476	3921	3476	3014
10°	3457	4407	3445	2606
15°	3420	4662	3396	2268
20°	3374	5033	3344	2051
25°	3315	5697	3278	1861
30°	3255	6055	3206	1726
35°	3177	4980	3132	1599
40°	3039	3382	3013	1486
45°	2858	2431	2854	1374
50°	2671	1870	2684	1270
55°	2462	1520	2457	1171
60°	2267	1246	2256	1040
65°	2040	1038	2053	837
70°	1853	834	1844	696
75°	1565	632	1565	573
80°	1267	385	1254	385
85°	892	203	869	229

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4953 cd/sqm

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.0
10°-20°	152.7	2.8
20°-30°	242.1	4.4
30°-40°	292.5	5.3
40°-50°	260.4	4.8
50°-60°	199.7	3.7
60°-70°	129.7	2.4
70°-80°	62.9	1.2
80°-90°	16.8	0.3
90°-100°	44.9	0.8
100°-110°	298.4	5.5
110°-120°	537.3	9.8
120°-130°	689.7	12.6
130°-140°	741.8	13.6
140°-150°	696.2	12.7
150°-160°	563.1	10.3
160°-170°	364.2	6.7
170°-180°	125.6	2.3
0°-30°	446.8	8.2
0°-40°	739.4	13.5
0°-60°	1199.5	21.9
0°-90°	1409.0	25.8
90°-120°	880.5	16.1
90°-150°	3008.1	55.0
90°-180°	4061.0	74.2
0°-180°	5470.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	543	543	543	543	543	
5°	542	622	542	478	542	51
15°	519	748	515	364	519	146
25°	474	895	469	292	474	219
35°	413	743	408	238	413	257
45°	323	332	323	188	323	249
55°	228	182	228	140	228	205
65°	142	103	143	83	142	142
75°	69	48	69	44	69	74
85°	16	10	15	12	16	18
90°	1	24	1	24	1	4
95°	56	21	56	21	56	68
105°	288	291	288	291	288	305
115°	541	537	541	537	541	536
125°	769	769	769	769	769	687
135°	959	956	959	956	959	740
145°	1112	1109	1112	1109	1112	696
155°	1225	1216	1225	1216	1225	564
165°	1293	1286	1293	1286	1293	365
175°	1322	1316	1322	1316	1322	126
180°	1322	1322	1322	1322	1322	

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	543.5	548.0	549.3	552.9	556.9	557.8	560.0	563.1	564.9	564.5	564.5
5°	541.7	549.3	554.7	560.9	568.5	571.6	574.3	581.0	586.3	589.4	594.8
7.5°	538.6	549.8	558.7	568.0	579.6	585.0	590.8	600.1	610.0	616.2	622.0
10°	533.7	548.0	560.5	574.3	589.9	597.9	605.1	619.3	631.4	639.4	652.8
12.5°	526.6	544.4	561.8	580.1	599.7	608.2	618.0	633.6	650.5	662.1	673.3
15°	519.0	540.4	559.1	581.0	604.6	617.5	630.0	646.5	661.7	674.6	687.5
17.5°	510.1	532.8	556.0	581.0	607.7	620.7	631.4	651.0	667.0	680.0	691.6
20°	499.4	524.8	551.1	578.7	605.9	618.0	628.2	649.6	663.9	677.7	694.2
22.5°	487.8	515.4	543.5	570.7	597.5	610.4	622.4	641.2	656.8	675.5	696.9
25°	474.4	504.7	533.3	560.5	585.9	597.9	608.6	629.1	651.0	674.6	698.7
27.5°	461.0	490.5	518.1	543.1	570.7	581.9	592.6	618.4	644.3	669.3	702.3
30°	446.3	476.2	500.3	523.5	550.2	561.8	575.2	604.6	634.0	667.9	708.1
32.5°	429.8	457.0	479.3	503.4	527.5	541.7	558.7	590.8	624.7	665.2	716.5
35°	413.3	435.2	455.7	478.4	507.4	522.6	539.1	573.0	615.3	663.9	723.7
37.5°	392.4	413.3	429.4	452.6	482.4	500.3	516.8	556.0	604.2	660.8	723.2
40°	371.0	388.8	404.0	428.0	460.6	477.1	494.9	537.7	592.6	651.9	712.5
42.5°	347.8	362.9	379.4	402.6	434.3	450.3	470.8	520.8	576.5	639.4	684.9
45°	323.3	338.0	351.8	375.9	407.5	424.9	447.2	498.5	556.9	613.1	640.3
47.5°	299.2	312.1	326.8	347.8	379.9	399.1	421.8	476.6	530.6	577.9	580.1
50°	276.0	286.3	298.7	320.1	353.6	371.9	395.5	446.8	499.4	531.9	510.1
52.5°	251.9	261.3	274.2	292.9	324.2	345.6	366.1	417.3	461.5	483.3	443.2
55°	228.3	236.3	249.7	270.6	297.8	314.3	335.3	383.0	421.8	422.2	378.5
57.5°	205.1	212.2	223.4	242.1	267.5	286.7	305.9	347.3	373.6	366.1	317.5
60°	184.6	189.1	199.3	217.6	241.2	255.0	275.6	310.3	327.7	313.9	261.7
62.5°	163.2	167.6	175.7	190.4	212.7	227.4	240.3	268.9	280.9	259.9	217.1
65°	141.8	147.1	152.9	164.5	185.5	195.3	206.9	227.8	239.4	214.9	177.9
67.5°	123.1	125.7	131.5	143.6	158.3	167.2	175.2	189.5	191.7	172.1	141.8
70°	105.7	106.6	111.9	119.0	130.2	135.5	142.2	150.7	150.7	134.7	110.6
72.5°	86.1	87.4	91.4	99.0	105.7	108.3	110.6	115.9	115.0	100.3	83.8
75°	69.1	70.0	73.1	76.7	79.4	84.3	86.1	85.2	84.7	72.2	62.9
77.5°	53.5	54.0	56.2	59.3	59.7	61.5	60.2	60.2	56.2	49.0	44.1
80°	39.2	39.7	40.6	41.5	41.5	41.5	41.5	39.2	36.6	32.1	30.8
82.5°	26.3	26.3	26.8	27.6	27.2	26.3	25.4	23.2	21.4	20.1	19.2
85°	15.6	15.6	16.1	15.6	13.8	13.4	12.5	12.0	11.6	11.1	11.1
87.5°	7.6	7.1	6.2	5.4	5.4	5.4	5.4	5.4	5.4	4.9	4.9
90°	1.0	2.7	4.5	6.2	7.9	8.8	9.6	11.1	12.6	14.2	15.7
92.5°	18.6	16.6	14.7	12.7	10.8	9.8	10.5	11.8	13.1	14.4	15.7
95°	55.9	55.2	54.6	53.9	53.2	52.9	48.8	40.5	32.2	24.0	15.7
97.5°	104.9	106.2	107.5	108.8	110.1	110.7	100.4	79.7	59.0	38.3	17.6
100°	163.7	164.3	165.0	165.6	166.3	166.6	167.0	167.9	168.8	169.6	170.5
102.5°	223.4	224.3	225.2	226.1	227.0	227.4	227.6	228.0	228.5	228.9	229.3
105°	288.1	289.0	289.8	290.7	291.6	292.0	292.0	292.0	292.0	292.0	292.0
107.5°	354.8	354.8	354.8	354.8	354.8	354.8	355.0	355.4	355.9	356.3	356.7
110°	419.4	419.4	419.4	419.4	419.4	419.4	419.6	420.1	420.5	421.0	421.4

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	480.2	480.8	481.5	482.1	482.8	483.1	483.2	483.4	483.7	483.9	484.1
115°	541.0	542.1	543.2	544.3	545.4	545.9	546.0	546.2	546.4	546.6	546.8
117.5°	604.7	604.7	604.7	604.7	604.7	604.7	605.1	606.0	606.9	607.7	608.6
120°	663.5	663.3	663.1	662.8	662.6	662.5	662.8	663.5	664.1	664.8	665.4
122.5°	715.4	716.5	717.6	718.7	719.8	720.3	720.4	720.6	720.9	721.1	721.3
125°	769.3	770.8	772.4	773.9	775.4	776.2	776.2	776.2	776.2	776.2	776.2
127.5°	821.3	822.4	823.5	824.6	825.7	826.2	826.1	825.9	825.6	825.4	825.2
130°	868.3	869.4	870.5	871.6	872.7	873.2	873.3	873.5	873.8	874.0	874.2
132.5°	915.3	916.6	917.9	919.2	920.5	921.2	920.9	920.2	919.6	918.9	918.3
135°	959.4	960.7	962.0	963.3	964.6	965.3	965.1	964.7	964.2	963.8	963.4
137.5°	1000.6	1001.9	1003.2	1004.5	1005.8	1006.5	1006.3	1005.8	1005.4	1004.9	1004.5
140°	1040.8	1041.2	1041.6	1042.1	1042.5	1042.7	1042.6	1042.4	1042.2	1042.0	1041.8
142.5°	1077.0	1077.2	1077.4	1077.7	1077.9	1078.0	1078.2	1078.7	1079.1	1079.6	1080.0
145°	1112.3	1112.7	1113.2	1113.6	1114.1	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3
147.5°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.8	1144.0	1144.3	1144.5	1144.7
150°	1173.1	1172.7	1172.2	1171.8	1171.3	1171.1	1171.3	1171.8	1172.2	1172.7	1173.1
152.5°	1201.5	1200.4	1199.3	1198.2	1197.1	1196.6	1196.8	1197.3	1197.7	1198.2	1198.6
155°	1225.0	1223.7	1222.4	1221.1	1219.8	1219.1	1219.3	1219.8	1220.2	1220.7	1221.1
157.5°	1243.6	1243.0	1242.3	1241.7	1241.0	1240.7	1240.7	1240.7	1240.7	1240.7	1240.7
160°	1263.2	1261.9	1260.6	1259.3	1258.0	1257.4	1257.5	1257.7	1257.9	1258.1	1258.3
162.5°	1278.9	1277.6	1276.3	1275.0	1273.7	1273.0	1273.1	1273.3	1273.6	1273.8	1274.0
165°	1292.6	1291.3	1290.0	1288.7	1287.4	1286.8	1286.9	1287.1	1287.3	1287.5	1287.7
167.5°	1303.4	1302.1	1300.8	1299.5	1298.2	1297.5	1297.6	1297.8	1298.1	1298.3	1298.5
170°	1312.2	1310.7	1309.2	1307.7	1306.2	1305.4	1305.5	1305.7	1306.0	1306.2	1306.4
172.5°	1318.1	1316.6	1315.1	1313.6	1312.1	1311.3	1311.5	1311.9	1312.4	1312.8	1313.2
175°	1322.0	1320.7	1319.4	1318.1	1316.8	1316.2	1316.3	1316.5	1316.7	1316.9	1317.1
177.5°	1325.0	1323.7	1322.4	1321.1	1319.8	1319.1	1319.2	1319.4	1319.7	1319.9	1320.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	566.7	569.8	572.5	571.2	576.5	576.1	577.0	578.7	579.2	578.3	576.5
5°	597.5	601.9	609.5	613.5	612.6	616.2	618.0	620.7	623.3	622.4	622.4
7.5°	631.8	638.0	645.6	655.9	657.2	660.3	665.7	665.7	668.8	667.5	667.0
10°	661.7	669.3	681.3	689.3	692.9	694.7	700.0	701.8	705.4	705.8	705.8
12.5°	686.2	699.6	707.6	715.6	717.4	720.1	724.1	726.8	728.1	728.1	726.8
15°	699.1	709.8	719.2	727.7	732.6	734.8	738.8	741.9	743.7	747.7	748.6
17.5°	704.5	717.4	732.6	744.6	753.1	755.3	763.3	766.0	769.6	771.4	773.6
20°	712.1	730.8	749.1	763.8	771.8	777.6	786.1	798.6	802.1	802.1	800.8
22.5°	718.8	742.8	767.8	791.4	798.1	809.7	825.3	838.7	844.0	846.3	844.5
25°	726.8	759.8	792.3	821.7	840.0	848.5	869.5	885.5	891.8	895.3	896.2
27.5°	740.6	782.1	823.5	861.0	879.7	889.5	911.4	925.2	932.8	935.9	933.7
30°	756.2	807.0	855.2	888.6	901.1	913.2	927.4	932.8	931.0	931.0	937.7
32.5°	772.3	824.9	867.7	889.5	894.0	892.2	886.4	870.3	861.0	861.0	866.8
35°	781.2	826.7	848.5	841.4	824.0	813.7	782.1	764.2	744.2	742.8	749.5
37.5°	776.3	795.9	787.0	740.2	716.5	696.9	647.4	627.8	613.1	592.6	624.2
40°	741.9	735.2	688.9	621.6	595.2	567.6	528.4	508.7	488.2	485.1	492.7
42.5°	684.0	644.3	576.5	511.4	484.7	465.0	435.2	416.0	403.1	397.7	406.6
45°	611.7	549.3	481.5	429.8	400.4	390.1	362.9	346.0	336.2	332.2	338.4
47.5°	523.5	460.6	396.4	352.7	335.3	325.0	306.8	292.0	283.6	280.9	283.6
50°	444.5	379.9	325.9	297.8	282.2	273.8	258.6	249.2	242.6	240.8	245.2
52.5°	376.3	317.5	276.4	251.5	241.2	234.1	223.4	215.4	211.3	209.6	212.7
55°	315.2	267.5	234.5	213.1	205.5	201.1	191.7	187.3	182.8	182.4	185.5
57.5°	261.3	228.3	198.0	182.8	180.6	173.9	165.9	161.9	159.6	159.2	160.5
60°	217.6	188.2	169.9	156.5	153.4	148.0	143.6	140.9	138.2	137.3	138.2
62.5°	181.0	157.8	143.1	134.2	129.7	128.4	123.5	120.4	119.9	119.9	120.8
65°	149.4	129.7	120.4	113.3	110.1	108.8	105.2	103.0	103.4	103.4	103.9
67.5°	121.7	107.5	99.0	95.4	92.7	92.3	88.7	87.8	86.9	86.9	87.8
70°	96.8	87.8	81.6	79.8	79.4	76.2	74.9	74.5	73.1	73.6	73.6
72.5°	75.8	70.0	66.4	63.8	64.2	62.4	60.6	60.6	59.7	61.1	61.1
75°	56.2	53.5	50.8	49.9	50.8	49.9	48.6	48.2	48.6	48.2	48.2
77.5°	41.5	40.1	39.2	38.8	38.8	37.0	36.1	37.0	35.2	36.1	36.1
80°	29.0	27.2	26.8	25.9	26.3	25.0	25.4	24.5	24.5	24.5	24.5
82.5°	18.3	17.8	17.8	17.8	17.4	17.4	17.4	17.4	17.4	17.4	16.9
85°	11.1	10.7	10.7	10.7	10.3	10.3	10.3	10.3	10.3	10.3	10.3
87.5°	4.5	4.9	4.9	5.4	4.9	4.5	4.5	4.5	4.9	4.9	4.5
90°	16.8	17.9	19.0	20.1	20.6	20.9	21.6	22.2	22.9	23.5	22.9
92.5°	16.8	17.9	19.0	20.1	20.6	20.7	20.9	21.2	21.4	21.6	21.4
95°	16.8	17.9	19.0	20.1	20.6	20.6	20.6	20.6	20.6	20.6	20.6
97.5°	18.0	18.5	18.9	19.4	19.6	19.7	19.9	20.2	20.4	20.6	20.4
100°	138.1	105.6	73.2	40.7	24.5	24.1	23.2	22.3	21.5	20.6	21.5
102.5°	229.7	230.2	230.6	231.1	231.3	222.2	203.9	185.6	167.3	149.0	167.3
105°	292.0	292.0	292.0	292.0	292.0	291.9	291.7	291.5	291.3	291.1	291.3
107.5°	356.9	357.1	357.4	357.6	357.7	357.3	356.4	355.5	354.7	353.8	354.7
110°	420.8	420.1	419.5	418.8	418.5	418.6	418.8	419.0	419.2	419.4	419.2

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	483.2	482.4	481.5	480.6	480.2	480.0	479.5	479.1	478.6	478.2	478.6
115°	545.9	545.1	544.2	543.3	542.9	542.2	540.9	539.6	538.3	537.0	538.3
117.5°	607.3	606.0	604.7	603.4	602.7	602.5	602.1	601.6	601.2	600.8	601.2
120°	665.0	664.6	664.1	663.7	663.5	663.0	661.9	660.8	659.7	658.6	659.7
122.5°	720.9	720.4	720.0	719.5	719.3	718.7	717.4	716.1	714.8	713.5	714.8
125°	775.3	774.5	773.6	772.7	772.3	772.0	771.3	770.6	770.0	769.3	770.0
127.5°	824.8	824.3	823.9	823.4	823.2	822.3	820.6	818.9	817.1	815.4	817.1
130°	873.5	872.9	872.2	871.5	871.2	870.7	869.6	868.5	867.4	866.3	867.4
132.5°	918.3	918.3	918.3	918.3	918.3	917.8	916.7	915.6	914.5	913.4	914.5
135°	963.0	962.5	962.1	961.6	961.4	960.7	959.4	958.1	956.8	955.5	956.8
137.5°	1004.5	1004.5	1004.5	1004.5	1004.5	1004.0	1002.9	1001.8	1000.7	999.6	1000.7
140°	1042.2	1042.6	1043.1	1043.5	1043.7	1043.0	1041.7	1040.4	1039.1	1037.8	1039.1
142.5°	1080.0	1080.0	1080.0	1080.0	1080.0	1079.3	1078.0	1076.7	1075.4	1074.1	1075.4
145°	1114.5	1114.7	1115.0	1115.2	1115.3	1114.6	1113.3	1112.0	1110.7	1109.4	1110.7
147.5°	1144.9	1145.1	1145.3	1145.5	1145.6	1144.8	1143.3	1141.8	1140.3	1138.8	1140.3
150°	1173.5	1173.9	1174.4	1174.8	1175.0	1174.1	1172.4	1170.7	1168.9	1167.2	1168.9
152.5°	1199.0	1199.4	1199.9	1200.3	1200.5	1199.7	1198.2	1196.7	1195.2	1193.7	1195.2
155°	1221.7	1222.4	1223.0	1223.7	1224.0	1223.1	1221.4	1219.7	1217.9	1216.2	1217.9
157.5°	1241.3	1242.0	1242.6	1243.3	1243.6	1242.7	1241.0	1239.3	1237.5	1235.8	1237.5
160°	1259.2	1260.1	1261.0	1261.9	1262.3	1261.4	1259.7	1257.9	1256.2	1254.4	1256.2
162.5°	1275.3	1276.6	1277.9	1279.2	1279.9	1278.9	1277.0	1275.0	1273.1	1271.1	1273.1
165°	1289.0	1290.3	1291.6	1292.9	1293.6	1292.7	1291.0	1289.3	1287.5	1285.8	1287.5
167.5°	1300.0	1301.6	1303.1	1304.6	1305.4	1304.4	1302.5	1300.5	1298.6	1296.6	1298.6
170°	1308.1	1309.9	1311.6	1313.3	1314.2	1313.2	1311.3	1309.3	1307.4	1305.4	1307.4
172.5°	1314.7	1316.3	1317.8	1319.3	1320.1	1319.1	1317.2	1315.2	1313.3	1311.3	1313.3
175°	1318.9	1320.6	1322.4	1324.1	1325.0	1324.0	1322.1	1320.1	1318.2	1316.2	1318.2
177.5°	1321.6	1323.1	1324.6	1326.1	1326.9	1326.0	1324.3	1322.6	1320.8	1319.1	1320.8
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	578.7	575.6	577.0	575.6	574.3	573.0	569.8	565.4	561.8	559.1	558.7
5°	623.3	619.3	616.6	615.3	612.6	609.1	603.3	596.6	588.6	585.4	579.2
7.5°	664.4	663.0	656.8	655.9	654.1	647.4	637.6	628.7	618.4	610.0	601.9
10°	703.1	700.0	695.6	689.3	688.4	680.0	670.6	658.1	644.7	636.7	622.4
12.5°	727.2	723.7	718.8	714.7	712.5	707.2	694.2	681.7	669.7	655.0	642.5
15°	744.6	740.2	731.2	728.1	725.4	718.3	708.9	696.0	680.0	669.7	651.9
17.5°	768.2	762.9	754.0	748.2	743.3	732.1	718.8	701.4	686.2	674.6	658.6
20°	795.4	787.4	775.8	768.2	761.1	748.2	729.5	708.9	687.1	672.8	656.3
22.5°	840.5	825.3	807.0	796.3	786.5	764.2	741.9	716.5	692.0	670.6	650.5
25°	884.2	869.0	846.3	831.6	816.4	790.5	761.1	725.9	694.7	669.7	643.4
27.5°	924.7	909.1	888.2	870.3	855.6	816.8	778.1	738.4	698.7	664.4	637.6
30°	934.1	927.4	911.4	895.8	882.4	846.7	801.7	751.3	703.6	659.5	629.6
32.5°	877.5	894.0	898.0	895.8	887.3	861.9	820.4	767.4	710.7	657.2	616.2
35°	759.8	789.6	820.4	836.9	844.9	848.5	824.0	775.4	715.6	653.7	607.3
37.5°	630.0	659.0	707.6	732.1	759.3	795.0	804.8	773.6	713.4	651.0	593.0
40°	517.7	554.7	594.8	617.1	640.7	704.9	753.5	750.0	706.3	641.2	581.9
42.5°	421.4	444.5	479.8	504.3	533.3	605.1	670.2	702.3	684.9	629.1	567.6
45°	351.4	369.2	394.2	419.1	437.0	502.1	579.2	631.8	648.3	607.7	545.8
47.5°	296.1	309.4	331.3	346.9	366.1	417.3	484.2	558.2	593.0	577.4	522.6
50°	253.7	264.4	281.8	291.6	308.5	352.7	403.5	481.1	533.7	535.5	491.8
52.5°	216.7	227.4	242.1	250.6	260.8	290.7	342.0	407.5	468.2	490.5	456.6
55°	188.6	194.8	206.9	213.6	222.9	251.9	284.5	340.2	403.5	440.1	418.7
57.5°	162.7	169.4	177.0	182.4	189.1	212.2	241.7	283.6	346.4	386.1	379.0
60°	141.8	145.8	152.9	156.9	163.2	178.4	198.9	240.8	290.7	328.2	332.2
62.5°	122.2	125.7	130.6	134.2	138.2	150.3	165.4	195.3	239.0	279.6	284.9
65°	105.2	108.3	111.0	114.1	117.3	124.8	137.8	161.0	194.8	232.7	244.3
67.5°	90.1	91.0	95.0	95.4	97.2	103.0	112.4	131.1	155.6	185.9	201.1
70°	75.4	77.1	78.0	79.4	81.1	85.2	92.7	102.6	120.8	145.4	159.6
72.5°	61.1	61.5	62.9	63.8	65.5	68.7	72.2	79.8	91.4	109.2	122.2
75°	48.6	49.0	49.9	50.4	51.7	52.6	54.4	59.7	67.8	78.5	87.8
77.5°	36.6	37.5	38.3	38.3	38.8	39.7	40.6	42.4	46.4	53.5	61.5
80°	25.0	25.4	25.4	25.9	25.4	26.8	28.1	30.3	32.1	34.3	38.3
82.5°	17.4	17.4	17.4	17.8	17.8	18.3	18.3	18.7	19.2	20.5	22.3
85°	10.7	10.7	11.1	10.3	10.7	11.1	11.1	10.7	11.1	11.6	12.0
87.5°	4.5	4.5	4.9	4.9	4.9	4.9	4.5	4.9	4.5	4.9	4.9
90°	22.2	21.6	20.9	20.6	20.1	19.0	17.9	16.8	15.7	14.2	12.6
92.5°	21.2	20.9	20.7	20.6	20.1	19.0	17.9	16.8	15.7	14.4	13.1
95°	20.6	20.6	20.6	20.6	20.1	19.0	17.9	16.8	15.7	24.0	32.2
97.5°	20.2	19.9	19.7	19.6	19.4	18.9	18.5	18.0	17.6	38.3	59.0
100°	22.3	23.2	24.1	24.5	40.7	73.2	105.6	138.1	170.5	169.6	168.8
102.5°	185.6	203.9	222.2	231.3	231.1	230.6	230.2	229.7	229.3	228.9	228.5
105°	291.5	291.7	291.9	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0
107.5°	355.5	356.4	357.3	357.7	357.6	357.4	357.1	356.9	356.7	356.3	355.9
110°	419.0	418.8	418.6	418.5	418.8	419.5	420.1	420.8	421.4	421.0	420.5

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	479.1	479.5	480.0	480.2	480.6	481.5	482.4	483.2	484.1	483.9	483.7
115°	539.6	540.9	542.2	542.9	543.3	544.2	545.1	545.9	546.8	546.6	546.4
117.5°	601.6	602.1	602.5	602.7	603.4	604.7	606.0	607.3	608.6	607.7	606.9
120°	660.8	661.9	663.0	663.5	663.7	664.1	664.6	665.0	665.4	664.8	664.1
122.5°	716.1	717.4	718.7	719.3	719.5	720.0	720.4	720.9	721.3	721.1	720.9
125°	770.6	771.3	772.0	772.3	772.7	773.6	774.5	775.3	776.2	776.2	776.2
127.5°	818.9	820.6	822.3	823.2	823.4	823.9	824.3	824.8	825.2	825.4	825.6
130°	868.5	869.6	870.7	871.2	871.5	872.2	872.9	873.5	874.2	874.0	873.8
132.5°	915.6	916.7	917.8	918.3	918.3	918.3	918.3	918.3	918.3	918.9	919.6
135°	958.1	959.4	960.7	961.4	961.6	962.1	962.5	963.0	963.4	963.8	964.2
137.5°	1001.8	1002.9	1004.0	1004.5	1004.5	1004.5	1004.5	1004.5	1004.5	1004.9	1005.4
140°	1040.4	1041.7	1043.0	1043.7	1043.5	1043.1	1042.6	1042.2	1041.8	1042.0	1042.2
142.5°	1076.7	1078.0	1079.3	1080.0	1080.0	1080.0	1080.0	1080.0	1080.0	1079.6	1079.1
145°	1112.0	1113.3	1114.6	1115.3	1115.2	1115.0	1114.7	1114.5	1114.3	1114.3	1114.3
147.5°	1141.8	1143.3	1144.8	1145.6	1145.5	1145.3	1145.1	1144.9	1144.7	1144.5	1144.3
150°	1170.7	1172.4	1174.1	1175.0	1174.8	1174.4	1173.9	1173.5	1173.1	1172.7	1172.2
152.5°	1196.7	1198.2	1199.7	1200.5	1200.3	1199.9	1199.4	1199.0	1198.6	1198.2	1197.7
155°	1219.7	1221.4	1223.1	1224.0	1223.7	1223.0	1222.4	1221.7	1221.1	1220.7	1220.2
157.5°	1239.3	1241.0	1242.7	1243.6	1243.3	1242.6	1242.0	1241.3	1240.7	1240.7	1240.7
160°	1257.9	1259.7	1261.4	1262.3	1261.9	1261.0	1260.1	1259.2	1258.3	1258.1	1257.9
162.5°	1275.0	1277.0	1278.9	1279.9	1279.2	1277.9	1276.6	1275.3	1274.0	1273.8	1273.6
165°	1289.3	1291.0	1292.7	1293.6	1292.9	1291.6	1290.3	1289.0	1287.7	1287.5	1287.3
167.5°	1300.5	1302.5	1304.4	1305.4	1304.6	1303.1	1301.6	1300.0	1298.5	1298.3	1298.1
170°	1309.3	1311.3	1313.2	1314.2	1313.3	1311.6	1309.9	1308.1	1306.4	1306.2	1306.0
172.5°	1315.2	1317.2	1319.1	1320.1	1319.3	1317.8	1316.3	1314.7	1313.2	1312.8	1312.4
175°	1320.1	1322.1	1324.0	1325.0	1324.1	1322.4	1320.6	1318.9	1317.1	1316.9	1316.7
177.5°	1322.6	1324.3	1326.0	1326.9	1326.1	1324.6	1323.1	1321.6	1320.1	1319.9	1319.7
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	557.3	554.7	552.9	552.4	549.8	547.5	544.9	544.4	543.1	539.5	537.3
5°	574.7	568.5	567.2	563.1	556.5	551.5	545.3	541.7	537.7	531.0	525.7
7.5°	592.6	584.1	577.9	572.1	562.7	553.8	544.9	537.7	530.6	520.8	512.8
10°	610.0	597.0	589.4	581.0	568.0	554.7	542.2	531.9	520.3	508.7	497.2
12.5°	626.0	609.5	598.4	586.3	570.3	553.8	537.7	523.5	511.4	495.8	482.9
15°	635.8	617.5	606.4	594.8	570.7	552.4	533.7	515.4	499.4	482.9	470.8
17.5°	641.6	621.1	608.6	597.9	573.4	548.4	524.3	504.7	487.3	467.7	451.7
20°	638.9	618.9	607.3	597.0	568.5	543.5	517.7	494.9	473.1	453.0	436.1
22.5°	633.1	612.2	599.3	589.9	564.5	535.1	506.5	482.0	459.3	439.2	420.0
25°	620.7	600.1	589.0	577.4	552.4	524.3	495.4	469.1	445.0	423.6	402.2
27.5°	609.5	584.5	573.0	562.7	536.4	511.4	482.9	453.9	429.4	407.1	385.7
30°	596.6	568.5	556.0	542.2	518.6	494.9	466.4	439.6	414.2	390.6	370.1
32.5°	582.8	550.2	535.9	520.3	496.3	474.0	449.9	423.6	398.2	375.0	353.6
35°	564.9	530.1	513.6	498.9	474.0	451.7	429.4	407.5	382.1	357.6	337.1
37.5°	548.0	509.6	492.2	475.3	449.0	427.6	409.3	388.8	364.3	340.6	321.0
40°	528.8	484.7	466.8	451.2	424.0	400.4	383.9	367.8	346.4	323.7	302.3
42.5°	511.4	461.5	442.8	426.7	398.2	375.9	360.3	346.9	328.2	307.2	285.4
45°	487.3	436.5	417.3	400.4	371.4	350.5	334.4	322.8	308.1	288.5	268.9
47.5°	465.0	412.4	391.5	371.0	344.7	323.3	308.5	299.6	289.8	272.4	252.4
50°	437.9	384.8	363.4	346.4	316.6	298.3	283.6	277.3	268.4	251.9	235.9
52.5°	408.4	358.0	338.0	317.5	289.8	272.0	259.1	251.9	244.8	232.7	217.6
55°	374.1	328.2	309.4	291.2	263.5	247.0	235.4	227.8	223.8	212.7	201.5
57.5°	341.1	297.8	280.5	263.5	239.4	220.7	213.1	206.4	200.6	192.6	183.3
60°	307.7	268.4	249.7	234.5	213.6	196.6	190.4	183.7	179.2	173.0	166.3
62.5°	269.3	235.9	221.6	207.3	189.5	176.1	169.0	163.6	157.8	153.8	148.0
65°	228.7	205.1	191.3	180.6	163.6	151.6	146.2	142.7	137.8	133.8	129.3
67.5°	190.8	172.1	166.3	154.7	141.8	131.1	127.1	122.6	118.6	116.4	112.4
70°	154.3	140.9	135.1	132.0	117.7	110.6	107.0	105.2	100.3	98.1	95.4
72.5°	119.5	114.6	110.6	106.6	97.2	92.7	88.7	86.9	83.4	81.6	80.7
75°	88.3	85.2	82.9	82.5	78.5	74.0	70.0	69.1	66.4	64.7	63.8
77.5°	62.0	61.1	60.6	61.1	58.4	55.7	54.8	54.0	50.8	50.4	50.4
80°	40.6	42.8	42.8	42.4	41.5	41.0	39.7	38.8	37.0	36.6	37.0
82.5°	25.0	26.3	26.8	27.6	27.2	26.8	25.9	25.4	25.9	25.0	25.4
85°	12.5	13.4	15.2	15.2	15.6	15.6	15.6	15.2	14.3	14.7	14.3
87.5°	4.9	5.4	5.4	5.4	4.9	6.2	6.7	6.7	6.7	5.8	5.8
90°	11.1	9.6	8.8	7.9	6.2	4.5	2.7	1.0	2.7	4.5	6.2
92.5°	11.8	10.5	9.8	10.8	12.7	14.7	16.6	18.6	16.6	14.7	12.7
95°	40.5	48.8	52.9	53.2	53.9	54.6	55.2	55.9	55.2	54.6	53.9
97.5°	79.7	100.4	110.7	110.1	108.8	107.5	106.2	104.9	106.2	107.5	108.8
100°	167.9	167.0	166.6	166.3	165.6	165.0	164.3	163.7	164.3	165.0	165.6
102.5°	228.0	227.6	227.4	227.0	226.1	225.2	224.3	223.4	224.3	225.2	226.1
105°	292.0	292.0	292.0	291.6	290.7	289.8	289.0	288.1	289.0	289.8	290.7
107.5°	355.4	355.0	354.8	354.8	354.8	354.8	354.8	354.8	354.8	354.8	354.8
110°	420.1	419.6	419.4	419.4	419.4	419.4	419.4	419.4	419.4	419.4	419.4

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	483.4	483.2	483.1	482.8	482.1	481.5	480.8	480.2	480.8	481.5	482.1
115°	546.2	546.0	545.9	545.4	544.3	543.2	542.1	541.0	542.1	543.2	544.3
117.5°	606.0	605.1	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7	604.7
120°	663.5	662.8	662.5	662.6	662.8	663.1	663.3	663.5	663.3	663.1	662.8
122.5°	720.6	720.4	720.3	719.8	718.7	717.6	716.5	715.4	716.5	717.6	718.7
125°	776.2	776.2	776.2	775.4	773.9	772.4	770.8	769.3	770.8	772.4	773.9
127.5°	825.9	826.1	826.2	825.7	824.6	823.5	822.4	821.3	822.4	823.5	824.6
130°	873.5	873.3	873.2	872.7	871.6	870.5	869.4	868.3	869.4	870.5	871.6
132.5°	920.2	920.9	921.2	920.5	919.2	917.9	916.6	915.3	916.6	917.9	919.2
135°	964.7	965.1	965.3	964.6	963.3	962.0	960.7	959.4	960.7	962.0	963.3
137.5°	1005.8	1006.3	1006.5	1005.8	1004.5	1003.2	1001.9	1000.6	1001.9	1003.2	1004.5
140°	1042.4	1042.6	1042.7	1042.5	1042.1	1041.6	1041.2	1040.8	1041.2	1041.6	1042.1
142.5°	1078.7	1078.2	1078.0	1077.9	1077.7	1077.4	1077.2	1077.0	1077.2	1077.4	1077.7
145°	1114.3	1114.3	1114.3	1114.1	1113.6	1113.2	1112.7	1112.3	1112.7	1113.2	1113.6
147.5°	1144.0	1143.8	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
150°	1171.8	1171.3	1171.1	1171.3	1171.8	1172.2	1172.7	1173.1	1172.7	1172.2	1171.8
152.5°	1197.3	1196.8	1196.6	1197.1	1198.2	1199.3	1200.4	1201.5	1200.4	1199.3	1198.2
155°	1219.8	1219.3	1219.1	1219.8	1221.1	1222.4	1223.7	1225.0	1223.7	1222.4	1221.1
157.5°	1240.7	1240.7	1240.7	1241.0	1241.7	1242.3	1243.0	1243.6	1243.0	1242.3	1241.7
160°	1257.7	1257.5	1257.4	1258.0	1259.3	1260.6	1261.9	1263.2	1261.9	1260.6	1259.3
162.5°	1273.3	1273.1	1273.0	1273.7	1275.0	1276.3	1277.6	1278.9	1277.6	1276.3	1275.0
165°	1287.1	1286.9	1286.8	1287.4	1288.7	1290.0	1291.3	1292.6	1291.3	1290.0	1288.7
167.5°	1297.8	1297.6	1297.5	1298.2	1299.5	1300.8	1302.1	1303.4	1302.1	1300.8	1299.5
170°	1305.7	1305.5	1305.4	1306.2	1307.7	1309.2	1310.7	1312.2	1310.7	1309.2	1307.7
172.5°	1311.9	1311.5	1311.3	1312.1	1313.6	1315.1	1316.6	1318.1	1316.6	1315.1	1313.6
175°	1316.5	1316.3	1316.2	1316.8	1318.1	1319.4	1320.7	1322.0	1320.7	1319.4	1318.1
177.5°	1319.4	1319.2	1319.1	1319.8	1321.1	1322.4	1323.7	1325.0	1323.7	1322.4	1321.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	535.9	534.2	532.8	531.5	525.7	519.4	518.6	517.2	514.5	517.7	516.3
5°	522.1	518.1	515.9	510.1	502.9	497.6	493.1	487.8	485.6	483.8	483.3
7.5°	505.2	501.6	497.6	491.8	482.9	474.0	467.3	461.9	457.5	455.2	455.2
10°	488.7	484.2	478.9	469.1	460.6	449.4	442.3	437.0	430.7	427.1	424.0
12.5°	471.7	466.8	461.9	449.4	439.6	428.0	417.8	411.1	408.0	404.0	398.6
15°	454.8	447.2	442.3	429.8	417.3	405.7	399.1	391.9	384.8	380.8	379.0
17.5°	437.0	431.6	423.6	410.2	396.4	386.1	376.3	369.6	361.2	357.1	353.1
20°	420.9	412.9	404.9	391.5	378.1	364.3	354.5	346.4	341.1	338.0	334.4
22.5°	401.7	394.2	387.5	373.2	358.5	345.6	334.9	329.9	324.6	319.7	316.1
25°	385.2	377.7	371.0	355.4	339.3	327.3	319.2	313.0	307.2	305.0	301.4
27.5°	367.8	360.7	351.8	336.2	321.9	311.7	303.2	297.4	292.9	288.5	285.8
30°	351.4	343.3	335.3	318.4	306.8	296.5	288.5	281.3	277.8	275.6	271.1
32.5°	335.3	325.0	318.4	302.7	291.6	281.8	275.1	268.9	264.4	260.4	256.8
35°	317.9	306.8	300.1	287.1	275.6	265.7	259.9	255.5	250.1	246.6	244.8
37.5°	301.4	292.0	285.4	272.0	260.4	252.4	246.1	240.3	238.1	233.2	232.3
40°	283.6	275.6	269.3	256.4	245.7	239.4	232.7	227.4	223.4	221.2	218.0
42.5°	267.5	260.8	254.1	242.1	231.9	224.3	219.4	214.5	210.9	207.3	205.1
45°	252.8	245.7	239.4	227.8	217.6	210.9	206.0	200.2	199.3	194.4	192.2
47.5°	237.2	231.0	225.6	213.6	204.2	197.5	191.7	187.7	183.7	181.9	178.8
50°	222.0	215.8	209.6	198.9	190.4	183.7	177.9	173.4	171.2	168.5	165.9
52.5°	205.5	200.6	195.7	184.6	176.1	170.3	165.4	159.6	157.4	155.2	153.4
55°	191.7	184.6	179.2	169.9	162.3	156.1	150.7	146.2	144.0	142.2	140.0
57.5°	173.0	168.5	164.1	155.6	148.5	142.2	136.9	133.3	130.6	129.3	129.7
60°	156.9	152.0	149.4	140.5	133.3	128.4	123.5	119.9	117.3	115.9	115.5
62.5°	140.0	136.4	131.5	125.3	118.2	113.7	110.1	107.5	103.0	102.6	101.2
65°	123.5	120.8	116.4	110.6	104.8	100.8	96.8	93.2	91.4	89.2	87.8
67.5°	107.5	104.8	100.8	95.9	91.9	87.8	84.3	80.7	77.6	75.8	74.9
70°	91.9	89.6	86.9	81.1	76.2	73.1	70.4	68.2	65.1	64.2	63.8
72.5°	76.7	74.5	73.1	68.2	63.8	61.1	58.4	56.2	54.8	54.4	53.1
75°	62.9	60.6	58.9	54.4	51.7	49.9	47.3	46.4	45.0	44.6	44.1
77.5°	49.0	46.8	46.4	43.2	40.1	39.2	38.3	36.6	36.6	36.6	35.7
80°	35.2	34.8	34.3	31.2	29.9	29.0	28.5	27.2	26.3	25.4	25.0
82.5°	23.6	23.2	22.7	21.4	20.1	19.6	19.2	18.3	18.3	18.7	17.8
85°	14.3	13.4	12.9	12.5	11.6	11.6	12.0	11.6	11.6	11.6	11.1
87.5°	5.4	5.4	5.4	5.4	5.8	4.9	5.4	5.4	4.9	4.9	4.5
90°	7.9	8.8	9.6	11.1	12.6	14.2	15.7	16.8	17.9	19.0	20.1
92.5°	10.8	9.8	10.5	11.8	13.1	14.4	15.7	16.8	17.9	19.0	20.1
95°	53.2	52.9	48.8	40.5	32.2	24.0	15.7	16.8	17.9	19.0	20.1
97.5°	110.1	110.7	100.4	79.7	59.0	38.3	17.6	18.0	18.5	18.9	19.4
100°	166.3	166.6	167.0	167.9	168.8	169.6	170.5	138.1	105.6	73.2	40.7
102.5°	227.0	227.4	227.6	228.0	228.5	228.9	229.3	229.7	230.2	230.6	231.1
105°	291.6	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0
107.5°	354.8	354.8	355.0	355.4	355.9	356.3	356.7	356.9	357.1	357.4	357.6
110°	419.4	419.4	419.6	420.1	420.5	421.0	421.4	420.8	420.1	419.5	418.8

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	482.8	483.1	483.2	483.4	483.7	483.9	484.1	483.2	482.4	481.5	480.6
115°	545.4	545.9	546.0	546.2	546.4	546.6	546.8	545.9	545.1	544.2	543.3
117.5°	604.7	604.7	605.1	606.0	606.9	607.7	608.6	607.3	606.0	604.7	603.4
120°	662.6	662.5	662.8	663.5	664.1	664.8	665.4	665.0	664.6	664.1	663.7
122.5°	719.8	720.3	720.4	720.6	720.9	721.1	721.3	720.9	720.4	720.0	719.5
125°	775.4	776.2	776.2	776.2	776.2	776.2	776.2	775.3	774.5	773.6	772.7
127.5°	825.7	826.2	826.1	825.9	825.6	825.4	825.2	824.8	824.3	823.9	823.4
130°	872.7	873.2	873.3	873.5	873.8	874.0	874.2	873.5	872.9	872.2	871.5
132.5°	920.5	921.2	920.9	920.2	919.6	918.9	918.3	918.3	918.3	918.3	918.3
135°	964.6	965.3	965.1	964.7	964.2	963.8	963.4	963.0	962.5	962.1	961.6
137.5°	1005.8	1006.5	1006.3	1005.8	1005.4	1004.9	1004.5	1004.5	1004.5	1004.5	1004.5
140°	1042.5	1042.7	1042.6	1042.4	1042.2	1042.0	1041.8	1042.2	1042.6	1043.1	1043.5
142.5°	1077.9	1078.0	1078.2	1078.7	1079.1	1079.6	1080.0	1080.0	1080.0	1080.0	1080.0
145°	1114.1	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3	1114.5	1114.7	1115.0	1115.2
147.5°	1143.7	1143.7	1143.8	1144.0	1144.3	1144.5	1144.7	1144.9	1145.1	1145.3	1145.5
150°	1171.3	1171.1	1171.3	1171.8	1172.2	1172.7	1173.1	1173.5	1173.9	1174.4	1174.8
152.5°	1197.1	1196.6	1196.8	1197.3	1197.7	1198.2	1198.6	1199.0	1199.4	1199.9	1200.3
155°	1219.8	1219.1	1219.3	1219.8	1220.2	1220.7	1221.1	1221.7	1222.4	1223.0	1223.7
157.5°	1241.0	1240.7	1240.7	1240.7	1240.7	1240.7	1240.7	1241.3	1242.0	1242.6	1243.3
160°	1258.0	1257.4	1257.5	1257.7	1257.9	1258.1	1258.3	1259.2	1260.1	1261.0	1261.9
162.5°	1273.7	1273.0	1273.1	1273.3	1273.6	1273.8	1274.0	1275.3	1276.6	1277.9	1279.2
165°	1287.4	1286.8	1286.9	1287.1	1287.3	1287.5	1287.7	1289.0	1290.3	1291.6	1292.9
167.5°	1298.2	1297.5	1297.6	1297.8	1298.1	1298.3	1298.5	1300.0	1301.6	1303.1	1304.6
170°	1306.2	1305.4	1305.5	1305.7	1306.0	1306.2	1306.4	1308.1	1309.9	1311.6	1313.3
172.5°	1312.1	1311.3	1311.5	1311.9	1312.4	1312.8	1313.2	1314.7	1316.3	1317.8	1319.3
175°	1316.8	1316.2	1316.3	1316.5	1316.7	1316.9	1317.1	1318.9	1320.6	1322.4	1324.1
177.5°	1319.8	1319.1	1319.2	1319.4	1319.7	1319.9	1320.1	1321.6	1323.1	1324.6	1326.1
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	514.1	515.0	512.8	511.9	510.1	512.3	512.8	512.3	516.3	514.5	515.4
5°	484.2	482.4	481.1	478.0	478.0	478.4	479.8	477.5	478.9	482.0	481.5
7.5°	451.2	450.3	450.8	447.2	444.5	445.4	444.5	448.6	450.8	449.9	451.7
10°	421.4	423.1	419.1	417.3	415.6	417.3	416.9	417.8	420.5	422.2	425.4
12.5°	397.3	396.8	394.6	392.8	389.7	390.6	393.3	392.4	392.8	396.8	396.4
15°	374.5	371.9	370.1	366.1	367.0	363.8	366.5	369.6	371.0	374.5	376.8
17.5°	351.8	351.4	349.1	348.7	343.8	342.4	345.1	346.0	347.3	349.1	352.2
20°	332.6	332.2	329.1	328.2	324.2	326.8	325.9	327.7	328.6	332.2	333.5
22.5°	315.2	313.0	312.1	310.8	309.4	309.0	310.8	310.3	313.5	314.8	315.2
25°	299.2	297.4	297.0	294.7	293.8	292.5	293.8	295.2	298.7	300.1	301.9
27.5°	284.5	283.1	282.2	280.5	279.1	279.1	280.0	281.8	283.1	284.0	284.9
30°	271.1	270.2	267.5	266.6	265.3	265.3	265.3	266.2	268.4	271.1	272.4
32.5°	257.3	255.5	253.7	253.7	252.4	252.4	252.8	253.7	255.9	256.4	258.6
35°	243.9	242.1	240.8	239.9	240.3	238.5	239.4	240.8	243.4	244.3	245.7
37.5°	231.0	230.5	227.8	226.5	227.4	227.4	227.0	227.8	229.6	231.4	232.3
40°	216.7	215.8	215.8	214.5	214.9	213.1	214.5	215.4	216.2	218.0	219.4
42.5°	204.2	203.3	201.5	202.0	200.6	200.6	201.5	202.0	203.3	205.5	206.4
45°	190.8	190.8	189.9	188.6	189.1	187.7	188.6	189.1	190.8	193.1	192.2
47.5°	177.9	177.5	177.5	175.7	176.6	175.2	176.6	177.0	177.9	179.2	178.8
50°	165.4	164.1	164.5	164.1	163.6	163.6	164.5	164.5	165.4	165.4	166.8
52.5°	152.5	152.5	151.6	152.0	152.9	152.0	153.4	152.0	152.9	153.4	154.3
55°	140.9	140.0	140.5	140.0	141.8	140.5	141.8	140.9	141.8	141.3	142.2
57.5°	128.4	127.1	127.5	127.1	128.4	128.0	129.3	128.0	128.4	128.9	130.2
60°	114.1	114.1	114.1	113.3	114.6	114.6	114.1	114.1	115.9	116.8	116.4
62.5°	100.8	100.3	99.0	98.5	99.0	98.1	99.9	99.4	100.3	101.2	102.1
65°	86.1	85.2	84.7	83.8	83.8	83.4	83.8	85.6	86.1	86.5	88.7
67.5°	74.0	73.6	73.1	71.8	71.8	72.7	72.7	72.7	75.4	74.0	75.8
70°	63.3	62.4	61.5	61.1	61.1	61.5	62.0	62.4	62.0	63.8	64.2
72.5°	53.1	53.5	52.6	52.6	52.6	52.2	52.2	53.1	53.5	53.1	53.5
75°	44.1	44.1	43.7	44.1	44.1	43.7	43.7	44.6	44.6	44.1	45.5
77.5°	35.7	35.2	34.3	33.4	33.9	33.4	33.9	33.4	34.8	36.1	35.2
80°	25.0	24.5	24.5	24.5	25.0	24.5	25.4	24.5	25.0	25.0	25.4
82.5°	17.8	18.3	18.3	17.8	18.3	17.8	18.3	18.3	18.3	17.8	18.3
85°	11.6	11.6	11.6	11.6	11.1	11.6	11.6	11.6	12.0	11.6	12.0
87.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	5.4	4.9	5.4
90°	20.6	20.9	21.6	22.2	22.9	23.5	22.9	22.2	21.6	20.9	20.6
92.5°	20.6	20.7	20.9	21.2	21.4	21.6	21.4	21.2	20.9	20.7	20.6
95°	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6	20.6
97.5°	19.6	19.7	19.9	20.2	20.4	20.6	20.4	20.2	19.9	19.7	19.6
100°	24.5	24.1	23.2	22.3	21.5	20.6	21.5	22.3	23.2	24.1	24.5
102.5°	231.3	222.2	203.9	185.6	167.3	149.0	167.3	185.6	203.9	222.2	231.3
105°	292.0	291.9	291.7	291.5	291.3	291.1	291.3	291.5	291.7	291.9	292.0
107.5°	357.7	357.3	356.4	355.5	354.7	353.8	354.7	355.5	356.4	357.3	357.7
110°	418.5	418.6	418.8	419.0	419.2	419.4	419.2	419.0	418.8	418.6	418.5

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	480.2	480.0	479.5	479.1	478.6	478.2	478.6	479.1	479.5	480.0	480.2
115°	542.9	542.2	540.9	539.6	538.3	537.0	538.3	539.6	540.9	542.2	542.9
117.5°	602.7	602.5	602.1	601.6	601.2	600.8	601.2	601.6	602.1	602.5	602.7
120°	663.5	663.0	661.9	660.8	659.7	658.6	659.7	660.8	661.9	663.0	663.5
122.5°	719.3	718.7	717.4	716.1	714.8	713.5	714.8	716.1	717.4	718.7	719.3
125°	772.3	772.0	771.3	770.6	770.0	769.3	770.0	770.6	771.3	772.0	772.3
127.5°	823.2	822.3	820.6	818.9	817.1	815.4	817.1	818.9	820.6	822.3	823.2
130°	871.2	870.7	869.6	868.5	867.4	866.3	867.4	868.5	869.6	870.7	871.2
132.5°	918.3	917.8	916.7	915.6	914.5	913.4	914.5	915.6	916.7	917.8	918.3
135°	961.4	960.7	959.4	958.1	956.8	955.5	956.8	958.1	959.4	960.7	961.4
137.5°	1004.5	1004.0	1002.9	1001.8	1000.7	999.6	1000.7	1001.8	1002.9	1004.0	1004.5
140°	1043.7	1043.0	1041.7	1040.4	1039.1	1037.8	1039.1	1040.4	1041.7	1043.0	1043.7
142.5°	1080.0	1079.3	1078.0	1076.7	1075.4	1074.1	1075.4	1076.7	1078.0	1079.3	1080.0
145°	1115.3	1114.6	1113.3	1112.0	1110.7	1109.4	1110.7	1112.0	1113.3	1114.6	1115.3
147.5°	1145.6	1144.8	1143.3	1141.8	1140.3	1138.8	1140.3	1141.8	1143.3	1144.8	1145.6
150°	1175.0	1174.1	1172.4	1170.7	1168.9	1167.2	1168.9	1170.7	1172.4	1174.1	1175.0
152.5°	1200.5	1199.7	1198.2	1196.7	1195.2	1193.7	1195.2	1196.7	1198.2	1199.7	1200.5
155°	1224.0	1223.1	1221.4	1219.7	1217.9	1216.2	1217.9	1219.7	1221.4	1223.1	1224.0
157.5°	1243.6	1242.7	1241.0	1239.3	1237.5	1235.8	1237.5	1239.3	1241.0	1242.7	1243.6
160°	1262.3	1261.4	1259.7	1257.9	1256.2	1254.4	1256.2	1257.9	1259.7	1261.4	1262.3
162.5°	1279.9	1278.9	1277.0	1275.0	1273.1	1271.1	1273.1	1275.0	1277.0	1278.9	1279.9
165°	1293.6	1292.7	1291.0	1289.3	1287.5	1285.8	1287.5	1289.3	1291.0	1292.7	1293.6
167.5°	1305.4	1304.4	1302.5	1300.5	1298.6	1296.6	1298.6	1300.5	1302.5	1304.4	1305.4
170°	1314.2	1313.2	1311.3	1309.3	1307.4	1305.4	1307.4	1309.3	1311.3	1313.2	1314.2
172.5°	1320.1	1319.1	1317.2	1315.2	1313.3	1311.3	1313.3	1315.2	1317.2	1319.1	1320.1
175°	1325.0	1324.0	1322.1	1320.1	1318.2	1316.2	1318.2	1320.1	1322.1	1324.0	1325.0
177.5°	1326.9	1326.0	1324.3	1322.6	1320.8	1319.1	1320.8	1322.6	1324.3	1326.0	1326.9
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1	543.1
2.5°	513.6	515.9	514.1	512.8	516.3	518.1	518.1	521.2	524.3	527.0	527.5
5°	482.0	485.6	486.5	486.0	491.4	494.0	499.8	502.9	507.4	510.5	514.1
7.5°	453.0	457.9	458.4	459.3	467.3	471.7	476.6	484.7	490.9	495.4	499.4
10°	424.0	427.1	430.3	434.3	442.3	449.9	457.0	465.5	473.5	478.0	483.8
12.5°	402.2	404.4	408.0	410.7	419.1	425.8	435.2	446.8	458.4	461.9	469.1
15°	379.4	380.8	387.9	390.6	397.7	408.9	414.7	425.8	438.3	445.0	453.0
17.5°	353.1	361.2	365.6	368.7	377.7	386.6	395.9	407.5	423.6	429.8	435.6
20°	334.4	340.2	345.1	349.1	357.1	370.5	379.0	388.4	403.5	410.7	419.1
22.5°	317.9	322.8	327.3	331.7	337.1	349.1	358.9	371.9	387.0	393.7	403.5
25°	302.3	307.2	309.9	315.2	322.4	330.8	342.4	354.0	369.2	376.8	386.1
27.5°	287.1	292.0	297.0	301.4	306.3	314.3	322.4	337.1	352.7	361.6	369.6
30°	274.2	276.4	280.9	285.8	290.7	298.3	307.7	317.9	335.7	343.8	353.6
32.5°	259.9	264.0	267.1	270.6	276.9	283.1	291.6	304.5	318.8	326.4	337.1
35°	246.6	250.1	252.4	258.6	262.6	269.3	277.8	289.4	301.4	309.9	319.2
37.5°	233.6	237.2	239.9	243.4	248.8	254.6	263.5	272.0	286.3	293.4	304.1
40°	220.3	223.4	226.5	230.5	235.4	242.6	247.9	258.6	270.2	278.2	286.3
42.5°	207.3	209.1	212.7	217.1	222.0	228.3	235.9	244.3	255.9	263.1	270.2
45°	193.5	196.6	200.6	203.8	208.2	214.5	221.2	228.7	240.3	247.5	255.0
47.5°	180.6	182.8	185.5	190.4	196.2	200.6	207.8	214.9	225.6	232.3	239.4
50°	167.2	169.4	173.4	176.6	181.0	186.8	193.5	201.1	211.3	215.8	222.9
52.5°	154.7	155.6	159.6	162.7	167.2	173.9	179.2	185.9	195.7	200.6	207.8
55°	142.2	143.1	145.4	148.5	153.4	158.7	164.5	172.1	180.6	185.0	191.7
57.5°	129.3	130.2	132.4	134.7	139.6	144.5	151.2	157.4	165.9	169.9	176.1
60°	116.4	116.4	118.6	121.7	125.3	129.7	135.5	143.1	149.4	154.3	158.7
62.5°	102.6	103.9	105.2	107.5	111.5	116.8	121.7	127.1	134.7	138.2	142.2
65°	88.7	90.1	92.7	95.0	98.1	101.7	107.9	112.4	118.2	122.2	125.7
67.5°	76.7	78.0	79.8	82.5	84.7	88.7	93.2	97.6	103.9	106.6	109.2
70°	64.2	65.5	66.9	70.4	72.7	75.8	78.9	83.4	88.7	90.5	92.7
72.5°	54.4	54.8	56.6	57.5	60.6	63.3	66.9	69.6	73.6	75.8	77.6
75°	45.9	45.9	46.4	47.3	49.0	50.8	53.5	56.2	59.7	61.1	63.3
77.5°	36.1	37.5	37.0	37.9	38.8	39.7	41.9	43.7	47.3	48.2	49.0
80°	25.9	26.3	27.6	29.0	29.0	30.3	31.7	32.1	34.3	35.7	35.7
82.5°	18.7	19.2	18.7	19.2	19.6	20.1	21.4	23.2	23.2	23.6	24.5
85°	11.6	11.6	12.0	12.5	12.5	12.0	12.9	12.5	12.9	13.8	13.8
87.5°	5.8	5.4	5.4	5.4	5.4	5.4	5.8	5.4	5.8	5.8	5.8
90°	20.1	19.0	17.9	16.8	15.7	14.2	12.6	11.1	9.6	8.8	7.9
92.5°	20.1	19.0	17.9	16.8	15.7	14.4	13.1	11.8	10.5	9.8	10.8
95°	20.1	19.0	17.9	16.8	15.7	24.0	32.2	40.5	48.8	52.9	53.2
97.5°	19.4	18.9	18.5	18.0	17.6	38.3	59.0	79.7	100.4	110.7	110.1
100°	40.7	73.2	105.6	138.1	170.5	169.6	168.8	167.9	167.0	166.6	166.3
102.5°	231.1	230.6	230.2	229.7	229.3	228.9	228.5	228.0	227.6	227.4	227.0
105°	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0	292.0	291.6
107.5°	357.6	357.4	357.1	356.9	356.7	356.3	355.9	355.4	355.0	354.8	354.8
110°	418.8	419.5	420.1	420.8	421.4	421.0	420.5	420.1	419.6	419.4	419.4

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	480.6	481.5	482.4	483.2	484.1	483.9	483.7	483.4	483.2	483.1	482.8
115°	543.3	544.2	545.1	545.9	546.8	546.6	546.4	546.2	546.0	545.9	545.4
117.5°	603.4	604.7	606.0	607.3	608.6	607.7	606.9	606.0	605.1	604.7	604.7
120°	663.7	664.1	664.6	665.0	665.4	664.8	664.1	663.5	662.8	662.5	662.6
122.5°	719.5	720.0	720.4	720.9	721.3	721.1	720.9	720.6	720.4	720.3	719.8
125°	772.7	773.6	774.5	775.3	776.2	776.2	776.2	776.2	776.2	776.2	775.4
127.5°	823.4	823.9	824.3	824.8	825.2	825.4	825.6	825.9	826.1	826.2	825.7
130°	871.5	872.2	872.9	873.5	874.2	874.0	873.8	873.5	873.3	873.2	872.7
132.5°	918.3	918.3	918.3	918.3	918.3	918.9	919.6	920.2	920.9	921.2	920.5
135°	961.6	962.1	962.5	963.0	963.4	963.8	964.2	964.7	965.1	965.3	964.6
137.5°	1004.5	1004.5	1004.5	1004.5	1004.5	1004.9	1005.4	1005.8	1006.3	1006.5	1005.8
140°	1043.5	1043.1	1042.6	1042.2	1041.8	1042.0	1042.2	1042.4	1042.6	1042.7	1042.5
142.5°	1080.0	1080.0	1080.0	1080.0	1080.0	1079.6	1079.1	1078.7	1078.2	1078.0	1077.9
145°	1115.2	1115.0	1114.7	1114.5	1114.3	1114.3	1114.3	1114.3	1114.3	1114.3	1114.1
147.5°	1145.5	1145.3	1145.1	1144.9	1144.7	1144.5	1144.3	1144.0	1143.8	1143.7	1143.7
150°	1174.8	1174.4	1173.9	1173.5	1173.1	1172.7	1172.2	1171.8	1171.3	1171.1	1171.3
152.5°	1200.3	1199.9	1199.4	1199.0	1198.6	1198.2	1197.7	1197.3	1196.8	1196.6	1197.1
155°	1223.7	1223.0	1222.4	1221.7	1221.1	1220.7	1220.2	1219.8	1219.3	1219.1	1219.8
157.5°	1243.3	1242.6	1242.0	1241.3	1240.7	1240.7	1240.7	1240.7	1240.7	1240.7	1241.0
160°	1261.9	1261.0	1260.1	1259.2	1258.3	1258.1	1257.9	1257.7	1257.5	1257.4	1258.0
162.5°	1279.2	1277.9	1276.6	1275.3	1274.0	1273.8	1273.6	1273.3	1273.1	1273.0	1273.7
165°	1292.9	1291.6	1290.3	1289.0	1287.7	1287.5	1287.3	1287.1	1286.9	1286.8	1287.4
167.5°	1304.6	1303.1	1301.6	1300.0	1298.5	1298.3	1298.1	1297.8	1297.6	1297.5	1298.2
170°	1313.3	1311.6	1309.9	1308.1	1306.4	1306.2	1306.0	1305.7	1305.5	1305.4	1306.2
172.5°	1319.3	1317.8	1316.3	1314.7	1313.2	1312.8	1312.4	1311.9	1311.5	1311.3	1312.1
175°	1324.1	1322.4	1320.6	1318.9	1317.1	1316.9	1316.7	1316.5	1316.3	1316.2	1316.8
177.5°	1326.1	1324.6	1323.1	1321.6	1320.1	1319.9	1319.7	1319.4	1319.2	1319.1	1319.8
180°	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0	1322.0

TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	543.1	543.1	543.1	543.1
2.5°	530.6	534.6	538.6	543.5
5°	519.9	527.0	534.6	541.7
7.5°	508.3	518.6	528.4	538.6
10°	495.4	508.3	519.4	533.7
12.5°	481.1	494.9	510.5	526.6
15°	466.8	484.2	500.7	519.0
17.5°	453.5	470.0	488.2	510.1
20°	437.4	455.7	476.2	499.4
22.5°	420.5	440.5	462.8	487.8
25°	406.2	426.7	448.1	474.4
27.5°	390.6	412.0	432.9	461.0
30°	372.8	395.9	417.3	446.3
32.5°	355.8	379.0	402.6	429.8
35°	339.3	362.1	385.7	413.3
37.5°	323.7	344.2	367.4	392.4
40°	309.0	327.7	348.2	371.0
42.5°	290.3	312.1	331.3	347.8
45°	274.2	292.0	309.9	323.3
47.5°	255.5	273.3	288.5	299.2
50°	239.9	254.1	266.6	276.0
52.5°	221.2	234.5	244.8	251.9
55°	202.9	214.5	223.4	228.3
57.5°	186.4	194.0	200.6	205.1
60°	168.1	173.9	179.7	184.6
62.5°	148.5	154.7	157.8	163.2
65°	131.1	135.1	140.0	141.8
67.5°	114.1	116.4	119.5	123.1
70°	96.3	97.6	100.8	105.7
72.5°	80.7	82.0	84.3	86.1
75°	64.2	65.5	67.3	69.1
77.5°	50.4	50.8	51.7	53.5
80°	36.6	37.9	38.8	39.2
82.5°	25.4	25.9	25.9	26.3
85°	16.1	15.2	15.2	15.6
87.5°	5.8	6.7	6.7	7.6
90°	6.2	4.5	2.7	1.0
92.5°	12.7	14.7	16.6	18.6
95°	53.9	54.6	55.2	55.9
97.5°	108.8	107.5	106.2	104.9
100°	165.6	165.0	164.3	163.7
102.5°	226.1	225.2	224.3	223.4
105°	290.7	289.8	289.0	288.1
107.5°	354.8	354.8	354.8	354.8
110°	419.4	419.4	419.4	419.4



TEST NUMBER: P1027154

CATALOG NUMBER: S125RDIP-B375D1090UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	482.1	481.5	480.8	480.2
115°	544.3	543.2	542.1	541.0
117.5°	604.7	604.7	604.7	604.7
120°	662.8	663.1	663.3	663.5
122.5°	718.7	717.6	716.5	715.4
125°	773.9	772.4	770.8	769.3
127.5°	824.6	823.5	822.4	821.3
130°	871.6	870.5	869.4	868.3
132.5°	919.2	917.9	916.6	915.3
135°	963.3	962.0	960.7	959.4
137.5°	1004.5	1003.2	1001.9	1000.6
140°	1042.1	1041.6	1041.2	1040.8
142.5°	1077.7	1077.4	1077.2	1077.0
145°	1113.6	1113.2	1112.7	1112.3
147.5°	1143.7	1143.7	1143.7	1143.7
150°	1171.8	1172.2	1172.7	1173.1
152.5°	1198.2	1199.3	1200.4	1201.5
155°	1221.1	1222.4	1223.7	1225.0
157.5°	1241.7	1242.3	1243.0	1243.6
160°	1259.3	1260.6	1261.9	1263.2
162.5°	1275.0	1276.3	1277.6	1278.9
165°	1288.7	1290.0	1291.3	1292.6
167.5°	1299.5	1300.8	1302.1	1303.4
170°	1307.7	1309.2	1310.7	1312.2
172.5°	1313.6	1315.1	1316.6	1318.1
175°	1318.1	1319.4	1320.7	1322.0
177.5°	1321.1	1322.4	1323.7	1325.0
180°	1322.0	1322.0	1322.0	1322.0

(END OF REPORT)