

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027166

Luminaire Tested: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027166
REPORT IS A COMBINATION OF REPORTS P1005367 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6262.0 lumens
Efficiency: N/A
Efficacy: 130.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23		
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20		
2	84	77	71	66	74	68	64	60	53	49	47	38	36	34	25	24	23	17		
3	76	68	61	55	68	60	55	50	47	43	39	34	31	29	22	21	19	14		
4	70	60	52	47	62	53	47	42	41	37	34	30	27	25	20	18	17	12		
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15	11		
6	59	47	40	34	52	43	36	31	33	28	25	24	21	19	16	14	13	10		
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	9		
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	8		
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9	7		
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3526	3526	3526	3526
5°	3524	3974	3524	3055
10°	3504	4467	3492	2641
15°	3466	4725	3442	2299
20°	3420	5101	3389	2078
25°	3360	5774	3322	1886
30°	3299	6137	3250	1749
35°	3220	5047	3175	1621
40°	3080	3428	3054	1506
45°	2896	2464	2892	1392
50°	2707	1895	2721	1287
55°	2496	1540	2490	1186
60°	2298	1263	2287	1053
65°	2068	1052	2081	848
70°	1877	845	1869	707
75°	1585	640	1585	581
80°	1286	391	1270	391
85°	903	205	880	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 5020 cd/sqm

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	0.8
10°-20°	154.7	2.5
20°-30°	245.4	3.9
30°-40°	296.5	4.7
40°-50°	264.0	4.2
50°-60°	202.4	3.2
60°-70°	131.5	2.1
70°-80°	63.8	1.0
80°-90°	17.3	0.3
90°-100°	53.4	0.9
100°-110°	355.1	5.7
110°-120°	639.5	10.2
120°-130°	820.9	13.1
130°-140°	882.9	14.1
140°-150°	828.6	13.2
150°-160°	670.3	10.7
160°-170°	433.5	6.9
170°-180°	149.5	2.4
0°-30°	452.9	7.2
0°-40°	749.4	12.0
0°-60°	1215.7	19.4
0°-90°	1428.3	22.8
90°-120°	1048.1	16.7
90°-150°	3580.5	57.2
90°-180°	4834.0	77.2
0°-180°	6262.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	550	550	550	550	550	
5°	549	631	549	485	549	52
15°	526	758	522	369	526	148
25°	481	907	475	296	481	222
35°	419	753	413	242	419	261
45°	328	337	327	190	328	253
55°	231	185	231	142	231	207
65°	144	105	145	84	144	144
75°	70	49	70	44	70	75
85°	16	10	15	12	16	18
90°	1	28	1	28	1	4
95°	66	24	66	24	66	81
105°	343	346	343	346	343	363
115°	644	639	644	639	644	638
125°	916	916	916	916	916	818
135°	1142	1137	1142	1137	1142	880
145°	1324	1320	1324	1320	1324	828
155°	1458	1448	1458	1448	1458	672
165°	1539	1530	1539	1530	1539	435
175°	1574	1567	1574	1567	1574	150
180°	1574	1574	1574	1574	1574	

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	550.9	555.4	556.7	560.4	564.4	565.3	567.6	570.7	572.6	572.1	572.1
5°	549.1	556.7	562.2	568.5	576.2	579.3	582.0	588.8	594.2	597.4	602.8
7.5°	545.9	557.2	566.2	575.7	587.5	592.9	598.8	608.3	618.2	624.5	630.4
10°	540.9	555.4	568.0	582.0	597.9	606.0	613.2	627.7	639.9	648.0	661.6
12.5°	533.7	551.8	569.4	587.9	607.8	616.4	626.3	642.1	659.3	671.1	682.4
15°	526.0	547.7	566.7	588.8	612.8	625.9	638.5	655.3	670.6	683.7	696.8
17.5°	517.0	540.0	563.5	588.8	615.9	629.0	639.9	659.8	676.0	689.1	700.9
20°	506.1	531.9	558.5	586.6	614.1	626.3	636.7	658.4	672.9	686.9	703.6
22.5°	494.4	522.4	550.9	578.4	605.5	618.6	630.8	649.8	665.6	684.6	706.3
25°	480.8	511.5	540.5	568.0	593.8	606.0	616.8	637.6	659.8	683.7	708.1
27.5°	467.3	497.1	525.1	550.4	578.4	589.7	600.6	626.8	653.0	678.3	711.7
30°	452.3	482.6	507.0	530.5	557.6	569.4	582.9	612.8	642.6	676.9	717.6
32.5°	435.6	463.2	485.8	510.2	534.6	549.1	566.2	598.8	633.1	674.2	726.2
35°	418.9	441.1	461.8	484.9	514.3	529.6	546.3	580.7	623.6	672.9	733.4
37.5°	397.7	418.9	435.2	458.7	489.0	507.0	523.7	563.5	612.3	669.7	733.0
40°	376.0	394.1	409.4	433.8	466.8	483.5	501.6	545.0	600.6	660.7	722.1
42.5°	352.5	367.8	384.6	408.1	440.1	456.4	477.2	527.8	584.3	648.0	694.1
45°	327.6	342.5	356.5	380.9	413.0	430.7	453.3	505.2	564.4	621.4	648.9
47.5°	303.2	316.3	331.2	352.5	385.0	404.4	427.5	483.1	537.8	585.7	587.9
50°	279.7	290.1	302.8	324.5	358.4	376.9	400.8	452.8	506.1	539.1	517.0
52.5°	255.3	264.8	277.9	296.9	328.5	350.2	371.0	423.0	467.7	489.9	449.2
55°	231.4	239.5	253.1	274.3	301.9	318.6	339.8	388.2	427.5	427.9	383.7
57.5°	207.9	215.1	226.4	245.4	271.1	290.6	310.0	352.0	378.7	371.0	321.8
60°	187.1	191.6	202.0	220.5	244.5	258.5	279.3	314.5	332.1	318.1	265.3
62.5°	165.4	169.9	178.0	193.0	215.6	230.5	243.6	272.5	284.7	263.5	220.1
65°	143.7	149.1	155.0	166.7	188.0	197.9	209.7	230.9	242.7	217.8	180.3
67.5°	124.7	127.4	133.3	145.5	160.4	169.5	177.6	192.1	194.3	174.4	143.7
70°	107.1	108.0	113.4	120.7	132.0	137.4	144.2	152.7	152.7	136.5	112.1
72.5°	87.2	88.6	92.6	100.3	107.1	109.8	112.1	117.5	116.6	101.7	85.0
75°	70.0	70.9	74.1	77.7	80.4	85.4	87.2	86.3	85.9	73.2	63.7
77.5°	54.2	54.7	56.9	60.1	60.6	62.4	61.0	61.0	56.9	49.7	44.7
80°	39.8	40.2	41.1	42.0	42.0	42.0	42.0	39.8	37.1	32.5	31.2
82.5°	26.7	26.7	27.1	28.0	27.6	26.7	25.8	23.5	21.7	20.3	19.4
85°	15.8	15.8	16.3	15.8	14.0	13.6	12.7	12.2	11.7	11.3	11.3
87.5°	7.7	7.2	6.3	5.4	5.4	5.4	5.4	5.4	5.4	5.0	5.0
90°	1.2	3.3	5.3	7.4	9.5	10.5	11.4	13.2	15.1	16.9	18.7
92.5°	22.2	19.9	17.5	15.2	12.9	11.7	12.5	14.0	15.6	17.1	18.7
95°	66.5	65.7	64.9	64.2	63.4	63.0	58.1	48.2	38.4	28.5	18.7
97.5°	124.8	126.4	127.9	129.5	131.0	131.8	119.5	94.9	70.2	45.6	21.0
100°	194.8	195.6	196.4	197.1	197.9	198.3	198.8	199.9	200.9	202.0	203.0
102.5°	266.0	267.0	268.0	269.1	270.1	270.6	270.9	271.4	271.9	272.5	273.0
105°	342.9	343.9	345.0	346.0	347.1	347.6	347.6	347.6	347.6	347.6	347.6
107.5°	422.3	422.3	422.3	422.3	422.3	422.3	422.6	423.1	423.6	424.1	424.6
110°	499.2	499.2	499.2	499.2	499.2	499.2	499.5	500.0	500.5	501.1	501.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	571.6	572.4	573.2	573.9	574.7	575.1	575.2	575.5	575.7	576.0	576.2
115°	643.9	645.2	646.5	647.8	649.1	649.7	649.8	650.1	650.4	650.6	650.9
117.5°	719.7	719.7	719.7	719.7	719.7	719.7	720.2	721.3	722.3	723.4	724.4
120°	789.7	789.4	789.2	788.9	788.6	788.5	788.9	789.7	790.4	791.2	792.0
122.5°	851.5	852.8	854.1	855.4	856.7	857.4	857.5	857.8	858.0	858.3	858.5
125°	915.7	917.5	919.3	921.1	922.9	923.8	923.8	923.8	923.8	923.8	923.8
127.5°	977.5	978.8	980.1	981.4	982.7	983.3	983.2	982.9	982.7	982.4	982.2
130°	1033.5	1034.8	1036.1	1037.4	1038.7	1039.3	1039.4	1039.7	1040.0	1040.2	1040.5
132.5°	1089.5	1091.1	1092.6	1094.2	1095.7	1096.5	1096.1	1095.3	1094.6	1093.8	1093.0
135°	1142.0	1143.6	1145.1	1146.7	1148.2	1149.0	1148.7	1148.2	1147.7	1147.1	1146.6
137.5°	1191.0	1192.6	1194.1	1195.7	1197.2	1198.0	1197.7	1197.2	1196.7	1196.1	1195.6
140°	1238.8	1239.3	1239.8	1240.3	1240.8	1241.1	1241.0	1240.7	1240.5	1240.2	1240.0
142.5°	1281.9	1282.2	1282.4	1282.7	1283.0	1283.1	1283.4	1283.9	1284.4	1284.9	1285.4
145°	1323.9	1324.4	1325.0	1325.5	1326.0	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3
147.5°	1361.3	1361.3	1361.3	1361.3	1361.3	1361.3	1361.4	1361.7	1361.9	1362.2	1362.4
150°	1396.3	1395.8	1395.2	1394.7	1394.2	1393.9	1394.2	1394.7	1395.2	1395.8	1396.3
152.5°	1430.1	1428.8	1427.5	1426.2	1424.9	1424.3	1424.6	1425.1	1425.6	1426.1	1426.6
155°	1458.1	1456.5	1455.0	1453.4	1451.9	1451.1	1451.4	1451.9	1452.4	1452.9	1453.4
157.5°	1480.2	1479.4	1478.7	1477.9	1477.2	1476.8	1476.8	1476.8	1476.8	1476.8	1476.8
160°	1503.6	1502.0	1500.5	1498.9	1497.4	1496.6	1496.7	1497.0	1497.2	1497.5	1497.7
162.5°	1522.2	1520.6	1519.1	1517.5	1516.0	1515.2	1515.3	1515.6	1515.9	1516.1	1516.4
165°	1538.6	1537.0	1535.5	1533.9	1532.4	1531.6	1531.7	1532.0	1532.2	1532.5	1532.7
167.5°	1551.4	1549.8	1548.3	1546.7	1545.2	1544.4	1544.5	1544.8	1545.1	1545.3	1545.6
170°	1561.9	1560.1	1558.3	1556.4	1554.6	1553.7	1553.8	1554.1	1554.4	1554.6	1554.9
172.5°	1568.9	1567.1	1565.3	1563.4	1561.6	1560.7	1561.0	1561.5	1562.0	1562.6	1563.1
175°	1573.6	1572.0	1570.5	1568.9	1567.4	1566.6	1566.7	1567.0	1567.2	1567.5	1567.7
177.5°	1577.1	1575.5	1574.0	1572.4	1570.9	1570.1	1570.2	1570.5	1570.7	1571.0	1571.2
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	574.4	577.5	580.2	578.9	584.3	583.9	584.8	586.6	587.0	586.1	584.3
5°	605.5	610.1	617.7	621.8	620.9	624.5	626.3	629.0	631.8	630.8	630.8
7.5°	640.3	646.7	654.3	664.7	666.1	669.3	674.7	674.7	677.8	676.5	676.0
10°	670.6	678.3	690.5	698.6	702.2	704.1	709.5	711.3	714.9	715.4	715.4
12.5°	695.5	709.0	717.2	725.3	727.1	729.8	733.9	736.6	737.9	737.9	736.6
15°	708.6	719.4	728.9	737.5	742.5	744.7	748.8	752.0	753.8	757.8	758.7
17.5°	714.0	727.1	742.5	754.7	763.3	765.5	773.6	776.4	780.0	781.8	784.0
20°	721.7	740.7	759.2	774.1	782.2	788.1	796.7	809.3	813.0	813.0	811.6
22.5°	728.5	752.9	778.2	802.1	808.9	820.6	836.5	850.0	855.4	857.7	855.9
25°	736.6	770.0	803.0	832.8	851.4	860.0	881.2	897.5	903.8	907.4	908.3
27.5°	750.6	792.6	834.7	872.6	891.6	901.5	923.7	937.7	945.4	948.5	946.3
30°	766.4	817.9	866.7	900.6	913.3	925.5	939.9	945.4	943.6	943.6	950.3
32.5°	782.7	836.0	879.4	901.5	906.1	904.2	898.4	882.1	872.6	872.6	878.5
35°	791.7	837.8	860.0	852.7	835.1	824.7	792.6	774.6	754.2	752.9	759.6
37.5°	786.8	806.6	797.6	750.1	726.2	706.3	656.2	636.3	621.4	600.6	632.7
40°	752.0	745.2	698.2	629.9	603.3	575.3	535.5	515.6	494.8	491.7	499.3
42.5°	693.2	653.0	584.3	518.3	491.2	471.3	441.1	421.6	408.5	403.1	412.1
45°	620.0	556.7	488.0	435.6	405.8	395.4	367.8	350.7	340.7	336.7	343.0
47.5°	530.5	466.8	401.7	357.5	339.8	329.4	310.9	296.0	287.4	284.7	287.4
50°	450.5	385.0	330.3	301.9	286.1	277.5	262.1	252.6	245.8	244.0	248.5
52.5°	381.4	321.8	280.2	254.9	244.5	237.2	226.4	218.3	214.2	212.4	215.6
55°	319.5	271.1	237.7	216.0	208.3	203.8	194.3	189.8	185.3	184.8	188.0
57.5°	264.8	231.4	200.6	185.3	183.0	176.2	168.1	164.0	161.8	161.3	162.7
60°	220.5	190.7	172.2	158.6	155.5	150.0	145.5	142.8	140.1	139.2	140.1
62.5°	183.5	160.0	145.1	136.0	131.5	130.1	125.2	122.0	121.6	121.6	122.5
65°	151.4	131.5	122.0	114.8	111.6	110.3	106.6	104.4	104.8	104.8	105.3
67.5°	123.4	108.9	100.3	96.7	94.0	93.5	89.9	89.0	88.1	88.1	89.0
70°	98.1	89.0	82.7	80.9	80.4	77.3	75.9	75.5	74.1	74.6	74.6
72.5°	76.8	70.9	67.3	64.6	65.1	63.3	61.5	61.5	60.6	61.9	61.9
75°	56.9	54.2	51.5	50.6	51.5	50.6	49.3	48.8	49.3	48.8	48.8
77.5°	42.0	40.7	39.8	39.3	39.3	37.5	36.6	37.5	35.7	36.6	36.6
80°	29.4	27.6	27.1	26.2	26.7	25.3	25.8	24.9	24.9	24.9	24.9
82.5°	18.5	18.1	18.1	18.1	17.6	17.6	17.6	17.6	17.6	17.6	17.2
85°	11.3	10.8	10.8	10.8	10.4	10.4	10.4	10.4	10.4	10.4	10.4
87.5°	4.5	5.0	5.0	5.4	5.0	4.5	4.5	4.5	5.0	5.0	4.5
90°	20.0	21.3	22.6	23.9	24.5	24.9	25.7	26.4	27.2	28.0	27.2
92.5°	20.0	21.3	22.6	23.9	24.5	24.6	24.9	25.2	25.4	25.7	25.4
95°	20.0	21.3	22.6	23.9	24.5	24.5	24.5	24.5	24.5	24.5	24.5
97.5°	21.5	22.0	22.5	23.0	23.3	23.4	23.7	24.0	24.2	24.5	24.2
100°	164.4	125.8	87.1	48.5	29.2	28.7	27.6	26.6	25.5	24.5	25.5
102.5°	273.5	274.0	274.5	275.0	275.3	264.4	242.6	220.9	199.1	177.3	199.1
105°	347.6	347.6	347.6	347.6	347.6	347.5	347.2	346.9	346.7	346.4	346.7
107.5°	424.9	425.1	425.4	425.7	425.8	425.3	424.2	423.2	422.1	421.1	422.1
110°	500.8	500.0	499.3	498.5	498.1	498.2	498.5	498.7	499.0	499.2	499.0

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	575.2	574.2	573.1	572.1	571.6	571.3	570.8	570.3	569.7	569.2	569.7
115°	649.9	648.8	647.8	646.7	646.2	645.4	643.9	642.3	640.8	639.2	640.8
117.5°	722.8	721.3	719.7	718.2	717.4	717.1	716.6	716.1	715.5	715.0	715.5
120°	791.5	791.0	790.5	790.0	789.7	789.1	787.8	786.5	785.2	783.9	785.2
122.5°	858.0	857.5	857.0	856.5	856.2	855.4	853.9	852.3	850.8	849.2	850.8
125°	922.8	921.8	920.7	919.7	919.2	918.8	918.0	917.3	916.5	915.7	916.5
127.5°	981.7	981.1	980.6	980.1	979.8	978.8	976.7	974.6	972.6	970.5	972.6
130°	1039.7	1038.9	1038.2	1037.4	1037.0	1036.4	1035.1	1033.8	1032.5	1031.2	1032.5
132.5°	1093.0	1093.0	1093.0	1093.0	1093.0	1092.3	1091.0	1089.7	1088.4	1087.1	1088.4
135°	1146.1	1145.6	1145.1	1144.6	1144.3	1143.5	1142.0	1140.4	1138.9	1137.3	1138.9
137.5°	1195.6	1195.6	1195.6	1195.6	1195.6	1195.0	1193.7	1192.4	1191.1	1189.8	1191.1
140°	1240.5	1241.0	1241.5	1242.0	1242.3	1241.5	1240.0	1238.4	1236.9	1235.3	1236.9
142.5°	1285.4	1285.4	1285.4	1285.4	1285.4	1284.6	1283.1	1281.6	1280.0	1278.5	1280.0
145°	1326.5	1326.8	1327.0	1327.3	1327.4	1326.6	1325.1	1323.5	1322.0	1320.4	1322.0
147.5°	1362.7	1362.9	1363.2	1363.5	1363.6	1362.7	1360.9	1359.0	1357.2	1355.4	1357.2
150°	1396.8	1397.3	1397.8	1398.3	1398.6	1397.6	1395.5	1393.4	1391.4	1389.3	1391.4
152.5°	1427.1	1427.6	1428.1	1428.6	1428.9	1428.0	1426.2	1424.4	1422.6	1420.8	1422.6
155°	1454.2	1455.0	1455.7	1456.5	1456.9	1455.9	1453.8	1451.7	1449.7	1447.6	1449.7
157.5°	1477.6	1478.3	1479.1	1479.8	1480.2	1479.2	1477.1	1475.0	1473.0	1470.9	1473.0
160°	1498.7	1499.8	1500.8	1501.9	1502.4	1501.4	1499.3	1497.2	1495.2	1493.1	1495.2
162.5°	1518.0	1519.5	1521.1	1522.6	1523.4	1522.2	1519.9	1517.6	1515.2	1512.9	1515.2
165°	1534.3	1535.8	1537.4	1538.9	1539.7	1538.7	1536.6	1534.5	1532.5	1530.4	1532.5
167.5°	1547.4	1549.2	1551.0	1552.8	1553.7	1552.5	1550.2	1547.9	1545.5	1543.2	1545.5
170°	1557.0	1559.0	1561.1	1563.2	1564.2	1563.0	1560.7	1558.4	1556.0	1553.7	1556.0
172.5°	1564.9	1566.7	1568.5	1570.3	1571.2	1570.0	1567.7	1565.4	1563.0	1560.7	1563.0
175°	1569.8	1571.9	1574.0	1576.1	1577.1	1575.9	1573.6	1571.3	1568.9	1566.6	1568.9
177.5°	1573.0	1574.8	1576.7	1578.5	1579.4	1578.4	1576.3	1574.2	1572.2	1570.1	1572.2
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	586.6	583.4	584.8	583.4	582.0	580.7	577.5	573.0	569.4	566.7	566.2
5°	631.8	627.7	625.0	623.6	620.9	617.3	611.4	604.6	596.5	593.3	587.0
7.5°	673.3	672.0	665.6	664.7	662.9	656.2	646.2	637.2	626.8	618.2	610.1
10°	712.6	709.5	705.0	698.6	697.7	689.1	679.7	667.0	653.4	645.3	630.8
12.5°	737.0	733.4	728.5	724.4	722.1	716.7	703.6	691.0	678.7	663.8	651.2
15°	754.7	750.1	741.1	737.9	735.2	728.0	718.5	705.4	689.1	678.7	660.7
17.5°	778.6	773.2	764.2	758.3	753.3	742.0	728.5	710.8	695.5	683.7	667.5
20°	806.2	798.0	786.3	778.6	771.4	758.3	739.3	718.5	696.4	681.9	665.2
22.5°	851.8	836.5	817.9	807.1	797.1	774.6	752.0	726.2	701.3	679.7	659.3
25°	896.1	880.7	857.7	842.8	827.4	801.2	771.4	735.7	704.1	678.7	652.1
27.5°	937.2	921.4	900.2	882.1	867.2	827.9	788.6	748.3	708.1	673.3	646.2
30°	946.7	939.9	923.7	907.9	894.3	858.2	812.5	761.4	713.1	668.4	638.1
32.5°	889.3	906.1	910.1	907.9	899.3	873.5	831.5	777.7	720.3	666.1	624.5
35°	770.0	800.3	831.5	848.2	856.3	860.0	835.1	785.8	725.3	662.5	615.5
37.5°	638.5	667.9	717.2	742.0	769.6	805.7	815.7	784.0	723.0	659.8	601.0
40°	524.7	562.2	602.8	625.4	649.4	714.4	763.7	760.1	715.8	649.8	589.7
42.5°	427.0	450.5	486.2	511.1	540.5	613.2	679.2	711.7	694.1	637.6	575.3
45°	356.1	374.2	399.5	424.8	442.9	508.8	587.0	640.3	657.1	615.9	553.1
47.5°	300.1	313.6	335.8	351.6	371.0	423.0	490.8	565.8	601.0	585.2	529.6
50°	257.1	268.0	285.6	295.5	312.7	357.5	409.0	487.6	540.9	542.7	498.4
52.5°	219.6	230.5	245.4	254.0	264.4	294.6	346.6	413.0	474.5	497.1	462.7
55°	191.2	197.5	209.7	216.5	225.9	255.3	288.3	344.8	409.0	446.0	424.3
57.5°	164.9	171.7	179.4	184.8	191.6	215.1	244.9	287.4	351.1	391.3	384.1
60°	143.7	147.8	155.0	159.1	165.4	180.8	201.5	244.0	294.6	332.6	336.7
62.5°	123.8	127.4	132.4	136.0	140.1	152.3	167.7	197.9	242.2	283.3	288.8
65°	106.6	109.8	112.5	115.7	118.8	126.5	139.6	163.1	197.5	235.9	247.6
67.5°	91.3	92.2	96.3	96.7	98.5	104.4	113.9	132.9	157.7	188.4	203.8
70°	76.4	78.2	79.1	80.4	82.2	86.3	94.0	103.9	122.5	147.3	161.8
72.5°	61.9	62.4	63.7	64.6	66.4	69.6	73.2	80.9	92.6	110.7	123.8
75°	49.3	49.7	50.6	51.1	52.4	53.3	55.1	60.6	68.7	79.5	89.0
77.5°	37.1	38.0	38.9	38.9	39.3	40.2	41.1	42.9	47.0	54.2	62.4
80°	25.3	25.8	25.8	26.2	25.8	27.1	28.5	30.7	32.5	34.8	38.9
82.5°	17.6	17.6	17.6	18.1	18.1	18.5	18.5	19.0	19.4	20.8	22.6
85°	10.8	10.8	11.3	10.4	10.8	11.3	11.3	10.8	11.3	11.7	12.2
87.5°	4.5	4.5	5.0	5.0	5.0	5.0	4.5	5.0	4.5	5.0	5.0
90°	26.4	25.7	24.9	24.5	23.9	22.6	21.3	20.0	18.7	16.9	15.1
92.5°	25.2	24.9	24.6	24.5	23.9	22.6	21.3	20.0	18.7	17.1	15.6
95°	24.5	24.5	24.5	24.5	23.9	22.6	21.3	20.0	18.7	28.5	38.4
97.5°	24.0	23.7	23.4	23.3	23.0	22.5	22.0	21.5	21.0	45.6	70.2
100°	26.6	27.6	28.7	29.2	48.5	87.1	125.8	164.4	203.0	202.0	200.9
102.5°	220.9	242.6	264.4	275.3	275.0	274.5	274.0	273.5	273.0	272.5	271.9
105°	346.9	347.2	347.5	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6
107.5°	423.2	424.2	425.3	425.8	425.7	425.4	425.1	424.9	424.6	424.1	423.6
110°	498.7	498.5	498.2	498.1	498.5	499.3	500.0	500.8	501.6	501.1	500.5

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	570.3	570.8	571.3	571.6	572.1	573.1	574.2	575.2	576.2	576.0	575.7
115°	642.3	643.9	645.4	646.2	646.7	647.8	648.8	649.9	650.9	650.6	650.4
117.5°	716.1	716.6	717.1	717.4	718.2	719.7	721.3	722.8	724.4	723.4	722.3
120°	786.5	787.8	789.1	789.7	790.0	790.5	791.0	791.5	792.0	791.2	790.4
122.5°	852.3	853.9	855.4	856.2	856.5	857.0	857.5	858.0	858.5	858.3	858.0
125°	917.3	918.0	918.8	919.2	919.7	920.7	921.8	922.8	923.8	923.8	923.8
127.5°	974.6	976.7	978.8	979.8	980.1	980.6	981.1	981.7	982.2	982.4	982.7
130°	1033.8	1035.1	1036.4	1037.0	1037.4	1038.2	1038.9	1039.7	1040.5	1040.2	1040.0
132.5°	1089.7	1091.0	1092.3	1093.0	1093.0	1093.0	1093.0	1093.0	1093.0	1093.8	1094.6
135°	1140.4	1142.0	1143.5	1144.3	1144.6	1145.1	1145.6	1146.1	1146.6	1147.1	1147.7
137.5°	1192.4	1193.7	1195.0	1195.6	1195.6	1195.6	1195.6	1195.6	1195.6	1196.1	1196.7
140°	1238.4	1240.0	1241.5	1242.3	1242.0	1241.5	1241.0	1240.5	1240.0	1240.2	1240.5
142.5°	1281.6	1283.1	1284.6	1285.4	1285.4	1285.4	1285.4	1285.4	1285.4	1284.9	1284.4
145°	1323.5	1325.1	1326.6	1327.4	1327.3	1327.0	1326.8	1326.5	1326.3	1326.3	1326.3
147.5°	1359.0	1360.9	1362.7	1363.6	1363.5	1363.2	1362.9	1362.7	1362.4	1362.2	1361.9
150°	1393.4	1395.5	1397.6	1398.6	1398.3	1397.8	1397.3	1396.8	1396.3	1395.8	1395.2
152.5°	1424.4	1426.2	1428.0	1428.9	1428.6	1428.1	1427.6	1427.1	1426.6	1426.1	1425.6
155°	1451.7	1453.8	1455.9	1456.9	1456.5	1455.7	1455.0	1454.2	1453.4	1452.9	1452.4
157.5°	1475.0	1477.1	1479.2	1480.2	1479.8	1479.1	1478.3	1477.6	1476.8	1476.8	1476.8
160°	1497.2	1499.3	1501.4	1502.4	1501.9	1500.8	1499.8	1498.7	1497.7	1497.5	1497.2
162.5°	1517.6	1519.9	1522.2	1523.4	1522.6	1521.1	1519.5	1518.0	1516.4	1516.1	1515.9
165°	1534.5	1536.6	1538.7	1539.7	1538.9	1537.4	1535.8	1534.3	1532.7	1532.5	1532.2
167.5°	1547.9	1550.2	1552.5	1553.7	1552.8	1551.0	1549.2	1547.4	1545.6	1545.3	1545.1
170°	1558.4	1560.7	1563.0	1564.2	1563.2	1561.1	1559.0	1557.0	1554.9	1554.6	1554.4
172.5°	1565.4	1567.7	1570.0	1571.2	1570.3	1568.5	1566.7	1564.9	1563.1	1562.6	1562.0
175°	1571.3	1573.6	1575.9	1577.1	1576.1	1574.0	1571.9	1569.8	1567.7	1567.5	1567.2
177.5°	1574.2	1576.3	1578.4	1579.4	1578.5	1576.7	1574.8	1573.0	1571.2	1571.0	1570.7
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	564.9	562.2	560.4	559.9	557.2	554.9	552.2	551.8	550.4	546.8	544.5
5°	582.5	576.2	574.8	570.7	564.0	559.0	552.7	549.1	545.0	538.2	532.8
7.5°	600.6	592.0	585.7	579.8	570.3	561.3	552.2	545.0	537.8	527.8	519.7
10°	618.2	605.1	597.4	588.8	575.7	562.2	549.5	539.1	527.4	515.6	503.9
12.5°	634.5	617.7	606.4	594.2	578.0	561.3	545.0	530.5	518.3	502.5	489.4
15°	644.4	625.9	614.6	602.8	578.4	559.9	540.9	522.4	506.1	489.4	477.2
17.5°	650.3	629.5	616.8	606.0	581.1	555.8	531.4	511.5	493.9	474.0	457.8
20°	647.6	627.2	615.5	605.1	576.2	550.9	524.7	501.6	479.5	459.1	442.0
22.5°	641.7	620.5	607.3	597.9	572.1	542.3	513.4	488.5	465.5	445.1	425.7
25°	629.0	608.3	597.0	585.2	559.9	531.4	502.1	475.4	451.0	429.3	407.6
27.5°	617.7	592.4	580.7	570.3	543.6	518.3	489.4	460.0	435.2	412.6	390.9
30°	604.6	576.2	563.5	549.5	525.6	501.6	472.7	445.6	419.8	395.9	375.1
32.5°	590.6	557.6	543.2	527.4	503.0	480.4	456.0	429.3	403.5	380.0	358.4
35°	572.6	537.3	520.6	505.7	480.4	457.8	435.2	413.0	387.3	362.4	341.6
37.5°	555.4	516.5	498.9	481.7	455.1	433.4	414.8	394.1	369.2	345.2	325.4
40°	535.9	491.2	473.1	457.3	429.8	405.8	389.1	372.8	351.1	328.1	306.4
42.5°	518.3	467.7	448.7	432.5	403.5	380.9	365.1	351.6	332.6	311.4	289.2
45°	493.9	442.4	423.0	405.8	376.4	355.2	338.9	327.2	312.3	292.4	272.5
47.5°	471.3	418.0	396.8	376.0	349.3	327.6	312.7	303.7	293.7	276.1	255.8
50°	443.8	390.0	368.3	351.1	320.8	302.3	287.4	281.1	272.0	255.3	239.1
52.5°	413.9	362.9	342.5	321.8	293.7	275.7	262.6	255.3	248.1	235.9	220.5
55°	379.1	332.6	313.6	295.1	267.1	250.4	238.6	230.9	226.9	215.6	204.3
57.5°	345.7	301.9	284.2	267.1	242.7	223.7	216.0	209.2	203.4	195.2	185.7
60°	311.8	272.0	253.1	237.7	216.5	199.3	193.0	186.2	181.7	175.3	168.6
62.5°	272.9	239.1	224.6	210.1	192.1	178.5	171.3	165.8	160.0	155.9	150.0
65°	231.8	207.9	193.9	183.0	165.8	153.6	148.2	144.6	139.6	135.6	131.1
67.5°	193.4	174.4	168.6	156.8	143.7	132.9	128.8	124.3	120.2	117.9	113.9
70°	156.4	142.8	136.9	133.8	119.3	112.1	108.5	106.6	101.7	99.4	96.7
72.5°	121.1	116.1	112.1	108.0	98.5	94.0	89.9	88.1	84.5	82.7	81.8
75°	89.5	86.3	84.1	83.6	79.5	75.0	70.9	70.0	67.3	65.5	64.6
77.5°	62.8	61.9	61.5	61.9	59.2	56.5	55.6	54.7	51.5	51.1	51.1
80°	41.1	43.4	43.4	42.9	42.0	41.6	40.2	39.3	37.5	37.1	37.5
82.5°	25.3	26.7	27.1	28.0	27.6	27.1	26.2	25.8	26.2	25.3	25.8
85°	12.7	13.6	15.4	15.4	15.8	15.8	15.8	15.4	14.5	14.9	14.5
87.5°	5.0	5.4	5.4	5.4	5.0	6.3	6.8	6.8	6.8	5.9	5.9
90°	13.2	11.4	10.5	9.5	7.4	5.3	3.3	1.2	3.3	5.3	7.4
92.5°	14.0	12.5	11.7	12.9	15.2	17.5	19.9	22.2	19.9	17.5	15.2
95°	48.2	58.1	63.0	63.4	64.2	64.9	65.7	66.5	65.7	64.9	64.2
97.5°	94.9	119.5	131.8	131.0	129.5	127.9	126.4	124.8	126.4	127.9	129.5
100°	199.9	198.8	198.3	197.9	197.1	196.4	195.6	194.8	195.6	196.4	197.1
102.5°	271.4	270.9	270.6	270.1	269.1	268.0	267.0	266.0	267.0	268.0	269.1
105°	347.6	347.6	347.6	347.1	346.0	345.0	343.9	342.9	343.9	345.0	346.0
107.5°	423.1	422.6	422.3	422.3	422.3	422.3	422.3	422.3	422.3	422.3	422.3
110°	500.0	499.5	499.2	499.2	499.2	499.2	499.2	499.2	499.2	499.2	499.2

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	575.5	575.2	575.1	574.7	573.9	573.2	572.4	571.6	572.4	573.2	573.9
115°	650.1	649.8	649.7	649.1	647.8	646.5	645.2	643.9	645.2	646.5	647.8
117.5°	721.3	720.2	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7
120°	789.7	788.9	788.5	788.6	788.9	789.2	789.4	789.7	789.4	789.2	788.9
122.5°	857.8	857.5	857.4	856.7	855.4	854.1	852.8	851.5	852.8	854.1	855.4
125°	923.8	923.8	923.8	922.9	921.1	919.3	917.5	915.7	917.5	919.3	921.1
127.5°	982.9	983.2	983.3	982.7	981.4	980.1	978.8	977.5	978.8	980.1	981.4
130°	1039.7	1039.4	1039.3	1038.7	1037.4	1036.1	1034.8	1033.5	1034.8	1036.1	1037.4
132.5°	1095.3	1096.1	1096.5	1095.7	1094.2	1092.6	1091.1	1089.5	1091.1	1092.6	1094.2
135°	1148.2	1148.7	1149.0	1148.2	1146.7	1145.1	1143.6	1142.0	1143.6	1145.1	1146.7
137.5°	1197.2	1197.7	1198.0	1197.2	1195.7	1194.1	1192.6	1191.0	1192.6	1194.1	1195.7
140°	1240.7	1241.0	1241.1	1240.8	1240.3	1239.8	1239.3	1238.8	1239.3	1239.8	1240.3
142.5°	1283.9	1283.4	1283.1	1283.0	1282.7	1282.4	1282.2	1281.9	1282.2	1282.4	1282.7
145°	1326.3	1326.3	1326.3	1326.0	1325.5	1325.0	1324.4	1323.9	1324.4	1325.0	1325.5
147.5°	1361.7	1361.4	1361.3	1361.3	1361.3	1361.3	1361.3	1361.3	1361.3	1361.3	1361.3
150°	1394.7	1394.2	1393.9	1394.2	1394.7	1395.2	1395.8	1396.3	1395.8	1395.2	1394.7
152.5°	1425.1	1424.6	1424.3	1424.9	1426.2	1427.5	1428.8	1430.1	1428.8	1427.5	1426.2
155°	1451.9	1451.4	1451.1	1451.9	1453.4	1455.0	1456.5	1458.1	1456.5	1455.0	1453.4
157.5°	1476.8	1476.8	1476.8	1477.2	1477.9	1478.7	1479.4	1480.2	1479.4	1478.7	1477.9
160°	1497.0	1496.7	1496.6	1497.4	1498.9	1500.5	1502.0	1503.6	1502.0	1500.5	1498.9
162.5°	1515.6	1515.3	1515.2	1516.0	1517.5	1519.1	1520.6	1522.2	1520.6	1519.1	1517.5
165°	1532.0	1531.7	1531.6	1532.4	1533.9	1535.5	1537.0	1538.6	1537.0	1535.5	1533.9
167.5°	1544.8	1544.5	1544.4	1545.2	1546.7	1548.3	1549.8	1551.4	1549.8	1548.3	1546.7
170°	1554.1	1553.8	1553.7	1554.6	1556.4	1558.3	1560.1	1561.9	1560.1	1558.3	1556.4
172.5°	1561.5	1561.0	1560.7	1561.6	1563.4	1565.3	1567.1	1568.9	1567.1	1565.3	1563.4
175°	1567.0	1566.7	1566.6	1567.4	1568.9	1570.5	1572.0	1573.6	1572.0	1570.5	1568.9
177.5°	1570.5	1570.2	1570.1	1570.9	1572.4	1574.0	1575.5	1577.1	1575.5	1574.0	1572.4
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	543.2	541.4	540.0	538.7	532.8	526.5	525.6	524.2	521.5	524.7	523.3
5°	529.2	525.1	522.8	517.0	509.7	504.3	499.8	494.4	492.1	490.3	489.9
7.5°	512.0	508.4	504.3	498.4	489.4	480.4	473.6	468.2	463.6	461.4	461.4
10°	495.3	490.8	485.3	475.4	466.8	455.5	448.3	442.9	436.5	432.9	429.8
12.5°	478.1	473.1	468.2	455.5	445.6	433.8	423.4	416.6	413.5	409.4	404.0
15°	460.9	453.3	448.3	435.6	423.0	411.2	404.4	397.2	390.0	385.9	384.1
17.5°	442.9	437.4	429.3	415.7	401.7	391.3	381.4	374.6	366.0	362.0	357.9
20°	426.6	418.5	410.3	396.8	383.2	369.2	359.3	351.1	345.7	342.5	338.9
22.5°	407.2	399.5	392.7	378.2	363.3	350.2	339.4	334.4	329.0	324.0	320.4
25°	390.4	382.8	376.0	360.2	343.9	331.7	323.6	317.2	311.4	309.1	305.5
27.5°	372.8	365.6	356.5	340.7	326.3	315.9	307.3	301.4	296.9	292.4	289.7
30°	356.1	348.0	339.8	322.7	310.9	300.5	292.4	285.1	281.5	279.3	274.8
32.5°	339.8	329.4	322.7	306.8	295.5	285.6	278.8	272.5	268.0	263.9	260.3
35°	322.2	310.9	304.1	291.0	279.3	269.3	263.5	258.9	253.5	249.9	248.1
37.5°	305.5	296.0	289.2	275.7	263.9	255.8	249.4	243.6	241.3	236.3	235.4
40°	287.4	279.3	272.9	259.8	249.0	242.7	235.9	230.5	226.4	224.1	221.0
42.5°	271.1	264.4	257.6	245.4	235.0	227.3	222.3	217.4	213.7	210.1	207.9
45°	256.2	249.0	242.7	230.9	220.5	213.7	208.8	202.9	202.0	197.0	194.8
47.5°	240.4	234.1	228.7	216.5	207.0	200.2	194.3	190.2	186.2	184.4	181.2
50°	225.0	218.7	212.4	201.5	193.0	186.2	180.3	175.8	173.5	170.8	168.1
52.5°	208.3	203.4	198.4	187.1	178.5	172.6	167.7	161.8	159.5	157.3	155.5
55°	194.3	187.1	181.7	172.2	164.5	158.2	152.7	148.2	146.0	144.2	141.9
57.5°	175.3	170.8	166.3	157.7	150.5	144.2	138.7	135.1	132.4	131.1	131.5
60°	159.1	154.1	151.4	142.3	135.1	130.1	125.2	121.6	118.8	117.5	117.0
62.5°	141.9	138.3	133.3	127.0	119.8	115.2	111.6	108.9	104.4	103.9	102.6
65°	125.2	122.5	117.9	112.1	106.2	102.1	98.1	94.4	92.6	90.4	89.0
67.5°	108.9	106.2	102.1	97.2	93.1	89.0	85.4	81.8	78.6	76.8	75.9
70°	93.1	90.8	88.1	82.2	77.3	74.1	71.4	69.1	66.0	65.1	64.6
72.5°	77.7	75.5	74.1	69.1	64.6	61.9	59.2	56.9	55.6	55.1	53.8
75°	63.7	61.5	59.7	55.1	52.4	50.6	47.9	47.0	45.6	45.2	44.7
77.5°	49.7	47.4	47.0	43.8	40.7	39.8	38.9	37.1	37.1	37.1	36.2
80°	35.7	35.2	34.8	31.6	30.3	29.4	28.9	27.6	26.7	25.8	25.3
82.5°	24.0	23.5	23.0	21.7	20.3	19.9	19.4	18.5	18.5	19.0	18.1
85°	14.5	13.6	13.1	12.7	11.7	11.7	12.2	11.7	11.7	11.7	11.3
87.5°	5.4	5.4	5.4	5.4	5.9	5.0	5.4	5.4	5.0	5.0	4.5
90°	9.5	10.5	11.4	13.2	15.1	16.9	18.7	20.0	21.3	22.6	23.9
92.5°	12.9	11.7	12.5	14.0	15.6	17.1	18.7	20.0	21.3	22.6	23.9
95°	63.4	63.0	58.1	48.2	38.4	28.5	18.7	20.0	21.3	22.6	23.9
97.5°	131.0	131.8	119.5	94.9	70.2	45.6	21.0	21.5	22.0	22.5	23.0
100°	197.9	198.3	198.8	199.9	200.9	202.0	203.0	164.4	125.8	87.1	48.5
102.5°	270.1	270.6	270.9	271.4	271.9	272.5	273.0	273.5	274.0	274.5	275.0
105°	347.1	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6
107.5°	422.3	422.3	422.6	423.1	423.6	424.1	424.6	424.9	425.1	425.4	425.7
110°	499.2	499.2	499.5	500.0	500.5	501.1	501.6	500.8	500.0	499.3	498.5

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	574.7	575.1	575.2	575.5	575.7	576.0	576.2	575.2	574.2	573.1	572.1
115°	649.1	649.7	649.8	650.1	650.4	650.6	650.9	649.9	648.8	647.8	646.7
117.5°	719.7	719.7	720.2	721.3	722.3	723.4	724.4	722.8	721.3	719.7	718.2
120°	788.6	788.5	788.9	789.7	790.4	791.2	792.0	791.5	791.0	790.5	790.0
122.5°	856.7	857.4	857.5	857.8	858.0	858.3	858.5	858.0	857.5	857.0	856.5
125°	922.9	923.8	923.8	923.8	923.8	923.8	923.8	922.8	921.8	920.7	919.7
127.5°	982.7	983.3	983.2	982.9	982.7	982.4	982.2	981.7	981.1	980.6	980.1
130°	1038.7	1039.3	1039.4	1039.7	1040.0	1040.2	1040.5	1039.7	1038.9	1038.2	1037.4
132.5°	1095.7	1096.5	1096.1	1095.3	1094.6	1093.8	1093.0	1093.0	1093.0	1093.0	1093.0
135°	1148.2	1149.0	1148.7	1148.2	1147.7	1147.1	1146.6	1146.1	1145.6	1145.1	1144.6
137.5°	1197.2	1198.0	1197.7	1197.2	1196.7	1196.1	1195.6	1195.6	1195.6	1195.6	1195.6
140°	1240.8	1241.1	1241.0	1240.7	1240.5	1240.2	1240.0	1240.5	1241.0	1241.5	1242.0
142.5°	1283.0	1283.1	1283.4	1283.9	1284.4	1284.9	1285.4	1285.4	1285.4	1285.4	1285.4
145°	1326.0	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3	1326.5	1326.8	1327.0	1327.3
147.5°	1361.3	1361.3	1361.4	1361.7	1361.9	1362.2	1362.4	1362.7	1362.9	1363.2	1363.5
150°	1394.2	1393.9	1394.2	1394.7	1395.2	1395.8	1396.3	1396.8	1397.3	1397.8	1398.3
152.5°	1424.9	1424.3	1424.6	1425.1	1425.6	1426.1	1426.6	1427.1	1427.6	1428.1	1428.6
155°	1451.9	1451.1	1451.4	1451.9	1452.4	1452.9	1453.4	1454.2	1455.0	1455.7	1456.5
157.5°	1477.2	1476.8	1476.8	1476.8	1476.8	1476.8	1476.8	1477.6	1478.3	1479.1	1479.8
160°	1497.4	1496.6	1496.7	1497.0	1497.2	1497.5	1497.7	1498.7	1499.8	1500.8	1501.9
162.5°	1516.0	1515.2	1515.3	1515.6	1515.9	1516.1	1516.4	1518.0	1519.5	1521.1	1522.6
165°	1532.4	1531.6	1531.7	1532.0	1532.2	1532.5	1532.7	1534.3	1535.8	1537.4	1538.9
167.5°	1545.2	1544.4	1544.5	1544.8	1545.1	1545.3	1545.6	1547.4	1549.2	1551.0	1552.8
170°	1554.6	1553.7	1553.8	1554.1	1554.4	1554.6	1554.9	1557.0	1559.0	1561.1	1563.2
172.5°	1561.6	1560.7	1561.0	1561.5	1562.0	1562.6	1563.1	1564.9	1566.7	1568.5	1570.3
175°	1567.4	1566.6	1566.7	1567.0	1567.2	1567.5	1567.7	1569.8	1571.9	1574.0	1576.1
177.5°	1570.9	1570.1	1570.2	1570.5	1570.7	1571.0	1571.2	1573.0	1574.8	1576.7	1578.5
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	521.0	521.9	519.7	518.8	517.0	519.2	519.7	519.2	523.3	521.5	522.4
5°	490.8	489.0	487.6	484.4	484.4	484.9	486.2	484.0	485.3	488.5	488.0
7.5°	457.3	456.4	456.9	453.3	450.5	451.4	450.5	454.6	456.9	456.0	457.8
10°	427.0	428.9	424.8	423.0	421.2	423.0	422.5	423.4	426.1	427.9	431.1
12.5°	402.6	402.2	399.9	398.1	395.0	395.9	398.6	397.7	398.1	402.2	401.7
15°	379.6	376.9	375.1	371.0	371.9	368.7	371.5	374.6	376.0	379.6	381.9
17.5°	356.5	356.1	353.8	353.4	348.4	347.1	349.8	350.7	352.0	353.8	357.0
20°	337.1	336.7	333.5	332.6	328.5	331.2	330.3	332.1	333.0	336.7	338.0
22.5°	319.5	317.2	316.3	315.0	313.6	313.2	315.0	314.5	317.7	319.0	319.5
25°	303.2	301.4	301.0	298.7	297.8	296.4	297.8	299.2	302.8	304.1	305.9
27.5°	288.3	287.0	286.1	284.2	282.9	282.9	283.8	285.6	287.0	287.9	288.8
30°	274.8	273.8	271.1	270.2	268.9	268.9	268.9	269.8	272.0	274.8	276.1
32.5°	260.7	258.9	257.1	257.1	255.8	255.8	256.2	257.1	259.4	259.8	262.1
35°	247.2	245.4	244.0	243.1	243.6	241.8	242.7	244.0	246.7	247.6	249.0
37.5°	234.1	233.6	230.9	229.6	230.5	230.5	230.0	230.9	232.7	234.5	235.4
40°	219.6	218.7	218.7	217.4	217.8	216.0	217.4	218.3	219.2	221.0	222.3
42.5°	207.0	206.1	204.3	204.7	203.4	203.4	204.3	204.7	206.1	208.3	209.2
45°	193.4	193.4	192.5	191.2	191.6	190.2	191.2	191.6	193.4	195.7	194.8
47.5°	180.3	179.9	179.9	178.0	179.0	177.6	179.0	179.4	180.3	181.7	181.2
50°	167.7	166.3	166.7	166.3	165.8	165.8	166.7	166.7	167.7	167.7	169.0
52.5°	154.5	154.5	153.6	154.1	155.0	154.1	155.5	154.1	155.0	155.5	156.4
55°	142.8	141.9	142.3	141.9	143.7	142.3	143.7	142.8	143.7	143.3	144.2
57.5°	130.1	128.8	129.2	128.8	130.1	129.7	131.1	129.7	130.1	130.6	132.0
60°	115.7	115.7	115.7	114.8	116.1	116.1	115.7	115.7	117.5	118.4	117.9
62.5°	102.1	101.7	100.3	99.9	100.3	99.4	101.2	100.8	101.7	102.6	103.5
65°	87.2	86.3	85.9	85.0	85.0	84.5	85.0	86.8	87.2	87.7	89.9
67.5°	75.0	74.6	74.1	72.8	72.8	73.7	73.7	73.7	76.4	75.0	76.8
70°	64.2	63.3	62.4	61.9	61.9	62.4	62.8	63.3	62.8	64.6	65.1
72.5°	53.8	54.2	53.3	53.3	53.3	52.9	52.9	53.8	54.2	53.8	54.2
75°	44.7	44.7	44.3	44.7	44.7	44.3	44.3	45.2	45.2	44.7	46.1
77.5°	36.2	35.7	34.8	33.9	34.3	33.9	34.3	33.9	35.2	36.6	35.7
80°	25.3	24.9	24.9	24.9	25.3	24.9	25.8	24.9	25.3	25.3	25.8
82.5°	18.1	18.5	18.5	18.1	18.5	18.1	18.5	18.5	18.5	18.1	18.5
85°	11.7	11.7	11.7	11.7	11.3	11.7	11.7	11.7	12.2	11.7	12.2
87.5°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.4	5.0	5.4
90°	24.5	24.9	25.7	26.4	27.2	28.0	27.2	26.4	25.7	24.9	24.5
92.5°	24.5	24.6	24.9	25.2	25.4	25.7	25.4	25.2	24.9	24.6	24.5
95°	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5	24.5
97.5°	23.3	23.4	23.7	24.0	24.2	24.5	24.2	24.0	23.7	23.4	23.3
100°	29.2	28.7	27.6	26.6	25.5	24.5	25.5	26.6	27.6	28.7	29.2
102.5°	275.3	264.4	242.6	220.9	199.1	177.3	199.1	220.9	242.6	264.4	275.3
105°	347.6	347.5	347.2	346.9	346.7	346.4	346.7	346.9	347.2	347.5	347.6
107.5°	425.8	425.3	424.2	423.2	422.1	421.1	422.1	423.2	424.2	425.3	425.8
110°	498.1	498.2	498.5	498.7	499.0	499.2	499.0	498.7	498.5	498.2	498.1

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	571.6	571.3	570.8	570.3	569.7	569.2	569.7	570.3	570.8	571.3	571.6
115°	646.2	645.4	643.9	642.3	640.8	639.2	640.8	642.3	643.9	645.4	646.2
117.5°	717.4	717.1	716.6	716.1	715.5	715.0	715.5	716.1	716.6	717.1	717.4
120°	789.7	789.1	787.8	786.5	785.2	783.9	785.2	786.5	787.8	789.1	789.7
122.5°	856.2	855.4	853.9	852.3	850.8	849.2	850.8	852.3	853.9	855.4	856.2
125°	919.2	918.8	918.0	917.3	916.5	915.7	916.5	917.3	918.0	918.8	919.2
127.5°	979.8	978.8	976.7	974.6	972.6	970.5	972.6	974.6	976.7	978.8	979.8
130°	1037.0	1036.4	1035.1	1033.8	1032.5	1031.2	1032.5	1033.8	1035.1	1036.4	1037.0
132.5°	1093.0	1092.3	1091.0	1089.7	1088.4	1087.1	1088.4	1089.7	1091.0	1092.3	1093.0
135°	1144.3	1143.5	1142.0	1140.4	1138.9	1137.3	1138.9	1140.4	1142.0	1143.5	1144.3
137.5°	1195.6	1195.0	1193.7	1192.4	1191.1	1189.8	1191.1	1192.4	1193.7	1195.0	1195.6
140°	1242.3	1241.5	1240.0	1238.4	1236.9	1235.3	1236.9	1238.4	1240.0	1241.5	1242.3
142.5°	1285.4	1284.6	1283.1	1281.6	1280.0	1278.5	1280.0	1281.6	1283.1	1284.6	1285.4
145°	1327.4	1326.6	1325.1	1323.5	1322.0	1320.4	1322.0	1323.5	1325.1	1326.6	1327.4
147.5°	1363.6	1362.7	1360.9	1359.0	1357.2	1355.4	1357.2	1359.0	1360.9	1362.7	1363.6
150°	1398.6	1397.6	1395.5	1393.4	1391.4	1389.3	1391.4	1393.4	1395.5	1397.6	1398.6
152.5°	1428.9	1428.0	1426.2	1424.4	1422.6	1420.8	1422.6	1424.4	1426.2	1428.0	1428.9
155°	1456.9	1455.9	1453.8	1451.7	1449.7	1447.6	1449.7	1451.7	1453.8	1455.9	1456.9
157.5°	1480.2	1479.2	1477.1	1475.0	1473.0	1470.9	1473.0	1475.0	1477.1	1479.2	1480.2
160°	1502.4	1501.4	1499.3	1497.2	1495.2	1493.1	1495.2	1497.2	1499.3	1501.4	1502.4
162.5°	1523.4	1522.2	1519.9	1517.6	1515.2	1512.9	1515.2	1517.6	1519.9	1522.2	1523.4
165°	1539.7	1538.7	1536.6	1534.5	1532.5	1530.4	1532.5	1534.5	1536.6	1538.7	1539.7
167.5°	1553.7	1552.5	1550.2	1547.9	1545.5	1543.2	1545.5	1547.9	1550.2	1552.5	1553.7
170°	1564.2	1563.0	1560.7	1558.4	1556.0	1553.7	1556.0	1558.4	1560.7	1563.0	1564.2
172.5°	1571.2	1570.0	1567.7	1565.4	1563.0	1560.7	1563.0	1565.4	1567.7	1570.0	1571.2
175°	1577.1	1575.9	1573.6	1571.3	1568.9	1566.6	1568.9	1571.3	1573.6	1575.9	1577.1
177.5°	1579.4	1578.4	1576.3	1574.2	1572.2	1570.1	1572.2	1574.2	1576.3	1578.4	1579.4
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4	550.4
2.5°	520.6	522.8	521.0	519.7	523.3	525.1	525.1	528.3	531.4	534.1	534.6
5°	488.5	492.1	493.0	492.6	498.0	500.7	506.6	509.7	514.3	517.4	521.0
7.5°	459.1	464.1	464.5	465.5	473.6	478.1	483.1	491.2	497.5	502.1	506.1
10°	429.8	432.9	436.1	440.1	448.3	456.0	463.2	471.8	479.9	484.4	490.3
12.5°	407.6	409.9	413.5	416.2	424.8	431.6	441.1	452.8	464.5	468.2	475.4
15°	384.6	385.9	393.2	395.9	403.1	414.4	420.3	431.6	444.2	451.0	459.1
17.5°	357.9	366.0	370.6	373.7	382.8	391.8	401.3	413.0	429.3	435.6	441.5
20°	338.9	344.8	349.8	353.8	362.0	375.5	384.1	393.6	409.0	416.2	424.8
22.5°	322.2	327.2	331.7	336.2	341.6	353.8	363.8	376.9	392.2	399.0	409.0
25°	306.4	311.4	314.1	319.5	326.7	335.3	347.1	358.8	374.2	381.9	391.3
27.5°	291.0	296.0	301.0	305.5	310.5	318.6	326.7	341.6	357.5	366.5	374.6
30°	277.9	280.2	284.7	289.7	294.6	302.3	311.8	322.2	340.3	348.4	358.4
32.5°	263.5	267.5	270.7	274.3	280.6	287.0	295.5	308.6	323.1	330.8	341.6
35°	249.9	253.5	255.8	262.1	266.2	272.9	281.5	293.3	305.5	314.1	323.6
37.5°	236.8	240.4	243.1	246.7	252.2	258.0	267.1	275.7	290.1	297.3	308.2
40°	223.2	226.4	229.6	233.6	238.6	245.8	251.3	262.1	273.8	282.0	290.1
42.5°	210.1	211.9	215.6	220.1	225.0	231.4	239.1	247.6	259.4	266.6	273.8
45°	196.1	199.3	203.4	206.5	211.0	217.4	224.1	231.8	243.6	250.8	258.5
47.5°	183.0	185.3	188.0	193.0	198.8	203.4	210.6	217.8	228.7	235.4	242.7
50°	169.5	171.7	175.8	179.0	183.5	189.3	196.1	203.8	214.2	218.7	225.9
52.5°	156.8	157.7	161.8	164.9	169.5	176.2	181.7	188.4	198.4	203.4	210.6
55°	144.2	145.1	147.3	150.5	155.5	160.9	166.7	174.4	183.0	187.5	194.3
57.5°	131.1	132.0	134.2	136.5	141.4	146.4	153.2	159.5	168.1	172.2	178.5
60°	117.9	117.9	120.2	123.4	127.0	131.5	137.4	145.1	151.4	156.4	160.9
62.5°	103.9	105.3	106.6	108.9	113.0	118.4	123.4	128.8	136.5	140.1	144.2
65°	89.9	91.3	94.0	96.3	99.4	103.0	109.4	113.9	119.8	123.8	127.4
67.5°	77.7	79.1	80.9	83.6	85.9	89.9	94.4	99.0	105.3	108.0	110.7
70°	65.1	66.4	67.8	71.4	73.7	76.8	80.0	84.5	89.9	91.7	94.0
72.5°	55.1	55.6	57.4	58.3	61.5	64.2	67.8	70.5	74.6	76.8	78.6
75°	46.5	46.5	47.0	47.9	49.7	51.5	54.2	56.9	60.6	61.9	64.2
77.5°	36.6	38.0	37.5	38.4	39.3	40.2	42.5	44.3	47.9	48.8	49.7
80°	26.2	26.7	28.0	29.4	29.4	30.7	32.1	32.5	34.8	36.2	36.2
82.5°	19.0	19.4	19.0	19.4	19.9	20.3	21.7	23.5	23.5	24.0	24.9
85°	11.7	11.7	12.2	12.7	12.7	12.2	13.1	12.7	13.1	14.0	14.0
87.5°	5.9	5.4	5.4	5.4	5.4	5.4	5.9	5.4	5.9	5.9	5.9
90°	23.9	22.6	21.3	20.0	18.7	16.9	15.1	13.2	11.4	10.5	9.5
92.5°	23.9	22.6	21.3	20.0	18.7	17.1	15.6	14.0	12.5	11.7	12.9
95°	23.9	22.6	21.3	20.0	18.7	28.5	38.4	48.2	58.1	63.0	63.4
97.5°	23.0	22.5	22.0	21.5	21.0	45.6	70.2	94.9	119.5	131.8	131.0
100°	48.5	87.1	125.8	164.4	203.0	202.0	200.9	199.9	198.8	198.3	197.9
102.5°	275.0	274.5	274.0	273.5	273.0	272.5	271.9	271.4	270.9	270.6	270.1
105°	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.6	347.1
107.5°	425.7	425.4	425.1	424.9	424.6	424.1	423.6	423.1	422.6	422.3	422.3
110°	498.5	499.3	500.0	500.8	501.6	501.1	500.5	500.0	499.5	499.2	499.2

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	572.1	573.1	574.2	575.2	576.2	576.0	575.7	575.5	575.2	575.1	574.7
115°	646.7	647.8	648.8	649.9	650.9	650.6	650.4	650.1	649.8	649.7	649.1
117.5°	718.2	719.7	721.3	722.8	724.4	723.4	722.3	721.3	720.2	719.7	719.7
120°	790.0	790.5	791.0	791.5	792.0	791.2	790.4	789.7	788.9	788.5	788.6
122.5°	856.5	857.0	857.5	858.0	858.5	858.3	858.0	857.8	857.5	857.4	856.7
125°	919.7	920.7	921.8	922.8	923.8	923.8	923.8	923.8	923.8	923.8	922.9
127.5°	980.1	980.6	981.1	981.7	982.2	982.4	982.7	982.9	983.2	983.3	982.7
130°	1037.4	1038.2	1038.9	1039.7	1040.5	1040.2	1040.0	1039.7	1039.4	1039.3	1038.7
132.5°	1093.0	1093.0	1093.0	1093.0	1093.0	1093.8	1094.6	1095.3	1096.1	1096.5	1095.7
135°	1144.6	1145.1	1145.6	1146.1	1146.6	1147.1	1147.7	1148.2	1148.7	1149.0	1148.2
137.5°	1195.6	1195.6	1195.6	1195.6	1195.6	1196.1	1196.7	1197.2	1197.7	1198.0	1197.2
140°	1242.0	1241.5	1241.0	1240.5	1240.0	1240.2	1240.5	1240.7	1241.0	1241.1	1240.8
142.5°	1285.4	1285.4	1285.4	1285.4	1285.4	1284.9	1284.4	1283.9	1283.4	1283.1	1283.0
145°	1327.3	1327.0	1326.8	1326.5	1326.3	1326.3	1326.3	1326.3	1326.3	1326.3	1326.0
147.5°	1363.5	1363.2	1362.9	1362.7	1362.4	1362.2	1361.9	1361.7	1361.4	1361.3	1361.3
150°	1398.3	1397.8	1397.3	1396.8	1396.3	1395.8	1395.2	1394.7	1394.2	1393.9	1394.2
152.5°	1428.6	1428.1	1427.6	1427.1	1426.6	1426.1	1425.6	1425.1	1424.6	1424.3	1424.9
155°	1456.5	1455.7	1455.0	1454.2	1453.4	1452.9	1452.4	1451.9	1451.4	1451.1	1451.9
157.5°	1479.8	1479.1	1478.3	1477.6	1476.8	1476.8	1476.8	1476.8	1476.8	1476.8	1477.2
160°	1501.9	1500.8	1499.8	1498.7	1497.7	1497.5	1497.2	1497.0	1496.7	1496.6	1497.4
162.5°	1522.6	1521.1	1519.5	1518.0	1516.4	1516.1	1515.9	1515.6	1515.3	1515.2	1516.0
165°	1538.9	1537.4	1535.8	1534.3	1532.7	1532.5	1532.2	1532.0	1531.7	1531.6	1532.4
167.5°	1552.8	1551.0	1549.2	1547.4	1545.6	1545.3	1545.1	1544.8	1544.5	1544.4	1545.2
170°	1563.2	1561.1	1559.0	1557.0	1554.9	1554.6	1554.4	1554.1	1553.8	1553.7	1554.6
172.5°	1570.3	1568.5	1566.7	1564.9	1563.1	1562.6	1562.0	1561.5	1561.0	1560.7	1561.6
175°	1576.1	1574.0	1571.9	1569.8	1567.7	1567.5	1567.2	1567.0	1566.7	1566.6	1567.4
177.5°	1578.5	1576.7	1574.8	1573.0	1571.2	1571.0	1570.7	1570.5	1570.2	1570.1	1570.9
180°	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6	1573.6

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	550.4	550.4	550.4	550.4
2.5°	537.8	541.8	545.9	550.9
5°	526.9	534.1	541.8	549.1
7.5°	515.2	525.6	535.5	545.9
10°	502.1	515.2	526.5	540.9
12.5°	487.6	501.6	517.4	533.7
15°	473.1	490.8	507.5	526.0
17.5°	459.6	476.3	494.8	517.0
20°	443.3	461.8	482.6	506.1
22.5°	426.1	446.5	469.1	494.4
25°	411.7	432.5	454.2	480.8
27.5°	395.9	417.6	438.8	467.3
30°	377.8	401.3	423.0	452.3
32.5°	360.6	384.1	408.1	435.6
35°	343.9	366.9	390.9	418.9
37.5°	328.1	348.9	372.4	397.7
40°	313.2	332.1	352.9	376.0
42.5°	294.2	316.3	335.8	352.5
45°	277.9	296.0	314.1	327.6
47.5°	258.9	277.0	292.4	303.2
50°	243.1	257.6	270.2	279.7
52.5°	224.1	237.7	248.1	255.3
55°	205.6	217.4	226.4	231.4
57.5°	188.9	196.6	203.4	207.9
60°	170.4	176.2	182.1	187.1
62.5°	150.5	156.8	160.0	165.4
65°	132.9	136.9	141.9	143.7
67.5°	115.7	117.9	121.1	124.7
70°	97.6	99.0	102.1	107.1
72.5°	81.8	83.1	85.4	87.2
75°	65.1	66.4	68.2	70.0
77.5°	51.1	51.5	52.4	54.2
80°	37.1	38.4	39.3	39.8
82.5°	25.8	26.2	26.2	26.7
85°	16.3	15.4	15.4	15.8
87.5°	5.9	6.8	6.8	7.7
90°	7.4	5.3	3.3	1.2
92.5°	15.2	17.5	19.9	22.2
95°	64.2	64.9	65.7	66.5
97.5°	129.5	127.9	126.4	124.8
100°	197.1	196.4	195.6	194.8
102.5°	269.1	268.0	267.0	266.0
105°	346.0	345.0	343.9	342.9
107.5°	422.3	422.3	422.3	422.3
110°	499.2	499.2	499.2	499.2

TEST NUMBER: P1027166

CATALOG NUMBER: S125RDIP-B375D1270UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	573.9	573.2	572.4	571.6
115°	647.8	646.5	645.2	643.9
117.5°	719.7	719.7	719.7	719.7
120°	788.9	789.2	789.4	789.7
122.5°	855.4	854.1	852.8	851.5
125°	921.1	919.3	917.5	915.7
127.5°	981.4	980.1	978.8	977.5
130°	1037.4	1036.1	1034.8	1033.5
132.5°	1094.2	1092.6	1091.1	1089.5
135°	1146.7	1145.1	1143.6	1142.0
137.5°	1195.7	1194.1	1192.6	1191.0
140°	1240.3	1239.8	1239.3	1238.8
142.5°	1282.7	1282.4	1282.2	1281.9
145°	1325.5	1325.0	1324.4	1323.9
147.5°	1361.3	1361.3	1361.3	1361.3
150°	1394.7	1395.2	1395.8	1396.3
152.5°	1426.2	1427.5	1428.8	1430.1
155°	1453.4	1455.0	1456.5	1458.1
157.5°	1477.9	1478.7	1479.4	1480.2
160°	1498.9	1500.5	1502.0	1503.6
162.5°	1517.5	1519.1	1520.6	1522.2
165°	1533.9	1535.5	1537.0	1538.6
167.5°	1546.7	1548.3	1549.8	1551.4
170°	1556.4	1558.3	1560.1	1561.9
172.5°	1563.4	1565.3	1567.1	1568.9
175°	1568.9	1570.5	1572.0	1573.6
177.5°	1572.4	1574.0	1575.5	1577.1
180°	1573.6	1573.6	1573.6	1573.6

(END OF REPORT)