

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027234

Luminaire Tested: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027234
REPORT IS A COMBINATION OF REPORTS P1005645 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4717.0 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	50	49	48
2	90	83	77	72	83	77	71	67	65	61	58	55	52	50	45	43	41
3	82	73	66	60	76	68	61	56	58	53	49	49	45	42	40	38	36
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	35	29	25	30	25	22	25	22	19
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5854	5854	5854	5854
5°	5849	6597	5849	5071
10°	5816	7414	5797	4384
15°	5753	7843	5713	3817
20°	5676	8467	5626	3450
25°	5577	9584	5514	3131
30°	5476	10187	5394	2903
35°	5345	8378	5270	2690
40°	5113	5689	5069	2499
45°	4807	4090	4801	2311
50°	4494	3145	4516	2138
55°	4143	2557	4134	1970
60°	3814	2096	3795	1749
65°	3432	1746	3453	1408
70°	3117	1402	3103	1172
75°	2633	1062	2633	963
80°	2133	648	2110	648
85°	1504	342	1458	385

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8332 cd/sqm

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.6	1.9
10°-20°	256.9	5.4
20°-30°	407.3	8.6
30°-40°	492.1	10.4
40°-50°	438.1	9.3
50°-60°	336.0	7.1
60°-70°	218.2	4.6
70°-80°	105.9	2.2
80°-90°	26.1	0.6
90°-100°	26.0	0.6
100°-110°	172.6	3.7
110°-120°	310.8	6.6
120°-130°	398.9	8.5
130°-140°	429.0	9.1
140°-150°	402.7	8.5
150°-160°	325.7	6.9
160°-170°	210.6	4.5
170°-180°	72.6	1.5
0°-30°	751.7	15.9
0°-40°	1243.9	26.4
0°-60°	2018.0	42.8
0°-90°	2368.2	50.2
90°-120°	509.3	10.8
90°-150°	1739.8	36.9
90°-180°	2349.0	49.8
0°-180°	4717.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	914	914	914	914	914	
5°	911	1047	911	805	911	87
15°	873	1258	867	612	873	246
25°	798	1506	789	492	798	368
35°	695	1250	686	401	695	433
45°	544	559	543	316	544	420
55°	384	307	383	236	384	344
65°	238	174	240	140	238	238
75°	116	81	116	74	116	125
85°	26	17	26	20	26	30
90°	1	14	1	14	1	3
95°	32	12	32	12	32	40
105°	167	168	167	168	167	177
115°	313	311	313	311	313	310
125°	445	445	445	445	445	397
135°	555	553	555	553	555	428
145°	643	642	643	642	643	402
155°	708	703	708	703	708	326
165°	748	744	748	744	748	211
175°	765	761	765	761	765	73
180°	765	765	765	765	765	

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	914.4	921.9	924.1	930.1	936.9	938.4	942.1	947.4	950.4	949.6	949.6
5°	911.4	924.1	933.1	943.6	956.4	961.6	966.1	977.4	986.4	991.6	1000.6
7.5°	906.1	924.9	939.9	955.6	975.1	984.1	993.9	1009.6	1026.1	1036.6	1046.4
10°	897.9	921.9	942.9	966.1	992.4	1005.9	1017.9	1041.9	1062.1	1075.6	1098.1
12.5°	885.9	915.9	945.1	975.9	1008.9	1023.1	1039.6	1065.9	1094.4	1113.9	1132.6
15°	873.1	909.1	940.6	977.4	1017.1	1038.9	1059.9	1087.6	1113.1	1134.9	1156.7
17.5°	858.1	896.4	935.4	977.4	1022.4	1044.1	1062.1	1095.1	1122.1	1143.9	1163.4
20°	840.1	882.9	927.1	973.6	1019.4	1039.6	1056.9	1092.9	1116.9	1140.1	1167.9
22.5°	820.6	867.1	914.4	960.1	1005.1	1026.9	1047.1	1078.6	1104.9	1136.4	1172.4
25°	798.1	849.1	897.1	942.9	985.6	1005.9	1023.9	1058.4	1095.1	1134.9	1175.4
27.5°	775.6	825.1	871.6	913.6	960.1	978.9	996.9	1040.4	1083.9	1125.9	1181.4
30°	750.8	801.1	841.6	880.6	925.6	945.1	967.6	1017.1	1066.6	1123.6	1191.2
32.5°	723.1	768.9	806.4	846.9	887.4	911.4	939.9	993.9	1050.9	1119.1	1205.4
35°	695.3	732.1	766.6	804.9	853.6	879.1	906.9	963.9	1035.1	1116.9	1217.4
37.5°	660.1	695.3	722.3	761.3	811.6	841.6	869.4	935.4	1016.4	1111.6	1216.7
40°	624.1	654.1	679.6	720.1	774.9	802.6	832.6	904.6	996.9	1096.6	1198.7
42.5°	585.1	610.6	638.3	677.3	730.6	757.6	792.1	876.1	969.9	1075.6	1152.2
45°	543.8	568.6	591.8	632.3	685.6	714.8	752.3	838.6	936.9	1031.4	1077.1
47.5°	503.3	525.1	549.8	585.1	639.1	671.3	709.6	801.9	892.6	972.1	975.9
50°	464.3	481.6	502.6	538.6	594.8	625.6	665.3	751.6	840.1	894.9	858.1
52.5°	423.8	439.6	461.3	492.8	545.3	581.3	615.8	702.1	776.4	813.1	745.6
55°	384.1	397.6	420.1	455.3	501.1	528.8	564.1	644.3	709.6	710.3	636.8
57.5°	345.0	357.0	375.8	407.3	450.1	482.3	514.6	584.3	628.6	615.8	534.1
60°	310.5	318.0	335.3	366.0	405.8	429.1	463.6	522.1	551.3	528.1	440.3
62.5°	274.5	282.0	295.5	320.3	357.8	382.6	404.3	452.3	472.6	437.3	365.3
65°	238.5	247.5	257.3	276.8	312.0	328.5	348.0	383.3	402.8	361.5	299.3
67.5°	207.0	211.5	221.3	241.5	266.3	281.3	294.8	318.8	322.5	289.5	238.5
70°	177.8	179.3	188.3	200.3	219.0	228.0	239.3	253.5	253.5	226.5	186.0
72.5°	144.8	147.0	153.8	166.5	177.8	182.3	186.0	195.0	193.5	168.8	141.0
75°	116.3	117.8	123.0	129.0	133.5	141.8	144.8	143.3	142.5	121.5	105.8
77.5°	90.0	90.8	94.5	99.8	100.5	103.5	101.3	101.3	94.5	82.5	74.3
80°	66.0	66.8	68.3	69.8	69.8	69.8	69.8	66.0	61.5	54.0	51.8
82.5°	44.3	44.3	45.0	46.5	45.8	44.3	42.8	39.0	36.0	33.8	32.3
85°	26.3	26.3	27.0	26.3	23.3	22.5	21.0	20.3	19.5	18.8	18.8
87.5°	12.8	12.0	10.5	9.0	9.0	9.0	9.0	9.0	9.0	8.3	8.3
90°	0.6	1.6	2.6	3.6	4.6	5.1	5.5	6.4	7.3	8.2	9.1
92.5°	10.8	9.7	8.5	7.4	6.3	5.7	6.1	6.8	7.6	8.3	9.1
95°	32.3	31.9	31.5	31.2	30.8	30.6	28.2	23.4	18.7	13.9	9.1
97.5°	60.7	61.5	62.2	63.0	63.7	64.1	58.1	46.1	34.2	22.2	10.2
100°	94.7	95.1	95.5	95.8	96.2	96.4	96.6	97.1	97.6	98.1	98.6
102.5°	129.2	129.7	130.2	130.7	131.2	131.5	131.6	131.9	132.1	132.4	132.6
105°	166.6	167.1	167.6	168.1	168.6	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.2	205.2	205.2	205.2	205.2	205.2	205.3	205.6	205.8	206.1	206.3
110°	242.6	242.6	242.6	242.6	242.6	242.6	242.7	243.0	243.2	243.5	243.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	277.7	278.1	278.5	278.8	279.2	279.4	279.5	279.6	279.7	279.9	280.0
115°	312.9	313.5	314.1	314.8	315.4	315.7	315.8	315.9	316.0	316.2	316.3
117.5°	349.7	349.7	349.7	349.7	349.7	349.7	350.0	350.5	351.0	351.5	352.0
120°	383.7	383.6	383.5	383.4	383.3	383.2	383.4	383.8	384.1	384.5	384.9
122.5°	413.8	414.4	415.0	415.7	416.3	416.6	416.7	416.8	416.9	417.1	417.2
125°	445.0	445.9	446.7	447.6	448.5	448.9	448.9	448.9	448.9	448.9	448.9
127.5°	475.0	475.6	476.2	476.9	477.5	477.8	477.7	477.6	477.5	477.4	477.3
130°	502.2	502.8	503.4	504.1	504.7	505.0	505.1	505.2	505.3	505.5	505.6
132.5°	529.4	530.2	530.9	531.7	532.4	532.8	532.6	532.2	531.9	531.5	531.1
135°	554.9	555.7	556.4	557.2	557.9	558.3	558.2	557.9	557.7	557.4	557.2
137.5°	578.7	579.5	580.2	581.0	581.7	582.1	582.0	581.7	581.5	581.2	581.0
140°	602.0	602.2	602.5	602.7	603.0	603.1	603.0	602.9	602.8	602.6	602.5
142.5°	622.9	623.0	623.2	623.3	623.4	623.5	623.6	623.9	624.1	624.4	624.6
145°	643.4	643.6	643.9	644.1	644.4	644.5	644.5	644.5	644.5	644.5	644.5
147.5°	661.5	661.5	661.5	661.5	661.5	661.5	661.6	661.7	661.8	662.0	662.1
150°	678.5	678.3	678.0	677.8	677.5	677.4	677.5	677.8	678.0	678.3	678.5
152.5°	694.9	694.3	693.7	693.0	692.4	692.1	692.2	692.5	692.7	693.0	693.2
155°	708.5	707.7	707.0	706.2	705.5	705.1	705.2	705.5	705.8	706.0	706.3
157.5°	719.3	718.9	718.5	718.2	717.8	717.6	717.6	717.6	717.6	717.6	717.6
160°	730.6	729.8	729.1	728.3	727.6	727.2	727.3	727.4	727.5	727.7	727.8
162.5°	739.7	738.9	738.2	737.4	736.7	736.3	736.4	736.5	736.6	736.8	736.9
165°	747.7	746.9	746.2	745.4	744.7	744.3	744.4	744.5	744.6	744.7	744.8
167.5°	753.9	753.1	752.4	751.6	750.9	750.5	750.6	750.7	750.8	751.0	751.1
170°	759.0	758.1	757.2	756.3	755.4	755.0	755.1	755.2	755.3	755.5	755.6
172.5°	762.4	761.5	760.6	759.7	758.8	758.4	758.5	758.8	759.1	759.3	759.6
175°	764.7	763.9	763.2	762.4	761.7	761.3	761.4	761.5	761.6	761.7	761.8
177.5°	766.4	765.6	764.9	764.1	763.4	763.0	763.1	763.2	763.3	763.4	763.5
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	953.4	958.6	963.1	960.9	969.9	969.1	970.6	973.6	974.4	972.9	969.9
5°	1005.1	1012.6	1025.4	1032.1	1030.6	1036.6	1039.6	1044.1	1048.6	1047.1	1047.1
7.5°	1062.9	1073.4	1086.1	1103.4	1105.6	1110.9	1119.9	1119.9	1125.1	1122.9	1122.1
10°	1113.1	1125.9	1146.1	1159.7	1165.7	1168.7	1177.7	1180.7	1186.7	1187.4	1187.4
12.5°	1154.4	1176.9	1190.4	1203.9	1206.9	1211.4	1218.2	1222.7	1224.9	1224.9	1222.7
15°	1176.2	1194.2	1209.9	1224.2	1232.4	1236.2	1242.9	1248.2	1251.2	1257.9	1259.4
17.5°	1185.2	1206.9	1232.4	1252.7	1266.9	1270.7	1284.2	1288.7	1294.7	1297.7	1301.4
20°	1197.9	1229.4	1260.2	1284.9	1298.4	1308.2	1322.4	1343.4	1349.4	1349.4	1347.2
22.5°	1209.2	1249.7	1291.7	1331.4	1342.7	1362.2	1388.4	1410.9	1419.9	1423.7	1420.7
25°	1222.7	1278.2	1332.9	1382.4	1413.2	1427.4	1462.7	1489.7	1500.2	1506.2	1507.7
27.5°	1245.9	1315.7	1385.4	1448.4	1479.9	1496.4	1533.2	1556.5	1569.2	1574.5	1570.7
30°	1272.2	1357.7	1438.7	1494.9	1515.9	1536.2	1560.2	1569.2	1566.2	1566.2	1577.5
32.5°	1299.2	1387.7	1459.7	1496.4	1503.9	1500.9	1491.2	1464.2	1448.4	1448.4	1458.2
35°	1314.2	1390.7	1427.4	1415.4	1386.2	1368.9	1315.7	1285.7	1251.9	1249.7	1260.9
37.5°	1305.9	1338.9	1323.9	1245.2	1205.4	1172.4	1089.1	1056.1	1031.4	996.9	1050.1
40°	1248.2	1236.9	1158.9	1045.6	1001.4	954.9	888.9	855.9	821.4	816.1	828.9
42.5°	1150.7	1083.9	969.9	860.4	815.4	782.4	732.1	699.8	678.1	669.1	684.1
45°	1029.1	924.1	810.1	723.1	673.6	656.3	610.6	582.1	565.6	558.8	569.3
47.5°	880.6	774.9	666.8	593.3	564.1	546.8	516.1	491.3	477.1	472.6	477.1
50°	747.8	639.1	548.3	501.1	474.8	460.6	435.1	419.3	408.1	405.1	412.6
52.5°	633.1	534.1	465.1	423.1	405.8	393.8	375.8	362.3	355.5	352.5	357.8
55°	530.3	450.1	394.6	358.5	345.8	338.3	322.5	315.0	307.5	306.8	312.0
57.5°	439.6	384.1	333.0	307.5	303.8	292.5	279.0	272.3	268.5	267.8	270.0
60°	366.0	316.5	285.8	263.3	258.0	249.0	241.5	237.0	232.5	231.0	232.5
62.5°	304.5	265.5	240.8	225.8	218.3	216.0	207.8	202.5	201.8	201.8	203.3
65°	251.3	218.3	202.5	190.5	185.3	183.0	177.0	173.3	174.0	174.0	174.8
67.5°	204.8	180.8	166.5	160.5	156.0	155.3	149.3	147.8	146.3	146.3	147.8
70°	162.8	147.8	137.3	134.3	133.5	128.3	126.0	125.3	123.0	123.8	123.8
72.5°	127.5	117.8	111.8	107.3	108.0	105.0	102.0	102.0	100.5	102.8	102.8
75°	94.5	90.0	85.5	84.0	85.5	84.0	81.8	81.0	81.8	81.0	81.0
77.5°	69.8	67.5	66.0	65.3	65.3	62.3	60.8	62.3	59.3	60.8	60.8
80°	48.8	45.8	45.0	43.5	44.3	42.0	42.8	41.3	41.3	41.3	41.3
82.5°	30.8	30.0	30.0	30.0	29.3	29.3	29.3	29.3	29.3	29.3	28.5
85°	18.8	18.0	18.0	18.0	17.3	17.3	17.3	17.3	17.3	17.3	17.3
87.5°	7.5	8.3	8.3	9.0	8.3	7.5	7.5	7.5	8.3	8.3	7.5
90°	9.7	10.3	11.0	11.6	11.9	12.1	12.5	12.8	13.2	13.6	13.2
92.5°	9.7	10.3	11.0	11.6	11.9	12.0	12.1	12.2	12.4	12.5	12.4
95°	9.7	10.3	11.0	11.6	11.9	11.9	11.9	11.9	11.9	11.9	11.9
97.5°	10.4	10.7	10.9	11.2	11.3	11.4	11.5	11.6	11.8	11.9	11.8
100°	79.8	61.1	42.3	23.6	14.2	13.9	13.4	12.9	12.4	11.9	12.4
102.5°	132.9	133.1	133.4	133.7	133.8	128.5	117.9	107.4	96.8	86.2	96.8
105°	168.9	168.9	168.9	168.9	168.9	168.8	168.7	168.6	168.4	168.3	168.4
107.5°	206.4	206.6	206.7	206.8	206.9	206.6	206.1	205.6	205.1	204.6	205.1
110°	243.3	242.9	242.6	242.2	242.0	242.1	242.2	242.3	242.5	242.6	242.5

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	279.5	279.0	278.5	278.0	277.7	277.6	277.3	277.1	276.8	276.6	276.8
115°	315.8	315.3	314.8	314.3	314.0	313.6	312.9	312.1	311.4	310.6	311.4
117.5°	351.2	350.5	349.7	349.0	348.6	348.5	348.2	348.0	347.7	347.5	347.7
120°	384.6	384.4	384.1	383.8	383.7	383.4	382.8	382.1	381.5	380.9	381.5
122.5°	417.0	416.7	416.5	416.2	416.1	415.7	415.0	414.2	413.5	412.7	413.5
125°	448.4	447.9	447.4	446.9	446.7	446.5	446.1	445.8	445.4	445.0	445.4
127.5°	477.0	476.8	476.5	476.2	476.1	475.6	474.6	473.6	472.6	471.6	472.6
130°	505.2	504.8	504.5	504.1	503.9	503.6	503.0	502.3	501.7	501.1	501.7
132.5°	531.1	531.1	531.1	531.1	531.1	530.8	530.2	529.5	528.9	528.3	528.9
135°	557.0	556.7	556.5	556.2	556.1	555.7	555.0	554.2	553.5	552.7	553.5
137.5°	581.0	581.0	581.0	581.0	581.0	580.7	580.1	579.4	578.8	578.2	578.8
140°	602.8	603.0	603.3	603.6	603.7	603.3	602.6	601.8	601.1	600.3	601.1
142.5°	624.6	624.6	624.6	624.6	624.6	624.2	623.5	622.7	622.0	621.2	622.0
145°	644.6	644.8	644.9	645.0	645.1	644.7	644.0	643.2	642.5	641.7	642.5
147.5°	662.2	662.3	662.4	662.5	662.6	662.2	661.3	660.4	659.6	658.7	659.6
150°	678.7	679.0	679.2	679.5	679.6	679.1	678.1	677.1	676.1	675.1	676.1
152.5°	693.5	693.7	694.0	694.3	694.4	694.0	693.1	692.2	691.3	690.4	691.3
155°	706.7	707.1	707.4	707.8	708.0	707.5	706.5	705.4	704.4	703.4	704.4
157.5°	718.0	718.4	718.7	719.1	719.3	718.8	717.8	716.8	715.8	714.8	715.8
160°	728.3	728.8	729.3	729.8	730.1	729.6	728.6	727.5	726.5	725.5	726.5
162.5°	737.7	738.4	739.2	739.9	740.3	739.7	738.6	737.5	736.3	735.2	736.3
165°	745.6	746.3	747.1	747.8	748.2	747.7	746.7	745.7	744.7	743.7	744.7
167.5°	752.0	752.8	753.7	754.6	755.0	754.4	753.3	752.2	751.0	749.9	751.0
170°	756.6	757.6	758.6	759.6	760.1	759.5	758.4	757.3	756.1	755.0	756.1
172.5°	760.5	761.3	762.2	763.1	763.5	762.9	761.8	760.7	759.5	758.4	759.5
175°	762.8	763.8	764.9	765.9	766.4	765.8	764.7	763.6	762.4	761.3	762.4
177.5°	764.4	765.3	766.2	767.1	767.5	767.0	766.0	765.0	764.0	763.0	764.0
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	973.6	968.4	970.6	968.4	966.1	963.9	958.6	951.1	945.1	940.6	939.9
5°	1048.6	1041.9	1037.4	1035.1	1030.6	1024.6	1014.9	1003.6	990.1	984.9	974.4
7.5°	1117.6	1115.4	1104.9	1103.4	1100.4	1089.1	1072.6	1057.6	1040.4	1026.1	1012.6
10°	1182.9	1177.7	1170.2	1159.7	1158.2	1143.9	1128.1	1107.1	1084.6	1071.1	1047.1
12.5°	1223.4	1217.4	1209.2	1202.4	1198.7	1189.7	1167.9	1146.9	1126.6	1101.9	1080.9
15°	1252.7	1245.2	1230.2	1224.9	1220.4	1208.4	1192.7	1170.9	1143.9	1126.6	1096.6
17.5°	1292.4	1283.4	1268.4	1258.7	1250.4	1231.7	1209.2	1179.9	1154.4	1134.9	1107.9
20°	1338.2	1324.7	1305.2	1292.4	1280.4	1258.7	1227.2	1192.7	1155.9	1131.9	1104.1
22.5°	1413.9	1388.4	1357.7	1339.7	1323.2	1285.7	1248.2	1205.4	1164.2	1128.1	1094.4
25°	1487.4	1461.9	1423.7	1398.9	1373.4	1329.9	1280.4	1221.2	1168.7	1126.6	1082.4
27.5°	1555.7	1529.5	1494.2	1464.2	1439.4	1374.2	1308.9	1242.2	1175.4	1117.6	1072.6
30°	1571.5	1560.2	1533.2	1506.9	1484.4	1424.4	1348.7	1263.9	1183.7	1109.4	1059.1
32.5°	1476.2	1503.9	1510.7	1506.9	1492.7	1449.9	1380.2	1290.9	1195.7	1105.6	1036.6
35°	1278.2	1328.4	1380.2	1407.9	1421.4	1427.4	1386.2	1304.4	1203.9	1099.6	1021.6
37.5°	1059.9	1108.6	1190.4	1231.7	1277.4	1337.4	1353.9	1301.4	1200.2	1095.1	997.6
40°	870.9	933.1	1000.6	1038.1	1077.9	1185.9	1267.7	1261.7	1188.2	1078.6	978.9
42.5°	708.8	747.8	807.1	848.4	897.1	1017.9	1127.4	1181.4	1152.2	1058.4	954.9
45°	591.1	621.1	663.1	705.1	735.1	844.6	974.4	1062.9	1090.6	1022.4	918.1
47.5°	498.1	520.6	557.3	583.6	615.8	702.1	814.6	939.1	997.6	971.4	879.1
50°	426.8	444.8	474.1	490.6	519.1	593.3	678.8	809.4	897.9	900.9	827.4
52.5°	364.5	382.6	407.3	421.6	438.8	489.1	575.3	685.6	787.6	825.1	768.1
55°	317.3	327.8	348.0	359.3	375.0	423.8	478.6	572.3	678.8	740.3	704.3
57.5°	273.8	285.0	297.8	306.8	318.0	357.0	406.6	477.1	582.8	649.6	637.6
60°	238.5	245.3	257.3	264.0	274.5	300.0	334.5	405.1	489.1	552.1	558.8
62.5°	205.5	211.5	219.8	225.8	232.5	252.8	278.3	328.5	402.1	470.3	479.3
65°	177.0	182.3	186.8	192.0	197.3	210.0	231.8	270.8	327.8	391.6	411.1
67.5°	151.5	153.0	159.8	160.5	163.5	173.3	189.0	220.5	261.8	312.8	338.3
70°	126.8	129.8	131.3	133.5	136.5	143.3	156.0	172.5	203.3	244.5	268.5
72.5°	102.8	103.5	105.8	107.3	110.3	115.5	121.5	134.3	153.8	183.8	205.5
75°	81.8	82.5	84.0	84.8	87.0	88.5	91.5	100.5	114.0	132.0	147.8
77.5°	61.5	63.0	64.5	64.5	65.3	66.8	68.3	71.3	78.0	90.0	103.5
80°	42.0	42.8	42.8	43.5	42.8	45.0	47.3	51.0	54.0	57.8	64.5
82.5°	29.3	29.3	29.3	30.0	30.0	30.8	30.8	31.5	32.3	34.5	37.5
85°	18.0	18.0	18.8	17.3	18.0	18.8	18.8	18.0	18.8	19.5	20.3
87.5°	7.5	7.5	8.3	8.3	8.3	8.3	7.5	8.3	7.5	8.3	8.3
90°	12.8	12.5	12.1	11.9	11.6	11.0	10.3	9.7	9.1	8.2	7.3
92.5°	12.2	12.1	12.0	11.9	11.6	11.0	10.3	9.7	9.1	8.3	7.6
95°	11.9	11.9	11.9	11.9	11.6	11.0	10.3	9.7	9.1	13.9	18.7
97.5°	11.6	11.5	11.4	11.3	11.2	10.9	10.7	10.4	10.2	22.2	34.2
100°	12.9	13.4	13.9	14.2	23.6	42.3	61.1	79.8	98.6	98.1	97.6
102.5°	107.4	117.9	128.5	133.8	133.7	133.4	133.1	132.9	132.6	132.4	132.1
105°	168.6	168.7	168.8	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.6	206.1	206.6	206.9	206.8	206.7	206.6	206.4	206.3	206.1	205.8
110°	242.3	242.2	242.1	242.0	242.2	242.6	242.9	243.3	243.7	243.5	243.2

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	277.1	277.3	277.6	277.7	278.0	278.5	279.0	279.5	280.0	279.9	279.7
115°	312.1	312.9	313.6	314.0	314.3	314.8	315.3	315.8	316.3	316.2	316.0
117.5°	348.0	348.2	348.5	348.6	349.0	349.7	350.5	351.2	352.0	351.5	351.0
120°	382.1	382.8	383.4	383.7	383.8	384.1	384.4	384.6	384.9	384.5	384.1
122.5°	414.2	415.0	415.7	416.1	416.2	416.5	416.7	417.0	417.2	417.1	416.9
125°	445.8	446.1	446.5	446.7	446.9	447.4	447.9	448.4	448.9	448.9	448.9
127.5°	473.6	474.6	475.6	476.1	476.2	476.5	476.8	477.0	477.3	477.4	477.5
130°	502.3	503.0	503.6	503.9	504.1	504.5	504.8	505.2	505.6	505.5	505.3
132.5°	529.5	530.2	530.8	531.1	531.1	531.1	531.1	531.1	531.1	531.5	531.9
135°	554.2	555.0	555.7	556.1	556.2	556.5	556.7	557.0	557.2	557.4	557.7
137.5°	579.4	580.1	580.7	581.0	581.0	581.0	581.0	581.0	581.0	581.2	581.5
140°	601.8	602.6	603.3	603.7	603.6	603.3	603.0	602.8	602.5	602.6	602.8
142.5°	622.7	623.5	624.2	624.6	624.6	624.6	624.6	624.6	624.6	624.4	624.1
145°	643.2	644.0	644.7	645.1	645.0	644.9	644.8	644.6	644.5	644.5	644.5
147.5°	660.4	661.3	662.2	662.6	662.5	662.4	662.3	662.2	662.1	662.0	661.8
150°	677.1	678.1	679.1	679.6	679.5	679.2	679.0	678.7	678.5	678.3	678.0
152.5°	692.2	693.1	694.0	694.4	694.3	694.0	693.7	693.5	693.2	693.0	692.7
155°	705.4	706.5	707.5	708.0	707.8	707.4	707.1	706.7	706.3	706.0	705.8
157.5°	716.8	717.8	718.8	719.3	719.1	718.7	718.4	718.0	717.6	717.6	717.6
160°	727.5	728.6	729.6	730.1	729.8	729.3	728.8	728.3	727.8	727.7	727.5
162.5°	737.5	738.6	739.7	740.3	739.9	739.2	738.4	737.7	736.9	736.8	736.6
165°	745.7	746.7	747.7	748.2	747.8	747.1	746.3	745.6	744.8	744.7	744.6
167.5°	752.2	753.3	754.4	755.0	754.6	753.7	752.8	752.0	751.1	751.0	750.8
170°	757.3	758.4	759.5	760.1	759.6	758.6	757.6	756.6	755.6	755.5	755.3
172.5°	760.7	761.8	762.9	763.5	763.1	762.2	761.3	760.5	759.6	759.3	759.1
175°	763.6	764.7	765.8	766.4	765.9	764.9	763.8	762.8	761.8	761.7	761.6
177.5°	765.0	766.0	767.0	767.5	767.1	766.2	765.3	764.4	763.5	763.4	763.3
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	937.6	933.1	930.1	929.4	924.9	921.1	916.6	915.9	913.6	907.6	903.9
5°	966.9	956.4	954.1	947.4	936.1	927.9	917.4	911.4	904.6	893.4	884.4
7.5°	996.9	982.6	972.1	962.4	946.6	931.6	916.6	904.6	892.6	876.1	862.6
10°	1026.1	1004.4	991.6	977.4	955.6	933.1	912.1	894.9	875.4	855.9	836.4
12.5°	1053.1	1025.4	1006.6	986.4	959.4	931.6	904.6	880.6	860.4	834.1	812.4
15°	1069.6	1038.9	1020.1	1000.6	960.1	929.4	897.9	867.1	840.1	812.4	792.1
17.5°	1079.4	1044.9	1023.9	1005.9	964.6	922.6	882.1	849.1	819.9	786.9	759.8
20°	1074.9	1041.1	1021.6	1004.4	956.4	914.4	870.9	832.6	795.9	762.1	733.6
22.5°	1065.1	1029.9	1008.1	992.4	949.6	900.1	852.1	810.9	772.6	738.8	706.6
25°	1044.1	1009.6	990.9	971.4	929.4	882.1	833.4	789.1	748.6	712.6	676.6
27.5°	1025.4	983.4	963.9	946.6	902.4	860.4	812.4	763.6	722.3	684.8	648.8
30°	1003.6	956.4	935.4	912.1	872.4	832.6	784.6	739.6	696.8	657.1	622.6
32.5°	980.4	925.6	901.6	875.4	834.9	797.4	756.8	712.6	669.8	630.8	594.8
35°	950.4	891.9	864.1	839.4	797.4	759.8	722.3	685.6	642.8	601.6	567.1
37.5°	921.9	857.4	828.1	799.6	755.3	719.3	688.6	654.1	612.8	573.1	540.1
40°	889.6	815.4	785.4	759.1	713.3	673.6	645.8	618.8	582.8	544.6	508.6
42.5°	860.4	776.4	744.8	717.8	669.8	632.3	606.1	583.6	552.1	516.8	480.1
45°	819.9	734.3	702.1	673.6	624.8	589.6	562.6	543.1	518.3	485.3	452.3
47.5°	782.4	693.8	658.6	624.1	579.8	543.8	519.1	504.1	487.6	458.3	424.6
50°	736.6	647.3	611.3	582.8	532.6	501.8	477.1	466.6	451.6	423.8	396.8
52.5°	687.1	602.3	568.6	534.1	487.6	457.6	435.8	423.8	411.8	391.6	366.0
55°	629.3	552.1	520.6	489.8	443.3	415.6	396.1	383.3	376.5	357.8	339.0
57.5°	573.8	501.1	471.8	443.3	402.8	371.3	358.5	347.3	337.5	324.0	308.3
60°	517.6	451.6	420.1	394.6	359.3	330.8	320.3	309.0	301.5	291.0	279.8
62.5°	453.1	396.8	372.8	348.8	318.8	296.3	284.3	275.3	265.5	258.8	249.0
65°	384.8	345.0	321.8	303.8	275.3	255.0	246.0	240.0	231.8	225.0	217.5
67.5°	321.0	289.5	279.8	260.3	238.5	220.5	213.8	206.3	199.5	195.8	189.0
70°	259.5	237.0	227.3	222.0	198.0	186.0	180.0	177.0	168.8	165.0	160.5
72.5°	201.0	192.8	186.0	179.3	163.5	156.0	149.3	146.3	140.3	137.3	135.8
75°	148.5	143.3	139.5	138.8	132.0	124.5	117.8	116.3	111.8	108.8	107.3
77.5°	104.3	102.8	102.0	102.8	98.3	93.8	92.3	90.8	85.5	84.8	84.8
80°	68.3	72.0	72.0	71.3	69.8	69.0	66.8	65.3	62.3	61.5	62.3
82.5°	42.0	44.3	45.0	46.5	45.8	45.0	43.5	42.8	43.5	42.0	42.8
85°	21.0	22.5	25.5	25.5	26.3	26.3	26.3	25.5	24.0	24.8	24.0
87.5°	8.3	9.0	9.0	9.0	8.3	10.5	11.3	11.3	11.3	9.8	9.8
90°	6.4	5.5	5.1	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	6.8	6.1	5.7	6.3	7.4	8.5	9.7	10.8	9.7	8.5	7.4
95°	23.4	28.2	30.6	30.8	31.2	31.5	31.9	32.3	31.9	31.5	31.2
97.5°	46.1	58.1	64.1	63.7	63.0	62.2	61.5	60.7	61.5	62.2	63.0
100°	97.1	96.6	96.4	96.2	95.8	95.5	95.1	94.7	95.1	95.5	95.8
102.5°	131.9	131.6	131.5	131.2	130.7	130.2	129.7	129.2	129.7	130.2	130.7
105°	168.9	168.9	168.9	168.6	168.1	167.6	167.1	166.6	167.1	167.6	168.1
107.5°	205.6	205.3	205.2	205.2	205.2	205.2	205.2	205.2	205.2	205.2	205.2
110°	243.0	242.7	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6	242.6

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	279.6	279.5	279.4	279.2	278.8	278.5	278.1	277.7	278.1	278.5	278.8
115°	315.9	315.8	315.7	315.4	314.8	314.1	313.5	312.9	313.5	314.1	314.8
117.5°	350.5	350.0	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7	349.7
120°	383.8	383.4	383.2	383.3	383.4	383.5	383.6	383.7	383.6	383.5	383.4
122.5°	416.8	416.7	416.6	416.3	415.7	415.0	414.4	413.8	414.4	415.0	415.7
125°	448.9	448.9	448.9	448.5	447.6	446.7	445.9	445.0	445.9	446.7	447.6
127.5°	477.6	477.7	477.8	477.5	476.9	476.2	475.6	475.0	475.6	476.2	476.9
130°	505.2	505.1	505.0	504.7	504.1	503.4	502.8	502.2	502.8	503.4	504.1
132.5°	532.2	532.6	532.8	532.4	531.7	530.9	530.2	529.4	530.2	530.9	531.7
135°	557.9	558.2	558.3	557.9	557.2	556.4	555.7	554.9	555.7	556.4	557.2
137.5°	581.7	582.0	582.1	581.7	581.0	580.2	579.5	578.7	579.5	580.2	581.0
140°	602.9	603.0	603.1	603.0	602.7	602.5	602.2	602.0	602.2	602.5	602.7
142.5°	623.9	623.6	623.5	623.4	623.3	623.2	623.0	622.9	623.0	623.2	623.3
145°	644.5	644.5	644.5	644.4	644.1	643.9	643.6	643.4	643.6	643.9	644.1
147.5°	661.7	661.6	661.5	661.5	661.5	661.5	661.5	661.5	661.5	661.5	661.5
150°	677.8	677.5	677.4	677.5	677.8	678.0	678.3	678.5	678.3	678.0	677.8
152.5°	692.5	692.2	692.1	692.4	693.0	693.7	694.3	694.9	694.3	693.7	693.0
155°	705.5	705.2	705.1	705.5	706.2	707.0	707.7	708.5	707.7	707.0	706.2
157.5°	717.6	717.6	717.6	717.8	718.2	718.5	718.9	719.3	718.9	718.5	718.2
160°	727.4	727.3	727.2	727.6	728.3	729.1	729.8	730.6	729.8	729.1	728.3
162.5°	736.5	736.4	736.3	736.7	737.4	738.2	738.9	739.7	738.9	738.2	737.4
165°	744.5	744.4	744.3	744.7	745.4	746.2	746.9	747.7	746.9	746.2	745.4
167.5°	750.7	750.6	750.5	750.9	751.6	752.4	753.1	753.9	753.1	752.4	751.6
170°	755.2	755.1	755.0	755.4	756.3	757.2	758.1	759.0	758.1	757.2	756.3
172.5°	758.8	758.5	758.4	758.8	759.7	760.6	761.5	762.4	761.5	760.6	759.7
175°	761.5	761.4	761.3	761.7	762.4	763.2	763.9	764.7	763.9	763.2	762.4
177.5°	763.2	763.1	763.0	763.4	764.1	764.9	765.6	766.4	765.6	764.9	764.1
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	901.6	898.6	896.4	894.1	884.4	873.9	872.4	870.1	865.6	870.9	868.6
5°	878.4	871.6	867.9	858.1	846.1	837.1	829.6	820.6	816.9	813.9	813.1
7.5°	849.9	843.9	837.1	827.4	812.4	797.4	786.1	777.1	769.6	765.9	765.9
10°	822.1	814.6	805.6	789.1	774.9	756.1	744.1	735.1	724.6	718.6	713.3
12.5°	793.6	785.4	777.1	756.1	739.6	720.1	702.8	691.6	686.3	679.6	670.6
15°	765.1	752.3	744.1	723.1	702.1	682.6	671.3	659.3	647.3	640.6	637.6
17.5°	735.1	726.1	712.6	690.1	666.8	649.6	633.1	621.8	607.6	600.8	594.1
20°	708.1	694.6	681.1	658.6	636.1	612.8	596.3	582.8	573.8	568.6	562.6
22.5°	675.8	663.1	651.8	627.8	603.1	581.3	563.3	555.1	546.1	537.8	531.8
25°	648.1	635.3	624.1	597.8	570.8	550.6	537.1	526.6	516.8	513.1	507.1
27.5°	618.8	606.8	591.8	565.6	541.6	524.3	510.1	500.3	492.8	485.3	480.8
30°	591.1	577.6	564.1	535.6	516.1	498.8	485.3	473.3	467.3	463.6	456.1
32.5°	564.1	546.8	535.6	509.3	490.6	474.1	462.8	452.3	444.8	438.1	432.1
35°	534.8	516.1	504.8	483.1	463.6	447.1	437.3	429.8	420.8	414.8	411.8
37.5°	507.1	491.3	480.1	457.6	438.1	424.6	414.1	404.3	400.6	392.3	390.8
40°	477.1	463.6	453.1	431.3	413.3	402.8	391.6	382.6	375.8	372.0	366.8
42.5°	450.1	438.8	427.6	407.3	390.1	377.3	369.0	360.8	354.8	348.8	345.0
45°	425.3	413.3	402.8	383.3	366.0	354.8	346.5	336.8	335.3	327.0	323.3
47.5°	399.1	388.6	379.5	359.3	343.5	332.3	322.5	315.8	309.0	306.0	300.8
50°	373.5	363.0	352.5	334.5	320.3	309.0	299.3	291.8	288.0	283.5	279.0
52.5°	345.8	337.5	329.3	310.5	296.3	286.5	278.3	268.5	264.8	261.0	258.0
55°	322.5	310.5	301.5	285.8	273.0	262.5	253.5	246.0	242.3	239.3	235.5
57.5°	291.0	283.5	276.0	261.8	249.8	239.3	230.3	224.3	219.8	217.5	218.3
60°	264.0	255.8	251.3	236.3	224.3	216.0	207.8	201.8	197.3	195.0	194.3
62.5°	235.5	229.5	221.3	210.8	198.8	191.3	185.3	180.8	173.3	172.5	170.3
65°	207.8	203.3	195.8	186.0	176.3	169.5	162.8	156.8	153.8	150.0	147.8
67.5°	180.8	176.3	169.5	161.3	154.5	147.8	141.8	135.8	130.5	127.5	126.0
70°	154.5	150.8	146.3	136.5	128.3	123.0	118.5	114.8	109.5	108.0	107.3
72.5°	129.0	125.3	123.0	114.8	107.3	102.8	98.3	94.5	92.3	91.5	89.3
75°	105.8	102.0	99.0	91.5	87.0	84.0	79.5	78.0	75.8	75.0	74.3
77.5°	82.5	78.8	78.0	72.8	67.5	66.0	64.5	61.5	61.5	61.5	60.0
80°	59.3	58.5	57.8	52.5	50.3	48.8	48.0	45.8	44.3	42.8	42.0
82.5°	39.8	39.0	38.3	36.0	33.8	33.0	32.3	30.8	30.8	31.5	30.0
85°	24.0	22.5	21.8	21.0	19.5	19.5	20.3	19.5	19.5	19.5	18.8
87.5°	9.0	9.0	9.0	9.0	9.8	8.3	9.0	9.0	8.3	8.3	7.5
90°	4.6	5.1	5.5	6.4	7.3	8.2	9.1	9.7	10.3	11.0	11.6
92.5°	6.3	5.7	6.1	6.8	7.6	8.3	9.1	9.7	10.3	11.0	11.6
95°	30.8	30.6	28.2	23.4	18.7	13.9	9.1	9.7	10.3	11.0	11.6
97.5°	63.7	64.1	58.1	46.1	34.2	22.2	10.2	10.4	10.7	10.9	11.2
100°	96.2	96.4	96.6	97.1	97.6	98.1	98.6	79.8	61.1	42.3	23.6
102.5°	131.2	131.5	131.6	131.9	132.1	132.4	132.6	132.9	133.1	133.4	133.7
105°	168.6	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9
107.5°	205.2	205.2	205.3	205.6	205.8	206.1	206.3	206.4	206.6	206.7	206.8
110°	242.6	242.6	242.7	243.0	243.2	243.5	243.7	243.3	242.9	242.6	242.2

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	279.2	279.4	279.5	279.6	279.7	279.9	280.0	279.5	279.0	278.5	278.0
115°	315.4	315.7	315.8	315.9	316.0	316.2	316.3	315.8	315.3	314.8	314.3
117.5°	349.7	349.7	350.0	350.5	351.0	351.5	352.0	351.2	350.5	349.7	349.0
120°	383.3	383.2	383.4	383.8	384.1	384.5	384.9	384.6	384.4	384.1	383.8
122.5°	416.3	416.6	416.7	416.8	416.9	417.1	417.2	417.0	416.7	416.5	416.2
125°	448.5	448.9	448.9	448.9	448.9	448.9	448.9	448.4	447.9	447.4	446.9
127.5°	477.5	477.8	477.7	477.6	477.5	477.4	477.3	477.0	476.8	476.5	476.2
130°	504.7	505.0	505.1	505.2	505.3	505.5	505.6	505.2	504.8	504.5	504.1
132.5°	532.4	532.8	532.6	532.2	531.9	531.5	531.1	531.1	531.1	531.1	531.1
135°	557.9	558.3	558.2	557.9	557.7	557.4	557.2	557.0	556.7	556.5	556.2
137.5°	581.7	582.1	582.0	581.7	581.5	581.2	581.0	581.0	581.0	581.0	581.0
140°	603.0	603.1	603.0	602.9	602.8	602.6	602.5	602.8	603.0	603.3	603.6
142.5°	623.4	623.5	623.6	623.9	624.1	624.4	624.6	624.6	624.6	624.6	624.6
145°	644.4	644.5	644.5	644.5	644.5	644.5	644.5	644.6	644.8	644.9	645.0
147.5°	661.5	661.5	661.6	661.7	661.8	662.0	662.1	662.2	662.3	662.4	662.5
150°	677.5	677.4	677.5	677.8	678.0	678.3	678.5	678.7	679.0	679.2	679.5
152.5°	692.4	692.1	692.2	692.5	692.7	693.0	693.2	693.5	693.7	694.0	694.3
155°	705.5	705.1	705.2	705.5	705.8	706.0	706.3	706.7	707.1	707.4	707.8
157.5°	717.8	717.6	717.6	717.6	717.6	717.6	717.6	718.0	718.4	718.7	719.1
160°	727.6	727.2	727.3	727.4	727.5	727.7	727.8	728.3	728.8	729.3	729.8
162.5°	736.7	736.3	736.4	736.5	736.6	736.8	736.9	737.7	738.4	739.2	739.9
165°	744.7	744.3	744.4	744.5	744.6	744.7	744.8	745.6	746.3	747.1	747.8
167.5°	750.9	750.5	750.6	750.7	750.8	751.0	751.1	752.0	752.8	753.7	754.6
170°	755.4	755.0	755.1	755.2	755.3	755.5	755.6	756.6	757.6	758.6	759.6
172.5°	758.8	758.4	758.5	758.8	759.1	759.3	759.6	760.5	761.3	762.2	763.1
175°	761.7	761.3	761.4	761.5	761.6	761.7	761.8	762.8	763.8	764.9	765.9
177.5°	763.4	763.0	763.1	763.2	763.3	763.4	763.5	764.4	765.3	766.2	767.1
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	864.9	866.4	862.6	861.1	858.1	861.9	862.6	861.9	868.6	865.6	867.1
5°	814.6	811.6	809.4	804.1	804.1	804.9	807.1	803.4	805.6	810.9	810.1
7.5°	759.1	757.6	758.3	752.3	747.8	749.3	747.8	754.6	758.3	756.8	759.8
10°	708.8	711.8	705.1	702.1	699.1	702.1	701.3	702.8	707.3	710.3	715.6
12.5°	668.3	667.6	663.8	660.8	655.6	657.1	661.6	660.1	660.8	667.6	666.8
15°	630.1	625.6	622.6	615.8	617.3	612.1	616.6	621.8	624.1	630.1	633.8
17.5°	591.8	591.1	587.3	586.6	578.3	576.1	580.6	582.1	584.3	587.3	592.6
20°	559.6	558.8	553.6	552.1	545.3	549.8	548.3	551.3	552.8	558.8	561.1
22.5°	530.3	526.6	525.1	522.8	520.6	519.8	522.8	522.1	527.3	529.6	530.3
25°	503.3	500.3	499.6	495.8	494.3	492.1	494.3	496.6	502.6	504.8	507.8
27.5°	478.6	476.3	474.8	471.8	469.6	469.6	471.1	474.1	476.3	477.8	479.3
30°	456.1	454.6	450.1	448.6	446.3	446.3	446.3	447.8	451.6	456.1	458.3
32.5°	432.8	429.8	426.8	426.8	424.6	424.6	425.3	426.8	430.6	431.3	435.1
35°	410.3	407.3	405.1	403.6	404.3	401.3	402.8	405.1	409.6	411.1	413.3
37.5°	388.6	387.8	383.3	381.0	382.6	382.6	381.8	383.3	386.3	389.3	390.8
40°	364.5	363.0	363.0	360.8	361.5	358.5	360.8	362.3	363.8	366.8	369.0
42.5°	343.5	342.0	339.0	339.8	337.5	337.5	339.0	339.8	342.0	345.8	347.3
45°	321.0	321.0	319.5	317.3	318.0	315.8	317.3	318.0	321.0	324.8	323.3
47.5°	299.3	298.5	298.5	295.5	297.0	294.8	297.0	297.8	299.3	301.5	300.8
50°	278.3	276.0	276.8	276.0	275.3	275.3	276.8	276.8	278.3	278.3	280.5
52.5°	256.5	256.5	255.0	255.8	257.3	255.8	258.0	255.8	257.3	258.0	259.5
55°	237.0	235.5	236.3	235.5	238.5	236.3	238.5	237.0	238.5	237.8	239.3
57.5°	216.0	213.8	214.5	213.8	216.0	215.3	217.5	215.3	216.0	216.8	219.0
60°	192.0	192.0	192.0	190.5	192.8	192.8	192.0	192.0	195.0	196.5	195.8
62.5°	169.5	168.8	166.5	165.8	166.5	165.0	168.0	167.3	168.8	170.3	171.8
65°	144.8	143.3	142.5	141.0	141.0	140.3	141.0	144.0	144.8	145.5	149.3
67.5°	124.5	123.8	123.0	120.8	120.8	122.3	122.3	122.3	126.8	124.5	127.5
70°	106.5	105.0	103.5	102.8	102.8	103.5	104.3	105.0	104.3	107.3	108.0
72.5°	89.3	90.0	88.5	88.5	88.5	87.8	87.8	89.3	90.0	89.3	90.0
75°	74.3	74.3	73.5	74.3	74.3	73.5	73.5	75.0	75.0	74.3	76.5
77.5°	60.0	59.3	57.8	56.3	57.0	56.3	57.0	56.3	58.5	60.8	59.3
80°	42.0	41.3	41.3	41.3	42.0	41.3	42.8	41.3	42.0	42.0	42.8
82.5°	30.0	30.8	30.8	30.0	30.8	30.0	30.8	30.8	30.8	30.0	30.8
85°	19.5	19.5	19.5	19.5	18.8	19.5	19.5	19.5	20.3	19.5	20.3
87.5°	8.3	8.3	8.3	8.3	8.3	8.3	8.3	8.3	9.0	8.3	9.0
90°	11.9	12.1	12.5	12.8	13.2	13.6	13.2	12.8	12.5	12.1	11.9
92.5°	11.9	12.0	12.1	12.2	12.4	12.5	12.4	12.2	12.1	12.0	11.9
95°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9
97.5°	11.3	11.4	11.5	11.6	11.8	11.9	11.8	11.6	11.5	11.4	11.3
100°	14.2	13.9	13.4	12.9	12.4	11.9	12.4	12.9	13.4	13.9	14.2
102.5°	133.8	128.5	117.9	107.4	96.8	86.2	96.8	107.4	117.9	128.5	133.8
105°	168.9	168.8	168.7	168.6	168.4	168.3	168.4	168.6	168.7	168.8	168.9
107.5°	206.9	206.6	206.1	205.6	205.1	204.6	205.1	205.6	206.1	206.6	206.9
110°	242.0	242.1	242.2	242.3	242.5	242.6	242.5	242.3	242.2	242.1	242.0

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	277.7	277.6	277.3	277.1	276.8	276.6	276.8	277.1	277.3	277.6	277.7
115°	314.0	313.6	312.9	312.1	311.4	310.6	311.4	312.1	312.9	313.6	314.0
117.5°	348.6	348.5	348.2	348.0	347.7	347.5	347.7	348.0	348.2	348.5	348.6
120°	383.7	383.4	382.8	382.1	381.5	380.9	381.5	382.1	382.8	383.4	383.7
122.5°	416.1	415.7	415.0	414.2	413.5	412.7	413.5	414.2	415.0	415.7	416.1
125°	446.7	446.5	446.1	445.8	445.4	445.0	445.4	445.8	446.1	446.5	446.7
127.5°	476.1	475.6	474.6	473.6	472.6	471.6	472.6	473.6	474.6	475.6	476.1
130°	503.9	503.6	503.0	502.3	501.7	501.1	501.7	502.3	503.0	503.6	503.9
132.5°	531.1	530.8	530.2	529.5	528.9	528.3	528.9	529.5	530.2	530.8	531.1
135°	556.1	555.7	555.0	554.2	553.5	552.7	553.5	554.2	555.0	555.7	556.1
137.5°	581.0	580.7	580.1	579.4	578.8	578.2	578.8	579.4	580.1	580.7	581.0
140°	603.7	603.3	602.6	601.8	601.1	600.3	601.1	601.8	602.6	603.3	603.7
142.5°	624.6	624.2	623.5	622.7	622.0	621.2	622.0	622.7	623.5	624.2	624.6
145°	645.1	644.7	644.0	643.2	642.5	641.7	642.5	643.2	644.0	644.7	645.1
147.5°	662.6	662.2	661.3	660.4	659.6	658.7	659.6	660.4	661.3	662.2	662.6
150°	679.6	679.1	678.1	677.1	676.1	675.1	676.1	677.1	678.1	679.1	679.6
152.5°	694.4	694.0	693.1	692.2	691.3	690.4	691.3	692.2	693.1	694.0	694.4
155°	708.0	707.5	706.5	705.4	704.4	703.4	704.4	705.4	706.5	707.5	708.0
157.5°	719.3	718.8	717.8	716.8	715.8	714.8	715.8	716.8	717.8	718.8	719.3
160°	730.1	729.6	728.6	727.5	726.5	725.5	726.5	727.5	728.6	729.6	730.1
162.5°	740.3	739.7	738.6	737.5	736.3	735.2	736.3	737.5	738.6	739.7	740.3
165°	748.2	747.7	746.7	745.7	744.7	743.7	744.7	745.7	746.7	747.7	748.2
167.5°	755.0	754.4	753.3	752.2	751.0	749.9	751.0	752.2	753.3	754.4	755.0
170°	760.1	759.5	758.4	757.3	756.1	755.0	756.1	757.3	758.4	759.5	760.1
172.5°	763.5	762.9	761.8	760.7	759.5	758.4	759.5	760.7	761.8	762.9	763.5
175°	766.4	765.8	764.7	763.6	762.4	761.3	762.4	763.6	764.7	765.8	766.4
177.5°	767.5	767.0	766.0	765.0	764.0	763.0	764.0	765.0	766.0	767.0	767.5
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6	913.6
2.5°	864.1	867.9	864.9	862.6	868.6	871.6	871.6	876.9	882.1	886.6	887.4
5°	810.9	816.9	818.4	817.6	826.6	831.1	840.9	846.1	853.6	858.9	864.9
7.5°	762.1	770.4	771.1	772.6	786.1	793.6	801.9	815.4	825.9	833.4	840.1
10°	713.3	718.6	723.8	730.6	744.1	756.8	768.9	783.1	796.6	804.1	813.9
12.5°	676.6	680.3	686.3	690.8	705.1	716.3	732.1	751.6	771.1	777.1	789.1
15°	638.3	640.6	652.6	657.1	669.1	687.8	697.6	716.3	737.3	748.6	762.1
17.5°	594.1	607.6	615.1	620.3	635.3	650.3	666.1	685.6	712.6	723.1	732.8
20°	562.6	572.3	580.6	587.3	600.8	623.3	637.6	653.3	678.8	690.8	705.1
22.5°	534.8	543.1	550.6	558.1	567.1	587.3	603.8	625.6	651.1	662.3	678.8
25°	508.6	516.8	521.3	530.3	542.3	556.6	576.1	595.6	621.1	633.8	649.6
27.5°	483.1	491.3	499.6	507.1	515.3	528.8	542.3	567.1	593.3	608.3	621.8
30°	461.3	465.1	472.6	480.8	489.1	501.8	517.6	534.8	564.8	578.3	594.8
32.5°	437.3	444.1	449.3	455.3	465.8	476.3	490.6	512.3	536.3	549.1	567.1
35°	414.8	420.8	424.6	435.1	441.8	453.1	467.3	486.8	507.1	521.3	537.1
37.5°	393.1	399.1	403.6	409.6	418.6	428.3	443.3	457.6	481.6	493.6	511.6
40°	370.5	375.8	381.0	387.8	396.1	408.1	417.1	435.1	454.6	468.1	481.6
42.5°	348.8	351.8	357.8	365.3	373.5	384.1	396.8	411.1	430.6	442.6	454.6
45°	325.5	330.8	337.5	342.8	350.3	360.8	372.0	384.8	404.3	416.3	429.1
47.5°	303.8	307.5	312.0	320.3	330.0	337.5	349.5	361.5	379.5	390.8	402.8
50°	281.3	285.0	291.8	297.0	304.5	314.3	325.5	338.3	355.5	363.0	375.0
52.5°	260.3	261.8	268.5	273.8	281.3	292.5	301.5	312.8	329.3	337.5	349.5
55°	239.3	240.8	244.5	249.8	258.0	267.0	276.8	289.5	303.8	311.3	322.5
57.5°	217.5	219.0	222.8	226.5	234.8	243.0	254.3	264.8	279.0	285.8	296.3
60°	195.8	195.8	199.5	204.8	210.8	218.3	228.0	240.8	251.3	259.5	267.0
62.5°	172.5	174.8	177.0	180.8	187.5	196.5	204.8	213.8	226.5	232.5	239.3
65°	149.3	151.5	156.0	159.8	165.0	171.0	181.5	189.0	198.8	205.5	211.5
67.5°	129.0	131.3	134.3	138.8	142.5	149.3	156.8	164.3	174.8	179.3	183.8
70°	108.0	110.3	112.5	118.5	122.3	127.5	132.8	140.3	149.3	152.3	156.0
72.5°	91.5	92.3	95.3	96.8	102.0	106.5	112.5	117.0	123.8	127.5	130.5
75°	77.3	77.3	78.0	79.5	82.5	85.5	90.0	94.5	100.5	102.8	106.5
77.5°	60.8	63.0	62.3	63.8	65.3	66.8	70.5	73.5	79.5	81.0	82.5
80°	43.5	44.3	46.5	48.8	48.8	51.0	53.3	54.0	57.8	60.0	60.0
82.5°	31.5	32.3	31.5	32.3	33.0	33.8	36.0	39.0	39.0	39.8	41.3
85°	19.5	19.5	20.3	21.0	21.0	20.3	21.8	21.0	21.8	23.3	23.3
87.5°	9.8	9.0	9.0	9.0	9.0	9.0	9.8	9.0	9.8	9.8	9.8
90°	11.6	11.0	10.3	9.7	9.1	8.2	7.3	6.4	5.5	5.1	4.6
92.5°	11.6	11.0	10.3	9.7	9.1	8.3	7.6	6.8	6.1	5.7	6.3
95°	11.6	11.0	10.3	9.7	9.1	13.9	18.7	23.4	28.2	30.6	30.8
97.5°	11.2	10.9	10.7	10.4	10.2	22.2	34.2	46.1	58.1	64.1	63.7
100°	23.6	42.3	61.1	79.8	98.6	98.1	97.6	97.1	96.6	96.4	96.2
102.5°	133.7	133.4	133.1	132.9	132.6	132.4	132.1	131.9	131.6	131.5	131.2
105°	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.9	168.6
107.5°	206.8	206.7	206.6	206.4	206.3	206.1	205.8	205.6	205.3	205.2	205.2
110°	242.2	242.6	242.9	243.3	243.7	243.5	243.2	243.0	242.7	242.6	242.6

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	278.0	278.5	279.0	279.5	280.0	279.9	279.7	279.6	279.5	279.4	279.2
115°	314.3	314.8	315.3	315.8	316.3	316.2	316.0	315.9	315.8	315.7	315.4
117.5°	349.0	349.7	350.5	351.2	352.0	351.5	351.0	350.5	350.0	349.7	349.7
120°	383.8	384.1	384.4	384.6	384.9	384.5	384.1	383.8	383.4	383.2	383.3
122.5°	416.2	416.5	416.7	417.0	417.2	417.1	416.9	416.8	416.7	416.6	416.3
125°	446.9	447.4	447.9	448.4	448.9	448.9	448.9	448.9	448.9	448.9	448.5
127.5°	476.2	476.5	476.8	477.0	477.3	477.4	477.5	477.6	477.7	477.8	477.5
130°	504.1	504.5	504.8	505.2	505.6	505.5	505.3	505.2	505.1	505.0	504.7
132.5°	531.1	531.1	531.1	531.1	531.1	531.5	531.9	532.2	532.6	532.8	532.4
135°	556.2	556.5	556.7	557.0	557.2	557.4	557.7	557.9	558.2	558.3	557.9
137.5°	581.0	581.0	581.0	581.0	581.0	581.2	581.5	581.7	582.0	582.1	581.7
140°	603.6	603.3	603.0	602.8	602.5	602.6	602.8	602.9	603.0	603.1	603.0
142.5°	624.6	624.6	624.6	624.6	624.6	624.4	624.1	623.9	623.6	623.5	623.4
145°	645.0	644.9	644.8	644.6	644.5	644.5	644.5	644.5	644.5	644.5	644.4
147.5°	662.5	662.4	662.3	662.2	662.1	662.0	661.8	661.7	661.6	661.5	661.5
150°	679.5	679.2	679.0	678.7	678.5	678.3	678.0	677.8	677.5	677.4	677.5
152.5°	694.3	694.0	693.7	693.5	693.2	693.0	692.7	692.5	692.2	692.1	692.4
155°	707.8	707.4	707.1	706.7	706.3	706.0	705.8	705.5	705.2	705.1	705.5
157.5°	719.1	718.7	718.4	718.0	717.6	717.6	717.6	717.6	717.6	717.6	717.8
160°	729.8	729.3	728.8	728.3	727.8	727.7	727.5	727.4	727.3	727.2	727.6
162.5°	739.9	739.2	738.4	737.7	736.9	736.8	736.6	736.5	736.4	736.3	736.7
165°	747.8	747.1	746.3	745.6	744.8	744.7	744.6	744.5	744.4	744.3	744.7
167.5°	754.6	753.7	752.8	752.0	751.1	751.0	750.8	750.7	750.6	750.5	750.9
170°	759.6	758.6	757.6	756.6	755.6	755.5	755.3	755.2	755.1	755.0	755.4
172.5°	763.1	762.2	761.3	760.5	759.6	759.3	759.1	758.8	758.5	758.4	758.8
175°	765.9	764.9	763.8	762.8	761.8	761.7	761.6	761.5	761.4	761.3	761.7
177.5°	767.1	766.2	765.3	764.4	763.5	763.4	763.3	763.2	763.1	763.0	763.4
180°	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7	764.7

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	913.6	913.6	913.6	913.6
2.5°	892.6	899.4	906.1	914.4
5°	874.6	886.6	899.4	911.4
7.5°	855.1	872.4	888.9	906.1
10°	833.4	855.1	873.9	897.9
12.5°	809.4	832.6	858.9	885.9
15°	785.4	814.6	842.4	873.1
17.5°	762.8	790.6	821.4	858.1
20°	735.8	766.6	801.1	840.1
22.5°	707.3	741.1	778.6	820.6
25°	683.3	717.8	753.8	798.1
27.5°	657.1	693.1	728.3	775.6
30°	627.1	666.1	702.1	750.8
32.5°	598.6	637.6	677.3	723.1
35°	570.8	609.1	648.8	695.3
37.5°	544.6	579.1	618.1	660.1
40°	519.8	551.3	585.8	624.1
42.5°	488.3	525.1	557.3	585.1
45°	461.3	491.3	521.3	543.8
47.5°	429.8	459.8	485.3	503.3
50°	403.6	427.6	448.6	464.3
52.5°	372.0	394.6	411.8	423.8
55°	341.3	360.8	375.8	384.1
57.5°	313.5	326.3	337.5	345.0
60°	282.8	292.5	302.3	310.5
62.5°	249.8	260.3	265.5	274.5
65°	220.5	227.3	235.5	238.5
67.5°	192.0	195.8	201.0	207.0
70°	162.0	164.3	169.5	177.8
72.5°	135.8	138.0	141.8	144.8
75°	108.0	110.3	113.3	116.3
77.5°	84.8	85.5	87.0	90.0
80°	61.5	63.8	65.3	66.0
82.5°	42.8	43.5	43.5	44.3
85°	27.0	25.5	25.5	26.3
87.5°	9.8	11.3	11.3	12.8
90°	3.6	2.6	1.6	0.6
92.5°	7.4	8.5	9.7	10.8
95°	31.2	31.5	31.9	32.3
97.5°	63.0	62.2	61.5	60.7
100°	95.8	95.5	95.1	94.7
102.5°	130.7	130.2	129.7	129.2
105°	168.1	167.6	167.1	166.6
107.5°	205.2	205.2	205.2	205.2
110°	242.6	242.6	242.6	242.6

TEST NUMBER: P1027234

CATALOG NUMBER: S125RDIP-B610D610UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	278.8	278.5	278.1	277.7
115°	314.8	314.1	313.5	312.9
117.5°	349.7	349.7	349.7	349.7
120°	383.4	383.5	383.6	383.7
122.5°	415.7	415.0	414.4	413.8
125°	447.6	446.7	445.9	445.0
127.5°	476.9	476.2	475.6	475.0
130°	504.1	503.4	502.8	502.2
132.5°	531.7	530.9	530.2	529.4
135°	557.2	556.4	555.7	554.9
137.5°	581.0	580.2	579.5	578.7
140°	602.7	602.5	602.2	602.0
142.5°	623.3	623.2	623.0	622.9
145°	644.1	643.9	643.6	643.4
147.5°	661.5	661.5	661.5	661.5
150°	677.8	678.0	678.3	678.5
152.5°	693.0	693.7	694.3	694.9
155°	706.2	707.0	707.7	708.5
157.5°	718.2	718.5	718.9	719.3
160°	728.3	729.1	729.8	730.6
162.5°	737.4	738.2	738.9	739.7
165°	745.4	746.2	746.9	747.7
167.5°	751.6	752.4	753.1	753.9
170°	756.3	757.2	758.1	759.0
172.5°	759.7	760.6	761.5	762.4
175°	762.4	763.2	763.9	764.7
177.5°	764.1	764.9	765.6	766.4
180°	764.7	764.7	764.7	764.7

(END OF REPORT)