

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027255

Luminaire Tested: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027255
REPORT IS A COMBINATION OF REPORTS P1005726 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K
Description: Define 5 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7393.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44			38
2	89	81	76	71	81	75	70	66	63	59	56	51	49	46	41	39	38			33
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	33	30	28			24
5	68	57	49	43	62	53	46	40	44	39	35	37	33	30	30	27	25			21
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	25	22	19			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17			15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8149	8149	8149	8149
5°	8142	9184	8142	7059
10°	8096	10320	8069	6103
15°	8008	10919	7954	5313
20°	7902	11787	7831	4803
25°	7764	13341	7676	4359
30°	7623	14180	7509	4041
35°	7441	11662	7337	3745
40°	7117	7920	7057	3479
45°	6692	5693	6683	3217
50°	6256	4378	6287	2975
55°	5766	3560	5755	2742
60°	5310	2918	5284	2435
65°	4777	2431	4807	1960
70°	4338	1951	4319	1632
75°	3664	1479	3664	1341
80°	2970	901	2934	901
85°	2087	474	2030	535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11599 cd/sqm

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	1.6
10°-20°	357.6	4.8
20°-30°	566.9	7.7
30°-40°	685.1	9.3
40°-50°	609.9	8.3
50°-60°	467.7	6.3
60°-70°	303.8	4.1
70°-80°	147.4	2.0
80°-90°	36.6	0.5
90°-100°	45.3	0.6
100°-110°	300.9	4.1
110°-120°	541.9	7.3
120°-130°	695.6	9.4
130°-140°	748.1	10.1
140°-150°	702.2	9.5
150°-160°	568.0	7.7
160°-170°	367.3	5.0
170°-180°	126.7	1.7
0°-30°	1046.5	14.2
0°-40°	1731.5	23.4
0°-60°	2809.2	38.0
0°-90°	3297.0	44.6
90°-120°	888.1	12.0
90°-150°	3034.1	41.0
90°-180°	4096.0	55.4
0°-180°	7393.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1272	1272	1272	1272	1272	
5°	1269	1458	1269	1120	1269	121
15°	1215	1751	1207	852	1215	343
25°	1111	2097	1098	685	1111	512
35°	968	1740	954	559	968	603
45°	757	778	756	440	757	584
55°	535	427	534	329	535	479
65°	332	242	334	195	332	332
75°	162	113	162	102	162	174
85°	36	24	36	27	36	42
90°	1	24	1	24	1	5
95°	56	21	56	21	56	69
105°	291	294	291	294	291	308
115°	546	542	546	542	546	541
125°	776	776	776	776	776	693
135°	968	964	968	964	968	746
145°	1122	1119	1122	1119	1122	702
155°	1236	1227	1236	1227	1236	569
165°	1304	1297	1304	1297	1304	368
175°	1333	1328	1333	1328	1333	127
180°	1333	1333	1333	1333	1333	

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1272.9	1283.3	1286.4	1294.8	1304.2	1306.3	1311.5	1318.8	1323.0	1321.9	1321.9
5°	1268.7	1286.4	1299.0	1313.6	1331.3	1338.6	1344.9	1360.6	1373.1	1380.4	1392.9
7.5°	1261.4	1287.5	1308.4	1330.3	1357.4	1370.0	1383.5	1405.5	1428.4	1443.1	1456.6
10°	1249.9	1283.3	1312.5	1344.9	1381.4	1400.2	1417.0	1450.4	1478.6	1497.4	1528.7
12.5°	1233.2	1274.9	1315.7	1358.5	1404.4	1424.3	1447.2	1483.8	1523.5	1550.6	1576.7
15°	1215.4	1265.5	1309.4	1360.6	1415.9	1446.2	1475.4	1514.1	1549.6	1579.8	1610.1
17.5°	1194.5	1247.8	1302.1	1360.6	1423.2	1453.5	1478.6	1524.5	1562.1	1592.4	1619.5
20°	1169.5	1229.0	1290.6	1355.3	1419.0	1447.2	1471.2	1521.4	1554.8	1587.2	1625.8
22.5°	1142.3	1207.1	1272.9	1336.5	1399.2	1429.5	1457.7	1501.5	1538.1	1581.9	1632.1
25°	1111.0	1182.0	1248.8	1312.5	1372.1	1400.2	1425.3	1473.3	1524.5	1579.8	1636.2
27.5°	1079.7	1148.6	1213.3	1271.8	1336.5	1362.7	1387.7	1448.3	1508.8	1567.3	1644.6
30°	1045.2	1115.2	1171.6	1225.9	1288.5	1315.7	1347.0	1415.9	1484.8	1564.2	1658.2
32.5°	1006.6	1070.3	1122.5	1178.9	1235.3	1268.7	1308.4	1383.5	1462.9	1557.9	1678.0
35°	968.0	1019.1	1067.2	1120.4	1188.3	1223.8	1262.4	1341.8	1441.0	1554.8	1694.7
37.5°	918.9	968.0	1005.5	1059.8	1129.8	1171.6	1210.2	1302.1	1414.9	1547.5	1693.7
40°	868.8	910.5	946.0	1002.4	1078.6	1117.3	1159.0	1259.3	1387.7	1526.6	1668.6
42.5°	814.5	850.0	888.6	942.9	1017.0	1054.6	1102.7	1219.6	1350.1	1497.4	1603.9
45°	757.0	791.5	823.9	880.2	954.4	995.1	1047.3	1167.4	1304.2	1435.7	1499.4
47.5°	700.6	730.9	765.4	814.5	889.6	934.5	987.8	1116.2	1242.6	1353.3	1358.5
50°	646.3	670.4	699.6	749.7	828.0	870.8	926.2	1046.3	1169.5	1245.7	1194.5
52.5°	590.0	611.9	642.2	686.0	759.1	809.2	857.3	977.4	1080.7	1131.9	1037.9
55°	534.6	553.4	584.7	633.8	697.5	736.1	785.2	897.0	987.8	988.8	886.5
57.5°	480.3	497.0	523.1	567.0	626.5	671.4	716.3	813.4	875.0	857.3	743.5
60°	432.3	442.7	466.7	509.6	564.9	597.3	645.3	726.7	767.5	735.1	612.9
62.5°	382.2	392.6	411.4	445.9	498.1	532.5	562.8	629.6	657.8	608.8	508.5
65°	332.0	344.6	358.2	385.3	434.4	457.4	484.5	533.6	560.7	503.3	416.6
67.5°	288.2	294.5	308.0	336.2	370.7	391.6	410.4	443.8	449.0	403.1	332.0
70°	247.5	249.6	262.1	278.8	304.9	317.4	333.1	352.9	352.9	315.3	259.0
72.5°	201.5	204.7	214.1	231.8	247.5	253.7	259.0	271.5	269.4	234.9	196.3
75°	161.8	163.9	171.2	179.6	185.9	197.3	201.5	199.4	198.4	169.2	147.2
77.5°	125.3	126.3	131.6	138.9	139.9	144.1	141.0	141.0	131.6	114.9	103.4
80°	91.9	92.9	95.0	97.1	97.1	97.1	97.1	91.9	85.6	75.2	72.0
82.5°	61.6	61.6	62.7	64.7	63.7	61.6	59.5	54.3	50.1	47.0	44.9
85°	36.5	36.5	37.6	36.5	32.4	31.3	29.2	28.2	27.1	26.1	26.1
87.5°	17.8	16.7	14.6	12.5	12.5	12.5	12.5	12.5	12.5	11.5	11.5
90°	1.0	2.8	4.5	6.3	8.0	8.9	9.7	11.2	12.7	14.3	15.8
92.5°	18.8	16.8	14.8	12.9	10.9	9.9	10.6	11.9	13.2	14.5	15.8
95°	56.3	55.7	55.0	54.4	53.7	53.4	49.2	40.9	32.5	24.2	15.8
97.5°	105.8	107.1	108.4	109.7	111.0	111.7	101.3	80.4	59.5	38.7	17.8
100°	165.1	165.7	166.4	167.0	167.7	168.0	168.4	169.3	170.2	171.1	172.0
102.5°	225.4	226.3	227.1	228.0	228.9	229.3	229.5	230.0	230.4	230.9	231.3
105°	290.6	291.5	292.4	293.3	294.2	294.6	294.6	294.6	294.6	294.6	294.6
107.5°	357.8	357.8	357.8	357.8	357.8	357.8	358.0	358.5	358.9	359.4	359.8
110°	423.1	423.1	423.1	423.1	423.1	423.1	423.3	423.7	424.2	424.6	425.0

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	484.3	485.0	485.6	486.3	487.0	487.3	487.4	487.6	487.9	488.1	488.3
115°	545.6	546.7	547.8	548.9	550.0	550.6	550.7	550.9	551.2	551.4	551.6
117.5°	609.9	609.9	609.9	609.9	609.9	609.9	610.3	611.2	612.1	612.9	613.8
120°	669.2	669.0	668.8	668.5	668.3	668.2	668.5	669.2	669.9	670.5	671.2
122.5°	721.6	722.7	723.8	724.9	726.0	726.5	726.6	726.8	727.1	727.3	727.5
125°	775.9	777.5	779.0	780.6	782.1	782.9	782.9	782.9	782.9	782.9	782.9
127.5°	828.3	829.4	830.5	831.6	832.7	833.3	833.2	833.0	832.7	832.5	832.3
130°	875.8	876.9	878.0	879.1	880.2	880.7	880.8	881.0	881.3	881.5	881.7
132.5°	923.2	924.5	925.9	927.2	928.5	929.2	928.9	928.2	927.5	926.9	926.2
135°	967.7	969.0	970.3	971.6	972.9	973.6	973.4	973.0	972.5	972.1	971.7
137.5°	1009.2	1010.5	1011.8	1013.1	1014.4	1015.1	1014.9	1014.5	1014.0	1013.6	1013.2
140°	1049.7	1050.1	1050.6	1051.0	1051.5	1051.7	1051.6	1051.4	1051.1	1050.9	1050.7
142.5°	1086.3	1086.5	1086.7	1087.0	1087.2	1087.3	1087.5	1088.0	1088.4	1088.9	1089.3
145°	1121.9	1122.3	1122.8	1123.2	1123.7	1123.9	1123.9	1123.9	1123.9	1123.9	1123.9
147.5°	1153.5	1153.5	1153.5	1153.5	1153.5	1153.5	1153.6	1153.8	1154.1	1154.3	1154.5
150°	1183.2	1182.8	1182.3	1181.9	1181.4	1181.2	1181.4	1181.9	1182.3	1182.8	1183.2
152.5°	1211.9	1210.8	1209.7	1208.6	1207.5	1206.9	1207.1	1207.6	1208.0	1208.5	1208.9
155°	1235.6	1234.3	1232.9	1231.6	1230.3	1229.6	1229.8	1230.3	1230.7	1231.2	1231.6
157.5°	1254.4	1253.7	1253.1	1252.4	1251.7	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4
160°	1274.1	1272.8	1271.5	1270.2	1268.9	1268.2	1268.3	1268.5	1268.8	1269.0	1269.2
162.5°	1289.9	1288.6	1287.3	1286.0	1284.7	1284.0	1284.1	1284.3	1284.6	1284.8	1285.0
165°	1303.8	1302.5	1301.1	1299.8	1298.5	1297.8	1297.9	1298.1	1298.4	1298.6	1298.8
167.5°	1314.7	1313.4	1312.0	1310.7	1309.4	1308.7	1308.8	1309.0	1309.3	1309.5	1309.7
170°	1323.5	1322.0	1320.4	1318.9	1317.4	1316.6	1316.7	1316.9	1317.2	1317.4	1317.6
172.5°	1329.5	1328.0	1326.4	1324.9	1323.4	1322.6	1322.8	1323.2	1323.7	1324.1	1324.5
175°	1333.4	1332.1	1330.8	1329.5	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5
177.5°	1336.4	1335.1	1333.8	1332.5	1331.2	1330.5	1330.6	1330.8	1331.1	1331.3	1331.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1327.2	1334.5	1340.7	1337.6	1350.1	1349.1	1351.2	1355.3	1356.4	1354.3	1350.1
5°	1399.2	1409.6	1427.4	1436.8	1434.7	1443.1	1447.2	1453.5	1459.8	1457.7	1457.7
7.5°	1479.6	1494.2	1512.0	1536.0	1539.1	1546.4	1559.0	1559.0	1566.3	1563.1	1562.1
10°	1549.6	1567.3	1595.5	1614.3	1622.7	1626.8	1639.4	1643.5	1651.9	1652.9	1652.9
12.5°	1607.0	1638.3	1657.1	1675.9	1680.1	1686.4	1695.7	1702.0	1705.1	1705.1	1702.0
15°	1637.3	1662.3	1684.3	1704.1	1715.6	1720.8	1730.2	1737.5	1741.7	1751.1	1753.2
17.5°	1649.8	1680.1	1715.6	1743.8	1763.6	1768.8	1787.6	1793.9	1802.3	1806.4	1811.7
20°	1667.6	1711.4	1754.2	1788.7	1807.5	1821.0	1840.9	1870.1	1878.5	1878.5	1875.3
22.5°	1683.2	1739.6	1798.1	1853.4	1869.1	1896.2	1932.8	1964.1	1976.6	1981.9	1977.7
25°	1702.0	1779.3	1855.5	1924.4	1967.2	1987.1	2036.2	2073.7	2088.4	2096.7	2098.8
27.5°	1734.4	1831.5	1928.6	2016.3	2060.2	2083.1	2134.3	2166.7	2184.4	2191.7	2186.5
30°	1770.9	1890.0	2002.7	2081.1	2110.3	2138.5	2171.9	2184.4	2180.2	2180.2	2195.9
32.5°	1808.5	1931.7	2032.0	2083.1	2093.6	2089.4	2075.8	2038.2	2016.3	2016.3	2029.9
35°	1829.4	1935.9	1987.1	1970.4	1929.6	1905.6	1831.5	1789.7	1742.7	1739.6	1755.3
37.5°	1817.9	1863.9	1843.0	1733.3	1678.0	1632.1	1516.1	1470.2	1435.7	1387.7	1461.9
40°	1737.5	1721.9	1613.3	1455.6	1394.0	1329.2	1237.4	1191.4	1143.4	1136.1	1153.8
42.5°	1601.8	1508.8	1350.1	1197.7	1135.0	1089.1	1019.1	974.2	943.9	931.4	952.3
45°	1432.6	1286.4	1127.7	1006.6	937.7	913.7	850.0	810.3	787.3	777.9	792.5
47.5°	1225.9	1078.6	928.3	825.9	785.2	761.2	718.4	683.9	664.1	657.8	664.1
50°	1041.0	889.6	763.3	697.5	661.0	641.1	605.6	583.7	568.0	563.9	574.3
52.5°	881.3	743.5	647.4	588.9	564.9	548.2	523.1	504.3	494.9	490.8	498.1
55°	738.2	626.5	549.2	499.1	481.4	470.9	449.0	438.6	428.1	427.1	434.4
57.5°	611.9	534.6	463.6	428.1	422.9	407.2	388.4	379.0	373.8	372.8	375.9
60°	509.6	440.6	397.8	366.5	359.2	346.7	336.2	330.0	323.7	321.6	323.7
62.5°	423.9	369.6	335.2	314.3	303.9	300.7	289.2	281.9	280.9	280.9	283.0
65°	349.8	303.9	281.9	265.2	257.9	254.8	246.4	241.2	242.2	242.2	243.3
67.5°	285.1	251.6	231.8	223.5	217.2	216.1	207.8	205.7	203.6	203.6	205.7
70°	226.6	205.7	191.1	186.9	185.9	178.6	175.4	174.4	171.2	172.3	172.3
72.5°	177.5	163.9	155.6	149.3	150.4	146.2	142.0	142.0	139.9	143.1	143.1
75°	131.6	125.3	119.0	116.9	119.0	116.9	113.8	112.8	113.8	112.8	112.8
77.5°	97.1	94.0	91.9	90.8	90.8	86.7	84.6	86.7	82.5	84.6	84.6
80°	67.9	63.7	62.7	60.6	61.6	58.5	59.5	57.4	57.4	57.4	57.4
82.5°	42.8	41.8	41.8	41.8	40.7	40.7	40.7	40.7	40.7	40.7	39.7
85°	26.1	25.1	25.1	25.1	24.0	24.0	24.0	24.0	24.0	24.0	24.0
87.5°	10.4	11.5	11.5	12.5	11.5	10.4	10.4	10.4	11.5	11.5	10.4
90°	16.9	18.0	19.1	20.2	20.8	21.1	21.8	22.4	23.1	23.7	23.1
92.5°	16.9	18.0	19.1	20.2	20.8	20.9	21.1	21.3	21.5	21.7	21.5
95°	16.9	18.0	19.1	20.2	20.8	20.8	20.8	20.8	20.8	20.8	20.8
97.5°	18.2	18.7	19.1	19.6	19.8	19.9	20.1	20.4	20.6	20.8	20.6
100°	139.3	106.5	73.8	41.1	24.7	24.3	23.4	22.5	21.7	20.8	21.7
102.5°	231.7	232.2	232.6	233.1	233.3	224.1	205.6	187.1	168.7	150.2	168.7
105°	294.6	294.6	294.6	294.6	294.6	294.5	294.3	294.0	293.8	293.6	293.8
107.5°	360.0	360.2	360.5	360.7	360.8	360.4	359.5	358.6	357.7	356.8	357.7
110°	424.4	423.7	423.1	422.4	422.1	422.2	422.4	422.7	422.9	423.1	422.9

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	487.4	486.5	485.6	484.7	484.3	484.1	483.7	483.2	482.8	482.4	482.8
115°	550.7	549.8	548.9	548.0	547.6	546.9	545.6	544.3	543.0	541.7	543.0
117.5°	612.5	611.2	609.9	608.6	607.9	607.7	607.2	606.8	606.3	605.9	606.3
120°	670.8	670.3	669.9	669.4	669.2	668.6	667.5	666.4	665.3	664.2	665.3
122.5°	727.1	726.6	726.2	725.7	725.5	724.8	723.5	722.2	720.9	719.6	720.9
125°	782.0	781.1	780.2	779.3	778.9	778.6	777.9	777.2	776.6	775.9	776.6
127.5°	831.9	831.4	831.0	830.5	830.3	829.4	827.7	825.9	824.2	822.4	824.2
130°	881.0	880.4	879.7	879.0	878.7	878.2	877.1	876.0	874.9	873.8	874.9
132.5°	926.2	926.2	926.2	926.2	926.2	925.6	924.5	923.4	922.3	921.2	922.3
135°	971.3	970.8	970.4	969.9	969.7	969.0	967.7	966.4	965.0	963.7	965.0
137.5°	1013.2	1013.2	1013.2	1013.2	1013.2	1012.6	1011.5	1010.4	1009.3	1008.2	1009.3
140°	1051.1	1051.6	1052.0	1052.5	1052.7	1052.0	1050.7	1049.4	1048.1	1046.8	1048.1
142.5°	1089.3	1089.3	1089.3	1089.3	1089.3	1088.6	1087.3	1086.0	1084.7	1083.4	1084.7
145°	1124.1	1124.3	1124.6	1124.8	1124.9	1124.2	1122.9	1121.6	1120.2	1118.9	1120.2
147.5°	1154.7	1154.9	1155.2	1155.4	1155.5	1154.7	1153.2	1151.7	1150.1	1148.6	1150.1
150°	1183.6	1184.1	1184.5	1185.0	1185.2	1184.3	1182.6	1180.8	1179.1	1177.3	1179.1
152.5°	1209.3	1209.8	1210.2	1210.7	1210.9	1210.1	1208.6	1207.0	1205.5	1203.9	1205.5
155°	1232.3	1232.9	1233.6	1234.3	1234.6	1233.7	1232.0	1230.2	1228.5	1226.7	1228.5
157.5°	1252.1	1252.7	1253.4	1254.1	1254.4	1253.5	1251.7	1250.0	1248.2	1246.4	1248.2
160°	1270.1	1270.9	1271.8	1272.7	1273.1	1272.2	1270.5	1268.7	1267.0	1265.2	1267.0
162.5°	1286.3	1287.6	1288.9	1290.2	1290.9	1289.9	1287.9	1286.0	1284.0	1282.0	1284.0
165°	1300.1	1301.5	1302.8	1304.1	1304.8	1303.9	1302.2	1300.4	1298.7	1296.9	1298.7
167.5°	1311.2	1312.8	1314.3	1315.8	1316.6	1315.6	1313.6	1311.7	1309.7	1307.7	1309.7
170°	1319.4	1321.1	1322.9	1324.6	1325.5	1324.5	1322.5	1320.6	1318.6	1316.6	1318.6
172.5°	1326.1	1327.6	1329.2	1330.7	1331.5	1330.5	1328.5	1326.6	1324.6	1322.6	1324.6
175°	1330.3	1332.0	1333.8	1335.5	1336.4	1335.4	1333.4	1331.5	1329.5	1327.5	1329.5
177.5°	1333.0	1334.6	1336.1	1337.6	1338.4	1337.5	1335.8	1334.0	1332.3	1330.5	1332.3
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1355.3	1348.0	1351.2	1348.0	1344.9	1341.8	1334.5	1324.0	1315.7	1309.4	1308.4
5°	1459.8	1450.4	1444.1	1441.0	1434.7	1426.3	1412.8	1397.1	1378.3	1371.0	1356.4
7.5°	1555.8	1552.7	1538.1	1536.0	1531.8	1516.1	1493.2	1472.3	1448.3	1428.4	1409.6
10°	1646.7	1639.4	1628.9	1614.3	1612.2	1592.4	1570.4	1541.2	1509.9	1491.1	1457.7
12.5°	1703.1	1694.7	1683.2	1673.8	1668.6	1656.1	1625.8	1596.6	1568.4	1533.9	1504.7
15°	1743.8	1733.3	1712.5	1705.1	1698.9	1682.2	1660.2	1630.0	1592.4	1568.4	1526.6
17.5°	1799.1	1786.6	1765.7	1752.1	1740.6	1714.5	1683.2	1642.5	1607.0	1579.8	1542.3
20°	1862.8	1844.0	1816.9	1799.1	1782.4	1752.1	1708.3	1660.2	1609.1	1575.7	1537.0
22.5°	1968.3	1932.8	1890.0	1864.9	1841.9	1789.7	1737.5	1678.0	1620.6	1570.4	1523.5
25°	2070.6	2035.1	1981.9	1947.4	1911.9	1851.3	1782.4	1699.9	1626.8	1568.4	1506.8
27.5°	2165.6	2129.1	2080.0	2038.2	2003.8	1912.9	1822.1	1729.2	1636.2	1555.8	1493.2
30°	2187.6	2171.9	2134.3	2097.8	2066.4	1982.9	1877.4	1759.4	1647.7	1544.3	1474.4
32.5°	2054.9	2093.6	2103.0	2097.8	2077.9	2018.4	1921.3	1797.0	1664.4	1539.1	1443.1
35°	1779.3	1849.2	1921.3	1959.9	1978.7	1987.1	1929.6	1815.8	1675.9	1530.8	1422.2
37.5°	1475.4	1543.3	1657.1	1714.5	1778.2	1861.8	1884.7	1811.7	1670.7	1524.5	1388.8
40°	1212.3	1299.0	1392.9	1445.1	1500.5	1650.8	1764.7	1756.3	1654.0	1501.5	1362.7
42.5°	986.7	1041.0	1123.5	1181.0	1248.8	1417.0	1569.4	1644.6	1603.9	1473.3	1329.2
45°	822.8	864.6	923.1	981.5	1023.3	1175.7	1356.4	1479.6	1518.2	1423.2	1278.1
47.5°	693.3	724.7	775.8	812.4	857.3	977.4	1134.0	1307.3	1388.8	1352.2	1223.8
50°	594.1	619.2	659.9	682.9	722.6	825.9	945.0	1126.7	1249.9	1254.1	1151.7
52.5°	507.5	532.5	567.0	586.8	610.8	680.8	800.9	954.4	1096.4	1148.6	1069.2
55°	441.7	456.3	484.5	500.2	522.1	590.0	666.2	796.7	945.0	1030.6	980.5
57.5°	381.1	396.8	414.5	427.1	442.7	497.0	565.9	664.1	811.3	904.3	887.6
60°	332.0	341.4	358.2	367.6	382.2	417.7	465.7	563.9	680.8	768.5	777.9
62.5°	286.1	294.5	305.9	314.3	323.7	351.9	387.4	457.4	559.7	654.7	667.2
65°	246.4	253.7	260.0	267.3	274.6	292.4	322.7	376.9	456.3	545.1	572.2
67.5°	210.9	213.0	222.4	223.5	227.6	241.2	263.1	307.0	364.4	435.4	470.9
70°	176.5	180.6	182.7	185.9	190.0	199.4	217.2	240.2	283.0	340.4	373.8
72.5°	143.1	144.1	147.2	149.3	153.5	160.8	169.2	186.9	214.1	255.8	286.1
75°	113.8	114.9	116.9	118.0	121.1	123.2	127.4	139.9	158.7	183.8	205.7
77.5°	85.6	87.7	89.8	89.8	90.8	92.9	95.0	99.2	108.6	125.3	144.1
80°	58.5	59.5	59.5	60.6	59.5	62.7	65.8	71.0	75.2	80.4	89.8
82.5°	40.7	40.7	40.7	41.8	41.8	42.8	42.8	43.9	44.9	48.0	52.2
85°	25.1	25.1	26.1	24.0	25.1	26.1	26.1	25.1	26.1	27.1	28.2
87.5°	10.4	10.4	11.5	11.5	11.5	11.5	10.4	11.5	10.4	11.5	11.5
90°	22.4	21.8	21.1	20.8	20.2	19.1	18.0	16.9	15.8	14.3	12.7
92.5°	21.3	21.1	20.9	20.8	20.2	19.1	18.0	16.9	15.8	14.5	13.2
95°	20.8	20.8	20.8	20.8	20.2	19.1	18.0	16.9	15.8	24.2	32.5
97.5°	20.4	20.1	19.9	19.8	19.6	19.1	18.7	18.2	17.8	38.7	59.5
100°	22.5	23.4	24.3	24.7	41.1	73.8	106.5	139.3	172.0	171.1	170.2
102.5°	187.1	205.6	224.1	233.3	233.1	232.6	232.2	231.7	231.3	230.9	230.4
105°	294.0	294.3	294.5	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6
107.5°	358.6	359.5	360.4	360.8	360.7	360.5	360.2	360.0	359.8	359.4	358.9
110°	422.7	422.4	422.2	422.1	422.4	423.1	423.7	424.4	425.0	424.6	424.2

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	483.2	483.7	484.1	484.3	484.7	485.6	486.5	487.4	488.3	488.1	487.9
115°	544.3	545.6	546.9	547.6	548.0	548.9	549.8	550.7	551.6	551.4	551.2
117.5°	606.8	607.2	607.7	607.9	608.6	609.9	611.2	612.5	613.8	612.9	612.1
120°	666.4	667.5	668.6	669.2	669.4	669.9	670.3	670.8	671.2	670.5	669.9
122.5°	722.2	723.5	724.8	725.5	725.7	726.2	726.6	727.1	727.5	727.3	727.1
125°	777.2	777.9	778.6	778.9	779.3	780.2	781.1	782.0	782.9	782.9	782.9
127.5°	825.9	827.7	829.4	830.3	830.5	831.0	831.4	831.9	832.3	832.5	832.7
130°	876.0	877.1	878.2	878.7	879.0	879.7	880.4	881.0	881.7	881.5	881.3
132.5°	923.4	924.5	925.6	926.2	926.2	926.2	926.2	926.2	926.2	926.9	927.5
135°	966.4	967.7	969.0	969.7	969.9	970.4	970.8	971.3	971.7	972.1	972.5
137.5°	1010.4	1011.5	1012.6	1013.2	1013.2	1013.2	1013.2	1013.2	1013.2	1013.6	1014.0
140°	1049.4	1050.7	1052.0	1052.7	1052.5	1052.0	1051.6	1051.1	1050.7	1050.9	1051.1
142.5°	1086.0	1087.3	1088.6	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1088.9	1088.4
145°	1121.6	1122.9	1124.2	1124.9	1124.8	1124.6	1124.3	1124.1	1123.9	1123.9	1123.9
147.5°	1151.7	1153.2	1154.7	1155.5	1155.4	1155.2	1154.9	1154.7	1154.5	1154.3	1154.1
150°	1180.8	1182.6	1184.3	1185.2	1185.0	1184.5	1184.1	1183.6	1183.2	1182.8	1182.3
152.5°	1207.0	1208.6	1210.1	1210.9	1210.7	1210.2	1209.8	1209.3	1208.9	1208.5	1208.0
155°	1230.2	1232.0	1233.7	1234.6	1234.3	1233.6	1232.9	1232.3	1231.6	1231.2	1230.7
157.5°	1250.0	1251.7	1253.5	1254.4	1254.1	1253.4	1252.7	1252.1	1251.4	1251.4	1251.4
160°	1268.7	1270.5	1272.2	1273.1	1272.7	1271.8	1270.9	1270.1	1269.2	1269.0	1268.8
162.5°	1286.0	1287.9	1289.9	1290.9	1290.2	1288.9	1287.6	1286.3	1285.0	1284.8	1284.6
165°	1300.4	1302.2	1303.9	1304.8	1304.1	1302.8	1301.5	1300.1	1298.8	1298.6	1298.4
167.5°	1311.7	1313.6	1315.6	1316.6	1315.8	1314.3	1312.8	1311.2	1309.7	1309.5	1309.3
170°	1320.6	1322.5	1324.5	1325.5	1324.6	1322.9	1321.1	1319.4	1317.6	1317.4	1317.2
172.5°	1326.6	1328.5	1330.5	1331.5	1330.7	1329.2	1327.6	1326.1	1324.5	1324.1	1323.7
175°	1331.5	1333.4	1335.4	1336.4	1335.5	1333.8	1332.0	1330.3	1328.5	1328.3	1328.1
177.5°	1334.0	1335.8	1337.5	1338.4	1337.6	1336.1	1334.6	1333.0	1331.5	1331.3	1331.1
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1305.2	1299.0	1294.8	1293.7	1287.5	1282.3	1276.0	1274.9	1271.8	1263.5	1258.2
5°	1345.9	1331.3	1328.2	1318.8	1303.1	1291.7	1277.0	1268.7	1259.3	1243.6	1231.1
7.5°	1387.7	1367.9	1353.3	1339.7	1317.8	1296.9	1276.0	1259.3	1242.6	1219.6	1200.8
10°	1428.4	1398.2	1380.4	1360.6	1330.3	1299.0	1269.7	1245.7	1218.6	1191.4	1164.3
12.5°	1466.0	1427.4	1401.3	1373.1	1335.5	1296.9	1259.3	1225.9	1197.7	1161.1	1130.8
15°	1489.0	1446.2	1420.1	1392.9	1336.5	1293.7	1249.9	1207.1	1169.5	1130.8	1102.7
17.5°	1502.6	1454.5	1425.3	1400.2	1342.8	1284.3	1228.0	1182.0	1141.3	1095.3	1057.8
20°	1496.3	1449.3	1422.2	1398.2	1331.3	1272.9	1212.3	1159.0	1107.9	1060.9	1021.2
22.5°	1482.7	1433.7	1403.4	1381.4	1321.9	1253.0	1186.2	1128.8	1075.5	1028.5	983.6
25°	1453.5	1405.5	1379.4	1352.2	1293.7	1228.0	1160.1	1098.5	1042.1	992.0	941.9
27.5°	1427.4	1368.9	1341.8	1317.8	1256.1	1197.7	1130.8	1063.0	1005.5	953.3	903.2
30°	1397.1	1331.3	1302.1	1269.7	1214.4	1159.0	1092.2	1029.6	970.0	914.7	866.7
32.5°	1364.7	1288.5	1255.1	1218.6	1162.2	1110.0	1053.6	992.0	932.5	878.2	828.0
35°	1323.0	1241.5	1202.9	1168.4	1110.0	1057.8	1005.5	954.4	894.9	837.4	789.4
37.5°	1283.3	1193.5	1152.8	1113.1	1051.5	1001.4	958.6	910.5	853.1	797.8	751.8
40°	1238.4	1135.0	1093.3	1056.7	993.0	937.7	899.0	861.4	811.3	758.1	708.0
42.5°	1197.7	1080.7	1036.9	999.3	932.5	880.2	843.7	812.4	768.5	719.4	668.3
45°	1141.3	1022.3	977.4	937.7	869.8	820.7	783.1	756.0	721.5	675.6	629.6
47.5°	1089.1	965.9	916.8	868.8	807.2	757.0	722.6	701.7	678.7	638.0	591.0
50°	1025.4	901.1	851.0	811.3	741.4	698.6	664.1	649.5	628.6	590.0	552.4
52.5°	956.5	838.5	791.5	743.5	678.7	636.9	606.7	590.0	573.3	545.1	509.6
55°	876.1	768.5	724.7	681.8	617.1	578.5	551.3	533.6	524.2	498.1	472.0
57.5°	798.8	697.5	656.8	617.1	560.7	516.9	499.1	483.5	469.9	451.1	429.2
60°	720.5	628.6	584.7	549.2	500.2	460.5	445.9	430.2	419.8	405.1	389.5
62.5°	630.7	552.4	519.0	485.5	443.8	412.5	395.7	383.2	369.6	360.2	346.7
65°	535.7	480.3	448.0	422.9	383.2	355.0	342.5	334.1	322.7	313.3	302.8
67.5°	446.9	403.1	389.5	362.3	332.0	307.0	297.6	287.1	277.8	272.5	263.1
70°	361.3	330.0	316.4	309.1	275.7	259.0	250.6	246.4	234.9	229.7	223.5
72.5°	279.8	268.4	259.0	249.6	227.6	217.2	207.8	203.6	195.3	191.1	189.0
75°	206.7	199.4	194.2	193.2	183.8	173.3	163.9	161.8	155.6	151.4	149.3
77.5°	145.1	143.1	142.0	143.1	136.8	130.5	128.4	126.3	119.0	118.0	118.0
80°	95.0	100.2	100.2	99.2	97.1	96.1	92.9	90.8	86.7	85.6	86.7
82.5°	58.5	61.6	62.7	64.7	63.7	62.7	60.6	59.5	60.6	58.5	59.5
85°	29.2	31.3	35.5	35.5	36.5	36.5	36.5	35.5	33.4	34.5	33.4
87.5°	11.5	12.5	12.5	12.5	11.5	14.6	15.7	15.7	15.7	13.6	13.6
90°	11.2	9.7	8.9	8.0	6.3	4.5	2.8	1.0	2.8	4.5	6.3
92.5°	11.9	10.6	9.9	10.9	12.9	14.8	16.8	18.8	16.8	14.8	12.9
95°	40.9	49.2	53.4	53.7	54.4	55.0	55.7	56.3	55.7	55.0	54.4
97.5°	80.4	101.3	111.7	111.0	109.7	108.4	107.1	105.8	107.1	108.4	109.7
100°	169.3	168.4	168.0	167.7	167.0	166.4	165.7	165.1	165.7	166.4	167.0
102.5°	230.0	229.5	229.3	228.9	228.0	227.1	226.3	225.4	226.3	227.1	228.0
105°	294.6	294.6	294.6	294.2	293.3	292.4	291.5	290.6	291.5	292.4	293.3
107.5°	358.5	358.0	357.8	357.8	357.8	357.8	357.8	357.8	357.8	357.8	357.8
110°	423.7	423.3	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1	423.1

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	487.6	487.4	487.3	487.0	486.3	485.6	485.0	484.3	485.0	485.6	486.3
115°	550.9	550.7	550.6	550.0	548.9	547.8	546.7	545.6	546.7	547.8	548.9
117.5°	611.2	610.3	609.9	609.9	609.9	609.9	609.9	609.9	609.9	609.9	609.9
120°	669.2	668.5	668.2	668.3	668.5	668.8	669.0	669.2	669.0	668.8	668.5
122.5°	726.8	726.6	726.5	726.0	724.9	723.8	722.7	721.6	722.7	723.8	724.9
125°	782.9	782.9	782.9	782.1	780.6	779.0	777.5	775.9	777.5	779.0	780.6
127.5°	833.0	833.2	833.3	832.7	831.6	830.5	829.4	828.3	829.4	830.5	831.6
130°	881.0	880.8	880.7	880.2	879.1	878.0	876.9	875.8	876.9	878.0	879.1
132.5°	928.2	928.9	929.2	928.5	927.2	925.9	924.5	923.2	924.5	925.9	927.2
135°	973.0	973.4	973.6	972.9	971.6	970.3	969.0	967.7	969.0	970.3	971.6
137.5°	1014.5	1014.9	1015.1	1014.4	1013.1	1011.8	1010.5	1009.2	1010.5	1011.8	1013.1
140°	1051.4	1051.6	1051.7	1051.5	1051.0	1050.6	1050.1	1049.7	1050.1	1050.6	1051.0
142.5°	1088.0	1087.5	1087.3	1087.2	1087.0	1086.7	1086.5	1086.3	1086.5	1086.7	1087.0
145°	1123.9	1123.9	1123.9	1123.7	1123.2	1122.8	1122.3	1121.9	1122.3	1122.8	1123.2
147.5°	1153.8	1153.6	1153.5	1153.5	1153.5	1153.5	1153.5	1153.5	1153.5	1153.5	1153.5
150°	1181.9	1181.4	1181.2	1181.4	1181.9	1182.3	1182.8	1183.2	1182.8	1182.3	1181.9
152.5°	1207.6	1207.1	1206.9	1207.5	1208.6	1209.7	1210.8	1211.9	1210.8	1209.7	1208.6
155°	1230.3	1229.8	1229.6	1230.3	1231.6	1232.9	1234.3	1235.6	1234.3	1232.9	1231.6
157.5°	1251.4	1251.4	1251.4	1251.7	1252.4	1253.1	1253.7	1254.4	1253.7	1253.1	1252.4
160°	1268.5	1268.3	1268.2	1268.9	1270.2	1271.5	1272.8	1274.1	1272.8	1271.5	1270.2
162.5°	1284.3	1284.1	1284.0	1284.7	1286.0	1287.3	1288.6	1289.9	1288.6	1287.3	1286.0
165°	1298.1	1297.9	1297.8	1298.5	1299.8	1301.1	1302.5	1303.8	1302.5	1301.1	1299.8
167.5°	1309.0	1308.8	1308.7	1309.4	1310.7	1312.0	1313.4	1314.7	1313.4	1312.0	1310.7
170°	1316.9	1316.7	1316.6	1317.4	1318.9	1320.4	1322.0	1323.5	1322.0	1320.4	1318.9
172.5°	1323.2	1322.8	1322.6	1323.4	1324.9	1326.4	1328.0	1329.5	1328.0	1326.4	1324.9
175°	1327.8	1327.6	1327.5	1328.2	1329.5	1330.8	1332.1	1333.4	1332.1	1330.8	1329.5
177.5°	1330.8	1330.6	1330.5	1331.2	1332.5	1333.8	1335.1	1336.4	1335.1	1333.8	1332.5
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1255.1	1250.9	1247.8	1244.7	1231.1	1216.5	1214.4	1211.2	1205.0	1212.3	1209.2
5°	1222.7	1213.3	1208.1	1194.5	1177.8	1165.3	1154.9	1142.3	1137.1	1132.9	1131.9
7.5°	1183.1	1174.7	1165.3	1151.7	1130.8	1110.0	1094.3	1081.8	1071.3	1066.1	1066.1
10°	1144.4	1134.0	1121.4	1098.5	1078.6	1052.5	1035.8	1023.3	1008.7	1000.3	993.0
12.5°	1104.7	1093.3	1081.8	1052.5	1029.6	1002.4	978.4	962.7	955.4	946.0	933.5
15°	1065.1	1047.3	1035.8	1006.6	977.4	950.2	934.5	917.8	901.1	891.7	887.6
17.5°	1023.3	1010.8	992.0	960.6	928.3	904.3	881.3	865.6	845.8	836.4	827.0
20°	985.7	966.9	948.1	916.8	885.5	853.1	830.1	811.3	798.8	791.5	783.1
22.5°	940.8	923.1	907.4	874.0	839.5	809.2	784.2	772.7	760.2	748.7	740.3
25°	902.2	884.4	868.8	832.2	794.6	766.4	747.6	733.0	719.4	714.2	705.9
27.5°	861.4	844.7	823.9	787.3	753.9	729.9	710.0	696.5	686.0	675.6	669.3
30°	822.8	804.0	785.2	745.5	718.4	694.4	675.6	658.9	650.5	645.3	634.9
32.5°	785.2	761.2	745.5	709.0	682.9	659.9	644.3	629.6	619.2	609.8	601.4
35°	744.5	718.4	702.7	672.5	645.3	622.3	608.8	598.3	585.8	577.4	573.3
37.5°	705.9	683.9	668.3	636.9	609.8	591.0	576.4	562.8	557.6	546.1	544.0
40°	664.1	645.3	630.7	600.4	575.3	560.7	545.1	532.5	523.1	517.9	510.6
42.5°	626.5	610.8	595.2	567.0	543.0	525.2	513.7	502.3	493.9	485.5	480.3
45°	592.0	575.3	560.7	533.6	509.6	493.9	482.4	468.8	466.7	455.3	450.0
47.5°	555.5	540.9	528.4	500.2	478.2	462.6	449.0	439.6	430.2	426.0	418.7
50°	520.0	505.4	490.8	465.7	445.9	430.2	416.6	406.2	401.0	394.7	388.4
52.5°	481.4	469.9	458.4	432.3	412.5	398.9	387.4	373.8	368.6	363.4	359.2
55°	449.0	432.3	419.8	397.8	380.1	365.5	352.9	342.5	337.3	333.1	327.9
57.5°	405.1	394.7	384.3	364.4	347.7	333.1	320.6	312.2	305.9	302.8	303.9
60°	367.6	356.1	349.8	328.9	312.2	300.7	289.2	280.9	274.6	271.5	270.4
62.5°	327.9	319.5	308.0	293.4	276.7	266.3	257.9	251.6	241.2	240.2	237.0
65°	289.2	283.0	272.5	259.0	245.4	236.0	226.6	218.2	214.1	208.8	205.7
67.5°	251.6	245.4	236.0	224.5	215.1	205.7	197.3	189.0	181.7	177.5	175.4
70°	215.1	209.9	203.6	190.0	178.6	171.2	165.0	159.8	152.5	150.4	149.3
72.5°	179.6	174.4	171.2	159.8	149.3	143.1	136.8	131.6	128.4	127.4	124.3
75°	147.2	142.0	137.8	127.4	121.1	116.9	110.7	108.6	105.5	104.4	103.4
77.5°	114.9	109.6	108.6	101.3	94.0	91.9	89.8	85.6	85.6	85.6	83.5
80°	82.5	81.4	80.4	73.1	70.0	67.9	66.8	63.7	61.6	59.5	58.5
82.5°	55.3	54.3	53.3	50.1	47.0	45.9	44.9	42.8	42.8	43.9	41.8
85°	33.4	31.3	30.3	29.2	27.1	27.1	28.2	27.1	27.1	27.1	26.1
87.5°	12.5	12.5	12.5	12.5	13.6	11.5	12.5	12.5	11.5	11.5	10.4
90°	8.0	8.9	9.7	11.2	12.7	14.3	15.8	16.9	18.0	19.1	20.2
92.5°	10.9	9.9	10.6	11.9	13.2	14.5	15.8	16.9	18.0	19.1	20.2
95°	53.7	53.4	49.2	40.9	32.5	24.2	15.8	16.9	18.0	19.1	20.2
97.5°	111.0	111.7	101.3	80.4	59.5	38.7	17.8	18.2	18.7	19.1	19.6
100°	167.7	168.0	168.4	169.3	170.2	171.1	172.0	139.3	106.5	73.8	41.1
102.5°	228.9	229.3	229.5	230.0	230.4	230.9	231.3	231.7	232.2	232.6	233.1
105°	294.2	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6
107.5°	357.8	357.8	358.0	358.5	358.9	359.4	359.8	360.0	360.2	360.5	360.7
110°	423.1	423.1	423.3	423.7	424.2	424.6	425.0	424.4	423.7	423.1	422.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	487.0	487.3	487.4	487.6	487.9	488.1	488.3	487.4	486.5	485.6	484.7
115°	550.0	550.6	550.7	550.9	551.2	551.4	551.6	550.7	549.8	548.9	548.0
117.5°	609.9	609.9	610.3	611.2	612.1	612.9	613.8	612.5	611.2	609.9	608.6
120°	668.3	668.2	668.5	669.2	669.9	670.5	671.2	670.8	670.3	669.9	669.4
122.5°	726.0	726.5	726.6	726.8	727.1	727.3	727.5	727.1	726.6	726.2	725.7
125°	782.1	782.9	782.9	782.9	782.9	782.9	782.9	782.0	781.1	780.2	779.3
127.5°	832.7	833.3	833.2	833.0	832.7	832.5	832.3	831.9	831.4	831.0	830.5
130°	880.2	880.7	880.8	881.0	881.3	881.5	881.7	881.0	880.4	879.7	879.0
132.5°	928.5	929.2	928.9	928.2	927.5	926.9	926.2	926.2	926.2	926.2	926.2
135°	972.9	973.6	973.4	973.0	972.5	972.1	971.7	971.3	970.8	970.4	969.9
137.5°	1014.4	1015.1	1014.9	1014.5	1014.0	1013.6	1013.2	1013.2	1013.2	1013.2	1013.2
140°	1051.5	1051.7	1051.6	1051.4	1051.1	1050.9	1050.7	1051.1	1051.6	1052.0	1052.5
142.5°	1087.2	1087.3	1087.5	1088.0	1088.4	1088.9	1089.3	1089.3	1089.3	1089.3	1089.3
145°	1123.7	1123.9	1123.9	1123.9	1123.9	1123.9	1123.9	1124.1	1124.3	1124.6	1124.8
147.5°	1153.5	1153.5	1153.6	1153.8	1154.1	1154.3	1154.5	1154.7	1154.9	1155.2	1155.4
150°	1181.4	1181.2	1181.4	1181.9	1182.3	1182.8	1183.2	1183.6	1184.1	1184.5	1185.0
152.5°	1207.5	1206.9	1207.1	1207.6	1208.0	1208.5	1208.9	1209.3	1209.8	1210.2	1210.7
155°	1230.3	1229.6	1229.8	1230.3	1230.7	1231.2	1231.6	1232.3	1232.9	1233.6	1234.3
157.5°	1251.7	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1252.1	1252.7	1253.4	1254.1
160°	1268.9	1268.2	1268.3	1268.5	1268.8	1269.0	1269.2	1270.1	1270.9	1271.8	1272.7
162.5°	1284.7	1284.0	1284.1	1284.3	1284.6	1284.8	1285.0	1286.3	1287.6	1288.9	1290.2
165°	1298.5	1297.8	1297.9	1298.1	1298.4	1298.6	1298.8	1300.1	1301.5	1302.8	1304.1
167.5°	1309.4	1308.7	1308.8	1309.0	1309.3	1309.5	1309.7	1311.2	1312.8	1314.3	1315.8
170°	1317.4	1316.6	1316.7	1316.9	1317.2	1317.4	1317.6	1319.4	1321.1	1322.9	1324.6
172.5°	1323.4	1322.6	1322.8	1323.2	1323.7	1324.1	1324.5	1326.1	1327.6	1329.2	1330.7
175°	1328.2	1327.5	1327.6	1327.8	1328.1	1328.3	1328.5	1330.3	1332.0	1333.8	1335.5
177.5°	1331.2	1330.5	1330.6	1330.8	1331.1	1331.3	1331.5	1333.0	1334.6	1336.1	1337.6
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1203.9	1206.0	1200.8	1198.7	1194.5	1199.8	1200.8	1199.8	1209.2	1205.0	1207.1
5°	1134.0	1129.8	1126.7	1119.4	1119.4	1120.4	1123.5	1118.3	1121.4	1128.8	1127.7
7.5°	1056.7	1054.6	1055.7	1047.3	1041.0	1043.1	1041.0	1050.4	1055.7	1053.6	1057.8
10°	986.7	990.9	981.5	977.4	973.2	977.4	976.3	978.4	984.7	988.8	996.1
12.5°	930.4	929.3	924.1	919.9	912.6	914.7	921.0	918.9	919.9	929.3	928.3
15°	877.1	870.8	866.7	857.3	859.4	852.1	858.3	865.6	868.8	877.1	882.3
17.5°	823.9	822.8	817.6	816.5	805.1	801.9	808.2	810.3	813.4	817.6	824.9
20°	779.0	777.9	770.6	768.5	759.1	765.4	763.3	767.5	769.6	777.9	781.0
22.5°	738.2	733.0	730.9	727.8	724.7	723.6	727.8	726.7	734.1	737.2	738.2
25°	700.6	696.5	695.4	690.2	688.1	685.0	688.1	691.2	699.6	702.7	706.9
27.5°	666.2	663.1	661.0	656.8	653.7	653.7	655.7	659.9	663.1	665.1	667.2
30°	634.9	632.8	626.5	624.4	621.3	621.3	621.3	623.4	628.6	634.9	638.0
32.5°	602.5	598.3	594.1	594.1	591.0	591.0	592.0	594.1	599.4	600.4	605.6
35°	571.2	567.0	563.9	561.8	562.8	558.6	560.7	563.9	570.1	572.2	575.3
37.5°	540.9	539.8	533.6	530.4	532.5	532.5	531.5	533.6	537.8	541.9	544.0
40°	507.5	505.4	505.4	502.3	503.3	499.1	502.3	504.3	506.4	510.6	513.7
42.5°	478.2	476.1	472.0	473.0	469.9	469.9	472.0	473.0	476.1	481.4	483.5
45°	446.9	446.9	444.8	441.7	442.7	439.6	441.7	442.7	446.9	452.1	450.0
47.5°	416.6	415.6	415.6	411.4	413.5	410.4	413.5	414.5	416.6	419.8	418.7
50°	387.4	384.3	385.3	384.3	383.2	383.2	385.3	385.3	387.4	387.4	390.5
52.5°	357.1	357.1	355.0	356.1	358.2	356.1	359.2	356.1	358.2	359.2	361.3
55°	330.0	327.9	328.9	327.9	332.0	328.9	332.0	330.0	332.0	331.0	333.1
57.5°	300.7	297.6	298.6	297.6	300.7	299.7	302.8	299.7	300.7	301.8	304.9
60°	267.3	267.3	267.3	265.2	268.4	268.4	267.3	267.3	271.5	273.6	272.5
62.5°	236.0	234.9	231.8	230.8	231.8	229.7	233.9	232.9	234.9	237.0	239.1
65°	201.5	199.4	198.4	196.3	196.3	195.3	196.3	200.5	201.5	202.6	207.8
67.5°	173.3	172.3	171.2	168.1	168.1	170.2	170.2	170.2	176.5	173.3	177.5
70°	148.3	146.2	144.1	143.1	143.1	144.1	145.1	146.2	145.1	149.3	150.4
72.5°	124.3	125.3	123.2	123.2	123.2	122.2	122.2	124.3	125.3	124.3	125.3
75°	103.4	103.4	102.3	103.4	103.4	102.3	102.3	104.4	104.4	103.4	106.5
77.5°	83.5	82.5	80.4	78.3	79.4	78.3	79.4	78.3	81.4	84.6	82.5
80°	58.5	57.4	57.4	57.4	58.5	57.4	59.5	57.4	58.5	58.5	59.5
82.5°	41.8	42.8	42.8	41.8	42.8	41.8	42.8	42.8	42.8	41.8	42.8
85°	27.1	27.1	27.1	27.1	26.1	27.1	27.1	27.1	28.2	27.1	28.2
87.5°	11.5	11.5	11.5	11.5	11.5	11.5	11.5	11.5	12.5	11.5	12.5
90°	20.8	21.1	21.8	22.4	23.1	23.7	23.1	22.4	21.8	21.1	20.8
92.5°	20.8	20.9	21.1	21.3	21.5	21.7	21.5	21.3	21.1	20.9	20.8
95°	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8	20.8
97.5°	19.8	19.9	20.1	20.4	20.6	20.8	20.6	20.4	20.1	19.9	19.8
100°	24.7	24.3	23.4	22.5	21.7	20.8	21.7	22.5	23.4	24.3	24.7
102.5°	233.3	224.1	205.6	187.1	168.7	150.2	168.7	187.1	205.6	224.1	233.3
105°	294.6	294.5	294.3	294.0	293.8	293.6	293.8	294.0	294.3	294.5	294.6
107.5°	360.8	360.4	359.5	358.6	357.7	356.8	357.7	358.6	359.5	360.4	360.8
110°	422.1	422.2	422.4	422.7	422.9	423.1	422.9	422.7	422.4	422.2	422.1

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	484.3	484.1	483.7	483.2	482.8	482.4	482.8	483.2	483.7	484.1	484.3
115°	547.6	546.9	545.6	544.3	543.0	541.7	543.0	544.3	545.6	546.9	547.6
117.5°	607.9	607.7	607.2	606.8	606.3	605.9	606.3	606.8	607.2	607.7	607.9
120°	669.2	668.6	667.5	666.4	665.3	664.2	665.3	666.4	667.5	668.6	669.2
122.5°	725.5	724.8	723.5	722.2	720.9	719.6	720.9	722.2	723.5	724.8	725.5
125°	778.9	778.6	777.9	777.2	776.6	775.9	776.6	777.2	777.9	778.6	778.9
127.5°	830.3	829.4	827.7	825.9	824.2	822.4	824.2	825.9	827.7	829.4	830.3
130°	878.7	878.2	877.1	876.0	874.9	873.8	874.9	876.0	877.1	878.2	878.7
132.5°	926.2	925.6	924.5	923.4	922.3	921.2	922.3	923.4	924.5	925.6	926.2
135°	969.7	969.0	967.7	966.4	965.0	963.7	965.0	966.4	967.7	969.0	969.7
137.5°	1013.2	1012.6	1011.5	1010.4	1009.3	1008.2	1009.3	1010.4	1011.5	1012.6	1013.2
140°	1052.7	1052.0	1050.7	1049.4	1048.1	1046.8	1048.1	1049.4	1050.7	1052.0	1052.7
142.5°	1089.3	1088.6	1087.3	1086.0	1084.7	1083.4	1084.7	1086.0	1087.3	1088.6	1089.3
145°	1124.9	1124.2	1122.9	1121.6	1120.2	1118.9	1120.2	1121.6	1122.9	1124.2	1124.9
147.5°	1155.5	1154.7	1153.2	1151.7	1150.1	1148.6	1150.1	1151.7	1153.2	1154.7	1155.5
150°	1185.2	1184.3	1182.6	1180.8	1179.1	1177.3	1179.1	1180.8	1182.6	1184.3	1185.2
152.5°	1210.9	1210.1	1208.6	1207.0	1205.5	1203.9	1205.5	1207.0	1208.6	1210.1	1210.9
155°	1234.6	1233.7	1232.0	1230.2	1228.5	1226.7	1228.5	1230.2	1232.0	1233.7	1234.6
157.5°	1254.4	1253.5	1251.7	1250.0	1248.2	1246.4	1248.2	1250.0	1251.7	1253.5	1254.4
160°	1273.1	1272.2	1270.5	1268.7	1267.0	1265.2	1267.0	1268.7	1270.5	1272.2	1273.1
162.5°	1290.9	1289.9	1287.9	1286.0	1284.0	1282.0	1284.0	1286.0	1287.9	1289.9	1290.9
165°	1304.8	1303.9	1302.2	1300.4	1298.7	1296.9	1298.7	1300.4	1302.2	1303.9	1304.8
167.5°	1316.6	1315.6	1313.6	1311.7	1309.7	1307.7	1309.7	1311.7	1313.6	1315.6	1316.6
170°	1325.5	1324.5	1322.5	1320.6	1318.6	1316.6	1318.6	1320.6	1322.5	1324.5	1325.5
172.5°	1331.5	1330.5	1328.5	1326.6	1324.6	1322.6	1324.6	1326.6	1328.5	1330.5	1331.5
175°	1336.4	1335.4	1333.4	1331.5	1329.5	1327.5	1329.5	1331.5	1333.4	1335.4	1336.4
177.5°	1338.4	1337.5	1335.8	1334.0	1332.3	1330.5	1332.3	1334.0	1335.8	1337.5	1338.4
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8	1271.8
2.5°	1202.9	1208.1	1203.9	1200.8	1209.2	1213.3	1213.3	1220.6	1228.0	1234.2	1235.3
5°	1128.8	1137.1	1139.2	1138.2	1150.7	1157.0	1170.5	1177.8	1188.3	1195.6	1203.9
7.5°	1060.9	1072.4	1073.4	1075.5	1094.3	1104.7	1116.2	1135.0	1149.6	1160.1	1169.5
10°	993.0	1000.3	1007.6	1017.0	1035.8	1053.6	1070.3	1090.1	1108.9	1119.4	1132.9
12.5°	941.9	947.1	955.4	961.7	981.5	997.2	1019.1	1046.3	1073.4	1081.8	1098.5
15°	888.6	891.7	908.4	914.7	931.4	957.5	971.1	997.2	1026.4	1042.1	1060.9
17.5°	827.0	845.8	856.2	863.5	884.4	905.3	927.2	954.4	992.0	1006.6	1020.2
20°	783.1	796.7	808.2	817.6	836.4	867.7	887.6	909.5	945.0	961.7	981.5
22.5°	744.5	756.0	766.4	776.9	789.4	817.6	840.6	870.8	906.3	922.0	945.0
25°	708.0	719.4	725.7	738.2	754.9	774.8	801.9	829.1	864.6	882.3	904.3
27.5°	672.5	683.9	695.4	705.9	717.4	736.1	754.9	789.4	825.9	846.8	865.6
30°	642.2	647.4	657.8	669.3	680.8	698.6	720.5	744.5	786.3	805.1	828.0
32.5°	608.8	618.2	625.5	633.8	648.4	663.1	682.9	713.2	746.6	764.3	789.4
35°	577.4	585.8	591.0	605.6	615.0	630.7	650.5	677.7	705.9	725.7	747.6
37.5°	547.2	555.5	561.8	570.1	582.7	596.2	617.1	636.9	670.4	687.1	712.1
40°	515.8	523.1	530.4	539.8	551.3	568.0	580.6	605.6	632.8	651.6	670.4
42.5°	485.5	489.7	498.1	508.5	520.0	534.6	552.4	572.2	599.4	616.1	632.8
45°	453.2	460.5	469.9	477.2	487.6	502.3	517.9	535.7	562.8	579.5	597.3
47.5°	422.9	428.1	434.4	445.9	459.4	469.9	486.6	503.3	528.4	544.0	560.7
50°	391.6	396.8	406.2	413.5	423.9	437.5	453.2	470.9	494.9	505.4	522.1
52.5°	362.3	364.4	373.8	381.1	391.6	407.2	419.8	435.4	458.4	469.9	486.6
55°	333.1	335.2	340.4	347.7	359.2	371.7	385.3	403.1	422.9	433.3	449.0
57.5°	302.8	304.9	310.1	315.3	326.8	338.3	354.0	368.6	388.4	397.8	412.5
60°	272.5	272.5	277.8	285.1	293.4	303.9	317.4	335.2	349.8	361.3	371.7
62.5°	240.2	243.3	246.4	251.6	261.0	273.6	285.1	297.6	315.3	323.7	333.1
65°	207.8	210.9	217.2	222.4	229.7	238.1	252.7	263.1	276.7	286.1	294.5
67.5°	179.6	182.7	186.9	193.2	198.4	207.8	218.2	228.7	243.3	249.6	255.8
70°	150.4	153.5	156.6	165.0	170.2	177.5	184.8	195.3	207.8	212.0	217.2
72.5°	127.4	128.4	132.6	134.7	142.0	148.3	156.6	162.9	172.3	177.5	181.7
75°	107.6	107.6	108.6	110.7	114.9	119.0	125.3	131.6	139.9	143.1	148.3
77.5°	84.6	87.7	86.7	88.8	90.8	92.9	98.2	102.3	110.7	112.8	114.9
80°	60.6	61.6	64.7	67.9	67.9	71.0	74.1	75.2	80.4	83.5	83.5
82.5°	43.9	44.9	43.9	44.9	45.9	47.0	50.1	54.3	54.3	55.3	57.4
85°	27.1	27.1	28.2	29.2	29.2	28.2	30.3	29.2	30.3	32.4	32.4
87.5°	13.6	12.5	12.5	12.5	12.5	12.5	13.6	12.5	13.6	13.6	13.6
90°	20.2	19.1	18.0	16.9	15.8	14.3	12.7	11.2	9.7	8.9	8.0
92.5°	20.2	19.1	18.0	16.9	15.8	14.5	13.2	11.9	10.6	9.9	10.9
95°	20.2	19.1	18.0	16.9	15.8	24.2	32.5	40.9	49.2	53.4	53.7
97.5°	19.6	19.1	18.7	18.2	17.8	38.7	59.5	80.4	101.3	111.7	111.0
100°	41.1	73.8	106.5	139.3	172.0	171.1	170.2	169.3	168.4	168.0	167.7
102.5°	233.1	232.6	232.2	231.7	231.3	230.9	230.4	230.0	229.5	229.3	228.9
105°	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.6	294.2
107.5°	360.7	360.5	360.2	360.0	359.8	359.4	358.9	358.5	358.0	357.8	357.8
110°	422.4	423.1	423.7	424.4	425.0	424.6	424.2	423.7	423.3	423.1	423.1

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	484.7	485.6	486.5	487.4	488.3	488.1	487.9	487.6	487.4	487.3	487.0
115°	548.0	548.9	549.8	550.7	551.6	551.4	551.2	550.9	550.7	550.6	550.0
117.5°	608.6	609.9	611.2	612.5	613.8	612.9	612.1	611.2	610.3	609.9	609.9
120°	669.4	669.9	670.3	670.8	671.2	670.5	669.9	669.2	668.5	668.2	668.3
122.5°	725.7	726.2	726.6	727.1	727.5	727.3	727.1	726.8	726.6	726.5	726.0
125°	779.3	780.2	781.1	782.0	782.9	782.9	782.9	782.9	782.9	782.9	782.1
127.5°	830.5	831.0	831.4	831.9	832.3	832.5	832.7	833.0	833.2	833.3	832.7
130°	879.0	879.7	880.4	881.0	881.7	881.5	881.3	881.0	880.8	880.7	880.2
132.5°	926.2	926.2	926.2	926.2	926.2	926.9	927.5	928.2	928.9	929.2	928.5
135°	969.9	970.4	970.8	971.3	971.7	972.1	972.5	973.0	973.4	973.6	972.9
137.5°	1013.2	1013.2	1013.2	1013.2	1013.2	1013.6	1014.0	1014.5	1014.9	1015.1	1014.4
140°	1052.5	1052.0	1051.6	1051.1	1050.7	1050.9	1051.1	1051.4	1051.6	1051.7	1051.5
142.5°	1089.3	1089.3	1089.3	1089.3	1089.3	1088.9	1088.4	1088.0	1087.5	1087.3	1087.2
145°	1124.8	1124.6	1124.3	1124.1	1123.9	1123.9	1123.9	1123.9	1123.9	1123.9	1123.7
147.5°	1155.4	1155.2	1154.9	1154.7	1154.5	1154.3	1154.1	1153.8	1153.6	1153.5	1153.5
150°	1185.0	1184.5	1184.1	1183.6	1183.2	1182.8	1182.3	1181.9	1181.4	1181.2	1181.4
152.5°	1210.7	1210.2	1209.8	1209.3	1208.9	1208.5	1208.0	1207.6	1207.1	1206.9	1207.5
155°	1234.3	1233.6	1232.9	1232.3	1231.6	1231.2	1230.7	1230.3	1229.8	1229.6	1230.3
157.5°	1254.1	1253.4	1252.7	1252.1	1251.4	1251.4	1251.4	1251.4	1251.4	1251.4	1251.7
160°	1272.7	1271.8	1270.9	1270.1	1269.2	1269.0	1268.8	1268.5	1268.3	1268.2	1268.9
162.5°	1290.2	1288.9	1287.6	1286.3	1285.0	1284.8	1284.6	1284.3	1284.1	1284.0	1284.7
165°	1304.1	1302.8	1301.5	1300.1	1298.8	1298.6	1298.4	1298.1	1297.9	1297.8	1298.5
167.5°	1315.8	1314.3	1312.8	1311.2	1309.7	1309.5	1309.3	1309.0	1308.8	1308.7	1309.4
170°	1324.6	1322.9	1321.1	1319.4	1317.6	1317.4	1317.2	1316.9	1316.7	1316.6	1317.4
172.5°	1330.7	1329.2	1327.6	1326.1	1324.5	1324.1	1323.7	1323.2	1322.8	1322.6	1323.4
175°	1335.5	1333.8	1332.0	1330.3	1328.5	1328.3	1328.1	1327.8	1327.6	1327.5	1328.2
177.5°	1337.6	1336.1	1334.6	1333.0	1331.5	1331.3	1331.1	1330.8	1330.6	1330.5	1331.2
180°	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4	1333.4

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1271.8	1271.8	1271.8	1271.8
2.5°	1242.6	1252.0	1261.4	1272.9
5°	1217.5	1234.2	1252.0	1268.7
7.5°	1190.4	1214.4	1237.4	1261.4
10°	1160.1	1190.4	1216.5	1249.9
12.5°	1126.7	1159.0	1195.6	1233.2
15°	1093.3	1134.0	1172.6	1215.4
17.5°	1061.9	1100.6	1143.4	1194.5
20°	1024.3	1067.2	1115.2	1169.5
22.5°	984.7	1031.6	1083.9	1142.3
25°	951.2	999.3	1049.4	1111.0
27.5°	914.7	964.8	1013.9	1079.7
30°	872.9	927.2	977.4	1045.2
32.5°	833.3	887.6	942.9	1006.6
35°	794.6	847.9	903.2	968.0
37.5°	758.1	806.1	860.4	918.9
40°	723.6	767.5	815.5	868.8
42.5°	679.8	730.9	775.8	814.5
45°	642.2	683.9	725.7	757.0
47.5°	598.3	640.1	675.6	700.6
50°	561.8	595.2	624.4	646.3
52.5°	517.9	549.2	573.3	590.0
55°	475.1	502.3	523.1	534.6
57.5°	436.5	454.2	469.9	480.3
60°	393.7	407.2	420.8	432.3
62.5°	347.7	362.3	369.6	382.2
65°	307.0	316.4	327.9	332.0
67.5°	267.3	272.5	279.8	288.2
70°	225.5	228.7	236.0	247.5
72.5°	189.0	192.1	197.3	201.5
75°	150.4	153.5	157.7	161.8
77.5°	118.0	119.0	121.1	125.3
80°	85.6	88.8	90.8	91.9
82.5°	59.5	60.6	60.6	61.6
85°	37.6	35.5	35.5	36.5
87.5°	13.6	15.7	15.7	17.8
90°	6.3	4.5	2.8	1.0
92.5°	12.9	14.8	16.8	18.8
95°	54.4	55.0	55.7	56.3
97.5°	109.7	108.4	107.1	105.8
100°	167.0	166.4	165.7	165.1
102.5°	228.0	227.1	226.3	225.4
105°	293.3	292.4	291.5	290.6
107.5°	357.8	357.8	357.8	357.8
110°	423.1	423.1	423.1	423.1

TEST NUMBER: P1027255

CATALOG NUMBER: S125RDIP-B850D1090UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	486.3	485.6	485.0	484.3
115°	548.9	547.8	546.7	545.6
117.5°	609.9	609.9	609.9	609.9
120°	668.5	668.8	669.0	669.2
122.5°	724.9	723.8	722.7	721.6
125°	780.6	779.0	777.5	775.9
127.5°	831.6	830.5	829.4	828.3
130°	879.1	878.0	876.9	875.8
132.5°	927.2	925.9	924.5	923.2
135°	971.6	970.3	969.0	967.7
137.5°	1013.1	1011.8	1010.5	1009.2
140°	1051.0	1050.6	1050.1	1049.7
142.5°	1087.0	1086.7	1086.5	1086.3
145°	1123.2	1122.8	1122.3	1121.9
147.5°	1153.5	1153.5	1153.5	1153.5
150°	1181.9	1182.3	1182.8	1183.2
152.5°	1208.6	1209.7	1210.8	1211.9
155°	1231.6	1232.9	1234.3	1235.6
157.5°	1252.4	1253.1	1253.7	1254.4
160°	1270.2	1271.5	1272.8	1274.1
162.5°	1286.0	1287.3	1288.6	1289.9
165°	1299.8	1301.1	1302.5	1303.8
167.5°	1310.7	1312.0	1313.4	1314.7
170°	1318.9	1320.4	1322.0	1323.5
172.5°	1324.9	1326.4	1328.0	1329.5
175°	1329.5	1330.8	1332.1	1333.4
177.5°	1332.5	1333.8	1335.1	1336.4
180°	1333.4	1333.4	1333.4	1333.4

(END OF REPORT)