

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027277

Luminaire Tested: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027277
REPORT IS A COMBINATION OF REPORTS P1005808 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4742.0 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 45.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	74	74	74			69
1	103	98	95	91	97	93	90	87	83	81	79	74	73	71	66	65	63			59
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54			51
3	86	77	69	64	81	73	66	61	66	60	56	59	55	51	53	49	47			44
4	79	68	60	54	74	65	58	52	59	53	48	53	48	44	47	44	41			38
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	43	39	36			33
6	67	55	47	41	63	52	45	40	48	42	37	43	38	34	39	35	32			29
7	62	50	42	36	59	48	40	35	43	37	33	39	34	30	36	31	28			26
8	58	45	38	32	55	43	36	31	40	34	29	36	31	27	33	29	25			23
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	30	26	23			21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	22	28	24	21			19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8102	8102	8102	8102
5°	8095	9131	8095	7018
10°	8049	10261	8022	6067
15°	7962	10856	7907	5282
20°	7856	11718	7787	4775
25°	7719	13264	7632	4333
30°	7579	14099	7465	4018
35°	7398	11595	7294	3723
40°	7075	7874	7016	3459
45°	6654	5660	6644	3199
50°	6220	4353	6250	2958
55°	5732	3539	5722	2726
60°	5279	2901	5253	2421
65°	4750	2418	4780	1948
70°	4312	1940	4295	1623
75°	3643	1469	3643	1333
80°	2954	896	2918	896
85°	2075	472	2018	533

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 11532 cd/sqm

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.6
10°-20°	355.5	7.5
20°-30°	563.7	11.9
30°-40°	681.1	14.4
40°-50°	606.4	12.8
50°-60°	465.0	9.8
60°-70°	302.0	6.4
70°-80°	146.6	3.1
80°-90°	35.2	0.7
90°-100°	16.2	0.3
100°-110°	107.7	2.3
110°-120°	193.9	4.1
120°-130°	248.8	5.2
130°-140°	267.6	5.6
140°-150°	251.2	5.3
150°-160°	203.2	4.3
160°-170°	131.4	2.8
170°-180°	45.3	1.0
0°-30°	1040.4	21.9
0°-40°	1721.5	36.3
0°-60°	2793.0	58.9
0°-90°	3276.7	69.1
90°-120°	317.7	6.7
90°-150°	1085.4	22.9
90°-180°	1465.0	30.9
0°-180°	4742.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1264	1264	1264	1264	1264	
5°	1261	1449	1261	1114	1261	120
15°	1208	1741	1200	847	1208	341
25°	1105	2085	1092	681	1105	509
35°	962	1730	949	555	962	599
45°	753	773	752	437	753	581
55°	532	425	530	327	532	476
65°	330	241	332	194	330	330
75°	161	112	161	102	161	173
85°	36	24	35	27	36	41
90°	0	8	0	8	0	3
95°	20	7	20	7	20	25
105°	104	105	104	105	104	110
115°	195	194	195	194	195	194
125°	278	278	278	278	278	248
135°	346	345	346	345	346	267
145°	401	400	401	400	401	251
155°	442	439	442	439	442	204
165°	466	464	466	464	466	132
175°	477	475	477	475	477	45
180°	477	477	477	477	477	

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1265.5	1275.9	1279.0	1287.3	1296.7	1298.7	1303.9	1311.2	1315.3	1314.3	1314.3
5°	1261.4	1279.0	1291.5	1306.0	1323.7	1330.9	1337.1	1352.7	1365.2	1372.4	1384.9
7.5°	1254.1	1280.0	1300.8	1322.6	1349.6	1362.1	1375.6	1397.4	1420.2	1434.7	1448.2
10°	1242.7	1275.9	1305.0	1337.1	1373.5	1392.2	1408.8	1442.0	1470.0	1488.7	1519.9
12.5°	1226.1	1267.6	1308.1	1350.6	1396.3	1416.0	1438.9	1475.2	1514.7	1541.7	1567.6
15°	1208.4	1258.2	1301.9	1352.7	1407.7	1437.8	1466.9	1505.3	1540.6	1570.7	1600.8
17.5°	1187.7	1240.6	1294.6	1352.7	1415.0	1445.1	1470.0	1515.7	1553.1	1583.2	1610.2
20°	1162.7	1221.9	1283.2	1347.5	1410.9	1438.9	1462.8	1512.6	1545.8	1578.0	1616.4
22.5°	1135.7	1200.1	1265.5	1328.8	1391.1	1421.2	1449.3	1492.9	1529.2	1572.8	1622.6
25°	1104.6	1175.2	1241.6	1305.0	1364.1	1392.2	1417.1	1464.8	1515.7	1570.7	1626.8
27.5°	1073.5	1142.0	1206.3	1264.5	1328.8	1354.8	1379.7	1439.9	1500.1	1558.3	1635.1
30°	1039.2	1108.8	1164.8	1218.8	1281.1	1308.1	1339.2	1407.7	1476.3	1555.2	1648.6
32.5°	1000.8	1064.1	1116.0	1172.1	1228.1	1261.4	1300.8	1375.6	1454.5	1548.9	1668.3
35°	962.4	1013.2	1061.0	1113.9	1181.4	1216.7	1255.1	1334.0	1432.7	1545.8	1684.9
37.5°	913.6	962.4	999.7	1053.7	1123.3	1164.8	1203.2	1294.6	1406.7	1538.6	1683.9
40°	863.7	905.3	940.6	996.6	1072.4	1110.8	1152.4	1252.0	1379.7	1517.8	1659.0
42.5°	809.8	845.1	883.5	937.5	1011.2	1048.5	1096.3	1212.6	1342.3	1488.7	1594.6
45°	752.7	786.9	819.1	875.2	948.9	989.4	1041.3	1160.7	1296.7	1427.5	1490.8
47.5°	696.6	726.7	761.0	809.8	884.5	929.2	982.1	1109.8	1235.4	1345.5	1350.6
50°	642.6	666.5	695.6	745.4	823.3	865.8	920.8	1040.2	1162.7	1238.5	1187.7
52.5°	586.6	608.4	638.5	682.1	754.7	804.6	852.3	971.7	1074.5	1125.4	1031.9
55°	531.5	550.2	581.4	630.2	693.5	731.9	780.7	891.8	982.1	983.1	881.4
57.5°	477.6	494.2	520.1	563.7	622.9	667.5	712.2	808.7	870.0	852.3	739.2
60°	429.8	440.2	464.1	506.6	561.6	593.8	641.6	722.6	763.0	730.9	609.4
62.5°	380.0	390.3	409.0	443.3	495.2	529.5	559.6	626.0	654.0	605.2	505.6
65°	330.1	342.6	356.1	383.1	431.9	454.7	481.7	530.5	557.5	500.4	414.2
67.5°	286.5	292.8	306.3	334.3	368.5	389.3	408.0	441.2	446.4	400.7	330.1
70°	246.0	248.1	260.6	277.2	303.1	315.6	331.2	350.9	350.9	313.5	257.5
72.5°	200.4	203.5	212.8	230.5	246.0	252.3	257.5	269.9	267.8	233.6	195.2
75°	160.9	163.0	170.3	178.6	184.8	196.2	200.4	198.3	197.3	168.2	146.4
77.5°	124.6	125.6	130.8	138.1	139.1	143.3	140.2	140.2	130.8	114.2	102.8
80°	91.4	92.4	94.5	96.5	96.5	96.5	96.5	91.4	85.1	74.7	71.6
82.5°	61.3	61.3	62.3	64.4	63.3	61.3	59.2	54.0	49.8	46.7	44.6
85°	36.3	36.3	37.4	36.3	32.2	31.1	29.1	28.0	27.0	26.0	26.0
87.5°	17.6	16.6	14.5	12.5	12.5	12.5	12.5	12.5	12.5	11.4	11.4
90°	0.4	1.0	1.6	2.3	2.9	3.2	3.5	4.0	4.6	5.1	5.7
92.5°	6.7	6.0	5.3	4.6	3.9	3.5	3.7	4.2	4.7	5.2	5.7
95°	20.2	20.0	19.7	19.5	19.2	19.1	17.6	14.6	11.7	8.7	5.7
97.5°	37.8	38.3	38.8	39.3	39.8	40.0	36.3	28.8	21.3	13.9	6.4
100°	59.1	59.3	59.5	59.8	60.0	60.1	60.3	60.6	60.9	61.2	61.5
102.5°	80.6	80.9	81.2	81.5	81.8	82.0	82.1	82.2	82.4	82.5	82.7
105°	104.0	104.3	104.6	104.9	105.2	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.0	128.0	128.0	128.0	128.0	128.0	128.1	128.2	128.4	128.5	128.7
110°	151.3	151.3	151.3	151.3	151.3	151.3	151.4	151.6	151.7	151.9	152.1

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	173.3	173.5	173.7	174.0	174.2	174.3	174.3	174.4	174.5	174.6	174.7
115°	195.2	195.6	196.0	196.4	196.8	197.0	197.0	197.1	197.2	197.2	197.3
117.5°	218.2	218.2	218.2	218.2	218.2	218.2	218.4	218.7	219.0	219.3	219.6
120°	239.4	239.3	239.2	239.1	239.0	239.0	239.1	239.4	239.6	239.9	240.1
122.5°	258.1	258.5	258.9	259.3	259.7	259.9	259.9	260.0	260.1	260.2	260.3
125°	277.6	278.2	278.7	279.3	279.8	280.1	280.1	280.1	280.1	280.1	280.1
127.5°	296.3	296.7	297.1	297.5	297.9	298.1	298.1	298.0	297.9	297.8	297.7
130°	313.3	313.7	314.1	314.5	314.9	315.1	315.1	315.2	315.3	315.3	315.4
132.5°	330.3	330.8	331.2	331.7	332.2	332.4	332.3	332.0	331.8	331.5	331.3
135°	346.2	346.7	347.1	347.6	348.1	348.3	348.2	348.1	347.9	347.8	347.6
137.5°	361.0	361.5	362.0	362.5	363.0	363.2	363.1	362.9	362.8	362.6	362.4
140°	375.5	375.7	375.8	376.0	376.1	376.2	376.2	376.1	376.0	376.0	375.9
142.5°	388.6	388.7	388.8	388.9	389.0	389.0	389.1	389.2	389.4	389.5	389.7
145°	401.3	401.5	401.7	401.8	402.0	402.1	402.1	402.1	402.1	402.1	402.1
147.5°	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.8	412.9	412.9	413.0
150°	423.3	423.1	423.0	422.8	422.7	422.6	422.7	422.8	423.0	423.1	423.3
152.5°	433.5	433.1	432.7	432.4	432.0	431.8	431.9	432.0	432.2	432.3	432.5
155°	442.0	441.5	441.1	440.6	440.1	439.9	440.0	440.1	440.3	440.4	440.6
157.5°	448.7	448.5	448.3	448.0	447.8	447.7	447.7	447.7	447.7	447.7	447.7
160°	455.8	455.3	454.9	454.4	453.9	453.7	453.7	453.8	453.9	453.9	454.0
162.5°	461.5	461.0	460.5	460.0	459.5	459.3	459.3	459.4	459.5	459.6	459.7
165°	466.4	465.9	465.5	465.0	464.5	464.3	464.3	464.4	464.5	464.5	464.6
167.5°	470.3	469.8	469.4	468.9	468.4	468.2	468.2	468.3	468.4	468.4	468.5
170°	473.5	472.9	472.4	471.8	471.3	471.0	471.0	471.1	471.2	471.3	471.4
172.5°	475.6	475.0	474.5	473.9	473.4	473.1	473.2	473.3	473.5	473.6	473.8
175°	477.0	476.5	476.1	475.6	475.1	474.9	474.9	475.0	475.1	475.1	475.2
177.5°	478.1	477.6	477.2	476.7	476.2	476.0	476.0	476.1	476.2	476.2	476.3
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1319.5	1326.8	1333.0	1329.9	1342.3	1341.3	1343.4	1347.5	1348.6	1346.5	1342.3
5°	1391.1	1401.5	1419.2	1428.5	1426.4	1434.7	1438.9	1445.1	1451.3	1449.3	1449.3
7.5°	1471.1	1485.6	1503.3	1527.1	1530.2	1537.5	1550.0	1550.0	1557.2	1554.1	1553.1
10°	1540.6	1558.3	1586.3	1605.0	1613.3	1617.5	1629.9	1634.1	1642.4	1643.4	1643.4
12.5°	1597.7	1628.9	1647.6	1666.2	1670.4	1676.6	1686.0	1692.2	1695.3	1695.3	1692.2
15°	1627.8	1652.7	1674.5	1694.3	1705.7	1710.9	1720.2	1727.5	1731.6	1741.0	1743.1
17.5°	1640.3	1670.4	1705.7	1733.7	1753.4	1758.6	1777.3	1783.6	1791.9	1796.0	1801.2
20°	1657.9	1701.5	1744.1	1778.4	1797.1	1810.5	1830.3	1859.3	1867.6	1867.6	1864.5
22.5°	1673.5	1729.6	1787.7	1842.7	1858.3	1885.3	1921.6	1952.8	1965.2	1970.4	1966.3
25°	1692.2	1769.0	1844.8	1913.3	1955.9	1975.6	2024.4	2061.8	2076.3	2084.6	2086.7
27.5°	1724.4	1820.9	1917.5	2004.7	2048.3	2071.1	2122.0	2154.2	2171.8	2179.1	2173.9
30°	1760.7	1879.1	1991.2	2069.1	2098.1	2126.1	2159.4	2171.8	2167.7	2167.7	2183.2
32.5°	1798.1	1920.6	2020.3	2071.1	2081.5	2077.4	2063.9	2026.5	2004.7	2004.7	2018.2
35°	1818.9	1924.7	1975.6	1959.0	1918.5	1894.6	1820.9	1779.4	1732.7	1729.6	1745.1
37.5°	1807.4	1853.1	1832.3	1723.3	1668.3	1622.6	1507.4	1461.7	1427.5	1379.7	1453.4
40°	1727.5	1711.9	1604.0	1447.2	1385.9	1321.6	1230.2	1184.5	1136.8	1129.5	1147.2
42.5°	1592.5	1500.1	1342.3	1190.8	1128.5	1082.8	1013.2	968.6	938.5	926.0	946.8
45°	1424.4	1279.0	1121.2	1000.8	932.3	908.4	845.1	805.6	782.8	773.4	788.0
47.5°	1218.8	1072.4	922.9	821.2	780.7	756.8	714.3	680.0	660.3	654.0	660.3
50°	1035.0	884.5	758.9	693.5	657.2	637.4	602.1	580.3	564.8	560.6	571.0
52.5°	876.2	739.2	643.7	585.5	561.6	545.0	520.1	501.4	492.1	487.9	495.2
55°	734.0	622.9	546.1	496.2	478.6	468.2	446.4	436.0	425.6	424.6	431.9
57.5°	608.4	531.5	460.9	425.6	420.5	404.9	386.2	376.9	371.7	370.6	373.7
60°	506.6	438.1	395.5	364.4	357.1	344.7	334.3	328.1	321.8	319.8	321.8
62.5°	421.5	367.5	333.2	312.5	302.1	299.0	287.6	280.3	279.3	279.3	281.3
65°	347.8	302.1	280.3	263.7	256.4	253.3	245.0	239.8	240.9	240.9	241.9
67.5°	283.4	250.2	230.5	222.2	215.9	214.9	206.6	204.5	202.4	202.4	204.5
70°	225.3	204.5	190.0	185.8	184.8	177.5	174.4	173.4	170.3	171.3	171.3
72.5°	176.5	163.0	154.7	148.5	149.5	145.3	141.2	141.2	139.1	142.2	142.2
75°	130.8	124.6	118.4	116.3	118.4	116.3	113.2	112.1	113.2	112.1	112.1
77.5°	96.5	93.4	91.4	90.3	90.3	86.2	84.1	86.2	82.0	84.1	84.1
80°	67.5	63.3	62.3	60.2	61.3	58.1	59.2	57.1	57.1	57.1	57.1
82.5°	42.6	41.5	41.5	41.5	40.5	40.5	40.5	40.5	40.5	40.5	39.5
85°	26.0	24.9	24.9	24.9	23.9	23.9	23.9	23.9	23.9	23.9	23.9
87.5°	10.4	11.4	11.4	12.5	11.4	10.4	10.4	10.4	11.4	11.4	10.4
90°	6.1	6.5	6.8	7.2	7.4	7.5	7.8	8.0	8.3	8.5	8.3
92.5°	6.1	6.5	6.8	7.2	7.4	7.4	7.5	7.6	7.7	7.8	7.7
95°	6.1	6.5	6.8	7.2	7.4	7.4	7.4	7.4	7.4	7.4	7.4
97.5°	6.6	6.7	6.9	7.0	7.1	7.1	7.2	7.3	7.3	7.4	7.3
100°	49.8	38.1	26.4	14.7	8.8	8.6	8.3	8.0	7.7	7.4	7.7
102.5°	82.9	83.1	83.2	83.4	83.5	80.2	73.6	66.9	60.3	53.7	60.3
105°	105.4	105.4	105.4	105.4	105.4	105.4	105.3	105.2	105.1	105.0	105.1
107.5°	128.8	128.9	129.0	129.1	129.1	128.9	128.6	128.3	128.0	127.7	128.0
110°	151.9	151.6	151.4	151.1	151.0	151.0	151.1	151.2	151.2	151.3	151.2

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	174.4	174.1	173.8	173.5	173.3	173.2	173.1	172.9	172.8	172.6	172.8
115°	197.0	196.7	196.4	196.1	195.9	195.7	195.2	194.7	194.3	193.8	194.3
117.5°	219.1	218.7	218.2	217.7	217.5	217.4	217.3	217.1	217.0	216.8	217.0
120°	239.9	239.8	239.6	239.5	239.4	239.2	238.8	238.4	238.0	237.6	238.0
122.5°	260.1	259.9	259.8	259.6	259.5	259.3	258.8	258.3	257.9	257.4	257.9
125°	279.8	279.4	279.1	278.8	278.6	278.5	278.3	278.0	277.8	277.6	277.8
127.5°	297.5	297.4	297.2	297.1	297.0	296.7	296.1	295.4	294.8	294.2	294.8
130°	315.2	315.0	314.7	314.5	314.4	314.2	313.8	313.4	313.0	312.6	313.0
132.5°	331.3	331.3	331.3	331.3	331.3	331.1	330.7	330.4	330.0	329.6	330.0
135°	347.4	347.3	347.1	347.0	346.9	346.7	346.2	345.7	345.3	344.8	345.3
137.5°	362.4	362.4	362.4	362.4	362.4	362.2	361.8	361.5	361.1	360.7	361.1
140°	376.1	376.2	376.4	376.5	376.6	376.4	375.9	375.4	375.0	374.5	375.0
142.5°	389.7	389.7	389.7	389.7	389.7	389.5	389.0	388.5	388.1	387.6	388.1
145°	402.2	402.2	402.3	402.4	402.4	402.2	401.7	401.2	400.8	400.3	400.8
147.5°	413.1	413.2	413.3	413.4	413.4	413.1	412.6	412.0	411.5	410.9	411.5
150°	423.5	423.6	423.8	423.9	424.0	423.7	423.0	422.4	421.7	421.1	421.7
152.5°	432.7	432.8	433.0	433.1	433.2	432.9	432.4	431.8	431.3	430.7	431.3
155°	440.8	441.1	441.3	441.6	441.7	441.4	440.7	440.1	439.4	438.8	439.4
157.5°	447.9	448.1	448.4	448.6	448.7	448.4	447.8	447.1	446.5	445.9	446.5
160°	454.3	454.6	454.9	455.2	455.4	455.1	454.5	453.8	453.2	452.6	453.2
162.5°	460.2	460.6	461.1	461.6	461.8	461.4	460.7	460.0	459.3	458.6	459.3
165°	465.1	465.6	466.1	466.6	466.8	466.5	465.8	465.2	464.5	463.9	464.5
167.5°	469.1	469.6	470.2	470.7	471.0	470.6	469.9	469.2	468.5	467.8	468.5
170°	472.0	472.6	473.3	473.9	474.2	473.8	473.1	472.4	471.7	471.0	471.7
172.5°	474.4	474.9	475.5	476.0	476.3	475.9	475.2	474.5	473.8	473.1	473.8
175°	475.8	476.5	477.1	477.8	478.1	477.7	477.0	476.3	475.6	474.9	475.6
177.5°	476.9	477.4	478.0	478.5	478.8	478.5	477.9	477.2	476.6	476.0	476.6
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1347.5	1340.3	1343.4	1340.3	1337.1	1334.0	1326.8	1316.4	1308.1	1301.9	1300.8
5°	1451.3	1442.0	1435.8	1432.7	1426.4	1418.1	1404.6	1389.1	1370.4	1363.1	1348.6
7.5°	1546.9	1543.7	1529.2	1527.1	1523.0	1507.4	1484.6	1463.8	1439.9	1420.2	1401.5
10°	1637.2	1629.9	1619.5	1605.0	1602.9	1583.2	1561.4	1532.3	1501.2	1482.5	1449.3
12.5°	1693.2	1684.9	1673.5	1664.2	1659.0	1646.5	1616.4	1587.3	1559.3	1525.1	1496.0
15°	1733.7	1723.3	1702.6	1695.3	1689.1	1672.5	1650.7	1620.6	1583.2	1559.3	1517.8
17.5°	1788.7	1776.3	1755.5	1742.0	1730.6	1704.7	1673.5	1633.0	1597.7	1570.7	1533.4
20°	1852.1	1833.4	1806.4	1788.7	1772.1	1742.0	1698.4	1650.7	1599.8	1566.6	1528.2
22.5°	1956.9	1921.6	1879.1	1854.2	1831.3	1779.4	1727.5	1668.3	1611.2	1561.4	1514.7
25°	2058.7	2023.4	1970.4	1936.2	1900.9	1840.7	1772.1	1690.1	1617.5	1559.3	1498.1
27.5°	2153.1	2116.8	2068.0	2026.5	1992.2	1901.9	1811.6	1719.2	1626.8	1546.9	1484.6
30°	2174.9	2159.4	2122.0	2085.7	2054.5	1971.5	1866.6	1749.3	1638.2	1535.4	1465.9
32.5°	2043.1	2081.5	2090.9	2085.7	2065.9	2006.8	1910.2	1786.7	1654.8	1530.2	1434.7
35°	1769.0	1838.6	1910.2	1948.6	1967.3	1975.6	1918.5	1805.4	1666.2	1521.9	1414.0
37.5°	1466.9	1534.4	1647.6	1704.7	1768.0	1851.0	1873.9	1801.2	1661.1	1515.7	1380.8
40°	1205.3	1291.5	1384.9	1436.8	1491.8	1641.3	1754.5	1746.2	1644.4	1492.9	1354.8
42.5°	981.1	1035.0	1117.1	1174.2	1241.6	1408.8	1560.4	1635.1	1594.6	1464.8	1321.6
45°	818.1	859.6	917.7	975.9	1017.4	1169.0	1348.6	1471.1	1509.5	1415.0	1270.7
47.5°	689.3	720.5	771.4	807.7	852.3	971.7	1127.4	1299.8	1380.8	1344.4	1216.7
50°	590.7	615.6	656.1	679.0	718.4	821.2	939.5	1120.2	1242.7	1246.8	1145.1
52.5°	504.5	529.5	563.7	583.4	607.3	676.9	796.3	948.9	1090.1	1142.0	1063.1
55°	439.1	453.7	481.7	497.3	519.1	586.6	662.3	792.1	939.5	1024.7	974.8
57.5°	378.9	394.5	412.1	424.6	440.2	494.2	562.7	660.3	806.6	899.0	882.4
60°	330.1	339.5	356.1	365.4	380.0	415.3	463.0	560.6	676.9	764.1	773.4
62.5°	284.5	292.8	304.2	312.5	321.8	349.9	385.2	454.7	556.5	650.9	663.4
65°	245.0	252.3	258.5	265.8	273.0	290.7	320.8	374.8	453.7	541.9	568.9
67.5°	209.7	211.8	221.1	222.2	226.3	239.8	261.6	305.2	362.3	432.9	468.2
70°	175.4	179.6	181.7	184.8	188.9	198.3	215.9	238.8	281.3	338.4	371.7
72.5°	142.2	143.3	146.4	148.5	152.6	159.9	168.2	185.8	212.8	254.3	284.5
75°	113.2	114.2	116.3	117.3	120.4	122.5	126.7	139.1	157.8	182.7	204.5
77.5°	85.1	87.2	89.3	89.3	90.3	92.4	94.5	98.6	108.0	124.6	143.3
80°	58.1	59.2	59.2	60.2	59.2	62.3	65.4	70.6	74.7	79.9	89.3
82.5°	40.5	40.5	40.5	41.5	41.5	42.6	42.6	43.6	44.6	47.8	51.9
85°	24.9	24.9	26.0	23.9	24.9	26.0	26.0	24.9	26.0	27.0	28.0
87.5°	10.4	10.4	11.4	11.4	11.4	11.4	10.4	11.4	10.4	11.4	11.4
90°	8.0	7.8	7.5	7.4	7.2	6.8	6.5	6.1	5.7	5.1	4.6
92.5°	7.6	7.5	7.4	7.4	7.2	6.8	6.5	6.1	5.7	5.2	4.7
95°	7.4	7.4	7.4	7.4	7.2	6.8	6.5	6.1	5.7	8.7	11.7
97.5°	7.3	7.2	7.1	7.1	7.0	6.9	6.7	6.6	6.4	13.9	21.3
100°	8.0	8.3	8.6	8.8	14.7	26.4	38.1	49.8	61.5	61.2	60.9
102.5°	66.9	73.6	80.2	83.5	83.4	83.2	83.1	82.9	82.7	82.5	82.4
105°	105.2	105.3	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.3	128.6	128.9	129.1	129.1	129.0	128.9	128.8	128.7	128.5	128.4
110°	151.2	151.1	151.0	151.0	151.1	151.4	151.6	151.9	152.1	151.9	151.7

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	172.9	173.1	173.2	173.3	173.5	173.8	174.1	174.4	174.7	174.6	174.5
115°	194.7	195.2	195.7	195.9	196.1	196.4	196.7	197.0	197.3	197.2	197.2
117.5°	217.1	217.3	217.4	217.5	217.7	218.2	218.7	219.1	219.6	219.3	219.0
120°	238.4	238.8	239.2	239.4	239.5	239.6	239.8	239.9	240.1	239.9	239.6
122.5°	258.3	258.8	259.3	259.5	259.6	259.8	259.9	260.1	260.3	260.2	260.1
125°	278.0	278.3	278.5	278.6	278.8	279.1	279.4	279.8	280.1	280.1	280.1
127.5°	295.4	296.1	296.7	297.0	297.1	297.2	297.4	297.5	297.7	297.8	297.9
130°	313.4	313.8	314.2	314.4	314.5	314.7	315.0	315.2	315.4	315.3	315.3
132.5°	330.4	330.7	331.1	331.3	331.3	331.3	331.3	331.3	331.3	331.5	331.8
135°	345.7	346.2	346.7	346.9	347.0	347.1	347.3	347.4	347.6	347.8	347.9
137.5°	361.5	361.8	362.2	362.4	362.4	362.4	362.4	362.4	362.4	362.6	362.8
140°	375.4	375.9	376.4	376.6	376.5	376.4	376.2	376.1	375.9	376.0	376.0
142.5°	388.5	389.0	389.5	389.7	389.7	389.7	389.7	389.7	389.7	389.5	389.4
145°	401.2	401.7	402.2	402.4	402.4	402.3	402.2	402.2	402.1	402.1	402.1
147.5°	412.0	412.6	413.1	413.4	413.4	413.3	413.2	413.1	413.0	412.9	412.9
150°	422.4	423.0	423.7	424.0	423.9	423.8	423.6	423.5	423.3	423.1	423.0
152.5°	431.8	432.4	432.9	433.2	433.1	433.0	432.8	432.7	432.5	432.3	432.2
155°	440.1	440.7	441.4	441.7	441.6	441.3	441.1	440.8	440.6	440.4	440.3
157.5°	447.1	447.8	448.4	448.7	448.6	448.4	448.1	447.9	447.7	447.7	447.7
160°	453.8	454.5	455.1	455.4	455.2	454.9	454.6	454.3	454.0	453.9	453.9
162.5°	460.0	460.7	461.4	461.8	461.6	461.1	460.6	460.2	459.7	459.6	459.5
165°	465.2	465.8	466.5	466.8	466.6	466.1	465.6	465.1	464.6	464.5	464.5
167.5°	469.2	469.9	470.6	471.0	470.7	470.2	469.6	469.1	468.5	468.4	468.4
170°	472.4	473.1	473.8	474.2	473.9	473.3	472.6	472.0	471.4	471.3	471.2
172.5°	474.5	475.2	475.9	476.3	476.0	475.5	474.9	474.4	473.8	473.6	473.5
175°	476.3	477.0	477.7	478.1	477.8	477.1	476.5	475.8	475.2	475.1	475.1
177.5°	477.2	477.9	478.5	478.8	478.5	478.0	477.4	476.9	476.3	476.2	476.2
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1297.7	1291.5	1287.3	1286.3	1280.0	1274.9	1268.6	1267.6	1264.5	1256.2	1251.0
5°	1338.2	1323.7	1320.5	1311.2	1295.6	1284.2	1269.7	1261.4	1252.0	1236.4	1224.0
7.5°	1379.7	1360.0	1345.5	1332.0	1310.2	1289.4	1268.6	1252.0	1235.4	1212.6	1193.9
10°	1420.2	1390.1	1372.4	1352.7	1322.6	1291.5	1262.4	1238.5	1211.5	1184.5	1157.5
12.5°	1457.6	1419.2	1393.2	1365.2	1327.8	1289.4	1252.0	1218.8	1190.8	1154.4	1124.3
15°	1480.4	1437.8	1411.9	1384.9	1328.8	1286.3	1242.7	1200.1	1162.7	1124.3	1096.3
17.5°	1493.9	1446.2	1417.1	1392.2	1335.1	1276.9	1220.9	1175.2	1134.7	1089.0	1051.7
20°	1487.7	1441.0	1414.0	1390.1	1323.7	1265.5	1205.3	1152.4	1101.5	1054.8	1015.3
22.5°	1474.2	1425.4	1395.3	1373.5	1314.3	1245.8	1179.3	1122.2	1069.3	1022.6	977.9
25°	1445.1	1397.4	1371.4	1344.4	1286.3	1220.9	1153.4	1092.1	1036.1	986.3	936.4
27.5°	1419.2	1361.0	1334.0	1310.2	1248.9	1190.8	1124.3	1056.8	999.7	947.8	898.0
30°	1389.1	1323.7	1294.6	1262.4	1207.4	1152.4	1085.9	1023.6	964.4	909.4	861.7
32.5°	1356.9	1281.1	1247.9	1211.5	1155.5	1103.6	1047.5	986.3	927.1	873.1	823.3
35°	1315.3	1234.4	1196.0	1161.7	1103.6	1051.7	999.7	948.9	889.7	832.6	784.8
37.5°	1275.9	1186.6	1146.1	1106.7	1045.4	995.6	953.0	905.3	848.2	793.2	747.5
40°	1231.3	1128.5	1087.0	1050.6	987.3	932.3	893.9	856.5	806.6	753.7	703.9
42.5°	1190.8	1074.5	1030.9	993.5	927.1	875.2	838.8	807.7	764.1	715.3	664.4
45°	1134.7	1016.4	971.7	932.3	864.8	816.0	778.6	751.6	717.4	671.7	626.0
47.5°	1082.8	960.3	911.5	863.7	802.5	752.7	718.4	697.6	674.8	634.3	587.6
50°	1019.5	895.9	846.1	806.6	737.1	694.5	660.3	645.7	625.0	586.6	549.2
52.5°	951.0	833.6	786.9	739.2	674.8	633.3	603.2	586.6	569.9	541.9	506.6
55°	871.0	764.1	720.5	677.9	613.6	575.1	548.1	530.5	521.2	495.2	469.2
57.5°	794.2	693.5	653.0	613.6	557.5	513.9	496.2	480.7	467.2	448.5	426.7
60°	716.3	625.0	581.4	546.1	497.3	457.8	443.3	427.7	417.3	402.8	387.2
62.5°	627.0	549.2	516.0	482.7	441.2	410.1	393.5	381.0	367.5	358.2	344.7
65°	532.6	477.6	445.4	420.5	381.0	353.0	340.5	332.2	320.8	311.4	301.1
67.5°	444.3	400.7	387.2	360.2	330.1	305.2	295.9	285.5	276.2	271.0	261.6
70°	359.2	328.1	314.6	307.3	274.1	257.5	249.2	245.0	233.6	228.4	222.2
72.5°	278.2	266.8	257.5	248.1	226.3	215.9	206.6	202.4	194.1	190.0	187.9
75°	205.6	198.3	193.1	192.1	182.7	172.3	163.0	160.9	154.7	150.5	148.5
77.5°	144.3	142.2	141.2	142.2	136.0	129.8	127.7	125.6	118.4	117.3	117.3
80°	94.5	99.7	99.7	98.6	96.5	95.5	92.4	90.3	86.2	85.1	86.2
82.5°	58.1	61.3	62.3	64.4	63.3	62.3	60.2	59.2	60.2	58.1	59.2
85°	29.1	31.1	35.3	35.3	36.3	36.3	36.3	35.3	33.2	34.3	33.2
87.5°	11.4	12.5	12.5	12.5	11.4	14.5	15.6	15.6	15.6	13.5	13.5
90°	4.0	3.5	3.2	2.9	2.3	1.6	1.0	0.4	1.0	1.6	2.3
92.5°	4.2	3.7	3.5	3.9	4.6	5.3	6.0	6.7	6.0	5.3	4.6
95°	14.6	17.6	19.1	19.2	19.5	19.7	20.0	20.2	20.0	19.7	19.5
97.5°	28.8	36.3	40.0	39.8	39.3	38.8	38.3	37.8	38.3	38.8	39.3
100°	60.6	60.3	60.1	60.0	59.8	59.5	59.3	59.1	59.3	59.5	59.8
102.5°	82.2	82.1	82.0	81.8	81.5	81.2	80.9	80.6	80.9	81.2	81.5
105°	105.4	105.4	105.4	105.2	104.9	104.6	104.3	104.0	104.3	104.6	104.9
107.5°	128.2	128.1	128.0	128.0	128.0	128.0	128.0	128.0	128.0	128.0	128.0
110°	151.6	151.4	151.3	151.3	151.3	151.3	151.3	151.3	151.3	151.3	151.3

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	174.4	174.3	174.3	174.2	174.0	173.7	173.5	173.3	173.5	173.7	174.0
115°	197.1	197.0	197.0	196.8	196.4	196.0	195.6	195.2	195.6	196.0	196.4
117.5°	218.7	218.4	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2	218.2
120°	239.4	239.1	239.0	239.0	239.1	239.2	239.3	239.4	239.3	239.2	239.1
122.5°	260.0	259.9	259.9	259.7	259.3	258.9	258.5	258.1	258.5	258.9	259.3
125°	280.1	280.1	280.1	279.8	279.3	278.7	278.2	277.6	278.2	278.7	279.3
127.5°	298.0	298.1	298.1	297.9	297.5	297.1	296.7	296.3	296.7	297.1	297.5
130°	315.2	315.1	315.1	314.9	314.5	314.1	313.7	313.3	313.7	314.1	314.5
132.5°	332.0	332.3	332.4	332.2	331.7	331.2	330.8	330.3	330.8	331.2	331.7
135°	348.1	348.2	348.3	348.1	347.6	347.1	346.7	346.2	346.7	347.1	347.6
137.5°	362.9	363.1	363.2	363.0	362.5	362.0	361.5	361.0	361.5	362.0	362.5
140°	376.1	376.2	376.2	376.1	376.0	375.8	375.7	375.5	375.7	375.8	376.0
142.5°	389.2	389.1	389.0	389.0	388.9	388.8	388.7	388.6	388.7	388.8	388.9
145°	402.1	402.1	402.1	402.0	401.8	401.7	401.5	401.3	401.5	401.7	401.8
147.5°	412.8	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7	412.7
150°	422.8	422.7	422.6	422.7	422.8	423.0	423.1	423.3	423.1	423.0	422.8
152.5°	432.0	431.9	431.8	432.0	432.4	432.7	433.1	433.5	433.1	432.7	432.4
155°	440.1	440.0	439.9	440.1	440.6	441.1	441.5	442.0	441.5	441.1	440.6
157.5°	447.7	447.7	447.7	447.8	448.0	448.3	448.5	448.7	448.5	448.3	448.0
160°	453.8	453.7	453.7	453.9	454.4	454.9	455.3	455.8	455.3	454.9	454.4
162.5°	459.4	459.3	459.3	459.5	460.0	460.5	461.0	461.5	461.0	460.5	460.0
165°	464.4	464.3	464.3	464.5	465.0	465.5	465.9	466.4	465.9	465.5	465.0
167.5°	468.3	468.2	468.2	468.4	468.9	469.4	469.8	470.3	469.8	469.4	468.9
170°	471.1	471.0	471.0	471.3	471.8	472.4	472.9	473.5	472.9	472.4	471.8
172.5°	473.3	473.2	473.1	473.4	473.9	474.5	475.0	475.6	475.0	474.5	473.9
175°	475.0	474.9	474.9	475.1	475.6	476.1	476.5	477.0	476.5	476.1	475.6
177.5°	476.1	476.0	476.0	476.2	476.7	477.2	477.6	478.1	477.6	477.2	476.7
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1247.9	1243.7	1240.6	1237.5	1224.0	1209.5	1207.4	1204.3	1198.0	1205.3	1202.2
5°	1215.7	1206.3	1201.1	1187.7	1171.0	1158.6	1148.2	1135.7	1130.6	1126.4	1125.4
7.5°	1176.2	1167.9	1158.6	1145.1	1124.3	1103.6	1088.0	1075.5	1065.2	1060.0	1060.0
10°	1137.8	1127.4	1115.0	1092.1	1072.4	1046.5	1029.9	1017.4	1002.9	994.6	987.3
12.5°	1098.4	1087.0	1075.5	1046.5	1023.6	996.6	972.8	957.2	949.9	940.6	928.1
15°	1058.9	1041.3	1029.9	1000.8	971.7	944.7	929.2	912.5	895.9	886.6	882.4
17.5°	1017.4	1004.9	986.3	955.1	922.9	899.0	876.2	860.6	840.9	831.6	822.2
20°	980.0	961.3	942.6	911.5	880.4	848.2	825.3	806.6	794.2	786.9	778.6
22.5°	935.4	917.7	902.2	868.9	834.7	804.6	779.7	768.2	755.8	744.4	736.1
25°	897.0	879.3	863.7	827.4	790.0	762.0	743.3	728.8	715.3	710.1	701.8
27.5°	856.5	839.9	819.1	782.8	749.6	725.7	705.9	692.5	682.1	671.7	665.5
30°	818.1	799.4	780.7	741.2	714.3	690.4	671.7	655.1	646.8	641.6	631.2
32.5°	780.7	756.8	741.2	704.9	679.0	656.1	640.5	626.0	615.6	606.3	598.0
35°	740.2	714.3	698.7	668.6	641.6	618.7	605.2	594.9	582.4	574.1	569.9
37.5°	701.8	680.0	664.4	633.3	606.3	587.6	573.1	559.6	554.4	543.0	540.9
40°	660.3	641.6	627.0	596.9	572.0	557.5	541.9	529.5	520.1	514.9	507.7
42.5°	622.9	607.3	591.8	563.7	539.8	522.2	510.8	499.4	491.0	482.7	477.6
45°	588.6	572.0	557.5	530.5	506.6	491.0	479.6	466.1	464.1	452.6	447.4
47.5°	552.3	537.8	525.3	497.3	475.5	459.9	446.4	437.1	427.7	423.6	416.3
50°	517.0	502.5	487.9	463.0	443.3	427.7	414.2	403.8	398.7	392.4	386.2
52.5°	478.6	467.2	455.8	429.8	410.1	396.6	385.2	371.7	366.5	361.3	357.1
55°	446.4	429.8	417.3	395.5	377.9	363.4	350.9	340.5	335.3	331.2	326.0
57.5°	402.8	392.4	382.0	362.3	345.7	331.2	318.7	310.4	304.2	301.1	302.1
60°	365.4	354.0	347.8	327.0	310.4	299.0	287.6	279.3	273.0	269.9	268.9
62.5°	326.0	317.7	306.3	291.7	275.1	264.7	256.4	250.2	239.8	238.8	235.7
65°	287.6	281.3	271.0	257.5	244.0	234.6	225.3	217.0	212.8	207.6	204.5
67.5°	250.2	244.0	234.6	223.2	213.9	204.5	196.2	187.9	180.6	176.5	174.4
70°	213.9	208.7	202.4	188.9	177.5	170.3	164.0	158.8	151.6	149.5	148.5
72.5°	178.6	173.4	170.3	158.8	148.5	142.2	136.0	130.8	127.7	126.7	123.5
75°	146.4	141.2	137.0	126.7	120.4	116.3	110.0	108.0	104.9	103.8	102.8
77.5°	114.2	109.0	108.0	100.7	93.4	91.4	89.3	85.1	85.1	85.1	83.1
80°	82.0	81.0	79.9	72.7	69.6	67.5	66.4	63.3	61.3	59.2	58.1
82.5°	55.0	54.0	52.9	49.8	46.7	45.7	44.6	42.6	42.6	43.6	41.5
85°	33.2	31.1	30.1	29.1	27.0	27.0	28.0	27.0	27.0	27.0	26.0
87.5°	12.5	12.5	12.5	12.5	13.5	11.4	12.5	12.5	11.4	11.4	10.4
90°	2.9	3.2	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.8	7.2
92.5°	3.9	3.5	3.7	4.2	4.7	5.2	5.7	6.1	6.5	6.8	7.2
95°	19.2	19.1	17.6	14.6	11.7	8.7	5.7	6.1	6.5	6.8	7.2
97.5°	39.8	40.0	36.3	28.8	21.3	13.9	6.4	6.6	6.7	6.9	7.0
100°	60.0	60.1	60.3	60.6	60.9	61.2	61.5	49.8	38.1	26.4	14.7
102.5°	81.8	82.0	82.1	82.2	82.4	82.5	82.7	82.9	83.1	83.2	83.4
105°	105.2	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
107.5°	128.0	128.0	128.1	128.2	128.4	128.5	128.7	128.8	128.9	129.0	129.1
110°	151.3	151.3	151.4	151.6	151.7	151.9	152.1	151.9	151.6	151.4	151.1

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	174.2	174.3	174.3	174.4	174.5	174.6	174.7	174.4	174.1	173.8	173.5
115°	196.8	197.0	197.0	197.1	197.2	197.2	197.3	197.0	196.7	196.4	196.1
117.5°	218.2	218.2	218.4	218.7	219.0	219.3	219.6	219.1	218.7	218.2	217.7
120°	239.0	239.0	239.1	239.4	239.6	239.9	240.1	239.9	239.8	239.6	239.5
122.5°	259.7	259.9	259.9	260.0	260.1	260.2	260.3	260.1	259.9	259.8	259.6
125°	279.8	280.1	280.1	280.1	280.1	280.1	280.1	279.8	279.4	279.1	278.8
127.5°	297.9	298.1	298.1	298.0	297.9	297.8	297.7	297.5	297.4	297.2	297.1
130°	314.9	315.1	315.1	315.2	315.3	315.3	315.4	315.2	315.0	314.7	314.5
132.5°	332.2	332.4	332.3	332.0	331.8	331.5	331.3	331.3	331.3	331.3	331.3
135°	348.1	348.3	348.2	348.1	347.9	347.8	347.6	347.4	347.3	347.1	347.0
137.5°	363.0	363.2	363.1	362.9	362.8	362.6	362.4	362.4	362.4	362.4	362.4
140°	376.1	376.2	376.2	376.1	376.0	376.0	375.9	376.1	376.2	376.4	376.5
142.5°	389.0	389.0	389.1	389.2	389.4	389.5	389.7	389.7	389.7	389.7	389.7
145°	402.0	402.1	402.1	402.1	402.1	402.1	402.1	402.2	402.2	402.3	402.4
147.5°	412.7	412.7	412.7	412.8	412.9	412.9	413.0	413.1	413.2	413.3	413.4
150°	422.7	422.6	422.7	422.8	423.0	423.1	423.3	423.5	423.6	423.8	423.9
152.5°	432.0	431.8	431.9	432.0	432.2	432.3	432.5	432.7	432.8	433.0	433.1
155°	440.1	439.9	440.0	440.1	440.3	440.4	440.6	440.8	441.1	441.3	441.6
157.5°	447.8	447.7	447.7	447.7	447.7	447.7	447.7	447.9	448.1	448.4	448.6
160°	453.9	453.7	453.7	453.8	453.9	453.9	454.0	454.3	454.6	454.9	455.2
162.5°	459.5	459.3	459.3	459.4	459.5	459.6	459.7	460.2	460.6	461.1	461.6
165°	464.5	464.3	464.3	464.4	464.5	464.5	464.6	465.1	465.6	466.1	466.6
167.5°	468.4	468.2	468.2	468.3	468.4	468.4	468.5	469.1	469.6	470.2	470.7
170°	471.3	471.0	471.0	471.1	471.2	471.3	471.4	472.0	472.6	473.3	473.9
172.5°	473.4	473.1	473.2	473.3	473.5	473.6	473.8	474.4	474.9	475.5	476.0
175°	475.1	474.9	474.9	475.0	475.1	475.1	475.2	475.8	476.5	477.1	477.8
177.5°	476.2	476.0	476.0	476.1	476.2	476.2	476.3	476.9	477.4	478.0	478.5
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1197.0	1199.1	1193.9	1191.8	1187.7	1192.8	1193.9	1192.8	1202.2	1198.0	1200.1
5°	1127.4	1123.3	1120.2	1112.9	1112.9	1113.9	1117.1	1111.9	1115.0	1122.2	1121.2
7.5°	1050.6	1048.5	1049.6	1041.3	1035.0	1037.1	1035.0	1044.4	1049.6	1047.5	1051.7
10°	981.1	985.2	975.9	971.7	967.6	971.7	970.7	972.8	979.0	983.1	990.4
12.5°	925.0	924.0	918.8	914.6	907.4	909.4	915.7	913.6	914.6	924.0	922.9
15°	872.1	865.8	861.7	852.3	854.4	847.1	853.4	860.6	863.7	872.1	877.2
17.5°	819.1	818.1	812.9	811.8	800.4	797.3	803.5	805.6	808.7	812.9	820.1
20°	774.5	773.4	766.2	764.1	754.7	761.0	758.9	763.0	765.1	773.4	776.5
22.5°	734.0	728.8	726.7	723.6	720.5	719.4	723.6	722.6	729.8	732.9	734.0
25°	696.6	692.5	691.4	686.2	684.1	681.0	684.1	687.3	695.6	698.7	702.8
27.5°	662.3	659.2	657.2	653.0	649.9	649.9	652.0	656.1	659.2	661.3	663.4
30°	631.2	629.1	622.9	620.8	617.7	617.7	617.7	619.8	625.0	631.2	634.3
32.5°	599.0	594.9	590.7	590.7	587.6	587.6	588.6	590.7	595.9	596.9	602.1
35°	567.9	563.7	560.6	558.5	559.6	555.4	557.5	560.6	566.8	568.9	572.0
37.5°	537.8	536.7	530.5	527.4	529.5	529.5	528.4	530.5	534.7	538.8	540.9
40°	504.5	502.5	502.5	499.4	500.4	496.2	499.4	501.4	503.5	507.7	510.8
42.5°	475.5	473.4	469.2	470.3	467.2	467.2	469.2	470.3	473.4	478.6	480.7
45°	444.3	444.3	442.3	439.1	440.2	437.1	439.1	440.2	444.3	449.5	447.4
47.5°	414.2	413.2	413.2	409.0	411.1	408.0	411.1	412.1	414.2	417.3	416.3
50°	385.2	382.0	383.1	382.0	381.0	381.0	383.1	383.1	385.2	385.2	388.3
52.5°	355.1	355.1	353.0	354.0	356.1	354.0	357.1	354.0	356.1	357.1	359.2
55°	328.1	326.0	327.0	326.0	330.1	327.0	330.1	328.1	330.1	329.1	331.2
57.5°	299.0	295.9	296.9	295.9	299.0	298.0	301.1	298.0	299.0	300.0	303.1
60°	265.8	265.8	265.8	263.7	266.8	266.8	265.8	265.8	269.9	272.0	271.0
62.5°	234.6	233.6	230.5	229.4	230.5	228.4	232.5	231.5	233.6	235.7	237.7
65°	200.4	198.3	197.3	195.2	195.2	194.1	195.2	199.3	200.4	201.4	206.6
67.5°	172.3	171.3	170.3	167.1	167.1	169.2	169.2	169.2	175.4	172.3	176.5
70°	147.4	145.3	143.3	142.2	142.2	143.3	144.3	145.3	144.3	148.5	149.5
72.5°	123.5	124.6	122.5	122.5	122.5	121.5	121.5	123.5	124.6	123.5	124.6
75°	102.8	102.8	101.7	102.8	102.8	101.7	101.7	103.8	103.8	102.8	105.9
77.5°	83.1	82.0	79.9	77.9	78.9	77.9	78.9	77.9	81.0	84.1	82.0
80°	58.1	57.1	57.1	57.1	58.1	57.1	59.2	57.1	58.1	58.1	59.2
82.5°	41.5	42.6	42.6	41.5	42.6	41.5	42.6	42.6	42.6	41.5	42.6
85°	27.0	27.0	27.0	27.0	26.0	27.0	27.0	27.0	28.0	27.0	28.0
87.5°	11.4	11.4	11.4	11.4	11.4	11.4	11.4	11.4	12.5	11.4	12.5
90°	7.4	7.5	7.8	8.0	8.3	8.5	8.3	8.0	7.8	7.5	7.4
92.5°	7.4	7.4	7.5	7.6	7.7	7.8	7.7	7.6	7.5	7.4	7.4
95°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
97.5°	7.1	7.1	7.2	7.3	7.3	7.4	7.3	7.3	7.2	7.1	7.1
100°	8.8	8.6	8.3	8.0	7.7	7.4	7.7	8.0	8.3	8.6	8.8
102.5°	83.5	80.2	73.6	66.9	60.3	53.7	60.3	66.9	73.6	80.2	83.5
105°	105.4	105.4	105.3	105.2	105.1	105.0	105.1	105.2	105.3	105.4	105.4
107.5°	129.1	128.9	128.6	128.3	128.0	127.7	128.0	128.3	128.6	128.9	129.1
110°	151.0	151.0	151.1	151.2	151.2	151.3	151.2	151.2	151.1	151.0	151.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	173.3	173.2	173.1	172.9	172.8	172.6	172.8	172.9	173.1	173.2	173.3
115°	195.9	195.7	195.2	194.7	194.3	193.8	194.3	194.7	195.2	195.7	195.9
117.5°	217.5	217.4	217.3	217.1	217.0	216.8	217.0	217.1	217.3	217.4	217.5
120°	239.4	239.2	238.8	238.4	238.0	237.6	238.0	238.4	238.8	239.2	239.4
122.5°	259.5	259.3	258.8	258.3	257.9	257.4	257.9	258.3	258.8	259.3	259.5
125°	278.6	278.5	278.3	278.0	277.8	277.6	277.8	278.0	278.3	278.5	278.6
127.5°	297.0	296.7	296.1	295.4	294.8	294.2	294.8	295.4	296.1	296.7	297.0
130°	314.4	314.2	313.8	313.4	313.0	312.6	313.0	313.4	313.8	314.2	314.4
132.5°	331.3	331.1	330.7	330.4	330.0	329.6	330.0	330.4	330.7	331.1	331.3
135°	346.9	346.7	346.2	345.7	345.3	344.8	345.3	345.7	346.2	346.7	346.9
137.5°	362.4	362.2	361.8	361.5	361.1	360.7	361.1	361.5	361.8	362.2	362.4
140°	376.6	376.4	375.9	375.4	375.0	374.5	375.0	375.4	375.9	376.4	376.6
142.5°	389.7	389.5	389.0	388.5	388.1	387.6	388.1	388.5	389.0	389.5	389.7
145°	402.4	402.2	401.7	401.2	400.8	400.3	400.8	401.2	401.7	402.2	402.4
147.5°	413.4	413.1	412.6	412.0	411.5	410.9	411.5	412.0	412.6	413.1	413.4
150°	424.0	423.7	423.0	422.4	421.7	421.1	421.7	422.4	423.0	423.7	424.0
152.5°	433.2	432.9	432.4	431.8	431.3	430.7	431.3	431.8	432.4	432.9	433.2
155°	441.7	441.4	440.7	440.1	439.4	438.8	439.4	440.1	440.7	441.4	441.7
157.5°	448.7	448.4	447.8	447.1	446.5	445.9	446.5	447.1	447.8	448.4	448.7
160°	455.4	455.1	454.5	453.8	453.2	452.6	453.2	453.8	454.5	455.1	455.4
162.5°	461.8	461.4	460.7	460.0	459.3	458.6	459.3	460.0	460.7	461.4	461.8
165°	466.8	466.5	465.8	465.2	464.5	463.9	464.5	465.2	465.8	466.5	466.8
167.5°	471.0	470.6	469.9	469.2	468.5	467.8	468.5	469.2	469.9	470.6	471.0
170°	474.2	473.8	473.1	472.4	471.7	471.0	471.7	472.4	473.1	473.8	474.2
172.5°	476.3	475.9	475.2	474.5	473.8	473.1	473.8	474.5	475.2	475.9	476.3
175°	478.1	477.7	477.0	476.3	475.6	474.9	475.6	476.3	477.0	477.7	478.1
177.5°	478.8	478.5	477.9	477.2	476.6	476.0	476.6	477.2	477.9	478.5	478.8
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5	1264.5
2.5°	1196.0	1201.1	1197.0	1193.9	1202.2	1206.3	1206.3	1213.6	1220.9	1227.1	1228.1
5°	1122.2	1130.6	1132.6	1131.6	1144.1	1150.3	1163.8	1171.0	1181.4	1188.7	1197.0
7.5°	1054.8	1066.2	1067.2	1069.3	1088.0	1098.4	1109.8	1128.5	1143.0	1153.4	1162.7
10°	987.3	994.6	1001.8	1011.2	1029.9	1047.5	1064.1	1083.8	1102.5	1112.9	1126.4
12.5°	936.4	941.6	949.9	956.1	975.9	991.4	1013.2	1040.2	1067.2	1075.5	1092.1
15°	883.5	886.6	903.2	909.4	926.0	952.0	965.5	991.4	1020.5	1036.1	1054.8
17.5°	822.2	840.9	851.3	858.6	879.3	900.1	921.9	948.9	986.3	1000.8	1014.3
20°	778.6	792.1	803.5	812.9	831.6	862.7	882.4	904.2	939.5	956.1	975.9
22.5°	740.2	751.6	762.0	772.4	784.8	812.9	835.7	865.8	901.1	916.7	939.5
25°	703.9	715.3	721.5	734.0	750.6	770.3	797.3	824.3	859.6	877.2	899.0
27.5°	668.6	680.0	691.4	701.8	713.2	731.9	750.6	784.8	821.2	841.9	860.6
30°	638.5	643.7	654.0	665.5	676.9	694.5	716.3	740.2	781.7	800.4	823.3
32.5°	605.2	614.6	621.9	630.2	644.7	659.2	679.0	709.1	742.3	759.9	784.8
35°	574.1	582.4	587.6	602.1	611.5	627.0	646.8	673.8	701.8	721.5	743.3
37.5°	544.0	552.3	558.5	566.8	579.3	592.8	613.6	633.3	666.5	683.1	708.0
40°	512.9	520.1	527.4	536.7	548.1	564.8	577.2	602.1	629.1	647.8	666.5
42.5°	482.7	486.9	495.2	505.6	517.0	531.5	549.2	568.9	595.9	612.5	629.1
45°	450.6	457.8	467.2	474.4	484.8	499.4	514.9	532.6	559.6	576.2	593.8
47.5°	420.5	425.6	431.9	443.3	456.8	467.2	483.8	500.4	525.3	540.9	557.5
50°	389.3	394.5	403.8	411.1	421.5	435.0	450.6	468.2	492.1	502.5	519.1
52.5°	360.2	362.3	371.7	378.9	389.3	404.9	417.3	432.9	455.8	467.2	483.8
55°	331.2	333.2	338.4	345.7	357.1	369.6	383.1	400.7	420.5	430.8	446.4
57.5°	301.1	303.1	308.3	313.5	324.9	336.4	351.9	366.5	386.2	395.5	410.1
60°	271.0	271.0	276.2	283.4	291.7	302.1	315.6	333.2	347.8	359.2	369.6
62.5°	238.8	241.9	245.0	250.2	259.5	272.0	283.4	295.9	313.5	321.8	331.2
65°	206.6	209.7	215.9	221.1	228.4	236.7	251.2	261.6	275.1	284.5	292.8
67.5°	178.6	181.7	185.8	192.1	197.3	206.6	217.0	227.4	241.9	248.1	254.3
70°	149.5	152.6	155.7	164.0	169.2	176.5	183.8	194.1	206.6	210.7	215.9
72.5°	126.7	127.7	131.8	133.9	141.2	147.4	155.7	162.0	171.3	176.5	180.6
75°	106.9	106.9	108.0	110.0	114.2	118.4	124.6	130.8	139.1	142.2	147.4
77.5°	84.1	87.2	86.2	88.2	90.3	92.4	97.6	101.7	110.0	112.1	114.2
80°	60.2	61.3	64.4	67.5	67.5	70.6	73.7	74.7	79.9	83.1	83.1
82.5°	43.6	44.6	43.6	44.6	45.7	46.7	49.8	54.0	54.0	55.0	57.1
85°	27.0	27.0	28.0	29.1	29.1	28.0	30.1	29.1	30.1	32.2	32.2
87.5°	13.5	12.5	12.5	12.5	12.5	12.5	13.5	12.5	13.5	13.5	13.5
90°	7.2	6.8	6.5	6.1	5.7	5.1	4.6	4.0	3.5	3.2	2.9
92.5°	7.2	6.8	6.5	6.1	5.7	5.2	4.7	4.2	3.7	3.5	3.9
95°	7.2	6.8	6.5	6.1	5.7	8.7	11.7	14.6	17.6	19.1	19.2
97.5°	7.0	6.9	6.7	6.6	6.4	13.9	21.3	28.8	36.3	40.0	39.8
100°	14.7	26.4	38.1	49.8	61.5	61.2	60.9	60.6	60.3	60.1	60.0
102.5°	83.4	83.2	83.1	82.9	82.7	82.5	82.4	82.2	82.1	82.0	81.8
105°	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.2
107.5°	129.1	129.0	128.9	128.8	128.7	128.5	128.4	128.2	128.1	128.0	128.0
110°	151.1	151.4	151.6	151.9	152.1	151.9	151.7	151.6	151.4	151.3	151.3

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	173.5	173.8	174.1	174.4	174.7	174.6	174.5	174.4	174.3	174.3	174.2
115°	196.1	196.4	196.7	197.0	197.3	197.2	197.2	197.1	197.0	197.0	196.8
117.5°	217.7	218.2	218.7	219.1	219.6	219.3	219.0	218.7	218.4	218.2	218.2
120°	239.5	239.6	239.8	239.9	240.1	239.9	239.6	239.4	239.1	239.0	239.0
122.5°	259.6	259.8	259.9	260.1	260.3	260.2	260.1	260.0	259.9	259.9	259.7
125°	278.8	279.1	279.4	279.8	280.1	280.1	280.1	280.1	280.1	280.1	279.8
127.5°	297.1	297.2	297.4	297.5	297.7	297.8	297.9	298.0	298.1	298.1	297.9
130°	314.5	314.7	315.0	315.2	315.4	315.3	315.3	315.2	315.1	315.1	314.9
132.5°	331.3	331.3	331.3	331.3	331.3	331.5	331.8	332.0	332.3	332.4	332.2
135°	347.0	347.1	347.3	347.4	347.6	347.8	347.9	348.1	348.2	348.3	348.1
137.5°	362.4	362.4	362.4	362.4	362.4	362.6	362.8	362.9	363.1	363.2	363.0
140°	376.5	376.4	376.2	376.1	375.9	376.0	376.0	376.1	376.2	376.2	376.1
142.5°	389.7	389.7	389.7	389.7	389.7	389.5	389.4	389.2	389.1	389.0	389.0
145°	402.4	402.3	402.2	402.2	402.1	402.1	402.1	402.1	402.1	402.1	402.0
147.5°	413.4	413.3	413.2	413.1	413.0	412.9	412.9	412.8	412.7	412.7	412.7
150°	423.9	423.8	423.6	423.5	423.3	423.1	423.0	422.8	422.7	422.6	422.7
152.5°	433.1	433.0	432.8	432.7	432.5	432.3	432.2	432.0	431.9	431.8	432.0
155°	441.6	441.3	441.1	440.8	440.6	440.4	440.3	440.1	440.0	439.9	440.1
157.5°	448.6	448.4	448.1	447.9	447.7	447.7	447.7	447.7	447.7	447.7	447.8
160°	455.2	454.9	454.6	454.3	454.0	453.9	453.9	453.8	453.7	453.7	453.9
162.5°	461.6	461.1	460.6	460.2	459.7	459.6	459.5	459.4	459.3	459.3	459.5
165°	466.6	466.1	465.6	465.1	464.6	464.5	464.5	464.4	464.3	464.3	464.5
167.5°	470.7	470.2	469.6	469.1	468.5	468.4	468.4	468.3	468.2	468.2	468.4
170°	473.9	473.3	472.6	472.0	471.4	471.3	471.2	471.1	471.0	471.0	471.3
172.5°	476.0	475.5	474.9	474.4	473.8	473.6	473.5	473.3	473.2	473.1	473.4
175°	477.8	477.1	476.5	475.8	475.2	475.1	475.1	475.0	474.9	474.9	475.1
177.5°	478.5	478.0	477.4	476.9	476.3	476.2	476.2	476.1	476.0	476.0	476.2
180°	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0	477.0

TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1264.5	1264.5	1264.5	1264.5
2.5°	1235.4	1244.8	1254.1	1265.5
5°	1210.5	1227.1	1244.8	1261.4
7.5°	1183.5	1207.4	1230.2	1254.1
10°	1153.4	1183.5	1209.5	1242.7
12.5°	1120.2	1152.4	1188.7	1226.1
15°	1087.0	1127.4	1165.9	1208.4
17.5°	1055.8	1094.2	1136.8	1187.7
20°	1018.4	1061.0	1108.8	1162.7
22.5°	979.0	1025.7	1077.6	1135.7
25°	945.8	993.5	1043.3	1104.6
27.5°	909.4	959.3	1008.1	1073.5
30°	867.9	921.9	971.7	1039.2
32.5°	828.5	882.4	937.5	1000.8
35°	790.0	843.0	898.0	962.4
37.5°	753.7	801.5	855.4	913.6
40°	719.4	763.0	810.8	863.7
42.5°	675.8	726.7	771.4	809.8
45°	638.5	680.0	721.5	752.7
47.5°	594.9	636.4	671.7	696.6
50°	558.5	591.8	620.8	642.6
52.5°	514.9	546.1	569.9	586.6
55°	472.4	499.4	520.1	531.5
57.5°	434.0	451.6	467.2	477.6
60°	391.4	404.9	418.4	429.8
62.5°	345.7	360.2	367.5	380.0
65°	305.2	314.6	326.0	330.1
67.5°	265.8	271.0	278.2	286.5
70°	224.2	227.4	234.6	246.0
72.5°	187.9	191.0	196.2	200.4
75°	149.5	152.6	156.8	160.9
77.5°	117.3	118.4	120.4	124.6
80°	85.1	88.2	90.3	91.4
82.5°	59.2	60.2	60.2	61.3
85°	37.4	35.3	35.3	36.3
87.5°	13.5	15.6	15.6	17.6
90°	2.3	1.6	1.0	0.4
92.5°	4.6	5.3	6.0	6.7
95°	19.5	19.7	20.0	20.2
97.5°	39.3	38.8	38.3	37.8
100°	59.8	59.5	59.3	59.1
102.5°	81.5	81.2	80.9	80.6
105°	104.9	104.6	104.3	104.0
107.5°	128.0	128.0	128.0	128.0
110°	151.3	151.3	151.3	151.3



TEST NUMBER: P1027277

CATALOG NUMBER: S125RDIP-B850D375UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	174.0	173.7	173.5	173.3
115°	196.4	196.0	195.6	195.2
117.5°	218.2	218.2	218.2	218.2
120°	239.1	239.2	239.3	239.4
122.5°	259.3	258.9	258.5	258.1
125°	279.3	278.7	278.2	277.6
127.5°	297.5	297.1	296.7	296.3
130°	314.5	314.1	313.7	313.3
132.5°	331.7	331.2	330.8	330.3
135°	347.6	347.1	346.7	346.2
137.5°	362.5	362.0	361.5	361.0
140°	376.0	375.8	375.7	375.5
142.5°	388.9	388.8	388.7	388.6
145°	401.8	401.7	401.5	401.3
147.5°	412.7	412.7	412.7	412.7
150°	422.8	423.0	423.1	423.3
152.5°	432.4	432.7	433.1	433.5
155°	440.6	441.1	441.5	442.0
157.5°	448.0	448.3	448.5	448.7
160°	454.4	454.9	455.3	455.8
162.5°	460.0	460.5	461.0	461.5
165°	465.0	465.5	465.9	466.4
167.5°	468.9	469.4	469.8	470.3
170°	471.8	472.4	472.9	473.5
172.5°	473.9	474.5	475.0	475.6
175°	475.6	476.1	476.5	477.0
177.5°	476.7	477.2	477.6	478.1
180°	477.0	477.0	477.0	477.0

(END OF REPORT)