

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027342

Luminaire Tested: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027342
REPORT IS A COMBINATION OF REPORTS P1001272 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7831.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55						
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	52	47						
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39						
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	38	34						
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	32	29						
5	70	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25						
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22						
7	59	47	39	33	55	44	37	32	39	33	29	33	29	25	28	25	22	20						
8	55	43	35	30	51	40	33	28	35	29	25	31	26	23	26	23	20	18						
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16						
10	48	36	29	24	44	34	27	23	30	24	21	26	22	18	22	19	16	14						

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9738	9738	9738	9738
5°	9746	11048	9754	8381
10°	9686	12592	9669	7194
15°	9615	13653	9555	6500
20°	9494	14961	9407	5934
25°	9386	17143	9214	5599
30°	9231	18085	9071	5296
35°	8986	14497	8798	5051
40°	8604	10020	8477	4794
45°	8121	7460	8029	4580
50°	7568	6141	7443	4408
55°	6972	5238	6917	4259
60°	6387	4484	6275	4144
65°	5756	3872	5662	3975
70°	5089	3215	5020	3682
75°	4381	2487	4325	3197
80°	3461	1681	3335	2350
85°	2213	842	2138	1197

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14875 cd/sqm

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.3	1.9
10°-20°	435.7	5.6
20°-30°	707.8	9.0
30°-40°	865.0	11.0
40°-50°	784.6	10.0
50°-60°	624.9	8.0
60°-70°	435.3	5.6
70°-80°	231.9	3.0
80°-90°	59.4	0.8
90°-100°	342.8	4.4
100°-110°	739.3	9.4
110°-120°	689.3	8.8
120°-130°	558.3	7.1
130°-140°	448.3	5.7
140°-150°	338.1	4.3
150°-160°	238.1	3.0
160°-170°	140.3	1.8
170°-180°	45.6	0.6
0°-30°	1289.8	16.5
0°-40°	2154.8	27.5
0°-60°	3564.3	45.5
0°-90°	4290.9	54.8
90°-120°	1771.4	22.6
90°-150°	3116.1	39.8
90°-180°	3540.0	45.2
0°-180°	7831.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1520	1520	1520	1520	1520	
5°	1519	1754	1520	1330	1519	144
15°	1459	2190	1450	1042	1459	412
25°	1343	2694	1319	880	1343	619
35°	1169	2162	1144	754	1169	730
45°	919	1019	908	626	919	708
55°	646	628	641	511	646	578
65°	400	386	394	396	400	397
75°	194	190	191	244	194	206
85°	39	43	37	61	39	46
90°	1	22	1	22	1	5
95°	31	223	31	223	31	33
105°	107	1259	107	1259	107	113
115°	192	1403	192	1403	192	189
125°	266	1105	266	1105	266	236
135°	312	918	312	918	312	242
145°	363	724	363	724	363	228
155°	414	607	414	607	414	191
165°	452	532	452	532	452	127
175°	470	478	470	478	470	45
180°	471	471	471	471	471	

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1522.5	1531.5	1541.9	1549.6	1562.5	1566.4	1572.8	1576.7	1580.6	1584.4	1587.0
5°	1518.6	1540.6	1559.9	1574.1	1598.6	1607.7	1619.3	1633.5	1650.2	1664.4	1673.5
7.5°	1508.3	1543.1	1569.0	1597.3	1630.9	1652.8	1664.4	1694.1	1721.2	1741.8	1768.9
10°	1495.4	1536.7	1576.7	1619.3	1667.0	1691.5	1714.8	1756.0	1793.5	1827.0	1854.1
12.5°	1481.2	1531.5	1579.3	1634.8	1699.3	1728.9	1744.4	1815.4	1861.8	1879.9	1932.8
15°	1459.3	1518.6	1587.0	1655.4	1709.6	1744.4	1787.0	1843.8	1890.2	1930.2	1972.8
17.5°	1438.6	1503.1	1572.8	1648.9	1727.7	1772.8	1805.1	1855.4	1905.7	1957.3	1997.3
20°	1405.1	1489.0	1559.9	1641.2	1734.1	1766.4	1799.9	1859.3	1913.5	1968.9	2019.3
22.5°	1378.0	1458.0	1554.8	1632.2	1710.9	1743.1	1784.4	1846.4	1910.9	1974.1	2047.6
25°	1343.2	1432.2	1516.1	1598.6	1679.9	1714.8	1752.2	1832.2	1899.3	1980.5	2061.8
27.5°	1305.7	1397.3	1481.2	1556.0	1632.2	1679.9	1719.9	1803.8	1892.8	1981.8	2087.6
30°	1265.7	1352.2	1432.2	1505.7	1589.6	1638.6	1678.6	1776.7	1876.0	1989.6	2116.0
32.5°	1223.2	1304.4	1372.8	1447.7	1536.7	1581.9	1636.0	1743.1	1860.5	1996.0	2154.7
35°	1169.0	1246.4	1307.0	1383.2	1472.2	1530.2	1587.0	1707.0	1843.8	1994.7	2176.7
37.5°	1114.8	1175.4	1233.5	1314.8	1418.0	1470.9	1530.2	1661.9	1818.0	1990.9	2185.7
40°	1050.3	1109.6	1159.9	1242.5	1350.9	1411.5	1473.5	1611.5	1788.3	1976.7	2153.4
42.5°	985.8	1036.1	1091.6	1178.0	1282.5	1347.0	1412.8	1566.4	1749.6	1935.4	2064.4
45°	918.7	957.4	1018.0	1096.7	1207.7	1269.6	1344.4	1510.9	1695.4	1860.5	1925.1
47.5°	849.0	887.7	944.5	1020.6	1130.3	1203.8	1274.8	1441.2	1627.0	1754.7	1754.7
50°	781.9	812.9	868.3	944.5	1055.4	1122.5	1194.8	1371.5	1521.2	1615.4	1531.5
52.5°	709.6	744.5	790.9	870.9	980.6	1041.2	1119.9	1270.9	1412.8	1451.5	1322.5
55°	646.4	674.8	718.7	794.8	896.7	960.0	1027.0	1171.6	1291.5	1289.0	1150.9
57.5°	580.6	603.8	650.3	720.0	814.2	870.9	938.0	1063.2	1161.2	1126.4	996.1
60°	520.0	536.7	581.9	638.7	729.0	781.9	846.4	948.3	1023.2	974.1	842.5
62.5°	456.8	476.1	512.2	567.7	647.7	690.3	738.0	841.2	889.0	845.1	710.9
65°	400.0	415.5	447.7	494.2	566.4	605.1	646.4	731.6	776.7	713.5	602.5
67.5°	343.2	361.3	384.5	425.8	482.6	518.7	554.8	628.4	649.0	592.2	499.3
70°	290.3	305.8	327.7	357.4	405.1	437.4	464.5	525.1	539.3	486.4	412.9
72.5°	238.7	249.0	267.1	291.6	335.5	353.5	381.9	423.2	441.3	393.5	340.6
75°	193.5	201.3	212.9	231.0	260.6	280.0	303.2	341.9	340.6	307.1	269.7
77.5°	149.7	151.0	163.9	180.6	198.7	215.5	227.1	254.2	256.8	236.1	205.2
80°	107.1	111.0	116.1	129.0	144.5	151.0	165.2	181.9	184.5	169.0	148.4
82.5°	68.4	71.0	74.8	82.6	92.9	100.6	108.4	114.8	121.3	112.3	95.5
85°	38.7	40.0	43.9	46.4	51.6	55.5	61.9	68.4	67.1	60.6	55.5
87.5°	19.4	19.4	19.4	21.9	24.5	24.5	27.1	28.4	29.7	27.1	24.5
90°	1.0	1.9	3.8	5.7	7.6	8.6	9.5	10.5	12.4	13.3	15.2
92.5°	14.3	17.1	26.6	40.9	60.8	77.9	95.0	159.6	268.0	385.8	379.2
95°	31.4	32.3	39.9	50.4	71.3	92.6	114.0	215.7	424.8	687.0	841.9
97.5°	48.5	49.4	55.1	65.6	84.6	100.2	115.9	186.3	346.8	630.0	909.4
100°	66.5	68.4	72.2	82.7	100.7	115.0	129.2	184.3	307.9	547.3	858.1
102.5°	86.5	87.4	90.3	101.7	117.8	131.6	145.4	192.9	291.7	484.6	767.8
105°	107.4	107.4	112.1	121.6	136.8	150.1	163.4	205.3	289.8	448.5	688.9
107.5°	127.3	129.2	134.0	141.6	157.7	169.6	181.5	222.4	296.5	429.5	630.0
110°	149.2	151.1	154.9	163.4	177.7	190.0	202.4	241.4	306.9	421.9	591.1

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	171.0	172.9	175.8	184.3	198.6	210.5	222.4	259.4	320.2	421.9	568.3
115°	192.0	193.9	196.7	205.3	219.5	231.4	243.3	278.4	333.5	424.8	553.0
117.5°	211.0	213.8	216.7	225.2	241.4	252.8	264.2	297.4	348.7	429.5	544.5
120°	230.0	232.8	236.6	245.2	261.3	273.2	285.1	318.3	363.9	437.1	538.8
122.5°	249.9	251.8	254.7	263.2	281.3	293.2	305.0	338.3	381.1	443.8	534.0
125°	266.1	268.0	272.7	281.3	299.3	311.6	324.0	355.4	396.3	451.4	530.2
127.5°	279.4	282.2	287.9	298.4	317.4	329.8	342.1	372.5	410.5	459.9	528.3
130°	291.7	294.6	302.2	314.5	334.5	346.8	359.2	388.7	424.8	467.5	526.4
132.5°	301.2	305.0	314.5	328.8	349.7	362.0	374.4	403.9	437.1	476.1	526.4
135°	311.7	315.5	326.9	342.1	362.0	374.8	387.7	417.2	448.5	483.7	526.4
137.5°	325.0	327.8	338.3	353.5	373.5	386.8	400.1	426.7	457.1	491.3	527.4
140°	336.4	339.2	350.6	365.8	383.9	396.8	409.6	437.1	465.6	496.0	528.3
142.5°	349.7	351.6	362.0	377.3	394.4	406.2	418.1	443.8	470.4	498.9	529.3
145°	363.0	364.9	374.4	387.7	404.8	415.8	426.7	451.4	475.1	500.8	528.3
147.5°	377.3	378.2	386.8	399.1	414.3	424.3	434.3	456.1	478.0	501.7	526.4
150°	389.6	391.5	398.2	410.5	423.8	431.9	440.0	460.9	480.8	501.7	523.6
152.5°	402.9	403.9	409.6	420.0	432.4	439.5	446.6	465.6	482.7	500.8	519.8
155°	414.3	414.3	420.0	429.5	439.0	445.6	452.3	468.5	483.7	498.9	515.0
157.5°	424.8	424.8	429.5	438.1	446.6	451.8	457.1	471.3	484.6	497.0	510.3
160°	435.2	434.3	438.1	444.7	452.3	456.6	460.9	473.2	484.6	494.1	505.5
162.5°	443.8	442.8	446.6	452.3	458.0	461.4	464.7	475.1	483.7	491.3	499.8
165°	452.3	450.4	453.3	458.0	461.8	464.6	467.5	475.1	482.7	488.4	494.1
167.5°	458.0	457.1	459.0	461.8	464.7	466.6	468.5	475.1	480.8	483.7	488.4
170°	463.7	462.8	463.7	465.6	467.5	469.0	470.4	475.1	478.9	480.8	483.7
172.5°	467.5	465.6	466.6	468.5	469.4	469.9	470.4	474.2	477.0	477.0	478.0
175°	470.4	468.5	469.4	470.4	470.4	470.4	470.4	473.2	475.1	474.2	474.2
177.5°	472.3	470.4	470.4	471.3	470.4	470.4	470.4	472.3	473.2	471.3	471.3
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1589.6	1598.6	1606.4	1612.8	1618.0	1625.7	1620.6	1621.9	1624.4	1629.6	1629.6
5°	1692.8	1707.0	1714.8	1740.6	1747.0	1745.7	1741.8	1762.5	1761.2	1753.5	1752.2
7.5°	1793.5	1818.0	1839.9	1860.5	1867.0	1883.8	1887.6	1896.7	1894.1	1907.0	1900.5
10°	1885.1	1923.8	1944.4	1975.4	1983.1	1990.9	2001.2	2006.3	2018.0	2016.7	2016.7
12.5°	1956.0	2002.5	2029.6	2037.3	2067.0	2076.0	2085.1	2101.8	2098.0	2099.2	2107.0
15°	2011.5	2056.7	2079.9	2116.0	2136.7	2147.0	2162.5	2180.5	2178.0	2189.6	2187.0
17.5°	2052.8	2095.4	2138.0	2192.1	2193.4	2220.5	2256.7	2264.4	2281.2	2269.6	2269.6
20°	2086.3	2143.1	2203.8	2273.4	2281.2	2297.9	2341.8	2371.5	2390.8	2384.4	2388.3
22.5°	2122.5	2203.8	2274.7	2344.4	2381.8	2411.5	2454.1	2500.5	2517.3	2527.6	2525.0
25°	2168.9	2254.1	2358.6	2455.4	2494.1	2550.8	2607.6	2652.8	2665.7	2694.1	2668.3
27.5°	2216.7	2336.7	2467.0	2580.5	2629.5	2676.0	2744.4	2777.9	2794.7	2807.6	2798.6
30°	2256.7	2421.8	2563.7	2668.3	2703.1	2730.2	2768.9	2776.6	2770.2	2780.5	2793.4
32.5°	2318.6	2479.9	2599.9	2650.2	2646.3	2645.0	2615.3	2574.1	2565.0	2540.5	2574.1
35°	2352.1	2481.2	2527.6	2460.5	2433.4	2384.4	2290.2	2228.3	2174.1	2162.5	2165.1
37.5°	2332.8	2383.1	2327.6	2150.9	2107.0	2032.2	1907.0	1819.3	1779.3	1748.3	1788.3
40°	2228.3	2172.8	2020.5	1805.1	1741.8	1670.9	1553.5	1505.7	1449.0	1437.3	1490.2
42.5°	2055.4	1886.4	1670.9	1504.4	1438.6	1398.6	1300.6	1255.4	1215.4	1197.4	1227.0
45°	1820.6	1615.4	1398.6	1261.9	1206.4	1158.7	1100.6	1052.8	1027.0	1019.3	1043.8
47.5°	1578.0	1361.2	1188.3	1086.4	1028.3	992.2	938.0	910.9	890.3	892.9	896.7
50°	1345.7	1148.3	1015.4	913.5	885.1	856.7	820.6	797.4	787.1	790.9	788.3
52.5°	1145.7	985.8	873.5	794.8	781.9	754.8	725.1	705.8	701.9	703.2	707.1
55°	970.3	845.1	756.1	699.3	685.1	665.8	647.7	634.8	624.5	628.4	627.1
57.5°	837.4	727.7	659.3	612.9	602.5	590.9	574.2	567.7	563.8	556.1	562.6
60°	720.0	630.9	571.6	543.2	534.2	526.4	508.4	500.6	498.0	494.2	504.5
62.5°	609.0	545.8	500.6	474.8	465.8	458.0	449.0	442.6	443.8	438.7	443.8
65°	521.3	469.7	437.4	414.2	402.6	397.4	396.1	385.8	384.5	385.8	387.1
67.5°	440.0	396.1	371.6	357.4	348.4	343.2	339.3	332.9	338.0	334.2	336.8
70°	366.4	336.8	311.0	296.8	292.9	294.2	287.7	285.1	286.4	283.9	286.4
72.5°	295.5	271.0	260.6	250.3	245.1	243.9	240.0	236.1	240.0	238.7	238.7
75°	236.1	218.1	206.4	200.0	200.0	197.4	191.0	191.0	191.0	189.7	191.0
77.5°	181.9	166.4	161.3	154.8	154.8	151.0	149.7	149.7	147.1	151.0	148.4
80°	135.5	123.9	116.1	112.3	112.3	111.0	108.4	107.1	108.4	107.1	107.1
82.5°	87.7	82.6	78.7	74.8	73.5	74.8	73.5	71.0	72.3	71.0	73.5
85°	50.3	45.2	45.2	42.6	43.9	41.3	42.6	40.0	38.7	42.6	40.0
87.5°	21.9	20.6	20.6	18.1	18.1	18.1	16.8	18.1	16.8	15.5	16.8
90°	16.2	17.1	18.1	19.0	20.0	20.9	20.9	20.9	21.9	21.9	21.9
92.5°	306.0	206.2	148.2	110.2	101.2	92.2	77.0	74.1	72.2	70.3	72.2
95°	823.9	683.2	538.8	421.9	382.0	342.1	274.6	246.1	238.5	223.3	238.5
97.5°	1029.1	979.7	864.7	746.9	689.9	632.9	575.9	526.4	500.8	489.4	500.8
100°	1095.6	1168.8	1122.3	1024.4	975.0	925.5	860.0	791.6	756.4	741.2	756.4
102.5°	1055.7	1232.5	1280.0	1245.8	1216.4	1186.9	1115.6	1071.9	1032.9	1022.5	1032.9
105°	961.7	1189.7	1319.9	1361.7	1356.5	1351.3	1320.9	1289.5	1270.5	1259.1	1270.5
107.5°	872.3	1102.3	1274.3	1375.0	1395.9	1416.8	1425.4	1420.6	1411.1	1401.6	1411.1
110°	798.2	1003.5	1184.0	1318.0	1358.4	1398.8	1441.5	1459.6	1466.2	1466.2	1466.2



TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	743.1	925.5	1094.7	1230.6	1280.0	1329.4	1396.9	1431.1	1450.1	1458.6	1450.1
115°	706.0	862.8	1010.1	1140.3	1192.1	1243.9	1318.0	1363.6	1390.2	1402.6	1390.2
117.5°	681.3	819.1	949.3	1063.3	1112.2	1161.2	1236.3	1283.8	1310.4	1318.0	1310.4
120°	661.4	784.9	898.9	1003.5	1045.3	1087.1	1157.4	1203.0	1228.7	1236.3	1228.7
122.5°	644.3	759.3	862.8	953.1	991.6	1030.1	1090.9	1131.8	1157.4	1164.1	1157.4
125°	629.1	734.5	831.5	914.1	948.4	982.6	1035.8	1074.7	1095.6	1105.1	1095.6
127.5°	614.8	708.9	801.1	879.0	911.3	943.6	992.1	1027.2	1047.2	1051.0	1047.2
130°	600.6	685.1	768.8	842.9	873.8	904.6	952.2	983.5	1002.5	1008.2	1002.5
132.5°	589.2	661.4	738.3	803.9	833.4	862.8	910.3	941.7	958.8	965.5	958.8
135°	580.6	641.4	707.0	767.8	794.9	822.0	863.8	895.1	912.2	917.9	912.2
137.5°	572.1	623.4	678.5	730.7	754.5	778.3	816.3	845.7	861.9	868.5	861.9
140°	566.4	609.1	653.8	697.5	717.4	737.4	772.6	797.3	811.5	816.3	811.5
142.5°	561.6	596.8	632.9	669.0	685.6	702.2	730.7	750.7	764.0	767.8	764.0
145°	556.8	586.3	615.8	645.2	658.0	670.9	693.7	709.8	720.3	724.1	720.3
147.5°	552.1	575.9	600.6	624.3	634.3	644.3	663.3	676.6	683.2	685.1	683.2
150°	546.4	567.3	588.2	606.3	614.8	623.4	637.6	649.0	652.8	653.8	652.8
152.5°	539.7	557.8	575.9	592.0	598.2	604.4	615.8	624.3	628.1	629.1	628.1
155°	532.1	548.3	563.5	576.8	582.0	587.3	596.8	603.4	606.3	607.2	606.3
157.5°	525.5	538.8	552.1	562.6	566.8	571.1	578.7	584.4	587.3	587.3	587.3
160°	516.9	529.3	538.8	548.3	551.6	554.9	561.6	566.4	568.3	567.3	568.3
162.5°	509.3	518.8	527.4	535.0	537.8	540.7	545.4	549.2	549.2	549.2	549.2
165°	501.7	509.3	516.0	521.7	524.0	526.4	530.2	532.1	532.1	532.1	532.1
167.5°	494.1	499.8	504.6	509.3	511.2	513.1	515.0	516.9	516.0	516.0	516.0
170°	487.5	492.2	495.1	497.9	498.8	499.8	501.7	502.7	502.7	501.7	502.7
172.5°	480.8	483.7	486.5	488.4	488.9	489.4	489.4	491.3	489.4	488.4	489.4
175°	475.1	478.0	478.0	479.9	479.9	479.9	479.9	480.8	478.9	478.0	478.9
177.5°	472.3	473.2	474.2	474.2	474.2	474.2	473.2	474.2	471.3	471.3	471.3
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1627.0	1618.0	1620.6	1618.0	1611.5	1607.7	1597.3	1584.4	1579.3	1572.8	1569.0
5°	1757.3	1750.9	1749.6	1739.3	1736.7	1721.2	1695.4	1682.5	1667.0	1651.5	1636.0
7.5°	1899.3	1891.5	1865.7	1861.8	1864.4	1845.1	1811.5	1785.7	1753.5	1731.5	1701.8
10°	2016.7	2001.2	1979.3	1980.5	1971.5	1945.7	1912.2	1885.1	1838.6	1810.2	1767.7
12.5°	2087.6	2074.7	2072.2	2059.2	2051.5	2018.0	1978.0	1943.1	1908.3	1869.6	1837.3
15°	2174.1	2157.3	2145.7	2127.6	2122.5	2087.6	2043.8	2003.8	1963.8	1927.6	1859.3
17.5°	2269.6	2251.5	2207.6	2203.8	2172.8	2139.2	2096.7	2037.3	1994.7	1943.1	1892.8
20°	2377.9	2352.1	2295.4	2281.2	2256.7	2201.2	2143.1	2077.3	2008.9	1956.0	1896.7
22.5°	2499.2	2454.1	2412.8	2367.6	2349.6	2281.2	2201.2	2121.2	2038.6	1966.4	1895.4
25°	2656.6	2597.3	2539.2	2494.1	2463.1	2374.1	2267.0	2161.2	2065.7	1971.5	1878.6
27.5°	2780.5	2728.9	2665.7	2606.3	2566.3	2460.5	2337.9	2201.2	2082.5	1967.6	1868.3
30°	2789.5	2774.1	2735.3	2703.1	2659.2	2545.7	2410.2	2255.4	2108.3	1968.9	1847.6
32.5°	2620.5	2651.5	2668.3	2673.4	2664.4	2598.6	2474.7	2304.4	2131.5	1957.3	1829.6
35°	2256.7	2339.2	2441.2	2479.9	2517.3	2552.1	2487.6	2339.2	2139.2	1954.7	1801.2
37.5°	1858.0	1932.8	2101.8	2179.2	2223.1	2361.2	2414.1	2334.1	2154.7	1957.3	1774.1
40°	1499.3	1618.0	1739.3	1843.8	1912.2	2067.0	2230.9	2248.9	2132.8	1932.8	1739.3
42.5°	1261.9	1331.5	1423.2	1519.9	1580.6	1763.8	1985.7	2116.0	2064.4	1892.8	1696.7
45°	1074.8	1126.4	1212.8	1245.1	1322.5	1498.0	1732.8	1921.2	1947.0	1829.6	1647.7
47.5°	922.5	966.4	1021.9	1061.9	1123.8	1255.4	1454.1	1661.9	1785.7	1743.1	1579.3
50°	812.9	849.0	895.4	918.7	958.7	1077.4	1227.0	1433.5	1599.9	1614.1	1490.2
52.5°	721.3	741.9	778.0	803.8	836.1	908.3	1043.8	1214.1	1401.2	1478.6	1380.6
55°	641.3	658.0	690.3	707.1	723.8	785.8	891.6	1046.4	1221.9	1323.8	1268.3
57.5°	569.0	583.2	610.3	625.8	634.8	694.2	775.4	896.7	1054.1	1178.0	1147.0
60°	509.7	522.6	538.0	549.6	560.0	609.0	665.8	763.8	904.5	1024.5	1016.7
62.5°	446.4	458.0	474.8	486.4	495.5	526.4	574.2	649.0	769.0	880.0	901.9
65°	390.9	400.0	411.6	416.8	428.4	451.6	490.3	557.4	655.5	754.8	770.3
67.5°	340.6	343.2	350.9	362.6	365.1	385.8	420.6	470.9	547.1	628.4	652.9
70°	286.4	290.3	296.8	305.8	311.0	323.9	353.5	387.1	452.9	523.8	541.9
72.5°	238.7	243.9	246.4	251.6	254.2	274.8	287.7	321.3	366.4	425.8	445.1
75°	193.5	198.7	200.0	202.6	205.2	214.2	232.2	252.9	290.3	329.0	354.8
77.5°	153.5	152.3	154.8	158.7	157.4	165.2	176.8	194.8	219.3	251.6	268.4
80°	108.4	108.4	112.3	116.1	114.8	122.6	126.4	139.3	160.0	180.6	187.1
82.5°	72.3	72.3	76.1	76.1	78.7	80.0	85.2	91.6	108.4	118.7	122.6
85°	41.3	41.3	42.6	42.6	42.6	45.2	49.0	51.6	56.8	63.2	65.8
87.5°	16.8	18.1	18.1	18.1	18.1	20.6	20.6	23.2	24.5	27.1	27.1
90°	20.9	20.9	20.9	20.0	19.0	18.1	17.1	16.2	15.2	13.3	12.4
92.5°	74.1	77.0	92.2	101.2	110.2	148.2	206.2	306.0	379.2	385.8	268.0
95°	246.1	274.6	342.1	382.0	421.9	538.8	683.2	823.9	841.9	687.0	424.8
97.5°	526.4	575.9	632.9	689.9	746.9	864.7	979.7	1029.1	909.4	630.0	346.8
100°	791.6	860.0	925.5	975.0	1024.4	1122.3	1168.8	1095.6	858.1	547.3	307.9
102.5°	1071.9	1115.6	1186.9	1216.4	1245.8	1280.0	1232.5	1055.7	767.8	484.6	291.7
105°	1289.5	1320.9	1351.3	1356.5	1361.7	1319.9	1189.7	961.7	688.9	448.5	289.8
107.5°	1420.6	1425.4	1416.8	1395.9	1375.0	1274.3	1102.3	872.3	630.0	429.5	296.5
110°	1459.6	1441.5	1398.8	1358.4	1318.0	1184.0	1003.5	798.2	591.1	421.9	306.9

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1431.1	1396.9	1329.4	1280.0	1230.6	1094.7	925.5	743.1	568.3	421.9	320.2
115°	1363.6	1318.0	1243.9	1192.1	1140.3	1010.1	862.8	706.0	553.0	424.8	333.5
117.5°	1283.8	1236.3	1161.2	1112.2	1063.3	949.3	819.1	681.3	544.5	429.5	348.7
120°	1203.0	1157.4	1087.1	1045.3	1003.5	898.9	784.9	661.4	538.8	437.1	363.9
122.5°	1131.8	1090.9	1030.1	991.6	953.1	862.8	759.3	644.3	534.0	443.8	381.1
125°	1074.7	1035.8	982.6	948.4	914.1	831.5	734.5	629.1	530.2	451.4	396.3
127.5°	1027.2	992.1	943.6	911.3	879.0	801.1	708.9	614.8	528.3	459.9	410.5
130°	983.5	952.2	904.6	873.8	842.9	768.8	685.1	600.6	526.4	467.5	424.8
132.5°	941.7	910.3	862.8	833.4	803.9	738.3	661.4	589.2	526.4	476.1	437.1
135°	895.1	863.8	822.0	794.9	767.8	707.0	641.4	580.6	526.4	483.7	448.5
137.5°	845.7	816.3	778.3	754.5	730.7	678.5	623.4	572.1	527.4	491.3	457.1
140°	797.3	772.6	737.4	717.4	697.5	653.8	609.1	566.4	528.3	496.0	465.6
142.5°	750.7	730.7	702.2	685.6	669.0	632.9	596.8	561.6	529.3	498.9	470.4
145°	709.8	693.7	670.9	658.0	645.2	615.8	586.3	556.8	528.3	500.8	475.1
147.5°	676.6	663.3	644.3	634.3	624.3	600.6	575.9	552.1	526.4	501.7	478.0
150°	649.0	637.6	623.4	614.8	606.3	588.2	567.3	546.4	523.6	501.7	480.8
152.5°	624.3	615.8	604.4	598.2	592.0	575.9	557.8	539.7	519.8	500.8	482.7
155°	603.4	596.8	587.3	582.0	576.8	563.5	548.3	532.1	515.0	498.9	483.7
157.5°	584.4	578.7	571.1	566.8	562.6	552.1	538.8	525.5	510.3	497.0	484.6
160°	566.4	561.6	554.9	551.6	548.3	538.8	529.3	516.9	505.5	494.1	484.6
162.5°	549.2	545.4	540.7	537.8	535.0	527.4	518.8	509.3	499.8	491.3	483.7
165°	532.1	530.2	526.4	524.0	521.7	516.0	509.3	501.7	494.1	488.4	482.7
167.5°	516.9	515.0	513.1	511.2	509.3	504.6	499.8	494.1	488.4	483.7	480.8
170°	502.7	501.7	499.8	498.8	497.9	495.1	492.2	487.5	483.7	480.8	478.9
172.5°	491.3	489.4	489.4	488.9	488.4	486.5	483.7	480.8	478.0	477.0	477.0
175°	480.8	479.9	479.9	479.9	479.9	478.0	478.0	475.1	474.2	474.2	475.1
177.5°	474.2	473.2	474.2	474.2	474.2	474.2	473.2	472.3	471.3	471.3	473.2
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1563.8	1557.3	1549.6	1549.6	1540.6	1536.7	1529.0	1526.4	1519.9	1509.6	1501.9
5°	1619.3	1602.5	1592.2	1583.1	1563.8	1549.6	1535.4	1519.9	1504.4	1486.4	1465.7
7.5°	1673.5	1642.5	1628.3	1612.8	1584.4	1554.8	1526.4	1505.7	1485.1	1456.7	1430.9
10°	1730.2	1691.5	1665.7	1645.1	1601.2	1563.8	1522.5	1492.8	1460.6	1424.4	1390.9
12.5°	1778.0	1727.7	1705.7	1667.0	1616.7	1571.5	1519.9	1474.8	1432.2	1389.6	1348.3
15°	1818.0	1770.2	1716.0	1700.6	1630.9	1566.4	1508.3	1450.2	1397.3	1354.8	1307.0
17.5°	1830.9	1770.2	1743.1	1705.7	1623.1	1556.0	1482.5	1419.3	1369.0	1305.7	1268.3
20°	1834.7	1776.7	1739.3	1704.4	1630.9	1541.9	1469.6	1392.2	1331.5	1268.3	1209.0
22.5°	1824.4	1756.0	1719.9	1686.4	1603.8	1527.7	1443.8	1358.6	1287.7	1229.6	1170.3
25°	1805.1	1725.1	1690.2	1654.1	1575.4	1491.5	1399.9	1318.6	1252.8	1183.2	1125.1
27.5°	1779.3	1687.7	1647.7	1610.2	1532.8	1454.1	1367.7	1283.8	1210.3	1136.7	1082.5
30°	1747.0	1641.2	1605.1	1556.0	1481.2	1406.4	1327.7	1243.8	1161.2	1091.6	1032.2
32.5°	1705.7	1594.8	1547.0	1500.6	1419.3	1350.9	1276.1	1197.4	1117.4	1049.0	987.0
35°	1668.3	1541.9	1489.0	1442.5	1352.2	1279.9	1218.0	1144.5	1073.5	1002.5	947.0
37.5°	1618.0	1489.0	1425.7	1378.0	1286.4	1212.8	1154.8	1098.0	1023.2	954.8	903.2
40°	1565.1	1423.2	1363.8	1316.1	1220.6	1140.6	1085.1	1034.8	974.1	910.9	856.7
42.5°	1517.3	1359.9	1296.7	1238.6	1141.9	1070.9	1014.1	975.4	920.0	863.2	814.2
45°	1456.7	1292.8	1224.5	1163.8	1070.9	993.5	939.3	908.3	867.1	811.6	769.0
47.5°	1394.8	1220.6	1149.6	1090.3	989.6	921.2	868.3	838.7	810.3	766.4	723.8
50°	1313.5	1144.5	1079.9	1011.6	912.2	842.5	798.7	769.0	747.1	716.1	680.0
52.5°	1224.5	1065.8	996.1	936.7	838.7	775.4	725.1	708.4	686.4	663.2	632.2
55°	1130.3	980.6	913.5	855.4	765.1	700.6	659.3	641.3	624.5	606.4	585.8
57.5°	1036.1	891.6	828.3	776.7	692.9	630.9	597.4	572.9	561.3	550.9	534.2
60°	918.7	796.1	747.1	700.6	618.0	561.3	529.0	510.9	500.6	495.5	487.7
62.5°	815.4	714.8	660.6	615.5	549.6	499.3	468.4	454.2	445.1	442.6	433.5
65°	705.8	619.3	576.7	538.0	481.3	436.1	410.3	393.5	387.1	385.8	385.8
67.5°	602.5	532.9	490.3	463.2	414.2	374.2	349.7	343.2	339.3	334.2	332.9
70°	505.8	450.3	412.9	389.7	345.8	316.1	296.8	286.4	286.4	282.6	280.0
72.5°	420.6	365.1	340.6	321.3	285.1	259.3	245.1	242.6	233.5	232.2	232.2
75°	329.0	287.7	271.0	254.2	227.1	209.0	197.4	191.0	185.8	185.8	187.1
77.5°	247.7	219.3	203.9	191.0	171.6	160.0	151.0	148.4	143.2	143.2	143.2
80°	175.5	160.0	148.4	138.1	123.9	113.5	108.4	103.2	103.2	101.9	103.2
82.5°	113.5	100.6	94.2	92.9	80.0	76.1	69.7	71.0	67.1	65.8	68.4
85°	65.8	59.4	51.6	49.0	43.9	38.7	36.1	37.4	36.1	34.8	36.1
87.5°	25.8	21.9	20.6	20.6	16.8	15.5	14.2	15.5	12.9	12.9	14.2
90°	10.5	9.5	8.6	7.6	5.7	3.8	1.9	1.0	1.9	3.8	5.7
92.5°	159.6	95.0	77.9	60.8	40.9	26.6	17.1	14.3	17.1	26.6	40.9
95°	215.7	114.0	92.6	71.3	50.4	39.9	32.3	31.4	32.3	39.9	50.4
97.5°	186.3	115.9	100.2	84.6	65.6	55.1	49.4	48.5	49.4	55.1	65.6
100°	184.3	129.2	115.0	100.7	82.7	72.2	68.4	66.5	68.4	72.2	82.7
102.5°	192.9	145.4	131.6	117.8	101.7	90.3	87.4	86.5	87.4	90.3	101.7
105°	205.3	163.4	150.1	136.8	121.6	112.1	107.4	107.4	107.4	112.1	121.6
107.5°	222.4	181.5	169.6	157.7	141.6	134.0	129.2	127.3	129.2	134.0	141.6
110°	241.4	202.4	190.0	177.7	163.4	154.9	151.1	149.2	151.1	154.9	163.4

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	259.4	222.4	210.5	198.6	184.3	175.8	172.9	171.0	172.9	175.8	184.3
115°	278.4	243.3	231.4	219.5	205.3	196.7	193.9	192.0	193.9	196.7	205.3
117.5°	297.4	264.2	252.8	241.4	225.2	216.7	213.8	211.0	213.8	216.7	225.2
120°	318.3	285.1	273.2	261.3	245.2	236.6	232.8	230.0	232.8	236.6	245.2
122.5°	338.3	305.0	293.2	281.3	263.2	254.7	251.8	249.9	251.8	254.7	263.2
125°	355.4	324.0	311.6	299.3	281.3	272.7	268.0	266.1	268.0	272.7	281.3
127.5°	372.5	342.1	329.8	317.4	298.4	287.9	282.2	279.4	282.2	287.9	298.4
130°	388.7	359.2	346.8	334.5	314.5	302.2	294.6	291.7	294.6	302.2	314.5
132.5°	403.9	374.4	362.0	349.7	328.8	314.5	305.0	301.2	305.0	314.5	328.8
135°	417.2	387.7	374.8	362.0	342.1	326.9	315.5	311.7	315.5	326.9	342.1
137.5°	426.7	400.1	386.8	373.5	353.5	338.3	327.8	325.0	327.8	338.3	353.5
140°	437.1	409.6	396.8	383.9	365.8	350.6	339.2	336.4	339.2	350.6	365.8
142.5°	443.8	418.1	406.2	394.4	377.3	362.0	351.6	349.7	351.6	362.0	377.3
145°	451.4	426.7	415.8	404.8	387.7	374.4	364.9	363.0	364.9	374.4	387.7
147.5°	456.1	434.3	424.3	414.3	399.1	386.8	378.2	377.3	378.2	386.8	399.1
150°	460.9	440.0	431.9	423.8	410.5	398.2	391.5	389.6	391.5	398.2	410.5
152.5°	465.6	446.6	439.5	432.4	420.0	409.6	403.9	402.9	403.9	409.6	420.0
155°	468.5	452.3	445.6	439.0	429.5	420.0	414.3	414.3	414.3	420.0	429.5
157.5°	471.3	457.1	451.8	446.6	438.1	429.5	424.8	424.8	424.8	429.5	438.1
160°	473.2	460.9	456.6	452.3	444.7	438.1	434.3	435.2	434.3	438.1	444.7
162.5°	475.1	464.7	461.4	458.0	452.3	446.6	442.8	443.8	442.8	446.6	452.3
165°	475.1	467.5	464.6	461.8	458.0	453.3	450.4	452.3	450.4	453.3	458.0
167.5°	475.1	468.5	466.6	464.7	461.8	459.0	457.1	458.0	457.1	459.0	461.8
170°	475.1	470.4	469.0	467.5	465.6	463.7	462.8	463.7	462.8	463.7	465.6
172.5°	474.2	470.4	469.9	469.4	468.5	466.6	465.6	467.5	465.6	466.6	468.5
175°	473.2	470.4	470.4	470.4	470.4	469.4	468.5	470.4	468.5	469.4	470.4
177.5°	472.3	470.4	470.4	470.4	471.3	470.4	470.4	472.3	470.4	470.4	471.3
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1499.3	1496.7	1490.2	1486.4	1473.5	1458.0	1452.8	1439.9	1445.1	1436.1	1436.1
5°	1459.3	1447.7	1439.9	1428.3	1403.8	1387.0	1369.0	1359.9	1354.8	1348.3	1343.2
7.5°	1407.7	1398.6	1390.9	1369.0	1341.9	1318.6	1296.7	1287.7	1270.9	1259.3	1254.1
10°	1362.5	1349.6	1331.5	1305.7	1277.4	1247.7	1228.3	1209.0	1196.1	1189.6	1175.4
12.5°	1316.1	1300.6	1281.2	1243.8	1212.8	1194.8	1159.9	1141.9	1135.4	1130.3	1113.5
15°	1268.3	1251.5	1228.3	1193.5	1166.4	1123.8	1103.2	1089.0	1073.5	1072.2	1059.3
17.5°	1225.7	1205.1	1185.7	1143.2	1109.6	1072.2	1060.6	1045.1	1030.9	1015.4	1009.0
20°	1171.6	1152.2	1138.0	1091.6	1054.1	1030.9	1011.6	998.7	989.6	974.1	971.6
22.5°	1122.5	1101.9	1082.5	1047.7	1015.4	985.8	962.5	948.3	944.5	938.0	926.4
25°	1074.8	1054.1	1030.9	998.7	965.1	944.5	923.8	914.8	907.1	896.7	887.7
27.5°	1034.8	1015.4	993.5	953.5	925.1	909.6	887.7	877.4	867.1	861.9	858.0
30°	987.0	965.1	948.3	917.4	886.4	865.8	850.3	841.2	832.2	827.1	824.5
32.5°	940.6	920.0	908.3	874.8	850.3	825.8	814.2	807.7	802.5	797.4	792.2
35°	903.2	882.5	864.5	833.5	809.0	792.2	783.2	772.9	769.0	763.8	763.8
37.5°	856.7	841.2	823.2	793.5	771.6	758.7	750.9	738.0	736.7	734.2	730.3
40°	816.7	801.2	784.5	758.7	739.3	723.8	713.5	707.1	703.2	700.6	698.0
42.5°	774.2	757.4	749.6	720.0	703.2	687.7	682.5	676.1	674.8	669.6	663.2
45°	732.9	718.7	703.2	681.3	667.1	654.2	646.4	641.3	634.8	633.5	629.6
47.5°	696.7	680.0	665.8	645.1	629.6	619.3	612.9	606.4	601.3	597.4	593.5
50°	650.3	637.4	625.8	603.8	590.9	580.6	571.6	566.4	561.3	561.3	561.3
52.5°	605.1	593.5	583.2	567.7	552.2	543.2	532.9	529.0	526.4	522.6	526.4
55°	561.3	549.6	539.3	527.7	509.7	501.9	491.6	487.7	489.0	489.0	492.9
57.5°	514.8	505.8	499.3	485.1	468.4	460.6	454.2	450.3	450.3	455.5	456.8
60°	469.7	460.6	449.0	436.1	425.8	416.8	412.9	414.2	414.2	416.8	423.2
62.5°	419.3	414.2	407.7	389.7	383.2	376.8	371.6	375.5	374.2	380.6	389.7
65°	372.9	367.7	358.7	349.7	341.9	335.5	334.2	335.5	338.0	344.5	354.8
67.5°	321.3	321.3	313.5	305.8	299.3	292.9	294.2	295.5	298.0	305.8	321.3
70°	278.7	273.5	265.8	260.6	255.5	252.9	250.3	255.5	263.2	268.4	280.0
72.5°	232.2	228.4	221.9	216.8	215.5	212.9	211.6	214.2	221.9	231.0	243.9
75°	183.2	184.5	180.6	176.8	176.8	172.9	175.5	175.5	183.2	192.2	202.6
77.5°	141.9	140.6	139.3	136.8	135.5	135.5	135.5	138.1	145.8	151.0	161.3
80°	100.6	101.9	98.1	99.3	98.1	99.3	99.3	104.5	108.4	114.8	122.6
82.5°	67.1	67.1	64.5	65.8	65.8	65.8	67.1	69.7	74.8	80.0	85.2
85°	37.4	38.7	36.1	38.7	38.7	38.7	40.0	41.3	45.2	46.4	51.6
87.5°	14.2	16.8	16.8	14.2	15.5	16.8	18.1	16.8	19.4	21.9	23.2
90°	7.6	8.6	9.5	10.5	12.4	13.3	15.2	16.2	17.1	18.1	19.0
92.5°	60.8	77.9	95.0	159.6	268.0	385.8	379.2	306.0	206.2	148.2	110.2
95°	71.3	92.6	114.0	215.7	424.8	687.0	841.9	823.9	683.2	538.8	421.9
97.5°	84.6	100.2	115.9	186.3	346.8	630.0	909.4	1029.1	979.7	864.7	746.9
100°	100.7	115.0	129.2	184.3	307.9	547.3	858.1	1095.6	1168.8	1122.3	1024.4
102.5°	117.8	131.6	145.4	192.9	291.7	484.6	767.8	1055.7	1232.5	1280.0	1245.8
105°	136.8	150.1	163.4	205.3	289.8	448.5	688.9	961.7	1189.7	1319.9	1361.7
107.5°	157.7	169.6	181.5	222.4	296.5	429.5	630.0	872.3	1102.3	1274.3	1375.0
110°	177.7	190.0	202.4	241.4	306.9	421.9	591.1	798.2	1003.5	1184.0	1318.0

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	198.6	210.5	222.4	259.4	320.2	421.9	568.3	743.1	925.5	1094.7	1230.6
115°	219.5	231.4	243.3	278.4	333.5	424.8	553.0	706.0	862.8	1010.1	1140.3
117.5°	241.4	252.8	264.2	297.4	348.7	429.5	544.5	681.3	819.1	949.3	1063.3
120°	261.3	273.2	285.1	318.3	363.9	437.1	538.8	661.4	784.9	898.9	1003.5
122.5°	281.3	293.2	305.0	338.3	381.1	443.8	534.0	644.3	759.3	862.8	953.1
125°	299.3	311.6	324.0	355.4	396.3	451.4	530.2	629.1	734.5	831.5	914.1
127.5°	317.4	329.8	342.1	372.5	410.5	459.9	528.3	614.8	708.9	801.1	879.0
130°	334.5	346.8	359.2	388.7	424.8	467.5	526.4	600.6	685.1	768.8	842.9
132.5°	349.7	362.0	374.4	403.9	437.1	476.1	526.4	589.2	661.4	738.3	803.9
135°	362.0	374.8	387.7	417.2	448.5	483.7	526.4	580.6	641.4	707.0	767.8
137.5°	373.5	386.8	400.1	426.7	457.1	491.3	527.4	572.1	623.4	678.5	730.7
140°	383.9	396.8	409.6	437.1	465.6	496.0	528.3	566.4	609.1	653.8	697.5
142.5°	394.4	406.2	418.1	443.8	470.4	498.9	529.3	561.6	596.8	632.9	669.0
145°	404.8	415.8	426.7	451.4	475.1	500.8	528.3	556.8	586.3	615.8	645.2
147.5°	414.3	424.3	434.3	456.1	478.0	501.7	526.4	552.1	575.9	600.6	624.3
150°	423.8	431.9	440.0	460.9	480.8	501.7	523.6	546.4	567.3	588.2	606.3
152.5°	432.4	439.5	446.6	465.6	482.7	500.8	519.8	539.7	557.8	575.9	592.0
155°	439.0	445.6	452.3	468.5	483.7	498.9	515.0	532.1	548.3	563.5	576.8
157.5°	446.6	451.8	457.1	471.3	484.6	497.0	510.3	525.5	538.8	552.1	562.6
160°	452.3	456.6	460.9	473.2	484.6	494.1	505.5	516.9	529.3	538.8	548.3
162.5°	458.0	461.4	464.7	475.1	483.7	491.3	499.8	509.3	518.8	527.4	535.0
165°	461.8	464.6	467.5	475.1	482.7	488.4	494.1	501.7	509.3	516.0	521.7
167.5°	464.7	466.6	468.5	475.1	480.8	483.7	488.4	494.1	499.8	504.6	509.3
170°	467.5	469.0	470.4	475.1	478.9	480.8	483.7	487.5	492.2	495.1	497.9
172.5°	469.4	469.9	470.4	474.2	477.0	477.0	478.0	480.8	483.7	486.5	488.4
175°	470.4	470.4	470.4	473.2	475.1	474.2	474.2	475.1	478.0	478.0	479.9
177.5°	470.4	470.4	470.4	472.3	473.2	471.3	471.3	472.3	473.2	474.2	474.2
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1441.2	1432.2	1430.9	1433.5	1428.3	1436.1	1433.5	1436.1	1429.6	1436.1	1432.2
5°	1341.9	1339.3	1334.1	1327.7	1329.0	1330.3	1336.7	1330.3	1335.4	1336.7	1343.2
7.5°	1249.0	1243.8	1247.7	1245.1	1233.5	1230.9	1233.5	1237.4	1245.1	1250.3	1254.1
10°	1174.1	1171.6	1166.4	1162.5	1156.1	1152.2	1157.4	1152.2	1162.5	1171.6	1171.6
12.5°	1117.4	1107.0	1100.6	1099.3	1085.1	1087.7	1092.8	1096.7	1108.3	1113.5	1113.5
15°	1058.0	1050.3	1047.7	1042.5	1037.4	1042.5	1039.9	1043.8	1049.0	1054.1	1056.7
17.5°	1006.4	1005.1	1006.4	993.5	997.4	990.9	992.2	998.7	994.8	998.7	1006.4
20°	960.0	962.5	958.7	953.5	953.5	945.8	954.8	952.2	953.5	961.2	972.9
22.5°	925.1	923.8	920.0	916.1	910.9	912.2	913.5	910.9	921.2	927.7	929.0
25°	887.7	885.1	883.8	880.0	874.8	880.0	878.7	880.0	882.5	892.9	885.1
27.5°	852.9	847.7	850.3	846.4	845.1	846.4	846.4	847.7	850.3	851.6	852.9
30°	823.2	818.0	816.7	814.2	812.9	814.2	816.7	814.2	824.5	823.2	823.2
32.5°	790.9	787.1	784.5	784.5	783.2	781.9	783.2	784.5	792.2	787.1	792.2
35°	760.0	757.4	757.4	754.8	753.5	753.5	753.5	758.7	756.1	760.0	760.0
37.5°	730.3	730.3	729.0	726.4	725.1	726.4	725.1	727.7	726.4	727.7	729.0
40°	699.3	696.7	695.4	695.4	691.6	687.7	691.6	691.6	692.9	696.7	698.0
42.5°	661.9	663.2	663.2	658.0	658.0	658.0	659.3	660.6	660.6	663.2	663.2
45°	629.6	627.1	627.1	627.1	624.5	625.8	628.4	628.4	628.4	628.4	625.8
47.5°	593.5	593.5	594.8	594.8	598.7	597.4	597.4	596.1	593.5	593.5	594.8
50°	560.0	563.8	565.1	565.1	566.4	567.7	567.7	565.1	563.8	560.0	560.0
52.5°	527.7	530.3	532.9	536.7	539.3	538.0	538.0	535.5	530.3	529.0	527.7
55°	492.9	496.7	501.9	505.8	509.7	510.9	510.9	505.8	500.6	494.2	494.2
57.5°	460.6	464.5	473.5	477.4	482.6	482.6	480.0	476.1	468.4	463.2	459.3
60°	428.4	434.8	441.3	449.0	455.5	456.8	452.9	447.7	438.7	432.2	427.1
62.5°	393.5	400.0	412.9	420.6	425.8	425.8	425.8	419.3	407.7	398.7	390.9
65°	360.0	366.4	378.0	388.4	392.2	396.1	392.2	385.8	376.8	366.4	358.7
67.5°	325.1	332.9	344.5	352.2	357.4	361.3	358.7	353.5	341.9	327.7	322.6
70°	286.4	290.3	307.1	314.8	322.6	325.1	322.6	314.8	303.2	287.7	282.6
72.5°	250.3	254.2	269.7	276.1	282.6	285.1	281.3	276.1	265.8	251.6	245.1
75°	209.0	215.5	223.2	233.5	241.3	243.9	240.0	236.1	223.2	214.2	209.0
77.5°	165.2	171.6	181.9	191.0	198.7	197.4	192.2	193.5	179.3	169.0	165.2
80°	125.2	130.3	138.1	145.8	149.7	149.7	148.4	143.2	138.1	130.3	123.9
82.5°	86.4	92.9	99.3	104.5	104.5	105.8	103.2	101.9	96.8	90.3	89.0
85°	51.6	52.9	58.1	58.1	63.2	60.6	59.4	63.2	58.1	54.2	52.9
87.5°	23.2	21.9	23.2	23.2	21.9	24.5	24.5	23.2	24.5	23.2	23.2
90°	20.0	20.9	20.9	20.9	21.9	21.9	21.9	20.9	20.9	20.9	20.0
92.5°	101.2	92.2	77.0	74.1	72.2	70.3	72.2	74.1	77.0	92.2	101.2
95°	382.0	342.1	274.6	246.1	238.5	223.3	238.5	246.1	274.6	342.1	382.0
97.5°	689.9	632.9	575.9	526.4	500.8	489.4	500.8	526.4	575.9	632.9	689.9
100°	975.0	925.5	860.0	791.6	756.4	741.2	756.4	791.6	860.0	925.5	975.0
102.5°	1216.4	1186.9	1115.6	1071.9	1032.9	1022.5	1032.9	1071.9	1115.6	1186.9	1216.4
105°	1356.5	1351.3	1320.9	1289.5	1270.5	1259.1	1270.5	1289.5	1320.9	1351.3	1356.5
107.5°	1395.9	1416.8	1425.4	1420.6	1411.1	1401.6	1411.1	1420.6	1425.4	1416.8	1395.9
110°	1358.4	1398.8	1441.5	1459.6	1466.2	1466.2	1466.2	1459.6	1441.5	1398.8	1358.4

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1280.0	1329.4	1396.9	1431.1	1450.1	1458.6	1450.1	1431.1	1396.9	1329.4	1280.0
115°	1192.1	1243.9	1318.0	1363.6	1390.2	1402.6	1390.2	1363.6	1318.0	1243.9	1192.1
117.5°	1112.2	1161.2	1236.3	1283.8	1310.4	1318.0	1310.4	1283.8	1236.3	1161.2	1112.2
120°	1045.3	1087.1	1157.4	1203.0	1228.7	1236.3	1228.7	1203.0	1157.4	1087.1	1045.3
122.5°	991.6	1030.1	1090.9	1131.8	1157.4	1164.1	1157.4	1131.8	1090.9	1030.1	991.6
125°	948.4	982.6	1035.8	1074.7	1095.6	1105.1	1095.6	1074.7	1035.8	982.6	948.4
127.5°	911.3	943.6	992.1	1027.2	1047.2	1051.0	1047.2	1027.2	992.1	943.6	911.3
130°	873.8	904.6	952.2	983.5	1002.5	1008.2	1002.5	983.5	952.2	904.6	873.8
132.5°	833.4	862.8	910.3	941.7	958.8	965.5	958.8	941.7	910.3	862.8	833.4
135°	794.9	822.0	863.8	895.1	912.2	917.9	912.2	895.1	863.8	822.0	794.9
137.5°	754.5	778.3	816.3	845.7	861.9	868.5	861.9	845.7	816.3	778.3	754.5
140°	717.4	737.4	772.6	797.3	811.5	816.3	811.5	797.3	772.6	737.4	717.4
142.5°	685.6	702.2	730.7	750.7	764.0	767.8	764.0	750.7	730.7	702.2	685.6
145°	658.0	670.9	693.7	709.8	720.3	724.1	720.3	709.8	693.7	670.9	658.0
147.5°	634.3	644.3	663.3	676.6	683.2	685.1	683.2	676.6	663.3	644.3	634.3
150°	614.8	623.4	637.6	649.0	652.8	653.8	652.8	649.0	637.6	623.4	614.8
152.5°	598.2	604.4	615.8	624.3	628.1	629.1	628.1	624.3	615.8	604.4	598.2
155°	582.0	587.3	596.8	603.4	606.3	607.2	606.3	603.4	596.8	587.3	582.0
157.5°	566.8	571.1	578.7	584.4	587.3	587.3	587.3	584.4	578.7	571.1	566.8
160°	551.6	554.9	561.6	566.4	568.3	567.3	568.3	566.4	561.6	554.9	551.6
162.5°	537.8	540.7	545.4	549.2	549.2	549.2	549.2	549.2	545.4	540.7	537.8
165°	524.0	526.4	530.2	532.1	532.1	532.1	532.1	532.1	530.2	526.4	524.0
167.5°	511.2	513.1	515.0	516.9	516.0	516.0	516.0	516.9	515.0	513.1	511.2
170°	498.8	499.8	501.7	502.7	502.7	501.7	502.7	502.7	501.7	499.8	498.8
172.5°	488.9	489.4	489.4	491.3	489.4	488.4	489.4	491.3	489.4	489.4	488.9
175°	479.9	479.9	479.9	480.8	478.9	478.0	478.9	480.8	479.9	479.9	479.9
177.5°	474.2	474.2	473.2	474.2	471.3	471.3	471.3	474.2	473.2	474.2	474.2
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9	1519.9
2.5°	1443.8	1436.1	1445.1	1433.5	1436.1	1450.2	1449.0	1461.9	1469.6	1468.3	1474.8
5°	1348.3	1348.3	1352.2	1350.9	1363.8	1375.4	1390.9	1403.8	1418.0	1425.7	1434.8
7.5°	1254.1	1267.0	1269.6	1276.1	1291.5	1310.9	1326.4	1345.7	1366.4	1380.6	1390.9
10°	1176.7	1187.0	1197.4	1202.5	1219.3	1245.1	1267.0	1298.0	1323.8	1339.3	1353.5
12.5°	1108.3	1119.9	1125.1	1148.3	1159.9	1176.7	1207.7	1241.2	1269.6	1286.4	1298.0
15°	1059.3	1065.8	1077.4	1091.6	1103.2	1123.8	1149.6	1187.0	1214.1	1228.3	1268.3
17.5°	1018.0	1025.8	1032.2	1038.7	1056.7	1078.7	1103.2	1135.4	1170.3	1194.8	1215.4
20°	975.4	979.3	987.0	997.4	1010.3	1030.9	1052.8	1086.4	1117.4	1136.7	1163.8
22.5°	925.1	936.7	944.5	952.2	966.4	989.6	1010.3	1034.8	1073.5	1095.4	1123.8
25°	895.4	900.6	905.8	914.8	925.1	945.8	969.0	994.8	1025.8	1049.0	1073.5
27.5°	856.7	864.5	870.9	882.5	889.0	905.8	927.7	953.5	990.9	1010.3	1030.9
30°	824.5	832.2	837.4	842.5	851.6	869.6	890.3	910.9	945.8	970.3	990.9
32.5°	792.2	800.0	806.4	810.3	819.3	830.9	847.7	873.5	903.2	920.0	947.0
35°	763.8	763.8	771.6	776.7	784.5	794.8	810.3	829.6	860.6	882.5	907.1
37.5°	731.6	732.9	739.3	743.2	750.9	761.3	776.7	794.8	820.6	837.4	861.9
40°	698.0	701.9	704.5	710.9	720.0	723.8	739.3	760.0	785.8	801.2	821.9
42.5°	664.5	667.1	673.5	678.7	686.4	692.9	703.2	722.5	741.9	765.1	781.9
45°	627.1	633.5	637.4	646.4	650.3	656.7	667.1	682.5	705.8	720.0	739.3
47.5°	594.8	597.4	600.0	611.6	619.3	623.2	633.5	642.5	667.1	680.0	698.0
50°	560.0	560.0	563.8	569.0	578.0	585.8	594.8	605.1	624.5	637.4	655.5
52.5°	527.7	523.8	526.4	529.0	538.0	545.8	554.8	569.0	587.1	594.8	610.3
55°	492.9	486.4	490.3	494.2	496.7	507.1	517.4	526.4	540.6	552.2	566.4
57.5°	455.5	454.2	451.6	452.9	459.3	465.8	473.5	485.1	501.9	510.9	518.7
60°	421.9	414.2	411.6	414.2	418.0	421.9	432.2	442.6	456.8	465.8	474.8
62.5°	387.1	379.3	374.2	370.3	374.2	383.2	389.7	397.4	409.0	419.3	427.1
65°	353.5	341.9	336.8	334.2	332.9	339.3	344.5	354.8	365.1	369.0	378.0
67.5°	316.1	305.8	299.3	295.5	295.5	295.5	300.6	311.0	321.3	322.6	331.6
70°	278.7	267.1	260.6	255.5	252.9	255.5	261.9	263.2	272.2	274.8	280.0
72.5°	238.7	228.4	220.6	214.2	215.5	218.1	218.1	220.6	225.8	232.2	232.2
75°	201.3	187.1	183.2	178.1	175.5	175.5	175.5	180.6	184.5	189.7	188.4
77.5°	158.7	151.0	143.2	140.6	136.8	135.5	138.1	138.1	140.6	144.5	145.8
80°	122.6	113.5	108.4	105.8	100.6	99.3	100.6	100.6	104.5	103.2	104.5
82.5°	85.2	78.7	74.8	71.0	68.4	69.7	68.4	68.4	69.7	68.4	68.4
85°	49.0	47.7	45.2	43.9	42.6	40.0	42.6	41.3	40.0	38.7	41.3
87.5°	23.2	21.9	21.9	19.4	19.4	18.1	19.4	19.4	18.1	18.1	18.1
90°	19.0	18.1	17.1	16.2	15.2	13.3	12.4	10.5	9.5	8.6	7.6
92.5°	110.2	148.2	206.2	306.0	379.2	385.8	268.0	159.6	95.0	77.9	60.8
95°	421.9	538.8	683.2	823.9	841.9	687.0	424.8	215.7	114.0	92.6	71.3
97.5°	746.9	864.7	979.7	1029.1	909.4	630.0	346.8	186.3	115.9	100.2	84.6
100°	1024.4	1122.3	1168.8	1095.6	858.1	547.3	307.9	184.3	129.2	115.0	100.7
102.5°	1245.8	1280.0	1232.5	1055.7	767.8	484.6	291.7	192.9	145.4	131.6	117.8
105°	1361.7	1319.9	1189.7	961.7	688.9	448.5	289.8	205.3	163.4	150.1	136.8
107.5°	1375.0	1274.3	1102.3	872.3	630.0	429.5	296.5	222.4	181.5	169.6	157.7
110°	1318.0	1184.0	1003.5	798.2	591.1	421.9	306.9	241.4	202.4	190.0	177.7

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1230.6	1094.7	925.5	743.1	568.3	421.9	320.2	259.4	222.4	210.5	198.6
115°	1140.3	1010.1	862.8	706.0	553.0	424.8	333.5	278.4	243.3	231.4	219.5
117.5°	1063.3	949.3	819.1	681.3	544.5	429.5	348.7	297.4	264.2	252.8	241.4
120°	1003.5	898.9	784.9	661.4	538.8	437.1	363.9	318.3	285.1	273.2	261.3
122.5°	953.1	862.8	759.3	644.3	534.0	443.8	381.1	338.3	305.0	293.2	281.3
125°	914.1	831.5	734.5	629.1	530.2	451.4	396.3	355.4	324.0	311.6	299.3
127.5°	879.0	801.1	708.9	614.8	528.3	459.9	410.5	372.5	342.1	329.8	317.4
130°	842.9	768.8	685.1	600.6	526.4	467.5	424.8	388.7	359.2	346.8	334.5
132.5°	803.9	738.3	661.4	589.2	526.4	476.1	437.1	403.9	374.4	362.0	349.7
135°	767.8	707.0	641.4	580.6	526.4	483.7	448.5	417.2	387.7	374.8	362.0
137.5°	730.7	678.5	623.4	572.1	527.4	491.3	457.1	426.7	400.1	386.8	373.5
140°	697.5	653.8	609.1	566.4	528.3	496.0	465.6	437.1	409.6	396.8	383.9
142.5°	669.0	632.9	596.8	561.6	529.3	498.9	470.4	443.8	418.1	406.2	394.4
145°	645.2	615.8	586.3	556.8	528.3	500.8	475.1	451.4	426.7	415.8	404.8
147.5°	624.3	600.6	575.9	552.1	526.4	501.7	478.0	456.1	434.3	424.3	414.3
150°	606.3	588.2	567.3	546.4	523.6	501.7	480.8	460.9	440.0	431.9	423.8
152.5°	592.0	575.9	557.8	539.7	519.8	500.8	482.7	465.6	446.6	439.5	432.4
155°	576.8	563.5	548.3	532.1	515.0	498.9	483.7	468.5	452.3	445.6	439.0
157.5°	562.6	552.1	538.8	525.5	510.3	497.0	484.6	471.3	457.1	451.8	446.6
160°	548.3	538.8	529.3	516.9	505.5	494.1	484.6	473.2	460.9	456.6	452.3
162.5°	535.0	527.4	518.8	509.3	499.8	491.3	483.7	475.1	464.7	461.4	458.0
165°	521.7	516.0	509.3	501.7	494.1	488.4	482.7	475.1	467.5	464.6	461.8
167.5°	509.3	504.6	499.8	494.1	488.4	483.7	480.8	475.1	468.5	466.6	464.7
170°	497.9	495.1	492.2	487.5	483.7	480.8	478.9	475.1	470.4	469.0	467.5
172.5°	488.4	486.5	483.7	480.8	478.0	477.0	477.0	474.2	470.4	469.9	469.4
175°	479.9	478.0	478.0	475.1	474.2	474.2	475.1	473.2	470.4	470.4	470.4
177.5°	474.2	474.2	473.2	472.3	471.3	471.3	473.2	472.3	470.4	470.4	470.4
180°	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3	471.3

TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1519.9	1519.9	1519.9	1519.9
2.5°	1483.8	1496.7	1505.7	1522.5
5°	1450.2	1473.5	1495.4	1518.6
7.5°	1416.7	1443.8	1478.6	1508.3
10°	1379.3	1414.1	1455.4	1495.4
12.5°	1341.9	1383.2	1428.3	1481.2
15°	1296.7	1349.6	1402.5	1459.3
17.5°	1256.7	1310.9	1367.7	1438.6
20°	1211.6	1270.9	1332.8	1405.1
22.5°	1171.6	1237.4	1301.9	1378.0
25°	1126.4	1190.9	1261.9	1343.2
27.5°	1089.0	1148.3	1218.0	1305.7
30°	1043.8	1108.3	1178.0	1265.7
32.5°	1001.2	1063.2	1136.7	1223.2
35°	957.4	1020.6	1086.4	1169.0
37.5°	916.1	970.3	1036.1	1114.8
40°	869.6	929.0	988.3	1050.3
42.5°	827.1	881.2	936.7	985.8
45°	779.3	825.8	878.7	918.7
47.5°	735.4	776.7	818.0	849.0
50°	691.6	723.8	754.8	781.9
52.5°	640.0	676.1	692.9	709.6
55°	593.5	614.2	629.6	646.4
57.5°	548.4	557.4	565.1	580.6
60°	489.0	499.3	508.4	520.0
62.5°	437.4	442.6	445.1	456.8
65°	388.4	387.1	393.5	400.0
67.5°	335.5	334.2	340.6	343.2
70°	283.9	282.6	283.9	290.3
72.5°	234.8	234.8	236.1	238.7
75°	189.7	189.7	191.0	193.5
77.5°	143.2	145.8	144.5	149.7
80°	104.5	101.9	104.5	107.1
82.5°	68.4	71.0	71.0	68.4
85°	38.7	38.7	38.7	38.7
87.5°	16.8	16.8	18.1	19.4
90°	5.7	3.8	1.9	1.0
92.5°	40.9	26.6	17.1	14.3
95°	50.4	39.9	32.3	31.4
97.5°	65.6	55.1	49.4	48.5
100°	82.7	72.2	68.4	66.5
102.5°	101.7	90.3	87.4	86.5
105°	121.6	112.1	107.4	107.4
107.5°	141.6	134.0	129.2	127.3
110°	163.4	154.9	151.1	149.2



TEST NUMBER: P1027342

CATALOG NUMBER: S125DIP-B1090D1090UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	184.3	175.8	172.9	171.0
115°	205.3	196.7	193.9	192.0
117.5°	225.2	216.7	213.8	211.0
120°	245.2	236.6	232.8	230.0
122.5°	263.2	254.7	251.8	249.9
125°	281.3	272.7	268.0	266.1
127.5°	298.4	287.9	282.2	279.4
130°	314.5	302.2	294.6	291.7
132.5°	328.8	314.5	305.0	301.2
135°	342.1	326.9	315.5	311.7
137.5°	353.5	338.3	327.8	325.0
140°	365.8	350.6	339.2	336.4
142.5°	377.3	362.0	351.6	349.7
145°	387.7	374.4	364.9	363.0
147.5°	399.1	386.8	378.2	377.3
150°	410.5	398.2	391.5	389.6
152.5°	420.0	409.6	403.9	402.9
155°	429.5	420.0	414.3	414.3
157.5°	438.1	429.5	424.8	424.8
160°	444.7	438.1	434.3	435.2
162.5°	452.3	446.6	442.8	443.8
165°	458.0	453.3	450.4	452.3
167.5°	461.8	459.0	457.1	458.0
170°	465.6	463.7	462.8	463.7
172.5°	468.5	466.6	465.6	467.5
175°	470.4	469.4	468.5	470.4
177.5°	471.3	470.4	470.4	472.3
180°	471.3	471.3	471.3	471.3

(END OF REPORT)