

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027513

Luminaire Tested: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027513
REPORT IS A COMBINATION OF REPORTS P1001503 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1090D850UB40-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7265.0 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	96	92	89	94	90	87	84	79	76	74	69	67	65	59	58	57
2	92	84	78	73	86	79	74	69	70	65	62	61	57	55	52	50	48
3	84	74	67	61	78	70	63	58	62	56	52	54	50	47	47	44	41
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	38	36
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31
6	65	53	45	39	61	50	43	37	44	38	34	39	34	31	34	30	27
7	60	48	40	34	56	45	38	33	40	34	30	36	31	27	31	27	24
8	56	44	36	30	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	26	23	20
10	49	37	29	24	46	35	28	23	31	25	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10077	11423	10086	8666
10°	10016	13020	9998	7439
15°	9943	14117	9881	6722
20°	9817	15470	9727	6136
25°	9706	17726	9528	5790
30°	9545	18701	9380	5476
35°	9292	14991	9097	5224
40°	8897	10361	8765	4957
45°	8397	7714	8303	4736
50°	7826	6351	7697	4558
55°	7209	5416	7152	4404
60°	6604	4636	6489	4285
65°	5951	4003	5855	4111
70°	5262	3324	5192	3807
75°	4531	2570	4472	3306
80°	3577	1738	3448	2430
85°	2287	869	2213	1239

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 15381 cd/sqm

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.1
10°-20°	450.6	6.2
20°-30°	731.9	10.1
30°-40°	894.4	12.3
40°-50°	811.3	11.2
50°-60°	646.2	8.9
60°-70°	450.1	6.2
70°-80°	239.8	3.3
80°-90°	60.9	0.8
90°-100°	273.9	3.8
100°-110°	590.7	8.1
110°-120°	550.7	7.6
120°-130°	446.0	6.1
130°-140°	358.2	4.9
140°-150°	270.1	3.7
150°-160°	190.2	2.6
160°-170°	112.1	1.5
170°-180°	36.5	0.5
0°-30°	1333.7	18.4
0°-40°	2228.1	30.7
0°-60°	3685.7	50.7
0°-90°	4436.5	61.1
90°-120°	1415.4	19.5
90°-150°	2489.7	34.3
90°-180°	2829.0	38.9
0°-180°	7265.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1570	1813	1572	1376	1570	149
15°	1509	2264	1500	1078	1509	426
25°	1389	2786	1364	910	1389	640
35°	1209	2236	1183	779	1209	755
45°	950	1054	939	647	950	732
55°	668	650	663	528	668	598
65°	414	399	407	410	414	410
75°	200	196	198	252	200	213
85°	40	44	39	63	40	48
90°	1	18	1	18	1	5
95°	25	178	25	178	25	26
105°	86	1006	86	1006	86	90
115°	153	1121	153	1121	153	151
125°	213	883	213	883	213	189
135°	249	733	249	733	249	193
145°	290	578	290	578	290	182
155°	331	485	331	485	331	152
165°	361	425	361	425	361	102
175°	376	382	376	382	376	36
180°	377	377	377	377	377	

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1574.3	1583.7	1594.3	1602.3	1615.7	1619.7	1626.4	1630.4	1634.4	1638.4	1641.0
5°	1570.3	1593.0	1613.0	1627.7	1653.0	1662.4	1674.4	1689.1	1706.4	1721.1	1730.4
7.5°	1559.7	1595.7	1622.4	1651.7	1686.4	1709.1	1721.1	1751.8	1779.8	1801.1	1829.2
10°	1546.3	1589.0	1630.4	1674.4	1723.8	1749.1	1773.1	1815.8	1854.5	1889.2	1917.2
12.5°	1531.6	1583.7	1633.0	1690.4	1757.1	1787.8	1803.8	1877.2	1925.2	1943.9	1998.6
15°	1509.0	1570.3	1641.0	1711.7	1767.8	1803.8	1847.8	1906.5	1954.6	1995.9	2040.0
17.5°	1487.6	1554.3	1626.4	1705.1	1786.5	1833.2	1866.5	1918.5	1970.6	2023.9	2065.3
20°	1452.9	1539.6	1613.0	1697.1	1793.1	1826.5	1861.2	1922.5	1978.6	2036.0	2088.0
22.5°	1424.9	1507.6	1607.7	1687.7	1769.1	1802.5	1845.2	1909.2	1975.9	2041.3	2117.3
25°	1388.9	1480.9	1567.7	1653.0	1737.1	1773.1	1811.8	1894.5	1963.9	2048.0	2132.0
27.5°	1350.2	1444.9	1531.6	1609.0	1687.7	1737.1	1778.5	1865.2	1957.2	2049.3	2158.7
30°	1308.8	1398.2	1480.9	1557.0	1643.7	1694.4	1735.8	1837.2	1939.9	2057.3	2188.1
32.5°	1264.8	1348.9	1419.6	1496.9	1589.0	1635.7	1691.7	1802.5	1923.9	2064.0	2228.1
35°	1208.8	1288.8	1351.5	1430.2	1522.3	1582.3	1641.0	1765.1	1906.5	2062.6	2250.8
37.5°	1152.7	1215.4	1275.5	1359.5	1466.3	1521.0	1582.3	1718.4	1879.9	2058.6	2260.1
40°	1086.0	1147.4	1199.4	1284.8	1396.9	1459.6	1523.6	1666.4	1849.2	2044.0	2226.7
42.5°	1019.3	1071.3	1128.7	1218.1	1326.2	1392.9	1460.9	1619.7	1809.1	2001.3	2134.7
45°	949.9	990.0	1052.7	1134.1	1248.8	1312.8	1390.2	1562.3	1753.1	1923.9	1990.6
47.5°	877.9	917.9	976.6	1055.3	1168.7	1244.8	1318.2	1490.3	1682.4	1814.5	1814.5
50°	808.5	840.5	897.9	976.6	1091.4	1160.7	1235.4	1418.2	1573.0	1670.4	1583.7
52.5°	733.8	769.8	817.9	900.6	1014.0	1076.7	1158.1	1314.2	1460.9	1500.9	1367.5
55°	668.4	697.8	743.1	821.9	927.3	992.6	1062.0	1211.4	1335.5	1332.8	1190.1
57.5°	600.4	624.4	672.4	744.5	841.9	900.6	969.9	1099.4	1200.8	1164.7	1030.0
60°	537.7	555.0	601.7	660.4	753.8	808.5	875.2	980.6	1058.0	1007.3	871.2
62.5°	472.3	492.3	529.7	587.0	669.8	713.8	763.1	869.9	919.2	873.9	735.1
65°	413.6	429.6	463.0	511.0	585.7	625.7	668.4	756.5	803.2	737.8	623.1
67.5°	354.9	373.6	397.6	440.3	499.0	536.3	573.7	649.7	671.1	612.4	516.3
70°	300.2	316.2	338.9	369.6	418.9	452.3	480.3	543.0	557.7	503.0	426.9
72.5°	246.8	257.5	276.2	301.5	346.9	365.6	394.9	437.6	456.3	406.9	352.2
75°	200.1	208.1	220.1	238.8	269.5	289.5	313.5	353.6	352.2	317.5	278.8
77.5°	154.8	156.1	169.4	186.8	205.5	222.8	234.8	262.8	265.5	244.2	212.1
80°	110.7	114.7	120.1	133.4	149.4	156.1	170.8	188.1	190.8	174.8	153.4
82.5°	70.7	73.4	77.4	85.4	96.1	104.1	112.1	118.7	125.4	116.1	98.7
85°	40.0	41.4	45.4	48.0	53.4	57.4	64.0	70.7	69.4	62.7	57.4
87.5°	20.0	20.0	20.0	22.7	25.3	25.3	28.0	29.4	30.7	28.0	25.3
90°	0.8	1.5	3.0	4.6	6.1	6.8	7.6	8.4	9.9	10.6	12.1
92.5°	11.4	13.7	21.3	32.6	48.6	62.2	75.9	127.6	214.1	308.3	302.9
95°	25.1	25.8	31.9	40.2	56.9	74.0	91.1	172.3	339.4	548.9	672.7
97.5°	38.7	39.5	44.0	52.4	67.6	80.1	92.6	148.8	277.1	503.4	726.6
100°	53.1	54.7	57.7	66.1	80.5	91.9	103.3	147.3	246.0	437.3	685.6
102.5°	69.1	69.8	72.1	81.2	94.1	105.2	116.2	154.1	233.1	387.2	613.5
105°	85.8	85.8	89.6	97.2	109.3	120.0	130.6	164.0	231.6	358.4	550.4
107.5°	101.7	103.3	107.1	113.1	126.0	135.5	145.0	177.7	236.9	343.2	503.4
110°	119.2	120.7	123.8	130.6	142.0	151.8	161.7	192.8	245.2	337.1	472.2

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	136.7	138.2	140.5	147.3	158.7	168.2	177.7	207.3	255.9	337.1	454.0
115°	153.4	154.9	157.2	164.0	175.4	184.9	194.4	222.5	266.5	339.4	441.9
117.5°	168.6	170.8	173.1	179.9	192.8	202.0	211.1	237.6	278.6	343.2	435.0
120°	183.7	186.0	189.1	195.9	208.8	218.3	227.8	254.3	290.8	349.2	430.5
122.5°	199.7	201.2	203.5	210.3	224.7	234.2	243.7	270.3	304.5	354.6	426.7
125°	212.6	214.1	217.9	224.7	239.2	249.0	258.9	284.0	316.6	360.6	423.7
127.5°	223.2	225.5	230.0	238.4	253.6	263.4	273.3	297.6	328.0	367.5	422.1
130°	233.1	235.4	241.4	251.3	267.3	277.2	287.0	310.5	339.4	373.5	420.6
132.5°	240.7	243.7	251.3	262.7	279.4	289.2	299.1	322.7	349.2	380.4	420.6
135°	249.0	252.1	261.2	273.3	289.3	299.6	309.8	333.3	358.4	386.5	420.6
137.5°	259.7	261.9	270.3	282.4	298.4	309.0	319.6	340.9	365.2	392.5	421.4
140°	268.8	271.0	280.2	292.3	306.7	317.0	327.2	349.2	372.0	396.3	422.1
142.5°	279.4	280.9	289.3	301.4	315.1	324.6	334.1	354.6	375.8	398.6	422.9
145°	290.0	291.5	299.1	309.8	323.4	332.2	340.9	360.6	379.6	400.1	422.1
147.5°	301.4	302.2	309.0	318.9	331.0	339.0	347.0	364.4	381.9	400.9	420.6
150°	311.3	312.8	318.1	328.0	338.6	345.0	351.5	368.2	384.2	400.9	418.3
152.5°	321.9	322.7	327.2	335.6	345.5	351.2	356.8	372.0	385.7	400.1	415.3
155°	331.0	331.0	335.6	343.2	350.8	356.1	361.4	374.3	386.5	398.6	411.5
157.5°	339.4	339.4	343.2	350.0	356.8	361.0	365.2	376.6	387.2	397.1	407.7
160°	347.7	347.0	350.0	355.3	361.4	364.8	368.2	378.1	387.2	394.8	403.9
162.5°	354.6	353.8	356.8	361.4	366.0	368.6	371.3	379.6	386.5	392.5	399.4
165°	361.4	359.9	362.2	366.0	369.0	371.2	373.5	379.6	385.7	390.2	394.8
167.5°	366.0	365.2	366.7	369.0	371.3	372.8	374.3	379.6	384.2	386.5	390.2
170°	370.5	369.7	370.5	372.0	373.5	374.6	375.8	379.6	382.7	384.2	386.5
172.5°	373.5	372.0	372.8	374.3	375.1	375.5	375.8	378.9	381.1	381.1	381.9
175°	375.8	374.3	375.1	375.8	375.8	375.8	375.8	378.1	379.6	378.9	378.9
177.5°	377.3	375.8	375.8	376.6	375.8	375.8	375.8	377.3	378.1	376.6	376.6
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1643.7	1653.0	1661.1	1667.7	1673.1	1681.1	1675.7	1677.1	1679.7	1685.1	1685.1
5°	1750.4	1765.1	1773.1	1799.8	1806.5	1805.1	1801.1	1822.5	1821.2	1813.1	1811.8
7.5°	1854.5	1879.9	1902.5	1923.9	1930.6	1947.9	1951.9	1961.2	1958.6	1971.9	1965.2
10°	1949.2	1989.3	2010.6	2042.6	2050.6	2058.6	2069.3	2074.6	2086.7	2085.3	2085.3
12.5°	2022.6	2070.6	2098.7	2106.7	2137.4	2146.7	2156.0	2173.4	2169.4	2170.7	2178.7
15°	2080.0	2126.7	2150.7	2188.1	2209.4	2220.1	2236.1	2254.8	2252.1	2264.1	2261.4
17.5°	2122.7	2166.7	2210.7	2266.8	2268.1	2296.1	2333.5	2341.5	2358.8	2346.8	2346.8
20°	2157.4	2216.1	2278.8	2350.8	2358.8	2376.2	2421.5	2452.2	2472.2	2465.6	2469.6
22.5°	2194.7	2278.8	2352.2	2424.2	2462.9	2493.6	2537.6	2585.6	2603.0	2613.7	2611.0
25°	2242.8	2330.8	2438.9	2538.9	2579.0	2637.7	2696.4	2743.1	2756.4	2785.8	2759.1
27.5°	2292.1	2416.2	2550.9	2668.4	2719.1	2767.1	2837.8	2872.5	2889.8	2903.2	2893.8
30°	2333.5	2504.3	2651.0	2759.1	2795.1	2823.1	2863.1	2871.1	2864.5	2875.2	2888.5
32.5°	2397.5	2564.3	2688.4	2740.4	2736.4	2735.1	2704.4	2661.7	2652.3	2627.0	2661.7
35°	2432.2	2565.6	2613.7	2544.3	2516.3	2465.6	2368.2	2304.1	2248.1	2236.1	2238.7
37.5°	2412.2	2464.2	2406.9	2224.1	2178.7	2101.3	1971.9	1881.2	1839.8	1807.8	1849.2
40°	2304.1	2246.8	2089.3	1866.5	1801.1	1727.8	1606.3	1557.0	1498.3	1486.3	1541.0
42.5°	2125.3	1950.6	1727.8	1555.7	1487.6	1446.2	1344.9	1298.2	1256.8	1238.1	1268.8
45°	1882.5	1670.4	1446.2	1304.8	1247.5	1198.1	1138.1	1088.7	1062.0	1054.0	1079.3
47.5°	1631.7	1407.6	1228.8	1123.4	1063.3	1026.0	969.9	941.9	920.6	923.3	927.3
50°	1391.5	1187.4	1050.0	944.6	915.2	885.9	848.5	824.5	813.8	817.9	815.2
52.5°	1184.7	1019.3	903.2	821.9	808.5	780.5	749.8	729.8	725.8	727.1	731.1
55°	1003.3	873.9	781.8	723.1	708.4	688.4	669.8	656.4	645.7	649.7	648.4
57.5°	865.9	752.5	681.8	633.7	623.1	611.1	593.7	587.0	583.0	575.0	581.7
60°	744.5	652.4	591.0	561.7	552.3	544.3	525.7	517.7	515.0	511.0	521.7
62.5°	629.7	564.4	517.7	491.0	481.6	473.6	464.3	457.6	459.0	453.6	459.0
65°	539.0	485.6	452.3	428.3	416.3	410.9	409.6	398.9	397.6	398.9	400.3
67.5°	455.0	409.6	384.2	369.6	360.2	354.9	350.9	344.2	349.6	345.6	348.2
70°	378.9	348.2	321.5	306.9	302.9	304.2	297.5	294.9	296.2	293.5	296.2
72.5°	305.5	280.2	269.5	258.8	253.5	252.2	248.2	244.2	248.2	246.8	246.8
75°	244.2	225.5	213.5	206.8	206.8	204.1	197.5	197.5	197.5	196.1	197.5
77.5°	188.1	172.1	166.8	160.1	160.1	156.1	154.8	154.8	152.1	156.1	153.4
80°	140.1	128.1	120.1	116.1	116.1	114.7	112.1	110.7	112.1	110.7	110.7
82.5°	90.7	85.4	81.4	77.4	76.0	77.4	76.0	73.4	74.7	73.4	76.0
85°	52.0	46.7	46.7	44.0	45.4	42.7	44.0	41.4	40.0	44.0	41.4
87.5°	22.7	21.3	21.3	18.7	18.7	18.7	17.3	18.7	17.3	16.0	17.3
90°	12.9	13.7	14.4	15.2	16.0	16.7	16.7	16.7	17.5	17.5	17.5
92.5°	244.5	164.8	118.4	88.1	80.8	73.6	61.5	59.2	57.7	56.2	57.7
95°	658.3	545.9	430.5	337.1	305.2	273.3	219.4	196.6	190.6	178.4	190.6
97.5°	822.3	782.8	690.9	596.8	551.2	505.7	460.1	420.6	400.1	391.0	400.1
100°	875.4	933.9	896.7	818.5	779.0	739.5	687.1	632.4	604.4	592.2	604.4
102.5°	843.5	984.7	1022.7	995.4	971.8	948.3	891.3	856.4	825.3	816.9	825.3
105°	768.3	950.6	1054.6	1088.0	1083.8	1079.6	1055.3	1030.3	1015.1	1006.0	1015.1
107.5°	697.0	880.7	1018.1	1098.6	1115.3	1132.0	1138.9	1135.1	1127.5	1119.9	1127.5
110°	637.8	801.8	946.0	1053.1	1085.4	1117.6	1151.8	1166.2	1171.5	1171.5	1171.5

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	593.7	739.5	874.6	983.2	1022.7	1062.2	1116.1	1143.4	1158.6	1165.4	1158.6
115°	564.1	689.4	807.1	911.1	952.4	993.8	1053.1	1089.5	1110.8	1120.6	1110.8
117.5°	544.4	654.5	758.5	849.6	888.7	927.8	987.8	1025.7	1047.0	1053.1	1047.0
120°	528.4	627.1	718.2	801.8	835.2	868.6	924.8	961.2	981.7	987.8	981.7
122.5°	514.8	606.6	689.4	761.5	792.2	823.0	871.6	904.3	924.8	930.1	924.8
125°	502.6	586.9	664.3	730.4	757.8	785.1	827.6	858.7	875.4	883.0	875.4
127.5°	491.2	566.4	640.0	702.3	728.1	753.9	792.6	820.7	836.7	839.7	836.7
130°	479.8	547.4	614.2	673.4	698.1	722.8	760.8	785.8	801.0	805.6	801.0
132.5°	470.7	528.4	589.9	642.3	665.8	689.4	727.4	752.4	766.1	771.4	766.1
135°	463.9	512.5	564.9	613.5	635.1	656.7	690.1	715.2	728.9	733.4	728.9
137.5°	457.1	498.1	542.1	583.9	602.8	621.8	652.2	675.7	688.6	693.9	688.6
140°	452.5	486.7	522.4	557.3	573.2	589.2	617.3	637.0	648.4	652.2	648.4
142.5°	448.7	476.8	505.7	534.5	547.8	561.1	583.9	599.8	610.4	613.5	610.4
145°	444.9	468.5	492.0	515.5	525.8	536.0	554.2	567.2	575.5	578.5	575.5
147.5°	441.1	460.1	479.8	498.8	506.8	514.8	529.9	540.6	545.9	547.4	545.9
150°	436.6	453.3	470.0	484.4	491.2	498.1	509.4	518.6	521.6	522.4	521.6
152.5°	431.2	445.7	460.1	473.0	478.0	482.9	492.0	498.8	501.9	502.6	501.9
155°	425.2	438.1	450.2	460.9	465.0	469.2	476.8	482.1	484.4	485.2	484.4
157.5°	419.9	430.5	441.1	449.5	452.9	456.3	462.4	466.9	469.2	469.2	469.2
160°	413.0	422.9	430.5	438.1	440.8	443.4	448.7	452.5	454.0	453.3	454.0
162.5°	407.0	414.5	421.4	427.5	429.8	432.0	435.8	438.8	438.8	438.8	438.8
165°	400.9	407.0	412.3	416.8	418.7	420.6	423.7	425.2	425.2	425.2	425.2
167.5°	394.8	399.4	403.2	407.0	408.5	410.0	411.5	413.0	412.3	412.3	412.3
170°	389.5	393.3	395.6	397.8	398.6	399.4	400.9	401.6	401.6	400.9	401.6
172.5°	384.2	386.5	388.7	390.2	390.6	391.0	391.0	392.5	391.0	390.2	391.0
175°	379.6	381.9	381.9	383.4	383.4	383.4	383.4	384.2	382.7	381.9	382.7
177.5°	377.3	378.1	378.9	378.9	378.9	378.9	378.1	378.9	376.6	376.6	376.6
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1682.4	1673.1	1675.7	1673.1	1666.4	1662.4	1651.7	1638.4	1633.0	1626.4	1622.4
5°	1817.1	1810.5	1809.1	1798.5	1795.8	1779.8	1753.1	1739.8	1723.8	1707.7	1691.7
7.5°	1963.9	1955.9	1929.2	1925.2	1927.9	1907.9	1873.2	1846.5	1813.1	1790.5	1759.8
10°	2085.3	2069.3	2046.6	2048.0	2038.6	2011.9	1977.3	1949.2	1901.2	1871.9	1827.8
12.5°	2158.7	2145.4	2142.7	2129.3	2121.3	2086.7	2045.3	2009.3	1973.2	1933.2	1899.9
15°	2248.1	2230.7	2218.7	2200.1	2194.7	2158.7	2113.3	2072.0	2030.6	1993.3	1922.5
17.5°	2346.8	2328.1	2282.8	2278.8	2246.8	2212.1	2168.0	2106.7	2062.6	2009.3	1957.2
20°	2458.9	2432.2	2373.5	2358.8	2333.5	2276.1	2216.1	2148.0	2077.3	2022.6	1961.2
22.5°	2584.3	2537.6	2494.9	2448.2	2429.5	2358.8	2276.1	2193.4	2108.0	2033.3	1959.9
25°	2747.1	2685.7	2625.7	2579.0	2546.9	2454.9	2344.1	2234.7	2136.0	2038.6	1942.6
27.5°	2875.2	2821.8	2756.4	2695.0	2653.7	2544.3	2417.5	2276.1	2153.4	2034.6	1931.9
30°	2884.5	2868.5	2828.5	2795.1	2749.7	2632.3	2492.2	2332.1	2180.0	2036.0	1910.5
32.5°	2709.7	2741.7	2759.1	2764.4	2755.1	2687.0	2559.0	2382.8	2204.1	2023.9	1891.9
35°	2333.5	2418.9	2524.3	2564.3	2603.0	2639.0	2572.3	2418.9	2212.1	2021.3	1862.5
37.5°	1921.2	1998.6	2173.4	2253.4	2298.8	2441.5	2496.2	2413.5	2228.1	2023.9	1834.5
40°	1550.3	1673.1	1798.5	1906.5	1977.3	2137.4	2306.8	2325.5	2205.4	1998.6	1798.5
42.5°	1304.8	1376.9	1471.6	1571.7	1634.4	1823.8	2053.3	2188.1	2134.7	1957.2	1754.4
45°	1111.4	1164.7	1254.1	1287.5	1367.5	1549.0	1791.8	1986.6	2013.3	1891.9	1703.7
47.5°	953.9	999.3	1056.7	1098.0	1162.1	1298.2	1503.6	1718.4	1846.5	1802.5	1633.0
50°	840.5	877.9	925.9	949.9	991.3	1114.0	1268.8	1482.3	1654.4	1669.1	1541.0
52.5°	745.8	767.2	804.5	831.2	864.5	939.3	1079.3	1255.5	1448.9	1529.0	1427.6
55°	663.1	680.4	713.8	731.1	748.5	812.5	921.9	1082.0	1263.5	1368.9	1311.5
57.5°	588.4	603.0	631.1	647.1	656.4	717.8	801.8	927.3	1090.0	1218.1	1186.1
60°	527.0	540.3	556.4	568.4	579.0	629.7	688.4	789.8	935.3	1059.3	1051.3
62.5°	461.6	473.6	491.0	503.0	512.3	544.3	593.7	671.1	795.2	909.9	932.6
65°	404.3	413.6	425.6	430.9	442.9	467.0	507.0	576.4	677.8	780.5	796.5
67.5°	352.2	354.9	362.9	374.9	377.6	398.9	434.9	487.0	565.7	649.7	675.1
70°	296.2	300.2	306.9	316.2	321.5	334.9	365.6	400.3	468.3	541.7	560.4
72.5°	246.8	252.2	254.8	260.2	262.8	284.2	297.5	332.2	378.9	440.3	460.3
75°	200.1	205.5	206.8	209.5	212.1	221.5	240.2	261.5	300.2	340.2	366.9
77.5°	158.8	157.4	160.1	164.1	162.8	170.8	182.8	201.5	226.8	260.2	277.5
80°	112.1	112.1	116.1	120.1	118.7	126.7	130.7	144.1	165.4	186.8	193.5
82.5°	74.7	74.7	78.7	78.7	81.4	82.7	88.1	94.7	112.1	122.7	126.7
85°	42.7	42.7	44.0	44.0	44.0	46.7	50.7	53.4	58.7	65.4	68.0
87.5°	17.3	18.7	18.7	18.7	18.7	21.3	21.3	24.0	25.3	28.0	28.0
90°	16.7	16.7	16.7	16.0	15.2	14.4	13.7	12.9	12.1	10.6	9.9
92.5°	59.2	61.5	73.6	80.8	88.1	118.4	164.8	244.5	302.9	308.3	214.1
95°	196.6	219.4	273.3	305.2	337.1	430.5	545.9	658.3	672.7	548.9	339.4
97.5°	420.6	460.1	505.7	551.2	596.8	690.9	782.8	822.3	726.6	503.4	277.1
100°	632.4	687.1	739.5	779.0	818.5	896.7	933.9	875.4	685.6	437.3	246.0
102.5°	856.4	891.3	948.3	971.8	995.4	1022.7	984.7	843.5	613.5	387.2	233.1
105°	1030.3	1055.3	1079.6	1083.8	1088.0	1054.6	950.6	768.3	550.4	358.4	231.6
107.5°	1135.1	1138.9	1132.0	1115.3	1098.6	1018.1	880.7	697.0	503.4	343.2	236.9
110°	1166.2	1151.8	1117.6	1085.4	1053.1	946.0	801.8	637.8	472.2	337.1	245.2

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1143.4	1116.1	1062.2	1022.7	983.2	874.6	739.5	593.7	454.0	337.1	255.9
115°	1089.5	1053.1	993.8	952.4	911.1	807.1	689.4	564.1	441.9	339.4	266.5
117.5°	1025.7	987.8	927.8	888.7	849.6	758.5	654.5	544.4	435.0	343.2	278.6
120°	961.2	924.8	868.6	835.2	801.8	718.2	627.1	528.4	430.5	349.2	290.8
122.5°	904.3	871.6	823.0	792.2	761.5	689.4	606.6	514.8	426.7	354.6	304.5
125°	858.7	827.6	785.1	757.8	730.4	664.3	586.9	502.6	423.7	360.6	316.6
127.5°	820.7	792.6	753.9	728.1	702.3	640.0	566.4	491.2	422.1	367.5	328.0
130°	785.8	760.8	722.8	698.1	673.4	614.2	547.4	479.8	420.6	373.5	339.4
132.5°	752.4	727.4	689.4	665.8	642.3	589.9	528.4	470.7	420.6	380.4	349.2
135°	715.2	690.1	656.7	635.1	613.5	564.9	512.5	463.9	420.6	386.5	358.4
137.5°	675.7	652.2	621.8	602.8	583.9	542.1	498.1	457.1	421.4	392.5	365.2
140°	637.0	617.3	589.2	573.2	557.3	522.4	486.7	452.5	422.1	396.3	372.0
142.5°	599.8	583.9	561.1	547.8	534.5	505.7	476.8	448.7	422.9	398.6	375.8
145°	567.2	554.2	536.0	525.8	515.5	492.0	468.5	444.9	422.1	400.1	379.6
147.5°	540.6	529.9	514.8	506.8	498.8	479.8	460.1	441.1	420.6	400.9	381.9
150°	518.6	509.4	498.1	491.2	484.4	470.0	453.3	436.6	418.3	400.9	384.2
152.5°	498.8	492.0	482.9	478.0	473.0	460.1	445.7	431.2	415.3	400.1	385.7
155°	482.1	476.8	469.2	465.0	460.9	450.2	438.1	425.2	411.5	398.6	386.5
157.5°	466.9	462.4	456.3	452.9	449.5	441.1	430.5	419.9	407.7	397.1	387.2
160°	452.5	448.7	443.4	440.8	438.1	430.5	422.9	413.0	403.9	394.8	387.2
162.5°	438.8	435.8	432.0	429.8	427.5	421.4	414.5	407.0	399.4	392.5	386.5
165°	425.2	423.7	420.6	418.7	416.8	412.3	407.0	400.9	394.8	390.2	385.7
167.5°	413.0	411.5	410.0	408.5	407.0	403.2	399.4	394.8	390.2	386.5	384.2
170°	401.6	400.9	399.4	398.6	397.8	395.6	393.3	389.5	386.5	384.2	382.7
172.5°	392.5	391.0	391.0	390.6	390.2	388.7	386.5	384.2	381.9	381.1	381.1
175°	384.2	383.4	383.4	383.4	383.4	381.9	381.9	379.6	378.9	378.9	379.6
177.5°	378.9	378.1	378.9	378.9	378.9	378.9	378.1	377.3	376.6	376.6	378.1
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1617.0	1610.4	1602.3	1602.3	1593.0	1589.0	1581.0	1578.3	1571.7	1561.0	1553.0
5°	1674.4	1657.0	1646.4	1637.0	1617.0	1602.3	1587.7	1571.7	1555.7	1537.0	1515.6
7.5°	1730.4	1698.4	1683.7	1667.7	1638.4	1607.7	1578.3	1557.0	1535.6	1506.3	1479.6
10°	1789.1	1749.1	1722.4	1701.1	1655.7	1617.0	1574.3	1543.6	1510.3	1472.9	1438.2
12.5°	1838.5	1786.5	1763.8	1723.8	1671.7	1625.0	1571.7	1525.0	1480.9	1436.9	1394.2
15°	1879.9	1830.5	1774.5	1758.4	1686.4	1619.7	1559.7	1499.6	1444.9	1400.9	1351.5
17.5°	1893.2	1830.5	1802.5	1763.8	1678.4	1609.0	1533.0	1467.6	1415.6	1350.2	1311.5
20°	1897.2	1837.2	1798.5	1762.4	1686.4	1594.3	1519.6	1439.6	1376.9	1311.5	1250.1
22.5°	1886.5	1815.8	1778.5	1743.8	1658.4	1579.7	1492.9	1404.9	1331.5	1271.5	1210.1
25°	1866.5	1783.8	1747.8	1710.4	1629.0	1542.3	1447.6	1363.5	1295.5	1223.4	1163.4
27.5°	1839.8	1745.1	1703.7	1665.1	1585.0	1503.6	1414.2	1327.5	1251.5	1175.4	1119.4
30°	1806.5	1697.1	1659.7	1609.0	1531.6	1454.3	1372.9	1286.1	1200.8	1128.7	1067.3
32.5°	1763.8	1649.0	1599.7	1551.6	1467.6	1396.9	1319.5	1238.1	1155.4	1084.7	1020.6
35°	1725.1	1594.3	1539.6	1491.6	1398.2	1323.5	1259.5	1183.4	1110.0	1036.7	979.3
37.5°	1673.1	1539.6	1474.3	1424.9	1330.2	1254.1	1194.1	1135.4	1058.0	987.3	933.9
40°	1618.4	1471.6	1410.2	1360.9	1262.1	1179.4	1122.0	1070.0	1007.3	941.9	885.9
42.5°	1569.0	1406.2	1340.8	1280.8	1180.7	1107.4	1048.7	1008.6	951.3	892.6	841.9
45°	1506.3	1336.8	1266.1	1203.4	1107.4	1027.3	971.3	939.3	896.6	839.2	795.2
47.5°	1442.2	1262.1	1188.8	1127.4	1023.3	952.6	897.9	867.2	837.9	792.5	748.5
50°	1358.2	1183.4	1116.7	1046.0	943.3	871.2	825.9	795.2	772.5	740.5	703.1
52.5°	1266.1	1102.0	1030.0	968.6	867.2	801.8	749.8	732.5	709.8	685.8	653.7
55°	1168.7	1014.0	944.6	884.6	791.2	724.5	681.8	663.1	645.7	627.1	605.7
57.5°	1071.3	921.9	856.5	803.2	716.5	652.4	617.7	592.4	580.4	569.7	552.3
60°	949.9	823.2	772.5	724.5	639.1	580.4	547.0	528.3	517.7	512.3	504.3
62.5°	843.2	739.1	683.1	636.4	568.4	516.3	484.3	469.6	460.3	457.6	448.3
65°	729.8	640.4	596.4	556.4	497.6	451.0	424.3	406.9	400.3	398.9	398.9
67.5°	623.1	551.0	507.0	479.0	428.3	386.9	361.6	354.9	350.9	345.6	344.2
70°	523.0	465.6	426.9	402.9	357.6	326.9	306.9	296.2	296.2	292.2	289.5
72.5°	434.9	377.6	352.2	332.2	294.9	268.2	253.5	250.8	241.5	240.2	240.2
75°	340.2	297.5	280.2	262.8	234.8	216.1	204.1	197.5	192.1	192.1	193.5
77.5°	256.2	226.8	210.8	197.5	177.4	165.4	156.1	153.4	148.1	148.1	148.1
80°	181.4	165.4	153.4	142.8	128.1	117.4	112.1	106.7	106.7	105.4	106.7
82.5°	117.4	104.1	97.4	96.1	82.7	78.7	72.0	73.4	69.4	68.0	70.7
85°	68.0	61.4	53.4	50.7	45.4	40.0	37.4	38.7	37.4	36.0	37.4
87.5°	26.7	22.7	21.3	21.3	17.3	16.0	14.7	16.0	13.3	13.3	14.7
90°	8.4	7.6	6.8	6.1	4.6	3.0	1.5	0.8	1.5	3.0	4.6
92.5°	127.6	75.9	62.2	48.6	32.6	21.3	13.7	11.4	13.7	21.3	32.6
95°	172.3	91.1	74.0	56.9	40.2	31.9	25.8	25.1	25.8	31.9	40.2
97.5°	148.8	92.6	80.1	67.6	52.4	44.0	39.5	38.7	39.5	44.0	52.4
100°	147.3	103.3	91.9	80.5	66.1	57.7	54.7	53.1	54.7	57.7	66.1
102.5°	154.1	116.2	105.2	94.1	81.2	72.1	69.8	69.1	69.8	72.1	81.2
105°	164.0	130.6	120.0	109.3	97.2	89.6	85.8	85.8	85.8	89.6	97.2
107.5°	177.7	145.0	135.5	126.0	113.1	107.1	103.3	101.7	103.3	107.1	113.1
110°	192.8	161.7	151.8	142.0	130.6	123.8	120.7	119.2	120.7	123.8	130.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	207.3	177.7	168.2	158.7	147.3	140.5	138.2	136.7	138.2	140.5	147.3
115°	222.5	194.4	184.9	175.4	164.0	157.2	154.9	153.4	154.9	157.2	164.0
117.5°	237.6	211.1	202.0	192.8	179.9	173.1	170.8	168.6	170.8	173.1	179.9
120°	254.3	227.8	218.3	208.8	195.9	189.1	186.0	183.7	186.0	189.1	195.9
122.5°	270.3	243.7	234.2	224.7	210.3	203.5	201.2	199.7	201.2	203.5	210.3
125°	284.0	258.9	249.0	239.2	224.7	217.9	214.1	212.6	214.1	217.9	224.7
127.5°	297.6	273.3	263.4	253.6	238.4	230.0	225.5	223.2	225.5	230.0	238.4
130°	310.5	287.0	277.2	267.3	251.3	241.4	235.4	233.1	235.4	241.4	251.3
132.5°	322.7	299.1	289.2	279.4	262.7	251.3	243.7	240.7	243.7	251.3	262.7
135°	333.3	309.8	299.6	289.3	273.3	261.2	252.1	249.0	252.1	261.2	273.3
137.5°	340.9	319.6	309.0	298.4	282.4	270.3	261.9	259.7	261.9	270.3	282.4
140°	349.2	327.2	317.0	306.7	292.3	280.2	271.0	268.8	271.0	280.2	292.3
142.5°	354.6	334.1	324.6	315.1	301.4	289.3	280.9	279.4	280.9	289.3	301.4
145°	360.6	340.9	332.2	323.4	309.8	299.1	291.5	290.0	291.5	299.1	309.8
147.5°	364.4	347.0	339.0	331.0	318.9	309.0	302.2	301.4	302.2	309.0	318.9
150°	368.2	351.5	345.0	338.6	328.0	318.1	312.8	311.3	312.8	318.1	328.0
152.5°	372.0	356.8	351.2	345.5	335.6	327.2	322.7	321.9	322.7	327.2	335.6
155°	374.3	361.4	356.1	350.8	343.2	335.6	331.0	331.0	331.0	335.6	343.2
157.5°	376.6	365.2	361.0	356.8	350.0	343.2	339.4	339.4	339.4	343.2	350.0
160°	378.1	368.2	364.8	361.4	355.3	350.0	347.0	347.7	347.0	350.0	355.3
162.5°	379.6	371.3	368.6	366.0	361.4	356.8	353.8	354.6	353.8	356.8	361.4
165°	379.6	373.5	371.2	369.0	366.0	362.2	359.9	361.4	359.9	362.2	366.0
167.5°	379.6	374.3	372.8	371.3	369.0	366.7	365.2	366.0	365.2	366.7	369.0
170°	379.6	375.8	374.6	373.5	372.0	370.5	369.7	370.5	369.7	370.5	372.0
172.5°	378.9	375.8	375.5	375.1	374.3	372.8	372.0	373.5	372.0	372.8	374.3
175°	378.1	375.8	375.8	375.8	375.8	375.1	374.3	375.8	374.3	375.1	375.8
177.5°	377.3	375.8	375.8	375.8	376.6	375.8	375.8	377.3	375.8	375.8	376.6
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1550.3	1547.6	1541.0	1537.0	1523.6	1507.6	1502.3	1488.9	1494.3	1484.9	1484.9
5°	1509.0	1496.9	1488.9	1476.9	1451.6	1434.2	1415.6	1406.2	1400.9	1394.2	1388.9
7.5°	1455.6	1446.2	1438.2	1415.6	1387.5	1363.5	1340.8	1331.5	1314.2	1302.2	1296.8
10°	1408.9	1395.5	1376.9	1350.2	1320.8	1290.1	1270.1	1250.1	1236.8	1230.1	1215.4
12.5°	1360.9	1344.9	1324.8	1286.1	1254.1	1235.4	1199.4	1180.7	1174.1	1168.7	1151.4
15°	1311.5	1294.2	1270.1	1234.1	1206.1	1162.1	1140.7	1126.0	1110.0	1108.7	1095.4
17.5°	1267.5	1246.1	1226.1	1182.1	1147.4	1108.7	1096.7	1080.7	1066.0	1050.0	1043.3
20°	1211.4	1191.4	1176.7	1128.7	1090.0	1066.0	1046.0	1032.7	1023.3	1007.3	1004.6
22.5°	1160.7	1139.4	1119.4	1083.4	1050.0	1019.3	995.3	980.6	976.6	969.9	957.9
25°	1111.4	1090.0	1066.0	1032.7	998.0	976.6	955.3	945.9	937.9	927.3	917.9
27.5°	1070.0	1050.0	1027.3	986.0	956.6	940.6	917.9	907.2	896.6	891.2	887.2
30°	1020.6	998.0	980.6	948.6	916.6	895.2	879.2	869.9	860.5	855.2	852.5
32.5°	972.6	951.3	939.3	904.6	879.2	853.9	841.9	835.2	829.9	824.5	819.2
35°	933.9	912.6	893.9	861.9	836.5	819.2	809.8	799.2	795.2	789.8	789.8
37.5°	885.9	869.9	851.2	820.5	797.8	784.5	776.5	763.1	761.8	759.1	755.1
40°	844.5	828.5	811.2	784.5	764.5	748.5	737.8	731.1	727.1	724.5	721.8
42.5°	800.5	783.2	775.2	744.5	727.1	711.1	705.8	699.1	697.8	692.4	685.8
45°	757.8	743.1	727.1	704.4	689.8	676.4	668.4	663.1	656.4	655.1	651.1
47.5°	720.5	703.1	688.4	667.1	651.1	640.4	633.7	627.1	621.7	617.7	613.7
50°	672.4	659.1	647.1	624.4	611.1	600.4	591.0	585.7	580.4	580.4	580.4
52.5°	625.7	613.7	603.0	587.0	571.0	561.7	551.0	547.0	544.3	540.3	544.3
55°	580.4	568.4	557.7	545.7	527.0	519.0	508.3	504.3	505.7	505.7	509.7
57.5°	532.3	523.0	516.3	501.7	484.3	476.3	469.6	465.6	465.6	471.0	472.3
60°	485.6	476.3	464.3	451.0	440.3	430.9	426.9	428.3	428.3	430.9	437.6
62.5°	433.6	428.3	421.6	402.9	396.3	389.6	384.2	388.2	386.9	393.6	402.9
65°	385.6	380.2	370.9	361.6	353.6	346.9	345.6	346.9	349.6	356.2	366.9
67.5°	332.2	332.2	324.2	316.2	309.5	302.9	304.2	305.5	308.2	316.2	332.2
70°	288.2	282.8	274.8	269.5	264.2	261.5	258.8	264.2	272.2	277.5	289.5
72.5°	240.2	236.1	229.5	224.1	222.8	220.1	218.8	221.5	229.5	238.8	252.2
75°	189.5	190.8	186.8	182.8	182.8	178.8	181.4	181.4	189.5	198.8	209.5
77.5°	146.8	145.4	144.1	141.4	140.1	140.1	140.1	142.8	150.8	156.1	166.8
80°	104.1	105.4	101.4	102.7	101.4	102.7	102.7	108.1	112.1	118.7	126.7
82.5°	69.4	69.4	66.7	68.0	68.0	68.0	69.4	72.0	77.4	82.7	88.1
85°	38.7	40.0	37.4	40.0	40.0	40.0	41.4	42.7	46.7	48.0	53.4
87.5°	14.7	17.3	17.3	14.7	16.0	17.3	18.7	17.3	20.0	22.7	24.0
90°	6.1	6.8	7.6	8.4	9.9	10.6	12.1	12.9	13.7	14.4	15.2
92.5°	48.6	62.2	75.9	127.6	214.1	308.3	302.9	244.5	164.8	118.4	88.1
95°	56.9	74.0	91.1	172.3	339.4	548.9	672.7	658.3	545.9	430.5	337.1
97.5°	67.6	80.1	92.6	148.8	277.1	503.4	726.6	822.3	782.8	690.9	596.8
100°	80.5	91.9	103.3	147.3	246.0	437.3	685.6	875.4	933.9	896.7	818.5
102.5°	94.1	105.2	116.2	154.1	233.1	387.2	613.5	843.5	984.7	1022.7	995.4
105°	109.3	120.0	130.6	164.0	231.6	358.4	550.4	768.3	950.6	1054.6	1088.0
107.5°	126.0	135.5	145.0	177.7	236.9	343.2	503.4	697.0	880.7	1018.1	1098.6
110°	142.0	151.8	161.7	192.8	245.2	337.1	472.2	637.8	801.8	946.0	1053.1

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	158.7	168.2	177.7	207.3	255.9	337.1	454.0	593.7	739.5	874.6	983.2
115°	175.4	184.9	194.4	222.5	266.5	339.4	441.9	564.1	689.4	807.1	911.1
117.5°	192.8	202.0	211.1	237.6	278.6	343.2	435.0	544.4	654.5	758.5	849.6
120°	208.8	218.3	227.8	254.3	290.8	349.2	430.5	528.4	627.1	718.2	801.8
122.5°	224.7	234.2	243.7	270.3	304.5	354.6	426.7	514.8	606.6	689.4	761.5
125°	239.2	249.0	258.9	284.0	316.6	360.6	423.7	502.6	586.9	664.3	730.4
127.5°	253.6	263.4	273.3	297.6	328.0	367.5	422.1	491.2	566.4	640.0	702.3
130°	267.3	277.2	287.0	310.5	339.4	373.5	420.6	479.8	547.4	614.2	673.4
132.5°	279.4	289.2	299.1	322.7	349.2	380.4	420.6	470.7	528.4	589.9	642.3
135°	289.3	299.6	309.8	333.3	358.4	386.5	420.6	463.9	512.5	564.9	613.5
137.5°	298.4	309.0	319.6	340.9	365.2	392.5	421.4	457.1	498.1	542.1	583.9
140°	306.7	317.0	327.2	349.2	372.0	396.3	422.1	452.5	486.7	522.4	557.3
142.5°	315.1	324.6	334.1	354.6	375.8	398.6	422.9	448.7	476.8	505.7	534.5
145°	323.4	332.2	340.9	360.6	379.6	400.1	422.1	444.9	468.5	492.0	515.5
147.5°	331.0	339.0	347.0	364.4	381.9	400.9	420.6	441.1	460.1	479.8	498.8
150°	338.6	345.0	351.5	368.2	384.2	400.9	418.3	436.6	453.3	470.0	484.4
152.5°	345.5	351.2	356.8	372.0	385.7	400.1	415.3	431.2	445.7	460.1	473.0
155°	350.8	356.1	361.4	374.3	386.5	398.6	411.5	425.2	438.1	450.2	460.9
157.5°	356.8	361.0	365.2	376.6	387.2	397.1	407.7	419.9	430.5	441.1	449.5
160°	361.4	364.8	368.2	378.1	387.2	394.8	403.9	413.0	422.9	430.5	438.1
162.5°	366.0	368.6	371.3	379.6	386.5	392.5	399.4	407.0	414.5	421.4	427.5
165°	369.0	371.2	373.5	379.6	385.7	390.2	394.8	400.9	407.0	412.3	416.8
167.5°	371.3	372.8	374.3	379.6	384.2	386.5	390.2	394.8	399.4	403.2	407.0
170°	373.5	374.6	375.8	379.6	382.7	384.2	386.5	389.5	393.3	395.6	397.8
172.5°	375.1	375.5	375.8	378.9	381.1	381.1	381.9	384.2	386.5	388.7	390.2
175°	375.8	375.8	375.8	378.1	379.6	378.9	378.9	379.6	381.9	381.9	383.4
177.5°	375.8	375.8	375.8	377.3	378.1	376.6	376.6	377.3	378.1	378.9	378.9
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1490.3	1480.9	1479.6	1482.3	1476.9	1484.9	1482.3	1484.9	1478.3	1484.9	1480.9
5°	1387.5	1384.9	1379.5	1372.9	1374.2	1375.5	1382.2	1375.5	1380.9	1382.2	1388.9
7.5°	1291.5	1286.1	1290.1	1287.5	1275.5	1272.8	1275.5	1279.5	1287.5	1292.8	1296.8
10°	1214.1	1211.4	1206.1	1202.1	1195.4	1191.4	1196.8	1191.4	1202.1	1211.4	1211.4
12.5°	1155.4	1144.7	1138.1	1136.7	1122.0	1124.7	1130.0	1134.1	1146.1	1151.4	1151.4
15°	1094.0	1086.0	1083.4	1078.0	1072.7	1078.0	1075.3	1079.3	1084.7	1090.0	1092.7
17.5°	1040.7	1039.3	1040.7	1027.3	1031.3	1024.6	1026.0	1032.7	1028.7	1032.7	1040.7
20°	992.6	995.3	991.3	986.0	986.0	978.0	987.3	984.6	986.0	994.0	1006.0
22.5°	956.6	955.3	951.3	947.3	941.9	943.3	944.6	941.9	952.6	959.3	960.6
25°	917.9	915.2	913.9	909.9	904.6	909.9	908.6	909.9	912.6	923.3	915.2
27.5°	881.9	876.6	879.2	875.2	873.9	875.2	875.2	876.6	879.2	880.6	881.9
30°	851.2	845.9	844.5	841.9	840.5	841.9	844.5	841.9	852.5	851.2	851.2
32.5°	817.9	813.8	811.2	811.2	809.8	808.5	809.8	811.2	819.2	813.8	819.2
35°	785.8	783.2	783.2	780.5	779.2	779.2	779.2	784.5	781.8	785.8	785.8
37.5°	755.1	755.1	753.8	751.1	749.8	751.1	749.8	752.5	751.1	752.5	753.8
40°	723.1	720.5	719.1	719.1	715.1	711.1	715.1	715.1	716.5	720.5	721.8
42.5°	684.4	685.8	685.8	680.4	680.4	680.4	681.8	683.1	683.1	685.8	685.8
45°	651.1	648.4	648.4	648.4	645.7	647.1	649.7	649.7	649.7	649.7	647.1
47.5°	613.7	613.7	615.1	615.1	619.1	617.7	617.7	616.4	613.7	613.7	615.1
50°	579.0	583.0	584.4	584.4	585.7	587.0	587.0	584.4	583.0	579.0	579.0
52.5°	545.7	548.3	551.0	555.0	557.7	556.4	556.4	553.7	548.3	547.0	545.7
55°	509.7	513.7	519.0	523.0	527.0	528.3	528.3	523.0	517.7	511.0	511.0
57.5°	476.3	480.3	489.6	493.6	499.0	499.0	496.3	492.3	484.3	479.0	475.0
60°	442.9	449.6	456.3	464.3	471.0	472.3	468.3	463.0	453.6	446.9	441.6
62.5°	406.9	413.6	426.9	434.9	440.3	440.3	440.3	433.6	421.6	412.3	404.3
65°	372.2	378.9	390.9	401.6	405.6	409.6	405.6	398.9	389.6	378.9	370.9
67.5°	336.2	344.2	356.2	364.2	369.6	373.6	370.9	365.6	353.6	338.9	333.5
70°	296.2	300.2	317.5	325.5	333.5	336.2	333.5	325.5	313.5	297.5	292.2
72.5°	258.8	262.8	278.8	285.5	292.2	294.9	290.9	285.5	274.8	260.2	253.5
75°	216.1	222.8	230.8	241.5	249.5	252.2	248.2	244.2	230.8	221.5	216.1
77.5°	170.8	177.4	188.1	197.5	205.5	204.1	198.8	200.1	185.5	174.8	170.8
80°	129.4	134.8	142.8	150.8	154.8	154.8	153.4	148.1	142.8	134.8	128.1
82.5°	89.4	96.1	102.7	108.1	108.1	109.4	106.7	105.4	100.1	93.4	92.1
85°	53.4	54.7	60.0	60.0	65.4	62.7	61.4	65.4	60.0	56.0	54.7
87.5°	24.0	22.7	24.0	24.0	22.7	25.3	25.3	24.0	25.3	24.0	24.0
90°	16.0	16.7	16.7	16.7	17.5	17.5	17.5	16.7	16.7	16.7	16.0
92.5°	80.8	73.6	61.5	59.2	57.7	56.2	57.7	59.2	61.5	73.6	80.8
95°	305.2	273.3	219.4	196.6	190.6	178.4	190.6	196.6	219.4	273.3	305.2
97.5°	551.2	505.7	460.1	420.6	400.1	391.0	400.1	420.6	460.1	505.7	551.2
100°	779.0	739.5	687.1	632.4	604.4	592.2	604.4	632.4	687.1	739.5	779.0
102.5°	971.8	948.3	891.3	856.4	825.3	816.9	825.3	856.4	891.3	948.3	971.8
105°	1083.8	1079.6	1055.3	1030.3	1015.1	1006.0	1015.1	1030.3	1055.3	1079.6	1083.8
107.5°	1115.3	1132.0	1138.9	1135.1	1127.5	1119.9	1127.5	1135.1	1138.9	1132.0	1115.3
110°	1085.4	1117.6	1151.8	1166.2	1171.5	1171.5	1171.5	1166.2	1151.8	1117.6	1085.4

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1022.7	1062.2	1116.1	1143.4	1158.6	1165.4	1158.6	1143.4	1116.1	1062.2	1022.7
115°	952.4	993.8	1053.1	1089.5	1110.8	1120.6	1110.8	1089.5	1053.1	993.8	952.4
117.5°	888.7	927.8	987.8	1025.7	1047.0	1053.1	1047.0	1025.7	987.8	927.8	888.7
120°	835.2	868.6	924.8	961.2	981.7	987.8	981.7	961.2	924.8	868.6	835.2
122.5°	792.2	823.0	871.6	904.3	924.8	930.1	924.8	904.3	871.6	823.0	792.2
125°	757.8	785.1	827.6	858.7	875.4	883.0	875.4	858.7	827.6	785.1	757.8
127.5°	728.1	753.9	792.6	820.7	836.7	839.7	836.7	820.7	792.6	753.9	728.1
130°	698.1	722.8	760.8	785.8	801.0	805.6	801.0	785.8	760.8	722.8	698.1
132.5°	665.8	689.4	727.4	752.4	766.1	771.4	766.1	752.4	727.4	689.4	665.8
135°	635.1	656.7	690.1	715.2	728.9	733.4	728.9	715.2	690.1	656.7	635.1
137.5°	602.8	621.8	652.2	675.7	688.6	693.9	688.6	675.7	652.2	621.8	602.8
140°	573.2	589.2	617.3	637.0	648.4	652.2	648.4	637.0	617.3	589.2	573.2
142.5°	547.8	561.1	583.9	599.8	610.4	613.5	610.4	599.8	583.9	561.1	547.8
145°	525.8	536.0	554.2	567.2	575.5	578.5	575.5	567.2	554.2	536.0	525.8
147.5°	506.8	514.8	529.9	540.6	545.9	547.4	545.9	540.6	529.9	514.8	506.8
150°	491.2	498.1	509.4	518.6	521.6	522.4	521.6	518.6	509.4	498.1	491.2
152.5°	478.0	482.9	492.0	498.8	501.9	502.6	501.9	498.8	492.0	482.9	478.0
155°	465.0	469.2	476.8	482.1	484.4	485.2	484.4	482.1	476.8	469.2	465.0
157.5°	452.9	456.3	462.4	466.9	469.2	469.2	469.2	466.9	462.4	456.3	452.9
160°	440.8	443.4	448.7	452.5	454.0	453.3	454.0	452.5	448.7	443.4	440.8
162.5°	429.8	432.0	435.8	438.8	438.8	438.8	438.8	438.8	435.8	432.0	429.8
165°	418.7	420.6	423.7	425.2	425.2	425.2	425.2	425.2	423.7	420.6	418.7
167.5°	408.5	410.0	411.5	413.0	412.3	412.3	412.3	413.0	411.5	410.0	408.5
170°	398.6	399.4	400.9	401.6	401.6	400.9	401.6	401.6	400.9	399.4	398.6
172.5°	390.6	391.0	391.0	392.5	391.0	390.2	391.0	392.5	391.0	391.0	390.6
175°	383.4	383.4	383.4	384.2	382.7	381.9	382.7	384.2	383.4	383.4	383.4
177.5°	378.9	378.9	378.1	378.9	376.6	376.6	376.6	378.9	378.1	378.9	378.9
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1492.9	1484.9	1494.3	1482.3	1484.9	1499.6	1498.3	1511.6	1519.6	1518.3	1525.0
5°	1394.2	1394.2	1398.2	1396.9	1410.2	1422.2	1438.2	1451.6	1466.3	1474.3	1483.6
7.5°	1296.8	1310.2	1312.8	1319.5	1335.5	1355.5	1371.5	1391.5	1412.9	1427.6	1438.2
10°	1216.8	1227.4	1238.1	1243.5	1260.8	1287.5	1310.2	1342.2	1368.9	1384.9	1399.6
12.5°	1146.1	1158.1	1163.4	1187.4	1199.4	1216.8	1248.8	1283.5	1312.8	1330.2	1342.2
15°	1095.4	1102.0	1114.0	1128.7	1140.7	1162.1	1188.8	1227.4	1255.5	1270.1	1311.5
17.5°	1052.7	1060.7	1067.3	1074.0	1092.7	1115.4	1140.7	1174.1	1210.1	1235.4	1256.8
20°	1008.6	1012.6	1020.6	1031.3	1044.7	1066.0	1088.7	1123.4	1155.4	1175.4	1203.4
22.5°	956.6	968.6	976.6	984.6	999.3	1023.3	1044.7	1070.0	1110.0	1132.7	1162.1
25°	925.9	931.3	936.6	945.9	956.6	978.0	1002.0	1028.7	1060.7	1084.7	1110.0
27.5°	885.9	893.9	900.6	912.6	919.2	936.6	959.3	986.0	1024.6	1044.7	1066.0
30°	852.5	860.5	865.9	871.2	880.6	899.2	920.6	941.9	978.0	1003.3	1024.6
32.5°	819.2	827.2	833.9	837.9	847.2	859.2	876.6	903.2	933.9	951.3	979.3
35°	789.8	789.8	797.8	803.2	811.2	821.9	837.9	857.9	889.9	912.6	937.9
37.5°	756.5	757.8	764.5	768.5	776.5	787.2	803.2	821.9	848.5	865.9	891.2
40°	721.8	725.8	728.5	735.1	744.5	748.5	764.5	785.8	812.5	828.5	849.9
42.5°	687.1	689.8	696.4	701.8	709.8	716.5	727.1	747.1	767.2	791.2	808.5
45°	648.4	655.1	659.1	668.4	672.4	679.1	689.8	705.8	729.8	744.5	764.5
47.5°	615.1	617.7	620.4	632.4	640.4	644.4	655.1	664.4	689.8	703.1	721.8
50°	579.0	579.0	583.0	588.4	597.7	605.7	615.1	625.7	645.7	659.1	677.8
52.5°	545.7	541.7	544.3	547.0	556.4	564.4	573.7	588.4	607.1	615.1	631.1
55°	509.7	503.0	507.0	511.0	513.7	524.3	535.0	544.3	559.0	571.0	585.7
57.5°	471.0	469.6	467.0	468.3	475.0	481.6	489.6	501.7	519.0	528.3	536.3
60°	436.3	428.3	425.6	428.3	432.3	436.3	446.9	457.6	472.3	481.6	491.0
62.5°	400.3	392.2	386.9	382.9	386.9	396.3	402.9	410.9	422.9	433.6	441.6
65°	365.6	353.6	348.2	345.6	344.2	350.9	356.2	366.9	377.6	381.6	390.9
67.5°	326.9	316.2	309.5	305.5	305.5	305.5	310.9	321.5	332.2	333.5	342.9
70°	288.2	276.2	269.5	264.2	261.5	264.2	270.8	272.2	281.5	284.2	289.5
72.5°	246.8	236.1	228.1	221.5	222.8	225.5	225.5	228.1	233.5	240.2	240.2
75°	208.1	193.5	189.5	184.1	181.4	181.4	181.4	186.8	190.8	196.1	194.8
77.5°	164.1	156.1	148.1	145.4	141.4	140.1	142.8	142.8	145.4	149.4	150.8
80°	126.7	117.4	112.1	109.4	104.1	102.7	104.1	104.1	108.1	106.7	108.1
82.5°	88.1	81.4	77.4	73.4	70.7	72.0	70.7	70.7	72.0	70.7	70.7
85°	50.7	49.4	46.7	45.4	44.0	41.4	44.0	42.7	41.4	40.0	42.7
87.5°	24.0	22.7	22.7	20.0	20.0	18.7	20.0	20.0	18.7	18.7	18.7
90°	15.2	14.4	13.7	12.9	12.1	10.6	9.9	8.4	7.6	6.8	6.1
92.5°	88.1	118.4	164.8	244.5	302.9	308.3	214.1	127.6	75.9	62.2	48.6
95°	337.1	430.5	545.9	658.3	672.7	548.9	339.4	172.3	91.1	74.0	56.9
97.5°	596.8	690.9	782.8	822.3	726.6	503.4	277.1	148.8	92.6	80.1	67.6
100°	818.5	896.7	933.9	875.4	685.6	437.3	246.0	147.3	103.3	91.9	80.5
102.5°	995.4	1022.7	984.7	843.5	613.5	387.2	233.1	154.1	116.2	105.2	94.1
105°	1088.0	1054.6	950.6	768.3	550.4	358.4	231.6	164.0	130.6	120.0	109.3
107.5°	1098.6	1018.1	880.7	697.0	503.4	343.2	236.9	177.7	145.0	135.5	126.0
110°	1053.1	946.0	801.8	637.8	472.2	337.1	245.2	192.8	161.7	151.8	142.0



TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	983.2	874.6	739.5	593.7	454.0	337.1	255.9	207.3	177.7	168.2	158.7
115°	911.1	807.1	689.4	564.1	441.9	339.4	266.5	222.5	194.4	184.9	175.4
117.5°	849.6	758.5	654.5	544.4	435.0	343.2	278.6	237.6	211.1	202.0	192.8
120°	801.8	718.2	627.1	528.4	430.5	349.2	290.8	254.3	227.8	218.3	208.8
122.5°	761.5	689.4	606.6	514.8	426.7	354.6	304.5	270.3	243.7	234.2	224.7
125°	730.4	664.3	586.9	502.6	423.7	360.6	316.6	284.0	258.9	249.0	239.2
127.5°	702.3	640.0	566.4	491.2	422.1	367.5	328.0	297.6	273.3	263.4	253.6
130°	673.4	614.2	547.4	479.8	420.6	373.5	339.4	310.5	287.0	277.2	267.3
132.5°	642.3	589.9	528.4	470.7	420.6	380.4	349.2	322.7	299.1	289.2	279.4
135°	613.5	564.9	512.5	463.9	420.6	386.5	358.4	333.3	309.8	299.6	289.3
137.5°	583.9	542.1	498.1	457.1	421.4	392.5	365.2	340.9	319.6	309.0	298.4
140°	557.3	522.4	486.7	452.5	422.1	396.3	372.0	349.2	327.2	317.0	306.7
142.5°	534.5	505.7	476.8	448.7	422.9	398.6	375.8	354.6	334.1	324.6	315.1
145°	515.5	492.0	468.5	444.9	422.1	400.1	379.6	360.6	340.9	332.2	323.4
147.5°	498.8	479.8	460.1	441.1	420.6	400.9	381.9	364.4	347.0	339.0	331.0
150°	484.4	470.0	453.3	436.6	418.3	400.9	384.2	368.2	351.5	345.0	338.6
152.5°	473.0	460.1	445.7	431.2	415.3	400.1	385.7	372.0	356.8	351.2	345.5
155°	460.9	450.2	438.1	425.2	411.5	398.6	386.5	374.3	361.4	356.1	350.8
157.5°	449.5	441.1	430.5	419.9	407.7	397.1	387.2	376.6	365.2	361.0	356.8
160°	438.1	430.5	422.9	413.0	403.9	394.8	387.2	378.1	368.2	364.8	361.4
162.5°	427.5	421.4	414.5	407.0	399.4	392.5	386.5	379.6	371.3	368.6	366.0
165°	416.8	412.3	407.0	400.9	394.8	390.2	385.7	379.6	373.5	371.2	369.0
167.5°	407.0	403.2	399.4	394.8	390.2	386.5	384.2	379.6	374.3	372.8	371.3
170°	397.8	395.6	393.3	389.5	386.5	384.2	382.7	379.6	375.8	374.6	373.5
172.5°	390.2	388.7	386.5	384.2	381.9	381.1	381.1	378.9	375.8	375.5	375.1
175°	383.4	381.9	381.9	379.6	378.9	378.9	379.6	378.1	375.8	375.8	375.8
177.5°	378.9	378.9	378.1	377.3	376.6	376.6	378.1	377.3	375.8	375.8	375.8
180°	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6	376.6

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1534.3	1547.6	1557.0	1574.3
5°	1499.6	1523.6	1546.3	1570.3
7.5°	1464.9	1492.9	1529.0	1559.7
10°	1426.2	1462.3	1505.0	1546.3
12.5°	1387.5	1430.2	1476.9	1531.6
15°	1340.8	1395.5	1450.3	1509.0
17.5°	1299.5	1355.5	1414.2	1487.6
20°	1252.8	1314.2	1378.2	1452.9
22.5°	1211.4	1279.5	1346.2	1424.9
25°	1164.7	1231.4	1304.8	1388.9
27.5°	1126.0	1187.4	1259.5	1350.2
30°	1079.3	1146.1	1218.1	1308.8
32.5°	1035.3	1099.4	1175.4	1264.8
35°	990.0	1055.3	1123.4	1208.8
37.5°	947.3	1003.3	1071.3	1152.7
40°	899.2	960.6	1022.0	1086.0
42.5°	855.2	911.2	968.6	1019.3
45°	805.8	853.9	908.6	949.9
47.5°	760.5	803.2	845.9	877.9
50°	715.1	748.5	780.5	808.5
52.5°	661.8	699.1	716.5	733.8
55°	613.7	635.1	651.1	668.4
57.5°	567.0	576.4	584.4	600.4
60°	505.7	516.3	525.7	537.7
62.5°	452.3	457.6	460.3	472.3
65°	401.6	400.3	406.9	413.6
67.5°	346.9	345.6	352.2	354.9
70°	293.5	292.2	293.5	300.2
72.5°	242.8	242.8	244.2	246.8
75°	196.1	196.1	197.5	200.1
77.5°	148.1	150.8	149.4	154.8
80°	108.1	105.4	108.1	110.7
82.5°	70.7	73.4	73.4	70.7
85°	40.0	40.0	40.0	40.0
87.5°	17.3	17.3	18.7	20.0
90°	4.6	3.0	1.5	0.8
92.5°	32.6	21.3	13.7	11.4
95°	40.2	31.9	25.8	25.1
97.5°	52.4	44.0	39.5	38.7
100°	66.1	57.7	54.7	53.1
102.5°	81.2	72.1	69.8	69.1
105°	97.2	89.6	85.8	85.8
107.5°	113.1	107.1	103.3	101.7
110°	130.6	123.8	120.7	119.2

TEST NUMBER: P1027513

CATALOG NUMBER: S125DIP-B1090D850UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	147.3	140.5	138.2	136.7
115°	164.0	157.2	154.9	153.4
117.5°	179.9	173.1	170.8	168.6
120°	195.9	189.1	186.0	183.7
122.5°	210.3	203.5	201.2	199.7
125°	224.7	217.9	214.1	212.6
127.5°	238.4	230.0	225.5	223.2
130°	251.3	241.4	235.4	233.1
132.5°	262.7	251.3	243.7	240.7
135°	273.3	261.2	252.1	249.0
137.5°	282.4	270.3	261.9	259.7
140°	292.3	280.2	271.0	268.8
142.5°	301.4	289.3	280.9	279.4
145°	309.8	299.1	291.5	290.0
147.5°	318.9	309.0	302.2	301.4
150°	328.0	318.1	312.8	311.3
152.5°	335.6	327.2	322.7	321.9
155°	343.2	335.6	331.0	331.0
157.5°	350.0	343.2	339.4	339.4
160°	355.3	350.0	347.0	347.7
162.5°	361.4	356.8	353.8	354.6
165°	366.0	362.2	359.9	361.4
167.5°	369.0	366.7	365.2	366.0
170°	372.0	370.5	369.7	370.5
172.5°	374.3	372.8	372.0	373.5
175°	375.8	375.1	374.3	375.8
177.5°	376.6	375.8	375.8	377.3
180°	376.6	376.6	376.6	376.6

(END OF REPORT)