

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027582

Luminaire Tested: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027582
REPORT IS A COMBINATION OF REPORTS P1001605 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9522.0 lumens
Efficiency: N/A
Efficacy: 98.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	55		
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51	46		
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	39		
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37	34		
4	76	65	57	51	70	61	54	48	52	47	43	45	41	38	38	35	32	29		
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28	25		
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25	22		
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22	20		
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	23	20	18		
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16		
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11793	11793	11793	11793
5°	11802	13378	11812	10149
10°	11730	15249	11710	8712
15°	11644	16534	11572	7872
20°	11497	18118	11391	7186
25°	11367	20759	11159	6780
30°	11179	21901	10985	6412
35°	10882	17556	10653	6117
40°	10419	12134	10265	5806
45°	9834	9034	9724	5546
50°	9165	7437	9014	5338
55°	8443	6343	8376	5158
60°	7734	5429	7600	5018
65°	6970	4689	6858	4814
70°	6163	3893	6081	4460
75°	5307	3011	5237	3871
80°	4191	2036	4039	2846
85°	2682	1019	2590	1450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18013 cd/sqm

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	1.9
10°-20°	527.7	5.5
20°-30°	857.1	9.0
30°-40°	1047.5	11.0
40°-50°	950.2	10.0
50°-60°	756.8	7.9
60°-70°	527.1	5.5
70°-80°	280.8	2.9
80°-90°	71.9	0.8
90°-100°	418.9	4.4
100°-110°	903.4	9.5
110°-120°	842.2	8.8
120°-130°	682.1	7.2
130°-140°	547.7	5.8
140°-150°	413.1	4.3
150°-160°	290.9	3.1
160°-170°	171.5	1.8
170°-180°	55.8	0.6
0°-30°	1561.9	16.4
0°-40°	2609.4	27.4
0°-60°	4316.4	45.3
0°-90°	5196.3	54.6
90°-120°	2164.5	22.7
90°-150°	3807.5	40.0
90°-180°	4326.0	45.4
0°-180°	9522.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1841	1841	1841	1841	1841	
5°	1839	2123	1841	1611	1839	175
15°	1767	2652	1756	1262	1767	499
25°	1627	3262	1597	1066	1627	749
35°	1416	2619	1386	912	1416	884
45°	1112	1234	1100	758	1112	857
55°	783	761	777	619	783	700
65°	484	467	477	480	484	481
75°	234	230	231	295	234	249
85°	47	52	45	73	47	56
90°	1	27	1	27	1	6
95°	38	273	38	273	38	40
105°	131	1538	131	1538	131	138
115°	234	1714	234	1714	234	231
125°	325	1350	325	1350	325	289
135°	381	1122	381	1122	381	296
145°	444	885	444	885	444	278
155°	506	742	506	742	506	233
165°	553	650	553	650	553	156
175°	575	584	575	584	575	55
180°	576	576	576	576	576	

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1843.8	1854.7	1867.2	1876.6	1892.2	1896.9	1904.7	1909.4	1914.1	1918.8	1921.9
5°	1839.1	1865.6	1889.1	1906.3	1935.9	1946.9	1960.9	1978.1	1998.4	2015.6	2026.6
7.5°	1826.6	1868.8	1900.0	1934.4	1975.0	2001.6	2015.6	2051.6	2084.4	2109.4	2142.2
10°	1810.9	1860.9	1909.4	1960.9	2018.8	2048.4	2076.6	2126.6	2171.9	2212.5	2245.3
12.5°	1793.8	1854.7	1912.5	1979.7	2057.8	2093.8	2112.5	2198.4	2254.7	2276.6	2340.6
15°	1767.2	1839.1	1921.9	2004.7	2070.3	2112.5	2164.1	2232.8	2289.1	2337.5	2389.1
17.5°	1742.2	1820.3	1904.7	1996.9	2092.2	2146.9	2185.9	2246.9	2307.8	2370.3	2418.8
20°	1701.6	1803.1	1889.1	1987.5	2100.0	2139.1	2179.7	2251.6	2317.2	2384.4	2445.3
22.5°	1668.8	1765.6	1882.8	1976.6	2071.9	2110.9	2160.9	2235.9	2314.1	2390.6	2479.7
25°	1626.6	1734.4	1835.9	1935.9	2034.4	2076.6	2121.9	2218.8	2300.0	2398.4	2496.9
27.5°	1581.3	1692.2	1793.8	1884.4	1976.6	2034.4	2082.8	2184.4	2292.2	2400.0	2528.1
30°	1532.8	1637.5	1734.4	1823.4	1925.0	1984.4	2032.8	2151.6	2271.9	2409.4	2562.5
32.5°	1481.3	1579.7	1662.5	1753.1	1860.9	1915.6	1981.3	2110.9	2253.1	2417.2	2609.4
35°	1415.6	1509.4	1582.8	1675.0	1782.8	1853.1	1921.9	2067.2	2232.8	2415.6	2635.9
37.5°	1350.0	1423.4	1493.8	1592.2	1717.2	1781.3	1853.1	2012.5	2201.6	2410.9	2646.9
40°	1271.9	1343.8	1404.7	1504.7	1635.9	1709.4	1784.4	1951.6	2165.6	2393.8	2607.8
42.5°	1193.8	1254.7	1321.9	1426.6	1553.1	1631.3	1710.9	1896.9	2118.8	2343.8	2500.0
45°	1112.5	1159.4	1232.8	1328.1	1462.5	1537.5	1628.1	1829.7	2053.1	2253.1	2331.3
47.5°	1028.1	1075.0	1143.8	1235.9	1368.8	1457.8	1543.8	1745.3	1970.3	2125.0	2125.0
50°	946.9	984.4	1051.6	1143.8	1278.1	1359.4	1446.9	1660.9	1842.2	1956.3	1854.7
52.5°	859.4	901.6	957.8	1054.7	1187.5	1260.9	1356.3	1539.1	1710.9	1757.8	1601.6
55°	782.8	817.2	870.3	962.5	1085.9	1162.5	1243.8	1418.8	1564.1	1560.9	1393.8
57.5°	703.1	731.3	787.5	871.9	985.9	1054.7	1135.9	1287.5	1406.3	1364.1	1206.3
60°	629.7	650.0	704.7	773.4	882.8	946.9	1025.0	1148.4	1239.1	1179.7	1020.3
62.5°	553.1	576.6	620.3	687.5	784.4	835.9	893.8	1018.8	1076.6	1023.4	860.9
65°	484.4	503.1	542.2	598.4	685.9	732.8	782.8	885.9	940.6	864.1	729.7
67.5°	415.6	437.5	465.6	515.6	584.4	628.1	671.9	760.9	785.9	717.2	604.7
70°	351.6	370.3	396.9	432.8	490.6	529.7	562.5	635.9	653.1	589.1	500.0
72.5°	289.1	301.6	323.4	353.1	406.3	428.1	462.5	512.5	534.4	476.6	412.5
75°	234.4	243.8	257.8	279.7	315.6	339.1	367.2	414.1	412.5	371.9	326.6
77.5°	181.3	182.8	198.4	218.8	240.6	260.9	275.0	307.8	310.9	285.9	248.4
80°	129.7	134.4	140.6	156.3	175.0	182.8	200.0	220.3	223.4	204.7	179.7
82.5°	82.8	85.9	90.6	100.0	112.5	121.9	131.3	139.1	146.9	135.9	115.6
85°	46.9	48.4	53.1	56.3	62.5	67.2	75.0	82.8	81.3	73.4	67.2
87.5°	23.4	23.4	23.4	26.6	29.7	29.7	32.8	34.4	35.9	32.8	29.7
90°	1.2	2.3	4.6	7.0	9.3	10.4	11.6	12.8	15.1	16.3	18.6
92.5°	17.4	20.9	32.5	49.9	74.3	95.2	116.1	195.1	327.4	471.4	463.3
95°	38.3	39.5	48.8	61.5	87.1	113.2	139.3	263.6	519.0	839.5	1028.8
97.5°	59.2	60.4	67.3	80.1	103.3	122.5	141.7	227.6	423.8	769.8	1111.2
100°	81.3	83.6	88.2	101.0	123.1	140.5	157.9	225.3	376.2	668.8	1048.5
102.5°	105.7	106.8	110.3	124.2	144.0	160.8	177.7	235.7	356.5	592.2	938.2
105°	131.2	131.2	137.0	148.6	167.2	183.4	199.7	250.8	354.1	548.1	841.8
107.5°	155.6	157.9	163.7	173.0	192.7	207.2	221.8	271.7	362.3	524.8	769.8
110°	182.3	184.6	189.3	199.7	217.1	232.2	247.3	294.9	375.0	515.5	722.2

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	209.0	211.3	214.8	225.3	242.7	257.2	271.7	317.0	391.3	515.5	694.4
115°	234.5	236.9	240.4	250.8	268.2	282.7	297.2	340.2	407.6	519.0	675.8
117.5°	257.8	261.3	264.7	275.2	294.9	308.8	322.8	363.4	426.1	524.8	665.3
120°	281.0	284.5	289.1	299.6	319.3	333.8	348.3	389.0	444.7	534.1	658.4
122.5°	305.4	307.7	311.2	321.6	343.7	358.2	372.7	413.4	465.6	542.2	652.6
125°	325.1	327.4	333.2	343.7	365.8	380.8	395.9	434.3	484.2	551.5	647.9
127.5°	341.4	344.9	351.8	364.6	387.8	402.9	418.0	455.2	501.6	562.0	645.6
130°	356.5	359.9	369.2	384.3	408.7	423.8	438.9	474.9	519.0	571.3	643.3
132.5°	368.1	372.7	384.3	401.7	427.3	442.4	457.5	493.5	534.1	581.7	643.3
135°	380.8	385.5	399.4	418.0	442.4	458.0	473.7	509.7	548.1	591.0	643.3
137.5°	397.1	400.6	413.4	431.9	456.3	472.6	488.8	521.3	558.5	600.3	644.4
140°	411.0	414.5	428.5	447.0	469.1	484.8	500.4	534.1	569.0	606.1	645.6
142.5°	427.3	429.6	442.4	461.0	481.9	496.4	510.9	542.2	574.8	609.6	646.7
145°	443.5	445.9	457.5	473.7	494.6	508.0	521.3	551.5	580.6	611.9	645.6
147.5°	461.0	462.1	472.6	487.7	506.3	518.4	530.6	557.3	584.0	613.1	643.3
150°	476.1	478.4	486.5	501.6	517.9	527.8	537.6	563.1	587.5	613.1	639.8
152.5°	492.3	493.5	500.4	513.2	528.3	537.0	545.7	569.0	589.9	611.9	635.1
155°	506.3	506.3	513.2	524.8	536.4	544.6	552.7	572.4	591.0	609.6	629.3
157.5°	519.0	519.0	524.8	535.3	545.7	552.1	558.5	575.9	592.2	607.3	623.5
160°	531.8	530.6	535.3	543.4	552.7	557.9	563.1	578.2	592.2	603.8	617.7
162.5°	542.2	541.1	545.7	552.7	559.7	563.8	567.8	580.6	591.0	600.3	610.8
165°	552.7	550.4	553.9	559.7	564.3	567.8	571.3	580.6	589.9	596.8	603.8
167.5°	559.7	558.5	560.8	564.3	567.8	570.1	572.4	580.6	587.5	591.0	596.8
170°	566.6	565.5	566.6	569.0	571.3	573.0	574.8	580.6	585.2	587.5	591.0
172.5°	571.3	569.0	570.1	572.4	573.6	574.2	574.8	579.4	582.9	582.9	584.0
175°	574.8	572.4	573.6	574.8	574.8	574.8	574.8	578.2	580.6	579.4	579.4
177.5°	577.1	574.8	574.8	575.9	574.8	574.8	574.8	577.1	578.2	575.9	575.9
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1925.0	1935.9	1945.3	1953.1	1959.4	1968.8	1962.5	1964.1	1967.2	1973.4	1973.4
5°	2050.0	2067.2	2076.6	2107.8	2115.6	2114.1	2109.4	2134.4	2132.8	2123.4	2121.9
7.5°	2171.9	2201.6	2228.1	2253.1	2260.9	2281.3	2285.9	2296.9	2293.8	2309.4	2301.6
10°	2282.8	2329.7	2354.7	2392.2	2401.6	2410.9	2423.4	2429.7	2443.8	2442.2	2442.2
12.5°	2368.8	2425.0	2457.8	2467.2	2503.1	2514.1	2525.0	2545.3	2540.6	2542.2	2551.6
15°	2435.9	2490.6	2518.8	2562.5	2587.5	2600.0	2618.8	2640.6	2637.5	2651.6	2648.4
17.5°	2485.9	2537.5	2589.1	2654.7	2656.3	2689.1	2732.8	2742.2	2762.5	2748.4	2748.4
20°	2526.6	2595.3	2668.8	2753.1	2762.5	2782.8	2835.9	2871.9	2895.3	2887.5	2892.2
22.5°	2570.3	2668.8	2754.7	2839.1	2884.4	2920.3	2971.9	3028.1	3048.5	3061.0	3057.8
25°	2626.6	2729.7	2856.3	2973.5	3020.3	3089.1	3157.8	3212.5	3228.1	3262.5	3231.3
27.5°	2684.4	2829.7	2987.5	3125.0	3184.4	3240.6	3323.5	3364.1	3384.4	3400.0	3389.1
30°	2732.8	2932.8	3104.7	3231.3	3273.5	3306.3	3353.1	3362.5	3354.7	3367.2	3382.8
32.5°	2807.8	3003.1	3148.5	3209.4	3204.7	3203.1	3167.2	3117.2	3106.3	3076.6	3117.2
35°	2848.4	3004.7	3061.0	2979.7	2946.9	2887.5	2773.4	2698.4	2632.8	2618.8	2621.9
37.5°	2825.0	2886.0	2818.8	2604.7	2551.6	2460.9	2309.4	2203.1	2154.7	2117.2	2165.6
40°	2698.4	2631.3	2446.9	2185.9	2109.4	2023.4	1881.3	1823.4	1754.7	1740.6	1804.7
42.5°	2489.1	2284.4	2023.4	1821.9	1742.2	1693.8	1575.0	1520.3	1471.9	1450.0	1485.9
45°	2204.7	1956.3	1693.8	1528.1	1460.9	1403.1	1332.8	1275.0	1243.8	1234.4	1264.1
47.5°	1910.9	1648.4	1439.1	1315.6	1245.3	1201.6	1135.9	1103.1	1078.1	1081.3	1085.9
50°	1629.7	1390.6	1229.7	1106.3	1071.9	1037.5	993.8	965.6	953.1	957.8	954.7
52.5°	1387.5	1193.8	1057.8	962.5	946.9	914.1	878.1	854.7	850.0	851.6	856.3
55°	1175.0	1023.4	915.6	846.9	829.7	806.3	784.4	768.8	756.3	760.9	759.4
57.5°	1014.1	881.3	798.4	742.2	729.7	715.6	695.3	687.5	682.8	673.4	681.3
60°	871.9	764.1	692.2	657.8	646.9	637.5	615.6	606.3	603.1	598.4	610.9
62.5°	737.5	660.9	606.3	575.0	564.1	554.7	543.8	535.9	537.5	531.3	537.5
65°	631.3	568.8	529.7	501.6	487.5	481.3	479.7	467.2	465.6	467.2	468.8
67.5°	532.8	479.7	450.0	432.8	421.9	415.6	410.9	403.1	409.4	404.7	407.8
70°	443.8	407.8	376.6	359.4	354.7	356.3	348.4	345.3	346.9	343.8	346.9
72.5°	357.8	328.1	315.6	303.1	296.9	295.3	290.6	285.9	290.6	289.1	289.1
75°	285.9	264.1	250.0	242.2	242.2	239.1	231.3	231.3	231.3	229.7	231.3
77.5°	220.3	201.6	195.3	187.5	187.5	182.8	181.3	181.3	178.1	182.8	179.7
80°	164.1	150.0	140.6	135.9	135.9	134.4	131.3	129.7	131.3	129.7	129.7
82.5°	106.3	100.0	95.3	90.6	89.1	90.6	89.1	85.9	87.5	85.9	89.1
85°	60.9	54.7	54.7	51.6	53.1	50.0	51.6	48.4	46.9	51.6	48.4
87.5°	26.6	25.0	25.0	21.9	21.9	21.9	20.3	21.9	20.3	18.8	20.3
90°	19.7	20.9	22.1	23.2	24.4	25.5	25.5	25.5	26.7	26.7	26.7
92.5°	373.9	252.0	181.1	134.7	123.6	112.6	94.1	90.6	88.2	85.9	88.2
95°	1006.7	834.8	658.4	515.5	466.8	418.0	335.6	300.7	291.4	272.9	291.4
97.5°	1257.5	1197.1	1056.6	912.6	843.0	773.3	703.6	643.3	611.9	598.0	611.9
100°	1338.8	1428.2	1371.3	1251.7	1191.3	1130.9	1050.8	967.2	924.3	905.7	924.3
102.5°	1290.0	1506.0	1564.0	1522.2	1486.2	1450.2	1363.2	1309.7	1262.1	1249.4	1262.1
105°	1175.1	1453.7	1612.8	1663.9	1657.5	1651.1	1614.0	1575.6	1552.4	1538.5	1552.4
107.5°	1065.9	1346.9	1557.1	1680.1	1705.6	1731.2	1741.7	1735.9	1724.3	1712.7	1724.3
110°	975.3	1226.1	1446.8	1610.5	1659.8	1709.2	1761.4	1783.5	1791.6	1791.6	1791.6

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	908.0	1130.9	1337.6	1503.7	1564.1	1624.4	1706.9	1748.7	1771.9	1782.3	1771.9
115°	862.7	1054.3	1234.3	1393.4	1456.6	1519.9	1610.5	1666.2	1698.7	1713.8	1698.7
117.5°	832.5	1000.9	1160.0	1299.3	1359.1	1418.9	1510.6	1568.7	1601.2	1610.5	1601.2
120°	808.1	959.1	1098.4	1226.1	1277.2	1328.3	1414.3	1470.0	1501.3	1510.6	1501.3
122.5°	787.2	927.7	1054.3	1164.6	1211.6	1258.7	1333.0	1382.9	1414.3	1422.4	1414.3
125°	768.7	897.5	1016.0	1117.0	1158.8	1200.6	1265.6	1313.2	1338.8	1350.4	1338.8
127.5°	751.2	866.2	978.8	1074.0	1113.5	1153.0	1212.2	1255.2	1279.6	1284.2	1279.6
130°	733.8	837.2	939.4	1029.9	1067.6	1105.4	1163.4	1201.8	1225.0	1232.0	1225.0
132.5°	719.9	808.1	902.2	982.3	1018.3	1054.3	1112.4	1150.7	1171.6	1179.7	1171.6
135°	709.4	783.8	863.9	938.2	971.3	1004.4	1055.5	1093.8	1114.7	1121.6	1114.7
137.5°	699.0	761.7	829.0	892.9	922.0	951.0	997.4	1033.4	1053.1	1061.3	1053.1
140°	692.0	744.3	798.9	852.3	876.6	901.0	944.0	974.2	991.6	997.4	991.6
142.5°	686.2	729.2	773.3	817.4	837.8	858.1	892.9	917.3	933.5	938.2	933.5
145°	680.4	716.4	752.4	788.4	804.1	819.8	847.6	867.4	880.1	884.8	880.1
147.5°	674.6	703.6	733.8	762.9	775.0	787.2	810.5	826.7	834.8	837.2	834.8
150°	667.6	693.2	718.7	740.8	751.2	761.7	779.1	793.0	797.7	798.9	797.7
152.5°	659.5	681.6	703.6	723.4	731.0	738.5	752.4	762.9	767.5	768.7	767.5
155°	650.2	670.0	688.5	704.8	711.2	717.6	729.2	737.3	740.8	742.0	740.8
157.5°	642.1	658.4	674.6	687.4	692.6	697.8	707.1	714.1	717.6	717.6	717.6
160°	631.7	646.7	658.4	670.0	674.0	678.1	686.2	692.0	694.4	693.2	694.4
162.5°	622.4	634.0	644.4	653.7	657.2	660.7	666.5	671.1	671.1	671.1	671.1
165°	613.1	622.4	630.5	637.5	640.4	643.3	647.9	650.2	650.2	650.2	650.2
167.5°	603.8	610.8	616.6	622.4	624.7	627.0	629.3	631.7	630.5	630.5	630.5
170°	595.7	601.5	604.9	608.4	609.6	610.8	613.1	614.2	614.2	613.1	614.2
172.5°	587.5	591.0	594.5	596.8	597.4	598.0	598.0	600.3	598.0	596.8	598.0
175°	580.6	584.0	584.0	586.4	586.4	586.4	586.4	587.5	585.2	584.0	585.2
177.5°	577.1	578.2	579.4	579.4	579.4	579.4	578.2	579.4	575.9	575.9	575.9
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1970.3	1959.4	1962.5	1959.4	1951.6	1946.9	1934.4	1918.8	1912.5	1904.7	1900.0
5°	2128.1	2120.3	2118.8	2106.3	2103.1	2084.4	2053.1	2037.5	2018.8	2000.0	1981.3
7.5°	2300.0	2290.6	2259.4	2254.7	2257.8	2234.4	2193.8	2162.5	2123.4	2096.9	2060.9
10°	2442.2	2423.4	2396.9	2398.4	2387.5	2356.3	2315.6	2282.8	2226.6	2192.2	2140.6
12.5°	2528.1	2512.5	2509.4	2493.8	2484.4	2443.8	2395.3	2353.1	2310.9	2264.1	2225.0
15°	2632.8	2612.5	2598.4	2576.6	2570.3	2528.1	2475.0	2426.6	2378.1	2334.4	2251.6
17.5°	2748.4	2726.6	2673.4	2668.8	2631.3	2590.6	2539.1	2467.2	2415.6	2353.1	2292.2
20°	2879.7	2848.4	2779.7	2762.5	2732.8	2665.6	2595.3	2515.6	2432.8	2368.8	2296.9
22.5°	3026.6	2971.9	2921.9	2867.2	2845.3	2762.5	2665.6	2568.8	2468.8	2381.3	2295.3
25°	3217.2	3145.3	3075.0	3020.3	2982.8	2875.0	2745.3	2617.2	2501.6	2387.5	2275.0
27.5°	3367.2	3304.7	3228.1	3156.3	3107.8	2979.7	2831.3	2665.6	2521.9	2382.8	2262.5
30°	3378.1	3359.4	3312.5	3273.5	3220.3	3082.8	2918.8	2731.3	2553.1	2384.4	2237.5
32.5°	3173.5	3211.0	3231.3	3237.5	3226.6	3146.9	2996.9	2790.6	2581.3	2370.3	2215.6
35°	2732.8	2832.8	2956.3	3003.1	3048.5	3090.6	3012.5	2832.8	2590.6	2367.2	2181.3
37.5°	2250.0	2340.6	2545.3	2639.1	2692.2	2859.4	2923.5	2826.6	2609.4	2370.3	2148.4
40°	1815.6	1959.4	2106.3	2232.8	2315.6	2503.1	2701.6	2723.4	2582.8	2340.6	2106.3
42.5°	1528.1	1612.5	1723.4	1840.6	1914.1	2135.9	2404.7	2562.5	2500.0	2292.2	2054.7
45°	1301.6	1364.1	1468.8	1507.8	1601.6	1814.1	2098.4	2326.6	2357.8	2215.6	1995.3
47.5°	1117.2	1170.3	1237.5	1285.9	1360.9	1520.3	1760.9	2012.5	2162.5	2110.9	1912.5
50°	984.4	1028.1	1084.4	1112.5	1160.9	1304.7	1485.9	1735.9	1937.5	1954.7	1804.7
52.5°	873.4	898.4	942.2	973.4	1012.5	1100.0	1264.1	1470.3	1696.9	1790.6	1671.9
55°	776.6	796.9	835.9	856.3	876.6	951.6	1079.7	1267.2	1479.7	1603.1	1535.9
57.5°	689.1	706.3	739.1	757.8	768.8	840.6	939.1	1085.9	1276.6	1426.6	1389.1
60°	617.2	632.8	651.6	665.6	678.1	737.5	806.3	925.0	1095.3	1240.6	1231.3
62.5°	540.6	554.7	575.0	589.1	600.0	637.5	695.3	785.9	931.3	1065.6	1092.2
65°	473.4	484.4	498.4	504.7	518.8	546.9	593.8	675.0	793.8	914.1	932.8
67.5°	412.5	415.6	425.0	439.1	442.2	467.2	509.4	570.3	662.5	760.9	790.6
70°	346.9	351.6	359.4	370.3	376.6	392.2	428.1	468.8	548.4	634.4	656.3
72.5°	289.1	295.3	298.4	304.7	307.8	332.8	348.4	389.1	443.8	515.6	539.1
75°	234.4	240.6	242.2	245.3	248.4	259.4	281.3	306.3	351.6	398.4	429.7
77.5°	185.9	184.4	187.5	192.2	190.6	200.0	214.1	235.9	265.6	304.7	325.0
80°	131.3	131.3	135.9	140.6	139.1	148.4	153.1	168.8	193.8	218.8	226.6
82.5°	87.5	87.5	92.2	92.2	95.3	96.9	103.1	110.9	131.3	143.8	148.4
85°	50.0	50.0	51.6	51.6	51.6	54.7	59.4	62.5	68.8	76.6	79.7
87.5°	20.3	21.9	21.9	21.9	21.9	25.0	25.0	28.1	29.7	32.8	32.8
90°	25.5	25.5	25.5	24.4	23.2	22.1	20.9	19.7	18.6	16.3	15.1
92.5°	90.6	94.1	112.6	123.6	134.7	181.1	252.0	373.9	463.3	471.4	327.4
95°	300.7	335.6	418.0	466.8	515.5	658.4	834.8	1006.7	1028.8	839.5	519.0
97.5°	643.3	703.6	773.3	843.0	912.6	1056.6	1197.1	1257.5	1111.2	769.8	423.8
100°	967.2	1050.8	1130.9	1191.3	1251.7	1371.3	1428.2	1338.8	1048.5	668.8	376.2
102.5°	1309.7	1363.2	1450.2	1486.2	1522.2	1564.0	1506.0	1290.0	938.2	592.2	356.5
105°	1575.6	1614.0	1651.1	1657.5	1663.9	1612.8	1453.7	1175.1	841.8	548.1	354.1
107.5°	1735.9	1741.7	1731.2	1705.6	1680.1	1557.1	1346.9	1065.9	769.8	524.8	362.3
110°	1783.5	1761.4	1709.2	1659.8	1610.5	1446.8	1226.1	975.3	722.2	515.5	375.0

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1748.7	1706.9	1624.4	1564.1	1503.7	1337.6	1130.9	908.0	694.4	515.5	391.3
115°	1666.2	1610.5	1519.9	1456.6	1393.4	1234.3	1054.3	862.7	675.8	519.0	407.6
117.5°	1568.7	1510.6	1418.9	1359.1	1299.3	1160.0	1000.9	832.5	665.3	524.8	426.1
120°	1470.0	1414.3	1328.3	1277.2	1226.1	1098.4	959.1	808.1	658.4	534.1	444.7
122.5°	1382.9	1333.0	1258.7	1211.6	1164.6	1054.3	927.7	787.2	652.6	542.2	465.6
125°	1313.2	1265.6	1200.6	1158.8	1117.0	1016.0	897.5	768.7	647.9	551.5	484.2
127.5°	1255.2	1212.2	1153.0	1113.5	1074.0	978.8	866.2	751.2	645.6	562.0	501.6
130°	1201.8	1163.4	1105.4	1067.6	1029.9	939.4	837.2	733.8	643.3	571.3	519.0
132.5°	1150.7	1112.4	1054.3	1018.3	982.3	902.2	808.1	719.9	643.3	581.7	534.1
135°	1093.8	1055.5	1004.4	971.3	938.2	863.9	783.8	709.4	643.3	591.0	548.1
137.5°	1033.4	997.4	951.0	922.0	892.9	829.0	761.7	699.0	644.4	600.3	558.5
140°	974.2	944.0	901.0	876.6	852.3	798.9	744.3	692.0	645.6	606.1	569.0
142.5°	917.3	892.9	858.1	837.8	817.4	773.3	729.2	686.2	646.7	609.6	574.8
145°	867.4	847.6	819.8	804.1	788.4	752.4	716.4	680.4	645.6	611.9	580.6
147.5°	826.7	810.5	787.2	775.0	762.9	733.8	703.6	674.6	643.3	613.1	584.0
150°	793.0	779.1	761.7	751.2	740.8	718.7	693.2	667.6	639.8	613.1	587.5
152.5°	762.9	752.4	738.5	731.0	723.4	703.6	681.6	659.5	635.1	611.9	589.9
155°	737.3	729.2	717.6	711.2	704.8	688.5	670.0	650.2	629.3	609.6	591.0
157.5°	714.1	707.1	697.8	692.6	687.4	674.6	658.4	642.1	623.5	607.3	592.2
160°	692.0	686.2	678.1	674.0	670.0	658.4	646.7	631.7	617.7	603.8	592.2
162.5°	671.1	666.5	660.7	657.2	653.7	644.4	634.0	622.4	610.8	600.3	591.0
165°	650.2	647.9	643.3	640.4	637.5	630.5	622.4	613.1	603.8	596.8	589.9
167.5°	631.7	629.3	627.0	624.7	622.4	616.6	610.8	603.8	596.8	591.0	587.5
170°	614.2	613.1	610.8	609.6	608.4	604.9	601.5	595.7	591.0	587.5	585.2
172.5°	600.3	598.0	598.0	597.4	596.8	594.5	591.0	587.5	584.0	582.9	582.9
175°	587.5	586.4	586.4	586.4	586.4	584.0	584.0	580.6	579.4	579.4	580.6
177.5°	579.4	578.2	579.4	579.4	579.4	579.4	578.2	577.1	575.9	575.9	578.2
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1893.8	1885.9	1876.6	1876.6	1865.6	1860.9	1851.6	1848.4	1840.6	1828.1	1818.8
5°	1960.9	1940.6	1928.1	1917.2	1893.8	1876.6	1859.4	1840.6	1821.9	1800.0	1775.0
7.5°	2026.6	1989.1	1971.9	1953.1	1918.8	1882.8	1848.4	1823.4	1798.4	1764.1	1732.8
10°	2095.3	2048.4	2017.2	1992.2	1939.1	1893.8	1843.8	1807.8	1768.8	1725.0	1684.4
12.5°	2153.1	2092.2	2065.6	2018.8	1957.8	1903.1	1840.6	1785.9	1734.4	1682.8	1632.8
15°	2201.6	2143.8	2078.1	2059.4	1975.0	1896.9	1826.6	1756.3	1692.2	1640.6	1582.8
17.5°	2217.2	2143.8	2110.9	2065.6	1965.6	1884.4	1795.3	1718.8	1657.8	1581.3	1535.9
20°	2221.9	2151.6	2106.3	2064.1	1975.0	1867.2	1779.7	1685.9	1612.5	1535.9	1464.1
22.5°	2209.4	2126.6	2082.8	2042.2	1942.2	1850.0	1748.4	1645.3	1559.4	1489.1	1417.2
25°	2185.9	2089.1	2046.9	2003.1	1907.8	1806.3	1695.3	1596.9	1517.2	1432.8	1362.5
27.5°	2154.7	2043.8	1995.3	1950.0	1856.3	1760.9	1656.3	1554.7	1465.6	1376.6	1310.9
30°	2115.6	1987.5	1943.8	1884.4	1793.8	1703.1	1607.8	1506.3	1406.3	1321.9	1250.0
32.5°	2065.6	1931.3	1873.4	1817.2	1718.8	1635.9	1545.3	1450.0	1353.1	1270.3	1195.3
35°	2020.3	1867.2	1803.1	1746.9	1637.5	1550.0	1475.0	1385.9	1300.0	1214.1	1146.9
37.5°	1959.4	1803.1	1726.6	1668.8	1557.8	1468.8	1398.4	1329.7	1239.1	1156.3	1093.8
40°	1895.3	1723.4	1651.6	1593.8	1478.1	1381.3	1314.1	1253.1	1179.7	1103.1	1037.5
42.5°	1837.5	1646.9	1570.3	1500.0	1382.8	1296.9	1228.1	1181.3	1114.1	1045.3	985.9
45°	1764.1	1565.6	1482.8	1409.4	1296.9	1203.1	1137.5	1100.0	1050.0	982.8	931.3
47.5°	1689.1	1478.1	1392.2	1320.3	1198.4	1115.6	1051.6	1015.6	981.3	928.1	876.6
50°	1590.6	1385.9	1307.8	1225.0	1104.7	1020.3	967.2	931.3	904.7	867.2	823.4
52.5°	1482.8	1290.6	1206.3	1134.4	1015.6	939.1	878.1	857.8	831.3	803.1	765.6
55°	1368.8	1187.5	1106.3	1035.9	926.6	848.4	798.4	776.6	756.3	734.4	709.4
57.5°	1254.7	1079.7	1003.1	940.6	839.1	764.1	723.4	693.8	679.7	667.2	646.9
60°	1112.5	964.1	904.7	848.4	748.4	679.7	640.6	618.8	606.3	600.0	590.6
62.5°	987.5	865.6	800.0	745.3	665.6	604.7	567.2	550.0	539.1	535.9	525.0
65°	854.7	750.0	698.4	651.6	582.8	528.1	496.9	476.6	468.8	467.2	467.2
67.5°	729.7	645.3	593.8	560.9	501.6	453.1	423.4	415.6	410.9	404.7	403.1
70°	612.5	545.3	500.0	471.9	418.8	382.8	359.4	346.9	346.9	342.2	339.1
72.5°	509.4	442.2	412.5	389.1	345.3	314.1	296.9	293.8	282.8	281.3	281.3
75°	398.4	348.4	328.1	307.8	275.0	253.1	239.1	231.3	225.0	225.0	226.6
77.5°	300.0	265.6	246.9	231.3	207.8	193.8	182.8	179.7	173.4	173.4	173.4
80°	212.5	193.8	179.7	167.2	150.0	137.5	131.3	125.0	125.0	123.4	125.0
82.5°	137.5	121.9	114.1	112.5	96.9	92.2	84.4	85.9	81.3	79.7	82.8
85°	79.7	71.9	62.5	59.4	53.1	46.9	43.8	45.3	43.8	42.2	43.8
87.5°	31.3	26.6	25.0	25.0	20.3	18.8	17.2	18.8	15.6	15.6	17.2
90°	12.8	11.6	10.4	9.3	7.0	4.6	2.3	1.2	2.3	4.6	7.0
92.5°	195.1	116.1	95.2	74.3	49.9	32.5	20.9	17.4	20.9	32.5	49.9
95°	263.6	139.3	113.2	87.1	61.5	48.8	39.5	38.3	39.5	48.8	61.5
97.5°	227.6	141.7	122.5	103.3	80.1	67.3	60.4	59.2	60.4	67.3	80.1
100°	225.3	157.9	140.5	123.1	101.0	88.2	83.6	81.3	83.6	88.2	101.0
102.5°	235.7	177.7	160.8	144.0	124.2	110.3	106.8	105.7	106.8	110.3	124.2
105°	250.8	199.7	183.4	167.2	148.6	137.0	131.2	131.2	131.2	137.0	148.6
107.5°	271.7	221.8	207.2	192.7	173.0	163.7	157.9	155.6	157.9	163.7	173.0
110°	294.9	247.3	232.2	217.1	199.7	189.3	184.6	182.3	184.6	189.3	199.7

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	317.0	271.7	257.2	242.7	225.3	214.8	211.3	209.0	211.3	214.8	225.3
115°	340.2	297.2	282.7	268.2	250.8	240.4	236.9	234.5	236.9	240.4	250.8
117.5°	363.4	322.8	308.8	294.9	275.2	264.7	261.3	257.8	261.3	264.7	275.2
120°	389.0	348.3	333.8	319.3	299.6	289.1	284.5	281.0	284.5	289.1	299.6
122.5°	413.4	372.7	358.2	343.7	321.6	311.2	307.7	305.4	307.7	311.2	321.6
125°	434.3	395.9	380.8	365.8	343.7	333.2	327.4	325.1	327.4	333.2	343.7
127.5°	455.2	418.0	402.9	387.8	364.6	351.8	344.9	341.4	344.9	351.8	364.6
130°	474.9	438.9	423.8	408.7	384.3	369.2	359.9	356.5	359.9	369.2	384.3
132.5°	493.5	457.5	442.4	427.3	401.7	384.3	372.7	368.1	372.7	384.3	401.7
135°	509.7	473.7	458.0	442.4	418.0	399.4	385.5	380.8	385.5	399.4	418.0
137.5°	521.3	488.8	472.6	456.3	431.9	413.4	400.6	397.1	400.6	413.4	431.9
140°	534.1	500.4	484.8	469.1	447.0	428.5	414.5	411.0	414.5	428.5	447.0
142.5°	542.2	510.9	496.4	481.9	461.0	442.4	429.6	427.3	429.6	442.4	461.0
145°	551.5	521.3	508.0	494.6	473.7	457.5	445.9	443.5	445.9	457.5	473.7
147.5°	557.3	530.6	518.4	506.3	487.7	472.6	462.1	461.0	462.1	472.6	487.7
150°	563.1	537.6	527.8	517.9	501.6	486.5	478.4	476.1	478.4	486.5	501.6
152.5°	569.0	545.7	537.0	528.3	513.2	500.4	493.5	492.3	493.5	500.4	513.2
155°	572.4	552.7	544.6	536.4	524.8	513.2	506.3	506.3	506.3	513.2	524.8
157.5°	575.9	558.5	552.1	545.7	535.3	524.8	519.0	519.0	519.0	524.8	535.3
160°	578.2	563.1	557.9	552.7	543.4	535.3	530.6	531.8	530.6	535.3	543.4
162.5°	580.6	567.8	563.8	559.7	552.7	545.7	541.1	542.2	541.1	545.7	552.7
165°	580.6	571.3	567.8	564.3	559.7	553.9	550.4	552.7	550.4	553.9	559.7
167.5°	580.6	572.4	570.1	567.8	564.3	560.8	558.5	559.7	558.5	560.8	564.3
170°	580.6	574.8	573.0	571.3	569.0	566.6	565.5	566.6	565.5	566.6	569.0
172.5°	579.4	574.8	574.2	573.6	572.4	570.1	569.0	571.3	569.0	570.1	572.4
175°	578.2	574.8	574.8	574.8	574.8	573.6	572.4	574.8	572.4	573.6	574.8
177.5°	577.1	574.8	574.8	574.8	575.9	574.8	574.8	577.1	574.8	574.8	575.9
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1815.6	1812.5	1804.7	1800.0	1784.4	1765.6	1759.4	1743.8	1750.0	1739.1	1739.1
5°	1767.2	1753.1	1743.8	1729.7	1700.0	1679.7	1657.8	1646.9	1640.6	1632.8	1626.6
7.5°	1704.7	1693.8	1684.4	1657.8	1625.0	1596.9	1570.3	1559.4	1539.1	1525.0	1518.8
10°	1650.0	1634.4	1612.5	1581.3	1546.9	1510.9	1487.5	1464.1	1448.4	1440.6	1423.4
12.5°	1593.8	1575.0	1551.6	1506.3	1468.8	1446.9	1404.7	1382.8	1375.0	1368.8	1348.4
15°	1535.9	1515.6	1487.5	1445.3	1412.5	1360.9	1335.9	1318.8	1300.0	1298.4	1282.8
17.5°	1484.4	1459.4	1435.9	1384.4	1343.8	1298.4	1284.4	1265.6	1248.4	1229.7	1221.9
20°	1418.8	1395.3	1378.1	1321.9	1276.6	1248.4	1225.0	1209.4	1198.4	1179.7	1176.6
22.5°	1359.4	1334.4	1310.9	1268.8	1229.7	1193.8	1165.6	1148.4	1143.8	1135.9	1121.9
25°	1301.6	1276.6	1248.4	1209.4	1168.8	1143.8	1118.8	1107.8	1098.4	1085.9	1075.0
27.5°	1253.1	1229.7	1203.1	1154.7	1120.3	1101.6	1075.0	1062.5	1050.0	1043.8	1039.1
30°	1195.3	1168.8	1148.4	1110.9	1073.4	1048.4	1029.7	1018.8	1007.8	1001.6	998.4
32.5°	1139.1	1114.1	1100.0	1059.4	1029.7	1000.0	985.9	978.1	971.9	965.6	959.4
35°	1093.8	1068.8	1046.9	1009.4	979.7	959.4	948.4	935.9	931.3	925.0	925.0
37.5°	1037.5	1018.8	996.9	960.9	934.4	918.8	909.4	893.8	892.2	889.1	884.4
40°	989.1	970.3	950.0	918.8	895.3	876.6	864.1	856.3	851.6	848.4	845.3
42.5°	937.5	917.2	907.8	871.9	851.6	832.8	826.6	818.8	817.2	810.9	803.1
45°	887.5	870.3	851.6	825.0	807.8	792.2	782.8	776.6	768.8	767.2	762.5
47.5°	843.8	823.4	806.3	781.3	762.5	750.0	742.2	734.4	728.1	723.4	718.8
50°	787.5	771.9	757.8	731.3	715.6	703.1	692.2	685.9	679.7	679.7	679.7
52.5°	732.8	718.8	706.3	687.5	668.8	657.8	645.3	640.6	637.5	632.8	637.5
55°	679.7	665.6	653.1	639.1	617.2	607.8	595.3	590.6	592.2	592.2	596.9
57.5°	623.4	612.5	604.7	587.5	567.2	557.8	550.0	545.3	545.3	551.6	553.1
60°	568.8	557.8	543.8	528.1	515.6	504.7	500.0	501.6	501.6	504.7	512.5
62.5°	507.8	501.6	493.8	471.9	464.1	456.3	450.0	454.7	453.1	460.9	471.9
65°	451.6	445.3	434.4	423.4	414.1	406.3	404.7	406.3	409.4	417.2	429.7
67.5°	389.1	389.1	379.7	370.3	362.5	354.7	356.3	357.8	360.9	370.3	389.1
70°	337.5	331.3	321.9	315.6	309.4	306.3	303.1	309.4	318.8	325.0	339.1
72.5°	281.3	276.6	268.8	262.5	260.9	257.8	256.3	259.4	268.8	279.7	295.3
75°	221.9	223.4	218.8	214.1	214.1	209.4	212.5	212.5	221.9	232.8	245.3
77.5°	171.9	170.3	168.8	165.6	164.1	164.1	164.1	167.2	176.6	182.8	195.3
80°	121.9	123.4	118.8	120.3	118.8	120.3	120.3	126.6	131.3	139.1	148.4
82.5°	81.3	81.3	78.1	79.7	79.7	79.7	81.3	84.4	90.6	96.9	103.1
85°	45.3	46.9	43.8	46.9	46.9	46.9	48.4	50.0	54.7	56.3	62.5
87.5°	17.2	20.3	20.3	17.2	18.8	20.3	21.9	20.3	23.4	26.6	28.1
90°	9.3	10.4	11.6	12.8	15.1	16.3	18.6	19.7	20.9	22.1	23.2
92.5°	74.3	95.2	116.1	195.1	327.4	471.4	463.3	373.9	252.0	181.1	134.7
95°	87.1	113.2	139.3	263.6	519.0	839.5	1028.8	1006.7	834.8	658.4	515.5
97.5°	103.3	122.5	141.7	227.6	423.8	769.8	1111.2	1257.5	1197.1	1056.6	912.6
100°	123.1	140.5	157.9	225.3	376.2	668.8	1048.5	1338.8	1428.2	1371.3	1251.7
102.5°	144.0	160.8	177.7	235.7	356.5	592.2	938.2	1290.0	1506.0	1564.0	1522.2
105°	167.2	183.4	199.7	250.8	354.1	548.1	841.8	1175.1	1453.7	1612.8	1663.9
107.5°	192.7	207.2	221.8	271.7	362.3	524.8	769.8	1065.9	1346.9	1557.1	1680.1
110°	217.1	232.2	247.3	294.9	375.0	515.5	722.2	975.3	1226.1	1446.8	1610.5

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	242.7	257.2	271.7	317.0	391.3	515.5	694.4	908.0	1130.9	1337.6	1503.7
115°	268.2	282.7	297.2	340.2	407.6	519.0	675.8	862.7	1054.3	1234.3	1393.4
117.5°	294.9	308.8	322.8	363.4	426.1	524.8	665.3	832.5	1000.9	1160.0	1299.3
120°	319.3	333.8	348.3	389.0	444.7	534.1	658.4	808.1	959.1	1098.4	1226.1
122.5°	343.7	358.2	372.7	413.4	465.6	542.2	652.6	787.2	927.7	1054.3	1164.6
125°	365.8	380.8	395.9	434.3	484.2	551.5	647.9	768.7	897.5	1016.0	1117.0
127.5°	387.8	402.9	418.0	455.2	501.6	562.0	645.6	751.2	866.2	978.8	1074.0
130°	408.7	423.8	438.9	474.9	519.0	571.3	643.3	733.8	837.2	939.4	1029.9
132.5°	427.3	442.4	457.5	493.5	534.1	581.7	643.3	719.9	808.1	902.2	982.3
135°	442.4	458.0	473.7	509.7	548.1	591.0	643.3	709.4	783.8	863.9	938.2
137.5°	456.3	472.6	488.8	521.3	558.5	600.3	644.4	699.0	761.7	829.0	892.9
140°	469.1	484.8	500.4	534.1	569.0	606.1	645.6	692.0	744.3	798.9	852.3
142.5°	481.9	496.4	510.9	542.2	574.8	609.6	646.7	686.2	729.2	773.3	817.4
145°	494.6	508.0	521.3	551.5	580.6	611.9	645.6	680.4	716.4	752.4	788.4
147.5°	506.3	518.4	530.6	557.3	584.0	613.1	643.3	674.6	703.6	733.8	762.9
150°	517.9	527.8	537.6	563.1	587.5	613.1	639.8	667.6	693.2	718.7	740.8
152.5°	528.3	537.0	545.7	569.0	589.9	611.9	635.1	659.5	681.6	703.6	723.4
155°	536.4	544.6	552.7	572.4	591.0	609.6	629.3	650.2	670.0	688.5	704.8
157.5°	545.7	552.1	558.5	575.9	592.2	607.3	623.5	642.1	658.4	674.6	687.4
160°	552.7	557.9	563.1	578.2	592.2	603.8	617.7	631.7	646.7	658.4	670.0
162.5°	559.7	563.8	567.8	580.6	591.0	600.3	610.8	622.4	634.0	644.4	653.7
165°	564.3	567.8	571.3	580.6	589.9	596.8	603.8	613.1	622.4	630.5	637.5
167.5°	567.8	570.1	572.4	580.6	587.5	591.0	596.8	603.8	610.8	616.6	622.4
170°	571.3	573.0	574.8	580.6	585.2	587.5	591.0	595.7	601.5	604.9	608.4
172.5°	573.6	574.2	574.8	579.4	582.9	582.9	584.0	587.5	591.0	594.5	596.8
175°	574.8	574.8	574.8	578.2	580.6	579.4	579.4	580.6	584.0	584.0	586.4
177.5°	574.8	574.8	574.8	577.1	578.2	575.9	575.9	577.1	578.2	579.4	579.4
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1745.3	1734.4	1732.8	1735.9	1729.7	1739.1	1735.9	1739.1	1731.3	1739.1	1734.4
5°	1625.0	1621.9	1615.6	1607.8	1609.4	1610.9	1618.8	1610.9	1617.2	1618.8	1626.6
7.5°	1512.5	1506.3	1510.9	1507.8	1493.8	1490.6	1493.8	1498.4	1507.8	1514.1	1518.8
10°	1421.9	1418.8	1412.5	1407.8	1400.0	1395.3	1401.6	1395.3	1407.8	1418.8	1418.8
12.5°	1353.1	1340.6	1332.8	1331.3	1314.1	1317.2	1323.4	1328.1	1342.2	1348.4	1348.4
15°	1281.3	1271.9	1268.8	1262.5	1256.3	1262.5	1259.4	1264.1	1270.3	1276.6	1279.7
17.5°	1218.8	1217.2	1218.8	1203.1	1207.8	1200.0	1201.6	1209.4	1204.7	1209.4	1218.8
20°	1162.5	1165.6	1160.9	1154.7	1154.7	1145.3	1156.3	1153.1	1154.7	1164.1	1178.1
22.5°	1120.3	1118.8	1114.1	1109.4	1103.1	1104.7	1106.3	1103.1	1115.6	1123.4	1125.0
25°	1075.0	1071.9	1070.3	1065.6	1059.4	1065.6	1064.1	1065.6	1068.8	1081.3	1071.9
27.5°	1032.8	1026.6	1029.7	1025.0	1023.4	1025.0	1025.0	1026.6	1029.7	1031.3	1032.8
30°	996.9	990.6	989.1	985.9	984.4	985.9	989.1	985.9	998.4	996.9	996.9
32.5°	957.8	953.1	950.0	950.0	948.4	946.9	948.4	950.0	959.4	953.1	959.4
35°	920.3	917.2	917.2	914.1	912.5	912.5	912.5	918.8	915.6	920.3	920.3
37.5°	884.4	884.4	882.8	879.7	878.1	879.7	878.1	881.3	879.7	881.3	882.8
40°	846.9	843.8	842.2	842.2	837.5	832.8	837.5	837.5	839.1	843.8	845.3
42.5°	801.6	803.1	803.1	796.9	796.9	796.9	798.4	800.0	800.0	803.1	803.1
45°	762.5	759.4	759.4	759.4	756.3	757.8	760.9	760.9	760.9	760.9	757.8
47.5°	718.8	718.8	720.3	720.3	725.0	723.4	723.4	721.9	718.8	718.8	720.3
50°	678.1	682.8	684.4	684.4	685.9	687.5	687.5	684.4	682.8	678.1	678.1
52.5°	639.1	642.2	645.3	650.0	653.1	651.6	651.6	648.4	642.2	640.6	639.1
55°	596.9	601.6	607.8	612.5	617.2	618.8	618.8	612.5	606.3	598.4	598.4
57.5°	557.8	562.5	573.4	578.1	584.4	584.4	581.3	576.6	567.2	560.9	556.3
60°	518.8	526.6	534.4	543.8	551.6	553.1	548.4	542.2	531.3	523.4	517.2
62.5°	476.6	484.4	500.0	509.4	515.6	515.6	515.6	507.8	493.8	482.8	473.4
65°	435.9	443.8	457.8	470.3	475.0	479.7	475.0	467.2	456.3	443.8	434.4
67.5°	393.8	403.1	417.2	426.6	432.8	437.5	434.4	428.1	414.1	396.9	390.6
70°	346.9	351.6	371.9	381.3	390.6	393.8	390.6	381.3	367.2	348.4	342.2
72.5°	303.1	307.8	326.6	334.4	342.2	345.3	340.6	334.4	321.9	304.7	296.9
75°	253.1	260.9	270.3	282.8	292.2	295.3	290.6	285.9	270.3	259.4	253.1
77.5°	200.0	207.8	220.3	231.3	240.6	239.1	232.8	234.4	217.2	204.7	200.0
80°	151.6	157.8	167.2	176.6	181.3	181.3	179.7	173.4	167.2	157.8	150.0
82.5°	104.7	112.5	120.3	126.6	126.6	128.1	125.0	123.4	117.2	109.4	107.8
85°	62.5	64.1	70.3	70.3	76.6	73.4	71.9	76.6	70.3	65.6	64.1
87.5°	28.1	26.6	28.1	28.1	26.6	29.7	29.7	28.1	29.7	28.1	28.1
90°	24.4	25.5	25.5	25.5	26.7	26.7	26.7	25.5	25.5	25.5	24.4
92.5°	123.6	112.6	94.1	90.6	88.2	85.9	88.2	90.6	94.1	112.6	123.6
95°	466.8	418.0	335.6	300.7	291.4	272.9	291.4	300.7	335.6	418.0	466.8
97.5°	843.0	773.3	703.6	643.3	611.9	598.0	611.9	643.3	703.6	773.3	843.0
100°	1191.3	1130.9	1050.8	967.2	924.3	905.7	924.3	967.2	1050.8	1130.9	1191.3
102.5°	1486.2	1450.2	1363.2	1309.7	1262.1	1249.4	1262.1	1309.7	1363.2	1450.2	1486.2
105°	1657.5	1651.1	1614.0	1575.6	1552.4	1538.5	1552.4	1575.6	1614.0	1651.1	1657.5
107.5°	1705.6	1731.2	1741.7	1735.9	1724.3	1712.7	1724.3	1735.9	1741.7	1731.2	1705.6
110°	1659.8	1709.2	1761.4	1783.5	1791.6	1791.6	1791.6	1783.5	1761.4	1709.2	1659.8



TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1564.1	1624.4	1706.9	1748.7	1771.9	1782.3	1771.9	1748.7	1706.9	1624.4	1564.1
115°	1456.6	1519.9	1610.5	1666.2	1698.7	1713.8	1698.7	1666.2	1610.5	1519.9	1456.6
117.5°	1359.1	1418.9	1510.6	1568.7	1601.2	1610.5	1601.2	1568.7	1510.6	1418.9	1359.1
120°	1277.2	1328.3	1414.3	1470.0	1501.3	1510.6	1501.3	1470.0	1414.3	1328.3	1277.2
122.5°	1211.6	1258.7	1333.0	1382.9	1414.3	1422.4	1414.3	1382.9	1333.0	1258.7	1211.6
125°	1158.8	1200.6	1265.6	1313.2	1338.8	1350.4	1338.8	1313.2	1265.6	1200.6	1158.8
127.5°	1113.5	1153.0	1212.2	1255.2	1279.6	1284.2	1279.6	1255.2	1212.2	1153.0	1113.5
130°	1067.6	1105.4	1163.4	1201.8	1225.0	1232.0	1225.0	1201.8	1163.4	1105.4	1067.6
132.5°	1018.3	1054.3	1112.4	1150.7	1171.6	1179.7	1171.6	1150.7	1112.4	1054.3	1018.3
135°	971.3	1004.4	1055.5	1093.8	1114.7	1121.6	1114.7	1093.8	1055.5	1004.4	971.3
137.5°	922.0	951.0	997.4	1033.4	1053.1	1061.3	1053.1	1033.4	997.4	951.0	922.0
140°	876.6	901.0	944.0	974.2	991.6	997.4	991.6	974.2	944.0	901.0	876.6
142.5°	837.8	858.1	892.9	917.3	933.5	938.2	933.5	917.3	892.9	858.1	837.8
145°	804.1	819.8	847.6	867.4	880.1	884.8	880.1	867.4	847.6	819.8	804.1
147.5°	775.0	787.2	810.5	826.7	834.8	837.2	834.8	826.7	810.5	787.2	775.0
150°	751.2	761.7	779.1	793.0	797.7	798.9	797.7	793.0	779.1	761.7	751.2
152.5°	731.0	738.5	752.4	762.9	767.5	768.7	767.5	762.9	752.4	738.5	731.0
155°	711.2	717.6	729.2	737.3	740.8	742.0	740.8	737.3	729.2	717.6	711.2
157.5°	692.6	697.8	707.1	714.1	717.6	717.6	717.6	714.1	707.1	697.8	692.6
160°	674.0	678.1	686.2	692.0	694.4	693.2	694.4	692.0	686.2	678.1	674.0
162.5°	657.2	660.7	666.5	671.1	671.1	671.1	671.1	671.1	666.5	660.7	657.2
165°	640.4	643.3	647.9	650.2	650.2	650.2	650.2	650.2	647.9	643.3	640.4
167.5°	624.7	627.0	629.3	631.7	630.5	630.5	630.5	631.7	629.3	627.0	624.7
170°	609.6	610.8	613.1	614.2	614.2	613.1	614.2	614.2	613.1	610.8	609.6
172.5°	597.4	598.0	598.0	600.3	598.0	596.8	598.0	600.3	598.0	598.0	597.4
175°	586.4	586.4	586.4	587.5	585.2	584.0	585.2	587.5	586.4	586.4	586.4
177.5°	579.4	579.4	578.2	579.4	575.9	575.9	575.9	579.4	578.2	579.4	579.4
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1748.4	1739.1	1750.0	1735.9	1739.1	1756.3	1754.7	1770.3	1779.7	1778.1	1785.9
5°	1632.8	1632.8	1637.5	1635.9	1651.6	1665.6	1684.4	1700.0	1717.2	1726.6	1737.5
7.5°	1518.8	1534.4	1537.5	1545.3	1564.1	1587.5	1606.3	1629.7	1654.7	1671.9	1684.4
10°	1425.0	1437.5	1450.0	1456.3	1476.6	1507.8	1534.4	1571.9	1603.1	1621.9	1639.1
12.5°	1342.2	1356.3	1362.5	1390.6	1404.7	1425.0	1462.5	1503.1	1537.5	1557.8	1571.9
15°	1282.8	1290.6	1304.7	1321.9	1335.9	1360.9	1392.2	1437.5	1470.3	1487.5	1535.9
17.5°	1232.8	1242.2	1250.0	1257.8	1279.7	1306.3	1335.9	1375.0	1417.2	1446.9	1471.9
20°	1181.3	1185.9	1195.3	1207.8	1223.4	1248.4	1275.0	1315.6	1353.1	1376.6	1409.4
22.5°	1120.3	1134.4	1143.8	1153.1	1170.3	1198.4	1223.4	1253.1	1300.0	1326.6	1360.9
25°	1084.4	1090.6	1096.9	1107.8	1120.3	1145.3	1173.4	1204.7	1242.2	1270.3	1300.0
27.5°	1037.5	1046.9	1054.7	1068.8	1076.6	1096.9	1123.4	1154.7	1200.0	1223.4	1248.4
30°	998.4	1007.8	1014.1	1020.3	1031.3	1053.1	1078.1	1103.1	1145.3	1175.0	1200.0
32.5°	959.4	968.8	976.6	981.3	992.2	1006.3	1026.6	1057.8	1093.8	1114.1	1146.9
35°	925.0	925.0	934.4	940.6	950.0	962.5	981.3	1004.7	1042.2	1068.8	1098.4
37.5°	885.9	887.5	895.3	900.0	909.4	921.9	940.6	962.5	993.8	1014.1	1043.8
40°	845.3	850.0	853.1	860.9	871.9	876.6	895.3	920.3	951.6	970.3	995.3
42.5°	804.7	807.8	815.6	821.9	831.3	839.1	851.6	875.0	898.4	926.6	946.9
45°	759.4	767.2	771.9	782.8	787.5	795.3	807.8	826.6	854.7	871.9	895.3
47.5°	720.3	723.4	726.6	740.6	750.0	754.7	767.2	778.1	807.8	823.4	845.3
50°	678.1	678.1	682.8	689.1	700.0	709.4	720.3	732.8	756.3	771.9	793.8
52.5°	639.1	634.4	637.5	640.6	651.6	660.9	671.9	689.1	710.9	720.3	739.1
55°	596.9	589.1	593.8	598.4	601.6	614.1	626.6	637.5	654.7	668.8	685.9
57.5°	551.6	550.0	546.9	548.4	556.3	564.1	573.4	587.5	607.8	618.8	628.1
60°	510.9	501.6	498.4	501.6	506.3	510.9	523.4	535.9	553.1	564.1	575.0
62.5°	468.8	459.4	453.1	448.4	453.1	464.1	471.9	481.3	495.3	507.8	517.2
65°	428.1	414.1	407.8	404.7	403.1	410.9	417.2	429.7	442.2	446.9	457.8
67.5°	382.8	370.3	362.5	357.8	357.8	357.8	364.1	376.6	389.1	390.6	401.6
70°	337.5	323.4	315.6	309.4	306.3	309.4	317.2	318.8	329.7	332.8	339.1
72.5°	289.1	276.6	267.2	259.4	260.9	264.1	264.1	267.2	273.4	281.3	281.3
75°	243.8	226.6	221.9	215.6	212.5	212.5	212.5	218.8	223.4	229.7	228.1
77.5°	192.2	182.8	173.4	170.3	165.6	164.1	167.2	167.2	170.3	175.0	176.6
80°	148.4	137.5	131.3	128.1	121.9	120.3	121.9	121.9	126.6	125.0	126.6
82.5°	103.1	95.3	90.6	85.9	82.8	84.4	82.8	82.8	84.4	82.8	82.8
85°	59.4	57.8	54.7	53.1	51.6	48.4	51.6	50.0	48.4	46.9	50.0
87.5°	28.1	26.6	26.6	23.4	23.4	21.9	23.4	23.4	21.9	21.9	21.9
90°	23.2	22.1	20.9	19.7	18.6	16.3	15.1	12.8	11.6	10.4	9.3
92.5°	134.7	181.1	252.0	373.9	463.3	471.4	327.4	195.1	116.1	95.2	74.3
95°	515.5	658.4	834.8	1006.7	1028.8	839.5	519.0	263.6	139.3	113.2	87.1
97.5°	912.6	1056.6	1197.1	1257.5	1111.2	769.8	423.8	227.6	141.7	122.5	103.3
100°	1251.7	1371.3	1428.2	1338.8	1048.5	668.8	376.2	225.3	157.9	140.5	123.1
102.5°	1522.2	1564.0	1506.0	1290.0	938.2	592.2	356.5	235.7	177.7	160.8	144.0
105°	1663.9	1612.8	1453.7	1175.1	841.8	548.1	354.1	250.8	199.7	183.4	167.2
107.5°	1680.1	1557.1	1346.9	1065.9	769.8	524.8	362.3	271.7	221.8	207.2	192.7
110°	1610.5	1446.8	1226.1	975.3	722.2	515.5	375.0	294.9	247.3	232.2	217.1



TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1503.7	1337.6	1130.9	908.0	694.4	515.5	391.3	317.0	271.7	257.2	242.7
115°	1393.4	1234.3	1054.3	862.7	675.8	519.0	407.6	340.2	297.2	282.7	268.2
117.5°	1299.3	1160.0	1000.9	832.5	665.3	524.8	426.1	363.4	322.8	308.8	294.9
120°	1226.1	1098.4	959.1	808.1	658.4	534.1	444.7	389.0	348.3	333.8	319.3
122.5°	1164.6	1054.3	927.7	787.2	652.6	542.2	465.6	413.4	372.7	358.2	343.7
125°	1117.0	1016.0	897.5	768.7	647.9	551.5	484.2	434.3	395.9	380.8	365.8
127.5°	1074.0	978.8	866.2	751.2	645.6	562.0	501.6	455.2	418.0	402.9	387.8
130°	1029.9	939.4	837.2	733.8	643.3	571.3	519.0	474.9	438.9	423.8	408.7
132.5°	982.3	902.2	808.1	719.9	643.3	581.7	534.1	493.5	457.5	442.4	427.3
135°	938.2	863.9	783.8	709.4	643.3	591.0	548.1	509.7	473.7	458.0	442.4
137.5°	892.9	829.0	761.7	699.0	644.4	600.3	558.5	521.3	488.8	472.6	456.3
140°	852.3	798.9	744.3	692.0	645.6	606.1	569.0	534.1	500.4	484.8	469.1
142.5°	817.4	773.3	729.2	686.2	646.7	609.6	574.8	542.2	510.9	496.4	481.9
145°	788.4	752.4	716.4	680.4	645.6	611.9	580.6	551.5	521.3	508.0	494.6
147.5°	762.9	733.8	703.6	674.6	643.3	613.1	584.0	557.3	530.6	518.4	506.3
150°	740.8	718.7	693.2	667.6	639.8	613.1	587.5	563.1	537.6	527.8	517.9
152.5°	723.4	703.6	681.6	659.5	635.1	611.9	589.9	569.0	545.7	537.0	528.3
155°	704.8	688.5	670.0	650.2	629.3	609.6	591.0	572.4	552.7	544.6	536.4
157.5°	687.4	674.6	658.4	642.1	623.5	607.3	592.2	575.9	558.5	552.1	545.7
160°	670.0	658.4	646.7	631.7	617.7	603.8	592.2	578.2	563.1	557.9	552.7
162.5°	653.7	644.4	634.0	622.4	610.8	600.3	591.0	580.6	567.8	563.8	559.7
165°	637.5	630.5	622.4	613.1	603.8	596.8	589.9	580.6	571.3	567.8	564.3
167.5°	622.4	616.6	610.8	603.8	596.8	591.0	587.5	580.6	572.4	570.1	567.8
170°	608.4	604.9	601.5	595.7	591.0	587.5	585.2	580.6	574.8	573.0	571.3
172.5°	596.8	594.5	591.0	587.5	584.0	582.9	582.9	579.4	574.8	574.2	573.6
175°	586.4	584.0	584.0	580.6	579.4	579.4	580.6	578.2	574.8	574.8	574.8
177.5°	579.4	579.4	578.2	577.1	575.9	575.9	578.2	577.1	574.8	574.8	574.8
180°	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9	575.9

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.6	1840.6	1840.6	1840.6
2.5°	1796.9	1812.5	1823.4	1843.8
5°	1756.3	1784.4	1810.9	1839.1
7.5°	1715.6	1748.4	1790.6	1826.6
10°	1670.3	1712.5	1762.5	1810.9
12.5°	1625.0	1675.0	1729.7	1793.8
15°	1570.3	1634.4	1698.4	1767.2
17.5°	1521.9	1587.5	1656.3	1742.2
20°	1467.2	1539.1	1614.1	1701.6
22.5°	1418.8	1498.4	1576.6	1668.8
25°	1364.1	1442.2	1528.1	1626.6
27.5°	1318.8	1390.6	1475.0	1581.3
30°	1264.1	1342.2	1426.6	1532.8
32.5°	1212.5	1287.5	1376.6	1481.3
35°	1159.4	1235.9	1315.6	1415.6
37.5°	1109.4	1175.0	1254.7	1350.0
40°	1053.1	1125.0	1196.9	1271.9
42.5°	1001.6	1067.2	1134.4	1193.8
45°	943.8	1000.0	1064.1	1112.5
47.5°	890.6	940.6	990.6	1028.1
50°	837.5	876.6	914.1	946.9
52.5°	775.0	818.8	839.1	859.4
55°	718.8	743.8	762.5	782.8
57.5°	664.1	675.0	684.4	703.1
60°	592.2	604.7	615.6	629.7
62.5°	529.7	535.9	539.1	553.1
65°	470.3	468.8	476.6	484.4
67.5°	406.3	404.7	412.5	415.6
70°	343.8	342.2	343.8	351.6
72.5°	284.4	284.4	285.9	289.1
75°	229.7	229.7	231.3	234.4
77.5°	173.4	176.6	175.0	181.3
80°	126.6	123.4	126.6	129.7
82.5°	82.8	85.9	85.9	82.8
85°	46.9	46.9	46.9	46.9
87.5°	20.3	20.3	21.9	23.4
90°	7.0	4.6	2.3	1.2
92.5°	49.9	32.5	20.9	17.4
95°	61.5	48.8	39.5	38.3
97.5°	80.1	67.3	60.4	59.2
100°	101.0	88.2	83.6	81.3
102.5°	124.2	110.3	106.8	105.7
105°	148.6	137.0	131.2	131.2
107.5°	173.0	163.7	157.9	155.6
110°	199.7	189.3	184.6	182.3

TEST NUMBER: P1027582

CATALOG NUMBER: S125DIP-B1270D1270UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	225.3	214.8	211.3	209.0
115°	250.8	240.4	236.9	234.5
117.5°	275.2	264.7	261.3	257.8
120°	299.6	289.1	284.5	281.0
122.5°	321.6	311.2	307.7	305.4
125°	343.7	333.2	327.4	325.1
127.5°	364.6	351.8	344.9	341.4
130°	384.3	369.2	359.9	356.5
132.5°	401.7	384.3	372.7	368.1
135°	418.0	399.4	385.5	380.8
137.5°	431.9	413.4	400.6	397.1
140°	447.0	428.5	414.5	411.0
142.5°	461.0	442.4	429.6	427.3
145°	473.7	457.5	445.9	443.5
147.5°	487.7	472.6	462.1	461.0
150°	501.6	486.5	478.4	476.1
152.5°	513.2	500.4	493.5	492.3
155°	524.8	513.2	506.3	506.3
157.5°	535.3	524.8	519.0	519.0
160°	543.4	535.3	530.6	531.8
162.5°	552.7	545.7	541.1	542.2
165°	559.7	553.9	550.4	552.7
167.5°	564.3	560.8	558.5	559.7
170°	569.0	566.6	565.5	566.6
172.5°	572.4	570.1	569.0	571.3
175°	574.8	573.6	572.4	574.8
177.5°	575.9	574.8	574.8	577.1
180°	575.9	575.9	575.9	575.9

(END OF REPORT)