

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027591

Luminaire Tested: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027591
REPORT IS A COMBINATION OF REPORTS P1001614 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9564.0 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	88	85	82	76	73	71	64	63	61	54	53	51
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44
3	83	73	66	60	76	68	62	57	59	54	50	50	47	44	42	40	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	38	38	35	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	33	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	37	32	29	31	28	25
7	59	47	39	33	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	23	20
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11845	11845	11845	11845
5°	11854	13437	11865	10195
10°	11782	15316	11762	8751
15°	11695	16607	11623	7907
20°	11548	18198	11442	7218
25°	11417	20852	11209	6810
30°	11228	21998	11034	6441
35°	10930	17634	10701	6144
40°	10465	12188	10311	5831
45°	9878	9073	9767	5571
50°	9206	7470	9054	5361
55°	8481	6371	8413	5181
60°	7769	5454	7633	5041
65°	7000	4710	6888	4835
70°	6190	3910	6107	4479
75°	5330	3024	5260	3888
80°	4211	2046	4059	2859
85°	2693	1023	2601	1458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18093 cd/sqm

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	1.9
10°-20°	530.0	5.5
20°-30°	860.9	9.0
30°-40°	1052.2	11.0
40°-50°	954.4	10.0
50°-60°	760.2	7.9
60°-70°	529.4	5.5
70°-80°	282.1	2.9
80°-90°	72.2	0.8
90°-100°	420.8	4.4
100°-110°	907.4	9.5
110°-120°	845.9	8.8
120°-130°	685.1	7.2
130°-140°	550.1	5.8
140°-150°	414.9	4.3
150°-160°	292.2	3.1
160°-170°	172.2	1.8
170°-180°	56.0	0.6
0°-30°	1568.8	16.4
0°-40°	2621.0	27.4
0°-60°	4335.5	45.3
0°-90°	5219.3	54.6
90°-120°	2174.1	22.7
90°-150°	3824.3	40.0
90°-180°	4345.0	45.4
0°-180°	9564.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1849	1849	1849	1849	1849	
5°	1847	2133	1849	1618	1847	175
15°	1775	2663	1764	1268	1775	501
25°	1634	3277	1604	1070	1634	752
35°	1422	2630	1392	916	1422	888
45°	1117	1240	1105	761	1117	861
55°	786	764	780	622	786	703
65°	486	469	479	482	486	483
75°	235	231	232	297	235	250
85°	47	52	46	74	47	56
90°	1	27	1	27	1	6
95°	38	274	38	274	38	40
105°	132	1545	132	1545	132	139
115°	236	1721	236	1721	236	232
125°	326	1356	326	1356	326	290
135°	382	1127	382	1127	382	297
145°	446	889	446	889	446	279
155°	508	745	508	745	508	234
165°	555	653	555	653	555	156
175°	577	587	577	587	577	55
180°	578	578	578	578	578	

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1851.9	1862.9	1875.5	1884.9	1900.6	1905.3	1913.1	1917.8	1922.5	1927.3	1930.4
5°	1847.2	1873.9	1897.4	1914.7	1944.5	1955.5	1969.6	1986.9	2007.3	2024.6	2035.5
7.5°	1834.7	1877.0	1908.4	1942.9	1983.8	2010.4	2024.6	2060.7	2093.6	2118.7	2151.7
10°	1819.0	1869.2	1917.8	1969.6	2027.7	2057.5	2085.8	2136.0	2181.5	2222.3	2255.3
12.5°	1801.7	1862.9	1921.0	1988.5	2066.9	2103.0	2121.9	2208.2	2264.7	2286.7	2351.0
15°	1775.0	1847.2	1930.4	2013.6	2079.5	2121.9	2173.7	2242.7	2299.2	2347.9	2399.7
17.5°	1749.9	1828.4	1913.1	2005.7	2101.5	2156.4	2195.6	2256.8	2318.0	2380.8	2429.5
20°	1709.1	1811.1	1897.4	1996.3	2109.3	2148.5	2189.3	2261.5	2327.5	2394.9	2456.2
22.5°	1676.1	1773.5	1891.2	1985.3	2081.1	2120.3	2170.5	2245.8	2324.3	2401.2	2490.7
25°	1633.8	1742.1	1844.1	1944.5	2043.4	2085.8	2131.3	2228.6	2310.2	2409.1	2507.9
27.5°	1588.3	1699.7	1801.7	1892.7	1985.3	2043.4	2092.0	2194.1	2302.3	2410.6	2539.3
30°	1539.6	1644.8	1742.1	1831.5	1933.5	1993.2	2041.8	2161.1	2281.9	2420.1	2573.9
32.5°	1487.8	1586.7	1669.9	1760.9	1869.2	1924.1	1990.0	2120.3	2263.1	2427.9	2620.9
35°	1421.9	1516.1	1589.8	1682.4	1790.7	1861.3	1930.4	2076.4	2242.7	2426.3	2647.6
37.5°	1356.0	1429.7	1500.4	1599.2	1724.8	1789.1	1861.3	2021.4	2211.3	2421.6	2658.6
40°	1277.5	1349.7	1410.9	1511.4	1643.2	1717.0	1792.3	1960.2	2175.2	2404.4	2619.4
42.5°	1199.0	1260.2	1327.7	1432.9	1560.0	1638.5	1718.5	1905.3	2128.1	2354.1	2511.1
45°	1117.4	1164.5	1238.3	1334.0	1469.0	1544.3	1635.3	1837.8	2062.2	2263.1	2341.6
47.5°	1032.7	1079.8	1148.8	1241.4	1374.8	1464.3	1550.6	1753.0	1979.0	2134.4	2134.4
50°	951.1	988.7	1056.2	1148.8	1283.8	1365.4	1453.3	1668.3	1850.4	1964.9	1862.9
52.5°	863.2	905.6	962.1	1059.4	1192.8	1266.5	1362.3	1545.9	1718.5	1765.6	1608.7
55°	786.3	820.8	874.2	966.8	1090.8	1167.7	1249.3	1425.0	1571.0	1567.9	1399.9
57.5°	706.2	734.5	791.0	875.7	990.3	1059.4	1141.0	1293.2	1412.5	1370.1	1211.6
60°	632.5	652.9	707.8	776.9	886.7	951.1	1029.5	1153.5	1244.6	1184.9	1024.8
62.5°	555.6	579.1	623.1	690.5	787.9	839.6	897.7	1023.3	1081.3	1028.0	864.8
65°	486.5	505.4	544.6	601.1	689.0	736.1	786.3	889.9	944.8	867.9	732.9
67.5°	417.5	439.4	467.7	517.9	587.0	630.9	674.9	764.3	789.4	720.4	607.4
70°	353.1	372.0	398.6	434.7	492.8	532.0	565.0	638.8	656.0	591.7	502.2
72.5°	290.3	302.9	324.9	354.7	408.1	430.0	464.6	514.8	536.7	478.7	414.3
75°	235.4	244.8	259.0	280.9	317.0	340.6	368.8	415.9	414.3	373.5	328.0
77.5°	182.1	183.6	199.3	219.7	241.7	262.1	276.2	309.2	312.3	287.2	249.5
80°	130.3	135.0	141.2	156.9	175.8	183.6	200.9	221.3	224.4	205.6	180.5
82.5°	83.2	86.3	91.0	100.4	113.0	122.4	131.8	139.7	147.5	136.5	116.1
85°	47.1	48.7	53.4	56.5	62.8	67.5	75.3	83.2	81.6	73.8	67.5
87.5°	23.5	23.5	23.5	26.7	29.8	29.8	33.0	34.5	36.1	33.0	29.8
90°	1.2	2.3	4.7	7.0	9.3	10.5	11.7	12.8	15.2	16.3	18.7
92.5°	17.5	21.0	32.7	50.1	74.6	95.6	116.6	195.9	328.9	473.5	465.3
95°	38.5	39.7	49.0	61.8	87.5	113.7	139.9	264.7	521.3	843.2	1033.3
97.5°	59.5	60.6	67.6	80.5	103.8	123.0	142.3	228.6	425.7	773.2	1116.1
100°	81.6	84.0	88.6	101.5	123.6	141.1	158.6	226.2	377.9	671.7	1053.1
102.5°	106.1	107.3	110.8	124.8	144.6	161.5	178.4	236.7	358.0	594.8	942.3
105°	131.8	131.8	137.6	149.3	167.9	184.2	200.6	251.9	355.7	550.5	845.5
107.5°	156.3	158.6	164.4	173.8	193.6	208.2	222.7	272.9	363.9	527.1	773.2
110°	183.1	185.4	190.1	200.6	218.1	233.2	248.4	296.2	376.7	517.8	725.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	209.9	212.3	215.8	226.2	243.7	258.3	272.9	318.4	393.0	517.8	697.4
115°	235.6	237.9	241.4	251.9	269.4	284.0	298.6	341.7	409.3	521.3	678.7
117.5°	258.9	262.4	265.9	276.4	296.2	310.2	324.2	365.0	428.0	527.1	668.2
120°	282.2	285.7	290.4	300.9	320.7	335.3	349.9	390.7	446.7	536.5	661.2
122.5°	306.7	309.0	312.5	323.0	345.2	359.8	374.4	415.2	467.7	544.6	655.4
125°	326.5	328.9	334.7	345.2	367.4	382.5	397.7	436.2	486.3	554.0	650.8
127.5°	342.9	346.4	353.4	366.2	389.5	404.6	419.8	457.2	503.8	564.5	648.4
130°	358.0	361.5	370.9	386.0	410.5	425.6	440.8	477.0	521.3	573.8	646.1
132.5°	369.7	374.4	386.0	403.5	429.2	444.4	459.5	495.6	536.5	584.3	646.1
135°	382.5	387.2	401.2	419.8	444.3	460.0	475.8	512.0	550.5	593.6	646.1
137.5°	398.8	402.3	415.2	433.8	458.3	474.6	491.0	523.6	561.0	602.9	647.3
140°	412.8	416.3	430.3	449.0	471.2	486.9	502.6	536.5	571.4	608.8	648.4
142.5°	429.2	431.5	444.3	463.0	484.0	498.6	513.1	544.6	577.3	612.3	649.6
145°	445.5	447.8	459.5	475.8	496.8	510.2	523.6	554.0	583.1	614.6	648.4
147.5°	463.0	464.2	474.7	489.8	508.5	520.8	533.0	559.8	586.6	615.8	646.1
150°	478.2	480.5	488.6	503.8	520.1	530.0	540.0	565.6	590.1	615.8	642.6
152.5°	494.5	495.6	502.6	515.5	530.6	539.4	548.1	571.4	592.4	614.6	637.9
155°	508.5	508.5	515.5	527.1	538.8	547.0	555.1	574.9	593.6	612.3	632.1
157.5°	521.3	521.3	527.1	537.6	548.1	554.6	561.0	578.4	594.8	609.9	626.3
160°	534.1	533.0	537.6	545.8	555.1	560.4	565.6	580.8	594.8	606.4	620.4
162.5°	544.6	543.5	548.1	555.1	562.1	566.2	570.3	583.1	593.6	602.9	613.4
165°	555.1	552.8	556.3	562.1	566.8	570.3	573.8	583.1	592.4	599.4	606.4
167.5°	562.1	561.0	563.3	566.8	570.3	572.6	574.9	583.1	590.1	593.6	599.4
170°	569.1	568.0	569.1	571.4	573.8	575.6	577.3	583.1	587.8	590.1	593.6
172.5°	573.8	571.4	572.6	574.9	576.1	576.7	577.3	581.9	585.4	585.4	586.6
175°	577.3	574.9	576.1	577.3	577.3	577.3	577.3	580.8	583.1	581.9	581.9
177.5°	579.6	577.3	577.3	578.4	577.3	577.3	577.3	579.6	580.8	578.4	578.4
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1933.5	1944.5	1953.9	1961.8	1968.1	1977.5	1971.2	1972.8	1975.9	1982.2	1982.2
5°	2059.1	2076.4	2085.8	2117.2	2125.0	2123.4	2118.7	2143.8	2142.3	2132.8	2131.3
7.5°	2181.5	2211.3	2238.0	2263.1	2271.0	2291.4	2296.1	2307.1	2303.9	2319.6	2311.8
10°	2292.9	2340.0	2365.1	2402.8	2412.2	2421.6	2434.2	2440.5	2454.6	2453.0	2453.0
12.5°	2379.2	2435.7	2468.7	2478.1	2514.2	2525.2	2536.2	2556.6	2551.9	2553.5	2562.9
15°	2446.7	2501.7	2529.9	2573.9	2599.0	2611.5	2630.4	2652.3	2649.2	2663.3	2660.2
17.5°	2497.0	2548.7	2600.5	2666.5	2668.0	2701.0	2744.9	2754.3	2774.7	2760.6	2760.6
20°	2537.8	2606.8	2680.6	2765.3	2774.7	2795.1	2848.5	2884.6	2908.1	2900.3	2905.0
22.5°	2581.7	2680.6	2766.9	2851.6	2897.2	2933.3	2985.0	3041.5	3061.9	3074.5	3071.4
25°	2638.2	2741.8	2868.9	2986.6	3033.7	3102.8	3171.8	3226.7	3242.4	3277.0	3245.6
27.5°	2696.3	2842.2	3000.7	3138.9	3198.5	3255.0	3338.2	3379.0	3399.4	3415.1	3404.1
30°	2744.9	2945.8	3118.4	3245.6	3287.9	3320.9	3368.0	3377.4	3369.6	3382.1	3397.8
32.5°	2820.3	3016.4	3162.4	3223.6	3218.9	3217.3	3181.2	3131.0	3120.0	3090.2	3131.0
35°	2861.1	3018.0	3074.5	2992.9	2959.9	2900.3	2785.7	2710.4	2644.5	2630.4	2633.5
37.5°	2837.5	2898.7	2831.2	2616.2	2562.9	2471.8	2319.6	2212.9	2164.2	2126.6	2175.2
40°	2710.4	2642.9	2457.7	2195.6	2118.7	2032.4	1889.6	1831.5	1762.5	1748.3	1812.7
42.5°	2500.1	2294.5	2032.4	1830.0	1749.9	1701.3	1582.0	1527.1	1478.4	1456.4	1492.5
45°	2214.5	1964.9	1701.3	1534.9	1467.4	1409.3	1338.7	1280.7	1249.3	1239.8	1269.7
47.5°	1919.4	1655.7	1445.4	1321.5	1250.8	1206.9	1141.0	1108.0	1082.9	1086.0	1090.8
50°	1636.9	1396.8	1235.1	1111.2	1076.6	1042.1	998.2	969.9	957.3	962.1	958.9
52.5°	1393.7	1199.0	1062.5	966.8	951.1	918.1	882.0	858.5	853.8	855.3	860.0
55°	1180.2	1028.0	919.7	850.6	833.4	809.8	787.9	772.2	759.6	764.3	762.7
57.5°	1018.6	885.2	802.0	745.5	732.9	718.8	698.4	690.5	685.8	676.4	684.3
60°	875.7	767.4	695.3	660.7	649.7	640.3	618.4	608.9	605.8	601.1	613.6
62.5°	740.8	663.9	608.9	577.5	566.6	557.1	546.2	538.3	539.9	533.6	539.9
65°	634.0	571.3	532.0	503.8	489.7	483.4	481.8	469.3	467.7	469.3	470.8
67.5°	535.2	481.8	452.0	434.7	423.7	417.5	412.8	404.9	411.2	406.5	409.6
70°	445.7	409.6	378.2	361.0	356.3	357.8	350.0	346.8	348.4	345.3	348.4
72.5°	359.4	329.6	317.0	304.5	298.2	296.6	291.9	287.2	291.9	290.3	290.3
75°	287.2	265.2	251.1	243.3	243.3	240.1	232.3	232.3	232.3	230.7	232.3
77.5°	221.3	202.5	196.2	188.3	188.3	183.6	182.1	182.1	178.9	183.6	180.5
80°	164.8	150.7	141.2	136.5	136.5	135.0	131.8	130.3	131.8	130.3	130.3
82.5°	106.7	100.4	95.7	91.0	89.5	91.0	89.5	86.3	87.9	86.3	89.5
85°	61.2	54.9	54.9	51.8	53.4	50.2	51.8	48.7	47.1	51.8	48.7
87.5°	26.7	25.1	25.1	22.0	22.0	22.0	20.4	22.0	20.4	18.8	20.4
90°	19.8	21.0	22.2	23.3	24.5	25.7	25.7	25.7	26.8	26.8	26.8
92.5°	375.5	253.1	181.9	135.3	124.2	113.1	94.5	91.0	88.6	86.3	88.6
95°	1011.1	838.5	661.2	517.8	468.8	419.8	337.0	302.1	292.7	274.1	292.7
97.5°	1263.0	1202.4	1061.3	916.7	846.7	776.7	706.7	646.1	614.6	600.6	614.6
100°	1344.7	1434.5	1377.3	1257.2	1196.6	1135.9	1055.4	971.5	928.3	909.7	928.3
102.5°	1295.7	1512.6	1570.9	1528.9	1492.8	1456.6	1369.1	1315.5	1267.7	1254.9	1267.7
105°	1180.2	1460.1	1619.9	1671.2	1664.8	1658.4	1621.0	1582.6	1559.2	1545.2	1559.2
107.5°	1070.6	1352.8	1563.9	1687.5	1713.2	1738.8	1749.3	1743.5	1731.8	1720.2	1731.8
110°	979.6	1231.5	1453.1	1617.6	1667.2	1716.7	1769.2	1791.3	1799.5	1799.5	1799.5

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	912.0	1135.9	1343.5	1510.3	1570.9	1631.5	1714.3	1756.3	1779.7	1790.2	1779.7
115°	866.5	1058.9	1239.7	1399.5	1463.0	1526.6	1617.6	1673.5	1706.2	1721.3	1706.2
117.5°	836.2	1005.3	1165.1	1305.0	1365.0	1425.1	1517.3	1575.6	1608.2	1617.6	1608.2
120°	811.7	963.3	1103.2	1231.5	1282.8	1334.2	1420.5	1476.4	1507.9	1517.3	1507.9
122.5°	790.7	931.8	1058.9	1169.7	1217.0	1264.2	1338.8	1389.0	1420.5	1428.6	1420.5
125°	772.0	901.5	1020.4	1121.9	1163.9	1205.9	1271.2	1319.0	1344.7	1356.3	1344.7
127.5°	754.5	870.0	983.1	1078.8	1118.4	1158.1	1217.5	1260.7	1285.2	1289.8	1285.2
130°	737.1	840.8	943.5	1034.4	1072.3	1110.2	1168.6	1207.0	1230.4	1237.4	1230.4
132.5°	723.1	811.7	906.2	986.6	1022.8	1058.9	1117.2	1155.7	1176.7	1184.9	1176.7
135°	712.6	787.2	867.7	942.3	975.6	1008.8	1060.1	1098.6	1119.6	1126.6	1119.6
137.5°	702.1	765.0	832.7	896.8	926.0	955.1	1001.8	1037.9	1057.8	1065.9	1057.8
140°	695.1	747.5	802.4	856.0	880.5	905.0	948.1	978.5	996.0	1001.8	996.0
142.5°	689.2	732.4	776.7	821.0	841.4	861.8	896.8	921.3	937.6	942.3	937.6
145°	683.4	719.6	755.7	791.9	807.6	823.4	851.3	871.2	884.0	888.7	884.0
147.5°	677.6	706.7	737.1	766.2	778.4	790.7	814.0	830.4	838.5	840.8	838.5
150°	670.6	696.2	721.9	744.1	754.6	765.0	782.5	796.5	801.2	802.4	801.2
152.5°	662.4	684.6	706.7	726.6	734.2	741.7	755.7	766.2	770.9	772.0	770.9
155°	653.1	672.9	691.6	707.9	714.3	720.7	732.4	740.6	744.1	745.2	744.1
157.5°	644.9	661.2	677.6	690.4	695.6	700.9	710.2	717.2	720.7	720.7	720.7
160°	634.4	649.6	661.2	672.9	677.0	681.1	689.2	695.1	697.4	696.2	697.4
162.5°	625.1	636.8	647.3	656.6	660.1	663.6	669.4	674.1	674.1	674.1	674.1
165°	615.8	625.1	633.3	640.3	643.2	646.1	650.8	653.1	653.1	653.1	653.1
167.5°	606.4	613.4	619.3	625.1	627.4	629.8	632.1	634.4	633.3	633.3	633.3
170°	598.3	604.1	607.6	611.1	612.2	613.4	615.8	616.9	616.9	615.8	616.9
172.5°	590.1	593.6	597.1	599.4	600.0	600.6	600.6	602.9	600.6	599.4	600.6
175°	583.1	586.6	586.6	588.9	588.9	588.9	588.9	590.1	587.8	586.6	587.8
177.5°	579.6	580.8	581.9	581.9	581.9	581.9	580.8	581.9	578.4	578.4	578.4
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1979.0	1968.1	1971.2	1968.1	1960.2	1955.5	1942.9	1927.3	1921.0	1913.1	1908.4
5°	2137.6	2129.7	2128.1	2115.6	2112.4	2093.6	2062.2	2046.5	2027.7	2008.9	1990.0
7.5°	2310.2	2300.8	2269.4	2264.7	2267.8	2244.3	2203.5	2172.1	2132.8	2106.2	2070.1
10°	2453.0	2434.2	2407.5	2409.1	2398.1	2366.7	2325.9	2292.9	2236.4	2201.9	2150.1
12.5°	2539.3	2523.6	2520.5	2504.8	2495.4	2454.6	2405.9	2363.6	2321.2	2274.1	2234.9
15°	2644.5	2624.1	2610.0	2588.0	2581.7	2539.3	2486.0	2437.3	2388.7	2344.7	2261.5
17.5°	2760.6	2738.6	2685.3	2680.6	2642.9	2602.1	2550.3	2478.1	2426.3	2363.6	2302.3
20°	2892.5	2861.1	2792.0	2774.7	2744.9	2677.4	2606.8	2526.8	2443.6	2379.2	2307.1
22.5°	3040.0	2985.0	2934.8	2879.9	2857.9	2774.7	2677.4	2580.1	2479.7	2391.8	2305.5
25°	3231.4	3159.3	3088.6	3033.7	2996.0	2887.7	2757.5	2628.8	2512.7	2398.1	2285.1
27.5°	3382.1	3319.3	3242.4	3170.2	3121.6	2992.9	2843.8	2677.4	2533.1	2393.4	2272.5
30°	3393.1	3374.3	3327.2	3287.9	3234.6	3096.5	2931.7	2743.4	2564.4	2394.9	2247.4
32.5°	3187.5	3225.2	3245.6	3251.9	3240.9	3160.8	3010.2	2803.0	2592.7	2380.8	2225.4
35°	2744.9	2845.4	2969.4	3016.4	3061.9	3104.3	3025.9	2845.4	2602.1	2377.7	2190.9
37.5°	2260.0	2351.0	2556.6	2650.8	2704.1	2872.0	2936.4	2839.1	2620.9	2380.8	2158.0
40°	1823.7	1968.1	2115.6	2242.7	2325.9	2514.2	2713.5	2735.5	2594.3	2351.0	2115.6
42.5°	1534.9	1619.6	1731.1	1848.8	1922.5	2145.4	2415.3	2573.9	2511.1	2302.3	2063.8
45°	1307.3	1370.1	1475.3	1514.5	1608.7	1822.1	2107.7	2336.9	2368.3	2225.4	2004.2
47.5°	1122.1	1175.5	1243.0	1291.6	1367.0	1527.1	1768.7	2021.4	2172.1	2120.3	1921.0
50°	988.7	1032.7	1089.2	1117.4	1166.1	1310.5	1492.5	1743.6	1946.1	1963.4	1812.7
52.5°	877.3	902.4	946.4	977.8	1017.0	1104.9	1269.7	1476.8	1704.4	1798.6	1679.3
55°	780.0	800.4	839.6	860.0	880.4	955.8	1084.5	1272.8	1486.2	1610.2	1542.7
57.5°	692.1	709.4	742.3	761.2	772.2	844.4	943.2	1090.8	1282.2	1432.9	1395.2
60°	619.9	635.6	654.5	668.6	681.1	740.8	809.8	929.1	1100.2	1246.1	1236.7
62.5°	543.0	557.1	577.5	591.7	602.7	640.3	698.4	789.4	935.4	1070.3	1097.0
65°	475.5	486.5	500.6	506.9	521.0	549.3	596.4	678.0	797.3	918.1	936.9
67.5°	414.3	417.5	426.9	441.0	444.1	469.3	511.6	572.8	665.4	764.3	794.1
70°	348.4	353.1	361.0	372.0	378.2	393.9	430.0	470.8	550.9	637.2	659.2
72.5°	290.3	296.6	299.8	306.0	309.2	334.3	350.0	390.8	445.7	517.9	541.5
75°	235.4	241.7	243.3	246.4	249.5	260.5	282.5	307.6	353.1	400.2	431.6
77.5°	186.8	185.2	188.3	193.0	191.5	200.9	215.0	237.0	266.8	306.0	326.4
80°	131.8	131.8	136.5	141.2	139.7	149.1	153.8	169.5	194.6	219.7	227.6
82.5°	87.9	87.9	92.6	92.6	95.7	97.3	103.6	111.4	131.8	144.4	149.1
85°	50.2	50.2	51.8	51.8	51.8	54.9	59.6	62.8	69.1	76.9	80.0
87.5°	20.4	22.0	22.0	22.0	22.0	25.1	25.1	28.2	29.8	33.0	33.0
90°	25.7	25.7	25.7	24.5	23.3	22.2	21.0	19.8	18.7	16.3	15.2
92.5°	91.0	94.5	113.1	124.2	135.3	181.9	253.1	375.5	465.3	473.5	328.9
95°	302.1	337.0	419.8	468.8	517.8	661.2	838.5	1011.1	1033.3	843.2	521.3
97.5°	646.1	706.7	776.7	846.7	916.7	1061.3	1202.4	1263.0	1116.1	773.2	425.7
100°	971.5	1055.4	1135.9	1196.6	1257.2	1377.3	1434.5	1344.7	1053.1	671.7	377.9
102.5°	1315.5	1369.1	1456.6	1492.8	1528.9	1570.9	1512.6	1295.7	942.3	594.8	358.0
105°	1582.6	1621.0	1658.4	1664.8	1671.2	1619.9	1460.1	1180.2	845.5	550.5	355.7
107.5°	1743.5	1749.3	1738.8	1713.2	1687.5	1563.9	1352.8	1070.6	773.2	527.1	363.9
110°	1791.3	1769.2	1716.7	1667.2	1617.6	1453.1	1231.5	979.6	725.4	517.8	376.7

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1756.3	1714.3	1631.5	1570.9	1510.3	1343.5	1135.9	912.0	697.4	517.8	393.0
115°	1673.5	1617.6	1526.6	1463.0	1399.5	1239.7	1058.9	866.5	678.7	521.3	409.3
117.5°	1575.6	1517.3	1425.1	1365.0	1305.0	1165.1	1005.3	836.2	668.2	527.1	428.0
120°	1476.4	1420.5	1334.2	1282.8	1231.5	1103.2	963.3	811.7	661.2	536.5	446.7
122.5°	1389.0	1338.8	1264.2	1217.0	1169.7	1058.9	931.8	790.7	655.4	544.6	467.7
125°	1319.0	1271.2	1205.9	1163.9	1121.9	1020.4	901.5	772.0	650.8	554.0	486.3
127.5°	1260.7	1217.5	1158.1	1118.4	1078.8	983.1	870.0	754.5	648.4	564.5	503.8
130°	1207.0	1168.6	1110.2	1072.3	1034.4	943.5	840.8	737.1	646.1	573.8	521.3
132.5°	1155.7	1117.2	1058.9	1022.8	986.6	906.2	811.7	723.1	646.1	584.3	536.5
135°	1098.6	1060.1	1008.8	975.6	942.3	867.7	787.2	712.6	646.1	593.6	550.5
137.5°	1037.9	1001.8	955.1	926.0	896.8	832.7	765.0	702.1	647.3	602.9	561.0
140°	978.5	948.1	905.0	880.5	856.0	802.4	747.5	695.1	648.4	608.8	571.4
142.5°	921.3	896.8	861.8	841.4	821.0	776.7	732.4	689.2	649.6	612.3	577.3
145°	871.2	851.3	823.4	807.6	791.9	755.7	719.6	683.4	648.4	614.6	583.1
147.5°	830.4	814.0	790.7	778.4	766.2	737.1	706.7	677.6	646.1	615.8	586.6
150°	796.5	782.5	765.0	754.6	744.1	721.9	696.2	670.6	642.6	615.8	590.1
152.5°	766.2	755.7	741.7	734.2	726.6	706.7	684.6	662.4	637.9	614.6	592.4
155°	740.6	732.4	720.7	714.3	707.9	691.6	672.9	653.1	632.1	612.3	593.6
157.5°	717.2	710.2	700.9	695.6	690.4	677.6	661.2	644.9	626.3	609.9	594.8
160°	695.1	689.2	681.1	677.0	672.9	661.2	649.6	634.4	620.4	606.4	594.8
162.5°	674.1	669.4	663.6	660.1	656.6	647.3	636.8	625.1	613.4	602.9	593.6
165°	653.1	650.8	646.1	643.2	640.3	633.3	625.1	615.8	606.4	599.4	592.4
167.5°	634.4	632.1	629.8	627.4	625.1	619.3	613.4	606.4	599.4	593.6	590.1
170°	616.9	615.8	613.4	612.2	611.1	607.6	604.1	598.3	593.6	590.1	587.8
172.5°	602.9	600.6	600.6	600.0	599.4	597.1	593.6	590.1	586.6	585.4	585.4
175°	590.1	588.9	588.9	588.9	588.9	586.6	586.6	583.1	581.9	581.9	583.1
177.5°	581.9	580.8	581.9	581.9	581.9	581.9	580.8	579.6	578.4	578.4	580.8
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1902.1	1894.3	1884.9	1884.9	1873.9	1869.2	1859.8	1856.6	1848.8	1836.2	1826.8
5°	1969.6	1949.2	1936.7	1925.7	1902.1	1884.9	1867.6	1848.8	1830.0	1808.0	1782.9
7.5°	2035.5	1997.9	1980.6	1961.8	1927.3	1891.2	1856.6	1831.5	1806.4	1771.9	1740.5
10°	2104.6	2057.5	2026.1	2001.0	1947.7	1902.1	1851.9	1815.8	1776.6	1732.6	1691.8
12.5°	2162.7	2101.5	2074.8	2027.7	1966.5	1911.6	1848.8	1793.9	1742.1	1690.3	1640.1
15°	2211.3	2153.3	2087.3	2068.5	1983.8	1905.3	1834.7	1764.0	1699.7	1647.9	1589.8
17.5°	2227.0	2153.3	2120.3	2074.8	1974.3	1892.7	1803.3	1726.4	1665.2	1588.3	1542.7
20°	2231.7	2161.1	2115.6	2073.2	1983.8	1875.5	1787.6	1693.4	1619.6	1542.7	1470.6
22.5°	2219.2	2136.0	2092.0	2051.2	1950.8	1858.2	1756.2	1652.6	1566.3	1495.7	1423.5
25°	2195.6	2098.3	2055.9	2012.0	1916.3	1814.3	1702.8	1604.0	1523.9	1439.2	1368.5
27.5°	2164.2	2052.8	2004.2	1958.6	1864.5	1768.7	1663.6	1561.6	1472.1	1382.7	1316.7
30°	2125.0	1996.3	1952.4	1892.7	1801.7	1710.7	1614.9	1512.9	1412.5	1327.7	1255.5
32.5°	2074.8	1939.8	1881.7	1825.2	1726.4	1643.2	1552.2	1456.4	1359.1	1275.9	1200.6
35°	2029.3	1875.5	1811.1	1754.6	1644.8	1556.9	1481.5	1392.1	1305.8	1219.4	1152.0
37.5°	1968.1	1811.1	1734.2	1676.1	1564.7	1475.3	1404.6	1335.6	1244.6	1161.4	1098.6
40°	1903.7	1731.1	1658.9	1600.8	1484.7	1387.4	1319.9	1258.7	1184.9	1108.0	1042.1
42.5°	1845.6	1654.2	1577.3	1506.6	1388.9	1302.6	1233.6	1186.5	1119.0	1049.9	990.3
45°	1771.9	1572.6	1489.4	1415.6	1302.6	1208.5	1142.5	1104.9	1054.7	987.2	935.4
47.5°	1696.5	1484.7	1398.4	1326.2	1203.7	1120.6	1056.2	1020.1	985.6	932.2	880.4
50°	1597.7	1392.1	1313.6	1230.4	1109.6	1024.8	971.5	935.4	908.7	871.0	827.1
52.5°	1489.4	1296.3	1211.6	1139.4	1020.1	943.2	882.0	861.6	834.9	806.7	769.0
55°	1374.8	1192.8	1111.2	1040.5	930.7	852.2	802.0	780.0	759.6	737.6	712.5
57.5°	1260.2	1084.5	1007.6	944.8	842.8	767.4	726.6	696.8	682.7	670.1	649.7
60°	1117.4	968.3	908.7	852.2	751.8	682.7	643.5	621.5	608.9	602.7	593.2
62.5°	991.9	869.5	803.5	748.6	668.6	607.4	569.7	552.4	541.5	538.3	527.3
65°	858.5	753.3	701.5	654.5	585.4	530.5	499.1	478.7	470.8	469.3	469.3
67.5°	732.9	648.2	596.4	563.4	503.8	455.1	425.3	417.5	412.8	406.5	404.9
70°	615.2	547.7	502.2	474.0	420.6	384.5	361.0	348.4	348.4	343.7	340.6
72.5°	511.6	444.1	414.3	390.8	346.8	315.5	298.2	295.1	284.1	282.5	282.5
75°	400.2	350.0	329.6	309.2	276.2	254.2	240.1	232.3	226.0	226.0	227.6
77.5°	301.3	266.8	248.0	232.3	208.7	194.6	183.6	180.5	174.2	174.2	174.2
80°	213.4	194.6	180.5	167.9	150.7	138.1	131.8	125.6	125.6	124.0	125.6
82.5°	138.1	122.4	114.6	113.0	97.3	92.6	84.7	86.3	81.6	80.0	83.2
85°	80.0	72.2	62.8	59.6	53.4	47.1	43.9	45.5	43.9	42.4	43.9
87.5°	31.4	26.7	25.1	25.1	20.4	18.8	17.3	18.8	15.7	15.7	17.3
90°	12.8	11.7	10.5	9.3	7.0	4.7	2.3	1.2	2.3	4.7	7.0
92.5°	195.9	116.6	95.6	74.6	50.1	32.7	21.0	17.5	21.0	32.7	50.1
95°	264.7	139.9	113.7	87.5	61.8	49.0	39.7	38.5	39.7	49.0	61.8
97.5°	228.6	142.3	123.0	103.8	80.5	67.6	60.6	59.5	60.6	67.6	80.5
100°	226.2	158.6	141.1	123.6	101.5	88.6	84.0	81.6	84.0	88.6	101.5
102.5°	236.7	178.4	161.5	144.6	124.8	110.8	107.3	106.1	107.3	110.8	124.8
105°	251.9	200.6	184.2	167.9	149.3	137.6	131.8	131.8	131.8	137.6	149.3
107.5°	272.9	222.7	208.2	193.6	173.8	164.4	158.6	156.3	158.6	164.4	173.8
110°	296.2	248.4	233.2	218.1	200.6	190.1	185.4	183.1	185.4	190.1	200.6

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	318.4	272.9	258.3	243.7	226.2	215.8	212.3	209.9	212.3	215.8	226.2
115°	341.7	298.6	284.0	269.4	251.9	241.4	237.9	235.6	237.9	241.4	251.9
117.5°	365.0	324.2	310.2	296.2	276.4	265.9	262.4	258.9	262.4	265.9	276.4
120°	390.7	349.9	335.3	320.7	300.9	290.4	285.7	282.2	285.7	290.4	300.9
122.5°	415.2	374.4	359.8	345.2	323.0	312.5	309.0	306.7	309.0	312.5	323.0
125°	436.2	397.7	382.5	367.4	345.2	334.7	328.9	326.5	328.9	334.7	345.2
127.5°	457.2	419.8	404.6	389.5	366.2	353.4	346.4	342.9	346.4	353.4	366.2
130°	477.0	440.8	425.6	410.5	386.0	370.9	361.5	358.0	361.5	370.9	386.0
132.5°	495.6	459.5	444.4	429.2	403.5	386.0	374.4	369.7	374.4	386.0	403.5
135°	512.0	475.8	460.0	444.3	419.8	401.2	387.2	382.5	387.2	401.2	419.8
137.5°	523.6	491.0	474.6	458.3	433.8	415.2	402.3	398.8	402.3	415.2	433.8
140°	536.5	502.6	486.9	471.2	449.0	430.3	416.3	412.8	416.3	430.3	449.0
142.5°	544.6	513.1	498.6	484.0	463.0	444.3	431.5	429.2	431.5	444.3	463.0
145°	554.0	523.6	510.2	496.8	475.8	459.5	447.8	445.5	447.8	459.5	475.8
147.5°	559.8	533.0	520.8	508.5	489.8	474.7	464.2	463.0	464.2	474.7	489.8
150°	565.6	540.0	530.0	520.1	503.8	488.6	480.5	478.2	480.5	488.6	503.8
152.5°	571.4	548.1	539.4	530.6	515.5	502.6	495.6	494.5	495.6	502.6	515.5
155°	574.9	555.1	547.0	538.8	527.1	515.5	508.5	508.5	508.5	515.5	527.1
157.5°	578.4	561.0	554.6	548.1	537.6	527.1	521.3	521.3	521.3	527.1	537.6
160°	580.8	565.6	560.4	555.1	545.8	537.6	533.0	534.1	533.0	537.6	545.8
162.5°	583.1	570.3	566.2	562.1	555.1	548.1	543.5	544.6	543.5	548.1	555.1
165°	583.1	573.8	570.3	566.8	562.1	556.3	552.8	555.1	552.8	556.3	562.1
167.5°	583.1	574.9	572.6	570.3	566.8	563.3	561.0	562.1	561.0	563.3	566.8
170°	583.1	577.3	575.6	573.8	571.4	569.1	568.0	569.1	568.0	569.1	571.4
172.5°	581.9	577.3	576.7	576.1	574.9	572.6	571.4	573.8	571.4	572.6	574.9
175°	580.8	577.3	577.3	577.3	577.3	576.1	574.9	577.3	574.9	576.1	577.3
177.5°	579.6	577.3	577.3	577.3	578.4	577.3	577.3	579.6	577.3	577.3	578.4
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1823.7	1820.5	1812.7	1808.0	1792.3	1773.5	1767.2	1751.5	1757.8	1746.8	1746.8
5°	1775.0	1760.9	1751.5	1737.4	1707.5	1687.1	1665.2	1654.2	1647.9	1640.1	1633.8
7.5°	1712.2	1701.3	1691.8	1665.2	1632.2	1604.0	1577.3	1566.3	1545.9	1531.8	1525.5
10°	1657.3	1641.6	1619.6	1588.3	1553.7	1517.6	1494.1	1470.6	1454.9	1447.0	1429.7
12.5°	1600.8	1582.0	1558.4	1512.9	1475.3	1453.3	1410.9	1388.9	1381.1	1374.8	1354.4
15°	1542.7	1522.3	1494.1	1451.7	1418.8	1367.0	1341.9	1324.6	1305.8	1304.2	1288.5
17.5°	1491.0	1465.8	1442.3	1390.5	1349.7	1304.2	1290.1	1271.2	1254.0	1235.1	1227.3
20°	1425.0	1401.5	1384.2	1327.7	1282.2	1254.0	1230.4	1214.7	1203.7	1184.9	1181.8
22.5°	1365.4	1340.3	1316.7	1274.4	1235.1	1199.0	1170.8	1153.5	1148.8	1141.0	1126.8
25°	1307.3	1282.2	1254.0	1214.7	1173.9	1148.8	1123.7	1112.7	1103.3	1090.8	1079.8
27.5°	1258.7	1235.1	1208.5	1159.8	1125.3	1106.4	1079.8	1067.2	1054.7	1048.4	1043.7
30°	1200.6	1173.9	1153.5	1115.9	1078.2	1053.1	1034.3	1023.3	1012.3	1006.0	1002.9
32.5°	1144.1	1119.0	1104.9	1064.1	1034.3	1004.4	990.3	982.5	976.2	969.9	963.6
35°	1098.6	1073.5	1051.5	1013.8	984.0	963.6	952.6	940.1	935.4	929.1	929.1
37.5°	1042.1	1023.3	1001.3	965.2	938.5	922.8	913.4	897.7	896.1	893.0	888.3
40°	993.4	974.6	954.2	922.8	899.3	880.4	867.9	860.0	855.3	852.2	849.1
42.5°	941.7	921.3	911.8	875.7	855.3	836.5	830.2	822.4	820.8	814.5	806.7
45°	891.4	874.2	855.3	828.7	811.4	795.7	786.3	780.0	772.2	770.6	765.9
47.5°	847.5	827.1	809.8	784.7	765.9	753.3	745.5	737.6	731.4	726.6	721.9
50°	791.0	775.3	761.2	734.5	718.8	706.2	695.3	689.0	682.7	682.7	682.7
52.5°	736.1	721.9	709.4	690.5	671.7	660.7	648.2	643.5	640.3	635.6	640.3
55°	682.7	668.6	656.0	641.9	619.9	610.5	598.0	593.2	594.8	594.8	599.5
57.5°	626.2	615.2	607.4	590.1	569.7	560.3	552.4	547.7	547.7	554.0	555.6
60°	571.3	560.3	546.2	530.5	517.9	506.9	502.2	503.8	503.8	506.9	514.8
62.5°	510.1	503.8	495.9	474.0	466.1	458.3	452.0	456.7	455.1	463.0	474.0
65°	453.6	447.3	436.3	425.3	415.9	408.1	406.5	408.1	411.2	419.0	431.6
67.5°	390.8	390.8	381.4	372.0	364.1	356.3	357.8	359.4	362.5	372.0	390.8
70°	339.0	332.7	323.3	317.0	310.7	307.6	304.5	310.7	320.2	326.4	340.6
72.5°	282.5	277.8	269.9	263.7	262.1	259.0	257.4	260.5	269.9	280.9	296.6
75°	222.9	224.4	219.7	215.0	215.0	210.3	213.4	213.4	222.9	233.8	246.4
77.5°	172.6	171.1	169.5	166.4	164.8	164.8	164.8	167.9	177.3	183.6	196.2
80°	122.4	124.0	119.3	120.8	119.3	120.8	120.8	127.1	131.8	139.7	149.1
82.5°	81.6	81.6	78.5	80.0	80.0	80.0	81.6	84.7	91.0	97.3	103.6
85°	45.5	47.1	43.9	47.1	47.1	47.1	48.7	50.2	54.9	56.5	62.8
87.5°	17.3	20.4	20.4	17.3	18.8	20.4	22.0	20.4	23.5	26.7	28.2
90°	9.3	10.5	11.7	12.8	15.2	16.3	18.7	19.8	21.0	22.2	23.3
92.5°	74.6	95.6	116.6	195.9	328.9	473.5	465.3	375.5	253.1	181.9	135.3
95°	87.5	113.7	139.9	264.7	521.3	843.2	1033.3	1011.1	838.5	661.2	517.8
97.5°	103.8	123.0	142.3	228.6	425.7	773.2	1116.1	1263.0	1202.4	1061.3	916.7
100°	123.6	141.1	158.6	226.2	377.9	671.7	1053.1	1344.7	1434.5	1377.3	1257.2
102.5°	144.6	161.5	178.4	236.7	358.0	594.8	942.3	1295.7	1512.6	1570.9	1528.9
105°	167.9	184.2	200.6	251.9	355.7	550.5	845.5	1180.2	1460.1	1619.9	1671.2
107.5°	193.6	208.2	222.7	272.9	363.9	527.1	773.2	1070.6	1352.8	1563.9	1687.5
110°	218.1	233.2	248.4	296.2	376.7	517.8	725.4	979.6	1231.5	1453.1	1617.6

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	243.7	258.3	272.9	318.4	393.0	517.8	697.4	912.0	1135.9	1343.5	1510.3
115°	269.4	284.0	298.6	341.7	409.3	521.3	678.7	866.5	1058.9	1239.7	1399.5
117.5°	296.2	310.2	324.2	365.0	428.0	527.1	668.2	836.2	1005.3	1165.1	1305.0
120°	320.7	335.3	349.9	390.7	446.7	536.5	661.2	811.7	963.3	1103.2	1231.5
122.5°	345.2	359.8	374.4	415.2	467.7	544.6	655.4	790.7	931.8	1058.9	1169.7
125°	367.4	382.5	397.7	436.2	486.3	554.0	650.8	772.0	901.5	1020.4	1121.9
127.5°	389.5	404.6	419.8	457.2	503.8	564.5	648.4	754.5	870.0	983.1	1078.8
130°	410.5	425.6	440.8	477.0	521.3	573.8	646.1	737.1	840.8	943.5	1034.4
132.5°	429.2	444.4	459.5	495.6	536.5	584.3	646.1	723.1	811.7	906.2	986.6
135°	444.3	460.0	475.8	512.0	550.5	593.6	646.1	712.6	787.2	867.7	942.3
137.5°	458.3	474.6	491.0	523.6	561.0	602.9	647.3	702.1	765.0	832.7	896.8
140°	471.2	486.9	502.6	536.5	571.4	608.8	648.4	695.1	747.5	802.4	856.0
142.5°	484.0	498.6	513.1	544.6	577.3	612.3	649.6	689.2	732.4	776.7	821.0
145°	496.8	510.2	523.6	554.0	583.1	614.6	648.4	683.4	719.6	755.7	791.9
147.5°	508.5	520.8	533.0	559.8	586.6	615.8	646.1	677.6	706.7	737.1	766.2
150°	520.1	530.0	540.0	565.6	590.1	615.8	642.6	670.6	696.2	721.9	744.1
152.5°	530.6	539.4	548.1	571.4	592.4	614.6	637.9	662.4	684.6	706.7	726.6
155°	538.8	547.0	555.1	574.9	593.6	612.3	632.1	653.1	672.9	691.6	707.9
157.5°	548.1	554.6	561.0	578.4	594.8	609.9	626.3	644.9	661.2	677.6	690.4
160°	555.1	560.4	565.6	580.8	594.8	606.4	620.4	634.4	649.6	661.2	672.9
162.5°	562.1	566.2	570.3	583.1	593.6	602.9	613.4	625.1	636.8	647.3	656.6
165°	566.8	570.3	573.8	583.1	592.4	599.4	606.4	615.8	625.1	633.3	640.3
167.5°	570.3	572.6	574.9	583.1	590.1	593.6	599.4	606.4	613.4	619.3	625.1
170°	573.8	575.6	577.3	583.1	587.8	590.1	593.6	598.3	604.1	607.6	611.1
172.5°	576.1	576.7	577.3	581.9	585.4	585.4	586.6	590.1	593.6	597.1	599.4
175°	577.3	577.3	577.3	580.8	583.1	581.9	581.9	583.1	586.6	586.6	588.9
177.5°	577.3	577.3	577.3	579.6	580.8	578.4	578.4	579.6	580.8	581.9	581.9
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1753.0	1742.1	1740.5	1743.6	1737.4	1746.8	1743.6	1746.8	1738.9	1746.8	1742.1
5°	1632.2	1629.1	1622.8	1614.9	1616.5	1618.1	1625.9	1618.1	1624.4	1625.9	1633.8
7.5°	1519.2	1512.9	1517.6	1514.5	1500.4	1497.2	1500.4	1505.1	1514.5	1520.8	1525.5
10°	1428.2	1425.0	1418.8	1414.1	1406.2	1401.5	1407.8	1401.5	1414.1	1425.0	1425.0
12.5°	1359.1	1346.6	1338.7	1337.2	1319.9	1323.0	1329.3	1334.0	1348.1	1354.4	1354.4
15°	1286.9	1277.5	1274.4	1268.1	1261.8	1268.1	1265.0	1269.7	1275.9	1282.2	1285.4
17.5°	1224.2	1222.6	1224.2	1208.5	1213.2	1205.3	1206.9	1214.7	1210.0	1214.7	1224.2
20°	1167.7	1170.8	1166.1	1159.8	1159.8	1150.4	1161.4	1158.2	1159.8	1169.2	1183.3
22.5°	1125.3	1123.7	1119.0	1114.3	1108.0	1109.6	1111.2	1108.0	1120.6	1128.4	1130.0
25°	1079.8	1076.6	1075.1	1070.3	1064.1	1070.3	1068.8	1070.3	1073.5	1086.0	1076.6
27.5°	1037.4	1031.1	1034.3	1029.5	1028.0	1029.5	1029.5	1031.1	1034.3	1035.8	1037.4
30°	1001.3	995.0	993.4	990.3	988.7	990.3	993.4	990.3	1002.9	1001.3	1001.3
32.5°	962.1	957.3	954.2	954.2	952.6	951.1	952.6	954.2	963.6	957.3	963.6
35°	924.4	921.3	921.3	918.1	916.5	916.5	916.5	922.8	919.7	924.4	924.4
37.5°	888.3	888.3	886.7	883.6	882.0	883.6	882.0	885.2	883.6	885.2	886.7
40°	850.6	847.5	845.9	845.9	841.2	836.5	841.2	841.2	842.8	847.5	849.1
42.5°	805.1	806.7	806.7	800.4	800.4	800.4	802.0	803.5	803.5	806.7	806.7
45°	765.9	762.7	762.7	762.7	759.6	761.2	764.3	764.3	764.3	764.3	761.2
47.5°	721.9	721.9	723.5	723.5	728.2	726.6	726.6	725.1	721.9	721.9	723.5
50°	681.1	685.8	687.4	687.4	689.0	690.5	690.5	687.4	685.8	681.1	681.1
52.5°	641.9	645.0	648.2	652.9	656.0	654.5	654.5	651.3	645.0	643.5	641.9
55°	599.5	604.2	610.5	615.2	619.9	621.5	621.5	615.2	608.9	601.1	601.1
57.5°	560.3	565.0	576.0	580.7	587.0	587.0	583.8	579.1	569.7	563.4	558.7
60°	521.0	528.9	536.7	546.2	554.0	555.6	550.9	544.6	533.6	525.8	519.5
62.5°	478.7	486.5	502.2	511.6	517.9	517.9	517.9	510.1	495.9	485.0	475.5
65°	437.9	445.7	459.8	472.4	477.1	481.8	477.1	469.3	458.3	445.7	436.3
67.5°	395.5	404.9	419.0	428.5	434.7	439.4	436.3	430.0	415.9	398.6	392.4
70°	348.4	353.1	373.5	382.9	392.4	395.5	392.4	382.9	368.8	350.0	343.7
72.5°	304.5	309.2	328.0	335.9	343.7	346.8	342.1	335.9	323.3	306.0	298.2
75°	254.2	262.1	271.5	284.1	293.5	296.6	291.9	287.2	271.5	260.5	254.2
77.5°	200.9	208.7	221.3	232.3	241.7	240.1	233.8	235.4	218.2	205.6	200.9
80°	152.2	158.5	167.9	177.3	182.1	182.1	180.5	174.2	167.9	158.5	150.7
82.5°	105.2	113.0	120.8	127.1	127.1	128.7	125.6	124.0	117.7	109.9	108.3
85°	62.8	64.3	70.6	70.6	76.9	73.8	72.2	76.9	70.6	65.9	64.3
87.5°	28.2	26.7	28.2	28.2	26.7	29.8	29.8	28.2	29.8	28.2	28.2
90°	24.5	25.7	25.7	25.7	26.8	26.8	26.8	25.7	25.7	25.7	24.5
92.5°	124.2	113.1	94.5	91.0	88.6	86.3	88.6	91.0	94.5	113.1	124.2
95°	468.8	419.8	337.0	302.1	292.7	274.1	292.7	302.1	337.0	419.8	468.8
97.5°	846.7	776.7	706.7	646.1	614.6	600.6	614.6	646.1	706.7	776.7	846.7
100°	1196.6	1135.9	1055.4	971.5	928.3	909.7	928.3	971.5	1055.4	1135.9	1196.6
102.5°	1492.8	1456.6	1369.1	1315.5	1267.7	1254.9	1267.7	1315.5	1369.1	1456.6	1492.8
105°	1664.8	1658.4	1621.0	1582.6	1559.2	1545.2	1559.2	1582.6	1621.0	1658.4	1664.8
107.5°	1713.2	1738.8	1749.3	1743.5	1731.8	1720.2	1731.8	1743.5	1749.3	1738.8	1713.2
110°	1667.2	1716.7	1769.2	1791.3	1799.5	1799.5	1799.5	1791.3	1769.2	1716.7	1667.2

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1570.9	1631.5	1714.3	1756.3	1779.7	1790.2	1779.7	1756.3	1714.3	1631.5	1570.9
115°	1463.0	1526.6	1617.6	1673.5	1706.2	1721.3	1706.2	1673.5	1617.6	1526.6	1463.0
117.5°	1365.0	1425.1	1517.3	1575.6	1608.2	1617.6	1608.2	1575.6	1517.3	1425.1	1365.0
120°	1282.8	1334.2	1420.5	1476.4	1507.9	1517.3	1507.9	1476.4	1420.5	1334.2	1282.8
122.5°	1217.0	1264.2	1338.8	1389.0	1420.5	1428.6	1420.5	1389.0	1338.8	1264.2	1217.0
125°	1163.9	1205.9	1271.2	1319.0	1344.7	1356.3	1344.7	1319.0	1271.2	1205.9	1163.9
127.5°	1118.4	1158.1	1217.5	1260.7	1285.2	1289.8	1285.2	1260.7	1217.5	1158.1	1118.4
130°	1072.3	1110.2	1168.6	1207.0	1230.4	1237.4	1230.4	1207.0	1168.6	1110.2	1072.3
132.5°	1022.8	1058.9	1117.2	1155.7	1176.7	1184.9	1176.7	1155.7	1117.2	1058.9	1022.8
135°	975.6	1008.8	1060.1	1098.6	1119.6	1126.6	1119.6	1098.6	1060.1	1008.8	975.6
137.5°	926.0	955.1	1001.8	1037.9	1057.8	1065.9	1057.8	1037.9	1001.8	955.1	926.0
140°	880.5	905.0	948.1	978.5	996.0	1001.8	996.0	978.5	948.1	905.0	880.5
142.5°	841.4	861.8	896.8	921.3	937.6	942.3	937.6	921.3	896.8	861.8	841.4
145°	807.6	823.4	851.3	871.2	884.0	888.7	884.0	871.2	851.3	823.4	807.6
147.5°	778.4	790.7	814.0	830.4	838.5	840.8	838.5	830.4	814.0	790.7	778.4
150°	754.6	765.0	782.5	796.5	801.2	802.4	801.2	796.5	782.5	765.0	754.6
152.5°	734.2	741.7	755.7	766.2	770.9	772.0	770.9	766.2	755.7	741.7	734.2
155°	714.3	720.7	732.4	740.6	744.1	745.2	744.1	740.6	732.4	720.7	714.3
157.5°	695.6	700.9	710.2	717.2	720.7	720.7	720.7	717.2	710.2	700.9	695.6
160°	677.0	681.1	689.2	695.1	697.4	696.2	697.4	695.1	689.2	681.1	677.0
162.5°	660.1	663.6	669.4	674.1	674.1	674.1	674.1	674.1	669.4	663.6	660.1
165°	643.2	646.1	650.8	653.1	653.1	653.1	653.1	653.1	650.8	646.1	643.2
167.5°	627.4	629.8	632.1	634.4	633.3	633.3	633.3	634.4	632.1	629.8	627.4
170°	612.2	613.4	615.8	616.9	616.9	615.8	616.9	616.9	615.8	613.4	612.2
172.5°	600.0	600.6	600.6	602.9	600.6	599.4	600.6	602.9	600.6	600.6	600.0
175°	588.9	588.9	588.9	590.1	587.8	586.6	587.8	590.1	588.9	588.9	588.9
177.5°	581.9	581.9	580.8	581.9	578.4	578.4	578.4	581.9	580.8	581.9	581.9
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1756.2	1746.8	1757.8	1743.6	1746.8	1764.0	1762.5	1778.2	1787.6	1786.0	1793.9
5°	1640.1	1640.1	1644.8	1643.2	1658.9	1673.0	1691.8	1707.5	1724.8	1734.2	1745.2
7.5°	1525.5	1541.2	1544.3	1552.2	1571.0	1594.5	1613.4	1636.9	1662.0	1679.3	1691.8
10°	1431.3	1443.9	1456.4	1462.7	1483.1	1514.5	1541.2	1578.8	1610.2	1629.1	1646.3
12.5°	1348.1	1362.3	1368.5	1396.8	1410.9	1431.3	1469.0	1509.8	1544.3	1564.7	1578.8
15°	1288.5	1296.3	1310.5	1327.7	1341.9	1367.0	1398.4	1443.9	1476.8	1494.1	1542.7
17.5°	1238.3	1247.7	1255.5	1263.4	1285.4	1312.0	1341.9	1381.1	1423.5	1453.3	1478.4
20°	1186.5	1191.2	1200.6	1213.2	1228.9	1254.0	1280.7	1321.5	1359.1	1382.7	1415.6
22.5°	1125.3	1139.4	1148.8	1158.2	1175.5	1203.7	1228.9	1258.7	1305.8	1332.4	1367.0
25°	1089.2	1095.5	1101.7	1112.7	1125.3	1150.4	1178.6	1210.0	1247.7	1275.9	1305.8
27.5°	1042.1	1051.5	1059.4	1073.5	1081.3	1101.7	1128.4	1159.8	1205.3	1228.9	1254.0
30°	1002.9	1012.3	1018.6	1024.8	1035.8	1057.8	1082.9	1108.0	1150.4	1180.2	1205.3
32.5°	963.6	973.0	980.9	985.6	996.6	1010.7	1031.1	1062.5	1098.6	1119.0	1152.0
35°	929.1	929.1	938.5	944.8	954.2	966.8	985.6	1009.1	1046.8	1073.5	1103.3
37.5°	889.9	891.4	899.3	904.0	913.4	926.0	944.8	966.8	998.2	1018.6	1048.4
40°	849.1	853.8	856.9	864.8	875.7	880.4	899.3	924.4	955.8	974.6	999.7
42.5°	808.3	811.4	819.2	825.5	834.9	842.8	855.3	878.9	902.4	930.7	951.1
45°	762.7	770.6	775.3	786.3	791.0	798.8	811.4	830.2	858.5	875.7	899.3
47.5°	723.5	726.6	729.8	743.9	753.3	758.0	770.6	781.6	811.4	827.1	849.1
50°	681.1	681.1	685.8	692.1	703.1	712.5	723.5	736.1	759.6	775.3	797.3
52.5°	641.9	637.2	640.3	643.5	654.5	663.9	674.9	692.1	714.1	723.5	742.3
55°	599.5	591.7	596.4	601.1	604.2	616.8	629.3	640.3	657.6	671.7	689.0
57.5°	554.0	552.4	549.3	550.9	558.7	566.6	576.0	590.1	610.5	621.5	630.9
60°	513.2	503.8	500.6	503.8	508.5	513.2	525.8	538.3	555.6	566.6	577.5
62.5°	470.8	461.4	455.1	450.4	455.1	466.1	474.0	483.4	497.5	510.1	519.5
65°	430.0	415.9	409.6	406.5	404.9	412.8	419.0	431.6	444.1	448.9	459.8
67.5°	384.5	372.0	364.1	359.4	359.4	359.4	365.7	378.2	390.8	392.4	403.3
70°	339.0	324.9	317.0	310.7	307.6	310.7	318.6	320.2	331.1	334.3	340.6
72.5°	290.3	277.8	268.4	260.5	262.1	265.2	265.2	268.4	274.6	282.5	282.5
75°	244.8	227.6	222.9	216.6	213.4	213.4	213.4	219.7	224.4	230.7	229.1
77.5°	193.0	183.6	174.2	171.1	166.4	164.8	167.9	167.9	171.1	175.8	177.3
80°	149.1	138.1	131.8	128.7	122.4	120.8	122.4	122.4	127.1	125.6	127.1
82.5°	103.6	95.7	91.0	86.3	83.2	84.7	83.2	83.2	84.7	83.2	83.2
85°	59.6	58.1	54.9	53.4	51.8	48.7	51.8	50.2	48.7	47.1	50.2
87.5°	28.2	26.7	26.7	23.5	23.5	22.0	23.5	23.5	22.0	22.0	22.0
90°	23.3	22.2	21.0	19.8	18.7	16.3	15.2	12.8	11.7	10.5	9.3
92.5°	135.3	181.9	253.1	375.5	465.3	473.5	328.9	195.9	116.6	95.6	74.6
95°	517.8	661.2	838.5	1011.1	1033.3	843.2	521.3	264.7	139.9	113.7	87.5
97.5°	916.7	1061.3	1202.4	1263.0	1116.1	773.2	425.7	228.6	142.3	123.0	103.8
100°	1257.2	1377.3	1434.5	1344.7	1053.1	671.7	377.9	226.2	158.6	141.1	123.6
102.5°	1528.9	1570.9	1512.6	1295.7	942.3	594.8	358.0	236.7	178.4	161.5	144.6
105°	1671.2	1619.9	1460.1	1180.2	845.5	550.5	355.7	251.9	200.6	184.2	167.9
107.5°	1687.5	1563.9	1352.8	1070.6	773.2	527.1	363.9	272.9	222.7	208.2	193.6
110°	1617.6	1453.1	1231.5	979.6	725.4	517.8	376.7	296.2	248.4	233.2	218.1

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1510.3	1343.5	1135.9	912.0	697.4	517.8	393.0	318.4	272.9	258.3	243.7
115°	1399.5	1239.7	1058.9	866.5	678.7	521.3	409.3	341.7	298.6	284.0	269.4
117.5°	1305.0	1165.1	1005.3	836.2	668.2	527.1	428.0	365.0	324.2	310.2	296.2
120°	1231.5	1103.2	963.3	811.7	661.2	536.5	446.7	390.7	349.9	335.3	320.7
122.5°	1169.7	1058.9	931.8	790.7	655.4	544.6	467.7	415.2	374.4	359.8	345.2
125°	1121.9	1020.4	901.5	772.0	650.8	554.0	486.3	436.2	397.7	382.5	367.4
127.5°	1078.8	983.1	870.0	754.5	648.4	564.5	503.8	457.2	419.8	404.6	389.5
130°	1034.4	943.5	840.8	737.1	646.1	573.8	521.3	477.0	440.8	425.6	410.5
132.5°	986.6	906.2	811.7	723.1	646.1	584.3	536.5	495.6	459.5	444.4	429.2
135°	942.3	867.7	787.2	712.6	646.1	593.6	550.5	512.0	475.8	460.0	444.3
137.5°	896.8	832.7	765.0	702.1	647.3	602.9	561.0	523.6	491.0	474.6	458.3
140°	856.0	802.4	747.5	695.1	648.4	608.8	571.4	536.5	502.6	486.9	471.2
142.5°	821.0	776.7	732.4	689.2	649.6	612.3	577.3	544.6	513.1	498.6	484.0
145°	791.9	755.7	719.6	683.4	648.4	614.6	583.1	554.0	523.6	510.2	496.8
147.5°	766.2	737.1	706.7	677.6	646.1	615.8	586.6	559.8	533.0	520.8	508.5
150°	744.1	721.9	696.2	670.6	642.6	615.8	590.1	565.6	540.0	530.0	520.1
152.5°	726.6	706.7	684.6	662.4	637.9	614.6	592.4	571.4	548.1	539.4	530.6
155°	707.9	691.6	672.9	653.1	632.1	612.3	593.6	574.9	555.1	547.0	538.8
157.5°	690.4	677.6	661.2	644.9	626.3	609.9	594.8	578.4	561.0	554.6	548.1
160°	672.9	661.2	649.6	634.4	620.4	606.4	594.8	580.8	565.6	560.4	555.1
162.5°	656.6	647.3	636.8	625.1	613.4	602.9	593.6	583.1	570.3	566.2	562.1
165°	640.3	633.3	625.1	615.8	606.4	599.4	592.4	583.1	573.8	570.3	566.8
167.5°	625.1	619.3	613.4	606.4	599.4	593.6	590.1	583.1	574.9	572.6	570.3
170°	611.1	607.6	604.1	598.3	593.6	590.1	587.8	583.1	577.3	575.6	573.8
172.5°	599.4	597.1	593.6	590.1	586.6	585.4	585.4	581.9	577.3	576.7	576.1
175°	588.9	586.6	586.6	583.1	581.9	581.9	583.1	580.8	577.3	577.3	577.3
177.5°	581.9	581.9	580.8	579.6	578.4	578.4	580.8	579.6	577.3	577.3	577.3
180°	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4	578.4

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.8	1848.8	1848.8	1848.8
2.5°	1804.8	1820.5	1831.5	1851.9
5°	1764.0	1792.3	1819.0	1847.2
7.5°	1723.2	1756.2	1798.6	1834.7
10°	1677.7	1720.1	1770.3	1819.0
12.5°	1632.2	1682.4	1737.4	1801.7
15°	1577.3	1641.6	1706.0	1775.0
17.5°	1528.6	1594.5	1663.6	1749.9
20°	1473.7	1545.9	1621.2	1709.1
22.5°	1425.0	1505.1	1583.6	1676.1
25°	1370.1	1448.6	1534.9	1633.8
27.5°	1324.6	1396.8	1481.5	1588.3
30°	1269.7	1348.1	1432.9	1539.6
32.5°	1217.9	1293.2	1382.7	1487.8
35°	1164.5	1241.4	1321.5	1421.9
37.5°	1114.3	1180.2	1260.2	1356.0
40°	1057.8	1130.0	1202.2	1277.5
42.5°	1006.0	1071.9	1139.4	1199.0
45°	947.9	1004.4	1068.8	1117.4
47.5°	894.6	944.8	995.0	1032.7
50°	841.2	880.4	918.1	951.1
52.5°	778.4	822.4	842.8	863.2
55°	721.9	747.0	765.9	786.3
57.5°	667.0	678.0	687.4	706.2
60°	594.8	607.4	618.4	632.5
62.5°	532.0	538.3	541.5	555.6
65°	472.4	470.8	478.7	486.5
67.5°	408.1	406.5	414.3	417.5
70°	345.3	343.7	345.3	353.1
72.5°	285.6	285.6	287.2	290.3
75°	230.7	230.7	232.3	235.4
77.5°	174.2	177.3	175.8	182.1
80°	127.1	124.0	127.1	130.3
82.5°	83.2	86.3	86.3	83.2
85°	47.1	47.1	47.1	47.1
87.5°	20.4	20.4	22.0	23.5
90°	7.0	4.7	2.3	1.2
92.5°	50.1	32.7	21.0	17.5
95°	61.8	49.0	39.7	38.5
97.5°	80.5	67.6	60.6	59.5
100°	101.5	88.6	84.0	81.6
102.5°	124.8	110.8	107.3	106.1
105°	149.3	137.6	131.8	131.8
107.5°	173.8	164.4	158.6	156.3
110°	200.6	190.1	185.4	183.1

TEST NUMBER: P1027591

CATALOG NUMBER: S125DIP-B1270D1270UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	226.2	215.8	212.3	209.9
115°	251.9	241.4	237.9	235.6
117.5°	276.4	265.9	262.4	258.9
120°	300.9	290.4	285.7	282.2
122.5°	323.0	312.5	309.0	306.7
125°	345.2	334.7	328.9	326.5
127.5°	366.2	353.4	346.4	342.9
130°	386.0	370.9	361.5	358.0
132.5°	403.5	386.0	374.4	369.7
135°	419.8	401.2	387.2	382.5
137.5°	433.8	415.2	402.3	398.8
140°	449.0	430.3	416.3	412.8
142.5°	463.0	444.3	431.5	429.2
145°	475.8	459.5	447.8	445.5
147.5°	489.8	474.7	464.2	463.0
150°	503.8	488.6	480.5	478.2
152.5°	515.5	502.6	495.6	494.5
155°	527.1	515.5	508.5	508.5
157.5°	537.6	527.1	521.3	521.3
160°	545.8	537.6	533.0	534.1
162.5°	555.1	548.1	543.5	544.6
165°	562.1	556.3	552.8	555.1
167.5°	566.8	563.3	561.0	562.1
170°	571.4	569.1	568.0	569.1
172.5°	574.9	572.6	571.4	573.8
175°	577.3	576.1	574.9	577.3
177.5°	578.4	577.3	577.3	579.6
180°	578.4	578.4	578.4	578.4

(END OF REPORT)