

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027636

Luminaire Tested: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027636
REPORT IS A COMBINATION OF REPORTS P1001674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D375UB35-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6548.0 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																					
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	80			
1	105	100	97	93	100	96	93	90	88	86	83	81	79	77	74	73	71	68			
2	96	88	82	77	91	85	79	74	78	73	69	72	68	65	66	63	61	57			
3	88	78	70	64	83	75	68	62	69	63	59	64	59	55	59	55	52	49			
4	80	69	61	55	77	67	59	53	62	55	50	57	52	48	53	48	45	42			
5	74	62	53	47	71	60	52	46	55	49	44	51	46	42	47	43	39	37			
6	68	56	47	41	65	54	46	40	50	43	38	46	41	37	43	38	35	32			
7	63	51	42	36	60	49	41	36	45	39	34	42	37	32	39	35	31	29			
8	59	46	38	32	56	45	37	32	42	35	30	39	33	29	36	31	28	26			
9	55	42	34	29	53	41	34	29	38	32	27	36	30	26	33	29	25	23			
10	51	39	31	26	49	38	31	26	35	29	25	33	28	24	31	26	23	21			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11845	11845	11845	11845
5°	11854	13437	11865	10195
10°	11782	15316	11762	8751
15°	11695	16607	11623	7907
20°	11548	18198	11442	7218
25°	11417	20852	11209	6810
30°	11228	21998	11034	6441
35°	10930	17634	10701	6144
40°	10465	12188	10311	5831
45°	9878	9073	9767	5571
50°	9206	7470	9054	5361
55°	8481	6371	8413	5181
60°	7769	5454	7633	5041
65°	7000	4710	6888	4835
70°	6190	3910	6107	4479
75°	5330	3024	5260	3888
80°	4211	2046	4059	2859
85°	2693	1023	2601	1458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18093 cd/sqm

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	2.7
10°-20°	530.0	8.1
20°-30°	860.9	13.1
30°-40°	1052.2	16.1
40°-50°	954.4	14.6
50°-60°	760.2	11.6
60°-70°	529.4	8.1
70°-80°	282.1	4.3
80°-90°	70.6	1.1
90°-100°	128.8	2.0
100°-110°	277.8	4.2
110°-120°	259.0	4.0
120°-130°	209.8	3.2
130°-140°	168.4	2.6
140°-150°	127.0	1.9
150°-160°	89.5	1.4
160°-170°	52.7	0.8
170°-180°	17.1	0.3
0°-30°	1568.8	24.0
0°-40°	2621.0	40.0
0°-60°	4335.5	66.2
0°-90°	5217.7	79.7
90°-120°	665.7	10.2
90°-150°	1170.9	17.9
90°-180°	1330.0	20.3
0°-180°	6548.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1849	1849	1849	1849	1849	
5°	1847	2133	1849	1618	1847	175
15°	1775	2663	1764	1268	1775	501
25°	1634	3277	1604	1070	1634	752
35°	1422	2630	1392	916	1422	888
45°	1117	1240	1105	761	1117	861
55°	786	764	780	622	786	703
65°	486	469	479	482	486	483
75°	235	231	232	297	235	250
85°	47	52	46	74	47	56
90°	0	8	0	8	0	4
95°	12	84	12	84	12	12
105°	40	473	40	473	40	43
115°	72	527	72	527	72	71
125°	100	415	100	415	100	89
135°	117	345	117	345	117	91
145°	136	272	136	272	136	86
155°	156	228	156	228	156	72
165°	170	200	170	200	170	48
175°	177	180	177	180	177	17
180°	177	177	177	177	177	

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1851.9	1862.9	1875.5	1884.9	1900.6	1905.3	1913.1	1917.8	1922.5	1927.3	1930.4
5°	1847.2	1873.9	1897.4	1914.7	1944.5	1955.5	1969.6	1986.9	2007.3	2024.6	2035.5
7.5°	1834.7	1877.0	1908.4	1942.9	1983.8	2010.4	2024.6	2060.7	2093.6	2118.7	2151.7
10°	1819.0	1869.2	1917.8	1969.6	2027.7	2057.5	2085.8	2136.0	2181.5	2222.3	2255.3
12.5°	1801.7	1862.9	1921.0	1988.5	2066.9	2103.0	2121.9	2208.2	2264.7	2286.7	2351.0
15°	1775.0	1847.2	1930.4	2013.6	2079.5	2121.9	2173.7	2242.7	2299.2	2347.9	2399.7
17.5°	1749.9	1828.4	1913.1	2005.7	2101.5	2156.4	2195.6	2256.8	2318.0	2380.8	2429.5
20°	1709.1	1811.1	1897.4	1996.3	2109.3	2148.5	2189.3	2261.5	2327.5	2394.9	2456.2
22.5°	1676.1	1773.5	1891.2	1985.3	2081.1	2120.3	2170.5	2245.8	2324.3	2401.2	2490.7
25°	1633.8	1742.1	1844.1	1944.5	2043.4	2085.8	2131.3	2228.6	2310.2	2409.1	2507.9
27.5°	1588.3	1699.7	1801.7	1892.7	1985.3	2043.4	2092.0	2194.1	2302.3	2410.6	2539.3
30°	1539.6	1644.8	1742.1	1831.5	1933.5	1993.2	2041.8	2161.1	2281.9	2420.1	2573.9
32.5°	1487.8	1586.7	1669.9	1760.9	1869.2	1924.1	1990.0	2120.3	2263.1	2427.9	2620.9
35°	1421.9	1516.1	1589.8	1682.4	1790.7	1861.3	1930.4	2076.4	2242.7	2426.3	2647.6
37.5°	1356.0	1429.7	1500.4	1599.2	1724.8	1789.1	1861.3	2021.4	2211.3	2421.6	2658.6
40°	1277.5	1349.7	1410.9	1511.4	1643.2	1717.0	1792.3	1960.2	2175.2	2404.4	2619.4
42.5°	1199.0	1260.2	1327.7	1432.9	1560.0	1638.5	1718.5	1905.3	2128.1	2354.1	2511.1
45°	1117.4	1164.5	1238.3	1334.0	1469.0	1544.3	1635.3	1837.8	2062.2	2263.1	2341.6
47.5°	1032.7	1079.8	1148.8	1241.4	1374.8	1464.3	1550.6	1753.0	1979.0	2134.4	2134.4
50°	951.1	988.7	1056.2	1148.8	1283.8	1365.4	1453.3	1668.3	1850.4	1964.9	1862.9
52.5°	863.2	905.6	962.1	1059.4	1192.8	1266.5	1362.3	1545.9	1718.5	1765.6	1608.7
55°	786.3	820.8	874.2	966.8	1090.8	1167.7	1249.3	1425.0	1571.0	1567.9	1399.9
57.5°	706.2	734.5	791.0	875.7	990.3	1059.4	1141.0	1293.2	1412.5	1370.1	1211.6
60°	632.5	652.9	707.8	776.9	886.7	951.1	1029.5	1153.5	1244.6	1184.9	1024.8
62.5°	555.6	579.1	623.1	690.5	787.9	839.6	897.7	1023.3	1081.3	1028.0	864.8
65°	486.5	505.4	544.6	601.1	689.0	736.1	786.3	889.9	944.8	867.9	732.9
67.5°	417.5	439.4	467.7	517.9	587.0	630.9	674.9	764.3	789.4	720.4	607.4
70°	353.1	372.0	398.6	434.7	492.8	532.0	565.0	638.8	656.0	591.7	502.2
72.5°	290.3	302.9	324.9	354.7	408.1	430.0	464.6	514.8	536.7	478.7	414.3
75°	235.4	244.8	259.0	280.9	317.0	340.6	368.8	415.9	414.3	373.5	328.0
77.5°	182.1	183.6	199.3	219.7	241.7	262.1	276.2	309.2	312.3	287.2	249.5
80°	130.3	135.0	141.2	156.9	175.8	183.6	200.9	221.3	224.4	205.6	180.5
82.5°	83.2	86.3	91.0	100.4	113.0	122.4	131.8	139.7	147.5	136.5	116.1
85°	47.1	48.7	53.4	56.5	62.8	67.5	75.3	83.2	81.6	73.8	67.5
87.5°	23.5	23.5	23.5	26.7	29.8	29.8	33.0	34.5	36.1	33.0	29.8
90°	0.4	0.7	1.4	2.1	2.9	3.2	3.6	3.9	4.6	5.0	5.7
92.5°	5.4	6.4	10.0	15.4	22.9	29.3	35.7	60.0	100.7	145.0	142.5
95°	11.8	12.1	15.0	18.9	26.8	34.8	42.9	81.1	159.6	258.2	316.4
97.5°	18.2	18.6	20.7	24.6	31.8	37.7	43.6	70.0	130.3	236.7	341.7
100°	25.0	25.7	27.1	31.1	37.9	43.2	48.6	69.3	115.7	205.7	322.4
102.5°	32.5	32.9	33.9	38.2	44.3	49.4	54.6	72.5	109.6	182.1	288.5
105°	40.4	40.4	42.1	45.7	51.4	56.4	61.4	77.1	108.9	168.5	258.9
107.5°	47.8	48.6	50.3	53.2	59.3	63.8	68.2	83.6	111.4	161.4	236.7
110°	56.1	56.8	58.2	61.4	66.8	71.4	76.1	90.7	115.3	158.5	222.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	64.3	65.0	66.1	69.3	74.6	79.1	83.6	97.5	120.3	158.5	213.5
115°	72.1	72.8	73.9	77.1	82.5	87.0	91.4	104.6	125.3	159.6	207.8
117.5°	79.3	80.3	81.4	84.6	90.7	95.0	99.3	111.8	131.0	161.4	204.6
120°	86.4	87.5	88.9	92.1	98.2	102.6	107.1	119.6	136.8	164.3	202.5
122.5°	93.9	94.6	95.7	98.9	105.7	110.2	114.6	127.1	143.2	166.8	200.7
125°	100.0	100.7	102.5	105.7	112.5	117.2	121.8	133.5	148.9	169.6	199.3
127.5°	105.0	106.1	108.2	112.1	119.3	124.0	128.6	140.0	154.3	172.8	198.5
130°	109.6	110.7	113.6	118.2	125.7	130.4	135.0	146.0	159.6	175.7	197.8
132.5°	113.2	114.6	118.2	123.6	131.4	136.0	140.7	151.8	164.3	178.9	197.8
135°	117.1	118.6	122.8	128.6	136.0	140.8	145.7	156.8	168.5	181.8	197.8
137.5°	122.1	123.2	127.1	132.8	140.3	145.3	150.3	160.3	171.8	184.6	198.2
140°	126.4	127.5	131.8	137.5	144.3	149.1	153.9	164.3	175.0	186.4	198.5
142.5°	131.4	132.1	136.0	141.8	148.2	152.6	157.1	166.8	176.8	187.5	198.9
145°	136.4	137.1	140.7	145.7	152.1	156.2	160.3	169.6	178.5	188.2	198.5
147.5°	141.8	142.1	145.3	150.0	155.7	159.4	163.2	171.4	179.6	188.5	197.8
150°	146.4	147.1	149.6	154.3	159.3	162.3	165.3	173.2	180.7	188.5	196.8
152.5°	151.4	151.8	153.9	157.8	162.5	165.2	167.8	175.0	181.4	188.2	195.3
155°	155.7	155.7	157.8	161.4	165.0	167.5	170.0	176.0	181.8	187.5	193.5
157.5°	159.6	159.6	161.4	164.6	167.8	169.8	171.8	177.1	182.1	186.8	191.8
160°	163.5	163.2	164.6	167.1	170.0	171.6	173.2	177.8	182.1	185.7	190.0
162.5°	166.8	166.4	167.8	170.0	172.1	173.4	174.6	178.5	181.8	184.6	187.8
165°	170.0	169.3	170.3	172.1	173.5	174.6	175.7	178.5	181.4	183.5	185.7
167.5°	172.1	171.8	172.5	173.5	174.6	175.3	176.0	178.5	180.7	181.8	183.5
170°	174.3	173.9	174.3	175.0	175.7	176.2	176.8	178.5	180.0	180.7	181.8
172.5°	175.7	175.0	175.3	176.0	176.4	176.6	176.8	178.2	179.3	179.3	179.6
175°	176.8	176.0	176.4	176.8	176.8	176.8	176.8	177.8	178.5	178.2	178.2
177.5°	177.5	176.8	176.8	177.1	176.8	176.8	176.8	177.5	177.8	177.1	177.1
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1933.5	1944.5	1953.9	1961.8	1968.1	1977.5	1971.2	1972.8	1975.9	1982.2	1982.2
5°	2059.1	2076.4	2085.8	2117.2	2125.0	2123.4	2118.7	2143.8	2142.3	2132.8	2131.3
7.5°	2181.5	2211.3	2238.0	2263.1	2271.0	2291.4	2296.1	2307.1	2303.9	2319.6	2311.8
10°	2292.9	2340.0	2365.1	2402.8	2412.2	2421.6	2434.2	2440.5	2454.6	2453.0	2453.0
12.5°	2379.2	2435.7	2468.7	2478.1	2514.2	2525.2	2536.2	2556.6	2551.9	2553.5	2562.9
15°	2446.7	2501.7	2529.9	2573.9	2599.0	2611.5	2630.4	2652.3	2649.2	2663.3	2660.2
17.5°	2497.0	2548.7	2600.5	2666.5	2668.0	2701.0	2744.9	2754.3	2774.7	2760.6	2760.6
20°	2537.8	2606.8	2680.6	2765.3	2774.7	2795.1	2848.5	2884.6	2908.1	2900.3	2905.0
22.5°	2581.7	2680.6	2766.9	2851.6	2897.2	2933.3	2985.0	3041.5	3061.9	3074.5	3071.4
25°	2638.2	2741.8	2868.9	2986.6	3033.7	3102.8	3171.8	3226.7	3242.4	3277.0	3245.6
27.5°	2696.3	2842.2	3000.7	3138.9	3198.5	3255.0	3338.2	3379.0	3399.4	3415.1	3404.1
30°	2744.9	2945.8	3118.4	3245.6	3287.9	3320.9	3368.0	3377.4	3369.6	3382.1	3397.8
32.5°	2820.3	3016.4	3162.4	3223.6	3218.9	3217.3	3181.2	3131.0	3120.0	3090.2	3131.0
35°	2861.1	3018.0	3074.5	2992.9	2959.9	2900.3	2785.7	2710.4	2644.5	2630.4	2633.5
37.5°	2837.5	2898.7	2831.2	2616.2	2562.9	2471.8	2319.6	2212.9	2164.2	2126.6	2175.2
40°	2710.4	2642.9	2457.7	2195.6	2118.7	2032.4	1889.6	1831.5	1762.5	1748.3	1812.7
42.5°	2500.1	2294.5	2032.4	1830.0	1749.9	1701.3	1582.0	1527.1	1478.4	1456.4	1492.5
45°	2214.5	1964.9	1701.3	1534.9	1467.4	1409.3	1338.7	1280.7	1249.3	1239.8	1269.7
47.5°	1919.4	1655.7	1445.4	1321.5	1250.8	1206.9	1141.0	1108.0	1082.9	1086.0	1090.8
50°	1636.9	1396.8	1235.1	1111.2	1076.6	1042.1	998.2	969.9	957.3	962.1	958.9
52.5°	1393.7	1199.0	1062.5	966.8	951.1	918.1	882.0	858.5	853.8	855.3	860.0
55°	1180.2	1028.0	919.7	850.6	833.4	809.8	787.9	772.2	759.6	764.3	762.7
57.5°	1018.6	885.2	802.0	745.5	732.9	718.8	698.4	690.5	685.8	676.4	684.3
60°	875.7	767.4	695.3	660.7	649.7	640.3	618.4	608.9	605.8	601.1	613.6
62.5°	740.8	663.9	608.9	577.5	566.6	557.1	546.2	538.3	539.9	533.6	539.9
65°	634.0	571.3	532.0	503.8	489.7	483.4	481.8	469.3	467.7	469.3	470.8
67.5°	535.2	481.8	452.0	434.7	423.7	417.5	412.8	404.9	411.2	406.5	409.6
70°	445.7	409.6	378.2	361.0	356.3	357.8	350.0	346.8	348.4	345.3	348.4
72.5°	359.4	329.6	317.0	304.5	298.2	296.6	291.9	287.2	291.9	290.3	290.3
75°	287.2	265.2	251.1	243.3	243.3	240.1	232.3	232.3	232.3	230.7	232.3
77.5°	221.3	202.5	196.2	188.3	188.3	183.6	182.1	182.1	178.9	183.6	180.5
80°	164.8	150.7	141.2	136.5	136.5	135.0	131.8	130.3	131.8	130.3	130.3
82.5°	106.7	100.4	95.7	91.0	89.5	91.0	89.5	86.3	87.9	86.3	89.5
85°	61.2	54.9	54.9	51.8	53.4	50.2	51.8	48.7	47.1	51.8	48.7
87.5°	26.7	25.1	25.1	22.0	22.0	22.0	20.4	22.0	20.4	18.8	20.4
90°	6.1	6.4	6.8	7.1	7.5	7.9	7.9	7.9	8.2	8.2	8.2
92.5°	115.0	77.5	55.7	41.4	38.0	34.6	28.9	27.9	27.1	26.4	27.1
95°	309.6	256.7	202.5	158.5	143.6	128.6	103.2	92.5	89.6	83.9	89.6
97.5°	386.7	368.2	324.9	280.7	259.2	237.8	216.4	197.8	188.2	183.9	188.2
100°	411.7	439.2	421.7	384.9	366.4	347.8	323.2	297.5	284.2	278.5	284.2
102.5°	396.7	463.1	481.0	468.1	457.0	446.0	419.2	402.8	388.1	384.2	388.1
105°	361.4	447.1	496.0	511.7	509.8	507.8	496.3	484.6	477.4	473.1	477.4
107.5°	327.8	414.2	478.8	516.7	524.6	532.4	535.6	533.8	530.3	526.7	530.3
110°	300.0	377.1	444.9	495.3	510.4	525.6	541.7	548.5	551.0	551.0	551.0

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	279.2	347.8	411.4	462.4	481.0	499.6	524.9	537.8	544.9	548.1	544.9
115°	265.3	324.2	379.6	428.5	448.0	467.4	495.3	512.4	522.4	527.1	522.4
117.5°	256.0	307.8	356.7	399.6	418.0	436.4	464.6	482.4	492.4	495.3	492.4
120°	248.5	295.0	337.8	377.1	392.8	408.5	434.9	452.1	461.7	464.6	461.7
122.5°	242.1	285.3	324.2	358.2	372.6	387.1	409.9	425.3	434.9	437.4	434.9
125°	236.4	276.0	312.4	343.5	356.4	369.2	389.2	403.9	411.7	415.3	411.7
127.5°	231.0	266.4	301.0	330.3	342.5	354.6	372.8	386.0	393.5	394.9	393.5
130°	225.7	257.5	288.9	316.7	328.3	339.9	357.8	369.6	376.7	378.9	376.7
132.5°	221.4	248.5	277.5	302.1	313.2	324.2	342.1	353.9	360.3	362.8	360.3
135°	218.2	241.0	265.7	288.5	298.7	308.9	324.6	336.4	342.8	344.9	342.8
137.5°	215.0	234.2	255.0	274.6	283.6	292.5	306.7	317.8	323.9	326.4	323.9
140°	212.8	228.9	245.7	262.1	269.6	277.1	290.3	299.6	304.9	306.7	304.9
142.5°	211.0	224.2	237.8	251.4	257.6	263.9	274.6	282.1	287.1	288.5	287.1
145°	209.3	220.3	231.4	242.5	247.3	252.1	260.7	266.7	270.7	272.1	270.7
147.5°	207.5	216.4	225.7	234.6	238.4	242.1	249.2	254.2	256.7	257.5	256.7
150°	205.3	213.2	221.0	227.8	231.0	234.2	239.6	243.9	245.3	245.7	245.3
152.5°	202.8	209.6	216.4	222.5	224.8	227.1	231.4	234.6	236.0	236.4	236.0
155°	200.0	206.0	211.8	216.7	218.7	220.7	224.2	226.7	227.8	228.2	227.8
157.5°	197.5	202.5	207.5	211.4	213.0	214.6	217.5	219.6	220.7	220.7	220.7
160°	194.3	198.9	202.5	206.0	207.2	208.5	211.0	212.8	213.5	213.2	213.5
162.5°	191.4	195.0	198.2	201.0	202.1	203.2	205.0	206.4	206.4	206.4	206.4
165°	188.5	191.4	193.9	196.0	196.9	197.8	199.3	200.0	200.0	200.0	200.0
167.5°	185.7	187.8	189.6	191.4	192.1	192.8	193.5	194.3	193.9	193.9	193.9
170°	183.2	185.0	186.0	187.1	187.4	187.8	188.5	188.9	188.9	188.5	188.9
172.5°	180.7	181.8	182.8	183.5	183.7	183.9	183.9	184.6	183.9	183.5	183.9
175°	178.5	179.6	179.6	180.3	180.3	180.3	180.3	180.7	180.0	179.6	180.0
177.5°	177.5	177.8	178.2	178.2	178.2	178.2	177.8	178.2	177.1	177.1	177.1
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1979.0	1968.1	1971.2	1968.1	1960.2	1955.5	1942.9	1927.3	1921.0	1913.1	1908.4
5°	2137.6	2129.7	2128.1	2115.6	2112.4	2093.6	2062.2	2046.5	2027.7	2008.9	1990.0
7.5°	2310.2	2300.8	2269.4	2264.7	2267.8	2244.3	2203.5	2172.1	2132.8	2106.2	2070.1
10°	2453.0	2434.2	2407.5	2409.1	2398.1	2366.7	2325.9	2292.9	2236.4	2201.9	2150.1
12.5°	2539.3	2523.6	2520.5	2504.8	2495.4	2454.6	2405.9	2363.6	2321.2	2274.1	2234.9
15°	2644.5	2624.1	2610.0	2588.0	2581.7	2539.3	2486.0	2437.3	2388.7	2344.7	2261.5
17.5°	2760.6	2738.6	2685.3	2680.6	2642.9	2602.1	2550.3	2478.1	2426.3	2363.6	2302.3
20°	2892.5	2861.1	2792.0	2774.7	2744.9	2677.4	2606.8	2526.8	2443.6	2379.2	2307.1
22.5°	3040.0	2985.0	2934.8	2879.9	2857.9	2774.7	2677.4	2580.1	2479.7	2391.8	2305.5
25°	3231.4	3159.3	3088.6	3033.7	2996.0	2887.7	2757.5	2628.8	2512.7	2398.1	2285.1
27.5°	3382.1	3319.3	3242.4	3170.2	3121.6	2992.9	2843.8	2677.4	2533.1	2393.4	2272.5
30°	3393.1	3374.3	3327.2	3287.9	3234.6	3096.5	2931.7	2743.4	2564.4	2394.9	2247.4
32.5°	3187.5	3225.2	3245.6	3251.9	3240.9	3160.8	3010.2	2803.0	2592.7	2380.8	2225.4
35°	2744.9	2845.4	2969.4	3016.4	3061.9	3104.3	3025.9	2845.4	2602.1	2377.7	2190.9
37.5°	2260.0	2351.0	2556.6	2650.8	2704.1	2872.0	2936.4	2839.1	2620.9	2380.8	2158.0
40°	1823.7	1968.1	2115.6	2242.7	2325.9	2514.2	2713.5	2735.5	2594.3	2351.0	2115.6
42.5°	1534.9	1619.6	1731.1	1848.8	1922.5	2145.4	2415.3	2573.9	2511.1	2302.3	2063.8
45°	1307.3	1370.1	1475.3	1514.5	1608.7	1822.1	2107.7	2336.9	2368.3	2225.4	2004.2
47.5°	1122.1	1175.5	1243.0	1291.6	1367.0	1527.1	1768.7	2021.4	2172.1	2120.3	1921.0
50°	988.7	1032.7	1089.2	1117.4	1166.1	1310.5	1492.5	1743.6	1946.1	1963.4	1812.7
52.5°	877.3	902.4	946.4	977.8	1017.0	1104.9	1269.7	1476.8	1704.4	1798.6	1679.3
55°	780.0	800.4	839.6	860.0	880.4	955.8	1084.5	1272.8	1486.2	1610.2	1542.7
57.5°	692.1	709.4	742.3	761.2	772.2	844.4	943.2	1090.8	1282.2	1432.9	1395.2
60°	619.9	635.6	654.5	668.6	681.1	740.8	809.8	929.1	1100.2	1246.1	1236.7
62.5°	543.0	557.1	577.5	591.7	602.7	640.3	698.4	789.4	935.4	1070.3	1097.0
65°	475.5	486.5	500.6	506.9	521.0	549.3	596.4	678.0	797.3	918.1	936.9
67.5°	414.3	417.5	426.9	441.0	444.1	469.3	511.6	572.8	665.4	764.3	794.1
70°	348.4	353.1	361.0	372.0	378.2	393.9	430.0	470.8	550.9	637.2	659.2
72.5°	290.3	296.6	299.8	306.0	309.2	334.3	350.0	390.8	445.7	517.9	541.5
75°	235.4	241.7	243.3	246.4	249.5	260.5	282.5	307.6	353.1	400.2	431.6
77.5°	186.8	185.2	188.3	193.0	191.5	200.9	215.0	237.0	266.8	306.0	326.4
80°	131.8	131.8	136.5	141.2	139.7	149.1	153.8	169.5	194.6	219.7	227.6
82.5°	87.9	87.9	92.6	92.6	95.7	97.3	103.6	111.4	131.8	144.4	149.1
85°	50.2	50.2	51.8	51.8	51.8	54.9	59.6	62.8	69.1	76.9	80.0
87.5°	20.4	22.0	22.0	22.0	22.0	25.1	25.1	28.2	29.8	33.0	33.0
90°	7.9	7.9	7.9	7.5	7.1	6.8	6.4	6.1	5.7	5.0	4.6
92.5°	27.9	28.9	34.6	38.0	41.4	55.7	77.5	115.0	142.5	145.0	100.7
95°	92.5	103.2	128.6	143.6	158.5	202.5	256.7	309.6	316.4	258.2	159.6
97.5°	197.8	216.4	237.8	259.2	280.7	324.9	368.2	386.7	341.7	236.7	130.3
100°	297.5	323.2	347.8	366.4	384.9	421.7	439.2	411.7	322.4	205.7	115.7
102.5°	402.8	419.2	446.0	457.0	468.1	481.0	463.1	396.7	288.5	182.1	109.6
105°	484.6	496.3	507.8	509.8	511.7	496.0	447.1	361.4	258.9	168.5	108.9
107.5°	533.8	535.6	532.4	524.6	516.7	478.8	414.2	327.8	236.7	161.4	111.4
110°	548.5	541.7	525.6	510.4	495.3	444.9	377.1	300.0	222.1	158.5	115.3

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	537.8	524.9	499.6	481.0	462.4	411.4	347.8	279.2	213.5	158.5	120.3
115°	512.4	495.3	467.4	448.0	428.5	379.6	324.2	265.3	207.8	159.6	125.3
117.5°	482.4	464.6	436.4	418.0	399.6	356.7	307.8	256.0	204.6	161.4	131.0
120°	452.1	434.9	408.5	392.8	377.1	337.8	295.0	248.5	202.5	164.3	136.8
122.5°	425.3	409.9	387.1	372.6	358.2	324.2	285.3	242.1	200.7	166.8	143.2
125°	403.9	389.2	369.2	356.4	343.5	312.4	276.0	236.4	199.3	169.6	148.9
127.5°	386.0	372.8	354.6	342.5	330.3	301.0	266.4	231.0	198.5	172.8	154.3
130°	369.6	357.8	339.9	328.3	316.7	288.9	257.5	225.7	197.8	175.7	159.6
132.5°	353.9	342.1	324.2	313.2	302.1	277.5	248.5	221.4	197.8	178.9	164.3
135°	336.4	324.6	308.9	298.7	288.5	265.7	241.0	218.2	197.8	181.8	168.5
137.5°	317.8	306.7	292.5	283.6	274.6	255.0	234.2	215.0	198.2	184.6	171.8
140°	299.6	290.3	277.1	269.6	262.1	245.7	228.9	212.8	198.5	186.4	175.0
142.5°	282.1	274.6	263.9	257.6	251.4	237.8	224.2	211.0	198.9	187.5	176.8
145°	266.7	260.7	252.1	247.3	242.5	231.4	220.3	209.3	198.5	188.2	178.5
147.5°	254.2	249.2	242.1	238.4	234.6	225.7	216.4	207.5	197.8	188.5	179.6
150°	243.9	239.6	234.2	231.0	227.8	221.0	213.2	205.3	196.8	188.5	180.7
152.5°	234.6	231.4	227.1	224.8	222.5	216.4	209.6	202.8	195.3	188.2	181.4
155°	226.7	224.2	220.7	218.7	216.7	211.8	206.0	200.0	193.5	187.5	181.8
157.5°	219.6	217.5	214.6	213.0	211.4	207.5	202.5	197.5	191.8	186.8	182.1
160°	212.8	211.0	208.5	207.2	206.0	202.5	198.9	194.3	190.0	185.7	182.1
162.5°	206.4	205.0	203.2	202.1	201.0	198.2	195.0	191.4	187.8	184.6	181.8
165°	200.0	199.3	197.8	196.9	196.0	193.9	191.4	188.5	185.7	183.5	181.4
167.5°	194.3	193.5	192.8	192.1	191.4	189.6	187.8	185.7	183.5	181.8	180.7
170°	188.9	188.5	187.8	187.4	187.1	186.0	185.0	183.2	181.8	180.7	180.0
172.5°	184.6	183.9	183.9	183.7	183.5	182.8	181.8	180.7	179.6	179.3	179.3
175°	180.7	180.3	180.3	180.3	180.3	179.6	179.6	178.5	178.2	178.2	178.5
177.5°	178.2	177.8	178.2	178.2	178.2	178.2	177.8	177.5	177.1	177.1	177.8
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1902.1	1894.3	1884.9	1884.9	1873.9	1869.2	1859.8	1856.6	1848.8	1836.2	1826.8
5°	1969.6	1949.2	1936.7	1925.7	1902.1	1884.9	1867.6	1848.8	1830.0	1808.0	1782.9
7.5°	2035.5	1997.9	1980.6	1961.8	1927.3	1891.2	1856.6	1831.5	1806.4	1771.9	1740.5
10°	2104.6	2057.5	2026.1	2001.0	1947.7	1902.1	1851.9	1815.8	1776.6	1732.6	1691.8
12.5°	2162.7	2101.5	2074.8	2027.7	1966.5	1911.6	1848.8	1793.9	1742.1	1690.3	1640.1
15°	2211.3	2153.3	2087.3	2068.5	1983.8	1905.3	1834.7	1764.0	1699.7	1647.9	1589.8
17.5°	2227.0	2153.3	2120.3	2074.8	1974.3	1892.7	1803.3	1726.4	1665.2	1588.3	1542.7
20°	2231.7	2161.1	2115.6	2073.2	1983.8	1875.5	1787.6	1693.4	1619.6	1542.7	1470.6
22.5°	2219.2	2136.0	2092.0	2051.2	1950.8	1858.2	1756.2	1652.6	1566.3	1495.7	1423.5
25°	2195.6	2098.3	2055.9	2012.0	1916.3	1814.3	1702.8	1604.0	1523.9	1439.2	1368.5
27.5°	2164.2	2052.8	2004.2	1958.6	1864.5	1768.7	1663.6	1561.6	1472.1	1382.7	1316.7
30°	2125.0	1996.3	1952.4	1892.7	1801.7	1710.7	1614.9	1512.9	1412.5	1327.7	1255.5
32.5°	2074.8	1939.8	1881.7	1825.2	1726.4	1643.2	1552.2	1456.4	1359.1	1275.9	1200.6
35°	2029.3	1875.5	1811.1	1754.6	1644.8	1556.9	1481.5	1392.1	1305.8	1219.4	1152.0
37.5°	1968.1	1811.1	1734.2	1676.1	1564.7	1475.3	1404.6	1335.6	1244.6	1161.4	1098.6
40°	1903.7	1731.1	1658.9	1600.8	1484.7	1387.4	1319.9	1258.7	1184.9	1108.0	1042.1
42.5°	1845.6	1654.2	1577.3	1506.6	1388.9	1302.6	1233.6	1186.5	1119.0	1049.9	990.3
45°	1771.9	1572.6	1489.4	1415.6	1302.6	1208.5	1142.5	1104.9	1054.7	987.2	935.4
47.5°	1696.5	1484.7	1398.4	1326.2	1203.7	1120.6	1056.2	1020.1	985.6	932.2	880.4
50°	1597.7	1392.1	1313.6	1230.4	1109.6	1024.8	971.5	935.4	908.7	871.0	827.1
52.5°	1489.4	1296.3	1211.6	1139.4	1020.1	943.2	882.0	861.6	834.9	806.7	769.0
55°	1374.8	1192.8	1111.2	1040.5	930.7	852.2	802.0	780.0	759.6	737.6	712.5
57.5°	1260.2	1084.5	1007.6	944.8	842.8	767.4	726.6	696.8	682.7	670.1	649.7
60°	1117.4	968.3	908.7	852.2	751.8	682.7	643.5	621.5	608.9	602.7	593.2
62.5°	991.9	869.5	803.5	748.6	668.6	607.4	569.7	552.4	541.5	538.3	527.3
65°	858.5	753.3	701.5	654.5	585.4	530.5	499.1	478.7	470.8	469.3	469.3
67.5°	732.9	648.2	596.4	563.4	503.8	455.1	425.3	417.5	412.8	406.5	404.9
70°	615.2	547.7	502.2	474.0	420.6	384.5	361.0	348.4	348.4	343.7	340.6
72.5°	511.6	444.1	414.3	390.8	346.8	315.5	298.2	295.1	284.1	282.5	282.5
75°	400.2	350.0	329.6	309.2	276.2	254.2	240.1	232.3	226.0	226.0	227.6
77.5°	301.3	266.8	248.0	232.3	208.7	194.6	183.6	180.5	174.2	174.2	174.2
80°	213.4	194.6	180.5	167.9	150.7	138.1	131.8	125.6	125.6	124.0	125.6
82.5°	138.1	122.4	114.6	113.0	97.3	92.6	84.7	86.3	81.6	80.0	83.2
85°	80.0	72.2	62.8	59.6	53.4	47.1	43.9	45.5	43.9	42.4	43.9
87.5°	31.4	26.7	25.1	25.1	20.4	18.8	17.3	18.8	15.7	15.7	17.3
90°	3.9	3.6	3.2	2.9	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	60.0	35.7	29.3	22.9	15.4	10.0	6.4	5.4	6.4	10.0	15.4
95°	81.1	42.9	34.8	26.8	18.9	15.0	12.1	11.8	12.1	15.0	18.9
97.5°	70.0	43.6	37.7	31.8	24.6	20.7	18.6	18.2	18.6	20.7	24.6
100°	69.3	48.6	43.2	37.9	31.1	27.1	25.7	25.0	25.7	27.1	31.1
102.5°	72.5	54.6	49.4	44.3	38.2	33.9	32.9	32.5	32.9	33.9	38.2
105°	77.1	61.4	56.4	51.4	45.7	42.1	40.4	40.4	40.4	42.1	45.7
107.5°	83.6	68.2	63.8	59.3	53.2	50.3	48.6	47.8	48.6	50.3	53.2
110°	90.7	76.1	71.4	66.8	61.4	58.2	56.8	56.1	56.8	58.2	61.4

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	97.5	83.6	79.1	74.6	69.3	66.1	65.0	64.3	65.0	66.1	69.3
115°	104.6	91.4	87.0	82.5	77.1	73.9	72.8	72.1	72.8	73.9	77.1
117.5°	111.8	99.3	95.0	90.7	84.6	81.4	80.3	79.3	80.3	81.4	84.6
120°	119.6	107.1	102.6	98.2	92.1	88.9	87.5	86.4	87.5	88.9	92.1
122.5°	127.1	114.6	110.2	105.7	98.9	95.7	94.6	93.9	94.6	95.7	98.9
125°	133.5	121.8	117.2	112.5	105.7	102.5	100.7	100.0	100.7	102.5	105.7
127.5°	140.0	128.6	124.0	119.3	112.1	108.2	106.1	105.0	106.1	108.2	112.1
130°	146.0	135.0	130.4	125.7	118.2	113.6	110.7	109.6	110.7	113.6	118.2
132.5°	151.8	140.7	136.0	131.4	123.6	118.2	114.6	113.2	114.6	118.2	123.6
135°	156.8	145.7	140.8	136.0	128.6	122.8	118.6	117.1	118.6	122.8	128.6
137.5°	160.3	150.3	145.3	140.3	132.8	127.1	123.2	122.1	123.2	127.1	132.8
140°	164.3	153.9	149.1	144.3	137.5	131.8	127.5	126.4	127.5	131.8	137.5
142.5°	166.8	157.1	152.6	148.2	141.8	136.0	132.1	131.4	132.1	136.0	141.8
145°	169.6	160.3	156.2	152.1	145.7	140.7	137.1	136.4	137.1	140.7	145.7
147.5°	171.4	163.2	159.4	155.7	150.0	145.3	142.1	141.8	142.1	145.3	150.0
150°	173.2	165.3	162.3	159.3	154.3	149.6	147.1	146.4	147.1	149.6	154.3
152.5°	175.0	167.8	165.2	162.5	157.8	153.9	151.8	151.4	151.8	153.9	157.8
155°	176.0	170.0	167.5	165.0	161.4	157.8	155.7	155.7	155.7	157.8	161.4
157.5°	177.1	171.8	169.8	167.8	164.6	161.4	159.6	159.6	159.6	161.4	164.6
160°	177.8	173.2	171.6	170.0	167.1	164.6	163.2	163.5	163.2	164.6	167.1
162.5°	178.5	174.6	173.4	172.1	170.0	167.8	166.4	166.8	166.4	167.8	170.0
165°	178.5	175.7	174.6	173.5	172.1	170.3	169.3	170.0	169.3	170.3	172.1
167.5°	178.5	176.0	175.3	174.6	173.5	172.5	171.8	172.1	171.8	172.5	173.5
170°	178.5	176.8	176.2	175.7	175.0	174.3	173.9	174.3	173.9	174.3	175.0
172.5°	178.2	176.8	176.6	176.4	176.0	175.3	175.0	175.7	175.0	175.3	176.0
175°	177.8	176.8	176.8	176.8	176.8	176.4	176.0	176.8	176.0	176.4	176.8
177.5°	177.5	176.8	176.8	176.8	177.1	176.8	176.8	177.5	176.8	176.8	177.1
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1823.7	1820.5	1812.7	1808.0	1792.3	1773.5	1767.2	1751.5	1757.8	1746.8	1746.8
5°	1775.0	1760.9	1751.5	1737.4	1707.5	1687.1	1665.2	1654.2	1647.9	1640.1	1633.8
7.5°	1712.2	1701.3	1691.8	1665.2	1632.2	1604.0	1577.3	1566.3	1545.9	1531.8	1525.5
10°	1657.3	1641.6	1619.6	1588.3	1553.7	1517.6	1494.1	1470.6	1454.9	1447.0	1429.7
12.5°	1600.8	1582.0	1558.4	1512.9	1475.3	1453.3	1410.9	1388.9	1381.1	1374.8	1354.4
15°	1542.7	1522.3	1494.1	1451.7	1418.8	1367.0	1341.9	1324.6	1305.8	1304.2	1288.5
17.5°	1491.0	1465.8	1442.3	1390.5	1349.7	1304.2	1290.1	1271.2	1254.0	1235.1	1227.3
20°	1425.0	1401.5	1384.2	1327.7	1282.2	1254.0	1230.4	1214.7	1203.7	1184.9	1181.8
22.5°	1365.4	1340.3	1316.7	1274.4	1235.1	1199.0	1170.8	1153.5	1148.8	1141.0	1126.8
25°	1307.3	1282.2	1254.0	1214.7	1173.9	1148.8	1123.7	1112.7	1103.3	1090.8	1079.8
27.5°	1258.7	1235.1	1208.5	1159.8	1125.3	1106.4	1079.8	1067.2	1054.7	1048.4	1043.7
30°	1200.6	1173.9	1153.5	1115.9	1078.2	1053.1	1034.3	1023.3	1012.3	1006.0	1002.9
32.5°	1144.1	1119.0	1104.9	1064.1	1034.3	1004.4	990.3	982.5	976.2	969.9	963.6
35°	1098.6	1073.5	1051.5	1013.8	984.0	963.6	952.6	940.1	935.4	929.1	929.1
37.5°	1042.1	1023.3	1001.3	965.2	938.5	922.8	913.4	897.7	896.1	893.0	888.3
40°	993.4	974.6	954.2	922.8	899.3	880.4	867.9	860.0	855.3	852.2	849.1
42.5°	941.7	921.3	911.8	875.7	855.3	836.5	830.2	822.4	820.8	814.5	806.7
45°	891.4	874.2	855.3	828.7	811.4	795.7	786.3	780.0	772.2	770.6	765.9
47.5°	847.5	827.1	809.8	784.7	765.9	753.3	745.5	737.6	731.4	726.6	721.9
50°	791.0	775.3	761.2	734.5	718.8	706.2	695.3	689.0	682.7	682.7	682.7
52.5°	736.1	721.9	709.4	690.5	671.7	660.7	648.2	643.5	640.3	635.6	640.3
55°	682.7	668.6	656.0	641.9	619.9	610.5	598.0	593.2	594.8	594.8	599.5
57.5°	626.2	615.2	607.4	590.1	569.7	560.3	552.4	547.7	547.7	554.0	555.6
60°	571.3	560.3	546.2	530.5	517.9	506.9	502.2	503.8	503.8	506.9	514.8
62.5°	510.1	503.8	495.9	474.0	466.1	458.3	452.0	456.7	455.1	463.0	474.0
65°	453.6	447.3	436.3	425.3	415.9	408.1	406.5	408.1	411.2	419.0	431.6
67.5°	390.8	390.8	381.4	372.0	364.1	356.3	357.8	359.4	362.5	372.0	390.8
70°	339.0	332.7	323.3	317.0	310.7	307.6	304.5	310.7	320.2	326.4	340.6
72.5°	282.5	277.8	269.9	263.7	262.1	259.0	257.4	260.5	269.9	280.9	296.6
75°	222.9	224.4	219.7	215.0	215.0	210.3	213.4	213.4	222.9	233.8	246.4
77.5°	172.6	171.1	169.5	166.4	164.8	164.8	164.8	167.9	177.3	183.6	196.2
80°	122.4	124.0	119.3	120.8	119.3	120.8	120.8	127.1	131.8	139.7	149.1
82.5°	81.6	81.6	78.5	80.0	80.0	80.0	81.6	84.7	91.0	97.3	103.6
85°	45.5	47.1	43.9	47.1	47.1	47.1	48.7	50.2	54.9	56.5	62.8
87.5°	17.3	20.4	20.4	17.3	18.8	20.4	22.0	20.4	23.5	26.7	28.2
90°	2.9	3.2	3.6	3.9	4.6	5.0	5.7	6.1	6.4	6.8	7.1
92.5°	22.9	29.3	35.7	60.0	100.7	145.0	142.5	115.0	77.5	55.7	41.4
95°	26.8	34.8	42.9	81.1	159.6	258.2	316.4	309.6	256.7	202.5	158.5
97.5°	31.8	37.7	43.6	70.0	130.3	236.7	341.7	386.7	368.2	324.9	280.7
100°	37.9	43.2	48.6	69.3	115.7	205.7	322.4	411.7	439.2	421.7	384.9
102.5°	44.3	49.4	54.6	72.5	109.6	182.1	288.5	396.7	463.1	481.0	468.1
105°	51.4	56.4	61.4	77.1	108.9	168.5	258.9	361.4	447.1	496.0	511.7
107.5°	59.3	63.8	68.2	83.6	111.4	161.4	236.7	327.8	414.2	478.8	516.7
110°	66.8	71.4	76.1	90.7	115.3	158.5	222.1	300.0	377.1	444.9	495.3

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	74.6	79.1	83.6	97.5	120.3	158.5	213.5	279.2	347.8	411.4	462.4
115°	82.5	87.0	91.4	104.6	125.3	159.6	207.8	265.3	324.2	379.6	428.5
117.5°	90.7	95.0	99.3	111.8	131.0	161.4	204.6	256.0	307.8	356.7	399.6
120°	98.2	102.6	107.1	119.6	136.8	164.3	202.5	248.5	295.0	337.8	377.1
122.5°	105.7	110.2	114.6	127.1	143.2	166.8	200.7	242.1	285.3	324.2	358.2
125°	112.5	117.2	121.8	133.5	148.9	169.6	199.3	236.4	276.0	312.4	343.5
127.5°	119.3	124.0	128.6	140.0	154.3	172.8	198.5	231.0	266.4	301.0	330.3
130°	125.7	130.4	135.0	146.0	159.6	175.7	197.8	225.7	257.5	288.9	316.7
132.5°	131.4	136.0	140.7	151.8	164.3	178.9	197.8	221.4	248.5	277.5	302.1
135°	136.0	140.8	145.7	156.8	168.5	181.8	197.8	218.2	241.0	265.7	288.5
137.5°	140.3	145.3	150.3	160.3	171.8	184.6	198.2	215.0	234.2	255.0	274.6
140°	144.3	149.1	153.9	164.3	175.0	186.4	198.5	212.8	228.9	245.7	262.1
142.5°	148.2	152.6	157.1	166.8	176.8	187.5	198.9	211.0	224.2	237.8	251.4
145°	152.1	156.2	160.3	169.6	178.5	188.2	198.5	209.3	220.3	231.4	242.5
147.5°	155.7	159.4	163.2	171.4	179.6	188.5	197.8	207.5	216.4	225.7	234.6
150°	159.3	162.3	165.3	173.2	180.7	188.5	196.8	205.3	213.2	221.0	227.8
152.5°	162.5	165.2	167.8	175.0	181.4	188.2	195.3	202.8	209.6	216.4	222.5
155°	165.0	167.5	170.0	176.0	181.8	187.5	193.5	200.0	206.0	211.8	216.7
157.5°	167.8	169.8	171.8	177.1	182.1	186.8	191.8	197.5	202.5	207.5	211.4
160°	170.0	171.6	173.2	177.8	182.1	185.7	190.0	194.3	198.9	202.5	206.0
162.5°	172.1	173.4	174.6	178.5	181.8	184.6	187.8	191.4	195.0	198.2	201.0
165°	173.5	174.6	175.7	178.5	181.4	183.5	185.7	188.5	191.4	193.9	196.0
167.5°	174.6	175.3	176.0	178.5	180.7	181.8	183.5	185.7	187.8	189.6	191.4
170°	175.7	176.2	176.8	178.5	180.0	180.7	181.8	183.2	185.0	186.0	187.1
172.5°	176.4	176.6	176.8	178.2	179.3	179.3	179.6	180.7	181.8	182.8	183.5
175°	176.8	176.8	176.8	177.8	178.5	178.2	178.2	178.5	179.6	179.6	180.3
177.5°	176.8	176.8	176.8	177.5	177.8	177.1	177.1	177.5	177.8	178.2	178.2
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1753.0	1742.1	1740.5	1743.6	1737.4	1746.8	1743.6	1746.8	1738.9	1746.8	1742.1
5°	1632.2	1629.1	1622.8	1614.9	1616.5	1618.1	1625.9	1618.1	1624.4	1625.9	1633.8
7.5°	1519.2	1512.9	1517.6	1514.5	1500.4	1497.2	1500.4	1505.1	1514.5	1520.8	1525.5
10°	1428.2	1425.0	1418.8	1414.1	1406.2	1401.5	1407.8	1401.5	1414.1	1425.0	1425.0
12.5°	1359.1	1346.6	1338.7	1337.2	1319.9	1323.0	1329.3	1334.0	1348.1	1354.4	1354.4
15°	1286.9	1277.5	1274.4	1268.1	1261.8	1268.1	1265.0	1269.7	1275.9	1282.2	1285.4
17.5°	1224.2	1222.6	1224.2	1208.5	1213.2	1205.3	1206.9	1214.7	1210.0	1214.7	1224.2
20°	1167.7	1170.8	1166.1	1159.8	1159.8	1150.4	1161.4	1158.2	1159.8	1169.2	1183.3
22.5°	1125.3	1123.7	1119.0	1114.3	1108.0	1109.6	1111.2	1108.0	1120.6	1128.4	1130.0
25°	1079.8	1076.6	1075.1	1070.3	1064.1	1070.3	1068.8	1070.3	1073.5	1086.0	1076.6
27.5°	1037.4	1031.1	1034.3	1029.5	1028.0	1029.5	1029.5	1031.1	1034.3	1035.8	1037.4
30°	1001.3	995.0	993.4	990.3	988.7	990.3	993.4	990.3	1002.9	1001.3	1001.3
32.5°	962.1	957.3	954.2	954.2	952.6	951.1	952.6	954.2	963.6	957.3	963.6
35°	924.4	921.3	921.3	918.1	916.5	916.5	916.5	922.8	919.7	924.4	924.4
37.5°	888.3	888.3	886.7	883.6	882.0	883.6	882.0	885.2	883.6	885.2	886.7
40°	850.6	847.5	845.9	845.9	841.2	836.5	841.2	841.2	842.8	847.5	849.1
42.5°	805.1	806.7	806.7	800.4	800.4	800.4	802.0	803.5	803.5	806.7	806.7
45°	765.9	762.7	762.7	762.7	759.6	761.2	764.3	764.3	764.3	764.3	761.2
47.5°	721.9	721.9	723.5	723.5	728.2	726.6	726.6	725.1	721.9	721.9	723.5
50°	681.1	685.8	687.4	687.4	689.0	690.5	690.5	687.4	685.8	681.1	681.1
52.5°	641.9	645.0	648.2	652.9	656.0	654.5	654.5	651.3	645.0	643.5	641.9
55°	599.5	604.2	610.5	615.2	619.9	621.5	621.5	615.2	608.9	601.1	601.1
57.5°	560.3	565.0	576.0	580.7	587.0	587.0	583.8	579.1	569.7	563.4	558.7
60°	521.0	528.9	536.7	546.2	554.0	555.6	550.9	544.6	533.6	525.8	519.5
62.5°	478.7	486.5	502.2	511.6	517.9	517.9	517.9	510.1	495.9	485.0	475.5
65°	437.9	445.7	459.8	472.4	477.1	481.8	477.1	469.3	458.3	445.7	436.3
67.5°	395.5	404.9	419.0	428.5	434.7	439.4	436.3	430.0	415.9	398.6	392.4
70°	348.4	353.1	373.5	382.9	392.4	395.5	392.4	382.9	368.8	350.0	343.7
72.5°	304.5	309.2	328.0	335.9	343.7	346.8	342.1	335.9	323.3	306.0	298.2
75°	254.2	262.1	271.5	284.1	293.5	296.6	291.9	287.2	271.5	260.5	254.2
77.5°	200.9	208.7	221.3	232.3	241.7	240.1	233.8	235.4	218.2	205.6	200.9
80°	152.2	158.5	167.9	177.3	182.1	182.1	180.5	174.2	167.9	158.5	150.7
82.5°	105.2	113.0	120.8	127.1	127.1	128.7	125.6	124.0	117.7	109.9	108.3
85°	62.8	64.3	70.6	70.6	76.9	73.8	72.2	76.9	70.6	65.9	64.3
87.5°	28.2	26.7	28.2	28.2	26.7	29.8	29.8	28.2	29.8	28.2	28.2
90°	7.5	7.9	7.9	7.9	8.2	8.2	8.2	7.9	7.9	7.9	7.5
92.5°	38.0	34.6	28.9	27.9	27.1	26.4	27.1	27.9	28.9	34.6	38.0
95°	143.6	128.6	103.2	92.5	89.6	83.9	89.6	92.5	103.2	128.6	143.6
97.5°	259.2	237.8	216.4	197.8	188.2	183.9	188.2	197.8	216.4	237.8	259.2
100°	366.4	347.8	323.2	297.5	284.2	278.5	284.2	297.5	323.2	347.8	366.4
102.5°	457.0	446.0	419.2	402.8	388.1	384.2	388.1	402.8	419.2	446.0	457.0
105°	509.8	507.8	496.3	484.6	477.4	473.1	477.4	484.6	496.3	507.8	509.8
107.5°	524.6	532.4	535.6	533.8	530.3	526.7	530.3	533.8	535.6	532.4	524.6
110°	510.4	525.6	541.7	548.5	551.0	551.0	551.0	548.5	541.7	525.6	510.4

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	481.0	499.6	524.9	537.8	544.9	548.1	544.9	537.8	524.9	499.6	481.0
115°	448.0	467.4	495.3	512.4	522.4	527.1	522.4	512.4	495.3	467.4	448.0
117.5°	418.0	436.4	464.6	482.4	492.4	495.3	492.4	482.4	464.6	436.4	418.0
120°	392.8	408.5	434.9	452.1	461.7	464.6	461.7	452.1	434.9	408.5	392.8
122.5°	372.6	387.1	409.9	425.3	434.9	437.4	434.9	425.3	409.9	387.1	372.6
125°	356.4	369.2	389.2	403.9	411.7	415.3	411.7	403.9	389.2	369.2	356.4
127.5°	342.5	354.6	372.8	386.0	393.5	394.9	393.5	386.0	372.8	354.6	342.5
130°	328.3	339.9	357.8	369.6	376.7	378.9	376.7	369.6	357.8	339.9	328.3
132.5°	313.2	324.2	342.1	353.9	360.3	362.8	360.3	353.9	342.1	324.2	313.2
135°	298.7	308.9	324.6	336.4	342.8	344.9	342.8	336.4	324.6	308.9	298.7
137.5°	283.6	292.5	306.7	317.8	323.9	326.4	323.9	317.8	306.7	292.5	283.6
140°	269.6	277.1	290.3	299.6	304.9	306.7	304.9	299.6	290.3	277.1	269.6
142.5°	257.6	263.9	274.6	282.1	287.1	288.5	287.1	282.1	274.6	263.9	257.6
145°	247.3	252.1	260.7	266.7	270.7	272.1	270.7	266.7	260.7	252.1	247.3
147.5°	238.4	242.1	249.2	254.2	256.7	257.5	256.7	254.2	249.2	242.1	238.4
150°	231.0	234.2	239.6	243.9	245.3	245.7	245.3	243.9	239.6	234.2	231.0
152.5°	224.8	227.1	231.4	234.6	236.0	236.4	236.0	234.6	231.4	227.1	224.8
155°	218.7	220.7	224.2	226.7	227.8	228.2	227.8	226.7	224.2	220.7	218.7
157.5°	213.0	214.6	217.5	219.6	220.7	220.7	220.7	219.6	217.5	214.6	213.0
160°	207.2	208.5	211.0	212.8	213.5	213.2	213.5	212.8	211.0	208.5	207.2
162.5°	202.1	203.2	205.0	206.4	206.4	206.4	206.4	206.4	205.0	203.2	202.1
165°	196.9	197.8	199.3	200.0	200.0	200.0	200.0	200.0	199.3	197.8	196.9
167.5°	192.1	192.8	193.5	194.3	193.9	193.9	193.9	194.3	193.5	192.8	192.1
170°	187.4	187.8	188.5	188.9	188.9	188.5	188.9	188.9	188.5	187.8	187.4
172.5°	183.7	183.9	183.9	184.6	183.9	183.5	183.9	184.6	183.9	183.9	183.7
175°	180.3	180.3	180.3	180.7	180.0	179.6	180.0	180.7	180.3	180.3	180.3
177.5°	178.2	178.2	177.8	178.2	177.1	177.1	177.1	178.2	177.8	178.2	178.2
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1756.2	1746.8	1757.8	1743.6	1746.8	1764.0	1762.5	1778.2	1787.6	1786.0	1793.9
5°	1640.1	1640.1	1644.8	1643.2	1658.9	1673.0	1691.8	1707.5	1724.8	1734.2	1745.2
7.5°	1525.5	1541.2	1544.3	1552.2	1571.0	1594.5	1613.4	1636.9	1662.0	1679.3	1691.8
10°	1431.3	1443.9	1456.4	1462.7	1483.1	1514.5	1541.2	1578.8	1610.2	1629.1	1646.3
12.5°	1348.1	1362.3	1368.5	1396.8	1410.9	1431.3	1469.0	1509.8	1544.3	1564.7	1578.8
15°	1288.5	1296.3	1310.5	1327.7	1341.9	1367.0	1398.4	1443.9	1476.8	1494.1	1542.7
17.5°	1238.3	1247.7	1255.5	1263.4	1285.4	1312.0	1341.9	1381.1	1423.5	1453.3	1478.4
20°	1186.5	1191.2	1200.6	1213.2	1228.9	1254.0	1280.7	1321.5	1359.1	1382.7	1415.6
22.5°	1125.3	1139.4	1148.8	1158.2	1175.5	1203.7	1228.9	1258.7	1305.8	1332.4	1367.0
25°	1089.2	1095.5	1101.7	1112.7	1125.3	1150.4	1178.6	1210.0	1247.7	1275.9	1305.8
27.5°	1042.1	1051.5	1059.4	1073.5	1081.3	1101.7	1128.4	1159.8	1205.3	1228.9	1254.0
30°	1002.9	1012.3	1018.6	1024.8	1035.8	1057.8	1082.9	1108.0	1150.4	1180.2	1205.3
32.5°	963.6	973.0	980.9	985.6	996.6	1010.7	1031.1	1062.5	1098.6	1119.0	1152.0
35°	929.1	929.1	938.5	944.8	954.2	966.8	985.6	1009.1	1046.8	1073.5	1103.3
37.5°	889.9	891.4	899.3	904.0	913.4	926.0	944.8	966.8	998.2	1018.6	1048.4
40°	849.1	853.8	856.9	864.8	875.7	880.4	899.3	924.4	955.8	974.6	999.7
42.5°	808.3	811.4	819.2	825.5	834.9	842.8	855.3	878.9	902.4	930.7	951.1
45°	762.7	770.6	775.3	786.3	791.0	798.8	811.4	830.2	858.5	875.7	899.3
47.5°	723.5	726.6	729.8	743.9	753.3	758.0	770.6	781.6	811.4	827.1	849.1
50°	681.1	681.1	685.8	692.1	703.1	712.5	723.5	736.1	759.6	775.3	797.3
52.5°	641.9	637.2	640.3	643.5	654.5	663.9	674.9	692.1	714.1	723.5	742.3
55°	599.5	591.7	596.4	601.1	604.2	616.8	629.3	640.3	657.6	671.7	689.0
57.5°	554.0	552.4	549.3	550.9	558.7	566.6	576.0	590.1	610.5	621.5	630.9
60°	513.2	503.8	500.6	503.8	508.5	513.2	525.8	538.3	555.6	566.6	577.5
62.5°	470.8	461.4	455.1	450.4	455.1	466.1	474.0	483.4	497.5	510.1	519.5
65°	430.0	415.9	409.6	406.5	404.9	412.8	419.0	431.6	444.1	448.9	459.8
67.5°	384.5	372.0	364.1	359.4	359.4	359.4	365.7	378.2	390.8	392.4	403.3
70°	339.0	324.9	317.0	310.7	307.6	310.7	318.6	320.2	331.1	334.3	340.6
72.5°	290.3	277.8	268.4	260.5	262.1	265.2	265.2	268.4	274.6	282.5	282.5
75°	244.8	227.6	222.9	216.6	213.4	213.4	213.4	219.7	224.4	230.7	229.1
77.5°	193.0	183.6	174.2	171.1	166.4	164.8	167.9	167.9	171.1	175.8	177.3
80°	149.1	138.1	131.8	128.7	122.4	120.8	122.4	122.4	127.1	125.6	127.1
82.5°	103.6	95.7	91.0	86.3	83.2	84.7	83.2	83.2	84.7	83.2	83.2
85°	59.6	58.1	54.9	53.4	51.8	48.7	51.8	50.2	48.7	47.1	50.2
87.5°	28.2	26.7	26.7	23.5	23.5	22.0	23.5	23.5	22.0	22.0	22.0
90°	7.1	6.8	6.4	6.1	5.7	5.0	4.6	3.9	3.6	3.2	2.9
92.5°	41.4	55.7	77.5	115.0	142.5	145.0	100.7	60.0	35.7	29.3	22.9
95°	158.5	202.5	256.7	309.6	316.4	258.2	159.6	81.1	42.9	34.8	26.8
97.5°	280.7	324.9	368.2	386.7	341.7	236.7	130.3	70.0	43.6	37.7	31.8
100°	384.9	421.7	439.2	411.7	322.4	205.7	115.7	69.3	48.6	43.2	37.9
102.5°	468.1	481.0	463.1	396.7	288.5	182.1	109.6	72.5	54.6	49.4	44.3
105°	511.7	496.0	447.1	361.4	258.9	168.5	108.9	77.1	61.4	56.4	51.4
107.5°	516.7	478.8	414.2	327.8	236.7	161.4	111.4	83.6	68.2	63.8	59.3
110°	495.3	444.9	377.1	300.0	222.1	158.5	115.3	90.7	76.1	71.4	66.8

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	462.4	411.4	347.8	279.2	213.5	158.5	120.3	97.5	83.6	79.1	74.6
115°	428.5	379.6	324.2	265.3	207.8	159.6	125.3	104.6	91.4	87.0	82.5
117.5°	399.6	356.7	307.8	256.0	204.6	161.4	131.0	111.8	99.3	95.0	90.7
120°	377.1	337.8	295.0	248.5	202.5	164.3	136.8	119.6	107.1	102.6	98.2
122.5°	358.2	324.2	285.3	242.1	200.7	166.8	143.2	127.1	114.6	110.2	105.7
125°	343.5	312.4	276.0	236.4	199.3	169.6	148.9	133.5	121.8	117.2	112.5
127.5°	330.3	301.0	266.4	231.0	198.5	172.8	154.3	140.0	128.6	124.0	119.3
130°	316.7	288.9	257.5	225.7	197.8	175.7	159.6	146.0	135.0	130.4	125.7
132.5°	302.1	277.5	248.5	221.4	197.8	178.9	164.3	151.8	140.7	136.0	131.4
135°	288.5	265.7	241.0	218.2	197.8	181.8	168.5	156.8	145.7	140.8	136.0
137.5°	274.6	255.0	234.2	215.0	198.2	184.6	171.8	160.3	150.3	145.3	140.3
140°	262.1	245.7	228.9	212.8	198.5	186.4	175.0	164.3	153.9	149.1	144.3
142.5°	251.4	237.8	224.2	211.0	198.9	187.5	176.8	166.8	157.1	152.6	148.2
145°	242.5	231.4	220.3	209.3	198.5	188.2	178.5	169.6	160.3	156.2	152.1
147.5°	234.6	225.7	216.4	207.5	197.8	188.5	179.6	171.4	163.2	159.4	155.7
150°	227.8	221.0	213.2	205.3	196.8	188.5	180.7	173.2	165.3	162.3	159.3
152.5°	222.5	216.4	209.6	202.8	195.3	188.2	181.4	175.0	167.8	165.2	162.5
155°	216.7	211.8	206.0	200.0	193.5	187.5	181.8	176.0	170.0	167.5	165.0
157.5°	211.4	207.5	202.5	197.5	191.8	186.8	182.1	177.1	171.8	169.8	167.8
160°	206.0	202.5	198.9	194.3	190.0	185.7	182.1	177.8	173.2	171.6	170.0
162.5°	201.0	198.2	195.0	191.4	187.8	184.6	181.8	178.5	174.6	173.4	172.1
165°	196.0	193.9	191.4	188.5	185.7	183.5	181.4	178.5	175.7	174.6	173.5
167.5°	191.4	189.6	187.8	185.7	183.5	181.8	180.7	178.5	176.0	175.3	174.6
170°	187.1	186.0	185.0	183.2	181.8	180.7	180.0	178.5	176.8	176.2	175.7
172.5°	183.5	182.8	181.8	180.7	179.6	179.3	179.3	178.2	176.8	176.6	176.4
175°	180.3	179.6	179.6	178.5	178.2	178.2	178.5	177.8	176.8	176.8	176.8
177.5°	178.2	178.2	177.8	177.5	177.1	177.1	177.8	177.5	176.8	176.8	176.8
180°	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1	177.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.8	1848.8	1848.8	1848.8
2.5°	1804.8	1820.5	1831.5	1851.9
5°	1764.0	1792.3	1819.0	1847.2
7.5°	1723.2	1756.2	1798.6	1834.7
10°	1677.7	1720.1	1770.3	1819.0
12.5°	1632.2	1682.4	1737.4	1801.7
15°	1577.3	1641.6	1706.0	1775.0
17.5°	1528.6	1594.5	1663.6	1749.9
20°	1473.7	1545.9	1621.2	1709.1
22.5°	1425.0	1505.1	1583.6	1676.1
25°	1370.1	1448.6	1534.9	1633.8
27.5°	1324.6	1396.8	1481.5	1588.3
30°	1269.7	1348.1	1432.9	1539.6
32.5°	1217.9	1293.2	1382.7	1487.8
35°	1164.5	1241.4	1321.5	1421.9
37.5°	1114.3	1180.2	1260.2	1356.0
40°	1057.8	1130.0	1202.2	1277.5
42.5°	1006.0	1071.9	1139.4	1199.0
45°	947.9	1004.4	1068.8	1117.4
47.5°	894.6	944.8	995.0	1032.7
50°	841.2	880.4	918.1	951.1
52.5°	778.4	822.4	842.8	863.2
55°	721.9	747.0	765.9	786.3
57.5°	667.0	678.0	687.4	706.2
60°	594.8	607.4	618.4	632.5
62.5°	532.0	538.3	541.5	555.6
65°	472.4	470.8	478.7	486.5
67.5°	408.1	406.5	414.3	417.5
70°	345.3	343.7	345.3	353.1
72.5°	285.6	285.6	287.2	290.3
75°	230.7	230.7	232.3	235.4
77.5°	174.2	177.3	175.8	182.1
80°	127.1	124.0	127.1	130.3
82.5°	83.2	86.3	86.3	83.2
85°	47.1	47.1	47.1	47.1
87.5°	20.4	20.4	22.0	23.5
90°	2.1	1.4	0.7	0.4
92.5°	15.4	10.0	6.4	5.4
95°	18.9	15.0	12.1	11.8
97.5°	24.6	20.7	18.6	18.2
100°	31.1	27.1	25.7	25.0
102.5°	38.2	33.9	32.9	32.5
105°	45.7	42.1	40.4	40.4
107.5°	53.2	50.3	48.6	47.8
110°	61.4	58.2	56.8	56.1

TEST NUMBER: P1027636

CATALOG NUMBER: S125DIP-B1270D375UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	69.3	66.1	65.0	64.3
115°	77.1	73.9	72.8	72.1
117.5°	84.6	81.4	80.3	79.3
120°	92.1	88.9	87.5	86.4
122.5°	98.9	95.7	94.6	93.9
125°	105.7	102.5	100.7	100.0
127.5°	112.1	108.2	106.1	105.0
130°	118.2	113.6	110.7	109.6
132.5°	123.6	118.2	114.6	113.2
135°	128.6	122.8	118.6	117.1
137.5°	132.8	127.1	123.2	122.1
140°	137.5	131.8	127.5	126.4
142.5°	141.8	136.0	132.1	131.4
145°	145.7	140.7	137.1	136.4
147.5°	150.0	145.3	142.1	141.8
150°	154.3	149.6	147.1	146.4
152.5°	157.8	153.9	151.8	151.4
155°	161.4	157.8	155.7	155.7
157.5°	164.6	161.4	159.6	159.6
160°	167.1	164.6	163.2	163.5
162.5°	170.0	167.8	166.4	166.8
165°	172.1	170.3	169.3	170.0
167.5°	173.5	172.5	171.8	172.1
170°	175.0	174.3	173.9	174.3
172.5°	176.0	175.3	175.0	175.7
175°	176.8	176.4	176.0	176.8
177.5°	177.1	176.8	176.8	177.5
180°	177.1	177.1	177.1	177.1

(END OF REPORT)