

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027672

Luminaire Tested: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027672
REPORT IS A COMBINATION OF REPORTS P1001725 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB30-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7325.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	75	75	75	71	71	71
1	103	98	95	91	97	93	90	87	84	81	79	75	73	71	67	66	64	60	60	60
2	94	86	80	75	89	82	77	72	74	70	66	66	63	60	59	57	55	51	51	51
3	86	76	69	63	81	72	66	60	65	60	56	59	55	51	53	50	47	44	44	44
4	79	68	60	53	74	64	57	52	58	52	48	53	48	44	47	44	41	38	38	38
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	43	39	35	33	33	33
6	67	54	46	40	63	52	44	39	47	41	36	43	38	34	39	35	31	29	29	29
7	62	49	41	35	59	47	40	34	43	37	32	39	34	30	36	31	28	26	26	26
8	58	45	37	31	54	43	36	31	39	33	29	36	31	27	33	28	25	23	23	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21	21	21
10	50	38	30	25	48	36	29	25	33	27	23	31	25	22	28	24	21	19	19	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11793	11793	11793	11793
5°	11802	13378	11812	10149
10°	11730	15249	11710	8712
15°	11644	16534	11572	7872
20°	11497	18118	11391	7186
25°	11367	20759	11159	6780
30°	11179	21901	10985	6412
35°	10882	17556	10653	6117
40°	10419	12134	10265	5806
45°	9834	9034	9724	5546
50°	9165	7437	9014	5338
55°	8443	6343	8376	5158
60°	7734	5429	7600	5018
65°	6970	4689	6858	4814
70°	6163	3893	6081	4460
75°	5307	3011	5237	3871
80°	4191	2036	4039	2846
85°	2682	1019	2590	1450

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18013 cd/sqm

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.2	2.4
10°-20°	527.7	7.2
20°-30°	857.1	11.7
30°-40°	1047.5	14.3
40°-50°	950.2	13.0
50°-60°	756.8	10.3
60°-70°	527.1	7.2
70°-80°	280.8	3.8
80°-90°	70.8	1.0
90°-100°	206.3	2.8
100°-110°	444.8	6.1
110°-120°	414.7	5.7
120°-130°	335.9	4.6
130°-140°	269.7	3.7
140°-150°	203.4	2.8
150°-160°	143.2	2.0
160°-170°	84.4	1.2
170°-180°	27.5	0.4
0°-30°	1561.9	21.3
0°-40°	2609.4	35.6
0°-60°	4316.4	58.9
0°-90°	5195.1	70.9
90°-120°	1065.8	14.5
90°-150°	1874.8	25.6
90°-180°	2130.0	29.1
0°-180°	7325.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1841	1841	1841	1841	1841	
5°	1839	2123	1841	1611	1839	175
15°	1767	2652	1756	1262	1767	499
25°	1627	3262	1597	1066	1627	749
35°	1416	2619	1386	912	1416	884
45°	1112	1234	1100	758	1112	857
55°	783	761	777	619	783	700
65°	484	467	477	480	484	481
75°	234	230	231	295	234	249
85°	47	52	45	73	47	56
90°	1	13	1	13	1	5
95°	19	134	19	134	19	20
105°	65	758	65	758	65	68
115°	116	844	116	844	116	114
125°	160	665	160	665	160	142
135°	188	552	188	552	188	146
145°	218	436	218	436	218	137
155°	249	365	249	365	249	115
165°	272	320	272	320	272	77
175°	283	288	283	288	283	27
180°	284	284	284	284	284	

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1843.8	1854.7	1867.2	1876.6	1892.2	1896.9	1904.7	1909.4	1914.1	1918.8	1921.9
5°	1839.1	1865.6	1889.1	1906.3	1935.9	1946.9	1960.9	1978.1	1998.4	2015.6	2026.6
7.5°	1826.6	1868.8	1900.0	1934.4	1975.0	2001.6	2015.6	2051.6	2084.4	2109.4	2142.2
10°	1810.9	1860.9	1909.4	1960.9	2018.8	2048.4	2076.6	2126.6	2171.9	2212.5	2245.3
12.5°	1793.8	1854.7	1912.5	1979.7	2057.8	2093.8	2112.5	2198.4	2254.7	2276.6	2340.6
15°	1767.2	1839.1	1921.9	2004.7	2070.3	2112.5	2164.1	2232.8	2289.1	2337.5	2389.1
17.5°	1742.2	1820.3	1904.7	1996.9	2092.2	2146.9	2185.9	2246.9	2307.8	2370.3	2418.8
20°	1701.6	1803.1	1889.1	1987.5	2100.0	2139.1	2179.7	2251.6	2317.2	2384.4	2445.3
22.5°	1668.8	1765.6	1882.8	1976.6	2071.9	2110.9	2160.9	2235.9	2314.1	2390.6	2479.7
25°	1626.6	1734.4	1835.9	1935.9	2034.4	2076.6	2121.9	2218.8	2300.0	2398.4	2496.9
27.5°	1581.3	1692.2	1793.8	1884.4	1976.6	2034.4	2082.8	2184.4	2292.2	2400.0	2528.1
30°	1532.8	1637.5	1734.4	1823.4	1925.0	1984.4	2032.8	2151.6	2271.9	2409.4	2562.5
32.5°	1481.3	1579.7	1662.5	1753.1	1860.9	1915.6	1981.3	2110.9	2253.1	2417.2	2609.4
35°	1415.6	1509.4	1582.8	1675.0	1782.8	1853.1	1921.9	2067.2	2232.8	2415.6	2635.9
37.5°	1350.0	1423.4	1493.8	1592.2	1717.2	1781.3	1853.1	2012.5	2201.6	2410.9	2646.9
40°	1271.9	1343.8	1404.7	1504.7	1635.9	1709.4	1784.4	1951.6	2165.6	2393.8	2607.8
42.5°	1193.8	1254.7	1321.9	1426.6	1553.1	1631.3	1710.9	1896.9	2118.8	2343.8	2500.0
45°	1112.5	1159.4	1232.8	1328.1	1462.5	1537.5	1628.1	1829.7	2053.1	2253.1	2331.3
47.5°	1028.1	1075.0	1143.8	1235.9	1368.8	1457.8	1543.8	1745.3	1970.3	2125.0	2125.0
50°	946.9	984.4	1051.6	1143.8	1278.1	1359.4	1446.9	1660.9	1842.2	1956.3	1854.7
52.5°	859.4	901.6	957.8	1054.7	1187.5	1260.9	1356.3	1539.1	1710.9	1757.8	1601.6
55°	782.8	817.2	870.3	962.5	1085.9	1162.5	1243.8	1418.8	1564.1	1560.9	1393.8
57.5°	703.1	731.3	787.5	871.9	985.9	1054.7	1135.9	1287.5	1406.3	1364.1	1206.3
60°	629.7	650.0	704.7	773.4	882.8	946.9	1025.0	1148.4	1239.1	1179.7	1020.3
62.5°	553.1	576.6	620.3	687.5	784.4	835.9	893.8	1018.8	1076.6	1023.4	860.9
65°	484.4	503.1	542.2	598.4	685.9	732.8	782.8	885.9	940.6	864.1	729.7
67.5°	415.6	437.5	465.6	515.6	584.4	628.1	671.9	760.9	785.9	717.2	604.7
70°	351.6	370.3	396.9	432.8	490.6	529.7	562.5	635.9	653.1	589.1	500.0
72.5°	289.1	301.6	323.4	353.1	406.3	428.1	462.5	512.5	534.4	476.6	412.5
75°	234.4	243.8	257.8	279.7	315.6	339.1	367.2	414.1	412.5	371.9	326.6
77.5°	181.3	182.8	198.4	218.8	240.6	260.9	275.0	307.8	310.9	285.9	248.4
80°	129.7	134.4	140.6	156.3	175.0	182.8	200.0	220.3	223.4	204.7	179.7
82.5°	82.8	85.9	90.6	100.0	112.5	121.9	131.3	139.1	146.9	135.9	115.6
85°	46.9	48.4	53.1	56.3	62.5	67.2	75.0	82.8	81.3	73.4	67.2
87.5°	23.4	23.4	23.4	26.6	29.7	29.7	32.8	34.4	35.9	32.8	29.7
90°	0.6	1.1	2.3	3.4	4.6	5.2	5.7	6.3	7.4	8.0	9.1
92.5°	8.6	10.3	16.0	24.6	36.6	46.9	57.2	96.0	161.2	232.1	228.1
95°	18.9	19.4	24.0	30.3	42.9	55.8	68.6	129.8	255.6	413.3	506.5
97.5°	29.2	29.7	33.2	39.4	50.9	60.3	69.7	112.1	208.7	379.0	547.1
100°	40.0	41.2	43.4	49.7	60.6	69.2	77.8	110.9	185.2	329.3	516.3
102.5°	52.0	52.6	54.3	61.2	70.9	79.2	87.5	116.1	175.5	291.6	461.9
105°	64.6	64.6	67.5	73.2	82.3	90.3	98.3	123.5	174.4	269.8	414.5
107.5°	76.6	77.8	80.6	85.2	94.9	102.1	109.2	133.8	178.4	258.4	379.0
110°	89.8	90.9	93.2	98.3	106.9	114.4	121.8	145.2	184.7	253.8	355.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	102.9	104.1	105.8	110.9	119.5	126.6	133.8	156.1	192.7	253.8	341.9
115°	115.5	116.6	118.3	123.5	132.1	139.2	146.4	167.5	200.7	255.6	332.7
117.5°	126.9	128.6	130.3	135.5	145.2	152.0	158.9	178.9	209.8	258.4	327.6
120°	138.4	140.1	142.4	147.5	157.2	164.4	171.5	191.5	219.0	263.0	324.2
122.5°	150.4	151.5	153.2	158.4	169.2	176.4	183.5	203.5	229.3	267.0	321.3
125°	160.1	161.2	164.1	169.2	180.1	187.6	195.0	213.8	238.4	271.6	319.0
127.5°	168.1	169.8	173.2	179.5	191.0	198.4	205.8	224.1	247.0	276.7	317.9
130°	175.5	177.2	181.8	189.2	201.2	208.6	216.1	233.8	255.6	281.3	316.7
132.5°	181.2	183.5	189.2	197.8	210.4	217.8	225.3	243.0	263.0	286.4	316.7
135°	187.5	189.8	196.7	205.8	217.8	225.6	233.3	251.0	269.8	291.0	316.7
137.5°	195.5	197.2	203.5	212.7	224.7	232.7	240.7	256.7	275.0	295.6	317.3
140°	202.4	204.1	211.0	220.1	231.0	238.7	246.4	263.0	280.1	298.4	317.9
142.5°	210.4	211.5	217.8	227.0	237.3	244.4	251.6	267.0	283.0	300.1	318.4
145°	218.4	219.5	225.3	233.3	243.5	250.1	256.7	271.6	285.9	301.3	317.9
147.5°	227.0	227.5	232.7	240.1	249.3	255.3	261.3	274.4	287.6	301.9	316.7
150°	234.4	235.5	239.5	247.0	255.0	259.8	264.7	277.3	289.3	301.9	315.0
152.5°	242.4	243.0	246.4	252.7	260.1	264.4	268.7	280.1	290.4	301.3	312.7
155°	249.3	249.3	252.7	258.4	264.1	268.1	272.1	281.9	291.0	300.1	309.9
157.5°	255.6	255.6	258.4	263.6	268.7	271.8	275.0	283.6	291.6	299.0	307.0
160°	261.8	261.3	263.6	267.6	272.1	274.7	277.3	284.7	291.6	297.3	304.1
162.5°	267.0	266.4	268.7	272.1	275.6	277.6	279.6	285.9	291.0	295.6	300.7
165°	272.1	271.0	272.7	275.6	277.9	279.6	281.3	285.9	290.4	293.9	297.3
167.5°	275.6	275.0	276.1	277.9	279.6	280.8	281.9	285.9	289.3	291.0	293.9
170°	279.0	278.4	279.0	280.1	281.3	282.2	283.0	285.9	288.1	289.3	291.0
172.5°	281.3	280.1	280.7	281.9	282.4	282.7	283.0	285.3	287.0	287.0	287.6
175°	283.0	281.9	282.4	283.0	283.0	283.0	283.0	284.7	285.9	285.3	285.3
177.5°	284.1	283.0	283.0	283.6	283.0	283.0	283.0	284.1	284.7	283.6	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1925.0	1935.9	1945.3	1953.1	1959.4	1968.8	1962.5	1964.1	1967.2	1973.4	1973.4
5°	2050.0	2067.2	2076.6	2107.8	2115.6	2114.1	2109.4	2134.4	2132.8	2123.4	2121.9
7.5°	2171.9	2201.6	2228.1	2253.1	2260.9	2281.3	2285.9	2296.9	2293.8	2309.4	2301.6
10°	2282.8	2329.7	2354.7	2392.2	2401.6	2410.9	2423.4	2429.7	2443.8	2442.2	2442.2
12.5°	2368.8	2425.0	2457.8	2467.2	2503.1	2514.1	2525.0	2545.3	2540.6	2542.2	2551.6
15°	2435.9	2490.6	2518.8	2562.5	2587.5	2600.0	2618.8	2640.6	2637.5	2651.6	2648.4
17.5°	2485.9	2537.5	2589.1	2654.7	2656.3	2689.1	2732.8	2742.2	2762.5	2748.4	2748.4
20°	2526.6	2595.3	2668.8	2753.1	2762.5	2782.8	2835.9	2871.9	2895.3	2887.5	2892.2
22.5°	2570.3	2668.8	2754.7	2839.1	2884.4	2920.3	2971.9	3028.1	3048.5	3061.0	3057.8
25°	2626.6	2729.7	2856.3	2973.5	3020.3	3089.1	3157.8	3212.5	3228.1	3262.5	3231.3
27.5°	2684.4	2829.7	2987.5	3125.0	3184.4	3240.6	3323.5	3364.1	3384.4	3400.0	3389.1
30°	2732.8	2932.8	3104.7	3231.3	3273.5	3306.3	3353.1	3362.5	3354.7	3367.2	3382.8
32.5°	2807.8	3003.1	3148.5	3209.4	3204.7	3203.1	3167.2	3117.2	3106.3	3076.6	3117.2
35°	2848.4	3004.7	3061.0	2979.7	2946.9	2887.5	2773.4	2698.4	2632.8	2618.8	2621.9
37.5°	2825.0	2886.0	2818.8	2604.7	2551.6	2460.9	2309.4	2203.1	2154.7	2117.2	2165.6
40°	2698.4	2631.3	2446.9	2185.9	2109.4	2023.4	1881.3	1823.4	1754.7	1740.6	1804.7
42.5°	2489.1	2284.4	2023.4	1821.9	1742.2	1693.8	1575.0	1520.3	1471.9	1450.0	1485.9
45°	2204.7	1956.3	1693.8	1528.1	1460.9	1403.1	1332.8	1275.0	1243.8	1234.4	1264.1
47.5°	1910.9	1648.4	1439.1	1315.6	1245.3	1201.6	1135.9	1103.1	1078.1	1081.3	1085.9
50°	1629.7	1390.6	1229.7	1106.3	1071.9	1037.5	993.8	965.6	953.1	957.8	954.7
52.5°	1387.5	1193.8	1057.8	962.5	946.9	914.1	878.1	854.7	850.0	851.6	856.3
55°	1175.0	1023.4	915.6	846.9	829.7	806.3	784.4	768.8	756.3	760.9	759.4
57.5°	1014.1	881.3	798.4	742.2	729.7	715.6	695.3	687.5	682.8	673.4	681.3
60°	871.9	764.1	692.2	657.8	646.9	637.5	615.6	606.3	603.1	598.4	610.9
62.5°	737.5	660.9	606.3	575.0	564.1	554.7	543.8	535.9	537.5	531.3	537.5
65°	631.3	568.8	529.7	501.6	487.5	481.3	479.7	467.2	465.6	467.2	468.8
67.5°	532.8	479.7	450.0	432.8	421.9	415.6	410.9	403.1	409.4	404.7	407.8
70°	443.8	407.8	376.6	359.4	354.7	356.3	348.4	345.3	346.9	343.8	346.9
72.5°	357.8	328.1	315.6	303.1	296.9	295.3	290.6	285.9	290.6	289.1	289.1
75°	285.9	264.1	250.0	242.2	242.2	239.1	231.3	231.3	231.3	229.7	231.3
77.5°	220.3	201.6	195.3	187.5	187.5	182.8	181.3	181.3	178.1	182.8	179.7
80°	164.1	150.0	140.6	135.9	135.9	134.4	131.3	129.7	131.3	129.7	129.7
82.5°	106.3	100.0	95.3	90.6	89.1	90.6	89.1	85.9	87.5	85.9	89.1
85°	60.9	54.7	54.7	51.6	53.1	50.0	51.6	48.4	46.9	51.6	48.4
87.5°	26.6	25.0	25.0	21.9	21.9	21.9	20.3	21.9	20.3	18.8	20.3
90°	9.7	10.3	10.9	11.4	12.0	12.6	12.6	12.6	13.1	13.1	13.1
92.5°	184.1	124.1	89.2	66.3	60.9	55.5	46.3	44.6	43.4	42.3	43.4
95°	495.7	411.1	324.2	253.8	229.8	205.8	165.2	148.1	143.5	134.4	143.5
97.5°	619.2	589.4	520.3	449.4	415.1	380.8	346.5	316.7	301.3	294.4	301.3
100°	659.2	703.2	675.2	616.3	586.6	556.8	517.4	476.2	455.1	445.9	455.1
102.5°	635.2	741.5	770.1	749.5	731.8	714.1	671.2	644.9	621.4	615.2	621.4
105°	578.6	715.8	794.1	819.3	816.2	813.0	794.7	775.8	764.4	757.5	764.4
107.5°	524.8	663.2	766.7	827.3	839.8	852.4	857.6	854.7	849.0	843.3	849.0
110°	480.2	603.7	712.3	793.0	817.3	841.6	867.3	878.1	882.1	882.1	882.1

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	447.1	556.8	658.6	740.4	770.1	799.8	840.4	861.0	872.4	877.6	872.4
115°	424.8	519.1	607.7	686.1	717.2	748.4	793.0	820.4	836.4	843.8	836.4
117.5°	409.9	492.8	571.1	639.7	669.2	698.6	743.8	772.4	788.4	793.0	788.4
120°	397.9	472.2	540.8	603.7	628.8	654.0	696.3	723.8	739.2	743.8	739.2
122.5°	387.6	456.8	519.1	573.4	596.6	619.7	656.3	680.9	696.3	700.3	696.3
125°	378.5	441.9	500.2	550.0	570.6	591.1	623.2	646.6	659.2	664.9	659.2
127.5°	369.9	426.5	482.0	528.8	548.2	567.7	596.9	618.0	630.0	632.3	630.0
130°	361.3	412.2	462.5	507.1	525.7	544.3	572.9	591.7	603.2	606.6	603.2
132.5°	354.5	397.9	444.2	483.7	501.4	519.1	547.7	566.6	576.9	580.9	576.9
135°	349.3	385.9	425.4	461.9	478.2	494.5	519.7	538.6	548.8	552.3	548.8
137.5°	344.2	375.0	408.2	439.6	453.9	468.2	491.1	508.8	518.5	522.5	518.5
140°	340.7	366.5	393.3	419.6	431.6	443.6	464.8	479.7	488.2	491.1	488.2
142.5°	337.9	359.0	380.8	402.5	412.5	422.5	439.6	451.7	459.7	461.9	459.7
145°	335.0	352.7	370.5	388.2	395.9	403.6	417.3	427.1	433.4	435.6	433.4
147.5°	332.2	346.5	361.3	375.6	381.6	387.6	399.1	407.1	411.1	412.2	411.1
150°	328.7	341.3	353.9	364.8	369.9	375.0	383.6	390.5	392.8	393.3	392.8
152.5°	324.7	335.6	346.5	356.2	359.9	363.6	370.5	375.6	377.9	378.5	377.9
155°	320.2	329.9	339.0	347.0	350.2	353.3	359.0	363.0	364.8	365.3	364.8
157.5°	316.2	324.2	332.2	338.5	341.0	343.6	348.2	351.6	353.3	353.3	353.3
160°	311.0	318.4	324.2	329.9	331.9	333.9	337.9	340.7	341.9	341.3	341.9
162.5°	306.4	312.2	317.3	321.9	323.6	325.3	328.2	330.4	330.4	330.4	330.4
165°	301.9	306.4	310.4	313.9	315.3	316.7	319.0	320.2	320.2	320.2	320.2
167.5°	297.3	300.7	303.6	306.4	307.5	308.7	309.9	311.0	310.4	310.4	310.4
170°	293.3	296.1	297.9	299.6	300.2	300.7	301.9	302.4	302.4	301.9	302.4
172.5°	289.3	291.0	292.7	293.9	294.2	294.4	294.4	295.6	294.4	293.9	294.4
175°	285.9	287.6	287.6	288.7	288.7	288.7	288.7	289.3	288.1	287.6	288.1
177.5°	284.1	284.7	285.3	285.3	285.3	285.3	284.7	285.3	283.6	283.6	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1970.3	1959.4	1962.5	1959.4	1951.6	1946.9	1934.4	1918.8	1912.5	1904.7	1900.0
5°	2128.1	2120.3	2118.8	2106.3	2103.1	2084.4	2053.1	2037.5	2018.8	2000.0	1981.3
7.5°	2300.0	2290.6	2259.4	2254.7	2257.8	2234.4	2193.8	2162.5	2123.4	2096.9	2060.9
10°	2442.2	2423.4	2396.9	2398.4	2387.5	2356.3	2315.6	2282.8	2226.6	2192.2	2140.6
12.5°	2528.1	2512.5	2509.4	2493.8	2484.4	2443.8	2395.3	2353.1	2310.9	2264.1	2225.0
15°	2632.8	2612.5	2598.4	2576.6	2570.3	2528.1	2475.0	2426.6	2378.1	2334.4	2251.6
17.5°	2748.4	2726.6	2673.4	2668.8	2631.3	2590.6	2539.1	2467.2	2415.6	2353.1	2292.2
20°	2879.7	2848.4	2779.7	2762.5	2732.8	2665.6	2595.3	2515.6	2432.8	2368.8	2296.9
22.5°	3026.6	2971.9	2921.9	2867.2	2845.3	2762.5	2665.6	2568.8	2468.8	2381.3	2295.3
25°	3217.2	3145.3	3075.0	3020.3	2982.8	2875.0	2745.3	2617.2	2501.6	2387.5	2275.0
27.5°	3367.2	3304.7	3228.1	3156.3	3107.8	2979.7	2831.3	2665.6	2521.9	2382.8	2262.5
30°	3378.1	3359.4	3312.5	3273.5	3220.3	3082.8	2918.8	2731.3	2553.1	2384.4	2237.5
32.5°	3173.5	3211.0	3231.3	3237.5	3226.6	3146.9	2996.9	2790.6	2581.3	2370.3	2215.6
35°	2732.8	2832.8	2956.3	3003.1	3048.5	3090.6	3012.5	2832.8	2590.6	2367.2	2181.3
37.5°	2250.0	2340.6	2545.3	2639.1	2692.2	2859.4	2923.5	2826.6	2609.4	2370.3	2148.4
40°	1815.6	1959.4	2106.3	2232.8	2315.6	2503.1	2701.6	2723.4	2582.8	2340.6	2106.3
42.5°	1528.1	1612.5	1723.4	1840.6	1914.1	2135.9	2404.7	2562.5	2500.0	2292.2	2054.7
45°	1301.6	1364.1	1468.8	1507.8	1601.6	1814.1	2098.4	2326.6	2357.8	2215.6	1995.3
47.5°	1117.2	1170.3	1237.5	1285.9	1360.9	1520.3	1760.9	2012.5	2162.5	2110.9	1912.5
50°	984.4	1028.1	1084.4	1112.5	1160.9	1304.7	1485.9	1735.9	1937.5	1954.7	1804.7
52.5°	873.4	898.4	942.2	973.4	1012.5	1100.0	1264.1	1470.3	1696.9	1790.6	1671.9
55°	776.6	796.9	835.9	856.3	876.6	951.6	1079.7	1267.2	1479.7	1603.1	1535.9
57.5°	689.1	706.3	739.1	757.8	768.8	840.6	939.1	1085.9	1276.6	1426.6	1389.1
60°	617.2	632.8	651.6	665.6	678.1	737.5	806.3	925.0	1095.3	1240.6	1231.3
62.5°	540.6	554.7	575.0	589.1	600.0	637.5	695.3	785.9	931.3	1065.6	1092.2
65°	473.4	484.4	498.4	504.7	518.8	546.9	593.8	675.0	793.8	914.1	932.8
67.5°	412.5	415.6	425.0	439.1	442.2	467.2	509.4	570.3	662.5	760.9	790.6
70°	346.9	351.6	359.4	370.3	376.6	392.2	428.1	468.8	548.4	634.4	656.3
72.5°	289.1	295.3	298.4	304.7	307.8	332.8	348.4	389.1	443.8	515.6	539.1
75°	234.4	240.6	242.2	245.3	248.4	259.4	281.3	306.3	351.6	398.4	429.7
77.5°	185.9	184.4	187.5	192.2	190.6	200.0	214.1	235.9	265.6	304.7	325.0
80°	131.3	131.3	135.9	140.6	139.1	148.4	153.1	168.8	193.8	218.8	226.6
82.5°	87.5	87.5	92.2	92.2	95.3	96.9	103.1	110.9	131.3	143.8	148.4
85°	50.0	50.0	51.6	51.6	51.6	54.7	59.4	62.5	68.8	76.6	79.7
87.5°	20.3	21.9	21.9	21.9	21.9	25.0	25.0	28.1	29.7	32.8	32.8
90°	12.6	12.6	12.6	12.0	11.4	10.9	10.3	9.7	9.1	8.0	7.4
92.5°	44.6	46.3	55.5	60.9	66.3	89.2	124.1	184.1	228.1	232.1	161.2
95°	148.1	165.2	205.8	229.8	253.8	324.2	411.1	495.7	506.5	413.3	255.6
97.5°	316.7	346.5	380.8	415.1	449.4	520.3	589.4	619.2	547.1	379.0	208.7
100°	476.2	517.4	556.8	586.6	616.3	675.2	703.2	659.2	516.3	329.3	185.2
102.5°	644.9	671.2	714.1	731.8	749.5	770.1	741.5	635.2	461.9	291.6	175.5
105°	775.8	794.7	813.0	816.2	819.3	794.1	715.8	578.6	414.5	269.8	174.4
107.5°	854.7	857.6	852.4	839.8	827.3	766.7	663.2	524.8	379.0	258.4	178.4
110°	878.1	867.3	841.6	817.3	793.0	712.3	603.7	480.2	355.6	253.8	184.7

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	861.0	840.4	799.8	770.1	740.4	658.6	556.8	447.1	341.9	253.8	192.7
115°	820.4	793.0	748.4	717.2	686.1	607.7	519.1	424.8	332.7	255.6	200.7
117.5°	772.4	743.8	698.6	669.2	639.7	571.1	492.8	409.9	327.6	258.4	209.8
120°	723.8	696.3	654.0	628.8	603.7	540.8	472.2	397.9	324.2	263.0	219.0
122.5°	680.9	656.3	619.7	596.6	573.4	519.1	456.8	387.6	321.3	267.0	229.3
125°	646.6	623.2	591.1	570.6	550.0	500.2	441.9	378.5	319.0	271.6	238.4
127.5°	618.0	596.9	567.7	548.2	528.8	482.0	426.5	369.9	317.9	276.7	247.0
130°	591.7	572.9	544.3	525.7	507.1	462.5	412.2	361.3	316.7	281.3	255.6
132.5°	566.6	547.7	519.1	501.4	483.7	444.2	397.9	354.5	316.7	286.4	263.0
135°	538.6	519.7	494.5	478.2	461.9	425.4	385.9	349.3	316.7	291.0	269.8
137.5°	508.8	491.1	468.2	453.9	439.6	408.2	375.0	344.2	317.3	295.6	275.0
140°	479.7	464.8	443.6	431.6	419.6	393.3	366.5	340.7	317.9	298.4	280.1
142.5°	451.7	439.6	422.5	412.5	402.5	380.8	359.0	337.9	318.4	300.1	283.0
145°	427.1	417.3	403.6	395.9	388.2	370.5	352.7	335.0	317.9	301.3	285.9
147.5°	407.1	399.1	387.6	381.6	375.6	361.3	346.5	332.2	316.7	301.9	287.6
150°	390.5	383.6	375.0	369.9	364.8	353.9	341.3	328.7	315.0	301.9	289.3
152.5°	375.6	370.5	363.6	359.9	356.2	346.5	335.6	324.7	312.7	301.3	290.4
155°	363.0	359.0	353.3	350.2	347.0	339.0	329.9	320.2	309.9	300.1	291.0
157.5°	351.6	348.2	343.6	341.0	338.5	332.2	324.2	316.2	307.0	299.0	291.6
160°	340.7	337.9	333.9	331.9	329.9	324.2	318.4	311.0	304.1	297.3	291.6
162.5°	330.4	328.2	325.3	323.6	321.9	317.3	312.2	306.4	300.7	295.6	291.0
165°	320.2	319.0	316.7	315.3	313.9	310.4	306.4	301.9	297.3	293.9	290.4
167.5°	311.0	309.9	308.7	307.5	306.4	303.6	300.7	297.3	293.9	291.0	289.3
170°	302.4	301.9	300.7	300.2	299.6	297.9	296.1	293.3	291.0	289.3	288.1
172.5°	295.6	294.4	294.4	294.2	293.9	292.7	291.0	289.3	287.6	287.0	287.0
175°	289.3	288.7	288.7	288.7	288.7	287.6	287.6	285.9	285.3	285.3	285.9
177.5°	285.3	284.7	285.3	285.3	285.3	285.3	284.7	284.1	283.6	283.6	284.7
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1893.8	1885.9	1876.6	1876.6	1865.6	1860.9	1851.6	1848.4	1840.6	1828.1	1818.8
5°	1960.9	1940.6	1928.1	1917.2	1893.8	1876.6	1859.4	1840.6	1821.9	1800.0	1775.0
7.5°	2026.6	1989.1	1971.9	1953.1	1918.8	1882.8	1848.4	1823.4	1798.4	1764.1	1732.8
10°	2095.3	2048.4	2017.2	1992.2	1939.1	1893.8	1843.8	1807.8	1768.8	1725.0	1684.4
12.5°	2153.1	2092.2	2065.6	2018.8	1957.8	1903.1	1840.6	1785.9	1734.4	1682.8	1632.8
15°	2201.6	2143.8	2078.1	2059.4	1975.0	1896.9	1826.6	1756.3	1692.2	1640.6	1582.8
17.5°	2217.2	2143.8	2110.9	2065.6	1965.6	1884.4	1795.3	1718.8	1657.8	1581.3	1535.9
20°	2221.9	2151.6	2106.3	2064.1	1975.0	1867.2	1779.7	1685.9	1612.5	1535.9	1464.1
22.5°	2209.4	2126.6	2082.8	2042.2	1942.2	1850.0	1748.4	1645.3	1559.4	1489.1	1417.2
25°	2185.9	2089.1	2046.9	2003.1	1907.8	1806.3	1695.3	1596.9	1517.2	1432.8	1362.5
27.5°	2154.7	2043.8	1995.3	1950.0	1856.3	1760.9	1656.3	1554.7	1465.6	1376.6	1310.9
30°	2115.6	1987.5	1943.8	1884.4	1793.8	1703.1	1607.8	1506.3	1406.3	1321.9	1250.0
32.5°	2065.6	1931.3	1873.4	1817.2	1718.8	1635.9	1545.3	1450.0	1353.1	1270.3	1195.3
35°	2020.3	1867.2	1803.1	1746.9	1637.5	1550.0	1475.0	1385.9	1300.0	1214.1	1146.9
37.5°	1959.4	1803.1	1726.6	1668.8	1557.8	1468.8	1398.4	1329.7	1239.1	1156.3	1093.8
40°	1895.3	1723.4	1651.6	1593.8	1478.1	1381.3	1314.1	1253.1	1179.7	1103.1	1037.5
42.5°	1837.5	1646.9	1570.3	1500.0	1382.8	1296.9	1228.1	1181.3	1114.1	1045.3	985.9
45°	1764.1	1565.6	1482.8	1409.4	1296.9	1203.1	1137.5	1100.0	1050.0	982.8	931.3
47.5°	1689.1	1478.1	1392.2	1320.3	1198.4	1115.6	1051.6	1015.6	981.3	928.1	876.6
50°	1590.6	1385.9	1307.8	1225.0	1104.7	1020.3	967.2	931.3	904.7	867.2	823.4
52.5°	1482.8	1290.6	1206.3	1134.4	1015.6	939.1	878.1	857.8	831.3	803.1	765.6
55°	1368.8	1187.5	1106.3	1035.9	926.6	848.4	798.4	776.6	756.3	734.4	709.4
57.5°	1254.7	1079.7	1003.1	940.6	839.1	764.1	723.4	693.8	679.7	667.2	646.9
60°	1112.5	964.1	904.7	848.4	748.4	679.7	640.6	618.8	606.3	600.0	590.6
62.5°	987.5	865.6	800.0	745.3	665.6	604.7	567.2	550.0	539.1	535.9	525.0
65°	854.7	750.0	698.4	651.6	582.8	528.1	496.9	476.6	468.8	467.2	467.2
67.5°	729.7	645.3	593.8	560.9	501.6	453.1	423.4	415.6	410.9	404.7	403.1
70°	612.5	545.3	500.0	471.9	418.8	382.8	359.4	346.9	346.9	342.2	339.1
72.5°	509.4	442.2	412.5	389.1	345.3	314.1	296.9	293.8	282.8	281.3	281.3
75°	398.4	348.4	328.1	307.8	275.0	253.1	239.1	231.3	225.0	225.0	226.6
77.5°	300.0	265.6	246.9	231.3	207.8	193.8	182.8	179.7	173.4	173.4	173.4
80°	212.5	193.8	179.7	167.2	150.0	137.5	131.3	125.0	125.0	123.4	125.0
82.5°	137.5	121.9	114.1	112.5	96.9	92.2	84.4	85.9	81.3	79.7	82.8
85°	79.7	71.9	62.5	59.4	53.1	46.9	43.8	45.3	43.8	42.2	43.8
87.5°	31.3	26.6	25.0	25.0	20.3	18.8	17.2	18.8	15.6	15.6	17.2
90°	6.3	5.7	5.2	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	96.0	57.2	46.9	36.6	24.6	16.0	10.3	8.6	10.3	16.0	24.6
95°	129.8	68.6	55.8	42.9	30.3	24.0	19.4	18.9	19.4	24.0	30.3
97.5°	112.1	69.7	60.3	50.9	39.4	33.2	29.7	29.2	29.7	33.2	39.4
100°	110.9	77.8	69.2	60.6	49.7	43.4	41.2	40.0	41.2	43.4	49.7
102.5°	116.1	87.5	79.2	70.9	61.2	54.3	52.6	52.0	52.6	54.3	61.2
105°	123.5	98.3	90.3	82.3	73.2	67.5	64.6	64.6	64.6	67.5	73.2
107.5°	133.8	109.2	102.1	94.9	85.2	80.6	77.8	76.6	77.8	80.6	85.2
110°	145.2	121.8	114.4	106.9	98.3	93.2	90.9	89.8	90.9	93.2	98.3



TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	156.1	133.8	126.6	119.5	110.9	105.8	104.1	102.9	104.1	105.8	110.9
115°	167.5	146.4	139.2	132.1	123.5	118.3	116.6	115.5	116.6	118.3	123.5
117.5°	178.9	158.9	152.0	145.2	135.5	130.3	128.6	126.9	128.6	130.3	135.5
120°	191.5	171.5	164.4	157.2	147.5	142.4	140.1	138.4	140.1	142.4	147.5
122.5°	203.5	183.5	176.4	169.2	158.4	153.2	151.5	150.4	151.5	153.2	158.4
125°	213.8	195.0	187.6	180.1	169.2	164.1	161.2	160.1	161.2	164.1	169.2
127.5°	224.1	205.8	198.4	191.0	179.5	173.2	169.8	168.1	169.8	173.2	179.5
130°	233.8	216.1	208.6	201.2	189.2	181.8	177.2	175.5	177.2	181.8	189.2
132.5°	243.0	225.3	217.8	210.4	197.8	189.2	183.5	181.2	183.5	189.2	197.8
135°	251.0	233.3	225.6	217.8	205.8	196.7	189.8	187.5	189.8	196.7	205.8
137.5°	256.7	240.7	232.7	224.7	212.7	203.5	197.2	195.5	197.2	203.5	212.7
140°	263.0	246.4	238.7	231.0	220.1	211.0	204.1	202.4	204.1	211.0	220.1
142.5°	267.0	251.6	244.4	237.3	227.0	217.8	211.5	210.4	211.5	217.8	227.0
145°	271.6	256.7	250.1	243.5	233.3	225.3	219.5	218.4	219.5	225.3	233.3
147.5°	274.4	261.3	255.3	249.3	240.1	232.7	227.5	227.0	227.5	232.7	240.1
150°	277.3	264.7	259.8	255.0	247.0	239.5	235.5	234.4	235.5	239.5	247.0
152.5°	280.1	268.7	264.4	260.1	252.7	246.4	243.0	242.4	243.0	246.4	252.7
155°	281.9	272.1	268.1	264.1	258.4	252.7	249.3	249.3	249.3	252.7	258.4
157.5°	283.6	275.0	271.8	268.7	263.6	258.4	255.6	255.6	255.6	258.4	263.6
160°	284.7	277.3	274.7	272.1	267.6	263.6	261.3	261.8	261.3	263.6	267.6
162.5°	285.9	279.6	277.6	275.6	272.1	268.7	266.4	267.0	266.4	268.7	272.1
165°	285.9	281.3	279.6	277.9	275.6	272.7	271.0	272.1	271.0	272.7	275.6
167.5°	285.9	281.9	280.8	279.6	277.9	276.1	275.0	275.6	275.0	276.1	277.9
170°	285.9	283.0	282.2	281.3	280.1	279.0	278.4	279.0	278.4	279.0	280.1
172.5°	285.3	283.0	282.7	282.4	281.9	280.7	280.1	281.3	280.1	280.7	281.9
175°	284.7	283.0	283.0	283.0	283.0	282.4	281.9	283.0	281.9	282.4	283.0
177.5°	284.1	283.0	283.0	283.0	283.6	283.0	283.0	284.1	283.0	283.0	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1815.6	1812.5	1804.7	1800.0	1784.4	1765.6	1759.4	1743.8	1750.0	1739.1	1739.1
5°	1767.2	1753.1	1743.8	1729.7	1700.0	1679.7	1657.8	1646.9	1640.6	1632.8	1626.6
7.5°	1704.7	1693.8	1684.4	1657.8	1625.0	1596.9	1570.3	1559.4	1539.1	1525.0	1518.8
10°	1650.0	1634.4	1612.5	1581.3	1546.9	1510.9	1487.5	1464.1	1448.4	1440.6	1423.4
12.5°	1593.8	1575.0	1551.6	1506.3	1468.8	1446.9	1404.7	1382.8	1375.0	1368.8	1348.4
15°	1535.9	1515.6	1487.5	1445.3	1412.5	1360.9	1335.9	1318.8	1300.0	1298.4	1282.8
17.5°	1484.4	1459.4	1435.9	1384.4	1343.8	1298.4	1284.4	1265.6	1248.4	1229.7	1221.9
20°	1418.8	1395.3	1378.1	1321.9	1276.6	1248.4	1225.0	1209.4	1198.4	1179.7	1176.6
22.5°	1359.4	1334.4	1310.9	1268.8	1229.7	1193.8	1165.6	1148.4	1143.8	1135.9	1121.9
25°	1301.6	1276.6	1248.4	1209.4	1168.8	1143.8	1118.8	1107.8	1098.4	1085.9	1075.0
27.5°	1253.1	1229.7	1203.1	1154.7	1120.3	1101.6	1075.0	1062.5	1050.0	1043.8	1039.1
30°	1195.3	1168.8	1148.4	1110.9	1073.4	1048.4	1029.7	1018.8	1007.8	1001.6	998.4
32.5°	1139.1	1114.1	1100.0	1059.4	1029.7	1000.0	985.9	978.1	971.9	965.6	959.4
35°	1093.8	1068.8	1046.9	1009.4	979.7	959.4	948.4	935.9	931.3	925.0	925.0
37.5°	1037.5	1018.8	996.9	960.9	934.4	918.8	909.4	893.8	892.2	889.1	884.4
40°	989.1	970.3	950.0	918.8	895.3	876.6	864.1	856.3	851.6	848.4	845.3
42.5°	937.5	917.2	907.8	871.9	851.6	832.8	826.6	818.8	817.2	810.9	803.1
45°	887.5	870.3	851.6	825.0	807.8	792.2	782.8	776.6	768.8	767.2	762.5
47.5°	843.8	823.4	806.3	781.3	762.5	750.0	742.2	734.4	728.1	723.4	718.8
50°	787.5	771.9	757.8	731.3	715.6	703.1	692.2	685.9	679.7	679.7	679.7
52.5°	732.8	718.8	706.3	687.5	668.8	657.8	645.3	640.6	637.5	632.8	637.5
55°	679.7	665.6	653.1	639.1	617.2	607.8	595.3	590.6	592.2	592.2	596.9
57.5°	623.4	612.5	604.7	587.5	567.2	557.8	550.0	545.3	545.3	551.6	553.1
60°	568.8	557.8	543.8	528.1	515.6	504.7	500.0	501.6	501.6	504.7	512.5
62.5°	507.8	501.6	493.8	471.9	464.1	456.3	450.0	454.7	453.1	460.9	471.9
65°	451.6	445.3	434.4	423.4	414.1	406.3	404.7	406.3	409.4	417.2	429.7
67.5°	389.1	389.1	379.7	370.3	362.5	354.7	356.3	357.8	360.9	370.3	389.1
70°	337.5	331.3	321.9	315.6	309.4	306.3	303.1	309.4	318.8	325.0	339.1
72.5°	281.3	276.6	268.8	262.5	260.9	257.8	256.3	259.4	268.8	279.7	295.3
75°	221.9	223.4	218.8	214.1	214.1	209.4	212.5	212.5	221.9	232.8	245.3
77.5°	171.9	170.3	168.8	165.6	164.1	164.1	164.1	167.2	176.6	182.8	195.3
80°	121.9	123.4	118.8	120.3	118.8	120.3	120.3	126.6	131.3	139.1	148.4
82.5°	81.3	81.3	78.1	79.7	79.7	79.7	81.3	84.4	90.6	96.9	103.1
85°	45.3	46.9	43.8	46.9	46.9	46.9	48.4	50.0	54.7	56.3	62.5
87.5°	17.2	20.3	20.3	17.2	18.8	20.3	21.9	20.3	23.4	26.6	28.1
90°	4.6	5.2	5.7	6.3	7.4	8.0	9.1	9.7	10.3	10.9	11.4
92.5°	36.6	46.9	57.2	96.0	161.2	232.1	228.1	184.1	124.1	89.2	66.3
95°	42.9	55.8	68.6	129.8	255.6	413.3	506.5	495.7	411.1	324.2	253.8
97.5°	50.9	60.3	69.7	112.1	208.7	379.0	547.1	619.2	589.4	520.3	449.4
100°	60.6	69.2	77.8	110.9	185.2	329.3	516.3	659.2	703.2	675.2	616.3
102.5°	70.9	79.2	87.5	116.1	175.5	291.6	461.9	635.2	741.5	770.1	749.5
105°	82.3	90.3	98.3	123.5	174.4	269.8	414.5	578.6	715.8	794.1	819.3
107.5°	94.9	102.1	109.2	133.8	178.4	258.4	379.0	524.8	663.2	766.7	827.3
110°	106.9	114.4	121.8	145.2	184.7	253.8	355.6	480.2	603.7	712.3	793.0

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	119.5	126.6	133.8	156.1	192.7	253.8	341.9	447.1	556.8	658.6	740.4
115°	132.1	139.2	146.4	167.5	200.7	255.6	332.7	424.8	519.1	607.7	686.1
117.5°	145.2	152.0	158.9	178.9	209.8	258.4	327.6	409.9	492.8	571.1	639.7
120°	157.2	164.4	171.5	191.5	219.0	263.0	324.2	397.9	472.2	540.8	603.7
122.5°	169.2	176.4	183.5	203.5	229.3	267.0	321.3	387.6	456.8	519.1	573.4
125°	180.1	187.6	195.0	213.8	238.4	271.6	319.0	378.5	441.9	500.2	550.0
127.5°	191.0	198.4	205.8	224.1	247.0	276.7	317.9	369.9	426.5	482.0	528.8
130°	201.2	208.6	216.1	233.8	255.6	281.3	316.7	361.3	412.2	462.5	507.1
132.5°	210.4	217.8	225.3	243.0	263.0	286.4	316.7	354.5	397.9	444.2	483.7
135°	217.8	225.6	233.3	251.0	269.8	291.0	316.7	349.3	385.9	425.4	461.9
137.5°	224.7	232.7	240.7	256.7	275.0	295.6	317.3	344.2	375.0	408.2	439.6
140°	231.0	238.7	246.4	263.0	280.1	298.4	317.9	340.7	366.5	393.3	419.6
142.5°	237.3	244.4	251.6	267.0	283.0	300.1	318.4	337.9	359.0	380.8	402.5
145°	243.5	250.1	256.7	271.6	285.9	301.3	317.9	335.0	352.7	370.5	388.2
147.5°	249.3	255.3	261.3	274.4	287.6	301.9	316.7	332.2	346.5	361.3	375.6
150°	255.0	259.8	264.7	277.3	289.3	301.9	315.0	328.7	341.3	353.9	364.8
152.5°	260.1	264.4	268.7	280.1	290.4	301.3	312.7	324.7	335.6	346.5	356.2
155°	264.1	268.1	272.1	281.9	291.0	300.1	309.9	320.2	329.9	339.0	347.0
157.5°	268.7	271.8	275.0	283.6	291.6	299.0	307.0	316.2	324.2	332.2	338.5
160°	272.1	274.7	277.3	284.7	291.6	297.3	304.1	311.0	318.4	324.2	329.9
162.5°	275.6	277.6	279.6	285.9	291.0	295.6	300.7	306.4	312.2	317.3	321.9
165°	277.9	279.6	281.3	285.9	290.4	293.9	297.3	301.9	306.4	310.4	313.9
167.5°	279.6	280.8	281.9	285.9	289.3	291.0	293.9	297.3	300.7	303.6	306.4
170°	281.3	282.2	283.0	285.9	288.1	289.3	291.0	293.3	296.1	297.9	299.6
172.5°	282.4	282.7	283.0	285.3	287.0	287.0	287.6	289.3	291.0	292.7	293.9
175°	283.0	283.0	283.0	284.7	285.9	285.3	285.3	285.9	287.6	287.6	288.7
177.5°	283.0	283.0	283.0	284.1	284.7	283.6	283.6	284.1	284.7	285.3	285.3
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1745.3	1734.4	1732.8	1735.9	1729.7	1739.1	1735.9	1739.1	1731.3	1739.1	1734.4
5°	1625.0	1621.9	1615.6	1607.8	1609.4	1610.9	1618.8	1610.9	1617.2	1618.8	1626.6
7.5°	1512.5	1506.3	1510.9	1507.8	1493.8	1490.6	1493.8	1498.4	1507.8	1514.1	1518.8
10°	1421.9	1418.8	1412.5	1407.8	1400.0	1395.3	1401.6	1395.3	1407.8	1418.8	1418.8
12.5°	1353.1	1340.6	1332.8	1331.3	1314.1	1317.2	1323.4	1328.1	1342.2	1348.4	1348.4
15°	1281.3	1271.9	1268.8	1262.5	1256.3	1262.5	1259.4	1264.1	1270.3	1276.6	1279.7
17.5°	1218.8	1217.2	1218.8	1203.1	1207.8	1200.0	1201.6	1209.4	1204.7	1209.4	1218.8
20°	1162.5	1165.6	1160.9	1154.7	1154.7	1145.3	1156.3	1153.1	1154.7	1164.1	1178.1
22.5°	1120.3	1118.8	1114.1	1109.4	1103.1	1104.7	1106.3	1103.1	1115.6	1123.4	1125.0
25°	1075.0	1071.9	1070.3	1065.6	1059.4	1065.6	1064.1	1065.6	1068.8	1081.3	1071.9
27.5°	1032.8	1026.6	1029.7	1025.0	1023.4	1025.0	1025.0	1026.6	1029.7	1031.3	1032.8
30°	996.9	990.6	989.1	985.9	984.4	985.9	989.1	985.9	998.4	996.9	996.9
32.5°	957.8	953.1	950.0	950.0	948.4	946.9	948.4	950.0	959.4	953.1	959.4
35°	920.3	917.2	917.2	914.1	912.5	912.5	912.5	918.8	915.6	920.3	920.3
37.5°	884.4	884.4	882.8	879.7	878.1	879.7	878.1	881.3	879.7	881.3	882.8
40°	846.9	843.8	842.2	842.2	837.5	832.8	837.5	837.5	839.1	843.8	845.3
42.5°	801.6	803.1	803.1	796.9	796.9	796.9	798.4	800.0	800.0	803.1	803.1
45°	762.5	759.4	759.4	759.4	756.3	757.8	760.9	760.9	760.9	760.9	757.8
47.5°	718.8	718.8	720.3	720.3	725.0	723.4	723.4	721.9	718.8	718.8	720.3
50°	678.1	682.8	684.4	684.4	685.9	687.5	687.5	684.4	682.8	678.1	678.1
52.5°	639.1	642.2	645.3	650.0	653.1	651.6	651.6	648.4	642.2	640.6	639.1
55°	596.9	601.6	607.8	612.5	617.2	618.8	618.8	612.5	606.3	598.4	598.4
57.5°	557.8	562.5	573.4	578.1	584.4	584.4	581.3	576.6	567.2	560.9	556.3
60°	518.8	526.6	534.4	543.8	551.6	553.1	548.4	542.2	531.3	523.4	517.2
62.5°	476.6	484.4	500.0	509.4	515.6	515.6	515.6	507.8	493.8	482.8	473.4
65°	435.9	443.8	457.8	470.3	475.0	479.7	475.0	467.2	456.3	443.8	434.4
67.5°	393.8	403.1	417.2	426.6	432.8	437.5	434.4	428.1	414.1	396.9	390.6
70°	346.9	351.6	371.9	381.3	390.6	393.8	390.6	381.3	367.2	348.4	342.2
72.5°	303.1	307.8	326.6	334.4	342.2	345.3	340.6	334.4	321.9	304.7	296.9
75°	253.1	260.9	270.3	282.8	292.2	295.3	290.6	285.9	270.3	259.4	253.1
77.5°	200.0	207.8	220.3	231.3	240.6	239.1	232.8	234.4	217.2	204.7	200.0
80°	151.6	157.8	167.2	176.6	181.3	181.3	179.7	173.4	167.2	157.8	150.0
82.5°	104.7	112.5	120.3	126.6	126.6	128.1	125.0	123.4	117.2	109.4	107.8
85°	62.5	64.1	70.3	70.3	76.6	73.4	71.9	76.6	70.3	65.6	64.1
87.5°	28.1	26.6	28.1	28.1	26.6	29.7	29.7	28.1	29.7	28.1	28.1
90°	12.0	12.6	12.6	12.6	13.1	13.1	13.1	12.6	12.6	12.6	12.0
92.5°	60.9	55.5	46.3	44.6	43.4	42.3	43.4	44.6	46.3	55.5	60.9
95°	229.8	205.8	165.2	148.1	143.5	134.4	143.5	148.1	165.2	205.8	229.8
97.5°	415.1	380.8	346.5	316.7	301.3	294.4	301.3	316.7	346.5	380.8	415.1
100°	586.6	556.8	517.4	476.2	455.1	445.9	455.1	476.2	517.4	556.8	586.6
102.5°	731.8	714.1	671.2	644.9	621.4	615.2	621.4	644.9	671.2	714.1	731.8
105°	816.2	813.0	794.7	775.8	764.4	757.5	764.4	775.8	794.7	813.0	816.2
107.5°	839.8	852.4	857.6	854.7	849.0	843.3	849.0	854.7	857.6	852.4	839.8
110°	817.3	841.6	867.3	878.1	882.1	882.1	882.1	878.1	867.3	841.6	817.3

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	770.1	799.8	840.4	861.0	872.4	877.6	872.4	861.0	840.4	799.8	770.1
115°	717.2	748.4	793.0	820.4	836.4	843.8	836.4	820.4	793.0	748.4	717.2
117.5°	669.2	698.6	743.8	772.4	788.4	793.0	788.4	772.4	743.8	698.6	669.2
120°	628.8	654.0	696.3	723.8	739.2	743.8	739.2	723.8	696.3	654.0	628.8
122.5°	596.6	619.7	656.3	680.9	696.3	700.3	696.3	680.9	656.3	619.7	596.6
125°	570.6	591.1	623.2	646.6	659.2	664.9	659.2	646.6	623.2	591.1	570.6
127.5°	548.2	567.7	596.9	618.0	630.0	632.3	630.0	618.0	596.9	567.7	548.2
130°	525.7	544.3	572.9	591.7	603.2	606.6	603.2	591.7	572.9	544.3	525.7
132.5°	501.4	519.1	547.7	566.6	576.9	580.9	576.9	566.6	547.7	519.1	501.4
135°	478.2	494.5	519.7	538.6	548.8	552.3	548.8	538.6	519.7	494.5	478.2
137.5°	453.9	468.2	491.1	508.8	518.5	522.5	518.5	508.8	491.1	468.2	453.9
140°	431.6	443.6	464.8	479.7	488.2	491.1	488.2	479.7	464.8	443.6	431.6
142.5°	412.5	422.5	439.6	451.7	459.7	461.9	459.7	451.7	439.6	422.5	412.5
145°	395.9	403.6	417.3	427.1	433.4	435.6	433.4	427.1	417.3	403.6	395.9
147.5°	381.6	387.6	399.1	407.1	411.1	412.2	411.1	407.1	399.1	387.6	381.6
150°	369.9	375.0	383.6	390.5	392.8	393.3	392.8	390.5	383.6	375.0	369.9
152.5°	359.9	363.6	370.5	375.6	377.9	378.5	377.9	375.6	370.5	363.6	359.9
155°	350.2	353.3	359.0	363.0	364.8	365.3	364.8	363.0	359.0	353.3	350.2
157.5°	341.0	343.6	348.2	351.6	353.3	353.3	353.3	351.6	348.2	343.6	341.0
160°	331.9	333.9	337.9	340.7	341.9	341.3	341.9	340.7	337.9	333.9	331.9
162.5°	323.6	325.3	328.2	330.4	330.4	330.4	330.4	330.4	328.2	325.3	323.6
165°	315.3	316.7	319.0	320.2	320.2	320.2	320.2	320.2	319.0	316.7	315.3
167.5°	307.5	308.7	309.9	311.0	310.4	310.4	310.4	311.0	309.9	308.7	307.5
170°	300.2	300.7	301.9	302.4	302.4	301.9	302.4	302.4	301.9	300.7	300.2
172.5°	294.2	294.4	294.4	295.6	294.4	293.9	294.4	295.6	294.4	294.4	294.2
175°	288.7	288.7	288.7	289.3	288.1	287.6	288.1	289.3	288.7	288.7	288.7
177.5°	285.3	285.3	284.7	285.3	283.6	283.6	283.6	285.3	284.7	285.3	285.3
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6	1840.6
2.5°	1748.4	1739.1	1750.0	1735.9	1739.1	1756.3	1754.7	1770.3	1779.7	1778.1	1785.9
5°	1632.8	1632.8	1637.5	1635.9	1651.6	1665.6	1684.4	1700.0	1717.2	1726.6	1737.5
7.5°	1518.8	1534.4	1537.5	1545.3	1564.1	1587.5	1606.3	1629.7	1654.7	1671.9	1684.4
10°	1425.0	1437.5	1450.0	1456.3	1476.6	1507.8	1534.4	1571.9	1603.1	1621.9	1639.1
12.5°	1342.2	1356.3	1362.5	1390.6	1404.7	1425.0	1462.5	1503.1	1537.5	1557.8	1571.9
15°	1282.8	1290.6	1304.7	1321.9	1335.9	1360.9	1392.2	1437.5	1470.3	1487.5	1535.9
17.5°	1232.8	1242.2	1250.0	1257.8	1279.7	1306.3	1335.9	1375.0	1417.2	1446.9	1471.9
20°	1181.3	1185.9	1195.3	1207.8	1223.4	1248.4	1275.0	1315.6	1353.1	1376.6	1409.4
22.5°	1120.3	1134.4	1143.8	1153.1	1170.3	1198.4	1223.4	1253.1	1300.0	1326.6	1360.9
25°	1084.4	1090.6	1096.9	1107.8	1120.3	1145.3	1173.4	1204.7	1242.2	1270.3	1300.0
27.5°	1037.5	1046.9	1054.7	1068.8	1076.6	1096.9	1123.4	1154.7	1200.0	1223.4	1248.4
30°	998.4	1007.8	1014.1	1020.3	1031.3	1053.1	1078.1	1103.1	1145.3	1175.0	1200.0
32.5°	959.4	968.8	976.6	981.3	992.2	1006.3	1026.6	1057.8	1093.8	1114.1	1146.9
35°	925.0	925.0	934.4	940.6	950.0	962.5	981.3	1004.7	1042.2	1068.8	1098.4
37.5°	885.9	887.5	895.3	900.0	909.4	921.9	940.6	962.5	993.8	1014.1	1043.8
40°	845.3	850.0	853.1	860.9	871.9	876.6	895.3	920.3	951.6	970.3	995.3
42.5°	804.7	807.8	815.6	821.9	831.3	839.1	851.6	875.0	898.4	926.6	946.9
45°	759.4	767.2	771.9	782.8	787.5	795.3	807.8	826.6	854.7	871.9	895.3
47.5°	720.3	723.4	726.6	740.6	750.0	754.7	767.2	778.1	807.8	823.4	845.3
50°	678.1	678.1	682.8	689.1	700.0	709.4	720.3	732.8	756.3	771.9	793.8
52.5°	639.1	634.4	637.5	640.6	651.6	660.9	671.9	689.1	710.9	720.3	739.1
55°	596.9	589.1	593.8	598.4	601.6	614.1	626.6	637.5	654.7	668.8	685.9
57.5°	551.6	550.0	546.9	548.4	556.3	564.1	573.4	587.5	607.8	618.8	628.1
60°	510.9	501.6	498.4	501.6	506.3	510.9	523.4	535.9	553.1	564.1	575.0
62.5°	468.8	459.4	453.1	448.4	453.1	464.1	471.9	481.3	495.3	507.8	517.2
65°	428.1	414.1	407.8	404.7	403.1	410.9	417.2	429.7	442.2	446.9	457.8
67.5°	382.8	370.3	362.5	357.8	357.8	357.8	364.1	376.6	389.1	390.6	401.6
70°	337.5	323.4	315.6	309.4	306.3	309.4	317.2	318.8	329.7	332.8	339.1
72.5°	289.1	276.6	267.2	259.4	260.9	264.1	264.1	267.2	273.4	281.3	281.3
75°	243.8	226.6	221.9	215.6	212.5	212.5	212.5	218.8	223.4	229.7	228.1
77.5°	192.2	182.8	173.4	170.3	165.6	164.1	167.2	167.2	170.3	175.0	176.6
80°	148.4	137.5	131.3	128.1	121.9	120.3	121.9	121.9	126.6	125.0	126.6
82.5°	103.1	95.3	90.6	85.9	82.8	84.4	82.8	82.8	84.4	82.8	82.8
85°	59.4	57.8	54.7	53.1	51.6	48.4	51.6	50.0	48.4	46.9	50.0
87.5°	28.1	26.6	26.6	23.4	23.4	21.9	23.4	23.4	21.9	21.9	21.9
90°	11.4	10.9	10.3	9.7	9.1	8.0	7.4	6.3	5.7	5.2	4.6
92.5°	66.3	89.2	124.1	184.1	228.1	232.1	161.2	96.0	57.2	46.9	36.6
95°	253.8	324.2	411.1	495.7	506.5	413.3	255.6	129.8	68.6	55.8	42.9
97.5°	449.4	520.3	589.4	619.2	547.1	379.0	208.7	112.1	69.7	60.3	50.9
100°	616.3	675.2	703.2	659.2	516.3	329.3	185.2	110.9	77.8	69.2	60.6
102.5°	749.5	770.1	741.5	635.2	461.9	291.6	175.5	116.1	87.5	79.2	70.9
105°	819.3	794.1	715.8	578.6	414.5	269.8	174.4	123.5	98.3	90.3	82.3
107.5°	827.3	766.7	663.2	524.8	379.0	258.4	178.4	133.8	109.2	102.1	94.9
110°	793.0	712.3	603.7	480.2	355.6	253.8	184.7	145.2	121.8	114.4	106.9

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	740.4	658.6	556.8	447.1	341.9	253.8	192.7	156.1	133.8	126.6	119.5
115°	686.1	607.7	519.1	424.8	332.7	255.6	200.7	167.5	146.4	139.2	132.1
117.5°	639.7	571.1	492.8	409.9	327.6	258.4	209.8	178.9	158.9	152.0	145.2
120°	603.7	540.8	472.2	397.9	324.2	263.0	219.0	191.5	171.5	164.4	157.2
122.5°	573.4	519.1	456.8	387.6	321.3	267.0	229.3	203.5	183.5	176.4	169.2
125°	550.0	500.2	441.9	378.5	319.0	271.6	238.4	213.8	195.0	187.6	180.1
127.5°	528.8	482.0	426.5	369.9	317.9	276.7	247.0	224.1	205.8	198.4	191.0
130°	507.1	462.5	412.2	361.3	316.7	281.3	255.6	233.8	216.1	208.6	201.2
132.5°	483.7	444.2	397.9	354.5	316.7	286.4	263.0	243.0	225.3	217.8	210.4
135°	461.9	425.4	385.9	349.3	316.7	291.0	269.8	251.0	233.3	225.6	217.8
137.5°	439.6	408.2	375.0	344.2	317.3	295.6	275.0	256.7	240.7	232.7	224.7
140°	419.6	393.3	366.5	340.7	317.9	298.4	280.1	263.0	246.4	238.7	231.0
142.5°	402.5	380.8	359.0	337.9	318.4	300.1	283.0	267.0	251.6	244.4	237.3
145°	388.2	370.5	352.7	335.0	317.9	301.3	285.9	271.6	256.7	250.1	243.5
147.5°	375.6	361.3	346.5	332.2	316.7	301.9	287.6	274.4	261.3	255.3	249.3
150°	364.8	353.9	341.3	328.7	315.0	301.9	289.3	277.3	264.7	259.8	255.0
152.5°	356.2	346.5	335.6	324.7	312.7	301.3	290.4	280.1	268.7	264.4	260.1
155°	347.0	339.0	329.9	320.2	309.9	300.1	291.0	281.9	272.1	268.1	264.1
157.5°	338.5	332.2	324.2	316.2	307.0	299.0	291.6	283.6	275.0	271.8	268.7
160°	329.9	324.2	318.4	311.0	304.1	297.3	291.6	284.7	277.3	274.7	272.1
162.5°	321.9	317.3	312.2	306.4	300.7	295.6	291.0	285.9	279.6	277.6	275.6
165°	313.9	310.4	306.4	301.9	297.3	293.9	290.4	285.9	281.3	279.6	277.9
167.5°	306.4	303.6	300.7	297.3	293.9	291.0	289.3	285.9	281.9	280.8	279.6
170°	299.6	297.9	296.1	293.3	291.0	289.3	288.1	285.9	283.0	282.2	281.3
172.5°	293.9	292.7	291.0	289.3	287.6	287.0	287.0	285.3	283.0	282.7	282.4
175°	288.7	287.6	287.6	285.9	285.3	285.3	285.9	284.7	283.0	283.0	283.0
177.5°	285.3	285.3	284.7	284.1	283.6	283.6	284.7	284.1	283.0	283.0	283.0
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1840.6	1840.6	1840.6	1840.6
2.5°	1796.9	1812.5	1823.4	1843.8
5°	1756.3	1784.4	1810.9	1839.1
7.5°	1715.6	1748.4	1790.6	1826.6
10°	1670.3	1712.5	1762.5	1810.9
12.5°	1625.0	1675.0	1729.7	1793.8
15°	1570.3	1634.4	1698.4	1767.2
17.5°	1521.9	1587.5	1656.3	1742.2
20°	1467.2	1539.1	1614.1	1701.6
22.5°	1418.8	1498.4	1576.6	1668.8
25°	1364.1	1442.2	1528.1	1626.6
27.5°	1318.8	1390.6	1475.0	1581.3
30°	1264.1	1342.2	1426.6	1532.8
32.5°	1212.5	1287.5	1376.6	1481.3
35°	1159.4	1235.9	1315.6	1415.6
37.5°	1109.4	1175.0	1254.7	1350.0
40°	1053.1	1125.0	1196.9	1271.9
42.5°	1001.6	1067.2	1134.4	1193.8
45°	943.8	1000.0	1064.1	1112.5
47.5°	890.6	940.6	990.6	1028.1
50°	837.5	876.6	914.1	946.9
52.5°	775.0	818.8	839.1	859.4
55°	718.8	743.8	762.5	782.8
57.5°	664.1	675.0	684.4	703.1
60°	592.2	604.7	615.6	629.7
62.5°	529.7	535.9	539.1	553.1
65°	470.3	468.8	476.6	484.4
67.5°	406.3	404.7	412.5	415.6
70°	343.8	342.2	343.8	351.6
72.5°	284.4	284.4	285.9	289.1
75°	229.7	229.7	231.3	234.4
77.5°	173.4	176.6	175.0	181.3
80°	126.6	123.4	126.6	129.7
82.5°	82.8	85.9	85.9	82.8
85°	46.9	46.9	46.9	46.9
87.5°	20.3	20.3	21.9	23.4
90°	3.4	2.3	1.1	0.6
92.5°	24.6	16.0	10.3	8.6
95°	30.3	24.0	19.4	18.9
97.5°	39.4	33.2	29.7	29.2
100°	49.7	43.4	41.2	40.0
102.5°	61.2	54.3	52.6	52.0
105°	73.2	67.5	64.6	64.6
107.5°	85.2	80.6	77.8	76.6
110°	98.3	93.2	90.9	89.8

TEST NUMBER: P1027672

CATALOG NUMBER: S125DIP-B1270D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	110.9	105.8	104.1	102.9
115°	123.5	118.3	116.6	115.5
117.5°	135.5	130.3	128.6	126.9
120°	147.5	142.4	140.1	138.4
122.5°	158.4	153.2	151.5	150.4
125°	169.2	164.1	161.2	160.1
127.5°	179.5	173.2	169.8	168.1
130°	189.2	181.8	177.2	175.5
132.5°	197.8	189.2	183.5	181.2
135°	205.8	196.7	189.8	187.5
137.5°	212.7	203.5	197.2	195.5
140°	220.1	211.0	204.1	202.4
142.5°	227.0	217.8	211.5	210.4
145°	233.3	225.3	219.5	218.4
147.5°	240.1	232.7	227.5	227.0
150°	247.0	239.5	235.5	234.4
152.5°	252.7	246.4	243.0	242.4
155°	258.4	252.7	249.3	249.3
157.5°	263.6	258.4	255.6	255.6
160°	267.6	263.6	261.3	261.8
162.5°	272.1	268.7	266.4	267.0
165°	275.6	272.7	271.0	272.1
167.5°	277.9	276.1	275.0	275.6
170°	280.1	279.0	278.4	279.0
172.5°	281.9	280.7	280.1	281.3
175°	283.0	282.4	281.9	283.0
177.5°	283.6	283.0	283.0	284.1
180°	283.6	283.6	283.6	283.6

(END OF REPORT)