

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027679

Luminaire Tested: S125DIP-B1270D610UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027679
REPORT IS A COMBINATION OF REPORTS P1001732 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B1270D610UB35-4F0-XX-W2A-A
Description: Define 5 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7597.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69		
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59		
2	93	86	80	75	88	81	76	71	73	69	65	65	62	59	58	55	53	49		
3	85	76	68	62	80	72	65	60	65	59	55	58	54	50	51	48	46	42		
4	78	67	59	53	74	64	57	51	58	52	47	52	47	43	46	42	39	36		
5	72	60	52	46	68	57	50	44	52	46	41	46	42	38	42	38	34	32		
6	66	54	46	40	63	52	44	39	47	40	36	42	37	33	38	34	30	28		
7	62	49	41	35	58	47	39	34	42	36	32	38	33	29	35	30	27	25		
8	57	45	37	31	54	43	35	30	39	33	28	35	30	26	32	27	24	22		
9	53	41	33	28	50	39	32	27	36	30	25	32	27	24	29	25	22	20		
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11845	11845	11845	11845
5°	11854	13437	11865	10195
10°	11782	15316	11762	8751
15°	11695	16607	11623	7907
20°	11548	18198	11442	7218
25°	11417	20852	11209	6810
30°	11228	21998	11034	6441
35°	10930	17634	10701	6144
40°	10465	12188	10311	5831
45°	9878	9073	9767	5571
50°	9206	7470	9054	5361
55°	8481	6371	8413	5181
60°	7769	5454	7633	5041
65°	7000	4710	6888	4835
70°	6190	3910	6107	4479
75°	5330	3024	5260	3888
80°	4211	2046	4059	2859
85°	2693	1023	2601	1458

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 18093 cd/sqm

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.9	2.3
10°-20°	530.0	7.0
20°-30°	860.9	11.3
30°-40°	1052.2	13.8
40°-50°	954.4	12.6
50°-60°	760.2	10.0
60°-70°	529.4	7.0
70°-80°	282.1	3.7
80°-90°	71.1	0.9
90°-100°	26.3	0.3
100°-110°	174.8	2.3
110°-120°	314.7	4.1
120°-130°	404.0	5.3
130°-140°	434.5	5.7
140°-150°	407.8	5.4
150°-160°	329.9	4.3
160°-170°	213.3	2.8
170°-180°	73.6	1.0
0°-30°	1568.8	20.7
0°-40°	2621.0	34.5
0°-60°	4335.5	57.1
0°-90°	5218.1	68.7
90°-120°	515.8	6.8
90°-150°	1762.1	23.2
90°-180°	2379.0	31.3
0°-180°	7597.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1849	1849	1849	1849	1849	
5°	1847	2133	1849	1618	1847	175
15°	1775	2663	1764	1268	1775	501
25°	1634	3277	1604	1070	1634	752
35°	1422	2630	1392	916	1422	888
45°	1117	1240	1105	761	1117	861
55°	786	764	780	622	786	703
65°	486	469	479	482	486	483
75°	235	231	232	297	235	250
85°	47	52	46	74	47	56
90°	1	14	1	14	1	5
95°	33	12	33	12	33	40
105°	169	170	169	170	169	179
115°	317	315	317	315	317	314
125°	451	451	451	451	451	403
135°	562	560	562	560	562	433
145°	652	650	652	650	652	408
155°	718	712	718	712	718	331
165°	757	753	757	753	757	214
175°	774	771	774	771	774	74
180°	774	774	774	774	774	

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1851.9	1862.9	1875.5	1884.9	1900.6	1905.3	1913.1	1917.8	1922.5	1927.3	1930.4
5°	1847.2	1873.9	1897.4	1914.7	1944.5	1955.5	1969.6	1986.9	2007.3	2024.6	2035.5
7.5°	1834.7	1877.0	1908.4	1942.9	1983.8	2010.4	2024.6	2060.7	2093.6	2118.7	2151.7
10°	1819.0	1869.2	1917.8	1969.6	2027.7	2057.5	2085.8	2136.0	2181.5	2222.3	2255.3
12.5°	1801.7	1862.9	1921.0	1988.5	2066.9	2103.0	2121.9	2208.2	2264.7	2286.7	2351.0
15°	1775.0	1847.2	1930.4	2013.6	2079.5	2121.9	2173.7	2242.7	2299.2	2347.9	2399.7
17.5°	1749.9	1828.4	1913.1	2005.7	2101.5	2156.4	2195.6	2256.8	2318.0	2380.8	2429.5
20°	1709.1	1811.1	1897.4	1996.3	2109.3	2148.5	2189.3	2261.5	2327.5	2394.9	2456.2
22.5°	1676.1	1773.5	1891.2	1985.3	2081.1	2120.3	2170.5	2245.8	2324.3	2401.2	2490.7
25°	1633.8	1742.1	1844.1	1944.5	2043.4	2085.8	2131.3	2228.6	2310.2	2409.1	2507.9
27.5°	1588.3	1699.7	1801.7	1892.7	1985.3	2043.4	2092.0	2194.1	2302.3	2410.6	2539.3
30°	1539.6	1644.8	1742.1	1831.5	1933.5	1993.2	2041.8	2161.1	2281.9	2420.1	2573.9
32.5°	1487.8	1586.7	1669.9	1760.9	1869.2	1924.1	1990.0	2120.3	2263.1	2427.9	2620.9
35°	1421.9	1516.1	1589.8	1682.4	1790.7	1861.3	1930.4	2076.4	2242.7	2426.3	2647.6
37.5°	1356.0	1429.7	1500.4	1599.2	1724.8	1789.1	1861.3	2021.4	2211.3	2421.6	2658.6
40°	1277.5	1349.7	1410.9	1511.4	1643.2	1717.0	1792.3	1960.2	2175.2	2404.4	2619.4
42.5°	1199.0	1260.2	1327.7	1432.9	1560.0	1638.5	1718.5	1905.3	2128.1	2354.1	2511.1
45°	1117.4	1164.5	1238.3	1334.0	1469.0	1544.3	1635.3	1837.8	2062.2	2263.1	2341.6
47.5°	1032.7	1079.8	1148.8	1241.4	1374.8	1464.3	1550.6	1753.0	1979.0	2134.4	2134.4
50°	951.1	988.7	1056.2	1148.8	1283.8	1365.4	1453.3	1668.3	1850.4	1964.9	1862.9
52.5°	863.2	905.6	962.1	1059.4	1192.8	1266.5	1362.3	1545.9	1718.5	1765.6	1608.7
55°	786.3	820.8	874.2	966.8	1090.8	1167.7	1249.3	1425.0	1571.0	1567.9	1399.9
57.5°	706.2	734.5	791.0	875.7	990.3	1059.4	1141.0	1293.2	1412.5	1370.1	1211.6
60°	632.5	652.9	707.8	776.9	886.7	951.1	1029.5	1153.5	1244.6	1184.9	1024.8
62.5°	555.6	579.1	623.1	690.5	787.9	839.6	897.7	1023.3	1081.3	1028.0	864.8
65°	486.5	505.4	544.6	601.1	689.0	736.1	786.3	889.9	944.8	867.9	732.9
67.5°	417.5	439.4	467.7	517.9	587.0	630.9	674.9	764.3	789.4	720.4	607.4
70°	353.1	372.0	398.6	434.7	492.8	532.0	565.0	638.8	656.0	591.7	502.2
72.5°	290.3	302.9	324.9	354.7	408.1	430.0	464.6	514.8	536.7	478.7	414.3
75°	235.4	244.8	259.0	280.9	317.0	340.6	368.8	415.9	414.3	373.5	328.0
77.5°	182.1	183.6	199.3	219.7	241.7	262.1	276.2	309.2	312.3	287.2	249.5
80°	130.3	135.0	141.2	156.9	175.8	183.6	200.9	221.3	224.4	205.6	180.5
82.5°	83.2	86.3	91.0	100.4	113.0	122.4	131.8	139.7	147.5	136.5	116.1
85°	47.1	48.7	53.4	56.5	62.8	67.5	75.3	83.2	81.6	73.8	67.5
87.5°	23.5	23.5	23.5	26.7	29.8	29.8	33.0	34.5	36.1	33.0	29.8
90°	0.6	1.6	2.6	3.7	4.7	5.2	5.6	6.5	7.4	8.3	9.2
92.5°	10.9	9.7	8.6	7.4	6.3	5.7	6.1	6.9	7.6	8.4	9.2
95°	32.7	32.3	31.9	31.6	31.2	31.0	28.6	23.7	18.9	14.0	9.2
97.5°	61.4	62.2	63.0	63.7	64.5	64.9	58.8	46.7	34.6	22.4	10.3
100°	95.9	96.3	96.7	97.0	97.4	97.6	97.9	98.4	98.9	99.4	99.9
102.5°	130.9	131.4	131.9	132.4	132.9	133.2	133.3	133.6	133.8	134.1	134.3
105°	168.8	169.3	169.8	170.3	170.8	171.1	171.1	171.1	171.1	171.1	171.1
107.5°	207.8	207.8	207.8	207.8	207.8	207.8	207.9	208.2	208.5	208.7	209.0
110°	245.7	245.7	245.7	245.7	245.7	245.7	245.8	246.1	246.3	246.6	246.8

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	281.3	281.7	282.1	282.4	282.8	283.0	283.1	283.2	283.3	283.5	283.6
115°	316.9	317.5	318.2	318.8	319.5	319.8	319.9	320.0	320.1	320.2	320.3
117.5°	354.2	354.2	354.2	354.2	354.2	354.2	354.5	355.0	355.5	356.0	356.5
120°	388.6	388.5	388.4	388.3	388.2	388.1	388.3	388.7	389.0	389.4	389.8
122.5°	419.1	419.7	420.3	421.0	421.6	421.9	422.0	422.1	422.2	422.4	422.5
125°	450.6	451.5	452.4	453.3	454.2	454.7	454.7	454.7	454.7	454.7	454.7
127.5°	481.1	481.7	482.3	483.0	483.6	483.9	483.8	483.7	483.6	483.5	483.4
130°	508.6	509.2	509.9	510.5	511.2	511.5	511.6	511.7	511.8	512.0	512.1
132.5°	536.2	537.0	537.7	538.5	539.2	539.6	539.4	539.0	538.7	538.3	537.9
135°	562.0	562.8	563.6	564.3	565.1	565.5	565.4	565.1	564.8	564.6	564.3
137.5°	586.1	586.9	587.7	588.4	589.2	589.6	589.5	589.2	588.9	588.7	588.4
140°	609.7	609.9	610.2	610.4	610.7	610.8	610.7	610.6	610.5	610.3	610.2
142.5°	630.9	631.0	631.2	631.3	631.4	631.5	631.6	631.9	632.1	632.4	632.6
145°	651.6	651.8	652.1	652.3	652.6	652.7	652.7	652.7	652.7	652.7	652.7
147.5°	669.9	669.9	669.9	669.9	669.9	669.9	670.0	670.1	670.2	670.4	670.5
150°	687.2	686.9	686.7	686.4	686.1	686.0	686.1	686.4	686.7	686.9	687.2
152.5°	703.8	703.2	702.5	701.9	701.2	700.9	701.0	701.3	701.6	701.8	702.1
155°	717.6	716.8	716.0	715.3	714.5	714.1	714.2	714.5	714.8	715.0	715.3
157.5°	728.5	728.1	727.7	727.4	727.0	726.8	726.8	726.8	726.8	726.8	726.8
160°	740.0	739.2	738.4	737.7	736.9	736.5	736.6	736.7	736.8	737.0	737.1
162.5°	749.2	748.4	747.6	746.9	746.1	745.7	745.8	745.9	746.0	746.2	746.3
165°	757.2	756.4	755.7	754.9	754.2	753.8	753.9	754.0	754.1	754.2	754.3
167.5°	763.5	762.7	762.0	761.2	760.5	760.1	760.2	760.3	760.4	760.5	760.6
170°	768.7	767.8	766.9	766.0	765.1	764.7	764.8	764.9	765.0	765.1	765.2
172.5°	772.1	771.2	770.3	769.4	768.5	768.1	768.2	768.5	768.8	769.0	769.3
175°	774.4	773.6	772.9	772.1	771.4	771.0	771.1	771.2	771.3	771.4	771.5
177.5°	776.1	775.3	774.6	773.8	773.1	772.7	772.8	772.9	773.0	773.2	773.3
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1933.5	1944.5	1953.9	1961.8	1968.1	1977.5	1971.2	1972.8	1975.9	1982.2	1982.2
5°	2059.1	2076.4	2085.8	2117.2	2125.0	2123.4	2118.7	2143.8	2142.3	2132.8	2131.3
7.5°	2181.5	2211.3	2238.0	2263.1	2271.0	2291.4	2296.1	2307.1	2303.9	2319.6	2311.8
10°	2292.9	2340.0	2365.1	2402.8	2412.2	2421.6	2434.2	2440.5	2454.6	2453.0	2453.0
12.5°	2379.2	2435.7	2468.7	2478.1	2514.2	2525.2	2536.2	2556.6	2551.9	2553.5	2562.9
15°	2446.7	2501.7	2529.9	2573.9	2599.0	2611.5	2630.4	2652.3	2649.2	2663.3	2660.2
17.5°	2497.0	2548.7	2600.5	2666.5	2668.0	2701.0	2744.9	2754.3	2774.7	2760.6	2760.6
20°	2537.8	2606.8	2680.6	2765.3	2774.7	2795.1	2848.5	2884.6	2908.1	2900.3	2905.0
22.5°	2581.7	2680.6	2766.9	2851.6	2897.2	2933.3	2985.0	3041.5	3061.9	3074.5	3071.4
25°	2638.2	2741.8	2868.9	2986.6	3033.7	3102.8	3171.8	3226.7	3242.4	3277.0	3245.6
27.5°	2696.3	2842.2	3000.7	3138.9	3198.5	3255.0	3338.2	3379.0	3399.4	3415.1	3404.1
30°	2744.9	2945.8	3118.4	3245.6	3287.9	3320.9	3368.0	3377.4	3369.6	3382.1	3397.8
32.5°	2820.3	3016.4	3162.4	3223.6	3218.9	3217.3	3181.2	3131.0	3120.0	3090.2	3131.0
35°	2861.1	3018.0	3074.5	2992.9	2959.9	2900.3	2785.7	2710.4	2644.5	2630.4	2633.5
37.5°	2837.5	2898.7	2831.2	2616.2	2562.9	2471.8	2319.6	2212.9	2164.2	2126.6	2175.2
40°	2710.4	2642.9	2457.7	2195.6	2118.7	2032.4	1889.6	1831.5	1762.5	1748.3	1812.7
42.5°	2500.1	2294.5	2032.4	1830.0	1749.9	1701.3	1582.0	1527.1	1478.4	1456.4	1492.5
45°	2214.5	1964.9	1701.3	1534.9	1467.4	1409.3	1338.7	1280.7	1249.3	1239.8	1269.7
47.5°	1919.4	1655.7	1445.4	1321.5	1250.8	1206.9	1141.0	1108.0	1082.9	1086.0	1090.8
50°	1636.9	1396.8	1235.1	1111.2	1076.6	1042.1	998.2	969.9	957.3	962.1	958.9
52.5°	1393.7	1199.0	1062.5	966.8	951.1	918.1	882.0	858.5	853.8	855.3	860.0
55°	1180.2	1028.0	919.7	850.6	833.4	809.8	787.9	772.2	759.6	764.3	762.7
57.5°	1018.6	885.2	802.0	745.5	732.9	718.8	698.4	690.5	685.8	676.4	684.3
60°	875.7	767.4	695.3	660.7	649.7	640.3	618.4	608.9	605.8	601.1	613.6
62.5°	740.8	663.9	608.9	577.5	566.6	557.1	546.2	538.3	539.9	533.6	539.9
65°	634.0	571.3	532.0	503.8	489.7	483.4	481.8	469.3	467.7	469.3	470.8
67.5°	535.2	481.8	452.0	434.7	423.7	417.5	412.8	404.9	411.2	406.5	409.6
70°	445.7	409.6	378.2	361.0	356.3	357.8	350.0	346.8	348.4	345.3	348.4
72.5°	359.4	329.6	317.0	304.5	298.2	296.6	291.9	287.2	291.9	290.3	290.3
75°	287.2	265.2	251.1	243.3	243.3	240.1	232.3	232.3	232.3	230.7	232.3
77.5°	221.3	202.5	196.2	188.3	188.3	183.6	182.1	182.1	178.9	183.6	180.5
80°	164.8	150.7	141.2	136.5	136.5	135.0	131.8	130.3	131.8	130.3	130.3
82.5°	106.7	100.4	95.7	91.0	89.5	91.0	89.5	86.3	87.9	86.3	89.5
85°	61.2	54.9	54.9	51.8	53.4	50.2	51.8	48.7	47.1	51.8	48.7
87.5°	26.7	25.1	25.1	22.0	22.0	22.0	20.4	22.0	20.4	18.8	20.4
90°	9.8	10.5	11.1	11.8	12.1	12.3	12.7	13.0	13.4	13.8	13.4
92.5°	9.8	10.5	11.1	11.8	12.1	12.2	12.3	12.4	12.5	12.6	12.5
95°	9.8	10.5	11.1	11.8	12.1	12.1	12.1	12.1	12.1	12.1	12.1
97.5°	10.6	10.8	11.1	11.4	11.5	11.6	11.7	11.8	12.0	12.1	12.0
100°	80.9	61.9	42.9	23.9	14.4	14.1	13.6	13.1	12.6	12.1	12.6
102.5°	134.6	134.8	135.1	135.4	135.5	130.1	119.4	108.7	98.0	87.3	98.0
105°	171.1	171.1	171.1	171.1	171.1	171.0	170.9	170.8	170.6	170.5	170.6
107.5°	209.1	209.2	209.3	209.4	209.5	209.2	208.7	208.2	207.7	207.2	207.7
110°	246.4	246.0	245.7	245.3	245.1	245.2	245.3	245.4	245.6	245.7	245.6

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	283.1	282.6	282.1	281.6	281.3	281.2	280.9	280.6	280.4	280.1	280.4
115°	319.8	319.3	318.8	318.3	318.0	317.6	316.9	316.1	315.4	314.6	315.4
117.5°	355.7	355.0	354.2	353.5	353.1	353.0	352.7	352.4	352.2	351.9	352.2
120°	389.5	389.3	389.0	388.7	388.6	388.3	387.7	387.0	386.4	385.8	386.4
122.5°	422.3	422.0	421.8	421.5	421.4	421.0	420.2	419.5	418.7	417.9	418.7
125°	454.2	453.7	453.2	452.7	452.4	452.2	451.8	451.4	451.0	450.6	451.0
127.5°	483.1	482.9	482.6	482.3	482.2	481.7	480.7	479.6	478.6	477.6	478.6
130°	511.7	511.3	510.9	510.5	510.3	510.0	509.4	508.7	508.1	507.5	508.1
132.5°	537.9	537.9	537.9	537.9	537.9	537.6	536.9	536.3	535.6	535.0	535.6
135°	564.1	563.8	563.6	563.3	563.2	562.8	562.0	561.3	560.5	559.7	560.5
137.5°	588.4	588.4	588.4	588.4	588.4	588.1	587.5	586.8	586.2	585.6	586.2
140°	610.5	610.7	611.0	611.3	611.4	611.0	610.2	609.5	608.7	607.9	608.7
142.5°	632.6	632.6	632.6	632.6	632.6	632.2	631.5	630.7	630.0	629.2	630.0
145°	652.8	653.0	653.1	653.2	653.3	652.9	652.1	651.4	650.6	649.8	650.6
147.5°	670.6	670.8	670.9	671.0	671.1	670.7	669.8	668.9	668.0	667.1	668.0
150°	687.4	687.7	687.9	688.2	688.3	687.8	686.8	685.7	684.7	683.7	684.7
152.5°	702.3	702.6	702.8	703.1	703.2	702.8	701.9	701.0	700.1	699.2	700.1
155°	715.7	716.1	716.4	716.8	717.0	716.5	715.5	714.4	713.4	712.4	713.4
157.5°	727.2	727.6	727.9	728.3	728.5	728.0	727.0	725.9	724.9	723.9	724.9
160°	737.6	738.1	738.6	739.1	739.4	738.9	737.9	736.8	735.8	734.8	735.8
162.5°	747.1	747.8	748.6	749.3	749.7	749.1	748.0	746.9	745.7	744.6	745.7
165°	755.1	755.9	756.6	757.4	757.8	757.3	756.3	755.2	754.2	753.2	754.2
167.5°	761.5	762.4	763.3	764.2	764.7	764.1	763.0	761.8	760.7	759.5	760.7
170°	766.2	767.2	768.3	769.3	769.8	769.2	768.1	767.0	765.8	764.7	765.8
172.5°	770.2	771.1	772.0	772.9	773.3	772.7	771.6	770.4	769.3	768.1	769.3
175°	772.5	773.5	774.6	775.6	776.1	775.5	774.4	773.3	772.1	771.0	772.1
177.5°	774.2	775.1	776.0	776.9	777.3	776.8	775.8	774.7	773.7	772.7	773.7
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1979.0	1968.1	1971.2	1968.1	1960.2	1955.5	1942.9	1927.3	1921.0	1913.1	1908.4
5°	2137.6	2129.7	2128.1	2115.6	2112.4	2093.6	2062.2	2046.5	2027.7	2008.9	1990.0
7.5°	2310.2	2300.8	2269.4	2264.7	2267.8	2244.3	2203.5	2172.1	2132.8	2106.2	2070.1
10°	2453.0	2434.2	2407.5	2409.1	2398.1	2366.7	2325.9	2292.9	2236.4	2201.9	2150.1
12.5°	2539.3	2523.6	2520.5	2504.8	2495.4	2454.6	2405.9	2363.6	2321.2	2274.1	2234.9
15°	2644.5	2624.1	2610.0	2588.0	2581.7	2539.3	2486.0	2437.3	2388.7	2344.7	2261.5
17.5°	2760.6	2738.6	2685.3	2680.6	2642.9	2602.1	2550.3	2478.1	2426.3	2363.6	2302.3
20°	2892.5	2861.1	2792.0	2774.7	2744.9	2677.4	2606.8	2526.8	2443.6	2379.2	2307.1
22.5°	3040.0	2985.0	2934.8	2879.9	2857.9	2774.7	2677.4	2580.1	2479.7	2391.8	2305.5
25°	3231.4	3159.3	3088.6	3033.7	2996.0	2887.7	2757.5	2628.8	2512.7	2398.1	2285.1
27.5°	3382.1	3319.3	3242.4	3170.2	3121.6	2992.9	2843.8	2677.4	2533.1	2393.4	2272.5
30°	3393.1	3374.3	3327.2	3287.9	3234.6	3096.5	2931.7	2743.4	2564.4	2394.9	2247.4
32.5°	3187.5	3225.2	3245.6	3251.9	3240.9	3160.8	3010.2	2803.0	2592.7	2380.8	2225.4
35°	2744.9	2845.4	2969.4	3016.4	3061.9	3104.3	3025.9	2845.4	2602.1	2377.7	2190.9
37.5°	2260.0	2351.0	2556.6	2650.8	2704.1	2872.0	2936.4	2839.1	2620.9	2380.8	2158.0
40°	1823.7	1968.1	2115.6	2242.7	2325.9	2514.2	2713.5	2735.5	2594.3	2351.0	2115.6
42.5°	1534.9	1619.6	1731.1	1848.8	1922.5	2145.4	2415.3	2573.9	2511.1	2302.3	2063.8
45°	1307.3	1370.1	1475.3	1514.5	1608.7	1822.1	2107.7	2336.9	2368.3	2225.4	2004.2
47.5°	1122.1	1175.5	1243.0	1291.6	1367.0	1527.1	1768.7	2021.4	2172.1	2120.3	1921.0
50°	988.7	1032.7	1089.2	1117.4	1166.1	1310.5	1492.5	1743.6	1946.1	1963.4	1812.7
52.5°	877.3	902.4	946.4	977.8	1017.0	1104.9	1269.7	1476.8	1704.4	1798.6	1679.3
55°	780.0	800.4	839.6	860.0	880.4	955.8	1084.5	1272.8	1486.2	1610.2	1542.7
57.5°	692.1	709.4	742.3	761.2	772.2	844.4	943.2	1090.8	1282.2	1432.9	1395.2
60°	619.9	635.6	654.5	668.6	681.1	740.8	809.8	929.1	1100.2	1246.1	1236.7
62.5°	543.0	557.1	577.5	591.7	602.7	640.3	698.4	789.4	935.4	1070.3	1097.0
65°	475.5	486.5	500.6	506.9	521.0	549.3	596.4	678.0	797.3	918.1	936.9
67.5°	414.3	417.5	426.9	441.0	444.1	469.3	511.6	572.8	665.4	764.3	794.1
70°	348.4	353.1	361.0	372.0	378.2	393.9	430.0	470.8	550.9	637.2	659.2
72.5°	290.3	296.6	299.8	306.0	309.2	334.3	350.0	390.8	445.7	517.9	541.5
75°	235.4	241.7	243.3	246.4	249.5	260.5	282.5	307.6	353.1	400.2	431.6
77.5°	186.8	185.2	188.3	193.0	191.5	200.9	215.0	237.0	266.8	306.0	326.4
80°	131.8	131.8	136.5	141.2	139.7	149.1	153.8	169.5	194.6	219.7	227.6
82.5°	87.9	87.9	92.6	92.6	95.7	97.3	103.6	111.4	131.8	144.4	149.1
85°	50.2	50.2	51.8	51.8	51.8	54.9	59.6	62.8	69.1	76.9	80.0
87.5°	20.4	22.0	22.0	22.0	22.0	25.1	25.1	28.2	29.8	33.0	33.0
90°	13.0	12.7	12.3	12.1	11.8	11.1	10.5	9.8	9.2	8.3	7.4
92.5°	12.4	12.3	12.2	12.1	11.8	11.1	10.5	9.8	9.2	8.4	7.6
95°	12.1	12.1	12.1	12.1	11.8	11.1	10.5	9.8	9.2	14.0	18.9
97.5°	11.8	11.7	11.6	11.5	11.4	11.1	10.8	10.6	10.3	22.4	34.6
100°	13.1	13.6	14.1	14.4	23.9	42.9	61.9	80.9	99.9	99.4	98.9
102.5°	108.7	119.4	130.1	135.5	135.4	135.1	134.8	134.6	134.3	134.1	133.8
105°	170.8	170.9	171.0	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1
107.5°	208.2	208.7	209.2	209.5	209.4	209.3	209.2	209.1	209.0	208.7	208.5
110°	245.4	245.3	245.2	245.1	245.3	245.7	246.0	246.4	246.8	246.6	246.3

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	280.6	280.9	281.2	281.3	281.6	282.1	282.6	283.1	283.6	283.5	283.3
115°	316.1	316.9	317.6	318.0	318.3	318.8	319.3	319.8	320.3	320.2	320.1
117.5°	352.4	352.7	353.0	353.1	353.5	354.2	355.0	355.7	356.5	356.0	355.5
120°	387.0	387.7	388.3	388.6	388.7	389.0	389.3	389.5	389.8	389.4	389.0
122.5°	419.5	420.2	421.0	421.4	421.5	421.8	422.0	422.3	422.5	422.4	422.2
125°	451.4	451.8	452.2	452.4	452.7	453.2	453.7	454.2	454.7	454.7	454.7
127.5°	479.6	480.7	481.7	482.2	482.3	482.6	482.9	483.1	483.4	483.5	483.6
130°	508.7	509.4	510.0	510.3	510.5	510.9	511.3	511.7	512.1	512.0	511.8
132.5°	536.3	536.9	537.6	537.9	537.9	537.9	537.9	537.9	537.9	538.3	538.7
135°	561.3	562.0	562.8	563.2	563.3	563.6	563.8	564.1	564.3	564.6	564.8
137.5°	586.8	587.5	588.1	588.4	588.4	588.4	588.4	588.4	588.4	588.7	588.9
140°	609.5	610.2	611.0	611.4	611.3	611.0	610.7	610.5	610.2	610.3	610.5
142.5°	630.7	631.5	632.2	632.6	632.6	632.6	632.6	632.6	632.6	632.4	632.1
145°	651.4	652.1	652.9	653.3	653.2	653.1	653.0	652.8	652.7	652.7	652.7
147.5°	668.9	669.8	670.7	671.1	671.0	670.9	670.8	670.6	670.5	670.4	670.2
150°	685.7	686.8	687.8	688.3	688.2	687.9	687.7	687.4	687.2	686.9	686.7
152.5°	701.0	701.9	702.8	703.2	703.1	702.8	702.6	702.3	702.1	701.8	701.6
155°	714.4	715.5	716.5	717.0	716.8	716.4	716.1	715.7	715.3	715.0	714.8
157.5°	725.9	727.0	728.0	728.5	728.3	727.9	727.6	727.2	726.8	726.8	726.8
160°	736.8	737.9	738.9	739.4	739.1	738.6	738.1	737.6	737.1	737.0	736.8
162.5°	746.9	748.0	749.1	749.7	749.3	748.6	747.8	747.1	746.3	746.2	746.0
165°	755.2	756.3	757.3	757.8	757.4	756.6	755.9	755.1	754.3	754.2	754.1
167.5°	761.8	763.0	764.1	764.7	764.2	763.3	762.4	761.5	760.6	760.5	760.4
170°	767.0	768.1	769.2	769.8	769.3	768.3	767.2	766.2	765.2	765.1	765.0
172.5°	770.4	771.6	772.7	773.3	772.9	772.0	771.1	770.2	769.3	769.0	768.8
175°	773.3	774.4	775.5	776.1	775.6	774.6	773.5	772.5	771.5	771.4	771.3
177.5°	774.7	775.8	776.8	777.3	776.9	776.0	775.1	774.2	773.3	773.2	773.0
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1902.1	1894.3	1884.9	1884.9	1873.9	1869.2	1859.8	1856.6	1848.8	1836.2	1826.8
5°	1969.6	1949.2	1936.7	1925.7	1902.1	1884.9	1867.6	1848.8	1830.0	1808.0	1782.9
7.5°	2035.5	1997.9	1980.6	1961.8	1927.3	1891.2	1856.6	1831.5	1806.4	1771.9	1740.5
10°	2104.6	2057.5	2026.1	2001.0	1947.7	1902.1	1851.9	1815.8	1776.6	1732.6	1691.8
12.5°	2162.7	2101.5	2074.8	2027.7	1966.5	1911.6	1848.8	1793.9	1742.1	1690.3	1640.1
15°	2211.3	2153.3	2087.3	2068.5	1983.8	1905.3	1834.7	1764.0	1699.7	1647.9	1589.8
17.5°	2227.0	2153.3	2120.3	2074.8	1974.3	1892.7	1803.3	1726.4	1665.2	1588.3	1542.7
20°	2231.7	2161.1	2115.6	2073.2	1983.8	1875.5	1787.6	1693.4	1619.6	1542.7	1470.6
22.5°	2219.2	2136.0	2092.0	2051.2	1950.8	1858.2	1756.2	1652.6	1566.3	1495.7	1423.5
25°	2195.6	2098.3	2055.9	2012.0	1916.3	1814.3	1702.8	1604.0	1523.9	1439.2	1368.5
27.5°	2164.2	2052.8	2004.2	1958.6	1864.5	1768.7	1663.6	1561.6	1472.1	1382.7	1316.7
30°	2125.0	1996.3	1952.4	1892.7	1801.7	1710.7	1614.9	1512.9	1412.5	1327.7	1255.5
32.5°	2074.8	1939.8	1881.7	1825.2	1726.4	1643.2	1552.2	1456.4	1359.1	1275.9	1200.6
35°	2029.3	1875.5	1811.1	1754.6	1644.8	1556.9	1481.5	1392.1	1305.8	1219.4	1152.0
37.5°	1968.1	1811.1	1734.2	1676.1	1564.7	1475.3	1404.6	1335.6	1244.6	1161.4	1098.6
40°	1903.7	1731.1	1658.9	1600.8	1484.7	1387.4	1319.9	1258.7	1184.9	1108.0	1042.1
42.5°	1845.6	1654.2	1577.3	1506.6	1388.9	1302.6	1233.6	1186.5	1119.0	1049.9	990.3
45°	1771.9	1572.6	1489.4	1415.6	1302.6	1208.5	1142.5	1104.9	1054.7	987.2	935.4
47.5°	1696.5	1484.7	1398.4	1326.2	1203.7	1120.6	1056.2	1020.1	985.6	932.2	880.4
50°	1597.7	1392.1	1313.6	1230.4	1109.6	1024.8	971.5	935.4	908.7	871.0	827.1
52.5°	1489.4	1296.3	1211.6	1139.4	1020.1	943.2	882.0	861.6	834.9	806.7	769.0
55°	1374.8	1192.8	1111.2	1040.5	930.7	852.2	802.0	780.0	759.6	737.6	712.5
57.5°	1260.2	1084.5	1007.6	944.8	842.8	767.4	726.6	696.8	682.7	670.1	649.7
60°	1117.4	968.3	908.7	852.2	751.8	682.7	643.5	621.5	608.9	602.7	593.2
62.5°	991.9	869.5	803.5	748.6	668.6	607.4	569.7	552.4	541.5	538.3	527.3
65°	858.5	753.3	701.5	654.5	585.4	530.5	499.1	478.7	470.8	469.3	469.3
67.5°	732.9	648.2	596.4	563.4	503.8	455.1	425.3	417.5	412.8	406.5	404.9
70°	615.2	547.7	502.2	474.0	420.6	384.5	361.0	348.4	348.4	343.7	340.6
72.5°	511.6	444.1	414.3	390.8	346.8	315.5	298.2	295.1	284.1	282.5	282.5
75°	400.2	350.0	329.6	309.2	276.2	254.2	240.1	232.3	226.0	226.0	227.6
77.5°	301.3	266.8	248.0	232.3	208.7	194.6	183.6	180.5	174.2	174.2	174.2
80°	213.4	194.6	180.5	167.9	150.7	138.1	131.8	125.6	125.6	124.0	125.6
82.5°	138.1	122.4	114.6	113.0	97.3	92.6	84.7	86.3	81.6	80.0	83.2
85°	80.0	72.2	62.8	59.6	53.4	47.1	43.9	45.5	43.9	42.4	43.9
87.5°	31.4	26.7	25.1	25.1	20.4	18.8	17.3	18.8	15.7	15.7	17.3
90°	6.5	5.6	5.2	4.7	3.7	2.6	1.6	0.6	1.6	2.6	3.7
92.5°	6.9	6.1	5.7	6.3	7.4	8.6	9.7	10.9	9.7	8.6	7.4
95°	23.7	28.6	31.0	31.2	31.6	31.9	32.3	32.7	32.3	31.9	31.6
97.5°	46.7	58.8	64.9	64.5	63.7	63.0	62.2	61.4	62.2	63.0	63.7
100°	98.4	97.9	97.6	97.4	97.0	96.7	96.3	95.9	96.3	96.7	97.0
102.5°	133.6	133.3	133.2	132.9	132.4	131.9	131.4	130.9	131.4	131.9	132.4
105°	171.1	171.1	171.1	170.8	170.3	169.8	169.3	168.8	169.3	169.8	170.3
107.5°	208.2	207.9	207.8	207.8	207.8	207.8	207.8	207.8	207.8	207.8	207.8
110°	246.1	245.8	245.7	245.7	245.7	245.7	245.7	245.7	245.7	245.7	245.7

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	283.2	283.1	283.0	282.8	282.4	282.1	281.7	281.3	281.7	282.1	282.4
115°	320.0	319.9	319.8	319.5	318.8	318.2	317.5	316.9	317.5	318.2	318.8
117.5°	355.0	354.5	354.2	354.2	354.2	354.2	354.2	354.2	354.2	354.2	354.2
120°	388.7	388.3	388.1	388.2	388.3	388.4	388.5	388.6	388.5	388.4	388.3
122.5°	422.1	422.0	421.9	421.6	421.0	420.3	419.7	419.1	419.7	420.3	421.0
125°	454.7	454.7	454.7	454.2	453.3	452.4	451.5	450.6	451.5	452.4	453.3
127.5°	483.7	483.8	483.9	483.6	483.0	482.3	481.7	481.1	481.7	482.3	483.0
130°	511.7	511.6	511.5	511.2	510.5	509.9	509.2	508.6	509.2	509.9	510.5
132.5°	539.0	539.4	539.6	539.2	538.5	537.7	537.0	536.2	537.0	537.7	538.5
135°	565.1	565.4	565.5	565.1	564.3	563.6	562.8	562.0	562.8	563.6	564.3
137.5°	589.2	589.5	589.6	589.2	588.4	587.7	586.9	586.1	586.9	587.7	588.4
140°	610.6	610.7	610.8	610.7	610.4	610.2	609.9	609.7	609.9	610.2	610.4
142.5°	631.9	631.6	631.5	631.4	631.3	631.2	631.0	630.9	631.0	631.2	631.3
145°	652.7	652.7	652.7	652.6	652.3	652.1	651.8	651.6	651.8	652.1	652.3
147.5°	670.1	670.0	669.9	669.9	669.9	669.9	669.9	669.9	669.9	669.9	669.9
150°	686.4	686.1	686.0	686.1	686.4	686.7	686.9	687.2	686.9	686.7	686.4
152.5°	701.3	701.0	700.9	701.2	701.9	702.5	703.2	703.8	703.2	702.5	701.9
155°	714.5	714.2	714.1	714.5	715.3	716.0	716.8	717.6	716.8	716.0	715.3
157.5°	726.8	726.8	726.8	727.0	727.4	727.7	728.1	728.5	728.1	727.7	727.4
160°	736.7	736.6	736.5	736.9	737.7	738.4	739.2	740.0	739.2	738.4	737.7
162.5°	745.9	745.8	745.7	746.1	746.9	747.6	748.4	749.2	748.4	747.6	746.9
165°	754.0	753.9	753.8	754.2	754.9	755.7	756.4	757.2	756.4	755.7	754.9
167.5°	760.3	760.2	760.1	760.5	761.2	762.0	762.7	763.5	762.7	762.0	761.2
170°	764.9	764.8	764.7	765.1	766.0	766.9	767.8	768.7	767.8	766.9	766.0
172.5°	768.5	768.2	768.1	768.5	769.4	770.3	771.2	772.1	771.2	770.3	769.4
175°	771.2	771.1	771.0	771.4	772.1	772.9	773.6	774.4	773.6	772.9	772.1
177.5°	772.9	772.8	772.7	773.1	773.8	774.6	775.3	776.1	775.3	774.6	773.8
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1823.7	1820.5	1812.7	1808.0	1792.3	1773.5	1767.2	1751.5	1757.8	1746.8	1746.8
5°	1775.0	1760.9	1751.5	1737.4	1707.5	1687.1	1665.2	1654.2	1647.9	1640.1	1633.8
7.5°	1712.2	1701.3	1691.8	1665.2	1632.2	1604.0	1577.3	1566.3	1545.9	1531.8	1525.5
10°	1657.3	1641.6	1619.6	1588.3	1553.7	1517.6	1494.1	1470.6	1454.9	1447.0	1429.7
12.5°	1600.8	1582.0	1558.4	1512.9	1475.3	1453.3	1410.9	1388.9	1381.1	1374.8	1354.4
15°	1542.7	1522.3	1494.1	1451.7	1418.8	1367.0	1341.9	1324.6	1305.8	1304.2	1288.5
17.5°	1491.0	1465.8	1442.3	1390.5	1349.7	1304.2	1290.1	1271.2	1254.0	1235.1	1227.3
20°	1425.0	1401.5	1384.2	1327.7	1282.2	1254.0	1230.4	1214.7	1203.7	1184.9	1181.8
22.5°	1365.4	1340.3	1316.7	1274.4	1235.1	1199.0	1170.8	1153.5	1148.8	1141.0	1126.8
25°	1307.3	1282.2	1254.0	1214.7	1173.9	1148.8	1123.7	1112.7	1103.3	1090.8	1079.8
27.5°	1258.7	1235.1	1208.5	1159.8	1125.3	1106.4	1079.8	1067.2	1054.7	1048.4	1043.7
30°	1200.6	1173.9	1153.5	1115.9	1078.2	1053.1	1034.3	1023.3	1012.3	1006.0	1002.9
32.5°	1144.1	1119.0	1104.9	1064.1	1034.3	1004.4	990.3	982.5	976.2	969.9	963.6
35°	1098.6	1073.5	1051.5	1013.8	984.0	963.6	952.6	940.1	935.4	929.1	929.1
37.5°	1042.1	1023.3	1001.3	965.2	938.5	922.8	913.4	897.7	896.1	893.0	888.3
40°	993.4	974.6	954.2	922.8	899.3	880.4	867.9	860.0	855.3	852.2	849.1
42.5°	941.7	921.3	911.8	875.7	855.3	836.5	830.2	822.4	820.8	814.5	806.7
45°	891.4	874.2	855.3	828.7	811.4	795.7	786.3	780.0	772.2	770.6	765.9
47.5°	847.5	827.1	809.8	784.7	765.9	753.3	745.5	737.6	731.4	726.6	721.9
50°	791.0	775.3	761.2	734.5	718.8	706.2	695.3	689.0	682.7	682.7	682.7
52.5°	736.1	721.9	709.4	690.5	671.7	660.7	648.2	643.5	640.3	635.6	640.3
55°	682.7	668.6	656.0	641.9	619.9	610.5	598.0	593.2	594.8	594.8	599.5
57.5°	626.2	615.2	607.4	590.1	569.7	560.3	552.4	547.7	547.7	554.0	555.6
60°	571.3	560.3	546.2	530.5	517.9	506.9	502.2	503.8	503.8	506.9	514.8
62.5°	510.1	503.8	495.9	474.0	466.1	458.3	452.0	456.7	455.1	463.0	474.0
65°	453.6	447.3	436.3	425.3	415.9	408.1	406.5	408.1	411.2	419.0	431.6
67.5°	390.8	390.8	381.4	372.0	364.1	356.3	357.8	359.4	362.5	372.0	390.8
70°	339.0	332.7	323.3	317.0	310.7	307.6	304.5	310.7	320.2	326.4	340.6
72.5°	282.5	277.8	269.9	263.7	262.1	259.0	257.4	260.5	269.9	280.9	296.6
75°	222.9	224.4	219.7	215.0	215.0	210.3	213.4	213.4	222.9	233.8	246.4
77.5°	172.6	171.1	169.5	166.4	164.8	164.8	164.8	167.9	177.3	183.6	196.2
80°	122.4	124.0	119.3	120.8	119.3	120.8	120.8	127.1	131.8	139.7	149.1
82.5°	81.6	81.6	78.5	80.0	80.0	80.0	81.6	84.7	91.0	97.3	103.6
85°	45.5	47.1	43.9	47.1	47.1	47.1	48.7	50.2	54.9	56.5	62.8
87.5°	17.3	20.4	20.4	17.3	18.8	20.4	22.0	20.4	23.5	26.7	28.2
90°	4.7	5.2	5.6	6.5	7.4	8.3	9.2	9.8	10.5	11.1	11.8
92.5°	6.3	5.7	6.1	6.9	7.6	8.4	9.2	9.8	10.5	11.1	11.8
95°	31.2	31.0	28.6	23.7	18.9	14.0	9.2	9.8	10.5	11.1	11.8
97.5°	64.5	64.9	58.8	46.7	34.6	22.4	10.3	10.6	10.8	11.1	11.4
100°	97.4	97.6	97.9	98.4	98.9	99.4	99.9	80.9	61.9	42.9	23.9
102.5°	132.9	133.2	133.3	133.6	133.8	134.1	134.3	134.6	134.8	135.1	135.4
105°	170.8	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1
107.5°	207.8	207.8	207.9	208.2	208.5	208.7	209.0	209.1	209.2	209.3	209.4
110°	245.7	245.7	245.8	246.1	246.3	246.6	246.8	246.4	246.0	245.7	245.3

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	282.8	283.0	283.1	283.2	283.3	283.5	283.6	283.1	282.6	282.1	281.6
115°	319.5	319.8	319.9	320.0	320.1	320.2	320.3	319.8	319.3	318.8	318.3
117.5°	354.2	354.2	354.5	355.0	355.5	356.0	356.5	355.7	355.0	354.2	353.5
120°	388.2	388.1	388.3	388.7	389.0	389.4	389.8	389.5	389.3	389.0	388.7
122.5°	421.6	421.9	422.0	422.1	422.2	422.4	422.5	422.3	422.0	421.8	421.5
125°	454.2	454.7	454.7	454.7	454.7	454.7	454.7	454.2	453.7	453.2	452.7
127.5°	483.6	483.9	483.8	483.7	483.6	483.5	483.4	483.1	482.9	482.6	482.3
130°	511.2	511.5	511.6	511.7	511.8	512.0	512.1	511.7	511.3	510.9	510.5
132.5°	539.2	539.6	539.4	539.0	538.7	538.3	537.9	537.9	537.9	537.9	537.9
135°	565.1	565.5	565.4	565.1	564.8	564.6	564.3	564.1	563.8	563.6	563.3
137.5°	589.2	589.6	589.5	589.2	588.9	588.7	588.4	588.4	588.4	588.4	588.4
140°	610.7	610.8	610.7	610.6	610.5	610.3	610.2	610.5	610.7	611.0	611.3
142.5°	631.4	631.5	631.6	631.9	632.1	632.4	632.6	632.6	632.6	632.6	632.6
145°	652.6	652.7	652.7	652.7	652.7	652.7	652.7	652.8	653.0	653.1	653.2
147.5°	669.9	669.9	670.0	670.1	670.2	670.4	670.5	670.6	670.8	670.9	671.0
150°	686.1	686.0	686.1	686.4	686.7	686.9	687.2	687.4	687.7	687.9	688.2
152.5°	701.2	700.9	701.0	701.3	701.6	701.8	702.1	702.3	702.6	702.8	703.1
155°	714.5	714.1	714.2	714.5	714.8	715.0	715.3	715.7	716.1	716.4	716.8
157.5°	727.0	726.8	726.8	726.8	726.8	726.8	726.8	727.2	727.6	727.9	728.3
160°	736.9	736.5	736.6	736.7	736.8	737.0	737.1	737.6	738.1	738.6	739.1
162.5°	746.1	745.7	745.8	745.9	746.0	746.2	746.3	747.1	747.8	748.6	749.3
165°	754.2	753.8	753.9	754.0	754.1	754.2	754.3	755.1	755.9	756.6	757.4
167.5°	760.5	760.1	760.2	760.3	760.4	760.5	760.6	761.5	762.4	763.3	764.2
170°	765.1	764.7	764.8	764.9	765.0	765.1	765.2	766.2	767.2	768.3	769.3
172.5°	768.5	768.1	768.2	768.5	768.8	769.0	769.3	770.2	771.1	772.0	772.9
175°	771.4	771.0	771.1	771.2	771.3	771.4	771.5	772.5	773.5	774.6	775.6
177.5°	773.1	772.7	772.8	772.9	773.0	773.2	773.3	774.2	775.1	776.0	776.9
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1753.0	1742.1	1740.5	1743.6	1737.4	1746.8	1743.6	1746.8	1738.9	1746.8	1742.1
5°	1632.2	1629.1	1622.8	1614.9	1616.5	1618.1	1625.9	1618.1	1624.4	1625.9	1633.8
7.5°	1519.2	1512.9	1517.6	1514.5	1500.4	1497.2	1500.4	1505.1	1514.5	1520.8	1525.5
10°	1428.2	1425.0	1418.8	1414.1	1406.2	1401.5	1407.8	1401.5	1414.1	1425.0	1425.0
12.5°	1359.1	1346.6	1338.7	1337.2	1319.9	1323.0	1329.3	1334.0	1348.1	1354.4	1354.4
15°	1286.9	1277.5	1274.4	1268.1	1261.8	1268.1	1265.0	1269.7	1275.9	1282.2	1285.4
17.5°	1224.2	1222.6	1224.2	1208.5	1213.2	1205.3	1206.9	1214.7	1210.0	1214.7	1224.2
20°	1167.7	1170.8	1166.1	1159.8	1159.8	1150.4	1161.4	1158.2	1159.8	1169.2	1183.3
22.5°	1125.3	1123.7	1119.0	1114.3	1108.0	1109.6	1111.2	1108.0	1120.6	1128.4	1130.0
25°	1079.8	1076.6	1075.1	1070.3	1064.1	1070.3	1068.8	1070.3	1073.5	1086.0	1076.6
27.5°	1037.4	1031.1	1034.3	1029.5	1028.0	1029.5	1029.5	1031.1	1034.3	1035.8	1037.4
30°	1001.3	995.0	993.4	990.3	988.7	990.3	993.4	990.3	1002.9	1001.3	1001.3
32.5°	962.1	957.3	954.2	954.2	952.6	951.1	952.6	954.2	963.6	957.3	963.6
35°	924.4	921.3	921.3	918.1	916.5	916.5	916.5	922.8	919.7	924.4	924.4
37.5°	888.3	888.3	886.7	883.6	882.0	883.6	882.0	885.2	883.6	885.2	886.7
40°	850.6	847.5	845.9	845.9	841.2	836.5	841.2	841.2	842.8	847.5	849.1
42.5°	805.1	806.7	806.7	800.4	800.4	800.4	802.0	803.5	803.5	806.7	806.7
45°	765.9	762.7	762.7	762.7	759.6	761.2	764.3	764.3	764.3	764.3	761.2
47.5°	721.9	721.9	723.5	723.5	728.2	726.6	726.6	725.1	721.9	721.9	723.5
50°	681.1	685.8	687.4	687.4	689.0	690.5	690.5	687.4	685.8	681.1	681.1
52.5°	641.9	645.0	648.2	652.9	656.0	654.5	654.5	651.3	645.0	643.5	641.9
55°	599.5	604.2	610.5	615.2	619.9	621.5	621.5	615.2	608.9	601.1	601.1
57.5°	560.3	565.0	576.0	580.7	587.0	587.0	583.8	579.1	569.7	563.4	558.7
60°	521.0	528.9	536.7	546.2	554.0	555.6	550.9	544.6	533.6	525.8	519.5
62.5°	478.7	486.5	502.2	511.6	517.9	517.9	517.9	510.1	495.9	485.0	475.5
65°	437.9	445.7	459.8	472.4	477.1	481.8	477.1	469.3	458.3	445.7	436.3
67.5°	395.5	404.9	419.0	428.5	434.7	439.4	436.3	430.0	415.9	398.6	392.4
70°	348.4	353.1	373.5	382.9	392.4	395.5	392.4	382.9	368.8	350.0	343.7
72.5°	304.5	309.2	328.0	335.9	343.7	346.8	342.1	335.9	323.3	306.0	298.2
75°	254.2	262.1	271.5	284.1	293.5	296.6	291.9	287.2	271.5	260.5	254.2
77.5°	200.9	208.7	221.3	232.3	241.7	240.1	233.8	235.4	218.2	205.6	200.9
80°	152.2	158.5	167.9	177.3	182.1	182.1	180.5	174.2	167.9	158.5	150.7
82.5°	105.2	113.0	120.8	127.1	127.1	128.7	125.6	124.0	117.7	109.9	108.3
85°	62.8	64.3	70.6	70.6	76.9	73.8	72.2	76.9	70.6	65.9	64.3
87.5°	28.2	26.7	28.2	28.2	26.7	29.8	29.8	28.2	29.8	28.2	28.2
90°	12.1	12.3	12.7	13.0	13.4	13.8	13.4	13.0	12.7	12.3	12.1
92.5°	12.1	12.2	12.3	12.4	12.5	12.6	12.5	12.4	12.3	12.2	12.1
95°	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1	12.1
97.5°	11.5	11.6	11.7	11.8	12.0	12.1	12.0	11.8	11.7	11.6	11.5
100°	14.4	14.1	13.6	13.1	12.6	12.1	12.6	13.1	13.6	14.1	14.4
102.5°	135.5	130.1	119.4	108.7	98.0	87.3	98.0	108.7	119.4	130.1	135.5
105°	171.1	171.0	170.9	170.8	170.6	170.5	170.6	170.8	170.9	171.0	171.1
107.5°	209.5	209.2	208.7	208.2	207.7	207.2	207.7	208.2	208.7	209.2	209.5
110°	245.1	245.2	245.3	245.4	245.6	245.7	245.6	245.4	245.3	245.2	245.1

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	281.3	281.2	280.9	280.6	280.4	280.1	280.4	280.6	280.9	281.2	281.3
115°	318.0	317.6	316.9	316.1	315.4	314.6	315.4	316.1	316.9	317.6	318.0
117.5°	353.1	353.0	352.7	352.4	352.2	351.9	352.2	352.4	352.7	353.0	353.1
120°	388.6	388.3	387.7	387.0	386.4	385.8	386.4	387.0	387.7	388.3	388.6
122.5°	421.4	421.0	420.2	419.5	418.7	417.9	418.7	419.5	420.2	421.0	421.4
125°	452.4	452.2	451.8	451.4	451.0	450.6	451.0	451.4	451.8	452.2	452.4
127.5°	482.2	481.7	480.7	479.6	478.6	477.6	478.6	479.6	480.7	481.7	482.2
130°	510.3	510.0	509.4	508.7	508.1	507.5	508.1	508.7	509.4	510.0	510.3
132.5°	537.9	537.6	536.9	536.3	535.6	535.0	535.6	536.3	536.9	537.6	537.9
135°	563.2	562.8	562.0	561.3	560.5	559.7	560.5	561.3	562.0	562.8	563.2
137.5°	588.4	588.1	587.5	586.8	586.2	585.6	586.2	586.8	587.5	588.1	588.4
140°	611.4	611.0	610.2	609.5	608.7	607.9	608.7	609.5	610.2	611.0	611.4
142.5°	632.6	632.2	631.5	630.7	630.0	629.2	630.0	630.7	631.5	632.2	632.6
145°	653.3	652.9	652.1	651.4	650.6	649.8	650.6	651.4	652.1	652.9	653.3
147.5°	671.1	670.7	669.8	668.9	668.0	667.1	668.0	668.9	669.8	670.7	671.1
150°	688.3	687.8	686.8	685.7	684.7	683.7	684.7	685.7	686.8	687.8	688.3
152.5°	703.2	702.8	701.9	701.0	700.1	699.2	700.1	701.0	701.9	702.8	703.2
155°	717.0	716.5	715.5	714.4	713.4	712.4	713.4	714.4	715.5	716.5	717.0
157.5°	728.5	728.0	727.0	725.9	724.9	723.9	724.9	725.9	727.0	728.0	728.5
160°	739.4	738.9	737.9	736.8	735.8	734.8	735.8	736.8	737.9	738.9	739.4
162.5°	749.7	749.1	748.0	746.9	745.7	744.6	745.7	746.9	748.0	749.1	749.7
165°	757.8	757.3	756.3	755.2	754.2	753.2	754.2	755.2	756.3	757.3	757.8
167.5°	764.7	764.1	763.0	761.8	760.7	759.5	760.7	761.8	763.0	764.1	764.7
170°	769.8	769.2	768.1	767.0	765.8	764.7	765.8	767.0	768.1	769.2	769.8
172.5°	773.3	772.7	771.6	770.4	769.3	768.1	769.3	770.4	771.6	772.7	773.3
175°	776.1	775.5	774.4	773.3	772.1	771.0	772.1	773.3	774.4	775.5	776.1
177.5°	777.3	776.8	775.8	774.7	773.7	772.7	773.7	774.7	775.8	776.8	777.3
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8	1848.8
2.5°	1756.2	1746.8	1757.8	1743.6	1746.8	1764.0	1762.5	1778.2	1787.6	1786.0	1793.9
5°	1640.1	1640.1	1644.8	1643.2	1658.9	1673.0	1691.8	1707.5	1724.8	1734.2	1745.2
7.5°	1525.5	1541.2	1544.3	1552.2	1571.0	1594.5	1613.4	1636.9	1662.0	1679.3	1691.8
10°	1431.3	1443.9	1456.4	1462.7	1483.1	1514.5	1541.2	1578.8	1610.2	1629.1	1646.3
12.5°	1348.1	1362.3	1368.5	1396.8	1410.9	1431.3	1469.0	1509.8	1544.3	1564.7	1578.8
15°	1288.5	1296.3	1310.5	1327.7	1341.9	1367.0	1398.4	1443.9	1476.8	1494.1	1542.7
17.5°	1238.3	1247.7	1255.5	1263.4	1285.4	1312.0	1341.9	1381.1	1423.5	1453.3	1478.4
20°	1186.5	1191.2	1200.6	1213.2	1228.9	1254.0	1280.7	1321.5	1359.1	1382.7	1415.6
22.5°	1125.3	1139.4	1148.8	1158.2	1175.5	1203.7	1228.9	1258.7	1305.8	1332.4	1367.0
25°	1089.2	1095.5	1101.7	1112.7	1125.3	1150.4	1178.6	1210.0	1247.7	1275.9	1305.8
27.5°	1042.1	1051.5	1059.4	1073.5	1081.3	1101.7	1128.4	1159.8	1205.3	1228.9	1254.0
30°	1002.9	1012.3	1018.6	1024.8	1035.8	1057.8	1082.9	1108.0	1150.4	1180.2	1205.3
32.5°	963.6	973.0	980.9	985.6	996.6	1010.7	1031.1	1062.5	1098.6	1119.0	1152.0
35°	929.1	929.1	938.5	944.8	954.2	966.8	985.6	1009.1	1046.8	1073.5	1103.3
37.5°	889.9	891.4	899.3	904.0	913.4	926.0	944.8	966.8	998.2	1018.6	1048.4
40°	849.1	853.8	856.9	864.8	875.7	880.4	899.3	924.4	955.8	974.6	999.7
42.5°	808.3	811.4	819.2	825.5	834.9	842.8	855.3	878.9	902.4	930.7	951.1
45°	762.7	770.6	775.3	786.3	791.0	798.8	811.4	830.2	858.5	875.7	899.3
47.5°	723.5	726.6	729.8	743.9	753.3	758.0	770.6	781.6	811.4	827.1	849.1
50°	681.1	681.1	685.8	692.1	703.1	712.5	723.5	736.1	759.6	775.3	797.3
52.5°	641.9	637.2	640.3	643.5	654.5	663.9	674.9	692.1	714.1	723.5	742.3
55°	599.5	591.7	596.4	601.1	604.2	616.8	629.3	640.3	657.6	671.7	689.0
57.5°	554.0	552.4	549.3	550.9	558.7	566.6	576.0	590.1	610.5	621.5	630.9
60°	513.2	503.8	500.6	503.8	508.5	513.2	525.8	538.3	555.6	566.6	577.5
62.5°	470.8	461.4	455.1	450.4	455.1	466.1	474.0	483.4	497.5	510.1	519.5
65°	430.0	415.9	409.6	406.5	404.9	412.8	419.0	431.6	444.1	448.9	459.8
67.5°	384.5	372.0	364.1	359.4	359.4	359.4	365.7	378.2	390.8	392.4	403.3
70°	339.0	324.9	317.0	310.7	307.6	310.7	318.6	320.2	331.1	334.3	340.6
72.5°	290.3	277.8	268.4	260.5	262.1	265.2	265.2	268.4	274.6	282.5	282.5
75°	244.8	227.6	222.9	216.6	213.4	213.4	213.4	219.7	224.4	230.7	229.1
77.5°	193.0	183.6	174.2	171.1	166.4	164.8	167.9	167.9	171.1	175.8	177.3
80°	149.1	138.1	131.8	128.7	122.4	120.8	122.4	122.4	127.1	125.6	127.1
82.5°	103.6	95.7	91.0	86.3	83.2	84.7	83.2	83.2	84.7	83.2	83.2
85°	59.6	58.1	54.9	53.4	51.8	48.7	51.8	50.2	48.7	47.1	50.2
87.5°	28.2	26.7	26.7	23.5	23.5	22.0	23.5	23.5	22.0	22.0	22.0
90°	11.8	11.1	10.5	9.8	9.2	8.3	7.4	6.5	5.6	5.2	4.7
92.5°	11.8	11.1	10.5	9.8	9.2	8.4	7.6	6.9	6.1	5.7	6.3
95°	11.8	11.1	10.5	9.8	9.2	14.0	18.9	23.7	28.6	31.0	31.2
97.5°	11.4	11.1	10.8	10.6	10.3	22.4	34.6	46.7	58.8	64.9	64.5
100°	23.9	42.9	61.9	80.9	99.9	99.4	98.9	98.4	97.9	97.6	97.4
102.5°	135.4	135.1	134.8	134.6	134.3	134.1	133.8	133.6	133.3	133.2	132.9
105°	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	171.1	170.8
107.5°	209.4	209.3	209.2	209.1	209.0	208.7	208.5	208.2	207.9	207.8	207.8
110°	245.3	245.7	246.0	246.4	246.8	246.6	246.3	246.1	245.8	245.7	245.7

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	281.6	282.1	282.6	283.1	283.6	283.5	283.3	283.2	283.1	283.0	282.8
115°	318.3	318.8	319.3	319.8	320.3	320.2	320.1	320.0	319.9	319.8	319.5
117.5°	353.5	354.2	355.0	355.7	356.5	356.0	355.5	355.0	354.5	354.2	354.2
120°	388.7	389.0	389.3	389.5	389.8	389.4	389.0	388.7	388.3	388.1	388.2
122.5°	421.5	421.8	422.0	422.3	422.5	422.4	422.2	422.1	422.0	421.9	421.6
125°	452.7	453.2	453.7	454.2	454.7	454.7	454.7	454.7	454.7	454.7	454.2
127.5°	482.3	482.6	482.9	483.1	483.4	483.5	483.6	483.7	483.8	483.9	483.6
130°	510.5	510.9	511.3	511.7	512.1	512.0	511.8	511.7	511.6	511.5	511.2
132.5°	537.9	537.9	537.9	537.9	537.9	538.3	538.7	539.0	539.4	539.6	539.2
135°	563.3	563.6	563.8	564.1	564.3	564.6	564.8	565.1	565.4	565.5	565.1
137.5°	588.4	588.4	588.4	588.4	588.4	588.7	588.9	589.2	589.5	589.6	589.2
140°	611.3	611.0	610.7	610.5	610.2	610.3	610.5	610.6	610.7	610.8	610.7
142.5°	632.6	632.6	632.6	632.6	632.6	632.4	632.1	631.9	631.6	631.5	631.4
145°	653.2	653.1	653.0	652.8	652.7	652.7	652.7	652.7	652.7	652.7	652.6
147.5°	671.0	670.9	670.8	670.6	670.5	670.4	670.2	670.1	670.0	669.9	669.9
150°	688.2	687.9	687.7	687.4	687.2	686.9	686.7	686.4	686.1	686.0	686.1
152.5°	703.1	702.8	702.6	702.3	702.1	701.8	701.6	701.3	701.0	700.9	701.2
155°	716.8	716.4	716.1	715.7	715.3	715.0	714.8	714.5	714.2	714.1	714.5
157.5°	728.3	727.9	727.6	727.2	726.8	726.8	726.8	726.8	726.8	726.8	727.0
160°	739.1	738.6	738.1	737.6	737.1	737.0	736.8	736.7	736.6	736.5	736.9
162.5°	749.3	748.6	747.8	747.1	746.3	746.2	746.0	745.9	745.8	745.7	746.1
165°	757.4	756.6	755.9	755.1	754.3	754.2	754.1	754.0	753.9	753.8	754.2
167.5°	764.2	763.3	762.4	761.5	760.6	760.5	760.4	760.3	760.2	760.1	760.5
170°	769.3	768.3	767.2	766.2	765.2	765.1	765.0	764.9	764.8	764.7	765.1
172.5°	772.9	772.0	771.1	770.2	769.3	769.0	768.8	768.5	768.2	768.1	768.5
175°	775.6	774.6	773.5	772.5	771.5	771.4	771.3	771.2	771.1	771.0	771.4
177.5°	776.9	776.0	775.1	774.2	773.3	773.2	773.0	772.9	772.8	772.7	773.1
180°	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4	774.4

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1848.8	1848.8	1848.8	1848.8
2.5°	1804.8	1820.5	1831.5	1851.9
5°	1764.0	1792.3	1819.0	1847.2
7.5°	1723.2	1756.2	1798.6	1834.7
10°	1677.7	1720.1	1770.3	1819.0
12.5°	1632.2	1682.4	1737.4	1801.7
15°	1577.3	1641.6	1706.0	1775.0
17.5°	1528.6	1594.5	1663.6	1749.9
20°	1473.7	1545.9	1621.2	1709.1
22.5°	1425.0	1505.1	1583.6	1676.1
25°	1370.1	1448.6	1534.9	1633.8
27.5°	1324.6	1396.8	1481.5	1588.3
30°	1269.7	1348.1	1432.9	1539.6
32.5°	1217.9	1293.2	1382.7	1487.8
35°	1164.5	1241.4	1321.5	1421.9
37.5°	1114.3	1180.2	1260.2	1356.0
40°	1057.8	1130.0	1202.2	1277.5
42.5°	1006.0	1071.9	1139.4	1199.0
45°	947.9	1004.4	1068.8	1117.4
47.5°	894.6	944.8	995.0	1032.7
50°	841.2	880.4	918.1	951.1
52.5°	778.4	822.4	842.8	863.2
55°	721.9	747.0	765.9	786.3
57.5°	667.0	678.0	687.4	706.2
60°	594.8	607.4	618.4	632.5
62.5°	532.0	538.3	541.5	555.6
65°	472.4	470.8	478.7	486.5
67.5°	408.1	406.5	414.3	417.5
70°	345.3	343.7	345.3	353.1
72.5°	285.6	285.6	287.2	290.3
75°	230.7	230.7	232.3	235.4
77.5°	174.2	177.3	175.8	182.1
80°	127.1	124.0	127.1	130.3
82.5°	83.2	86.3	86.3	83.2
85°	47.1	47.1	47.1	47.1
87.5°	20.4	20.4	22.0	23.5
90°	3.7	2.6	1.6	0.6
92.5°	7.4	8.6	9.7	10.9
95°	31.6	31.9	32.3	32.7
97.5°	63.7	63.0	62.2	61.4
100°	97.0	96.7	96.3	95.9
102.5°	132.4	131.9	131.4	130.9
105°	170.3	169.8	169.3	168.8
107.5°	207.8	207.8	207.8	207.8
110°	245.7	245.7	245.7	245.7

TEST NUMBER: P1027679

CATALOG NUMBER: S125DIP-B1270D610UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	282.4	282.1	281.7	281.3
115°	318.8	318.2	317.5	316.9
117.5°	354.2	354.2	354.2	354.2
120°	388.3	388.4	388.5	388.6
122.5°	421.0	420.3	419.7	419.1
125°	453.3	452.4	451.5	450.6
127.5°	483.0	482.3	481.7	481.1
130°	510.5	509.9	509.2	508.6
132.5°	538.5	537.7	537.0	536.2
135°	564.3	563.6	562.8	562.0
137.5°	588.4	587.7	586.9	586.1
140°	610.4	610.2	609.9	609.7
142.5°	631.3	631.2	631.0	630.9
145°	652.3	652.1	651.8	651.6
147.5°	669.9	669.9	669.9	669.9
150°	686.4	686.7	686.9	687.2
152.5°	701.9	702.5	703.2	703.8
155°	715.3	716.0	716.8	717.6
157.5°	727.4	727.7	728.1	728.5
160°	737.7	738.4	739.2	740.0
162.5°	746.9	747.6	748.4	749.2
165°	754.9	755.7	756.4	757.2
167.5°	761.2	762.0	762.7	763.5
170°	766.0	766.9	767.8	768.7
172.5°	769.4	770.3	771.2	772.1
175°	772.1	772.9	773.6	774.4
177.5°	773.8	774.6	775.3	776.1
180°	774.4	774.4	774.4	774.4

(END OF REPORT)