

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027785

Luminaire Tested: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027785
REPORT IS A COMBINATION OF REPORTS P1001871 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1090UB50-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4848.0 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	84	80	77	74	63	61	59	48	46	45	33	33	32
2	85	78	72	67	76	70	65	61	56	52	49	42	40	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	25	23
4	71	61	53	47	63	55	48	43	44	39	35	33	30	27	23	22	20
5	65	54	46	40	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	40	35	53	44	37	32	35	30	26	27	23	21	19	17	15
7	55	43	36	30	49	39	33	28	32	27	23	24	21	18	17	15	14
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12
9	48	36	29	24	43	32	26	22	26	21	18	20	17	14	15	13	11
10	44	33	26	21	40	30	24	19	24	19	16	19	15	13	14	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3265	3265	3265	3265
5°	3268	3704	3270	2810
10°	3248	4221	3242	2412
15°	3224	4577	3204	2179
20°	3183	5016	3154	1990
25°	3147	5748	3089	1877
30°	3095	6063	3041	1776
35°	3013	4860	2950	1693
40°	2884	3359	2842	1608
45°	2723	2501	2692	1535
50°	2538	2059	2495	1478
55°	2337	1756	2319	1428
60°	2141	1503	2104	1389
65°	1930	1298	1898	1333
70°	1706	1078	1683	1234
75°	1470	834	1449	1072
80°	1160	564	1118	788
85°	743	282	715	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4987 cd/sqm

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.0
10°-20°	146.1	3.0
20°-30°	237.3	4.9
30°-40°	290.0	6.0
40°-50°	263.1	5.4
50°-60°	209.5	4.3
60°-70°	145.9	3.0
70°-80°	77.7	1.6
80°-90°	21.2	0.4
90°-100°	81.2	1.7
100°-110°	241.2	5.0
110°-120°	409.1	8.4
120°-130°	538.6	11.1
130°-140°	603.5	12.4
140°-150°	591.6	12.2
150°-160°	496.9	10.2
160°-170°	330.3	6.8
170°-180°	115.6	2.4
0°-30°	432.4	8.9
0°-40°	722.4	14.9
0°-60°	1195.0	24.7
0°-90°	1439.9	29.7
90°-120°	731.6	15.1
90°-150°	2465.3	50.9
90°-180°	3408.0	70.3
0°-180°	4848.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	510	510	510	510	510	
5°	509	588	510	446	509	48
15°	489	734	486	350	489	138
25°	450	903	442	295	450	207
35°	392	725	384	253	392	245
45°	308	342	304	210	308	237
55°	217	211	215	171	217	194
65°	134	129	132	133	134	133
75°	65	64	64	82	65	69
85°	13	14	12	20	13	16
90°	1	23	1	23	1	5
95°	62	82	62	82	62	65
105°	217	236	217	236	217	231
115°	410	413	410	413	410	405
125°	598	602	598	602	598	536
135°	777	780	777	780	777	599
145°	942	946	942	946	942	589
155°	1078	1078	1078	1078	1078	496
165°	1172	1169	1172	1169	1172	331
175°	1218	1214	1218	1214	1218	116
180°	1221	1221	1221	1221	1221	

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	510.5	513.5	516.9	519.5	523.9	525.2	527.3	528.6	529.9	531.2	532.1
5°	509.2	516.5	523.0	527.8	536.0	539.0	542.9	547.7	553.3	558.0	561.1
7.5°	505.7	517.4	526.0	535.5	546.8	554.2	558.0	568.0	577.1	584.0	593.1
10°	501.4	515.2	528.6	542.9	558.9	567.1	574.9	588.8	601.3	612.6	621.6
12.5°	496.6	513.5	529.5	548.1	569.7	579.7	584.9	608.7	624.2	630.3	648.0
15°	489.3	509.2	532.1	555.0	573.2	584.9	599.1	618.2	633.7	647.2	661.4
17.5°	482.3	504.0	527.3	552.9	579.2	594.4	605.2	622.1	638.9	656.2	669.7
20°	471.1	499.2	523.0	550.3	581.4	592.2	603.5	623.4	641.5	660.1	677.0
22.5°	462.0	488.8	521.3	547.2	573.6	584.4	598.3	619.0	640.7	661.9	686.5
25°	450.3	480.2	508.3	536.0	563.2	574.9	587.5	614.3	636.8	664.0	691.3
27.5°	437.8	468.5	496.6	521.7	547.2	563.2	576.6	604.8	634.6	664.5	699.9
30°	424.4	453.4	480.2	504.8	533.0	549.4	562.8	595.7	629.0	667.1	709.5
32.5°	410.1	437.4	460.3	485.4	515.2	530.4	548.5	584.4	623.8	669.2	722.4
35°	391.9	417.9	438.2	463.7	493.6	513.1	532.1	572.3	618.2	668.8	729.8
37.5°	373.8	394.1	413.6	440.8	475.4	493.2	513.1	557.2	609.5	667.5	732.8
40°	352.1	372.0	388.9	416.6	452.9	473.3	494.0	540.3	599.6	662.7	722.0
42.5°	330.5	347.4	366.0	395.0	430.0	451.6	473.7	525.2	586.6	648.9	692.1
45°	308.0	321.0	341.3	367.7	404.9	425.7	450.8	506.6	568.4	623.8	645.4
47.5°	284.6	297.6	316.7	342.2	379.0	403.6	427.4	483.2	545.5	588.3	588.3
50°	262.2	272.5	291.1	316.7	353.9	376.4	400.6	459.8	510.0	541.6	513.5
52.5°	237.9	249.6	265.2	292.0	328.8	349.1	375.5	426.1	473.7	486.7	443.4
55°	216.7	226.2	241.0	266.5	300.7	321.8	344.3	392.8	433.0	432.2	385.9
57.5°	194.7	202.5	218.0	241.4	273.0	292.0	314.5	356.5	389.3	377.7	334.0
60°	174.3	180.0	195.1	214.1	244.4	262.2	283.8	318.0	343.0	326.6	282.5
62.5°	153.1	159.6	171.7	190.3	217.2	231.4	247.4	282.1	298.1	283.3	238.4
65°	134.1	139.3	150.1	165.7	189.9	202.9	216.7	245.3	260.4	239.2	202.0
67.5°	115.1	121.1	128.9	142.8	161.8	173.9	186.0	210.7	217.6	198.6	167.4
70°	97.3	102.5	109.9	119.8	135.8	146.6	155.7	176.1	180.8	163.1	138.4
72.5°	80.0	83.5	89.5	97.8	112.5	118.5	128.0	141.9	147.9	131.9	114.2
75°	64.9	67.5	71.4	77.4	87.4	93.9	101.7	114.6	114.2	103.0	90.4
77.5°	50.2	50.6	54.9	60.6	66.6	72.2	76.1	85.2	86.1	79.2	68.8
80°	35.9	37.2	38.9	43.3	48.5	50.6	55.4	61.0	61.9	56.7	49.7
82.5°	22.9	23.8	25.1	27.7	31.1	33.7	36.3	38.5	40.7	37.6	32.0
85°	13.0	13.4	14.7	15.6	17.3	18.6	20.8	22.9	22.5	20.3	18.6
87.5°	6.5	6.5	6.5	7.4	8.2	8.2	9.1	9.5	9.9	9.1	8.2
90°	1.0	2.7	4.4	6.1	7.8	8.6	9.3	10.8	12.3	13.7	15.2
92.5°	28.5	29.6	30.6	31.7	32.8	33.3	34.2	36.1	38.0	39.9	41.8
95°	61.8	62.2	62.6	63.1	63.5	63.7	64.8	66.9	69.0	71.1	73.2
97.5°	95.0	95.2	95.4	95.7	95.9	96.0	97.5	100.4	103.4	106.3	109.3
100°	133.0	133.0	133.0	133.0	133.0	133.0	134.4	137.1	139.9	142.6	145.4
102.5°	173.9	175.0	176.0	177.1	178.2	178.7	179.2	180.3	181.3	182.4	183.4
105°	216.7	217.7	218.8	219.8	220.9	221.4	222.0	223.3	224.6	225.8	227.1
107.5°	263.2	264.3	265.3	266.4	267.5	268.0	268.5	269.6	270.6	271.7	272.7
110°	311.7	312.8	313.8	314.9	316.0	316.5	316.8	317.4	318.1	318.7	319.3

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	361.1	361.5	361.9	362.4	362.8	363.0	363.4	364.3	365.1	366.0	366.8
115°	409.6	410.4	411.3	412.1	413.0	413.4	413.6	414.0	414.5	414.9	415.3
117.5°	459.0	459.2	459.4	459.6	459.8	459.9	460.1	460.5	461.0	461.4	461.8
120°	504.6	505.7	506.7	507.8	508.9	509.4	509.5	509.7	509.9	510.1	510.3
122.5°	554.0	554.2	554.4	554.7	554.9	555.0	555.3	555.9	556.6	557.2	557.8
125°	597.7	599.0	600.2	601.5	602.8	603.4	603.5	603.7	604.0	604.2	604.4
127.5°	646.2	646.8	647.5	648.1	648.8	649.1	649.2	649.4	649.6	649.8	650.0
130°	689.0	690.0	691.1	692.1	693.2	693.7	693.9	694.3	694.8	695.2	695.6
132.5°	731.7	733.6	735.5	737.4	739.3	740.3	740.2	740.0	739.7	739.5	739.3
135°	777.3	778.6	779.8	781.1	782.4	783.0	783.1	783.3	783.6	783.8	784.0
137.5°	820.1	821.4	822.6	823.9	825.2	825.8	826.0	826.4	826.9	827.3	827.7
140°	861.0	862.0	863.1	864.1	865.2	865.7	866.0	866.7	867.3	868.0	868.6
142.5°	901.8	902.6	903.5	904.3	905.2	905.6	906.0	906.9	907.7	908.6	909.4
145°	941.7	942.6	943.4	944.3	945.2	945.6	945.9	946.5	947.2	947.8	948.4
147.5°	978.8	979.4	980.1	980.7	981.4	981.7	981.9	982.3	982.8	983.2	983.6
150°	1015.9	1015.7	1015.5	1015.2	1015.0	1014.9	1015.3	1016.2	1017.0	1017.9	1018.7
152.5°	1046.3	1046.7	1047.1	1047.6	1048.0	1048.2	1048.3	1048.5	1048.7	1048.9	1049.1
155°	1077.6	1077.6	1077.6	1077.6	1077.6	1077.6	1077.7	1077.9	1078.2	1078.4	1078.6
157.5°	1106.2	1105.8	1105.4	1104.9	1104.5	1104.3	1104.4	1104.6	1104.8	1105.0	1105.2
160°	1130.9	1130.3	1129.6	1129.0	1128.3	1128.0	1128.1	1128.3	1128.6	1128.8	1129.0
162.5°	1152.7	1152.3	1151.9	1151.4	1151.0	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8
165°	1171.7	1171.3	1170.9	1170.4	1170.0	1169.8	1169.9	1170.1	1170.4	1170.6	1170.8
167.5°	1188.8	1188.0	1187.1	1186.3	1185.4	1185.0	1185.0	1185.0	1185.0	1185.0	1185.0
170°	1202.1	1201.3	1200.4	1199.6	1198.7	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3
172.5°	1211.6	1210.8	1209.9	1209.1	1208.2	1207.8	1207.8	1207.8	1207.8	1207.8	1207.8
175°	1218.3	1217.5	1216.6	1215.8	1214.9	1214.5	1214.5	1214.5	1214.5	1214.5	1214.5
177.5°	1223.0	1222.2	1221.3	1220.5	1219.6	1219.2	1219.1	1218.9	1218.7	1218.5	1218.3
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	533.0	536.0	538.6	540.7	542.5	545.1	543.3	543.8	544.6	546.4	546.4
5°	567.6	572.3	574.9	583.6	585.7	585.3	584.0	590.9	590.5	587.9	587.5
7.5°	601.3	609.5	616.9	623.8	626.0	631.6	632.9	635.9	635.0	639.4	637.2
10°	632.0	645.0	651.9	662.3	664.9	667.5	671.0	672.7	676.6	676.1	676.1
12.5°	655.8	671.4	680.5	683.1	693.0	696.0	699.1	704.7	703.4	703.8	706.4
15°	674.4	689.6	697.3	709.5	716.4	719.8	725.0	731.1	730.2	734.1	733.2
17.5°	688.3	702.5	716.8	735.0	735.4	744.5	756.6	759.2	764.8	760.9	760.9
20°	699.5	718.5	738.9	762.2	764.8	770.4	785.2	795.1	801.6	799.4	800.7
22.5°	711.6	738.9	762.7	786.0	798.6	808.5	822.8	838.4	844.0	847.4	846.6
25°	727.2	755.7	790.8	823.2	836.2	855.2	874.3	889.4	893.7	903.3	894.6
27.5°	743.2	783.4	827.1	865.2	881.6	897.2	920.1	931.4	937.0	941.3	938.3
30°	756.6	812.0	859.6	894.6	906.3	915.4	928.3	930.9	928.8	932.2	936.6
32.5°	777.4	831.4	871.7	888.5	887.2	886.8	876.9	863.0	860.0	851.8	863.0
35°	788.6	831.9	847.4	825.0	815.9	799.4	767.9	747.1	728.9	725.0	725.9
37.5°	782.1	799.0	780.4	721.1	706.4	681.3	639.4	610.0	596.5	586.2	599.6
40°	747.1	728.5	677.4	605.2	584.0	560.2	520.8	504.8	485.8	481.9	499.6
42.5°	689.1	632.5	560.2	504.4	482.3	468.9	436.1	420.9	407.5	401.4	411.4
45°	610.4	541.6	468.9	423.1	404.5	388.5	369.0	353.0	344.3	341.7	350.0
47.5°	529.1	456.4	398.4	364.2	344.8	332.7	314.5	305.4	298.5	299.4	300.7
50°	451.2	385.0	340.5	306.3	296.8	287.2	275.1	267.3	263.9	265.2	264.3
52.5°	384.1	330.5	292.9	266.5	262.2	253.1	243.1	236.6	235.3	235.8	237.1
55°	325.3	283.3	253.5	234.5	229.7	223.2	217.2	212.8	209.4	210.7	210.2
57.5°	280.8	244.0	221.1	205.5	202.0	198.1	192.5	190.3	189.0	186.4	188.6
60°	241.4	211.5	191.6	182.1	179.1	176.5	170.4	167.8	167.0	165.7	169.1
62.5°	204.2	183.0	167.8	159.2	156.2	153.6	150.5	148.4	148.8	147.1	148.8
65°	174.8	157.5	146.6	138.9	135.0	133.2	132.8	129.3	128.9	129.3	129.8
67.5°	147.5	132.8	124.6	119.8	116.8	115.1	113.8	111.6	113.3	112.0	112.9
70°	122.9	112.9	104.3	99.5	98.2	98.6	96.5	95.6	96.0	95.2	96.0
72.5°	99.1	90.8	87.4	83.9	82.2	81.8	80.5	79.2	80.5	80.0	80.0
75°	79.2	73.1	69.2	67.1	67.1	66.2	64.0	64.0	64.0	63.6	64.0
77.5°	61.0	55.8	54.1	51.9	51.9	50.6	50.2	50.2	49.3	50.6	49.7
80°	45.4	41.5	38.9	37.6	37.6	37.2	36.3	35.9	36.3	35.9	35.9
82.5°	29.4	27.7	26.4	25.1	24.7	25.1	24.7	23.8	24.2	23.8	24.7
85°	16.9	15.1	15.1	14.3	14.7	13.8	14.3	13.4	13.0	14.3	13.4
87.5°	7.4	6.9	6.9	6.1	6.1	6.1	5.6	6.1	5.6	5.2	5.6
90°	16.3	17.3	18.4	19.5	20.0	20.3	20.9	21.6	22.2	22.8	22.2
92.5°	43.3	44.8	46.3	47.8	48.5	48.7	49.1	49.6	50.0	50.4	50.0
95°	74.7	76.1	77.6	79.1	79.8	80.0	80.4	80.9	81.3	81.7	81.3
97.5°	110.6	111.8	113.1	114.4	115.0	115.1	115.3	115.5	115.7	115.9	115.7
100°	147.3	149.2	151.1	153.0	153.9	154.1	154.5	155.0	155.4	155.8	155.4
102.5°	185.5	187.6	189.7	191.8	192.9	193.2	193.9	194.5	195.2	195.8	195.2
105°	228.4	229.6	230.9	232.2	232.8	233.1	233.8	234.4	235.1	235.7	235.1
107.5°	273.3	274.0	274.6	275.3	275.6	275.6	275.6	275.6	275.6	275.6	275.6
110°	319.9	320.6	321.2	321.9	322.2	322.1	321.9	321.6	321.4	321.2	321.4

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	367.0	367.2	367.5	367.7	367.8	367.6	367.2	366.7	366.3	365.9	366.3
115°	415.1	414.9	414.6	414.4	414.3	414.2	414.0	413.8	413.6	413.4	413.6
117.5°	462.0	462.2	462.5	462.7	462.8	462.4	461.5	460.7	459.8	459.0	459.8
120°	510.3	510.3	510.3	510.3	510.3	509.9	509.0	508.2	507.3	506.5	507.3
122.5°	557.6	557.4	557.2	557.0	556.9	556.6	555.9	555.3	554.6	554.0	554.6
125°	604.0	603.6	603.1	602.7	602.5	602.4	602.2	601.9	601.7	601.5	601.7
127.5°	649.8	649.6	649.4	649.2	649.1	648.9	648.5	648.0	647.6	647.2	647.6
130°	695.4	695.2	695.0	694.8	694.7	694.5	694.1	693.6	693.2	692.8	693.2
132.5°	739.1	738.9	738.7	738.5	738.4	738.1	737.4	736.8	736.1	735.5	736.1
135°	784.0	784.0	784.0	784.0	784.0	783.6	782.7	781.9	781.0	780.2	781.0
137.5°	827.9	828.1	828.4	828.6	828.7	828.2	827.1	826.0	825.0	823.9	825.0
140°	869.0	869.4	869.9	870.3	870.5	870.0	868.9	867.8	866.8	865.7	866.8
142.5°	909.6	909.8	910.1	910.3	910.4	909.9	908.8	907.7	906.7	905.6	906.7
145°	948.4	948.4	948.4	948.4	948.4	948.1	947.5	946.8	946.2	945.6	946.2
147.5°	984.2	984.8	985.5	986.1	986.4	985.6	983.9	982.2	980.5	978.8	980.5
150°	1018.7	1018.7	1018.7	1018.7	1018.7	1018.5	1018.1	1017.6	1017.2	1016.8	1017.2
152.5°	1049.7	1050.4	1051.0	1051.7	1052.0	1051.6	1050.7	1049.9	1049.0	1048.2	1049.0
155°	1079.4	1080.3	1081.1	1082.0	1082.4	1081.9	1080.8	1079.7	1078.7	1077.6	1078.7
157.5°	1106.0	1106.9	1107.7	1108.6	1109.0	1108.3	1106.8	1105.3	1103.9	1102.4	1103.9
160°	1129.8	1130.7	1131.5	1132.4	1132.8	1132.3	1131.2	1130.1	1129.1	1128.0	1129.1
162.5°	1151.9	1152.9	1154.0	1155.1	1155.6	1155.0	1153.7	1152.4	1151.2	1149.9	1151.2
165°	1171.6	1172.5	1173.3	1174.2	1174.6	1174.0	1172.7	1171.4	1170.2	1168.9	1170.2
167.5°	1186.3	1187.5	1188.8	1190.1	1190.7	1190.1	1188.8	1187.5	1186.3	1185.0	1186.3
170°	1199.6	1200.8	1202.1	1203.4	1204.0	1203.3	1201.8	1200.3	1198.9	1197.4	1198.9
172.5°	1209.1	1210.3	1211.6	1212.9	1213.5	1212.9	1211.6	1210.3	1209.1	1207.8	1209.1
175°	1215.8	1217.0	1218.3	1219.6	1220.2	1219.5	1218.0	1216.5	1215.0	1213.5	1215.0
177.5°	1219.6	1220.8	1222.1	1223.4	1224.0	1223.3	1221.8	1220.3	1218.8	1217.3	1218.8
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	545.5	542.5	543.3	542.5	540.3	539.0	535.5	531.2	529.5	527.3	526.0
5°	589.2	587.0	586.6	583.1	582.3	577.1	568.4	564.1	558.9	553.7	548.5
7.5°	636.8	634.2	625.5	624.2	625.1	618.6	607.4	598.7	587.9	580.5	570.6
10°	676.1	671.0	663.6	664.0	661.0	652.3	641.1	632.0	616.4	606.9	592.7
12.5°	699.9	695.6	694.7	690.4	687.8	676.6	663.2	651.5	639.8	626.8	616.0
15°	728.9	723.3	719.4	713.3	711.6	699.9	685.2	671.8	658.4	646.3	623.4
17.5°	760.9	754.9	740.2	738.9	728.5	717.2	703.0	683.1	668.8	651.5	634.6
20°	797.3	788.6	769.6	764.8	756.6	738.0	718.5	696.5	673.5	655.8	635.9
22.5°	837.9	822.8	808.9	793.8	787.8	764.8	738.0	711.2	683.5	659.3	635.5
25°	890.7	870.8	851.3	836.2	825.8	796.0	760.1	724.6	692.6	661.0	629.9
27.5°	932.2	914.9	893.7	873.8	860.4	825.0	783.9	738.0	698.2	659.7	626.4
30°	935.3	930.1	917.1	906.3	891.6	853.5	808.1	756.2	706.9	660.1	619.5
32.5°	878.6	889.0	894.6	896.3	893.3	871.2	829.7	772.6	714.6	656.2	613.4
35°	756.6	784.3	818.5	831.4	844.0	855.7	834.0	784.3	717.2	655.4	603.9
37.5°	622.9	648.0	704.7	730.6	745.4	791.6	809.4	782.6	722.4	656.2	594.8
40°	502.7	542.5	583.1	618.2	641.1	693.0	748.0	754.0	715.1	648.0	583.1
42.5°	423.1	446.4	477.1	509.6	529.9	591.4	665.8	709.5	692.1	634.6	568.9
45°	360.3	377.7	406.6	417.5	443.4	502.2	581.0	644.1	652.8	613.4	552.4
47.5°	309.3	324.0	342.6	356.0	376.8	420.9	487.5	557.2	598.7	584.4	529.5
50°	272.5	284.6	300.2	308.0	321.4	361.2	411.4	480.6	536.4	541.2	499.6
52.5°	241.8	248.7	260.9	269.5	280.3	304.5	350.0	407.1	469.8	495.8	462.9
55°	215.0	220.6	231.4	237.1	242.7	263.4	298.9	350.8	409.7	443.8	425.2
57.5°	190.8	195.5	204.6	209.8	212.8	232.7	260.0	300.7	353.4	395.0	384.6
60°	170.9	175.2	180.4	184.3	187.7	204.2	223.2	256.1	303.2	343.5	340.9
62.5°	149.7	153.6	159.2	163.1	166.1	176.5	192.5	217.6	257.8	295.0	302.4
65°	131.1	134.1	138.0	139.7	143.6	151.4	164.4	186.9	219.8	253.1	258.3
67.5°	114.2	115.1	117.7	121.6	122.4	129.3	141.0	157.9	183.4	210.7	218.9
70°	96.0	97.3	99.5	102.5	104.3	108.6	118.5	129.8	151.8	175.6	181.7
72.5°	80.0	81.8	82.6	84.4	85.2	92.1	96.5	107.7	122.9	142.8	149.2
75°	64.9	66.6	67.1	67.9	68.8	71.8	77.9	84.8	97.3	110.3	119.0
77.5°	51.5	51.0	51.9	53.2	52.8	55.4	59.3	65.3	73.5	84.4	90.0
80°	36.3	36.3	37.6	38.9	38.5	41.1	42.4	46.7	53.6	60.6	62.7
82.5°	24.2	24.2	25.5	25.5	26.4	26.8	28.6	30.7	36.3	39.8	41.1
85°	13.8	13.8	14.3	14.3	14.3	15.1	16.4	17.3	19.0	21.2	22.1
87.5°	5.6	6.1	6.1	6.1	6.1	6.9	6.9	7.8	8.2	9.1	9.1
90°	21.6	20.9	20.3	20.0	19.5	18.4	17.3	16.3	15.2	13.7	12.3
92.5°	49.6	49.1	48.7	48.5	47.8	46.3	44.8	43.3	41.8	39.9	38.0
95°	80.9	80.4	80.0	79.8	79.1	77.6	76.1	74.7	73.2	71.1	69.0
97.5°	115.5	115.3	115.1	115.0	114.4	113.1	111.8	110.6	109.3	106.3	103.4
100°	155.0	154.5	154.1	153.9	153.0	151.1	149.2	147.3	145.4	142.6	139.9
102.5°	194.5	193.9	193.2	192.9	191.8	189.7	187.6	185.5	183.4	182.4	181.3
105°	234.4	233.8	233.1	232.8	232.2	230.9	229.6	228.4	227.1	225.8	224.6
107.5°	275.6	275.6	275.6	275.6	275.3	274.6	274.0	273.3	272.7	271.7	270.6
110°	321.6	321.9	322.1	322.2	321.9	321.2	320.6	319.9	319.3	318.7	318.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	366.7	367.2	367.6	367.8	367.7	367.5	367.2	367.0	366.8	366.0	365.1
115°	413.8	414.0	414.2	414.3	414.4	414.6	414.9	415.1	415.3	414.9	414.5
117.5°	460.7	461.5	462.4	462.8	462.7	462.5	462.2	462.0	461.8	461.4	461.0
120°	508.2	509.0	509.9	510.3	510.3	510.3	510.3	510.3	510.3	510.1	509.9
122.5°	555.3	555.9	556.6	556.9	557.0	557.2	557.4	557.6	557.8	557.2	556.6
125°	601.9	602.2	602.4	602.5	602.7	603.1	603.6	604.0	604.4	604.2	604.0
127.5°	648.0	648.5	648.9	649.1	649.2	649.4	649.6	649.8	650.0	649.8	649.6
130°	693.6	694.1	694.5	694.7	694.8	695.0	695.2	695.4	695.6	695.2	694.8
132.5°	736.8	737.4	738.1	738.4	738.5	738.7	738.9	739.1	739.3	739.5	739.7
135°	781.9	782.7	783.6	784.0	784.0	784.0	784.0	784.0	784.0	783.8	783.6
137.5°	826.0	827.1	828.2	828.7	828.6	828.4	828.1	827.9	827.7	827.3	826.9
140°	867.8	868.9	870.0	870.5	870.3	869.9	869.4	869.0	868.6	868.0	867.3
142.5°	907.7	908.8	909.9	910.4	910.3	910.1	909.8	909.6	909.4	908.6	907.7
145°	946.8	947.5	948.1	948.4	948.4	948.4	948.4	948.4	948.4	947.8	947.2
147.5°	982.2	983.9	985.6	986.4	986.1	985.5	984.8	984.2	983.6	983.2	982.8
150°	1017.6	1018.1	1018.5	1018.7	1018.7	1018.7	1018.7	1018.7	1018.7	1017.9	1017.0
152.5°	1049.9	1050.7	1051.6	1052.0	1051.7	1051.0	1050.4	1049.7	1049.1	1048.9	1048.7
155°	1079.7	1080.8	1081.9	1082.4	1082.0	1081.1	1080.3	1079.4	1078.6	1078.4	1078.2
157.5°	1105.3	1106.8	1108.3	1109.0	1108.6	1107.7	1106.9	1106.0	1105.2	1105.0	1104.8
160°	1130.1	1131.2	1132.3	1132.8	1132.4	1131.5	1130.7	1129.8	1129.0	1128.8	1128.6
162.5°	1152.4	1153.7	1155.0	1155.6	1155.1	1154.0	1152.9	1151.9	1150.8	1150.8	1150.8
165°	1171.4	1172.7	1174.0	1174.6	1174.2	1173.3	1172.5	1171.6	1170.8	1170.6	1170.4
167.5°	1187.5	1188.8	1190.1	1190.7	1190.1	1188.8	1187.5	1186.3	1185.0	1185.0	1185.0
170°	1200.3	1201.8	1203.3	1204.0	1203.4	1202.1	1200.8	1199.6	1198.3	1198.3	1198.3
172.5°	1210.3	1211.6	1212.9	1213.5	1212.9	1211.6	1210.3	1209.1	1207.8	1207.8	1207.8
175°	1216.5	1218.0	1219.5	1220.2	1219.6	1218.3	1217.0	1215.8	1214.5	1214.5	1214.5
177.5°	1220.3	1221.8	1223.3	1224.0	1223.4	1222.1	1220.8	1219.6	1218.3	1218.5	1218.7
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	524.3	522.1	519.5	519.5	516.5	515.2	512.6	511.8	509.6	506.1	503.5
5°	542.9	537.3	533.8	530.8	524.3	519.5	514.8	509.6	504.4	498.3	491.4
7.5°	561.1	550.7	545.9	540.7	531.2	521.3	511.8	504.8	497.9	488.4	479.7
10°	580.1	567.1	558.5	551.6	536.8	524.3	510.5	500.5	489.7	477.6	466.3
12.5°	596.1	579.2	571.9	558.9	542.0	526.9	509.6	494.5	480.2	465.9	452.1
15°	609.5	593.5	575.3	570.2	546.8	525.2	505.7	486.2	468.5	454.2	438.2
17.5°	613.8	593.5	584.4	571.9	544.2	521.7	497.0	475.9	459.0	437.8	425.2
20°	615.1	595.7	583.1	571.5	546.8	516.9	492.7	466.8	446.4	425.2	405.3
22.5°	611.7	588.8	576.6	565.4	537.7	512.2	484.1	455.5	431.7	412.3	392.4
25°	605.2	578.4	566.7	554.6	528.2	500.1	469.4	442.1	420.0	396.7	377.2
27.5°	596.5	565.8	552.4	539.9	513.9	487.5	458.5	430.4	405.8	381.1	362.9
30°	585.7	550.3	538.1	521.7	496.6	471.5	445.1	417.0	389.3	366.0	346.1
32.5°	571.9	534.7	518.7	503.1	475.9	452.9	427.8	401.4	374.6	351.7	330.9
35°	559.3	516.9	499.2	483.6	453.4	429.1	408.4	383.7	359.9	336.1	317.5
37.5°	542.5	499.2	478.0	462.0	431.3	406.6	387.2	368.1	343.0	320.1	302.8
40°	524.7	477.1	457.3	441.2	409.2	382.4	363.8	346.9	326.6	305.4	287.2
42.5°	508.7	456.0	434.8	415.3	382.8	359.1	340.0	327.0	308.4	289.4	273.0
45°	488.4	433.5	410.5	390.2	359.1	333.1	314.9	304.5	290.7	272.1	257.8
47.5°	467.6	409.2	385.4	365.5	331.8	308.9	291.1	281.2	271.7	257.0	242.7
50°	440.4	383.7	362.1	339.2	305.8	282.5	267.8	257.8	250.5	240.1	228.0
52.5°	410.5	357.3	334.0	314.1	281.2	260.0	243.1	237.5	230.1	222.4	212.0
55°	379.0	328.8	306.3	286.8	256.5	234.9	221.1	215.0	209.4	203.3	196.4
57.5°	347.4	298.9	277.7	260.4	232.3	211.5	200.3	192.1	188.2	184.7	179.1
60°	308.0	266.9	250.5	234.9	207.2	188.2	177.4	171.3	167.8	166.1	163.5
62.5°	273.4	239.7	221.5	206.3	184.3	167.4	157.0	152.3	149.2	148.4	145.4
65°	236.6	207.6	193.4	180.4	161.4	146.2	137.6	131.9	129.8	129.3	129.3
67.5°	202.0	178.7	164.4	155.3	138.9	125.5	117.2	115.1	113.8	112.0	111.6
70°	169.6	151.0	138.4	130.6	115.9	106.0	99.5	96.0	96.0	94.7	93.9
72.5°	141.0	122.4	114.2	107.7	95.6	87.0	82.2	81.3	78.3	77.9	77.9
75°	110.3	96.5	90.8	85.2	76.1	70.1	66.2	64.0	62.3	62.3	62.7
77.5°	83.1	73.5	68.3	64.0	57.5	53.6	50.6	49.7	48.0	48.0	48.0
80°	58.8	53.6	49.7	46.3	41.5	38.1	36.3	34.6	34.6	34.2	34.6
82.5°	38.1	33.7	31.6	31.1	26.8	25.5	23.4	23.8	22.5	22.1	22.9
85°	22.1	19.9	17.3	16.4	14.7	13.0	12.1	12.5	12.1	11.7	12.1
87.5°	8.7	7.4	6.9	6.9	5.6	5.2	4.8	5.2	4.3	4.3	4.8
90°	10.8	9.3	8.6	7.8	6.1	4.4	2.7	1.0	2.7	4.4	6.1
92.5°	36.1	34.2	33.3	32.8	31.7	30.6	29.6	28.5	29.6	30.6	31.7
95°	66.9	64.8	63.7	63.5	63.1	62.6	62.2	61.8	62.2	62.6	63.1
97.5°	100.4	97.5	96.0	95.9	95.7	95.4	95.2	95.0	95.2	95.4	95.7
100°	137.1	134.4	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0	133.0
102.5°	180.3	179.2	178.7	178.2	177.1	176.0	175.0	173.9	175.0	176.0	177.1
105°	223.3	222.0	221.4	220.9	219.8	218.8	217.7	216.7	217.7	218.8	219.8
107.5°	269.6	268.5	268.0	267.5	266.4	265.3	264.3	263.2	264.3	265.3	266.4
110°	317.4	316.8	316.5	316.0	314.9	313.8	312.8	311.7	312.8	313.8	314.9

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.3	363.4	363.0	362.8	362.4	361.9	361.5	361.1	361.5	361.9	362.4
115°	414.0	413.6	413.4	413.0	412.1	411.3	410.4	409.6	410.4	411.3	412.1
117.5°	460.5	460.1	459.9	459.8	459.6	459.4	459.2	459.0	459.2	459.4	459.6
120°	509.7	509.5	509.4	508.9	507.8	506.7	505.7	504.6	505.7	506.7	507.8
122.5°	555.9	555.3	555.0	554.9	554.7	554.4	554.2	554.0	554.2	554.4	554.7
125°	603.7	603.5	603.4	602.8	601.5	600.2	599.0	597.7	599.0	600.2	601.5
127.5°	649.4	649.2	649.1	648.8	648.1	647.5	646.8	646.2	646.8	647.5	648.1
130°	694.3	693.9	693.7	693.2	692.1	691.1	690.0	689.0	690.0	691.1	692.1
132.5°	740.0	740.2	740.3	739.3	737.4	735.5	733.6	731.7	733.6	735.5	737.4
135°	783.3	783.1	783.0	782.4	781.1	779.8	778.6	777.3	778.6	779.8	781.1
137.5°	826.4	826.0	825.8	825.2	823.9	822.6	821.4	820.1	821.4	822.6	823.9
140°	866.7	866.0	865.7	865.2	864.1	863.1	862.0	861.0	862.0	863.1	864.1
142.5°	906.9	906.0	905.6	905.2	904.3	903.5	902.6	901.8	902.6	903.5	904.3
145°	946.5	945.9	945.6	945.2	944.3	943.4	942.6	941.7	942.6	943.4	944.3
147.5°	982.3	981.9	981.7	981.4	980.7	980.1	979.4	978.8	979.4	980.1	980.7
150°	1016.2	1015.3	1014.9	1015.0	1015.2	1015.5	1015.7	1015.9	1015.7	1015.5	1015.2
152.5°	1048.5	1048.3	1048.2	1048.0	1047.6	1047.1	1046.7	1046.3	1046.7	1047.1	1047.6
155°	1077.9	1077.7	1077.6	1077.6	1077.6	1077.6	1077.6	1077.6	1077.6	1077.6	1077.6
157.5°	1104.6	1104.4	1104.3	1104.5	1104.9	1105.4	1105.8	1106.2	1105.8	1105.4	1104.9
160°	1128.3	1128.1	1128.0	1128.3	1129.0	1129.6	1130.3	1130.9	1130.3	1129.6	1129.0
162.5°	1150.8	1150.8	1150.8	1151.0	1151.4	1151.9	1152.3	1152.7	1152.3	1151.9	1151.4
165°	1170.1	1169.9	1169.8	1170.0	1170.4	1170.9	1171.3	1171.7	1171.3	1170.9	1170.4
167.5°	1185.0	1185.0	1185.0	1185.4	1186.3	1187.1	1188.0	1188.8	1188.0	1187.1	1186.3
170°	1198.3	1198.3	1198.3	1198.7	1199.6	1200.4	1201.3	1202.1	1201.3	1200.4	1199.6
172.5°	1207.8	1207.8	1207.8	1208.2	1209.1	1209.9	1210.8	1211.6	1210.8	1209.9	1209.1
175°	1214.5	1214.5	1214.5	1214.9	1215.8	1216.6	1217.5	1218.3	1217.5	1216.6	1215.8
177.5°	1218.9	1219.1	1219.2	1219.6	1220.5	1221.3	1222.2	1223.0	1222.2	1221.3	1220.5
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	502.7	501.8	499.6	498.3	494.0	488.8	487.1	482.8	484.5	481.5	481.5
5°	489.3	485.4	482.8	478.9	470.7	465.0	459.0	456.0	454.2	452.1	450.3
7.5°	472.0	468.9	466.3	459.0	449.9	442.1	434.8	431.7	426.1	422.2	420.5
10°	456.8	452.5	446.4	437.8	428.3	418.3	411.8	405.3	401.0	398.9	394.1
12.5°	441.2	436.1	429.6	417.0	406.6	400.6	388.9	382.8	380.7	379.0	373.3
15°	425.2	419.6	411.8	400.1	391.1	376.8	369.9	365.1	359.9	359.5	355.2
17.5°	411.0	404.0	397.6	383.3	372.0	359.5	355.6	350.4	345.6	340.5	338.3
20°	392.8	386.3	381.5	366.0	353.4	345.6	339.2	334.8	331.8	326.6	325.7
22.5°	376.4	369.4	362.9	351.3	340.5	330.5	322.7	318.0	316.7	314.5	310.6
25°	360.3	353.4	345.6	334.8	323.6	316.7	309.7	306.7	304.1	300.7	297.6
27.5°	346.9	340.5	333.1	319.7	310.2	305.0	297.6	294.2	290.7	289.0	287.7
30°	330.9	323.6	318.0	307.6	297.2	290.3	285.1	282.1	279.0	277.3	276.4
32.5°	315.4	308.4	304.5	293.3	285.1	276.9	273.0	270.8	269.1	267.3	265.6
35°	302.8	295.9	289.8	279.5	271.2	265.6	262.6	259.1	257.8	256.1	256.1
37.5°	287.2	282.1	276.0	266.0	258.7	254.4	251.8	247.4	247.0	246.1	244.8
40°	273.8	268.6	263.0	254.4	247.9	242.7	239.2	237.1	235.8	234.9	234.0
42.5°	259.6	253.9	251.3	241.4	235.8	230.6	228.8	226.7	226.2	224.5	222.4
45°	245.7	241.0	235.8	228.4	223.7	219.3	216.7	215.0	212.8	212.4	211.1
47.5°	233.6	228.0	223.2	216.3	211.1	207.6	205.5	203.3	201.6	200.3	199.0
50°	218.0	213.7	209.8	202.5	198.1	194.7	191.6	189.9	188.2	188.2	188.2
52.5°	202.9	199.0	195.5	190.3	185.1	182.1	178.7	177.4	176.5	175.2	176.5
55°	188.2	184.3	180.8	176.9	170.9	168.3	164.8	163.5	164.0	164.0	165.3
57.5°	172.6	169.6	167.4	162.7	157.0	154.4	152.3	151.0	151.0	152.7	153.1
60°	157.5	154.4	150.5	146.2	142.8	139.7	138.4	138.9	138.9	139.7	141.9
62.5°	140.6	138.9	136.7	130.6	128.5	126.3	124.6	125.9	125.5	127.6	130.6
65°	125.0	123.3	120.3	117.2	114.6	112.5	112.0	112.5	113.3	115.5	119.0
67.5°	107.7	107.7	105.1	102.5	100.4	98.2	98.6	99.1	99.9	102.5	107.7
70°	93.4	91.7	89.1	87.4	85.7	84.8	83.9	85.7	88.2	90.0	93.9
72.5°	77.9	76.6	74.4	72.7	72.2	71.4	70.9	71.8	74.4	77.4	81.8
75°	61.4	61.9	60.6	59.3	59.3	58.0	58.8	58.8	61.4	64.5	67.9
77.5°	47.6	47.2	46.7	45.9	45.4	45.4	45.4	46.3	48.9	50.6	54.1
80°	33.7	34.2	32.9	33.3	32.9	33.3	33.3	35.0	36.3	38.5	41.1
82.5°	22.5	22.5	21.6	22.1	22.1	22.1	22.5	23.4	25.1	26.8	28.6
85°	12.5	13.0	12.1	13.0	13.0	13.0	13.4	13.8	15.1	15.6	17.3
87.5°	4.8	5.6	5.6	4.8	5.2	5.6	6.1	5.6	6.5	7.4	7.8
90°	7.8	8.6	9.3	10.8	12.3	13.7	15.2	16.3	17.3	18.4	19.5
92.5°	32.8	33.3	34.2	36.1	38.0	39.9	41.8	43.3	44.8	46.3	47.8
95°	63.5	63.7	64.8	66.9	69.0	71.1	73.2	74.7	76.1	77.6	79.1
97.5°	95.9	96.0	97.5	100.4	103.4	106.3	109.3	110.6	111.8	113.1	114.4
100°	133.0	133.0	134.4	137.1	139.9	142.6	145.4	147.3	149.2	151.1	153.0
102.5°	178.2	178.7	179.2	180.3	181.3	182.4	183.4	185.5	187.6	189.7	191.8
105°	220.9	221.4	222.0	223.3	224.6	225.8	227.1	228.4	229.6	230.9	232.2
107.5°	267.5	268.0	268.5	269.6	270.6	271.7	272.7	273.3	274.0	274.6	275.3
110°	316.0	316.5	316.8	317.4	318.1	318.7	319.3	319.9	320.6	321.2	321.9

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	362.8	363.0	363.4	364.3	365.1	366.0	366.8	367.0	367.2	367.5	367.7
115°	413.0	413.4	413.6	414.0	414.5	414.9	415.3	415.1	414.9	414.6	414.4
117.5°	459.8	459.9	460.1	460.5	461.0	461.4	461.8	462.0	462.2	462.5	462.7
120°	508.9	509.4	509.5	509.7	509.9	510.1	510.3	510.3	510.3	510.3	510.3
122.5°	554.9	555.0	555.3	555.9	556.6	557.2	557.8	557.6	557.4	557.2	557.0
125°	602.8	603.4	603.5	603.7	604.0	604.2	604.4	604.0	603.6	603.1	602.7
127.5°	648.8	649.1	649.2	649.4	649.6	649.8	650.0	649.8	649.6	649.4	649.2
130°	693.2	693.7	693.9	694.3	694.8	695.2	695.6	695.4	695.2	695.0	694.8
132.5°	739.3	740.3	740.2	740.0	739.7	739.5	739.3	739.1	738.9	738.7	738.5
135°	782.4	783.0	783.1	783.3	783.6	783.8	784.0	784.0	784.0	784.0	784.0
137.5°	825.2	825.8	826.0	826.4	826.9	827.3	827.7	827.9	828.1	828.4	828.6
140°	865.2	865.7	866.0	866.7	867.3	868.0	868.6	869.0	869.4	869.9	870.3
142.5°	905.2	905.6	906.0	906.9	907.7	908.6	909.4	909.6	909.8	910.1	910.3
145°	945.2	945.6	945.9	946.5	947.2	947.8	948.4	948.4	948.4	948.4	948.4
147.5°	981.4	981.7	981.9	982.3	982.8	983.2	983.6	984.2	984.8	985.5	986.1
150°	1015.0	1014.9	1015.3	1016.2	1017.0	1017.9	1018.7	1018.7	1018.7	1018.7	1018.7
152.5°	1048.0	1048.2	1048.3	1048.5	1048.7	1048.9	1049.1	1049.7	1050.4	1051.0	1051.7
155°	1077.6	1077.6	1077.7	1077.9	1078.2	1078.4	1078.6	1079.4	1080.3	1081.1	1082.0
157.5°	1104.5	1104.3	1104.4	1104.6	1104.8	1105.0	1105.2	1106.0	1106.9	1107.7	1108.6
160°	1128.3	1128.0	1128.1	1128.3	1128.6	1128.8	1129.0	1129.8	1130.7	1131.5	1132.4
162.5°	1151.0	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1151.9	1152.9	1154.0	1155.1
165°	1170.0	1169.8	1169.9	1170.1	1170.4	1170.6	1170.8	1171.6	1172.5	1173.3	1174.2
167.5°	1185.4	1185.0	1185.0	1185.0	1185.0	1185.0	1185.0	1186.3	1187.5	1188.8	1190.1
170°	1198.7	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1199.6	1200.8	1202.1	1203.4
172.5°	1208.2	1207.8	1207.8	1207.8	1207.8	1207.8	1207.8	1209.1	1210.3	1211.6	1212.9
175°	1214.9	1214.5	1214.5	1214.5	1214.5	1214.5	1214.5	1215.8	1217.0	1218.3	1219.6
177.5°	1219.6	1219.2	1219.1	1218.9	1218.7	1218.5	1218.3	1219.6	1220.8	1222.1	1223.4
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	483.2	480.2	479.7	480.6	478.9	481.5	480.6	481.5	479.3	481.5	480.2
5°	449.9	449.0	447.3	445.1	445.6	446.0	448.2	446.0	447.7	448.2	450.3
7.5°	418.7	417.0	418.3	417.5	413.6	412.7	413.6	414.9	417.5	419.2	420.5
10°	393.7	392.8	391.1	389.8	387.6	386.3	388.0	386.3	389.8	392.8	392.8
12.5°	374.6	371.2	369.0	368.6	363.8	364.7	366.4	367.7	371.6	373.3	373.3
15°	354.7	352.1	351.3	349.5	347.8	349.5	348.7	350.0	351.7	353.4	354.3
17.5°	337.4	337.0	337.4	333.1	334.4	332.2	332.7	334.8	333.5	334.8	337.4
20°	321.8	322.7	321.4	319.7	319.7	317.1	320.1	319.3	319.7	322.3	326.2
22.5°	310.2	309.7	308.4	307.1	305.4	305.8	306.3	305.4	308.9	311.0	311.5
25°	297.6	296.8	296.3	295.0	293.3	295.0	294.6	295.0	295.9	299.4	296.8
27.5°	285.9	284.2	285.1	283.8	283.3	283.8	283.8	284.2	285.1	285.5	285.9
30°	276.0	274.3	273.8	273.0	272.5	273.0	273.8	273.0	276.4	276.0	276.0
32.5°	265.2	263.9	263.0	263.0	262.6	262.2	262.6	263.0	265.6	263.9	265.6
35°	254.8	253.9	253.9	253.1	252.6	252.6	252.6	254.4	253.5	254.8	254.8
37.5°	244.8	244.8	244.4	243.5	243.1	243.5	243.1	244.0	243.5	244.0	244.4
40°	234.5	233.6	233.2	233.2	231.9	230.6	231.9	231.9	232.3	233.6	234.0
42.5°	221.9	222.4	222.4	220.6	220.6	220.6	221.1	221.5	221.5	222.4	222.4
45°	211.1	210.2	210.2	210.2	209.4	209.8	210.7	210.7	210.7	210.7	209.8
47.5°	199.0	199.0	199.4	199.4	200.7	200.3	200.3	199.9	199.0	199.0	199.4
50°	187.7	189.0	189.5	189.5	189.9	190.3	190.3	189.5	189.0	187.7	187.7
52.5°	176.9	177.8	178.7	180.0	180.8	180.4	180.4	179.5	177.8	177.4	176.9
55°	165.3	166.5	168.3	169.6	170.9	171.3	171.3	169.6	167.8	165.7	165.7
57.5°	154.4	155.7	158.8	160.1	161.8	161.8	160.9	159.6	157.0	155.3	154.0
60°	143.6	145.8	147.9	150.5	152.7	153.1	151.8	150.1	147.1	144.9	143.2
62.5°	131.9	134.1	138.4	141.0	142.8	142.8	142.8	140.6	136.7	133.7	131.1
65°	120.7	122.9	126.7	130.2	131.5	132.8	131.5	129.3	126.3	122.9	120.3
67.5°	109.0	111.6	115.5	118.1	119.8	121.1	120.3	118.5	114.6	109.9	108.1
70°	96.0	97.3	103.0	105.6	108.1	109.0	108.1	105.6	101.7	96.5	94.7
72.5°	83.9	85.2	90.4	92.6	94.7	95.6	94.3	92.6	89.1	84.4	82.2
75°	70.1	72.2	74.8	78.3	80.9	81.8	80.5	79.2	74.8	71.8	70.1
77.5°	55.4	57.5	61.0	64.0	66.6	66.2	64.5	64.9	60.1	56.7	55.4
80°	42.0	43.7	46.3	48.9	50.2	50.2	49.7	48.0	46.3	43.7	41.5
82.5°	29.0	31.1	33.3	35.0	35.0	35.5	34.6	34.2	32.4	30.3	29.8
85°	17.3	17.7	19.5	19.5	21.2	20.3	19.9	21.2	19.5	18.2	17.7
87.5°	7.8	7.4	7.8	7.8	7.4	8.2	8.2	7.8	8.2	7.8	7.8
90°	20.0	20.3	20.9	21.6	22.2	22.8	22.2	21.6	20.9	20.3	20.0
92.5°	48.5	48.7	49.1	49.6	50.0	50.4	50.0	49.6	49.1	48.7	48.5
95°	79.8	80.0	80.4	80.9	81.3	81.7	81.3	80.9	80.4	80.0	79.8
97.5°	115.0	115.1	115.3	115.5	115.7	115.9	115.7	115.5	115.3	115.1	115.0
100°	153.9	154.1	154.5	155.0	155.4	155.8	155.4	155.0	154.5	154.1	153.9
102.5°	192.9	193.2	193.9	194.5	195.2	195.8	195.2	194.5	193.9	193.2	192.9
105°	232.8	233.1	233.8	234.4	235.1	235.7	235.1	234.4	233.8	233.1	232.8
107.5°	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6	275.6
110°	322.2	322.1	321.9	321.6	321.4	321.2	321.4	321.6	321.9	322.1	322.2

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	367.8	367.6	367.2	366.7	366.3	365.9	366.3	366.7	367.2	367.6	367.8
115°	414.3	414.2	414.0	413.8	413.6	413.4	413.6	413.8	414.0	414.2	414.3
117.5°	462.8	462.4	461.5	460.7	459.8	459.0	459.8	460.7	461.5	462.4	462.8
120°	510.3	509.9	509.0	508.2	507.3	506.5	507.3	508.2	509.0	509.9	510.3
122.5°	556.9	556.6	555.9	555.3	554.6	554.0	554.6	555.3	555.9	556.6	556.9
125°	602.5	602.4	602.2	601.9	601.7	601.5	601.7	601.9	602.2	602.4	602.5
127.5°	649.1	648.9	648.5	648.0	647.6	647.2	647.6	648.0	648.5	648.9	649.1
130°	694.7	694.5	694.1	693.6	693.2	692.8	693.2	693.6	694.1	694.5	694.7
132.5°	738.4	738.1	737.4	736.8	736.1	735.5	736.1	736.8	737.4	738.1	738.4
135°	784.0	783.6	782.7	781.9	781.0	780.2	781.0	781.9	782.7	783.6	784.0
137.5°	828.7	828.2	827.1	826.0	825.0	823.9	825.0	826.0	827.1	828.2	828.7
140°	870.5	870.0	868.9	867.8	866.8	865.7	866.8	867.8	868.9	870.0	870.5
142.5°	910.4	909.9	908.8	907.7	906.7	905.6	906.7	907.7	908.8	909.9	910.4
145°	948.4	948.1	947.5	946.8	946.2	945.6	946.2	946.8	947.5	948.1	948.4
147.5°	986.4	985.6	983.9	982.2	980.5	978.8	980.5	982.2	983.9	985.6	986.4
150°	1018.7	1018.5	1018.1	1017.6	1017.2	1016.8	1017.2	1017.6	1018.1	1018.5	1018.7
152.5°	1052.0	1051.6	1050.7	1049.9	1049.0	1048.2	1049.0	1049.9	1050.7	1051.6	1052.0
155°	1082.4	1081.9	1080.8	1079.7	1078.7	1077.6	1078.7	1079.7	1080.8	1081.9	1082.4
157.5°	1109.0	1108.3	1106.8	1105.3	1103.9	1102.4	1103.9	1105.3	1106.8	1108.3	1109.0
160°	1132.8	1132.3	1131.2	1130.1	1129.1	1128.0	1129.1	1130.1	1131.2	1132.3	1132.8
162.5°	1155.6	1155.0	1153.7	1152.4	1151.2	1149.9	1151.2	1152.4	1153.7	1155.0	1155.6
165°	1174.6	1174.0	1172.7	1171.4	1170.2	1168.9	1170.2	1171.4	1172.7	1174.0	1174.6
167.5°	1190.7	1190.1	1188.8	1187.5	1186.3	1185.0	1186.3	1187.5	1188.8	1190.1	1190.7
170°	1204.0	1203.3	1201.8	1200.3	1198.9	1197.4	1198.9	1200.3	1201.8	1203.3	1204.0
172.5°	1213.5	1212.9	1211.6	1210.3	1209.1	1207.8	1209.1	1210.3	1211.6	1212.9	1213.5
175°	1220.2	1219.5	1218.0	1216.5	1215.0	1213.5	1215.0	1216.5	1218.0	1219.5	1220.2
177.5°	1224.0	1223.3	1221.8	1220.3	1218.8	1217.3	1218.8	1220.3	1221.8	1223.3	1224.0
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	484.1	481.5	484.5	480.6	481.5	486.2	485.8	490.1	492.7	492.3	494.5
5°	452.1	452.1	453.4	452.9	457.3	461.1	466.3	470.7	475.4	478.0	481.0
7.5°	420.5	424.8	425.7	427.8	433.0	439.5	444.7	451.2	458.1	462.9	466.3
10°	394.5	398.0	401.4	403.2	408.8	417.5	424.8	435.2	443.8	449.0	453.8
12.5°	371.6	375.5	377.2	385.0	388.9	394.5	404.9	416.2	425.7	431.3	435.2
15°	355.2	357.3	361.2	366.0	369.9	376.8	385.4	398.0	407.1	411.8	425.2
17.5°	341.3	343.9	346.1	348.2	354.3	361.6	369.9	380.7	392.4	400.6	407.5
20°	327.0	328.3	330.9	334.4	338.7	345.6	353.0	364.2	374.6	381.1	390.2
22.5°	310.2	314.1	316.7	319.3	324.0	331.8	338.7	346.9	359.9	367.3	376.8
25°	300.2	301.9	303.7	306.7	310.2	317.1	324.9	333.5	343.9	351.7	359.9
27.5°	287.2	289.8	292.0	295.9	298.1	303.7	311.0	319.7	332.2	338.7	345.6
30°	276.4	279.0	280.8	282.5	285.5	291.6	298.5	305.4	317.1	325.3	332.2
32.5°	265.6	268.2	270.4	271.7	274.7	278.6	284.2	292.9	302.8	308.4	317.5
35°	256.1	256.1	258.7	260.4	263.0	266.5	271.7	278.2	288.5	295.9	304.1
37.5°	245.3	245.7	247.9	249.2	251.8	255.2	260.4	266.5	275.1	280.8	289.0
40°	234.0	235.3	236.2	238.4	241.4	242.7	247.9	254.8	263.4	268.6	275.6
42.5°	222.8	223.7	225.8	227.5	230.1	232.3	235.8	242.3	248.7	256.5	262.2
45°	210.2	212.4	213.7	216.7	218.0	220.2	223.7	228.8	236.6	241.4	247.9
47.5°	199.4	200.3	201.2	205.0	207.6	208.9	212.4	215.4	223.7	228.0	234.0
50°	187.7	187.7	189.0	190.8	193.8	196.4	199.4	202.9	209.4	213.7	219.8
52.5°	176.9	175.6	176.5	177.4	180.4	183.0	186.0	190.8	196.8	199.4	204.6
55°	165.3	163.1	164.4	165.7	166.5	170.0	173.5	176.5	181.3	185.1	189.9
57.5°	152.7	152.3	151.4	151.8	154.0	156.2	158.8	162.7	168.3	171.3	173.9
60°	141.5	138.9	138.0	138.9	140.2	141.5	144.9	148.4	153.1	156.2	159.2
62.5°	129.8	127.2	125.5	124.2	125.5	128.5	130.6	133.2	137.1	140.6	143.2
65°	118.5	114.6	112.9	112.0	111.6	113.8	115.5	119.0	122.4	123.7	126.7
67.5°	106.0	102.5	100.4	99.1	99.1	99.1	100.8	104.3	107.7	108.1	111.2
70°	93.4	89.5	87.4	85.7	84.8	85.7	87.8	88.2	91.3	92.1	93.9
72.5°	80.0	76.6	74.0	71.8	72.2	73.1	73.1	74.0	75.7	77.9	77.9
75°	67.5	62.7	61.4	59.7	58.8	58.8	58.8	60.6	61.9	63.6	63.2
77.5°	53.2	50.6	48.0	47.2	45.9	45.4	46.3	46.3	47.2	48.5	48.9
80°	41.1	38.1	36.3	35.5	33.7	33.3	33.7	33.7	35.0	34.6	35.0
82.5°	28.6	26.4	25.1	23.8	22.9	23.4	22.9	22.9	23.4	22.9	22.9
85°	16.4	16.0	15.1	14.7	14.3	13.4	14.3	13.8	13.4	13.0	13.8
87.5°	7.8	7.4	7.4	6.5	6.5	6.1	6.5	6.5	6.1	6.1	6.1
90°	19.5	18.4	17.3	16.3	15.2	13.7	12.3	10.8	9.3	8.6	7.8
92.5°	47.8	46.3	44.8	43.3	41.8	39.9	38.0	36.1	34.2	33.3	32.8
95°	79.1	77.6	76.1	74.7	73.2	71.1	69.0	66.9	64.8	63.7	63.5
97.5°	114.4	113.1	111.8	110.6	109.3	106.3	103.4	100.4	97.5	96.0	95.9
100°	153.0	151.1	149.2	147.3	145.4	142.6	139.9	137.1	134.4	133.0	133.0
102.5°	191.8	189.7	187.6	185.5	183.4	182.4	181.3	180.3	179.2	178.7	178.2
105°	232.2	230.9	229.6	228.4	227.1	225.8	224.6	223.3	222.0	221.4	220.9
107.5°	275.3	274.6	274.0	273.3	272.7	271.7	270.6	269.6	268.5	268.0	267.5
110°	321.9	321.2	320.6	319.9	319.3	318.7	318.1	317.4	316.8	316.5	316.0

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	367.7	367.5	367.2	367.0	366.8	366.0	365.1	364.3	363.4	363.0	362.8
115°	414.4	414.6	414.9	415.1	415.3	414.9	414.5	414.0	413.6	413.4	413.0
117.5°	462.7	462.5	462.2	462.0	461.8	461.4	461.0	460.5	460.1	459.9	459.8
120°	510.3	510.3	510.3	510.3	510.3	510.1	509.9	509.7	509.5	509.4	508.9
122.5°	557.0	557.2	557.4	557.6	557.8	557.2	556.6	555.9	555.3	555.0	554.9
125°	602.7	603.1	603.6	604.0	604.4	604.2	604.0	603.7	603.5	603.4	602.8
127.5°	649.2	649.4	649.6	649.8	650.0	649.8	649.6	649.4	649.2	649.1	648.8
130°	694.8	695.0	695.2	695.4	695.6	695.2	694.8	694.3	693.9	693.7	693.2
132.5°	738.5	738.7	738.9	739.1	739.3	739.5	739.7	740.0	740.2	740.3	739.3
135°	784.0	784.0	784.0	784.0	784.0	783.8	783.6	783.3	783.1	783.0	782.4
137.5°	828.6	828.4	828.1	827.9	827.7	827.3	826.9	826.4	826.0	825.8	825.2
140°	870.3	869.9	869.4	869.0	868.6	868.0	867.3	866.7	866.0	865.7	865.2
142.5°	910.3	910.1	909.8	909.6	909.4	908.6	907.7	906.9	906.0	905.6	905.2
145°	948.4	948.4	948.4	948.4	948.4	947.8	947.2	946.5	945.9	945.6	945.2
147.5°	986.1	985.5	984.8	984.2	983.6	983.2	982.8	982.3	981.9	981.7	981.4
150°	1018.7	1018.7	1018.7	1018.7	1018.7	1017.9	1017.0	1016.2	1015.3	1014.9	1015.0
152.5°	1051.7	1051.0	1050.4	1049.7	1049.1	1048.9	1048.7	1048.5	1048.3	1048.2	1048.0
155°	1082.0	1081.1	1080.3	1079.4	1078.6	1078.4	1078.2	1077.9	1077.7	1077.6	1077.6
157.5°	1108.6	1107.7	1106.9	1106.0	1105.2	1105.0	1104.8	1104.6	1104.4	1104.3	1104.5
160°	1132.4	1131.5	1130.7	1129.8	1129.0	1128.8	1128.6	1128.3	1128.1	1128.0	1128.3
162.5°	1155.1	1154.0	1152.9	1151.9	1150.8	1150.8	1150.8	1150.8	1150.8	1150.8	1151.0
165°	1174.2	1173.3	1172.5	1171.6	1170.8	1170.6	1170.4	1170.1	1169.9	1169.8	1170.0
167.5°	1190.1	1188.8	1187.5	1186.3	1185.0	1185.0	1185.0	1185.0	1185.0	1185.0	1185.4
170°	1203.4	1202.1	1200.8	1199.6	1198.3	1198.3	1198.3	1198.3	1198.3	1198.3	1198.7
172.5°	1212.9	1211.6	1210.3	1209.1	1207.8	1207.8	1207.8	1207.8	1207.8	1207.8	1208.2
175°	1219.6	1218.3	1217.0	1215.8	1214.5	1214.5	1214.5	1214.5	1214.5	1214.5	1214.9
177.5°	1223.4	1222.1	1220.8	1219.6	1218.3	1218.5	1218.7	1218.9	1219.1	1219.2	1219.6
180°	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1	1221.1

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.6	509.6	509.6	509.6
2.5°	497.5	501.8	504.8	510.5
5°	486.2	494.0	501.4	509.2
7.5°	475.0	484.1	495.8	505.7
10°	462.4	474.1	488.0	501.4
12.5°	449.9	463.7	478.9	496.6
15°	434.8	452.5	470.2	489.3
17.5°	421.3	439.5	458.5	482.3
20°	406.2	426.1	446.9	471.1
22.5°	392.8	414.9	436.5	462.0
25°	377.7	399.3	423.1	450.3
27.5°	365.1	385.0	408.4	437.8
30°	350.0	371.6	395.0	424.4
32.5°	335.7	356.5	381.1	410.1
35°	321.0	342.2	364.2	391.9
37.5°	307.1	325.3	347.4	373.8
40°	291.6	311.5	331.4	352.1
42.5°	277.3	295.5	314.1	330.5
45°	261.3	276.9	294.6	308.0
47.5°	246.6	260.4	274.3	284.6
50°	231.9	242.7	253.1	262.2
52.5°	214.6	226.7	232.3	237.9
55°	199.0	205.9	211.1	216.7
57.5°	183.9	186.9	189.5	194.7
60°	164.0	167.4	170.4	174.3
62.5°	146.6	148.4	149.2	153.1
65°	130.2	129.8	131.9	134.1
67.5°	112.5	112.0	114.2	115.1
70°	95.2	94.7	95.2	97.3
72.5°	78.7	78.7	79.2	80.0
75°	63.6	63.6	64.0	64.9
77.5°	48.0	48.9	48.5	50.2
80°	35.0	34.2	35.0	35.9
82.5°	22.9	23.8	23.8	22.9
85°	13.0	13.0	13.0	13.0
87.5°	5.6	5.6	6.1	6.5
90°	6.1	4.4	2.7	1.0
92.5°	31.7	30.6	29.6	28.5
95°	63.1	62.6	62.2	61.8
97.5°	95.7	95.4	95.2	95.0
100°	133.0	133.0	133.0	133.0
102.5°	177.1	176.0	175.0	173.9
105°	219.8	218.8	217.7	216.7
107.5°	266.4	265.3	264.3	263.2
110°	314.9	313.8	312.8	311.7

TEST NUMBER: P1027785

CATALOG NUMBER: S125DIP-B375D1090UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	362.4	361.9	361.5	361.1
115°	412.1	411.3	410.4	409.6
117.5°	459.6	459.4	459.2	459.0
120°	507.8	506.7	505.7	504.6
122.5°	554.7	554.4	554.2	554.0
125°	601.5	600.2	599.0	597.7
127.5°	648.1	647.5	646.8	646.2
130°	692.1	691.1	690.0	689.0
132.5°	737.4	735.5	733.6	731.7
135°	781.1	779.8	778.6	777.3
137.5°	823.9	822.6	821.4	820.1
140°	864.1	863.1	862.0	861.0
142.5°	904.3	903.5	902.6	901.8
145°	944.3	943.4	942.6	941.7
147.5°	980.7	980.1	979.4	978.8
150°	1015.2	1015.5	1015.7	1015.9
152.5°	1047.6	1047.1	1046.7	1046.3
155°	1077.6	1077.6	1077.6	1077.6
157.5°	1104.9	1105.4	1105.8	1106.2
160°	1129.0	1129.6	1130.3	1130.9
162.5°	1151.4	1151.9	1152.3	1152.7
165°	1170.4	1170.9	1171.3	1171.7
167.5°	1186.3	1187.1	1188.0	1188.8
170°	1199.6	1200.4	1201.3	1202.1
172.5°	1209.1	1209.9	1210.8	1211.6
175°	1215.8	1216.6	1217.5	1218.3
177.5°	1220.5	1221.3	1222.2	1223.0
180°	1221.1	1221.1	1221.1	1221.1

(END OF REPORT)