

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027830

Luminaire Tested: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027830
REPORT IS A COMBINATION OF REPORTS P1001931 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D1270UB50-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5445.0 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26			
1	93	89	85	81	83	79	76	73	62	60	58	45	44	43	31	30	29	23			
2	84	77	72	67	75	69	64	60	54	51	48	40	38	36	27	26	25	19			
3	77	68	61	56	68	61	55	50	48	44	40	35	33	31	24	23	21	16			
4	70	60	53	47	63	54	48	43	42	38	34	32	29	26	22	20	18	14			
5	64	53	46	40	57	48	41	36	38	33	29	28	25	23	19	17	16	12			
6	59	48	40	34	53	43	36	31	34	29	26	25	22	20	18	16	14	11			
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	10			
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	15	13	11	9			
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8			
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	12	10	9	7			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3265	3265	3265	3265
5°	3268	3704	3270	2810
10°	3248	4221	3242	2412
15°	3224	4577	3204	2179
20°	3183	5016	3154	1990
25°	3147	5748	3089	1877
30°	3095	6063	3041	1776
35°	3013	4860	2950	1693
40°	2884	3359	2842	1608
45°	2723	2501	2692	1535
50°	2538	2059	2495	1478
55°	2337	1756	2319	1428
60°	2141	1503	2104	1389
65°	1930	1298	1898	1333
70°	1706	1078	1683	1234
75°	1470	834	1449	1072
80°	1160	564	1118	788
85°	743	282	715	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4987 cd/sqm

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	0.9
10°-20°	146.1	2.7
20°-30°	237.3	4.4
30°-40°	290.0	5.3
40°-50°	263.1	4.8
50°-60°	209.5	3.8
60°-70°	145.9	2.7
70°-80°	77.7	1.4
80°-90°	21.5	0.4
90°-100°	95.4	1.8
100°-110°	283.5	5.2
110°-120°	480.8	8.8
120°-130°	632.9	11.6
130°-140°	709.2	13.0
140°-150°	695.1	12.8
150°-160°	583.9	10.7
160°-170°	388.1	7.1
170°-180°	135.8	2.5
0°-30°	432.4	7.9
0°-40°	722.4	13.3
0°-60°	1195.0	21.9
0°-90°	1440.2	26.5
90°-120°	859.7	15.8
90°-150°	2896.9	53.2
90°-180°	4005.0	73.6
0°-180°	5445.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	510	510	510	510	510	
5°	509	588	510	446	509	48
15°	489	734	486	350	489	138
25°	450	903	442	295	450	207
35°	392	725	384	253	392	245
45°	308	342	304	210	308	237
55°	217	211	215	171	217	194
65°	134	129	132	133	134	133
75°	65	64	64	82	65	69
85°	13	14	12	20	13	16
90°	1	27	1	27	1	6
95°	73	96	73	96	73	76
105°	255	277	255	277	255	271
115°	481	486	481	486	481	476
125°	702	707	702	707	702	629
135°	913	917	913	917	913	704
145°	1107	1111	1107	1111	1107	692
155°	1266	1266	1266	1266	1266	583
165°	1377	1374	1377	1374	1377	388
175°	1432	1426	1432	1426	1432	136
180°	1435	1435	1435	1435	1435	

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	510.5	513.5	516.9	519.5	523.9	525.2	527.3	528.6	529.9	531.2	532.1
5°	509.2	516.5	523.0	527.8	536.0	539.0	542.9	547.7	553.3	558.0	561.1
7.5°	505.7	517.4	526.0	535.5	546.8	554.2	558.0	568.0	577.1	584.0	593.1
10°	501.4	515.2	528.6	542.9	558.9	567.1	574.9	588.8	601.3	612.6	621.6
12.5°	496.6	513.5	529.5	548.1	569.7	579.7	584.9	608.7	624.2	630.3	648.0
15°	489.3	509.2	532.1	555.0	573.2	584.9	599.1	618.2	633.7	647.2	661.4
17.5°	482.3	504.0	527.3	552.9	579.2	594.4	605.2	622.1	638.9	656.2	669.7
20°	471.1	499.2	523.0	550.3	581.4	592.2	603.5	623.4	641.5	660.1	677.0
22.5°	462.0	488.8	521.3	547.2	573.6	584.4	598.3	619.0	640.7	661.9	686.5
25°	450.3	480.2	508.3	536.0	563.2	574.9	587.5	614.3	636.8	664.0	691.3
27.5°	437.8	468.5	496.6	521.7	547.2	563.2	576.6	604.8	634.6	664.5	699.9
30°	424.4	453.4	480.2	504.8	533.0	549.4	562.8	595.7	629.0	667.1	709.5
32.5°	410.1	437.4	460.3	485.4	515.2	530.4	548.5	584.4	623.8	669.2	722.4
35°	391.9	417.9	438.2	463.7	493.6	513.1	532.1	572.3	618.2	668.8	729.8
37.5°	373.8	394.1	413.6	440.8	475.4	493.2	513.1	557.2	609.5	667.5	732.8
40°	352.1	372.0	388.9	416.6	452.9	473.3	494.0	540.3	599.6	662.7	722.0
42.5°	330.5	347.4	366.0	395.0	430.0	451.6	473.7	525.2	586.6	648.9	692.1
45°	308.0	321.0	341.3	367.7	404.9	425.7	450.8	506.6	568.4	623.8	645.4
47.5°	284.6	297.6	316.7	342.2	379.0	403.6	427.4	483.2	545.5	588.3	588.3
50°	262.2	272.5	291.1	316.7	353.9	376.4	400.6	459.8	510.0	541.6	513.5
52.5°	237.9	249.6	265.2	292.0	328.8	349.1	375.5	426.1	473.7	486.7	443.4
55°	216.7	226.2	241.0	266.5	300.7	321.8	344.3	392.8	433.0	432.2	385.9
57.5°	194.7	202.5	218.0	241.4	273.0	292.0	314.5	356.5	389.3	377.7	334.0
60°	174.3	180.0	195.1	214.1	244.4	262.2	283.8	318.0	343.0	326.6	282.5
62.5°	153.1	159.6	171.7	190.3	217.2	231.4	247.4	282.1	298.1	283.3	238.4
65°	134.1	139.3	150.1	165.7	189.9	202.9	216.7	245.3	260.4	239.2	202.0
67.5°	115.1	121.1	128.9	142.8	161.8	173.9	186.0	210.7	217.6	198.6	167.4
70°	97.3	102.5	109.9	119.8	135.8	146.6	155.7	176.1	180.8	163.1	138.4
72.5°	80.0	83.5	89.5	97.8	112.5	118.5	128.0	141.9	147.9	131.9	114.2
75°	64.9	67.5	71.4	77.4	87.4	93.9	101.7	114.6	114.2	103.0	90.4
77.5°	50.2	50.6	54.9	60.6	66.6	72.2	76.1	85.2	86.1	79.2	68.8
80°	35.9	37.2	38.9	43.3	48.5	50.6	55.4	61.0	61.9	56.7	49.7
82.5°	22.9	23.8	25.1	27.7	31.1	33.7	36.3	38.5	40.7	37.6	32.0
85°	13.0	13.4	14.7	15.6	17.3	18.6	20.8	22.9	22.5	20.3	18.6
87.5°	6.5	6.5	6.5	7.4	8.2	8.2	9.1	9.5	9.9	9.1	8.2
90°	1.1	3.1	5.1	7.1	9.1	10.1	11.0	12.7	14.4	16.2	17.9
92.5°	33.5	34.7	36.0	37.2	38.5	39.1	40.2	42.4	44.7	46.9	49.1
95°	72.6	73.1	73.6	74.1	74.6	74.8	76.0	78.5	81.0	83.5	86.0
97.5°	111.7	111.9	112.2	112.4	112.7	112.8	114.5	118.0	121.5	124.9	128.4
100°	156.3	156.3	156.3	156.3	156.3	156.3	157.9	161.2	164.4	167.7	170.9
102.5°	204.4	205.6	206.8	208.1	209.3	209.9	210.5	211.8	213.0	214.3	215.5
105°	254.6	255.8	257.1	258.3	259.6	260.2	260.9	262.4	263.9	265.4	266.9
107.5°	309.3	310.5	311.8	313.0	314.3	314.9	315.5	316.8	318.0	319.3	320.5
110°	366.3	367.5	368.8	370.0	371.3	371.9	372.3	373.0	373.7	374.5	375.2

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	424.3	424.8	425.3	425.8	426.3	426.6	427.1	428.1	429.0	430.0	431.0
115°	481.3	482.3	483.3	484.3	485.3	485.8	486.0	486.5	487.0	487.5	488.0
117.5°	539.4	539.6	539.9	540.1	540.4	540.5	540.7	541.2	541.7	542.2	542.7
120°	593.0	594.2	595.4	596.7	597.9	598.5	598.6	598.9	599.2	599.4	599.7
122.5°	651.0	651.2	651.5	651.7	652.0	652.1	652.5	653.2	654.0	654.7	655.5
125°	702.4	703.9	705.4	706.9	708.4	709.1	709.2	709.5	709.7	710.0	710.2
127.5°	759.3	760.1	760.8	761.6	762.3	762.7	762.8	763.1	763.3	763.6	763.8
130°	809.6	810.8	812.1	813.3	814.6	815.2	815.4	815.9	816.4	816.9	817.4
132.5°	859.8	862.0	864.3	866.5	868.8	869.9	869.8	869.5	869.3	869.0	868.8
135°	913.4	914.9	916.4	917.9	919.4	920.1	920.2	920.5	920.8	921.0	921.3
137.5°	963.7	965.2	966.7	968.2	969.7	970.4	970.6	971.1	971.6	972.1	972.6
140°	1011.7	1012.9	1014.2	1015.4	1016.7	1017.3	1017.7	1018.4	1019.1	1019.9	1020.6
142.5°	1059.7	1060.7	1061.7	1062.7	1063.7	1064.2	1064.7	1065.7	1066.7	1067.7	1068.7
145°	1106.6	1107.6	1108.6	1109.6	1110.6	1111.1	1111.5	1112.2	1112.9	1113.7	1114.4
147.5°	1150.2	1150.9	1151.7	1152.4	1153.1	1153.5	1153.8	1154.3	1154.8	1155.3	1155.8
150°	1193.7	1193.5	1193.2	1193.0	1192.7	1192.6	1193.1	1194.1	1195.1	1196.1	1197.1
152.5°	1229.5	1230.0	1230.5	1231.0	1231.5	1231.7	1231.8	1232.1	1232.3	1232.6	1232.8
155°	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.4	1266.7	1266.9	1267.2	1267.4
157.5°	1299.8	1299.3	1298.8	1298.3	1297.8	1297.6	1297.7	1298.0	1298.2	1298.5	1298.7
160°	1328.8	1328.1	1327.3	1326.6	1325.9	1325.5	1325.6	1325.9	1326.1	1326.4	1326.6
162.5°	1354.5	1354.0	1353.5	1353.0	1352.5	1352.3	1352.3	1352.3	1352.3	1352.3	1352.3
165°	1376.9	1376.4	1375.9	1375.4	1374.9	1374.6	1374.7	1375.0	1375.2	1375.5	1375.7
167.5°	1397.0	1396.0	1395.0	1394.0	1393.0	1392.5	1392.5	1392.5	1392.5	1392.5	1392.5
170°	1412.6	1411.6	1410.6	1409.6	1408.6	1408.1	1408.1	1408.1	1408.1	1408.1	1408.1
172.5°	1423.8	1422.8	1421.8	1420.8	1419.8	1419.3	1419.3	1419.3	1419.3	1419.3	1419.3
175°	1431.6	1430.6	1429.6	1428.6	1427.6	1427.1	1427.1	1427.1	1427.1	1427.1	1427.1
177.5°	1437.2	1436.2	1435.2	1434.2	1433.2	1432.7	1432.6	1432.3	1432.1	1431.8	1431.6
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	533.0	536.0	538.6	540.7	542.5	545.1	543.3	543.8	544.6	546.4	546.4
5°	567.6	572.3	574.9	583.6	585.7	585.3	584.0	590.9	590.5	587.9	587.5
7.5°	601.3	609.5	616.9	623.8	626.0	631.6	632.9	635.9	635.0	639.4	637.2
10°	632.0	645.0	651.9	662.3	664.9	667.5	671.0	672.7	676.6	676.1	676.1
12.5°	655.8	671.4	680.5	683.1	693.0	696.0	699.1	704.7	703.4	703.8	706.4
15°	674.4	689.6	697.3	709.5	716.4	719.8	725.0	731.1	730.2	734.1	733.2
17.5°	688.3	702.5	716.8	735.0	735.4	744.5	756.6	759.2	764.8	760.9	760.9
20°	699.5	718.5	738.9	762.2	764.8	770.4	785.2	795.1	801.6	799.4	800.7
22.5°	711.6	738.9	762.7	786.0	798.6	808.5	822.8	838.4	844.0	847.4	846.6
25°	727.2	755.7	790.8	823.2	836.2	855.2	874.3	889.4	893.7	903.3	894.6
27.5°	743.2	783.4	827.1	865.2	881.6	897.2	920.1	931.4	937.0	941.3	938.3
30°	756.6	812.0	859.6	894.6	906.3	915.4	928.3	930.9	928.8	932.2	936.6
32.5°	777.4	831.4	871.7	888.5	887.2	886.8	876.9	863.0	860.0	851.8	863.0
35°	788.6	831.9	847.4	825.0	815.9	799.4	767.9	747.1	728.9	725.0	725.9
37.5°	782.1	799.0	780.4	721.1	706.4	681.3	639.4	610.0	596.5	586.2	599.6
40°	747.1	728.5	677.4	605.2	584.0	560.2	520.8	504.8	485.8	481.9	499.6
42.5°	689.1	632.5	560.2	504.4	482.3	468.9	436.1	420.9	407.5	401.4	411.4
45°	610.4	541.6	468.9	423.1	404.5	388.5	369.0	353.0	344.3	341.7	350.0
47.5°	529.1	456.4	398.4	364.2	344.8	332.7	314.5	305.4	298.5	299.4	300.7
50°	451.2	385.0	340.5	306.3	296.8	287.2	275.1	267.3	263.9	265.2	264.3
52.5°	384.1	330.5	292.9	266.5	262.2	253.1	243.1	236.6	235.3	235.8	237.1
55°	325.3	283.3	253.5	234.5	229.7	223.2	217.2	212.8	209.4	210.7	210.2
57.5°	280.8	244.0	221.1	205.5	202.0	198.1	192.5	190.3	189.0	186.4	188.6
60°	241.4	211.5	191.6	182.1	179.1	176.5	170.4	167.8	167.0	165.7	169.1
62.5°	204.2	183.0	167.8	159.2	156.2	153.6	150.5	148.4	148.8	147.1	148.8
65°	174.8	157.5	146.6	138.9	135.0	133.2	132.8	129.3	128.9	129.3	129.8
67.5°	147.5	132.8	124.6	119.8	116.8	115.1	113.8	111.6	113.3	112.0	112.9
70°	122.9	112.9	104.3	99.5	98.2	98.6	96.5	95.6	96.0	95.2	96.0
72.5°	99.1	90.8	87.4	83.9	82.2	81.8	80.5	79.2	80.5	80.0	80.0
75°	79.2	73.1	69.2	67.1	67.1	66.2	64.0	64.0	64.0	63.6	64.0
77.5°	61.0	55.8	54.1	51.9	51.9	50.6	50.2	50.2	49.3	50.6	49.7
80°	45.4	41.5	38.9	37.6	37.6	37.2	36.3	35.9	36.3	35.9	35.9
82.5°	29.4	27.7	26.4	25.1	24.7	25.1	24.7	23.8	24.2	23.8	24.7
85°	16.9	15.1	15.1	14.3	14.7	13.8	14.3	13.4	13.0	14.3	13.4
87.5°	7.4	6.9	6.9	6.1	6.1	6.1	5.6	6.1	5.6	5.2	5.6
90°	19.1	20.4	21.6	22.9	23.5	23.9	24.6	25.3	26.1	26.8	26.1
92.5°	50.9	52.6	54.4	56.1	57.0	57.2	57.7	58.2	58.7	59.2	58.7
95°	87.7	89.5	91.2	92.9	93.8	94.0	94.5	95.0	95.5	96.0	95.5
97.5°	129.9	131.4	132.9	134.4	135.1	135.2	135.5	135.7	136.0	136.2	136.0
100°	173.1	175.3	177.6	179.8	180.9	181.1	181.6	182.1	182.6	183.1	182.6
102.5°	218.0	220.5	223.0	225.5	226.7	227.1	227.8	228.5	229.3	230.0	229.3
105°	268.4	269.9	271.4	272.9	273.6	274.0	274.7	275.4	276.2	276.9	276.2
107.5°	321.2	322.0	322.7	323.4	323.8	323.8	323.8	323.8	323.8	323.8	323.8
110°	376.0	376.7	377.5	378.2	378.6	378.5	378.2	377.9	377.7	377.4	377.7

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	431.3	431.5	431.8	432.1	432.2	431.9	431.4	430.9	430.4	429.9	430.4
115°	487.8	487.5	487.3	487.0	486.9	486.8	486.5	486.3	486.0	485.8	486.0
117.5°	542.9	543.2	543.4	543.7	543.8	543.3	542.3	541.4	540.4	539.4	540.4
120°	599.7	599.7	599.7	599.7	599.7	599.2	598.2	597.2	596.2	595.2	596.2
122.5°	655.3	655.0	654.8	654.5	654.4	654.0	653.3	652.5	651.8	651.0	651.8
125°	709.7	709.2	708.7	708.2	708.0	707.9	707.6	707.4	707.1	706.9	707.1
127.5°	763.6	763.3	763.1	762.8	762.7	762.5	762.0	761.5	761.0	760.5	761.0
130°	817.2	816.9	816.7	816.4	816.3	816.1	815.6	815.1	814.6	814.1	814.6
132.5°	868.6	868.3	868.1	867.8	867.7	867.3	866.6	865.8	865.1	864.3	865.1
135°	921.3	921.3	921.3	921.3	921.3	920.8	919.8	918.8	917.8	916.8	917.8
137.5°	972.8	973.1	973.3	973.6	973.7	973.1	971.9	970.6	969.4	968.2	969.4
140°	1021.1	1021.6	1022.1	1022.6	1022.9	1022.3	1021.0	1019.8	1018.5	1017.3	1018.5
142.5°	1068.9	1069.2	1069.4	1069.7	1069.8	1069.2	1067.9	1066.7	1065.4	1064.2	1065.4
145°	1114.4	1114.4	1114.4	1114.4	1114.4	1114.0	1113.3	1112.6	1111.8	1111.1	1111.8
147.5°	1156.5	1157.3	1158.0	1158.7	1159.1	1158.1	1156.1	1154.2	1152.2	1150.2	1152.2
150°	1197.1	1197.1	1197.1	1197.1	1197.1	1196.8	1196.3	1195.8	1195.3	1194.8	1195.3
152.5°	1233.6	1234.3	1235.1	1235.8	1236.2	1235.7	1234.7	1233.7	1232.7	1231.7	1232.7
155°	1268.4	1269.4	1270.4	1271.4	1271.9	1271.3	1270.0	1268.8	1267.5	1266.3	1267.5
157.5°	1299.7	1300.7	1301.7	1302.7	1303.2	1302.3	1300.6	1298.8	1297.1	1295.3	1297.1
160°	1327.6	1328.6	1329.6	1330.6	1331.1	1330.5	1329.2	1328.0	1326.7	1325.5	1326.7
162.5°	1353.5	1354.8	1356.0	1357.3	1357.9	1357.2	1355.7	1354.2	1352.7	1351.2	1352.7
165°	1376.7	1377.7	1378.7	1379.7	1380.2	1379.5	1378.0	1376.5	1375.0	1373.5	1375.0
167.5°	1394.0	1395.5	1397.0	1398.5	1399.2	1398.5	1397.0	1395.5	1394.0	1392.5	1394.0
170°	1409.6	1411.1	1412.6	1414.1	1414.8	1413.9	1412.2	1410.5	1408.7	1407.0	1408.7
172.5°	1420.8	1422.3	1423.8	1425.3	1426.0	1425.3	1423.8	1422.3	1420.8	1419.3	1420.8
175°	1428.6	1430.1	1431.6	1433.1	1433.8	1432.9	1431.2	1429.5	1427.7	1426.0	1427.7
177.5°	1433.1	1434.6	1436.1	1437.6	1438.3	1437.4	1435.7	1434.0	1432.2	1430.5	1432.2
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	545.5	542.5	543.3	542.5	540.3	539.0	535.5	531.2	529.5	527.3	526.0
5°	589.2	587.0	586.6	583.1	582.3	577.1	568.4	564.1	558.9	553.7	548.5
7.5°	636.8	634.2	625.5	624.2	625.1	618.6	607.4	598.7	587.9	580.5	570.6
10°	676.1	671.0	663.6	664.0	661.0	652.3	641.1	632.0	616.4	606.9	592.7
12.5°	699.9	695.6	694.7	690.4	687.8	676.6	663.2	651.5	639.8	626.8	616.0
15°	728.9	723.3	719.4	713.3	711.6	699.9	685.2	671.8	658.4	646.3	623.4
17.5°	760.9	754.9	740.2	738.9	728.5	717.2	703.0	683.1	668.8	651.5	634.6
20°	797.3	788.6	769.6	764.8	756.6	738.0	718.5	696.5	673.5	655.8	635.9
22.5°	837.9	822.8	808.9	793.8	787.8	764.8	738.0	711.2	683.5	659.3	635.5
25°	890.7	870.8	851.3	836.2	825.8	796.0	760.1	724.6	692.6	661.0	629.9
27.5°	932.2	914.9	893.7	873.8	860.4	825.0	783.9	738.0	698.2	659.7	626.4
30°	935.3	930.1	917.1	906.3	891.6	853.5	808.1	756.2	706.9	660.1	619.5
32.5°	878.6	889.0	894.6	896.3	893.3	871.2	829.7	772.6	714.6	656.2	613.4
35°	756.6	784.3	818.5	831.4	844.0	855.7	834.0	784.3	717.2	655.4	603.9
37.5°	622.9	648.0	704.7	730.6	745.4	791.6	809.4	782.6	722.4	656.2	594.8
40°	502.7	542.5	583.1	618.2	641.1	693.0	748.0	754.0	715.1	648.0	583.1
42.5°	423.1	446.4	477.1	509.6	529.9	591.4	665.8	709.5	692.1	634.6	568.9
45°	360.3	377.7	406.6	417.5	443.4	502.2	581.0	644.1	652.8	613.4	552.4
47.5°	309.3	324.0	342.6	356.0	376.8	420.9	487.5	557.2	598.7	584.4	529.5
50°	272.5	284.6	300.2	308.0	321.4	361.2	411.4	480.6	536.4	541.2	499.6
52.5°	241.8	248.7	260.9	269.5	280.3	304.5	350.0	407.1	469.8	495.8	462.9
55°	215.0	220.6	231.4	237.1	242.7	263.4	298.9	350.8	409.7	443.8	425.2
57.5°	190.8	195.5	204.6	209.8	212.8	232.7	260.0	300.7	353.4	395.0	384.6
60°	170.9	175.2	180.4	184.3	187.7	204.2	223.2	256.1	303.2	343.5	340.9
62.5°	149.7	153.6	159.2	163.1	166.1	176.5	192.5	217.6	257.8	295.0	302.4
65°	131.1	134.1	138.0	139.7	143.6	151.4	164.4	186.9	219.8	253.1	258.3
67.5°	114.2	115.1	117.7	121.6	122.4	129.3	141.0	157.9	183.4	210.7	218.9
70°	96.0	97.3	99.5	102.5	104.3	108.6	118.5	129.8	151.8	175.6	181.7
72.5°	80.0	81.8	82.6	84.4	85.2	92.1	96.5	107.7	122.9	142.8	149.2
75°	64.9	66.6	67.1	67.9	68.8	71.8	77.9	84.8	97.3	110.3	119.0
77.5°	51.5	51.0	51.9	53.2	52.8	55.4	59.3	65.3	73.5	84.4	90.0
80°	36.3	36.3	37.6	38.9	38.5	41.1	42.4	46.7	53.6	60.6	62.7
82.5°	24.2	24.2	25.5	25.5	26.4	26.8	28.6	30.7	36.3	39.8	41.1
85°	13.8	13.8	14.3	14.3	14.3	15.1	16.4	17.3	19.0	21.2	22.1
87.5°	5.6	6.1	6.1	6.1	6.1	6.9	6.9	7.8	8.2	9.1	9.1
90°	25.3	24.6	23.9	23.5	22.9	21.6	20.4	19.1	17.9	16.2	14.4
92.5°	58.2	57.7	57.2	57.0	56.1	54.4	52.6	50.9	49.1	46.9	44.7
95°	95.0	94.5	94.0	93.8	92.9	91.2	89.5	87.7	86.0	83.5	81.0
97.5°	135.7	135.5	135.2	135.1	134.4	132.9	131.4	129.9	128.4	124.9	121.5
100°	182.1	181.6	181.1	180.9	179.8	177.6	175.3	173.1	170.9	167.7	164.4
102.5°	228.5	227.8	227.1	226.7	225.5	223.0	220.5	218.0	215.5	214.3	213.0
105°	275.4	274.7	274.0	273.6	272.9	271.4	269.9	268.4	266.9	265.4	263.9
107.5°	323.8	323.8	323.8	323.8	323.4	322.7	322.0	321.2	320.5	319.3	318.0
110°	377.9	378.2	378.5	378.6	378.2	377.5	376.7	376.0	375.2	374.5	373.7

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	430.9	431.4	431.9	432.2	432.1	431.8	431.5	431.3	431.0	430.0	429.0
115°	486.3	486.5	486.8	486.9	487.0	487.3	487.5	487.8	488.0	487.5	487.0
117.5°	541.4	542.3	543.3	543.8	543.7	543.4	543.2	542.9	542.7	542.2	541.7
120°	597.2	598.2	599.2	599.7	599.7	599.7	599.7	599.7	599.7	599.4	599.2
122.5°	652.5	653.3	654.0	654.4	654.5	654.8	655.0	655.3	655.5	654.7	654.0
125°	707.4	707.6	707.9	708.0	708.2	708.7	709.2	709.7	710.2	710.0	709.7
127.5°	761.5	762.0	762.5	762.7	762.8	763.1	763.3	763.6	763.8	763.6	763.3
130°	815.1	815.6	816.1	816.3	816.4	816.7	816.9	817.2	817.4	816.9	816.4
132.5°	865.8	866.6	867.3	867.7	867.8	868.1	868.3	868.6	868.8	869.0	869.3
135°	918.8	919.8	920.8	921.3	921.3	921.3	921.3	921.3	921.3	921.0	920.8
137.5°	970.6	971.9	973.1	973.7	973.6	973.3	973.1	972.8	972.6	972.1	971.6
140°	1019.8	1021.0	1022.3	1022.9	1022.6	1022.1	1021.6	1021.1	1020.6	1019.9	1019.1
142.5°	1066.7	1067.9	1069.2	1069.8	1069.7	1069.4	1069.2	1068.9	1068.7	1067.7	1066.7
145°	1112.6	1113.3	1114.0	1114.4	1114.4	1114.4	1114.4	1114.4	1114.4	1113.7	1112.9
147.5°	1154.2	1156.1	1158.1	1159.1	1158.7	1158.0	1157.3	1156.5	1155.8	1155.3	1154.8
150°	1195.8	1196.3	1196.8	1197.1	1197.1	1197.1	1197.1	1197.1	1197.1	1196.1	1195.1
152.5°	1233.7	1234.7	1235.7	1236.2	1235.8	1235.1	1234.3	1233.6	1232.8	1232.6	1232.3
155°	1268.8	1270.0	1271.3	1271.9	1271.4	1270.4	1269.4	1268.4	1267.4	1267.2	1266.9
157.5°	1298.8	1300.6	1302.3	1303.2	1302.7	1301.7	1300.7	1299.7	1298.7	1298.5	1298.2
160°	1328.0	1329.2	1330.5	1331.1	1330.6	1329.6	1328.6	1327.6	1326.6	1326.4	1326.1
162.5°	1354.2	1355.7	1357.2	1357.9	1357.3	1356.0	1354.8	1353.5	1352.3	1352.3	1352.3
165°	1376.5	1378.0	1379.5	1380.2	1379.7	1378.7	1377.7	1376.7	1375.7	1375.5	1375.2
167.5°	1395.5	1397.0	1398.5	1399.2	1398.5	1397.0	1395.5	1394.0	1392.5	1392.5	1392.5
170°	1410.5	1412.2	1413.9	1414.8	1414.1	1412.6	1411.1	1409.6	1408.1	1408.1	1408.1
172.5°	1422.3	1423.8	1425.3	1426.0	1425.3	1423.8	1422.3	1420.8	1419.3	1419.3	1419.3
175°	1429.5	1431.2	1432.9	1433.8	1433.1	1431.6	1430.1	1428.6	1427.1	1427.1	1427.1
177.5°	1434.0	1435.7	1437.4	1438.3	1437.6	1436.1	1434.6	1433.1	1431.6	1431.8	1432.1
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	524.3	522.1	519.5	519.5	516.5	515.2	512.6	511.8	509.6	506.1	503.5
5°	542.9	537.3	533.8	530.8	524.3	519.5	514.8	509.6	504.4	498.3	491.4
7.5°	561.1	550.7	545.9	540.7	531.2	521.3	511.8	504.8	497.9	488.4	479.7
10°	580.1	567.1	558.5	551.6	536.8	524.3	510.5	500.5	489.7	477.6	466.3
12.5°	596.1	579.2	571.9	558.9	542.0	526.9	509.6	494.5	480.2	465.9	452.1
15°	609.5	593.5	575.3	570.2	546.8	525.2	505.7	486.2	468.5	454.2	438.2
17.5°	613.8	593.5	584.4	571.9	544.2	521.7	497.0	475.9	459.0	437.8	425.2
20°	615.1	595.7	583.1	571.5	546.8	516.9	492.7	466.8	446.4	425.2	405.3
22.5°	611.7	588.8	576.6	565.4	537.7	512.2	484.1	455.5	431.7	412.3	392.4
25°	605.2	578.4	566.7	554.6	528.2	500.1	469.4	442.1	420.0	396.7	377.2
27.5°	596.5	565.8	552.4	539.9	513.9	487.5	458.5	430.4	405.8	381.1	362.9
30°	585.7	550.3	538.1	521.7	496.6	471.5	445.1	417.0	389.3	366.0	346.1
32.5°	571.9	534.7	518.7	503.1	475.9	452.9	427.8	401.4	374.6	351.7	330.9
35°	559.3	516.9	499.2	483.6	453.4	429.1	408.4	383.7	359.9	336.1	317.5
37.5°	542.5	499.2	478.0	462.0	431.3	406.6	387.2	368.1	343.0	320.1	302.8
40°	524.7	477.1	457.3	441.2	409.2	382.4	363.8	346.9	326.6	305.4	287.2
42.5°	508.7	456.0	434.8	415.3	382.8	359.1	340.0	327.0	308.4	289.4	273.0
45°	488.4	433.5	410.5	390.2	359.1	333.1	314.9	304.5	290.7	272.1	257.8
47.5°	467.6	409.2	385.4	365.5	331.8	308.9	291.1	281.2	271.7	257.0	242.7
50°	440.4	383.7	362.1	339.2	305.8	282.5	267.8	257.8	250.5	240.1	228.0
52.5°	410.5	357.3	334.0	314.1	281.2	260.0	243.1	237.5	230.1	222.4	212.0
55°	379.0	328.8	306.3	286.8	256.5	234.9	221.1	215.0	209.4	203.3	196.4
57.5°	347.4	298.9	277.7	260.4	232.3	211.5	200.3	192.1	188.2	184.7	179.1
60°	308.0	266.9	250.5	234.9	207.2	188.2	177.4	171.3	167.8	166.1	163.5
62.5°	273.4	239.7	221.5	206.3	184.3	167.4	157.0	152.3	149.2	148.4	145.4
65°	236.6	207.6	193.4	180.4	161.4	146.2	137.6	131.9	129.8	129.3	129.3
67.5°	202.0	178.7	164.4	155.3	138.9	125.5	117.2	115.1	113.8	112.0	111.6
70°	169.6	151.0	138.4	130.6	115.9	106.0	99.5	96.0	96.0	94.7	93.9
72.5°	141.0	122.4	114.2	107.7	95.6	87.0	82.2	81.3	78.3	77.9	77.9
75°	110.3	96.5	90.8	85.2	76.1	70.1	66.2	64.0	62.3	62.3	62.7
77.5°	83.1	73.5	68.3	64.0	57.5	53.6	50.6	49.7	48.0	48.0	48.0
80°	58.8	53.6	49.7	46.3	41.5	38.1	36.3	34.6	34.6	34.2	34.6
82.5°	38.1	33.7	31.6	31.1	26.8	25.5	23.4	23.8	22.5	22.1	22.9
85°	22.1	19.9	17.3	16.4	14.7	13.0	12.1	12.5	12.1	11.7	12.1
87.5°	8.7	7.4	6.9	6.9	5.6	5.2	4.8	5.2	4.3	4.3	4.8
90°	12.7	11.0	10.1	9.1	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	42.4	40.2	39.1	38.5	37.2	36.0	34.7	33.5	34.7	36.0	37.2
95°	78.5	76.0	74.8	74.6	74.1	73.6	73.1	72.6	73.1	73.6	74.1
97.5°	118.0	114.5	112.8	112.7	112.4	112.2	111.9	111.7	111.9	112.2	112.4
100°	161.2	157.9	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3	156.3
102.5°	211.8	210.5	209.9	209.3	208.1	206.8	205.6	204.4	205.6	206.8	208.1
105°	262.4	260.9	260.2	259.6	258.3	257.1	255.8	254.6	255.8	257.1	258.3
107.5°	316.8	315.5	314.9	314.3	313.0	311.8	310.5	309.3	310.5	311.8	313.0
110°	373.0	372.3	371.9	371.3	370.0	368.8	367.5	366.3	367.5	368.8	370.0

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	428.1	427.1	426.6	426.3	425.8	425.3	424.8	424.3	424.8	425.3	425.8
115°	486.5	486.0	485.8	485.3	484.3	483.3	482.3	481.3	482.3	483.3	484.3
117.5°	541.2	540.7	540.5	540.4	540.1	539.9	539.6	539.4	539.6	539.9	540.1
120°	598.9	598.6	598.5	597.9	596.7	595.4	594.2	593.0	594.2	595.4	596.7
122.5°	653.2	652.5	652.1	652.0	651.7	651.5	651.2	651.0	651.2	651.5	651.7
125°	709.5	709.2	709.1	708.4	706.9	705.4	703.9	702.4	703.9	705.4	706.9
127.5°	763.1	762.8	762.7	762.3	761.6	760.8	760.1	759.3	760.1	760.8	761.6
130°	815.9	815.4	815.2	814.6	813.3	812.1	810.8	809.6	810.8	812.1	813.3
132.5°	869.5	869.8	869.9	868.8	866.5	864.3	862.0	859.8	862.0	864.3	866.5
135°	920.5	920.2	920.1	919.4	917.9	916.4	914.9	913.4	914.9	916.4	917.9
137.5°	971.1	970.6	970.4	969.7	968.2	966.7	965.2	963.7	965.2	966.7	968.2
140°	1018.4	1017.7	1017.3	1016.7	1015.4	1014.2	1012.9	1011.7	1012.9	1014.2	1015.4
142.5°	1065.7	1064.7	1064.2	1063.7	1062.7	1061.7	1060.7	1059.7	1060.7	1061.7	1062.7
145°	1112.2	1111.5	1111.1	1110.6	1109.6	1108.6	1107.6	1106.6	1107.6	1108.6	1109.6
147.5°	1154.3	1153.8	1153.5	1153.1	1152.4	1151.7	1150.9	1150.2	1150.9	1151.7	1152.4
150°	1194.1	1193.1	1192.6	1192.7	1193.0	1193.2	1193.5	1193.7	1193.5	1193.2	1193.0
152.5°	1232.1	1231.8	1231.7	1231.5	1231.0	1230.5	1230.0	1229.5	1230.0	1230.5	1231.0
155°	1266.7	1266.4	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3	1266.3
157.5°	1298.0	1297.7	1297.6	1297.8	1298.3	1298.8	1299.3	1299.8	1299.3	1298.8	1298.3
160°	1325.9	1325.6	1325.5	1325.9	1326.6	1327.3	1328.1	1328.8	1328.1	1327.3	1326.6
162.5°	1352.3	1352.3	1352.3	1352.5	1353.0	1353.5	1354.0	1354.5	1354.0	1353.5	1353.0
165°	1375.0	1374.7	1374.6	1374.9	1375.4	1375.9	1376.4	1376.9	1376.4	1375.9	1375.4
167.5°	1392.5	1392.5	1392.5	1393.0	1394.0	1395.0	1396.0	1397.0	1396.0	1395.0	1394.0
170°	1408.1	1408.1	1408.1	1408.6	1409.6	1410.6	1411.6	1412.6	1411.6	1410.6	1409.6
172.5°	1419.3	1419.3	1419.3	1419.8	1420.8	1421.8	1422.8	1423.8	1422.8	1421.8	1420.8
175°	1427.1	1427.1	1427.1	1427.6	1428.6	1429.6	1430.6	1431.6	1430.6	1429.6	1428.6
177.5°	1432.3	1432.6	1432.7	1433.2	1434.2	1435.2	1436.2	1437.2	1436.2	1435.2	1434.2
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	502.7	501.8	499.6	498.3	494.0	488.8	487.1	482.8	484.5	481.5	481.5
5°	489.3	485.4	482.8	478.9	470.7	465.0	459.0	456.0	454.2	452.1	450.3
7.5°	472.0	468.9	466.3	459.0	449.9	442.1	434.8	431.7	426.1	422.2	420.5
10°	456.8	452.5	446.4	437.8	428.3	418.3	411.8	405.3	401.0	398.9	394.1
12.5°	441.2	436.1	429.6	417.0	406.6	400.6	388.9	382.8	380.7	379.0	373.3
15°	425.2	419.6	411.8	400.1	391.1	376.8	369.9	365.1	359.9	359.5	355.2
17.5°	411.0	404.0	397.6	383.3	372.0	359.5	355.6	350.4	345.6	340.5	338.3
20°	392.8	386.3	381.5	366.0	353.4	345.6	339.2	334.8	331.8	326.6	325.7
22.5°	376.4	369.4	362.9	351.3	340.5	330.5	322.7	318.0	316.7	314.5	310.6
25°	360.3	353.4	345.6	334.8	323.6	316.7	309.7	306.7	304.1	300.7	297.6
27.5°	346.9	340.5	333.1	319.7	310.2	305.0	297.6	294.2	290.7	289.0	287.7
30°	330.9	323.6	318.0	307.6	297.2	290.3	285.1	282.1	279.0	277.3	276.4
32.5°	315.4	308.4	304.5	293.3	285.1	276.9	273.0	270.8	269.1	267.3	265.6
35°	302.8	295.9	289.8	279.5	271.2	265.6	262.6	259.1	257.8	256.1	256.1
37.5°	287.2	282.1	276.0	266.0	258.7	254.4	251.8	247.4	247.0	246.1	244.8
40°	273.8	268.6	263.0	254.4	247.9	242.7	239.2	237.1	235.8	234.9	234.0
42.5°	259.6	253.9	251.3	241.4	235.8	230.6	228.8	226.7	226.2	224.5	222.4
45°	245.7	241.0	235.8	228.4	223.7	219.3	216.7	215.0	212.8	212.4	211.1
47.5°	233.6	228.0	223.2	216.3	211.1	207.6	205.5	203.3	201.6	200.3	199.0
50°	218.0	213.7	209.8	202.5	198.1	194.7	191.6	189.9	188.2	188.2	188.2
52.5°	202.9	199.0	195.5	190.3	185.1	182.1	178.7	177.4	176.5	175.2	176.5
55°	188.2	184.3	180.8	176.9	170.9	168.3	164.8	163.5	164.0	164.0	165.3
57.5°	172.6	169.6	167.4	162.7	157.0	154.4	152.3	151.0	151.0	152.7	153.1
60°	157.5	154.4	150.5	146.2	142.8	139.7	138.4	138.9	138.9	139.7	141.9
62.5°	140.6	138.9	136.7	130.6	128.5	126.3	124.6	125.9	125.5	127.6	130.6
65°	125.0	123.3	120.3	117.2	114.6	112.5	112.0	112.5	113.3	115.5	119.0
67.5°	107.7	107.7	105.1	102.5	100.4	98.2	98.6	99.1	99.9	102.5	107.7
70°	93.4	91.7	89.1	87.4	85.7	84.8	83.9	85.7	88.2	90.0	93.9
72.5°	77.9	76.6	74.4	72.7	72.2	71.4	70.9	71.8	74.4	77.4	81.8
75°	61.4	61.9	60.6	59.3	59.3	58.0	58.8	58.8	61.4	64.5	67.9
77.5°	47.6	47.2	46.7	45.9	45.4	45.4	45.4	46.3	48.9	50.6	54.1
80°	33.7	34.2	32.9	33.3	32.9	33.3	33.3	35.0	36.3	38.5	41.1
82.5°	22.5	22.5	21.6	22.1	22.1	22.1	22.5	23.4	25.1	26.8	28.6
85°	12.5	13.0	12.1	13.0	13.0	13.0	13.4	13.8	15.1	15.6	17.3
87.5°	4.8	5.6	5.6	4.8	5.2	5.6	6.1	5.6	6.5	7.4	7.8
90°	9.1	10.1	11.0	12.7	14.4	16.2	17.9	19.1	20.4	21.6	22.9
92.5°	38.5	39.1	40.2	42.4	44.7	46.9	49.1	50.9	52.6	54.4	56.1
95°	74.6	74.8	76.0	78.5	81.0	83.5	86.0	87.7	89.5	91.2	92.9
97.5°	112.7	112.8	114.5	118.0	121.5	124.9	128.4	129.9	131.4	132.9	134.4
100°	156.3	156.3	157.9	161.2	164.4	167.7	170.9	173.1	175.3	177.6	179.8
102.5°	209.3	209.9	210.5	211.8	213.0	214.3	215.5	218.0	220.5	223.0	225.5
105°	259.6	260.2	260.9	262.4	263.9	265.4	266.9	268.4	269.9	271.4	272.9
107.5°	314.3	314.9	315.5	316.8	318.0	319.3	320.5	321.2	322.0	322.7	323.4
110°	371.3	371.9	372.3	373.0	373.7	374.5	375.2	376.0	376.7	377.5	378.2

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	426.3	426.6	427.1	428.1	429.0	430.0	431.0	431.3	431.5	431.8	432.1
115°	485.3	485.8	486.0	486.5	487.0	487.5	488.0	487.8	487.5	487.3	487.0
117.5°	540.4	540.5	540.7	541.2	541.7	542.2	542.7	542.9	543.2	543.4	543.7
120°	597.9	598.5	598.6	598.9	599.2	599.4	599.7	599.7	599.7	599.7	599.7
122.5°	652.0	652.1	652.5	653.2	654.0	654.7	655.5	655.3	655.0	654.8	654.5
125°	708.4	709.1	709.2	709.5	709.7	710.0	710.2	709.7	709.2	708.7	708.2
127.5°	762.3	762.7	762.8	763.1	763.3	763.6	763.8	763.6	763.3	763.1	762.8
130°	814.6	815.2	815.4	815.9	816.4	816.9	817.4	817.2	816.9	816.7	816.4
132.5°	868.8	869.9	869.8	869.5	869.3	869.0	868.8	868.6	868.3	868.1	867.8
135°	919.4	920.1	920.2	920.5	920.8	921.0	921.3	921.3	921.3	921.3	921.3
137.5°	969.7	970.4	970.6	971.1	971.6	972.1	972.6	972.8	973.1	973.3	973.6
140°	1016.7	1017.3	1017.7	1018.4	1019.1	1019.9	1020.6	1021.1	1021.6	1022.1	1022.6
142.5°	1063.7	1064.2	1064.7	1065.7	1066.7	1067.7	1068.7	1068.9	1069.2	1069.4	1069.7
145°	1110.6	1111.1	1111.5	1112.2	1112.9	1113.7	1114.4	1114.4	1114.4	1114.4	1114.4
147.5°	1153.1	1153.5	1153.8	1154.3	1154.8	1155.3	1155.8	1156.5	1157.3	1158.0	1158.7
150°	1192.7	1192.6	1193.1	1194.1	1195.1	1196.1	1197.1	1197.1	1197.1	1197.1	1197.1
152.5°	1231.5	1231.7	1231.8	1232.1	1232.3	1232.6	1232.8	1233.6	1234.3	1235.1	1235.8
155°	1266.3	1266.3	1266.4	1266.7	1266.9	1267.2	1267.4	1268.4	1269.4	1270.4	1271.4
157.5°	1297.8	1297.6	1297.7	1298.0	1298.2	1298.5	1298.7	1299.7	1300.7	1301.7	1302.7
160°	1325.9	1325.5	1325.6	1325.9	1326.1	1326.4	1326.6	1327.6	1328.6	1329.6	1330.6
162.5°	1352.5	1352.3	1352.3	1352.3	1352.3	1352.3	1352.3	1353.5	1354.8	1356.0	1357.3
165°	1374.9	1374.6	1374.7	1375.0	1375.2	1375.5	1375.7	1376.7	1377.7	1378.7	1379.7
167.5°	1393.0	1392.5	1392.5	1392.5	1392.5	1392.5	1392.5	1394.0	1395.5	1397.0	1398.5
170°	1408.6	1408.1	1408.1	1408.1	1408.1	1408.1	1408.1	1409.6	1411.1	1412.6	1414.1
172.5°	1419.8	1419.3	1419.3	1419.3	1419.3	1419.3	1419.3	1420.8	1422.3	1423.8	1425.3
175°	1427.6	1427.1	1427.1	1427.1	1427.1	1427.1	1427.1	1428.6	1430.1	1431.6	1433.1
177.5°	1433.2	1432.7	1432.6	1432.3	1432.1	1431.8	1431.6	1433.1	1434.6	1436.1	1437.6
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	483.2	480.2	479.7	480.6	478.9	481.5	480.6	481.5	479.3	481.5	480.2
5°	449.9	449.0	447.3	445.1	445.6	446.0	448.2	446.0	447.7	448.2	450.3
7.5°	418.7	417.0	418.3	417.5	413.6	412.7	413.6	414.9	417.5	419.2	420.5
10°	393.7	392.8	391.1	389.8	387.6	386.3	388.0	386.3	389.8	392.8	392.8
12.5°	374.6	371.2	369.0	368.6	363.8	364.7	366.4	367.7	371.6	373.3	373.3
15°	354.7	352.1	351.3	349.5	347.8	349.5	348.7	350.0	351.7	353.4	354.3
17.5°	337.4	337.0	337.4	333.1	334.4	332.2	332.7	334.8	333.5	334.8	337.4
20°	321.8	322.7	321.4	319.7	319.7	317.1	320.1	319.3	319.7	322.3	326.2
22.5°	310.2	309.7	308.4	307.1	305.4	305.8	306.3	305.4	308.9	311.0	311.5
25°	297.6	296.8	296.3	295.0	293.3	295.0	294.6	295.0	295.9	299.4	296.8
27.5°	285.9	284.2	285.1	283.8	283.3	283.8	283.8	284.2	285.1	285.5	285.9
30°	276.0	274.3	273.8	273.0	272.5	273.0	273.8	273.0	276.4	276.0	276.0
32.5°	265.2	263.9	263.0	263.0	262.6	262.2	262.6	263.0	265.6	263.9	265.6
35°	254.8	253.9	253.9	253.1	252.6	252.6	252.6	254.4	253.5	254.8	254.8
37.5°	244.8	244.8	244.4	243.5	243.1	243.5	243.1	244.0	243.5	244.0	244.4
40°	234.5	233.6	233.2	233.2	231.9	230.6	231.9	231.9	232.3	233.6	234.0
42.5°	221.9	222.4	222.4	220.6	220.6	220.6	221.1	221.5	221.5	222.4	222.4
45°	211.1	210.2	210.2	210.2	209.4	209.8	210.7	210.7	210.7	210.7	209.8
47.5°	199.0	199.0	199.4	199.4	200.7	200.3	200.3	199.9	199.0	199.0	199.4
50°	187.7	189.0	189.5	189.5	189.9	190.3	190.3	189.5	189.0	187.7	187.7
52.5°	176.9	177.8	178.7	180.0	180.8	180.4	180.4	179.5	177.8	177.4	176.9
55°	165.3	166.5	168.3	169.6	170.9	171.3	171.3	169.6	167.8	165.7	165.7
57.5°	154.4	155.7	158.8	160.1	161.8	161.8	160.9	159.6	157.0	155.3	154.0
60°	143.6	145.8	147.9	150.5	152.7	153.1	151.8	150.1	147.1	144.9	143.2
62.5°	131.9	134.1	138.4	141.0	142.8	142.8	142.8	140.6	136.7	133.7	131.1
65°	120.7	122.9	126.7	130.2	131.5	132.8	131.5	129.3	126.3	122.9	120.3
67.5°	109.0	111.6	115.5	118.1	119.8	121.1	120.3	118.5	114.6	109.9	108.1
70°	96.0	97.3	103.0	105.6	108.1	109.0	108.1	105.6	101.7	96.5	94.7
72.5°	83.9	85.2	90.4	92.6	94.7	95.6	94.3	92.6	89.1	84.4	82.2
75°	70.1	72.2	74.8	78.3	80.9	81.8	80.5	79.2	74.8	71.8	70.1
77.5°	55.4	57.5	61.0	64.0	66.6	66.2	64.5	64.9	60.1	56.7	55.4
80°	42.0	43.7	46.3	48.9	50.2	50.2	49.7	48.0	46.3	43.7	41.5
82.5°	29.0	31.1	33.3	35.0	35.0	35.5	34.6	34.2	32.4	30.3	29.8
85°	17.3	17.7	19.5	19.5	21.2	20.3	19.9	21.2	19.5	18.2	17.7
87.5°	7.8	7.4	7.8	7.8	7.4	8.2	8.2	7.8	8.2	7.8	7.8
90°	23.5	23.9	24.6	25.3	26.1	26.8	26.1	25.3	24.6	23.9	23.5
92.5°	57.0	57.2	57.7	58.2	58.7	59.2	58.7	58.2	57.7	57.2	57.0
95°	93.8	94.0	94.5	95.0	95.5	96.0	95.5	95.0	94.5	94.0	93.8
97.5°	135.1	135.2	135.5	135.7	136.0	136.2	136.0	135.7	135.5	135.2	135.1
100°	180.9	181.1	181.6	182.1	182.6	183.1	182.6	182.1	181.6	181.1	180.9
102.5°	226.7	227.1	227.8	228.5	229.3	230.0	229.3	228.5	227.8	227.1	226.7
105°	273.6	274.0	274.7	275.4	276.2	276.9	276.2	275.4	274.7	274.0	273.6
107.5°	323.8	323.8	323.8	323.8	323.8	323.8	323.8	323.8	323.8	323.8	323.8
110°	378.6	378.5	378.2	377.9	377.7	377.4	377.7	377.9	378.2	378.5	378.6

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	432.2	431.9	431.4	430.9	430.4	429.9	430.4	430.9	431.4	431.9	432.2
115°	486.9	486.8	486.5	486.3	486.0	485.8	486.0	486.3	486.5	486.8	486.9
117.5°	543.8	543.3	542.3	541.4	540.4	539.4	540.4	541.4	542.3	543.3	543.8
120°	599.7	599.2	598.2	597.2	596.2	595.2	596.2	597.2	598.2	599.2	599.7
122.5°	654.4	654.0	653.3	652.5	651.8	651.0	651.8	652.5	653.3	654.0	654.4
125°	708.0	707.9	707.6	707.4	707.1	706.9	707.1	707.4	707.6	707.9	708.0
127.5°	762.7	762.5	762.0	761.5	761.0	760.5	761.0	761.5	762.0	762.5	762.7
130°	816.3	816.1	815.6	815.1	814.6	814.1	814.6	815.1	815.6	816.1	816.3
132.5°	867.7	867.3	866.6	865.8	865.1	864.3	865.1	865.8	866.6	867.3	867.7
135°	921.3	920.8	919.8	918.8	917.8	916.8	917.8	918.8	919.8	920.8	921.3
137.5°	973.7	973.1	971.9	970.6	969.4	968.2	969.4	970.6	971.9	973.1	973.7
140°	1022.9	1022.3	1021.0	1019.8	1018.5	1017.3	1018.5	1019.8	1021.0	1022.3	1022.9
142.5°	1069.8	1069.2	1067.9	1066.7	1065.4	1064.2	1065.4	1066.7	1067.9	1069.2	1069.8
145°	1114.4	1114.0	1113.3	1112.6	1111.8	1111.1	1111.8	1112.6	1113.3	1114.0	1114.4
147.5°	1159.1	1158.1	1156.1	1154.2	1152.2	1150.2	1152.2	1154.2	1156.1	1158.1	1159.1
150°	1197.1	1196.8	1196.3	1195.8	1195.3	1194.8	1195.3	1195.8	1196.3	1196.8	1197.1
152.5°	1236.2	1235.7	1234.7	1233.7	1232.7	1231.7	1232.7	1233.7	1234.7	1235.7	1236.2
155°	1271.9	1271.3	1270.0	1268.8	1267.5	1266.3	1267.5	1268.8	1270.0	1271.3	1271.9
157.5°	1303.2	1302.3	1300.6	1298.8	1297.1	1295.3	1297.1	1298.8	1300.6	1302.3	1303.2
160°	1331.1	1330.5	1329.2	1328.0	1326.7	1325.5	1326.7	1328.0	1329.2	1330.5	1331.1
162.5°	1357.9	1357.2	1355.7	1354.2	1352.7	1351.2	1352.7	1354.2	1355.7	1357.2	1357.9
165°	1380.2	1379.5	1378.0	1376.5	1375.0	1373.5	1375.0	1376.5	1378.0	1379.5	1380.2
167.5°	1399.2	1398.5	1397.0	1395.5	1394.0	1392.5	1394.0	1395.5	1397.0	1398.5	1399.2
170°	1414.8	1413.9	1412.2	1410.5	1408.7	1407.0	1408.7	1410.5	1412.2	1413.9	1414.8
172.5°	1426.0	1425.3	1423.8	1422.3	1420.8	1419.3	1420.8	1422.3	1423.8	1425.3	1426.0
175°	1433.8	1432.9	1431.2	1429.5	1427.7	1426.0	1427.7	1429.5	1431.2	1432.9	1433.8
177.5°	1438.3	1437.4	1435.7	1434.0	1432.2	1430.5	1432.2	1434.0	1435.7	1437.4	1438.3
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	484.1	481.5	484.5	480.6	481.5	486.2	485.8	490.1	492.7	492.3	494.5
5°	452.1	452.1	453.4	452.9	457.3	461.1	466.3	470.7	475.4	478.0	481.0
7.5°	420.5	424.8	425.7	427.8	433.0	439.5	444.7	451.2	458.1	462.9	466.3
10°	394.5	398.0	401.4	403.2	408.8	417.5	424.8	435.2	443.8	449.0	453.8
12.5°	371.6	375.5	377.2	385.0	388.9	394.5	404.9	416.2	425.7	431.3	435.2
15°	355.2	357.3	361.2	366.0	369.9	376.8	385.4	398.0	407.1	411.8	425.2
17.5°	341.3	343.9	346.1	348.2	354.3	361.6	369.9	380.7	392.4	400.6	407.5
20°	327.0	328.3	330.9	334.4	338.7	345.6	353.0	364.2	374.6	381.1	390.2
22.5°	310.2	314.1	316.7	319.3	324.0	331.8	338.7	346.9	359.9	367.3	376.8
25°	300.2	301.9	303.7	306.7	310.2	317.1	324.9	333.5	343.9	351.7	359.9
27.5°	287.2	289.8	292.0	295.9	298.1	303.7	311.0	319.7	332.2	338.7	345.6
30°	276.4	279.0	280.8	282.5	285.5	291.6	298.5	305.4	317.1	325.3	332.2
32.5°	265.6	268.2	270.4	271.7	274.7	278.6	284.2	292.9	302.8	308.4	317.5
35°	256.1	256.1	258.7	260.4	263.0	266.5	271.7	278.2	288.5	295.9	304.1
37.5°	245.3	245.7	247.9	249.2	251.8	255.2	260.4	266.5	275.1	280.8	289.0
40°	234.0	235.3	236.2	238.4	241.4	242.7	247.9	254.8	263.4	268.6	275.6
42.5°	222.8	223.7	225.8	227.5	230.1	232.3	235.8	242.3	248.7	256.5	262.2
45°	210.2	212.4	213.7	216.7	218.0	220.2	223.7	228.8	236.6	241.4	247.9
47.5°	199.4	200.3	201.2	205.0	207.6	208.9	212.4	215.4	223.7	228.0	234.0
50°	187.7	187.7	189.0	190.8	193.8	196.4	199.4	202.9	209.4	213.7	219.8
52.5°	176.9	175.6	176.5	177.4	180.4	183.0	186.0	190.8	196.8	199.4	204.6
55°	165.3	163.1	164.4	165.7	166.5	170.0	173.5	176.5	181.3	185.1	189.9
57.5°	152.7	152.3	151.4	151.8	154.0	156.2	158.8	162.7	168.3	171.3	173.9
60°	141.5	138.9	138.0	138.9	140.2	141.5	144.9	148.4	153.1	156.2	159.2
62.5°	129.8	127.2	125.5	124.2	125.5	128.5	130.6	133.2	137.1	140.6	143.2
65°	118.5	114.6	112.9	112.0	111.6	113.8	115.5	119.0	122.4	123.7	126.7
67.5°	106.0	102.5	100.4	99.1	99.1	99.1	100.8	104.3	107.7	108.1	111.2
70°	93.4	89.5	87.4	85.7	84.8	85.7	87.8	88.2	91.3	92.1	93.9
72.5°	80.0	76.6	74.0	71.8	72.2	73.1	73.1	74.0	75.7	77.9	77.9
75°	67.5	62.7	61.4	59.7	58.8	58.8	58.8	60.6	61.9	63.6	63.2
77.5°	53.2	50.6	48.0	47.2	45.9	45.4	46.3	46.3	47.2	48.5	48.9
80°	41.1	38.1	36.3	35.5	33.7	33.3	33.7	33.7	35.0	34.6	35.0
82.5°	28.6	26.4	25.1	23.8	22.9	23.4	22.9	22.9	23.4	22.9	22.9
85°	16.4	16.0	15.1	14.7	14.3	13.4	14.3	13.8	13.4	13.0	13.8
87.5°	7.8	7.4	7.4	6.5	6.5	6.1	6.5	6.5	6.1	6.1	6.1
90°	22.9	21.6	20.4	19.1	17.9	16.2	14.4	12.7	11.0	10.1	9.1
92.5°	56.1	54.4	52.6	50.9	49.1	46.9	44.7	42.4	40.2	39.1	38.5
95°	92.9	91.2	89.5	87.7	86.0	83.5	81.0	78.5	76.0	74.8	74.6
97.5°	134.4	132.9	131.4	129.9	128.4	124.9	121.5	118.0	114.5	112.8	112.7
100°	179.8	177.6	175.3	173.1	170.9	167.7	164.4	161.2	157.9	156.3	156.3
102.5°	225.5	223.0	220.5	218.0	215.5	214.3	213.0	211.8	210.5	209.9	209.3
105°	272.9	271.4	269.9	268.4	266.9	265.4	263.9	262.4	260.9	260.2	259.6
107.5°	323.4	322.7	322.0	321.2	320.5	319.3	318.0	316.8	315.5	314.9	314.3
110°	378.2	377.5	376.7	376.0	375.2	374.5	373.7	373.0	372.3	371.9	371.3

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	432.1	431.8	431.5	431.3	431.0	430.0	429.0	428.1	427.1	426.6	426.3
115°	487.0	487.3	487.5	487.8	488.0	487.5	487.0	486.5	486.0	485.8	485.3
117.5°	543.7	543.4	543.2	542.9	542.7	542.2	541.7	541.2	540.7	540.5	540.4
120°	599.7	599.7	599.7	599.7	599.7	599.4	599.2	598.9	598.6	598.5	597.9
122.5°	654.5	654.8	655.0	655.3	655.5	654.7	654.0	653.2	652.5	652.1	652.0
125°	708.2	708.7	709.2	709.7	710.2	710.0	709.7	709.5	709.2	709.1	708.4
127.5°	762.8	763.1	763.3	763.6	763.8	763.6	763.3	763.1	762.8	762.7	762.3
130°	816.4	816.7	816.9	817.2	817.4	816.9	816.4	815.9	815.4	815.2	814.6
132.5°	867.8	868.1	868.3	868.6	868.8	869.0	869.3	869.5	869.8	869.9	868.8
135°	921.3	921.3	921.3	921.3	921.3	921.0	920.8	920.5	920.2	920.1	919.4
137.5°	973.6	973.3	973.1	972.8	972.6	972.1	971.6	971.1	970.6	970.4	969.7
140°	1022.6	1022.1	1021.6	1021.1	1020.6	1019.9	1019.1	1018.4	1017.7	1017.3	1016.7
142.5°	1069.7	1069.4	1069.2	1068.9	1068.7	1067.7	1066.7	1065.7	1064.7	1064.2	1063.7
145°	1114.4	1114.4	1114.4	1114.4	1114.4	1113.7	1112.9	1112.2	1111.5	1111.1	1110.6
147.5°	1158.7	1158.0	1157.3	1156.5	1155.8	1155.3	1154.8	1154.3	1153.8	1153.5	1153.1
150°	1197.1	1197.1	1197.1	1197.1	1197.1	1196.1	1195.1	1194.1	1193.1	1192.6	1192.7
152.5°	1235.8	1235.1	1234.3	1233.6	1232.8	1232.6	1232.3	1232.1	1231.8	1231.7	1231.5
155°	1271.4	1270.4	1269.4	1268.4	1267.4	1267.2	1266.9	1266.7	1266.4	1266.3	1266.3
157.5°	1302.7	1301.7	1300.7	1299.7	1298.7	1298.5	1298.2	1298.0	1297.7	1297.6	1297.8
160°	1330.6	1329.6	1328.6	1327.6	1326.6	1326.4	1326.1	1325.9	1325.6	1325.5	1325.9
162.5°	1357.3	1356.0	1354.8	1353.5	1352.3	1352.3	1352.3	1352.3	1352.3	1352.3	1352.5
165°	1379.7	1378.7	1377.7	1376.7	1375.7	1375.5	1375.2	1375.0	1374.7	1374.6	1374.9
167.5°	1398.5	1397.0	1395.5	1394.0	1392.5	1392.5	1392.5	1392.5	1392.5	1392.5	1393.0
170°	1414.1	1412.6	1411.1	1409.6	1408.1	1408.1	1408.1	1408.1	1408.1	1408.1	1408.6
172.5°	1425.3	1423.8	1422.3	1420.8	1419.3	1419.3	1419.3	1419.3	1419.3	1419.3	1419.8
175°	1433.1	1431.6	1430.1	1428.6	1427.1	1427.1	1427.1	1427.1	1427.1	1427.1	1427.6
177.5°	1437.6	1436.1	1434.6	1433.1	1431.6	1431.8	1432.1	1432.3	1432.6	1432.7	1433.2
180°	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9	1434.9

TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.6	509.6	509.6	509.6
2.5°	497.5	501.8	504.8	510.5
5°	486.2	494.0	501.4	509.2
7.5°	475.0	484.1	495.8	505.7
10°	462.4	474.1	488.0	501.4
12.5°	449.9	463.7	478.9	496.6
15°	434.8	452.5	470.2	489.3
17.5°	421.3	439.5	458.5	482.3
20°	406.2	426.1	446.9	471.1
22.5°	392.8	414.9	436.5	462.0
25°	377.7	399.3	423.1	450.3
27.5°	365.1	385.0	408.4	437.8
30°	350.0	371.6	395.0	424.4
32.5°	335.7	356.5	381.1	410.1
35°	321.0	342.2	364.2	391.9
37.5°	307.1	325.3	347.4	373.8
40°	291.6	311.5	331.4	352.1
42.5°	277.3	295.5	314.1	330.5
45°	261.3	276.9	294.6	308.0
47.5°	246.6	260.4	274.3	284.6
50°	231.9	242.7	253.1	262.2
52.5°	214.6	226.7	232.3	237.9
55°	199.0	205.9	211.1	216.7
57.5°	183.9	186.9	189.5	194.7
60°	164.0	167.4	170.4	174.3
62.5°	146.6	148.4	149.2	153.1
65°	130.2	129.8	131.9	134.1
67.5°	112.5	112.0	114.2	115.1
70°	95.2	94.7	95.2	97.3
72.5°	78.7	78.7	79.2	80.0
75°	63.6	63.6	64.0	64.9
77.5°	48.0	48.9	48.5	50.2
80°	35.0	34.2	35.0	35.9
82.5°	22.9	23.8	23.8	22.9
85°	13.0	13.0	13.0	13.0
87.5°	5.6	5.6	6.1	6.5
90°	7.1	5.1	3.1	1.1
92.5°	37.2	36.0	34.7	33.5
95°	74.1	73.6	73.1	72.6
97.5°	112.4	112.2	111.9	111.7
100°	156.3	156.3	156.3	156.3
102.5°	208.1	206.8	205.6	204.4
105°	258.3	257.1	255.8	254.6
107.5°	313.0	311.8	310.5	309.3
110°	370.0	368.8	367.5	366.3



TEST NUMBER: P1027830

CATALOG NUMBER: S125DIP-B375D1270UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	425.8	425.3	424.8	424.3
115°	484.3	483.3	482.3	481.3
117.5°	540.1	539.9	539.6	539.4
120°	596.7	595.4	594.2	593.0
122.5°	651.7	651.5	651.2	651.0
125°	706.9	705.4	703.9	702.4
127.5°	761.6	760.8	760.1	759.3
130°	813.3	812.1	810.8	809.6
132.5°	866.5	864.3	862.0	859.8
135°	917.9	916.4	914.9	913.4
137.5°	968.2	966.7	965.2	963.7
140°	1015.4	1014.2	1012.9	1011.7
142.5°	1062.7	1061.7	1060.7	1059.7
145°	1109.6	1108.6	1107.6	1106.6
147.5°	1152.4	1151.7	1150.9	1150.2
150°	1193.0	1193.2	1193.5	1193.7
152.5°	1231.0	1230.5	1230.0	1229.5
155°	1266.3	1266.3	1266.3	1266.3
157.5°	1298.3	1298.8	1299.3	1299.8
160°	1326.6	1327.3	1328.1	1328.8
162.5°	1353.0	1353.5	1354.0	1354.5
165°	1375.4	1375.9	1376.4	1376.9
167.5°	1394.0	1395.0	1396.0	1397.0
170°	1409.6	1410.6	1411.6	1412.6
172.5°	1420.8	1421.8	1422.8	1423.8
175°	1428.6	1429.6	1430.6	1431.6
177.5°	1434.2	1435.2	1436.2	1437.2
180°	1434.9	1434.9	1434.9	1434.9

(END OF REPORT)