

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1027920

Luminaire Tested: S125DIP-B375D610UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1027920
REPORT IS A COMBINATION OF REPORTS P1002051 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B375D610UB50-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3410.0 lumens
Efficiency: N/A
Efficacy: 120.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	88	85	88	84	81	78	70	67	65	56	54	53	44	43	42
2	88	81	75	70	80	74	69	64	61	57	54	49	47	45	39	37	35
3	80	71	64	58	73	65	59	54	54	49	46	44	41	38	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	33	31	28	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23
6	62	50	42	37	56	46	39	34	39	33	29	32	28	25	25	22	20
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	19	17	14
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	3265	3265	3265	3265
5°	3268	3704	3270	2810
10°	3248	4221	3242	2412
15°	3224	4577	3204	2179
20°	3183	5016	3154	1990
25°	3147	5748	3089	1877
30°	3095	6063	3041	1776
35°	3013	4860	2950	1693
40°	2884	3359	2842	1608
45°	2723	2501	2692	1535
50°	2538	2059	2495	1478
55°	2337	1756	2319	1428
60°	2141	1503	2104	1389
65°	1930	1298	1898	1333
70°	1706	1078	1683	1234
75°	1470	834	1449	1072
80°	1160	564	1118	788
85°	743	282	715	401

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 4987 cd/sqm

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.0	1.4
10°-20°	146.1	4.3
20°-30°	237.3	7.0
30°-40°	290.0	8.5
40°-50°	263.1	7.7
50°-60°	209.5	6.1
60°-70°	145.9	4.3
70°-80°	77.7	2.3
80°-90°	20.4	0.6
90°-100°	47.0	1.4
100°-110°	139.5	4.1
110°-120°	236.6	6.9
120°-130°	311.5	9.1
130°-140°	349.0	10.2
140°-150°	342.1	10.0
150°-160°	287.4	8.4
160°-170°	191.0	5.6
170°-180°	66.8	2.0
0°-30°	432.4	12.7
0°-40°	722.4	21.2
0°-60°	1195.0	35.0
0°-90°	1439.1	42.2
90°-120°	423.1	12.4
90°-150°	1425.7	41.8
90°-180°	1971.0	57.8
0°-180°	3410.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	510	510	510	510	510	
5°	509	588	510	446	509	48
15°	489	734	486	350	489	138
25°	450	903	442	295	450	207
35°	392	725	384	253	392	245
45°	308	342	304	210	308	237
55°	217	211	215	171	217	194
65°	134	129	132	133	134	133
75°	65	64	64	82	65	69
85°	13	14	12	20	13	16
90°	0	13	0	13	0	3
95°	36	47	36	47	36	37
105°	125	136	125	136	125	134
115°	237	239	237	239	237	234
125°	346	348	346	348	346	310
135°	450	451	450	451	450	346
145°	545	547	545	547	545	340
155°	623	623	623	623	623	287
165°	678	676	678	676	678	191
175°	704	702	704	702	704	67
180°	706	706	706	706	706	

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	510.5	513.5	516.9	519.5	523.9	525.2	527.3	528.6	529.9	531.2	532.1
5°	509.2	516.5	523.0	527.8	536.0	539.0	542.9	547.7	553.3	558.0	561.1
7.5°	505.7	517.4	526.0	535.5	546.8	554.2	558.0	568.0	577.1	584.0	593.1
10°	501.4	515.2	528.6	542.9	558.9	567.1	574.9	588.8	601.3	612.6	621.6
12.5°	496.6	513.5	529.5	548.1	569.7	579.7	584.9	608.7	624.2	630.3	648.0
15°	489.3	509.2	532.1	555.0	573.2	584.9	599.1	618.2	633.7	647.2	661.4
17.5°	482.3	504.0	527.3	552.9	579.2	594.4	605.2	622.1	638.9	656.2	669.7
20°	471.1	499.2	523.0	550.3	581.4	592.2	603.5	623.4	641.5	660.1	677.0
22.5°	462.0	488.8	521.3	547.2	573.6	584.4	598.3	619.0	640.7	661.9	686.5
25°	450.3	480.2	508.3	536.0	563.2	574.9	587.5	614.3	636.8	664.0	691.3
27.5°	437.8	468.5	496.6	521.7	547.2	563.2	576.6	604.8	634.6	664.5	699.9
30°	424.4	453.4	480.2	504.8	533.0	549.4	562.8	595.7	629.0	667.1	709.5
32.5°	410.1	437.4	460.3	485.4	515.2	530.4	548.5	584.4	623.8	669.2	722.4
35°	391.9	417.9	438.2	463.7	493.6	513.1	532.1	572.3	618.2	668.8	729.8
37.5°	373.8	394.1	413.6	440.8	475.4	493.2	513.1	557.2	609.5	667.5	732.8
40°	352.1	372.0	388.9	416.6	452.9	473.3	494.0	540.3	599.6	662.7	722.0
42.5°	330.5	347.4	366.0	395.0	430.0	451.6	473.7	525.2	586.6	648.9	692.1
45°	308.0	321.0	341.3	367.7	404.9	425.7	450.8	506.6	568.4	623.8	645.4
47.5°	284.6	297.6	316.7	342.2	379.0	403.6	427.4	483.2	545.5	588.3	588.3
50°	262.2	272.5	291.1	316.7	353.9	376.4	400.6	459.8	510.0	541.6	513.5
52.5°	237.9	249.6	265.2	292.0	328.8	349.1	375.5	426.1	473.7	486.7	443.4
55°	216.7	226.2	241.0	266.5	300.7	321.8	344.3	392.8	433.0	432.2	385.9
57.5°	194.7	202.5	218.0	241.4	273.0	292.0	314.5	356.5	389.3	377.7	334.0
60°	174.3	180.0	195.1	214.1	244.4	262.2	283.8	318.0	343.0	326.6	282.5
62.5°	153.1	159.6	171.7	190.3	217.2	231.4	247.4	282.1	298.1	283.3	238.4
65°	134.1	139.3	150.1	165.7	189.9	202.9	216.7	245.3	260.4	239.2	202.0
67.5°	115.1	121.1	128.9	142.8	161.8	173.9	186.0	210.7	217.6	198.6	167.4
70°	97.3	102.5	109.9	119.8	135.8	146.6	155.7	176.1	180.8	163.1	138.4
72.5°	80.0	83.5	89.5	97.8	112.5	118.5	128.0	141.9	147.9	131.9	114.2
75°	64.9	67.5	71.4	77.4	87.4	93.9	101.7	114.6	114.2	103.0	90.4
77.5°	50.2	50.6	54.9	60.6	66.6	72.2	76.1	85.2	86.1	79.2	68.8
80°	35.9	37.2	38.9	43.3	48.5	50.6	55.4	61.0	61.9	56.7	49.7
82.5°	22.9	23.8	25.1	27.7	31.1	33.7	36.3	38.5	40.7	37.6	32.0
85°	13.0	13.4	14.7	15.6	17.3	18.6	20.8	22.9	22.5	20.3	18.6
87.5°	6.5	6.5	6.5	7.4	8.2	8.2	9.1	9.5	9.9	9.1	8.2
90°	0.5	1.5	2.5	3.4	4.4	4.9	5.3	6.2	7.1	7.9	8.8
92.5°	16.5	17.1	17.7	18.3	18.9	19.2	19.8	20.9	22.0	23.1	24.2
95°	35.7	35.9	36.2	36.4	36.7	36.8	37.4	38.6	39.9	41.1	42.3
97.5°	55.0	55.1	55.2	55.3	55.4	55.5	56.4	58.1	59.8	61.5	63.2
100°	76.9	76.9	76.9	76.9	76.9	76.9	77.7	79.3	80.9	82.5	84.1
102.5°	100.6	101.2	101.8	102.4	103.0	103.3	103.6	104.2	104.9	105.5	106.1
105°	125.3	125.9	126.5	127.1	127.7	128.0	128.4	129.1	129.8	130.6	131.3
107.5°	152.2	152.8	153.4	154.1	154.7	155.0	155.3	155.9	156.5	157.1	157.7
110°	180.3	180.9	181.5	182.1	182.7	183.0	183.2	183.6	183.9	184.3	184.7



TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	208.8	209.0	209.3	209.5	209.8	209.9	210.1	210.6	211.1	211.6	212.1
115°	236.9	237.4	237.9	238.4	238.9	239.1	239.2	239.5	239.7	240.0	240.2
117.5°	265.4	265.5	265.7	265.8	265.9	266.0	266.1	266.4	266.6	266.9	267.1
120°	291.8	292.4	293.0	293.7	294.3	294.6	294.7	294.8	294.9	295.0	295.1
122.5°	320.4	320.5	320.6	320.7	320.8	320.9	321.1	321.5	321.8	322.2	322.6
125°	345.7	346.4	347.2	347.9	348.6	349.0	349.1	349.2	349.3	349.4	349.5
127.5°	373.7	374.1	374.4	374.8	375.1	375.3	375.4	375.5	375.6	375.8	375.9
130°	398.4	399.0	399.6	400.3	400.9	401.2	401.3	401.6	401.8	402.1	402.3
132.5°	423.2	424.3	425.4	426.5	427.6	428.1	428.0	427.9	427.8	427.7	427.6
135°	449.5	450.2	451.0	451.7	452.4	452.8	452.9	453.0	453.1	453.3	453.4
137.5°	474.3	475.0	475.8	476.5	477.2	477.6	477.7	478.0	478.2	478.5	478.7
140°	497.9	498.5	499.1	499.7	500.3	500.6	500.8	501.2	501.5	501.9	502.3
142.5°	521.5	522.0	522.5	523.0	523.5	523.7	523.9	524.4	524.9	525.4	525.9
145°	544.6	545.1	545.6	546.1	546.6	546.8	547.0	547.4	547.7	548.1	548.5
147.5°	566.0	566.4	566.8	567.1	567.5	567.7	567.8	568.1	568.3	568.6	568.8
150°	587.5	587.4	587.2	587.1	587.0	586.9	587.1	587.6	588.1	588.6	589.1
152.5°	605.1	605.3	605.6	605.8	606.1	606.2	606.3	606.4	606.5	606.6	606.7
155°	623.2	623.2	623.2	623.2	623.2	623.2	623.3	623.4	623.5	623.6	623.7
157.5°	639.7	639.5	639.2	639.0	638.7	638.6	638.7	638.8	638.9	639.0	639.1
160°	654.0	653.6	653.2	652.9	652.5	652.3	652.4	652.5	652.6	652.8	652.9
162.5°	666.6	666.4	666.1	665.9	665.6	665.5	665.5	665.5	665.5	665.5	665.5
165°	677.6	677.4	677.1	676.9	676.6	676.5	676.6	676.7	676.8	677.0	677.1
167.5°	687.5	687.0	686.5	686.0	685.5	685.3	685.3	685.3	685.3	685.3	685.3
170°	695.2	694.7	694.2	693.7	693.2	693.0	693.0	693.0	693.0	693.0	693.0
172.5°	700.7	700.2	699.7	699.2	698.7	698.5	698.5	698.5	698.5	698.5	698.5
175°	704.5	704.0	703.5	703.0	702.5	702.3	702.3	702.3	702.3	702.3	702.3
177.5°	707.3	706.8	706.3	705.8	705.3	705.1	705.0	704.9	704.8	704.6	704.5
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	533.0	536.0	538.6	540.7	542.5	545.1	543.3	543.8	544.6	546.4	546.4
5°	567.6	572.3	574.9	583.6	585.7	585.3	584.0	590.9	590.5	587.9	587.5
7.5°	601.3	609.5	616.9	623.8	626.0	631.6	632.9	635.9	635.0	639.4	637.2
10°	632.0	645.0	651.9	662.3	664.9	667.5	671.0	672.7	676.6	676.1	676.1
12.5°	655.8	671.4	680.5	683.1	693.0	696.0	699.1	704.7	703.4	703.8	706.4
15°	674.4	689.6	697.3	709.5	716.4	719.8	725.0	731.1	730.2	734.1	733.2
17.5°	688.3	702.5	716.8	735.0	735.4	744.5	756.6	759.2	764.8	760.9	760.9
20°	699.5	718.5	738.9	762.2	764.8	770.4	785.2	795.1	801.6	799.4	800.7
22.5°	711.6	738.9	762.7	786.0	798.6	808.5	822.8	838.4	844.0	847.4	846.6
25°	727.2	755.7	790.8	823.2	836.2	855.2	874.3	889.4	893.7	903.3	894.6
27.5°	743.2	783.4	827.1	865.2	881.6	897.2	920.1	931.4	937.0	941.3	938.3
30°	756.6	812.0	859.6	894.6	906.3	915.4	928.3	930.9	928.8	932.2	936.6
32.5°	777.4	831.4	871.7	888.5	887.2	886.8	876.9	863.0	860.0	851.8	863.0
35°	788.6	831.9	847.4	825.0	815.9	799.4	767.9	747.1	728.9	725.0	725.9
37.5°	782.1	799.0	780.4	721.1	706.4	681.3	639.4	610.0	596.5	586.2	599.6
40°	747.1	728.5	677.4	605.2	584.0	560.2	520.8	504.8	485.8	481.9	499.6
42.5°	689.1	632.5	560.2	504.4	482.3	468.9	436.1	420.9	407.5	401.4	411.4
45°	610.4	541.6	468.9	423.1	404.5	388.5	369.0	353.0	344.3	341.7	350.0
47.5°	529.1	456.4	398.4	364.2	344.8	332.7	314.5	305.4	298.5	299.4	300.7
50°	451.2	385.0	340.5	306.3	296.8	287.2	275.1	267.3	263.9	265.2	264.3
52.5°	384.1	330.5	292.9	266.5	262.2	253.1	243.1	236.6	235.3	235.8	237.1
55°	325.3	283.3	253.5	234.5	229.7	223.2	217.2	212.8	209.4	210.7	210.2
57.5°	280.8	244.0	221.1	205.5	202.0	198.1	192.5	190.3	189.0	186.4	188.6
60°	241.4	211.5	191.6	182.1	179.1	176.5	170.4	167.8	167.0	165.7	169.1
62.5°	204.2	183.0	167.8	159.2	156.2	153.6	150.5	148.4	148.8	147.1	148.8
65°	174.8	157.5	146.6	138.9	135.0	133.2	132.8	129.3	128.9	129.3	129.8
67.5°	147.5	132.8	124.6	119.8	116.8	115.1	113.8	111.6	113.3	112.0	112.9
70°	122.9	112.9	104.3	99.5	98.2	98.6	96.5	95.6	96.0	95.2	96.0
72.5°	99.1	90.8	87.4	83.9	82.2	81.8	80.5	79.2	80.5	80.0	80.0
75°	79.2	73.1	69.2	67.1	67.1	66.2	64.0	64.0	64.0	63.6	64.0
77.5°	61.0	55.8	54.1	51.9	51.9	50.6	50.2	50.2	49.3	50.6	49.7
80°	45.4	41.5	38.9	37.6	37.6	37.2	36.3	35.9	36.3	35.9	35.9
82.5°	29.4	27.7	26.4	25.1	24.7	25.1	24.7	23.8	24.2	23.8	24.7
85°	16.9	15.1	15.1	14.3	14.7	13.8	14.3	13.4	13.0	14.3	13.4
87.5°	7.4	6.9	6.9	6.1	6.1	6.1	5.6	6.1	5.6	5.2	5.6
90°	9.4	10.0	10.6	11.2	11.5	11.7	12.1	12.4	12.8	13.2	12.8
92.5°	25.0	25.9	26.7	27.6	28.0	28.1	28.4	28.6	28.9	29.1	28.9
95°	43.2	44.0	44.9	45.8	46.2	46.3	46.6	46.8	47.1	47.3	47.1
97.5°	63.9	64.7	65.4	66.1	66.5	66.6	66.7	66.8	66.9	67.0	66.9
100°	85.2	86.3	87.4	88.5	89.0	89.1	89.4	89.6	89.9	90.1	89.9
102.5°	107.3	108.5	109.8	111.0	111.6	111.8	112.1	112.5	112.8	113.2	112.8
105°	132.0	132.8	133.5	134.2	134.6	134.8	135.2	135.5	135.9	136.3	135.9
107.5°	158.1	158.5	158.8	159.2	159.4	159.4	159.4	159.4	159.4	159.4	159.4
110°	185.1	185.4	185.8	186.1	186.3	186.2	186.1	186.0	185.9	185.8	185.9

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	212.2	212.4	212.5	212.6	212.7	212.6	212.3	212.1	211.8	211.6	211.8
115°	240.1	239.9	239.8	239.7	239.6	239.5	239.4	239.3	239.2	239.1	239.2
117.5°	267.2	267.3	267.4	267.5	267.6	267.4	266.9	266.4	265.9	265.4	265.9
120°	295.1	295.1	295.1	295.1	295.1	294.9	294.4	293.9	293.4	292.9	293.4
122.5°	322.5	322.3	322.2	322.1	322.0	321.8	321.5	321.1	320.8	320.4	320.8
125°	349.3	349.0	348.8	348.5	348.4	348.3	348.2	348.1	348.0	347.9	348.0
127.5°	375.8	375.6	375.5	375.4	375.3	375.2	374.9	374.7	374.4	374.2	374.4
130°	402.2	402.0	401.9	401.8	401.7	401.6	401.3	401.1	400.8	400.6	400.8
132.5°	427.5	427.3	427.2	427.1	427.0	426.8	426.5	426.1	425.8	425.4	425.8
135°	453.4	453.4	453.4	453.4	453.4	453.2	452.7	452.2	451.7	451.2	451.7
137.5°	478.8	478.9	479.0	479.1	479.2	478.9	478.3	477.7	477.1	476.5	477.1
140°	502.5	502.8	503.0	503.3	503.4	503.1	502.5	501.8	501.2	500.6	501.2
142.5°	526.0	526.2	526.3	526.4	526.5	526.2	525.6	524.9	524.3	523.7	524.3
145°	548.5	548.5	548.5	548.5	548.5	548.3	547.9	547.6	547.2	546.8	547.2
147.5°	569.2	569.5	569.9	570.2	570.4	569.9	568.9	568.0	567.0	566.0	567.0
150°	589.1	589.1	589.1	589.1	589.1	589.0	588.7	588.5	588.2	588.0	588.2
152.5°	607.1	607.5	607.8	608.2	608.4	608.2	607.7	607.2	606.7	606.2	606.7
155°	624.2	624.7	625.2	625.7	625.9	625.6	625.0	624.4	623.8	623.2	623.8
157.5°	639.6	640.1	640.6	641.1	641.3	640.9	640.0	639.2	638.3	637.5	638.3
160°	653.4	653.9	654.4	654.9	655.1	654.8	654.2	653.5	652.9	652.3	652.9
162.5°	666.1	666.7	667.4	668.0	668.3	667.9	667.2	666.5	665.7	665.0	665.7
165°	677.6	678.1	678.6	679.1	679.3	678.9	678.2	677.5	676.7	676.0	676.7
167.5°	686.0	686.8	687.5	688.2	688.6	688.2	687.5	686.8	686.0	685.3	686.0
170°	693.7	694.5	695.2	695.9	696.3	695.9	695.0	694.1	693.3	692.4	693.3
172.5°	699.2	700.0	700.7	701.4	701.8	701.4	700.7	700.0	699.2	698.5	699.2
175°	703.0	703.8	704.5	705.2	705.6	705.2	704.3	703.5	702.6	701.8	702.6
177.5°	705.2	706.0	706.7	707.4	707.8	707.4	706.5	705.7	704.8	704.0	704.8
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	545.5	542.5	543.3	542.5	540.3	539.0	535.5	531.2	529.5	527.3	526.0
5°	589.2	587.0	586.6	583.1	582.3	577.1	568.4	564.1	558.9	553.7	548.5
7.5°	636.8	634.2	625.5	624.2	625.1	618.6	607.4	598.7	587.9	580.5	570.6
10°	676.1	671.0	663.6	664.0	661.0	652.3	641.1	632.0	616.4	606.9	592.7
12.5°	699.9	695.6	694.7	690.4	687.8	676.6	663.2	651.5	639.8	626.8	616.0
15°	728.9	723.3	719.4	713.3	711.6	699.9	685.2	671.8	658.4	646.3	623.4
17.5°	760.9	754.9	740.2	738.9	728.5	717.2	703.0	683.1	668.8	651.5	634.6
20°	797.3	788.6	769.6	764.8	756.6	738.0	718.5	696.5	673.5	655.8	635.9
22.5°	837.9	822.8	808.9	793.8	787.8	764.8	738.0	711.2	683.5	659.3	635.5
25°	890.7	870.8	851.3	836.2	825.8	796.0	760.1	724.6	692.6	661.0	629.9
27.5°	932.2	914.9	893.7	873.8	860.4	825.0	783.9	738.0	698.2	659.7	626.4
30°	935.3	930.1	917.1	906.3	891.6	853.5	808.1	756.2	706.9	660.1	619.5
32.5°	878.6	889.0	894.6	896.3	893.3	871.2	829.7	772.6	714.6	656.2	613.4
35°	756.6	784.3	818.5	831.4	844.0	855.7	834.0	784.3	717.2	655.4	603.9
37.5°	622.9	648.0	704.7	730.6	745.4	791.6	809.4	782.6	722.4	656.2	594.8
40°	502.7	542.5	583.1	618.2	641.1	693.0	748.0	754.0	715.1	648.0	583.1
42.5°	423.1	446.4	477.1	509.6	529.9	591.4	665.8	709.5	692.1	634.6	568.9
45°	360.3	377.7	406.6	417.5	443.4	502.2	581.0	644.1	652.8	613.4	552.4
47.5°	309.3	324.0	342.6	356.0	376.8	420.9	487.5	557.2	598.7	584.4	529.5
50°	272.5	284.6	300.2	308.0	321.4	361.2	411.4	480.6	536.4	541.2	499.6
52.5°	241.8	248.7	260.9	269.5	280.3	304.5	350.0	407.1	469.8	495.8	462.9
55°	215.0	220.6	231.4	237.1	242.7	263.4	298.9	350.8	409.7	443.8	425.2
57.5°	190.8	195.5	204.6	209.8	212.8	232.7	260.0	300.7	353.4	395.0	384.6
60°	170.9	175.2	180.4	184.3	187.7	204.2	223.2	256.1	303.2	343.5	340.9
62.5°	149.7	153.6	159.2	163.1	166.1	176.5	192.5	217.6	257.8	295.0	302.4
65°	131.1	134.1	138.0	139.7	143.6	151.4	164.4	186.9	219.8	253.1	258.3
67.5°	114.2	115.1	117.7	121.6	122.4	129.3	141.0	157.9	183.4	210.7	218.9
70°	96.0	97.3	99.5	102.5	104.3	108.6	118.5	129.8	151.8	175.6	181.7
72.5°	80.0	81.8	82.6	84.4	85.2	92.1	96.5	107.7	122.9	142.8	149.2
75°	64.9	66.6	67.1	67.9	68.8	71.8	77.9	84.8	97.3	110.3	119.0
77.5°	51.5	51.0	51.9	53.2	52.8	55.4	59.3	65.3	73.5	84.4	90.0
80°	36.3	36.3	37.6	38.9	38.5	41.1	42.4	46.7	53.6	60.6	62.7
82.5°	24.2	24.2	25.5	25.5	26.4	26.8	28.6	30.7	36.3	39.8	41.1
85°	13.8	13.8	14.3	14.3	14.3	15.1	16.4	17.3	19.0	21.2	22.1
87.5°	5.6	6.1	6.1	6.1	6.1	6.9	6.9	7.8	8.2	9.1	9.1
90°	12.4	12.1	11.7	11.5	11.2	10.6	10.0	9.4	8.8	7.9	7.1
92.5°	28.6	28.4	28.1	28.0	27.6	26.7	25.9	25.0	24.2	23.1	22.0
95°	46.8	46.6	46.3	46.2	45.8	44.9	44.0	43.2	42.3	41.1	39.9
97.5°	66.8	66.7	66.6	66.5	66.1	65.4	64.7	63.9	63.2	61.5	59.8
100°	89.6	89.4	89.1	89.0	88.5	87.4	86.3	85.2	84.1	82.5	80.9
102.5°	112.5	112.1	111.8	111.6	111.0	109.8	108.5	107.3	106.1	105.5	104.9
105°	135.5	135.2	134.8	134.6	134.2	133.5	132.8	132.0	131.3	130.6	129.8
107.5°	159.4	159.4	159.4	159.4	159.2	158.8	158.5	158.1	157.7	157.1	156.5
110°	186.0	186.1	186.2	186.3	186.1	185.8	185.4	185.1	184.7	184.3	183.9

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	212.1	212.3	212.6	212.7	212.6	212.5	212.4	212.2	212.1	211.6	211.1
115°	239.3	239.4	239.5	239.6	239.7	239.8	239.9	240.1	240.2	240.0	239.7
117.5°	266.4	266.9	267.4	267.6	267.5	267.4	267.3	267.2	267.1	266.9	266.6
120°	293.9	294.4	294.9	295.1	295.1	295.1	295.1	295.1	295.1	295.0	294.9
122.5°	321.1	321.5	321.8	322.0	322.1	322.2	322.3	322.5	322.6	322.2	321.8
125°	348.1	348.2	348.3	348.4	348.5	348.8	349.0	349.3	349.5	349.4	349.3
127.5°	374.7	374.9	375.2	375.3	375.4	375.5	375.6	375.8	375.9	375.8	375.6
130°	401.1	401.3	401.6	401.7	401.8	401.9	402.0	402.2	402.3	402.1	401.8
132.5°	426.1	426.5	426.8	427.0	427.1	427.2	427.3	427.5	427.6	427.7	427.8
135°	452.2	452.7	453.2	453.4	453.4	453.4	453.4	453.4	453.4	453.3	453.1
137.5°	477.7	478.3	478.9	479.2	479.1	479.0	478.9	478.8	478.7	478.5	478.2
140°	501.8	502.5	503.1	503.4	503.3	503.0	502.8	502.5	502.3	501.9	501.5
142.5°	524.9	525.6	526.2	526.5	526.4	526.3	526.2	526.0	525.9	525.4	524.9
145°	547.6	547.9	548.3	548.5	548.5	548.5	548.5	548.5	548.5	548.1	547.7
147.5°	568.0	568.9	569.9	570.4	570.2	569.9	569.5	569.2	568.8	568.6	568.3
150°	588.5	588.7	589.0	589.1	589.1	589.1	589.1	589.1	589.1	588.6	588.1
152.5°	607.2	607.7	608.2	608.4	608.2	607.8	607.5	607.1	606.7	606.6	606.5
155°	624.4	625.0	625.6	625.9	625.7	625.2	624.7	624.2	623.7	623.6	623.5
157.5°	639.2	640.0	640.9	641.3	641.1	640.6	640.1	639.6	639.1	639.0	638.9
160°	653.5	654.2	654.8	655.1	654.9	654.4	653.9	653.4	652.9	652.8	652.6
162.5°	666.5	667.2	667.9	668.3	668.0	667.4	666.7	666.1	665.5	665.5	665.5
165°	677.5	678.2	678.9	679.3	679.1	678.6	678.1	677.6	677.1	677.0	676.8
167.5°	686.8	687.5	688.2	688.6	688.2	687.5	686.8	686.0	685.3	685.3	685.3
170°	694.1	695.0	695.9	696.3	695.9	695.2	694.5	693.7	693.0	693.0	693.0
172.5°	700.0	700.7	701.4	701.8	701.4	700.7	700.0	699.2	698.5	698.5	698.5
175°	703.5	704.3	705.2	705.6	705.2	704.5	703.8	703.0	702.3	702.3	702.3
177.5°	705.7	706.5	707.4	707.8	707.4	706.7	706.0	705.2	704.5	704.6	704.8
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	524.3	522.1	519.5	519.5	516.5	515.2	512.6	511.8	509.6	506.1	503.5
5°	542.9	537.3	533.8	530.8	524.3	519.5	514.8	509.6	504.4	498.3	491.4
7.5°	561.1	550.7	545.9	540.7	531.2	521.3	511.8	504.8	497.9	488.4	479.7
10°	580.1	567.1	558.5	551.6	536.8	524.3	510.5	500.5	489.7	477.6	466.3
12.5°	596.1	579.2	571.9	558.9	542.0	526.9	509.6	494.5	480.2	465.9	452.1
15°	609.5	593.5	575.3	570.2	546.8	525.2	505.7	486.2	468.5	454.2	438.2
17.5°	613.8	593.5	584.4	571.9	544.2	521.7	497.0	475.9	459.0	437.8	425.2
20°	615.1	595.7	583.1	571.5	546.8	516.9	492.7	466.8	446.4	425.2	405.3
22.5°	611.7	588.8	576.6	565.4	537.7	512.2	484.1	455.5	431.7	412.3	392.4
25°	605.2	578.4	566.7	554.6	528.2	500.1	469.4	442.1	420.0	396.7	377.2
27.5°	596.5	565.8	552.4	539.9	513.9	487.5	458.5	430.4	405.8	381.1	362.9
30°	585.7	550.3	538.1	521.7	496.6	471.5	445.1	417.0	389.3	366.0	346.1
32.5°	571.9	534.7	518.7	503.1	475.9	452.9	427.8	401.4	374.6	351.7	330.9
35°	559.3	516.9	499.2	483.6	453.4	429.1	408.4	383.7	359.9	336.1	317.5
37.5°	542.5	499.2	478.0	462.0	431.3	406.6	387.2	368.1	343.0	320.1	302.8
40°	524.7	477.1	457.3	441.2	409.2	382.4	363.8	346.9	326.6	305.4	287.2
42.5°	508.7	456.0	434.8	415.3	382.8	359.1	340.0	327.0	308.4	289.4	273.0
45°	488.4	433.5	410.5	390.2	359.1	333.1	314.9	304.5	290.7	272.1	257.8
47.5°	467.6	409.2	385.4	365.5	331.8	308.9	291.1	281.2	271.7	257.0	242.7
50°	440.4	383.7	362.1	339.2	305.8	282.5	267.8	257.8	250.5	240.1	228.0
52.5°	410.5	357.3	334.0	314.1	281.2	260.0	243.1	237.5	230.1	222.4	212.0
55°	379.0	328.8	306.3	286.8	256.5	234.9	221.1	215.0	209.4	203.3	196.4
57.5°	347.4	298.9	277.7	260.4	232.3	211.5	200.3	192.1	188.2	184.7	179.1
60°	308.0	266.9	250.5	234.9	207.2	188.2	177.4	171.3	167.8	166.1	163.5
62.5°	273.4	239.7	221.5	206.3	184.3	167.4	157.0	152.3	149.2	148.4	145.4
65°	236.6	207.6	193.4	180.4	161.4	146.2	137.6	131.9	129.8	129.3	129.3
67.5°	202.0	178.7	164.4	155.3	138.9	125.5	117.2	115.1	113.8	112.0	111.6
70°	169.6	151.0	138.4	130.6	115.9	106.0	99.5	96.0	96.0	94.7	93.9
72.5°	141.0	122.4	114.2	107.7	95.6	87.0	82.2	81.3	78.3	77.9	77.9
75°	110.3	96.5	90.8	85.2	76.1	70.1	66.2	64.0	62.3	62.3	62.7
77.5°	83.1	73.5	68.3	64.0	57.5	53.6	50.6	49.7	48.0	48.0	48.0
80°	58.8	53.6	49.7	46.3	41.5	38.1	36.3	34.6	34.6	34.2	34.6
82.5°	38.1	33.7	31.6	31.1	26.8	25.5	23.4	23.8	22.5	22.1	22.9
85°	22.1	19.9	17.3	16.4	14.7	13.0	12.1	12.5	12.1	11.7	12.1
87.5°	8.7	7.4	6.9	6.9	5.6	5.2	4.8	5.2	4.3	4.3	4.8
90°	6.2	5.3	4.9	4.4	3.4	2.5	1.5	0.5	1.5	2.5	3.4
92.5°	20.9	19.8	19.2	18.9	18.3	17.7	17.1	16.5	17.1	17.7	18.3
95°	38.6	37.4	36.8	36.7	36.4	36.2	35.9	35.7	35.9	36.2	36.4
97.5°	58.1	56.4	55.5	55.4	55.3	55.2	55.1	55.0	55.1	55.2	55.3
100°	79.3	77.7	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9	76.9
102.5°	104.2	103.6	103.3	103.0	102.4	101.8	101.2	100.6	101.2	101.8	102.4
105°	129.1	128.4	128.0	127.7	127.1	126.5	125.9	125.3	125.9	126.5	127.1
107.5°	155.9	155.3	155.0	154.7	154.1	153.4	152.8	152.2	152.8	153.4	154.1
110°	183.6	183.2	183.0	182.7	182.1	181.5	180.9	180.3	180.9	181.5	182.1

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	210.6	210.1	209.9	209.8	209.5	209.3	209.0	208.8	209.0	209.3	209.5
115°	239.5	239.2	239.1	238.9	238.4	237.9	237.4	236.9	237.4	237.9	238.4
117.5°	266.4	266.1	266.0	265.9	265.8	265.7	265.5	265.4	265.5	265.7	265.8
120°	294.8	294.7	294.6	294.3	293.7	293.0	292.4	291.8	292.4	293.0	293.7
122.5°	321.5	321.1	320.9	320.8	320.7	320.6	320.5	320.4	320.5	320.6	320.7
125°	349.2	349.1	349.0	348.6	347.9	347.2	346.4	345.7	346.4	347.2	347.9
127.5°	375.5	375.4	375.3	375.1	374.8	374.4	374.1	373.7	374.1	374.4	374.8
130°	401.6	401.3	401.2	400.9	400.3	399.6	399.0	398.4	399.0	399.6	400.3
132.5°	427.9	428.0	428.1	427.6	426.5	425.4	424.3	423.2	424.3	425.4	426.5
135°	453.0	452.9	452.8	452.4	451.7	451.0	450.2	449.5	450.2	451.0	451.7
137.5°	478.0	477.7	477.6	477.2	476.5	475.8	475.0	474.3	475.0	475.8	476.5
140°	501.2	500.8	500.6	500.3	499.7	499.1	498.5	497.9	498.5	499.1	499.7
142.5°	524.4	523.9	523.7	523.5	523.0	522.5	522.0	521.5	522.0	522.5	523.0
145°	547.4	547.0	546.8	546.6	546.1	545.6	545.1	544.6	545.1	545.6	546.1
147.5°	568.1	567.8	567.7	567.5	567.1	566.8	566.4	566.0	566.4	566.8	567.1
150°	587.6	587.1	586.9	587.0	587.1	587.2	587.4	587.5	587.4	587.2	587.1
152.5°	606.4	606.3	606.2	606.1	605.8	605.6	605.3	605.1	605.3	605.6	605.8
155°	623.4	623.3	623.2	623.2	623.2	623.2	623.2	623.2	623.2	623.2	623.2
157.5°	638.8	638.7	638.6	638.7	639.0	639.2	639.5	639.7	639.5	639.2	639.0
160°	652.5	652.4	652.3	652.5	652.9	653.2	653.6	654.0	653.6	653.2	652.9
162.5°	665.5	665.5	665.5	665.6	665.9	666.1	666.4	666.6	666.4	666.1	665.9
165°	676.7	676.6	676.5	676.6	676.9	677.1	677.4	677.6	677.4	677.1	676.9
167.5°	685.3	685.3	685.3	685.5	686.0	686.5	687.0	687.5	687.0	686.5	686.0
170°	693.0	693.0	693.0	693.2	693.7	694.2	694.7	695.2	694.7	694.2	693.7
172.5°	698.5	698.5	698.5	698.7	699.2	699.7	700.2	700.7	700.2	699.7	699.2
175°	702.3	702.3	702.3	702.5	703.0	703.5	704.0	704.5	704.0	703.5	703.0
177.5°	704.9	705.0	705.1	705.3	705.8	706.3	706.8	707.3	706.8	706.3	705.8
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	502.7	501.8	499.6	498.3	494.0	488.8	487.1	482.8	484.5	481.5	481.5
5°	489.3	485.4	482.8	478.9	470.7	465.0	459.0	456.0	454.2	452.1	450.3
7.5°	472.0	468.9	466.3	459.0	449.9	442.1	434.8	431.7	426.1	422.2	420.5
10°	456.8	452.5	446.4	437.8	428.3	418.3	411.8	405.3	401.0	398.9	394.1
12.5°	441.2	436.1	429.6	417.0	406.6	400.6	388.9	382.8	380.7	379.0	373.3
15°	425.2	419.6	411.8	400.1	391.1	376.8	369.9	365.1	359.9	359.5	355.2
17.5°	411.0	404.0	397.6	383.3	372.0	359.5	355.6	350.4	345.6	340.5	338.3
20°	392.8	386.3	381.5	366.0	353.4	345.6	339.2	334.8	331.8	326.6	325.7
22.5°	376.4	369.4	362.9	351.3	340.5	330.5	322.7	318.0	316.7	314.5	310.6
25°	360.3	353.4	345.6	334.8	323.6	316.7	309.7	306.7	304.1	300.7	297.6
27.5°	346.9	340.5	333.1	319.7	310.2	305.0	297.6	294.2	290.7	289.0	287.7
30°	330.9	323.6	318.0	307.6	297.2	290.3	285.1	282.1	279.0	277.3	276.4
32.5°	315.4	308.4	304.5	293.3	285.1	276.9	273.0	270.8	269.1	267.3	265.6
35°	302.8	295.9	289.8	279.5	271.2	265.6	262.6	259.1	257.8	256.1	256.1
37.5°	287.2	282.1	276.0	266.0	258.7	254.4	251.8	247.4	247.0	246.1	244.8
40°	273.8	268.6	263.0	254.4	247.9	242.7	239.2	237.1	235.8	234.9	234.0
42.5°	259.6	253.9	251.3	241.4	235.8	230.6	228.8	226.7	226.2	224.5	222.4
45°	245.7	241.0	235.8	228.4	223.7	219.3	216.7	215.0	212.8	212.4	211.1
47.5°	233.6	228.0	223.2	216.3	211.1	207.6	205.5	203.3	201.6	200.3	199.0
50°	218.0	213.7	209.8	202.5	198.1	194.7	191.6	189.9	188.2	188.2	188.2
52.5°	202.9	199.0	195.5	190.3	185.1	182.1	178.7	177.4	176.5	175.2	176.5
55°	188.2	184.3	180.8	176.9	170.9	168.3	164.8	163.5	164.0	164.0	165.3
57.5°	172.6	169.6	167.4	162.7	157.0	154.4	152.3	151.0	151.0	152.7	153.1
60°	157.5	154.4	150.5	146.2	142.8	139.7	138.4	138.9	138.9	139.7	141.9
62.5°	140.6	138.9	136.7	130.6	128.5	126.3	124.6	125.9	125.5	127.6	130.6
65°	125.0	123.3	120.3	117.2	114.6	112.5	112.0	112.5	113.3	115.5	119.0
67.5°	107.7	107.7	105.1	102.5	100.4	98.2	98.6	99.1	99.9	102.5	107.7
70°	93.4	91.7	89.1	87.4	85.7	84.8	83.9	85.7	88.2	90.0	93.9
72.5°	77.9	76.6	74.4	72.7	72.2	71.4	70.9	71.8	74.4	77.4	81.8
75°	61.4	61.9	60.6	59.3	59.3	58.0	58.8	58.8	61.4	64.5	67.9
77.5°	47.6	47.2	46.7	45.9	45.4	45.4	45.4	46.3	48.9	50.6	54.1
80°	33.7	34.2	32.9	33.3	32.9	33.3	33.3	35.0	36.3	38.5	41.1
82.5°	22.5	22.5	21.6	22.1	22.1	22.1	22.5	23.4	25.1	26.8	28.6
85°	12.5	13.0	12.1	13.0	13.0	13.0	13.4	13.8	15.1	15.6	17.3
87.5°	4.8	5.6	5.6	4.8	5.2	5.6	6.1	5.6	6.5	7.4	7.8
90°	4.4	4.9	5.3	6.2	7.1	7.9	8.8	9.4	10.0	10.6	11.2
92.5°	18.9	19.2	19.8	20.9	22.0	23.1	24.2	25.0	25.9	26.7	27.6
95°	36.7	36.8	37.4	38.6	39.9	41.1	42.3	43.2	44.0	44.9	45.8
97.5°	55.4	55.5	56.4	58.1	59.8	61.5	63.2	63.9	64.7	65.4	66.1
100°	76.9	76.9	77.7	79.3	80.9	82.5	84.1	85.2	86.3	87.4	88.5
102.5°	103.0	103.3	103.6	104.2	104.9	105.5	106.1	107.3	108.5	109.8	111.0
105°	127.7	128.0	128.4	129.1	129.8	130.6	131.3	132.0	132.8	133.5	134.2
107.5°	154.7	155.0	155.3	155.9	156.5	157.1	157.7	158.1	158.5	158.8	159.2
110°	182.7	183.0	183.2	183.6	183.9	184.3	184.7	185.1	185.4	185.8	186.1

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	209.8	209.9	210.1	210.6	211.1	211.6	212.1	212.2	212.4	212.5	212.6
115°	238.9	239.1	239.2	239.5	239.7	240.0	240.2	240.1	239.9	239.8	239.7
117.5°	265.9	266.0	266.1	266.4	266.6	266.9	267.1	267.2	267.3	267.4	267.5
120°	294.3	294.6	294.7	294.8	294.9	295.0	295.1	295.1	295.1	295.1	295.1
122.5°	320.8	320.9	321.1	321.5	321.8	322.2	322.6	322.5	322.3	322.2	322.1
125°	348.6	349.0	349.1	349.2	349.3	349.4	349.5	349.3	349.0	348.8	348.5
127.5°	375.1	375.3	375.4	375.5	375.6	375.8	375.9	375.8	375.6	375.5	375.4
130°	400.9	401.2	401.3	401.6	401.8	402.1	402.3	402.2	402.0	401.9	401.8
132.5°	427.6	428.1	428.0	427.9	427.8	427.7	427.6	427.5	427.3	427.2	427.1
135°	452.4	452.8	452.9	453.0	453.1	453.3	453.4	453.4	453.4	453.4	453.4
137.5°	477.2	477.6	477.7	478.0	478.2	478.5	478.7	478.8	478.9	479.0	479.1
140°	500.3	500.6	500.8	501.2	501.5	501.9	502.3	502.5	502.8	503.0	503.3
142.5°	523.5	523.7	523.9	524.4	524.9	525.4	525.9	526.0	526.2	526.3	526.4
145°	546.6	546.8	547.0	547.4	547.7	548.1	548.5	548.5	548.5	548.5	548.5
147.5°	567.5	567.7	567.8	568.1	568.3	568.6	568.8	569.2	569.5	569.9	570.2
150°	587.0	586.9	587.1	587.6	588.1	588.6	589.1	589.1	589.1	589.1	589.1
152.5°	606.1	606.2	606.3	606.4	606.5	606.6	606.7	607.1	607.5	607.8	608.2
155°	623.2	623.2	623.3	623.4	623.5	623.6	623.7	624.2	624.7	625.2	625.7
157.5°	638.7	638.6	638.7	638.8	638.9	639.0	639.1	639.6	640.1	640.6	641.1
160°	652.5	652.3	652.4	652.5	652.6	652.8	652.9	653.4	653.9	654.4	654.9
162.5°	665.6	665.5	665.5	665.5	665.5	665.5	665.5	666.1	666.7	667.4	668.0
165°	676.6	676.5	676.6	676.7	676.8	677.0	677.1	677.6	678.1	678.6	679.1
167.5°	685.5	685.3	685.3	685.3	685.3	685.3	685.3	686.0	686.8	687.5	688.2
170°	693.2	693.0	693.0	693.0	693.0	693.0	693.0	693.7	694.5	695.2	695.9
172.5°	698.7	698.5	698.5	698.5	698.5	698.5	698.5	699.2	700.0	700.7	701.4
175°	702.5	702.3	702.3	702.3	702.3	702.3	702.3	703.0	703.8	704.5	705.2
177.5°	705.3	705.1	705.0	704.9	704.8	704.6	704.5	705.2	706.0	706.7	707.4
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	483.2	480.2	479.7	480.6	478.9	481.5	480.6	481.5	479.3	481.5	480.2
5°	449.9	449.0	447.3	445.1	445.6	446.0	448.2	446.0	447.7	448.2	450.3
7.5°	418.7	417.0	418.3	417.5	413.6	412.7	413.6	414.9	417.5	419.2	420.5
10°	393.7	392.8	391.1	389.8	387.6	386.3	388.0	386.3	389.8	392.8	392.8
12.5°	374.6	371.2	369.0	368.6	363.8	364.7	366.4	367.7	371.6	373.3	373.3
15°	354.7	352.1	351.3	349.5	347.8	349.5	348.7	350.0	351.7	353.4	354.3
17.5°	337.4	337.0	337.4	333.1	334.4	332.2	332.7	334.8	333.5	334.8	337.4
20°	321.8	322.7	321.4	319.7	319.7	317.1	320.1	319.3	319.7	322.3	326.2
22.5°	310.2	309.7	308.4	307.1	305.4	305.8	306.3	305.4	308.9	311.0	311.5
25°	297.6	296.8	296.3	295.0	293.3	295.0	294.6	295.0	295.9	299.4	296.8
27.5°	285.9	284.2	285.1	283.8	283.3	283.8	283.8	284.2	285.1	285.5	285.9
30°	276.0	274.3	273.8	273.0	272.5	273.0	273.8	273.0	276.4	276.0	276.0
32.5°	265.2	263.9	263.0	263.0	262.6	262.2	262.6	263.0	265.6	263.9	265.6
35°	254.8	253.9	253.9	253.1	252.6	252.6	252.6	254.4	253.5	254.8	254.8
37.5°	244.8	244.8	244.4	243.5	243.1	243.5	243.1	244.0	243.5	244.0	244.4
40°	234.5	233.6	233.2	233.2	231.9	230.6	231.9	231.9	232.3	233.6	234.0
42.5°	221.9	222.4	222.4	220.6	220.6	220.6	221.1	221.5	221.5	222.4	222.4
45°	211.1	210.2	210.2	210.2	209.4	209.8	210.7	210.7	210.7	210.7	209.8
47.5°	199.0	199.0	199.4	199.4	200.7	200.3	200.3	199.9	199.0	199.0	199.4
50°	187.7	189.0	189.5	189.5	189.9	190.3	190.3	189.5	189.0	187.7	187.7
52.5°	176.9	177.8	178.7	180.0	180.8	180.4	180.4	179.5	177.8	177.4	176.9
55°	165.3	166.5	168.3	169.6	170.9	171.3	171.3	169.6	167.8	165.7	165.7
57.5°	154.4	155.7	158.8	160.1	161.8	161.8	160.9	159.6	157.0	155.3	154.0
60°	143.6	145.8	147.9	150.5	152.7	153.1	151.8	150.1	147.1	144.9	143.2
62.5°	131.9	134.1	138.4	141.0	142.8	142.8	142.8	140.6	136.7	133.7	131.1
65°	120.7	122.9	126.7	130.2	131.5	132.8	131.5	129.3	126.3	122.9	120.3
67.5°	109.0	111.6	115.5	118.1	119.8	121.1	120.3	118.5	114.6	109.9	108.1
70°	96.0	97.3	103.0	105.6	108.1	109.0	108.1	105.6	101.7	96.5	94.7
72.5°	83.9	85.2	90.4	92.6	94.7	95.6	94.3	92.6	89.1	84.4	82.2
75°	70.1	72.2	74.8	78.3	80.9	81.8	80.5	79.2	74.8	71.8	70.1
77.5°	55.4	57.5	61.0	64.0	66.6	66.2	64.5	64.9	60.1	56.7	55.4
80°	42.0	43.7	46.3	48.9	50.2	50.2	49.7	48.0	46.3	43.7	41.5
82.5°	29.0	31.1	33.3	35.0	35.0	35.5	34.6	34.2	32.4	30.3	29.8
85°	17.3	17.7	19.5	19.5	21.2	20.3	19.9	21.2	19.5	18.2	17.7
87.5°	7.8	7.4	7.8	7.8	7.4	8.2	8.2	7.8	8.2	7.8	7.8
90°	11.5	11.7	12.1	12.4	12.8	13.2	12.8	12.4	12.1	11.7	11.5
92.5°	28.0	28.1	28.4	28.6	28.9	29.1	28.9	28.6	28.4	28.1	28.0
95°	46.2	46.3	46.6	46.8	47.1	47.3	47.1	46.8	46.6	46.3	46.2
97.5°	66.5	66.6	66.7	66.8	66.9	67.0	66.9	66.8	66.7	66.6	66.5
100°	89.0	89.1	89.4	89.6	89.9	90.1	89.9	89.6	89.4	89.1	89.0
102.5°	111.6	111.8	112.1	112.5	112.8	113.2	112.8	112.5	112.1	111.8	111.6
105°	134.6	134.8	135.2	135.5	135.9	136.3	135.9	135.5	135.2	134.8	134.6
107.5°	159.4	159.4	159.4	159.4	159.4	159.4	159.4	159.4	159.4	159.4	159.4
110°	186.3	186.2	186.1	186.0	185.9	185.8	185.9	186.0	186.1	186.2	186.3

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	212.7	212.6	212.3	212.1	211.8	211.6	211.8	212.1	212.3	212.6	212.7
115°	239.6	239.5	239.4	239.3	239.2	239.1	239.2	239.3	239.4	239.5	239.6
117.5°	267.6	267.4	266.9	266.4	265.9	265.4	265.9	266.4	266.9	267.4	267.6
120°	295.1	294.9	294.4	293.9	293.4	292.9	293.4	293.9	294.4	294.9	295.1
122.5°	322.0	321.8	321.5	321.1	320.8	320.4	320.8	321.1	321.5	321.8	322.0
125°	348.4	348.3	348.2	348.1	348.0	347.9	348.0	348.1	348.2	348.3	348.4
127.5°	375.3	375.2	374.9	374.7	374.4	374.2	374.4	374.7	374.9	375.2	375.3
130°	401.7	401.6	401.3	401.1	400.8	400.6	400.8	401.1	401.3	401.6	401.7
132.5°	427.0	426.8	426.5	426.1	425.8	425.4	425.8	426.1	426.5	426.8	427.0
135°	453.4	453.2	452.7	452.2	451.7	451.2	451.7	452.2	452.7	453.2	453.4
137.5°	479.2	478.9	478.3	477.7	477.1	476.5	477.1	477.7	478.3	478.9	479.2
140°	503.4	503.1	502.5	501.8	501.2	500.6	501.2	501.8	502.5	503.1	503.4
142.5°	526.5	526.2	525.6	524.9	524.3	523.7	524.3	524.9	525.6	526.2	526.5
145°	548.5	548.3	547.9	547.6	547.2	546.8	547.2	547.6	547.9	548.3	548.5
147.5°	570.4	569.9	568.9	568.0	567.0	566.0	567.0	568.0	568.9	569.9	570.4
150°	589.1	589.0	588.7	588.5	588.2	588.0	588.2	588.5	588.7	589.0	589.1
152.5°	608.4	608.2	607.7	607.2	606.7	606.2	606.7	607.2	607.7	608.2	608.4
155°	625.9	625.6	625.0	624.4	623.8	623.2	623.8	624.4	625.0	625.6	625.9
157.5°	641.3	640.9	640.0	639.2	638.3	637.5	638.3	639.2	640.0	640.9	641.3
160°	655.1	654.8	654.2	653.5	652.9	652.3	652.9	653.5	654.2	654.8	655.1
162.5°	668.3	667.9	667.2	666.5	665.7	665.0	665.7	666.5	667.2	667.9	668.3
165°	679.3	678.9	678.2	677.5	676.7	676.0	676.7	677.5	678.2	678.9	679.3
167.5°	688.6	688.2	687.5	686.8	686.0	685.3	686.0	686.8	687.5	688.2	688.6
170°	696.3	695.9	695.0	694.1	693.3	692.4	693.3	694.1	695.0	695.9	696.3
172.5°	701.8	701.4	700.7	700.0	699.2	698.5	699.2	700.0	700.7	701.4	701.8
175°	705.6	705.2	704.3	703.5	702.6	701.8	702.6	703.5	704.3	705.2	705.6
177.5°	707.8	707.4	706.5	705.7	704.8	704.0	704.8	705.7	706.5	707.4	707.8
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	484.1	481.5	484.5	480.6	481.5	486.2	485.8	490.1	492.7	492.3	494.5
5°	452.1	452.1	453.4	452.9	457.3	461.1	466.3	470.7	475.4	478.0	481.0
7.5°	420.5	424.8	425.7	427.8	433.0	439.5	444.7	451.2	458.1	462.9	466.3
10°	394.5	398.0	401.4	403.2	408.8	417.5	424.8	435.2	443.8	449.0	453.8
12.5°	371.6	375.5	377.2	385.0	388.9	394.5	404.9	416.2	425.7	431.3	435.2
15°	355.2	357.3	361.2	366.0	369.9	376.8	385.4	398.0	407.1	411.8	425.2
17.5°	341.3	343.9	346.1	348.2	354.3	361.6	369.9	380.7	392.4	400.6	407.5
20°	327.0	328.3	330.9	334.4	338.7	345.6	353.0	364.2	374.6	381.1	390.2
22.5°	310.2	314.1	316.7	319.3	324.0	331.8	338.7	346.9	359.9	367.3	376.8
25°	300.2	301.9	303.7	306.7	310.2	317.1	324.9	333.5	343.9	351.7	359.9
27.5°	287.2	289.8	292.0	295.9	298.1	303.7	311.0	319.7	332.2	338.7	345.6
30°	276.4	279.0	280.8	282.5	285.5	291.6	298.5	305.4	317.1	325.3	332.2
32.5°	265.6	268.2	270.4	271.7	274.7	278.6	284.2	292.9	302.8	308.4	317.5
35°	256.1	256.1	258.7	260.4	263.0	266.5	271.7	278.2	288.5	295.9	304.1
37.5°	245.3	245.7	247.9	249.2	251.8	255.2	260.4	266.5	275.1	280.8	289.0
40°	234.0	235.3	236.2	238.4	241.4	242.7	247.9	254.8	263.4	268.6	275.6
42.5°	222.8	223.7	225.8	227.5	230.1	232.3	235.8	242.3	248.7	256.5	262.2
45°	210.2	212.4	213.7	216.7	218.0	220.2	223.7	228.8	236.6	241.4	247.9
47.5°	199.4	200.3	201.2	205.0	207.6	208.9	212.4	215.4	223.7	228.0	234.0
50°	187.7	187.7	189.0	190.8	193.8	196.4	199.4	202.9	209.4	213.7	219.8
52.5°	176.9	175.6	176.5	177.4	180.4	183.0	186.0	190.8	196.8	199.4	204.6
55°	165.3	163.1	164.4	165.7	166.5	170.0	173.5	176.5	181.3	185.1	189.9
57.5°	152.7	152.3	151.4	151.8	154.0	156.2	158.8	162.7	168.3	171.3	173.9
60°	141.5	138.9	138.0	138.9	140.2	141.5	144.9	148.4	153.1	156.2	159.2
62.5°	129.8	127.2	125.5	124.2	125.5	128.5	130.6	133.2	137.1	140.6	143.2
65°	118.5	114.6	112.9	112.0	111.6	113.8	115.5	119.0	122.4	123.7	126.7
67.5°	106.0	102.5	100.4	99.1	99.1	99.1	100.8	104.3	107.7	108.1	111.2
70°	93.4	89.5	87.4	85.7	84.8	85.7	87.8	88.2	91.3	92.1	93.9
72.5°	80.0	76.6	74.0	71.8	72.2	73.1	73.1	74.0	75.7	77.9	77.9
75°	67.5	62.7	61.4	59.7	58.8	58.8	58.8	60.6	61.9	63.6	63.2
77.5°	53.2	50.6	48.0	47.2	45.9	45.4	46.3	46.3	47.2	48.5	48.9
80°	41.1	38.1	36.3	35.5	33.7	33.3	33.7	33.7	35.0	34.6	35.0
82.5°	28.6	26.4	25.1	23.8	22.9	23.4	22.9	22.9	23.4	22.9	22.9
85°	16.4	16.0	15.1	14.7	14.3	13.4	14.3	13.8	13.4	13.0	13.8
87.5°	7.8	7.4	7.4	6.5	6.5	6.1	6.5	6.5	6.1	6.1	6.1
90°	11.2	10.6	10.0	9.4	8.8	7.9	7.1	6.2	5.3	4.9	4.4
92.5°	27.6	26.7	25.9	25.0	24.2	23.1	22.0	20.9	19.8	19.2	18.9
95°	45.8	44.9	44.0	43.2	42.3	41.1	39.9	38.6	37.4	36.8	36.7
97.5°	66.1	65.4	64.7	63.9	63.2	61.5	59.8	58.1	56.4	55.5	55.4
100°	88.5	87.4	86.3	85.2	84.1	82.5	80.9	79.3	77.7	76.9	76.9
102.5°	111.0	109.8	108.5	107.3	106.1	105.5	104.9	104.2	103.6	103.3	103.0
105°	134.2	133.5	132.8	132.0	131.3	130.6	129.8	129.1	128.4	128.0	127.7
107.5°	159.2	158.8	158.5	158.1	157.7	157.1	156.5	155.9	155.3	155.0	154.7
110°	186.1	185.8	185.4	185.1	184.7	184.3	183.9	183.6	183.2	183.0	182.7

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	212.6	212.5	212.4	212.2	212.1	211.6	211.1	210.6	210.1	209.9	209.8
115°	239.7	239.8	239.9	240.1	240.2	240.0	239.7	239.5	239.2	239.1	238.9
117.5°	267.5	267.4	267.3	267.2	267.1	266.9	266.6	266.4	266.1	266.0	265.9
120°	295.1	295.1	295.1	295.1	295.1	295.0	294.9	294.8	294.7	294.6	294.3
122.5°	322.1	322.2	322.3	322.5	322.6	322.2	321.8	321.5	321.1	320.9	320.8
125°	348.5	348.8	349.0	349.3	349.5	349.4	349.3	349.2	349.1	349.0	348.6
127.5°	375.4	375.5	375.6	375.8	375.9	375.8	375.6	375.5	375.4	375.3	375.1
130°	401.8	401.9	402.0	402.2	402.3	402.1	401.8	401.6	401.3	401.2	400.9
132.5°	427.1	427.2	427.3	427.5	427.6	427.7	427.8	427.9	428.0	428.1	427.6
135°	453.4	453.4	453.4	453.4	453.4	453.3	453.1	453.0	452.9	452.8	452.4
137.5°	479.1	479.0	478.9	478.8	478.7	478.5	478.2	478.0	477.7	477.6	477.2
140°	503.3	503.0	502.8	502.5	502.3	501.9	501.5	501.2	500.8	500.6	500.3
142.5°	526.4	526.3	526.2	526.0	525.9	525.4	524.9	524.4	523.9	523.7	523.5
145°	548.5	548.5	548.5	548.5	548.5	548.1	547.7	547.4	547.0	546.8	546.6
147.5°	570.2	569.9	569.5	569.2	568.8	568.6	568.3	568.1	567.8	567.7	567.5
150°	589.1	589.1	589.1	589.1	589.1	588.6	588.1	587.6	587.1	586.9	587.0
152.5°	608.2	607.8	607.5	607.1	606.7	606.6	606.5	606.4	606.3	606.2	606.1
155°	625.7	625.2	624.7	624.2	623.7	623.6	623.5	623.4	623.3	623.2	623.2
157.5°	641.1	640.6	640.1	639.6	639.1	639.0	638.9	638.8	638.7	638.6	638.7
160°	654.9	654.4	653.9	653.4	652.9	652.8	652.6	652.5	652.4	652.3	652.5
162.5°	668.0	667.4	666.7	666.1	665.5	665.5	665.5	665.5	665.5	665.5	665.6
165°	679.1	678.6	678.1	677.6	677.1	677.0	676.8	676.7	676.6	676.5	676.6
167.5°	688.2	687.5	686.8	686.0	685.3	685.3	685.3	685.3	685.3	685.3	685.5
170°	695.9	695.2	694.5	693.7	693.0	693.0	693.0	693.0	693.0	693.0	693.2
172.5°	701.4	700.7	700.0	699.2	698.5	698.5	698.5	698.5	698.5	698.5	698.7
175°	705.2	704.5	703.8	703.0	702.3	702.3	702.3	702.3	702.3	702.3	702.5
177.5°	707.4	706.7	706.0	705.2	704.5	704.6	704.8	704.9	705.0	705.1	705.3
180°	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2	706.2

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.6	509.6	509.6	509.6
2.5°	497.5	501.8	504.8	510.5
5°	486.2	494.0	501.4	509.2
7.5°	475.0	484.1	495.8	505.7
10°	462.4	474.1	488.0	501.4
12.5°	449.9	463.7	478.9	496.6
15°	434.8	452.5	470.2	489.3
17.5°	421.3	439.5	458.5	482.3
20°	406.2	426.1	446.9	471.1
22.5°	392.8	414.9	436.5	462.0
25°	377.7	399.3	423.1	450.3
27.5°	365.1	385.0	408.4	437.8
30°	350.0	371.6	395.0	424.4
32.5°	335.7	356.5	381.1	410.1
35°	321.0	342.2	364.2	391.9
37.5°	307.1	325.3	347.4	373.8
40°	291.6	311.5	331.4	352.1
42.5°	277.3	295.5	314.1	330.5
45°	261.3	276.9	294.6	308.0
47.5°	246.6	260.4	274.3	284.6
50°	231.9	242.7	253.1	262.2
52.5°	214.6	226.7	232.3	237.9
55°	199.0	205.9	211.1	216.7
57.5°	183.9	186.9	189.5	194.7
60°	164.0	167.4	170.4	174.3
62.5°	146.6	148.4	149.2	153.1
65°	130.2	129.8	131.9	134.1
67.5°	112.5	112.0	114.2	115.1
70°	95.2	94.7	95.2	97.3
72.5°	78.7	78.7	79.2	80.0
75°	63.6	63.6	64.0	64.9
77.5°	48.0	48.9	48.5	50.2
80°	35.0	34.2	35.0	35.9
82.5°	22.9	23.8	23.8	22.9
85°	13.0	13.0	13.0	13.0
87.5°	5.6	5.6	6.1	6.5
90°	3.4	2.5	1.5	0.5
92.5°	18.3	17.7	17.1	16.5
95°	36.4	36.2	35.9	35.7
97.5°	55.3	55.2	55.1	55.0
100°	76.9	76.9	76.9	76.9
102.5°	102.4	101.8	101.2	100.6
105°	127.1	126.5	125.9	125.3
107.5°	154.1	153.4	152.8	152.2
110°	182.1	181.5	180.9	180.3

TEST NUMBER: P1027920

CATALOG NUMBER: S125DIP-B375D610UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	209.5	209.3	209.0	208.8
115°	238.4	237.9	237.4	236.9
117.5°	265.8	265.7	265.5	265.4
120°	293.7	293.0	292.4	291.8
122.5°	320.7	320.6	320.5	320.4
125°	347.9	347.2	346.4	345.7
127.5°	374.8	374.4	374.1	373.7
130°	400.3	399.6	399.0	398.4
132.5°	426.5	425.4	424.3	423.2
135°	451.7	451.0	450.2	449.5
137.5°	476.5	475.8	475.0	474.3
140°	499.7	499.1	498.5	497.9
142.5°	523.0	522.5	522.0	521.5
145°	546.1	545.6	545.1	544.6
147.5°	567.1	566.8	566.4	566.0
150°	587.1	587.2	587.4	587.5
152.5°	605.8	605.6	605.3	605.1
155°	623.2	623.2	623.2	623.2
157.5°	639.0	639.2	639.5	639.7
160°	652.9	653.2	653.6	654.0
162.5°	665.9	666.1	666.4	666.6
165°	676.9	677.1	677.4	677.6
167.5°	686.0	686.5	687.0	687.5
170°	693.7	694.2	694.7	695.2
172.5°	699.2	699.7	700.2	700.7
175°	703.0	703.5	704.0	704.5
177.5°	705.8	706.3	706.8	707.3
180°	706.2	706.2	706.2	706.2

(END OF REPORT)