

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028017

Luminaire Tested: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028017
REPORT IS A COMBINATION OF REPORTS P1002181 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D1270UB27-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6785.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	82	79	76	67	65	63	52	51	50	39	38	37
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	28	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	36	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	21	18	16
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14
9	49	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5663	5663	5663	5663
5°	5667	6424	5672	4873
10°	5633	7322	5623	4183
15°	5591	7939	5556	3780
20°	5520	8700	5470	3450
25°	5458	9968	5358	3256
30°	5368	10516	5275	3079
35°	5225	8430	5116	2938
40°	5003	5826	4929	2788
45°	4722	4338	4669	2663
50°	4401	3571	4329	2563
55°	4054	3046	4022	2477
60°	3714	2607	3649	2410
65°	3347	2251	3292	2311
70°	2959	1870	2920	2142
75°	2547	1446	2513	1859
80°	2013	978	1939	1366
85°	1286	490	1246	697

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8650 cd/sqm

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.3
10°-20°	253.4	3.7
20°-30°	411.6	6.1
30°-40°	503.0	7.4
40°-50°	456.3	6.7
50°-60°	363.4	5.4
60°-70°	253.1	3.7
70°-80°	134.8	2.0
80°-90°	35.7	0.5
90°-100°	415.3	6.1
100°-110°	895.7	13.2
110°-120°	835.0	12.3
120°-130°	676.3	10.0
130°-140°	543.1	8.0
140°-150°	409.6	6.0
150°-160°	288.4	4.3
160°-170°	170.0	2.5
170°-180°	55.3	0.8
0°-30°	750.0	11.1
0°-40°	1253.0	18.5
0°-60°	2072.6	30.5
0°-90°	2496.3	36.8
90°-120°	2146.0	31.6
90°-150°	3775.0	55.6
90°-180°	4289.0	63.2
0°-180°	6785.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1020	884	774	883	84
15°	849	1273	843	606	849	239
25°	781	1567	767	512	781	360
35°	680	1257	666	438	680	424
45°	534	593	528	364	534	411
55°	376	365	373	297	376	336
65°	233	224	229	230	233	231
75°	112	110	111	142	112	120
85°	22	25	22	35	22	27
90°	1	26	1	26	1	4
95°	38	270	38	270	38	40
105°	130	1525	130	1525	130	137
115°	232	1699	232	1699	232	229
125°	322	1339	322	1339	322	286
135°	378	1112	378	1112	378	293
145°	440	877	440	877	440	276
155°	502	736	502	736	502	231
165°	548	645	548	645	548	154
175°	570	579	570	579	570	54
180°	571	571	571	571	571	

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	885.3	890.6	896.6	901.1	908.6	910.8	914.6	916.8	919.1	921.3	922.8
5°	883.1	895.8	907.1	915.3	929.6	934.8	941.6	949.8	959.6	967.8	973.1
7.5°	877.1	897.3	912.3	928.8	948.3	961.1	967.8	985.1	1000.9	1012.9	1028.6
10°	869.6	893.6	916.8	941.6	969.3	983.6	997.1	1021.1	1042.9	1062.4	1078.1
12.5°	861.3	890.6	918.3	950.6	988.1	1005.4	1014.4	1055.6	1082.6	1093.1	1123.9
15°	848.6	883.1	922.8	962.6	994.1	1014.4	1039.1	1072.1	1099.1	1122.4	1147.2
17.5°	836.5	874.1	914.6	958.8	1004.6	1030.9	1049.6	1078.9	1108.1	1138.2	1161.4
20°	817.0	865.8	907.1	954.3	1008.4	1027.1	1046.6	1081.1	1112.6	1144.9	1174.2
22.5°	801.3	847.8	904.1	949.1	994.9	1013.6	1037.6	1073.6	1111.1	1147.9	1190.7
25°	781.0	832.8	881.6	929.6	976.8	997.1	1018.9	1065.4	1104.4	1151.7	1198.9
27.5°	759.3	812.5	861.3	904.8	949.1	976.8	1000.1	1048.9	1100.6	1152.4	1213.9
30°	736.0	786.3	832.8	875.6	924.3	952.8	976.1	1033.1	1090.9	1156.9	1230.4
32.5°	711.3	758.5	798.3	841.8	893.6	919.8	951.3	1013.6	1081.9	1160.7	1252.9
35°	679.7	724.8	760.0	804.3	856.1	889.8	922.8	992.6	1072.1	1159.9	1265.7
37.5°	648.2	683.5	717.3	764.5	824.5	855.3	889.8	966.3	1057.1	1157.7	1271.0
40°	610.7	645.2	674.5	722.5	785.5	820.8	856.8	937.1	1039.9	1149.4	1252.2
42.5°	573.2	602.5	634.7	685.0	745.8	783.3	821.5	910.8	1017.4	1125.4	1200.4
45°	534.2	556.7	592.0	637.7	702.3	738.3	781.8	878.6	985.9	1081.9	1119.4
47.5°	493.7	516.2	549.2	593.5	657.2	700.0	741.3	838.0	946.1	1020.4	1020.4
50°	454.7	472.7	504.9	549.2	613.7	652.7	694.7	797.5	884.6	939.3	890.6
52.5°	412.6	432.9	459.9	506.4	570.2	605.5	651.2	739.0	821.5	844.1	769.0
55°	375.9	392.4	417.9	462.2	521.4	558.2	597.2	681.2	751.0	749.5	669.2
57.5°	337.6	351.1	378.1	418.6	473.4	506.4	545.4	618.2	675.2	655.0	579.2
60°	302.4	312.1	338.4	371.4	423.9	454.7	492.2	551.4	595.0	566.5	489.9
62.5°	265.6	276.8	297.9	330.1	376.6	401.4	429.2	489.2	516.9	491.4	413.4
65°	232.6	241.6	260.3	287.4	329.4	351.9	375.9	425.4	451.7	414.9	350.4
67.5°	199.6	210.1	223.6	247.6	280.6	301.6	322.6	365.4	377.4	344.4	290.4
70°	168.8	177.8	190.6	207.8	235.6	254.3	270.1	305.4	313.6	282.9	240.1
72.5°	138.8	144.8	155.3	169.6	195.1	205.6	222.1	246.1	256.6	228.8	198.1
75°	112.5	117.0	123.8	134.3	151.6	162.8	176.3	198.8	198.1	178.6	156.8
77.5°	87.0	87.8	95.3	105.0	115.5	125.3	132.0	147.8	149.3	137.3	119.3
80°	62.3	64.5	67.5	75.0	84.0	87.8	96.0	105.8	107.3	98.3	86.3
82.5°	39.8	41.3	43.5	48.0	54.0	58.5	63.0	66.8	70.5	65.3	55.5
85°	22.5	23.3	25.5	27.0	30.0	32.3	36.0	39.8	39.0	35.3	32.3
87.5°	11.3	11.3	11.3	12.8	14.3	14.3	15.8	16.5	17.3	15.8	14.3
90°	1.2	2.3	4.6	6.9	9.2	10.4	11.5	12.7	15.0	16.1	18.4
92.5°	17.3	20.7	32.2	49.5	73.7	94.4	115.1	193.4	324.6	467.4	459.3
95°	38.0	39.1	48.4	61.0	86.3	112.2	138.1	261.3	514.6	832.3	1020.0
97.5°	58.7	59.9	66.8	79.4	102.5	121.4	140.4	225.6	420.2	763.2	1101.7
100°	80.6	82.9	87.5	100.2	122.0	139.3	156.6	223.3	373.0	663.1	1039.5
102.5°	104.8	105.9	109.4	123.2	142.7	159.4	176.1	233.7	353.4	587.1	930.2
105°	130.1	130.1	135.8	147.4	165.8	181.9	198.0	248.7	351.1	543.4	834.6
107.5°	154.3	156.6	162.3	171.5	191.1	205.5	219.9	269.4	359.2	520.3	763.2
110°	180.7	183.0	187.6	198.0	215.3	230.2	245.2	292.4	371.8	511.1	716.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	207.2	209.5	213.0	223.3	240.6	255.0	269.4	314.3	388.0	511.1	688.4
115°	232.5	234.8	238.3	248.7	265.9	280.3	294.7	337.3	404.1	514.6	670.0
117.5°	255.6	259.0	262.5	272.8	292.4	306.2	320.0	360.3	422.5	520.3	659.6
120°	278.6	282.0	286.6	297.0	316.6	331.0	345.4	385.7	440.9	529.6	652.7
122.5°	302.8	305.1	308.5	318.9	340.8	355.2	369.5	409.8	461.6	537.6	647.0
125°	322.3	324.6	330.4	340.8	362.6	377.6	392.6	430.5	480.0	546.8	642.4
127.5°	338.5	341.9	348.8	361.5	384.5	399.4	414.4	451.3	497.3	557.2	640.1
130°	353.4	356.9	366.1	381.0	405.2	420.2	435.2	470.8	514.6	566.4	637.8
132.5°	364.9	369.5	381.0	398.3	423.6	438.6	453.6	489.3	529.6	576.8	637.8
135°	377.6	382.2	396.0	414.4	438.6	454.2	469.7	505.4	543.4	586.0	637.8
137.5°	393.7	397.2	409.8	428.2	452.4	468.6	484.7	516.9	553.7	595.2	638.9
140°	407.5	411.0	424.8	443.2	465.1	480.6	496.2	529.6	564.1	600.9	640.1
142.5°	423.6	425.9	438.6	457.0	477.7	492.1	506.5	537.6	569.8	604.4	641.2
145°	439.8	442.1	453.6	469.7	490.4	503.6	516.9	546.8	575.6	606.7	640.1
147.5°	457.0	458.2	468.5	483.5	501.9	514.0	526.1	552.6	579.1	607.8	637.8
150°	472.0	474.3	482.4	497.3	513.4	523.2	533.0	558.3	582.5	607.8	634.3
152.5°	488.1	489.3	496.2	508.8	523.8	532.4	541.1	564.1	584.8	606.7	629.7
155°	501.9	501.9	508.8	520.3	531.9	540.0	548.0	567.5	586.0	604.4	623.9
157.5°	514.6	514.6	520.3	530.7	541.1	547.4	553.7	571.0	587.1	602.1	618.2
160°	527.2	526.1	530.7	538.8	548.0	553.2	558.3	573.3	587.1	598.6	612.4
162.5°	537.6	536.5	541.1	548.0	554.9	558.9	562.9	575.6	586.0	595.2	605.5
165°	548.0	545.7	549.1	554.9	559.5	563.0	566.4	575.6	584.8	591.7	598.6
167.5°	554.9	553.7	556.0	559.5	562.9	565.2	567.5	575.6	582.5	586.0	591.7
170°	561.8	560.6	561.8	564.1	566.4	568.1	569.8	575.6	580.2	582.5	586.0
172.5°	566.4	564.1	565.2	567.5	568.7	569.2	569.8	574.4	577.9	577.9	579.1
175°	569.8	567.5	568.7	569.8	569.8	569.8	569.8	573.3	575.6	574.4	574.4
177.5°	572.1	569.8	569.8	571.0	569.8	569.8	569.8	572.1	573.3	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	924.3	929.6	934.1	937.8	940.8	945.3	942.3	943.1	944.6	947.6	947.6
5°	984.4	992.6	997.1	1012.1	1015.9	1015.1	1012.9	1024.9	1024.1	1019.6	1018.9
7.5°	1042.9	1057.1	1069.9	1081.9	1085.6	1095.4	1097.6	1102.9	1101.4	1108.9	1105.1
10°	1096.1	1118.6	1130.7	1148.7	1153.2	1157.7	1163.7	1166.7	1173.4	1172.7	1172.7
12.5°	1137.4	1164.4	1180.2	1184.7	1201.9	1207.2	1212.4	1222.2	1219.9	1220.7	1225.2
15°	1169.7	1195.9	1209.4	1230.4	1242.4	1248.4	1257.4	1268.0	1266.5	1273.2	1271.7
17.5°	1193.7	1218.4	1243.2	1274.7	1275.5	1291.2	1312.2	1316.7	1326.5	1319.7	1319.7
20°	1213.2	1246.2	1281.5	1322.0	1326.5	1336.2	1361.7	1379.0	1390.2	1386.5	1388.7
22.5°	1234.2	1281.5	1322.7	1363.2	1385.0	1402.3	1427.0	1454.0	1463.8	1469.8	1468.3
25°	1261.2	1310.7	1371.5	1427.8	1450.3	1483.3	1516.3	1542.6	1550.1	1566.6	1551.6
27.5°	1289.0	1358.7	1434.5	1500.5	1529.0	1556.1	1595.8	1615.3	1625.1	1632.6	1627.3
30°	1312.2	1408.3	1490.8	1551.6	1571.8	1587.6	1610.1	1614.6	1610.8	1616.8	1624.3
32.5°	1348.2	1442.0	1511.8	1541.1	1538.8	1538.0	1520.8	1496.8	1491.5	1477.3	1496.8
35°	1367.7	1442.8	1469.8	1430.8	1415.0	1386.5	1331.7	1295.7	1264.2	1257.4	1258.9
37.5°	1356.5	1385.7	1353.5	1250.7	1225.2	1181.7	1108.9	1057.9	1034.6	1016.6	1039.9
40°	1295.7	1263.5	1174.9	1049.6	1012.9	971.6	903.3	875.6	842.6	835.8	866.6
42.5°	1195.2	1096.9	971.6	874.8	836.5	813.3	756.3	730.0	706.8	696.2	713.5
45°	1058.6	939.3	813.3	733.8	701.5	673.7	640.0	612.2	597.2	592.7	607.0
47.5°	917.6	791.5	691.0	631.7	598.0	577.0	545.4	529.7	517.7	519.2	521.4
50°	782.5	667.7	590.5	531.2	514.7	498.2	477.2	463.7	457.7	459.9	458.4
52.5°	666.2	573.2	507.9	462.2	454.7	438.9	421.7	410.4	408.1	408.9	411.1
55°	564.2	491.4	439.7	406.6	398.4	387.1	376.6	369.1	363.1	365.4	364.6
57.5°	486.9	423.2	383.4	356.4	350.4	343.6	333.9	330.1	327.9	323.4	327.1
60°	418.6	366.9	332.4	315.9	310.6	306.1	295.6	291.1	289.6	287.4	293.4
62.5°	354.1	317.4	291.1	276.1	270.8	266.3	261.1	257.3	258.1	255.1	258.1
65°	303.1	273.1	254.3	240.8	234.1	231.1	230.3	224.3	223.6	224.3	225.1
67.5°	255.8	230.3	216.1	207.8	202.6	199.6	197.3	193.6	196.6	194.3	195.8
70°	213.1	195.8	180.8	172.6	170.3	171.1	167.3	165.8	166.6	165.1	166.6
72.5°	171.8	157.6	151.6	145.6	142.6	141.8	139.5	137.3	139.5	138.8	138.8
75°	137.3	126.8	120.0	116.3	116.3	114.8	111.0	111.0	111.0	110.3	111.0
77.5°	105.8	96.8	93.8	90.0	90.0	87.8	87.0	87.0	85.5	87.8	86.3
80°	78.8	72.0	67.5	65.3	65.3	64.5	63.0	62.3	63.0	62.3	62.3
82.5°	51.0	48.0	45.8	43.5	42.8	43.5	42.8	41.3	42.0	41.3	42.8
85°	29.3	26.3	26.3	24.8	25.5	24.0	24.8	23.3	22.5	24.8	23.3
87.5°	12.8	12.0	12.0	10.5	10.5	10.5	9.8	10.5	9.8	9.0	9.8
90°	19.6	20.7	21.9	23.0	24.2	25.3	25.3	25.3	26.5	26.5	26.5
92.5°	370.7	249.8	179.6	133.5	122.6	111.7	93.2	89.8	87.5	85.2	87.5
95°	998.1	827.7	652.7	511.1	462.8	414.4	332.7	298.2	289.0	270.5	289.0
97.5°	1246.7	1186.9	1047.6	904.8	835.8	766.7	697.6	637.8	606.7	592.9	606.7
100°	1327.3	1416.0	1359.6	1241.0	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4
102.5°	1279.0	1493.1	1550.7	1509.2	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4
105°	1165.0	1441.3	1599.0	1649.7	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2
107.5°	1056.8	1335.4	1543.8	1665.8	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5
110°	967.0	1215.7	1434.4	1596.7	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	900.2	1121.3	1326.2	1490.8	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7
115°	855.3	1045.3	1223.7	1381.4	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2
117.5°	825.4	992.3	1150.0	1288.2	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5
120°	801.2	950.9	1089.0	1215.7	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5
122.5°	780.5	919.8	1045.3	1154.7	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2
125°	762.1	889.9	1007.3	1107.5	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3
127.5°	744.8	858.8	970.5	1064.9	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6
130°	727.6	830.0	931.3	1021.1	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5
132.5°	713.7	801.2	894.5	973.9	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6
135°	703.4	777.1	856.5	930.2	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2
137.5°	693.0	755.2	822.0	885.3	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1
140°	686.1	737.9	792.0	845.0	869.2	893.3	935.9	965.9	983.1	988.9	983.1
142.5°	680.4	723.0	766.7	810.4	830.6	850.7	885.3	909.4	925.6	930.2	925.6
145°	674.6	710.3	746.0	781.7	797.2	812.7	840.4	859.9	872.6	877.2	872.6
147.5°	668.8	697.6	727.6	756.3	768.4	780.5	803.5	819.7	827.7	830.0	827.7
150°	661.9	687.3	712.6	734.5	744.8	755.2	772.5	786.3	790.9	792.0	790.9
152.5°	653.9	675.8	697.6	717.2	724.7	732.2	746.0	756.3	760.9	762.1	760.9
155°	644.7	664.2	682.7	698.8	705.1	711.4	723.0	731.0	734.5	735.6	734.5
157.5°	636.6	652.7	668.8	681.5	686.7	691.9	701.1	708.0	711.4	711.4	711.4
160°	626.3	641.2	652.7	664.2	668.2	672.3	680.4	686.1	688.4	687.3	688.4
162.5°	617.0	628.6	638.9	648.1	651.6	655.0	660.8	665.4	665.4	665.4	665.4
165°	607.8	617.0	625.1	632.0	634.9	637.8	642.4	644.7	644.7	644.7	644.7
167.5°	598.6	605.5	611.3	617.0	619.3	621.6	623.9	626.3	625.1	625.1	625.1
170°	590.6	596.3	599.8	603.2	604.4	605.5	607.8	609.0	609.0	607.8	609.0
172.5°	582.5	586.0	589.4	591.7	592.3	592.9	592.9	595.2	592.9	591.7	592.9
175°	575.6	579.1	579.1	581.4	581.4	581.4	581.4	582.5	580.2	579.1	580.2
177.5°	572.1	573.3	574.4	574.4	574.4	574.4	573.3	574.4	571.0	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	946.1	940.8	942.3	940.8	937.1	934.8	928.8	921.3	918.3	914.6	912.3
5°	1021.9	1018.1	1017.4	1011.4	1009.9	1000.9	985.9	978.3	969.3	960.3	951.3
7.5°	1104.4	1099.9	1084.9	1082.6	1084.1	1072.9	1053.4	1038.4	1019.6	1006.9	989.6
10°	1172.7	1163.7	1150.9	1151.7	1146.4	1131.4	1111.9	1096.1	1069.1	1052.6	1027.9
12.5°	1213.9	1206.4	1204.9	1197.4	1192.9	1173.4	1150.2	1129.9	1109.6	1087.1	1068.4
15°	1264.2	1254.4	1247.7	1237.2	1234.2	1213.9	1188.4	1165.2	1141.9	1120.9	1081.1
17.5°	1319.7	1309.2	1283.7	1281.5	1263.5	1243.9	1219.2	1184.7	1159.9	1129.9	1100.6
20°	1382.7	1367.7	1334.7	1326.5	1312.2	1280.0	1246.2	1207.9	1168.2	1137.4	1102.9
22.5°	1453.3	1427.0	1403.0	1376.7	1366.2	1326.5	1280.0	1233.4	1185.4	1143.4	1102.1
25°	1544.8	1510.3	1476.5	1450.3	1432.3	1380.5	1318.2	1256.7	1201.2	1146.4	1092.4
27.5°	1616.8	1586.8	1550.1	1515.5	1492.3	1430.8	1359.5	1280.0	1210.9	1144.2	1086.4
30°	1622.1	1613.1	1590.6	1571.8	1546.3	1480.3	1401.5	1311.5	1225.9	1144.9	1074.4
32.5°	1523.8	1541.8	1551.6	1554.6	1549.3	1511.0	1439.0	1340.0	1239.4	1138.2	1063.9
35°	1312.2	1360.2	1419.5	1442.0	1463.8	1484.0	1446.5	1360.2	1243.9	1136.7	1047.4
37.5°	1080.4	1123.9	1222.2	1267.2	1292.7	1373.0	1403.8	1357.2	1252.9	1138.2	1031.6
40°	871.8	940.8	1011.4	1072.1	1111.9	1201.9	1297.2	1307.7	1240.2	1123.9	1011.4
42.5°	733.8	774.3	827.5	883.8	919.1	1025.6	1154.7	1230.4	1200.4	1100.6	986.6
45°	625.0	655.0	705.3	724.0	769.0	871.1	1007.6	1117.1	1132.2	1063.9	958.1
47.5°	536.4	562.0	594.2	617.5	653.5	730.0	845.6	966.3	1038.4	1013.6	918.3
50°	472.7	493.7	520.7	534.2	557.4	626.5	713.5	833.5	930.3	938.6	866.6
52.5°	419.4	431.4	452.4	467.4	486.2	528.2	607.0	706.0	814.8	859.8	802.8
55°	372.9	382.6	401.4	411.1	420.9	456.9	518.4	608.5	710.5	769.8	737.5
57.5°	330.9	339.1	354.9	363.9	369.1	403.6	450.9	521.4	613.0	685.0	667.0
60°	296.4	303.9	312.9	319.6	325.6	354.1	387.1	444.2	525.9	595.7	591.2
62.5°	259.6	266.3	276.1	282.9	288.1	306.1	333.9	377.4	447.2	511.7	524.4
65°	227.3	232.6	239.3	242.3	249.1	262.6	285.1	324.1	381.1	438.9	447.9
67.5°	198.1	199.6	204.1	210.8	212.3	224.3	244.6	273.8	318.1	365.4	379.6
70°	166.6	168.8	172.6	177.8	180.8	188.3	205.6	225.1	263.3	304.6	315.1
72.5°	138.8	141.8	143.3	146.3	147.8	159.8	167.3	186.8	213.1	247.6	258.8
75°	112.5	115.5	116.3	117.8	119.3	124.5	135.0	147.1	168.8	191.3	206.3
77.5°	89.3	88.5	90.0	92.3	91.5	96.0	102.8	113.3	127.5	146.3	156.1
80°	63.0	63.0	65.3	67.5	66.8	71.3	73.5	81.0	93.0	105.0	108.8
82.5°	42.0	42.0	44.3	44.3	45.8	46.5	49.5	53.3	63.0	69.0	71.3
85°	24.0	24.0	24.8	24.8	24.8	26.3	28.5	30.0	33.0	36.8	38.3
87.5°	9.8	10.5	10.5	10.5	10.5	12.0	12.0	13.5	14.3	15.8	15.8
90°	25.3	25.3	25.3	24.2	23.0	21.9	20.7	19.6	18.4	16.1	15.0
92.5°	89.8	93.2	111.7	122.6	133.5	179.6	249.8	370.7	459.3	467.4	324.6
95°	298.2	332.7	414.4	462.8	511.1	652.7	827.7	998.1	1020.0	832.3	514.6
97.5°	637.8	697.6	766.7	835.8	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2
100°	958.9	1041.8	1121.3	1181.2	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0
102.5°	1298.6	1351.5	1437.8	1473.5	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4
105°	1562.2	1600.2	1637.0	1643.4	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1
107.5°	1721.0	1726.8	1716.4	1691.1	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2
110°	1768.2	1746.4	1694.6	1645.6	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.7	1692.3	1610.5	1550.6	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0
115°	1652.0	1596.7	1506.9	1444.2	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1
117.5°	1555.3	1497.7	1406.8	1347.5	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5
120°	1457.4	1402.2	1317.0	1266.4	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9
122.5°	1371.1	1321.6	1247.9	1201.3	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6
125°	1302.0	1254.8	1190.3	1148.9	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0
127.5°	1244.4	1201.9	1143.1	1104.0	1064.9	970.5	858.8	744.8	640.1	557.2	497.3
130°	1191.5	1153.5	1095.9	1058.5	1021.1	931.3	830.0	727.6	637.8	566.4	514.6
132.5°	1140.8	1102.8	1045.3	1009.6	973.9	894.5	801.2	713.7	637.8	576.8	529.6
135°	1084.4	1046.4	995.8	963.0	930.2	856.5	777.1	703.4	637.8	586.0	543.4
137.5°	1024.6	988.9	942.8	914.0	885.3	822.0	755.2	693.0	638.9	595.2	553.7
140°	965.9	935.9	893.3	869.2	845.0	792.0	737.9	686.1	640.1	600.9	564.1
142.5°	909.4	885.3	850.7	830.6	810.4	766.7	723.0	680.4	641.2	604.4	569.8
145°	859.9	840.4	812.7	797.2	781.7	746.0	710.3	674.6	640.1	606.7	575.6
147.5°	819.7	803.5	780.5	768.4	756.3	727.6	697.6	668.8	637.8	607.8	579.1
150°	786.3	772.5	755.2	744.8	734.5	712.6	687.3	661.9	634.3	607.8	582.5
152.5°	756.3	746.0	732.2	724.7	717.2	697.6	675.8	653.9	629.7	606.7	584.8
155°	731.0	723.0	711.4	705.1	698.8	682.7	664.2	644.7	623.9	604.4	586.0
157.5°	708.0	701.1	691.9	686.7	681.5	668.8	652.7	636.6	618.2	602.1	587.1
160°	686.1	680.4	672.3	668.2	664.2	652.7	641.2	626.3	612.4	598.6	587.1
162.5°	665.4	660.8	655.0	651.6	648.1	638.9	628.6	617.0	605.5	595.2	586.0
165°	644.7	642.4	637.8	634.9	632.0	625.1	617.0	607.8	598.6	591.7	584.8
167.5°	626.3	623.9	621.6	619.3	617.0	611.3	605.5	598.6	591.7	586.0	582.5
170°	609.0	607.8	605.5	604.4	603.2	599.8	596.3	590.6	586.0	582.5	580.2
172.5°	595.2	592.9	592.9	592.3	591.7	589.4	586.0	582.5	579.1	577.9	577.9
175°	582.5	581.4	581.4	581.4	581.4	579.1	579.1	575.6	574.4	574.4	575.6
177.5°	574.4	573.3	574.4	574.4	574.4	574.4	573.3	572.1	571.0	571.0	573.3
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	909.3	905.6	901.1	901.1	895.8	893.6	889.1	887.6	883.8	877.8	873.3
5°	941.6	931.8	925.8	920.6	909.3	901.1	892.8	883.8	874.8	864.3	852.3
7.5°	973.1	955.1	946.8	937.8	921.3	904.1	887.6	875.6	863.6	847.1	832.0
10°	1006.1	983.6	968.6	956.6	931.1	909.3	885.3	868.1	849.3	828.3	808.8
12.5°	1033.9	1004.6	991.9	969.3	940.1	913.8	883.8	857.6	832.8	808.0	784.0
15°	1057.1	1029.4	997.9	988.9	948.3	910.8	877.1	843.3	812.5	787.8	760.0
17.5°	1064.6	1029.4	1013.6	991.9	943.8	904.8	862.1	825.3	796.0	759.3	737.5
20°	1066.9	1033.1	1011.4	991.1	948.3	896.6	854.6	809.5	774.3	737.5	703.0
22.5°	1060.9	1021.1	1000.1	980.6	932.6	888.3	839.5	790.0	748.8	715.0	680.5
25°	1049.6	1003.1	982.9	961.8	916.1	867.3	814.0	766.8	728.5	688.0	654.2
27.5°	1034.6	981.4	958.1	936.3	891.3	845.6	795.3	746.5	703.8	661.0	629.5
30°	1015.9	954.3	933.3	904.8	861.3	817.8	772.0	723.3	675.2	634.7	600.2
32.5°	991.9	927.3	899.6	872.6	825.3	785.5	742.0	696.2	649.7	610.0	574.0
35°	970.1	896.6	865.8	838.8	786.3	744.3	708.3	665.5	624.2	583.0	550.7
37.5°	940.8	865.8	829.0	801.3	748.0	705.3	671.5	638.5	595.0	555.2	525.2
40°	910.1	827.5	793.0	765.3	709.8	663.2	631.0	601.7	566.5	529.7	498.2
42.5°	882.3	790.8	754.0	720.3	664.0	622.7	589.7	567.2	534.9	501.9	473.4
45°	847.1	751.8	712.0	676.7	622.7	577.7	546.2	528.2	504.2	471.9	447.2
47.5°	811.0	709.8	668.5	634.0	575.5	535.7	504.9	487.7	471.2	445.7	420.9
50°	763.8	665.5	628.0	588.2	530.4	489.9	464.4	447.2	434.4	416.4	395.4
52.5°	712.0	619.7	579.2	544.7	487.7	450.9	421.7	411.9	399.1	385.6	367.6
55°	657.2	570.2	531.2	497.4	444.9	407.4	383.4	372.9	363.1	352.6	340.6
57.5°	602.5	518.4	481.7	451.7	402.9	366.9	347.4	333.1	326.4	320.4	310.6
60°	534.2	462.9	434.4	407.4	359.4	326.4	307.6	297.1	291.1	288.1	283.6
62.5°	474.2	415.6	384.1	357.9	319.6	290.4	272.3	264.1	258.8	257.3	252.1
65°	410.4	360.1	335.4	312.9	279.8	253.6	238.6	228.8	225.1	224.3	224.3
67.5°	350.4	309.9	285.1	269.3	240.8	217.6	203.3	199.6	197.3	194.3	193.6
70°	294.1	261.8	240.1	226.6	201.1	183.8	172.6	166.6	166.6	164.3	162.8
72.5°	244.6	212.3	198.1	186.8	165.8	150.8	142.6	141.1	135.8	135.0	135.0
75°	191.3	167.3	157.6	147.8	132.0	121.5	114.8	111.0	108.0	108.0	108.8
77.5°	144.1	127.5	118.5	111.0	99.8	93.0	87.8	86.3	83.3	83.3	83.3
80°	102.0	93.0	86.3	80.3	72.0	66.0	63.0	60.0	60.0	59.3	60.0
82.5°	66.0	58.5	54.8	54.0	46.5	44.3	40.5	41.3	39.0	38.3	39.8
85°	38.3	34.5	30.0	28.5	25.5	22.5	21.0	21.8	21.0	20.3	21.0
87.5°	15.0	12.8	12.0	12.0	9.8	9.0	8.3	9.0	7.5	7.5	8.3
90°	12.7	11.5	10.4	9.2	6.9	4.6	2.3	1.2	2.3	4.6	6.9
92.5°	193.4	115.1	94.4	73.7	49.5	32.2	20.7	17.3	20.7	32.2	49.5
95°	261.3	138.1	112.2	86.3	61.0	48.4	39.1	38.0	39.1	48.4	61.0
97.5°	225.6	140.4	121.4	102.5	79.4	66.8	59.9	58.7	59.9	66.8	79.4
100°	223.3	156.6	139.3	122.0	100.2	87.5	82.9	80.6	82.9	87.5	100.2
102.5°	233.7	176.1	159.4	142.7	123.2	109.4	105.9	104.8	105.9	109.4	123.2
105°	248.7	198.0	181.9	165.8	147.4	135.8	130.1	130.1	130.1	135.8	147.4
107.5°	269.4	219.9	205.5	191.1	171.5	162.3	156.6	154.3	156.6	162.3	171.5
110°	292.4	245.2	230.2	215.3	198.0	187.6	183.0	180.7	183.0	187.6	198.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	314.3	269.4	255.0	240.6	223.3	213.0	209.5	207.2	209.5	213.0	223.3
115°	337.3	294.7	280.3	265.9	248.7	238.3	234.8	232.5	234.8	238.3	248.7
117.5°	360.3	320.0	306.2	292.4	272.8	262.5	259.0	255.6	259.0	262.5	272.8
120°	385.7	345.4	331.0	316.6	297.0	286.6	282.0	278.6	282.0	286.6	297.0
122.5°	409.8	369.5	355.2	340.8	318.9	308.5	305.1	302.8	305.1	308.5	318.9
125°	430.5	392.6	377.6	362.6	340.8	330.4	324.6	322.3	324.6	330.4	340.8
127.5°	451.3	414.4	399.4	384.5	361.5	348.8	341.9	338.5	341.9	348.8	361.5
130°	470.8	435.2	420.2	405.2	381.0	366.1	356.9	353.4	356.9	366.1	381.0
132.5°	489.3	453.6	438.6	423.6	398.3	381.0	369.5	364.9	369.5	381.0	398.3
135°	505.4	469.7	454.2	438.6	414.4	396.0	382.2	377.6	382.2	396.0	414.4
137.5°	516.9	484.7	468.6	452.4	428.2	409.8	397.2	393.7	397.2	409.8	428.2
140°	529.6	496.2	480.6	465.1	443.2	424.8	411.0	407.5	411.0	424.8	443.2
142.5°	537.6	506.5	492.1	477.7	457.0	438.6	425.9	423.6	425.9	438.6	457.0
145°	546.8	516.9	503.6	490.4	469.7	453.6	442.1	439.8	442.1	453.6	469.7
147.5°	552.6	526.1	514.0	501.9	483.5	468.5	458.2	457.0	458.2	468.5	483.5
150°	558.3	533.0	523.2	513.4	497.3	482.4	474.3	472.0	474.3	482.4	497.3
152.5°	564.1	541.1	532.4	523.8	508.8	496.2	489.3	488.1	489.3	496.2	508.8
155°	567.5	548.0	540.0	531.9	520.3	508.8	501.9	501.9	501.9	508.8	520.3
157.5°	571.0	553.7	547.4	541.1	530.7	520.3	514.6	514.6	514.6	520.3	530.7
160°	573.3	558.3	553.2	548.0	538.8	530.7	526.1	527.2	526.1	530.7	538.8
162.5°	575.6	562.9	558.9	554.9	548.0	541.1	536.5	537.6	536.5	541.1	548.0
165°	575.6	566.4	563.0	559.5	554.9	549.1	545.7	548.0	545.7	549.1	554.9
167.5°	575.6	567.5	565.2	562.9	559.5	556.0	553.7	554.9	553.7	556.0	559.5
170°	575.6	569.8	568.1	566.4	564.1	561.8	560.6	561.8	560.6	561.8	564.1
172.5°	574.4	569.8	569.2	568.7	567.5	565.2	564.1	566.4	564.1	565.2	567.5
175°	573.3	569.8	569.8	569.8	569.8	568.7	567.5	569.8	567.5	568.7	569.8
177.5°	572.1	569.8	569.8	569.8	571.0	569.8	569.8	572.1	569.8	569.8	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	871.8	870.3	866.6	864.3	856.8	847.8	844.8	837.3	840.3	835.0	835.0
5°	848.6	841.8	837.3	830.5	816.3	806.5	796.0	790.8	787.8	784.0	781.0
7.5°	818.5	813.3	808.8	796.0	780.3	766.8	754.0	748.8	739.0	732.3	729.3
10°	792.3	784.8	774.3	759.3	742.8	725.5	714.3	703.0	695.5	691.7	683.5
12.5°	765.3	756.3	745.0	723.3	705.3	694.7	674.5	664.0	660.2	657.2	647.5
15°	737.5	727.8	714.3	694.0	678.2	653.5	641.5	633.2	624.2	623.5	616.0
17.5°	712.8	700.8	689.5	664.7	645.2	623.5	616.7	607.7	599.5	590.5	586.7
20°	681.2	670.0	661.7	634.7	613.0	599.5	588.2	580.7	575.5	566.5	565.0
22.5°	652.7	640.7	629.5	609.2	590.5	573.2	559.7	551.4	549.2	545.4	538.7
25°	625.0	613.0	599.5	580.7	561.2	549.2	537.2	531.9	527.4	521.4	516.2
27.5°	601.7	590.5	577.7	554.4	537.9	528.9	516.2	510.2	504.2	501.2	498.9
30°	574.0	561.2	551.4	533.4	515.4	503.4	494.4	489.2	483.9	480.9	479.4
32.5°	546.9	534.9	528.2	508.7	494.4	480.2	473.4	469.7	466.7	463.7	460.7
35°	525.2	513.2	502.7	484.7	470.4	460.7	455.4	449.4	447.2	444.2	444.2
37.5°	498.2	489.2	478.7	461.4	448.7	441.2	436.7	429.2	428.4	426.9	424.7
40°	474.9	465.9	456.2	441.2	429.9	420.9	414.9	411.1	408.9	407.4	405.9
42.5°	450.2	440.4	435.9	418.6	408.9	399.9	396.9	393.1	392.4	389.4	385.6
45°	426.2	417.9	408.9	396.1	387.9	380.4	375.9	372.9	369.1	368.4	366.1
47.5°	405.1	395.4	387.1	375.1	366.1	360.1	356.4	352.6	349.6	347.4	345.1
50°	378.1	370.6	363.9	351.1	343.6	337.6	332.4	329.4	326.4	326.4	326.4
52.5°	351.9	345.1	339.1	330.1	321.1	315.9	309.9	307.6	306.1	303.9	306.1
55°	326.4	319.6	313.6	306.9	296.4	291.9	285.9	283.6	284.4	284.4	286.6
57.5°	299.4	294.1	290.4	282.1	272.3	267.8	264.1	261.8	261.8	264.8	265.6
60°	273.1	267.8	261.1	253.6	247.6	242.3	240.1	240.8	240.8	242.3	246.1
62.5°	243.8	240.8	237.1	226.6	222.8	219.1	216.1	218.3	217.6	221.3	226.6
65°	216.8	213.8	208.6	203.3	198.8	195.1	194.3	195.1	196.6	200.3	206.3
67.5°	186.8	186.8	182.3	177.8	174.1	170.3	171.1	171.8	173.3	177.8	186.8
70°	162.1	159.1	154.6	151.6	148.6	147.1	145.6	148.6	153.1	156.1	162.8
72.5°	135.0	132.8	129.0	126.0	125.3	123.8	123.0	124.5	129.0	134.3	141.8
75°	106.5	107.3	105.0	102.8	102.8	100.5	102.0	102.0	106.5	111.8	117.8
77.5°	82.5	81.8	81.0	79.5	78.8	78.8	78.8	80.3	84.8	87.8	93.8
80°	58.5	59.3	57.0	57.8	57.0	57.8	57.8	60.8	63.0	66.8	71.3
82.5°	39.0	39.0	37.5	38.3	38.3	38.3	39.0	40.5	43.5	46.5	49.5
85°	21.8	22.5	21.0	22.5	22.5	22.5	23.3	24.0	26.3	27.0	30.0
87.5°	8.3	9.8	9.8	8.3	9.0	9.8	10.5	9.8	11.3	12.8	13.5
90°	9.2	10.4	11.5	12.7	15.0	16.1	18.4	19.6	20.7	21.9	23.0
92.5°	73.7	94.4	115.1	193.4	324.6	467.4	459.3	370.7	249.8	179.6	133.5
95°	86.3	112.2	138.1	261.3	514.6	832.3	1020.0	998.1	827.7	652.7	511.1
97.5°	102.5	121.4	140.4	225.6	420.2	763.2	1101.7	1246.7	1186.9	1047.6	904.8
100°	122.0	139.3	156.6	223.3	373.0	663.1	1039.5	1327.3	1416.0	1359.6	1241.0
102.5°	142.7	159.4	176.1	233.7	353.4	587.1	930.2	1279.0	1493.1	1550.7	1509.2
105°	165.8	181.9	198.0	248.7	351.1	543.4	834.6	1165.0	1441.3	1599.0	1649.7
107.5°	191.1	205.5	219.9	269.4	359.2	520.3	763.2	1056.8	1335.4	1543.8	1665.8
110°	215.3	230.2	245.2	292.4	371.8	511.1	716.0	967.0	1215.7	1434.4	1596.7

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	240.6	255.0	269.4	314.3	388.0	511.1	688.4	900.2	1121.3	1326.2	1490.8
115°	265.9	280.3	294.7	337.3	404.1	514.6	670.0	855.3	1045.3	1223.7	1381.4
117.5°	292.4	306.2	320.0	360.3	422.5	520.3	659.6	825.4	992.3	1150.0	1288.2
120°	316.6	331.0	345.4	385.7	440.9	529.6	652.7	801.2	950.9	1089.0	1215.7
122.5°	340.8	355.2	369.5	409.8	461.6	537.6	647.0	780.5	919.8	1045.3	1154.7
125°	362.6	377.6	392.6	430.5	480.0	546.8	642.4	762.1	889.9	1007.3	1107.5
127.5°	384.5	399.4	414.4	451.3	497.3	557.2	640.1	744.8	858.8	970.5	1064.9
130°	405.2	420.2	435.2	470.8	514.6	566.4	637.8	727.6	830.0	931.3	1021.1
132.5°	423.6	438.6	453.6	489.3	529.6	576.8	637.8	713.7	801.2	894.5	973.9
135°	438.6	454.2	469.7	505.4	543.4	586.0	637.8	703.4	777.1	856.5	930.2
137.5°	452.4	468.6	484.7	516.9	553.7	595.2	638.9	693.0	755.2	822.0	885.3
140°	465.1	480.6	496.2	529.6	564.1	600.9	640.1	686.1	737.9	792.0	845.0
142.5°	477.7	492.1	506.5	537.6	569.8	604.4	641.2	680.4	723.0	766.7	810.4
145°	490.4	503.6	516.9	546.8	575.6	606.7	640.1	674.6	710.3	746.0	781.7
147.5°	501.9	514.0	526.1	552.6	579.1	607.8	637.8	668.8	697.6	727.6	756.3
150°	513.4	523.2	533.0	558.3	582.5	607.8	634.3	661.9	687.3	712.6	734.5
152.5°	523.8	532.4	541.1	564.1	584.8	606.7	629.7	653.9	675.8	697.6	717.2
155°	531.9	540.0	548.0	567.5	586.0	604.4	623.9	644.7	664.2	682.7	698.8
157.5°	541.1	547.4	553.7	571.0	587.1	602.1	618.2	636.6	652.7	668.8	681.5
160°	548.0	553.2	558.3	573.3	587.1	598.6	612.4	626.3	641.2	652.7	664.2
162.5°	554.9	558.9	562.9	575.6	586.0	595.2	605.5	617.0	628.6	638.9	648.1
165°	559.5	563.0	566.4	575.6	584.8	591.7	598.6	607.8	617.0	625.1	632.0
167.5°	562.9	565.2	567.5	575.6	582.5	586.0	591.7	598.6	605.5	611.3	617.0
170°	566.4	568.1	569.8	575.6	580.2	582.5	586.0	590.6	596.3	599.8	603.2
172.5°	568.7	569.2	569.8	574.4	577.9	577.9	579.1	582.5	586.0	589.4	591.7
175°	569.8	569.8	569.8	573.3	575.6	574.4	574.4	575.6	579.1	579.1	581.4
177.5°	569.8	569.8	569.8	572.1	573.3	571.0	571.0	572.1	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	838.0	832.8	832.0	833.5	830.5	835.0	833.5	835.0	831.3	835.0	832.8
5°	780.3	778.8	775.8	772.0	772.8	773.5	777.3	773.5	776.5	777.3	781.0
7.5°	726.3	723.3	725.5	724.0	717.3	715.8	717.3	719.5	724.0	727.0	729.3
10°	682.7	681.2	678.2	676.0	672.2	670.0	673.0	670.0	676.0	681.2	681.2
12.5°	649.7	643.7	640.0	639.2	631.0	632.5	635.5	637.7	644.5	647.5	647.5
15°	615.2	610.7	609.2	606.2	603.2	606.2	604.7	607.0	610.0	613.0	614.5
17.5°	585.2	584.5	585.2	577.7	580.0	576.2	577.0	580.7	578.5	580.7	585.2
20°	558.2	559.7	557.4	554.4	554.4	549.9	555.2	553.7	554.4	558.9	565.7
22.5°	537.9	537.2	534.9	532.7	529.7	530.4	531.2	529.7	535.7	539.4	540.2
25°	516.2	514.7	513.9	511.7	508.7	511.7	510.9	511.7	513.2	519.2	514.7
27.5°	495.9	492.9	494.4	492.2	491.4	492.2	492.2	492.9	494.4	495.2	495.9
30°	478.7	475.7	474.9	473.4	472.7	473.4	474.9	473.4	479.4	478.7	478.7
32.5°	459.9	457.7	456.2	456.2	455.4	454.7	455.4	456.2	460.7	457.7	460.7
35°	441.9	440.4	440.4	438.9	438.2	438.2	438.2	441.2	439.7	441.9	441.9
37.5°	424.7	424.7	423.9	422.4	421.7	422.4	421.7	423.2	422.4	423.2	423.9
40°	406.6	405.1	404.4	404.4	402.1	399.9	402.1	402.1	402.9	405.1	405.9
42.5°	384.9	385.6	385.6	382.6	382.6	382.6	383.4	384.1	384.1	385.6	385.6
45°	366.1	364.6	364.6	364.6	363.1	363.9	365.4	365.4	365.4	365.4	363.9
47.5°	345.1	345.1	345.9	345.9	348.1	347.4	347.4	346.6	345.1	345.1	345.9
50°	325.6	327.9	328.6	328.6	329.4	330.1	330.1	328.6	327.9	325.6	325.6
52.5°	306.9	308.4	309.9	312.1	313.6	312.9	312.9	311.4	308.4	307.6	306.9
55°	286.6	288.9	291.9	294.1	296.4	297.1	297.1	294.1	291.1	287.4	287.4
57.5°	267.8	270.1	275.3	277.6	280.6	280.6	279.1	276.8	272.3	269.3	267.1
60°	249.1	252.8	256.6	261.1	264.8	265.6	263.3	260.3	255.1	251.3	248.3
62.5°	228.8	232.6	240.1	244.6	247.6	247.6	247.6	243.8	237.1	231.8	227.3
65°	209.3	213.1	219.8	225.8	228.1	230.3	228.1	224.3	219.1	213.1	208.6
67.5°	189.1	193.6	200.3	204.8	207.8	210.1	208.6	205.6	198.8	190.6	187.6
70°	166.6	168.8	178.6	183.1	187.6	189.1	187.6	183.1	176.3	167.3	164.3
72.5°	145.6	147.8	156.8	160.6	164.3	165.8	163.6	160.6	154.6	146.3	142.6
75°	121.5	125.3	129.8	135.8	140.3	141.8	139.5	137.3	129.8	124.5	121.5
77.5°	96.0	99.8	105.8	111.0	115.5	114.8	111.8	112.5	104.3	98.3	96.0
80°	72.8	75.8	80.3	84.8	87.0	87.0	86.3	83.3	80.3	75.8	72.0
82.5°	50.3	54.0	57.8	60.8	60.8	61.5	60.0	59.3	56.3	52.5	51.8
85°	30.0	30.8	33.8	33.8	36.8	35.3	34.5	36.8	33.8	31.5	30.8
87.5°	13.5	12.8	13.5	13.5	12.8	14.3	14.3	13.5	14.3	13.5	13.5
90°	24.2	25.3	25.3	25.3	26.5	26.5	26.5	25.3	25.3	25.3	24.2
92.5°	122.6	111.7	93.2	89.8	87.5	85.2	87.5	89.8	93.2	111.7	122.6
95°	462.8	414.4	332.7	298.2	289.0	270.5	289.0	298.2	332.7	414.4	462.8
97.5°	835.8	766.7	697.6	637.8	606.7	592.9	606.7	637.8	697.6	766.7	835.8
100°	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4	958.9	1041.8	1121.3	1181.2
102.5°	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4	1298.6	1351.5	1437.8	1473.5
105°	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2	1562.2	1600.2	1637.0	1643.4
107.5°	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5	1721.0	1726.8	1716.4	1691.1
110°	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3	1768.2	1746.4	1694.6	1645.6



TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7	1733.7	1692.3	1610.5	1550.6
115°	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2	1652.0	1596.7	1506.9	1444.2
117.5°	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5	1555.3	1497.7	1406.8	1347.5
120°	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5	1457.4	1402.2	1317.0	1266.4
122.5°	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2	1371.1	1321.6	1247.9	1201.3
125°	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3	1302.0	1254.8	1190.3	1148.9
127.5°	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6	1244.4	1201.9	1143.1	1104.0
130°	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5	1191.5	1153.5	1095.9	1058.5
132.5°	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6	1140.8	1102.8	1045.3	1009.6
135°	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2	1084.4	1046.4	995.8	963.0
137.5°	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1	1024.6	988.9	942.8	914.0
140°	869.2	893.3	935.9	965.9	983.1	988.9	983.1	965.9	935.9	893.3	869.2
142.5°	830.6	850.7	885.3	909.4	925.6	930.2	925.6	909.4	885.3	850.7	830.6
145°	797.2	812.7	840.4	859.9	872.6	877.2	872.6	859.9	840.4	812.7	797.2
147.5°	768.4	780.5	803.5	819.7	827.7	830.0	827.7	819.7	803.5	780.5	768.4
150°	744.8	755.2	772.5	786.3	790.9	792.0	790.9	786.3	772.5	755.2	744.8
152.5°	724.7	732.2	746.0	756.3	760.9	762.1	760.9	756.3	746.0	732.2	724.7
155°	705.1	711.4	723.0	731.0	734.5	735.6	734.5	731.0	723.0	711.4	705.1
157.5°	686.7	691.9	701.1	708.0	711.4	711.4	711.4	708.0	701.1	691.9	686.7
160°	668.2	672.3	680.4	686.1	688.4	687.3	688.4	686.1	680.4	672.3	668.2
162.5°	651.6	655.0	660.8	665.4	665.4	665.4	665.4	665.4	660.8	655.0	651.6
165°	634.9	637.8	642.4	644.7	644.7	644.7	644.7	644.7	642.4	637.8	634.9
167.5°	619.3	621.6	623.9	626.3	625.1	625.1	625.1	626.3	623.9	621.6	619.3
170°	604.4	605.5	607.8	609.0	609.0	607.8	609.0	609.0	607.8	605.5	604.4
172.5°	592.3	592.9	592.9	595.2	592.9	591.7	592.9	595.2	592.9	592.9	592.3
175°	581.4	581.4	581.4	582.5	580.2	579.1	580.2	582.5	581.4	581.4	581.4
177.5°	574.4	574.4	573.3	574.4	571.0	571.0	571.0	574.4	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	839.5	835.0	840.3	833.5	835.0	843.3	842.6	850.1	854.6	853.8	857.6
5°	784.0	784.0	786.3	785.5	793.0	799.8	808.8	816.3	824.5	829.0	834.3
7.5°	729.3	736.8	738.3	742.0	751.0	762.3	771.3	782.5	794.5	802.8	808.8
10°	684.2	690.2	696.2	699.2	709.0	724.0	736.8	754.8	769.8	778.8	787.0
12.5°	644.5	651.2	654.2	667.7	674.5	684.2	702.3	721.8	738.3	748.0	754.8
15°	616.0	619.7	626.5	634.7	641.5	653.5	668.5	690.2	706.0	714.3	737.5
17.5°	592.0	596.5	600.2	604.0	614.5	627.2	641.5	660.2	680.5	694.7	706.8
20°	567.2	569.5	574.0	580.0	587.5	599.5	612.2	631.7	649.7	661.0	676.7
22.5°	537.9	544.7	549.2	553.7	562.0	575.5	587.5	601.7	624.2	637.0	653.5
25°	520.7	523.7	526.7	531.9	537.9	549.9	563.5	578.5	596.5	610.0	624.2
27.5°	498.2	502.7	506.4	513.2	516.9	526.7	539.4	554.4	576.2	587.5	599.5
30°	479.4	483.9	486.9	489.9	495.2	505.7	517.7	529.7	549.9	564.2	576.2
32.5°	460.7	465.2	468.9	471.2	476.4	483.2	492.9	507.9	525.2	534.9	550.7
35°	444.2	444.2	448.7	451.7	456.2	462.2	471.2	482.4	500.4	513.2	527.4
37.5°	425.4	426.2	429.9	432.2	436.7	442.7	451.7	462.2	477.2	486.9	501.2
40°	405.9	408.1	409.6	413.4	418.6	420.9	429.9	441.9	456.9	465.9	477.9
42.5°	386.4	387.9	391.6	394.6	399.1	402.9	408.9	420.2	431.4	444.9	454.7
45°	364.6	368.4	370.6	375.9	378.1	381.9	387.9	396.9	410.4	418.6	429.9
47.5°	345.9	347.4	348.9	355.6	360.1	362.4	368.4	373.6	387.9	395.4	405.9
50°	325.6	325.6	327.9	330.9	336.1	340.6	345.9	351.9	363.1	370.6	381.1
52.5°	306.9	304.6	306.1	307.6	312.9	317.4	322.6	330.9	341.4	345.9	354.9
55°	286.6	282.9	285.1	287.4	288.9	294.9	300.9	306.1	314.4	321.1	329.4
57.5°	264.8	264.1	262.6	263.3	267.1	270.8	275.3	282.1	291.9	297.1	301.6
60°	245.3	240.8	239.3	240.8	243.1	245.3	251.3	257.3	265.6	270.8	276.1
62.5°	225.1	220.6	217.6	215.3	217.6	222.8	226.6	231.1	237.8	243.8	248.3
65°	205.6	198.8	195.8	194.3	193.6	197.3	200.3	206.3	212.3	214.6	219.8
67.5°	183.8	177.8	174.1	171.8	171.8	171.8	174.8	180.8	186.8	187.6	192.8
70°	162.1	155.3	151.6	148.6	147.1	148.6	152.3	153.1	158.3	159.8	162.8
72.5°	138.8	132.8	128.3	124.5	125.3	126.8	126.8	128.3	131.3	135.0	135.0
75°	117.0	108.8	106.5	103.5	102.0	102.0	102.0	105.0	107.3	110.3	109.5
77.5°	92.3	87.8	83.3	81.8	79.5	78.8	80.3	80.3	81.8	84.0	84.8
80°	71.3	66.0	63.0	61.5	58.5	57.8	58.5	58.5	60.8	60.0	60.8
82.5°	49.5	45.8	43.5	41.3	39.8	40.5	39.8	39.8	40.5	39.8	39.8
85°	28.5	27.8	26.3	25.5	24.8	23.3	24.8	24.0	23.3	22.5	24.0
87.5°	13.5	12.8	12.8	11.3	11.3	10.5	11.3	11.3	10.5	10.5	10.5
90°	23.0	21.9	20.7	19.6	18.4	16.1	15.0	12.7	11.5	10.4	9.2
92.5°	133.5	179.6	249.8	370.7	459.3	467.4	324.6	193.4	115.1	94.4	73.7
95°	511.1	652.7	827.7	998.1	1020.0	832.3	514.6	261.3	138.1	112.2	86.3
97.5°	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2	225.6	140.4	121.4	102.5
100°	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0	223.3	156.6	139.3	122.0
102.5°	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4	233.7	176.1	159.4	142.7
105°	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1	248.7	198.0	181.9	165.8
107.5°	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2	269.4	219.9	205.5	191.1
110°	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8	292.4	245.2	230.2	215.3

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0	314.3	269.4	255.0	240.6
115°	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1	337.3	294.7	280.3	265.9
117.5°	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5	360.3	320.0	306.2	292.4
120°	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9	385.7	345.4	331.0	316.6
122.5°	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6	409.8	369.5	355.2	340.8
125°	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0	430.5	392.6	377.6	362.6
127.5°	1064.9	970.5	858.8	744.8	640.1	557.2	497.3	451.3	414.4	399.4	384.5
130°	1021.1	931.3	830.0	727.6	637.8	566.4	514.6	470.8	435.2	420.2	405.2
132.5°	973.9	894.5	801.2	713.7	637.8	576.8	529.6	489.3	453.6	438.6	423.6
135°	930.2	856.5	777.1	703.4	637.8	586.0	543.4	505.4	469.7	454.2	438.6
137.5°	885.3	822.0	755.2	693.0	638.9	595.2	553.7	516.9	484.7	468.6	452.4
140°	845.0	792.0	737.9	686.1	640.1	600.9	564.1	529.6	496.2	480.6	465.1
142.5°	810.4	766.7	723.0	680.4	641.2	604.4	569.8	537.6	506.5	492.1	477.7
145°	781.7	746.0	710.3	674.6	640.1	606.7	575.6	546.8	516.9	503.6	490.4
147.5°	756.3	727.6	697.6	668.8	637.8	607.8	579.1	552.6	526.1	514.0	501.9
150°	734.5	712.6	687.3	661.9	634.3	607.8	582.5	558.3	533.0	523.2	513.4
152.5°	717.2	697.6	675.8	653.9	629.7	606.7	584.8	564.1	541.1	532.4	523.8
155°	698.8	682.7	664.2	644.7	623.9	604.4	586.0	567.5	548.0	540.0	531.9
157.5°	681.5	668.8	652.7	636.6	618.2	602.1	587.1	571.0	553.7	547.4	541.1
160°	664.2	652.7	641.2	626.3	612.4	598.6	587.1	573.3	558.3	553.2	548.0
162.5°	648.1	638.9	628.6	617.0	605.5	595.2	586.0	575.6	562.9	558.9	554.9
165°	632.0	625.1	617.0	607.8	598.6	591.7	584.8	575.6	566.4	563.0	559.5
167.5°	617.0	611.3	605.5	598.6	591.7	586.0	582.5	575.6	567.5	565.2	562.9
170°	603.2	599.8	596.3	590.6	586.0	582.5	580.2	575.6	569.8	568.1	566.4
172.5°	591.7	589.4	586.0	582.5	579.1	577.9	577.9	574.4	569.8	569.2	568.7
175°	581.4	579.1	579.1	575.6	574.4	574.4	575.6	573.3	569.8	569.8	569.8
177.5°	574.4	574.4	573.3	572.1	571.0	571.0	573.3	572.1	569.8	569.8	569.8
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.8	883.8	883.8	883.8
2.5°	862.8	870.3	875.6	885.3
5°	843.3	856.8	869.6	883.1
7.5°	823.8	839.5	859.8	877.1
10°	802.0	822.3	846.3	869.6
12.5°	780.3	804.3	830.5	861.3
15°	754.0	784.8	815.5	848.6
17.5°	730.8	762.3	795.3	836.5
20°	704.5	739.0	775.0	817.0
22.5°	681.2	719.5	757.0	801.3
25°	655.0	692.5	733.8	781.0
27.5°	633.2	667.7	708.3	759.3
30°	607.0	644.5	685.0	736.0
32.5°	582.2	618.2	661.0	711.3
35°	556.7	593.5	631.7	679.7
37.5°	532.7	564.2	602.5	648.2
40°	505.7	540.2	574.7	610.7
42.5°	480.9	512.4	544.7	573.2
45°	453.2	480.2	510.9	534.2
47.5°	427.7	451.7	475.7	493.7
50°	402.1	420.9	438.9	454.7
52.5°	372.1	393.1	402.9	412.6
55°	345.1	357.1	366.1	375.9
57.5°	318.9	324.1	328.6	337.6
60°	284.4	290.4	295.6	302.4
62.5°	254.3	257.3	258.8	265.6
65°	225.8	225.1	228.8	232.6
67.5°	195.1	194.3	198.1	199.6
70°	165.1	164.3	165.1	168.8
72.5°	136.5	136.5	137.3	138.8
75°	110.3	110.3	111.0	112.5
77.5°	83.3	84.8	84.0	87.0
80°	60.8	59.3	60.8	62.3
82.5°	39.8	41.3	41.3	39.8
85°	22.5	22.5	22.5	22.5
87.5°	9.8	9.8	10.5	11.3
90°	6.9	4.6	2.3	1.2
92.5°	49.5	32.2	20.7	17.3
95°	61.0	48.4	39.1	38.0
97.5°	79.4	66.8	59.9	58.7
100°	100.2	87.5	82.9	80.6
102.5°	123.2	109.4	105.9	104.8
105°	147.4	135.8	130.1	130.1
107.5°	171.5	162.3	156.6	154.3
110°	198.0	187.6	183.0	180.7

TEST NUMBER: P1028017

CATALOG NUMBER: S125DIP-B610D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	223.3	213.0	209.5	207.2
115°	248.7	238.3	234.8	232.5
117.5°	272.8	262.5	259.0	255.6
120°	297.0	286.6	282.0	278.6
122.5°	318.9	308.5	305.1	302.8
125°	340.8	330.4	324.6	322.3
127.5°	361.5	348.8	341.9	338.5
130°	381.0	366.1	356.9	353.4
132.5°	398.3	381.0	369.5	364.9
135°	414.4	396.0	382.2	377.6
137.5°	428.2	409.8	397.2	393.7
140°	443.2	424.8	411.0	407.5
142.5°	457.0	438.6	425.9	423.6
145°	469.7	453.6	442.1	439.8
147.5°	483.5	468.5	458.2	457.0
150°	497.3	482.4	474.3	472.0
152.5°	508.8	496.2	489.3	488.1
155°	520.3	508.8	501.9	501.9
157.5°	530.7	520.3	514.6	514.6
160°	538.8	530.7	526.1	527.2
162.5°	548.0	541.1	536.5	537.6
165°	554.9	549.1	545.7	548.0
167.5°	559.5	556.0	553.7	554.9
170°	564.1	561.8	560.6	561.8
172.5°	567.5	565.2	564.1	566.4
175°	569.8	568.7	567.5	569.8
177.5°	571.0	569.8	569.8	572.1
180°	571.0	571.0	571.0	571.0

(END OF REPORT)