

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028114

Luminaire Tested: S125DIP-B610D610UB30-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028114
REPORT IS A COMBINATION OF REPORTS P1002323 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB30-4F0-XX-W2A-A
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4885.0 lumens
Efficiency: N/A
Efficacy: 124.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	45	43	42
3	82	73	65	60	76	67	61	56	58	53	49	49	45	42	40	38	36
4	75	64	57	51	69	60	53	48	51	46	42	43	40	36	36	33	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	29	27
6	64	52	43	38	59	48	41	36	41	36	32	35	31	28	30	26	24
7	59	47	39	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5711	5711	5711	5711
5°	5715	6478	5720	4914
10°	5680	7383	5670	4218
15°	5638	8006	5603	3812
20°	5567	8773	5516	3480
25°	5504	10052	5403	3283
30°	5413	10604	5319	3105
35°	5269	8501	5159	2962
40°	5045	5875	4971	2811
45°	4762	4374	4708	2685
50°	4438	3601	4364	2585
55°	4088	3072	4055	2497
60°	3745	2629	3680	2430
65°	3374	2270	3321	2331
70°	2983	1884	2945	2160
75°	2570	1458	2536	1874
80°	2029	986	1955	1378
85°	1298	494	1252	703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8722 cd/sqm

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.8
10°-20°	255.5	5.2
20°-30°	415.0	8.5
30°-40°	507.2	10.4
40°-50°	460.1	9.4
50°-60°	366.5	7.5
60°-70°	255.2	5.2
70°-80°	136.0	2.8
80°-90°	34.9	0.7
90°-100°	26.2	0.5
100°-110°	174.1	3.6
110°-120°	313.4	6.4
120°-130°	402.3	8.2
130°-140°	432.7	8.9
140°-150°	406.1	8.3
150°-160°	328.5	6.7
160°-170°	212.4	4.3
170°-180°	73.3	1.5
0°-30°	756.3	15.5
0°-40°	1263.5	25.9
0°-60°	2090.1	42.8
0°-90°	2516.1	51.5
90°-120°	513.6	10.5
90°-150°	1754.7	35.9
90°-180°	2369.0	48.5
0°-180°	4885.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	891	891	891	891	891	
5°	890	1028	891	780	890	85
15°	856	1284	850	611	856	241
25°	788	1580	773	516	788	363
35°	686	1268	671	442	686	428
45°	539	598	533	367	539	415
55°	379	368	376	300	379	339
65°	234	226	231	232	234	233
75°	114	111	112	143	114	121
85°	23	25	22	36	23	27
90°	1	14	1	14	1	3
95°	33	12	33	12	33	40
105°	168	170	168	170	168	178
115°	316	313	316	313	316	313
125°	449	449	449	449	449	401
135°	560	557	560	557	560	431
145°	649	647	649	647	649	406
155°	715	709	715	709	715	329
165°	754	750	754	750	754	213
175°	771	768	771	768	771	73
180°	771	771	771	771	771	

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	892.8	898.1	904.1	908.7	916.2	918.5	922.3	924.5	926.8	929.1	930.6
5°	890.5	903.4	914.7	923.0	937.4	942.7	949.5	957.8	967.7	976.0	981.3
7.5°	884.4	904.9	920.0	936.7	956.3	969.2	976.0	993.4	1009.3	1021.4	1037.3
10°	876.9	901.1	924.5	949.5	977.5	991.9	1005.5	1029.7	1051.7	1071.3	1087.2
12.5°	868.6	898.1	926.1	958.6	996.4	1013.8	1022.9	1064.5	1091.8	1102.3	1133.4
15°	855.7	890.5	930.6	970.7	1002.5	1022.9	1047.9	1081.2	1108.4	1131.9	1156.8
17.5°	843.6	881.4	922.3	966.9	1013.1	1039.5	1058.5	1088.0	1117.5	1147.7	1171.2
20°	823.9	873.1	914.7	962.4	1016.9	1035.8	1055.4	1090.2	1122.0	1154.5	1184.1
22.5°	808.0	854.9	911.7	957.1	1003.2	1022.1	1046.4	1082.7	1120.5	1157.6	1200.7
25°	787.6	839.8	889.0	937.4	985.1	1005.5	1027.4	1074.4	1113.7	1161.4	1209.0
27.5°	765.7	819.4	868.6	912.4	957.1	985.1	1008.5	1057.7	1109.9	1162.1	1224.2
30°	742.2	792.9	839.8	882.9	932.1	960.9	984.3	1041.8	1100.1	1166.7	1240.8
32.5°	717.2	764.9	805.0	848.9	901.1	927.6	959.4	1022.1	1091.0	1170.4	1263.5
35°	685.5	730.9	766.4	811.1	863.3	897.3	930.6	1001.0	1081.2	1169.7	1276.4
37.5°	653.7	689.2	723.3	771.0	831.5	862.5	897.3	974.5	1066.0	1167.4	1281.7
40°	615.9	650.7	680.2	728.6	792.1	827.7	864.0	945.0	1048.6	1159.1	1262.7
42.5°	578.0	607.5	640.1	690.8	752.0	789.9	828.5	918.5	1025.9	1134.9	1210.5
45°	538.7	561.4	596.9	643.1	708.2	744.5	788.4	886.0	994.2	1091.0	1128.8
47.5°	497.8	520.5	553.8	598.5	662.8	705.9	747.5	845.1	954.1	1029.0	1029.0
50°	458.5	476.6	509.2	553.8	618.9	658.2	700.6	804.3	892.0	947.2	898.1
52.5°	416.1	436.5	463.8	510.7	575.0	610.6	656.7	745.2	828.5	851.2	775.5
55°	379.0	395.7	421.4	466.1	525.8	562.9	602.2	687.0	757.3	755.8	674.9
57.5°	340.5	354.1	381.3	422.2	477.4	510.7	550.0	623.4	680.9	660.5	584.1
60°	304.9	314.7	341.2	374.5	427.5	458.5	496.3	556.1	600.0	571.2	494.1
62.5°	267.8	279.2	300.4	332.9	379.8	404.8	432.8	493.3	521.3	495.6	416.9
65°	234.5	243.6	262.5	289.8	332.1	354.8	379.0	429.0	455.5	418.4	353.3
67.5°	201.3	211.8	225.5	249.7	283.0	304.1	325.3	368.5	380.6	347.3	292.8
70°	170.2	179.3	192.2	209.6	237.6	256.5	272.4	307.9	316.3	285.2	242.1
72.5°	140.0	146.0	156.6	171.0	196.7	207.3	223.9	248.2	258.8	230.8	199.7
75°	113.5	118.0	124.8	135.4	152.8	164.2	177.8	200.5	199.7	180.1	158.1
77.5°	87.8	88.5	96.1	105.9	116.5	126.3	133.2	149.0	150.6	138.5	120.3
80°	62.8	65.1	68.1	75.7	84.7	88.5	96.8	106.7	108.2	99.1	87.0
82.5°	40.1	41.6	43.9	48.4	54.5	59.0	63.6	67.3	71.1	65.8	56.0
85°	22.7	23.5	25.7	27.2	30.3	32.5	36.3	40.1	39.3	35.6	32.5
87.5°	11.3	11.3	11.3	12.9	14.4	14.4	15.9	16.6	17.4	15.9	14.4
90°	0.6	1.6	2.6	3.6	4.6	5.1	5.5	6.4	7.3	8.2	9.1
92.5°	10.9	9.7	8.6	7.4	6.3	5.7	6.1	6.8	7.6	8.3	9.1
95°	32.6	32.2	31.8	31.5	31.1	30.9	28.5	23.6	18.8	13.9	9.1
97.5°	61.2	62.0	62.7	63.5	64.2	64.6	58.6	46.5	34.4	22.4	10.3
100°	95.5	95.9	96.3	96.6	97.0	97.2	97.5	98.0	98.5	99.0	99.5
102.5°	130.3	130.8	131.3	131.8	132.3	132.6	132.7	133.0	133.3	133.5	133.8
105°	168.1	168.6	169.1	169.6	170.1	170.4	170.4	170.4	170.4	170.4	170.4
107.5°	206.9	206.9	206.9	206.9	206.9	206.9	207.0	207.3	207.6	207.8	208.1
110°	244.7	244.7	244.7	244.7	244.7	244.7	244.8	245.1	245.3	245.6	245.8

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	280.1	280.5	280.9	281.2	281.6	281.8	281.9	282.0	282.1	282.3	282.4
115°	315.6	316.2	316.8	317.5	318.1	318.4	318.5	318.6	318.7	318.9	319.0
117.5°	352.7	352.7	352.7	352.7	352.7	352.7	353.0	353.5	354.0	354.5	355.0
120°	387.0	386.9	386.7	386.6	386.5	386.4	386.6	387.0	387.4	387.8	388.2
122.5°	417.3	417.9	418.6	419.2	419.9	420.2	420.3	420.4	420.5	420.6	420.7
125°	448.8	449.7	450.6	451.5	452.4	452.8	452.8	452.8	452.8	452.8	452.8
127.5°	479.0	479.6	480.3	480.9	481.6	481.9	481.8	481.7	481.6	481.4	481.3
130°	506.5	507.1	507.7	508.4	509.0	509.3	509.4	509.5	509.6	509.8	509.9
132.5°	533.9	534.7	535.5	536.2	537.0	537.4	537.2	536.8	536.4	536.0	535.6
135°	559.7	560.5	561.2	562.0	562.7	563.1	563.0	562.7	562.4	562.2	561.9
137.5°	583.7	584.5	585.2	586.0	586.7	587.1	587.0	586.7	586.4	586.2	585.9
140°	607.1	607.3	607.6	607.8	608.1	608.2	608.1	608.0	607.9	607.8	607.7
142.5°	628.3	628.4	628.5	628.6	628.7	628.8	628.9	629.2	629.5	629.7	630.0
145°	648.8	649.1	649.3	649.6	649.9	650.0	650.0	650.0	650.0	650.0	650.0
147.5°	667.1	667.1	667.1	667.1	667.1	667.1	667.2	667.3	667.4	667.6	667.7
150°	684.3	684.0	683.8	683.5	683.2	683.1	683.2	683.5	683.8	684.0	684.3
152.5°	700.9	700.3	699.6	699.0	698.3	698.0	698.1	698.4	698.6	698.9	699.1
155°	714.6	713.8	713.0	712.3	711.5	711.1	711.2	711.5	711.8	712.0	712.3
157.5°	725.4	725.0	724.6	724.3	723.9	723.7	723.7	723.7	723.7	723.7	723.7
160°	736.9	736.1	735.3	734.6	733.8	733.4	733.5	733.6	733.7	733.9	734.0
162.5°	746.0	745.2	744.5	743.7	743.0	742.6	742.7	742.8	742.9	743.1	743.2
165°	754.0	753.2	752.5	751.7	751.0	750.6	750.7	750.8	750.9	751.1	751.2
167.5°	760.3	759.5	758.8	758.0	757.3	756.9	757.0	757.1	757.2	757.3	757.4
170°	765.4	764.5	763.6	762.7	761.8	761.4	761.5	761.6	761.7	761.9	762.0
172.5°	768.9	768.0	767.1	766.2	765.3	764.9	765.0	765.3	765.5	765.8	766.0
175°	771.2	770.4	769.6	768.9	768.1	767.7	767.8	767.9	768.0	768.2	768.3
177.5°	772.9	772.1	771.4	770.6	769.9	769.5	769.6	769.7	769.8	769.9	770.0
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	932.1	937.4	941.9	945.7	948.8	953.3	950.3	951.0	952.5	955.6	955.6
5°	992.6	1001.0	1005.5	1020.6	1024.4	1023.7	1021.4	1033.5	1032.7	1028.2	1027.4
7.5°	1051.7	1066.0	1078.9	1091.0	1094.8	1104.6	1106.9	1112.2	1110.7	1118.2	1114.5
10°	1105.4	1128.1	1140.2	1158.3	1162.9	1167.4	1173.5	1176.5	1183.3	1182.5	1182.5
12.5°	1147.0	1174.2	1190.1	1194.6	1212.0	1217.3	1222.6	1232.5	1230.2	1231.0	1235.5
15°	1179.5	1206.0	1219.6	1240.8	1252.9	1259.0	1268.0	1278.6	1277.1	1283.9	1282.4
17.5°	1203.7	1228.7	1253.7	1285.4	1286.2	1302.1	1323.3	1327.8	1337.6	1330.8	1330.8
20°	1223.4	1256.7	1292.2	1333.1	1337.6	1347.5	1373.2	1390.6	1402.0	1398.2	1400.4
22.5°	1244.6	1292.2	1333.9	1374.7	1396.7	1414.1	1439.0	1466.3	1476.1	1482.2	1480.6
25°	1271.8	1321.8	1383.0	1439.8	1462.5	1495.8	1529.1	1555.5	1563.1	1579.8	1564.6
27.5°	1299.8	1370.2	1446.6	1513.2	1541.9	1569.2	1609.3	1628.9	1638.8	1646.3	1641.0
30°	1323.3	1420.1	1503.3	1564.6	1585.0	1600.9	1623.6	1628.2	1624.4	1630.4	1638.0
32.5°	1359.6	1454.2	1524.5	1554.0	1551.8	1551.0	1533.6	1509.4	1504.1	1489.7	1509.4
35°	1379.3	1454.9	1482.2	1442.8	1426.9	1398.2	1342.9	1306.6	1274.8	1268.0	1269.6
37.5°	1367.9	1397.4	1364.9	1261.2	1235.5	1191.6	1118.2	1066.8	1043.3	1025.2	1048.6
40°	1306.6	1274.1	1184.8	1058.5	1021.4	979.8	910.9	882.9	849.6	842.8	873.9
42.5°	1205.2	1106.1	979.8	882.2	843.6	820.1	762.6	736.2	712.7	702.1	719.5
45°	1067.5	947.2	820.1	739.9	707.4	679.4	645.4	617.4	602.2	597.7	612.1
47.5°	925.3	798.2	696.8	637.0	603.0	581.8	550.0	534.1	522.0	523.6	525.8
50°	789.1	673.4	595.4	535.7	519.0	502.4	481.2	467.6	461.5	463.8	462.3
52.5°	671.8	578.0	512.2	466.1	458.5	442.6	425.2	413.9	411.6	412.3	414.6
55°	569.0	495.6	443.4	410.1	401.7	390.4	379.8	372.2	366.2	368.5	367.7
57.5°	491.0	426.7	386.6	359.4	353.3	346.5	336.7	332.9	330.6	326.1	329.9
60°	422.2	370.0	335.2	318.5	313.2	308.7	298.1	293.6	292.0	289.8	295.8
62.5°	357.1	320.0	293.6	278.4	273.1	268.6	263.3	259.5	260.3	257.2	260.3
65°	305.7	275.4	256.5	242.9	236.1	233.0	232.3	226.2	225.5	226.2	227.0
67.5°	258.0	232.3	217.9	209.6	204.3	201.3	199.0	195.2	198.2	196.0	197.5
70°	214.9	197.5	182.3	174.0	171.7	172.5	168.7	167.2	168.0	166.4	168.0
72.5°	173.3	158.9	152.8	146.8	143.8	143.0	140.7	138.5	140.7	140.0	140.0
75°	138.5	127.9	121.1	117.3	117.3	115.8	112.0	112.0	112.0	111.2	112.0
77.5°	106.7	97.6	94.6	90.8	90.8	88.5	87.8	87.8	86.3	88.5	87.0
80°	79.4	72.6	68.1	65.8	65.8	65.1	63.6	62.8	63.6	62.8	62.8
82.5°	51.4	48.4	46.2	43.9	43.1	43.9	43.1	41.6	42.4	41.6	43.1
85°	29.5	26.5	26.5	25.0	25.7	24.2	25.0	23.5	22.7	25.0	23.5
87.5°	12.9	12.1	12.1	10.6	10.6	10.6	9.8	10.6	9.8	9.1	9.8
90°	9.7	10.4	11.0	11.7	12.0	12.2	12.6	12.9	13.3	13.7	13.3
92.5°	9.7	10.4	11.0	11.7	12.0	12.1	12.2	12.3	12.5	12.6	12.5
95°	9.7	10.4	11.0	11.7	12.0	12.0	12.0	12.0	12.0	12.0	12.0
97.5°	10.5	10.8	11.0	11.3	11.4	11.5	11.6	11.7	11.9	12.0	11.9
100°	80.6	61.6	42.7	23.8	14.3	14.0	13.5	13.0	12.5	12.0	12.5
102.5°	134.0	134.3	134.5	134.8	134.9	129.6	118.9	108.2	97.6	86.9	97.6
105°	170.4	170.4	170.4	170.4	170.4	170.3	170.2	170.1	169.9	169.8	169.9
107.5°	208.2	208.4	208.5	208.6	208.7	208.4	207.9	207.4	206.9	206.4	206.9
110°	245.4	245.0	244.7	244.3	244.1	244.2	244.3	244.4	244.6	244.7	244.6

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	281.9	281.4	280.9	280.4	280.1	280.0	279.7	279.5	279.2	279.0	279.2
115°	318.5	318.0	317.5	317.0	316.7	316.3	315.6	314.8	314.1	313.3	314.1
117.5°	354.2	353.5	352.7	352.0	351.6	351.5	351.2	350.9	350.7	350.4	350.7
120°	387.9	387.7	387.4	387.1	387.0	386.7	386.1	385.4	384.8	384.2	384.8
122.5°	420.5	420.2	420.0	419.7	419.6	419.2	418.5	417.7	417.0	416.2	417.0
125°	452.3	451.8	451.3	450.8	450.5	450.3	449.9	449.6	449.2	448.8	449.2
127.5°	481.1	480.8	480.6	480.3	480.2	479.7	478.7	477.6	476.6	475.6	476.6
130°	509.5	509.1	508.8	508.4	508.2	507.9	507.2	506.6	505.9	505.3	505.9
132.5°	535.6	535.6	535.6	535.6	535.6	535.3	534.7	534.0	533.4	532.8	533.4
135°	561.7	561.4	561.2	560.9	560.8	560.4	559.7	558.9	558.2	557.4	558.2
137.5°	585.9	585.9	585.9	585.9	585.9	585.6	585.0	584.3	583.7	583.1	583.7
140°	607.9	608.2	608.4	608.7	608.8	608.4	607.7	606.9	606.2	605.4	606.2
142.5°	630.0	630.0	630.0	630.0	630.0	629.6	628.8	628.1	627.3	626.5	627.3
145°	650.1	650.2	650.3	650.4	650.5	650.1	649.4	648.6	647.9	647.1	647.9
147.5°	667.8	668.0	668.1	668.2	668.3	667.9	667.0	666.1	665.2	664.3	665.2
150°	684.5	684.8	685.0	685.3	685.4	684.9	683.9	682.8	681.8	680.8	681.8
152.5°	699.4	699.6	699.9	700.2	700.3	699.9	699.0	698.1	697.2	696.3	697.2
155°	712.7	713.1	713.4	713.8	714.0	713.5	712.5	711.4	710.4	709.4	710.4
157.5°	724.1	724.5	724.8	725.2	725.4	724.9	723.9	722.9	721.9	720.9	721.9
160°	734.5	735.0	735.5	736.0	736.3	735.8	734.8	733.7	732.7	731.7	732.7
162.5°	744.0	744.7	745.5	746.2	746.6	746.0	744.9	743.7	742.6	741.4	742.6
165°	752.0	752.7	753.5	754.2	754.6	754.1	753.1	752.0	751.0	750.0	751.0
167.5°	758.3	759.2	760.1	761.0	761.4	760.8	759.7	758.6	757.4	756.3	757.4
170°	763.0	764.0	765.1	766.1	766.6	766.0	764.9	763.7	762.6	761.4	762.6
172.5°	766.9	767.8	768.7	769.6	770.0	769.4	768.3	767.2	766.0	764.9	766.0
175°	769.3	770.3	771.4	772.4	772.9	772.3	771.2	770.0	768.9	767.7	768.9
177.5°	770.9	771.8	772.7	773.6	774.0	773.5	772.5	771.5	770.5	769.5	770.5
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	954.1	948.8	950.3	948.8	945.0	942.7	936.7	929.1	926.1	922.3	920.0
5°	1030.5	1026.7	1025.9	1019.9	1018.4	1009.3	994.2	986.6	977.5	968.4	959.4
7.5°	1113.7	1109.2	1094.0	1091.8	1093.3	1081.9	1062.2	1047.1	1028.2	1015.3	997.9
10°	1182.5	1173.5	1160.6	1161.4	1156.1	1140.9	1121.3	1105.4	1078.1	1061.5	1036.5
12.5°	1224.2	1216.6	1215.1	1207.5	1203.0	1183.3	1159.8	1139.4	1119.0	1096.3	1077.4
15°	1274.8	1265.0	1258.2	1247.6	1244.6	1224.2	1198.4	1175.0	1151.5	1130.3	1090.2
17.5°	1330.8	1320.2	1294.5	1292.2	1274.1	1254.4	1229.5	1194.6	1169.7	1139.4	1109.9
20°	1394.4	1379.3	1346.0	1337.6	1323.3	1290.7	1256.7	1218.1	1178.0	1147.0	1112.2
22.5°	1465.5	1439.0	1414.8	1388.3	1377.7	1337.6	1290.7	1243.8	1195.4	1153.0	1111.4
25°	1557.8	1523.0	1489.0	1462.5	1444.3	1392.1	1329.3	1267.3	1211.3	1156.1	1101.6
27.5°	1630.4	1600.2	1563.1	1528.3	1504.8	1442.8	1370.9	1290.7	1221.1	1153.8	1095.5
30°	1635.7	1626.7	1604.0	1585.0	1559.3	1492.7	1413.3	1322.5	1236.3	1154.5	1083.4
32.5°	1536.6	1554.8	1564.6	1567.6	1562.3	1523.8	1451.1	1351.3	1249.9	1147.7	1072.8
35°	1323.3	1371.7	1431.5	1454.2	1476.1	1496.5	1458.7	1371.7	1254.4	1146.2	1056.2
37.5°	1089.5	1133.4	1232.5	1277.9	1303.6	1384.6	1415.6	1368.7	1263.5	1147.7	1040.3
40°	879.2	948.8	1019.9	1081.2	1121.3	1212.0	1308.1	1318.7	1250.6	1133.4	1019.9
42.5°	739.9	780.8	834.5	891.3	926.8	1034.3	1164.4	1240.8	1210.5	1109.9	994.9
45°	630.2	660.5	711.2	730.1	775.5	878.4	1016.1	1126.6	1141.7	1072.8	966.2
47.5°	541.0	566.7	599.2	622.7	659.0	736.2	852.7	974.5	1047.1	1022.1	926.1
50°	476.6	497.8	525.1	538.7	562.1	631.7	719.5	840.6	938.2	946.5	873.9
52.5°	422.9	435.0	456.2	471.4	490.3	532.6	612.1	711.9	821.7	867.0	809.5
55°	376.0	385.9	404.8	414.6	424.4	460.8	522.8	613.6	716.5	776.3	743.7
57.5°	333.7	342.0	357.9	366.9	372.2	407.0	454.7	525.8	618.1	690.8	672.6
60°	298.9	306.4	315.5	322.3	328.4	357.1	390.4	447.9	530.4	600.7	596.2
62.5°	261.8	268.6	278.4	285.2	290.5	308.7	336.7	380.6	450.9	516.0	528.9
65°	229.2	234.5	241.4	244.4	251.2	264.8	287.5	326.8	384.3	442.6	451.7
67.5°	199.7	201.3	205.8	212.6	214.1	226.2	246.6	276.2	320.8	368.5	382.8
70°	168.0	170.2	174.0	179.3	182.3	189.9	207.3	227.0	265.6	307.2	317.8
72.5°	140.0	143.0	144.5	147.5	149.0	161.2	168.7	188.4	214.9	249.7	261.0
75°	113.5	116.5	117.3	118.8	120.3	125.6	136.2	148.3	170.2	192.9	208.1
77.5°	90.0	89.3	90.8	93.1	92.3	96.8	103.7	114.2	128.6	147.5	157.4
80°	63.6	63.6	65.8	68.1	67.3	71.9	74.1	81.7	93.8	105.9	109.7
82.5°	42.4	42.4	44.6	44.6	46.2	46.9	49.9	53.7	63.6	69.6	71.9
85°	24.2	24.2	25.0	25.0	25.0	26.5	28.8	30.3	33.3	37.1	38.6
87.5°	9.8	10.6	10.6	10.6	10.6	12.1	12.1	13.6	14.4	15.9	15.9
90°	12.9	12.6	12.2	12.0	11.7	11.0	10.4	9.7	9.1	8.2	7.3
92.5°	12.3	12.2	12.1	12.0	11.7	11.0	10.4	9.7	9.1	8.3	7.6
95°	12.0	12.0	12.0	12.0	11.7	11.0	10.4	9.7	9.1	13.9	18.8
97.5°	11.7	11.6	11.5	11.4	11.3	11.0	10.8	10.5	10.3	22.4	34.4
100°	13.0	13.5	14.0	14.3	23.8	42.7	61.6	80.6	99.5	99.0	98.5
102.5°	108.2	118.9	129.6	134.9	134.8	134.5	134.3	134.0	133.8	133.5	133.3
105°	170.1	170.2	170.3	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4
107.5°	207.4	207.9	208.4	208.7	208.6	208.5	208.4	208.2	208.1	207.8	207.6
110°	244.4	244.3	244.2	244.1	244.3	244.7	245.0	245.4	245.8	245.6	245.3

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	279.5	279.7	280.0	280.1	280.4	280.9	281.4	281.9	282.4	282.3	282.1
115°	314.8	315.6	316.3	316.7	317.0	317.5	318.0	318.5	319.0	318.9	318.7
117.5°	350.9	351.2	351.5	351.6	352.0	352.7	353.5	354.2	355.0	354.5	354.0
120°	385.4	386.1	386.7	387.0	387.1	387.4	387.7	387.9	388.2	387.8	387.4
122.5°	417.7	418.5	419.2	419.6	419.7	420.0	420.2	420.5	420.7	420.6	420.5
125°	449.6	449.9	450.3	450.5	450.8	451.3	451.8	452.3	452.8	452.8	452.8
127.5°	477.6	478.7	479.7	480.2	480.3	480.6	480.8	481.1	481.3	481.4	481.6
130°	506.6	507.2	507.9	508.2	508.4	508.8	509.1	509.5	509.9	509.8	509.6
132.5°	534.0	534.7	535.3	535.6	535.6	535.6	535.6	535.6	535.6	536.0	536.4
135°	558.9	559.7	560.4	560.8	560.9	561.2	561.4	561.7	561.9	562.2	562.4
137.5°	584.3	585.0	585.6	585.9	585.9	585.9	585.9	585.9	585.9	586.2	586.4
140°	606.9	607.7	608.4	608.8	608.7	608.4	608.2	607.9	607.7	607.8	607.9
142.5°	628.1	628.8	629.6	630.0	630.0	630.0	630.0	630.0	630.0	629.7	629.5
145°	648.6	649.4	650.1	650.5	650.4	650.3	650.2	650.1	650.0	650.0	650.0
147.5°	666.1	667.0	667.9	668.3	668.2	668.1	668.0	667.8	667.7	667.6	667.4
150°	682.8	683.9	684.9	685.4	685.3	685.0	684.8	684.5	684.3	684.0	683.8
152.5°	698.1	699.0	699.9	700.3	700.2	699.9	699.6	699.4	699.1	698.9	698.6
155°	711.4	712.5	713.5	714.0	713.8	713.4	713.1	712.7	712.3	712.0	711.8
157.5°	722.9	723.9	724.9	725.4	725.2	724.8	724.5	724.1	723.7	723.7	723.7
160°	733.7	734.8	735.8	736.3	736.0	735.5	735.0	734.5	734.0	733.9	733.7
162.5°	743.7	744.9	746.0	746.6	746.2	745.5	744.7	744.0	743.2	743.1	742.9
165°	752.0	753.1	754.1	754.6	754.2	753.5	752.7	752.0	751.2	751.1	750.9
167.5°	758.6	759.7	760.8	761.4	761.0	760.1	759.2	758.3	757.4	757.3	757.2
170°	763.7	764.9	766.0	766.6	766.1	765.1	764.0	763.0	762.0	761.9	761.7
172.5°	767.2	768.3	769.4	770.0	769.6	768.7	767.8	766.9	766.0	765.8	765.5
175°	770.0	771.2	772.3	772.9	772.4	771.4	770.3	769.3	768.3	768.2	768.0
177.5°	771.5	772.5	773.5	774.0	773.6	772.7	771.8	770.9	770.0	769.9	769.8
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	917.0	913.2	908.7	908.7	903.4	901.1	896.6	895.0	891.3	885.2	880.7
5°	949.5	939.7	933.6	928.3	917.0	908.7	900.3	891.3	882.2	871.6	859.5
7.5°	981.3	963.1	954.8	945.7	929.1	911.7	895.0	882.9	870.8	854.2	839.1
10°	1014.6	991.9	976.8	964.6	938.9	917.0	892.8	875.4	856.5	835.3	815.6
12.5°	1042.6	1013.1	1000.2	977.5	948.0	921.5	891.3	864.8	839.8	814.8	790.6
15°	1066.0	1038.0	1006.3	997.2	956.3	918.5	884.4	850.4	819.4	794.4	766.4
17.5°	1073.6	1038.0	1022.1	1000.2	951.8	912.4	869.3	832.2	802.7	765.7	743.7
20°	1075.9	1041.8	1019.9	999.4	956.3	904.1	861.8	816.4	780.8	743.7	708.9
22.5°	1069.8	1029.7	1008.5	988.9	940.4	895.8	846.6	796.7	755.1	721.0	686.2
25°	1058.5	1011.6	991.1	969.9	923.8	874.6	820.9	773.2	734.6	693.8	659.7
27.5°	1043.3	989.6	966.2	944.2	898.8	852.7	802.0	752.8	709.7	666.6	634.8
30°	1024.4	962.4	941.2	912.4	868.6	824.7	778.5	729.3	680.9	640.1	605.3
32.5°	1000.2	935.1	907.1	879.9	832.2	792.1	748.3	702.1	655.2	615.1	578.8
35°	978.3	904.1	873.1	845.9	792.9	750.5	714.2	671.1	629.5	587.9	555.3
37.5°	948.8	873.1	836.0	808.0	754.3	711.2	677.1	643.9	600.0	559.9	529.6
40°	917.7	834.5	799.7	771.7	715.7	668.8	636.3	606.8	571.2	534.1	502.4
42.5°	889.7	797.4	760.4	726.3	669.6	628.0	594.7	572.0	539.4	506.2	477.4
45°	854.2	758.1	718.0	682.4	628.0	582.6	550.8	532.6	508.4	475.9	450.9
47.5°	817.9	715.7	674.1	639.3	580.3	540.2	509.2	491.8	475.1	449.4	424.4
50°	770.2	671.1	633.3	593.2	534.9	494.1	468.3	450.9	438.1	419.9	398.7
52.5°	718.0	624.9	584.1	549.3	491.8	454.7	425.2	415.4	402.5	388.9	370.7
55°	662.8	575.0	535.7	501.6	448.7	410.8	386.6	376.0	366.2	355.6	343.5
57.5°	607.5	522.8	485.7	455.5	406.3	370.0	350.3	335.9	329.1	323.1	313.2
60°	538.7	466.8	438.1	410.8	362.4	329.1	310.2	299.6	293.6	290.5	286.0
62.5°	478.2	419.1	387.4	360.9	322.3	292.8	274.6	266.3	261.0	259.5	254.2
65°	413.9	363.2	338.2	315.5	282.2	255.7	240.6	230.8	227.0	226.2	226.2
67.5°	353.3	312.5	287.5	271.6	242.9	219.4	205.0	201.3	199.0	196.0	195.2
70°	296.6	264.0	242.1	228.5	202.8	185.4	174.0	168.0	168.0	165.7	164.2
72.5°	246.6	214.1	199.7	188.4	167.2	152.1	143.8	142.2	136.9	136.2	136.2
75°	192.9	168.7	158.9	149.0	133.2	122.6	115.8	112.0	108.9	108.9	109.7
77.5°	145.3	128.6	119.5	112.0	100.6	93.8	88.5	87.0	84.0	84.0	84.0
80°	102.9	93.8	87.0	81.0	72.6	66.6	63.6	60.5	60.5	59.8	60.5
82.5°	66.6	59.0	55.2	54.5	46.9	44.6	40.9	41.6	39.3	38.6	40.1
85°	38.6	34.8	30.3	28.8	25.7	22.7	21.2	21.9	21.2	20.4	21.2
87.5°	15.1	12.9	12.1	12.1	9.8	9.1	8.3	9.1	7.6	7.6	8.3
90°	6.4	5.5	5.1	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	6.8	6.1	5.7	6.3	7.4	8.6	9.7	10.9	9.7	8.6	7.4
95°	23.6	28.5	30.9	31.1	31.5	31.8	32.2	32.6	32.2	31.8	31.5
97.5°	46.5	58.6	64.6	64.2	63.5	62.7	62.0	61.2	62.0	62.7	63.5
100°	98.0	97.5	97.2	97.0	96.6	96.3	95.9	95.5	95.9	96.3	96.6
102.5°	133.0	132.7	132.6	132.3	131.8	131.3	130.8	130.3	130.8	131.3	131.8
105°	170.4	170.4	170.4	170.1	169.6	169.1	168.6	168.1	168.6	169.1	169.6
107.5°	207.3	207.0	206.9	206.9	206.9	206.9	206.9	206.9	206.9	206.9	206.9
110°	245.1	244.8	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7	244.7

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	282.0	281.9	281.8	281.6	281.2	280.9	280.5	280.1	280.5	280.9	281.2
115°	318.6	318.5	318.4	318.1	317.5	316.8	316.2	315.6	316.2	316.8	317.5
117.5°	353.5	353.0	352.7	352.7	352.7	352.7	352.7	352.7	352.7	352.7	352.7
120°	387.0	386.6	386.4	386.5	386.6	386.7	386.9	387.0	386.9	386.7	386.6
122.5°	420.4	420.3	420.2	419.9	419.2	418.6	417.9	417.3	417.9	418.6	419.2
125°	452.8	452.8	452.8	452.4	451.5	450.6	449.7	448.8	449.7	450.6	451.5
127.5°	481.7	481.8	481.9	481.6	480.9	480.3	479.6	479.0	479.6	480.3	480.9
130°	509.5	509.4	509.3	509.0	508.4	507.7	507.1	506.5	507.1	507.7	508.4
132.5°	536.8	537.2	537.4	537.0	536.2	535.5	534.7	533.9	534.7	535.5	536.2
135°	562.7	563.0	563.1	562.7	562.0	561.2	560.5	559.7	560.5	561.2	562.0
137.5°	586.7	587.0	587.1	586.7	586.0	585.2	584.5	583.7	584.5	585.2	586.0
140°	608.0	608.1	608.2	608.1	607.8	607.6	607.3	607.1	607.3	607.6	607.8
142.5°	629.2	628.9	628.8	628.7	628.6	628.5	628.4	628.3	628.4	628.5	628.6
145°	650.0	650.0	650.0	649.9	649.6	649.3	649.1	648.8	649.1	649.3	649.6
147.5°	667.3	667.2	667.1	667.1	667.1	667.1	667.1	667.1	667.1	667.1	667.1
150°	683.5	683.2	683.1	683.2	683.5	683.8	684.0	684.3	684.0	683.8	683.5
152.5°	698.4	698.1	698.0	698.3	699.0	699.6	700.3	700.9	700.3	699.6	699.0
155°	711.5	711.2	711.1	711.5	712.3	713.0	713.8	714.6	713.8	713.0	712.3
157.5°	723.7	723.7	723.7	723.9	724.3	724.6	725.0	725.4	725.0	724.6	724.3
160°	733.6	733.5	733.4	733.8	734.6	735.3	736.1	736.9	736.1	735.3	734.6
162.5°	742.8	742.7	742.6	743.0	743.7	744.5	745.2	746.0	745.2	744.5	743.7
165°	750.8	750.7	750.6	751.0	751.7	752.5	753.2	754.0	753.2	752.5	751.7
167.5°	757.1	757.0	756.9	757.3	758.0	758.8	759.5	760.3	759.5	758.8	758.0
170°	761.6	761.5	761.4	761.8	762.7	763.6	764.5	765.4	764.5	763.6	762.7
172.5°	765.3	765.0	764.9	765.3	766.2	767.1	768.0	768.9	768.0	767.1	766.2
175°	767.9	767.8	767.7	768.1	768.9	769.6	770.4	771.2	770.4	769.6	768.9
177.5°	769.7	769.6	769.5	769.9	770.6	771.4	772.1	772.9	772.1	771.4	770.6
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	879.2	877.6	873.9	871.6	864.0	854.9	851.9	844.3	847.4	842.1	842.1
5°	855.7	848.9	844.3	837.5	823.2	813.3	802.7	797.4	794.4	790.6	787.6
7.5°	825.4	820.1	815.6	802.7	786.8	773.2	760.4	755.1	745.2	738.4	735.4
10°	799.0	791.4	780.8	765.7	749.0	731.6	720.3	708.9	701.4	697.6	689.2
12.5°	771.7	762.6	751.3	729.3	711.2	700.6	680.2	669.6	665.8	662.8	652.9
15°	743.7	733.9	720.3	699.8	684.0	659.0	646.9	638.6	629.5	628.7	621.2
17.5°	718.8	706.7	695.3	670.3	650.7	628.7	621.9	612.8	604.5	595.4	591.6
20°	687.0	675.6	667.3	640.1	618.1	604.5	593.2	585.6	580.3	571.2	569.7
22.5°	658.2	646.1	634.8	614.3	595.4	578.0	564.4	556.1	553.8	550.0	543.2
25°	630.2	618.1	604.5	585.6	565.9	553.8	541.7	536.4	531.9	525.8	520.5
27.5°	606.8	595.4	582.6	559.1	542.5	533.4	520.5	514.5	508.4	505.4	503.1
30°	578.8	565.9	556.1	537.9	519.8	507.7	498.6	493.3	488.0	485.0	483.5
32.5°	551.6	539.4	532.6	513.0	498.6	484.2	477.4	473.6	470.6	467.6	464.5
35°	529.6	517.5	506.9	488.8	474.4	464.5	459.2	453.2	450.9	447.9	447.9
37.5°	502.4	493.3	482.7	465.3	452.4	444.9	440.3	432.8	432.0	430.5	428.2
40°	478.9	469.8	460.0	444.9	433.5	424.4	418.4	414.6	412.3	410.8	409.3
42.5°	454.0	444.1	439.6	422.2	412.3	403.3	400.2	396.5	395.7	392.7	388.9
45°	429.7	421.4	412.3	399.5	391.2	383.6	379.0	376.0	372.2	371.5	369.2
47.5°	408.6	398.7	390.4	378.3	369.2	363.2	359.4	355.6	352.6	350.3	348.0
50°	381.3	373.8	366.9	354.1	346.5	340.5	335.2	332.1	329.1	329.1	329.1
52.5°	354.8	348.0	342.0	332.9	323.8	318.5	312.5	310.2	308.7	306.4	308.7
55°	329.1	322.3	316.3	309.4	298.9	294.3	288.3	286.0	286.7	286.7	289.0
57.5°	301.9	296.6	292.8	284.5	274.6	270.1	266.3	264.0	264.0	267.1	267.8
60°	275.4	270.1	263.3	255.7	249.7	244.4	242.1	242.9	242.9	244.4	248.2
62.5°	245.9	242.9	239.1	228.5	224.7	220.9	217.9	220.2	219.4	223.2	228.5
65°	218.7	215.6	210.3	205.0	200.5	196.7	196.0	196.7	198.2	202.0	208.1
67.5°	188.4	188.4	183.9	179.3	175.5	171.7	172.5	173.3	174.8	179.3	188.4
70°	163.4	160.4	155.9	152.8	149.8	148.3	146.8	149.8	154.3	157.4	164.2
72.5°	136.2	133.9	130.1	127.1	126.3	124.8	124.1	125.6	130.1	135.4	143.0
75°	107.4	108.2	105.9	103.7	103.7	101.4	102.9	102.9	107.4	112.7	118.8
77.5°	83.2	82.5	81.7	80.2	79.4	79.4	79.4	81.0	85.5	88.5	94.6
80°	59.0	59.8	57.5	58.3	57.5	58.3	58.3	61.3	63.6	67.3	71.9
82.5°	39.3	39.3	37.8	38.6	38.6	38.6	39.3	40.9	43.9	46.9	49.9
85°	21.9	22.7	21.2	22.7	22.7	22.7	23.5	24.2	26.5	27.2	30.3
87.5°	8.3	9.8	9.8	8.3	9.1	9.8	10.6	9.8	11.3	12.9	13.6
90°	4.6	5.1	5.5	6.4	7.3	8.2	9.1	9.7	10.4	11.0	11.7
92.5°	6.3	5.7	6.1	6.8	7.6	8.3	9.1	9.7	10.4	11.0	11.7
95°	31.1	30.9	28.5	23.6	18.8	13.9	9.1	9.7	10.4	11.0	11.7
97.5°	64.2	64.6	58.6	46.5	34.4	22.4	10.3	10.5	10.8	11.0	11.3
100°	97.0	97.2	97.5	98.0	98.5	99.0	99.5	80.6	61.6	42.7	23.8
102.5°	132.3	132.6	132.7	133.0	133.3	133.5	133.8	134.0	134.3	134.5	134.8
105°	170.1	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4
107.5°	206.9	206.9	207.0	207.3	207.6	207.8	208.1	208.2	208.4	208.5	208.6
110°	244.7	244.7	244.8	245.1	245.3	245.6	245.8	245.4	245.0	244.7	244.3

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	281.6	281.8	281.9	282.0	282.1	282.3	282.4	281.9	281.4	280.9	280.4
115°	318.1	318.4	318.5	318.6	318.7	318.9	319.0	318.5	318.0	317.5	317.0
117.5°	352.7	352.7	353.0	353.5	354.0	354.5	355.0	354.2	353.5	352.7	352.0
120°	386.5	386.4	386.6	387.0	387.4	387.8	388.2	387.9	387.7	387.4	387.1
122.5°	419.9	420.2	420.3	420.4	420.5	420.6	420.7	420.5	420.2	420.0	419.7
125°	452.4	452.8	452.8	452.8	452.8	452.8	452.8	452.3	451.8	451.3	450.8
127.5°	481.6	481.9	481.8	481.7	481.6	481.4	481.3	481.1	480.8	480.6	480.3
130°	509.0	509.3	509.4	509.5	509.6	509.8	509.9	509.5	509.1	508.8	508.4
132.5°	537.0	537.4	537.2	536.8	536.4	536.0	535.6	535.6	535.6	535.6	535.6
135°	562.7	563.1	563.0	562.7	562.4	562.2	561.9	561.7	561.4	561.2	560.9
137.5°	586.7	587.1	587.0	586.7	586.4	586.2	585.9	585.9	585.9	585.9	585.9
140°	608.1	608.2	608.1	608.0	607.9	607.8	607.7	607.9	608.2	608.4	608.7
142.5°	628.7	628.8	628.9	629.2	629.5	629.7	630.0	630.0	630.0	630.0	630.0
145°	649.9	650.0	650.0	650.0	650.0	650.0	650.0	650.1	650.2	650.3	650.4
147.5°	667.1	667.1	667.2	667.3	667.4	667.6	667.7	667.8	668.0	668.1	668.2
150°	683.2	683.1	683.2	683.5	683.8	684.0	684.3	684.5	684.8	685.0	685.3
152.5°	698.3	698.0	698.1	698.4	698.6	698.9	699.1	699.4	699.6	699.9	700.2
155°	711.5	711.1	711.2	711.5	711.8	712.0	712.3	712.7	713.1	713.4	713.8
157.5°	723.9	723.7	723.7	723.7	723.7	723.7	723.7	724.1	724.5	724.8	725.2
160°	733.8	733.4	733.5	733.6	733.7	733.9	734.0	734.5	735.0	735.5	736.0
162.5°	743.0	742.6	742.7	742.8	742.9	743.1	743.2	744.0	744.7	745.5	746.2
165°	751.0	750.6	750.7	750.8	750.9	751.1	751.2	752.0	752.7	753.5	754.2
167.5°	757.3	756.9	757.0	757.1	757.2	757.3	757.4	758.3	759.2	760.1	761.0
170°	761.8	761.4	761.5	761.6	761.7	761.9	762.0	763.0	764.0	765.1	766.1
172.5°	765.3	764.9	765.0	765.3	765.5	765.8	766.0	766.9	767.8	768.7	769.6
175°	768.1	767.7	767.8	767.9	768.0	768.2	768.3	769.3	770.3	771.4	772.4
177.5°	769.9	769.5	769.6	769.7	769.8	769.9	770.0	770.9	771.8	772.7	773.6
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	845.1	839.8	839.1	840.6	837.5	842.1	840.6	842.1	838.3	842.1	839.8
5°	786.8	785.3	782.3	778.5	779.3	780.0	783.8	780.0	783.1	783.8	787.6
7.5°	732.4	729.3	731.6	730.1	723.3	721.8	723.3	725.6	730.1	733.1	735.4
10°	688.5	687.0	684.0	681.7	677.9	675.6	678.7	675.6	681.7	687.0	687.0
12.5°	655.2	649.2	645.4	644.6	636.3	637.8	640.8	643.1	649.9	652.9	652.9
15°	620.4	615.9	614.3	611.3	608.3	611.3	609.8	612.1	615.1	618.1	619.6
17.5°	590.1	589.4	590.1	582.6	584.8	581.1	581.8	585.6	583.3	585.6	590.1
20°	562.9	564.4	562.1	559.1	559.1	554.6	559.9	558.4	559.1	563.7	570.5
22.5°	542.5	541.7	539.4	537.2	534.1	534.9	535.7	534.1	540.2	544.0	544.7
25°	520.5	519.0	518.3	516.0	513.0	516.0	515.2	516.0	517.5	523.6	519.0
27.5°	500.1	497.1	498.6	496.3	495.6	496.3	496.3	497.1	498.6	499.3	500.1
30°	482.7	479.7	478.9	477.4	476.6	477.4	478.9	477.4	483.5	482.7	482.7
32.5°	463.8	461.5	460.0	460.0	459.2	458.5	459.2	460.0	464.5	461.5	464.5
35°	445.6	444.1	444.1	442.6	441.8	441.8	441.8	444.9	443.4	445.6	445.6
37.5°	428.2	428.2	427.5	426.0	425.2	426.0	425.2	426.7	426.0	426.7	427.5
40°	410.1	408.6	407.8	407.8	405.5	403.3	405.5	405.5	406.3	408.6	409.3
42.5°	388.1	388.9	388.9	385.9	385.9	385.9	386.6	387.4	387.4	388.9	388.9
45°	369.2	367.7	367.7	367.7	366.2	366.9	368.5	368.5	368.5	368.5	366.9
47.5°	348.0	348.0	348.8	348.8	351.1	350.3	350.3	349.5	348.0	348.0	348.8
50°	328.4	330.6	331.4	331.4	332.1	332.9	332.9	331.4	330.6	328.4	328.4
52.5°	309.4	311.0	312.5	314.7	316.3	315.5	315.5	314.0	311.0	310.2	309.4
55°	289.0	291.3	294.3	296.6	298.9	299.6	299.6	296.6	293.6	289.8	289.8
57.5°	270.1	272.4	277.7	279.9	283.0	283.0	281.4	279.2	274.6	271.6	269.3
60°	251.2	255.0	258.8	263.3	267.1	267.8	265.6	262.5	257.2	253.5	250.4
62.5°	230.8	234.5	242.1	246.6	249.7	249.7	249.7	245.9	239.1	233.8	229.2
65°	211.1	214.9	221.7	227.7	230.0	232.3	230.0	226.2	220.9	214.9	210.3
67.5°	190.7	195.2	202.0	206.5	209.6	211.8	210.3	207.3	200.5	192.2	189.1
70°	168.0	170.2	180.1	184.6	189.1	190.7	189.1	184.6	177.8	168.7	165.7
72.5°	146.8	149.0	158.1	161.9	165.7	167.2	164.9	161.9	155.9	147.5	143.8
75°	122.6	126.3	130.9	136.9	141.5	143.0	140.7	138.5	130.9	125.6	122.6
77.5°	96.8	100.6	106.7	112.0	116.5	115.8	112.7	113.5	105.2	99.1	96.8
80°	73.4	76.4	81.0	85.5	87.8	87.8	87.0	84.0	81.0	76.4	72.6
82.5°	50.7	54.5	58.3	61.3	61.3	62.0	60.5	59.8	56.7	53.0	52.2
85°	30.3	31.0	34.0	34.0	37.1	35.6	34.8	37.1	34.0	31.8	31.0
87.5°	13.6	12.9	13.6	13.6	12.9	14.4	14.4	13.6	14.4	13.6	13.6
90°	12.0	12.2	12.6	12.9	13.3	13.7	13.3	12.9	12.6	12.2	12.0
92.5°	12.0	12.1	12.2	12.3	12.5	12.6	12.5	12.3	12.2	12.1	12.0
95°	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0	12.0
97.5°	11.4	11.5	11.6	11.7	11.9	12.0	11.9	11.7	11.6	11.5	11.4
100°	14.3	14.0	13.5	13.0	12.5	12.0	12.5	13.0	13.5	14.0	14.3
102.5°	134.9	129.6	118.9	108.2	97.6	86.9	97.6	108.2	118.9	129.6	134.9
105°	170.4	170.3	170.2	170.1	169.9	169.8	169.9	170.1	170.2	170.3	170.4
107.5°	208.7	208.4	207.9	207.4	206.9	206.4	206.9	207.4	207.9	208.4	208.7
110°	244.1	244.2	244.3	244.4	244.6	244.7	244.6	244.4	244.3	244.2	244.1

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	280.1	280.0	279.7	279.5	279.2	279.0	279.2	279.5	279.7	280.0	280.1
115°	316.7	316.3	315.6	314.8	314.1	313.3	314.1	314.8	315.6	316.3	316.7
117.5°	351.6	351.5	351.2	350.9	350.7	350.4	350.7	350.9	351.2	351.5	351.6
120°	387.0	386.7	386.1	385.4	384.8	384.2	384.8	385.4	386.1	386.7	387.0
122.5°	419.6	419.2	418.5	417.7	417.0	416.2	417.0	417.7	418.5	419.2	419.6
125°	450.5	450.3	449.9	449.6	449.2	448.8	449.2	449.6	449.9	450.3	450.5
127.5°	480.2	479.7	478.7	477.6	476.6	475.6	476.6	477.6	478.7	479.7	480.2
130°	508.2	507.9	507.2	506.6	505.9	505.3	505.9	506.6	507.2	507.9	508.2
132.5°	535.6	535.3	534.7	534.0	533.4	532.8	533.4	534.0	534.7	535.3	535.6
135°	560.8	560.4	559.7	558.9	558.2	557.4	558.2	558.9	559.7	560.4	560.8
137.5°	585.9	585.6	585.0	584.3	583.7	583.1	583.7	584.3	585.0	585.6	585.9
140°	608.8	608.4	607.7	606.9	606.2	605.4	606.2	606.9	607.7	608.4	608.8
142.5°	630.0	629.6	628.8	628.1	627.3	626.5	627.3	628.1	628.8	629.6	630.0
145°	650.5	650.1	649.4	648.6	647.9	647.1	647.9	648.6	649.4	650.1	650.5
147.5°	668.3	667.9	667.0	666.1	665.2	664.3	665.2	666.1	667.0	667.9	668.3
150°	685.4	684.9	683.9	682.8	681.8	680.8	681.8	682.8	683.9	684.9	685.4
152.5°	700.3	699.9	699.0	698.1	697.2	696.3	697.2	698.1	699.0	699.9	700.3
155°	714.0	713.5	712.5	711.4	710.4	709.4	710.4	711.4	712.5	713.5	714.0
157.5°	725.4	724.9	723.9	722.9	721.9	720.9	721.9	722.9	723.9	724.9	725.4
160°	736.3	735.8	734.8	733.7	732.7	731.7	732.7	733.7	734.8	735.8	736.3
162.5°	746.6	746.0	744.9	743.7	742.6	741.4	742.6	743.7	744.9	746.0	746.6
165°	754.6	754.1	753.1	752.0	751.0	750.0	751.0	752.0	753.1	754.1	754.6
167.5°	761.4	760.8	759.7	758.6	757.4	756.3	757.4	758.6	759.7	760.8	761.4
170°	766.6	766.0	764.9	763.7	762.6	761.4	762.6	763.7	764.9	766.0	766.6
172.5°	770.0	769.4	768.3	767.2	766.0	764.9	766.0	767.2	768.3	769.4	770.0
175°	772.9	772.3	771.2	770.0	768.9	767.7	768.9	770.0	771.2	772.3	772.9
177.5°	774.0	773.5	772.5	771.5	770.5	769.5	770.5	771.5	772.5	773.5	774.0
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	846.6	842.1	847.4	840.6	842.1	850.4	849.6	857.2	861.8	861.0	864.8
5°	790.6	790.6	792.9	792.1	799.7	806.5	815.6	823.2	831.5	836.0	841.3
7.5°	735.4	743.0	744.5	748.3	757.3	768.7	777.8	789.1	801.2	809.5	815.6
10°	690.0	696.1	702.1	705.1	715.0	730.1	743.0	761.1	776.3	785.3	793.7
12.5°	649.9	656.7	659.7	673.4	680.2	690.0	708.2	727.8	744.5	754.3	761.1
15°	621.2	624.9	631.7	640.1	646.9	659.0	674.1	696.1	711.9	720.3	743.7
17.5°	596.9	601.5	605.3	609.1	619.6	632.5	646.9	665.8	686.2	700.6	712.7
20°	572.0	574.2	578.8	584.8	592.4	604.5	617.4	637.0	655.2	666.6	682.4
22.5°	542.5	549.3	553.8	558.4	566.7	580.3	592.4	606.8	629.5	642.3	659.0
25°	525.1	528.1	531.1	536.4	542.5	554.6	568.2	583.3	601.5	615.1	629.5
27.5°	502.4	506.9	510.7	517.5	521.3	531.1	544.0	559.1	581.1	592.4	604.5
30°	483.5	488.0	491.0	494.1	499.3	509.9	522.0	534.1	554.6	569.0	581.1
32.5°	464.5	469.1	472.9	475.1	480.4	487.2	497.1	512.2	529.6	539.4	555.3
35°	447.9	447.9	452.4	455.5	460.0	466.1	475.1	486.5	504.6	517.5	531.9
37.5°	429.0	429.7	433.5	435.8	440.3	446.4	455.5	466.1	481.2	491.0	505.4
40°	409.3	411.6	413.1	416.9	422.2	424.4	433.5	445.6	460.8	469.8	481.9
42.5°	389.6	391.2	394.9	398.0	402.5	406.3	412.3	423.7	435.0	448.7	458.5
45°	367.7	371.5	373.8	379.0	381.3	385.1	391.2	400.2	413.9	422.2	433.5
47.5°	348.8	350.3	351.8	358.6	363.2	365.4	371.5	376.8	391.2	398.7	409.3
50°	328.4	328.4	330.6	333.7	339.0	343.5	348.8	354.8	366.2	373.8	384.3
52.5°	309.4	307.2	308.7	310.2	315.5	320.0	325.3	333.7	344.2	348.8	357.9
55°	289.0	285.2	287.5	289.8	291.3	297.3	303.4	308.7	317.0	323.8	332.1
57.5°	267.1	266.3	264.8	265.6	269.3	273.1	277.7	284.5	294.3	299.6	304.1
60°	247.4	242.9	241.4	242.9	245.1	247.4	253.5	259.5	267.8	273.1	278.4
62.5°	227.0	222.4	219.4	217.1	219.4	224.7	228.5	233.0	239.8	245.9	250.4
65°	207.3	200.5	197.5	196.0	195.2	199.0	202.0	208.1	214.1	216.4	221.7
67.5°	185.4	179.3	175.5	173.3	173.3	173.3	176.3	182.3	188.4	189.1	194.4
70°	163.4	156.6	152.8	149.8	148.3	149.8	153.6	154.3	159.6	161.2	164.2
72.5°	140.0	133.9	129.4	125.6	126.3	127.9	127.9	129.4	132.4	136.2	136.2
75°	118.0	109.7	107.4	104.4	102.9	102.9	102.9	105.9	108.2	111.2	110.5
77.5°	93.1	88.5	84.0	82.5	80.2	79.4	81.0	81.0	82.5	84.7	85.5
80°	71.9	66.6	63.6	62.0	59.0	58.3	59.0	59.0	61.3	60.5	61.3
82.5°	49.9	46.2	43.9	41.6	40.1	40.9	40.1	40.1	40.9	40.1	40.1
85°	28.8	28.0	26.5	25.7	25.0	23.5	25.0	24.2	23.5	22.7	24.2
87.5°	13.6	12.9	12.9	11.3	11.3	10.6	11.3	11.3	10.6	10.6	10.6
90°	11.7	11.0	10.4	9.7	9.1	8.2	7.3	6.4	5.5	5.1	4.6
92.5°	11.7	11.0	10.4	9.7	9.1	8.3	7.6	6.8	6.1	5.7	6.3
95°	11.7	11.0	10.4	9.7	9.1	13.9	18.8	23.6	28.5	30.9	31.1
97.5°	11.3	11.0	10.8	10.5	10.3	22.4	34.4	46.5	58.6	64.6	64.2
100°	23.8	42.7	61.6	80.6	99.5	99.0	98.5	98.0	97.5	97.2	97.0
102.5°	134.8	134.5	134.3	134.0	133.8	133.5	133.3	133.0	132.7	132.6	132.3
105°	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.4	170.1
107.5°	208.6	208.5	208.4	208.2	208.1	207.8	207.6	207.3	207.0	206.9	206.9
110°	244.3	244.7	245.0	245.4	245.8	245.6	245.3	245.1	244.8	244.7	244.7

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	280.4	280.9	281.4	281.9	282.4	282.3	282.1	282.0	281.9	281.8	281.6
115°	317.0	317.5	318.0	318.5	319.0	318.9	318.7	318.6	318.5	318.4	318.1
117.5°	352.0	352.7	353.5	354.2	355.0	354.5	354.0	353.5	353.0	352.7	352.7
120°	387.1	387.4	387.7	387.9	388.2	387.8	387.4	387.0	386.6	386.4	386.5
122.5°	419.7	420.0	420.2	420.5	420.7	420.6	420.5	420.4	420.3	420.2	419.9
125°	450.8	451.3	451.8	452.3	452.8	452.8	452.8	452.8	452.8	452.8	452.4
127.5°	480.3	480.6	480.8	481.1	481.3	481.4	481.6	481.7	481.8	481.9	481.6
130°	508.4	508.8	509.1	509.5	509.9	509.8	509.6	509.5	509.4	509.3	509.0
132.5°	535.6	535.6	535.6	535.6	535.6	536.0	536.4	536.8	537.2	537.4	537.0
135°	560.9	561.2	561.4	561.7	561.9	562.2	562.4	562.7	563.0	563.1	562.7
137.5°	585.9	585.9	585.9	585.9	585.9	586.2	586.4	586.7	587.0	587.1	586.7
140°	608.7	608.4	608.2	607.9	607.7	607.8	607.9	608.0	608.1	608.2	608.1
142.5°	630.0	630.0	630.0	630.0	630.0	629.7	629.5	629.2	628.9	628.8	628.7
145°	650.4	650.3	650.2	650.1	650.0	650.0	650.0	650.0	650.0	650.0	649.9
147.5°	668.2	668.1	668.0	667.8	667.7	667.6	667.4	667.3	667.2	667.1	667.1
150°	685.3	685.0	684.8	684.5	684.3	684.0	683.8	683.5	683.2	683.1	683.2
152.5°	700.2	699.9	699.6	699.4	699.1	698.9	698.6	698.4	698.1	698.0	698.3
155°	713.8	713.4	713.1	712.7	712.3	712.0	711.8	711.5	711.2	711.1	711.5
157.5°	725.2	724.8	724.5	724.1	723.7	723.7	723.7	723.7	723.7	723.7	723.9
160°	736.0	735.5	735.0	734.5	734.0	733.9	733.7	733.6	733.5	733.4	733.8
162.5°	746.2	745.5	744.7	744.0	743.2	743.1	742.9	742.8	742.7	742.6	743.0
165°	754.2	753.5	752.7	752.0	751.2	751.1	750.9	750.8	750.7	750.6	751.0
167.5°	761.0	760.1	759.2	758.3	757.4	757.3	757.2	757.1	757.0	756.9	757.3
170°	766.1	765.1	764.0	763.0	762.0	761.9	761.7	761.6	761.5	761.4	761.8
172.5°	769.6	768.7	767.8	766.9	766.0	765.8	765.5	765.3	765.0	764.9	765.3
175°	772.4	771.4	770.3	769.3	768.3	768.2	768.0	767.9	767.8	767.7	768.1
177.5°	773.6	772.7	771.8	770.9	770.0	769.9	769.8	769.7	769.6	769.5	769.9
180°	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2	771.2

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	891.3	891.3	891.3	891.3
2.5°	870.1	877.6	882.9	892.8
5°	850.4	864.0	876.9	890.5
7.5°	830.7	846.6	867.0	884.4
10°	808.8	829.2	853.4	876.9
12.5°	786.8	811.1	837.5	868.6
15°	760.4	791.4	822.4	855.7
17.5°	736.9	768.7	802.0	843.6
20°	710.4	745.2	781.6	823.9
22.5°	687.0	725.6	763.4	808.0
25°	660.5	698.3	739.9	787.6
27.5°	638.6	673.4	714.2	765.7
30°	612.1	649.9	690.8	742.2
32.5°	587.1	623.4	666.6	717.2
35°	561.4	598.5	637.0	685.5
37.5°	537.2	569.0	607.5	653.7
40°	509.9	544.7	579.5	615.9
42.5°	485.0	516.7	549.3	578.0
45°	457.0	484.2	515.2	538.7
47.5°	431.3	455.5	479.7	497.8
50°	405.5	424.4	442.6	458.5
52.5°	375.3	396.5	406.3	416.1
55°	348.0	360.1	369.2	379.0
57.5°	321.5	326.8	331.4	340.5
60°	286.7	292.8	298.1	304.9
62.5°	256.5	259.5	261.0	267.8
65°	227.7	227.0	230.8	234.5
67.5°	196.7	196.0	199.7	201.3
70°	166.4	165.7	166.4	170.2
72.5°	137.7	137.7	138.5	140.0
75°	111.2	111.2	112.0	113.5
77.5°	84.0	85.5	84.7	87.8
80°	61.3	59.8	61.3	62.8
82.5°	40.1	41.6	41.6	40.1
85°	22.7	22.7	22.7	22.7
87.5°	9.8	9.8	10.6	11.3
90°	3.6	2.6	1.6	0.6
92.5°	7.4	8.6	9.7	10.9
95°	31.5	31.8	32.2	32.6
97.5°	63.5	62.7	62.0	61.2
100°	96.6	96.3	95.9	95.5
102.5°	131.8	131.3	130.8	130.3
105°	169.6	169.1	168.6	168.1
107.5°	206.9	206.9	206.9	206.9
110°	244.7	244.7	244.7	244.7

TEST NUMBER: P1028114

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	281.2	280.9	280.5	280.1
115°	317.5	316.8	316.2	315.6
117.5°	352.7	352.7	352.7	352.7
120°	386.6	386.7	386.9	387.0
122.5°	419.2	418.6	417.9	417.3
125°	451.5	450.6	449.7	448.8
127.5°	480.9	480.3	479.6	479.0
130°	508.4	507.7	507.1	506.5
132.5°	536.2	535.5	534.7	533.9
135°	562.0	561.2	560.5	559.7
137.5°	586.0	585.2	584.5	583.7
140°	607.8	607.6	607.3	607.1
142.5°	628.6	628.5	628.4	628.3
145°	649.6	649.3	649.1	648.8
147.5°	667.1	667.1	667.1	667.1
150°	683.5	683.8	684.0	684.3
152.5°	699.0	699.6	700.3	700.9
155°	712.3	713.0	713.8	714.6
157.5°	724.3	724.6	725.0	725.4
160°	734.6	735.3	736.1	736.9
162.5°	743.7	744.5	745.2	746.0
165°	751.7	752.5	753.2	754.0
167.5°	758.0	758.8	759.5	760.3
170°	762.7	763.6	764.5	765.4
172.5°	766.2	767.1	768.0	768.9
175°	768.9	769.6	770.4	771.2
177.5°	770.6	771.4	772.1	772.9
180°	771.2	771.2	771.2	771.2

(END OF REPORT)