

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028116

Luminaire Tested: S125DIP-B610D610UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028116
REPORT IS A COMBINATION OF REPORTS P1002325 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D610UB30-4F0-XX-W2A-A4
Description: Define 5 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4646.0 lumens
Efficiency: N/A
Efficacy: 117.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	72	72	72	60	60	60
1	99	95	91	87	92	88	85	82	76	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	67	66	62	59	56	54	51	47	45	43
3	83	73	66	60	76	68	62	57	59	54	50	50	46	43	42	39	37
4	76	65	57	51	70	61	54	48	52	47	43	45	41	37	38	35	32
5	69	58	50	44	64	54	47	41	47	41	37	40	36	32	34	31	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25
7	59	47	39	33	55	44	37	32	38	33	28	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	31	26	47	37	30	25	32	27	23	28	23	20	24	20	18
10	48	36	28	24	44	34	27	23	30	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5711	5711	5711	5711
5°	5715	6478	5720	4914
10°	5680	7383	5670	4218
15°	5638	8006	5603	3812
20°	5567	8773	5516	3480
25°	5504	10052	5403	3283
30°	5413	10604	5319	3105
35°	5269	8501	5159	2962
40°	5045	5875	4971	2811
45°	4762	4374	4708	2685
50°	4438	3601	4364	2585
55°	4088	3072	4055	2497
60°	3745	2629	3680	2430
65°	3374	2270	3321	2331
70°	2983	1884	2945	2160
75°	2570	1458	2536	1874
80°	2029	986	1955	1378
85°	1298	494	1252	703

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8722 cd/sqm

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.8
10°-20°	255.5	5.5
20°-30°	415.0	8.9
30°-40°	507.2	10.9
40°-50°	460.1	9.9
50°-60°	366.5	7.9
60°-70°	255.2	5.5
70°-80°	136.0	2.9
80°-90°	34.8	0.7
90°-100°	206.3	4.4
100°-110°	444.8	9.6
110°-120°	414.7	8.9
120°-130°	335.9	7.2
130°-140°	269.7	5.8
140°-150°	203.4	4.4
150°-160°	143.2	3.1
160°-170°	84.4	1.8
170°-180°	27.5	0.6
0°-30°	756.3	16.3
0°-40°	1263.5	27.2
0°-60°	2090.1	45.0
0°-90°	2516.1	54.2
90°-120°	1065.8	22.9
90°-150°	1874.8	40.4
90°-180°	2130.0	45.8
0°-180°	4646.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	891	891	891	891	891	
5°	890	1028	891	780	890	85
15°	856	1284	850	611	856	241
25°	788	1580	773	516	788	363
35°	686	1268	671	442	686	428
45°	539	598	533	367	539	415
55°	379	368	376	300	379	339
65°	234	226	231	232	234	233
75°	114	111	112	143	114	121
85°	23	25	22	36	23	27
90°	1	13	1	13	1	3
95°	19	134	19	134	19	20
105°	65	758	65	758	65	68
115°	116	844	116	844	116	114
125°	160	665	160	665	160	142
135°	188	552	188	552	188	146
145°	218	436	218	436	218	137
155°	249	365	249	365	249	115
165°	272	320	272	320	272	77
175°	283	288	283	288	283	27
180°	284	284	284	284	284	

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	892.8	898.1	904.1	908.7	916.2	918.5	922.3	924.5	926.8	929.1	930.6
5°	890.5	903.4	914.7	923.0	937.4	942.7	949.5	957.8	967.7	976.0	981.3
7.5°	884.4	904.9	920.0	936.7	956.3	969.2	976.0	993.4	1009.3	1021.4	1037.3
10°	876.9	901.1	924.5	949.5	977.5	991.9	1005.5	1029.7	1051.7	1071.3	1087.2
12.5°	868.6	898.1	926.1	958.6	996.4	1013.8	1022.9	1064.5	1091.8	1102.3	1133.4
15°	855.7	890.5	930.6	970.7	1002.5	1022.9	1047.9	1081.2	1108.4	1131.9	1156.8
17.5°	843.6	881.4	922.3	966.9	1013.1	1039.5	1058.5	1088.0	1117.5	1147.7	1171.2
20°	823.9	873.1	914.7	962.4	1016.9	1035.8	1055.4	1090.2	1122.0	1154.5	1184.1
22.5°	808.0	854.9	911.7	957.1	1003.2	1022.1	1046.4	1082.7	1120.5	1157.6	1200.7
25°	787.6	839.8	889.0	937.4	985.1	1005.5	1027.4	1074.4	1113.7	1161.4	1209.0
27.5°	765.7	819.4	868.6	912.4	957.1	985.1	1008.5	1057.7	1109.9	1162.1	1224.2
30°	742.2	792.9	839.8	882.9	932.1	960.9	984.3	1041.8	1100.1	1166.7	1240.8
32.5°	717.2	764.9	805.0	848.9	901.1	927.6	959.4	1022.1	1091.0	1170.4	1263.5
35°	685.5	730.9	766.4	811.1	863.3	897.3	930.6	1001.0	1081.2	1169.7	1276.4
37.5°	653.7	689.2	723.3	771.0	831.5	862.5	897.3	974.5	1066.0	1167.4	1281.7
40°	615.9	650.7	680.2	728.6	792.1	827.7	864.0	945.0	1048.6	1159.1	1262.7
42.5°	578.0	607.5	640.1	690.8	752.0	789.9	828.5	918.5	1025.9	1134.9	1210.5
45°	538.7	561.4	596.9	643.1	708.2	744.5	788.4	886.0	994.2	1091.0	1128.8
47.5°	497.8	520.5	553.8	598.5	662.8	705.9	747.5	845.1	954.1	1029.0	1029.0
50°	458.5	476.6	509.2	553.8	618.9	658.2	700.6	804.3	892.0	947.2	898.1
52.5°	416.1	436.5	463.8	510.7	575.0	610.6	656.7	745.2	828.5	851.2	775.5
55°	379.0	395.7	421.4	466.1	525.8	562.9	602.2	687.0	757.3	755.8	674.9
57.5°	340.5	354.1	381.3	422.2	477.4	510.7	550.0	623.4	680.9	660.5	584.1
60°	304.9	314.7	341.2	374.5	427.5	458.5	496.3	556.1	600.0	571.2	494.1
62.5°	267.8	279.2	300.4	332.9	379.8	404.8	432.8	493.3	521.3	495.6	416.9
65°	234.5	243.6	262.5	289.8	332.1	354.8	379.0	429.0	455.5	418.4	353.3
67.5°	201.3	211.8	225.5	249.7	283.0	304.1	325.3	368.5	380.6	347.3	292.8
70°	170.2	179.3	192.2	209.6	237.6	256.5	272.4	307.9	316.3	285.2	242.1
72.5°	140.0	146.0	156.6	171.0	196.7	207.3	223.9	248.2	258.8	230.8	199.7
75°	113.5	118.0	124.8	135.4	152.8	164.2	177.8	200.5	199.7	180.1	158.1
77.5°	87.8	88.5	96.1	105.9	116.5	126.3	133.2	149.0	150.6	138.5	120.3
80°	62.8	65.1	68.1	75.7	84.7	88.5	96.8	106.7	108.2	99.1	87.0
82.5°	40.1	41.6	43.9	48.4	54.5	59.0	63.6	67.3	71.1	65.8	56.0
85°	22.7	23.5	25.7	27.2	30.3	32.5	36.3	40.1	39.3	35.6	32.5
87.5°	11.3	11.3	11.3	12.9	14.4	14.4	15.9	16.6	17.4	15.9	14.4
90°	0.6	1.1	2.3	3.4	4.6	5.2	5.7	6.3	7.4	8.0	9.1
92.5°	8.6	10.3	16.0	24.6	36.6	46.9	57.2	96.0	161.2	232.1	228.1
95°	18.9	19.4	24.0	30.3	42.9	55.8	68.6	129.8	255.6	413.3	506.5
97.5°	29.2	29.7	33.2	39.4	50.9	60.3	69.7	112.1	208.7	379.0	547.1
100°	40.0	41.2	43.4	49.7	60.6	69.2	77.8	110.9	185.2	329.3	516.3
102.5°	52.0	52.6	54.3	61.2	70.9	79.2	87.5	116.1	175.5	291.6	461.9
105°	64.6	64.6	67.5	73.2	82.3	90.3	98.3	123.5	174.4	269.8	414.5
107.5°	76.6	77.8	80.6	85.2	94.9	102.1	109.2	133.8	178.4	258.4	379.0
110°	89.8	90.9	93.2	98.3	106.9	114.4	121.8	145.2	184.7	253.8	355.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	102.9	104.1	105.8	110.9	119.5	126.6	133.8	156.1	192.7	253.8	341.9
115°	115.5	116.6	118.3	123.5	132.1	139.2	146.4	167.5	200.7	255.6	332.7
117.5°	126.9	128.6	130.3	135.5	145.2	152.0	158.9	178.9	209.8	258.4	327.6
120°	138.4	140.1	142.4	147.5	157.2	164.4	171.5	191.5	219.0	263.0	324.2
122.5°	150.4	151.5	153.2	158.4	169.2	176.4	183.5	203.5	229.3	267.0	321.3
125°	160.1	161.2	164.1	169.2	180.1	187.6	195.0	213.8	238.4	271.6	319.0
127.5°	168.1	169.8	173.2	179.5	191.0	198.4	205.8	224.1	247.0	276.7	317.9
130°	175.5	177.2	181.8	189.2	201.2	208.6	216.1	233.8	255.6	281.3	316.7
132.5°	181.2	183.5	189.2	197.8	210.4	217.8	225.3	243.0	263.0	286.4	316.7
135°	187.5	189.8	196.7	205.8	217.8	225.6	233.3	251.0	269.8	291.0	316.7
137.5°	195.5	197.2	203.5	212.7	224.7	232.7	240.7	256.7	275.0	295.6	317.3
140°	202.4	204.1	211.0	220.1	231.0	238.7	246.4	263.0	280.1	298.4	317.9
142.5°	210.4	211.5	217.8	227.0	237.3	244.4	251.6	267.0	283.0	300.1	318.4
145°	218.4	219.5	225.3	233.3	243.5	250.1	256.7	271.6	285.9	301.3	317.9
147.5°	227.0	227.5	232.7	240.1	249.3	255.3	261.3	274.4	287.6	301.9	316.7
150°	234.4	235.5	239.5	247.0	255.0	259.8	264.7	277.3	289.3	301.9	315.0
152.5°	242.4	243.0	246.4	252.7	260.1	264.4	268.7	280.1	290.4	301.3	312.7
155°	249.3	249.3	252.7	258.4	264.1	268.1	272.1	281.9	291.0	300.1	309.9
157.5°	255.6	255.6	258.4	263.6	268.7	271.8	275.0	283.6	291.6	299.0	307.0
160°	261.8	261.3	263.6	267.6	272.1	274.7	277.3	284.7	291.6	297.3	304.1
162.5°	267.0	266.4	268.7	272.1	275.6	277.6	279.6	285.9	291.0	295.6	300.7
165°	272.1	271.0	272.7	275.6	277.9	279.6	281.3	285.9	290.4	293.9	297.3
167.5°	275.6	275.0	276.1	277.9	279.6	280.8	281.9	285.9	289.3	291.0	293.9
170°	279.0	278.4	279.0	280.1	281.3	282.2	283.0	285.9	288.1	289.3	291.0
172.5°	281.3	280.1	280.7	281.9	282.4	282.7	283.0	285.3	287.0	287.0	287.6
175°	283.0	281.9	282.4	283.0	283.0	283.0	283.0	284.7	285.9	285.3	285.3
177.5°	284.1	283.0	283.0	283.6	283.0	283.0	283.0	284.1	284.7	283.6	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	932.1	937.4	941.9	945.7	948.8	953.3	950.3	951.0	952.5	955.6	955.6
5°	992.6	1001.0	1005.5	1020.6	1024.4	1023.7	1021.4	1033.5	1032.7	1028.2	1027.4
7.5°	1051.7	1066.0	1078.9	1091.0	1094.8	1104.6	1106.9	1112.2	1110.7	1118.2	1114.5
10°	1105.4	1128.1	1140.2	1158.3	1162.9	1167.4	1173.5	1176.5	1183.3	1182.5	1182.5
12.5°	1147.0	1174.2	1190.1	1194.6	1212.0	1217.3	1222.6	1232.5	1230.2	1231.0	1235.5
15°	1179.5	1206.0	1219.6	1240.8	1252.9	1259.0	1268.0	1278.6	1277.1	1283.9	1282.4
17.5°	1203.7	1228.7	1253.7	1285.4	1286.2	1302.1	1323.3	1327.8	1337.6	1330.8	1330.8
20°	1223.4	1256.7	1292.2	1333.1	1337.6	1347.5	1373.2	1390.6	1402.0	1398.2	1400.4
22.5°	1244.6	1292.2	1333.9	1374.7	1396.7	1414.1	1439.0	1466.3	1476.1	1482.2	1480.6
25°	1271.8	1321.8	1383.0	1439.8	1462.5	1495.8	1529.1	1555.5	1563.1	1579.8	1564.6
27.5°	1299.8	1370.2	1446.6	1513.2	1541.9	1569.2	1609.3	1628.9	1638.8	1646.3	1641.0
30°	1323.3	1420.1	1503.3	1564.6	1585.0	1600.9	1623.6	1628.2	1624.4	1630.4	1638.0
32.5°	1359.6	1454.2	1524.5	1554.0	1551.8	1551.0	1533.6	1509.4	1504.1	1489.7	1509.4
35°	1379.3	1454.9	1482.2	1442.8	1426.9	1398.2	1342.9	1306.6	1274.8	1268.0	1269.6
37.5°	1367.9	1397.4	1364.9	1261.2	1235.5	1191.6	1118.2	1066.8	1043.3	1025.2	1048.6
40°	1306.6	1274.1	1184.8	1058.5	1021.4	979.8	910.9	882.9	849.6	842.8	873.9
42.5°	1205.2	1106.1	979.8	882.2	843.6	820.1	762.6	736.2	712.7	702.1	719.5
45°	1067.5	947.2	820.1	739.9	707.4	679.4	645.4	617.4	602.2	597.7	612.1
47.5°	925.3	798.2	696.8	637.0	603.0	581.8	550.0	534.1	522.0	523.6	525.8
50°	789.1	673.4	595.4	535.7	519.0	502.4	481.2	467.6	461.5	463.8	462.3
52.5°	671.8	578.0	512.2	466.1	458.5	442.6	425.2	413.9	411.6	412.3	414.6
55°	569.0	495.6	443.4	410.1	401.7	390.4	379.8	372.2	366.2	368.5	367.7
57.5°	491.0	426.7	386.6	359.4	353.3	346.5	336.7	332.9	330.6	326.1	329.9
60°	422.2	370.0	335.2	318.5	313.2	308.7	298.1	293.6	292.0	289.8	295.8
62.5°	357.1	320.0	293.6	278.4	273.1	268.6	263.3	259.5	260.3	257.2	260.3
65°	305.7	275.4	256.5	242.9	236.1	233.0	232.3	226.2	225.5	226.2	227.0
67.5°	258.0	232.3	217.9	209.6	204.3	201.3	199.0	195.2	198.2	196.0	197.5
70°	214.9	197.5	182.3	174.0	171.7	172.5	168.7	167.2	168.0	166.4	168.0
72.5°	173.3	158.9	152.8	146.8	143.8	143.0	140.7	138.5	140.7	140.0	140.0
75°	138.5	127.9	121.1	117.3	117.3	115.8	112.0	112.0	112.0	111.2	112.0
77.5°	106.7	97.6	94.6	90.8	90.8	88.5	87.8	87.8	86.3	88.5	87.0
80°	79.4	72.6	68.1	65.8	65.8	65.1	63.6	62.8	63.6	62.8	62.8
82.5°	51.4	48.4	46.2	43.9	43.1	43.9	43.1	41.6	42.4	41.6	43.1
85°	29.5	26.5	26.5	25.0	25.7	24.2	25.0	23.5	22.7	25.0	23.5
87.5°	12.9	12.1	12.1	10.6	10.6	10.6	9.8	10.6	9.8	9.1	9.8
90°	9.7	10.3	10.9	11.4	12.0	12.6	12.6	12.6	13.1	13.1	13.1
92.5°	184.1	124.1	89.2	66.3	60.9	55.5	46.3	44.6	43.4	42.3	43.4
95°	495.7	411.1	324.2	253.8	229.8	205.8	165.2	148.1	143.5	134.4	143.5
97.5°	619.2	589.4	520.3	449.4	415.1	380.8	346.5	316.7	301.3	294.4	301.3
100°	659.2	703.2	675.2	616.3	586.6	556.8	517.4	476.2	455.1	445.9	455.1
102.5°	635.2	741.5	770.1	749.5	731.8	714.1	671.2	644.9	621.4	615.2	621.4
105°	578.6	715.8	794.1	819.3	816.2	813.0	794.7	775.8	764.4	757.5	764.4
107.5°	524.8	663.2	766.7	827.3	839.8	852.4	857.6	854.7	849.0	843.3	849.0
110°	480.2	603.7	712.3	793.0	817.3	841.6	867.3	878.1	882.1	882.1	882.1

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	447.1	556.8	658.6	740.4	770.1	799.8	840.4	861.0	872.4	877.6	872.4
115°	424.8	519.1	607.7	686.1	717.2	748.4	793.0	820.4	836.4	843.8	836.4
117.5°	409.9	492.8	571.1	639.7	669.2	698.6	743.8	772.4	788.4	793.0	788.4
120°	397.9	472.2	540.8	603.7	628.8	654.0	696.3	723.8	739.2	743.8	739.2
122.5°	387.6	456.8	519.1	573.4	596.6	619.7	656.3	680.9	696.3	700.3	696.3
125°	378.5	441.9	500.2	550.0	570.6	591.1	623.2	646.6	659.2	664.9	659.2
127.5°	369.9	426.5	482.0	528.8	548.2	567.7	596.9	618.0	630.0	632.3	630.0
130°	361.3	412.2	462.5	507.1	525.7	544.3	572.9	591.7	603.2	606.6	603.2
132.5°	354.5	397.9	444.2	483.7	501.4	519.1	547.7	566.6	576.9	580.9	576.9
135°	349.3	385.9	425.4	461.9	478.2	494.5	519.7	538.6	548.8	552.3	548.8
137.5°	344.2	375.0	408.2	439.6	453.9	468.2	491.1	508.8	518.5	522.5	518.5
140°	340.7	366.5	393.3	419.6	431.6	443.6	464.8	479.7	488.2	491.1	488.2
142.5°	337.9	359.0	380.8	402.5	412.5	422.5	439.6	451.7	459.7	461.9	459.7
145°	335.0	352.7	370.5	388.2	395.9	403.6	417.3	427.1	433.4	435.6	433.4
147.5°	332.2	346.5	361.3	375.6	381.6	387.6	399.1	407.1	411.1	412.2	411.1
150°	328.7	341.3	353.9	364.8	369.9	375.0	383.6	390.5	392.8	393.3	392.8
152.5°	324.7	335.6	346.5	356.2	359.9	363.6	370.5	375.6	377.9	378.5	377.9
155°	320.2	329.9	339.0	347.0	350.2	353.3	359.0	363.0	364.8	365.3	364.8
157.5°	316.2	324.2	332.2	338.5	341.0	343.6	348.2	351.6	353.3	353.3	353.3
160°	311.0	318.4	324.2	329.9	331.9	333.9	337.9	340.7	341.9	341.3	341.9
162.5°	306.4	312.2	317.3	321.9	323.6	325.3	328.2	330.4	330.4	330.4	330.4
165°	301.9	306.4	310.4	313.9	315.3	316.7	319.0	320.2	320.2	320.2	320.2
167.5°	297.3	300.7	303.6	306.4	307.5	308.7	309.9	311.0	310.4	310.4	310.4
170°	293.3	296.1	297.9	299.6	300.2	300.7	301.9	302.4	302.4	301.9	302.4
172.5°	289.3	291.0	292.7	293.9	294.2	294.4	294.4	295.6	294.4	293.9	294.4
175°	285.9	287.6	287.6	288.7	288.7	288.7	288.7	289.3	288.1	287.6	288.1
177.5°	284.1	284.7	285.3	285.3	285.3	285.3	284.7	285.3	283.6	283.6	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	954.1	948.8	950.3	948.8	945.0	942.7	936.7	929.1	926.1	922.3	920.0
5°	1030.5	1026.7	1025.9	1019.9	1018.4	1009.3	994.2	986.6	977.5	968.4	959.4
7.5°	1113.7	1109.2	1094.0	1091.8	1093.3	1081.9	1062.2	1047.1	1028.2	1015.3	997.9
10°	1182.5	1173.5	1160.6	1161.4	1156.1	1140.9	1121.3	1105.4	1078.1	1061.5	1036.5
12.5°	1224.2	1216.6	1215.1	1207.5	1203.0	1183.3	1159.8	1139.4	1119.0	1096.3	1077.4
15°	1274.8	1265.0	1258.2	1247.6	1244.6	1224.2	1198.4	1175.0	1151.5	1130.3	1090.2
17.5°	1330.8	1320.2	1294.5	1292.2	1274.1	1254.4	1229.5	1194.6	1169.7	1139.4	1109.9
20°	1394.4	1379.3	1346.0	1337.6	1323.3	1290.7	1256.7	1218.1	1178.0	1147.0	1112.2
22.5°	1465.5	1439.0	1414.8	1388.3	1377.7	1337.6	1290.7	1243.8	1195.4	1153.0	1111.4
25°	1557.8	1523.0	1489.0	1462.5	1444.3	1392.1	1329.3	1267.3	1211.3	1156.1	1101.6
27.5°	1630.4	1600.2	1563.1	1528.3	1504.8	1442.8	1370.9	1290.7	1221.1	1153.8	1095.5
30°	1635.7	1626.7	1604.0	1585.0	1559.3	1492.7	1413.3	1322.5	1236.3	1154.5	1083.4
32.5°	1536.6	1554.8	1564.6	1567.6	1562.3	1523.8	1451.1	1351.3	1249.9	1147.7	1072.8
35°	1323.3	1371.7	1431.5	1454.2	1476.1	1496.5	1458.7	1371.7	1254.4	1146.2	1056.2
37.5°	1089.5	1133.4	1232.5	1277.9	1303.6	1384.6	1415.6	1368.7	1263.5	1147.7	1040.3
40°	879.2	948.8	1019.9	1081.2	1121.3	1212.0	1308.1	1318.7	1250.6	1133.4	1019.9
42.5°	739.9	780.8	834.5	891.3	926.8	1034.3	1164.4	1240.8	1210.5	1109.9	994.9
45°	630.2	660.5	711.2	730.1	775.5	878.4	1016.1	1126.6	1141.7	1072.8	966.2
47.5°	541.0	566.7	599.2	622.7	659.0	736.2	852.7	974.5	1047.1	1022.1	926.1
50°	476.6	497.8	525.1	538.7	562.1	631.7	719.5	840.6	938.2	946.5	873.9
52.5°	422.9	435.0	456.2	471.4	490.3	532.6	612.1	711.9	821.7	867.0	809.5
55°	376.0	385.9	404.8	414.6	424.4	460.8	522.8	613.6	716.5	776.3	743.7
57.5°	333.7	342.0	357.9	366.9	372.2	407.0	454.7	525.8	618.1	690.8	672.6
60°	298.9	306.4	315.5	322.3	328.4	357.1	390.4	447.9	530.4	600.7	596.2
62.5°	261.8	268.6	278.4	285.2	290.5	308.7	336.7	380.6	450.9	516.0	528.9
65°	229.2	234.5	241.4	244.4	251.2	264.8	287.5	326.8	384.3	442.6	451.7
67.5°	199.7	201.3	205.8	212.6	214.1	226.2	246.6	276.2	320.8	368.5	382.8
70°	168.0	170.2	174.0	179.3	182.3	189.9	207.3	227.0	265.6	307.2	317.8
72.5°	140.0	143.0	144.5	147.5	149.0	161.2	168.7	188.4	214.9	249.7	261.0
75°	113.5	116.5	117.3	118.8	120.3	125.6	136.2	148.3	170.2	192.9	208.1
77.5°	90.0	89.3	90.8	93.1	92.3	96.8	103.7	114.2	128.6	147.5	157.4
80°	63.6	63.6	65.8	68.1	67.3	71.9	74.1	81.7	93.8	105.9	109.7
82.5°	42.4	42.4	44.6	44.6	46.2	46.9	49.9	53.7	63.6	69.6	71.9
85°	24.2	24.2	25.0	25.0	25.0	26.5	28.8	30.3	33.3	37.1	38.6
87.5°	9.8	10.6	10.6	10.6	10.6	12.1	12.1	13.6	14.4	15.9	15.9
90°	12.6	12.6	12.6	12.0	11.4	10.9	10.3	9.7	9.1	8.0	7.4
92.5°	44.6	46.3	55.5	60.9	66.3	89.2	124.1	184.1	228.1	232.1	161.2
95°	148.1	165.2	205.8	229.8	253.8	324.2	411.1	495.7	506.5	413.3	255.6
97.5°	316.7	346.5	380.8	415.1	449.4	520.3	589.4	619.2	547.1	379.0	208.7
100°	476.2	517.4	556.8	586.6	616.3	675.2	703.2	659.2	516.3	329.3	185.2
102.5°	644.9	671.2	714.1	731.8	749.5	770.1	741.5	635.2	461.9	291.6	175.5
105°	775.8	794.7	813.0	816.2	819.3	794.1	715.8	578.6	414.5	269.8	174.4
107.5°	854.7	857.6	852.4	839.8	827.3	766.7	663.2	524.8	379.0	258.4	178.4
110°	878.1	867.3	841.6	817.3	793.0	712.3	603.7	480.2	355.6	253.8	184.7

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	861.0	840.4	799.8	770.1	740.4	658.6	556.8	447.1	341.9	253.8	192.7
115°	820.4	793.0	748.4	717.2	686.1	607.7	519.1	424.8	332.7	255.6	200.7
117.5°	772.4	743.8	698.6	669.2	639.7	571.1	492.8	409.9	327.6	258.4	209.8
120°	723.8	696.3	654.0	628.8	603.7	540.8	472.2	397.9	324.2	263.0	219.0
122.5°	680.9	656.3	619.7	596.6	573.4	519.1	456.8	387.6	321.3	267.0	229.3
125°	646.6	623.2	591.1	570.6	550.0	500.2	441.9	378.5	319.0	271.6	238.4
127.5°	618.0	596.9	567.7	548.2	528.8	482.0	426.5	369.9	317.9	276.7	247.0
130°	591.7	572.9	544.3	525.7	507.1	462.5	412.2	361.3	316.7	281.3	255.6
132.5°	566.6	547.7	519.1	501.4	483.7	444.2	397.9	354.5	316.7	286.4	263.0
135°	538.6	519.7	494.5	478.2	461.9	425.4	385.9	349.3	316.7	291.0	269.8
137.5°	508.8	491.1	468.2	453.9	439.6	408.2	375.0	344.2	317.3	295.6	275.0
140°	479.7	464.8	443.6	431.6	419.6	393.3	366.5	340.7	317.9	298.4	280.1
142.5°	451.7	439.6	422.5	412.5	402.5	380.8	359.0	337.9	318.4	300.1	283.0
145°	427.1	417.3	403.6	395.9	388.2	370.5	352.7	335.0	317.9	301.3	285.9
147.5°	407.1	399.1	387.6	381.6	375.6	361.3	346.5	332.2	316.7	301.9	287.6
150°	390.5	383.6	375.0	369.9	364.8	353.9	341.3	328.7	315.0	301.9	289.3
152.5°	375.6	370.5	363.6	359.9	356.2	346.5	335.6	324.7	312.7	301.3	290.4
155°	363.0	359.0	353.3	350.2	347.0	339.0	329.9	320.2	309.9	300.1	291.0
157.5°	351.6	348.2	343.6	341.0	338.5	332.2	324.2	316.2	307.0	299.0	291.6
160°	340.7	337.9	333.9	331.9	329.9	324.2	318.4	311.0	304.1	297.3	291.6
162.5°	330.4	328.2	325.3	323.6	321.9	317.3	312.2	306.4	300.7	295.6	291.0
165°	320.2	319.0	316.7	315.3	313.9	310.4	306.4	301.9	297.3	293.9	290.4
167.5°	311.0	309.9	308.7	307.5	306.4	303.6	300.7	297.3	293.9	291.0	289.3
170°	302.4	301.9	300.7	300.2	299.6	297.9	296.1	293.3	291.0	289.3	288.1
172.5°	295.6	294.4	294.4	294.2	293.9	292.7	291.0	289.3	287.6	287.0	287.0
175°	289.3	288.7	288.7	288.7	288.7	287.6	287.6	285.9	285.3	285.3	285.9
177.5°	285.3	284.7	285.3	285.3	285.3	285.3	284.7	284.1	283.6	283.6	284.7
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	917.0	913.2	908.7	908.7	903.4	901.1	896.6	895.0	891.3	885.2	880.7
5°	949.5	939.7	933.6	928.3	917.0	908.7	900.3	891.3	882.2	871.6	859.5
7.5°	981.3	963.1	954.8	945.7	929.1	911.7	895.0	882.9	870.8	854.2	839.1
10°	1014.6	991.9	976.8	964.6	938.9	917.0	892.8	875.4	856.5	835.3	815.6
12.5°	1042.6	1013.1	1000.2	977.5	948.0	921.5	891.3	864.8	839.8	814.8	790.6
15°	1066.0	1038.0	1006.3	997.2	956.3	918.5	884.4	850.4	819.4	794.4	766.4
17.5°	1073.6	1038.0	1022.1	1000.2	951.8	912.4	869.3	832.2	802.7	765.7	743.7
20°	1075.9	1041.8	1019.9	999.4	956.3	904.1	861.8	816.4	780.8	743.7	708.9
22.5°	1069.8	1029.7	1008.5	988.9	940.4	895.8	846.6	796.7	755.1	721.0	686.2
25°	1058.5	1011.6	991.1	969.9	923.8	874.6	820.9	773.2	734.6	693.8	659.7
27.5°	1043.3	989.6	966.2	944.2	898.8	852.7	802.0	752.8	709.7	666.6	634.8
30°	1024.4	962.4	941.2	912.4	868.6	824.7	778.5	729.3	680.9	640.1	605.3
32.5°	1000.2	935.1	907.1	879.9	832.2	792.1	748.3	702.1	655.2	615.1	578.8
35°	978.3	904.1	873.1	845.9	792.9	750.5	714.2	671.1	629.5	587.9	555.3
37.5°	948.8	873.1	836.0	808.0	754.3	711.2	677.1	643.9	600.0	559.9	529.6
40°	917.7	834.5	799.7	771.7	715.7	668.8	636.3	606.8	571.2	534.1	502.4
42.5°	889.7	797.4	760.4	726.3	669.6	628.0	594.7	572.0	539.4	506.2	477.4
45°	854.2	758.1	718.0	682.4	628.0	582.6	550.8	532.6	508.4	475.9	450.9
47.5°	817.9	715.7	674.1	639.3	580.3	540.2	509.2	491.8	475.1	449.4	424.4
50°	770.2	671.1	633.3	593.2	534.9	494.1	468.3	450.9	438.1	419.9	398.7
52.5°	718.0	624.9	584.1	549.3	491.8	454.7	425.2	415.4	402.5	388.9	370.7
55°	662.8	575.0	535.7	501.6	448.7	410.8	386.6	376.0	366.2	355.6	343.5
57.5°	607.5	522.8	485.7	455.5	406.3	370.0	350.3	335.9	329.1	323.1	313.2
60°	538.7	466.8	438.1	410.8	362.4	329.1	310.2	299.6	293.6	290.5	286.0
62.5°	478.2	419.1	387.4	360.9	322.3	292.8	274.6	266.3	261.0	259.5	254.2
65°	413.9	363.2	338.2	315.5	282.2	255.7	240.6	230.8	227.0	226.2	226.2
67.5°	353.3	312.5	287.5	271.6	242.9	219.4	205.0	201.3	199.0	196.0	195.2
70°	296.6	264.0	242.1	228.5	202.8	185.4	174.0	168.0	168.0	165.7	164.2
72.5°	246.6	214.1	199.7	188.4	167.2	152.1	143.8	142.2	136.9	136.2	136.2
75°	192.9	168.7	158.9	149.0	133.2	122.6	115.8	112.0	108.9	108.9	109.7
77.5°	145.3	128.6	119.5	112.0	100.6	93.8	88.5	87.0	84.0	84.0	84.0
80°	102.9	93.8	87.0	81.0	72.6	66.6	63.6	60.5	60.5	59.8	60.5
82.5°	66.6	59.0	55.2	54.5	46.9	44.6	40.9	41.6	39.3	38.6	40.1
85°	38.6	34.8	30.3	28.8	25.7	22.7	21.2	21.9	21.2	20.4	21.2
87.5°	15.1	12.9	12.1	12.1	9.8	9.1	8.3	9.1	7.6	7.6	8.3
90°	6.3	5.7	5.2	4.6	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	96.0	57.2	46.9	36.6	24.6	16.0	10.3	8.6	10.3	16.0	24.6
95°	129.8	68.6	55.8	42.9	30.3	24.0	19.4	18.9	19.4	24.0	30.3
97.5°	112.1	69.7	60.3	50.9	39.4	33.2	29.7	29.2	29.7	33.2	39.4
100°	110.9	77.8	69.2	60.6	49.7	43.4	41.2	40.0	41.2	43.4	49.7
102.5°	116.1	87.5	79.2	70.9	61.2	54.3	52.6	52.0	52.6	54.3	61.2
105°	123.5	98.3	90.3	82.3	73.2	67.5	64.6	64.6	64.6	67.5	73.2
107.5°	133.8	109.2	102.1	94.9	85.2	80.6	77.8	76.6	77.8	80.6	85.2
110°	145.2	121.8	114.4	106.9	98.3	93.2	90.9	89.8	90.9	93.2	98.3

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	156.1	133.8	126.6	119.5	110.9	105.8	104.1	102.9	104.1	105.8	110.9
115°	167.5	146.4	139.2	132.1	123.5	118.3	116.6	115.5	116.6	118.3	123.5
117.5°	178.9	158.9	152.0	145.2	135.5	130.3	128.6	126.9	128.6	130.3	135.5
120°	191.5	171.5	164.4	157.2	147.5	142.4	140.1	138.4	140.1	142.4	147.5
122.5°	203.5	183.5	176.4	169.2	158.4	153.2	151.5	150.4	151.5	153.2	158.4
125°	213.8	195.0	187.6	180.1	169.2	164.1	161.2	160.1	161.2	164.1	169.2
127.5°	224.1	205.8	198.4	191.0	179.5	173.2	169.8	168.1	169.8	173.2	179.5
130°	233.8	216.1	208.6	201.2	189.2	181.8	177.2	175.5	177.2	181.8	189.2
132.5°	243.0	225.3	217.8	210.4	197.8	189.2	183.5	181.2	183.5	189.2	197.8
135°	251.0	233.3	225.6	217.8	205.8	196.7	189.8	187.5	189.8	196.7	205.8
137.5°	256.7	240.7	232.7	224.7	212.7	203.5	197.2	195.5	197.2	203.5	212.7
140°	263.0	246.4	238.7	231.0	220.1	211.0	204.1	202.4	204.1	211.0	220.1
142.5°	267.0	251.6	244.4	237.3	227.0	217.8	211.5	210.4	211.5	217.8	227.0
145°	271.6	256.7	250.1	243.5	233.3	225.3	219.5	218.4	219.5	225.3	233.3
147.5°	274.4	261.3	255.3	249.3	240.1	232.7	227.5	227.0	227.5	232.7	240.1
150°	277.3	264.7	259.8	255.0	247.0	239.5	235.5	234.4	235.5	239.5	247.0
152.5°	280.1	268.7	264.4	260.1	252.7	246.4	243.0	242.4	243.0	246.4	252.7
155°	281.9	272.1	268.1	264.1	258.4	252.7	249.3	249.3	249.3	252.7	258.4
157.5°	283.6	275.0	271.8	268.7	263.6	258.4	255.6	255.6	255.6	258.4	263.6
160°	284.7	277.3	274.7	272.1	267.6	263.6	261.3	261.8	261.3	263.6	267.6
162.5°	285.9	279.6	277.6	275.6	272.1	268.7	266.4	267.0	266.4	268.7	272.1
165°	285.9	281.3	279.6	277.9	275.6	272.7	271.0	272.1	271.0	272.7	275.6
167.5°	285.9	281.9	280.8	279.6	277.9	276.1	275.0	275.6	275.0	276.1	277.9
170°	285.9	283.0	282.2	281.3	280.1	279.0	278.4	279.0	278.4	279.0	280.1
172.5°	285.3	283.0	282.7	282.4	281.9	280.7	280.1	281.3	280.1	280.7	281.9
175°	284.7	283.0	283.0	283.0	283.0	282.4	281.9	283.0	281.9	282.4	283.0
177.5°	284.1	283.0	283.0	283.0	283.6	283.0	283.0	284.1	283.0	283.0	283.6
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	879.2	877.6	873.9	871.6	864.0	854.9	851.9	844.3	847.4	842.1	842.1
5°	855.7	848.9	844.3	837.5	823.2	813.3	802.7	797.4	794.4	790.6	787.6
7.5°	825.4	820.1	815.6	802.7	786.8	773.2	760.4	755.1	745.2	738.4	735.4
10°	799.0	791.4	780.8	765.7	749.0	731.6	720.3	708.9	701.4	697.6	689.2
12.5°	771.7	762.6	751.3	729.3	711.2	700.6	680.2	669.6	665.8	662.8	652.9
15°	743.7	733.9	720.3	699.8	684.0	659.0	646.9	638.6	629.5	628.7	621.2
17.5°	718.8	706.7	695.3	670.3	650.7	628.7	621.9	612.8	604.5	595.4	591.6
20°	687.0	675.6	667.3	640.1	618.1	604.5	593.2	585.6	580.3	571.2	569.7
22.5°	658.2	646.1	634.8	614.3	595.4	578.0	564.4	556.1	553.8	550.0	543.2
25°	630.2	618.1	604.5	585.6	565.9	553.8	541.7	536.4	531.9	525.8	520.5
27.5°	606.8	595.4	582.6	559.1	542.5	533.4	520.5	514.5	508.4	505.4	503.1
30°	578.8	565.9	556.1	537.9	519.8	507.7	498.6	493.3	488.0	485.0	483.5
32.5°	551.6	539.4	532.6	513.0	498.6	484.2	477.4	473.6	470.6	467.6	464.5
35°	529.6	517.5	506.9	488.8	474.4	464.5	459.2	453.2	450.9	447.9	447.9
37.5°	502.4	493.3	482.7	465.3	452.4	444.9	440.3	432.8	432.0	430.5	428.2
40°	478.9	469.8	460.0	444.9	433.5	424.4	418.4	414.6	412.3	410.8	409.3
42.5°	454.0	444.1	439.6	422.2	412.3	403.3	400.2	396.5	395.7	392.7	388.9
45°	429.7	421.4	412.3	399.5	391.2	383.6	379.0	376.0	372.2	371.5	369.2
47.5°	408.6	398.7	390.4	378.3	369.2	363.2	359.4	355.6	352.6	350.3	348.0
50°	381.3	373.8	366.9	354.1	346.5	340.5	335.2	332.1	329.1	329.1	329.1
52.5°	354.8	348.0	342.0	332.9	323.8	318.5	312.5	310.2	308.7	306.4	308.7
55°	329.1	322.3	316.3	309.4	298.9	294.3	288.3	286.0	286.7	286.7	289.0
57.5°	301.9	296.6	292.8	284.5	274.6	270.1	266.3	264.0	264.0	267.1	267.8
60°	275.4	270.1	263.3	255.7	249.7	244.4	242.1	242.9	242.9	244.4	248.2
62.5°	245.9	242.9	239.1	228.5	224.7	220.9	217.9	220.2	219.4	223.2	228.5
65°	218.7	215.6	210.3	205.0	200.5	196.7	196.0	196.7	198.2	202.0	208.1
67.5°	188.4	188.4	183.9	179.3	175.5	171.7	172.5	173.3	174.8	179.3	188.4
70°	163.4	160.4	155.9	152.8	149.8	148.3	146.8	149.8	154.3	157.4	164.2
72.5°	136.2	133.9	130.1	127.1	126.3	124.8	124.1	125.6	130.1	135.4	143.0
75°	107.4	108.2	105.9	103.7	103.7	101.4	102.9	102.9	107.4	112.7	118.8
77.5°	83.2	82.5	81.7	80.2	79.4	79.4	79.4	81.0	85.5	88.5	94.6
80°	59.0	59.8	57.5	58.3	57.5	58.3	58.3	61.3	63.6	67.3	71.9
82.5°	39.3	39.3	37.8	38.6	38.6	38.6	39.3	40.9	43.9	46.9	49.9
85°	21.9	22.7	21.2	22.7	22.7	22.7	23.5	24.2	26.5	27.2	30.3
87.5°	8.3	9.8	9.8	8.3	9.1	9.8	10.6	9.8	11.3	12.9	13.6
90°	4.6	5.2	5.7	6.3	7.4	8.0	9.1	9.7	10.3	10.9	11.4
92.5°	36.6	46.9	57.2	96.0	161.2	232.1	228.1	184.1	124.1	89.2	66.3
95°	42.9	55.8	68.6	129.8	255.6	413.3	506.5	495.7	411.1	324.2	253.8
97.5°	50.9	60.3	69.7	112.1	208.7	379.0	547.1	619.2	589.4	520.3	449.4
100°	60.6	69.2	77.8	110.9	185.2	329.3	516.3	659.2	703.2	675.2	616.3
102.5°	70.9	79.2	87.5	116.1	175.5	291.6	461.9	635.2	741.5	770.1	749.5
105°	82.3	90.3	98.3	123.5	174.4	269.8	414.5	578.6	715.8	794.1	819.3
107.5°	94.9	102.1	109.2	133.8	178.4	258.4	379.0	524.8	663.2	766.7	827.3
110°	106.9	114.4	121.8	145.2	184.7	253.8	355.6	480.2	603.7	712.3	793.0

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	119.5	126.6	133.8	156.1	192.7	253.8	341.9	447.1	556.8	658.6	740.4
115°	132.1	139.2	146.4	167.5	200.7	255.6	332.7	424.8	519.1	607.7	686.1
117.5°	145.2	152.0	158.9	178.9	209.8	258.4	327.6	409.9	492.8	571.1	639.7
120°	157.2	164.4	171.5	191.5	219.0	263.0	324.2	397.9	472.2	540.8	603.7
122.5°	169.2	176.4	183.5	203.5	229.3	267.0	321.3	387.6	456.8	519.1	573.4
125°	180.1	187.6	195.0	213.8	238.4	271.6	319.0	378.5	441.9	500.2	550.0
127.5°	191.0	198.4	205.8	224.1	247.0	276.7	317.9	369.9	426.5	482.0	528.8
130°	201.2	208.6	216.1	233.8	255.6	281.3	316.7	361.3	412.2	462.5	507.1
132.5°	210.4	217.8	225.3	243.0	263.0	286.4	316.7	354.5	397.9	444.2	483.7
135°	217.8	225.6	233.3	251.0	269.8	291.0	316.7	349.3	385.9	425.4	461.9
137.5°	224.7	232.7	240.7	256.7	275.0	295.6	317.3	344.2	375.0	408.2	439.6
140°	231.0	238.7	246.4	263.0	280.1	298.4	317.9	340.7	366.5	393.3	419.6
142.5°	237.3	244.4	251.6	267.0	283.0	300.1	318.4	337.9	359.0	380.8	402.5
145°	243.5	250.1	256.7	271.6	285.9	301.3	317.9	335.0	352.7	370.5	388.2
147.5°	249.3	255.3	261.3	274.4	287.6	301.9	316.7	332.2	346.5	361.3	375.6
150°	255.0	259.8	264.7	277.3	289.3	301.9	315.0	328.7	341.3	353.9	364.8
152.5°	260.1	264.4	268.7	280.1	290.4	301.3	312.7	324.7	335.6	346.5	356.2
155°	264.1	268.1	272.1	281.9	291.0	300.1	309.9	320.2	329.9	339.0	347.0
157.5°	268.7	271.8	275.0	283.6	291.6	299.0	307.0	316.2	324.2	332.2	338.5
160°	272.1	274.7	277.3	284.7	291.6	297.3	304.1	311.0	318.4	324.2	329.9
162.5°	275.6	277.6	279.6	285.9	291.0	295.6	300.7	306.4	312.2	317.3	321.9
165°	277.9	279.6	281.3	285.9	290.4	293.9	297.3	301.9	306.4	310.4	313.9
167.5°	279.6	280.8	281.9	285.9	289.3	291.0	293.9	297.3	300.7	303.6	306.4
170°	281.3	282.2	283.0	285.9	288.1	289.3	291.0	293.3	296.1	297.9	299.6
172.5°	282.4	282.7	283.0	285.3	287.0	287.0	287.6	289.3	291.0	292.7	293.9
175°	283.0	283.0	283.0	284.7	285.9	285.3	285.3	285.9	287.6	287.6	288.7
177.5°	283.0	283.0	283.0	284.1	284.7	283.6	283.6	284.1	284.7	285.3	285.3
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	845.1	839.8	839.1	840.6	837.5	842.1	840.6	842.1	838.3	842.1	839.8
5°	786.8	785.3	782.3	778.5	779.3	780.0	783.8	780.0	783.1	783.8	787.6
7.5°	732.4	729.3	731.6	730.1	723.3	721.8	723.3	725.6	730.1	733.1	735.4
10°	688.5	687.0	684.0	681.7	677.9	675.6	678.7	675.6	681.7	687.0	687.0
12.5°	655.2	649.2	645.4	644.6	636.3	637.8	640.8	643.1	649.9	652.9	652.9
15°	620.4	615.9	614.3	611.3	608.3	611.3	609.8	612.1	615.1	618.1	619.6
17.5°	590.1	589.4	590.1	582.6	584.8	581.1	581.8	585.6	583.3	585.6	590.1
20°	562.9	564.4	562.1	559.1	559.1	554.6	559.9	558.4	559.1	563.7	570.5
22.5°	542.5	541.7	539.4	537.2	534.1	534.9	535.7	534.1	540.2	544.0	544.7
25°	520.5	519.0	518.3	516.0	513.0	516.0	515.2	516.0	517.5	523.6	519.0
27.5°	500.1	497.1	498.6	496.3	495.6	496.3	496.3	497.1	498.6	499.3	500.1
30°	482.7	479.7	478.9	477.4	476.6	477.4	478.9	477.4	483.5	482.7	482.7
32.5°	463.8	461.5	460.0	460.0	459.2	458.5	459.2	460.0	464.5	461.5	464.5
35°	445.6	444.1	444.1	442.6	441.8	441.8	441.8	444.9	443.4	445.6	445.6
37.5°	428.2	428.2	427.5	426.0	425.2	426.0	425.2	426.7	426.0	426.7	427.5
40°	410.1	408.6	407.8	407.8	405.5	403.3	405.5	405.5	406.3	408.6	409.3
42.5°	388.1	388.9	388.9	385.9	385.9	385.9	386.6	387.4	387.4	388.9	388.9
45°	369.2	367.7	367.7	367.7	366.2	366.9	368.5	368.5	368.5	368.5	366.9
47.5°	348.0	348.0	348.8	348.8	351.1	350.3	350.3	349.5	348.0	348.0	348.8
50°	328.4	330.6	331.4	331.4	332.1	332.9	332.9	331.4	330.6	328.4	328.4
52.5°	309.4	311.0	312.5	314.7	316.3	315.5	315.5	314.0	311.0	310.2	309.4
55°	289.0	291.3	294.3	296.6	298.9	299.6	299.6	296.6	293.6	289.8	289.8
57.5°	270.1	272.4	277.7	279.9	283.0	283.0	281.4	279.2	274.6	271.6	269.3
60°	251.2	255.0	258.8	263.3	267.1	267.8	265.6	262.5	257.2	253.5	250.4
62.5°	230.8	234.5	242.1	246.6	249.7	249.7	249.7	245.9	239.1	233.8	229.2
65°	211.1	214.9	221.7	227.7	230.0	232.3	230.0	226.2	220.9	214.9	210.3
67.5°	190.7	195.2	202.0	206.5	209.6	211.8	210.3	207.3	200.5	192.2	189.1
70°	168.0	170.2	180.1	184.6	189.1	190.7	189.1	184.6	177.8	168.7	165.7
72.5°	146.8	149.0	158.1	161.9	165.7	167.2	164.9	161.9	155.9	147.5	143.8
75°	122.6	126.3	130.9	136.9	141.5	143.0	140.7	138.5	130.9	125.6	122.6
77.5°	96.8	100.6	106.7	112.0	116.5	115.8	112.7	113.5	105.2	99.1	96.8
80°	73.4	76.4	81.0	85.5	87.8	87.8	87.0	84.0	81.0	76.4	72.6
82.5°	50.7	54.5	58.3	61.3	61.3	62.0	60.5	59.8	56.7	53.0	52.2
85°	30.3	31.0	34.0	34.0	37.1	35.6	34.8	37.1	34.0	31.8	31.0
87.5°	13.6	12.9	13.6	13.6	12.9	14.4	14.4	13.6	14.4	13.6	13.6
90°	12.0	12.6	12.6	12.6	13.1	13.1	13.1	12.6	12.6	12.6	12.0
92.5°	60.9	55.5	46.3	44.6	43.4	42.3	43.4	44.6	46.3	55.5	60.9
95°	229.8	205.8	165.2	148.1	143.5	134.4	143.5	148.1	165.2	205.8	229.8
97.5°	415.1	380.8	346.5	316.7	301.3	294.4	301.3	316.7	346.5	380.8	415.1
100°	586.6	556.8	517.4	476.2	455.1	445.9	455.1	476.2	517.4	556.8	586.6
102.5°	731.8	714.1	671.2	644.9	621.4	615.2	621.4	644.9	671.2	714.1	731.8
105°	816.2	813.0	794.7	775.8	764.4	757.5	764.4	775.8	794.7	813.0	816.2
107.5°	839.8	852.4	857.6	854.7	849.0	843.3	849.0	854.7	857.6	852.4	839.8
110°	817.3	841.6	867.3	878.1	882.1	882.1	882.1	878.1	867.3	841.6	817.3

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	770.1	799.8	840.4	861.0	872.4	877.6	872.4	861.0	840.4	799.8	770.1
115°	717.2	748.4	793.0	820.4	836.4	843.8	836.4	820.4	793.0	748.4	717.2
117.5°	669.2	698.6	743.8	772.4	788.4	793.0	788.4	772.4	743.8	698.6	669.2
120°	628.8	654.0	696.3	723.8	739.2	743.8	739.2	723.8	696.3	654.0	628.8
122.5°	596.6	619.7	656.3	680.9	696.3	700.3	696.3	680.9	656.3	619.7	596.6
125°	570.6	591.1	623.2	646.6	659.2	664.9	659.2	646.6	623.2	591.1	570.6
127.5°	548.2	567.7	596.9	618.0	630.0	632.3	630.0	618.0	596.9	567.7	548.2
130°	525.7	544.3	572.9	591.7	603.2	606.6	603.2	591.7	572.9	544.3	525.7
132.5°	501.4	519.1	547.7	566.6	576.9	580.9	576.9	566.6	547.7	519.1	501.4
135°	478.2	494.5	519.7	538.6	548.8	552.3	548.8	538.6	519.7	494.5	478.2
137.5°	453.9	468.2	491.1	508.8	518.5	522.5	518.5	508.8	491.1	468.2	453.9
140°	431.6	443.6	464.8	479.7	488.2	491.1	488.2	479.7	464.8	443.6	431.6
142.5°	412.5	422.5	439.6	451.7	459.7	461.9	459.7	451.7	439.6	422.5	412.5
145°	395.9	403.6	417.3	427.1	433.4	435.6	433.4	427.1	417.3	403.6	395.9
147.5°	381.6	387.6	399.1	407.1	411.1	412.2	411.1	407.1	399.1	387.6	381.6
150°	369.9	375.0	383.6	390.5	392.8	393.3	392.8	390.5	383.6	375.0	369.9
152.5°	359.9	363.6	370.5	375.6	377.9	378.5	377.9	375.6	370.5	363.6	359.9
155°	350.2	353.3	359.0	363.0	364.8	365.3	364.8	363.0	359.0	353.3	350.2
157.5°	341.0	343.6	348.2	351.6	353.3	353.3	353.3	351.6	348.2	343.6	341.0
160°	331.9	333.9	337.9	340.7	341.9	341.3	341.9	340.7	337.9	333.9	331.9
162.5°	323.6	325.3	328.2	330.4	330.4	330.4	330.4	330.4	328.2	325.3	323.6
165°	315.3	316.7	319.0	320.2	320.2	320.2	320.2	320.2	319.0	316.7	315.3
167.5°	307.5	308.7	309.9	311.0	310.4	310.4	310.4	311.0	309.9	308.7	307.5
170°	300.2	300.7	301.9	302.4	302.4	301.9	302.4	302.4	301.9	300.7	300.2
172.5°	294.2	294.4	294.4	295.6	294.4	293.9	294.4	295.6	294.4	294.4	294.2
175°	288.7	288.7	288.7	289.3	288.1	287.6	288.1	289.3	288.7	288.7	288.7
177.5°	285.3	285.3	284.7	285.3	283.6	283.6	283.6	285.3	284.7	285.3	285.3
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3	891.3
2.5°	846.6	842.1	847.4	840.6	842.1	850.4	849.6	857.2	861.8	861.0	864.8
5°	790.6	790.6	792.9	792.1	799.7	806.5	815.6	823.2	831.5	836.0	841.3
7.5°	735.4	743.0	744.5	748.3	757.3	768.7	777.8	789.1	801.2	809.5	815.6
10°	690.0	696.1	702.1	705.1	715.0	730.1	743.0	761.1	776.3	785.3	793.7
12.5°	649.9	656.7	659.7	673.4	680.2	690.0	708.2	727.8	744.5	754.3	761.1
15°	621.2	624.9	631.7	640.1	646.9	659.0	674.1	696.1	711.9	720.3	743.7
17.5°	596.9	601.5	605.3	609.1	619.6	632.5	646.9	665.8	686.2	700.6	712.7
20°	572.0	574.2	578.8	584.8	592.4	604.5	617.4	637.0	655.2	666.6	682.4
22.5°	542.5	549.3	553.8	558.4	566.7	580.3	592.4	606.8	629.5	642.3	659.0
25°	525.1	528.1	531.1	536.4	542.5	554.6	568.2	583.3	601.5	615.1	629.5
27.5°	502.4	506.9	510.7	517.5	521.3	531.1	544.0	559.1	581.1	592.4	604.5
30°	483.5	488.0	491.0	494.1	499.3	509.9	522.0	534.1	554.6	569.0	581.1
32.5°	464.5	469.1	472.9	475.1	480.4	487.2	497.1	512.2	529.6	539.4	555.3
35°	447.9	447.9	452.4	455.5	460.0	466.1	475.1	486.5	504.6	517.5	531.9
37.5°	429.0	429.7	433.5	435.8	440.3	446.4	455.5	466.1	481.2	491.0	505.4
40°	409.3	411.6	413.1	416.9	422.2	424.4	433.5	445.6	460.8	469.8	481.9
42.5°	389.6	391.2	394.9	398.0	402.5	406.3	412.3	423.7	435.0	448.7	458.5
45°	367.7	371.5	373.8	379.0	381.3	385.1	391.2	400.2	413.9	422.2	433.5
47.5°	348.8	350.3	351.8	358.6	363.2	365.4	371.5	376.8	391.2	398.7	409.3
50°	328.4	328.4	330.6	333.7	339.0	343.5	348.8	354.8	366.2	373.8	384.3
52.5°	309.4	307.2	308.7	310.2	315.5	320.0	325.3	333.7	344.2	348.8	357.9
55°	289.0	285.2	287.5	289.8	291.3	297.3	303.4	308.7	317.0	323.8	332.1
57.5°	267.1	266.3	264.8	265.6	269.3	273.1	277.7	284.5	294.3	299.6	304.1
60°	247.4	242.9	241.4	242.9	245.1	247.4	253.5	259.5	267.8	273.1	278.4
62.5°	227.0	222.4	219.4	217.1	219.4	224.7	228.5	233.0	239.8	245.9	250.4
65°	207.3	200.5	197.5	196.0	195.2	199.0	202.0	208.1	214.1	216.4	221.7
67.5°	185.4	179.3	175.5	173.3	173.3	173.3	176.3	182.3	188.4	189.1	194.4
70°	163.4	156.6	152.8	149.8	148.3	149.8	153.6	154.3	159.6	161.2	164.2
72.5°	140.0	133.9	129.4	125.6	126.3	127.9	127.9	129.4	132.4	136.2	136.2
75°	118.0	109.7	107.4	104.4	102.9	102.9	102.9	105.9	108.2	111.2	110.5
77.5°	93.1	88.5	84.0	82.5	80.2	79.4	81.0	81.0	82.5	84.7	85.5
80°	71.9	66.6	63.6	62.0	59.0	58.3	59.0	59.0	61.3	60.5	61.3
82.5°	49.9	46.2	43.9	41.6	40.1	40.9	40.1	40.1	40.9	40.1	40.1
85°	28.8	28.0	26.5	25.7	25.0	23.5	25.0	24.2	23.5	22.7	24.2
87.5°	13.6	12.9	12.9	11.3	11.3	10.6	11.3	11.3	10.6	10.6	10.6
90°	11.4	10.9	10.3	9.7	9.1	8.0	7.4	6.3	5.7	5.2	4.6
92.5°	66.3	89.2	124.1	184.1	228.1	232.1	161.2	96.0	57.2	46.9	36.6
95°	253.8	324.2	411.1	495.7	506.5	413.3	255.6	129.8	68.6	55.8	42.9
97.5°	449.4	520.3	589.4	619.2	547.1	379.0	208.7	112.1	69.7	60.3	50.9
100°	616.3	675.2	703.2	659.2	516.3	329.3	185.2	110.9	77.8	69.2	60.6
102.5°	749.5	770.1	741.5	635.2	461.9	291.6	175.5	116.1	87.5	79.2	70.9
105°	819.3	794.1	715.8	578.6	414.5	269.8	174.4	123.5	98.3	90.3	82.3
107.5°	827.3	766.7	663.2	524.8	379.0	258.4	178.4	133.8	109.2	102.1	94.9
110°	793.0	712.3	603.7	480.2	355.6	253.8	184.7	145.2	121.8	114.4	106.9

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	740.4	658.6	556.8	447.1	341.9	253.8	192.7	156.1	133.8	126.6	119.5
115°	686.1	607.7	519.1	424.8	332.7	255.6	200.7	167.5	146.4	139.2	132.1
117.5°	639.7	571.1	492.8	409.9	327.6	258.4	209.8	178.9	158.9	152.0	145.2
120°	603.7	540.8	472.2	397.9	324.2	263.0	219.0	191.5	171.5	164.4	157.2
122.5°	573.4	519.1	456.8	387.6	321.3	267.0	229.3	203.5	183.5	176.4	169.2
125°	550.0	500.2	441.9	378.5	319.0	271.6	238.4	213.8	195.0	187.6	180.1
127.5°	528.8	482.0	426.5	369.9	317.9	276.7	247.0	224.1	205.8	198.4	191.0
130°	507.1	462.5	412.2	361.3	316.7	281.3	255.6	233.8	216.1	208.6	201.2
132.5°	483.7	444.2	397.9	354.5	316.7	286.4	263.0	243.0	225.3	217.8	210.4
135°	461.9	425.4	385.9	349.3	316.7	291.0	269.8	251.0	233.3	225.6	217.8
137.5°	439.6	408.2	375.0	344.2	317.3	295.6	275.0	256.7	240.7	232.7	224.7
140°	419.6	393.3	366.5	340.7	317.9	298.4	280.1	263.0	246.4	238.7	231.0
142.5°	402.5	380.8	359.0	337.9	318.4	300.1	283.0	267.0	251.6	244.4	237.3
145°	388.2	370.5	352.7	335.0	317.9	301.3	285.9	271.6	256.7	250.1	243.5
147.5°	375.6	361.3	346.5	332.2	316.7	301.9	287.6	274.4	261.3	255.3	249.3
150°	364.8	353.9	341.3	328.7	315.0	301.9	289.3	277.3	264.7	259.8	255.0
152.5°	356.2	346.5	335.6	324.7	312.7	301.3	290.4	280.1	268.7	264.4	260.1
155°	347.0	339.0	329.9	320.2	309.9	300.1	291.0	281.9	272.1	268.1	264.1
157.5°	338.5	332.2	324.2	316.2	307.0	299.0	291.6	283.6	275.0	271.8	268.7
160°	329.9	324.2	318.4	311.0	304.1	297.3	291.6	284.7	277.3	274.7	272.1
162.5°	321.9	317.3	312.2	306.4	300.7	295.6	291.0	285.9	279.6	277.6	275.6
165°	313.9	310.4	306.4	301.9	297.3	293.9	290.4	285.9	281.3	279.6	277.9
167.5°	306.4	303.6	300.7	297.3	293.9	291.0	289.3	285.9	281.9	280.8	279.6
170°	299.6	297.9	296.1	293.3	291.0	289.3	288.1	285.9	283.0	282.2	281.3
172.5°	293.9	292.7	291.0	289.3	287.6	287.0	287.0	285.3	283.0	282.7	282.4
175°	288.7	287.6	287.6	285.9	285.3	285.3	285.9	284.7	283.0	283.0	283.0
177.5°	285.3	285.3	284.7	284.1	283.6	283.6	284.7	284.1	283.0	283.0	283.0
180°	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6	283.6

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	891.3	891.3	891.3	891.3
2.5°	870.1	877.6	882.9	892.8
5°	850.4	864.0	876.9	890.5
7.5°	830.7	846.6	867.0	884.4
10°	808.8	829.2	853.4	876.9
12.5°	786.8	811.1	837.5	868.6
15°	760.4	791.4	822.4	855.7
17.5°	736.9	768.7	802.0	843.6
20°	710.4	745.2	781.6	823.9
22.5°	687.0	725.6	763.4	808.0
25°	660.5	698.3	739.9	787.6
27.5°	638.6	673.4	714.2	765.7
30°	612.1	649.9	690.8	742.2
32.5°	587.1	623.4	666.6	717.2
35°	561.4	598.5	637.0	685.5
37.5°	537.2	569.0	607.5	653.7
40°	509.9	544.7	579.5	615.9
42.5°	485.0	516.7	549.3	578.0
45°	457.0	484.2	515.2	538.7
47.5°	431.3	455.5	479.7	497.8
50°	405.5	424.4	442.6	458.5
52.5°	375.3	396.5	406.3	416.1
55°	348.0	360.1	369.2	379.0
57.5°	321.5	326.8	331.4	340.5
60°	286.7	292.8	298.1	304.9
62.5°	256.5	259.5	261.0	267.8
65°	227.7	227.0	230.8	234.5
67.5°	196.7	196.0	199.7	201.3
70°	166.4	165.7	166.4	170.2
72.5°	137.7	137.7	138.5	140.0
75°	111.2	111.2	112.0	113.5
77.5°	84.0	85.5	84.7	87.8
80°	61.3	59.8	61.3	62.8
82.5°	40.1	41.6	41.6	40.1
85°	22.7	22.7	22.7	22.7
87.5°	9.8	9.8	10.6	11.3
90°	3.4	2.3	1.1	0.6
92.5°	24.6	16.0	10.3	8.6
95°	30.3	24.0	19.4	18.9
97.5°	39.4	33.2	29.7	29.2
100°	49.7	43.4	41.2	40.0
102.5°	61.2	54.3	52.6	52.0
105°	73.2	67.5	64.6	64.6
107.5°	85.2	80.6	77.8	76.6
110°	98.3	93.2	90.9	89.8

TEST NUMBER: P1028116

CATALOG NUMBER: S125DIP-B610D610UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	110.9	105.8	104.1	102.9
115°	123.5	118.3	116.6	115.5
117.5°	135.5	130.3	128.6	126.9
120°	147.5	142.4	140.1	138.4
122.5°	158.4	153.2	151.5	150.4
125°	169.2	164.1	161.2	160.1
127.5°	179.5	173.2	169.8	168.1
130°	189.2	181.8	177.2	175.5
132.5°	197.8	189.2	183.5	181.2
135°	205.8	196.7	189.8	187.5
137.5°	212.7	203.5	197.2	195.5
140°	220.1	211.0	204.1	202.4
142.5°	227.0	217.8	211.5	210.4
145°	233.3	225.3	219.5	218.4
147.5°	240.1	232.7	227.5	227.0
150°	247.0	239.5	235.5	234.4
152.5°	252.7	246.4	243.0	242.4
155°	258.4	252.7	249.3	249.3
157.5°	263.6	258.4	255.6	255.6
160°	267.6	263.6	261.3	261.8
162.5°	272.1	268.7	266.4	267.0
165°	275.6	272.7	271.0	272.1
167.5°	277.9	276.1	275.0	275.6
170°	280.1	279.0	278.4	279.0
172.5°	281.9	280.7	280.1	281.3
175°	283.0	282.4	281.9	283.0
177.5°	283.6	283.0	283.0	284.1
180°	283.6	283.6	283.6	283.6

(END OF REPORT)