

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028151

Luminaire Tested: S125DIP-B610D850UB27-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028151
REPORT IS A COMBINATION OF REPORTS P1002360 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIP-B610D850UB27-4F0-XX-W2A-A1
Description: Define 5 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5211.0 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.43 / 1.52
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39
3	81	72	65	59	75	67	60	55	56	52	48	47	43	41	38	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5663	5663	5663	5663
5°	5667	6424	5672	4873
10°	5633	7322	5623	4183
15°	5591	7939	5556	3780
20°	5520	8700	5470	3450
25°	5458	9968	5358	3256
30°	5368	10516	5275	3079
35°	5225	8430	5116	2938
40°	5003	5826	4929	2788
45°	4722	4338	4669	2663
50°	4401	3571	4329	2563
55°	4054	3046	4022	2477
60°	3714	2607	3649	2410
65°	3347	2251	3292	2311
70°	2959	1870	2920	2142
75°	2547	1446	2513	1859
80°	2013	978	1939	1366
85°	1286	490	1246	697

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 8650 cd/sqm

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	1.6
10°-20°	253.4	4.9
20°-30°	411.6	7.9
30°-40°	503.0	9.7
40°-50°	456.3	8.8
50°-60°	363.4	7.0
60°-70°	253.1	4.9
70°-80°	134.8	2.6
80°-90°	35.0	0.7
90°-100°	64.7	1.2
100°-110°	192.2	3.7
110°-120°	326.0	6.3
120°-130°	429.1	8.2
130°-140°	480.9	9.2
140°-150°	471.4	9.0
150°-160°	395.9	7.6
160°-170°	263.2	5.1
170°-180°	92.1	1.8
0°-30°	750.0	14.4
0°-40°	1253.0	24.0
0°-60°	2072.6	39.8
0°-90°	2495.5	47.9
90°-120°	582.9	11.2
90°-150°	1964.3	37.7
90°-180°	2715.0	52.1
0°-180°	5211.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1020	884	774	883	84
15°	849	1273	843	606	849	239
25°	781	1567	767	512	781	360
35°	680	1257	666	438	680	424
45°	534	593	528	364	534	411
55°	376	365	373	297	376	336
65°	233	224	229	230	233	231
75°	112	110	111	142	112	120
85°	22	25	22	35	22	27
90°	1	18	1	18	1	5
95°	49	65	49	65	49	51
105°	173	188	173	188	173	184
115°	326	329	326	329	326	323
125°	476	479	476	479	476	427
135°	619	622	619	622	619	477
145°	750	753	750	753	750	469
155°	859	859	859	859	859	396
165°	934	931	934	931	934	263
175°	971	967	971	967	971	92
180°	973	973	973	973	973	

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	885.3	890.6	896.6	901.1	908.6	910.8	914.6	916.8	919.1	921.3	922.8
5°	883.1	895.8	907.1	915.3	929.6	934.8	941.6	949.8	959.6	967.8	973.1
7.5°	877.1	897.3	912.3	928.8	948.3	961.1	967.8	985.1	1000.9	1012.9	1028.6
10°	869.6	893.6	916.8	941.6	969.3	983.6	997.1	1021.1	1042.9	1062.4	1078.1
12.5°	861.3	890.6	918.3	950.6	988.1	1005.4	1014.4	1055.6	1082.6	1093.1	1123.9
15°	848.6	883.1	922.8	962.6	994.1	1014.4	1039.1	1072.1	1099.1	1122.4	1147.2
17.5°	836.5	874.1	914.6	958.8	1004.6	1030.9	1049.6	1078.9	1108.1	1138.2	1161.4
20°	817.0	865.8	907.1	954.3	1008.4	1027.1	1046.6	1081.1	1112.6	1144.9	1174.2
22.5°	801.3	847.8	904.1	949.1	994.9	1013.6	1037.6	1073.6	1111.1	1147.9	1190.7
25°	781.0	832.8	881.6	929.6	976.8	997.1	1018.9	1065.4	1104.4	1151.7	1198.9
27.5°	759.3	812.5	861.3	904.8	949.1	976.8	1000.1	1048.9	1100.6	1152.4	1213.9
30°	736.0	786.3	832.8	875.6	924.3	952.8	976.1	1033.1	1090.9	1156.9	1230.4
32.5°	711.3	758.5	798.3	841.8	893.6	919.8	951.3	1013.6	1081.9	1160.7	1252.9
35°	679.7	724.8	760.0	804.3	856.1	889.8	922.8	992.6	1072.1	1159.9	1265.7
37.5°	648.2	683.5	717.3	764.5	824.5	855.3	889.8	966.3	1057.1	1157.7	1271.0
40°	610.7	645.2	674.5	722.5	785.5	820.8	856.8	937.1	1039.9	1149.4	1252.2
42.5°	573.2	602.5	634.7	685.0	745.8	783.3	821.5	910.8	1017.4	1125.4	1200.4
45°	534.2	556.7	592.0	637.7	702.3	738.3	781.8	878.6	985.9	1081.9	1119.4
47.5°	493.7	516.2	549.2	593.5	657.2	700.0	741.3	838.0	946.1	1020.4	1020.4
50°	454.7	472.7	504.9	549.2	613.7	652.7	694.7	797.5	884.6	939.3	890.6
52.5°	412.6	432.9	459.9	506.4	570.2	605.5	651.2	739.0	821.5	844.1	769.0
55°	375.9	392.4	417.9	462.2	521.4	558.2	597.2	681.2	751.0	749.5	669.2
57.5°	337.6	351.1	378.1	418.6	473.4	506.4	545.4	618.2	675.2	655.0	579.2
60°	302.4	312.1	338.4	371.4	423.9	454.7	492.2	551.4	595.0	566.5	489.9
62.5°	265.6	276.8	297.9	330.1	376.6	401.4	429.2	489.2	516.9	491.4	413.4
65°	232.6	241.6	260.3	287.4	329.4	351.9	375.9	425.4	451.7	414.9	350.4
67.5°	199.6	210.1	223.6	247.6	280.6	301.6	322.6	365.4	377.4	344.4	290.4
70°	168.8	177.8	190.6	207.8	235.6	254.3	270.1	305.4	313.6	282.9	240.1
72.5°	138.8	144.8	155.3	169.6	195.1	205.6	222.1	246.1	256.6	228.8	198.1
75°	112.5	117.0	123.8	134.3	151.6	162.8	176.3	198.8	198.1	178.6	156.8
77.5°	87.0	87.8	95.3	105.0	115.5	125.3	132.0	147.8	149.3	137.3	119.3
80°	62.3	64.5	67.5	75.0	84.0	87.8	96.0	105.8	107.3	98.3	86.3
82.5°	39.8	41.3	43.5	48.0	54.0	58.5	63.0	66.8	70.5	65.3	55.5
85°	22.5	23.3	25.5	27.0	30.0	32.3	36.0	39.8	39.0	35.3	32.3
87.5°	11.3	11.3	11.3	12.8	14.3	14.3	15.8	16.5	17.3	15.8	14.3
90°	0.8	2.1	3.5	4.8	6.1	6.8	7.4	8.6	9.7	10.9	12.1
92.5°	22.7	23.5	24.4	25.2	26.1	26.5	27.3	28.8	30.3	31.8	33.3
95°	49.2	49.5	49.9	50.2	50.5	50.7	51.5	53.2	54.9	56.6	58.3
97.5°	75.7	75.9	76.1	76.2	76.4	76.5	77.7	80.0	82.4	84.7	87.1
100°	106.0	106.0	106.0	106.0	106.0	106.0	107.1	109.3	111.4	113.6	115.8
102.5°	138.6	139.4	140.2	141.1	141.9	142.3	142.7	143.6	144.4	145.3	146.1
105°	172.6	173.4	174.3	175.1	176.0	176.4	176.9	177.9	179.0	180.0	181.0
107.5°	209.7	210.5	211.4	212.2	213.1	213.5	213.9	214.8	215.6	216.5	217.3
110°	248.4	249.2	250.0	250.9	251.7	252.1	252.4	252.9	253.4	253.9	254.4

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	287.7	288.0	288.4	288.7	289.0	289.2	289.5	290.2	290.9	291.6	292.3
115°	326.3	327.0	327.7	328.4	329.1	329.4	329.6	329.9	330.2	330.6	330.9
117.5°	365.7	365.9	366.1	366.2	366.4	366.5	366.7	367.0	367.3	367.7	368.0
120°	402.1	402.9	403.7	404.6	405.4	405.8	405.9	406.1	406.2	406.4	406.6
122.5°	441.4	441.6	441.8	441.9	442.1	442.2	442.5	443.0	443.5	444.0	444.5
125°	476.3	477.3	478.3	479.3	480.3	480.8	480.9	481.1	481.2	481.4	481.6
127.5°	514.9	515.4	515.9	516.4	516.9	517.2	517.3	517.4	517.6	517.7	517.9
130°	549.0	549.8	550.6	551.5	552.3	552.7	552.9	553.2	553.6	553.9	554.3
132.5°	583.0	584.5	586.0	587.5	589.0	589.8	589.7	589.6	589.4	589.3	589.1
135°	619.4	620.4	621.4	622.4	623.4	623.9	624.0	624.2	624.3	624.5	624.7
137.5°	653.4	654.4	655.4	656.5	657.5	658.0	658.2	658.5	658.8	659.2	659.5
140°	686.0	686.8	687.7	688.5	689.4	689.8	690.1	690.6	691.1	691.6	692.1
142.5°	718.6	719.3	719.9	720.6	721.3	721.6	721.9	722.6	723.3	723.9	724.6
145°	750.4	751.1	751.7	752.4	753.1	753.4	753.7	754.2	754.7	755.2	755.7
147.5°	779.9	780.4	780.9	781.4	781.9	782.2	782.4	782.7	783.0	783.4	783.7
150°	809.4	809.2	809.1	808.9	808.8	808.7	809.0	809.7	810.4	811.0	811.7
152.5°	833.7	834.0	834.4	834.7	835.0	835.2	835.3	835.4	835.6	835.7	835.9
155°	858.6	858.6	858.6	858.6	858.6	858.6	858.7	858.9	859.0	859.2	859.4
157.5°	881.4	881.0	880.7	880.3	880.0	879.8	879.9	880.1	880.2	880.4	880.6
160°	901.0	900.5	900.0	899.5	899.0	898.8	898.9	899.0	899.2	899.3	899.5
162.5°	918.5	918.1	917.8	917.4	917.1	916.9	916.9	916.9	916.9	916.9	916.9
165°	933.6	933.3	932.9	932.6	932.3	932.1	932.2	932.3	932.5	932.6	932.8
167.5°	947.2	946.5	945.9	945.2	944.5	944.2	944.2	944.2	944.2	944.2	944.2
170°	957.8	957.1	956.5	955.8	955.1	954.8	954.8	954.8	954.8	954.8	954.8
172.5°	965.4	964.7	964.1	963.4	962.7	962.4	962.4	962.4	962.4	962.4	962.4
175°	970.7	970.0	969.4	968.7	968.0	967.7	967.7	967.7	967.7	967.7	967.7
177.5°	974.5	973.8	973.2	972.5	971.8	971.5	971.4	971.2	971.1	970.9	970.7
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	924.3	929.6	934.1	937.8	940.8	945.3	942.3	943.1	944.6	947.6	947.6
5°	984.4	992.6	997.1	1012.1	1015.9	1015.1	1012.9	1024.9	1024.1	1019.6	1018.9
7.5°	1042.9	1057.1	1069.9	1081.9	1085.6	1095.4	1097.6	1102.9	1101.4	1108.9	1105.1
10°	1096.1	1118.6	1130.7	1148.7	1153.2	1157.7	1163.7	1166.7	1173.4	1172.7	1172.7
12.5°	1137.4	1164.4	1180.2	1184.7	1201.9	1207.2	1212.4	1222.2	1219.9	1220.7	1225.2
15°	1169.7	1195.9	1209.4	1230.4	1242.4	1248.4	1257.4	1268.0	1266.5	1273.2	1271.7
17.5°	1193.7	1218.4	1243.2	1274.7	1275.5	1291.2	1312.2	1316.7	1326.5	1319.7	1319.7
20°	1213.2	1246.2	1281.5	1322.0	1326.5	1336.2	1361.7	1379.0	1390.2	1386.5	1388.7
22.5°	1234.2	1281.5	1322.7	1363.2	1385.0	1402.3	1427.0	1454.0	1463.8	1469.8	1468.3
25°	1261.2	1310.7	1371.5	1427.8	1450.3	1483.3	1516.3	1542.6	1550.1	1566.6	1551.6
27.5°	1289.0	1358.7	1434.5	1500.5	1529.0	1556.1	1595.8	1615.3	1625.1	1632.6	1627.3
30°	1312.2	1408.3	1490.8	1551.6	1571.8	1587.6	1610.1	1614.6	1610.8	1616.8	1624.3
32.5°	1348.2	1442.0	1511.8	1541.1	1538.8	1538.0	1520.8	1496.8	1491.5	1477.3	1496.8
35°	1367.7	1442.8	1469.8	1430.8	1415.0	1386.5	1331.7	1295.7	1264.2	1257.4	1258.9
37.5°	1356.5	1385.7	1353.5	1250.7	1225.2	1181.7	1108.9	1057.9	1034.6	1016.6	1039.9
40°	1295.7	1263.5	1174.9	1049.6	1012.9	971.6	903.3	875.6	842.6	835.8	866.6
42.5°	1195.2	1096.9	971.6	874.8	836.5	813.3	756.3	730.0	706.8	696.2	713.5
45°	1058.6	939.3	813.3	733.8	701.5	673.7	640.0	612.2	597.2	592.7	607.0
47.5°	917.6	791.5	691.0	631.7	598.0	577.0	545.4	529.7	517.7	519.2	521.4
50°	782.5	667.7	590.5	531.2	514.7	498.2	477.2	463.7	457.7	459.9	458.4
52.5°	666.2	573.2	507.9	462.2	454.7	438.9	421.7	410.4	408.1	408.9	411.1
55°	564.2	491.4	439.7	406.6	398.4	387.1	376.6	369.1	363.1	365.4	364.6
57.5°	486.9	423.2	383.4	356.4	350.4	343.6	333.9	330.1	327.9	323.4	327.1
60°	418.6	366.9	332.4	315.9	310.6	306.1	295.6	291.1	289.6	287.4	293.4
62.5°	354.1	317.4	291.1	276.1	270.8	266.3	261.1	257.3	258.1	255.1	258.1
65°	303.1	273.1	254.3	240.8	234.1	231.1	230.3	224.3	223.6	224.3	225.1
67.5°	255.8	230.3	216.1	207.8	202.6	199.6	197.3	193.6	196.6	194.3	195.8
70°	213.1	195.8	180.8	172.6	170.3	171.1	167.3	165.8	166.6	165.1	166.6
72.5°	171.8	157.6	151.6	145.6	142.6	141.8	139.5	137.3	139.5	138.8	138.8
75°	137.3	126.8	120.0	116.3	116.3	114.8	111.0	111.0	111.0	110.3	111.0
77.5°	105.8	96.8	93.8	90.0	90.0	87.8	87.0	87.0	85.5	87.8	86.3
80°	78.8	72.0	67.5	65.3	65.3	64.5	63.0	62.3	63.0	62.3	62.3
82.5°	51.0	48.0	45.8	43.5	42.8	43.5	42.8	41.3	42.0	41.3	42.8
85°	29.3	26.3	26.3	24.8	25.5	24.0	24.8	23.3	22.5	24.8	23.3
87.5°	12.8	12.0	12.0	10.5	10.5	10.5	9.8	10.5	9.8	9.0	9.8
90°	12.9	13.8	14.6	15.5	15.9	16.2	16.7	17.2	17.7	18.2	17.7
92.5°	34.5	35.7	36.8	38.0	38.6	38.8	39.1	39.4	39.8	40.1	39.8
95°	59.5	60.7	61.8	63.0	63.6	63.8	64.1	64.4	64.8	65.1	64.8
97.5°	88.1	89.1	90.1	91.1	91.6	91.7	91.9	92.0	92.2	92.4	92.2
100°	117.3	118.9	120.4	121.9	122.7	122.9	123.2	123.5	123.9	124.2	123.9
102.5°	147.8	149.5	151.2	152.9	153.7	154.0	154.5	155.0	155.5	156.0	155.5
105°	182.0	183.0	184.0	185.0	185.5	185.8	186.3	186.8	187.3	187.8	187.3
107.5°	217.8	218.3	218.8	219.3	219.6	219.6	219.6	219.6	219.6	219.6	219.6
110°	254.9	255.4	255.9	256.4	256.7	256.6	256.4	256.3	256.1	255.9	256.1

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	292.5	292.6	292.8	292.9	293.0	292.8	292.5	292.2	291.8	291.5	291.8
115°	330.7	330.5	330.4	330.2	330.1	330.0	329.9	329.7	329.6	329.4	329.6
117.5°	368.2	368.3	368.5	368.6	368.7	368.4	367.7	367.0	366.4	365.7	366.4
120°	406.6	406.6	406.6	406.6	406.6	406.3	405.6	404.9	404.3	403.6	404.3
122.5°	444.3	444.1	444.0	443.8	443.7	443.4	442.9	442.4	441.9	441.4	441.9
125°	481.2	480.9	480.5	480.2	480.0	479.9	479.8	479.6	479.5	479.3	479.5
127.5°	517.7	517.6	517.4	517.3	517.2	517.0	516.7	516.3	516.0	515.6	516.0
130°	554.1	553.9	553.8	553.6	553.5	553.3	553.0	552.7	552.3	552.0	552.3
132.5°	588.9	588.7	588.6	588.4	588.3	588.1	587.6	587.1	586.6	586.1	586.6
135°	624.7	624.7	624.7	624.7	624.7	624.4	623.7	623.0	622.3	621.6	622.3
137.5°	659.7	659.9	660.0	660.2	660.3	659.9	659.0	658.2	657.3	656.5	657.3
140°	692.4	692.8	693.1	693.4	693.6	693.2	692.3	691.5	690.6	689.8	690.6
142.5°	724.8	725.0	725.1	725.3	725.4	725.0	724.1	723.3	722.4	721.6	722.4
145°	755.7	755.7	755.7	755.7	755.7	755.4	754.9	754.4	753.9	753.4	753.9
147.5°	784.2	784.7	785.2	785.7	785.9	785.2	783.9	782.6	781.2	779.9	781.2
150°	811.7	811.7	811.7	811.7	811.7	811.5	811.2	810.9	810.5	810.2	810.5
152.5°	836.4	836.9	837.4	837.9	838.2	837.9	837.2	836.5	835.9	835.2	835.9
155°	860.1	860.7	861.4	862.1	862.4	862.0	861.1	860.3	859.4	858.6	859.4
157.5°	881.3	881.9	882.6	883.3	883.6	883.0	881.8	880.7	879.5	878.3	879.5
160°	900.2	900.9	901.6	902.3	902.6	902.2	901.3	900.5	899.6	898.8	899.6
162.5°	917.7	918.6	919.4	920.3	920.7	920.2	919.2	918.2	917.2	916.2	917.2
165°	933.5	934.2	934.9	935.6	935.9	935.4	934.4	933.3	932.3	931.3	932.3
167.5°	945.2	946.2	947.2	948.2	948.7	948.2	947.2	946.2	945.2	944.2	945.2
170°	955.8	956.8	957.8	958.8	959.3	958.7	957.5	956.4	955.2	954.0	955.2
172.5°	963.4	964.4	965.4	966.4	966.9	966.4	965.4	964.4	963.4	962.4	963.4
175°	968.7	969.7	970.7	971.7	972.2	971.6	970.4	969.3	968.1	966.9	968.1
177.5°	971.7	972.7	973.7	974.7	975.2	974.6	973.4	972.3	971.1	969.9	971.1
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	946.1	940.8	942.3	940.8	937.1	934.8	928.8	921.3	918.3	914.6	912.3
5°	1021.9	1018.1	1017.4	1011.4	1009.9	1000.9	985.9	978.3	969.3	960.3	951.3
7.5°	1104.4	1099.9	1084.9	1082.6	1084.1	1072.9	1053.4	1038.4	1019.6	1006.9	989.6
10°	1172.7	1163.7	1150.9	1151.7	1146.4	1131.4	1111.9	1096.1	1069.1	1052.6	1027.9
12.5°	1213.9	1206.4	1204.9	1197.4	1192.9	1173.4	1150.2	1129.9	1109.6	1087.1	1068.4
15°	1264.2	1254.4	1247.7	1237.2	1234.2	1213.9	1188.4	1165.2	1141.9	1120.9	1081.1
17.5°	1319.7	1309.2	1283.7	1281.5	1263.5	1243.9	1219.2	1184.7	1159.9	1129.9	1100.6
20°	1382.7	1367.7	1334.7	1326.5	1312.2	1280.0	1246.2	1207.9	1168.2	1137.4	1102.9
22.5°	1453.3	1427.0	1403.0	1376.7	1366.2	1326.5	1280.0	1233.4	1185.4	1143.4	1102.1
25°	1544.8	1510.3	1476.5	1450.3	1432.3	1380.5	1318.2	1256.7	1201.2	1146.4	1092.4
27.5°	1616.8	1586.8	1550.1	1515.5	1492.3	1430.8	1359.5	1280.0	1210.9	1144.2	1086.4
30°	1622.1	1613.1	1590.6	1571.8	1546.3	1480.3	1401.5	1311.5	1225.9	1144.9	1074.4
32.5°	1523.8	1541.8	1551.6	1554.6	1549.3	1511.0	1439.0	1340.0	1239.4	1138.2	1063.9
35°	1312.2	1360.2	1419.5	1442.0	1463.8	1484.0	1446.5	1360.2	1243.9	1136.7	1047.4
37.5°	1080.4	1123.9	1222.2	1267.2	1292.7	1373.0	1403.8	1357.2	1252.9	1138.2	1031.6
40°	871.8	940.8	1011.4	1072.1	1111.9	1201.9	1297.2	1307.7	1240.2	1123.9	1011.4
42.5°	733.8	774.3	827.5	883.8	919.1	1025.6	1154.7	1230.4	1200.4	1100.6	986.6
45°	625.0	655.0	705.3	724.0	769.0	871.1	1007.6	1117.1	1132.2	1063.9	958.1
47.5°	536.4	562.0	594.2	617.5	653.5	730.0	845.6	966.3	1038.4	1013.6	918.3
50°	472.7	493.7	520.7	534.2	557.4	626.5	713.5	833.5	930.3	938.6	866.6
52.5°	419.4	431.4	452.4	467.4	486.2	528.2	607.0	706.0	814.8	859.8	802.8
55°	372.9	382.6	401.4	411.1	420.9	456.9	518.4	608.5	710.5	769.8	737.5
57.5°	330.9	339.1	354.9	363.9	369.1	403.6	450.9	521.4	613.0	685.0	667.0
60°	296.4	303.9	312.9	319.6	325.6	354.1	387.1	444.2	525.9	595.7	591.2
62.5°	259.6	266.3	276.1	282.9	288.1	306.1	333.9	377.4	447.2	511.7	524.4
65°	227.3	232.6	239.3	242.3	249.1	262.6	285.1	324.1	381.1	438.9	447.9
67.5°	198.1	199.6	204.1	210.8	212.3	224.3	244.6	273.8	318.1	365.4	379.6
70°	166.6	168.8	172.6	177.8	180.8	188.3	205.6	225.1	263.3	304.6	315.1
72.5°	138.8	141.8	143.3	146.3	147.8	159.8	167.3	186.8	213.1	247.6	258.8
75°	112.5	115.5	116.3	117.8	119.3	124.5	135.0	147.1	168.8	191.3	206.3
77.5°	89.3	88.5	90.0	92.3	91.5	96.0	102.8	113.3	127.5	146.3	156.1
80°	63.0	63.0	65.3	67.5	66.8	71.3	73.5	81.0	93.0	105.0	108.8
82.5°	42.0	42.0	44.3	44.3	45.8	46.5	49.5	53.3	63.0	69.0	71.3
85°	24.0	24.0	24.8	24.8	24.8	26.3	28.5	30.0	33.0	36.8	38.3
87.5°	9.8	10.5	10.5	10.5	10.5	12.0	12.0	13.5	14.3	15.8	15.8
90°	17.2	16.7	16.2	15.9	15.5	14.6	13.8	12.9	12.1	10.9	9.7
92.5°	39.4	39.1	38.8	38.6	38.0	36.8	35.7	34.5	33.3	31.8	30.3
95°	64.4	64.1	63.8	63.6	63.0	61.8	60.7	59.5	58.3	56.6	54.9
97.5°	92.0	91.9	91.7	91.6	91.1	90.1	89.1	88.1	87.1	84.7	82.4
100°	123.5	123.2	122.9	122.7	121.9	120.4	118.9	117.3	115.8	113.6	111.4
102.5°	155.0	154.5	154.0	153.7	152.9	151.2	149.5	147.8	146.1	145.3	144.4
105°	186.8	186.3	185.8	185.5	185.0	184.0	183.0	182.0	181.0	180.0	179.0
107.5°	219.6	219.6	219.6	219.6	219.3	218.8	218.3	217.8	217.3	216.5	215.6
110°	256.3	256.4	256.6	256.7	256.4	255.9	255.4	254.9	254.4	253.9	253.4

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	292.2	292.5	292.8	293.0	292.9	292.8	292.6	292.5	292.3	291.6	290.9
115°	329.7	329.9	330.0	330.1	330.2	330.4	330.5	330.7	330.9	330.6	330.2
117.5°	367.0	367.7	368.4	368.7	368.6	368.5	368.3	368.2	368.0	367.7	367.3
120°	404.9	405.6	406.3	406.6	406.6	406.6	406.6	406.6	406.6	406.4	406.2
122.5°	442.4	442.9	443.4	443.7	443.8	444.0	444.1	444.3	444.5	444.0	443.5
125°	479.6	479.8	479.9	480.0	480.2	480.5	480.9	481.2	481.6	481.4	481.2
127.5°	516.3	516.7	517.0	517.2	517.3	517.4	517.6	517.7	517.9	517.7	517.6
130°	552.7	553.0	553.3	553.5	553.6	553.8	553.9	554.1	554.3	553.9	553.6
132.5°	587.1	587.6	588.1	588.3	588.4	588.6	588.7	588.9	589.1	589.3	589.4
135°	623.0	623.7	624.4	624.7	624.7	624.7	624.7	624.7	624.7	624.5	624.3
137.5°	658.2	659.0	659.9	660.3	660.2	660.0	659.9	659.7	659.5	659.2	658.8
140°	691.5	692.3	693.2	693.6	693.4	693.1	692.8	692.4	692.1	691.6	691.1
142.5°	723.3	724.1	725.0	725.4	725.3	725.1	725.0	724.8	724.6	723.9	723.3
145°	754.4	754.9	755.4	755.7	755.7	755.7	755.7	755.7	755.7	755.2	754.7
147.5°	782.6	783.9	785.2	785.9	785.7	785.2	784.7	784.2	783.7	783.4	783.0
150°	810.9	811.2	811.5	811.7	811.7	811.7	811.7	811.7	811.7	811.0	810.4
152.5°	836.5	837.2	837.9	838.2	837.9	837.4	836.9	836.4	835.9	835.7	835.6
155°	860.3	861.1	862.0	862.4	862.1	861.4	860.7	860.1	859.4	859.2	859.0
157.5°	880.7	881.8	883.0	883.6	883.3	882.6	881.9	881.3	880.6	880.4	880.2
160°	900.5	901.3	902.2	902.6	902.3	901.6	900.9	900.2	899.5	899.3	899.2
162.5°	918.2	919.2	920.2	920.7	920.3	919.4	918.6	917.7	916.9	916.9	916.9
165°	933.3	934.4	935.4	935.9	935.6	934.9	934.2	933.5	932.8	932.6	932.5
167.5°	946.2	947.2	948.2	948.7	948.2	947.2	946.2	945.2	944.2	944.2	944.2
170°	956.4	957.5	958.7	959.3	958.8	957.8	956.8	955.8	954.8	954.8	954.8
172.5°	964.4	965.4	966.4	966.9	966.4	965.4	964.4	963.4	962.4	962.4	962.4
175°	969.3	970.4	971.6	972.2	971.7	970.7	969.7	968.7	967.7	967.7	967.7
177.5°	972.3	973.4	974.6	975.2	974.7	973.7	972.7	971.7	970.7	970.9	971.1
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	909.3	905.6	901.1	901.1	895.8	893.6	889.1	887.6	883.8	877.8	873.3
5°	941.6	931.8	925.8	920.6	909.3	901.1	892.8	883.8	874.8	864.3	852.3
7.5°	973.1	955.1	946.8	937.8	921.3	904.1	887.6	875.6	863.6	847.1	832.0
10°	1006.1	983.6	968.6	956.6	931.1	909.3	885.3	868.1	849.3	828.3	808.8
12.5°	1033.9	1004.6	991.9	969.3	940.1	913.8	883.8	857.6	832.8	808.0	784.0
15°	1057.1	1029.4	997.9	988.9	948.3	910.8	877.1	843.3	812.5	787.8	760.0
17.5°	1064.6	1029.4	1013.6	991.9	943.8	904.8	862.1	825.3	796.0	759.3	737.5
20°	1066.9	1033.1	1011.4	991.1	948.3	896.6	854.6	809.5	774.3	737.5	703.0
22.5°	1060.9	1021.1	1000.1	980.6	932.6	888.3	839.5	790.0	748.8	715.0	680.5
25°	1049.6	1003.1	982.9	961.8	916.1	867.3	814.0	766.8	728.5	688.0	654.2
27.5°	1034.6	981.4	958.1	936.3	891.3	845.6	795.3	746.5	703.8	661.0	629.5
30°	1015.9	954.3	933.3	904.8	861.3	817.8	772.0	723.3	675.2	634.7	600.2
32.5°	991.9	927.3	899.6	872.6	825.3	785.5	742.0	696.2	649.7	610.0	574.0
35°	970.1	896.6	865.8	838.8	786.3	744.3	708.3	665.5	624.2	583.0	550.7
37.5°	940.8	865.8	829.0	801.3	748.0	705.3	671.5	638.5	595.0	555.2	525.2
40°	910.1	827.5	793.0	765.3	709.8	663.2	631.0	601.7	566.5	529.7	498.2
42.5°	882.3	790.8	754.0	720.3	664.0	622.7	589.7	567.2	534.9	501.9	473.4
45°	847.1	751.8	712.0	676.7	622.7	577.7	546.2	528.2	504.2	471.9	447.2
47.5°	811.0	709.8	668.5	634.0	575.5	535.7	504.9	487.7	471.2	445.7	420.9
50°	763.8	665.5	628.0	588.2	530.4	489.9	464.4	447.2	434.4	416.4	395.4
52.5°	712.0	619.7	579.2	544.7	487.7	450.9	421.7	411.9	399.1	385.6	367.6
55°	657.2	570.2	531.2	497.4	444.9	407.4	383.4	372.9	363.1	352.6	340.6
57.5°	602.5	518.4	481.7	451.7	402.9	366.9	347.4	333.1	326.4	320.4	310.6
60°	534.2	462.9	434.4	407.4	359.4	326.4	307.6	297.1	291.1	288.1	283.6
62.5°	474.2	415.6	384.1	357.9	319.6	290.4	272.3	264.1	258.8	257.3	252.1
65°	410.4	360.1	335.4	312.9	279.8	253.6	238.6	228.8	225.1	224.3	224.3
67.5°	350.4	309.9	285.1	269.3	240.8	217.6	203.3	199.6	197.3	194.3	193.6
70°	294.1	261.8	240.1	226.6	201.1	183.8	172.6	166.6	166.6	164.3	162.8
72.5°	244.6	212.3	198.1	186.8	165.8	150.8	142.6	141.1	135.8	135.0	135.0
75°	191.3	167.3	157.6	147.8	132.0	121.5	114.8	111.0	108.0	108.0	108.8
77.5°	144.1	127.5	118.5	111.0	99.8	93.0	87.8	86.3	83.3	83.3	83.3
80°	102.0	93.0	86.3	80.3	72.0	66.0	63.0	60.0	60.0	59.3	60.0
82.5°	66.0	58.5	54.8	54.0	46.5	44.3	40.5	41.3	39.0	38.3	39.8
85°	38.3	34.5	30.0	28.5	25.5	22.5	21.0	21.8	21.0	20.3	21.0
87.5°	15.0	12.8	12.0	12.0	9.8	9.0	8.3	9.0	7.5	7.5	8.3
90°	8.6	7.4	6.8	6.1	4.8	3.5	2.1	0.8	2.1	3.5	4.8
92.5°	28.8	27.3	26.5	26.1	25.2	24.4	23.5	22.7	23.5	24.4	25.2
95°	53.2	51.5	50.7	50.5	50.2	49.9	49.5	49.2	49.5	49.9	50.2
97.5°	80.0	77.7	76.5	76.4	76.2	76.1	75.9	75.7	75.9	76.1	76.2
100°	109.3	107.1	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0	106.0
102.5°	143.6	142.7	142.3	141.9	141.1	140.2	139.4	138.6	139.4	140.2	141.1
105°	177.9	176.9	176.4	176.0	175.1	174.3	173.4	172.6	173.4	174.3	175.1
107.5°	214.8	213.9	213.5	213.1	212.2	211.4	210.5	209.7	210.5	211.4	212.2
110°	252.9	252.4	252.1	251.7	250.9	250.0	249.2	248.4	249.2	250.0	250.9

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	290.2	289.5	289.2	289.0	288.7	288.4	288.0	287.7	288.0	288.4	288.7
115°	329.9	329.6	329.4	329.1	328.4	327.7	327.0	326.3	327.0	327.7	328.4
117.5°	367.0	366.7	366.5	366.4	366.2	366.1	365.9	365.7	365.9	366.1	366.2
120°	406.1	405.9	405.8	405.4	404.6	403.7	402.9	402.1	402.9	403.7	404.6
122.5°	443.0	442.5	442.2	442.1	441.9	441.8	441.6	441.4	441.6	441.8	441.9
125°	481.1	480.9	480.8	480.3	479.3	478.3	477.3	476.3	477.3	478.3	479.3
127.5°	517.4	517.3	517.2	516.9	516.4	515.9	515.4	514.9	515.4	515.9	516.4
130°	553.2	552.9	552.7	552.3	551.5	550.6	549.8	549.0	549.8	550.6	551.5
132.5°	589.6	589.7	589.8	589.0	587.5	586.0	584.5	583.0	584.5	586.0	587.5
135°	624.2	624.0	623.9	623.4	622.4	621.4	620.4	619.4	620.4	621.4	622.4
137.5°	658.5	658.2	658.0	657.5	656.5	655.4	654.4	653.4	654.4	655.4	656.5
140°	690.6	690.1	689.8	689.4	688.5	687.7	686.8	686.0	686.8	687.7	688.5
142.5°	722.6	721.9	721.6	721.3	720.6	719.9	719.3	718.6	719.3	719.9	720.6
145°	754.2	753.7	753.4	753.1	752.4	751.7	751.1	750.4	751.1	751.7	752.4
147.5°	782.7	782.4	782.2	781.9	781.4	780.9	780.4	779.9	780.4	780.9	781.4
150°	809.7	809.0	808.7	808.8	808.9	809.1	809.2	809.4	809.2	809.1	808.9
152.5°	835.4	835.3	835.2	835.0	834.7	834.4	834.0	833.7	834.0	834.4	834.7
155°	858.9	858.7	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6	858.6
157.5°	880.1	879.9	879.8	880.0	880.3	880.7	881.0	881.4	881.0	880.7	880.3
160°	899.0	898.9	898.8	899.0	899.5	900.0	900.5	901.0	900.5	900.0	899.5
162.5°	916.9	916.9	916.9	917.1	917.4	917.8	918.1	918.5	918.1	917.8	917.4
165°	932.3	932.2	932.1	932.3	932.6	932.9	933.3	933.6	933.3	932.9	932.6
167.5°	944.2	944.2	944.2	944.5	945.2	945.9	946.5	947.2	946.5	945.9	945.2
170°	954.8	954.8	954.8	955.1	955.8	956.5	957.1	957.8	957.1	956.5	955.8
172.5°	962.4	962.4	962.4	962.7	963.4	964.1	964.7	965.4	964.7	964.1	963.4
175°	967.7	967.7	967.7	968.0	968.7	969.4	970.0	970.7	970.0	969.4	968.7
177.5°	971.2	971.4	971.5	971.8	972.5	973.2	973.8	974.5	973.8	973.2	972.5
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	871.8	870.3	866.6	864.3	856.8	847.8	844.8	837.3	840.3	835.0	835.0
5°	848.6	841.8	837.3	830.5	816.3	806.5	796.0	790.8	787.8	784.0	781.0
7.5°	818.5	813.3	808.8	796.0	780.3	766.8	754.0	748.8	739.0	732.3	729.3
10°	792.3	784.8	774.3	759.3	742.8	725.5	714.3	703.0	695.5	691.7	683.5
12.5°	765.3	756.3	745.0	723.3	705.3	694.7	674.5	664.0	660.2	657.2	647.5
15°	737.5	727.8	714.3	694.0	678.2	653.5	641.5	633.2	624.2	623.5	616.0
17.5°	712.8	700.8	689.5	664.7	645.2	623.5	616.7	607.7	599.5	590.5	586.7
20°	681.2	670.0	661.7	634.7	613.0	599.5	588.2	580.7	575.5	566.5	565.0
22.5°	652.7	640.7	629.5	609.2	590.5	573.2	559.7	551.4	549.2	545.4	538.7
25°	625.0	613.0	599.5	580.7	561.2	549.2	537.2	531.9	527.4	521.4	516.2
27.5°	601.7	590.5	577.7	554.4	537.9	528.9	516.2	510.2	504.2	501.2	498.9
30°	574.0	561.2	551.4	533.4	515.4	503.4	494.4	489.2	483.9	480.9	479.4
32.5°	546.9	534.9	528.2	508.7	494.4	480.2	473.4	469.7	466.7	463.7	460.7
35°	525.2	513.2	502.7	484.7	470.4	460.7	455.4	449.4	447.2	444.2	444.2
37.5°	498.2	489.2	478.7	461.4	448.7	441.2	436.7	429.2	428.4	426.9	424.7
40°	474.9	465.9	456.2	441.2	429.9	420.9	414.9	411.1	408.9	407.4	405.9
42.5°	450.2	440.4	435.9	418.6	408.9	399.9	396.9	393.1	392.4	389.4	385.6
45°	426.2	417.9	408.9	396.1	387.9	380.4	375.9	372.9	369.1	368.4	366.1
47.5°	405.1	395.4	387.1	375.1	366.1	360.1	356.4	352.6	349.6	347.4	345.1
50°	378.1	370.6	363.9	351.1	343.6	337.6	332.4	329.4	326.4	326.4	326.4
52.5°	351.9	345.1	339.1	330.1	321.1	315.9	309.9	307.6	306.1	303.9	306.1
55°	326.4	319.6	313.6	306.9	296.4	291.9	285.9	283.6	284.4	284.4	286.6
57.5°	299.4	294.1	290.4	282.1	272.3	267.8	264.1	261.8	261.8	264.8	265.6
60°	273.1	267.8	261.1	253.6	247.6	242.3	240.1	240.8	240.8	242.3	246.1
62.5°	243.8	240.8	237.1	226.6	222.8	219.1	216.1	218.3	217.6	221.3	226.6
65°	216.8	213.8	208.6	203.3	198.8	195.1	194.3	195.1	196.6	200.3	206.3
67.5°	186.8	186.8	182.3	177.8	174.1	170.3	171.1	171.8	173.3	177.8	186.8
70°	162.1	159.1	154.6	151.6	148.6	147.1	145.6	148.6	153.1	156.1	162.8
72.5°	135.0	132.8	129.0	126.0	125.3	123.8	123.0	124.5	129.0	134.3	141.8
75°	106.5	107.3	105.0	102.8	102.8	100.5	102.0	102.0	106.5	111.8	117.8
77.5°	82.5	81.8	81.0	79.5	78.8	78.8	78.8	80.3	84.8	87.8	93.8
80°	58.5	59.3	57.0	57.8	57.0	57.8	57.8	60.8	63.0	66.8	71.3
82.5°	39.0	39.0	37.5	38.3	38.3	38.3	39.0	40.5	43.5	46.5	49.5
85°	21.8	22.5	21.0	22.5	22.5	22.5	23.3	24.0	26.3	27.0	30.0
87.5°	8.3	9.8	9.8	8.3	9.0	9.8	10.5	9.8	11.3	12.8	13.5
90°	6.1	6.8	7.4	8.6	9.7	10.9	12.1	12.9	13.8	14.6	15.5
92.5°	26.1	26.5	27.3	28.8	30.3	31.8	33.3	34.5	35.7	36.8	38.0
95°	50.5	50.7	51.5	53.2	54.9	56.6	58.3	59.5	60.7	61.8	63.0
97.5°	76.4	76.5	77.7	80.0	82.4	84.7	87.1	88.1	89.1	90.1	91.1
100°	106.0	106.0	107.1	109.3	111.4	113.6	115.8	117.3	118.9	120.4	121.9
102.5°	141.9	142.3	142.7	143.6	144.4	145.3	146.1	147.8	149.5	151.2	152.9
105°	176.0	176.4	176.9	177.9	179.0	180.0	181.0	182.0	183.0	184.0	185.0
107.5°	213.1	213.5	213.9	214.8	215.6	216.5	217.3	217.8	218.3	218.8	219.3
110°	251.7	252.1	252.4	252.9	253.4	253.9	254.4	254.9	255.4	255.9	256.4

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	289.0	289.2	289.5	290.2	290.9	291.6	292.3	292.5	292.6	292.8	292.9
115°	329.1	329.4	329.6	329.9	330.2	330.6	330.9	330.7	330.5	330.4	330.2
117.5°	366.4	366.5	366.7	367.0	367.3	367.7	368.0	368.2	368.3	368.5	368.6
120°	405.4	405.8	405.9	406.1	406.2	406.4	406.6	406.6	406.6	406.6	406.6
122.5°	442.1	442.2	442.5	443.0	443.5	444.0	444.5	444.3	444.1	444.0	443.8
125°	480.3	480.8	480.9	481.1	481.2	481.4	481.6	481.2	480.9	480.5	480.2
127.5°	516.9	517.2	517.3	517.4	517.6	517.7	517.9	517.7	517.6	517.4	517.3
130°	552.3	552.7	552.9	553.2	553.6	553.9	554.3	554.1	553.9	553.8	553.6
132.5°	589.0	589.8	589.7	589.6	589.4	589.3	589.1	588.9	588.7	588.6	588.4
135°	623.4	623.9	624.0	624.2	624.3	624.5	624.7	624.7	624.7	624.7	624.7
137.5°	657.5	658.0	658.2	658.5	658.8	659.2	659.5	659.7	659.9	660.0	660.2
140°	689.4	689.8	690.1	690.6	691.1	691.6	692.1	692.4	692.8	693.1	693.4
142.5°	721.3	721.6	721.9	722.6	723.3	723.9	724.6	724.8	725.0	725.1	725.3
145°	753.1	753.4	753.7	754.2	754.7	755.2	755.7	755.7	755.7	755.7	755.7
147.5°	781.9	782.2	782.4	782.7	783.0	783.4	783.7	784.2	784.7	785.2	785.7
150°	808.8	808.7	809.0	809.7	810.4	811.0	811.7	811.7	811.7	811.7	811.7
152.5°	835.0	835.2	835.3	835.4	835.6	835.7	835.9	836.4	836.9	837.4	837.9
155°	858.6	858.6	858.7	858.9	859.0	859.2	859.4	860.1	860.7	861.4	862.1
157.5°	880.0	879.8	879.9	880.1	880.2	880.4	880.6	881.3	881.9	882.6	883.3
160°	899.0	898.8	898.9	899.0	899.2	899.3	899.5	900.2	900.9	901.6	902.3
162.5°	917.1	916.9	916.9	916.9	916.9	916.9	916.9	917.7	918.6	919.4	920.3
165°	932.3	932.1	932.2	932.3	932.5	932.6	932.8	933.5	934.2	934.9	935.6
167.5°	944.5	944.2	944.2	944.2	944.2	944.2	944.2	945.2	946.2	947.2	948.2
170°	955.1	954.8	954.8	954.8	954.8	954.8	954.8	955.8	956.8	957.8	958.8
172.5°	962.7	962.4	962.4	962.4	962.4	962.4	962.4	963.4	964.4	965.4	966.4
175°	968.0	967.7	967.7	967.7	967.7	967.7	967.7	968.7	969.7	970.7	971.7
177.5°	971.8	971.5	971.4	971.2	971.1	970.9	970.7	971.7	972.7	973.7	974.7
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	838.0	832.8	832.0	833.5	830.5	835.0	833.5	835.0	831.3	835.0	832.8
5°	780.3	778.8	775.8	772.0	772.8	773.5	777.3	773.5	776.5	777.3	781.0
7.5°	726.3	723.3	725.5	724.0	717.3	715.8	717.3	719.5	724.0	727.0	729.3
10°	682.7	681.2	678.2	676.0	672.2	670.0	673.0	670.0	676.0	681.2	681.2
12.5°	649.7	643.7	640.0	639.2	631.0	632.5	635.5	637.7	644.5	647.5	647.5
15°	615.2	610.7	609.2	606.2	603.2	606.2	604.7	607.0	610.0	613.0	614.5
17.5°	585.2	584.5	585.2	577.7	580.0	576.2	577.0	580.7	578.5	580.7	585.2
20°	558.2	559.7	557.4	554.4	554.4	549.9	555.2	553.7	554.4	558.9	565.7
22.5°	537.9	537.2	534.9	532.7	529.7	530.4	531.2	529.7	535.7	539.4	540.2
25°	516.2	514.7	513.9	511.7	508.7	511.7	510.9	511.7	513.2	519.2	514.7
27.5°	495.9	492.9	494.4	492.2	491.4	492.2	492.2	492.9	494.4	495.2	495.9
30°	478.7	475.7	474.9	473.4	472.7	473.4	474.9	473.4	479.4	478.7	478.7
32.5°	459.9	457.7	456.2	456.2	455.4	454.7	455.4	456.2	460.7	457.7	460.7
35°	441.9	440.4	440.4	438.9	438.2	438.2	438.2	441.2	439.7	441.9	441.9
37.5°	424.7	424.7	423.9	422.4	421.7	422.4	421.7	423.2	422.4	423.2	423.9
40°	406.6	405.1	404.4	404.4	402.1	399.9	402.1	402.1	402.9	405.1	405.9
42.5°	384.9	385.6	385.6	382.6	382.6	382.6	383.4	384.1	384.1	385.6	385.6
45°	366.1	364.6	364.6	364.6	363.1	363.9	365.4	365.4	365.4	365.4	363.9
47.5°	345.1	345.1	345.9	345.9	348.1	347.4	347.4	346.6	345.1	345.1	345.9
50°	325.6	327.9	328.6	328.6	329.4	330.1	330.1	328.6	327.9	325.6	325.6
52.5°	306.9	308.4	309.9	312.1	313.6	312.9	312.9	311.4	308.4	307.6	306.9
55°	286.6	288.9	291.9	294.1	296.4	297.1	297.1	294.1	291.1	287.4	287.4
57.5°	267.8	270.1	275.3	277.6	280.6	280.6	279.1	276.8	272.3	269.3	267.1
60°	249.1	252.8	256.6	261.1	264.8	265.6	263.3	260.3	255.1	251.3	248.3
62.5°	228.8	232.6	240.1	244.6	247.6	247.6	247.6	243.8	237.1	231.8	227.3
65°	209.3	213.1	219.8	225.8	228.1	230.3	228.1	224.3	219.1	213.1	208.6
67.5°	189.1	193.6	200.3	204.8	207.8	210.1	208.6	205.6	198.8	190.6	187.6
70°	166.6	168.8	178.6	183.1	187.6	189.1	187.6	183.1	176.3	167.3	164.3
72.5°	145.6	147.8	156.8	160.6	164.3	165.8	163.6	160.6	154.6	146.3	142.6
75°	121.5	125.3	129.8	135.8	140.3	141.8	139.5	137.3	129.8	124.5	121.5
77.5°	96.0	99.8	105.8	111.0	115.5	114.8	111.8	112.5	104.3	98.3	96.0
80°	72.8	75.8	80.3	84.8	87.0	87.0	86.3	83.3	80.3	75.8	72.0
82.5°	50.3	54.0	57.8	60.8	60.8	61.5	60.0	59.3	56.3	52.5	51.8
85°	30.0	30.8	33.8	33.8	36.8	35.3	34.5	36.8	33.8	31.5	30.8
87.5°	13.5	12.8	13.5	13.5	12.8	14.3	14.3	13.5	14.3	13.5	13.5
90°	15.9	16.2	16.7	17.2	17.7	18.2	17.7	17.2	16.7	16.2	15.9
92.5°	38.6	38.8	39.1	39.4	39.8	40.1	39.8	39.4	39.1	38.8	38.6
95°	63.6	63.8	64.1	64.4	64.8	65.1	64.8	64.4	64.1	63.8	63.6
97.5°	91.6	91.7	91.9	92.0	92.2	92.4	92.2	92.0	91.9	91.7	91.6
100°	122.7	122.9	123.2	123.5	123.9	124.2	123.9	123.5	123.2	122.9	122.7
102.5°	153.7	154.0	154.5	155.0	155.5	156.0	155.5	155.0	154.5	154.0	153.7
105°	185.5	185.8	186.3	186.8	187.3	187.8	187.3	186.8	186.3	185.8	185.5
107.5°	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6	219.6
110°	256.7	256.6	256.4	256.3	256.1	255.9	256.1	256.3	256.4	256.6	256.7

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	293.0	292.8	292.5	292.2	291.8	291.5	291.8	292.2	292.5	292.8	293.0
115°	330.1	330.0	329.9	329.7	329.6	329.4	329.6	329.7	329.9	330.0	330.1
117.5°	368.7	368.4	367.7	367.0	366.4	365.7	366.4	367.0	367.7	368.4	368.7
120°	406.6	406.3	405.6	404.9	404.3	403.6	404.3	404.9	405.6	406.3	406.6
122.5°	443.7	443.4	442.9	442.4	441.9	441.4	441.9	442.4	442.9	443.4	443.7
125°	480.0	479.9	479.8	479.6	479.5	479.3	479.5	479.6	479.8	479.9	480.0
127.5°	517.2	517.0	516.7	516.3	516.0	515.6	516.0	516.3	516.7	517.0	517.2
130°	553.5	553.3	553.0	552.7	552.3	552.0	552.3	552.7	553.0	553.3	553.5
132.5°	588.3	588.1	587.6	587.1	586.6	586.1	586.6	587.1	587.6	588.1	588.3
135°	624.7	624.4	623.7	623.0	622.3	621.6	622.3	623.0	623.7	624.4	624.7
137.5°	660.3	659.9	659.0	658.2	657.3	656.5	657.3	658.2	659.0	659.9	660.3
140°	693.6	693.2	692.3	691.5	690.6	689.8	690.6	691.5	692.3	693.2	693.6
142.5°	725.4	725.0	724.1	723.3	722.4	721.6	722.4	723.3	724.1	725.0	725.4
145°	755.7	755.4	754.9	754.4	753.9	753.4	753.9	754.4	754.9	755.4	755.7
147.5°	785.9	785.2	783.9	782.6	781.2	779.9	781.2	782.6	783.9	785.2	785.9
150°	811.7	811.5	811.2	810.9	810.5	810.2	810.5	810.9	811.2	811.5	811.7
152.5°	838.2	837.9	837.2	836.5	835.9	835.2	835.9	836.5	837.2	837.9	838.2
155°	862.4	862.0	861.1	860.3	859.4	858.6	859.4	860.3	861.1	862.0	862.4
157.5°	883.6	883.0	881.8	880.7	879.5	878.3	879.5	880.7	881.8	883.0	883.6
160°	902.6	902.2	901.3	900.5	899.6	898.8	899.6	900.5	901.3	902.2	902.6
162.5°	920.7	920.2	919.2	918.2	917.2	916.2	917.2	918.2	919.2	920.2	920.7
165°	935.9	935.4	934.4	933.3	932.3	931.3	932.3	933.3	934.4	935.4	935.9
167.5°	948.7	948.2	947.2	946.2	945.2	944.2	945.2	946.2	947.2	948.2	948.7
170°	959.3	958.7	957.5	956.4	955.2	954.0	955.2	956.4	957.5	958.7	959.3
172.5°	966.9	966.4	965.4	964.4	963.4	962.4	963.4	964.4	965.4	966.4	966.9
175°	972.2	971.6	970.4	969.3	968.1	966.9	968.1	969.3	970.4	971.6	972.2
177.5°	975.2	974.6	973.4	972.3	971.1	969.9	971.1	972.3	973.4	974.6	975.2
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8	883.8
2.5°	839.5	835.0	840.3	833.5	835.0	843.3	842.6	850.1	854.6	853.8	857.6
5°	784.0	784.0	786.3	785.5	793.0	799.8	808.8	816.3	824.5	829.0	834.3
7.5°	729.3	736.8	738.3	742.0	751.0	762.3	771.3	782.5	794.5	802.8	808.8
10°	684.2	690.2	696.2	699.2	709.0	724.0	736.8	754.8	769.8	778.8	787.0
12.5°	644.5	651.2	654.2	667.7	674.5	684.2	702.3	721.8	738.3	748.0	754.8
15°	616.0	619.7	626.5	634.7	641.5	653.5	668.5	690.2	706.0	714.3	737.5
17.5°	592.0	596.5	600.2	604.0	614.5	627.2	641.5	660.2	680.5	694.7	706.8
20°	567.2	569.5	574.0	580.0	587.5	599.5	612.2	631.7	649.7	661.0	676.7
22.5°	537.9	544.7	549.2	553.7	562.0	575.5	587.5	601.7	624.2	637.0	653.5
25°	520.7	523.7	526.7	531.9	537.9	549.9	563.5	578.5	596.5	610.0	624.2
27.5°	498.2	502.7	506.4	513.2	516.9	526.7	539.4	554.4	576.2	587.5	599.5
30°	479.4	483.9	486.9	489.9	495.2	505.7	517.7	529.7	549.9	564.2	576.2
32.5°	460.7	465.2	468.9	471.2	476.4	483.2	492.9	507.9	525.2	534.9	550.7
35°	444.2	444.2	448.7	451.7	456.2	462.2	471.2	482.4	500.4	513.2	527.4
37.5°	425.4	426.2	429.9	432.2	436.7	442.7	451.7	462.2	477.2	486.9	501.2
40°	405.9	408.1	409.6	413.4	418.6	420.9	429.9	441.9	456.9	465.9	477.9
42.5°	386.4	387.9	391.6	394.6	399.1	402.9	408.9	420.2	431.4	444.9	454.7
45°	364.6	368.4	370.6	375.9	378.1	381.9	387.9	396.9	410.4	418.6	429.9
47.5°	345.9	347.4	348.9	355.6	360.1	362.4	368.4	373.6	387.9	395.4	405.9
50°	325.6	325.6	327.9	330.9	336.1	340.6	345.9	351.9	363.1	370.6	381.1
52.5°	306.9	304.6	306.1	307.6	312.9	317.4	322.6	330.9	341.4	345.9	354.9
55°	286.6	282.9	285.1	287.4	288.9	294.9	300.9	306.1	314.4	321.1	329.4
57.5°	264.8	264.1	262.6	263.3	267.1	270.8	275.3	282.1	291.9	297.1	301.6
60°	245.3	240.8	239.3	240.8	243.1	245.3	251.3	257.3	265.6	270.8	276.1
62.5°	225.1	220.6	217.6	215.3	217.6	222.8	226.6	231.1	237.8	243.8	248.3
65°	205.6	198.8	195.8	194.3	193.6	197.3	200.3	206.3	212.3	214.6	219.8
67.5°	183.8	177.8	174.1	171.8	171.8	171.8	174.8	180.8	186.8	187.6	192.8
70°	162.1	155.3	151.6	148.6	147.1	148.6	152.3	153.1	158.3	159.8	162.8
72.5°	138.8	132.8	128.3	124.5	125.3	126.8	126.8	128.3	131.3	135.0	135.0
75°	117.0	108.8	106.5	103.5	102.0	102.0	102.0	105.0	107.3	110.3	109.5
77.5°	92.3	87.8	83.3	81.8	79.5	78.8	80.3	80.3	81.8	84.0	84.8
80°	71.3	66.0	63.0	61.5	58.5	57.8	58.5	58.5	60.8	60.0	60.8
82.5°	49.5	45.8	43.5	41.3	39.8	40.5	39.8	39.8	40.5	39.8	39.8
85°	28.5	27.8	26.3	25.5	24.8	23.3	24.8	24.0	23.3	22.5	24.0
87.5°	13.5	12.8	12.8	11.3	11.3	10.5	11.3	11.3	10.5	10.5	10.5
90°	15.5	14.6	13.8	12.9	12.1	10.9	9.7	8.6	7.4	6.8	6.1
92.5°	38.0	36.8	35.7	34.5	33.3	31.8	30.3	28.8	27.3	26.5	26.1
95°	63.0	61.8	60.7	59.5	58.3	56.6	54.9	53.2	51.5	50.7	50.5
97.5°	91.1	90.1	89.1	88.1	87.1	84.7	82.4	80.0	77.7	76.5	76.4
100°	121.9	120.4	118.9	117.3	115.8	113.6	111.4	109.3	107.1	106.0	106.0
102.5°	152.9	151.2	149.5	147.8	146.1	145.3	144.4	143.6	142.7	142.3	141.9
105°	185.0	184.0	183.0	182.0	181.0	180.0	179.0	177.9	176.9	176.4	176.0
107.5°	219.3	218.8	218.3	217.8	217.3	216.5	215.6	214.8	213.9	213.5	213.1
110°	256.4	255.9	255.4	254.9	254.4	253.9	253.4	252.9	252.4	252.1	251.7

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	292.9	292.8	292.6	292.5	292.3	291.6	290.9	290.2	289.5	289.2	289.0
115°	330.2	330.4	330.5	330.7	330.9	330.6	330.2	329.9	329.6	329.4	329.1
117.5°	368.6	368.5	368.3	368.2	368.0	367.7	367.3	367.0	366.7	366.5	366.4
120°	406.6	406.6	406.6	406.6	406.6	406.4	406.2	406.1	405.9	405.8	405.4
122.5°	443.8	444.0	444.1	444.3	444.5	444.0	443.5	443.0	442.5	442.2	442.1
125°	480.2	480.5	480.9	481.2	481.6	481.4	481.2	481.1	480.9	480.8	480.3
127.5°	517.3	517.4	517.6	517.7	517.9	517.7	517.6	517.4	517.3	517.2	516.9
130°	553.6	553.8	553.9	554.1	554.3	553.9	553.6	553.2	552.9	552.7	552.3
132.5°	588.4	588.6	588.7	588.9	589.1	589.3	589.4	589.6	589.7	589.8	589.0
135°	624.7	624.7	624.7	624.7	624.7	624.5	624.3	624.2	624.0	623.9	623.4
137.5°	660.2	660.0	659.9	659.7	659.5	659.2	658.8	658.5	658.2	658.0	657.5
140°	693.4	693.1	692.8	692.4	692.1	691.6	691.1	690.6	690.1	689.8	689.4
142.5°	725.3	725.1	725.0	724.8	724.6	723.9	723.3	722.6	721.9	721.6	721.3
145°	755.7	755.7	755.7	755.7	755.7	755.2	754.7	754.2	753.7	753.4	753.1
147.5°	785.7	785.2	784.7	784.2	783.7	783.4	783.0	782.7	782.4	782.2	781.9
150°	811.7	811.7	811.7	811.7	811.7	811.0	810.4	809.7	809.0	808.7	808.8
152.5°	837.9	837.4	836.9	836.4	835.9	835.7	835.6	835.4	835.3	835.2	835.0
155°	862.1	861.4	860.7	860.1	859.4	859.2	859.0	858.9	858.7	858.6	858.6
157.5°	883.3	882.6	881.9	881.3	880.6	880.4	880.2	880.1	879.9	879.8	880.0
160°	902.3	901.6	900.9	900.2	899.5	899.3	899.2	899.0	898.9	898.8	899.0
162.5°	920.3	919.4	918.6	917.7	916.9	916.9	916.9	916.9	916.9	916.9	917.1
165°	935.6	934.9	934.2	933.5	932.8	932.6	932.5	932.3	932.2	932.1	932.3
167.5°	948.2	947.2	946.2	945.2	944.2	944.2	944.2	944.2	944.2	944.2	944.5
170°	958.8	957.8	956.8	955.8	954.8	954.8	954.8	954.8	954.8	954.8	955.1
172.5°	966.4	965.4	964.4	963.4	962.4	962.4	962.4	962.4	962.4	962.4	962.7
175°	971.7	970.7	969.7	968.7	967.7	967.7	967.7	967.7	967.7	967.7	968.0
177.5°	974.7	973.7	972.7	971.7	970.7	970.9	971.1	971.2	971.4	971.5	971.8
180°	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0	973.0

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.8	883.8	883.8	883.8
2.5°	862.8	870.3	875.6	885.3
5°	843.3	856.8	869.6	883.1
7.5°	823.8	839.5	859.8	877.1
10°	802.0	822.3	846.3	869.6
12.5°	780.3	804.3	830.5	861.3
15°	754.0	784.8	815.5	848.6
17.5°	730.8	762.3	795.3	836.5
20°	704.5	739.0	775.0	817.0
22.5°	681.2	719.5	757.0	801.3
25°	655.0	692.5	733.8	781.0
27.5°	633.2	667.7	708.3	759.3
30°	607.0	644.5	685.0	736.0
32.5°	582.2	618.2	661.0	711.3
35°	556.7	593.5	631.7	679.7
37.5°	532.7	564.2	602.5	648.2
40°	505.7	540.2	574.7	610.7
42.5°	480.9	512.4	544.7	573.2
45°	453.2	480.2	510.9	534.2
47.5°	427.7	451.7	475.7	493.7
50°	402.1	420.9	438.9	454.7
52.5°	372.1	393.1	402.9	412.6
55°	345.1	357.1	366.1	375.9
57.5°	318.9	324.1	328.6	337.6
60°	284.4	290.4	295.6	302.4
62.5°	254.3	257.3	258.8	265.6
65°	225.8	225.1	228.8	232.6
67.5°	195.1	194.3	198.1	199.6
70°	165.1	164.3	165.1	168.8
72.5°	136.5	136.5	137.3	138.8
75°	110.3	110.3	111.0	112.5
77.5°	83.3	84.8	84.0	87.0
80°	60.8	59.3	60.8	62.3
82.5°	39.8	41.3	41.3	39.8
85°	22.5	22.5	22.5	22.5
87.5°	9.8	9.8	10.5	11.3
90°	4.8	3.5	2.1	0.8
92.5°	25.2	24.4	23.5	22.7
95°	50.2	49.9	49.5	49.2
97.5°	76.2	76.1	75.9	75.7
100°	106.0	106.0	106.0	106.0
102.5°	141.1	140.2	139.4	138.6
105°	175.1	174.3	173.4	172.6
107.5°	212.2	211.4	210.5	209.7
110°	250.9	250.0	249.2	248.4

TEST NUMBER: P1028151

CATALOG NUMBER: S125DIP-B610D850UB27-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	288.7	288.4	288.0	287.7
115°	328.4	327.7	327.0	326.3
117.5°	366.2	366.1	365.9	365.7
120°	404.6	403.7	402.9	402.1
122.5°	441.9	441.8	441.6	441.4
125°	479.3	478.3	477.3	476.3
127.5°	516.4	515.9	515.4	514.9
130°	551.5	550.6	549.8	549.0
132.5°	587.5	586.0	584.5	583.0
135°	622.4	621.4	620.4	619.4
137.5°	656.5	655.4	654.4	653.4
140°	688.5	687.7	686.8	686.0
142.5°	720.6	719.9	719.3	718.6
145°	752.4	751.7	751.1	750.4
147.5°	781.4	780.9	780.4	779.9
150°	808.9	809.1	809.2	809.4
152.5°	834.7	834.4	834.0	833.7
155°	858.6	858.6	858.6	858.6
157.5°	880.3	880.7	881.0	881.4
160°	899.5	900.0	900.5	901.0
162.5°	917.4	917.8	918.1	918.5
165°	932.6	932.9	933.3	933.6
167.5°	945.2	945.9	946.5	947.2
170°	955.8	956.5	957.1	957.8
172.5°	963.4	964.1	964.7	965.4
175°	968.7	969.4	970.0	970.7
177.5°	972.5	973.2	973.8	974.5
180°	973.0	973.0	973.0	973.0

(END OF REPORT)