

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028434

Luminaire Tested: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028434
REPORT IS A COMBINATION OF REPORTS P1004949 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7873.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	77	72	84	78	72	68	67	63	60	57	54	51	47	45	44
3	83	74	66	61	77	69	62	57	59	54	50	50	47	44	42	40	38
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	45	65	55	47	42	47	42	38	41	36	33	34	31	29
6	64	52	45	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	47	40	34	55	44	37	32	39	33	29	34	29	26	29	25	23
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20
9	52	39	32	27	48	37	30	26	33	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	2.0
10°-20°	456.8	5.8
20°-30°	724.4	9.2
30°-40°	875.3	11.1
40°-50°	779.3	9.9
50°-60°	597.6	7.6
60°-70°	388.1	4.9
70°-80°	188.4	2.4
80°-90°	46.2	0.6
90°-100°	354.6	4.5
100°-110°	764.6	9.7
110°-120°	712.8	9.1
120°-130°	577.3	7.3
130°-140°	463.6	5.9
140°-150°	349.6	4.4
150°-160°	246.2	3.1
160°-170°	145.1	1.8
170°-180°	47.2	0.6
0°-30°	1337.0	17.0
0°-40°	2212.3	28.1
0°-60°	3589.2	45.6
0°-90°	4211.9	53.5
90°-120°	1832.0	23.3
90°-150°	3222.5	40.9
90°-180°	3661.0	46.5
0°-180°	7873.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	1	23	1	23	1	5
95°	32	231	32	231	32	34
105°	111	1302	111	1302	111	117
115°	198	1450	198	1450	198	195
125°	275	1143	275	1143	275	244
135°	322	949	322	949	322	250
145°	375	749	375	749	375	235
155°	428	628	428	628	428	197
165°	468	550	468	550	468	132
175°	486	494	486	494	486	46
180°	487	487	487	487	487	

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	1.0	2.0	3.9	5.9	7.9	8.9	9.8	10.8	12.8	13.8	15.7
92.5°	14.7	17.7	27.5	42.3	62.9	80.6	98.3	165.1	277.1	399.0	392.1
95°	32.4	33.4	41.3	52.1	73.7	95.8	117.9	223.1	439.3	710.5	870.7
97.5°	50.1	51.1	57.0	67.8	87.5	103.7	119.9	192.6	358.7	651.5	940.5
100°	68.8	70.8	74.7	85.5	104.2	118.9	133.6	190.6	318.4	566.0	887.4
102.5°	89.4	90.4	93.4	105.2	121.9	136.2	150.4	199.5	301.7	501.2	794.0
105°	111.0	111.0	116.0	125.8	141.5	155.2	169.0	212.3	299.7	463.8	712.5
107.5°	131.7	133.6	138.6	146.4	163.1	175.4	187.7	230.0	306.6	444.2	651.5
110°	154.3	156.3	160.2	169.0	183.8	196.6	209.3	249.6	317.4	436.3	611.3

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	176.9	178.9	181.8	190.6	205.4	217.7	230.0	268.3	331.2	436.3	587.7
115°	198.5	200.5	203.4	212.3	227.0	239.3	251.6	287.9	344.9	439.3	571.9
117.5°	218.2	221.1	224.1	232.9	249.6	261.4	273.2	307.6	360.7	444.2	563.1
120°	237.8	240.8	244.7	253.5	270.2	282.5	294.8	329.2	376.4	452.1	557.2
122.5°	258.5	260.4	263.4	272.2	290.9	303.2	315.5	349.8	394.1	458.9	552.3
125°	275.2	277.1	282.0	290.9	309.6	322.4	335.1	367.5	409.8	466.8	548.4
127.5°	288.9	291.9	297.8	308.6	328.2	341.0	353.8	385.2	424.5	475.6	546.4
130°	301.7	304.6	312.5	325.3	345.9	358.7	371.5	401.9	439.3	483.5	544.4
132.5°	311.5	315.5	325.3	340.0	361.6	374.4	387.2	417.7	452.1	492.3	544.4
135°	322.3	326.3	338.1	353.8	374.4	387.6	400.9	431.4	463.8	500.2	544.4
137.5°	336.1	339.0	349.8	365.6	386.2	400.0	413.7	441.2	472.7	508.1	545.4
140°	347.9	350.8	362.6	378.3	397.0	410.3	423.6	452.1	481.5	513.0	546.4
142.5°	361.6	363.6	374.4	390.1	407.8	420.1	432.4	458.9	486.4	515.9	547.4
145°	375.4	377.4	387.2	400.9	418.6	429.9	441.2	466.8	491.4	517.9	546.4
147.5°	390.1	391.1	400.0	412.7	428.5	438.8	449.1	471.7	494.3	518.9	544.4
150°	402.9	404.9	411.8	424.5	438.3	446.6	455.0	476.6	497.3	518.9	541.5
152.5°	416.7	417.7	423.6	434.4	447.1	454.5	461.9	481.5	499.2	517.9	537.5
155°	428.5	428.5	434.4	444.2	454.0	460.9	467.8	484.5	500.2	515.9	532.6
157.5°	439.3	439.3	444.2	453.0	461.9	467.3	472.7	487.4	501.2	514.0	527.7
160°	450.1	449.1	453.0	459.9	467.8	472.2	476.6	489.4	501.2	511.0	522.8
162.5°	458.9	457.9	461.9	467.8	473.7	477.1	480.5	491.4	500.2	508.1	516.9
165°	467.8	465.8	468.8	473.7	477.6	480.6	483.5	491.4	499.2	505.1	511.0
167.5°	473.7	472.7	474.7	477.6	480.5	482.5	484.5	491.4	497.3	500.2	505.1
170°	479.6	478.6	479.6	481.5	483.5	485.0	486.4	491.4	495.3	497.3	500.2
172.5°	483.5	481.5	482.5	484.5	485.5	486.0	486.4	490.4	493.3	493.3	494.3
175°	486.4	484.5	485.5	486.4	486.4	486.4	486.4	489.4	491.4	490.4	490.4
177.5°	488.4	486.4	486.4	487.4	486.4	486.4	486.4	488.4	489.4	487.4	487.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	16.7	17.7	18.7	19.7	20.6	21.6	21.6	21.6	22.6	22.6	22.6
92.5°	316.4	213.2	153.3	114.0	104.6	95.3	79.6	76.7	74.7	72.7	74.7
95°	852.0	706.6	557.2	436.3	395.0	353.8	284.0	254.5	246.7	230.9	246.7
97.5°	1064.3	1013.2	894.3	772.4	713.4	654.5	595.5	544.4	517.9	506.1	517.9
100°	1133.1	1208.7	1160.6	1059.4	1008.3	957.2	889.4	818.6	782.2	766.5	782.2
102.5°	1091.8	1274.6	1323.7	1288.3	1257.8	1227.4	1153.7	1108.5	1068.2	1057.4	1068.2
105°	994.5	1230.4	1365.0	1408.2	1402.8	1397.4	1366.0	1333.5	1313.9	1302.1	1313.9
107.5°	902.1	1140.0	1317.8	1422.0	1443.6	1465.2	1474.1	1469.2	1459.3	1449.5	1459.3
110°	825.5	1037.7	1224.5	1363.0	1404.8	1446.6	1490.8	1509.5	1516.3	1516.3	1516.3

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	768.5	957.2	1132.1	1272.6	1323.7	1374.8	1444.6	1480.0	1499.6	1508.5	1499.6
115°	730.2	892.3	1044.6	1179.3	1232.8	1286.4	1363.0	1410.2	1437.7	1450.5	1437.7
117.5°	704.6	847.1	981.7	1099.7	1150.3	1200.9	1278.5	1327.7	1355.2	1363.0	1355.2
120°	684.0	811.7	929.7	1037.7	1081.0	1124.2	1197.0	1244.1	1270.7	1278.5	1270.7
122.5°	666.3	785.2	892.3	985.7	1025.5	1065.3	1128.2	1170.4	1197.0	1203.8	1197.0
125°	650.6	759.6	859.9	945.4	980.8	1016.1	1071.2	1111.5	1133.1	1142.9	1133.1
127.5°	635.8	733.1	828.4	909.0	942.4	975.8	1026.0	1062.3	1083.0	1086.9	1083.0
130°	621.1	708.5	795.0	871.7	903.6	935.5	984.7	1017.1	1036.8	1042.7	1036.8
132.5°	609.3	684.0	763.6	831.4	861.8	892.3	941.4	973.9	991.6	998.4	991.6
135°	600.4	663.3	731.1	794.0	822.0	850.1	893.3	925.7	943.4	949.3	943.4
137.5°	591.6	644.7	701.7	755.7	780.2	804.8	844.2	874.6	891.3	898.2	891.3
140°	585.7	629.9	676.1	721.3	742.0	762.6	798.9	824.5	839.2	844.2	839.2
142.5°	580.8	617.1	654.5	691.8	709.0	726.2	755.7	776.3	790.1	794.0	790.1
145°	575.9	606.3	636.8	667.3	680.6	693.8	717.4	734.1	744.9	748.8	744.9
147.5°	571.0	595.5	621.1	645.6	656.0	666.3	685.9	699.7	706.6	708.5	706.6
150°	565.1	586.7	608.3	627.0	635.8	644.7	659.4	671.2	675.1	676.1	675.1
152.5°	558.2	576.9	595.5	612.2	618.6	625.0	636.8	645.6	649.6	650.6	649.6
155°	550.3	567.0	582.8	596.5	601.9	607.3	617.1	624.0	627.0	628.0	627.0
157.5°	543.4	557.2	571.0	581.8	586.2	590.6	598.5	604.4	607.3	607.3	607.3
160°	534.6	547.4	557.2	567.0	570.4	573.9	580.8	585.7	587.7	586.7	587.7
162.5°	526.7	536.6	545.4	553.3	556.2	559.2	564.1	568.0	568.0	568.0	568.0
165°	518.9	526.7	533.6	539.5	542.0	544.4	548.4	550.3	550.3	550.3	550.3
167.5°	511.0	516.9	521.8	526.7	528.7	530.7	532.6	534.6	533.6	533.6	533.6
170°	504.1	509.0	512.0	514.9	515.9	516.9	518.9	519.9	519.9	518.9	519.9
172.5°	497.3	500.2	503.2	505.1	505.6	506.1	506.1	508.1	506.1	505.1	506.1
175°	491.4	494.3	494.3	496.3	496.3	496.3	496.3	497.3	495.3	494.3	495.3
177.5°	488.4	489.4	490.4	490.4	490.4	490.4	489.4	490.4	487.4	487.4	487.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	21.6	21.6	21.6	20.6	19.7	18.7	17.7	16.7	15.7	13.8	12.8
92.5°	76.7	79.6	95.3	104.6	114.0	153.3	213.2	316.4	392.1	399.0	277.1
95°	254.5	284.0	353.8	395.0	436.3	557.2	706.6	852.0	870.7	710.5	439.3
97.5°	544.4	595.5	654.5	713.4	772.4	894.3	1013.2	1064.3	940.5	651.5	358.7
100°	818.6	889.4	957.2	1008.3	1059.4	1160.6	1208.7	1133.1	887.4	566.0	318.4
102.5°	1108.5	1153.7	1227.4	1257.8	1288.3	1323.7	1274.6	1091.8	794.0	501.2	301.7
105°	1333.5	1366.0	1397.4	1402.8	1408.2	1365.0	1230.4	994.5	712.5	463.8	299.7
107.5°	1469.2	1474.1	1465.2	1443.6	1422.0	1317.8	1140.0	902.1	651.5	444.2	306.6
110°	1509.5	1490.8	1446.6	1404.8	1363.0	1224.5	1037.7	825.5	611.3	436.3	317.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1480.0	1444.6	1374.8	1323.7	1272.6	1132.1	957.2	768.5	587.7	436.3	331.2
115°	1410.2	1363.0	1286.4	1232.8	1179.3	1044.6	892.3	730.2	571.9	439.3	344.9
117.5°	1327.7	1278.5	1200.9	1150.3	1099.7	981.7	847.1	704.6	563.1	444.2	360.7
120°	1244.1	1197.0	1124.2	1081.0	1037.7	929.7	811.7	684.0	557.2	452.1	376.4
122.5°	1170.4	1128.2	1065.3	1025.5	985.7	892.3	785.2	666.3	552.3	458.9	394.1
125°	1111.5	1071.2	1016.1	980.8	945.4	859.9	759.6	650.6	548.4	466.8	409.8
127.5°	1062.3	1026.0	975.8	942.4	909.0	828.4	733.1	635.8	546.4	475.6	424.5
130°	1017.1	984.7	935.5	903.6	871.7	795.0	708.5	621.1	544.4	483.5	439.3
132.5°	973.9	941.4	892.3	861.8	831.4	763.6	684.0	609.3	544.4	492.3	452.1
135°	925.7	893.3	850.1	822.0	794.0	731.1	663.3	600.4	544.4	500.2	463.8
137.5°	874.6	844.2	804.8	780.2	755.7	701.7	644.7	591.6	545.4	508.1	472.7
140°	824.5	798.9	762.6	742.0	721.3	676.1	629.9	585.7	546.4	513.0	481.5
142.5°	776.3	755.7	726.2	709.0	691.8	654.5	617.1	580.8	547.4	515.9	486.4
145°	734.1	717.4	693.8	680.6	667.3	636.8	606.3	575.9	546.4	517.9	491.4
147.5°	699.7	685.9	666.3	656.0	645.6	621.1	595.5	571.0	544.4	518.9	494.3
150°	671.2	659.4	644.7	635.8	627.0	608.3	586.7	565.1	541.5	518.9	497.3
152.5°	645.6	636.8	625.0	618.6	612.2	595.5	576.9	558.2	537.5	517.9	499.2
155°	624.0	617.1	607.3	601.9	596.5	582.8	567.0	550.3	532.6	515.9	500.2
157.5°	604.4	598.5	590.6	586.2	581.8	571.0	557.2	543.4	527.7	514.0	501.2
160°	585.7	580.8	573.9	570.4	567.0	557.2	547.4	534.6	522.8	511.0	501.2
162.5°	568.0	564.1	559.2	556.2	553.3	545.4	536.6	526.7	516.9	508.1	500.2
165°	550.3	548.4	544.4	542.0	539.5	533.6	526.7	518.9	511.0	505.1	499.2
167.5°	534.6	532.6	530.7	528.7	526.7	521.8	516.9	511.0	505.1	500.2	497.3
170°	519.9	518.9	516.9	515.9	514.9	512.0	509.0	504.1	500.2	497.3	495.3
172.5°	508.1	506.1	506.1	505.6	505.1	503.2	500.2	497.3	494.3	493.3	493.3
175°	497.3	496.3	496.3	496.3	496.3	494.3	494.3	491.4	490.4	490.4	491.4
177.5°	490.4	489.4	490.4	490.4	490.4	490.4	489.4	488.4	487.4	487.4	489.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	10.8	9.8	8.9	7.9	5.9	3.9	2.0	1.0	2.0	3.9	5.9
92.5°	165.1	98.3	80.6	62.9	42.3	27.5	17.7	14.7	17.7	27.5	42.3
95°	223.1	117.9	95.8	73.7	52.1	41.3	33.4	32.4	33.4	41.3	52.1
97.5°	192.6	119.9	103.7	87.5	67.8	57.0	51.1	50.1	51.1	57.0	67.8
100°	190.6	133.6	118.9	104.2	85.5	74.7	70.8	68.8	70.8	74.7	85.5
102.5°	199.5	150.4	136.2	121.9	105.2	93.4	90.4	89.4	90.4	93.4	105.2
105°	212.3	169.0	155.2	141.5	125.8	116.0	111.0	111.0	111.0	116.0	125.8
107.5°	230.0	187.7	175.4	163.1	146.4	138.6	133.6	131.7	133.6	138.6	146.4
110°	249.6	209.3	196.6	183.8	169.0	160.2	156.3	154.3	156.3	160.2	169.0

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	268.3	230.0	217.7	205.4	190.6	181.8	178.9	176.9	178.9	181.8	190.6
115°	287.9	251.6	239.3	227.0	212.3	203.4	200.5	198.5	200.5	203.4	212.3
117.5°	307.6	273.2	261.4	249.6	232.9	224.1	221.1	218.2	221.1	224.1	232.9
120°	329.2	294.8	282.5	270.2	253.5	244.7	240.8	237.8	240.8	244.7	253.5
122.5°	349.8	315.5	303.2	290.9	272.2	263.4	260.4	258.5	260.4	263.4	272.2
125°	367.5	335.1	322.4	309.6	290.9	282.0	277.1	275.2	277.1	282.0	290.9
127.5°	385.2	353.8	341.0	328.2	308.6	297.8	291.9	288.9	291.9	297.8	308.6
130°	401.9	371.5	358.7	345.9	325.3	312.5	304.6	301.7	304.6	312.5	325.3
132.5°	417.7	387.2	374.4	361.6	340.0	325.3	315.5	311.5	315.5	325.3	340.0
135°	431.4	400.9	387.6	374.4	353.8	338.1	326.3	322.3	326.3	338.1	353.8
137.5°	441.2	413.7	400.0	386.2	365.6	349.8	339.0	336.1	339.0	349.8	365.6
140°	452.1	423.6	410.3	397.0	378.3	362.6	350.8	347.9	350.8	362.6	378.3
142.5°	458.9	432.4	420.1	407.8	390.1	374.4	363.6	361.6	363.6	374.4	390.1
145°	466.8	441.2	429.9	418.6	400.9	387.2	377.4	375.4	377.4	387.2	400.9
147.5°	471.7	449.1	438.8	428.5	412.7	400.0	391.1	390.1	391.1	400.0	412.7
150°	476.6	455.0	446.6	438.3	424.5	411.8	404.9	402.9	404.9	411.8	424.5
152.5°	481.5	461.9	454.5	447.1	434.4	423.6	417.7	416.7	417.7	423.6	434.4
155°	484.5	467.8	460.9	454.0	444.2	434.4	428.5	428.5	428.5	434.4	444.2
157.5°	487.4	472.7	467.3	461.9	453.0	444.2	439.3	439.3	439.3	444.2	453.0
160°	489.4	476.6	472.2	467.8	459.9	453.0	449.1	450.1	449.1	453.0	459.9
162.5°	491.4	480.5	477.1	473.7	467.8	461.9	457.9	458.9	457.9	461.9	467.8
165°	491.4	483.5	480.6	477.6	473.7	468.8	465.8	467.8	465.8	468.8	473.7
167.5°	491.4	484.5	482.5	480.5	477.6	474.7	472.7	473.7	472.7	474.7	477.6
170°	491.4	486.4	485.0	483.5	481.5	479.6	478.6	479.6	478.6	479.6	481.5
172.5°	490.4	486.4	486.0	485.5	484.5	482.5	481.5	483.5	481.5	482.5	484.5
175°	489.4	486.4	486.4	486.4	486.4	485.5	484.5	486.4	484.5	485.5	486.4
177.5°	488.4	486.4	486.4	486.4	487.4	486.4	486.4	488.4	486.4	486.4	487.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	7.9	8.9	9.8	10.8	12.8	13.8	15.7	16.7	17.7	18.7	19.7
92.5°	62.9	80.6	98.3	165.1	277.1	399.0	392.1	316.4	213.2	153.3	114.0
95°	73.7	95.8	117.9	223.1	439.3	710.5	870.7	852.0	706.6	557.2	436.3
97.5°	87.5	103.7	119.9	192.6	358.7	651.5	940.5	1064.3	1013.2	894.3	772.4
100°	104.2	118.9	133.6	190.6	318.4	566.0	887.4	1133.1	1208.7	1160.6	1059.4
102.5°	121.9	136.2	150.4	199.5	301.7	501.2	794.0	1091.8	1274.6	1323.7	1288.3
105°	141.5	155.2	169.0	212.3	299.7	463.8	712.5	994.5	1230.4	1365.0	1408.2
107.5°	163.1	175.4	187.7	230.0	306.6	444.2	651.5	902.1	1140.0	1317.8	1422.0
110°	183.8	196.6	209.3	249.6	317.4	436.3	611.3	825.5	1037.7	1224.5	1363.0

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	205.4	217.7	230.0	268.3	331.2	436.3	587.7	768.5	957.2	1132.1	1272.6
115°	227.0	239.3	251.6	287.9	344.9	439.3	571.9	730.2	892.3	1044.6	1179.3
117.5°	249.6	261.4	273.2	307.6	360.7	444.2	563.1	704.6	847.1	981.7	1099.7
120°	270.2	282.5	294.8	329.2	376.4	452.1	557.2	684.0	811.7	929.7	1037.7
122.5°	290.9	303.2	315.5	349.8	394.1	458.9	552.3	666.3	785.2	892.3	985.7
125°	309.6	322.4	335.1	367.5	409.8	466.8	548.4	650.6	759.6	859.9	945.4
127.5°	328.2	341.0	353.8	385.2	424.5	475.6	546.4	635.8	733.1	828.4	909.0
130°	345.9	358.7	371.5	401.9	439.3	483.5	544.4	621.1	708.5	795.0	871.7
132.5°	361.6	374.4	387.2	417.7	452.1	492.3	544.4	609.3	684.0	763.6	831.4
135°	374.4	387.6	400.9	431.4	463.8	500.2	544.4	600.4	663.3	731.1	794.0
137.5°	386.2	400.0	413.7	441.2	472.7	508.1	545.4	591.6	644.7	701.7	755.7
140°	397.0	410.3	423.6	452.1	481.5	513.0	546.4	585.7	629.9	676.1	721.3
142.5°	407.8	420.1	432.4	458.9	486.4	515.9	547.4	580.8	617.1	654.5	691.8
145°	418.6	429.9	441.2	466.8	491.4	517.9	546.4	575.9	606.3	636.8	667.3
147.5°	428.5	438.8	449.1	471.7	494.3	518.9	544.4	571.0	595.5	621.1	645.6
150°	438.3	446.6	455.0	476.6	497.3	518.9	541.5	565.1	586.7	608.3	627.0
152.5°	447.1	454.5	461.9	481.5	499.2	517.9	537.5	558.2	576.9	595.5	612.2
155°	454.0	460.9	467.8	484.5	500.2	515.9	532.6	550.3	567.0	582.8	596.5
157.5°	461.9	467.3	472.7	487.4	501.2	514.0	527.7	543.4	557.2	571.0	581.8
160°	467.8	472.2	476.6	489.4	501.2	511.0	522.8	534.6	547.4	557.2	567.0
162.5°	473.7	477.1	480.5	491.4	500.2	508.1	516.9	526.7	536.6	545.4	553.3
165°	477.6	480.6	483.5	491.4	499.2	505.1	511.0	518.9	526.7	533.6	539.5
167.5°	480.5	482.5	484.5	491.4	497.3	500.2	505.1	511.0	516.9	521.8	526.7
170°	483.5	485.0	486.4	491.4	495.3	497.3	500.2	504.1	509.0	512.0	514.9
172.5°	485.5	486.0	486.4	490.4	493.3	493.3	494.3	497.3	500.2	503.2	505.1
175°	486.4	486.4	486.4	489.4	491.4	490.4	490.4	491.4	494.3	494.3	496.3
177.5°	486.4	486.4	486.4	488.4	489.4	487.4	487.4	488.4	489.4	490.4	490.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	20.6	21.6	21.6	21.6	22.6	22.6	22.6	21.6	21.6	21.6	20.6
92.5°	104.6	95.3	79.6	76.7	74.7	72.7	74.7	76.7	79.6	95.3	104.6
95°	395.0	353.8	284.0	254.5	246.7	230.9	246.7	254.5	284.0	353.8	395.0
97.5°	713.4	654.5	595.5	544.4	517.9	506.1	517.9	544.4	595.5	654.5	713.4
100°	1008.3	957.2	889.4	818.6	782.2	766.5	782.2	818.6	889.4	957.2	1008.3
102.5°	1257.8	1227.4	1153.7	1108.5	1068.2	1057.4	1068.2	1108.5	1153.7	1227.4	1257.8
105°	1402.8	1397.4	1366.0	1333.5	1313.9	1302.1	1313.9	1333.5	1366.0	1397.4	1402.8
107.5°	1443.6	1465.2	1474.1	1469.2	1459.3	1449.5	1459.3	1469.2	1474.1	1465.2	1443.6
110°	1404.8	1446.6	1490.8	1509.5	1516.3	1516.3	1516.3	1509.5	1490.8	1446.6	1404.8

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1323.7	1374.8	1444.6	1480.0	1499.6	1508.5	1499.6	1480.0	1444.6	1374.8	1323.7
115°	1232.8	1286.4	1363.0	1410.2	1437.7	1450.5	1437.7	1410.2	1363.0	1286.4	1232.8
117.5°	1150.3	1200.9	1278.5	1327.7	1355.2	1363.0	1355.2	1327.7	1278.5	1200.9	1150.3
120°	1081.0	1124.2	1197.0	1244.1	1270.7	1278.5	1270.7	1244.1	1197.0	1124.2	1081.0
122.5°	1025.5	1065.3	1128.2	1170.4	1197.0	1203.8	1197.0	1170.4	1128.2	1065.3	1025.5
125°	980.8	1016.1	1071.2	1111.5	1133.1	1142.9	1133.1	1111.5	1071.2	1016.1	980.8
127.5°	942.4	975.8	1026.0	1062.3	1083.0	1086.9	1083.0	1062.3	1026.0	975.8	942.4
130°	903.6	935.5	984.7	1017.1	1036.8	1042.7	1036.8	1017.1	984.7	935.5	903.6
132.5°	861.8	892.3	941.4	973.9	991.6	998.4	991.6	973.9	941.4	892.3	861.8
135°	822.0	850.1	893.3	925.7	943.4	949.3	943.4	925.7	893.3	850.1	822.0
137.5°	780.2	804.8	844.2	874.6	891.3	898.2	891.3	874.6	844.2	804.8	780.2
140°	742.0	762.6	798.9	824.5	839.2	844.2	839.2	824.5	798.9	762.6	742.0
142.5°	709.0	726.2	755.7	776.3	790.1	794.0	790.1	776.3	755.7	726.2	709.0
145°	680.6	693.8	717.4	734.1	744.9	748.8	744.9	734.1	717.4	693.8	680.6
147.5°	656.0	666.3	685.9	699.7	706.6	708.5	706.6	699.7	685.9	666.3	656.0
150°	635.8	644.7	659.4	671.2	675.1	676.1	675.1	671.2	659.4	644.7	635.8
152.5°	618.6	625.0	636.8	645.6	649.6	650.6	649.6	645.6	636.8	625.0	618.6
155°	601.9	607.3	617.1	624.0	627.0	628.0	627.0	624.0	617.1	607.3	601.9
157.5°	586.2	590.6	598.5	604.4	607.3	607.3	607.3	604.4	598.5	590.6	586.2
160°	570.4	573.9	580.8	585.7	587.7	586.7	587.7	585.7	580.8	573.9	570.4
162.5°	556.2	559.2	564.1	568.0	568.0	568.0	568.0	568.0	564.1	559.2	556.2
165°	542.0	544.4	548.4	550.3	550.3	550.3	550.3	550.3	548.4	544.4	542.0
167.5°	528.7	530.7	532.6	534.6	533.6	533.6	533.6	534.6	532.6	530.7	528.7
170°	515.9	516.9	518.9	519.9	519.9	518.9	519.9	519.9	518.9	516.9	515.9
172.5°	505.6	506.1	506.1	508.1	506.1	505.1	506.1	508.1	506.1	506.1	505.6
175°	496.3	496.3	496.3	497.3	495.3	494.3	495.3	497.3	496.3	496.3	496.3
177.5°	490.4	490.4	489.4	490.4	487.4	487.4	487.4	490.4	489.4	490.4	490.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	19.7	18.7	17.7	16.7	15.7	13.8	12.8	10.8	9.8	8.9	7.9
92.5°	114.0	153.3	213.2	316.4	392.1	399.0	277.1	165.1	98.3	80.6	62.9
95°	436.3	557.2	706.6	852.0	870.7	710.5	439.3	223.1	117.9	95.8	73.7
97.5°	772.4	894.3	1013.2	1064.3	940.5	651.5	358.7	192.6	119.9	103.7	87.5
100°	1059.4	1160.6	1208.7	1133.1	887.4	566.0	318.4	190.6	133.6	118.9	104.2
102.5°	1288.3	1323.7	1274.6	1091.8	794.0	501.2	301.7	199.5	150.4	136.2	121.9
105°	1408.2	1365.0	1230.4	994.5	712.5	463.8	299.7	212.3	169.0	155.2	141.5
107.5°	1422.0	1317.8	1140.0	902.1	651.5	444.2	306.6	230.0	187.7	175.4	163.1
110°	1363.0	1224.5	1037.7	825.5	611.3	436.3	317.4	249.6	209.3	196.6	183.8

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1272.6	1132.1	957.2	768.5	587.7	436.3	331.2	268.3	230.0	217.7	205.4
115°	1179.3	1044.6	892.3	730.2	571.9	439.3	344.9	287.9	251.6	239.3	227.0
117.5°	1099.7	981.7	847.1	704.6	563.1	444.2	360.7	307.6	273.2	261.4	249.6
120°	1037.7	929.7	811.7	684.0	557.2	452.1	376.4	329.2	294.8	282.5	270.2
122.5°	985.7	892.3	785.2	666.3	552.3	458.9	394.1	349.8	315.5	303.2	290.9
125°	945.4	859.9	759.6	650.6	548.4	466.8	409.8	367.5	335.1	322.4	309.6
127.5°	909.0	828.4	733.1	635.8	546.4	475.6	424.5	385.2	353.8	341.0	328.2
130°	871.7	795.0	708.5	621.1	544.4	483.5	439.3	401.9	371.5	358.7	345.9
132.5°	831.4	763.6	684.0	609.3	544.4	492.3	452.1	417.7	387.2	374.4	361.6
135°	794.0	731.1	663.3	600.4	544.4	500.2	463.8	431.4	400.9	387.6	374.4
137.5°	755.7	701.7	644.7	591.6	545.4	508.1	472.7	441.2	413.7	400.0	386.2
140°	721.3	676.1	629.9	585.7	546.4	513.0	481.5	452.1	423.6	410.3	397.0
142.5°	691.8	654.5	617.1	580.8	547.4	515.9	486.4	458.9	432.4	420.1	407.8
145°	667.3	636.8	606.3	575.9	546.4	517.9	491.4	466.8	441.2	429.9	418.6
147.5°	645.6	621.1	595.5	571.0	544.4	518.9	494.3	471.7	449.1	438.8	428.5
150°	627.0	608.3	586.7	565.1	541.5	518.9	497.3	476.6	455.0	446.6	438.3
152.5°	612.2	595.5	576.9	558.2	537.5	517.9	499.2	481.5	461.9	454.5	447.1
155°	596.5	582.8	567.0	550.3	532.6	515.9	500.2	484.5	467.8	460.9	454.0
157.5°	581.8	571.0	557.2	543.4	527.7	514.0	501.2	487.4	472.7	467.3	461.9
160°	567.0	557.2	547.4	534.6	522.8	511.0	501.2	489.4	476.6	472.2	467.8
162.5°	553.3	545.4	536.6	526.7	516.9	508.1	500.2	491.4	480.5	477.1	473.7
165°	539.5	533.6	526.7	518.9	511.0	505.1	499.2	491.4	483.5	480.6	477.6
167.5°	526.7	521.8	516.9	511.0	505.1	500.2	497.3	491.4	484.5	482.5	480.5
170°	514.9	512.0	509.0	504.1	500.2	497.3	495.3	491.4	486.4	485.0	483.5
172.5°	505.1	503.2	500.2	497.3	494.3	493.3	493.3	490.4	486.4	486.0	485.5
175°	496.3	494.3	494.3	491.4	490.4	490.4	491.4	489.4	486.4	486.4	486.4
177.5°	490.4	490.4	489.4	488.4	487.4	487.4	489.4	488.4	486.4	486.4	486.4
180°	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4	487.4

TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	5.9	3.9	2.0	1.0
92.5°	42.3	27.5	17.7	14.7
95°	52.1	41.3	33.4	32.4
97.5°	67.8	57.0	51.1	50.1
100°	85.5	74.7	70.8	68.8
102.5°	105.2	93.4	90.4	89.4
105°	125.8	116.0	111.0	111.0
107.5°	146.4	138.6	133.6	131.7
110°	169.0	160.2	156.3	154.3



TEST NUMBER: P1028434

CATALOG NUMBER: S125RDIP-B1090D1090UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	190.6	181.8	178.9	176.9
115°	212.3	203.4	200.5	198.5
117.5°	232.9	224.1	221.1	218.2
120°	253.5	244.7	240.8	237.8
122.5°	272.2	263.4	260.4	258.5
125°	290.9	282.0	277.1	275.2
127.5°	308.6	297.8	291.9	288.9
130°	325.3	312.5	304.6	301.7
132.5°	340.0	325.3	315.5	311.5
135°	353.8	338.1	326.3	322.3
137.5°	365.6	349.8	339.0	336.1
140°	378.3	362.6	350.8	347.9
142.5°	390.1	374.4	363.6	361.6
145°	400.9	387.2	377.4	375.4
147.5°	412.7	400.0	391.1	390.1
150°	424.5	411.8	404.9	402.9
152.5°	434.4	423.6	417.7	416.7
155°	444.2	434.4	428.5	428.5
157.5°	453.0	444.2	439.3	439.3
160°	459.9	453.0	449.1	450.1
162.5°	467.8	461.9	457.9	458.9
165°	473.7	468.8	465.8	467.8
167.5°	477.6	474.7	472.7	473.7
170°	481.5	479.6	478.6	479.6
172.5°	484.5	482.5	481.5	483.5
175°	486.4	485.5	484.5	486.4
177.5°	487.4	486.4	486.4	488.4
180°	487.4	487.4	487.4	487.4

(END OF REPORT)