

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028470

Luminaire Tested: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028470
REPORT IS A COMBINATION OF REPORTS P1004995 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8234.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 81.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	73	71	69	61	60	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	19	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10070	10070	10070	10070
5°	10061	11349	10061	8723
10°	10005	12754	9972	7541
15°	9897	13493	9829	6566
20°	9766	14566	9678	5935
25°	9594	16487	9486	5386
30°	9420	17525	9279	4994
35°	9195	14412	9066	4628
40°	8795	9787	8721	4300
45°	8270	7036	8259	3976
50°	7732	5410	7769	3677
55°	7126	4400	7112	3389
60°	6561	3605	6529	3008
65°	5905	3005	5941	2422
70°	5360	2411	5338	2017
75°	4529	1827	4529	1658
80°	3671	1115	3629	1115
85°	2584	587	2510	664

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14334 cd/sqm

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	1.8
10°-20°	441.9	5.4
20°-30°	700.6	8.5
30°-40°	846.6	10.3
40°-50°	753.8	9.2
50°-60°	578.0	7.0
60°-70°	375.4	4.6
70°-80°	182.2	2.2
80°-90°	45.1	0.5
90°-100°	402.9	4.9
100°-110°	868.7	10.6
110°-120°	809.9	9.8
120°-130°	656.0	8.0
130°-140°	526.7	6.4
140°-150°	397.3	4.8
150°-160°	279.8	3.4
160°-170°	164.9	2.0
170°-180°	53.6	0.7
0°-30°	1293.2	15.7
0°-40°	2139.8	26.0
0°-60°	3471.6	42.2
0°-90°	4074.2	49.5
90°-120°	2081.5	25.3
90°-150°	3661.5	44.5
90°-180°	4160.0	50.5
0°-180°	8234.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1572	1572	1572	1572	1572	
5°	1568	1801	1568	1385	1568	149
15°	1502	2164	1492	1053	1502	424
25°	1373	2591	1358	846	1373	633
35°	1196	2150	1179	690	1196	745
45°	936	961	934	543	936	722
55°	661	528	659	406	661	592
65°	410	299	413	241	410	410
75°	200	139	200	126	200	214
85°	45	30	44	34	45	51
90°	1	26	1	26	1	6
95°	37	262	37	262	37	38
105°	126	1480	126	1480	126	133
115°	226	1648	226	1648	226	222
125°	313	1299	313	1299	313	278
135°	366	1079	366	1079	366	284
145°	426	851	426	851	426	267
155°	487	714	487	714	487	224
165°	532	625	532	625	532	150
175°	553	562	553	562	553	53
180°	554	554	554	554	554	

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1573.0	1585.9	1589.8	1600.1	1611.7	1614.3	1620.8	1629.8	1634.9	1633.7	1633.7
5°	1567.8	1589.8	1605.3	1623.3	1645.3	1654.3	1662.0	1681.4	1696.9	1705.9	1721.4
7.5°	1558.8	1591.1	1616.9	1644.0	1677.5	1693.0	1709.8	1736.9	1765.3	1783.3	1800.1
10°	1544.6	1585.9	1622.0	1662.0	1707.2	1730.4	1751.1	1792.4	1827.2	1850.4	1889.2
12.5°	1524.0	1575.6	1625.9	1678.8	1735.6	1760.1	1788.5	1833.7	1882.7	1916.3	1948.5
15°	1502.0	1564.0	1618.2	1681.4	1749.8	1787.2	1823.3	1871.1	1915.0	1952.4	1989.8
17.5°	1476.2	1542.0	1609.1	1681.4	1758.8	1796.3	1827.2	1884.0	1930.5	1967.9	2001.4
20°	1445.3	1518.8	1594.9	1675.0	1753.7	1788.5	1818.2	1880.1	1921.4	1961.4	2009.2
22.5°	1411.7	1491.7	1573.0	1651.7	1729.1	1766.6	1801.4	1855.6	1900.8	1955.0	2016.9
25°	1373.0	1460.7	1543.3	1622.0	1695.6	1730.4	1761.4	1820.8	1884.0	1952.4	2022.1
27.5°	1334.3	1419.5	1499.5	1571.7	1651.7	1684.0	1715.0	1789.8	1864.6	1936.9	2032.4
30°	1291.7	1378.2	1447.8	1514.9	1592.4	1625.9	1664.6	1749.8	1835.0	1933.0	2049.2
32.5°	1244.0	1322.7	1387.2	1456.9	1526.6	1567.8	1616.9	1709.8	1807.9	1925.3	2073.7
35°	1196.2	1259.4	1318.8	1384.6	1468.5	1512.4	1560.1	1658.2	1780.8	1921.4	2094.3
37.5°	1135.6	1196.2	1242.7	1309.8	1396.2	1447.8	1495.6	1609.1	1748.5	1912.4	2093.0
40°	1073.6	1125.2	1169.1	1238.8	1333.0	1380.7	1432.4	1556.2	1715.0	1886.6	2062.1
42.5°	1006.5	1050.4	1098.1	1165.2	1256.9	1303.3	1362.7	1507.2	1668.5	1850.4	1982.1
45°	935.5	978.1	1018.1	1087.8	1179.4	1229.8	1294.3	1442.7	1611.7	1774.3	1853.0
47.5°	865.9	903.3	945.9	1006.5	1099.4	1154.9	1220.7	1379.4	1535.6	1672.4	1678.8
50°	798.8	828.4	864.6	926.5	1023.3	1076.2	1144.6	1293.0	1445.3	1539.5	1476.2
52.5°	729.1	756.2	793.6	847.8	938.1	1000.1	1059.4	1207.8	1335.6	1398.8	1282.7
55°	660.7	683.9	722.6	783.3	862.0	909.7	970.4	1108.5	1220.7	1222.0	1095.6
57.5°	593.6	614.2	646.5	700.7	774.2	829.7	885.2	1005.2	1081.4	1059.4	918.8
60°	534.2	547.1	576.8	629.7	698.1	738.1	797.5	898.1	948.5	908.4	757.5
62.5°	472.3	485.2	508.4	551.0	615.5	658.1	695.5	778.1	813.0	752.3	628.4
65°	410.4	425.8	442.6	476.2	536.8	565.2	598.8	659.4	692.9	622.0	514.9
67.5°	356.2	363.9	380.7	415.5	458.1	483.9	507.1	548.4	554.9	498.1	410.4
70°	305.8	308.4	323.9	344.5	376.8	392.3	411.6	436.2	436.2	389.7	320.0
72.5°	249.0	252.9	264.5	286.5	305.8	313.6	320.0	335.5	332.9	290.3	242.6
75°	200.0	202.6	211.6	222.0	229.7	243.9	249.0	246.5	245.2	209.0	181.9
77.5°	154.8	156.1	162.6	171.6	172.9	178.1	174.2	174.2	162.6	141.9	127.8
80°	113.6	114.8	117.4	120.0	120.0	120.0	120.0	113.6	105.8	92.9	89.0
82.5°	76.1	76.1	77.4	80.0	78.7	76.1	73.6	67.1	61.9	58.1	55.5
85°	45.2	45.2	46.5	45.2	40.0	38.7	36.1	34.8	33.6	32.3	32.3
87.5°	21.9	20.6	18.1	15.5	15.5	15.5	15.5	15.5	15.5	14.2	14.2
90°	1.1	2.2	4.5	6.7	8.9	10.0	11.2	12.3	14.5	15.6	17.9
92.5°	16.7	20.1	31.3	48.0	71.5	91.6	111.7	187.6	314.9	453.3	445.5
95°	36.8	38.0	46.9	59.2	83.7	108.8	134.0	253.5	499.1	807.3	989.3
97.5°	56.9	58.1	64.8	77.0	99.4	117.8	136.2	218.9	407.6	740.3	1068.6
100°	78.2	80.4	84.9	97.1	118.4	135.2	151.9	216.6	361.8	643.2	1008.3
102.5°	101.6	102.7	106.1	119.5	138.5	154.6	170.8	226.7	342.8	569.5	902.2
105°	126.2	126.2	131.8	142.9	160.8	176.4	192.1	241.2	340.6	527.0	809.5
107.5°	149.6	151.9	157.4	166.4	185.4	199.4	213.3	261.3	348.4	504.7	740.3
110°	175.3	177.5	182.0	192.1	208.8	223.3	237.8	283.6	360.7	495.8	694.5

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	201.0	203.2	206.6	216.6	233.4	247.4	261.3	304.8	376.3	495.8	667.7
115°	225.6	227.8	231.1	241.2	257.9	271.8	285.8	327.2	391.9	499.1	649.9
117.5°	247.9	251.2	254.6	264.6	283.6	297.0	310.4	349.5	409.8	504.7	639.8
120°	270.2	273.6	278.0	288.1	307.1	321.0	335.0	374.1	427.7	513.6	633.1
122.5°	293.7	295.9	299.2	309.3	330.5	344.4	358.4	397.5	447.8	521.4	627.5
125°	312.6	314.9	320.5	330.5	351.7	366.2	380.8	417.6	465.6	530.4	623.1
127.5°	328.3	331.6	338.3	350.6	372.9	387.4	402.0	437.7	482.4	540.4	620.8
130°	342.8	346.1	355.1	369.6	393.0	407.6	422.1	456.7	499.1	549.4	618.6
132.5°	354.0	358.4	369.6	386.3	410.9	425.4	439.9	474.6	513.6	559.4	618.6
135°	366.2	370.7	384.1	402.0	425.4	440.5	455.6	490.2	527.0	568.3	618.6
137.5°	381.9	385.2	397.5	415.4	438.8	454.4	470.1	501.3	537.1	577.3	619.7
140°	395.3	398.6	412.0	429.9	451.1	466.2	481.3	513.6	547.1	582.9	620.8
142.5°	410.9	413.1	425.4	443.3	463.4	477.4	491.3	521.4	552.7	586.2	621.9
145°	426.5	428.8	439.9	455.6	475.7	488.5	501.3	530.4	558.3	588.4	620.8
147.5°	443.3	444.4	454.5	469.0	486.8	498.6	510.3	536.0	561.6	589.6	618.6
150°	457.8	460.0	467.9	482.4	498.0	507.5	517.0	541.5	565.0	589.6	615.2
152.5°	473.4	474.6	481.3	493.5	508.0	516.4	524.8	547.1	567.2	588.4	610.8
155°	486.8	486.8	493.5	504.7	515.9	523.7	531.5	550.5	568.3	586.2	605.2
157.5°	499.1	499.1	504.7	514.7	524.8	531.0	537.1	553.8	569.5	584.0	599.6
160°	511.4	510.3	514.7	522.6	531.5	536.5	541.5	556.1	569.5	580.6	594.0
162.5°	521.4	520.3	524.8	531.5	538.2	542.1	546.0	558.3	568.3	577.3	587.3
165°	531.5	529.3	532.6	538.2	542.7	546.0	549.4	558.3	567.2	573.9	580.6
167.5°	538.2	537.1	539.3	542.7	546.0	548.2	550.5	558.3	565.0	568.3	573.9
170°	544.9	543.8	544.9	547.1	549.4	551.0	552.7	558.3	562.8	565.0	568.3
172.5°	549.4	547.1	548.2	550.5	551.6	552.2	552.7	557.2	560.5	560.5	561.6
175°	552.7	550.5	551.6	552.7	552.7	552.7	552.7	556.1	558.3	557.2	557.2
177.5°	554.9	552.7	552.7	553.8	552.7	552.7	552.7	554.9	556.1	553.8	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1640.1	1649.1	1656.9	1653.0	1668.5	1667.2	1669.8	1675.0	1676.2	1673.7	1668.5
5°	1729.1	1742.1	1764.0	1775.6	1773.0	1783.3	1788.5	1796.3	1804.0	1801.4	1801.4
7.5°	1828.5	1846.6	1868.5	1898.2	1902.1	1911.1	1926.6	1926.6	1935.6	1931.7	1930.5
10°	1915.0	1936.9	1971.7	1995.0	2005.3	2010.5	2025.9	2031.1	2041.4	2042.7	2042.7
12.5°	1985.9	2024.7	2047.9	2071.1	2076.3	2084.0	2095.6	2103.4	2107.2	2107.2	2103.4
15°	2023.4	2054.3	2081.4	2105.9	2120.1	2126.6	2138.2	2147.2	2152.4	2164.0	2166.6
17.5°	2038.8	2076.3	2120.1	2155.0	2179.5	2186.0	2209.2	2216.9	2227.2	2232.4	2238.9
20°	2060.8	2115.0	2167.9	2210.5	2233.7	2250.5	2275.0	2311.1	2321.4	2321.4	2317.6
22.5°	2080.1	2149.8	2222.1	2290.5	2309.8	2343.4	2388.5	2427.3	2442.7	2449.2	2444.0
25°	2103.4	2198.9	2293.1	2378.2	2431.1	2455.6	2516.3	2562.8	2580.8	2591.1	2593.7
27.5°	2143.4	2263.4	2383.4	2491.8	2546.0	2574.4	2637.6	2677.6	2699.5	2708.6	2702.1
30°	2188.5	2335.6	2475.0	2571.8	2607.9	2642.8	2684.1	2699.5	2694.4	2694.4	2713.7
32.5°	2235.0	2387.3	2511.1	2574.4	2587.3	2582.1	2565.3	2518.9	2491.8	2491.8	2508.6
35°	2260.8	2392.4	2455.6	2435.0	2384.7	2355.0	2263.4	2211.8	2153.7	2149.8	2169.2
37.5°	2246.6	2303.4	2277.6	2142.1	2073.7	2016.9	1873.7	1816.9	1774.3	1715.0	1806.6
40°	2147.2	2127.9	1993.7	1798.8	1722.7	1642.7	1529.1	1472.4	1413.0	1404.0	1425.9
42.5°	1979.5	1864.6	1668.5	1480.1	1402.7	1345.9	1259.4	1204.0	1166.5	1151.0	1176.9
45°	1770.4	1589.8	1393.6	1244.0	1158.8	1129.1	1050.4	1001.4	973.0	961.4	979.4
47.5°	1514.9	1333.0	1147.2	1020.7	970.4	940.7	887.8	845.2	820.7	813.0	820.7
50°	1286.5	1099.4	943.3	862.0	816.8	792.3	748.4	721.3	702.0	696.8	709.7
52.5°	1089.1	918.8	800.1	727.8	698.1	677.5	646.5	623.3	611.7	606.5	615.5
55°	912.3	774.2	678.8	616.8	594.9	582.0	554.9	542.0	529.1	527.8	536.8
57.5°	756.2	660.7	572.9	529.1	522.6	503.3	480.0	468.4	462.0	460.7	464.5
60°	629.7	544.6	491.6	452.9	443.9	428.4	415.5	407.8	400.0	397.4	400.0
62.5°	523.9	456.8	414.2	388.4	375.5	371.6	357.4	348.4	347.1	347.1	349.7
65°	432.3	375.5	348.4	327.8	318.7	314.9	304.5	298.1	299.4	299.4	300.7
67.5°	352.3	311.0	286.5	276.1	268.4	267.1	256.8	254.2	251.6	251.6	254.2
70°	280.0	254.2	236.1	231.0	229.7	220.7	216.8	215.5	211.6	212.9	212.9
72.5°	219.4	202.6	192.3	184.5	185.8	180.7	175.5	175.5	172.9	176.8	176.8
75°	162.6	154.8	147.1	144.5	147.1	144.5	140.7	139.4	140.7	139.4	139.4
77.5°	120.0	116.1	113.6	112.3	112.3	107.1	104.5	107.1	101.9	104.5	104.5
80°	83.9	78.7	77.4	74.8	76.1	72.3	73.6	71.0	71.0	71.0	71.0
82.5°	52.9	51.6	51.6	51.6	50.3	50.3	50.3	50.3	50.3	50.3	49.0
85°	32.3	31.0	31.0	31.0	29.7	29.7	29.7	29.7	29.7	29.7	29.7
87.5°	12.9	14.2	14.2	15.5	14.2	12.9	12.9	12.9	14.2	14.2	12.9
90°	19.0	20.1	21.2	22.3	23.5	24.6	24.6	24.6	25.7	25.7	25.7
92.5°	359.5	242.3	174.2	129.5	118.9	108.3	90.4	87.1	84.9	82.6	84.9
95°	968.1	802.8	633.1	495.8	448.9	402.0	322.7	289.2	280.3	262.4	280.3
97.5°	1209.3	1151.2	1016.1	877.6	810.6	743.6	676.7	618.6	588.4	575.0	588.4
100°	1287.4	1373.4	1318.7	1203.7	1145.6	1087.6	1010.5	930.1	888.8	870.9	888.8
102.5°	1240.5	1448.2	1504.0	1463.9	1429.2	1394.6	1310.9	1259.5	1213.7	1201.5	1213.7
105°	1130.0	1398.0	1550.9	1600.1	1593.9	1587.8	1552.1	1515.2	1492.9	1479.5	1492.9
107.5°	1025.0	1295.2	1497.3	1615.7	1640.2	1664.8	1674.9	1669.3	1658.1	1647.0	1658.1
110°	937.9	1179.1	1391.3	1548.7	1596.2	1643.6	1693.9	1715.1	1722.9	1722.9	1722.9

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	873.2	1087.6	1286.3	1446.0	1504.0	1562.1	1641.4	1681.6	1703.9	1714.0	1703.9
115°	829.6	1013.9	1186.9	1339.9	1400.8	1461.6	1548.7	1602.3	1633.6	1648.1	1633.6
117.5°	800.6	962.5	1115.5	1249.5	1307.0	1364.5	1452.7	1508.5	1539.8	1548.7	1539.8
120°	777.1	922.3	1056.3	1179.1	1228.2	1277.4	1360.0	1413.6	1443.8	1452.7	1443.8
122.5°	757.0	892.2	1013.9	1119.9	1165.2	1210.4	1281.8	1329.9	1360.0	1367.8	1360.0
125°	739.2	863.1	977.0	1074.2	1114.4	1154.6	1217.1	1262.9	1287.4	1298.6	1287.4
127.5°	722.4	833.0	941.3	1032.8	1070.8	1108.8	1165.7	1207.0	1230.5	1234.9	1230.5
130°	705.7	805.1	903.3	990.4	1026.7	1063.0	1118.8	1155.7	1178.0	1184.7	1178.0
132.5°	692.3	777.1	867.6	944.6	979.2	1013.9	1069.7	1106.5	1126.6	1134.5	1126.6
135°	682.2	753.7	830.7	902.2	934.0	965.9	1015.0	1051.8	1071.9	1078.6	1071.9
137.5°	672.2	732.5	797.2	858.7	886.6	914.5	959.2	993.8	1012.7	1020.6	1012.7
140°	665.5	715.7	768.2	819.6	843.0	866.5	907.8	936.8	953.6	959.2	953.6
142.5°	659.9	701.2	743.6	786.1	805.7	825.2	858.7	882.1	897.7	902.2	897.7
145°	654.3	688.9	723.6	758.2	773.2	788.3	815.1	834.1	846.4	850.8	846.4
147.5°	648.7	676.7	705.7	733.6	745.3	757.0	779.4	795.0	802.8	805.1	802.8
150°	642.0	666.6	691.2	712.4	722.4	732.5	749.2	762.6	767.1	768.2	767.1
152.5°	634.2	655.4	676.7	695.6	702.9	710.2	723.6	733.6	738.1	739.2	738.1
155°	625.3	644.3	662.1	677.8	684.0	690.1	701.2	709.0	712.4	713.5	712.4
157.5°	617.5	633.1	648.7	661.0	666.0	671.1	680.0	686.7	690.1	690.1	690.1
160°	607.4	621.9	633.1	644.3	648.2	652.1	659.9	665.5	667.7	666.6	667.7
162.5°	598.5	609.7	619.7	628.6	632.0	635.3	640.9	645.4	645.4	645.4	645.4
165°	589.6	598.5	606.3	613.0	615.8	618.6	623.1	625.3	625.3	625.3	625.3
167.5°	580.6	587.3	592.9	598.5	600.8	603.0	605.2	607.4	606.3	606.3	606.3
170°	572.8	578.4	581.7	585.1	586.2	587.3	589.6	590.7	590.7	589.6	590.7
172.5°	565.0	568.3	571.7	573.9	574.4	575.0	575.0	577.3	575.0	573.9	575.0
175°	558.3	561.6	561.6	563.9	563.9	563.9	563.9	565.0	562.8	561.6	562.8
177.5°	554.9	556.1	557.2	557.2	557.2	557.2	556.1	557.2	553.8	553.8	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1675.0	1665.9	1669.8	1665.9	1662.0	1658.2	1649.1	1636.2	1625.9	1618.2	1616.9
5°	1804.0	1792.4	1784.6	1780.8	1773.0	1762.7	1745.9	1726.6	1703.3	1694.3	1676.2
7.5°	1922.7	1918.8	1900.8	1898.2	1893.0	1873.7	1845.3	1819.5	1789.8	1765.3	1742.1
10°	2035.0	2025.9	2013.0	1995.0	1992.4	1967.9	1940.8	1904.6	1865.9	1842.7	1801.4
12.5°	2104.7	2094.3	2080.1	2068.5	2062.1	2046.6	2009.2	1973.0	1938.2	1895.6	1859.5
15°	2155.0	2142.1	2116.3	2107.2	2099.5	2078.8	2051.8	2014.3	1967.9	1938.2	1886.6
17.5°	2223.4	2207.9	2182.1	2165.3	2151.1	2118.9	2080.1	2029.8	1985.9	1952.4	1905.9
20°	2302.1	2278.9	2245.3	2223.4	2202.7	2165.3	2111.1	2051.8	1988.5	1947.2	1899.5
22.5°	2432.4	2388.5	2335.6	2304.7	2276.3	2211.8	2147.2	2073.7	2002.7	1940.8	1882.7
25°	2558.9	2515.0	2449.2	2406.6	2362.7	2287.9	2202.7	2100.8	2010.5	1938.2	1862.1
27.5°	2676.3	2631.1	2570.5	2518.9	2476.3	2364.0	2251.8	2136.9	2022.1	1922.7	1845.3
30°	2703.4	2684.1	2637.6	2592.4	2553.7	2450.5	2320.2	2174.3	2036.3	1908.5	1822.1
32.5°	2539.5	2587.3	2598.9	2592.4	2567.9	2494.4	2374.4	2220.8	2056.9	1902.1	1783.3
35°	2198.9	2285.3	2374.4	2422.1	2445.3	2455.6	2384.7	2244.0	2071.1	1891.7	1757.5
37.5°	1823.3	1907.2	2047.9	2118.9	2197.6	2300.8	2329.2	2238.9	2064.7	1884.0	1716.2
40°	1498.2	1605.3	1721.4	1785.9	1854.3	2040.1	2180.8	2170.5	2044.0	1855.6	1684.0
42.5°	1219.4	1286.5	1388.5	1459.5	1543.3	1751.1	1939.5	2032.4	1982.1	1820.8	1642.7
45°	1016.8	1068.5	1140.7	1213.0	1264.6	1453.0	1676.2	1828.5	1876.3	1758.8	1579.5
47.5°	856.8	895.5	958.8	1003.9	1059.4	1207.8	1401.4	1615.6	1716.2	1671.1	1512.4
50°	734.2	765.2	815.5	843.9	893.0	1020.7	1167.8	1392.4	1544.6	1549.8	1423.3
52.5°	627.1	658.1	700.7	725.2	754.9	841.3	989.7	1179.4	1354.9	1419.5	1321.4
55°	545.8	563.9	598.8	618.1	645.2	729.1	823.3	984.6	1167.8	1273.6	1211.7
57.5°	471.0	490.4	512.3	527.8	547.1	614.2	699.4	820.7	1002.6	1117.5	1096.8
60°	410.4	422.0	442.6	454.2	472.3	516.2	575.5	696.8	841.3	949.7	961.4
62.5°	353.6	363.9	378.1	388.4	400.0	434.9	478.7	565.2	691.7	809.1	824.6
65°	304.5	313.6	321.3	330.3	339.4	361.3	398.7	465.8	563.9	673.6	707.1
67.5°	260.7	263.2	274.9	276.1	281.3	298.1	325.2	379.4	450.4	538.1	582.0
70°	218.1	223.2	225.8	229.7	234.9	246.5	268.4	296.8	349.7	420.7	462.0
72.5°	176.8	178.1	181.9	184.5	189.7	198.7	209.0	231.0	264.5	316.2	353.6
75°	140.7	141.9	144.5	145.8	149.7	152.3	157.4	172.9	196.1	227.1	254.2
77.5°	105.8	108.4	111.0	111.0	112.3	114.8	117.4	122.6	134.2	154.8	178.1
80°	72.3	73.6	73.6	74.8	73.6	77.4	81.3	87.7	92.9	99.4	111.0
82.5°	50.3	50.3	50.3	51.6	51.6	52.9	52.9	54.2	55.5	59.4	64.5
85°	31.0	31.0	32.3	29.7	31.0	32.3	32.3	31.0	32.3	33.6	34.8
87.5°	12.9	12.9	14.2	14.2	14.2	14.2	12.9	14.2	12.9	14.2	14.2
90°	24.6	24.6	24.6	23.5	22.3	21.2	20.1	19.0	17.9	15.6	14.5
92.5°	87.1	90.4	108.3	118.9	129.5	174.2	242.3	359.5	445.5	453.3	314.9
95°	289.2	322.7	402.0	448.9	495.8	633.1	802.8	968.1	989.3	807.3	499.1
97.5°	618.6	676.7	743.6	810.6	877.6	1016.1	1151.2	1209.3	1068.6	740.3	407.6
100°	930.1	1010.5	1087.6	1145.6	1203.7	1318.7	1373.4	1287.4	1008.3	643.2	361.8
102.5°	1259.5	1310.9	1394.6	1429.2	1463.9	1504.0	1448.2	1240.5	902.2	569.5	342.8
105°	1515.2	1552.1	1587.8	1593.9	1600.1	1550.9	1398.0	1130.0	809.5	527.0	340.6
107.5°	1669.3	1674.9	1664.8	1640.2	1615.7	1497.3	1295.2	1025.0	740.3	504.7	348.4
110°	1715.1	1693.9	1643.6	1596.2	1548.7	1391.3	1179.1	937.9	694.5	495.8	360.7

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1681.6	1641.4	1562.1	1504.0	1446.0	1286.3	1087.6	873.2	667.7	495.8	376.3
115°	1602.3	1548.7	1461.6	1400.8	1339.9	1186.9	1013.9	829.6	649.9	499.1	391.9
117.5°	1508.5	1452.7	1364.5	1307.0	1249.5	1115.5	962.5	800.6	639.8	504.7	409.8
120°	1413.6	1360.0	1277.4	1228.2	1179.1	1056.3	922.3	777.1	633.1	513.6	427.7
122.5°	1329.9	1281.8	1210.4	1165.2	1119.9	1013.9	892.2	757.0	627.5	521.4	447.8
125°	1262.9	1217.1	1154.6	1114.4	1074.2	977.0	863.1	739.2	623.1	530.4	465.6
127.5°	1207.0	1165.7	1108.8	1070.8	1032.8	941.3	833.0	722.4	620.8	540.4	482.4
130°	1155.7	1118.8	1063.0	1026.7	990.4	903.3	805.1	705.7	618.6	549.4	499.1
132.5°	1106.5	1069.7	1013.9	979.2	944.6	867.6	777.1	692.3	618.6	559.4	513.6
135°	1051.8	1015.0	965.9	934.0	902.2	830.7	753.7	682.2	618.6	568.3	527.0
137.5°	993.8	959.2	914.5	886.6	858.7	797.2	732.5	672.2	619.7	577.3	537.1
140°	936.8	907.8	866.5	843.0	819.6	768.2	715.7	665.5	620.8	582.9	547.1
142.5°	882.1	858.7	825.2	805.7	786.1	743.6	701.2	659.9	621.9	586.2	552.7
145°	834.1	815.1	788.3	773.2	758.2	723.6	688.9	654.3	620.8	588.4	558.3
147.5°	795.0	779.4	757.0	745.3	733.6	705.7	676.7	648.7	618.6	589.6	561.6
150°	762.6	749.2	732.5	722.4	712.4	691.2	666.6	642.0	615.2	589.6	565.0
152.5°	733.6	723.6	710.2	702.9	695.6	676.7	655.4	634.2	610.8	588.4	567.2
155°	709.0	701.2	690.1	684.0	677.8	662.1	644.3	625.3	605.2	586.2	568.3
157.5°	686.7	680.0	671.1	666.0	661.0	648.7	633.1	617.5	599.6	584.0	569.5
160°	665.5	659.9	652.1	648.2	644.3	633.1	621.9	607.4	594.0	580.6	569.5
162.5°	645.4	640.9	635.3	632.0	628.6	619.7	609.7	598.5	587.3	577.3	568.3
165°	625.3	623.1	618.6	615.8	613.0	606.3	598.5	589.6	580.6	573.9	567.2
167.5°	607.4	605.2	603.0	600.8	598.5	592.9	587.3	580.6	573.9	568.3	565.0
170°	590.7	589.6	587.3	586.2	585.1	581.7	578.4	572.8	568.3	565.0	562.8
172.5°	577.3	575.0	575.0	574.4	573.9	571.7	568.3	565.0	561.6	560.5	560.5
175°	565.0	563.9	563.9	563.9	563.9	561.6	561.6	558.3	557.2	557.2	558.3
177.5°	557.2	556.1	557.2	557.2	557.2	557.2	556.1	554.9	553.8	553.8	556.1
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1613.0	1605.3	1600.1	1598.8	1591.1	1584.6	1576.9	1575.6	1571.7	1561.4	1554.9
5°	1663.3	1645.3	1641.4	1629.8	1610.4	1596.2	1578.2	1567.8	1556.2	1536.9	1521.4
7.5°	1715.0	1690.4	1672.4	1655.6	1628.5	1602.7	1576.9	1556.2	1535.6	1507.2	1484.0
10°	1765.3	1727.9	1705.9	1681.4	1644.0	1605.3	1569.1	1539.5	1505.9	1472.4	1438.8
12.5°	1811.7	1764.0	1731.7	1696.9	1650.4	1602.7	1556.2	1514.9	1480.1	1434.9	1397.5
15°	1840.1	1787.2	1755.0	1721.4	1651.7	1598.8	1544.6	1491.7	1445.3	1397.5	1362.7
17.5°	1856.9	1797.5	1761.4	1730.4	1659.5	1587.2	1517.5	1460.7	1410.4	1353.6	1307.2
20°	1849.2	1791.1	1757.5	1727.9	1645.3	1573.0	1498.2	1432.4	1369.1	1311.1	1262.0
22.5°	1832.4	1771.7	1734.3	1707.2	1633.7	1548.5	1465.9	1394.9	1329.1	1271.1	1215.6
25°	1796.3	1736.9	1704.6	1671.1	1598.8	1517.5	1433.6	1357.5	1287.8	1225.9	1163.9
27.5°	1764.0	1691.7	1658.2	1628.5	1552.4	1480.1	1397.5	1313.6	1242.7	1178.1	1116.2
30°	1726.6	1645.3	1609.1	1569.1	1500.7	1432.4	1349.8	1272.3	1198.8	1130.4	1071.0
32.5°	1686.6	1592.4	1551.1	1505.9	1436.2	1371.7	1302.0	1225.9	1152.3	1085.2	1023.3
35°	1634.9	1534.3	1486.6	1444.0	1371.7	1307.2	1242.7	1179.4	1105.9	1034.9	975.5
37.5°	1585.9	1474.9	1424.6	1375.6	1299.4	1237.5	1184.6	1125.2	1054.3	985.9	929.1
40°	1530.4	1402.7	1351.1	1305.9	1227.2	1158.8	1111.0	1064.6	1002.6	936.8	874.9
42.5°	1480.1	1335.6	1281.4	1234.9	1152.3	1087.8	1042.7	1003.9	949.7	889.1	825.9
45°	1410.4	1263.3	1207.8	1158.8	1074.9	1014.3	967.8	934.3	891.7	834.9	778.1
47.5°	1345.9	1193.6	1133.0	1073.6	997.5	935.5	893.0	867.2	838.8	788.4	730.4
50°	1267.2	1113.6	1051.7	1002.6	916.2	863.3	820.7	802.6	776.8	729.1	682.6
52.5°	1182.0	1036.2	978.1	918.8	838.8	787.1	749.7	729.1	708.4	673.6	629.7
55°	1082.7	949.7	895.5	842.6	762.6	714.9	681.3	659.4	647.8	615.5	583.3
57.5°	987.2	862.0	811.7	762.6	692.9	638.8	616.8	597.5	580.7	557.5	530.4
60°	890.4	776.8	722.6	678.8	618.1	569.1	551.0	531.6	518.7	500.7	481.3
62.5°	779.4	682.6	641.3	600.0	548.4	509.7	489.1	473.6	456.8	445.2	428.4
65°	662.0	593.6	553.6	522.6	473.6	438.7	423.3	412.9	398.7	387.1	374.2
67.5°	552.3	498.1	481.3	447.8	410.4	379.4	367.8	354.9	343.2	336.8	325.2
70°	446.5	407.8	391.0	382.0	340.7	320.0	309.7	304.5	290.3	283.9	276.1
72.5°	345.8	331.6	320.0	308.4	281.3	268.4	256.8	251.6	241.3	236.1	233.6
75°	255.5	246.5	240.0	238.7	227.1	214.2	202.6	200.0	192.3	187.1	184.5
77.5°	179.4	176.8	175.5	176.8	169.0	161.3	158.7	156.1	147.1	145.8	145.8
80°	117.4	123.9	123.9	122.6	120.0	118.7	114.8	112.3	107.1	105.8	107.1
82.5°	72.3	76.1	77.4	80.0	78.7	77.4	74.8	73.6	74.8	72.3	73.6
85°	36.1	38.7	43.9	43.9	45.2	45.2	45.2	43.9	41.3	42.6	41.3
87.5°	14.2	15.5	15.5	15.5	14.2	18.1	19.4	19.4	19.4	16.8	16.8
90°	12.3	11.2	10.0	8.9	6.7	4.5	2.2	1.1	2.2	4.5	6.7
92.5°	187.6	111.7	91.6	71.5	48.0	31.3	20.1	16.7	20.1	31.3	48.0
95°	253.5	134.0	108.8	83.7	59.2	46.9	38.0	36.8	38.0	46.9	59.2
97.5°	218.9	136.2	117.8	99.4	77.0	64.8	58.1	56.9	58.1	64.8	77.0
100°	216.6	151.9	135.2	118.4	97.1	84.9	80.4	78.2	80.4	84.9	97.1
102.5°	226.7	170.8	154.6	138.5	119.5	106.1	102.7	101.6	102.7	106.1	119.5
105°	241.2	192.1	176.4	160.8	142.9	131.8	126.2	126.2	126.2	131.8	142.9
107.5°	261.3	213.3	199.4	185.4	166.4	157.4	151.9	149.6	151.9	157.4	166.4
110°	283.6	237.8	223.3	208.8	192.1	182.0	177.5	175.3	177.5	182.0	192.1

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.8	261.3	247.4	233.4	216.6	206.6	203.2	201.0	203.2	206.6	216.6
115°	327.2	285.8	271.8	257.9	241.2	231.1	227.8	225.6	227.8	231.1	241.2
117.5°	349.5	310.4	297.0	283.6	264.6	254.6	251.2	247.9	251.2	254.6	264.6
120°	374.1	335.0	321.0	307.1	288.1	278.0	273.6	270.2	273.6	278.0	288.1
122.5°	397.5	358.4	344.4	330.5	309.3	299.2	295.9	293.7	295.9	299.2	309.3
125°	417.6	380.8	366.2	351.7	330.5	320.5	314.9	312.6	314.9	320.5	330.5
127.5°	437.7	402.0	387.4	372.9	350.6	338.3	331.6	328.3	331.6	338.3	350.6
130°	456.7	422.1	407.6	393.0	369.6	355.1	346.1	342.8	346.1	355.1	369.6
132.5°	474.6	439.9	425.4	410.9	386.3	369.6	358.4	354.0	358.4	369.6	386.3
135°	490.2	455.6	440.5	425.4	402.0	384.1	370.7	366.2	370.7	384.1	402.0
137.5°	501.3	470.1	454.4	438.8	415.4	397.5	385.2	381.9	385.2	397.5	415.4
140°	513.6	481.3	466.2	451.1	429.9	412.0	398.6	395.3	398.6	412.0	429.9
142.5°	521.4	491.3	477.4	463.4	443.3	425.4	413.1	410.9	413.1	425.4	443.3
145°	530.4	501.3	488.5	475.7	455.6	439.9	428.8	426.5	428.8	439.9	455.6
147.5°	536.0	510.3	498.6	486.8	469.0	454.5	444.4	443.3	444.4	454.5	469.0
150°	541.5	517.0	507.5	498.0	482.4	467.9	460.0	457.8	460.0	467.9	482.4
152.5°	547.1	524.8	516.4	508.0	493.5	481.3	474.6	473.4	474.6	481.3	493.5
155°	550.5	531.5	523.7	515.9	504.7	493.5	486.8	486.8	486.8	493.5	504.7
157.5°	553.8	537.1	531.0	524.8	514.7	504.7	499.1	499.1	499.1	504.7	514.7
160°	556.1	541.5	536.5	531.5	522.6	514.7	510.3	511.4	510.3	514.7	522.6
162.5°	558.3	546.0	542.1	538.2	531.5	524.8	520.3	521.4	520.3	524.8	531.5
165°	558.3	549.4	546.0	542.7	538.2	532.6	529.3	531.5	529.3	532.6	538.2
167.5°	558.3	550.5	548.2	546.0	542.7	539.3	537.1	538.2	537.1	539.3	542.7
170°	558.3	552.7	551.0	549.4	547.1	544.9	543.8	544.9	543.8	544.9	547.1
172.5°	557.2	552.7	552.2	551.6	550.5	548.2	547.1	549.4	547.1	548.2	550.5
175°	556.1	552.7	552.7	552.7	552.7	551.6	550.5	552.7	550.5	551.6	552.7
177.5°	554.9	552.7	552.7	552.7	553.8	552.7	552.7	554.9	552.7	552.7	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1551.1	1545.9	1542.0	1538.2	1521.4	1503.3	1500.7	1496.9	1489.1	1498.2	1494.3
5°	1511.1	1499.5	1493.0	1476.2	1455.6	1440.1	1427.2	1411.7	1405.3	1400.1	1398.8
7.5°	1462.0	1451.7	1440.1	1423.3	1397.5	1371.7	1352.3	1336.9	1324.0	1317.5	1317.5
10°	1414.3	1401.4	1385.9	1357.5	1333.0	1300.7	1280.1	1264.6	1246.5	1236.2	1227.2
12.5°	1365.3	1351.1	1336.9	1300.7	1272.3	1238.8	1209.1	1189.8	1180.7	1169.1	1153.6
15°	1316.2	1294.3	1280.1	1244.0	1207.8	1174.3	1154.9	1134.3	1113.6	1102.0	1096.8
17.5°	1264.6	1249.1	1225.9	1187.2	1147.2	1117.5	1089.1	1069.7	1045.2	1033.6	1022.0
20°	1218.1	1194.9	1171.7	1133.0	1094.3	1054.3	1025.9	1002.6	987.2	978.1	967.8
22.5°	1162.7	1140.7	1121.4	1080.1	1037.5	1000.1	969.1	954.9	939.4	925.2	914.9
25°	1114.9	1093.0	1073.6	1028.5	982.0	947.2	923.9	905.9	889.1	882.6	872.3
27.5°	1064.6	1043.9	1018.1	973.0	931.7	902.0	877.5	860.7	847.8	834.9	827.2
30°	1016.8	993.6	970.4	921.4	887.8	858.1	834.9	814.2	803.9	797.5	784.6
32.5°	970.4	940.7	921.4	876.2	843.9	815.5	796.2	778.1	765.2	753.6	743.3
35°	920.1	887.8	868.4	831.0	797.5	769.1	752.3	739.4	723.9	713.6	708.4
37.5°	872.3	845.2	825.9	787.1	753.6	730.4	712.3	695.5	689.1	674.9	672.3
40°	820.7	797.5	779.4	742.0	711.0	692.9	673.6	658.1	646.5	640.0	631.0
42.5°	774.2	754.9	735.5	700.7	671.0	649.1	634.9	620.7	610.4	600.0	593.6
45°	731.7	711.0	692.9	659.4	629.7	610.4	596.2	579.4	576.8	562.6	556.2
47.5°	686.5	668.4	652.9	618.1	591.0	571.7	554.9	543.3	531.6	526.5	517.5
50°	642.6	624.6	606.5	575.5	551.0	531.6	514.9	502.0	495.5	487.8	480.0
52.5°	594.9	580.7	566.5	534.2	509.7	492.9	478.7	462.0	455.5	449.1	443.9
55°	554.9	534.2	518.7	491.6	469.7	451.6	436.2	423.3	416.8	411.6	405.2
57.5°	500.7	487.8	474.9	450.4	429.7	411.6	396.2	385.8	378.1	374.2	375.5
60°	454.2	440.0	432.3	406.5	385.8	371.6	357.4	347.1	339.4	335.5	334.2
62.5°	405.2	394.9	380.7	362.6	342.0	329.1	318.7	311.0	298.1	296.8	292.9
65°	357.4	349.7	336.8	320.0	303.2	291.6	280.0	269.7	264.5	258.1	254.2
67.5°	311.0	303.2	291.6	277.4	265.8	254.2	243.9	233.6	224.5	219.4	216.8
70°	265.8	259.4	251.6	234.9	220.7	211.6	203.9	197.4	188.4	185.8	184.5
72.5°	222.0	215.5	211.6	197.4	184.5	176.8	169.0	162.6	158.7	157.4	153.6
75°	181.9	175.5	170.3	157.4	149.7	144.5	136.8	134.2	130.3	129.0	127.8
77.5°	141.9	135.5	134.2	125.2	116.1	113.6	111.0	105.8	105.8	105.8	103.2
80°	101.9	100.7	99.4	90.3	86.5	83.9	82.6	78.7	76.1	73.6	72.3
82.5°	68.4	67.1	65.8	61.9	58.1	56.8	55.5	52.9	52.9	54.2	51.6
85°	41.3	38.7	37.4	36.1	33.6	33.6	34.8	33.6	33.6	33.6	32.3
87.5°	15.5	15.5	15.5	15.5	16.8	14.2	15.5	15.5	14.2	14.2	12.9
90°	8.9	10.0	11.2	12.3	14.5	15.6	17.9	19.0	20.1	21.2	22.3
92.5°	71.5	91.6	111.7	187.6	314.9	453.3	445.5	359.5	242.3	174.2	129.5
95°	83.7	108.8	134.0	253.5	499.1	807.3	989.3	968.1	802.8	633.1	495.8
97.5°	99.4	117.8	136.2	218.9	407.6	740.3	1068.6	1209.3	1151.2	1016.1	877.6
100°	118.4	135.2	151.9	216.6	361.8	643.2	1008.3	1287.4	1373.4	1318.7	1203.7
102.5°	138.5	154.6	170.8	226.7	342.8	569.5	902.2	1240.5	1448.2	1504.0	1463.9
105°	160.8	176.4	192.1	241.2	340.6	527.0	809.5	1130.0	1398.0	1550.9	1600.1
107.5°	185.4	199.4	213.3	261.3	348.4	504.7	740.3	1025.0	1295.2	1497.3	1615.7
110°	208.8	223.3	237.8	283.6	360.7	495.8	694.5	937.9	1179.1	1391.3	1548.7

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.4	247.4	261.3	304.8	376.3	495.8	667.7	873.2	1087.6	1286.3	1446.0
115°	257.9	271.8	285.8	327.2	391.9	499.1	649.9	829.6	1013.9	1186.9	1339.9
117.5°	283.6	297.0	310.4	349.5	409.8	504.7	639.8	800.6	962.5	1115.5	1249.5
120°	307.1	321.0	335.0	374.1	427.7	513.6	633.1	777.1	922.3	1056.3	1179.1
122.5°	330.5	344.4	358.4	397.5	447.8	521.4	627.5	757.0	892.2	1013.9	1119.9
125°	351.7	366.2	380.8	417.6	465.6	530.4	623.1	739.2	863.1	977.0	1074.2
127.5°	372.9	387.4	402.0	437.7	482.4	540.4	620.8	722.4	833.0	941.3	1032.8
130°	393.0	407.6	422.1	456.7	499.1	549.4	618.6	705.7	805.1	903.3	990.4
132.5°	410.9	425.4	439.9	474.6	513.6	559.4	618.6	692.3	777.1	867.6	944.6
135°	425.4	440.5	455.6	490.2	527.0	568.3	618.6	682.2	753.7	830.7	902.2
137.5°	438.8	454.4	470.1	501.3	537.1	577.3	619.7	672.2	732.5	797.2	858.7
140°	451.1	466.2	481.3	513.6	547.1	582.9	620.8	665.5	715.7	768.2	819.6
142.5°	463.4	477.4	491.3	521.4	552.7	586.2	621.9	659.9	701.2	743.6	786.1
145°	475.7	488.5	501.3	530.4	558.3	588.4	620.8	654.3	688.9	723.6	758.2
147.5°	486.8	498.6	510.3	536.0	561.6	589.6	618.6	648.7	676.7	705.7	733.6
150°	498.0	507.5	517.0	541.5	565.0	589.6	615.2	642.0	666.6	691.2	712.4
152.5°	508.0	516.4	524.8	547.1	567.2	588.4	610.8	634.2	655.4	676.7	695.6
155°	515.9	523.7	531.5	550.5	568.3	586.2	605.2	625.3	644.3	662.1	677.8
157.5°	524.8	531.0	537.1	553.8	569.5	584.0	599.6	617.5	633.1	648.7	661.0
160°	531.5	536.5	541.5	556.1	569.5	580.6	594.0	607.4	621.9	633.1	644.3
162.5°	538.2	542.1	546.0	558.3	568.3	577.3	587.3	598.5	609.7	619.7	628.6
165°	542.7	546.0	549.4	558.3	567.2	573.9	580.6	589.6	598.5	606.3	613.0
167.5°	546.0	548.2	550.5	558.3	565.0	568.3	573.9	580.6	587.3	592.9	598.5
170°	549.4	551.0	552.7	558.3	562.8	565.0	568.3	572.8	578.4	581.7	585.1
172.5°	551.6	552.2	552.7	557.2	560.5	560.5	561.6	565.0	568.3	571.7	573.9
175°	552.7	552.7	552.7	556.1	558.3	557.2	557.2	558.3	561.6	561.6	563.9
177.5°	552.7	552.7	552.7	554.9	556.1	553.8	553.8	554.9	556.1	557.2	557.2
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1487.8	1490.4	1484.0	1481.4	1476.2	1482.7	1484.0	1482.7	1494.3	1489.1	1491.7
5°	1401.4	1396.2	1392.4	1383.3	1383.3	1384.6	1388.5	1382.0	1385.9	1394.9	1393.6
7.5°	1305.9	1303.3	1304.6	1294.3	1286.5	1289.1	1286.5	1298.2	1304.6	1302.0	1307.2
10°	1219.4	1224.6	1213.0	1207.8	1202.7	1207.8	1206.5	1209.1	1216.9	1222.0	1231.1
12.5°	1149.8	1148.5	1142.0	1136.9	1127.8	1130.4	1138.1	1135.6	1136.9	1148.5	1147.2
15°	1083.9	1076.2	1071.0	1059.4	1062.0	1053.0	1060.7	1069.7	1073.6	1083.9	1090.4
17.5°	1018.1	1016.8	1010.4	1009.1	994.9	991.0	998.8	1001.4	1005.2	1010.4	1019.4
20°	962.6	961.4	952.3	949.7	938.1	945.9	943.3	948.5	951.0	961.4	965.2
22.5°	912.3	905.9	903.3	899.4	895.5	894.3	899.4	898.1	907.2	911.0	912.3
25°	865.9	860.7	859.4	853.0	850.4	846.5	850.4	854.3	864.6	868.4	873.6
27.5°	823.3	819.4	816.8	811.7	807.8	807.8	810.4	815.5	819.4	822.0	824.6
30°	784.6	782.0	774.2	771.7	767.8	767.8	767.8	770.4	776.8	784.6	788.4
32.5°	744.6	739.4	734.2	734.2	730.4	730.4	731.7	734.2	740.7	742.0	748.4
35°	705.9	700.7	696.8	694.2	695.5	690.4	692.9	696.8	704.6	707.1	711.0
37.5°	668.4	667.1	659.4	655.5	658.1	658.1	656.8	659.4	664.6	669.7	672.3
40°	627.1	624.6	624.6	620.7	622.0	616.8	620.7	623.3	625.8	631.0	634.9
42.5°	591.0	588.4	583.3	584.6	580.7	580.7	583.3	584.6	588.4	594.9	597.5
45°	552.3	552.3	549.7	545.8	547.1	543.3	545.8	547.1	552.3	558.7	556.2
47.5°	514.9	513.6	513.6	508.4	511.0	507.1	511.0	512.3	514.9	518.7	517.5
50°	478.7	474.9	476.2	474.9	473.6	473.6	476.2	476.2	478.7	478.7	482.6
52.5°	441.3	441.3	438.7	440.0	442.6	440.0	443.9	440.0	442.6	443.9	446.5
55°	407.8	405.2	406.5	405.2	410.4	406.5	410.4	407.8	410.4	409.1	411.6
57.5°	371.6	367.8	369.1	367.8	371.6	370.3	374.2	370.3	371.6	372.9	376.8
60°	330.3	330.3	330.3	327.8	331.6	331.6	330.3	330.3	335.5	338.1	336.8
62.5°	291.6	290.3	286.5	285.2	286.5	283.9	289.1	287.8	290.3	292.9	295.5
65°	249.0	246.5	245.2	242.6	242.6	241.3	242.6	247.8	249.0	250.3	256.8
67.5°	214.2	212.9	211.6	207.8	207.8	210.3	210.3	210.3	218.1	214.2	219.4
70°	183.2	180.7	178.1	176.8	176.8	178.1	179.4	180.7	179.4	184.5	185.8
72.5°	153.6	154.8	152.3	152.3	152.3	151.0	151.0	153.6	154.8	153.6	154.8
75°	127.8	127.8	126.5	127.8	127.8	126.5	126.5	129.0	129.0	127.8	131.6
77.5°	103.2	101.9	99.4	96.8	98.1	96.8	98.1	96.8	100.7	104.5	101.9
80°	72.3	71.0	71.0	71.0	72.3	71.0	73.6	71.0	72.3	72.3	73.6
82.5°	51.6	52.9	52.9	51.6	52.9	51.6	52.9	52.9	52.9	51.6	52.9
85°	33.6	33.6	33.6	33.6	32.3	33.6	33.6	33.6	34.8	33.6	34.8
87.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	15.5	14.2	15.5
90°	23.5	24.6	24.6	24.6	25.7	25.7	25.7	24.6	24.6	24.6	23.5
92.5°	118.9	108.3	90.4	87.1	84.9	82.6	84.9	87.1	90.4	108.3	118.9
95°	448.9	402.0	322.7	289.2	280.3	262.4	280.3	289.2	322.7	402.0	448.9
97.5°	810.6	743.6	676.7	618.6	588.4	575.0	588.4	618.6	676.7	743.6	810.6
100°	1145.6	1087.6	1010.5	930.1	888.8	870.9	888.8	930.1	1010.5	1087.6	1145.6
102.5°	1429.2	1394.6	1310.9	1259.5	1213.7	1201.5	1213.7	1259.5	1310.9	1394.6	1429.2
105°	1593.9	1587.8	1552.1	1515.2	1492.9	1479.5	1492.9	1515.2	1552.1	1587.8	1593.9
107.5°	1640.2	1664.8	1674.9	1669.3	1658.1	1647.0	1658.1	1669.3	1674.9	1664.8	1640.2
110°	1596.2	1643.6	1693.9	1715.1	1722.9	1722.9	1722.9	1715.1	1693.9	1643.6	1596.2

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1504.0	1562.1	1641.4	1681.6	1703.9	1714.0	1703.9	1681.6	1641.4	1562.1	1504.0
115°	1400.8	1461.6	1548.7	1602.3	1633.6	1648.1	1633.6	1602.3	1548.7	1461.6	1400.8
117.5°	1307.0	1364.5	1452.7	1508.5	1539.8	1548.7	1539.8	1508.5	1452.7	1364.5	1307.0
120°	1228.2	1277.4	1360.0	1413.6	1443.8	1452.7	1443.8	1413.6	1360.0	1277.4	1228.2
122.5°	1165.2	1210.4	1281.8	1329.9	1360.0	1367.8	1360.0	1329.9	1281.8	1210.4	1165.2
125°	1114.4	1154.6	1217.1	1262.9	1287.4	1298.6	1287.4	1262.9	1217.1	1154.6	1114.4
127.5°	1070.8	1108.8	1165.7	1207.0	1230.5	1234.9	1230.5	1207.0	1165.7	1108.8	1070.8
130°	1026.7	1063.0	1118.8	1155.7	1178.0	1184.7	1178.0	1155.7	1118.8	1063.0	1026.7
132.5°	979.2	1013.9	1069.7	1106.5	1126.6	1134.5	1126.6	1106.5	1069.7	1013.9	979.2
135°	934.0	965.9	1015.0	1051.8	1071.9	1078.6	1071.9	1051.8	1015.0	965.9	934.0
137.5°	886.6	914.5	959.2	993.8	1012.7	1020.6	1012.7	993.8	959.2	914.5	886.6
140°	843.0	866.5	907.8	936.8	953.6	959.2	953.6	936.8	907.8	866.5	843.0
142.5°	805.7	825.2	858.7	882.1	897.7	902.2	897.7	882.1	858.7	825.2	805.7
145°	773.2	788.3	815.1	834.1	846.4	850.8	846.4	834.1	815.1	788.3	773.2
147.5°	745.3	757.0	779.4	795.0	802.8	805.1	802.8	795.0	779.4	757.0	745.3
150°	722.4	732.5	749.2	762.6	767.1	768.2	767.1	762.6	749.2	732.5	722.4
152.5°	702.9	710.2	723.6	733.6	738.1	739.2	738.1	733.6	723.6	710.2	702.9
155°	684.0	690.1	701.2	709.0	712.4	713.5	712.4	709.0	701.2	690.1	684.0
157.5°	666.0	671.1	680.0	686.7	690.1	690.1	690.1	686.7	680.0	671.1	666.0
160°	648.2	652.1	659.9	665.5	667.7	666.6	667.7	665.5	659.9	652.1	648.2
162.5°	632.0	635.3	640.9	645.4	645.4	645.4	645.4	645.4	640.9	635.3	632.0
165°	615.8	618.6	623.1	625.3	625.3	625.3	625.3	625.3	623.1	618.6	615.8
167.5°	600.8	603.0	605.2	607.4	606.3	606.3	606.3	607.4	605.2	603.0	600.8
170°	586.2	587.3	589.6	590.7	590.7	589.6	590.7	590.7	589.6	587.3	586.2
172.5°	574.4	575.0	575.0	577.3	575.0	573.9	575.0	577.3	575.0	575.0	574.4
175°	563.9	563.9	563.9	565.0	562.8	561.6	562.8	565.0	563.9	563.9	563.9
177.5°	557.2	557.2	556.1	557.2	553.8	553.8	553.8	557.2	556.1	557.2	557.2
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1486.6	1493.0	1487.8	1484.0	1494.3	1499.5	1499.5	1508.5	1517.5	1525.3	1526.6
5°	1394.9	1405.3	1407.8	1406.5	1422.0	1429.8	1446.5	1455.6	1468.5	1477.5	1487.8
7.5°	1311.1	1325.3	1326.5	1329.1	1352.3	1365.3	1379.4	1402.7	1420.7	1433.6	1445.3
10°	1227.2	1236.2	1245.2	1256.9	1280.1	1302.0	1322.7	1347.2	1370.4	1383.3	1400.1
12.5°	1163.9	1170.4	1180.7	1188.5	1213.0	1232.3	1259.4	1293.0	1326.5	1336.9	1357.5
15°	1098.1	1102.0	1122.7	1130.4	1151.0	1183.3	1200.1	1232.3	1268.5	1287.8	1311.1
17.5°	1022.0	1045.2	1058.1	1067.2	1093.0	1118.8	1145.9	1179.4	1225.9	1244.0	1260.7
20°	967.8	984.6	998.8	1010.4	1033.6	1072.3	1096.8	1123.9	1167.8	1188.5	1213.0
22.5°	920.1	934.3	947.2	960.1	975.5	1010.4	1038.8	1076.2	1120.1	1139.4	1167.8
25°	874.9	889.1	896.8	912.3	933.0	957.5	991.0	1024.6	1068.5	1090.4	1117.5
27.5°	831.0	845.2	859.4	872.3	886.5	909.7	933.0	975.5	1020.7	1046.5	1069.7
30°	793.6	800.1	813.0	827.2	841.3	863.3	890.4	920.1	971.7	994.9	1023.3
32.5°	752.3	763.9	773.0	783.3	801.3	819.4	843.9	881.3	922.6	944.6	975.5
35°	713.6	723.9	730.4	748.4	760.1	779.4	803.9	837.5	872.3	896.8	923.9
37.5°	676.2	686.5	694.2	704.6	720.0	736.8	762.6	787.1	828.4	849.1	880.1
40°	637.5	646.5	655.5	667.1	681.3	702.0	717.5	748.4	782.0	805.2	828.4
42.5°	600.0	605.2	615.5	628.4	642.6	660.7	682.6	707.1	740.7	761.3	782.0
45°	560.0	569.1	580.7	589.7	602.6	620.7	640.0	662.0	695.5	716.2	738.1
47.5°	522.6	529.1	536.8	551.0	567.8	580.7	601.3	622.0	652.9	672.3	692.9
50°	483.9	490.4	502.0	511.0	523.9	540.7	560.0	582.0	611.7	624.6	645.2
52.5°	447.8	450.4	462.0	471.0	483.9	503.3	518.7	538.1	566.5	580.7	601.3
55°	411.6	414.2	420.7	429.7	443.9	459.4	476.2	498.1	522.6	535.5	554.9
57.5°	374.2	376.8	383.3	389.7	403.9	418.1	437.4	455.5	480.0	491.6	509.7
60°	336.8	336.8	343.2	352.3	362.6	375.5	392.3	414.2	432.3	446.5	459.4
62.5°	296.8	300.7	304.5	311.0	322.6	338.1	352.3	367.8	389.7	400.0	411.6
65°	256.8	260.7	268.4	274.9	283.9	294.2	312.3	325.2	342.0	353.6	363.9
67.5°	222.0	225.8	231.0	238.7	245.2	256.8	269.7	282.6	300.7	308.4	316.2
70°	185.8	189.7	193.6	203.9	210.3	219.4	228.4	241.3	256.8	262.0	268.4
72.5°	157.4	158.7	163.9	166.5	175.5	183.2	193.6	201.3	212.9	219.4	224.5
75°	132.9	132.9	134.2	136.8	141.9	147.1	154.8	162.6	172.9	176.8	183.2
77.5°	104.5	108.4	107.1	109.7	112.3	114.8	121.3	126.5	136.8	139.4	141.9
80°	74.8	76.1	80.0	83.9	83.9	87.7	91.6	92.9	99.4	103.2	103.2
82.5°	54.2	55.5	54.2	55.5	56.8	58.1	61.9	67.1	67.1	68.4	71.0
85°	33.6	33.6	34.8	36.1	36.1	34.8	37.4	36.1	37.4	40.0	40.0
87.5°	16.8	15.5	15.5	15.5	15.5	15.5	16.8	15.5	16.8	16.8	16.8
90°	22.3	21.2	20.1	19.0	17.9	15.6	14.5	12.3	11.2	10.0	8.9
92.5°	129.5	174.2	242.3	359.5	445.5	453.3	314.9	187.6	111.7	91.6	71.5
95°	495.8	633.1	802.8	968.1	989.3	807.3	499.1	253.5	134.0	108.8	83.7
97.5°	877.6	1016.1	1151.2	1209.3	1068.6	740.3	407.6	218.9	136.2	117.8	99.4
100°	1203.7	1318.7	1373.4	1287.4	1008.3	643.2	361.8	216.6	151.9	135.2	118.4
102.5°	1463.9	1504.0	1448.2	1240.5	902.2	569.5	342.8	226.7	170.8	154.6	138.5
105°	1600.1	1550.9	1398.0	1130.0	809.5	527.0	340.6	241.2	192.1	176.4	160.8
107.5°	1615.7	1497.3	1295.2	1025.0	740.3	504.7	348.4	261.3	213.3	199.4	185.4
110°	1548.7	1391.3	1179.1	937.9	694.5	495.8	360.7	283.6	237.8	223.3	208.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1446.0	1286.3	1087.6	873.2	667.7	495.8	376.3	304.8	261.3	247.4	233.4
115°	1339.9	1186.9	1013.9	829.6	649.9	499.1	391.9	327.2	285.8	271.8	257.9
117.5°	1249.5	1115.5	962.5	800.6	639.8	504.7	409.8	349.5	310.4	297.0	283.6
120°	1179.1	1056.3	922.3	777.1	633.1	513.6	427.7	374.1	335.0	321.0	307.1
122.5°	1119.9	1013.9	892.2	757.0	627.5	521.4	447.8	397.5	358.4	344.4	330.5
125°	1074.2	977.0	863.1	739.2	623.1	530.4	465.6	417.6	380.8	366.2	351.7
127.5°	1032.8	941.3	833.0	722.4	620.8	540.4	482.4	437.7	402.0	387.4	372.9
130°	990.4	903.3	805.1	705.7	618.6	549.4	499.1	456.7	422.1	407.6	393.0
132.5°	944.6	867.6	777.1	692.3	618.6	559.4	513.6	474.6	439.9	425.4	410.9
135°	902.2	830.7	753.7	682.2	618.6	568.3	527.0	490.2	455.6	440.5	425.4
137.5°	858.7	797.2	732.5	672.2	619.7	577.3	537.1	501.3	470.1	454.4	438.8
140°	819.6	768.2	715.7	665.5	620.8	582.9	547.1	513.6	481.3	466.2	451.1
142.5°	786.1	743.6	701.2	659.9	621.9	586.2	552.7	521.4	491.3	477.4	463.4
145°	758.2	723.6	688.9	654.3	620.8	588.4	558.3	530.4	501.3	488.5	475.7
147.5°	733.6	705.7	676.7	648.7	618.6	589.6	561.6	536.0	510.3	498.6	486.8
150°	712.4	691.2	666.6	642.0	615.2	589.6	565.0	541.5	517.0	507.5	498.0
152.5°	695.6	676.7	655.4	634.2	610.8	588.4	567.2	547.1	524.8	516.4	508.0
155°	677.8	662.1	644.3	625.3	605.2	586.2	568.3	550.5	531.5	523.7	515.9
157.5°	661.0	648.7	633.1	617.5	599.6	584.0	569.5	553.8	537.1	531.0	524.8
160°	644.3	633.1	621.9	607.4	594.0	580.6	569.5	556.1	541.5	536.5	531.5
162.5°	628.6	619.7	609.7	598.5	587.3	577.3	568.3	558.3	546.0	542.1	538.2
165°	613.0	606.3	598.5	589.6	580.6	573.9	567.2	558.3	549.4	546.0	542.7
167.5°	598.5	592.9	587.3	580.6	573.9	568.3	565.0	558.3	550.5	548.2	546.0
170°	585.1	581.7	578.4	572.8	568.3	565.0	562.8	558.3	552.7	551.0	549.4
172.5°	573.9	571.7	568.3	565.0	561.6	560.5	560.5	557.2	552.7	552.2	551.6
175°	563.9	561.6	561.6	558.3	557.2	557.2	558.3	556.1	552.7	552.7	552.7
177.5°	557.2	557.2	556.1	554.9	553.8	553.8	556.1	554.9	552.7	552.7	552.7
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1571.7	1571.7	1571.7	1571.7
2.5°	1535.6	1547.2	1558.8	1573.0
5°	1504.6	1525.3	1547.2	1567.8
7.5°	1471.1	1500.7	1529.1	1558.8
10°	1433.6	1471.1	1503.3	1544.6
12.5°	1392.4	1432.4	1477.5	1524.0
15°	1351.1	1401.4	1449.1	1502.0
17.5°	1312.3	1360.1	1413.0	1476.2
20°	1265.9	1318.8	1378.2	1445.3
22.5°	1216.9	1274.9	1339.4	1411.7
25°	1175.6	1234.9	1296.9	1373.0
27.5°	1130.4	1192.3	1253.0	1334.3
30°	1078.8	1145.9	1207.8	1291.7
32.5°	1029.7	1096.8	1165.2	1244.0
35°	982.0	1047.8	1116.2	1196.2
37.5°	936.8	996.2	1063.3	1135.6
40°	894.3	948.5	1007.8	1073.6
42.5°	840.1	903.3	958.8	1006.5
45°	793.6	845.2	896.8	935.5
47.5°	739.4	791.0	834.9	865.9
50°	694.2	735.5	771.7	798.8
52.5°	640.0	678.8	708.4	729.1
55°	587.1	620.7	646.5	660.7
57.5°	539.4	561.3	580.7	593.6
60°	486.5	503.3	520.0	534.2
62.5°	429.7	447.8	456.8	472.3
65°	379.4	391.0	405.2	410.4
67.5°	330.3	336.8	345.8	356.2
70°	278.7	282.6	291.6	305.8
72.5°	233.6	237.4	243.9	249.0
75°	185.8	189.7	194.9	200.0
77.5°	145.8	147.1	149.7	154.8
80°	105.8	109.7	112.3	113.6
82.5°	73.6	74.8	74.8	76.1
85°	46.5	43.9	43.9	45.2
87.5°	16.8	19.4	19.4	21.9
90°	6.7	4.5	2.2	1.1
92.5°	48.0	31.3	20.1	16.7
95°	59.2	46.9	38.0	36.8
97.5°	77.0	64.8	58.1	56.9
100°	97.1	84.9	80.4	78.2
102.5°	119.5	106.1	102.7	101.6
105°	142.9	131.8	126.2	126.2
107.5°	166.4	157.4	151.9	149.6
110°	192.1	182.0	177.5	175.3

TEST NUMBER: P1028470

CATALOG NUMBER: S125RDIP-B1090D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	216.6	206.6	203.2	201.0
115°	241.2	231.1	227.8	225.6
117.5°	264.6	254.6	251.2	247.9
120°	288.1	278.0	273.6	270.2
122.5°	309.3	299.2	295.9	293.7
125°	330.5	320.5	314.9	312.6
127.5°	350.6	338.3	331.6	328.3
130°	369.6	355.1	346.1	342.8
132.5°	386.3	369.6	358.4	354.0
135°	402.0	384.1	370.7	366.2
137.5°	415.4	397.5	385.2	381.9
140°	429.9	412.0	398.6	395.3
142.5°	443.3	425.4	413.1	410.9
145°	455.6	439.9	428.8	426.5
147.5°	469.0	454.5	444.4	443.3
150°	482.4	467.9	460.0	457.8
152.5°	493.5	481.3	474.6	473.4
155°	504.7	493.5	486.8	486.8
157.5°	514.7	504.7	499.1	499.1
160°	522.6	514.7	510.3	511.4
162.5°	531.5	524.8	520.3	521.4
165°	538.2	532.6	529.3	531.5
167.5°	542.7	539.3	537.1	538.2
170°	547.1	544.9	543.8	544.9
172.5°	550.5	548.2	547.1	549.4
175°	552.7	551.6	550.5	552.7
177.5°	553.8	552.7	552.7	554.9
180°	553.8	553.8	553.8	553.8

(END OF REPORT)