

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028476

Luminaire Tested: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028476
REPORT IS A COMBINATION OF REPORTS P1005001 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5512.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 56.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot





TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	80	80	80	76								
1	104	100	96	93	99	96	92	89	87	84	82	79	77	75	72	71	69	66								
2	96	88	82	77	91	84	79	74	77	73	69	70	67	64	64	61	59	56								
3	88	78	71	65	83	75	68	63	68	63	59	63	58	55	57	54	51	48								
4	80	70	62	55	76	67	59	54	61	55	51	56	51	47	52	48	44	42								
5	74	62	54	48	70	60	52	47	55	49	44	51	46	41	47	42	39	36								
6	68	56	48	42	65	54	46	41	50	43	39	46	41	37	42	38	34	32								
7	64	51	43	37	60	49	42	36	45	39	34	42	37	33	39	34	31	29								
8	59	46	39	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26								
9	55	43	35	30	53	41	34	29	38	32	28	36	30	26	33	28	25	23								
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10382	10382	10382	10382
5°	10373	11701	10373	8994
10°	10315	13149	10280	7775
15°	10203	13911	10133	6769
20°	10068	15017	9978	6118
25°	9891	16997	9780	5553
30°	9712	18067	9566	5149
35°	9480	14858	9347	4771
40°	9067	10090	8991	4433
45°	8526	7253	8515	4099
50°	7971	5578	8010	3791
55°	7346	4536	7332	3494
60°	6765	3717	6732	3102
65°	6087	3097	6125	2497
70°	5527	2486	5504	2079
75°	4669	1884	4669	1709
80°	3784	1149	3739	1149
85°	2664	604	2584	683

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14778 cd/sqm

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	2.8
10°-20°	455.5	8.3
20°-30°	722.3	13.1
30°-40°	872.8	15.8
40°-50°	777.1	14.1
50°-60°	595.9	10.8
60°-70°	387.0	7.0
70°-80°	187.8	3.4
80°-90°	44.9	0.8
90°-100°	127.2	2.3
100°-110°	274.3	5.0
110°-120°	255.7	4.6
120°-130°	207.1	3.8
130°-140°	166.3	3.0
140°-150°	125.4	2.3
150°-160°	88.3	1.6
160°-170°	52.1	0.9
170°-180°	16.9	0.3
0°-30°	1333.2	24.2
0°-40°	2206.0	40.0
0°-60°	3579.0	64.9
0°-90°	4198.7	76.2
90°-120°	657.2	11.9
90°-150°	1156.0	21.0
90°-180°	1313.0	23.8
0°-180°	5512.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1620	1620	1620	1620	1620	
5°	1616	1857	1616	1428	1616	154
15°	1548	2231	1538	1086	1548	437
25°	1416	2671	1400	873	1416	652
35°	1233	2216	1216	712	1233	768
45°	964	991	963	560	964	744
55°	681	544	680	419	681	610
65°	423	309	426	249	423	423
75°	206	144	206	130	206	221
85°	47	31	45	35	47	53
90°	0	8	0	8	0	4
95°	12	83	12	83	12	12
105°	40	467	40	467	40	42
115°	71	520	71	520	71	70
125°	99	410	99	410	99	88
135°	116	340	116	340	116	90
145°	135	269	135	269	135	84
155°	154	225	154	225	154	71
165°	168	197	168	197	168	47
175°	174	177	174	177	174	17
180°	175	175	175	175	175	

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1621.7	1635.0	1639.0	1649.6	1661.6	1664.3	1670.9	1680.2	1685.5	1684.2	1684.2
5°	1616.4	1639.0	1654.9	1673.6	1696.2	1705.5	1713.5	1733.4	1749.4	1758.7	1774.7
7.5°	1607.0	1640.3	1666.9	1694.9	1729.4	1745.4	1762.7	1790.6	1819.9	1838.5	1855.8
10°	1592.4	1635.0	1672.2	1713.5	1760.0	1784.0	1805.3	1847.8	1883.8	1907.7	1947.6
12.5°	1571.1	1624.3	1676.2	1730.8	1789.3	1814.6	1843.8	1890.4	1941.0	1975.6	2008.8
15°	1548.5	1612.4	1668.2	1733.4	1803.9	1842.5	1879.8	1929.0	1974.2	2012.8	2051.4
17.5°	1521.9	1589.8	1658.9	1733.4	1813.3	1851.8	1883.8	1942.3	1990.2	2028.8	2063.4
20°	1490.0	1565.8	1644.3	1726.8	1807.9	1843.8	1874.4	1938.3	1980.9	2022.1	2071.3
22.5°	1455.4	1537.9	1621.7	1702.8	1782.7	1821.2	1857.2	1913.0	1959.6	2015.5	2079.3
25°	1415.5	1505.9	1591.1	1672.2	1748.1	1784.0	1815.9	1877.1	1942.3	2012.8	2084.6
27.5°	1375.6	1463.4	1545.9	1620.4	1702.8	1736.1	1768.0	1845.2	1922.3	1996.8	2095.3
30°	1331.7	1420.8	1492.6	1561.8	1641.6	1676.2	1716.1	1803.9	1891.7	1992.8	2112.6
32.5°	1282.4	1363.6	1430.1	1502.0	1573.8	1616.4	1666.9	1762.7	1863.8	1984.9	2137.9
35°	1233.2	1298.4	1359.6	1427.5	1513.9	1559.2	1608.4	1709.5	1835.9	1980.9	2159.1
37.5°	1170.7	1233.2	1281.1	1350.3	1439.4	1492.6	1541.9	1658.9	1802.6	1971.6	2157.8
40°	1106.8	1160.1	1205.3	1277.1	1374.2	1423.5	1476.7	1604.4	1768.0	1945.0	2125.9
42.5°	1037.7	1082.9	1132.1	1201.3	1295.7	1343.6	1404.8	1553.8	1720.1	1907.7	2043.4
45°	964.5	1008.4	1049.6	1121.5	1215.9	1267.8	1334.3	1487.3	1661.6	1829.2	1910.4
47.5°	892.7	931.2	975.1	1037.7	1133.4	1190.7	1258.5	1422.1	1583.1	1724.1	1730.8
50°	823.5	854.1	891.3	955.2	1055.0	1109.5	1180.0	1333.0	1490.0	1587.1	1521.9
52.5°	751.6	779.6	818.2	874.0	967.2	1031.0	1092.2	1245.2	1376.9	1442.1	1322.4
55°	681.1	705.1	745.0	807.5	888.7	937.9	1000.4	1142.8	1258.5	1259.8	1129.5
57.5°	612.0	633.2	666.5	722.4	798.2	855.4	912.6	1036.3	1114.8	1092.2	947.2
60°	550.8	564.1	594.7	649.2	719.7	761.0	822.1	925.9	977.8	936.6	780.9
62.5°	486.9	500.2	524.2	568.1	634.6	678.5	717.1	802.2	838.1	775.6	647.9
65°	423.0	439.0	456.3	490.9	553.4	582.7	617.3	679.8	714.4	641.2	530.8
67.5°	367.2	375.2	392.4	428.4	472.3	498.9	522.8	565.4	572.0	513.5	423.0
70°	315.3	318.0	333.9	355.2	388.5	404.4	424.4	449.7	449.7	401.8	329.9
72.5°	256.8	260.7	272.7	295.3	315.3	323.3	329.9	345.9	343.2	299.3	250.1
75°	206.2	208.9	218.2	228.8	236.8	251.4	256.8	254.1	252.8	215.5	187.6
77.5°	159.6	161.0	167.6	176.9	178.3	183.6	179.6	179.6	167.6	146.3	131.7
80°	117.1	118.4	121.1	123.7	123.7	123.7	123.7	117.1	109.1	95.8	91.8
82.5°	78.5	78.5	79.8	82.5	81.2	78.5	75.8	69.2	63.9	59.9	57.2
85°	46.6	46.6	47.9	46.6	41.2	39.9	37.2	35.9	34.6	33.3	33.3
87.5°	22.6	21.3	18.6	16.0	16.0	16.0	16.0	16.0	16.0	14.6	14.6
90°	0.4	0.7	1.4	2.1	2.8	3.2	3.5	3.9	4.6	4.9	5.6
92.5°	5.3	6.3	9.9	15.2	22.6	29.0	35.3	59.2	99.4	143.1	140.7
95°	11.6	12.0	14.8	18.7	26.4	34.3	42.3	80.0	157.6	254.9	312.3
97.5°	18.0	18.3	20.4	24.3	31.4	37.2	43.0	69.1	128.7	233.7	337.4
100°	24.7	25.4	26.8	30.7	37.4	42.6	47.9	68.4	114.2	203.1	318.3
102.5°	32.1	32.4	33.5	37.7	43.7	48.8	53.9	71.6	108.2	179.8	284.8
105°	39.8	39.8	41.6	45.1	50.8	55.7	60.6	76.1	107.5	166.4	255.6
107.5°	47.2	47.9	49.7	52.5	58.5	62.9	67.3	82.5	110.0	159.3	233.7
110°	55.3	56.1	57.5	60.6	65.9	70.5	75.1	89.5	113.9	156.5	219.3

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	63.5	64.2	65.2	68.4	73.7	78.1	82.5	96.2	118.8	156.5	210.8
115°	71.2	71.9	73.0	76.1	81.4	85.8	90.2	103.3	123.7	157.6	205.2
117.5°	78.3	79.3	80.4	83.5	89.5	93.8	98.0	110.3	129.4	159.3	202.0
120°	85.3	86.4	87.8	91.0	96.9	101.4	105.8	118.1	135.0	162.2	199.9
122.5°	92.7	93.4	94.5	97.6	104.3	108.8	113.2	125.5	141.4	164.6	198.1
125°	98.7	99.4	101.2	104.3	111.0	115.6	120.2	131.8	147.0	167.4	196.7
127.5°	103.6	104.7	106.8	110.7	117.7	122.3	126.9	138.2	152.3	170.6	196.0
130°	108.2	109.3	112.1	116.7	124.1	128.7	133.3	144.2	157.6	173.4	195.3
132.5°	111.7	113.2	116.7	122.0	129.7	134.3	138.9	149.8	162.2	176.6	195.3
135°	115.6	117.0	121.3	126.9	134.3	139.0	143.8	154.8	166.4	179.4	195.3
137.5°	120.6	121.6	125.5	131.1	138.5	143.4	148.4	158.3	169.6	182.3	195.7
140°	124.8	125.9	130.1	135.7	142.4	147.2	151.9	162.2	172.7	184.0	196.0
142.5°	129.7	130.4	134.3	140.0	146.3	150.7	155.1	164.6	174.5	185.1	196.4
145°	134.7	135.4	138.9	143.8	150.2	154.2	158.3	167.4	176.3	185.8	196.0
147.5°	140.0	140.3	143.5	148.1	153.7	157.4	161.1	169.2	177.3	186.1	195.3
150°	144.5	145.2	147.7	152.3	157.2	160.2	163.2	171.0	178.4	186.1	194.2
152.5°	149.5	149.8	151.9	155.8	160.4	163.0	165.7	172.7	179.1	185.8	192.8
155°	153.7	153.7	155.8	159.3	162.9	165.4	167.8	173.8	179.4	185.1	191.1
157.5°	157.6	157.6	159.3	162.5	165.7	167.6	169.6	174.9	179.8	184.4	189.3
160°	161.5	161.1	162.5	165.0	167.8	169.4	171.0	175.6	179.8	183.3	187.5
162.5°	164.6	164.3	165.7	167.8	169.9	171.2	172.4	176.3	179.4	182.3	185.4
165°	167.8	167.1	168.2	169.9	171.3	172.4	173.4	176.3	179.1	181.2	183.3
167.5°	169.9	169.6	170.3	171.3	172.4	173.1	173.8	176.3	178.4	179.4	181.2
170°	172.0	171.7	172.0	172.7	173.4	174.0	174.5	176.3	177.7	178.4	179.4
172.5°	173.4	172.7	173.1	173.8	174.1	174.3	174.5	175.9	177.0	177.0	177.3
175°	174.5	173.8	174.1	174.5	174.5	174.5	174.5	175.6	176.3	175.9	175.9
177.5°	175.2	174.5	174.5	174.9	174.5	174.5	174.5	175.2	175.6	174.9	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1690.9	1700.2	1708.2	1704.2	1720.1	1718.8	1721.5	1726.8	1728.1	1725.4	1720.1
5°	1782.7	1796.0	1818.6	1830.5	1827.9	1838.5	1843.8	1851.8	1859.8	1857.2	1857.2
7.5°	1885.1	1903.7	1926.3	1956.9	1960.9	1970.2	1986.2	1986.2	1995.5	1991.5	1990.2
10°	1974.2	1996.8	2032.8	2056.7	2067.3	2072.7	2088.6	2094.0	2104.6	2105.9	2105.9
12.5°	2047.4	2087.3	2111.2	2135.2	2140.5	2148.5	2160.5	2168.5	2172.4	2172.4	2168.5
15°	2086.0	2117.9	2145.8	2171.1	2185.7	2192.4	2204.4	2213.7	2219.0	2231.0	2233.6
17.5°	2101.9	2140.5	2185.7	2221.7	2246.9	2253.6	2277.5	2285.5	2296.2	2301.5	2308.1
20°	2124.6	2180.4	2235.0	2278.9	2302.8	2320.1	2345.4	2382.6	2393.3	2393.3	2389.3
22.5°	2144.5	2216.3	2290.8	2361.4	2381.3	2415.9	2462.5	2502.4	2518.3	2525.0	2519.7
25°	2168.5	2266.9	2364.0	2451.8	2506.4	2531.6	2594.2	2642.1	2660.7	2671.3	2674.0
27.5°	2209.7	2333.4	2457.1	2568.9	2624.8	2654.0	2719.2	2760.5	2783.1	2792.4	2785.7
30°	2256.3	2407.9	2551.6	2651.4	2688.6	2724.5	2767.1	2783.1	2777.7	2777.7	2797.7
32.5°	2304.1	2461.1	2588.8	2654.0	2667.3	2662.0	2644.7	2596.8	2568.9	2568.9	2586.2
35°	2330.8	2466.4	2531.6	2510.3	2458.5	2427.9	2333.4	2280.2	2220.3	2216.3	2236.3
37.5°	2316.1	2374.7	2348.0	2208.4	2137.9	2079.3	1931.7	1873.1	1829.2	1768.0	1862.5
40°	2213.7	2193.7	2055.4	1854.5	1776.0	1693.5	1576.5	1517.9	1456.7	1447.4	1470.0
42.5°	2040.7	1922.3	1720.1	1525.9	1446.1	1387.5	1298.4	1241.2	1202.6	1186.7	1213.3
45°	1825.2	1639.0	1436.8	1282.4	1194.6	1164.0	1082.9	1032.3	1003.1	991.1	1009.7
47.5°	1561.8	1374.2	1182.7	1052.3	1000.4	969.8	915.3	871.4	846.1	838.1	846.1
50°	1326.3	1133.4	972.5	888.7	842.1	816.8	771.6	743.7	723.7	718.4	731.7
52.5°	1122.8	947.2	824.8	750.3	719.7	698.4	666.5	642.6	630.6	625.3	634.6
55°	940.5	798.2	699.8	635.9	613.3	600.0	572.0	558.7	545.4	544.1	553.4
57.5°	779.6	681.1	590.7	545.4	538.8	518.8	494.9	482.9	476.3	474.9	478.9
60°	649.2	561.4	506.9	466.9	457.6	441.7	428.4	420.4	412.4	409.7	412.4
62.5°	540.1	470.9	427.0	400.4	387.1	383.1	368.5	359.2	357.9	357.9	360.5
65°	445.7	387.1	359.2	337.9	328.6	324.6	314.0	307.3	308.6	308.6	310.0
67.5°	363.2	320.6	295.3	284.7	276.7	275.4	264.7	262.1	259.4	259.4	262.1
70°	288.7	262.1	243.5	238.1	236.8	227.5	223.5	222.2	218.2	219.5	219.5
72.5°	226.2	208.9	198.2	190.2	191.6	186.2	180.9	180.9	178.3	182.3	182.3
75°	167.6	159.6	151.7	149.0	151.7	149.0	145.0	143.7	145.0	143.7	143.7
77.5°	123.7	119.7	117.1	115.7	115.7	110.4	107.8	110.4	105.1	107.8	107.8
80°	86.5	81.2	79.8	77.2	78.5	74.5	75.8	73.2	73.2	73.2	73.2
82.5°	54.5	53.2	53.2	53.2	51.9	51.9	51.9	51.9	51.9	51.9	50.6
85°	33.3	31.9	31.9	31.9	30.6	30.6	30.6	30.6	30.6	30.6	30.6
87.5°	13.3	14.6	14.6	16.0	14.6	13.3	13.3	13.3	14.6	14.6	13.3
90°	6.0	6.3	6.7	7.1	7.4	7.8	7.8	7.8	8.1	8.1	8.1
92.5°	113.5	76.5	55.0	40.9	37.6	34.2	28.6	27.5	26.8	26.1	26.8
95°	305.6	253.5	199.9	156.5	141.7	126.9	101.9	91.3	88.5	82.8	88.5
97.5°	381.8	363.5	320.8	277.1	256.0	234.8	213.6	195.3	185.8	181.5	185.8
100°	406.5	433.6	416.3	380.0	361.7	343.4	319.0	293.7	280.6	275.0	280.6
102.5°	391.7	457.2	474.8	462.2	451.2	440.3	413.9	397.6	383.2	379.3	383.2
105°	356.8	441.4	489.7	505.2	503.2	501.3	490.0	478.4	471.3	467.1	471.3
107.5°	323.6	408.9	472.7	510.1	517.8	525.6	528.8	527.0	523.5	520.0	523.5
110°	296.1	372.3	439.2	488.9	503.9	518.9	534.8	541.5	543.9	543.9	543.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	275.7	343.4	406.1	456.5	474.8	493.2	518.2	530.9	537.9	541.1	537.9
115°	261.9	320.1	374.7	423.0	442.2	461.5	488.9	505.9	515.7	520.3	515.7
117.5°	252.8	303.9	352.2	394.5	412.6	430.8	458.6	476.3	486.1	488.9	486.1
120°	245.4	291.2	333.5	372.3	387.8	403.3	429.4	446.3	455.8	458.6	455.8
122.5°	239.0	281.7	320.1	353.6	367.8	382.1	404.7	419.9	429.4	431.8	429.4
125°	233.4	272.5	308.5	339.1	351.8	364.5	384.2	398.7	406.5	410.0	406.5
127.5°	228.1	263.0	297.2	326.1	338.1	350.1	368.0	381.1	388.5	389.9	388.5
130°	222.8	254.2	285.2	312.7	324.2	335.6	353.2	364.9	371.9	374.0	371.9
132.5°	218.6	245.4	273.9	298.2	309.2	320.1	337.7	349.4	355.7	358.2	355.7
135°	215.4	238.0	262.3	284.8	294.8	304.9	320.4	332.1	338.4	340.5	338.4
137.5°	212.2	231.3	251.7	271.1	279.9	288.7	302.8	313.7	319.7	322.2	319.7
140°	210.1	226.0	242.5	258.8	266.2	273.6	286.6	295.8	301.1	302.8	301.1
142.5°	208.3	221.4	234.8	248.2	254.4	260.5	271.1	278.5	283.4	284.8	283.4
145°	206.6	217.5	228.4	239.4	244.2	248.9	257.3	263.3	267.2	268.6	267.2
147.5°	204.8	213.6	222.8	231.6	235.3	239.0	246.1	251.0	253.5	254.2	253.5
150°	202.7	210.5	218.2	224.9	228.1	231.3	236.5	240.8	242.2	242.5	242.2
152.5°	200.2	206.9	213.6	219.6	221.9	224.2	228.4	231.6	233.0	233.4	233.0
155°	197.4	203.4	209.0	214.0	216.0	217.9	221.4	223.9	224.9	225.3	224.9
157.5°	194.9	199.9	204.8	208.7	210.3	211.9	214.7	216.8	217.9	217.9	217.9
160°	191.8	196.4	199.9	203.4	204.6	205.9	208.3	210.1	210.8	210.5	210.8
162.5°	189.0	192.5	195.7	198.5	199.6	200.6	202.3	203.8	203.8	203.8	203.8
165°	186.1	189.0	191.4	193.5	194.4	195.3	196.7	197.4	197.4	197.4	197.4
167.5°	183.3	185.4	187.2	189.0	189.7	190.4	191.1	191.8	191.4	191.4	191.4
170°	180.8	182.6	183.7	184.7	185.0	185.4	186.1	186.5	186.5	186.1	186.5
172.5°	178.4	179.4	180.5	181.2	181.4	181.5	181.5	182.3	181.5	181.2	181.5
175°	176.3	177.3	177.3	178.0	178.0	178.0	178.0	178.4	177.7	177.3	177.7
177.5°	175.2	175.6	175.9	175.9	175.9	175.9	175.6	175.9	174.9	174.9	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1726.8	1717.5	1721.5	1717.5	1713.5	1709.5	1700.2	1686.9	1676.2	1668.2	1666.9
5°	1859.8	1847.8	1839.9	1835.9	1827.9	1817.2	1799.9	1780.0	1756.0	1746.7	1728.1
7.5°	1982.2	1978.2	1959.6	1956.9	1951.6	1931.7	1902.4	1875.8	1845.2	1819.9	1796.0
10°	2097.9	2088.6	2075.3	2056.7	2054.0	2028.8	2000.8	1963.6	1923.7	1899.7	1857.2
12.5°	2169.8	2159.1	2144.5	2132.5	2125.9	2109.9	2071.3	2034.1	1998.2	1954.3	1917.0
15°	2221.7	2208.4	2181.8	2172.4	2164.5	2143.2	2115.2	2076.7	2028.8	1998.2	1945.0
17.5°	2292.2	2276.2	2249.6	2232.3	2217.7	2184.4	2144.5	2092.6	2047.4	2012.8	1964.9
20°	2373.3	2349.4	2314.8	2292.2	2270.9	2232.3	2176.4	2115.2	2050.1	2007.5	1958.3
22.5°	2507.7	2462.5	2407.9	2376.0	2346.7	2280.2	2213.7	2137.9	2064.7	2000.8	1941.0
25°	2638.1	2592.8	2525.0	2481.1	2435.9	2358.7	2270.9	2165.8	2072.7	1998.2	1919.7
27.5°	2759.1	2712.6	2650.0	2596.8	2552.9	2437.2	2321.4	2203.0	2084.6	1982.2	1902.4
30°	2787.1	2767.1	2719.2	2672.7	2632.7	2526.3	2391.9	2241.6	2099.3	1967.6	1878.4
32.5°	2618.1	2667.3	2679.3	2672.7	2647.4	2571.5	2447.8	2289.5	2120.6	1960.9	1838.5
35°	2266.9	2356.0	2447.8	2497.0	2521.0	2531.6	2458.5	2313.5	2135.2	1950.3	1811.9
37.5°	1879.8	1966.2	2111.2	2184.4	2265.6	2372.0	2401.3	2308.1	2128.5	1942.3	1769.4
40°	1544.5	1654.9	1774.7	1841.2	1911.7	2103.3	2248.3	2237.6	2107.3	1913.0	1736.1
42.5°	1257.2	1326.3	1431.4	1504.6	1591.1	1805.3	1999.5	2095.3	2043.4	1877.1	1693.5
45°	1048.3	1101.5	1176.0	1250.5	1303.7	1498.0	1728.1	1885.1	1934.3	1813.3	1628.3
47.5°	883.3	923.3	988.4	1035.0	1092.2	1245.2	1444.7	1665.6	1769.4	1722.8	1559.2
50°	757.0	788.9	840.8	870.0	920.6	1052.3	1204.0	1435.4	1592.4	1597.7	1467.4
52.5°	646.5	678.5	722.4	747.7	778.2	867.4	1020.4	1215.9	1396.9	1463.4	1362.3
55°	562.7	581.4	617.3	637.2	665.2	751.6	848.8	1015.0	1204.0	1313.0	1249.2
57.5°	485.6	505.5	528.1	544.1	564.1	633.2	721.0	846.1	1033.7	1152.1	1130.8
60°	423.0	435.0	456.3	468.3	486.9	532.1	593.3	718.4	867.4	979.1	991.1
62.5°	364.5	375.2	389.8	400.4	412.4	448.3	493.6	582.7	713.1	834.1	850.1
65°	314.0	323.3	331.3	340.6	349.9	372.5	411.1	480.3	581.4	694.4	729.0
67.5°	268.7	271.4	283.4	284.7	290.0	307.3	335.2	391.1	464.3	554.8	600.0
70°	224.8	230.1	232.8	236.8	242.1	254.1	276.7	306.0	360.5	433.7	476.3
72.5°	182.3	183.6	187.6	190.2	195.6	204.9	215.5	238.1	272.7	325.9	364.5
75°	145.0	146.3	149.0	150.3	154.3	157.0	162.3	178.3	202.2	234.1	262.1
77.5°	109.1	111.7	114.4	114.4	115.7	118.4	121.1	126.4	138.4	159.6	183.6
80°	74.5	75.8	75.8	77.2	75.8	79.8	83.8	90.5	95.8	102.4	114.4
82.5°	51.9	51.9	51.9	53.2	53.2	54.5	54.5	55.9	57.2	61.2	66.5
85°	31.9	31.9	33.3	30.6	31.9	33.3	33.3	31.9	33.3	34.6	35.9
87.5°	13.3	13.3	14.6	14.6	14.6	14.6	13.3	14.6	13.3	14.6	14.6
90°	7.8	7.8	7.8	7.4	7.1	6.7	6.3	6.0	5.6	4.9	4.6
92.5°	27.5	28.6	34.2	37.6	40.9	55.0	76.5	113.5	140.7	143.1	99.4
95°	91.3	101.9	126.9	141.7	156.5	199.9	253.5	305.6	312.3	254.9	157.6
97.5°	195.3	213.6	234.8	256.0	277.1	320.8	363.5	381.8	337.4	233.7	128.7
100°	293.7	319.0	343.4	361.7	380.0	416.3	433.6	406.5	318.3	203.1	114.2
102.5°	397.6	413.9	440.3	451.2	462.2	474.8	457.2	391.7	284.8	179.8	108.2
105°	478.4	490.0	501.3	503.2	505.2	489.7	441.4	356.8	255.6	166.4	107.5
107.5°	527.0	528.8	525.6	517.8	510.1	472.7	408.9	323.6	233.7	159.3	110.0
110°	541.5	534.8	518.9	503.9	488.9	439.2	372.3	296.1	219.3	156.5	113.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	530.9	518.2	493.2	474.8	456.5	406.1	343.4	275.7	210.8	156.5	118.8
115°	505.9	488.9	461.5	442.2	423.0	374.7	320.1	261.9	205.2	157.6	123.7
117.5°	476.3	458.6	430.8	412.6	394.5	352.2	303.9	252.8	202.0	159.3	129.4
120°	446.3	429.4	403.3	387.8	372.3	333.5	291.2	245.4	199.9	162.2	135.0
122.5°	419.9	404.7	382.1	367.8	353.6	320.1	281.7	239.0	198.1	164.6	141.4
125°	398.7	384.2	364.5	351.8	339.1	308.5	272.5	233.4	196.7	167.4	147.0
127.5°	381.1	368.0	350.1	338.1	326.1	297.2	263.0	228.1	196.0	170.6	152.3
130°	364.9	353.2	335.6	324.2	312.7	285.2	254.2	222.8	195.3	173.4	157.6
132.5°	349.4	337.7	320.1	309.2	298.2	273.9	245.4	218.6	195.3	176.6	162.2
135°	332.1	320.4	304.9	294.8	284.8	262.3	238.0	215.4	195.3	179.4	166.4
137.5°	313.7	302.8	288.7	279.9	271.1	251.7	231.3	212.2	195.7	182.3	169.6
140°	295.8	286.6	273.6	266.2	258.8	242.5	226.0	210.1	196.0	184.0	172.7
142.5°	278.5	271.1	260.5	254.4	248.2	234.8	221.4	208.3	196.4	185.1	174.5
145°	263.3	257.3	248.9	244.2	239.4	228.4	217.5	206.6	196.0	185.8	176.3
147.5°	251.0	246.1	239.0	235.3	231.6	222.8	213.6	204.8	195.3	186.1	177.3
150°	240.8	236.5	231.3	228.1	224.9	218.2	210.5	202.7	194.2	186.1	178.4
152.5°	231.6	228.4	224.2	221.9	219.6	213.6	206.9	200.2	192.8	185.8	179.1
155°	223.9	221.4	217.9	216.0	214.0	209.0	203.4	197.4	191.1	185.1	179.4
157.5°	216.8	214.7	211.9	210.3	208.7	204.8	199.9	194.9	189.3	184.4	179.8
160°	210.1	208.3	205.9	204.6	203.4	199.9	196.4	191.8	187.5	183.3	179.8
162.5°	203.8	202.3	200.6	199.6	198.5	195.7	192.5	189.0	185.4	182.3	179.4
165°	197.4	196.7	195.3	194.4	193.5	191.4	189.0	186.1	183.3	181.2	179.1
167.5°	191.8	191.1	190.4	189.7	189.0	187.2	185.4	183.3	181.2	179.4	178.4
170°	186.5	186.1	185.4	185.0	184.7	183.7	182.6	180.8	179.4	178.4	177.7
172.5°	182.3	181.5	181.5	181.4	181.2	180.5	179.4	178.4	177.3	177.0	177.0
175°	178.4	178.0	178.0	178.0	178.0	177.3	177.3	176.3	175.9	175.9	176.3
177.5°	175.9	175.6	175.9	175.9	175.9	175.9	175.6	175.2	174.9	174.9	175.6
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1662.9	1654.9	1649.6	1648.3	1640.3	1633.7	1625.7	1624.3	1620.4	1609.7	1603.1
5°	1714.8	1696.2	1692.2	1680.2	1660.3	1645.6	1627.0	1616.4	1604.4	1584.4	1568.5
7.5°	1768.0	1742.7	1724.1	1706.8	1678.9	1652.3	1625.7	1604.4	1583.1	1553.8	1529.9
10°	1819.9	1781.3	1758.7	1733.4	1694.9	1654.9	1617.7	1587.1	1552.5	1517.9	1483.3
12.5°	1867.8	1818.6	1785.3	1749.4	1701.5	1652.3	1604.4	1561.8	1525.9	1479.3	1440.8
15°	1897.1	1842.5	1809.3	1774.7	1702.8	1648.3	1592.4	1537.9	1490.0	1440.8	1404.8
17.5°	1914.4	1853.2	1815.9	1784.0	1710.8	1636.3	1564.5	1505.9	1454.1	1395.5	1347.6
20°	1906.4	1846.5	1811.9	1781.3	1696.2	1621.7	1544.5	1476.7	1411.5	1351.6	1301.1
22.5°	1889.1	1826.6	1788.0	1760.0	1684.2	1596.4	1511.3	1438.1	1370.2	1310.4	1253.2
25°	1851.8	1790.6	1757.4	1722.8	1648.3	1564.5	1478.0	1399.5	1327.7	1263.8	1200.0
27.5°	1818.6	1744.1	1709.5	1678.9	1600.4	1525.9	1440.8	1354.3	1281.1	1214.6	1150.7
30°	1780.0	1696.2	1658.9	1617.7	1547.2	1476.7	1391.5	1311.7	1235.9	1165.4	1104.2
32.5°	1738.8	1641.6	1599.1	1552.5	1480.7	1414.2	1342.3	1263.8	1188.0	1118.8	1055.0
35°	1685.5	1581.8	1532.6	1488.6	1414.2	1347.6	1281.1	1215.9	1140.1	1066.9	1005.7
37.5°	1635.0	1520.6	1468.7	1418.1	1339.7	1275.8	1221.3	1160.1	1086.9	1016.4	957.8
40°	1577.8	1446.1	1392.9	1346.3	1265.2	1194.6	1145.4	1097.5	1033.7	965.8	902.0
42.5°	1525.9	1376.9	1321.0	1273.1	1188.0	1121.5	1074.9	1035.0	979.1	916.6	851.4
45°	1454.1	1302.4	1245.2	1194.6	1108.2	1045.6	997.8	963.2	919.3	860.7	802.2
47.5°	1387.5	1230.6	1168.0	1106.8	1028.4	964.5	920.6	894.0	864.7	812.8	753.0
50°	1306.4	1148.1	1084.2	1033.7	944.5	890.0	846.1	827.5	800.9	751.6	703.7
52.5°	1218.6	1068.3	1008.4	947.2	864.7	811.5	772.9	751.6	730.4	694.4	649.2
55°	1116.2	979.1	923.3	868.7	786.2	737.0	702.4	679.8	667.8	634.6	601.3
57.5°	1017.7	888.7	836.8	786.2	714.4	658.5	635.9	615.9	598.7	574.7	546.8
60°	917.9	800.9	745.0	699.8	637.2	586.7	568.1	548.1	534.8	516.2	496.2
62.5°	803.5	703.7	661.2	618.6	565.4	525.5	504.2	488.2	470.9	459.0	441.7
65°	682.5	612.0	570.7	538.8	488.2	452.3	436.4	425.7	411.1	399.1	385.8
67.5°	569.4	513.5	496.2	461.6	423.0	391.1	379.1	365.8	353.9	347.2	335.2
70°	460.3	420.4	403.1	393.8	351.2	329.9	319.3	314.0	299.3	292.7	284.7
72.5°	356.5	341.9	329.9	318.0	290.0	276.7	264.7	259.4	248.8	243.5	240.8
75°	263.4	254.1	247.4	246.1	234.1	220.8	208.9	206.2	198.2	192.9	190.2
77.5°	184.9	182.3	180.9	182.3	174.3	166.3	163.6	161.0	151.7	150.3	150.3
80°	121.1	127.7	127.7	126.4	123.7	122.4	118.4	115.7	110.4	109.1	110.4
82.5°	74.5	78.5	79.8	82.5	81.2	79.8	77.2	75.8	77.2	74.5	75.8
85°	37.2	39.9	45.2	45.2	46.6	46.6	46.6	45.2	42.6	43.9	42.6
87.5°	14.6	16.0	16.0	16.0	14.6	18.6	20.0	20.0	20.0	17.3	17.3
90°	3.9	3.5	3.2	2.8	2.1	1.4	0.7	0.4	0.7	1.4	2.1
92.5°	59.2	35.3	29.0	22.6	15.2	9.9	6.3	5.3	6.3	9.9	15.2
95°	80.0	42.3	34.3	26.4	18.7	14.8	12.0	11.6	12.0	14.8	18.7
97.5°	69.1	43.0	37.2	31.4	24.3	20.4	18.3	18.0	18.3	20.4	24.3
100°	68.4	47.9	42.6	37.4	30.7	26.8	25.4	24.7	25.4	26.8	30.7
102.5°	71.6	53.9	48.8	43.7	37.7	33.5	32.4	32.1	32.4	33.5	37.7
105°	76.1	60.6	55.7	50.8	45.1	41.6	39.8	39.8	39.8	41.6	45.1
107.5°	82.5	67.3	62.9	58.5	52.5	49.7	47.9	47.2	47.9	49.7	52.5
110°	89.5	75.1	70.5	65.9	60.6	57.5	56.1	55.3	56.1	57.5	60.6

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	96.2	82.5	78.1	73.7	68.4	65.2	64.2	63.5	64.2	65.2	68.4
115°	103.3	90.2	85.8	81.4	76.1	73.0	71.9	71.2	71.9	73.0	76.1
117.5°	110.3	98.0	93.8	89.5	83.5	80.4	79.3	78.3	79.3	80.4	83.5
120°	118.1	105.8	101.4	96.9	91.0	87.8	86.4	85.3	86.4	87.8	91.0
122.5°	125.5	113.2	108.8	104.3	97.6	94.5	93.4	92.7	93.4	94.5	97.6
125°	131.8	120.2	115.6	111.0	104.3	101.2	99.4	98.7	99.4	101.2	104.3
127.5°	138.2	126.9	122.3	117.7	110.7	106.8	104.7	103.6	104.7	106.8	110.7
130°	144.2	133.3	128.7	124.1	116.7	112.1	109.3	108.2	109.3	112.1	116.7
132.5°	149.8	138.9	134.3	129.7	122.0	116.7	113.2	111.7	113.2	116.7	122.0
135°	154.8	143.8	139.0	134.3	126.9	121.3	117.0	115.6	117.0	121.3	126.9
137.5°	158.3	148.4	143.4	138.5	131.1	125.5	121.6	120.6	121.6	125.5	131.1
140°	162.2	151.9	147.2	142.4	135.7	130.1	125.9	124.8	125.9	130.1	135.7
142.5°	164.6	155.1	150.7	146.3	140.0	134.3	130.4	129.7	130.4	134.3	140.0
145°	167.4	158.3	154.2	150.2	143.8	138.9	135.4	134.7	135.4	138.9	143.8
147.5°	169.2	161.1	157.4	153.7	148.1	143.5	140.3	140.0	140.3	143.5	148.1
150°	171.0	163.2	160.2	157.2	152.3	147.7	145.2	144.5	145.2	147.7	152.3
152.5°	172.7	165.7	163.0	160.4	155.8	151.9	149.8	149.5	149.8	151.9	155.8
155°	173.8	167.8	165.4	162.9	159.3	155.8	153.7	153.7	153.7	155.8	159.3
157.5°	174.9	169.6	167.6	165.7	162.5	159.3	157.6	157.6	157.6	159.3	162.5
160°	175.6	171.0	169.4	167.8	165.0	162.5	161.1	161.5	161.1	162.5	165.0
162.5°	176.3	172.4	171.2	169.9	167.8	165.7	164.3	164.6	164.3	165.7	167.8
165°	176.3	173.4	172.4	171.3	169.9	168.2	167.1	167.8	167.1	168.2	169.9
167.5°	176.3	173.8	173.1	172.4	171.3	170.3	169.6	169.9	169.6	170.3	171.3
170°	176.3	174.5	174.0	173.4	172.7	172.0	171.7	172.0	171.7	172.0	172.7
172.5°	175.9	174.5	174.3	174.1	173.8	173.1	172.7	173.4	172.7	173.1	173.8
175°	175.6	174.5	174.5	174.5	174.5	174.1	173.8	174.5	173.8	174.1	174.5
177.5°	175.2	174.5	174.5	174.5	174.9	174.5	174.5	175.2	174.5	174.5	174.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1599.1	1593.7	1589.8	1585.8	1568.5	1549.8	1547.2	1543.2	1535.2	1544.5	1540.5
5°	1557.8	1545.9	1539.2	1521.9	1500.6	1484.7	1471.4	1455.4	1448.7	1443.4	1442.1
7.5°	1507.3	1496.6	1484.7	1467.4	1440.8	1414.2	1394.2	1378.2	1364.9	1358.3	1358.3
10°	1458.1	1444.7	1428.8	1399.5	1374.2	1341.0	1319.7	1303.7	1285.1	1274.5	1265.2
12.5°	1407.5	1392.9	1378.2	1341.0	1311.7	1277.1	1246.5	1226.6	1217.3	1205.3	1189.3
15°	1356.9	1334.3	1319.7	1282.4	1245.2	1210.6	1190.7	1169.4	1148.1	1136.1	1130.8
17.5°	1303.7	1287.8	1263.8	1223.9	1182.7	1152.1	1122.8	1102.9	1077.6	1065.6	1053.6
20°	1255.8	1231.9	1207.9	1168.0	1128.1	1086.9	1057.6	1033.7	1017.7	1008.4	997.8
22.5°	1198.6	1176.0	1156.1	1113.5	1069.6	1031.0	999.1	984.5	968.5	953.9	943.2
25°	1149.4	1126.8	1106.8	1060.3	1012.4	976.5	952.5	933.9	916.6	910.0	899.3
27.5°	1097.5	1076.2	1049.6	1003.1	960.5	929.9	904.6	887.3	874.0	860.7	852.7
30°	1048.3	1024.4	1000.4	949.9	915.3	884.7	860.7	839.4	828.8	822.1	808.8
32.5°	1000.4	969.8	949.9	903.3	870.0	840.8	820.8	802.2	788.9	776.9	766.3
35°	948.5	915.3	895.3	856.7	822.1	792.9	775.6	762.3	746.3	735.7	730.4
37.5°	899.3	871.4	851.4	811.5	776.9	753.0	734.3	717.1	710.4	695.8	693.1
40°	846.1	822.1	803.5	764.9	733.0	714.4	694.4	678.5	666.5	659.8	650.5
42.5°	798.2	778.2	758.3	722.4	691.8	669.2	654.5	639.9	629.3	618.6	612.0
45°	754.3	733.0	714.4	679.8	649.2	629.3	614.6	597.3	594.7	580.0	573.4
47.5°	707.7	689.1	673.2	637.2	609.3	589.3	572.0	560.1	548.1	542.8	533.5
50°	662.5	643.9	625.3	593.3	568.1	548.1	530.8	517.5	510.9	502.9	494.9
52.5°	613.3	598.7	584.0	550.8	525.5	508.2	493.6	476.3	469.6	463.0	457.6
55°	572.0	550.8	534.8	506.9	484.2	465.6	449.7	436.4	429.7	424.4	417.7
57.5°	516.2	502.9	489.6	464.3	443.0	424.4	408.4	397.8	389.8	385.8	387.1
60°	468.3	453.6	445.7	419.1	397.8	383.1	368.5	357.9	349.9	345.9	344.6
62.5°	417.7	407.1	392.4	373.8	352.5	339.2	328.6	320.6	307.3	306.0	302.0
65°	368.5	360.5	347.2	329.9	312.6	300.7	288.7	278.0	272.7	266.1	262.1
67.5°	320.6	312.6	300.7	286.0	274.0	262.1	251.4	240.8	231.5	226.2	223.5
70°	274.0	267.4	259.4	242.1	227.5	218.2	210.2	203.5	194.2	191.6	190.2
72.5°	228.8	222.2	218.2	203.5	190.2	182.3	174.3	167.6	163.6	162.3	158.3
75°	187.6	180.9	175.6	162.3	154.3	149.0	141.0	138.4	134.4	133.0	131.7
77.5°	146.3	139.7	138.4	129.0	119.7	117.1	114.4	109.1	109.1	109.1	106.4
80°	105.1	103.8	102.4	93.1	89.1	86.5	85.1	81.2	78.5	75.8	74.5
82.5°	70.5	69.2	67.8	63.9	59.9	58.5	57.2	54.5	54.5	55.9	53.2
85°	42.6	39.9	38.6	37.2	34.6	34.6	35.9	34.6	34.6	34.6	33.3
87.5°	16.0	16.0	16.0	16.0	17.3	14.6	16.0	16.0	14.6	14.6	13.3
90°	2.8	3.2	3.5	3.9	4.6	4.9	5.6	6.0	6.3	6.7	7.1
92.5°	22.6	29.0	35.3	59.2	99.4	143.1	140.7	113.5	76.5	55.0	40.9
95°	26.4	34.3	42.3	80.0	157.6	254.9	312.3	305.6	253.5	199.9	156.5
97.5°	31.4	37.2	43.0	69.1	128.7	233.7	337.4	381.8	363.5	320.8	277.1
100°	37.4	42.6	47.9	68.4	114.2	203.1	318.3	406.5	433.6	416.3	380.0
102.5°	43.7	48.8	53.9	71.6	108.2	179.8	284.8	391.7	457.2	474.8	462.2
105°	50.8	55.7	60.6	76.1	107.5	166.4	255.6	356.8	441.4	489.7	505.2
107.5°	58.5	62.9	67.3	82.5	110.0	159.3	233.7	323.6	408.9	472.7	510.1
110°	65.9	70.5	75.1	89.5	113.9	156.5	219.3	296.1	372.3	439.2	488.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	73.7	78.1	82.5	96.2	118.8	156.5	210.8	275.7	343.4	406.1	456.5
115°	81.4	85.8	90.2	103.3	123.7	157.6	205.2	261.9	320.1	374.7	423.0
117.5°	89.5	93.8	98.0	110.3	129.4	159.3	202.0	252.8	303.9	352.2	394.5
120°	96.9	101.4	105.8	118.1	135.0	162.2	199.9	245.4	291.2	333.5	372.3
122.5°	104.3	108.8	113.2	125.5	141.4	164.6	198.1	239.0	281.7	320.1	353.6
125°	111.0	115.6	120.2	131.8	147.0	167.4	196.7	233.4	272.5	308.5	339.1
127.5°	117.7	122.3	126.9	138.2	152.3	170.6	196.0	228.1	263.0	297.2	326.1
130°	124.1	128.7	133.3	144.2	157.6	173.4	195.3	222.8	254.2	285.2	312.7
132.5°	129.7	134.3	138.9	149.8	162.2	176.6	195.3	218.6	245.4	273.9	298.2
135°	134.3	139.0	143.8	154.8	166.4	179.4	195.3	215.4	238.0	262.3	284.8
137.5°	138.5	143.4	148.4	158.3	169.6	182.3	195.7	212.2	231.3	251.7	271.1
140°	142.4	147.2	151.9	162.2	172.7	184.0	196.0	210.1	226.0	242.5	258.8
142.5°	146.3	150.7	155.1	164.6	174.5	185.1	196.4	208.3	221.4	234.8	248.2
145°	150.2	154.2	158.3	167.4	176.3	185.8	196.0	206.6	217.5	228.4	239.4
147.5°	153.7	157.4	161.1	169.2	177.3	186.1	195.3	204.8	213.6	222.8	231.6
150°	157.2	160.2	163.2	171.0	178.4	186.1	194.2	202.7	210.5	218.2	224.9
152.5°	160.4	163.0	165.7	172.7	179.1	185.8	192.8	200.2	206.9	213.6	219.6
155°	162.9	165.4	167.8	173.8	179.4	185.1	191.1	197.4	203.4	209.0	214.0
157.5°	165.7	167.6	169.6	174.9	179.8	184.4	189.3	194.9	199.9	204.8	208.7
160°	167.8	169.4	171.0	175.6	179.8	183.3	187.5	191.8	196.4	199.9	203.4
162.5°	169.9	171.2	172.4	176.3	179.4	182.3	185.4	189.0	192.5	195.7	198.5
165°	171.3	172.4	173.4	176.3	179.1	181.2	183.3	186.1	189.0	191.4	193.5
167.5°	172.4	173.1	173.8	176.3	178.4	179.4	181.2	183.3	185.4	187.2	189.0
170°	173.4	174.0	174.5	176.3	177.7	178.4	179.4	180.8	182.6	183.7	184.7
172.5°	174.1	174.3	174.5	175.9	177.0	177.0	177.3	178.4	179.4	180.5	181.2
175°	174.5	174.5	174.5	175.6	176.3	175.9	175.9	176.3	177.3	177.3	178.0
177.5°	174.5	174.5	174.5	175.2	175.6	174.9	174.9	175.2	175.6	175.9	175.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1533.9	1536.5	1529.9	1527.2	1521.9	1528.6	1529.9	1528.6	1540.5	1535.2	1537.9
5°	1444.7	1439.4	1435.4	1426.1	1426.1	1427.5	1431.4	1424.8	1428.8	1438.1	1436.8
7.5°	1346.3	1343.6	1345.0	1334.3	1326.3	1329.0	1326.3	1338.3	1345.0	1342.3	1347.6
10°	1257.2	1262.5	1250.5	1245.2	1239.9	1245.2	1243.9	1246.5	1254.5	1259.8	1269.1
12.5°	1185.3	1184.0	1177.3	1172.0	1162.7	1165.4	1173.4	1170.7	1172.0	1184.0	1182.7
15°	1117.5	1109.5	1104.2	1092.2	1094.9	1085.6	1093.5	1102.9	1106.8	1117.5	1124.1
17.5°	1049.6	1048.3	1041.7	1040.3	1025.7	1021.7	1029.7	1032.3	1036.3	1041.7	1051.0
20°	992.4	991.1	981.8	979.1	967.2	975.1	972.5	977.8	980.5	991.1	995.1
22.5°	940.5	933.9	931.2	927.2	923.3	921.9	927.2	925.9	935.2	939.2	940.5
25°	892.7	887.3	886.0	879.4	876.7	872.7	876.7	880.7	891.3	895.3	900.6
27.5°	848.8	844.8	842.1	836.8	832.8	832.8	835.5	840.8	844.8	847.4	850.1
30°	808.8	806.2	798.2	795.5	791.6	791.6	791.6	794.2	800.9	808.8	812.8
32.5°	767.6	762.3	757.0	757.0	753.0	753.0	754.3	757.0	763.6	764.9	771.6
35°	727.7	722.4	718.4	715.7	717.1	711.7	714.4	718.4	726.4	729.0	733.0
37.5°	689.1	687.8	679.8	675.8	678.5	678.5	677.1	679.8	685.1	690.4	693.1
40°	646.5	643.9	643.9	639.9	641.2	635.9	639.9	642.6	645.2	650.5	654.5
42.5°	609.3	606.6	601.3	602.6	598.7	598.7	601.3	602.6	606.6	613.3	615.9
45°	569.4	569.4	566.7	562.7	564.1	560.1	562.7	564.1	569.4	576.0	573.4
47.5°	530.8	529.5	529.5	524.2	526.8	522.8	526.8	528.1	530.8	534.8	533.5
50°	493.6	489.6	490.9	489.6	488.2	488.2	490.9	490.9	493.6	493.6	497.5
52.5°	455.0	455.0	452.3	453.6	456.3	453.6	457.6	453.6	456.3	457.6	460.3
55°	420.4	417.7	419.1	417.7	423.0	419.1	423.0	420.4	423.0	421.7	424.4
57.5°	383.1	379.1	380.5	379.1	383.1	381.8	385.8	381.8	383.1	384.5	388.5
60°	340.6	340.6	340.6	337.9	341.9	341.9	340.6	340.6	345.9	348.5	347.2
62.5°	300.7	299.3	295.3	294.0	295.3	292.7	298.0	296.7	299.3	302.0	304.6
65°	256.8	254.1	252.8	250.1	250.1	248.8	250.1	255.4	256.8	258.1	264.7
67.5°	220.8	219.5	218.2	214.2	214.2	216.8	216.8	216.8	224.8	220.8	226.2
70°	188.9	186.2	183.6	182.3	182.3	183.6	184.9	186.2	184.9	190.2	191.6
72.5°	158.3	159.6	157.0	157.0	157.0	155.6	155.6	158.3	159.6	158.3	159.6
75°	131.7	131.7	130.4	131.7	131.7	130.4	130.4	133.0	133.0	131.7	135.7
77.5°	106.4	105.1	102.4	99.8	101.1	99.8	101.1	99.8	103.8	107.8	105.1
80°	74.5	73.2	73.2	73.2	74.5	73.2	75.8	73.2	74.5	74.5	75.8
82.5°	53.2	54.5	54.5	53.2	54.5	53.2	54.5	54.5	54.5	53.2	54.5
85°	34.6	34.6	34.6	34.6	33.3	34.6	34.6	34.6	35.9	34.6	35.9
87.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	16.0	14.6	16.0
90°	7.4	7.8	7.8	7.8	8.1	8.1	8.1	7.8	7.8	7.8	7.4
92.5°	37.6	34.2	28.6	27.5	26.8	26.1	26.8	27.5	28.6	34.2	37.6
95°	141.7	126.9	101.9	91.3	88.5	82.8	88.5	91.3	101.9	126.9	141.7
97.5°	256.0	234.8	213.6	195.3	185.8	181.5	185.8	195.3	213.6	234.8	256.0
100°	361.7	343.4	319.0	293.7	280.6	275.0	280.6	293.7	319.0	343.4	361.7
102.5°	451.2	440.3	413.9	397.6	383.2	379.3	383.2	397.6	413.9	440.3	451.2
105°	503.2	501.3	490.0	478.4	471.3	467.1	471.3	478.4	490.0	501.3	503.2
107.5°	517.8	525.6	528.8	527.0	523.5	520.0	523.5	527.0	528.8	525.6	517.8
110°	503.9	518.9	534.8	541.5	543.9	543.9	543.9	541.5	534.8	518.9	503.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	474.8	493.2	518.2	530.9	537.9	541.1	537.9	530.9	518.2	493.2	474.8
115°	442.2	461.5	488.9	505.9	515.7	520.3	515.7	505.9	488.9	461.5	442.2
117.5°	412.6	430.8	458.6	476.3	486.1	488.9	486.1	476.3	458.6	430.8	412.6
120°	387.8	403.3	429.4	446.3	455.8	458.6	455.8	446.3	429.4	403.3	387.8
122.5°	367.8	382.1	404.7	419.9	429.4	431.8	429.4	419.9	404.7	382.1	367.8
125°	351.8	364.5	384.2	398.7	406.5	410.0	406.5	398.7	384.2	364.5	351.8
127.5°	338.1	350.1	368.0	381.1	388.5	389.9	388.5	381.1	368.0	350.1	338.1
130°	324.2	335.6	353.2	364.9	371.9	374.0	371.9	364.9	353.2	335.6	324.2
132.5°	309.2	320.1	337.7	349.4	355.7	358.2	355.7	349.4	337.7	320.1	309.2
135°	294.8	304.9	320.4	332.1	338.4	340.5	338.4	332.1	320.4	304.9	294.8
137.5°	279.9	288.7	302.8	313.7	319.7	322.2	319.7	313.7	302.8	288.7	279.9
140°	266.2	273.6	286.6	295.8	301.1	302.8	301.1	295.8	286.6	273.6	266.2
142.5°	254.4	260.5	271.1	278.5	283.4	284.8	283.4	278.5	271.1	260.5	254.4
145°	244.2	248.9	257.3	263.3	267.2	268.6	267.2	263.3	257.3	248.9	244.2
147.5°	235.3	239.0	246.1	251.0	253.5	254.2	253.5	251.0	246.1	239.0	235.3
150°	228.1	231.3	236.5	240.8	242.2	242.5	242.2	240.8	236.5	231.3	228.1
152.5°	221.9	224.2	228.4	231.6	233.0	233.4	233.0	231.6	228.4	224.2	221.9
155°	216.0	217.9	221.4	223.9	224.9	225.3	224.9	223.9	221.4	217.9	216.0
157.5°	210.3	211.9	214.7	216.8	217.9	217.9	217.9	216.8	214.7	211.9	210.3
160°	204.6	205.9	208.3	210.1	210.8	210.5	210.8	210.1	208.3	205.9	204.6
162.5°	199.6	200.6	202.3	203.8	203.8	203.8	203.8	203.8	202.3	200.6	199.6
165°	194.4	195.3	196.7	197.4	197.4	197.4	197.4	197.4	196.7	195.3	194.4
167.5°	189.7	190.4	191.1	191.8	191.4	191.4	191.4	191.8	191.1	190.4	189.7
170°	185.0	185.4	186.1	186.5	186.5	186.1	186.5	186.5	186.1	185.4	185.0
172.5°	181.4	181.5	181.5	182.3	181.5	181.2	181.5	182.3	181.5	181.5	181.4
175°	178.0	178.0	178.0	178.4	177.7	177.3	177.7	178.4	178.0	178.0	178.0
177.5°	175.9	175.9	175.6	175.9	174.9	174.9	174.9	175.9	175.6	175.9	175.9
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1532.6	1539.2	1533.9	1529.9	1540.5	1545.9	1545.9	1555.2	1564.5	1572.5	1573.8
5°	1438.1	1448.7	1451.4	1450.1	1466.0	1474.0	1491.3	1500.6	1513.9	1523.2	1533.9
7.5°	1351.6	1366.3	1367.6	1370.2	1394.2	1407.5	1422.1	1446.1	1464.7	1478.0	1490.0
10°	1265.2	1274.5	1283.8	1295.7	1319.7	1342.3	1363.6	1388.9	1412.8	1426.1	1443.4
12.5°	1200.0	1206.6	1217.3	1225.2	1250.5	1270.5	1298.4	1333.0	1367.6	1378.2	1399.5
15°	1132.1	1136.1	1157.4	1165.4	1186.7	1219.9	1237.2	1270.5	1307.7	1327.7	1351.6
17.5°	1053.6	1077.6	1090.9	1100.2	1126.8	1153.4	1181.3	1215.9	1263.8	1282.4	1299.7
20°	997.8	1015.0	1029.7	1041.7	1065.6	1105.5	1130.8	1158.7	1204.0	1225.2	1250.5
22.5°	948.5	963.2	976.5	989.8	1005.7	1041.7	1070.9	1109.5	1154.7	1174.7	1204.0
25°	902.0	916.6	924.6	940.5	961.8	987.1	1021.7	1056.3	1101.5	1124.1	1152.1
27.5°	856.7	871.4	886.0	899.3	913.9	937.9	961.8	1005.7	1052.3	1078.9	1102.9
30°	818.2	824.8	838.1	852.7	867.4	890.0	917.9	948.5	1001.7	1025.7	1055.0
32.5°	775.6	787.6	796.9	807.5	826.1	844.8	870.0	908.6	951.2	973.8	1005.7
35°	735.7	746.3	753.0	771.6	783.6	803.5	828.8	863.4	899.3	924.6	952.5
37.5°	697.1	707.7	715.7	726.4	742.3	759.6	786.2	811.5	854.1	875.4	907.3
40°	657.2	666.5	675.8	687.8	702.4	723.7	739.7	771.6	806.2	830.1	854.1
42.5°	618.6	623.9	634.6	647.9	662.5	681.1	703.7	729.0	763.6	784.9	806.2
45°	577.4	586.7	598.7	608.0	621.3	639.9	659.8	682.5	717.1	738.3	761.0
47.5°	538.8	545.4	553.4	568.1	585.3	598.7	619.9	641.2	673.2	693.1	714.4
50°	498.9	505.5	517.5	526.8	540.1	557.4	577.4	600.0	630.6	643.9	665.2
52.5°	461.6	464.3	476.3	485.6	498.9	518.8	534.8	554.8	584.0	598.7	619.9
55°	424.4	427.0	433.7	443.0	457.6	473.6	490.9	513.5	538.8	552.1	572.0
57.5°	385.8	388.5	395.1	401.8	416.4	431.0	451.0	469.6	494.9	506.9	525.5
60°	347.2	347.2	353.9	363.2	373.8	387.1	404.4	427.0	445.7	460.3	473.6
62.5°	306.0	310.0	314.0	320.6	332.6	348.5	363.2	379.1	401.8	412.4	424.4
65°	264.7	268.7	276.7	283.4	292.7	303.3	321.9	335.2	352.5	364.5	375.2
67.5°	228.8	232.8	238.1	246.1	252.8	264.7	278.0	291.3	310.0	318.0	325.9
70°	191.6	195.6	199.6	210.2	216.8	226.2	235.5	248.8	264.7	270.1	276.7
72.5°	162.3	163.6	169.0	171.6	180.9	188.9	199.6	207.5	219.5	226.2	231.5
75°	137.0	137.0	138.4	141.0	146.3	151.7	159.6	167.6	178.3	182.3	188.9
77.5°	107.8	111.7	110.4	113.1	115.7	118.4	125.1	130.4	141.0	143.7	146.3
80°	77.2	78.5	82.5	86.5	86.5	90.5	94.5	95.8	102.4	106.4	106.4
82.5°	55.9	57.2	55.9	57.2	58.5	59.9	63.9	69.2	69.2	70.5	73.2
85°	34.6	34.6	35.9	37.2	37.2	35.9	38.6	37.2	38.6	41.2	41.2
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	7.1	6.7	6.3	6.0	5.6	4.9	4.6	3.9	3.5	3.2	2.8
92.5°	40.9	55.0	76.5	113.5	140.7	143.1	99.4	59.2	35.3	29.0	22.6
95°	156.5	199.9	253.5	305.6	312.3	254.9	157.6	80.0	42.3	34.3	26.4
97.5°	277.1	320.8	363.5	381.8	337.4	233.7	128.7	69.1	43.0	37.2	31.4
100°	380.0	416.3	433.6	406.5	318.3	203.1	114.2	68.4	47.9	42.6	37.4
102.5°	462.2	474.8	457.2	391.7	284.8	179.8	108.2	71.6	53.9	48.8	43.7
105°	505.2	489.7	441.4	356.8	255.6	166.4	107.5	76.1	60.6	55.7	50.8
107.5°	510.1	472.7	408.9	323.6	233.7	159.3	110.0	82.5	67.3	62.9	58.5
110°	488.9	439.2	372.3	296.1	219.3	156.5	113.9	89.5	75.1	70.5	65.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	456.5	406.1	343.4	275.7	210.8	156.5	118.8	96.2	82.5	78.1	73.7
115°	423.0	374.7	320.1	261.9	205.2	157.6	123.7	103.3	90.2	85.8	81.4
117.5°	394.5	352.2	303.9	252.8	202.0	159.3	129.4	110.3	98.0	93.8	89.5
120°	372.3	333.5	291.2	245.4	199.9	162.2	135.0	118.1	105.8	101.4	96.9
122.5°	353.6	320.1	281.7	239.0	198.1	164.6	141.4	125.5	113.2	108.8	104.3
125°	339.1	308.5	272.5	233.4	196.7	167.4	147.0	131.8	120.2	115.6	111.0
127.5°	326.1	297.2	263.0	228.1	196.0	170.6	152.3	138.2	126.9	122.3	117.7
130°	312.7	285.2	254.2	222.8	195.3	173.4	157.6	144.2	133.3	128.7	124.1
132.5°	298.2	273.9	245.4	218.6	195.3	176.6	162.2	149.8	138.9	134.3	129.7
135°	284.8	262.3	238.0	215.4	195.3	179.4	166.4	154.8	143.8	139.0	134.3
137.5°	271.1	251.7	231.3	212.2	195.7	182.3	169.6	158.3	148.4	143.4	138.5
140°	258.8	242.5	226.0	210.1	196.0	184.0	172.7	162.2	151.9	147.2	142.4
142.5°	248.2	234.8	221.4	208.3	196.4	185.1	174.5	164.6	155.1	150.7	146.3
145°	239.4	228.4	217.5	206.6	196.0	185.8	176.3	167.4	158.3	154.2	150.2
147.5°	231.6	222.8	213.6	204.8	195.3	186.1	177.3	169.2	161.1	157.4	153.7
150°	224.9	218.2	210.5	202.7	194.2	186.1	178.4	171.0	163.2	160.2	157.2
152.5°	219.6	213.6	206.9	200.2	192.8	185.8	179.1	172.7	165.7	163.0	160.4
155°	214.0	209.0	203.4	197.4	191.1	185.1	179.4	173.8	167.8	165.4	162.9
157.5°	208.7	204.8	199.9	194.9	189.3	184.4	179.8	174.9	169.6	167.6	165.7
160°	203.4	199.9	196.4	191.8	187.5	183.3	179.8	175.6	171.0	169.4	167.8
162.5°	198.5	195.7	192.5	189.0	185.4	182.3	179.4	176.3	172.4	171.2	169.9
165°	193.5	191.4	189.0	186.1	183.3	181.2	179.1	176.3	173.4	172.4	171.3
167.5°	189.0	187.2	185.4	183.3	181.2	179.4	178.4	176.3	173.8	173.1	172.4
170°	184.7	183.7	182.6	180.8	179.4	178.4	177.7	176.3	174.5	174.0	173.4
172.5°	181.2	180.5	179.4	178.4	177.3	177.0	177.0	175.9	174.5	174.3	174.1
175°	178.0	177.3	177.3	176.3	175.9	175.9	176.3	175.6	174.5	174.5	174.5
177.5°	175.9	175.9	175.6	175.2	174.9	174.9	175.6	175.2	174.5	174.5	174.5
180°	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1620.4	1620.4	1620.4	1620.4
2.5°	1583.1	1595.1	1607.0	1621.7
5°	1551.2	1572.5	1595.1	1616.4
7.5°	1516.6	1547.2	1576.5	1607.0
10°	1478.0	1516.6	1549.8	1592.4
12.5°	1435.4	1476.7	1523.2	1571.1
15°	1392.9	1444.7	1494.0	1548.5
17.5°	1353.0	1402.2	1456.7	1521.9
20°	1305.1	1359.6	1420.8	1490.0
22.5°	1254.5	1314.4	1380.9	1455.4
25°	1211.9	1273.1	1337.0	1415.5
27.5°	1165.4	1229.2	1291.8	1375.6
30°	1112.2	1181.3	1245.2	1331.7
32.5°	1061.6	1130.8	1201.3	1282.4
35°	1012.4	1080.2	1150.7	1233.2
37.5°	965.8	1027.0	1096.2	1170.7
40°	921.9	977.8	1039.0	1106.8
42.5°	866.1	931.2	988.4	1037.7
45°	818.2	871.4	924.6	964.5
47.5°	762.3	815.5	860.7	892.7
50°	715.7	758.3	795.5	823.5
52.5°	659.8	699.8	730.4	751.6
55°	605.3	639.9	666.5	681.1
57.5°	556.1	578.7	598.7	612.0
60°	501.5	518.8	536.1	550.8
62.5°	443.0	461.6	470.9	486.9
65°	391.1	403.1	417.7	423.0
67.5°	340.6	347.2	356.5	367.2
70°	287.4	291.3	300.7	315.3
72.5°	240.8	244.8	251.4	256.8
75°	191.6	195.6	200.9	206.2
77.5°	150.3	151.7	154.3	159.6
80°	109.1	113.1	115.7	117.1
82.5°	75.8	77.2	77.2	78.5
85°	47.9	45.2	45.2	46.6
87.5°	17.3	20.0	20.0	22.6
90°	2.1	1.4	0.7	0.4
92.5°	15.2	9.9	6.3	5.3
95°	18.7	14.8	12.0	11.6
97.5°	24.3	20.4	18.3	18.0
100°	30.7	26.8	25.4	24.7
102.5°	37.7	33.5	32.4	32.1
105°	45.1	41.6	39.8	39.8
107.5°	52.5	49.7	47.9	47.2
110°	60.6	57.5	56.1	55.3

TEST NUMBER: P1028476

CATALOG NUMBER: S125RDIP-B1090D375UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	68.4	65.2	64.2	63.5
115°	76.1	73.0	71.9	71.2
117.5°	83.5	80.4	79.3	78.3
120°	91.0	87.8	86.4	85.3
122.5°	97.6	94.5	93.4	92.7
125°	104.3	101.2	99.4	98.7
127.5°	110.7	106.8	104.7	103.6
130°	116.7	112.1	109.3	108.2
132.5°	122.0	116.7	113.2	111.7
135°	126.9	121.3	117.0	115.6
137.5°	131.1	125.5	121.6	120.6
140°	135.7	130.1	125.9	124.8
142.5°	140.0	134.3	130.4	129.7
145°	143.8	138.9	135.4	134.7
147.5°	148.1	143.5	140.3	140.0
150°	152.3	147.7	145.2	144.5
152.5°	155.8	151.9	149.8	149.5
155°	159.3	155.8	153.7	153.7
157.5°	162.5	159.3	157.6	157.6
160°	165.0	162.5	161.1	161.5
162.5°	167.8	165.7	164.3	164.6
165°	169.9	168.2	167.1	167.8
167.5°	171.3	170.3	169.6	169.9
170°	172.7	172.0	171.7	172.0
172.5°	173.8	173.1	172.7	173.4
175°	174.5	174.1	173.8	174.5
177.5°	174.9	174.5	174.5	175.2
180°	174.9	174.9	174.9	174.9

(END OF REPORT)