

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028523

Luminaire Tested: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028523
REPORT IS A COMBINATION OF REPORTS P1005068 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6250.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	69	69	69
1	102	98	94	91	96	93	89	86	83	80	78	73	71	70	65	63	62	58	56	55
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	58	55	53	49	47	46
3	86	76	69	63	81	72	66	61	65	60	56	58	54	51	51	48	46	42	40	39
4	79	68	60	54	74	64	57	52	58	52	48	52	47	44	46	43	40	37	35	34
5	72	61	53	47	68	58	50	45	52	46	42	47	42	38	42	38	35	32	30	29
6	67	55	47	41	63	52	45	39	47	41	36	42	37	34	38	34	31	28	26	25
7	62	50	42	36	58	47	40	35	43	37	32	39	34	30	35	31	28	25	23	22
8	58	45	37	32	54	43	36	31	39	33	29	36	30	27	32	28	25	23	21	20
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22	20	18	17
10	50	38	31	26	48	36	30	25	33	27	24	30	25	22	27	23	20	19	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	2.5
10°-20°	456.8	7.3
20°-30°	724.4	11.6
30°-40°	875.3	14.0
40°-50°	779.3	12.5
50°-60°	597.6	9.6
60°-70°	388.1	6.2
70°-80°	188.4	3.0
80°-90°	45.4	0.7
90°-100°	48.6	0.8
100°-110°	144.3	2.3
110°-120°	244.8	3.9
120°-130°	322.2	5.2
130°-140°	361.1	5.8
140°-150°	353.9	5.7
150°-160°	297.3	4.8
160°-170°	197.6	3.2
170°-180°	69.2	1.1
0°-30°	1337.0	21.4
0°-40°	2212.3	35.4
0°-60°	3589.2	57.4
0°-90°	4211.1	67.4
90°-120°	437.7	7.0
90°-150°	1474.8	23.6
90°-180°	2039.0	32.6
0°-180°	6250.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	1	14	1	14	1	6
95°	37	49	37	49	37	39
105°	130	141	130	141	130	138
115°	245	247	245	247	245	242
125°	358	360	358	360	358	320
135°	465	467	465	467	465	358
145°	563	566	563	566	563	352
155°	645	645	645	645	645	297
165°	701	699	701	699	701	198
175°	729	726	729	726	729	69
180°	730	730	730	730	730	

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	0.6	1.6	2.6	3.6	4.6	5.1	5.5	6.4	7.3	8.2	9.1
92.5°	17.1	17.7	18.3	19.0	19.6	19.9	20.5	21.6	22.7	23.9	25.0
95°	37.0	37.2	37.5	37.7	38.0	38.1	38.7	40.0	41.3	42.5	43.8
97.5°	56.9	57.0	57.1	57.2	57.3	57.4	58.3	60.1	61.8	63.6	65.4
100°	79.6	79.6	79.6	79.6	79.6	79.6	80.4	82.1	83.7	85.4	87.0
102.5°	104.0	104.6	105.3	105.9	106.6	106.9	107.2	107.8	108.5	109.1	109.7
105°	129.6	130.2	130.9	131.5	132.2	132.5	132.9	133.6	134.4	135.1	135.9
107.5°	157.5	158.1	158.7	159.4	160.0	160.3	160.6	161.3	161.9	162.6	163.2
110°	186.5	187.1	187.7	188.4	189.0	189.3	189.5	189.9	190.2	190.6	191.0

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	216.0	216.3	216.5	216.8	217.1	217.2	217.4	217.9	218.4	218.9	219.4
115°	245.0	245.5	246.0	246.5	247.0	247.3	247.4	247.7	247.9	248.2	248.4
117.5°	274.6	274.7	274.9	275.0	275.1	275.2	275.3	275.6	275.8	276.1	276.3
120°	301.9	302.5	303.1	303.8	304.4	304.7	304.8	304.9	305.0	305.2	305.3
122.5°	331.4	331.5	331.7	331.8	331.9	332.0	332.2	332.6	332.9	333.3	333.7
125°	357.6	358.4	359.1	359.9	360.6	361.0	361.1	361.2	361.3	361.5	361.6
127.5°	386.6	387.0	387.4	387.7	388.1	388.3	388.4	388.5	388.6	388.8	388.9
130°	412.2	412.8	413.4	414.1	414.7	415.0	415.1	415.4	415.6	415.9	416.1
132.5°	437.8	438.9	440.1	441.2	442.3	442.9	442.8	442.7	442.6	442.4	442.3
135°	465.0	465.8	466.6	467.3	468.1	468.5	468.6	468.7	468.8	468.9	469.0
137.5°	490.6	491.4	492.1	492.9	493.6	494.0	494.1	494.4	494.7	494.9	495.2
140°	515.1	515.7	516.3	517.0	517.6	517.9	518.1	518.5	518.8	519.2	519.6
142.5°	539.5	540.0	540.5	541.0	541.5	541.8	542.1	542.6	543.1	543.6	544.1
145°	563.4	563.9	564.4	564.9	565.4	565.7	565.9	566.3	566.6	567.0	567.4
147.5°	585.6	586.0	586.4	586.7	587.1	587.3	587.4	587.7	587.9	588.2	588.4
150°	607.7	607.6	607.5	607.4	607.3	607.2	607.4	607.9	608.4	608.9	609.4
152.5°	625.9	626.2	626.4	626.7	627.0	627.1	627.2	627.3	627.4	627.5	627.6
155°	644.7	644.7	644.7	644.7	644.7	644.7	644.8	644.9	645.0	645.2	645.3
157.5°	661.7	661.5	661.2	661.0	660.7	660.6	660.7	660.8	660.9	661.1	661.2
160°	676.5	676.1	675.7	675.4	675.0	674.8	674.9	675.0	675.1	675.3	675.4
162.5°	689.6	689.4	689.1	688.9	688.6	688.5	688.5	688.5	688.5	688.5	688.5
165°	701.0	700.7	700.5	700.2	699.9	699.8	699.9	700.0	700.1	700.3	700.4
167.5°	711.2	710.7	710.2	709.7	709.2	708.9	708.9	708.9	708.9	708.9	708.9
170°	719.2	718.7	718.2	717.7	717.2	716.9	716.9	716.9	716.9	716.9	716.9
172.5°	724.8	724.3	723.8	723.3	722.8	722.6	722.6	722.6	722.6	722.6	722.6
175°	728.8	728.3	727.8	727.3	726.8	726.6	726.6	726.6	726.6	726.6	726.6
177.5°	731.7	731.2	730.7	730.2	729.7	729.4	729.3	729.2	729.1	728.9	728.8
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	9.7	10.3	11.0	11.6	11.9	12.1	12.5	12.8	13.2	13.6	13.2
92.5°	25.9	26.8	27.7	28.6	29.0	29.1	29.4	29.6	29.9	30.1	29.9
95°	44.7	45.6	46.5	47.4	47.8	47.9	48.2	48.4	48.7	48.9	48.7
97.5°	66.2	66.9	67.7	68.4	68.8	68.9	69.0	69.1	69.3	69.4	69.3
100°	88.1	89.3	90.4	91.5	92.1	92.2	92.5	92.7	93.0	93.2	93.0
102.5°	111.0	112.2	113.5	114.8	115.4	115.6	116.0	116.3	116.7	117.1	116.7
105°	136.7	137.4	138.2	138.9	139.3	139.5	139.9	140.2	140.6	141.0	140.6
107.5°	163.6	164.0	164.3	164.7	164.9	164.9	164.9	164.9	164.9	164.9	164.9
110°	191.4	191.8	192.1	192.5	192.7	192.6	192.5	192.4	192.3	192.2	192.3

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	219.5	219.7	219.8	219.9	220.0	219.9	219.6	219.4	219.1	218.9	219.1
115°	248.3	248.2	248.1	248.0	247.9	247.8	247.7	247.6	247.4	247.3	247.4
117.5°	276.4	276.6	276.7	276.8	276.9	276.6	276.1	275.6	275.1	274.6	275.1
120°	305.3	305.3	305.3	305.3	305.3	305.0	304.5	304.0	303.5	303.0	303.5
122.5°	333.6	333.4	333.3	333.2	333.1	332.9	332.5	332.2	331.8	331.4	331.8
125°	361.3	361.1	360.8	360.5	360.4	360.3	360.2	360.1	360.0	359.9	360.0
127.5°	388.8	388.6	388.5	388.4	388.3	388.2	387.9	387.7	387.4	387.2	387.4
130°	416.0	415.9	415.8	415.7	415.6	415.5	415.2	414.9	414.7	414.4	414.7
132.5°	442.2	442.0	441.9	441.8	441.7	441.5	441.1	440.8	440.4	440.0	440.4
135°	469.0	469.0	469.0	469.0	469.0	468.7	468.2	467.7	467.2	466.7	467.2
137.5°	495.3	495.4	495.5	495.6	495.7	495.4	494.8	494.1	493.5	492.9	493.5
140°	519.9	520.1	520.4	520.7	520.8	520.5	519.8	519.2	518.5	517.9	518.5
142.5°	544.2	544.3	544.4	544.5	544.6	544.3	543.7	543.0	542.4	541.8	542.4
145°	567.4	567.4	567.4	567.4	567.4	567.2	566.8	566.5	566.1	565.7	566.1
147.5°	588.8	589.2	589.5	589.9	590.1	589.6	588.6	587.6	586.6	585.6	586.6
150°	609.4	609.4	609.4	609.4	609.4	609.3	609.0	608.8	608.5	608.3	608.5
152.5°	628.0	628.4	628.7	629.1	629.3	629.1	628.6	628.1	627.6	627.1	627.6
155°	645.8	646.3	646.8	647.3	647.5	647.2	646.6	645.9	645.3	644.7	645.3
157.5°	661.7	662.2	662.7	663.2	663.5	663.1	662.2	661.3	660.4	659.5	660.4
160°	675.9	676.4	676.9	677.4	677.7	677.4	676.7	676.1	675.4	674.8	675.4
162.5°	689.1	689.7	690.4	691.0	691.3	690.9	690.2	689.4	688.7	687.9	688.7
165°	700.9	701.4	701.9	702.4	702.7	702.3	701.6	700.8	700.1	699.3	700.1
167.5°	709.7	710.4	711.2	711.9	712.3	711.9	711.2	710.4	709.7	708.9	709.7
170°	717.7	718.4	719.2	719.9	720.3	719.9	719.0	718.1	717.2	716.3	717.2
172.5°	723.4	724.1	724.9	725.6	726.0	725.6	724.9	724.1	723.4	722.6	723.4
175°	727.4	728.1	728.9	729.6	730.0	729.6	728.7	727.8	726.9	726.0	726.9
177.5°	729.6	730.3	731.1	731.8	732.2	731.8	730.9	730.0	729.2	728.3	729.2
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	12.8	12.5	12.1	11.9	11.6	11.0	10.3	9.7	9.1	8.2	7.3
92.5°	29.6	29.4	29.1	29.0	28.6	27.7	26.8	25.9	25.0	23.9	22.7
95°	48.4	48.2	47.9	47.8	47.4	46.5	45.6	44.7	43.8	42.5	41.3
97.5°	69.1	69.0	68.9	68.8	68.4	67.7	66.9	66.2	65.4	63.6	61.8
100°	92.7	92.5	92.2	92.1	91.5	90.4	89.3	88.1	87.0	85.4	83.7
102.5°	116.3	116.0	115.6	115.4	114.8	113.5	112.2	111.0	109.7	109.1	108.5
105°	140.2	139.9	139.5	139.3	138.9	138.2	137.4	136.7	135.9	135.1	134.4
107.5°	164.9	164.9	164.9	164.9	164.7	164.3	164.0	163.6	163.2	162.6	161.9
110°	192.4	192.5	192.6	192.7	192.5	192.1	191.8	191.4	191.0	190.6	190.2

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	219.4	219.6	219.9	220.0	219.9	219.8	219.7	219.5	219.4	218.9	218.4
115°	247.6	247.7	247.8	247.9	248.0	248.1	248.2	248.3	248.4	248.2	247.9
117.5°	275.6	276.1	276.6	276.9	276.8	276.7	276.6	276.4	276.3	276.1	275.8
120°	304.0	304.5	305.0	305.3	305.3	305.3	305.3	305.3	305.3	305.2	305.0
122.5°	332.2	332.5	332.9	333.1	333.2	333.3	333.4	333.6	333.7	333.3	332.9
125°	360.1	360.2	360.3	360.4	360.5	360.8	361.1	361.3	361.6	361.5	361.3
127.5°	387.7	387.9	388.2	388.3	388.4	388.5	388.6	388.8	388.9	388.8	388.6
130°	414.9	415.2	415.5	415.6	415.7	415.8	415.9	416.0	416.1	415.9	415.6
132.5°	440.8	441.1	441.5	441.7	441.8	441.9	442.0	442.2	442.3	442.4	442.6
135°	467.7	468.2	468.7	469.0	469.0	469.0	469.0	469.0	469.0	468.9	468.8
137.5°	494.1	494.8	495.4	495.7	495.6	495.5	495.4	495.3	495.2	494.9	494.7
140°	519.2	519.8	520.5	520.8	520.7	520.4	520.1	519.9	519.6	519.2	518.8
142.5°	543.0	543.7	544.3	544.6	544.5	544.4	544.3	544.2	544.1	543.6	543.1
145°	566.5	566.8	567.2	567.4	567.4	567.4	567.4	567.4	567.4	567.0	566.6
147.5°	587.6	588.6	589.6	590.1	589.9	589.5	589.2	588.8	588.4	588.2	587.9
150°	608.8	609.0	609.3	609.4	609.4	609.4	609.4	609.4	609.4	608.9	608.4
152.5°	628.1	628.6	629.1	629.3	629.1	628.7	628.4	628.0	627.6	627.5	627.4
155°	645.9	646.6	647.2	647.5	647.3	646.8	646.3	645.8	645.3	645.2	645.0
157.5°	661.3	662.2	663.1	663.5	663.2	662.7	662.2	661.7	661.2	661.1	660.9
160°	676.1	676.7	677.4	677.7	677.4	676.9	676.4	675.9	675.4	675.3	675.1
162.5°	689.4	690.2	690.9	691.3	691.0	690.4	689.7	689.1	688.5	688.5	688.5
165°	700.8	701.6	702.3	702.7	702.4	701.9	701.4	700.9	700.4	700.3	700.1
167.5°	710.4	711.2	711.9	712.3	711.9	711.2	710.4	709.7	708.9	708.9	708.9
170°	718.1	719.0	719.9	720.3	719.9	719.2	718.4	717.7	716.9	716.9	716.9
172.5°	724.1	724.9	725.6	726.0	725.6	724.9	724.1	723.4	722.6	722.6	722.6
175°	727.8	728.7	729.6	730.0	729.6	728.9	728.1	727.4	726.6	726.6	726.6
177.5°	730.0	730.9	731.8	732.2	731.8	731.1	730.3	729.6	728.8	728.9	729.1
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	6.4	5.5	5.1	4.6	3.6	2.6	1.6	0.6	1.6	2.6	3.6
92.5°	21.6	20.5	19.9	19.6	19.0	18.3	17.7	17.1	17.7	18.3	19.0
95°	40.0	38.7	38.1	38.0	37.7	37.5	37.2	37.0	37.2	37.5	37.7
97.5°	60.1	58.3	57.4	57.3	57.2	57.1	57.0	56.9	57.0	57.1	57.2
100°	82.1	80.4	79.6	79.6	79.6	79.6	79.6	79.6	79.6	79.6	79.6
102.5°	107.8	107.2	106.9	106.6	105.9	105.3	104.6	104.0	104.6	105.3	105.9
105°	133.6	132.9	132.5	132.2	131.5	130.9	130.2	129.6	130.2	130.9	131.5
107.5°	161.3	160.6	160.3	160.0	159.4	158.7	158.1	157.5	158.1	158.7	159.4
110°	189.9	189.5	189.3	189.0	188.4	187.7	187.1	186.5	187.1	187.7	188.4

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4FO-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	217.9	217.4	217.2	217.1	216.8	216.5	216.3	216.0	216.3	216.5	216.8
115°	247.7	247.4	247.3	247.0	246.5	246.0	245.5	245.0	245.5	246.0	246.5
117.5°	275.6	275.3	275.2	275.1	275.0	274.9	274.7	274.6	274.7	274.9	275.0
120°	304.9	304.8	304.7	304.4	303.8	303.1	302.5	301.9	302.5	303.1	303.8
122.5°	332.6	332.2	332.0	331.9	331.8	331.7	331.5	331.4	331.5	331.7	331.8
125°	361.2	361.1	361.0	360.6	359.9	359.1	358.4	357.6	358.4	359.1	359.9
127.5°	388.5	388.4	388.3	388.1	387.7	387.4	387.0	386.6	387.0	387.4	387.7
130°	415.4	415.1	415.0	414.7	414.1	413.4	412.8	412.2	412.8	413.4	414.1
132.5°	442.7	442.8	442.9	442.3	441.2	440.1	438.9	437.8	438.9	440.1	441.2
135°	468.7	468.6	468.5	468.1	467.3	466.6	465.8	465.0	465.8	466.6	467.3
137.5°	494.4	494.1	494.0	493.6	492.9	492.1	491.4	490.6	491.4	492.1	492.9
140°	518.5	518.1	517.9	517.6	517.0	516.3	515.7	515.1	515.7	516.3	517.0
142.5°	542.6	542.1	541.8	541.5	541.0	540.5	540.0	539.5	540.0	540.5	541.0
145°	566.3	565.9	565.7	565.4	564.9	564.4	563.9	563.4	563.9	564.4	564.9
147.5°	587.7	587.4	587.3	587.1	586.7	586.4	586.0	585.6	586.0	586.4	586.7
150°	607.9	607.4	607.2	607.3	607.4	607.5	607.6	607.7	607.6	607.5	607.4
152.5°	627.3	627.2	627.1	627.0	626.7	626.4	626.2	625.9	626.2	626.4	626.7
155°	644.9	644.8	644.7	644.7	644.7	644.7	644.7	644.7	644.7	644.7	644.7
157.5°	660.8	660.7	660.6	660.7	661.0	661.2	661.5	661.7	661.5	661.2	661.0
160°	675.0	674.9	674.8	675.0	675.4	675.7	676.1	676.5	676.1	675.7	675.4
162.5°	688.5	688.5	688.5	688.6	688.9	689.1	689.4	689.6	689.4	689.1	688.9
165°	700.0	699.9	699.8	699.9	700.2	700.5	700.7	701.0	700.7	700.5	700.2
167.5°	708.9	708.9	708.9	709.2	709.7	710.2	710.7	711.2	710.7	710.2	709.7
170°	716.9	716.9	716.9	717.2	717.7	718.2	718.7	719.2	718.7	718.2	717.7
172.5°	722.6	722.6	722.6	722.8	723.3	723.8	724.3	724.8	724.3	723.8	723.3
175°	726.6	726.6	726.6	726.8	727.3	727.8	728.3	728.8	728.3	727.8	727.3
177.5°	729.2	729.3	729.4	729.7	730.2	730.7	731.2	731.7	731.2	730.7	730.2
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	4.6	5.1	5.5	6.4	7.3	8.2	9.1	9.7	10.3	11.0	11.6
92.5°	19.6	19.9	20.5	21.6	22.7	23.9	25.0	25.9	26.8	27.7	28.6
95°	38.0	38.1	38.7	40.0	41.3	42.5	43.8	44.7	45.6	46.5	47.4
97.5°	57.3	57.4	58.3	60.1	61.8	63.6	65.4	66.2	66.9	67.7	68.4
100°	79.6	79.6	80.4	82.1	83.7	85.4	87.0	88.1	89.3	90.4	91.5
102.5°	106.6	106.9	107.2	107.8	108.5	109.1	109.7	111.0	112.2	113.5	114.8
105°	132.2	132.5	132.9	133.6	134.4	135.1	135.9	136.7	137.4	138.2	138.9
107.5°	160.0	160.3	160.6	161.3	161.9	162.6	163.2	163.6	164.0	164.3	164.7
110°	189.0	189.3	189.5	189.9	190.2	190.6	191.0	191.4	191.8	192.1	192.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	217.1	217.2	217.4	217.9	218.4	218.9	219.4	219.5	219.7	219.8	219.9
115°	247.0	247.3	247.4	247.7	247.9	248.2	248.4	248.3	248.2	248.1	248.0
117.5°	275.1	275.2	275.3	275.6	275.8	276.1	276.3	276.4	276.6	276.7	276.8
120°	304.4	304.7	304.8	304.9	305.0	305.2	305.3	305.3	305.3	305.3	305.3
122.5°	331.9	332.0	332.2	332.6	332.9	333.3	333.7	333.6	333.4	333.3	333.2
125°	360.6	361.0	361.1	361.2	361.3	361.5	361.6	361.3	361.1	360.8	360.5
127.5°	388.1	388.3	388.4	388.5	388.6	388.8	388.9	388.8	388.6	388.5	388.4
130°	414.7	415.0	415.1	415.4	415.6	415.9	416.1	416.0	415.9	415.8	415.7
132.5°	442.3	442.9	442.8	442.7	442.6	442.4	442.3	442.2	442.0	441.9	441.8
135°	468.1	468.5	468.6	468.7	468.8	468.9	469.0	469.0	469.0	469.0	469.0
137.5°	493.6	494.0	494.1	494.4	494.7	494.9	495.2	495.3	495.4	495.5	495.6
140°	517.6	517.9	518.1	518.5	518.8	519.2	519.6	519.9	520.1	520.4	520.7
142.5°	541.5	541.8	542.1	542.6	543.1	543.6	544.1	544.2	544.3	544.4	544.5
145°	565.4	565.7	565.9	566.3	566.6	567.0	567.4	567.4	567.4	567.4	567.4
147.5°	587.1	587.3	587.4	587.7	587.9	588.2	588.4	588.8	589.2	589.5	589.9
150°	607.3	607.2	607.4	607.9	608.4	608.9	609.4	609.4	609.4	609.4	609.4
152.5°	627.0	627.1	627.2	627.3	627.4	627.5	627.6	628.0	628.4	628.7	629.1
155°	644.7	644.7	644.8	644.9	645.0	645.2	645.3	645.8	646.3	646.8	647.3
157.5°	660.7	660.6	660.7	660.8	660.9	661.1	661.2	661.7	662.2	662.7	663.2
160°	675.0	674.8	674.9	675.0	675.1	675.3	675.4	675.9	676.4	676.9	677.4
162.5°	688.6	688.5	688.5	688.5	688.5	688.5	688.5	689.1	689.7	690.4	691.0
165°	699.9	699.8	699.9	700.0	700.1	700.3	700.4	700.9	701.4	701.9	702.4
167.5°	709.2	708.9	708.9	708.9	708.9	708.9	708.9	709.7	710.4	711.2	711.9
170°	717.2	716.9	716.9	716.9	716.9	716.9	716.9	717.7	718.4	719.2	719.9
172.5°	722.8	722.6	722.6	722.6	722.6	722.6	722.6	723.4	724.1	724.9	725.6
175°	726.8	726.6	726.6	726.6	726.6	726.6	726.6	727.4	728.1	728.9	729.6
177.5°	729.7	729.4	729.3	729.2	729.1	728.9	728.8	729.6	730.3	731.1	731.8
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	11.9	12.1	12.5	12.8	13.2	13.6	13.2	12.8	12.5	12.1	11.9
92.5°	29.0	29.1	29.4	29.6	29.9	30.1	29.9	29.6	29.4	29.1	29.0
95°	47.8	47.9	48.2	48.4	48.7	48.9	48.7	48.4	48.2	47.9	47.8
97.5°	68.8	68.9	69.0	69.1	69.3	69.4	69.3	69.1	69.0	68.9	68.8
100°	92.1	92.2	92.5	92.7	93.0	93.2	93.0	92.7	92.5	92.2	92.1
102.5°	115.4	115.6	116.0	116.3	116.7	117.1	116.7	116.3	116.0	115.6	115.4
105°	139.3	139.5	139.9	140.2	140.6	141.0	140.6	140.2	139.9	139.5	139.3
107.5°	164.9	164.9	164.9	164.9	164.9	164.9	164.9	164.9	164.9	164.9	164.9
110°	192.7	192.6	192.5	192.4	192.3	192.2	192.3	192.4	192.5	192.6	192.7

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	220.0	219.9	219.6	219.4	219.1	218.9	219.1	219.4	219.6	219.9	220.0
115°	247.9	247.8	247.7	247.6	247.4	247.3	247.4	247.6	247.7	247.8	247.9
117.5°	276.9	276.6	276.1	275.6	275.1	274.6	275.1	275.6	276.1	276.6	276.9
120°	305.3	305.0	304.5	304.0	303.5	303.0	303.5	304.0	304.5	305.0	305.3
122.5°	333.1	332.9	332.5	332.2	331.8	331.4	331.8	332.2	332.5	332.9	333.1
125°	360.4	360.3	360.2	360.1	360.0	359.9	360.0	360.1	360.2	360.3	360.4
127.5°	388.3	388.2	387.9	387.7	387.4	387.2	387.4	387.7	387.9	388.2	388.3
130°	415.6	415.5	415.2	414.9	414.7	414.4	414.7	414.9	415.2	415.5	415.6
132.5°	441.7	441.5	441.1	440.8	440.4	440.0	440.4	440.8	441.1	441.5	441.7
135°	469.0	468.7	468.2	467.7	467.2	466.7	467.2	467.7	468.2	468.7	469.0
137.5°	495.7	495.4	494.8	494.1	493.5	492.9	493.5	494.1	494.8	495.4	495.7
140°	520.8	520.5	519.8	519.2	518.5	517.9	518.5	519.2	519.8	520.5	520.8
142.5°	544.6	544.3	543.7	543.0	542.4	541.8	542.4	543.0	543.7	544.3	544.6
145°	567.4	567.2	566.8	566.5	566.1	565.7	566.1	566.5	566.8	567.2	567.4
147.5°	590.1	589.6	588.6	587.6	586.6	585.6	586.6	587.6	588.6	589.6	590.1
150°	609.4	609.3	609.0	608.8	608.5	608.3	608.5	608.8	609.0	609.3	609.4
152.5°	629.3	629.1	628.6	628.1	627.6	627.1	627.6	628.1	628.6	629.1	629.3
155°	647.5	647.2	646.6	645.9	645.3	644.7	645.3	645.9	646.6	647.2	647.5
157.5°	663.5	663.1	662.2	661.3	660.4	659.5	660.4	661.3	662.2	663.1	663.5
160°	677.7	677.4	676.7	676.1	675.4	674.8	675.4	676.1	676.7	677.4	677.7
162.5°	691.3	690.9	690.2	689.4	688.7	687.9	688.7	689.4	690.2	690.9	691.3
165°	702.7	702.3	701.6	700.8	700.1	699.3	700.1	700.8	701.6	702.3	702.7
167.5°	712.3	711.9	711.2	710.4	709.7	708.9	709.7	710.4	711.2	711.9	712.3
170°	720.3	719.9	719.0	718.1	717.2	716.3	717.2	718.1	719.0	719.9	720.3
172.5°	726.0	725.6	724.9	724.1	723.4	722.6	723.4	724.1	724.9	725.6	726.0
175°	730.0	729.6	728.7	727.8	726.9	726.0	726.9	727.8	728.7	729.6	730.0
177.5°	732.2	731.8	730.9	730.0	729.2	728.3	729.2	730.0	730.9	731.8	732.2
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	11.6	11.0	10.3	9.7	9.1	8.2	7.3	6.4	5.5	5.1	4.6
92.5°	28.6	27.7	26.8	25.9	25.0	23.9	22.7	21.6	20.5	19.9	19.6
95°	47.4	46.5	45.6	44.7	43.8	42.5	41.3	40.0	38.7	38.1	38.0
97.5°	68.4	67.7	66.9	66.2	65.4	63.6	61.8	60.1	58.3	57.4	57.3
100°	91.5	90.4	89.3	88.1	87.0	85.4	83.7	82.1	80.4	79.6	79.6
102.5°	114.8	113.5	112.2	111.0	109.7	109.1	108.5	107.8	107.2	106.9	106.6
105°	138.9	138.2	137.4	136.7	135.9	135.1	134.4	133.6	132.9	132.5	132.2
107.5°	164.7	164.3	164.0	163.6	163.2	162.6	161.9	161.3	160.6	160.3	160.0
110°	192.5	192.1	191.8	191.4	191.0	190.6	190.2	189.9	189.5	189.3	189.0

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	219.9	219.8	219.7	219.5	219.4	218.9	218.4	217.9	217.4	217.2	217.1
115°	248.0	248.1	248.2	248.3	248.4	248.2	247.9	247.7	247.4	247.3	247.0
117.5°	276.8	276.7	276.6	276.4	276.3	276.1	275.8	275.6	275.3	275.2	275.1
120°	305.3	305.3	305.3	305.3	305.3	305.2	305.0	304.9	304.8	304.7	304.4
122.5°	333.2	333.3	333.4	333.6	333.7	333.3	332.9	332.6	332.2	332.0	331.9
125°	360.5	360.8	361.1	361.3	361.6	361.5	361.3	361.2	361.1	361.0	360.6
127.5°	388.4	388.5	388.6	388.8	388.9	388.8	388.6	388.5	388.4	388.3	388.1
130°	415.7	415.8	415.9	416.0	416.1	415.9	415.6	415.4	415.1	415.0	414.7
132.5°	441.8	441.9	442.0	442.2	442.3	442.4	442.6	442.7	442.8	442.9	442.3
135°	469.0	469.0	469.0	469.0	469.0	468.9	468.8	468.7	468.6	468.5	468.1
137.5°	495.6	495.5	495.4	495.3	495.2	494.9	494.7	494.4	494.1	494.0	493.6
140°	520.7	520.4	520.1	519.9	519.6	519.2	518.8	518.5	518.1	517.9	517.6
142.5°	544.5	544.4	544.3	544.2	544.1	543.6	543.1	542.6	542.1	541.8	541.5
145°	567.4	567.4	567.4	567.4	567.4	567.0	566.6	566.3	565.9	565.7	565.4
147.5°	589.9	589.5	589.2	588.8	588.4	588.2	587.9	587.7	587.4	587.3	587.1
150°	609.4	609.4	609.4	609.4	609.4	608.9	608.4	607.9	607.4	607.2	607.3
152.5°	629.1	628.7	628.4	628.0	627.6	627.5	627.4	627.3	627.2	627.1	627.0
155°	647.3	646.8	646.3	645.8	645.3	645.2	645.0	644.9	644.8	644.7	644.7
157.5°	663.2	662.7	662.2	661.7	661.2	661.1	660.9	660.8	660.7	660.6	660.7
160°	677.4	676.9	676.4	675.9	675.4	675.3	675.1	675.0	674.9	674.8	675.0
162.5°	691.0	690.4	689.7	689.1	688.5	688.5	688.5	688.5	688.5	688.5	688.6
165°	702.4	701.9	701.4	700.9	700.4	700.3	700.1	700.0	699.9	699.8	699.9
167.5°	711.9	711.2	710.4	709.7	708.9	708.9	708.9	708.9	708.9	708.9	709.2
170°	719.9	719.2	718.4	717.7	716.9	716.9	716.9	716.9	716.9	716.9	717.2
172.5°	725.6	724.9	724.1	723.4	722.6	722.6	722.6	722.6	722.6	722.6	722.8
175°	729.6	728.9	728.1	727.4	726.6	726.6	726.6	726.6	726.6	726.6	726.8
177.5°	731.8	731.1	730.3	729.6	728.8	728.9	729.1	729.2	729.3	729.4	729.7
180°	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5	730.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	3.6	2.6	1.6	0.6
92.5°	19.0	18.3	17.7	17.1
95°	37.7	37.5	37.2	37.0
97.5°	57.2	57.1	57.0	56.9
100°	79.6	79.6	79.6	79.6
102.5°	105.9	105.3	104.6	104.0
105°	131.5	130.9	130.2	129.6
107.5°	159.4	158.7	158.1	157.5
110°	188.4	187.7	187.1	186.5

TEST NUMBER: P1028523

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	216.8	216.5	216.3	216.0
115°	246.5	246.0	245.5	245.0
117.5°	275.0	274.9	274.7	274.6
120°	303.8	303.1	302.5	301.9
122.5°	331.8	331.7	331.5	331.4
125°	359.9	359.1	358.4	357.6
127.5°	387.7	387.4	387.0	386.6
130°	414.1	413.4	412.8	412.2
132.5°	441.2	440.1	438.9	437.8
135°	467.3	466.6	465.8	465.0
137.5°	492.9	492.1	491.4	490.6
140°	517.0	516.3	515.7	515.1
142.5°	541.0	540.5	540.0	539.5
145°	564.9	564.4	563.9	563.4
147.5°	586.7	586.4	586.0	585.6
150°	607.4	607.5	607.6	607.7
152.5°	626.7	626.4	626.2	625.9
155°	644.7	644.7	644.7	644.7
157.5°	661.0	661.2	661.5	661.7
160°	675.4	675.7	676.1	676.5
162.5°	688.9	689.1	689.4	689.6
165°	700.2	700.5	700.7	701.0
167.5°	709.7	710.2	710.7	711.2
170°	717.7	718.2	718.7	719.2
172.5°	723.3	723.8	724.3	724.8
175°	727.3	727.8	728.3	728.8
177.5°	730.2	730.7	731.2	731.7
180°	730.5	730.5	730.5	730.5

(END OF REPORT)