

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028524

Luminaire Tested: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028524
REPORT IS A COMBINATION OF REPORTS P1005069 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6328.0 lumens
Efficiency: N/A
Efficacy: 101.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	81	81	81	71	71	71	67		
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57		
2	93	86	80	75	88	81	76	72	73	69	65	64	61	59	57	55	53	49		
3	86	76	69	63	80	72	66	60	64	59	55	57	53	50	51	48	45	42		
4	79	68	60	54	74	64	57	52	58	52	47	51	47	43	46	42	39	36		
5	72	61	53	47	68	58	50	45	52	46	41	46	42	38	41	38	35	32		
6	67	55	46	41	63	52	45	39	47	41	36	42	37	33	38	34	31	28		
7	62	49	41	36	58	47	40	35	43	37	32	38	33	30	34	30	27	25		
8	57	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	41	34	29	51	39	32	28	36	30	26	32	28	24	29	25	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	18		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10412	10412	10412	10412
5°	10403	11734	10403	9019
10°	10344	13186	10309	7797
15°	10232	13951	10162	6788
20°	10096	15060	10006	6136
25°	9919	17046	9808	5569
30°	9740	18119	9594	5163
35°	9507	14901	9374	4785
40°	9093	10119	9017	4445
45°	8551	7274	8539	4111
50°	7993	5594	8032	3801
55°	7367	4549	7352	3504
60°	6784	3728	6752	3111
65°	6105	3106	6143	2504
70°	5543	2493	5520	2085
75°	4682	1889	4682	1713
80°	3794	1152	3752	1152
85°	2670	606	2596	685

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14820 cd/sqm

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	2.5
10°-20°	456.8	7.2
20°-30°	724.4	11.4
30°-40°	875.3	13.8
40°-50°	779.3	12.3
50°-60°	597.6	9.4
60°-70°	388.1	6.1
70°-80°	188.4	3.0
80°-90°	45.4	0.7
90°-100°	205.0	3.2
100°-110°	442.1	7.0
110°-120°	412.2	6.5
120°-130°	333.8	5.3
130°-140°	268.0	4.2
140°-150°	202.2	3.2
150°-160°	142.4	2.2
160°-170°	83.9	1.3
170°-180°	27.3	0.4
0°-30°	1337.0	21.1
0°-40°	2212.3	35.0
0°-60°	3589.2	56.7
0°-90°	4211.1	66.5
90°-120°	1059.3	16.7
90°-150°	1863.3	29.4
90°-180°	2117.0	33.5
0°-180°	6328.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1625	1625	1625	1625	1625	
5°	1621	1862	1621	1432	1621	154
15°	1553	2237	1542	1089	1553	438
25°	1420	2679	1404	875	1420	654
35°	1237	2223	1219	714	1237	770
45°	967	994	966	562	967	746
55°	683	546	682	420	683	612
65°	424	310	427	250	424	424
75°	207	144	207	131	207	222
85°	47	31	45	35	47	53
90°	1	13	1	13	1	4
95°	19	134	19	134	19	20
105°	64	753	64	753	64	68
115°	115	839	115	839	115	113
125°	159	661	159	661	159	141
135°	186	549	186	549	186	145
145°	217	433	217	433	217	136
155°	248	363	248	363	248	114
165°	270	318	270	318	270	76
175°	281	286	281	286	281	27
180°	282	282	282	282	282	

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1626.3	1639.7	1643.7	1654.3	1666.3	1669.0	1675.7	1685.0	1690.4	1689.0	1689.0
5°	1621.0	1643.7	1659.7	1678.4	1701.0	1710.4	1718.4	1738.4	1754.4	1763.7	1779.7
7.5°	1611.6	1645.0	1671.7	1699.7	1734.4	1750.4	1767.7	1795.8	1825.1	1843.8	1861.1
10°	1597.0	1639.7	1677.0	1718.4	1765.1	1789.1	1810.4	1853.1	1889.1	1913.2	1953.2
12.5°	1575.6	1629.0	1681.0	1735.7	1794.4	1819.8	1849.1	1895.8	1946.5	1981.2	2014.6
15°	1552.9	1617.0	1673.0	1738.4	1809.1	1847.8	1885.1	1934.5	1979.9	2018.6	2057.2
17.5°	1526.3	1594.3	1663.7	1738.4	1818.4	1857.1	1889.1	1947.8	1995.9	2034.6	2069.3
20°	1494.2	1570.3	1649.0	1731.7	1813.1	1849.1	1879.8	1943.8	1986.5	2027.9	2077.3
22.5°	1459.6	1542.3	1626.3	1707.7	1787.7	1826.4	1862.5	1918.5	1965.2	2021.2	2085.3
25°	1419.5	1510.2	1595.6	1677.0	1753.1	1789.1	1821.1	1882.5	1947.8	2018.6	2090.6
27.5°	1379.5	1467.6	1550.3	1625.0	1707.7	1741.1	1773.1	1850.5	1927.8	2002.5	2101.3
30°	1335.5	1424.9	1496.9	1566.3	1646.3	1681.0	1721.0	1809.1	1897.1	1998.5	2118.6
32.5°	1286.1	1367.5	1434.2	1506.2	1578.3	1621.0	1671.7	1767.7	1869.1	1990.5	2144.0
35°	1236.7	1302.1	1363.5	1431.5	1518.3	1563.6	1613.0	1714.4	1841.1	1986.5	2165.3
37.5°	1174.0	1236.7	1284.8	1354.2	1443.5	1496.9	1546.3	1663.7	1807.8	1977.2	2164.0
40°	1110.0	1163.4	1208.7	1280.8	1378.2	1427.5	1480.9	1609.0	1773.1	1950.5	2132.0
42.5°	1040.6	1086.0	1135.4	1204.7	1299.5	1347.5	1408.9	1558.3	1725.0	1913.2	2049.2
45°	967.3	1011.3	1052.6	1124.7	1219.4	1271.4	1338.1	1491.6	1666.3	1834.4	1915.8
47.5°	895.2	933.9	977.9	1040.6	1136.7	1194.1	1262.1	1426.2	1587.6	1729.0	1735.7
50°	825.8	856.5	893.9	957.9	1058.0	1112.7	1183.4	1336.8	1494.2	1591.6	1526.3
52.5°	753.8	781.8	820.5	876.5	969.9	1034.0	1095.3	1248.8	1380.8	1446.2	1326.1
55°	683.1	707.1	747.1	809.8	891.2	940.6	1003.3	1146.0	1262.1	1263.4	1132.7
57.5°	613.7	635.1	668.4	724.4	800.5	857.9	915.2	1039.3	1118.0	1095.3	949.9
60°	552.3	565.7	596.4	651.1	721.8	763.1	824.5	928.6	980.6	939.2	783.1
62.5°	488.3	501.6	525.7	569.7	636.4	680.4	719.1	804.5	840.5	777.8	649.7
65°	424.3	440.3	457.6	492.3	555.0	584.4	619.0	681.7	716.4	643.1	532.3
67.5°	368.2	376.2	393.6	429.6	473.6	500.3	524.3	567.0	573.7	515.0	424.3
70°	316.2	318.9	334.9	356.2	389.6	405.6	425.6	450.9	450.9	402.9	330.9
72.5°	257.5	261.5	273.5	296.2	316.2	324.2	330.9	346.9	344.2	300.2	250.8
75°	206.8	209.5	218.8	229.5	237.5	252.2	257.5	254.8	253.5	216.1	188.1
77.5°	160.1	161.4	168.1	177.4	178.8	184.1	180.1	180.1	168.1	146.8	132.1
80°	117.4	118.7	121.4	124.1	124.1	124.1	124.1	117.4	109.4	96.1	92.1
82.5°	78.7	78.7	80.0	82.7	81.4	78.7	76.0	69.4	64.0	60.0	57.4
85°	46.7	46.7	48.0	46.7	41.4	40.0	37.4	36.0	34.7	33.4	33.4
87.5°	22.7	21.3	18.7	16.0	16.0	16.0	16.0	16.0	16.0	14.7	14.7
90°	0.6	1.1	2.3	3.4	4.5	5.1	5.7	6.3	7.4	8.0	9.1
92.5°	8.5	10.2	15.9	24.4	36.4	46.6	56.8	95.5	160.2	230.7	226.7
95°	18.8	19.3	23.9	30.1	42.6	55.4	68.2	129.0	254.0	410.8	503.4
97.5°	29.0	29.5	33.0	39.2	50.6	60.0	69.3	111.4	207.4	376.7	543.8
100°	39.8	40.9	43.2	49.4	60.2	68.8	77.3	110.2	184.1	327.3	513.1
102.5°	51.7	52.3	54.0	60.8	70.5	78.7	86.9	115.3	174.4	289.8	459.1
105°	64.2	64.2	67.1	72.7	81.8	89.8	97.7	122.7	173.3	268.2	412.0
107.5°	76.1	77.3	80.1	84.7	94.3	101.4	108.5	133.0	177.3	256.8	376.7
110°	89.2	90.3	92.6	97.7	106.3	113.6	121.0	144.3	183.5	252.3	353.4

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	102.3	103.4	105.1	110.2	118.8	125.9	133.0	155.1	191.5	252.3	339.8
115°	114.8	115.9	117.6	122.7	131.3	138.4	145.5	166.5	199.4	254.0	330.7
117.5°	126.1	127.8	129.6	134.7	144.3	151.2	158.0	177.9	208.5	256.8	325.6
120°	137.5	139.2	141.5	146.6	156.3	163.4	170.5	190.4	217.6	261.4	322.2
122.5°	149.4	150.6	152.3	157.4	168.2	175.3	182.4	202.3	227.9	265.4	319.3
125°	159.1	160.2	163.1	168.2	179.0	186.4	193.8	212.5	236.9	269.9	317.1
127.5°	167.1	168.8	172.2	178.4	189.8	197.2	204.6	222.7	245.5	275.0	315.9
130°	174.4	176.1	180.7	188.1	200.0	207.4	214.8	232.4	254.0	279.6	314.8
132.5°	180.1	182.4	188.1	196.6	209.1	216.5	223.9	241.5	261.4	284.7	314.8
135°	186.4	188.6	195.5	204.6	216.5	224.2	231.8	249.4	268.2	289.2	314.8
137.5°	194.3	196.0	202.3	211.4	223.3	231.2	239.2	255.1	273.3	293.8	315.4
140°	201.2	202.9	209.7	218.8	229.6	237.2	244.9	261.4	278.4	296.6	315.9
142.5°	209.1	210.2	216.5	225.6	235.8	242.9	250.0	265.4	281.3	298.3	316.5
145°	217.1	218.2	223.9	231.8	242.1	248.6	255.1	269.9	284.1	299.5	315.9
147.5°	225.6	226.2	231.3	238.7	247.7	253.7	259.7	272.7	285.8	300.0	314.8
150°	233.0	234.1	238.1	245.5	253.4	258.2	263.1	275.6	287.5	300.0	313.1
152.5°	240.9	241.5	244.9	251.2	258.5	262.8	267.1	278.4	288.7	299.5	310.8
155°	247.7	247.7	251.2	256.8	262.5	266.5	270.5	280.1	289.2	298.3	308.0
157.5°	254.0	254.0	256.8	262.0	267.1	270.2	273.3	281.8	289.8	297.2	305.1
160°	260.2	259.7	262.0	265.9	270.5	273.0	275.6	283.0	289.8	295.5	302.3
162.5°	265.4	264.8	267.1	270.5	273.9	275.9	277.9	284.1	289.2	293.8	298.9
165°	270.5	269.3	271.0	273.9	276.2	277.9	279.6	284.1	288.7	292.1	295.5
167.5°	273.9	273.3	274.5	276.2	277.9	279.0	280.1	284.1	287.5	289.2	292.1
170°	277.3	276.7	277.3	278.4	279.6	280.5	281.3	284.1	286.4	287.5	289.2
172.5°	279.6	278.4	279.0	280.1	280.7	281.0	281.3	283.5	285.2	285.2	285.8
175°	281.3	280.1	280.7	281.3	281.3	281.3	281.3	283.0	284.1	283.5	283.5
177.5°	282.4	281.3	281.3	281.8	281.3	281.3	281.3	282.4	283.0	281.8	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1695.7	1705.0	1713.0	1709.0	1725.0	1723.7	1726.4	1731.7	1733.0	1730.4	1725.0
5°	1787.7	1801.1	1823.8	1835.8	1833.1	1843.8	1849.1	1857.1	1865.1	1862.5	1862.5
7.5°	1890.5	1909.2	1931.8	1962.5	1966.5	1975.9	1991.9	1991.9	2001.2	1997.2	1995.9
10°	1979.9	2002.5	2038.6	2062.6	2073.3	2078.6	2094.6	2099.9	2110.6	2111.9	2111.9
12.5°	2053.2	2093.3	2117.3	2141.3	2146.6	2154.6	2166.6	2174.7	2178.7	2178.7	2174.7
15°	2091.9	2124.0	2152.0	2177.3	2192.0	2198.7	2210.7	2220.0	2225.3	2237.4	2240.0
17.5°	2107.9	2146.6	2192.0	2228.0	2253.4	2260.0	2284.1	2292.1	2302.7	2308.1	2314.7
20°	2130.6	2186.7	2241.4	2285.4	2309.4	2326.7	2352.1	2389.4	2400.1	2400.1	2396.1
22.5°	2150.6	2222.7	2297.4	2368.1	2388.1	2422.8	2469.5	2509.5	2525.5	2532.2	2526.9
25°	2174.7	2273.4	2370.8	2458.8	2513.5	2538.9	2601.6	2649.6	2668.3	2679.0	2681.6
27.5°	2216.0	2340.1	2464.2	2576.2	2632.3	2661.6	2727.0	2768.3	2791.0	2800.4	2793.7
30°	2262.7	2414.8	2558.9	2658.9	2696.3	2732.3	2775.0	2791.0	2785.7	2785.7	2805.7
32.5°	2310.7	2468.2	2596.2	2661.6	2675.0	2669.6	2652.3	2604.2	2576.2	2576.2	2593.6
35°	2337.4	2473.5	2538.9	2517.5	2465.5	2434.8	2340.1	2286.7	2226.7	2222.7	2242.7
37.5°	2322.7	2381.4	2354.8	2214.7	2144.0	2085.3	1937.2	1878.5	1834.4	1773.1	1867.8
40°	2220.0	2200.0	2061.2	1859.8	1781.1	1698.4	1581.0	1522.3	1460.9	1451.5	1474.2
42.5°	2046.6	1927.8	1725.0	1530.3	1450.2	1391.5	1302.1	1244.8	1206.1	1190.1	1216.7
45°	1830.4	1643.7	1440.9	1286.1	1198.1	1167.4	1086.0	1035.3	1005.9	993.9	1012.6
47.5°	1566.3	1378.2	1186.1	1055.3	1003.3	972.6	917.9	873.9	848.5	840.5	848.5
50°	1330.1	1136.7	975.3	891.2	844.5	819.2	773.8	745.8	725.8	720.4	733.8
52.5°	1126.0	949.9	827.2	752.5	721.8	700.4	668.4	644.4	632.4	627.0	636.4
55°	943.2	800.5	701.8	637.7	615.0	601.7	573.7	560.3	547.0	545.7	555.0
57.5°	781.8	683.1	592.4	547.0	540.3	520.3	496.3	484.3	477.6	476.3	480.3
60°	651.1	563.0	508.3	468.3	458.9	442.9	429.6	421.6	413.6	410.9	413.6
62.5°	541.7	472.3	428.3	401.6	388.2	384.2	369.6	360.2	358.9	358.9	361.6
65°	446.9	388.2	360.2	338.9	329.5	325.5	314.9	308.2	309.5	309.5	310.9
67.5°	364.2	321.5	296.2	285.5	277.5	276.2	265.5	262.8	260.2	260.2	262.8
70°	289.5	262.8	244.1	238.8	237.5	228.1	224.1	222.8	218.8	220.1	220.1
72.5°	226.8	209.5	198.8	190.8	192.1	186.8	181.4	181.4	178.8	182.8	182.8
75°	168.1	160.1	152.1	149.4	152.1	149.4	145.4	144.1	145.4	144.1	144.1
77.5°	124.1	120.1	117.4	116.1	116.1	110.7	108.1	110.7	105.4	108.1	108.1
80°	86.7	81.4	80.0	77.4	78.7	74.7	76.0	73.4	73.4	73.4	73.4
82.5°	54.7	53.4	53.4	53.4	52.0	52.0	52.0	52.0	52.0	52.0	50.7
85°	33.4	32.0	32.0	32.0	30.7	30.7	30.7	30.7	30.7	30.7	30.7
87.5°	13.3	14.7	14.7	16.0	14.7	13.3	13.3	13.3	14.7	14.7	13.3
90°	9.7	10.2	10.8	11.4	12.0	12.5	12.5	12.5	13.1	13.1	13.1
92.5°	183.0	123.3	88.6	65.9	60.5	55.1	46.0	44.3	43.2	42.0	43.2
95°	492.6	408.6	322.2	252.3	228.4	204.6	164.2	147.2	142.6	133.5	142.6
97.5°	615.4	585.8	517.1	446.6	412.5	378.4	344.3	314.8	299.5	292.6	299.5
100°	655.2	698.9	671.1	612.5	583.0	553.4	514.2	473.3	452.3	443.2	452.3
102.5°	631.3	737.0	765.4	744.9	727.3	709.7	667.1	641.0	617.7	611.4	617.7
105°	575.0	711.4	789.3	814.3	811.2	808.0	789.8	771.1	759.7	752.9	759.7
107.5°	521.6	659.1	762.0	822.2	834.7	847.2	852.3	849.5	843.8	838.1	843.8
110°	477.3	600.0	708.0	788.1	812.2	836.4	862.0	872.8	876.8	876.8	876.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	444.3	553.4	654.6	735.8	765.3	794.9	835.3	855.7	867.1	872.2	867.1
115°	422.2	515.9	604.0	681.9	712.8	743.8	788.1	815.4	831.3	838.7	831.3
117.5°	407.4	489.8	567.7	635.8	665.1	694.4	739.3	767.7	783.6	788.1	783.6
120°	395.5	469.4	537.5	600.0	625.0	650.0	692.1	719.4	734.7	739.3	734.7
122.5°	385.3	454.0	515.9	569.9	593.0	616.0	652.3	676.8	692.1	696.1	692.1
125°	376.2	439.2	497.2	546.6	567.0	587.5	619.4	642.7	655.2	660.8	655.2
127.5°	367.6	423.9	479.0	525.6	544.9	564.2	593.2	614.2	626.2	628.5	626.2
130°	359.1	409.7	459.7	504.0	522.4	540.9	569.4	588.1	599.5	602.9	599.5
132.5°	352.3	395.5	441.5	480.7	498.3	515.9	544.4	563.1	573.3	577.3	573.3
135°	347.2	383.5	422.8	459.1	475.3	491.5	516.5	535.3	545.5	548.9	545.5
137.5°	342.1	372.8	405.7	437.0	451.2	465.4	488.1	505.7	515.4	519.4	515.4
140°	338.7	364.2	390.9	417.1	429.0	440.9	462.0	476.7	485.3	488.1	485.3
142.5°	335.8	356.8	378.4	400.0	410.0	419.9	437.0	448.9	456.9	459.1	456.9
145°	333.0	350.6	368.2	385.8	393.5	401.2	414.8	424.5	430.7	433.0	430.7
147.5°	330.1	344.3	359.1	373.3	379.3	385.3	396.6	404.6	408.6	409.7	408.6
150°	326.7	339.2	351.7	362.5	367.6	372.8	381.3	388.1	390.4	390.9	390.4
152.5°	322.7	333.5	344.3	354.0	357.7	361.4	368.2	373.3	375.6	376.2	375.6
155°	318.2	327.9	337.0	344.9	348.0	351.2	356.8	360.8	362.5	363.1	362.5
157.5°	314.2	322.2	330.1	336.4	339.0	341.5	346.0	349.5	351.2	351.2	351.2
160°	309.1	316.5	322.2	327.9	329.8	331.8	335.8	338.7	339.8	339.2	339.8
162.5°	304.6	310.2	315.4	319.9	321.6	323.3	326.2	328.4	328.4	328.4	328.4
165°	300.0	304.6	308.5	312.0	313.4	314.8	317.1	318.2	318.2	318.2	318.2
167.5°	295.5	298.9	301.7	304.6	305.7	306.8	308.0	309.1	308.5	308.5	308.5
170°	291.5	294.3	296.0	297.7	298.3	298.9	300.0	300.6	300.6	300.0	300.6
172.5°	287.5	289.2	290.9	292.1	292.4	292.6	292.6	293.8	292.6	292.1	292.6
175°	284.1	285.8	285.8	287.0	287.0	287.0	287.0	287.5	286.4	285.8	286.4
177.5°	282.4	283.0	283.5	283.5	283.5	283.5	283.0	283.5	281.8	281.8	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1731.7	1722.4	1726.4	1722.4	1718.4	1714.4	1705.0	1691.7	1681.0	1673.0	1671.7
5°	1865.1	1853.1	1845.1	1841.1	1833.1	1822.4	1805.1	1785.1	1761.1	1751.7	1733.0
7.5°	1987.9	1983.9	1965.2	1962.5	1957.2	1937.2	1907.8	1881.1	1850.5	1825.1	1801.1
10°	2103.9	2094.6	2081.3	2062.6	2059.9	2034.6	2006.5	1969.2	1929.2	1905.2	1862.5
12.5°	2176.0	2165.3	2150.6	2138.6	2132.0	2115.9	2077.3	2039.9	2003.9	1959.9	1922.5
15°	2228.0	2214.7	2188.0	2178.7	2170.6	2149.3	2121.3	2082.6	2034.6	2003.9	1950.5
17.5°	2298.7	2282.7	2256.0	2238.7	2224.0	2190.7	2150.6	2098.6	2053.2	2018.6	1970.5
20°	2380.1	2356.1	2321.4	2298.7	2277.4	2238.7	2182.7	2121.3	2055.9	2013.2	1963.9
22.5°	2514.9	2469.5	2414.8	2382.8	2353.4	2286.7	2220.0	2144.0	2070.6	2006.5	1946.5
25°	2645.6	2600.2	2532.2	2488.2	2442.8	2365.4	2277.4	2172.0	2078.6	2003.9	1925.2
27.5°	2767.0	2720.3	2657.6	2604.2	2560.2	2444.1	2328.1	2209.3	2090.6	1987.9	1907.8
30°	2795.0	2775.0	2727.0	2680.3	2640.3	2533.5	2398.8	2248.0	2105.3	1973.2	1883.8
32.5°	2625.6	2675.0	2687.0	2680.3	2654.9	2578.9	2454.8	2296.1	2126.6	1966.5	1843.8
35°	2273.4	2362.8	2454.8	2504.2	2528.2	2538.9	2465.5	2320.1	2141.3	1955.9	1817.1
37.5°	1885.1	1971.9	2117.3	2190.7	2272.0	2378.8	2408.1	2314.7	2134.6	1947.8	1774.4
40°	1548.9	1659.7	1779.7	1846.5	1917.2	2109.3	2254.7	2244.0	2113.3	1918.5	1741.1
42.5°	1260.8	1330.1	1435.5	1508.9	1595.6	1810.4	2005.2	2101.3	2049.2	1882.5	1698.4
45°	1051.3	1104.7	1179.4	1254.1	1307.5	1502.2	1733.0	1890.5	1939.8	1818.4	1633.0
47.5°	885.9	925.9	991.3	1038.0	1095.3	1248.8	1448.9	1670.3	1774.4	1727.7	1563.6
50°	759.1	791.1	843.2	872.5	923.2	1055.3	1207.4	1439.5	1597.0	1602.3	1471.6
52.5°	648.4	680.4	724.4	749.8	780.5	869.9	1023.3	1219.4	1400.8	1467.6	1366.2
55°	564.3	583.0	619.0	639.1	667.1	753.8	851.2	1017.9	1207.4	1316.8	1252.8
57.5°	487.0	507.0	529.7	545.7	565.7	635.1	723.1	848.5	1036.6	1155.4	1134.0
60°	424.3	436.3	457.6	469.6	488.3	533.7	595.0	720.4	869.9	981.9	993.9
62.5°	365.6	376.2	390.9	401.6	413.6	449.6	495.0	584.4	715.1	836.5	852.5
65°	314.9	324.2	332.2	341.5	350.9	373.6	412.2	481.6	583.0	696.4	731.1
67.5°	269.5	272.2	284.2	285.5	290.8	308.2	336.2	392.2	465.6	556.3	601.7
70°	225.5	230.8	233.5	237.5	242.8	254.8	277.5	306.9	361.6	434.9	477.6
72.5°	182.8	184.1	188.1	190.8	196.1	205.5	216.1	238.8	273.5	326.9	365.6
75°	145.4	146.8	149.4	150.8	154.8	157.4	162.8	178.8	202.8	234.8	262.8
77.5°	109.4	112.1	114.7	114.7	116.1	118.7	121.4	126.7	138.8	160.1	184.1
80°	74.7	76.0	76.0	77.4	76.0	80.0	84.1	90.7	96.1	102.7	114.7
82.5°	52.0	52.0	52.0	53.4	53.4	54.7	54.7	56.0	57.4	61.4	66.7
85°	32.0	32.0	33.4	30.7	32.0	33.4	33.4	32.0	33.4	34.7	36.0
87.5°	13.3	13.3	14.7	14.7	14.7	14.7	13.3	14.7	13.3	14.7	14.7
90°	12.5	12.5	12.5	12.0	11.4	10.8	10.2	9.7	9.1	8.0	7.4
92.5°	44.3	46.0	55.1	60.5	65.9	88.6	123.3	183.0	226.7	230.7	160.2
95°	147.2	164.2	204.6	228.4	252.3	322.2	408.6	492.6	503.4	410.8	254.0
97.5°	314.8	344.3	378.4	412.5	446.6	517.1	585.8	615.4	543.8	376.7	207.4
100°	473.3	514.2	553.4	583.0	612.5	671.1	698.9	655.2	513.1	327.3	184.1
102.5°	641.0	667.1	709.7	727.3	744.9	765.4	737.0	631.3	459.1	289.8	174.4
105°	771.1	789.8	808.0	811.2	814.3	789.3	711.4	575.0	412.0	268.2	173.3
107.5°	849.5	852.3	847.2	834.7	822.2	762.0	659.1	521.6	376.7	256.8	177.3
110°	872.8	862.0	836.4	812.2	788.1	708.0	600.0	477.3	353.4	252.3	183.5

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	855.7	835.3	794.9	765.3	735.8	654.6	553.4	444.3	339.8	252.3	191.5
115°	815.4	788.1	743.8	712.8	681.9	604.0	515.9	422.2	330.7	254.0	199.4
117.5°	767.7	739.3	694.4	665.1	635.8	567.7	489.8	407.4	325.6	256.8	208.5
120°	719.4	692.1	650.0	625.0	600.0	537.5	469.4	395.5	322.2	261.4	217.6
122.5°	676.8	652.3	616.0	593.0	569.9	515.9	454.0	385.3	319.3	265.4	227.9
125°	642.7	619.4	587.5	567.0	546.6	497.2	439.2	376.2	317.1	269.9	236.9
127.5°	614.2	593.2	564.2	544.9	525.6	479.0	423.9	367.6	315.9	275.0	245.5
130°	588.1	569.4	540.9	522.4	504.0	459.7	409.7	359.1	314.8	279.6	254.0
132.5°	563.1	544.4	515.9	498.3	480.7	441.5	395.5	352.3	314.8	284.7	261.4
135°	535.3	516.5	491.5	475.3	459.1	422.8	383.5	347.2	314.8	289.2	268.2
137.5°	505.7	488.1	465.4	451.2	437.0	405.7	372.8	342.1	315.4	293.8	273.3
140°	476.7	462.0	440.9	429.0	417.1	390.9	364.2	338.7	315.9	296.6	278.4
142.5°	448.9	437.0	419.9	410.0	400.0	378.4	356.8	335.8	316.5	298.3	281.3
145°	424.5	414.8	401.2	393.5	385.8	368.2	350.6	333.0	315.9	299.5	284.1
147.5°	404.6	396.6	385.3	379.3	373.3	359.1	344.3	330.1	314.8	300.0	285.8
150°	388.1	381.3	372.8	367.6	362.5	351.7	339.2	326.7	313.1	300.0	287.5
152.5°	373.3	368.2	361.4	357.7	354.0	344.3	333.5	322.7	310.8	299.5	288.7
155°	360.8	356.8	351.2	348.0	344.9	337.0	327.9	318.2	308.0	298.3	289.2
157.5°	349.5	346.0	341.5	339.0	336.4	330.1	322.2	314.2	305.1	297.2	289.8
160°	338.7	335.8	331.8	329.8	327.9	322.2	316.5	309.1	302.3	295.5	289.8
162.5°	328.4	326.2	323.3	321.6	319.9	315.4	310.2	304.6	298.9	293.8	289.2
165°	318.2	317.1	314.8	313.4	312.0	308.5	304.6	300.0	295.5	292.1	288.7
167.5°	309.1	308.0	306.8	305.7	304.6	301.7	298.9	295.5	292.1	289.2	287.5
170°	300.6	300.0	298.9	298.3	297.7	296.0	294.3	291.5	289.2	287.5	286.4
172.5°	293.8	292.6	292.6	292.4	292.1	290.9	289.2	287.5	285.8	285.2	285.2
175°	287.5	287.0	287.0	287.0	287.0	285.8	285.8	284.1	283.5	283.5	284.1
177.5°	283.5	283.0	283.5	283.5	283.5	283.5	283.0	282.4	281.8	281.8	283.0
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1667.7	1659.7	1654.3	1653.0	1645.0	1638.3	1630.3	1629.0	1625.0	1614.3	1607.6
5°	1719.7	1701.0	1697.0	1685.0	1665.0	1650.3	1631.7	1621.0	1609.0	1589.0	1573.0
7.5°	1773.1	1747.7	1729.0	1711.7	1683.7	1657.0	1630.3	1609.0	1587.6	1558.3	1534.3
10°	1825.1	1786.4	1763.7	1738.4	1699.7	1659.7	1622.3	1591.6	1556.9	1522.3	1487.6
12.5°	1873.1	1823.8	1790.4	1754.4	1706.4	1657.0	1609.0	1566.3	1530.3	1483.6	1444.9
15°	1902.5	1847.8	1814.4	1779.7	1707.7	1653.0	1597.0	1542.3	1494.2	1444.9	1408.9
17.5°	1919.8	1858.5	1821.1	1789.1	1715.7	1641.0	1569.0	1510.2	1458.2	1399.5	1351.5
20°	1911.8	1851.8	1817.1	1786.4	1701.0	1626.3	1548.9	1480.9	1415.5	1355.5	1304.8
22.5°	1894.5	1831.8	1793.1	1765.1	1689.0	1601.0	1515.6	1442.2	1374.2	1314.1	1256.8
25°	1857.1	1795.8	1762.4	1727.7	1653.0	1569.0	1482.2	1403.5	1331.5	1267.4	1203.4
27.5°	1823.8	1749.1	1714.4	1683.7	1605.0	1530.3	1444.9	1358.2	1284.8	1218.1	1154.0
30°	1785.1	1701.0	1663.7	1622.3	1551.6	1480.9	1395.5	1315.5	1239.4	1168.7	1107.3
32.5°	1743.7	1646.3	1603.6	1556.9	1484.9	1418.2	1346.1	1267.4	1191.4	1122.0	1058.0
35°	1690.4	1586.3	1536.9	1492.9	1418.2	1351.5	1284.8	1219.4	1143.4	1070.0	1008.6
37.5°	1639.7	1524.9	1472.9	1422.2	1343.5	1279.4	1224.7	1163.4	1090.0	1019.3	960.6
40°	1582.3	1450.2	1396.8	1350.2	1268.8	1198.1	1148.7	1100.7	1036.6	968.6	904.5
42.5°	1530.3	1380.8	1324.8	1276.8	1191.4	1124.7	1078.0	1038.0	981.9	919.2	853.9
45°	1458.2	1306.1	1248.8	1198.1	1111.3	1048.6	1000.6	965.9	921.9	863.2	804.5
47.5°	1391.5	1234.1	1171.4	1110.0	1031.3	967.3	923.2	896.5	867.2	815.2	755.1
50°	1310.1	1151.4	1087.3	1036.6	947.2	892.5	848.5	829.8	803.2	753.8	705.8
52.5°	1222.1	1071.3	1011.3	949.9	867.2	813.8	775.1	753.8	732.4	696.4	651.1
55°	1119.3	981.9	925.9	871.2	788.5	739.1	704.4	681.7	669.7	636.4	603.0
57.5°	1020.6	891.2	839.2	788.5	716.4	660.4	637.7	617.7	600.4	576.3	548.3
60°	920.6	803.2	747.1	701.8	639.1	588.4	569.7	549.7	536.3	517.6	497.6
62.5°	805.8	705.8	663.1	620.4	567.0	527.0	505.6	489.6	472.3	460.3	442.9
65°	684.4	613.7	572.3	540.3	489.6	453.6	437.6	426.9	412.2	400.2	386.9
67.5°	571.0	515.0	497.6	462.9	424.3	392.2	380.2	366.9	354.9	348.2	336.2
70°	461.6	421.6	404.2	394.9	352.2	330.9	320.2	314.9	300.2	293.5	285.5
72.5°	357.5	342.9	330.9	318.9	290.8	277.5	265.5	260.2	249.5	244.1	241.5
75°	264.2	254.8	248.2	246.8	234.8	221.5	209.5	206.8	198.8	193.5	190.8
77.5°	185.4	182.8	181.4	182.8	174.8	166.8	164.1	161.4	152.1	150.8	150.8
80°	121.4	128.1	128.1	126.7	124.1	122.7	118.7	116.1	110.7	109.4	110.7
82.5°	74.7	78.7	80.0	82.7	81.4	80.0	77.4	76.0	77.4	74.7	76.0
85°	37.4	40.0	45.4	45.4	46.7	46.7	46.7	45.4	42.7	44.0	42.7
87.5°	14.7	16.0	16.0	16.0	14.7	18.7	20.0	20.0	20.0	17.3	17.3
90°	6.3	5.7	5.1	4.5	3.4	2.3	1.1	0.6	1.1	2.3	3.4
92.5°	95.5	56.8	46.6	36.4	24.4	15.9	10.2	8.5	10.2	15.9	24.4
95°	129.0	68.2	55.4	42.6	30.1	23.9	19.3	18.8	19.3	23.9	30.1
97.5°	111.4	69.3	60.0	50.6	39.2	33.0	29.5	29.0	29.5	33.0	39.2
100°	110.2	77.3	68.8	60.2	49.4	43.2	40.9	39.8	40.9	43.2	49.4
102.5°	115.3	86.9	78.7	70.5	60.8	54.0	52.3	51.7	52.3	54.0	60.8
105°	122.7	97.7	89.8	81.8	72.7	67.1	64.2	64.2	64.2	67.1	72.7
107.5°	133.0	108.5	101.4	94.3	84.7	80.1	77.3	76.1	77.3	80.1	84.7
110°	144.3	121.0	113.6	106.3	97.7	92.6	90.3	89.2	90.3	92.6	97.7

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	155.1	133.0	125.9	118.8	110.2	105.1	103.4	102.3	103.4	105.1	110.2
115°	166.5	145.5	138.4	131.3	122.7	117.6	115.9	114.8	115.9	117.6	122.7
117.5°	177.9	158.0	151.2	144.3	134.7	129.6	127.8	126.1	127.8	129.6	134.7
120°	190.4	170.5	163.4	156.3	146.6	141.5	139.2	137.5	139.2	141.5	146.6
122.5°	202.3	182.4	175.3	168.2	157.4	152.3	150.6	149.4	150.6	152.3	157.4
125°	212.5	193.8	186.4	179.0	168.2	163.1	160.2	159.1	160.2	163.1	168.2
127.5°	222.7	204.6	197.2	189.8	178.4	172.2	168.8	167.1	168.8	172.2	178.4
130°	232.4	214.8	207.4	200.0	188.1	180.7	176.1	174.4	176.1	180.7	188.1
132.5°	241.5	223.9	216.5	209.1	196.6	188.1	182.4	180.1	182.4	188.1	196.6
135°	249.4	231.8	224.2	216.5	204.6	195.5	188.6	186.4	188.6	195.5	204.6
137.5°	255.1	239.2	231.2	223.3	211.4	202.3	196.0	194.3	196.0	202.3	211.4
140°	261.4	244.9	237.2	229.6	218.8	209.7	202.9	201.2	202.9	209.7	218.8
142.5°	265.4	250.0	242.9	235.8	225.6	216.5	210.2	209.1	210.2	216.5	225.6
145°	269.9	255.1	248.6	242.1	231.8	223.9	218.2	217.1	218.2	223.9	231.8
147.5°	272.7	259.7	253.7	247.7	238.7	231.3	226.2	225.6	226.2	231.3	238.7
150°	275.6	263.1	258.2	253.4	245.5	238.1	234.1	233.0	234.1	238.1	245.5
152.5°	278.4	267.1	262.8	258.5	251.2	244.9	241.5	240.9	241.5	244.9	251.2
155°	280.1	270.5	266.5	262.5	256.8	251.2	247.7	247.7	247.7	251.2	256.8
157.5°	281.8	273.3	270.2	267.1	262.0	256.8	254.0	254.0	254.0	256.8	262.0
160°	283.0	275.6	273.0	270.5	265.9	262.0	259.7	260.2	259.7	262.0	265.9
162.5°	284.1	277.9	275.9	273.9	270.5	267.1	264.8	265.4	264.8	267.1	270.5
165°	284.1	279.6	277.9	276.2	273.9	271.0	269.3	270.5	269.3	271.0	273.9
167.5°	284.1	280.1	279.0	277.9	276.2	274.5	273.3	273.9	273.3	274.5	276.2
170°	284.1	281.3	280.5	279.6	278.4	277.3	276.7	277.3	276.7	277.3	278.4
172.5°	283.5	281.3	281.0	280.7	280.1	279.0	278.4	279.6	278.4	279.0	280.1
175°	283.0	281.3	281.3	281.3	281.3	280.7	280.1	281.3	280.1	280.7	281.3
177.5°	282.4	281.3	281.3	281.3	281.8	281.3	281.3	282.4	281.3	281.3	281.8
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1603.6	1598.3	1594.3	1590.3	1573.0	1554.3	1551.6	1547.6	1539.6	1548.9	1544.9
5°	1562.3	1550.3	1543.6	1526.3	1504.9	1488.9	1475.6	1459.6	1452.9	1447.5	1446.2
7.5°	1511.6	1500.9	1488.9	1471.6	1444.9	1418.2	1398.2	1382.2	1368.8	1362.2	1362.2
10°	1462.2	1448.9	1432.9	1403.5	1378.2	1344.8	1323.5	1307.5	1288.8	1278.1	1268.8
12.5°	1411.5	1396.8	1382.2	1344.8	1315.5	1280.8	1250.1	1230.1	1220.7	1208.7	1192.7
15°	1360.8	1338.1	1323.5	1286.1	1248.8	1214.1	1194.1	1172.7	1151.4	1139.4	1134.0
17.5°	1307.5	1291.4	1267.4	1227.4	1186.1	1155.4	1126.0	1106.0	1080.7	1068.6	1056.6
20°	1259.4	1235.4	1211.4	1171.4	1131.4	1090.0	1060.6	1036.6	1020.6	1011.3	1000.6
22.5°	1202.1	1179.4	1159.4	1116.7	1072.6	1034.0	1001.9	987.3	971.3	956.6	945.9
25°	1152.7	1130.0	1110.0	1063.3	1015.3	979.3	955.2	936.6	919.2	912.6	901.9
27.5°	1100.7	1079.3	1052.6	1005.9	963.3	932.6	907.2	889.9	876.5	863.2	855.2
30°	1051.3	1027.3	1003.3	952.6	917.9	887.2	863.2	841.8	831.2	824.5	811.2
32.5°	1003.3	972.6	952.6	905.9	872.5	843.2	823.2	804.5	791.1	779.1	768.5
35°	951.2	917.9	897.9	859.2	824.5	795.1	777.8	764.5	748.5	737.8	732.4
37.5°	901.9	873.9	853.9	813.8	779.1	755.1	736.4	719.1	712.4	697.8	695.1
40°	848.5	824.5	805.8	767.1	735.1	716.4	696.4	680.4	668.4	661.7	652.4
42.5°	800.5	780.5	760.5	724.4	693.8	671.1	656.4	641.7	631.0	620.4	613.7
45°	756.5	735.1	716.4	681.7	651.1	631.0	616.4	599.0	596.4	581.7	575.0
47.5°	709.8	691.1	675.1	639.1	611.0	591.0	573.7	561.7	549.7	544.3	535.0
50°	664.4	645.7	627.0	595.0	569.7	549.7	532.3	519.0	512.3	504.3	496.3
52.5°	615.0	600.4	585.7	552.3	527.0	509.6	495.0	477.6	471.0	464.3	458.9
55°	573.7	552.3	536.3	508.3	485.6	466.9	450.9	437.6	430.9	425.6	418.9
57.5°	517.6	504.3	491.0	465.6	444.3	425.6	409.6	398.9	390.9	386.9	388.2
60°	469.6	454.9	446.9	420.3	398.9	384.2	369.6	358.9	350.9	346.9	345.5
62.5°	418.9	408.2	393.6	374.9	353.5	340.2	329.5	321.5	308.2	306.9	302.9
65°	369.6	361.6	348.2	330.9	313.5	301.5	289.5	278.8	273.5	266.8	262.8
67.5°	321.5	313.5	301.5	286.8	274.8	262.8	252.2	241.5	232.1	226.8	224.1
70°	274.8	268.2	260.2	242.8	228.1	218.8	210.8	204.1	194.8	192.1	190.8
72.5°	229.5	222.8	218.8	204.1	190.8	182.8	174.8	168.1	164.1	162.8	158.8
75°	188.1	181.4	176.1	162.8	154.8	149.4	141.4	138.8	134.7	133.4	132.1
77.5°	146.8	140.1	138.8	129.4	120.1	117.4	114.7	109.4	109.4	109.4	106.7
80°	105.4	104.1	102.7	93.4	89.4	86.7	85.4	81.4	78.7	76.0	74.7
82.5°	70.7	69.4	68.0	64.0	60.0	58.7	57.4	54.7	54.7	56.0	53.4
85°	42.7	40.0	38.7	37.4	34.7	34.7	36.0	34.7	34.7	34.7	33.4
87.5°	16.0	16.0	16.0	16.0	17.3	14.7	16.0	16.0	14.7	14.7	13.3
90°	4.5	5.1	5.7	6.3	7.4	8.0	9.1	9.7	10.2	10.8	11.4
92.5°	36.4	46.6	56.8	95.5	160.2	230.7	226.7	183.0	123.3	88.6	65.9
95°	42.6	55.4	68.2	129.0	254.0	410.8	503.4	492.6	408.6	322.2	252.3
97.5°	50.6	60.0	69.3	111.4	207.4	376.7	543.8	615.4	585.8	517.1	446.6
100°	60.2	68.8	77.3	110.2	184.1	327.3	513.1	655.2	698.9	671.1	612.5
102.5°	70.5	78.7	86.9	115.3	174.4	289.8	459.1	631.3	737.0	765.4	744.9
105°	81.8	89.8	97.7	122.7	173.3	268.2	412.0	575.0	711.4	789.3	814.3
107.5°	94.3	101.4	108.5	133.0	177.3	256.8	376.7	521.6	659.1	762.0	822.2
110°	106.3	113.6	121.0	144.3	183.5	252.3	353.4	477.3	600.0	708.0	788.1

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	118.8	125.9	133.0	155.1	191.5	252.3	339.8	444.3	553.4	654.6	735.8
115°	131.3	138.4	145.5	166.5	199.4	254.0	330.7	422.2	515.9	604.0	681.9
117.5°	144.3	151.2	158.0	177.9	208.5	256.8	325.6	407.4	489.8	567.7	635.8
120°	156.3	163.4	170.5	190.4	217.6	261.4	322.2	395.5	469.4	537.5	600.0
122.5°	168.2	175.3	182.4	202.3	227.9	265.4	319.3	385.3	454.0	515.9	569.9
125°	179.0	186.4	193.8	212.5	236.9	269.9	317.1	376.2	439.2	497.2	546.6
127.5°	189.8	197.2	204.6	222.7	245.5	275.0	315.9	367.6	423.9	479.0	525.6
130°	200.0	207.4	214.8	232.4	254.0	279.6	314.8	359.1	409.7	459.7	504.0
132.5°	209.1	216.5	223.9	241.5	261.4	284.7	314.8	352.3	395.5	441.5	480.7
135°	216.5	224.2	231.8	249.4	268.2	289.2	314.8	347.2	383.5	422.8	459.1
137.5°	223.3	231.2	239.2	255.1	273.3	293.8	315.4	342.1	372.8	405.7	437.0
140°	229.6	237.2	244.9	261.4	278.4	296.6	315.9	338.7	364.2	390.9	417.1
142.5°	235.8	242.9	250.0	265.4	281.3	298.3	316.5	335.8	356.8	378.4	400.0
145°	242.1	248.6	255.1	269.9	284.1	299.5	315.9	333.0	350.6	368.2	385.8
147.5°	247.7	253.7	259.7	272.7	285.8	300.0	314.8	330.1	344.3	359.1	373.3
150°	253.4	258.2	263.1	275.6	287.5	300.0	313.1	326.7	339.2	351.7	362.5
152.5°	258.5	262.8	267.1	278.4	288.7	299.5	310.8	322.7	333.5	344.3	354.0
155°	262.5	266.5	270.5	280.1	289.2	298.3	308.0	318.2	327.9	337.0	344.9
157.5°	267.1	270.2	273.3	281.8	289.8	297.2	305.1	314.2	322.2	330.1	336.4
160°	270.5	273.0	275.6	283.0	289.8	295.5	302.3	309.1	316.5	322.2	327.9
162.5°	273.9	275.9	277.9	284.1	289.2	293.8	298.9	304.6	310.2	315.4	319.9
165°	276.2	277.9	279.6	284.1	288.7	292.1	295.5	300.0	304.6	308.5	312.0
167.5°	277.9	279.0	280.1	284.1	287.5	289.2	292.1	295.5	298.9	301.7	304.6
170°	279.6	280.5	281.3	284.1	286.4	287.5	289.2	291.5	294.3	296.0	297.7
172.5°	280.7	281.0	281.3	283.5	285.2	285.2	285.8	287.5	289.2	290.9	292.1
175°	281.3	281.3	281.3	283.0	284.1	283.5	283.5	284.1	285.8	285.8	287.0
177.5°	281.3	281.3	281.3	282.4	283.0	281.8	281.8	282.4	283.0	283.5	283.5
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1538.3	1540.9	1534.3	1531.6	1526.3	1532.9	1534.3	1532.9	1544.9	1539.6	1542.3
5°	1448.9	1443.5	1439.5	1430.2	1430.2	1431.5	1435.5	1428.9	1432.9	1442.2	1440.9
7.5°	1350.2	1347.5	1348.8	1338.1	1330.1	1332.8	1330.1	1342.1	1348.8	1346.1	1351.5
10°	1260.8	1266.1	1254.1	1248.8	1243.4	1248.8	1247.4	1250.1	1258.1	1263.4	1272.8
12.5°	1188.7	1187.4	1180.7	1175.4	1166.0	1168.7	1176.7	1174.0	1175.4	1187.4	1186.1
15°	1120.7	1112.7	1107.3	1095.3	1098.0	1088.7	1096.7	1106.0	1110.0	1120.7	1127.3
17.5°	1052.6	1051.3	1044.6	1043.3	1028.6	1024.6	1032.6	1035.3	1039.3	1044.6	1054.0
20°	995.3	993.9	984.6	981.9	969.9	977.9	975.3	980.6	983.3	993.9	997.9
22.5°	943.2	936.6	933.9	929.9	925.9	924.6	929.9	928.6	937.9	941.9	943.2
25°	895.2	889.9	888.5	881.9	879.2	875.2	879.2	883.2	893.9	897.9	903.2
27.5°	851.2	847.2	844.5	839.2	835.2	835.2	837.8	843.2	847.2	849.8	852.5
30°	811.2	808.5	800.5	797.8	793.8	793.8	793.8	796.5	803.2	811.2	815.2
32.5°	769.8	764.5	759.1	759.1	755.1	755.1	756.5	759.1	765.8	767.1	773.8
35°	729.8	724.4	720.4	717.8	719.1	713.8	716.4	720.4	728.4	731.1	735.1
37.5°	691.1	689.8	681.7	677.7	680.4	680.4	679.1	681.7	687.1	692.4	695.1
40°	648.4	645.7	645.7	641.7	643.1	637.7	641.7	644.4	647.1	652.4	656.4
42.5°	611.0	608.4	603.0	604.4	600.4	600.4	603.0	604.4	608.4	615.0	617.7
45°	571.0	571.0	568.3	564.3	565.7	561.7	564.3	565.7	571.0	577.7	575.0
47.5°	532.3	531.0	531.0	525.7	528.3	524.3	528.3	529.7	532.3	536.3	535.0
50°	495.0	491.0	492.3	491.0	489.6	489.6	492.3	492.3	495.0	495.0	499.0
52.5°	456.3	456.3	453.6	454.9	457.6	454.9	458.9	454.9	457.6	458.9	461.6
55°	421.6	418.9	420.3	418.9	424.3	420.3	424.3	421.6	424.3	422.9	425.6
57.5°	384.2	380.2	381.6	380.2	384.2	382.9	386.9	382.9	384.2	385.6	389.6
60°	341.5	341.5	341.5	338.9	342.9	342.9	341.5	341.5	346.9	349.5	348.2
62.5°	301.5	300.2	296.2	294.8	296.2	293.5	298.8	297.5	300.2	302.9	305.5
65°	257.5	254.8	253.5	250.8	250.8	249.5	250.8	256.2	257.5	258.8	265.5
67.5°	221.5	220.1	218.8	214.8	214.8	217.5	217.5	217.5	225.5	221.5	226.8
70°	189.4	186.8	184.1	182.8	182.8	184.1	185.4	186.8	185.4	190.8	192.1
72.5°	158.8	160.1	157.4	157.4	157.4	156.1	156.1	158.8	160.1	158.8	160.1
75°	132.1	132.1	130.7	132.1	132.1	130.7	130.7	133.4	133.4	132.1	136.1
77.5°	106.7	105.4	102.7	100.1	101.4	100.1	101.4	100.1	104.1	108.1	105.4
80°	74.7	73.4	73.4	73.4	74.7	73.4	76.0	73.4	74.7	74.7	76.0
82.5°	53.4	54.7	54.7	53.4	54.7	53.4	54.7	54.7	54.7	53.4	54.7
85°	34.7	34.7	34.7	34.7	33.4	34.7	34.7	34.7	36.0	34.7	36.0
87.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.0	14.7	16.0
90°	12.0	12.5	12.5	12.5	13.1	13.1	13.1	12.5	12.5	12.5	12.0
92.5°	60.5	55.1	46.0	44.3	43.2	42.0	43.2	44.3	46.0	55.1	60.5
95°	228.4	204.6	164.2	147.2	142.6	133.5	142.6	147.2	164.2	204.6	228.4
97.5°	412.5	378.4	344.3	314.8	299.5	292.6	299.5	314.8	344.3	378.4	412.5
100°	583.0	553.4	514.2	473.3	452.3	443.2	452.3	473.3	514.2	553.4	583.0
102.5°	727.3	709.7	667.1	641.0	617.7	611.4	617.7	641.0	667.1	709.7	727.3
105°	811.2	808.0	789.8	771.1	759.7	752.9	759.7	771.1	789.8	808.0	811.2
107.5°	834.7	847.2	852.3	849.5	843.8	838.1	843.8	849.5	852.3	847.2	834.7
110°	812.2	836.4	862.0	872.8	876.8	876.8	876.8	872.8	862.0	836.4	812.2

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	765.3	794.9	835.3	855.7	867.1	872.2	867.1	855.7	835.3	794.9	765.3
115°	712.8	743.8	788.1	815.4	831.3	838.7	831.3	815.4	788.1	743.8	712.8
117.5°	665.1	694.4	739.3	767.7	783.6	788.1	783.6	767.7	739.3	694.4	665.1
120°	625.0	650.0	692.1	719.4	734.7	739.3	734.7	719.4	692.1	650.0	625.0
122.5°	593.0	616.0	652.3	676.8	692.1	696.1	692.1	676.8	652.3	616.0	593.0
125°	567.0	587.5	619.4	642.7	655.2	660.8	655.2	642.7	619.4	587.5	567.0
127.5°	544.9	564.2	593.2	614.2	626.2	628.5	626.2	614.2	593.2	564.2	544.9
130°	522.4	540.9	569.4	588.1	599.5	602.9	599.5	588.1	569.4	540.9	522.4
132.5°	498.3	515.9	544.4	563.1	573.3	577.3	573.3	563.1	544.4	515.9	498.3
135°	475.3	491.5	516.5	535.3	545.5	548.9	545.5	535.3	516.5	491.5	475.3
137.5°	451.2	465.4	488.1	505.7	515.4	519.4	515.4	505.7	488.1	465.4	451.2
140°	429.0	440.9	462.0	476.7	485.3	488.1	485.3	476.7	462.0	440.9	429.0
142.5°	410.0	419.9	437.0	448.9	456.9	459.1	456.9	448.9	437.0	419.9	410.0
145°	393.5	401.2	414.8	424.5	430.7	433.0	430.7	424.5	414.8	401.2	393.5
147.5°	379.3	385.3	396.6	404.6	408.6	409.7	408.6	404.6	396.6	385.3	379.3
150°	367.6	372.8	381.3	388.1	390.4	390.9	390.4	388.1	381.3	372.8	367.6
152.5°	357.7	361.4	368.2	373.3	375.6	376.2	375.6	373.3	368.2	361.4	357.7
155°	348.0	351.2	356.8	360.8	362.5	363.1	362.5	360.8	356.8	351.2	348.0
157.5°	339.0	341.5	346.0	349.5	351.2	351.2	351.2	349.5	346.0	341.5	339.0
160°	329.8	331.8	335.8	338.7	339.8	339.2	339.8	338.7	335.8	331.8	329.8
162.5°	321.6	323.3	326.2	328.4	328.4	328.4	328.4	328.4	326.2	323.3	321.6
165°	313.4	314.8	317.1	318.2	318.2	318.2	318.2	318.2	317.1	314.8	313.4
167.5°	305.7	306.8	308.0	309.1	308.5	308.5	308.5	309.1	308.0	306.8	305.7
170°	298.3	298.9	300.0	300.6	300.6	300.0	300.6	300.6	300.0	298.9	298.3
172.5°	292.4	292.6	292.6	293.8	292.6	292.1	292.6	293.8	292.6	292.6	292.4
175°	287.0	287.0	287.0	287.5	286.4	285.8	286.4	287.5	287.0	287.0	287.0
177.5°	283.5	283.5	283.0	283.5	281.8	281.8	281.8	283.5	283.0	283.5	283.5
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0	1625.0
2.5°	1536.9	1543.6	1538.3	1534.3	1544.9	1550.3	1550.3	1559.6	1569.0	1577.0	1578.3
5°	1442.2	1452.9	1455.5	1454.2	1470.2	1478.2	1495.6	1504.9	1518.3	1527.6	1538.3
7.5°	1355.5	1370.2	1371.5	1374.2	1398.2	1411.5	1426.2	1450.2	1468.9	1482.2	1494.2
10°	1268.8	1278.1	1287.4	1299.5	1323.5	1346.1	1367.5	1392.8	1416.9	1430.2	1447.5
12.5°	1203.4	1210.1	1220.7	1228.7	1254.1	1274.1	1302.1	1336.8	1371.5	1382.2	1403.5
15°	1135.4	1139.4	1160.7	1168.7	1190.1	1223.4	1240.8	1274.1	1311.5	1331.5	1355.5
17.5°	1056.6	1080.7	1094.0	1103.3	1130.0	1156.7	1184.7	1219.4	1267.4	1286.1	1303.5
20°	1000.6	1017.9	1032.6	1044.6	1068.6	1108.7	1134.0	1162.0	1207.4	1228.7	1254.1
22.5°	951.2	965.9	979.3	992.6	1008.6	1044.6	1074.0	1112.7	1158.0	1178.0	1207.4
25°	904.5	919.2	927.2	943.2	964.6	989.9	1024.6	1059.3	1104.7	1127.3	1155.4
27.5°	859.2	873.9	888.5	901.9	916.6	940.6	964.6	1008.6	1055.3	1082.0	1106.0
30°	820.5	827.2	840.5	855.2	869.9	892.5	920.6	951.2	1004.6	1028.6	1058.0
32.5°	777.8	789.8	799.2	809.8	828.5	847.2	872.5	911.2	953.9	976.6	1008.6
35°	737.8	748.5	755.1	773.8	785.8	805.8	831.2	865.9	901.9	927.2	955.2
37.5°	699.1	709.8	717.8	728.4	744.5	761.8	788.5	813.8	856.5	877.9	909.9
40°	659.1	668.4	677.7	689.8	704.4	725.8	741.8	773.8	808.5	832.5	856.5
42.5°	620.4	625.7	636.4	649.7	664.4	683.1	705.8	731.1	765.8	787.1	808.5
45°	579.0	588.4	600.4	609.7	623.0	641.7	661.7	684.4	719.1	740.4	763.1
47.5°	540.3	547.0	555.0	569.7	587.0	600.4	621.7	643.1	675.1	695.1	716.4
50°	500.3	507.0	519.0	528.3	541.7	559.0	579.0	601.7	632.4	645.7	667.1
52.5°	462.9	465.6	477.6	487.0	500.3	520.3	536.3	556.3	585.7	600.4	621.7
55°	425.6	428.3	434.9	444.3	458.9	475.0	492.3	515.0	540.3	553.7	573.7
57.5°	386.9	389.6	396.2	402.9	417.6	432.3	452.3	471.0	496.3	508.3	527.0
60°	348.2	348.2	354.9	364.2	374.9	388.2	405.6	428.3	446.9	461.6	475.0
62.5°	306.9	310.9	314.9	321.5	333.5	349.5	364.2	380.2	402.9	413.6	425.6
65°	265.5	269.5	277.5	284.2	293.5	304.2	322.9	336.2	353.5	365.6	376.2
67.5°	229.5	233.5	238.8	246.8	253.5	265.5	278.8	292.2	310.9	318.9	326.9
70°	192.1	196.1	200.1	210.8	217.5	226.8	236.1	249.5	265.5	270.8	277.5
72.5°	162.8	164.1	169.4	172.1	181.4	189.4	200.1	208.1	220.1	226.8	232.1
75°	137.4	137.4	138.8	141.4	146.8	152.1	160.1	168.1	178.8	182.8	189.4
77.5°	108.1	112.1	110.7	113.4	116.1	118.7	125.4	130.7	141.4	144.1	146.8
80°	77.4	78.7	82.7	86.7	86.7	90.7	94.7	96.1	102.7	106.7	106.7
82.5°	56.0	57.4	56.0	57.4	58.7	60.0	64.0	69.4	69.4	70.7	73.4
85°	34.7	34.7	36.0	37.4	37.4	36.0	38.7	37.4	38.7	41.4	41.4
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	11.4	10.8	10.2	9.7	9.1	8.0	7.4	6.3	5.7	5.1	4.5
92.5°	65.9	88.6	123.3	183.0	226.7	230.7	160.2	95.5	56.8	46.6	36.4
95°	252.3	322.2	408.6	492.6	503.4	410.8	254.0	129.0	68.2	55.4	42.6
97.5°	446.6	517.1	585.8	615.4	543.8	376.7	207.4	111.4	69.3	60.0	50.6
100°	612.5	671.1	698.9	655.2	513.1	327.3	184.1	110.2	77.3	68.8	60.2
102.5°	744.9	765.4	737.0	631.3	459.1	289.8	174.4	115.3	86.9	78.7	70.5
105°	814.3	789.3	711.4	575.0	412.0	268.2	173.3	122.7	97.7	89.8	81.8
107.5°	822.2	762.0	659.1	521.6	376.7	256.8	177.3	133.0	108.5	101.4	94.3
110°	788.1	708.0	600.0	477.3	353.4	252.3	183.5	144.3	121.0	113.6	106.3

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	735.8	654.6	553.4	444.3	339.8	252.3	191.5	155.1	133.0	125.9	118.8
115°	681.9	604.0	515.9	422.2	330.7	254.0	199.4	166.5	145.5	138.4	131.3
117.5°	635.8	567.7	489.8	407.4	325.6	256.8	208.5	177.9	158.0	151.2	144.3
120°	600.0	537.5	469.4	395.5	322.2	261.4	217.6	190.4	170.5	163.4	156.3
122.5°	569.9	515.9	454.0	385.3	319.3	265.4	227.9	202.3	182.4	175.3	168.2
125°	546.6	497.2	439.2	376.2	317.1	269.9	236.9	212.5	193.8	186.4	179.0
127.5°	525.6	479.0	423.9	367.6	315.9	275.0	245.5	222.7	204.6	197.2	189.8
130°	504.0	459.7	409.7	359.1	314.8	279.6	254.0	232.4	214.8	207.4	200.0
132.5°	480.7	441.5	395.5	352.3	314.8	284.7	261.4	241.5	223.9	216.5	209.1
135°	459.1	422.8	383.5	347.2	314.8	289.2	268.2	249.4	231.8	224.2	216.5
137.5°	437.0	405.7	372.8	342.1	315.4	293.8	273.3	255.1	239.2	231.2	223.3
140°	417.1	390.9	364.2	338.7	315.9	296.6	278.4	261.4	244.9	237.2	229.6
142.5°	400.0	378.4	356.8	335.8	316.5	298.3	281.3	265.4	250.0	242.9	235.8
145°	385.8	368.2	350.6	333.0	315.9	299.5	284.1	269.9	255.1	248.6	242.1
147.5°	373.3	359.1	344.3	330.1	314.8	300.0	285.8	272.7	259.7	253.7	247.7
150°	362.5	351.7	339.2	326.7	313.1	300.0	287.5	275.6	263.1	258.2	253.4
152.5°	354.0	344.3	333.5	322.7	310.8	299.5	288.7	278.4	267.1	262.8	258.5
155°	344.9	337.0	327.9	318.2	308.0	298.3	289.2	280.1	270.5	266.5	262.5
157.5°	336.4	330.1	322.2	314.2	305.1	297.2	289.8	281.8	273.3	270.2	267.1
160°	327.9	322.2	316.5	309.1	302.3	295.5	289.8	283.0	275.6	273.0	270.5
162.5°	319.9	315.4	310.2	304.6	298.9	293.8	289.2	284.1	277.9	275.9	273.9
165°	312.0	308.5	304.6	300.0	295.5	292.1	288.7	284.1	279.6	277.9	276.2
167.5°	304.6	301.7	298.9	295.5	292.1	289.2	287.5	284.1	280.1	279.0	277.9
170°	297.7	296.0	294.3	291.5	289.2	287.5	286.4	284.1	281.3	280.5	279.6
172.5°	292.1	290.9	289.2	287.5	285.8	285.2	285.2	283.5	281.3	281.0	280.7
175°	287.0	285.8	285.8	284.1	283.5	283.5	284.1	283.0	281.3	281.3	281.3
177.5°	283.5	283.5	283.0	282.4	281.8	281.8	283.0	282.4	281.3	281.3	281.3
180°	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8	281.8

TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1625.0	1625.0	1625.0	1625.0
2.5°	1587.6	1599.6	1611.6	1626.3
5°	1555.6	1577.0	1599.6	1621.0
7.5°	1520.9	1551.6	1581.0	1611.6
10°	1482.2	1520.9	1554.3	1597.0
12.5°	1439.5	1480.9	1527.6	1575.6
15°	1396.8	1448.9	1498.2	1552.9
17.5°	1356.8	1406.2	1460.9	1526.3
20°	1308.8	1363.5	1424.9	1494.2
22.5°	1258.1	1318.1	1384.8	1459.6
25°	1215.4	1276.8	1340.8	1419.5
27.5°	1168.7	1232.7	1295.5	1379.5
30°	1115.3	1184.7	1248.8	1335.5
32.5°	1064.6	1134.0	1204.7	1286.1
35°	1015.3	1083.3	1154.0	1236.7
37.5°	968.6	1030.0	1099.3	1174.0
40°	924.6	980.6	1042.0	1110.0
42.5°	868.5	933.9	991.3	1040.6
45°	820.5	873.9	927.2	967.3
47.5°	764.5	817.8	863.2	895.2
50°	717.8	760.5	797.8	825.8
52.5°	661.7	701.8	732.4	753.8
55°	607.0	641.7	668.4	683.1
57.5°	557.7	580.4	600.4	613.7
60°	503.0	520.3	537.7	552.3
62.5°	444.3	462.9	472.3	488.3
65°	392.2	404.2	418.9	424.3
67.5°	341.5	348.2	357.5	368.2
70°	288.2	292.2	301.5	316.2
72.5°	241.5	245.5	252.2	257.5
75°	192.1	196.1	201.5	206.8
77.5°	150.8	152.1	154.8	160.1
80°	109.4	113.4	116.1	117.4
82.5°	76.0	77.4	77.4	78.7
85°	48.0	45.4	45.4	46.7
87.5°	17.3	20.0	20.0	22.7
90°	3.4	2.3	1.1	0.6
92.5°	24.4	15.9	10.2	8.5
95°	30.1	23.9	19.3	18.8
97.5°	39.2	33.0	29.5	29.0
100°	49.4	43.2	40.9	39.8
102.5°	60.8	54.0	52.3	51.7
105°	72.7	67.1	64.2	64.2
107.5°	84.7	80.1	77.3	76.1
110°	97.7	92.6	90.3	89.2



TEST NUMBER: P1028524

CATALOG NUMBER: S125RDIP-B1090D610UB40-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	110.2	105.1	103.4	102.3
115°	122.7	117.6	115.9	114.8
117.5°	134.7	129.6	127.8	126.1
120°	146.6	141.5	139.2	137.5
122.5°	157.4	152.3	150.6	149.4
125°	168.2	163.1	160.2	159.1
127.5°	178.4	172.2	168.8	167.1
130°	188.1	180.7	176.1	174.4
132.5°	196.6	188.1	182.4	180.1
135°	204.6	195.5	188.6	186.4
137.5°	211.4	202.3	196.0	194.3
140°	218.8	209.7	202.9	201.2
142.5°	225.6	216.5	210.2	209.1
145°	231.8	223.9	218.2	217.1
147.5°	238.7	231.3	226.2	225.6
150°	245.5	238.1	234.1	233.0
152.5°	251.2	244.9	241.5	240.9
155°	256.8	251.2	247.7	247.7
157.5°	262.0	256.8	254.0	254.0
160°	265.9	262.0	259.7	260.2
162.5°	270.5	267.1	264.8	265.4
165°	273.9	271.0	269.3	270.5
167.5°	276.2	274.5	273.3	273.9
170°	278.4	277.3	276.7	277.3
172.5°	280.1	279.0	278.4	279.6
175°	281.3	280.7	280.1	281.3
177.5°	281.8	281.3	281.3	282.4
180°	281.8	281.8	281.8	281.8

(END OF REPORT)