

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028536

Luminaire Tested: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028536
REPORT IS A COMBINATION OF REPORTS P1005081 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7020.0 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65
1	101	96	93	89	94	90	87	84	79	76	74	68	66	65	58	57	56
2	92	85	79	74	86	79	74	70	70	66	62	60	57	55	52	50	48
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	42	39	36
5	71	59	51	45	66	56	49	43	50	44	39	43	39	35	38	34	32
6	66	54	45	40	61	50	43	38	45	39	35	39	35	31	34	31	28
7	61	48	41	35	57	46	39	33	41	35	31	36	31	28	31	28	25
8	56	44	36	31	53	42	35	30	37	31	27	33	28	25	29	25	22
9	53	40	33	28	49	38	31	27	34	28	24	30	26	22	27	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10382	10382	10382	10382
5°	10373	11701	10373	8994
10°	10315	13149	10280	7775
15°	10203	13911	10133	6769
20°	10068	15017	9978	6118
25°	9891	16997	9780	5553
30°	9712	18067	9566	5149
35°	9480	14858	9347	4771
40°	9067	10090	8991	4433
45°	8526	7253	8515	4099
50°	7971	5578	8010	3791
55°	7346	4536	7332	3494
60°	6765	3717	6732	3102
65°	6087	3097	6125	2497
70°	5527	2486	5504	2079
75°	4669	1884	4669	1709
80°	3784	1149	3739	1149
85°	2664	604	2584	683

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 14778 cd/sqm

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.4	2.2
10°-20°	455.5	6.5
20°-30°	722.3	10.3
30°-40°	872.8	12.4
40°-50°	777.1	11.1
50°-60°	595.9	8.5
60°-70°	387.0	5.5
70°-80°	187.8	2.7
80°-90°	45.7	0.7
90°-100°	273.2	3.9
100°-110°	589.0	8.4
110°-120°	549.2	7.8
120°-130°	444.8	6.3
130°-140°	357.1	5.1
140°-150°	269.4	3.8
150°-160°	189.7	2.7
160°-170°	111.8	1.6
170°-180°	36.4	0.5
0°-30°	1333.2	19.0
0°-40°	2206.0	31.4
0°-60°	3579.0	51.0
0°-90°	4199.5	59.8
90°-120°	1411.4	20.1
90°-150°	2482.7	35.4
90°-180°	2821.0	40.2
0°-180°	7020.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1620	1620	1620	1620	1620	
5°	1616	1857	1616	1428	1616	154
15°	1548	2231	1538	1086	1548	437
25°	1416	2671	1400	873	1416	652
35°	1233	2216	1216	712	1233	768
45°	964	991	963	560	964	744
55°	681	544	680	419	681	610
65°	423	309	426	249	423	423
75°	206	144	206	130	206	221
85°	47	31	45	35	47	53
90°	1	17	1	17	1	5
95°	25	178	25	178	25	26
105°	86	1003	86	1003	86	90
115°	153	1118	153	1118	153	151
125°	212	880	212	880	212	188
135°	248	731	248	731	248	193
145°	289	577	289	577	289	181
155°	330	484	330	484	330	152
165°	360	424	360	424	360	102
175°	375	381	375	381	375	36
180°	376	376	376	376	376	

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1621.7	1635.0	1639.0	1649.6	1661.6	1664.3	1670.9	1680.2	1685.5	1684.2	1684.2
5°	1616.4	1639.0	1654.9	1673.6	1696.2	1705.5	1713.5	1733.4	1749.4	1758.7	1774.7
7.5°	1607.0	1640.3	1666.9	1694.9	1729.4	1745.4	1762.7	1790.6	1819.9	1838.5	1855.8
10°	1592.4	1635.0	1672.2	1713.5	1760.0	1784.0	1805.3	1847.8	1883.8	1907.7	1947.6
12.5°	1571.1	1624.3	1676.2	1730.8	1789.3	1814.6	1843.8	1890.4	1941.0	1975.6	2008.8
15°	1548.5	1612.4	1668.2	1733.4	1803.9	1842.5	1879.8	1929.0	1974.2	2012.8	2051.4
17.5°	1521.9	1589.8	1658.9	1733.4	1813.3	1851.8	1883.8	1942.3	1990.2	2028.8	2063.4
20°	1490.0	1565.8	1644.3	1726.8	1807.9	1843.8	1874.4	1938.3	1980.9	2022.1	2071.3
22.5°	1455.4	1537.9	1621.7	1702.8	1782.7	1821.2	1857.2	1913.0	1959.6	2015.5	2079.3
25°	1415.5	1505.9	1591.1	1672.2	1748.1	1784.0	1815.9	1877.1	1942.3	2012.8	2084.6
27.5°	1375.6	1463.4	1545.9	1620.4	1702.8	1736.1	1768.0	1845.2	1922.3	1996.8	2095.3
30°	1331.7	1420.8	1492.6	1561.8	1641.6	1676.2	1716.1	1803.9	1891.7	1992.8	2112.6
32.5°	1282.4	1363.6	1430.1	1502.0	1573.8	1616.4	1666.9	1762.7	1863.8	1984.9	2137.9
35°	1233.2	1298.4	1359.6	1427.5	1513.9	1559.2	1608.4	1709.5	1835.9	1980.9	2159.1
37.5°	1170.7	1233.2	1281.1	1350.3	1439.4	1492.6	1541.9	1658.9	1802.6	1971.6	2157.8
40°	1106.8	1160.1	1205.3	1277.1	1374.2	1423.5	1476.7	1604.4	1768.0	1945.0	2125.9
42.5°	1037.7	1082.9	1132.1	1201.3	1295.7	1343.6	1404.8	1553.8	1720.1	1907.7	2043.4
45°	964.5	1008.4	1049.6	1121.5	1215.9	1267.8	1334.3	1487.3	1661.6	1829.2	1910.4
47.5°	892.7	931.2	975.1	1037.7	1133.4	1190.7	1258.5	1422.1	1583.1	1724.1	1730.8
50°	823.5	854.1	891.3	955.2	1055.0	1109.5	1180.0	1333.0	1490.0	1587.1	1521.9
52.5°	751.6	779.6	818.2	874.0	967.2	1031.0	1092.2	1245.2	1376.9	1442.1	1322.4
55°	681.1	705.1	745.0	807.5	888.7	937.9	1000.4	1142.8	1258.5	1259.8	1129.5
57.5°	612.0	633.2	666.5	722.4	798.2	855.4	912.6	1036.3	1114.8	1092.2	947.2
60°	550.8	564.1	594.7	649.2	719.7	761.0	822.1	925.9	977.8	936.6	780.9
62.5°	486.9	500.2	524.2	568.1	634.6	678.5	717.1	802.2	838.1	775.6	647.9
65°	423.0	439.0	456.3	490.9	553.4	582.7	617.3	679.8	714.4	641.2	530.8
67.5°	367.2	375.2	392.4	428.4	472.3	498.9	522.8	565.4	572.0	513.5	423.0
70°	315.3	318.0	333.9	355.2	388.5	404.4	424.4	449.7	449.7	401.8	329.9
72.5°	256.8	260.7	272.7	295.3	315.3	323.3	329.9	345.9	343.2	299.3	250.1
75°	206.2	208.9	218.2	228.8	236.8	251.4	256.8	254.1	252.8	215.5	187.6
77.5°	159.6	161.0	167.6	176.9	178.3	183.6	179.6	179.6	167.6	146.3	131.7
80°	117.1	118.4	121.1	123.7	123.7	123.7	123.7	117.1	109.1	95.8	91.8
82.5°	78.5	78.5	79.8	82.5	81.2	78.5	75.8	69.2	63.9	59.9	57.2
85°	46.6	46.6	47.9	46.6	41.2	39.9	37.2	35.9	34.6	33.3	33.3
87.5°	22.6	21.3	18.6	16.0	16.0	16.0	16.0	16.0	16.0	14.6	14.6
90°	0.8	1.5	3.0	4.5	6.1	6.8	7.6	8.3	9.8	10.6	12.1
92.5°	11.4	13.6	21.2	32.6	48.5	62.1	75.7	127.2	213.5	307.4	302.1
95°	25.0	25.7	31.8	40.1	56.8	73.8	90.9	171.9	338.4	547.4	670.8
97.5°	38.6	39.4	43.9	52.2	67.4	79.9	92.4	148.4	276.3	502.0	724.5
100°	53.0	54.5	57.5	65.9	80.3	91.6	103.0	146.9	245.3	436.1	683.7
102.5°	68.9	69.7	71.9	81.0	93.9	104.8	115.8	153.7	232.4	386.1	611.7
105°	85.6	85.6	89.3	96.9	109.0	119.6	130.2	163.5	230.9	357.3	548.9
107.5°	101.5	103.0	106.8	112.8	125.7	135.2	144.6	177.2	236.2	342.2	502.0
110°	118.9	120.4	123.4	130.2	141.6	151.4	161.3	192.3	244.5	336.1	470.9



TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	136.3	137.8	140.1	146.9	158.2	167.7	177.2	206.7	255.1	336.1	452.7
115°	152.9	154.4	156.7	163.5	174.9	184.4	193.8	221.8	265.7	338.4	440.6
117.5°	168.1	170.3	172.6	179.4	192.3	201.4	210.5	237.0	277.9	342.2	433.8
120°	183.2	185.5	188.5	195.3	208.2	217.6	227.1	253.6	290.0	348.3	429.3
122.5°	199.1	200.6	202.9	209.7	224.1	233.6	243.0	269.5	303.6	353.6	425.5
125°	212.0	213.5	217.3	224.1	238.5	248.4	258.2	283.2	315.7	359.6	422.5
127.5°	222.6	224.9	229.4	237.7	252.9	262.8	272.6	296.8	327.1	366.4	420.9
130°	232.4	234.7	240.8	250.6	266.5	276.4	286.2	309.7	338.4	372.5	419.4
132.5°	240.0	243.0	250.6	262.0	278.6	288.5	298.3	321.8	348.3	379.3	419.4
135°	248.3	251.4	260.4	272.6	288.5	298.7	308.9	332.4	357.3	385.4	419.4
137.5°	258.9	261.2	269.5	281.6	297.5	308.1	318.7	339.9	364.2	391.4	420.2
140°	268.0	270.3	279.4	291.5	305.9	316.1	326.3	348.3	371.0	395.2	420.9
142.5°	278.6	280.1	288.5	300.6	314.2	323.6	333.1	353.6	374.8	397.5	421.7
145°	289.2	290.7	298.3	308.9	322.5	331.2	339.9	359.6	378.5	399.0	420.9
147.5°	300.6	301.3	308.1	318.0	330.1	338.0	346.0	363.4	380.8	399.7	419.4
150°	310.4	311.9	317.2	327.1	337.7	344.1	350.5	367.2	383.1	399.7	417.2
152.5°	321.0	321.8	326.3	334.6	344.5	350.2	355.8	371.0	384.6	399.0	414.1
155°	330.1	330.1	334.6	342.2	349.8	355.1	360.4	373.2	385.4	397.5	410.3
157.5°	338.4	338.4	342.2	349.0	355.8	360.0	364.2	375.5	386.1	396.0	406.6
160°	346.7	346.0	349.0	354.3	360.4	363.8	367.2	377.0	386.1	393.7	402.8
162.5°	353.6	352.8	355.8	360.4	364.9	367.5	370.2	378.5	385.4	391.4	398.2
165°	360.4	358.9	361.1	364.9	367.9	370.2	372.5	378.5	384.6	389.1	393.7
167.5°	364.9	364.2	365.7	367.9	370.2	371.7	373.2	378.5	383.1	385.4	389.1
170°	369.5	368.7	369.5	371.0	372.5	373.6	374.8	378.5	381.6	383.1	385.4
172.5°	372.5	371.0	371.7	373.2	374.0	374.4	374.8	377.8	380.1	380.1	380.8
175°	374.8	373.2	374.0	374.8	374.8	374.8	374.8	377.0	378.5	377.8	377.8
177.5°	376.3	374.8	374.8	375.5	374.8	374.8	374.8	376.3	377.0	375.5	375.5
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1690.9	1700.2	1708.2	1704.2	1720.1	1718.8	1721.5	1726.8	1728.1	1725.4	1720.1
5°	1782.7	1796.0	1818.6	1830.5	1827.9	1838.5	1843.8	1851.8	1859.8	1857.2	1857.2
7.5°	1885.1	1903.7	1926.3	1956.9	1960.9	1970.2	1986.2	1986.2	1995.5	1991.5	1990.2
10°	1974.2	1996.8	2032.8	2056.7	2067.3	2072.7	2088.6	2094.0	2104.6	2105.9	2105.9
12.5°	2047.4	2087.3	2111.2	2135.2	2140.5	2148.5	2160.5	2168.5	2172.4	2172.4	2168.5
15°	2086.0	2117.9	2145.8	2171.1	2185.7	2192.4	2204.4	2213.7	2219.0	2231.0	2233.6
17.5°	2101.9	2140.5	2185.7	2221.7	2246.9	2253.6	2277.5	2285.5	2296.2	2301.5	2308.1
20°	2124.6	2180.4	2235.0	2278.9	2302.8	2320.1	2345.4	2382.6	2393.3	2393.3	2389.3
22.5°	2144.5	2216.3	2290.8	2361.4	2381.3	2415.9	2462.5	2502.4	2518.3	2525.0	2519.7
25°	2168.5	2266.9	2364.0	2451.8	2506.4	2531.6	2594.2	2642.1	2660.7	2671.3	2674.0
27.5°	2209.7	2333.4	2457.1	2568.9	2624.8	2654.0	2719.2	2760.5	2783.1	2792.4	2785.7
30°	2256.3	2407.9	2551.6	2651.4	2688.6	2724.5	2767.1	2783.1	2777.7	2777.7	2797.7
32.5°	2304.1	2461.1	2588.8	2654.0	2667.3	2662.0	2644.7	2596.8	2568.9	2568.9	2586.2
35°	2330.8	2466.4	2531.6	2510.3	2458.5	2427.9	2333.4	2280.2	2220.3	2216.3	2236.3
37.5°	2316.1	2374.7	2348.0	2208.4	2137.9	2079.3	1931.7	1873.1	1829.2	1768.0	1862.5
40°	2213.7	2193.7	2055.4	1854.5	1776.0	1693.5	1576.5	1517.9	1456.7	1447.4	1470.0
42.5°	2040.7	1922.3	1720.1	1525.9	1446.1	1387.5	1298.4	1241.2	1202.6	1186.7	1213.3
45°	1825.2	1639.0	1436.8	1282.4	1194.6	1164.0	1082.9	1032.3	1003.1	991.1	1009.7
47.5°	1561.8	1374.2	1182.7	1052.3	1000.4	969.8	915.3	871.4	846.1	838.1	846.1
50°	1326.3	1133.4	972.5	888.7	842.1	816.8	771.6	743.7	723.7	718.4	731.7
52.5°	1122.8	947.2	824.8	750.3	719.7	698.4	666.5	642.6	630.6	625.3	634.6
55°	940.5	798.2	699.8	635.9	613.3	600.0	572.0	558.7	545.4	544.1	553.4
57.5°	779.6	681.1	590.7	545.4	538.8	518.8	494.9	482.9	476.3	474.9	478.9
60°	649.2	561.4	506.9	466.9	457.6	441.7	428.4	420.4	412.4	409.7	412.4
62.5°	540.1	470.9	427.0	400.4	387.1	383.1	368.5	359.2	357.9	357.9	360.5
65°	445.7	387.1	359.2	337.9	328.6	324.6	314.0	307.3	308.6	308.6	310.0
67.5°	363.2	320.6	295.3	284.7	276.7	275.4	264.7	262.1	259.4	259.4	262.1
70°	288.7	262.1	243.5	238.1	236.8	227.5	223.5	222.2	218.2	219.5	219.5
72.5°	226.2	208.9	198.2	190.2	191.6	186.2	180.9	180.9	178.3	182.3	182.3
75°	167.6	159.6	151.7	149.0	151.7	149.0	145.0	143.7	145.0	143.7	143.7
77.5°	123.7	119.7	117.1	115.7	115.7	110.4	107.8	110.4	105.1	107.8	107.8
80°	86.5	81.2	79.8	77.2	78.5	74.5	75.8	73.2	73.2	73.2	73.2
82.5°	54.5	53.2	53.2	53.2	51.9	51.9	51.9	51.9	51.9	51.9	50.6
85°	33.3	31.9	31.9	31.9	30.6	30.6	30.6	30.6	30.6	30.6	30.6
87.5°	13.3	14.6	14.6	16.0	14.6	13.3	13.3	13.3	14.6	14.6	13.3
90°	12.9	13.6	14.4	15.1	15.9	16.7	16.7	16.7	17.4	17.4	17.4
92.5°	243.8	164.3	118.1	87.8	80.6	73.4	61.3	59.1	57.5	56.0	57.5
95°	656.4	544.3	429.3	336.1	304.4	272.6	218.8	196.1	190.0	177.9	190.0
97.5°	819.9	780.6	689.0	595.1	549.6	504.2	458.8	419.4	399.0	389.9	399.0
100°	872.9	931.2	894.1	816.1	776.8	737.4	685.2	630.7	602.6	590.5	602.6
102.5°	841.1	981.9	1019.8	992.5	969.0	945.6	888.8	854.0	823.0	814.6	823.0
105°	766.2	947.9	1051.6	1084.9	1080.8	1076.6	1052.4	1027.4	1012.2	1003.1	1012.2
107.5°	695.0	878.2	1015.3	1095.5	1112.2	1128.8	1135.6	1131.9	1124.3	1116.7	1124.3
110°	636.0	799.5	943.3	1050.1	1082.2	1114.4	1148.5	1162.9	1168.2	1168.2	1168.2

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	592.0	737.4	872.2	980.4	1019.8	1059.2	1112.9	1140.2	1155.3	1162.1	1155.3
115°	562.5	687.4	804.8	908.5	949.8	991.0	1050.1	1086.4	1107.6	1117.5	1107.6
117.5°	542.8	652.6	756.3	847.2	886.2	925.2	985.0	1022.8	1044.0	1050.1	1044.0
120°	526.9	625.4	716.2	799.5	832.8	866.1	922.1	958.5	978.9	985.0	978.9
122.5°	513.3	604.9	687.4	759.4	790.0	820.7	869.1	901.7	922.1	927.4	922.1
125°	501.2	585.2	662.5	728.3	755.6	782.8	825.2	856.3	872.9	880.5	872.9
127.5°	489.8	564.8	638.2	700.3	726.0	751.8	790.4	818.4	834.3	837.3	834.3
130°	478.5	545.9	612.5	671.5	696.2	720.8	758.6	783.6	798.7	803.3	798.7
132.5°	469.4	526.9	588.3	640.5	664.0	687.4	725.3	750.3	763.9	769.2	763.9
135°	462.6	511.0	563.3	611.7	633.3	654.9	688.2	713.2	726.8	731.4	726.8
137.5°	455.8	496.7	540.6	582.2	601.2	620.1	650.3	673.8	686.7	692.0	686.7
140°	451.2	485.3	520.9	555.7	571.6	587.5	615.5	635.2	646.6	650.3	646.6
142.5°	447.4	475.5	504.2	533.0	546.2	559.5	582.2	598.1	608.7	611.7	608.7
145°	443.7	467.1	490.6	514.1	524.3	534.5	552.7	565.5	573.9	576.9	573.9
147.5°	439.9	458.8	478.5	497.4	505.4	513.3	528.5	539.0	544.3	545.9	544.3
150°	435.3	452.0	468.6	483.0	489.8	496.7	508.0	517.1	520.1	520.9	520.1
152.5°	430.0	444.4	458.8	471.7	476.6	481.5	490.6	497.4	500.4	501.2	500.4
155°	424.0	436.8	449.0	459.6	463.8	467.9	475.5	480.8	483.0	483.8	483.0
157.5°	418.7	429.3	439.9	448.2	451.6	455.0	461.1	465.6	467.9	467.9	467.9
160°	411.9	421.7	429.3	436.8	439.4	442.1	447.4	451.2	452.7	452.0	452.7
162.5°	405.8	413.4	420.2	426.2	428.5	430.8	434.6	437.6	437.6	437.6	437.6
165°	399.7	405.8	411.1	415.6	417.5	419.4	422.5	424.0	424.0	424.0	424.0
167.5°	393.7	398.2	402.0	405.8	407.3	408.8	410.3	411.9	411.1	411.1	411.1
170°	388.4	392.2	394.4	396.7	397.4	398.2	399.7	400.5	400.5	399.7	400.5
172.5°	383.1	385.4	387.6	389.1	389.5	389.9	389.9	391.4	389.9	389.1	389.9
175°	378.5	380.8	380.8	382.3	382.3	382.3	382.3	383.1	381.6	380.8	381.6
177.5°	376.3	377.0	377.8	377.8	377.8	377.8	377.0	377.8	375.5	375.5	375.5
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1726.8	1717.5	1721.5	1717.5	1713.5	1709.5	1700.2	1686.9	1676.2	1668.2	1666.9
5°	1859.8	1847.8	1839.9	1835.9	1827.9	1817.2	1799.9	1780.0	1756.0	1746.7	1728.1
7.5°	1982.2	1978.2	1959.6	1956.9	1951.6	1931.7	1902.4	1875.8	1845.2	1819.9	1796.0
10°	2097.9	2088.6	2075.3	2056.7	2054.0	2028.8	2000.8	1963.6	1923.7	1899.7	1857.2
12.5°	2169.8	2159.1	2144.5	2132.5	2125.9	2109.9	2071.3	2034.1	1998.2	1954.3	1917.0
15°	2221.7	2208.4	2181.8	2172.4	2164.5	2143.2	2115.2	2076.7	2028.8	1998.2	1945.0
17.5°	2292.2	2276.2	2249.6	2232.3	2217.7	2184.4	2144.5	2092.6	2047.4	2012.8	1964.9
20°	2373.3	2349.4	2314.8	2292.2	2270.9	2232.3	2176.4	2115.2	2050.1	2007.5	1958.3
22.5°	2507.7	2462.5	2407.9	2376.0	2346.7	2280.2	2213.7	2137.9	2064.7	2000.8	1941.0
25°	2638.1	2592.8	2525.0	2481.1	2435.9	2358.7	2270.9	2165.8	2072.7	1998.2	1919.7
27.5°	2759.1	2712.6	2650.0	2596.8	2552.9	2437.2	2321.4	2203.0	2084.6	1982.2	1902.4
30°	2787.1	2767.1	2719.2	2672.7	2632.7	2526.3	2391.9	2241.6	2099.3	1967.6	1878.4
32.5°	2618.1	2667.3	2679.3	2672.7	2647.4	2571.5	2447.8	2289.5	2120.6	1960.9	1838.5
35°	2266.9	2356.0	2447.8	2497.0	2521.0	2531.6	2458.5	2313.5	2135.2	1950.3	1811.9
37.5°	1879.8	1966.2	2111.2	2184.4	2265.6	2372.0	2401.3	2308.1	2128.5	1942.3	1769.4
40°	1544.5	1654.9	1774.7	1841.2	1911.7	2103.3	2248.3	2237.6	2107.3	1913.0	1736.1
42.5°	1257.2	1326.3	1431.4	1504.6	1591.1	1805.3	1999.5	2095.3	2043.4	1877.1	1693.5
45°	1048.3	1101.5	1176.0	1250.5	1303.7	1498.0	1728.1	1885.1	1934.3	1813.3	1628.3
47.5°	883.3	923.3	988.4	1035.0	1092.2	1245.2	1444.7	1665.6	1769.4	1722.8	1559.2
50°	757.0	788.9	840.8	870.0	920.6	1052.3	1204.0	1435.4	1592.4	1597.7	1467.4
52.5°	646.5	678.5	722.4	747.7	778.2	867.4	1020.4	1215.9	1396.9	1463.4	1362.3
55°	562.7	581.4	617.3	637.2	665.2	751.6	848.8	1015.0	1204.0	1313.0	1249.2
57.5°	485.6	505.5	528.1	544.1	564.1	633.2	721.0	846.1	1033.7	1152.1	1130.8
60°	423.0	435.0	456.3	468.3	486.9	532.1	593.3	718.4	867.4	979.1	991.1
62.5°	364.5	375.2	389.8	400.4	412.4	448.3	493.6	582.7	713.1	834.1	850.1
65°	314.0	323.3	331.3	340.6	349.9	372.5	411.1	480.3	581.4	694.4	729.0
67.5°	268.7	271.4	283.4	284.7	290.0	307.3	335.2	391.1	464.3	554.8	600.0
70°	224.8	230.1	232.8	236.8	242.1	254.1	276.7	306.0	360.5	433.7	476.3
72.5°	182.3	183.6	187.6	190.2	195.6	204.9	215.5	238.1	272.7	325.9	364.5
75°	145.0	146.3	149.0	150.3	154.3	157.0	162.3	178.3	202.2	234.1	262.1
77.5°	109.1	111.7	114.4	114.4	115.7	118.4	121.1	126.4	138.4	159.6	183.6
80°	74.5	75.8	75.8	77.2	75.8	79.8	83.8	90.5	95.8	102.4	114.4
82.5°	51.9	51.9	51.9	53.2	53.2	54.5	54.5	55.9	57.2	61.2	66.5
85°	31.9	31.9	33.3	30.6	31.9	33.3	33.3	31.9	33.3	34.6	35.9
87.5°	13.3	13.3	14.6	14.6	14.6	14.6	13.3	14.6	13.3	14.6	14.6
90°	16.7	16.7	16.7	15.9	15.1	14.4	13.6	12.9	12.1	10.6	9.8
92.5°	59.1	61.3	73.4	80.6	87.8	118.1	164.3	243.8	302.1	307.4	213.5
95°	196.1	218.8	272.6	304.4	336.1	429.3	544.3	656.4	670.8	547.4	338.4
97.5°	419.4	458.8	504.2	549.6	595.1	689.0	780.6	819.9	724.5	502.0	276.3
100°	630.7	685.2	737.4	776.8	816.1	894.1	931.2	872.9	683.7	436.1	245.3
102.5°	854.0	888.8	945.6	969.0	992.5	1019.8	981.9	841.1	611.7	386.1	232.4
105°	1027.4	1052.4	1076.6	1080.8	1084.9	1051.6	947.9	766.2	548.9	357.3	230.9
107.5°	1131.9	1135.6	1128.8	1112.2	1095.5	1015.3	878.2	695.0	502.0	342.2	236.2
110°	1162.9	1148.5	1114.4	1082.2	1050.1	943.3	799.5	636.0	470.9	336.1	244.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1140.2	1112.9	1059.2	1019.8	980.4	872.2	737.4	592.0	452.7	336.1	255.1
115°	1086.4	1050.1	991.0	949.8	908.5	804.8	687.4	562.5	440.6	338.4	265.7
117.5°	1022.8	985.0	925.2	886.2	847.2	756.3	652.6	542.8	433.8	342.2	277.9
120°	958.5	922.1	866.1	832.8	799.5	716.2	625.4	526.9	429.3	348.3	290.0
122.5°	901.7	869.1	820.7	790.0	759.4	687.4	604.9	513.3	425.5	353.6	303.6
125°	856.3	825.2	782.8	755.6	728.3	662.5	585.2	501.2	422.5	359.6	315.7
127.5°	818.4	790.4	751.8	726.0	700.3	638.2	564.8	489.8	420.9	366.4	327.1
130°	783.6	758.6	720.8	696.2	671.5	612.5	545.9	478.5	419.4	372.5	338.4
132.5°	750.3	725.3	687.4	664.0	640.5	588.3	526.9	469.4	419.4	379.3	348.3
135°	713.2	688.2	654.9	633.3	611.7	563.3	511.0	462.6	419.4	385.4	357.3
137.5°	673.8	650.3	620.1	601.2	582.2	540.6	496.7	455.8	420.2	391.4	364.2
140°	635.2	615.5	587.5	571.6	555.7	520.9	485.3	451.2	420.9	395.2	371.0
142.5°	598.1	582.2	559.5	546.2	533.0	504.2	475.5	447.4	421.7	397.5	374.8
145°	565.5	552.7	534.5	524.3	514.1	490.6	467.1	443.7	420.9	399.0	378.5
147.5°	539.0	528.5	513.3	505.4	497.4	478.5	458.8	439.9	419.4	399.7	380.8
150°	517.1	508.0	496.7	489.8	483.0	468.6	452.0	435.3	417.2	399.7	383.1
152.5°	497.4	490.6	481.5	476.6	471.7	458.8	444.4	430.0	414.1	399.0	384.6
155°	480.8	475.5	467.9	463.8	459.6	449.0	436.8	424.0	410.3	397.5	385.4
157.5°	465.6	461.1	455.0	451.6	448.2	439.9	429.3	418.7	406.6	396.0	386.1
160°	451.2	447.4	442.1	439.4	436.8	429.3	421.7	411.9	402.8	393.7	386.1
162.5°	437.6	434.6	430.8	428.5	426.2	420.2	413.4	405.8	398.2	391.4	385.4
165°	424.0	422.5	419.4	417.5	415.6	411.1	405.8	399.7	393.7	389.1	384.6
167.5°	411.9	410.3	408.8	407.3	405.8	402.0	398.2	393.7	389.1	385.4	383.1
170°	400.5	399.7	398.2	397.4	396.7	394.4	392.2	388.4	385.4	383.1	381.6
172.5°	391.4	389.9	389.9	389.5	389.1	387.6	385.4	383.1	380.8	380.1	380.1
175°	383.1	382.3	382.3	382.3	382.3	380.8	380.8	378.5	377.8	377.8	378.5
177.5°	377.8	377.0	377.8	377.8	377.8	377.8	377.0	376.3	375.5	375.5	377.0
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1662.9	1654.9	1649.6	1648.3	1640.3	1633.7	1625.7	1624.3	1620.4	1609.7	1603.1
5°	1714.8	1696.2	1692.2	1680.2	1660.3	1645.6	1627.0	1616.4	1604.4	1584.4	1568.5
7.5°	1768.0	1742.7	1724.1	1706.8	1678.9	1652.3	1625.7	1604.4	1583.1	1553.8	1529.9
10°	1819.9	1781.3	1758.7	1733.4	1694.9	1654.9	1617.7	1587.1	1552.5	1517.9	1483.3
12.5°	1867.8	1818.6	1785.3	1749.4	1701.5	1652.3	1604.4	1561.8	1525.9	1479.3	1440.8
15°	1897.1	1842.5	1809.3	1774.7	1702.8	1648.3	1592.4	1537.9	1490.0	1440.8	1404.8
17.5°	1914.4	1853.2	1815.9	1784.0	1710.8	1636.3	1564.5	1505.9	1454.1	1395.5	1347.6
20°	1906.4	1846.5	1811.9	1781.3	1696.2	1621.7	1544.5	1476.7	1411.5	1351.6	1301.1
22.5°	1889.1	1826.6	1788.0	1760.0	1684.2	1596.4	1511.3	1438.1	1370.2	1310.4	1253.2
25°	1851.8	1790.6	1757.4	1722.8	1648.3	1564.5	1478.0	1399.5	1327.7	1263.8	1200.0
27.5°	1818.6	1744.1	1709.5	1678.9	1600.4	1525.9	1440.8	1354.3	1281.1	1214.6	1150.7
30°	1780.0	1696.2	1658.9	1617.7	1547.2	1476.7	1391.5	1311.7	1235.9	1165.4	1104.2
32.5°	1738.8	1641.6	1599.1	1552.5	1480.7	1414.2	1342.3	1263.8	1188.0	1118.8	1055.0
35°	1685.5	1581.8	1532.6	1488.6	1414.2	1347.6	1281.1	1215.9	1140.1	1066.9	1005.7
37.5°	1635.0	1520.6	1468.7	1418.1	1339.7	1275.8	1221.3	1160.1	1086.9	1016.4	957.8
40°	1577.8	1446.1	1392.9	1346.3	1265.2	1194.6	1145.4	1097.5	1033.7	965.8	902.0
42.5°	1525.9	1376.9	1321.0	1273.1	1188.0	1121.5	1074.9	1035.0	979.1	916.6	851.4
45°	1454.1	1302.4	1245.2	1194.6	1108.2	1045.6	997.8	963.2	919.3	860.7	802.2
47.5°	1387.5	1230.6	1168.0	1106.8	1028.4	964.5	920.6	894.0	864.7	812.8	753.0
50°	1306.4	1148.1	1084.2	1033.7	944.5	890.0	846.1	827.5	800.9	751.6	703.7
52.5°	1218.6	1068.3	1008.4	947.2	864.7	811.5	772.9	751.6	730.4	694.4	649.2
55°	1116.2	979.1	923.3	868.7	786.2	737.0	702.4	679.8	667.8	634.6	601.3
57.5°	1017.7	888.7	836.8	786.2	714.4	658.5	635.9	615.9	598.7	574.7	546.8
60°	917.9	800.9	745.0	699.8	637.2	586.7	568.1	548.1	534.8	516.2	496.2
62.5°	803.5	703.7	661.2	618.6	565.4	525.5	504.2	488.2	470.9	459.0	441.7
65°	682.5	612.0	570.7	538.8	488.2	452.3	436.4	425.7	411.1	399.1	385.8
67.5°	569.4	513.5	496.2	461.6	423.0	391.1	379.1	365.8	353.9	347.2	335.2
70°	460.3	420.4	403.1	393.8	351.2	329.9	319.3	314.0	299.3	292.7	284.7
72.5°	356.5	341.9	329.9	318.0	290.0	276.7	264.7	259.4	248.8	243.5	240.8
75°	263.4	254.1	247.4	246.1	234.1	220.8	208.9	206.2	198.2	192.9	190.2
77.5°	184.9	182.3	180.9	182.3	174.3	166.3	163.6	161.0	151.7	150.3	150.3
80°	121.1	127.7	127.7	126.4	123.7	122.4	118.4	115.7	110.4	109.1	110.4
82.5°	74.5	78.5	79.8	82.5	81.2	79.8	77.2	75.8	77.2	74.5	75.8
85°	37.2	39.9	45.2	45.2	46.6	46.6	46.6	45.2	42.6	43.9	42.6
87.5°	14.6	16.0	16.0	16.0	14.6	18.6	20.0	20.0	20.0	17.3	17.3
90°	8.3	7.6	6.8	6.1	4.5	3.0	1.5	0.8	1.5	3.0	4.5
92.5°	127.2	75.7	62.1	48.5	32.6	21.2	13.6	11.4	13.6	21.2	32.6
95°	171.9	90.9	73.8	56.8	40.1	31.8	25.7	25.0	25.7	31.8	40.1
97.5°	148.4	92.4	79.9	67.4	52.2	43.9	39.4	38.6	39.4	43.9	52.2
100°	146.9	103.0	91.6	80.3	65.9	57.5	54.5	53.0	54.5	57.5	65.9
102.5°	153.7	115.8	104.8	93.9	81.0	71.9	69.7	68.9	69.7	71.9	81.0
105°	163.5	130.2	119.6	109.0	96.9	89.3	85.6	85.6	85.6	89.3	96.9
107.5°	177.2	144.6	135.2	125.7	112.8	106.8	103.0	101.5	103.0	106.8	112.8
110°	192.3	161.3	151.4	141.6	130.2	123.4	120.4	118.9	120.4	123.4	130.2

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	206.7	177.2	167.7	158.2	146.9	140.1	137.8	136.3	137.8	140.1	146.9
115°	221.8	193.8	184.4	174.9	163.5	156.7	154.4	152.9	154.4	156.7	163.5
117.5°	237.0	210.5	201.4	192.3	179.4	172.6	170.3	168.1	170.3	172.6	179.4
120°	253.6	227.1	217.6	208.2	195.3	188.5	185.5	183.2	185.5	188.5	195.3
122.5°	269.5	243.0	233.6	224.1	209.7	202.9	200.6	199.1	200.6	202.9	209.7
125°	283.2	258.2	248.4	238.5	224.1	217.3	213.5	212.0	213.5	217.3	224.1
127.5°	296.8	272.6	262.8	252.9	237.7	229.4	224.9	222.6	224.9	229.4	237.7
130°	309.7	286.2	276.4	266.5	250.6	240.8	234.7	232.4	234.7	240.8	250.6
132.5°	321.8	298.3	288.5	278.6	262.0	250.6	243.0	240.0	243.0	250.6	262.0
135°	332.4	308.9	298.7	288.5	272.6	260.4	251.4	248.3	251.4	260.4	272.6
137.5°	339.9	318.7	308.1	297.5	281.6	269.5	261.2	258.9	261.2	269.5	281.6
140°	348.3	326.3	316.1	305.9	291.5	279.4	270.3	268.0	270.3	279.4	291.5
142.5°	353.6	333.1	323.6	314.2	300.6	288.5	280.1	278.6	280.1	288.5	300.6
145°	359.6	339.9	331.2	322.5	308.9	298.3	290.7	289.2	290.7	298.3	308.9
147.5°	363.4	346.0	338.0	330.1	318.0	308.1	301.3	300.6	301.3	308.1	318.0
150°	367.2	350.5	344.1	337.7	327.1	317.2	311.9	310.4	311.9	317.2	327.1
152.5°	371.0	355.8	350.2	344.5	334.6	326.3	321.8	321.0	321.8	326.3	334.6
155°	373.2	360.4	355.1	349.8	342.2	334.6	330.1	330.1	330.1	334.6	342.2
157.5°	375.5	364.2	360.0	355.8	349.0	342.2	338.4	338.4	338.4	342.2	349.0
160°	377.0	367.2	363.8	360.4	354.3	349.0	346.0	346.7	346.0	349.0	354.3
162.5°	378.5	370.2	367.5	364.9	360.4	355.8	352.8	353.6	352.8	355.8	360.4
165°	378.5	372.5	370.2	367.9	364.9	361.1	358.9	360.4	358.9	361.1	364.9
167.5°	378.5	373.2	371.7	370.2	367.9	365.7	364.2	364.9	364.2	365.7	367.9
170°	378.5	374.8	373.6	372.5	371.0	369.5	368.7	369.5	368.7	369.5	371.0
172.5°	377.8	374.8	374.4	374.0	373.2	371.7	371.0	372.5	371.0	371.7	373.2
175°	377.0	374.8	374.8	374.8	374.8	374.0	373.2	374.8	373.2	374.0	374.8
177.5°	376.3	374.8	374.8	374.8	375.5	374.8	374.8	376.3	374.8	374.8	375.5
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1599.1	1593.7	1589.8	1585.8	1568.5	1549.8	1547.2	1543.2	1535.2	1544.5	1540.5
5°	1557.8	1545.9	1539.2	1521.9	1500.6	1484.7	1471.4	1455.4	1448.7	1443.4	1442.1
7.5°	1507.3	1496.6	1484.7	1467.4	1440.8	1414.2	1394.2	1378.2	1364.9	1358.3	1358.3
10°	1458.1	1444.7	1428.8	1399.5	1374.2	1341.0	1319.7	1303.7	1285.1	1274.5	1265.2
12.5°	1407.5	1392.9	1378.2	1341.0	1311.7	1277.1	1246.5	1226.6	1217.3	1205.3	1189.3
15°	1356.9	1334.3	1319.7	1282.4	1245.2	1210.6	1190.7	1169.4	1148.1	1136.1	1130.8
17.5°	1303.7	1287.8	1263.8	1223.9	1182.7	1152.1	1122.8	1102.9	1077.6	1065.6	1053.6
20°	1255.8	1231.9	1207.9	1168.0	1128.1	1086.9	1057.6	1033.7	1017.7	1008.4	997.8
22.5°	1198.6	1176.0	1156.1	1113.5	1069.6	1031.0	999.1	984.5	968.5	953.9	943.2
25°	1149.4	1126.8	1106.8	1060.3	1012.4	976.5	952.5	933.9	916.6	910.0	899.3
27.5°	1097.5	1076.2	1049.6	1003.1	960.5	929.9	904.6	887.3	874.0	860.7	852.7
30°	1048.3	1024.4	1000.4	949.9	915.3	884.7	860.7	839.4	828.8	822.1	808.8
32.5°	1000.4	969.8	949.9	903.3	870.0	840.8	820.8	802.2	788.9	776.9	766.3
35°	948.5	915.3	895.3	856.7	822.1	792.9	775.6	762.3	746.3	735.7	730.4
37.5°	899.3	871.4	851.4	811.5	776.9	753.0	734.3	717.1	710.4	695.8	693.1
40°	846.1	822.1	803.5	764.9	733.0	714.4	694.4	678.5	666.5	659.8	650.5
42.5°	798.2	778.2	758.3	722.4	691.8	669.2	654.5	639.9	629.3	618.6	612.0
45°	754.3	733.0	714.4	679.8	649.2	629.3	614.6	597.3	594.7	580.0	573.4
47.5°	707.7	689.1	673.2	637.2	609.3	589.3	572.0	560.1	548.1	542.8	533.5
50°	662.5	643.9	625.3	593.3	568.1	548.1	530.8	517.5	510.9	502.9	494.9
52.5°	613.3	598.7	584.0	550.8	525.5	508.2	493.6	476.3	469.6	463.0	457.6
55°	572.0	550.8	534.8	506.9	484.2	465.6	449.7	436.4	429.7	424.4	417.7
57.5°	516.2	502.9	489.6	464.3	443.0	424.4	408.4	397.8	389.8	385.8	387.1
60°	468.3	453.6	445.7	419.1	397.8	383.1	368.5	357.9	349.9	345.9	344.6
62.5°	417.7	407.1	392.4	373.8	352.5	339.2	328.6	320.6	307.3	306.0	302.0
65°	368.5	360.5	347.2	329.9	312.6	300.7	288.7	278.0	272.7	266.1	262.1
67.5°	320.6	312.6	300.7	286.0	274.0	262.1	251.4	240.8	231.5	226.2	223.5
70°	274.0	267.4	259.4	242.1	227.5	218.2	210.2	203.5	194.2	191.6	190.2
72.5°	228.8	222.2	218.2	203.5	190.2	182.3	174.3	167.6	163.6	162.3	158.3
75°	187.6	180.9	175.6	162.3	154.3	149.0	141.0	138.4	134.4	133.0	131.7
77.5°	146.3	139.7	138.4	129.0	119.7	117.1	114.4	109.1	109.1	109.1	106.4
80°	105.1	103.8	102.4	93.1	89.1	86.5	85.1	81.2	78.5	75.8	74.5
82.5°	70.5	69.2	67.8	63.9	59.9	58.5	57.2	54.5	54.5	55.9	53.2
85°	42.6	39.9	38.6	37.2	34.6	34.6	35.9	34.6	34.6	34.6	33.3
87.5°	16.0	16.0	16.0	16.0	17.3	14.6	16.0	16.0	14.6	14.6	13.3
90°	6.1	6.8	7.6	8.3	9.8	10.6	12.1	12.9	13.6	14.4	15.1
92.5°	48.5	62.1	75.7	127.2	213.5	307.4	302.1	243.8	164.3	118.1	87.8
95°	56.8	73.8	90.9	171.9	338.4	547.4	670.8	656.4	544.3	429.3	336.1
97.5°	67.4	79.9	92.4	148.4	276.3	502.0	724.5	819.9	780.6	689.0	595.1
100°	80.3	91.6	103.0	146.9	245.3	436.1	683.7	872.9	931.2	894.1	816.1
102.5°	93.9	104.8	115.8	153.7	232.4	386.1	611.7	841.1	981.9	1019.8	992.5
105°	109.0	119.6	130.2	163.5	230.9	357.3	548.9	766.2	947.9	1051.6	1084.9
107.5°	125.7	135.2	144.6	177.2	236.2	342.2	502.0	695.0	878.2	1015.3	1095.5
110°	141.6	151.4	161.3	192.3	244.5	336.1	470.9	636.0	799.5	943.3	1050.1

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	158.2	167.7	177.2	206.7	255.1	336.1	452.7	592.0	737.4	872.2	980.4
115°	174.9	184.4	193.8	221.8	265.7	338.4	440.6	562.5	687.4	804.8	908.5
117.5°	192.3	201.4	210.5	237.0	277.9	342.2	433.8	542.8	652.6	756.3	847.2
120°	208.2	217.6	227.1	253.6	290.0	348.3	429.3	526.9	625.4	716.2	799.5
122.5°	224.1	233.6	243.0	269.5	303.6	353.6	425.5	513.3	604.9	687.4	759.4
125°	238.5	248.4	258.2	283.2	315.7	359.6	422.5	501.2	585.2	662.5	728.3
127.5°	252.9	262.8	272.6	296.8	327.1	366.4	420.9	489.8	564.8	638.2	700.3
130°	266.5	276.4	286.2	309.7	338.4	372.5	419.4	478.5	545.9	612.5	671.5
132.5°	278.6	288.5	298.3	321.8	348.3	379.3	419.4	469.4	526.9	588.3	640.5
135°	288.5	298.7	308.9	332.4	357.3	385.4	419.4	462.6	511.0	563.3	611.7
137.5°	297.5	308.1	318.7	339.9	364.2	391.4	420.2	455.8	496.7	540.6	582.2
140°	305.9	316.1	326.3	348.3	371.0	395.2	420.9	451.2	485.3	520.9	555.7
142.5°	314.2	323.6	333.1	353.6	374.8	397.5	421.7	447.4	475.5	504.2	533.0
145°	322.5	331.2	339.9	359.6	378.5	399.0	420.9	443.7	467.1	490.6	514.1
147.5°	330.1	338.0	346.0	363.4	380.8	399.7	419.4	439.9	458.8	478.5	497.4
150°	337.7	344.1	350.5	367.2	383.1	399.7	417.2	435.3	452.0	468.6	483.0
152.5°	344.5	350.2	355.8	371.0	384.6	399.0	414.1	430.0	444.4	458.8	471.7
155°	349.8	355.1	360.4	373.2	385.4	397.5	410.3	424.0	436.8	449.0	459.6
157.5°	355.8	360.0	364.2	375.5	386.1	396.0	406.6	418.7	429.3	439.9	448.2
160°	360.4	363.8	367.2	377.0	386.1	393.7	402.8	411.9	421.7	429.3	436.8
162.5°	364.9	367.5	370.2	378.5	385.4	391.4	398.2	405.8	413.4	420.2	426.2
165°	367.9	370.2	372.5	378.5	384.6	389.1	393.7	399.7	405.8	411.1	415.6
167.5°	370.2	371.7	373.2	378.5	383.1	385.4	389.1	393.7	398.2	402.0	405.8
170°	372.5	373.6	374.8	378.5	381.6	383.1	385.4	388.4	392.2	394.4	396.7
172.5°	374.0	374.4	374.8	377.8	380.1	380.1	380.8	383.1	385.4	387.6	389.1
175°	374.8	374.8	374.8	377.0	378.5	377.8	377.8	378.5	380.8	380.8	382.3
177.5°	374.8	374.8	374.8	376.3	377.0	375.5	375.5	376.3	377.0	377.8	377.8
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1533.9	1536.5	1529.9	1527.2	1521.9	1528.6	1529.9	1528.6	1540.5	1535.2	1537.9
5°	1444.7	1439.4	1435.4	1426.1	1426.1	1427.5	1431.4	1424.8	1428.8	1438.1	1436.8
7.5°	1346.3	1343.6	1345.0	1334.3	1326.3	1329.0	1326.3	1338.3	1345.0	1342.3	1347.6
10°	1257.2	1262.5	1250.5	1245.2	1239.9	1245.2	1243.9	1246.5	1254.5	1259.8	1269.1
12.5°	1185.3	1184.0	1177.3	1172.0	1162.7	1165.4	1173.4	1170.7	1172.0	1184.0	1182.7
15°	1117.5	1109.5	1104.2	1092.2	1094.9	1085.6	1093.5	1102.9	1106.8	1117.5	1124.1
17.5°	1049.6	1048.3	1041.7	1040.3	1025.7	1021.7	1029.7	1032.3	1036.3	1041.7	1051.0
20°	992.4	991.1	981.8	979.1	967.2	975.1	972.5	977.8	980.5	991.1	995.1
22.5°	940.5	933.9	931.2	927.2	923.3	921.9	927.2	925.9	935.2	939.2	940.5
25°	892.7	887.3	886.0	879.4	876.7	872.7	876.7	880.7	891.3	895.3	900.6
27.5°	848.8	844.8	842.1	836.8	832.8	832.8	835.5	840.8	844.8	847.4	850.1
30°	808.8	806.2	798.2	795.5	791.6	791.6	791.6	794.2	800.9	808.8	812.8
32.5°	767.6	762.3	757.0	757.0	753.0	753.0	754.3	757.0	763.6	764.9	771.6
35°	727.7	722.4	718.4	715.7	717.1	711.7	714.4	718.4	726.4	729.0	733.0
37.5°	689.1	687.8	679.8	675.8	678.5	678.5	677.1	679.8	685.1	690.4	693.1
40°	646.5	643.9	643.9	639.9	641.2	635.9	639.9	642.6	645.2	650.5	654.5
42.5°	609.3	606.6	601.3	602.6	598.7	598.7	601.3	602.6	606.6	613.3	615.9
45°	569.4	569.4	566.7	562.7	564.1	560.1	562.7	564.1	569.4	576.0	573.4
47.5°	530.8	529.5	529.5	524.2	526.8	522.8	526.8	528.1	530.8	534.8	533.5
50°	493.6	489.6	490.9	489.6	488.2	488.2	490.9	490.9	493.6	493.6	497.5
52.5°	455.0	455.0	452.3	453.6	456.3	453.6	457.6	453.6	456.3	457.6	460.3
55°	420.4	417.7	419.1	417.7	423.0	419.1	423.0	420.4	423.0	421.7	424.4
57.5°	383.1	379.1	380.5	379.1	383.1	381.8	385.8	381.8	383.1	384.5	388.5
60°	340.6	340.6	340.6	337.9	341.9	341.9	340.6	340.6	345.9	348.5	347.2
62.5°	300.7	299.3	295.3	294.0	295.3	292.7	298.0	296.7	299.3	302.0	304.6
65°	256.8	254.1	252.8	250.1	250.1	248.8	250.1	255.4	256.8	258.1	264.7
67.5°	220.8	219.5	218.2	214.2	214.2	216.8	216.8	216.8	224.8	220.8	226.2
70°	188.9	186.2	183.6	182.3	182.3	183.6	184.9	186.2	184.9	190.2	191.6
72.5°	158.3	159.6	157.0	157.0	157.0	155.6	155.6	158.3	159.6	158.3	159.6
75°	131.7	131.7	130.4	131.7	131.7	130.4	130.4	133.0	133.0	131.7	135.7
77.5°	106.4	105.1	102.4	99.8	101.1	99.8	101.1	99.8	103.8	107.8	105.1
80°	74.5	73.2	73.2	73.2	74.5	73.2	75.8	73.2	74.5	74.5	75.8
82.5°	53.2	54.5	54.5	53.2	54.5	53.2	54.5	54.5	54.5	53.2	54.5
85°	34.6	34.6	34.6	34.6	33.3	34.6	34.6	34.6	35.9	34.6	35.9
87.5°	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	16.0	14.6	16.0
90°	15.9	16.7	16.7	16.7	17.4	17.4	17.4	16.7	16.7	16.7	15.9
92.5°	80.6	73.4	61.3	59.1	57.5	56.0	57.5	59.1	61.3	73.4	80.6
95°	304.4	272.6	218.8	196.1	190.0	177.9	190.0	196.1	218.8	272.6	304.4
97.5°	549.6	504.2	458.8	419.4	399.0	389.9	399.0	419.4	458.8	504.2	549.6
100°	776.8	737.4	685.2	630.7	602.6	590.5	602.6	630.7	685.2	737.4	776.8
102.5°	969.0	945.6	888.8	854.0	823.0	814.6	823.0	854.0	888.8	945.6	969.0
105°	1080.8	1076.6	1052.4	1027.4	1012.2	1003.1	1012.2	1027.4	1052.4	1076.6	1080.8
107.5°	1112.2	1128.8	1135.6	1131.9	1124.3	1116.7	1124.3	1131.9	1135.6	1128.8	1112.2
110°	1082.2	1114.4	1148.5	1162.9	1168.2	1168.2	1168.2	1162.9	1148.5	1114.4	1082.2

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1019.8	1059.2	1112.9	1140.2	1155.3	1162.1	1155.3	1140.2	1112.9	1059.2	1019.8
115°	949.8	991.0	1050.1	1086.4	1107.6	1117.5	1107.6	1086.4	1050.1	991.0	949.8
117.5°	886.2	925.2	985.0	1022.8	1044.0	1050.1	1044.0	1022.8	985.0	925.2	886.2
120°	832.8	866.1	922.1	958.5	978.9	985.0	978.9	958.5	922.1	866.1	832.8
122.5°	790.0	820.7	869.1	901.7	922.1	927.4	922.1	901.7	869.1	820.7	790.0
125°	755.6	782.8	825.2	856.3	872.9	880.5	872.9	856.3	825.2	782.8	755.6
127.5°	726.0	751.8	790.4	818.4	834.3	837.3	834.3	818.4	790.4	751.8	726.0
130°	696.2	720.8	758.6	783.6	798.7	803.3	798.7	783.6	758.6	720.8	696.2
132.5°	664.0	687.4	725.3	750.3	763.9	769.2	763.9	750.3	725.3	687.4	664.0
135°	633.3	654.9	688.2	713.2	726.8	731.4	726.8	713.2	688.2	654.9	633.3
137.5°	601.2	620.1	650.3	673.8	686.7	692.0	686.7	673.8	650.3	620.1	601.2
140°	571.6	587.5	615.5	635.2	646.6	650.3	646.6	635.2	615.5	587.5	571.6
142.5°	546.2	559.5	582.2	598.1	608.7	611.7	608.7	598.1	582.2	559.5	546.2
145°	524.3	534.5	552.7	565.5	573.9	576.9	573.9	565.5	552.7	534.5	524.3
147.5°	505.4	513.3	528.5	539.0	544.3	545.9	544.3	539.0	528.5	513.3	505.4
150°	489.8	496.7	508.0	517.1	520.1	520.9	520.1	517.1	508.0	496.7	489.8
152.5°	476.6	481.5	490.6	497.4	500.4	501.2	500.4	497.4	490.6	481.5	476.6
155°	463.8	467.9	475.5	480.8	483.0	483.8	483.0	480.8	475.5	467.9	463.8
157.5°	451.6	455.0	461.1	465.6	467.9	467.9	467.9	465.6	461.1	455.0	451.6
160°	439.4	442.1	447.4	451.2	452.7	452.0	452.7	451.2	447.4	442.1	439.4
162.5°	428.5	430.8	434.6	437.6	437.6	437.6	437.6	437.6	434.6	430.8	428.5
165°	417.5	419.4	422.5	424.0	424.0	424.0	424.0	424.0	422.5	419.4	417.5
167.5°	407.3	408.8	410.3	411.9	411.1	411.1	411.1	411.9	410.3	408.8	407.3
170°	397.4	398.2	399.7	400.5	400.5	399.7	400.5	400.5	399.7	398.2	397.4
172.5°	389.5	389.9	389.9	391.4	389.9	389.1	389.9	391.4	389.9	389.9	389.5
175°	382.3	382.3	382.3	383.1	381.6	380.8	381.6	383.1	382.3	382.3	382.3
177.5°	377.8	377.8	377.0	377.8	375.5	375.5	375.5	377.8	377.0	377.8	377.8
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4	1620.4
2.5°	1532.6	1539.2	1533.9	1529.9	1540.5	1545.9	1545.9	1555.2	1564.5	1572.5	1573.8
5°	1438.1	1448.7	1451.4	1450.1	1466.0	1474.0	1491.3	1500.6	1513.9	1523.2	1533.9
7.5°	1351.6	1366.3	1367.6	1370.2	1394.2	1407.5	1422.1	1446.1	1464.7	1478.0	1490.0
10°	1265.2	1274.5	1283.8	1295.7	1319.7	1342.3	1363.6	1388.9	1412.8	1426.1	1443.4
12.5°	1200.0	1206.6	1217.3	1225.2	1250.5	1270.5	1298.4	1333.0	1367.6	1378.2	1399.5
15°	1132.1	1136.1	1157.4	1165.4	1186.7	1219.9	1237.2	1270.5	1307.7	1327.7	1351.6
17.5°	1053.6	1077.6	1090.9	1100.2	1126.8	1153.4	1181.3	1215.9	1263.8	1282.4	1299.7
20°	997.8	1015.0	1029.7	1041.7	1065.6	1105.5	1130.8	1158.7	1204.0	1225.2	1250.5
22.5°	948.5	963.2	976.5	989.8	1005.7	1041.7	1070.9	1109.5	1154.7	1174.7	1204.0
25°	902.0	916.6	924.6	940.5	961.8	987.1	1021.7	1056.3	1101.5	1124.1	1152.1
27.5°	856.7	871.4	886.0	899.3	913.9	937.9	961.8	1005.7	1052.3	1078.9	1102.9
30°	818.2	824.8	838.1	852.7	867.4	890.0	917.9	948.5	1001.7	1025.7	1055.0
32.5°	775.6	787.6	796.9	807.5	826.1	844.8	870.0	908.6	951.2	973.8	1005.7
35°	735.7	746.3	753.0	771.6	783.6	803.5	828.8	863.4	899.3	924.6	952.5
37.5°	697.1	707.7	715.7	726.4	742.3	759.6	786.2	811.5	854.1	875.4	907.3
40°	657.2	666.5	675.8	687.8	702.4	723.7	739.7	771.6	806.2	830.1	854.1
42.5°	618.6	623.9	634.6	647.9	662.5	681.1	703.7	729.0	763.6	784.9	806.2
45°	577.4	586.7	598.7	608.0	621.3	639.9	659.8	682.5	717.1	738.3	761.0
47.5°	538.8	545.4	553.4	568.1	585.3	598.7	619.9	641.2	673.2	693.1	714.4
50°	498.9	505.5	517.5	526.8	540.1	557.4	577.4	600.0	630.6	643.9	665.2
52.5°	461.6	464.3	476.3	485.6	498.9	518.8	534.8	554.8	584.0	598.7	619.9
55°	424.4	427.0	433.7	443.0	457.6	473.6	490.9	513.5	538.8	552.1	572.0
57.5°	385.8	388.5	395.1	401.8	416.4	431.0	451.0	469.6	494.9	506.9	525.5
60°	347.2	347.2	353.9	363.2	373.8	387.1	404.4	427.0	445.7	460.3	473.6
62.5°	306.0	310.0	314.0	320.6	332.6	348.5	363.2	379.1	401.8	412.4	424.4
65°	264.7	268.7	276.7	283.4	292.7	303.3	321.9	335.2	352.5	364.5	375.2
67.5°	228.8	232.8	238.1	246.1	252.8	264.7	278.0	291.3	310.0	318.0	325.9
70°	191.6	195.6	199.6	210.2	216.8	226.2	235.5	248.8	264.7	270.1	276.7
72.5°	162.3	163.6	169.0	171.6	180.9	188.9	199.6	207.5	219.5	226.2	231.5
75°	137.0	137.0	138.4	141.0	146.3	151.7	159.6	167.6	178.3	182.3	188.9
77.5°	107.8	111.7	110.4	113.1	115.7	118.4	125.1	130.4	141.0	143.7	146.3
80°	77.2	78.5	82.5	86.5	86.5	90.5	94.5	95.8	102.4	106.4	106.4
82.5°	55.9	57.2	55.9	57.2	58.5	59.9	63.9	69.2	69.2	70.5	73.2
85°	34.6	34.6	35.9	37.2	37.2	35.9	38.6	37.2	38.6	41.2	41.2
87.5°	17.3	16.0	16.0	16.0	16.0	16.0	17.3	16.0	17.3	17.3	17.3
90°	15.1	14.4	13.6	12.9	12.1	10.6	9.8	8.3	7.6	6.8	6.1
92.5°	87.8	118.1	164.3	243.8	302.1	307.4	213.5	127.2	75.7	62.1	48.5
95°	336.1	429.3	544.3	656.4	670.8	547.4	338.4	171.9	90.9	73.8	56.8
97.5°	595.1	689.0	780.6	819.9	724.5	502.0	276.3	148.4	92.4	79.9	67.4
100°	816.1	894.1	931.2	872.9	683.7	436.1	245.3	146.9	103.0	91.6	80.3
102.5°	992.5	1019.8	981.9	841.1	611.7	386.1	232.4	153.7	115.8	104.8	93.9
105°	1084.9	1051.6	947.9	766.2	548.9	357.3	230.9	163.5	130.2	119.6	109.0
107.5°	1095.5	1015.3	878.2	695.0	502.0	342.2	236.2	177.2	144.6	135.2	125.7
110°	1050.1	943.3	799.5	636.0	470.9	336.1	244.5	192.3	161.3	151.4	141.6

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	980.4	872.2	737.4	592.0	452.7	336.1	255.1	206.7	177.2	167.7	158.2
115°	908.5	804.8	687.4	562.5	440.6	338.4	265.7	221.8	193.8	184.4	174.9
117.5°	847.2	756.3	652.6	542.8	433.8	342.2	277.9	237.0	210.5	201.4	192.3
120°	799.5	716.2	625.4	526.9	429.3	348.3	290.0	253.6	227.1	217.6	208.2
122.5°	759.4	687.4	604.9	513.3	425.5	353.6	303.6	269.5	243.0	233.6	224.1
125°	728.3	662.5	585.2	501.2	422.5	359.6	315.7	283.2	258.2	248.4	238.5
127.5°	700.3	638.2	564.8	489.8	420.9	366.4	327.1	296.8	272.6	262.8	252.9
130°	671.5	612.5	545.9	478.5	419.4	372.5	338.4	309.7	286.2	276.4	266.5
132.5°	640.5	588.3	526.9	469.4	419.4	379.3	348.3	321.8	298.3	288.5	278.6
135°	611.7	563.3	511.0	462.6	419.4	385.4	357.3	332.4	308.9	298.7	288.5
137.5°	582.2	540.6	496.7	455.8	420.2	391.4	364.2	339.9	318.7	308.1	297.5
140°	555.7	520.9	485.3	451.2	420.9	395.2	371.0	348.3	326.3	316.1	305.9
142.5°	533.0	504.2	475.5	447.4	421.7	397.5	374.8	353.6	333.1	323.6	314.2
145°	514.1	490.6	467.1	443.7	420.9	399.0	378.5	359.6	339.9	331.2	322.5
147.5°	497.4	478.5	458.8	439.9	419.4	399.7	380.8	363.4	346.0	338.0	330.1
150°	483.0	468.6	452.0	435.3	417.2	399.7	383.1	367.2	350.5	344.1	337.7
152.5°	471.7	458.8	444.4	430.0	414.1	399.0	384.6	371.0	355.8	350.2	344.5
155°	459.6	449.0	436.8	424.0	410.3	397.5	385.4	373.2	360.4	355.1	349.8
157.5°	448.2	439.9	429.3	418.7	406.6	396.0	386.1	375.5	364.2	360.0	355.8
160°	436.8	429.3	421.7	411.9	402.8	393.7	386.1	377.0	367.2	363.8	360.4
162.5°	426.2	420.2	413.4	405.8	398.2	391.4	385.4	378.5	370.2	367.5	364.9
165°	415.6	411.1	405.8	399.7	393.7	389.1	384.6	378.5	372.5	370.2	367.9
167.5°	405.8	402.0	398.2	393.7	389.1	385.4	383.1	378.5	373.2	371.7	370.2
170°	396.7	394.4	392.2	388.4	385.4	383.1	381.6	378.5	374.8	373.6	372.5
172.5°	389.1	387.6	385.4	383.1	380.8	380.1	380.1	377.8	374.8	374.4	374.0
175°	382.3	380.8	380.8	378.5	377.8	377.8	378.5	377.0	374.8	374.8	374.8
177.5°	377.8	377.8	377.0	376.3	375.5	375.5	377.0	376.3	374.8	374.8	374.8
180°	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5	375.5

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1620.4	1620.4	1620.4	1620.4
2.5°	1583.1	1595.1	1607.0	1621.7
5°	1551.2	1572.5	1595.1	1616.4
7.5°	1516.6	1547.2	1576.5	1607.0
10°	1478.0	1516.6	1549.8	1592.4
12.5°	1435.4	1476.7	1523.2	1571.1
15°	1392.9	1444.7	1494.0	1548.5
17.5°	1353.0	1402.2	1456.7	1521.9
20°	1305.1	1359.6	1420.8	1490.0
22.5°	1254.5	1314.4	1380.9	1455.4
25°	1211.9	1273.1	1337.0	1415.5
27.5°	1165.4	1229.2	1291.8	1375.6
30°	1112.2	1181.3	1245.2	1331.7
32.5°	1061.6	1130.8	1201.3	1282.4
35°	1012.4	1080.2	1150.7	1233.2
37.5°	965.8	1027.0	1096.2	1170.7
40°	921.9	977.8	1039.0	1106.8
42.5°	866.1	931.2	988.4	1037.7
45°	818.2	871.4	924.6	964.5
47.5°	762.3	815.5	860.7	892.7
50°	715.7	758.3	795.5	823.5
52.5°	659.8	699.8	730.4	751.6
55°	605.3	639.9	666.5	681.1
57.5°	556.1	578.7	598.7	612.0
60°	501.5	518.8	536.1	550.8
62.5°	443.0	461.6	470.9	486.9
65°	391.1	403.1	417.7	423.0
67.5°	340.6	347.2	356.5	367.2
70°	287.4	291.3	300.7	315.3
72.5°	240.8	244.8	251.4	256.8
75°	191.6	195.6	200.9	206.2
77.5°	150.3	151.7	154.3	159.6
80°	109.1	113.1	115.7	117.1
82.5°	75.8	77.2	77.2	78.5
85°	47.9	45.2	45.2	46.6
87.5°	17.3	20.0	20.0	22.6
90°	4.5	3.0	1.5	0.8
92.5°	32.6	21.2	13.6	11.4
95°	40.1	31.8	25.7	25.0
97.5°	52.2	43.9	39.4	38.6
100°	65.9	57.5	54.5	53.0
102.5°	81.0	71.9	69.7	68.9
105°	96.9	89.3	85.6	85.6
107.5°	112.8	106.8	103.0	101.5
110°	130.2	123.4	120.4	118.9

TEST NUMBER: P1028536

CATALOG NUMBER: S125RDIP-B1090D850UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	146.9	140.1	137.8	136.3
115°	163.5	156.7	154.4	152.9
117.5°	179.4	172.6	170.3	168.1
120°	195.3	188.5	185.5	183.2
122.5°	209.7	202.9	200.6	199.1
125°	224.1	217.3	213.5	212.0
127.5°	237.7	229.4	224.9	222.6
130°	250.6	240.8	234.7	232.4
132.5°	262.0	250.6	243.0	240.0
135°	272.6	260.4	251.4	248.3
137.5°	281.6	269.5	261.2	258.9
140°	291.5	279.4	270.3	268.0
142.5°	300.6	288.5	280.1	278.6
145°	308.9	298.3	290.7	289.2
147.5°	318.0	308.1	301.3	300.6
150°	327.1	317.2	311.9	310.4
152.5°	334.6	326.3	321.8	321.0
155°	342.2	334.6	330.1	330.1
157.5°	349.0	342.2	338.4	338.4
160°	354.3	349.0	346.0	346.7
162.5°	360.4	355.8	352.8	353.6
165°	364.9	361.1	358.9	360.4
167.5°	367.9	365.7	364.2	364.9
170°	371.0	369.5	368.7	369.5
172.5°	373.2	371.7	371.0	372.5
175°	374.8	374.0	373.2	374.8
177.5°	375.5	374.8	374.8	376.3
180°	375.5	375.5	375.5	375.5

(END OF REPORT)