

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028594

Luminaire Tested: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028594
REPORT IS A COMBINATION OF REPORTS P1005161 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9179.0 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	23
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12088	12088	12088	12088
5°	12078	13624	12078	10472
10°	12010	15310	11970	9053
15°	11880	16197	11798	7881
20°	11722	17485	11618	7124
25°	11517	19791	11387	6465
30°	11308	21036	11139	5995
35°	11038	17300	10883	5556
40°	10558	11748	10469	5161
45°	9927	8446	9914	4772
50°	9280	6495	9326	4414
55°	8554	5281	8537	4067
60°	7877	4329	7839	3612
65°	7088	3607	7133	2907
70°	6435	2895	6409	2421
75°	5436	2193	5436	1990
80°	4405	1338	4356	1338
85°	3099	703	3013	796

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17206 cd/sqm

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.9	2.0
10°-20°	530.4	5.8
20°-30°	841.0	9.2
30°-40°	1016.3	11.1
40°-50°	904.8	9.9
50°-60°	693.8	7.6
60°-70°	450.6	4.9
70°-80°	218.7	2.4
80°-90°	53.7	0.6
90°-100°	415.3	4.5
100°-110°	895.7	9.8
110°-120°	835.0	9.1
120°-130°	676.3	7.4
130°-140°	543.1	5.9
140°-150°	409.6	4.5
150°-160°	288.4	3.1
160°-170°	170.0	1.9
170°-180°	55.3	0.6
0°-30°	1552.4	16.9
0°-40°	2568.6	28.0
0°-60°	4167.3	45.4
0°-90°	4890.3	53.3
90°-120°	2146.0	23.4
90°-150°	3775.0	41.1
90°-180°	4289.0	46.7
0°-180°	9179.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1887	1887	1887	1887	1887	
5°	1882	2162	1882	1662	1882	179
15°	1803	2598	1791	1264	1803	508
25°	1648	3110	1630	1016	1648	760
35°	1436	2581	1416	829	1436	894
45°	1123	1154	1122	652	1123	867
55°	793	634	792	488	793	711
65°	493	359	496	290	493	492
75°	240	167	240	152	240	257
85°	54	36	53	40	54	62
90°	1	26	1	26	1	6
95°	38	270	38	270	38	40
105°	130	1525	130	1525	130	137
115°	232	1699	232	1699	232	229
125°	322	1339	322	1339	322	286
135°	378	1112	378	1112	378	293
145°	440	877	440	877	440	276
155°	502	736	502	736	502	231
165°	548	645	548	645	548	154
175°	570	579	570	579	570	54
180°	571	571	571	571	571	

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1888.2	1903.7	1908.4	1920.8	1934.7	1937.8	1945.5	1956.4	1962.6	1961.0	1961.0
5°	1882.0	1908.4	1927.0	1948.6	1975.0	1985.8	1995.1	2018.3	2036.9	2047.8	2066.4
7.5°	1871.2	1909.9	1940.9	1973.4	2013.7	2032.3	2052.4	2085.0	2119.0	2140.7	2160.9
10°	1854.2	1903.7	1947.1	1995.1	2049.3	2077.2	2102.0	2151.6	2193.4	2221.3	2267.7
12.5°	1829.4	1891.3	1951.7	2015.2	2083.4	2112.8	2146.9	2201.1	2260.0	2300.3	2339.0
15°	1803.0	1877.4	1942.4	2018.3	2100.4	2145.4	2188.7	2246.0	2298.7	2343.6	2388.6
17.5°	1772.1	1851.1	1931.6	2018.3	2111.3	2156.2	2193.4	2261.5	2317.3	2362.2	2402.5
20°	1734.9	1823.2	1914.6	2010.6	2105.1	2146.9	2182.5	2256.9	2306.5	2354.5	2411.8
22.5°	1694.6	1790.6	1888.2	1982.7	2075.7	2120.6	2162.4	2227.5	2281.7	2346.7	2421.1
25°	1648.1	1753.5	1852.6	1947.1	2035.4	2077.2	2114.4	2185.6	2261.5	2343.6	2427.3
27.5°	1601.7	1703.9	1799.9	1886.7	1982.7	2021.4	2058.6	2148.5	2238.3	2325.0	2439.7
30°	1550.5	1654.3	1738.0	1818.5	1911.5	1951.7	1998.2	2100.4	2202.7	2320.4	2459.8
32.5°	1493.2	1587.7	1665.2	1748.8	1832.5	1882.0	1940.9	2052.4	2170.1	2311.1	2489.2
35°	1435.9	1511.8	1583.1	1662.1	1762.8	1815.4	1872.7	1990.5	2137.6	2306.5	2514.0
37.5°	1363.1	1435.9	1491.7	1572.2	1676.0	1738.0	1795.3	1931.6	2098.9	2295.6	2512.5
40°	1288.8	1350.7	1403.4	1487.0	1600.1	1657.4	1719.4	1868.1	2058.6	2264.6	2475.3
42.5°	1208.2	1260.9	1318.2	1398.7	1508.7	1564.5	1635.7	1809.2	2002.9	2221.3	2379.3
45°	1123.0	1174.1	1222.2	1305.8	1415.8	1476.2	1553.6	1731.8	1934.7	2129.9	2224.4
47.5°	1039.4	1084.3	1135.4	1208.2	1319.7	1386.4	1465.4	1655.9	1843.3	2007.5	2015.2
50°	958.8	994.5	1037.8	1112.2	1228.4	1291.9	1374.0	1552.1	1734.9	1848.0	1772.1
52.5°	875.2	907.7	952.6	1017.7	1126.1	1200.5	1271.7	1449.9	1603.2	1679.1	1539.7
55°	793.1	821.0	867.4	940.2	1034.7	1092.0	1164.8	1330.6	1465.4	1466.9	1315.1
57.5°	712.5	737.3	776.0	841.1	929.4	996.0	1062.6	1206.7	1298.1	1271.7	1102.9
60°	641.3	656.8	692.4	755.9	838.0	886.0	957.3	1078.1	1138.5	1090.5	909.3
62.5°	566.9	582.4	610.3	661.4	738.9	790.0	834.9	934.0	975.9	903.1	754.4
65°	492.6	511.2	531.3	571.6	644.4	678.5	718.7	791.5	831.8	746.6	618.1
67.5°	427.5	436.8	457.0	498.8	549.9	580.9	608.8	658.3	666.1	597.9	492.6
70°	367.1	370.2	388.8	413.6	452.3	470.9	494.1	523.6	523.6	467.8	384.2
72.5°	299.0	303.6	317.5	343.9	367.1	376.4	384.2	402.7	399.6	348.5	291.2
75°	240.1	243.2	254.0	266.4	275.7	292.8	299.0	295.9	294.3	250.9	218.4
77.5°	185.9	187.4	195.2	206.0	207.6	213.8	209.1	209.1	195.2	170.4	153.4
80°	136.3	137.9	141.0	144.1	144.1	144.1	144.1	136.3	127.0	111.5	106.9
82.5°	91.4	91.4	92.9	96.0	94.5	91.4	88.3	80.5	74.4	69.7	66.6
85°	54.2	54.2	55.8	54.2	48.0	46.5	43.4	41.8	40.3	38.7	38.7
87.5°	26.3	24.8	21.7	18.6	18.6	18.6	18.6	18.6	18.6	17.0	17.0
90°	1.2	2.3	4.6	6.9	9.2	10.4	11.5	12.7	15.0	16.1	18.4
92.5°	17.3	20.7	32.2	49.5	73.7	94.4	115.1	193.4	324.6	467.4	459.3
95°	38.0	39.1	48.4	61.0	86.3	112.2	138.1	261.3	514.6	832.3	1020.0
97.5°	58.7	59.9	66.8	79.4	102.5	121.4	140.4	225.6	420.2	763.2	1101.7
100°	80.6	82.9	87.5	100.2	122.0	139.3	156.6	223.3	373.0	663.1	1039.5
102.5°	104.8	105.9	109.4	123.2	142.7	159.4	176.1	233.7	353.4	587.1	930.2
105°	130.1	130.1	135.8	147.4	165.8	181.9	198.0	248.7	351.1	543.4	834.6
107.5°	154.3	156.6	162.3	171.5	191.1	205.5	219.9	269.4	359.2	520.3	763.2
110°	180.7	183.0	187.6	198.0	215.3	230.2	245.2	292.4	371.8	511.1	716.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	207.2	209.5	213.0	223.3	240.6	255.0	269.4	314.3	388.0	511.1	688.4
115°	232.5	234.8	238.3	248.7	265.9	280.3	294.7	337.3	404.1	514.6	670.0
117.5°	255.6	259.0	262.5	272.8	292.4	306.2	320.0	360.3	422.5	520.3	659.6
120°	278.6	282.0	286.6	297.0	316.6	331.0	345.4	385.7	440.9	529.6	652.7
122.5°	302.8	305.1	308.5	318.9	340.8	355.2	369.5	409.8	461.6	537.6	647.0
125°	322.3	324.6	330.4	340.8	362.6	377.6	392.6	430.5	480.0	546.8	642.4
127.5°	338.5	341.9	348.8	361.5	384.5	399.4	414.4	451.3	497.3	557.2	640.1
130°	353.4	356.9	366.1	381.0	405.2	420.2	435.2	470.8	514.6	566.4	637.8
132.5°	364.9	369.5	381.0	398.3	423.6	438.6	453.6	489.3	529.6	576.8	637.8
135°	377.6	382.2	396.0	414.4	438.6	454.2	469.7	505.4	543.4	586.0	637.8
137.5°	393.7	397.2	409.8	428.2	452.4	468.6	484.7	516.9	553.7	595.2	638.9
140°	407.5	411.0	424.8	443.2	465.1	480.6	496.2	529.6	564.1	600.9	640.1
142.5°	423.6	425.9	438.6	457.0	477.7	492.1	506.5	537.6	569.8	604.4	641.2
145°	439.8	442.1	453.6	469.7	490.4	503.6	516.9	546.8	575.6	606.7	640.1
147.5°	457.0	458.2	468.5	483.5	501.9	514.0	526.1	552.6	579.1	607.8	637.8
150°	472.0	474.3	482.4	497.3	513.4	523.2	533.0	558.3	582.5	607.8	634.3
152.5°	488.1	489.3	496.2	508.8	523.8	532.4	541.1	564.1	584.8	606.7	629.7
155°	501.9	501.9	508.8	520.3	531.9	540.0	548.0	567.5	586.0	604.4	623.9
157.5°	514.6	514.6	520.3	530.7	541.1	547.4	553.7	571.0	587.1	602.1	618.2
160°	527.2	526.1	530.7	538.8	548.0	553.2	558.3	573.3	587.1	598.6	612.4
162.5°	537.6	536.5	541.1	548.0	554.9	558.9	562.9	575.6	586.0	595.2	605.5
165°	548.0	545.7	549.1	554.9	559.5	563.0	566.4	575.6	584.8	591.7	598.6
167.5°	554.9	553.7	556.0	559.5	562.9	565.2	567.5	575.6	582.5	586.0	591.7
170°	561.8	560.6	561.8	564.1	566.4	568.1	569.8	575.6	580.2	582.5	586.0
172.5°	566.4	564.1	565.2	567.5	568.7	569.2	569.8	574.4	577.9	577.9	579.1
175°	569.8	567.5	568.7	569.8	569.8	569.8	569.8	573.3	575.6	574.4	574.4
177.5°	572.1	569.8	569.8	571.0	569.8	569.8	569.8	572.1	573.3	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1968.8	1979.6	1988.9	1984.3	2002.9	2001.3	2004.4	2010.6	2012.1	2009.1	2002.9
5°	2075.7	2091.1	2117.5	2131.4	2128.3	2140.7	2146.9	2156.2	2165.5	2162.4	2162.4
7.5°	2194.9	2216.6	2242.9	2278.6	2283.2	2294.1	2312.7	2312.7	2323.5	2318.9	2317.3
10°	2298.7	2325.0	2366.9	2394.8	2407.1	2413.3	2431.9	2438.1	2450.5	2452.1	2452.1
12.5°	2383.9	2430.4	2458.3	2486.1	2492.3	2501.6	2515.6	2524.9	2529.5	2529.5	2524.9
15°	2428.8	2466.0	2498.5	2528.0	2545.0	2552.7	2566.7	2577.5	2583.7	2597.7	2600.8
17.5°	2447.4	2492.3	2545.0	2586.8	2616.3	2624.0	2651.9	2661.2	2673.6	2679.8	2687.5
20°	2473.8	2538.8	2602.3	2653.4	2681.3	2701.5	2730.9	2774.3	2786.6	2786.6	2782.0
22.5°	2497.0	2580.6	2667.4	2749.5	2772.7	2813.0	2867.2	2913.7	2932.3	2940.0	2933.8
25°	2524.9	2639.5	2752.6	2854.8	2918.3	2947.7	3020.5	3076.3	3098.0	3110.4	3113.5
27.5°	2572.9	2716.9	2861.0	2991.1	3056.2	3090.3	3166.2	3214.2	3240.5	3251.3	3243.6
30°	2627.1	2803.7	2971.0	3087.2	3130.5	3172.3	3221.9	3240.5	3234.3	3234.3	3257.5
32.5°	2682.9	2865.6	3014.4	3090.3	3105.7	3099.5	3079.4	3023.6	2991.1	2991.1	3011.3
35°	2713.8	2871.8	2947.7	2923.0	2862.5	2826.9	2716.9	2655.0	2585.3	2580.6	2603.9
37.5°	2696.8	2765.0	2734.0	2571.3	2489.2	2421.1	2249.1	2181.0	2129.9	2058.6	2168.6
40°	2577.5	2554.3	2393.2	2159.3	2067.9	1971.9	1835.6	1767.4	1696.2	1685.3	1711.6
42.5°	2376.2	2238.3	2002.9	1776.7	1683.8	1615.6	1511.8	1445.2	1400.3	1381.7	1412.7
45°	2125.2	1908.4	1672.9	1493.2	1391.0	1355.4	1260.9	1202.0	1167.9	1154.0	1175.7
47.5°	1818.5	1600.1	1377.1	1225.3	1164.8	1129.2	1065.7	1014.6	985.2	975.9	985.2
50°	1544.4	1319.7	1132.3	1034.7	980.5	951.1	898.4	865.9	842.7	836.5	851.9
52.5°	1307.4	1102.9	960.4	873.6	838.0	813.2	776.0	748.2	734.2	728.0	738.9
55°	1095.1	929.4	814.8	740.4	714.1	698.6	666.1	650.6	635.1	633.5	644.4
57.5°	907.7	793.1	687.8	635.1	627.3	604.1	576.2	562.3	554.5	553.0	557.6
60°	755.9	653.7	590.2	543.7	532.9	514.3	498.8	489.5	480.2	477.1	480.2
62.5°	628.9	548.3	497.2	466.2	450.8	446.1	429.1	418.2	416.7	416.7	419.8
65°	518.9	450.8	418.2	393.4	382.6	378.0	365.6	357.8	359.4	359.4	360.9
67.5°	422.9	373.3	343.9	331.5	322.2	320.6	308.3	305.2	302.1	302.1	305.2
70°	336.1	305.2	283.5	277.3	275.7	264.9	260.2	258.7	254.0	255.6	255.6
72.5°	263.3	243.2	230.8	221.5	223.1	216.9	210.7	210.7	207.6	212.2	212.2
75°	195.2	185.9	176.6	173.5	176.6	173.5	168.8	167.3	168.8	167.3	167.3
77.5°	144.1	139.4	136.3	134.8	134.8	128.6	125.5	128.6	122.4	125.5	125.5
80°	100.7	94.5	92.9	89.8	91.4	86.7	88.3	85.2	85.2	85.2	85.2
82.5°	63.5	62.0	62.0	62.0	60.4	60.4	60.4	60.4	60.4	60.4	58.9
85°	38.7	37.2	37.2	37.2	35.6	35.6	35.6	35.6	35.6	35.6	35.6
87.5°	15.5	17.0	17.0	18.6	17.0	15.5	15.5	15.5	17.0	17.0	15.5
90°	19.6	20.7	21.9	23.0	24.2	25.3	25.3	25.3	26.5	26.5	26.5
92.5°	370.7	249.8	179.6	133.5	122.6	111.7	93.2	89.8	87.5	85.2	87.5
95°	998.1	827.7	652.7	511.1	462.8	414.4	332.7	298.2	289.0	270.5	289.0
97.5°	1246.7	1186.9	1047.6	904.8	835.8	766.7	697.6	637.8	606.7	592.9	606.7
100°	1327.3	1416.0	1359.6	1241.0	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4
102.5°	1279.0	1493.1	1550.7	1509.2	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4
105°	1165.0	1441.3	1599.0	1649.7	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2
107.5°	1056.8	1335.4	1543.8	1665.8	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5
110°	967.0	1215.7	1434.4	1596.7	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	900.2	1121.3	1326.2	1490.8	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7
115°	855.3	1045.3	1223.7	1381.4	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2
117.5°	825.4	992.3	1150.0	1288.2	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5
120°	801.2	950.9	1089.0	1215.7	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5
122.5°	780.5	919.8	1045.3	1154.7	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2
125°	762.1	889.9	1007.3	1107.5	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3
127.5°	744.8	858.8	970.5	1064.9	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6
130°	727.6	830.0	931.3	1021.1	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5
132.5°	713.7	801.2	894.5	973.9	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6
135°	703.4	777.1	856.5	930.2	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2
137.5°	693.0	755.2	822.0	885.3	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1
140°	686.1	737.9	792.0	845.0	869.2	893.3	935.9	965.9	983.1	988.9	983.1
142.5°	680.4	723.0	766.7	810.4	830.6	850.7	885.3	909.4	925.6	930.2	925.6
145°	674.6	710.3	746.0	781.7	797.2	812.7	840.4	859.9	872.6	877.2	872.6
147.5°	668.8	697.6	727.6	756.3	768.4	780.5	803.5	819.7	827.7	830.0	827.7
150°	661.9	687.3	712.6	734.5	744.8	755.2	772.5	786.3	790.9	792.0	790.9
152.5°	653.9	675.8	697.6	717.2	724.7	732.2	746.0	756.3	760.9	762.1	760.9
155°	644.7	664.2	682.7	698.8	705.1	711.4	723.0	731.0	734.5	735.6	734.5
157.5°	636.6	652.7	668.8	681.5	686.7	691.9	701.1	708.0	711.4	711.4	711.4
160°	626.3	641.2	652.7	664.2	668.2	672.3	680.4	686.1	688.4	687.3	688.4
162.5°	617.0	628.6	638.9	648.1	651.6	655.0	660.8	665.4	665.4	665.4	665.4
165°	607.8	617.0	625.1	632.0	634.9	637.8	642.4	644.7	644.7	644.7	644.7
167.5°	598.6	605.5	611.3	617.0	619.3	621.6	623.9	626.3	625.1	625.1	625.1
170°	590.6	596.3	599.8	603.2	604.4	605.5	607.8	609.0	609.0	607.8	609.0
172.5°	582.5	586.0	589.4	591.7	592.3	592.9	592.9	595.2	592.9	591.7	592.9
175°	575.6	579.1	579.1	581.4	581.4	581.4	581.4	582.5	580.2	579.1	580.2
177.5°	572.1	573.3	574.4	574.4	574.4	574.4	573.3	574.4	571.0	571.0	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	2010.6	1999.8	2004.4	1999.8	1995.1	1990.5	1979.6	1964.1	1951.7	1942.4	1940.9
5°	2165.5	2151.6	2142.3	2137.6	2128.3	2115.9	2095.8	2072.6	2044.7	2033.8	2012.1
7.5°	2308.0	2303.4	2281.7	2278.6	2272.4	2249.1	2215.1	2184.1	2148.5	2119.0	2091.1
10°	2442.8	2431.9	2416.4	2394.8	2391.7	2362.2	2329.7	2286.3	2239.9	2212.0	2162.4
12.5°	2526.4	2514.0	2497.0	2483.0	2475.3	2456.7	2411.8	2368.4	2326.6	2275.5	2232.1
15°	2586.8	2571.3	2540.4	2529.5	2520.2	2495.4	2462.9	2418.0	2362.2	2326.6	2264.6
17.5°	2668.9	2650.3	2619.4	2599.2	2582.2	2543.5	2497.0	2436.6	2383.9	2343.6	2287.9
20°	2763.4	2735.5	2695.3	2668.9	2644.1	2599.2	2534.2	2462.9	2387.0	2337.4	2280.1
22.5°	2919.9	2867.2	2803.7	2766.5	2732.4	2655.0	2577.5	2489.2	2404.0	2329.7	2260.0
25°	3071.7	3019.0	2940.0	2888.9	2836.2	2746.4	2644.1	2521.8	2413.3	2326.6	2235.2
27.5°	3212.6	3158.4	3085.6	3023.6	2972.5	2837.8	2703.0	2565.1	2427.3	2308.0	2215.1
30°	3245.2	3221.9	3166.2	3111.9	3065.5	2941.5	2785.1	2610.1	2444.3	2291.0	2187.2
32.5°	3048.4	3105.7	3119.7	3111.9	3082.5	2994.2	2850.2	2665.8	2469.1	2283.2	2140.7
35°	2639.5	2743.3	2850.2	2907.5	2935.4	2947.7	2862.5	2693.7	2486.1	2270.8	2109.7
37.5°	2188.7	2289.4	2458.3	2543.5	2637.9	2761.9	2795.9	2687.5	2478.4	2261.5	2060.2
40°	1798.4	1927.0	2066.4	2143.8	2225.9	2449.0	2617.8	2605.4	2453.6	2227.5	2021.4
42.5°	1463.8	1544.4	1666.7	1751.9	1852.6	2102.0	2328.1	2439.7	2379.3	2185.6	1971.9
45°	1220.6	1282.6	1369.3	1456.1	1518.0	1744.2	2012.1	2194.9	2252.2	2111.3	1896.0
47.5°	1028.5	1075.0	1150.9	1205.1	1271.7	1449.9	1682.2	1939.3	2060.2	2006.0	1815.4
50°	881.4	918.6	979.0	1013.0	1071.9	1225.3	1401.8	1671.4	1854.2	1860.3	1708.5
52.5°	752.8	790.0	841.1	870.5	906.2	1009.9	1188.1	1415.8	1626.4	1703.9	1586.2
55°	655.2	676.9	718.7	742.0	774.5	875.2	988.3	1181.9	1401.8	1528.9	1454.5
57.5°	565.4	588.6	615.0	633.5	656.8	737.3	839.6	985.2	1203.6	1341.4	1316.6
60°	492.6	506.5	531.3	545.2	566.9	619.6	690.9	836.5	1009.9	1140.1	1154.0
62.5°	424.4	436.8	453.9	466.2	480.2	522.0	574.7	678.5	830.3	971.2	989.8
65°	365.6	376.4	385.7	396.5	407.4	433.7	478.6	559.2	676.9	808.6	848.9
67.5°	312.9	316.0	329.9	331.5	337.7	357.8	390.3	455.4	540.6	645.9	698.6
70°	261.8	268.0	271.1	275.7	281.9	295.9	322.2	356.3	419.8	505.0	554.5
72.5°	212.2	213.8	218.4	221.5	227.7	238.5	250.9	277.3	317.5	379.5	424.4
75°	168.8	170.4	173.5	175.0	179.7	182.8	189.0	207.6	235.4	272.6	305.2
77.5°	127.0	130.1	133.2	133.2	134.8	137.9	141.0	147.2	161.1	185.9	213.8
80°	86.7	88.3	88.3	89.8	88.3	92.9	97.6	105.3	111.5	119.3	133.2
82.5°	60.4	60.4	60.4	62.0	62.0	63.5	63.5	65.1	66.6	71.3	77.4
85°	37.2	37.2	38.7	35.6	37.2	38.7	38.7	37.2	38.7	40.3	41.8
87.5°	15.5	15.5	17.0	17.0	17.0	17.0	15.5	17.0	15.5	17.0	17.0
90°	25.3	25.3	25.3	24.2	23.0	21.9	20.7	19.6	18.4	16.1	15.0
92.5°	89.8	93.2	111.7	122.6	133.5	179.6	249.8	370.7	459.3	467.4	324.6
95°	298.2	332.7	414.4	462.8	511.1	652.7	827.7	998.1	1020.0	832.3	514.6
97.5°	637.8	697.6	766.7	835.8	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2
100°	958.9	1041.8	1121.3	1181.2	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0
102.5°	1298.6	1351.5	1437.8	1473.5	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4
105°	1562.2	1600.2	1637.0	1643.4	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1
107.5°	1721.0	1726.8	1716.4	1691.1	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2
110°	1768.2	1746.4	1694.6	1645.6	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1733.7	1692.3	1610.5	1550.6	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0
115°	1652.0	1596.7	1506.9	1444.2	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1
117.5°	1555.3	1497.7	1406.8	1347.5	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5
120°	1457.4	1402.2	1317.0	1266.4	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9
122.5°	1371.1	1321.6	1247.9	1201.3	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6
125°	1302.0	1254.8	1190.3	1148.9	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0
127.5°	1244.4	1201.9	1143.1	1104.0	1064.9	970.5	858.8	744.8	640.1	557.2	497.3
130°	1191.5	1153.5	1095.9	1058.5	1021.1	931.3	830.0	727.6	637.8	566.4	514.6
132.5°	1140.8	1102.8	1045.3	1009.6	973.9	894.5	801.2	713.7	637.8	576.8	529.6
135°	1084.4	1046.4	995.8	963.0	930.2	856.5	777.1	703.4	637.8	586.0	543.4
137.5°	1024.6	988.9	942.8	914.0	885.3	822.0	755.2	693.0	638.9	595.2	553.7
140°	965.9	935.9	893.3	869.2	845.0	792.0	737.9	686.1	640.1	600.9	564.1
142.5°	909.4	885.3	850.7	830.6	810.4	766.7	723.0	680.4	641.2	604.4	569.8
145°	859.9	840.4	812.7	797.2	781.7	746.0	710.3	674.6	640.1	606.7	575.6
147.5°	819.7	803.5	780.5	768.4	756.3	727.6	697.6	668.8	637.8	607.8	579.1
150°	786.3	772.5	755.2	744.8	734.5	712.6	687.3	661.9	634.3	607.8	582.5
152.5°	756.3	746.0	732.2	724.7	717.2	697.6	675.8	653.9	629.7	606.7	584.8
155°	731.0	723.0	711.4	705.1	698.8	682.7	664.2	644.7	623.9	604.4	586.0
157.5°	708.0	701.1	691.9	686.7	681.5	668.8	652.7	636.6	618.2	602.1	587.1
160°	686.1	680.4	672.3	668.2	664.2	652.7	641.2	626.3	612.4	598.6	587.1
162.5°	665.4	660.8	655.0	651.6	648.1	638.9	628.6	617.0	605.5	595.2	586.0
165°	644.7	642.4	637.8	634.9	632.0	625.1	617.0	607.8	598.6	591.7	584.8
167.5°	626.3	623.9	621.6	619.3	617.0	611.3	605.5	598.6	591.7	586.0	582.5
170°	609.0	607.8	605.5	604.4	603.2	599.8	596.3	590.6	586.0	582.5	580.2
172.5°	595.2	592.9	592.9	592.3	591.7	589.4	586.0	582.5	579.1	577.9	577.9
175°	582.5	581.4	581.4	581.4	581.4	579.1	579.1	575.6	574.4	574.4	575.6
177.5°	574.4	573.3	574.4	574.4	574.4	574.4	573.3	572.1	571.0	571.0	573.3
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1936.2	1927.0	1920.8	1919.2	1909.9	1902.2	1892.9	1891.3	1886.7	1874.3	1866.5
5°	1996.7	1975.0	1970.3	1956.4	1933.2	1916.1	1894.4	1882.0	1868.1	1844.9	1826.3
7.5°	2058.6	2029.2	2007.5	1987.4	1954.8	1923.9	1892.9	1868.1	1843.3	1809.2	1781.3
10°	2119.0	2074.1	2047.8	2018.3	1973.4	1927.0	1883.6	1848.0	1807.7	1767.4	1727.1
12.5°	2174.8	2117.5	2078.8	2036.9	1981.2	1923.9	1868.1	1818.5	1776.7	1722.5	1677.6
15°	2208.9	2145.4	2106.6	2066.4	1982.7	1919.2	1854.2	1790.6	1734.9	1677.6	1635.7
17.5°	2229.0	2157.8	2114.4	2077.2	1992.0	1905.3	1821.6	1753.5	1693.1	1624.9	1569.1
20°	2219.7	2150.0	2109.7	2074.1	1975.0	1888.2	1798.4	1719.4	1643.5	1573.8	1514.9
22.5°	2199.6	2126.8	2081.9	2049.3	1961.0	1858.8	1759.7	1674.5	1595.5	1525.8	1459.2
25°	2156.2	2085.0	2046.2	2006.0	1919.2	1821.6	1720.9	1629.5	1545.9	1471.5	1397.2
27.5°	2117.5	2030.7	1990.5	1954.8	1863.4	1776.7	1677.6	1576.9	1491.7	1414.2	1339.9
30°	2072.6	1975.0	1931.6	1883.6	1801.5	1719.4	1620.3	1527.3	1439.0	1356.9	1285.7
32.5°	2024.5	1911.5	1861.9	1807.7	1724.0	1646.6	1562.9	1471.5	1383.3	1302.7	1228.4
35°	1962.6	1841.8	1784.4	1733.3	1646.6	1569.1	1491.7	1415.8	1327.5	1242.3	1171.0
37.5°	1903.7	1770.5	1710.1	1651.2	1559.8	1485.5	1422.0	1350.7	1265.5	1183.4	1115.3
40°	1837.1	1683.8	1621.8	1567.6	1473.1	1391.0	1333.7	1277.9	1203.6	1124.6	1050.2
42.5°	1776.7	1603.2	1538.2	1482.4	1383.3	1305.8	1251.6	1205.1	1140.1	1067.3	991.4
45°	1693.1	1516.5	1449.9	1391.0	1290.3	1217.5	1161.7	1121.5	1070.4	1002.2	934.0
47.5°	1615.6	1432.8	1360.0	1288.8	1197.4	1123.0	1071.9	1040.9	1006.8	946.4	876.7
50°	1521.1	1336.8	1262.4	1203.6	1099.8	1036.3	985.2	963.5	932.5	875.2	819.4
52.5°	1418.9	1243.8	1174.1	1102.9	1006.8	944.9	900.0	875.2	850.4	808.6	755.9
55°	1299.6	1140.1	1075.0	1011.5	915.5	858.1	817.9	791.5	777.6	738.9	700.1
57.5°	1185.0	1034.7	974.3	915.5	831.8	766.8	740.4	717.2	697.0	669.2	636.6
60°	1068.8	932.5	867.4	814.8	742.0	683.1	661.4	638.2	622.7	601.0	577.8
62.5°	935.6	819.4	769.9	720.3	658.3	611.9	587.1	568.5	548.3	534.4	514.3
65°	794.6	712.5	664.5	627.3	568.5	526.7	508.1	495.7	478.6	464.7	449.2
67.5°	663.0	597.9	577.8	537.5	492.6	455.4	441.5	426.0	412.0	404.3	390.3
70°	536.0	489.5	469.3	458.5	408.9	384.2	371.8	365.6	348.5	340.8	331.5
72.5°	415.1	398.1	384.2	370.2	337.7	322.2	308.3	302.1	289.7	283.5	280.4
75°	306.7	295.9	288.1	286.6	272.6	257.1	243.2	240.1	230.8	224.6	221.5
77.5°	215.3	212.2	210.7	212.2	202.9	193.6	190.5	187.4	176.6	175.0	175.0
80°	141.0	148.7	148.7	147.2	144.1	142.5	137.9	134.8	128.6	127.0	128.6
82.5°	86.7	91.4	92.9	96.0	94.5	92.9	89.8	88.3	89.8	86.7	88.3
85°	43.4	46.5	52.7	52.7	54.2	54.2	54.2	52.7	49.6	51.1	49.6
87.5°	17.0	18.6	18.6	18.6	17.0	21.7	23.2	23.2	23.2	20.1	20.1
90°	12.7	11.5	10.4	9.2	6.9	4.6	2.3	1.2	2.3	4.6	6.9
92.5°	193.4	115.1	94.4	73.7	49.5	32.2	20.7	17.3	20.7	32.2	49.5
95°	261.3	138.1	112.2	86.3	61.0	48.4	39.1	38.0	39.1	48.4	61.0
97.5°	225.6	140.4	121.4	102.5	79.4	66.8	59.9	58.7	59.9	66.8	79.4
100°	223.3	156.6	139.3	122.0	100.2	87.5	82.9	80.6	82.9	87.5	100.2
102.5°	233.7	176.1	159.4	142.7	123.2	109.4	105.9	104.8	105.9	109.4	123.2
105°	248.7	198.0	181.9	165.8	147.4	135.8	130.1	130.1	130.1	135.8	147.4
107.5°	269.4	219.9	205.5	191.1	171.5	162.3	156.6	154.3	156.6	162.3	171.5
110°	292.4	245.2	230.2	215.3	198.0	187.6	183.0	180.7	183.0	187.6	198.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	314.3	269.4	255.0	240.6	223.3	213.0	209.5	207.2	209.5	213.0	223.3
115°	337.3	294.7	280.3	265.9	248.7	238.3	234.8	232.5	234.8	238.3	248.7
117.5°	360.3	320.0	306.2	292.4	272.8	262.5	259.0	255.6	259.0	262.5	272.8
120°	385.7	345.4	331.0	316.6	297.0	286.6	282.0	278.6	282.0	286.6	297.0
122.5°	409.8	369.5	355.2	340.8	318.9	308.5	305.1	302.8	305.1	308.5	318.9
125°	430.5	392.6	377.6	362.6	340.8	330.4	324.6	322.3	324.6	330.4	340.8
127.5°	451.3	414.4	399.4	384.5	361.5	348.8	341.9	338.5	341.9	348.8	361.5
130°	470.8	435.2	420.2	405.2	381.0	366.1	356.9	353.4	356.9	366.1	381.0
132.5°	489.3	453.6	438.6	423.6	398.3	381.0	369.5	364.9	369.5	381.0	398.3
135°	505.4	469.7	454.2	438.6	414.4	396.0	382.2	377.6	382.2	396.0	414.4
137.5°	516.9	484.7	468.6	452.4	428.2	409.8	397.2	393.7	397.2	409.8	428.2
140°	529.6	496.2	480.6	465.1	443.2	424.8	411.0	407.5	411.0	424.8	443.2
142.5°	537.6	506.5	492.1	477.7	457.0	438.6	425.9	423.6	425.9	438.6	457.0
145°	546.8	516.9	503.6	490.4	469.7	453.6	442.1	439.8	442.1	453.6	469.7
147.5°	552.6	526.1	514.0	501.9	483.5	468.5	458.2	457.0	458.2	468.5	483.5
150°	558.3	533.0	523.2	513.4	497.3	482.4	474.3	472.0	474.3	482.4	497.3
152.5°	564.1	541.1	532.4	523.8	508.8	496.2	489.3	488.1	489.3	496.2	508.8
155°	567.5	548.0	540.0	531.9	520.3	508.8	501.9	501.9	501.9	508.8	520.3
157.5°	571.0	553.7	547.4	541.1	530.7	520.3	514.6	514.6	514.6	520.3	530.7
160°	573.3	558.3	553.2	548.0	538.8	530.7	526.1	527.2	526.1	530.7	538.8
162.5°	575.6	562.9	558.9	554.9	548.0	541.1	536.5	537.6	536.5	541.1	548.0
165°	575.6	566.4	563.0	559.5	554.9	549.1	545.7	548.0	545.7	549.1	554.9
167.5°	575.6	567.5	565.2	562.9	559.5	556.0	553.7	554.9	553.7	556.0	559.5
170°	575.6	569.8	568.1	566.4	564.1	561.8	560.6	561.8	560.6	561.8	564.1
172.5°	574.4	569.8	569.2	568.7	567.5	565.2	564.1	566.4	564.1	565.2	567.5
175°	573.3	569.8	569.8	569.8	569.8	568.7	567.5	569.8	567.5	568.7	569.8
177.5°	572.1	569.8	569.8	569.8	571.0	569.8	569.8	572.1	569.8	569.8	571.0
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1861.9	1855.7	1851.1	1846.4	1826.3	1804.6	1801.5	1796.8	1787.5	1798.4	1793.7
5°	1813.9	1799.9	1792.2	1772.1	1747.3	1728.7	1713.2	1694.6	1686.9	1680.7	1679.1
7.5°	1755.0	1742.6	1728.7	1708.5	1677.6	1646.6	1623.4	1604.8	1589.3	1581.5	1581.5
10°	1697.7	1682.2	1663.6	1629.5	1600.1	1561.4	1536.6	1518.0	1496.3	1483.9	1473.1
12.5°	1638.8	1621.8	1604.8	1561.4	1527.3	1487.0	1451.4	1428.2	1417.3	1403.4	1384.8
15°	1580.0	1553.6	1536.6	1493.2	1449.9	1409.6	1386.4	1361.6	1336.8	1322.8	1316.6
17.5°	1518.0	1499.4	1471.5	1425.1	1377.1	1341.4	1307.4	1284.1	1254.7	1240.7	1226.8
20°	1462.3	1434.4	1406.5	1360.0	1313.6	1265.5	1231.5	1203.6	1185.0	1174.1	1161.7
22.5°	1395.6	1369.3	1346.1	1296.5	1245.4	1200.5	1163.3	1146.3	1127.7	1110.6	1098.2
25°	1338.3	1312.0	1288.8	1234.6	1178.8	1137.0	1109.1	1087.4	1067.3	1059.5	1047.1
27.5°	1277.9	1253.1	1222.2	1167.9	1118.4	1082.7	1053.3	1033.2	1017.7	1002.2	992.9
30°	1220.6	1192.7	1164.8	1106.0	1065.7	1030.1	1002.2	977.4	965.0	957.3	941.8
32.5°	1164.8	1129.2	1106.0	1051.8	1013.0	979.0	955.7	934.0	918.6	904.6	892.2
35°	1104.4	1065.7	1042.5	997.6	957.3	923.2	903.1	887.6	869.0	856.6	850.4
37.5°	1047.1	1014.6	991.4	944.9	904.6	876.7	855.0	834.9	827.2	810.1	807.0
40°	985.2	957.3	935.6	890.7	853.5	831.8	808.6	790.0	776.0	768.3	757.5
42.5°	929.4	906.2	882.9	841.1	805.5	779.1	762.1	745.1	732.7	720.3	712.5
45°	878.3	853.5	831.8	791.5	755.9	732.7	715.6	695.5	692.4	675.4	667.6
47.5°	824.1	802.4	783.8	742.0	709.4	686.2	666.1	652.1	638.2	632.0	621.1
50°	771.4	749.7	728.0	690.9	661.4	638.2	618.1	602.6	594.8	585.5	576.2
52.5°	714.1	697.0	680.0	641.3	611.9	591.7	574.7	554.5	546.8	539.1	532.9
55°	666.1	641.3	622.7	590.2	563.8	542.1	523.6	508.1	500.3	494.1	486.4
57.5°	601.0	585.5	570.0	540.6	515.8	494.1	475.5	463.2	453.9	449.2	450.8
60°	545.2	528.2	518.9	487.9	463.2	446.1	429.1	416.7	407.4	402.7	401.2
62.5°	486.4	474.0	457.0	435.3	410.5	395.0	382.6	373.3	357.8	356.3	351.6
65°	429.1	419.8	404.3	384.2	364.0	350.1	336.1	323.7	317.5	309.8	305.2
67.5°	373.3	364.0	350.1	333.0	319.1	305.2	292.8	280.4	269.5	263.3	260.2
70°	319.1	311.3	302.1	281.9	264.9	254.0	244.7	237.0	226.2	223.1	221.5
72.5°	266.4	258.7	254.0	237.0	221.5	212.2	202.9	195.2	190.5	189.0	184.3
75°	218.4	210.7	204.5	189.0	179.7	173.5	164.2	161.1	156.4	154.9	153.4
77.5°	170.4	162.6	161.1	150.3	139.4	136.3	133.2	127.0	127.0	127.0	123.9
80°	122.4	120.8	119.3	108.4	103.8	100.7	99.1	94.5	91.4	88.3	86.7
82.5°	82.1	80.5	79.0	74.4	69.7	68.2	66.6	63.5	63.5	65.1	62.0
85°	49.6	46.5	44.9	43.4	40.3	40.3	41.8	40.3	40.3	40.3	38.7
87.5°	18.6	18.6	18.6	18.6	20.1	17.0	18.6	18.6	17.0	17.0	15.5
90°	9.2	10.4	11.5	12.7	15.0	16.1	18.4	19.6	20.7	21.9	23.0
92.5°	73.7	94.4	115.1	193.4	324.6	467.4	459.3	370.7	249.8	179.6	133.5
95°	86.3	112.2	138.1	261.3	514.6	832.3	1020.0	998.1	827.7	652.7	511.1
97.5°	102.5	121.4	140.4	225.6	420.2	763.2	1101.7	1246.7	1186.9	1047.6	904.8
100°	122.0	139.3	156.6	223.3	373.0	663.1	1039.5	1327.3	1416.0	1359.6	1241.0
102.5°	142.7	159.4	176.1	233.7	353.4	587.1	930.2	1279.0	1493.1	1550.7	1509.2
105°	165.8	181.9	198.0	248.7	351.1	543.4	834.6	1165.0	1441.3	1599.0	1649.7
107.5°	191.1	205.5	219.9	269.4	359.2	520.3	763.2	1056.8	1335.4	1543.8	1665.8
110°	215.3	230.2	245.2	292.4	371.8	511.1	716.0	967.0	1215.7	1434.4	1596.7

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	240.6	255.0	269.4	314.3	388.0	511.1	688.4	900.2	1121.3	1326.2	1490.8
115°	265.9	280.3	294.7	337.3	404.1	514.6	670.0	855.3	1045.3	1223.7	1381.4
117.5°	292.4	306.2	320.0	360.3	422.5	520.3	659.6	825.4	992.3	1150.0	1288.2
120°	316.6	331.0	345.4	385.7	440.9	529.6	652.7	801.2	950.9	1089.0	1215.7
122.5°	340.8	355.2	369.5	409.8	461.6	537.6	647.0	780.5	919.8	1045.3	1154.7
125°	362.6	377.6	392.6	430.5	480.0	546.8	642.4	762.1	889.9	1007.3	1107.5
127.5°	384.5	399.4	414.4	451.3	497.3	557.2	640.1	744.8	858.8	970.5	1064.9
130°	405.2	420.2	435.2	470.8	514.6	566.4	637.8	727.6	830.0	931.3	1021.1
132.5°	423.6	438.6	453.6	489.3	529.6	576.8	637.8	713.7	801.2	894.5	973.9
135°	438.6	454.2	469.7	505.4	543.4	586.0	637.8	703.4	777.1	856.5	930.2
137.5°	452.4	468.6	484.7	516.9	553.7	595.2	638.9	693.0	755.2	822.0	885.3
140°	465.1	480.6	496.2	529.6	564.1	600.9	640.1	686.1	737.9	792.0	845.0
142.5°	477.7	492.1	506.5	537.6	569.8	604.4	641.2	680.4	723.0	766.7	810.4
145°	490.4	503.6	516.9	546.8	575.6	606.7	640.1	674.6	710.3	746.0	781.7
147.5°	501.9	514.0	526.1	552.6	579.1	607.8	637.8	668.8	697.6	727.6	756.3
150°	513.4	523.2	533.0	558.3	582.5	607.8	634.3	661.9	687.3	712.6	734.5
152.5°	523.8	532.4	541.1	564.1	584.8	606.7	629.7	653.9	675.8	697.6	717.2
155°	531.9	540.0	548.0	567.5	586.0	604.4	623.9	644.7	664.2	682.7	698.8
157.5°	541.1	547.4	553.7	571.0	587.1	602.1	618.2	636.6	652.7	668.8	681.5
160°	548.0	553.2	558.3	573.3	587.1	598.6	612.4	626.3	641.2	652.7	664.2
162.5°	554.9	558.9	562.9	575.6	586.0	595.2	605.5	617.0	628.6	638.9	648.1
165°	559.5	563.0	566.4	575.6	584.8	591.7	598.6	607.8	617.0	625.1	632.0
167.5°	562.9	565.2	567.5	575.6	582.5	586.0	591.7	598.6	605.5	611.3	617.0
170°	566.4	568.1	569.8	575.6	580.2	582.5	586.0	590.6	596.3	599.8	603.2
172.5°	568.7	569.2	569.8	574.4	577.9	577.9	579.1	582.5	586.0	589.4	591.7
175°	569.8	569.8	569.8	573.3	575.6	574.4	574.4	575.6	579.1	579.1	581.4
177.5°	569.8	569.8	569.8	572.1	573.3	571.0	571.0	572.1	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1786.0	1789.1	1781.3	1778.3	1772.1	1779.8	1781.3	1779.8	1793.7	1787.5	1790.6
5°	1682.2	1676.0	1671.4	1660.5	1660.5	1662.1	1666.7	1659.0	1663.6	1674.5	1672.9
7.5°	1567.6	1564.5	1566.0	1553.6	1544.4	1547.4	1544.4	1558.3	1566.0	1562.9	1569.1
10°	1463.8	1470.0	1456.1	1449.9	1443.7	1449.9	1448.3	1451.4	1460.7	1466.9	1477.7
12.5°	1380.2	1378.6	1370.9	1364.7	1353.8	1356.9	1366.2	1363.1	1364.7	1378.6	1377.1
15°	1301.2	1291.9	1285.7	1271.7	1274.8	1264.0	1273.3	1284.1	1288.8	1301.2	1308.9
17.5°	1222.2	1220.6	1212.9	1211.3	1194.3	1189.6	1198.9	1202.0	1206.7	1212.9	1223.7
20°	1155.6	1154.0	1143.2	1140.1	1126.1	1135.4	1132.3	1138.5	1141.6	1154.0	1158.7
22.5°	1095.1	1087.4	1084.3	1079.7	1075.0	1073.5	1079.7	1078.1	1088.9	1093.6	1095.1
25°	1039.4	1033.2	1031.6	1023.9	1020.8	1016.1	1020.8	1025.4	1037.8	1042.5	1048.7
27.5°	988.3	983.6	980.5	974.3	969.7	969.7	972.8	979.0	983.6	986.7	989.8
30°	941.8	938.7	929.4	926.3	921.7	921.7	921.7	924.8	932.5	941.8	946.4
32.5°	893.8	887.6	881.4	881.4	876.7	876.7	878.3	881.4	889.1	890.7	898.4
35°	847.3	841.1	836.5	833.4	834.9	828.7	831.8	836.5	845.8	848.9	853.5
37.5°	802.4	800.8	791.5	786.9	790.0	790.0	788.4	791.5	797.7	803.9	807.0
40°	752.8	749.7	749.7	745.1	746.6	740.4	745.1	748.2	751.3	757.5	762.1
42.5°	709.4	706.3	700.1	701.7	697.0	697.0	700.1	701.7	706.3	714.1	717.2
45°	663.0	663.0	659.9	655.2	656.8	652.1	655.2	656.8	663.0	670.7	667.6
47.5°	618.1	616.5	616.5	610.3	613.4	608.8	613.4	615.0	618.1	622.7	621.1
50°	574.7	570.0	571.6	570.0	568.5	568.5	571.6	571.6	574.7	574.7	579.3
52.5°	529.8	529.8	526.7	528.2	531.3	528.2	532.9	528.2	531.3	532.9	536.0
55°	489.5	486.4	487.9	486.4	492.6	487.9	492.6	489.5	492.6	491.0	494.1
57.5°	446.1	441.5	443.0	441.5	446.1	444.6	449.2	444.6	446.1	447.7	452.3
60°	396.5	396.5	396.5	393.4	398.1	398.1	396.5	396.5	402.7	405.8	404.3
62.5°	350.1	348.5	343.9	342.3	343.9	340.8	347.0	345.4	348.5	351.6	354.7
65°	299.0	295.9	294.3	291.2	291.2	289.7	291.2	297.4	299.0	300.5	308.3
67.5°	257.1	255.6	254.0	249.4	249.4	252.5	252.5	252.5	261.8	257.1	263.3
70°	220.0	216.9	213.8	212.2	212.2	213.8	215.3	216.9	215.3	221.5	223.1
72.5°	184.3	185.9	182.8	182.8	182.8	181.2	181.2	184.3	185.9	184.3	185.9
75°	153.4	153.4	151.8	153.4	153.4	151.8	151.8	154.9	154.9	153.4	158.0
77.5°	123.9	122.4	119.3	116.2	117.7	116.2	117.7	116.2	120.8	125.5	122.4
80°	86.7	85.2	85.2	85.2	86.7	85.2	88.3	85.2	86.7	86.7	88.3
82.5°	62.0	63.5	63.5	62.0	63.5	62.0	63.5	63.5	63.5	62.0	63.5
85°	40.3	40.3	40.3	40.3	38.7	40.3	40.3	40.3	41.8	40.3	41.8
87.5°	17.0	17.0	17.0	17.0	17.0	17.0	17.0	17.0	18.6	17.0	18.6
90°	24.2	25.3	25.3	25.3	26.5	26.5	26.5	25.3	25.3	25.3	24.2
92.5°	122.6	111.7	93.2	89.8	87.5	85.2	87.5	89.8	93.2	111.7	122.6
95°	462.8	414.4	332.7	298.2	289.0	270.5	289.0	298.2	332.7	414.4	462.8
97.5°	835.8	766.7	697.6	637.8	606.7	592.9	606.7	637.8	697.6	766.7	835.8
100°	1181.2	1121.3	1041.8	958.9	916.4	897.9	916.4	958.9	1041.8	1121.3	1181.2
102.5°	1473.5	1437.8	1351.5	1298.6	1251.4	1238.7	1251.4	1298.6	1351.5	1437.8	1473.5
105°	1643.4	1637.0	1600.2	1562.2	1539.2	1525.3	1539.2	1562.2	1600.2	1637.0	1643.4
107.5°	1691.1	1716.4	1726.8	1721.0	1709.5	1698.0	1709.5	1721.0	1726.8	1716.4	1691.1
110°	1645.6	1694.6	1746.4	1768.2	1776.3	1776.3	1776.3	1768.2	1746.4	1694.6	1645.6

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1550.6	1610.5	1692.3	1733.7	1756.7	1767.1	1756.7	1733.7	1692.3	1610.5	1550.6
115°	1444.2	1506.9	1596.7	1652.0	1684.2	1699.2	1684.2	1652.0	1596.7	1506.9	1444.2
117.5°	1347.5	1406.8	1497.7	1555.3	1587.5	1596.7	1587.5	1555.3	1497.7	1406.8	1347.5
120°	1266.4	1317.0	1402.2	1457.4	1488.5	1497.7	1488.5	1457.4	1402.2	1317.0	1266.4
122.5°	1201.3	1247.9	1321.6	1371.1	1402.2	1410.2	1402.2	1371.1	1321.6	1247.9	1201.3
125°	1148.9	1190.3	1254.8	1302.0	1327.3	1338.8	1327.3	1302.0	1254.8	1190.3	1148.9
127.5°	1104.0	1143.1	1201.9	1244.4	1268.6	1273.2	1268.6	1244.4	1201.9	1143.1	1104.0
130°	1058.5	1095.9	1153.5	1191.5	1214.5	1221.4	1214.5	1191.5	1153.5	1095.9	1058.5
132.5°	1009.6	1045.3	1102.8	1140.8	1161.6	1169.6	1161.6	1140.8	1102.8	1045.3	1009.6
135°	963.0	995.8	1046.4	1084.4	1105.2	1112.1	1105.2	1084.4	1046.4	995.8	963.0
137.5°	914.0	942.8	988.9	1024.6	1044.1	1052.2	1044.1	1024.6	988.9	942.8	914.0
140°	869.2	893.3	935.9	965.9	983.1	988.9	983.1	965.9	935.9	893.3	869.2
142.5°	830.6	850.7	885.3	909.4	925.6	930.2	925.6	909.4	885.3	850.7	830.6
145°	797.2	812.7	840.4	859.9	872.6	877.2	872.6	859.9	840.4	812.7	797.2
147.5°	768.4	780.5	803.5	819.7	827.7	830.0	827.7	819.7	803.5	780.5	768.4
150°	744.8	755.2	772.5	786.3	790.9	792.0	790.9	786.3	772.5	755.2	744.8
152.5°	724.7	732.2	746.0	756.3	760.9	762.1	760.9	756.3	746.0	732.2	724.7
155°	705.1	711.4	723.0	731.0	734.5	735.6	734.5	731.0	723.0	711.4	705.1
157.5°	686.7	691.9	701.1	708.0	711.4	711.4	711.4	708.0	701.1	691.9	686.7
160°	668.2	672.3	680.4	686.1	688.4	687.3	688.4	686.1	680.4	672.3	668.2
162.5°	651.6	655.0	660.8	665.4	665.4	665.4	665.4	665.4	660.8	655.0	651.6
165°	634.9	637.8	642.4	644.7	644.7	644.7	644.7	644.7	642.4	637.8	634.9
167.5°	619.3	621.6	623.9	626.3	625.1	625.1	625.1	626.3	623.9	621.6	619.3
170°	604.4	605.5	607.8	609.0	609.0	607.8	609.0	609.0	607.8	605.5	604.4
172.5°	592.3	592.9	592.9	595.2	592.9	591.7	592.9	595.2	592.9	592.9	592.3
175°	581.4	581.4	581.4	582.5	580.2	579.1	580.2	582.5	581.4	581.4	581.4
177.5°	574.4	574.4	573.3	574.4	571.0	571.0	571.0	574.4	573.3	574.4	574.4
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7	1886.7
2.5°	1784.4	1792.2	1786.0	1781.3	1793.7	1799.9	1799.9	1810.8	1821.6	1830.9	1832.5
5°	1674.5	1686.9	1690.0	1688.4	1707.0	1716.3	1736.4	1747.3	1762.8	1773.6	1786.0
7.5°	1573.8	1590.8	1592.4	1595.5	1623.4	1638.8	1655.9	1683.8	1705.4	1720.9	1734.9
10°	1473.1	1483.9	1494.8	1508.7	1536.6	1562.9	1587.7	1617.2	1645.0	1660.5	1680.7
12.5°	1397.2	1404.9	1417.3	1426.6	1456.1	1479.3	1511.8	1552.1	1592.4	1604.8	1629.5
15°	1318.2	1322.8	1347.6	1356.9	1381.7	1420.4	1440.6	1479.3	1522.7	1545.9	1573.8
17.5°	1226.8	1254.7	1270.2	1281.0	1312.0	1343.0	1375.5	1415.8	1471.5	1493.2	1513.4
20°	1161.7	1181.9	1198.9	1212.9	1240.7	1287.2	1316.6	1349.2	1401.8	1426.6	1456.1
22.5°	1104.4	1121.5	1137.0	1152.5	1171.0	1212.9	1246.9	1291.9	1344.5	1367.8	1401.8
25°	1050.2	1067.3	1076.6	1095.1	1119.9	1149.4	1189.6	1229.9	1282.6	1308.9	1341.4
27.5°	997.6	1014.6	1031.6	1047.1	1064.2	1092.0	1119.9	1171.0	1225.3	1256.2	1284.1
30°	952.6	960.4	975.9	992.9	1009.9	1036.3	1068.8	1104.4	1166.4	1194.3	1228.4
32.5°	903.1	917.0	927.9	940.2	961.9	983.6	1013.0	1058.0	1107.5	1133.9	1171.0
35°	856.6	869.0	876.7	898.4	912.4	935.6	965.0	1005.3	1047.1	1076.6	1109.1
37.5°	811.7	824.1	833.4	845.8	864.3	884.5	915.5	944.9	994.5	1019.2	1056.4
40°	765.2	776.0	786.9	800.8	817.9	842.7	861.2	898.4	938.7	966.6	994.5
42.5°	720.3	726.5	738.9	754.4	771.4	793.1	819.4	848.9	889.1	913.9	938.7
45°	672.3	683.1	697.0	707.9	723.4	745.1	768.3	794.6	834.9	859.7	886.0
47.5°	627.3	635.1	644.4	661.4	681.6	697.0	721.8	746.6	783.8	807.0	831.8
50°	580.9	588.6	602.6	613.4	628.9	649.0	672.3	698.6	734.2	749.7	774.5
52.5°	537.5	540.6	554.5	565.4	580.9	604.1	622.7	645.9	680.0	697.0	721.8
55°	494.1	497.2	505.0	515.8	532.9	551.4	571.6	597.9	627.3	642.8	666.1
57.5°	449.2	452.3	460.1	467.8	484.8	501.9	525.1	546.8	576.2	590.2	611.9
60°	404.3	404.3	412.0	422.9	435.3	450.8	470.9	497.2	518.9	536.0	551.4
62.5°	356.3	360.9	365.6	373.3	387.2	405.8	422.9	441.5	467.8	480.2	494.1
65°	308.3	312.9	322.2	329.9	340.8	353.2	374.9	390.3	410.5	424.4	436.8
67.5°	266.4	271.1	277.3	286.6	294.3	308.3	323.7	339.2	360.9	370.2	379.5
70°	223.1	227.7	232.3	244.7	252.5	263.3	274.2	289.7	308.3	314.4	322.2
72.5°	189.0	190.5	196.7	199.8	210.7	220.0	232.3	241.6	255.6	263.3	269.5
75°	159.5	159.5	161.1	164.2	170.4	176.6	185.9	195.2	207.6	212.2	220.0
77.5°	125.5	130.1	128.6	131.7	134.8	137.9	145.6	151.8	164.2	167.3	170.4
80°	89.8	91.4	96.0	100.7	100.7	105.3	110.0	111.5	119.3	123.9	123.9
82.5°	65.1	66.6	65.1	66.6	68.2	69.7	74.4	80.5	80.5	82.1	85.2
85°	40.3	40.3	41.8	43.4	43.4	41.8	44.9	43.4	44.9	48.0	48.0
87.5°	20.1	18.6	18.6	18.6	18.6	18.6	20.1	18.6	20.1	20.1	20.1
90°	23.0	21.9	20.7	19.6	18.4	16.1	15.0	12.7	11.5	10.4	9.2
92.5°	133.5	179.6	249.8	370.7	459.3	467.4	324.6	193.4	115.1	94.4	73.7
95°	511.1	652.7	827.7	998.1	1020.0	832.3	514.6	261.3	138.1	112.2	86.3
97.5°	904.8	1047.6	1186.9	1246.7	1101.7	763.2	420.2	225.6	140.4	121.4	102.5
100°	1241.0	1359.6	1416.0	1327.3	1039.5	663.1	373.0	223.3	156.6	139.3	122.0
102.5°	1509.2	1550.7	1493.1	1279.0	930.2	587.1	353.4	233.7	176.1	159.4	142.7
105°	1649.7	1599.0	1441.3	1165.0	834.6	543.4	351.1	248.7	198.0	181.9	165.8
107.5°	1665.8	1543.8	1335.4	1056.8	763.2	520.3	359.2	269.4	219.9	205.5	191.1
110°	1596.7	1434.4	1215.7	967.0	716.0	511.1	371.8	292.4	245.2	230.2	215.3

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1490.8	1326.2	1121.3	900.2	688.4	511.1	388.0	314.3	269.4	255.0	240.6
115°	1381.4	1223.7	1045.3	855.3	670.0	514.6	404.1	337.3	294.7	280.3	265.9
117.5°	1288.2	1150.0	992.3	825.4	659.6	520.3	422.5	360.3	320.0	306.2	292.4
120°	1215.7	1089.0	950.9	801.2	652.7	529.6	440.9	385.7	345.4	331.0	316.6
122.5°	1154.7	1045.3	919.8	780.5	647.0	537.6	461.6	409.8	369.5	355.2	340.8
125°	1107.5	1007.3	889.9	762.1	642.4	546.8	480.0	430.5	392.6	377.6	362.6
127.5°	1064.9	970.5	858.8	744.8	640.1	557.2	497.3	451.3	414.4	399.4	384.5
130°	1021.1	931.3	830.0	727.6	637.8	566.4	514.6	470.8	435.2	420.2	405.2
132.5°	973.9	894.5	801.2	713.7	637.8	576.8	529.6	489.3	453.6	438.6	423.6
135°	930.2	856.5	777.1	703.4	637.8	586.0	543.4	505.4	469.7	454.2	438.6
137.5°	885.3	822.0	755.2	693.0	638.9	595.2	553.7	516.9	484.7	468.6	452.4
140°	845.0	792.0	737.9	686.1	640.1	600.9	564.1	529.6	496.2	480.6	465.1
142.5°	810.4	766.7	723.0	680.4	641.2	604.4	569.8	537.6	506.5	492.1	477.7
145°	781.7	746.0	710.3	674.6	640.1	606.7	575.6	546.8	516.9	503.6	490.4
147.5°	756.3	727.6	697.6	668.8	637.8	607.8	579.1	552.6	526.1	514.0	501.9
150°	734.5	712.6	687.3	661.9	634.3	607.8	582.5	558.3	533.0	523.2	513.4
152.5°	717.2	697.6	675.8	653.9	629.7	606.7	584.8	564.1	541.1	532.4	523.8
155°	698.8	682.7	664.2	644.7	623.9	604.4	586.0	567.5	548.0	540.0	531.9
157.5°	681.5	668.8	652.7	636.6	618.2	602.1	587.1	571.0	553.7	547.4	541.1
160°	664.2	652.7	641.2	626.3	612.4	598.6	587.1	573.3	558.3	553.2	548.0
162.5°	648.1	638.9	628.6	617.0	605.5	595.2	586.0	575.6	562.9	558.9	554.9
165°	632.0	625.1	617.0	607.8	598.6	591.7	584.8	575.6	566.4	563.0	559.5
167.5°	617.0	611.3	605.5	598.6	591.7	586.0	582.5	575.6	567.5	565.2	562.9
170°	603.2	599.8	596.3	590.6	586.0	582.5	580.2	575.6	569.8	568.1	566.4
172.5°	591.7	589.4	586.0	582.5	579.1	577.9	577.9	574.4	569.8	569.2	568.7
175°	581.4	579.1	579.1	575.6	574.4	574.4	575.6	573.3	569.8	569.8	569.8
177.5°	574.4	574.4	573.3	572.1	571.0	571.0	573.3	572.1	569.8	569.8	569.8
180°	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0	571.0

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1886.7	1886.7	1886.7	1886.7
2.5°	1843.3	1857.2	1871.2	1888.2
5°	1806.1	1830.9	1857.2	1882.0
7.5°	1765.9	1801.5	1835.6	1871.2
10°	1720.9	1765.9	1804.6	1854.2
12.5°	1671.4	1719.4	1773.6	1829.4
15°	1621.8	1682.2	1739.5	1803.0
17.5°	1575.3	1632.6	1696.2	1772.1
20°	1519.6	1583.1	1654.3	1734.9
22.5°	1460.7	1530.4	1607.9	1694.6
25°	1411.1	1482.4	1556.7	1648.1
27.5°	1356.9	1431.3	1504.1	1601.7
30°	1295.0	1375.5	1449.9	1550.5
32.5°	1236.1	1316.6	1398.7	1493.2
35°	1178.8	1257.8	1339.9	1435.9
37.5°	1124.6	1195.8	1276.4	1363.1
40°	1073.5	1138.5	1209.8	1288.8
42.5°	1008.4	1084.3	1150.9	1208.2
45°	952.6	1014.6	1076.6	1123.0
47.5°	887.6	949.5	1002.2	1039.4
50°	833.4	882.9	926.3	958.8
52.5°	768.3	814.8	850.4	875.2
55°	704.8	745.1	776.0	793.1
57.5°	647.5	673.8	697.0	712.5
60°	584.0	604.1	624.2	641.3
62.5°	515.8	537.5	548.3	566.9
65°	455.4	469.3	486.4	492.6
67.5°	396.5	404.3	415.1	427.5
70°	334.6	339.2	350.1	367.1
72.5°	280.4	285.0	292.8	299.0
75°	223.1	227.7	233.9	240.1
77.5°	175.0	176.6	179.7	185.9
80°	127.0	131.7	134.8	136.3
82.5°	88.3	89.8	89.8	91.4
85°	55.8	52.7	52.7	54.2
87.5°	20.1	23.2	23.2	26.3
90°	6.9	4.6	2.3	1.2
92.5°	49.5	32.2	20.7	17.3
95°	61.0	48.4	39.1	38.0
97.5°	79.4	66.8	59.9	58.7
100°	100.2	87.5	82.9	80.6
102.5°	123.2	109.4	105.9	104.8
105°	147.4	135.8	130.1	130.1
107.5°	171.5	162.3	156.6	154.3
110°	198.0	187.6	183.0	180.7

TEST NUMBER: P1028594

CATALOG NUMBER: S125RDIP-B1270D1270UB27-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	223.3	213.0	209.5	207.2
115°	248.7	238.3	234.8	232.5
117.5°	272.8	262.5	259.0	255.6
120°	297.0	286.6	282.0	278.6
122.5°	318.9	308.5	305.1	302.8
125°	340.8	330.4	324.6	322.3
127.5°	361.5	348.8	341.9	338.5
130°	381.0	366.1	356.9	353.4
132.5°	398.3	381.0	369.5	364.9
135°	414.4	396.0	382.2	377.6
137.5°	428.2	409.8	397.2	393.7
140°	443.2	424.8	411.0	407.5
142.5°	457.0	438.6	425.9	423.6
145°	469.7	453.6	442.1	439.8
147.5°	483.5	468.5	458.2	457.0
150°	497.3	482.4	474.3	472.0
152.5°	508.8	496.2	489.3	488.1
155°	520.3	508.8	501.9	501.9
157.5°	530.7	520.3	514.6	514.6
160°	538.8	530.7	526.1	527.2
162.5°	548.0	541.1	536.5	537.6
165°	554.9	549.1	545.7	548.0
167.5°	559.5	556.0	553.7	554.9
170°	564.1	561.8	560.6	561.8
172.5°	567.5	565.2	564.1	566.4
175°	569.8	568.7	567.5	569.8
177.5°	571.0	569.8	569.8	572.1
180°	571.0	571.0	571.0	571.0

(END OF REPORT)