

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028618

Luminaire Tested: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028618
REPORT IS A COMBINATION OF REPORTS P1005195 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4
Description: Define 5 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8903.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	75	73	71	64	62	61	53	52	51
2	90	83	77	72	84	77	72	68	67	63	59	56	54	51	47	45	43
3	83	74	66	61	76	69	62	57	59	54	50	50	47	44	42	40	37
4	76	65	58	52	70	61	54	49	53	47	43	45	41	38	38	35	33
5	70	58	50	44	65	55	47	42	47	42	37	41	36	33	34	31	29
6	64	52	44	39	60	49	42	37	43	37	33	37	32	29	31	28	25
7	60	47	40	34	55	44	37	32	39	33	29	33	29	26	28	25	23
8	55	43	35	30	51	40	34	29	35	30	26	31	26	23	26	23	20
9	52	39	32	27	48	37	30	26	32	27	23	28	24	21	24	21	18
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11724	11724	11724	11724
5°	11715	13214	11715	10157
10°	11649	14850	11610	8781
15°	11523	15710	11444	7644
20°	11370	16959	11268	6910
25°	11171	19196	11045	6271
30°	10968	20404	10804	5814
35°	10706	16780	10556	5389
40°	10240	11395	10154	5007
45°	9629	8192	9615	4629
50°	9002	6299	9045	4281
55°	8296	5122	8280	3945
60°	7640	4198	7603	3503
65°	6875	3499	6918	2820
70°	6242	2807	6216	2348
75°	5273	2127	5273	1929
80°	4272	1297	4224	1297
85°	3007	683	2922	772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 16689 cd/sqm

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.5	2.0
10°-20°	514.5	5.8
20°-30°	815.7	9.2
30°-40°	985.7	11.1
40°-50°	877.6	9.9
50°-60°	673.0	7.6
60°-70°	437.1	4.9
70°-80°	212.1	2.4
80°-90°	52.1	0.6
90°-100°	402.9	4.5
100°-110°	868.7	9.8
110°-120°	809.9	9.1
120°-130°	656.0	7.4
130°-140°	526.7	5.9
140°-150°	397.3	4.5
150°-160°	279.8	3.1
160°-170°	164.9	1.9
170°-180°	53.6	0.6
0°-30°	1505.7	16.9
0°-40°	2491.4	28.0
0°-60°	4041.9	45.4
0°-90°	4743.2	53.3
90°-120°	2081.5	23.4
90°-150°	3661.5	41.1
90°-180°	4160.0	46.7
0°-180°	8903.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1830	1830	1830	1830	1830	
5°	1825	2097	1825	1612	1825	173
15°	1749	2520	1737	1226	1749	493
25°	1599	3017	1580	986	1599	737
35°	1393	2503	1373	804	1393	867
45°	1089	1119	1088	632	1089	841
55°	769	614	768	473	769	689
65°	478	349	481	281	478	478
75°	233	162	233	147	233	250
85°	53	35	51	39	53	60
90°	1	26	1	26	1	6
95°	37	262	37	262	37	38
105°	126	1480	126	1480	126	133
115°	226	1648	226	1648	226	222
125°	313	1299	313	1299	313	278
135°	366	1079	366	1079	366	284
145°	426	851	426	851	426	267
155°	487	714	487	714	487	224
165°	532	625	532	625	532	150
175°	553	562	553	562	553	53
180°	554	554	554	554	554	

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1831.4	1846.5	1851.0	1863.0	1876.5	1879.5	1887.0	1897.5	1903.6	1902.1	1902.1
5°	1825.4	1851.0	1869.0	1890.0	1915.6	1926.1	1935.1	1957.6	1975.7	1986.2	2004.2
7.5°	1814.9	1852.5	1882.5	1914.1	1953.1	1971.2	1990.7	2022.2	2055.3	2076.3	2095.9
10°	1798.4	1846.5	1888.5	1935.1	1987.7	2014.7	2038.8	2086.9	2127.4	2154.5	2199.5
12.5°	1774.4	1834.4	1893.0	1954.6	2020.7	2049.3	2082.3	2134.9	2192.0	2231.1	2268.6
15°	1748.8	1820.9	1884.0	1957.6	2037.3	2080.8	2122.9	2178.5	2229.6	2273.2	2316.7
17.5°	1718.8	1795.4	1873.5	1957.6	2047.8	2091.4	2127.4	2193.5	2247.6	2291.2	2330.2
20°	1682.7	1768.3	1857.0	1950.1	2041.8	2082.3	2116.9	2189.0	2237.1	2283.7	2339.3
22.5°	1643.6	1736.8	1831.4	1923.1	2013.2	2056.8	2097.4	2160.5	2213.1	2276.2	2348.3
25°	1598.6	1700.7	1796.9	1888.5	1974.2	2014.7	2050.8	2119.9	2193.5	2273.2	2354.3
27.5°	1553.5	1652.7	1745.8	1829.9	1923.1	1960.7	1996.7	2083.8	2171.0	2255.1	2366.3
30°	1503.9	1604.6	1685.7	1763.8	1854.0	1893.0	1938.1	2037.3	2136.4	2250.6	2385.8
32.5°	1448.3	1540.0	1615.1	1696.2	1777.4	1825.4	1882.5	1990.7	2104.9	2241.6	2414.4
35°	1392.7	1466.4	1535.5	1612.1	1709.7	1760.8	1816.4	1930.6	2073.3	2237.1	2438.4
37.5°	1322.1	1392.7	1446.8	1525.0	1625.6	1685.7	1741.3	1873.5	2035.8	2226.6	2436.9
40°	1250.0	1310.1	1361.2	1442.3	1552.0	1607.6	1667.7	1811.9	1996.7	2196.5	2400.9
42.5°	1171.9	1223.0	1278.6	1356.7	1463.4	1517.4	1586.5	1754.8	1942.6	2154.5	2307.7
45°	1089.3	1138.8	1185.4	1266.5	1373.2	1431.8	1506.9	1679.7	1876.5	2065.8	2157.5
47.5°	1008.1	1051.7	1101.3	1171.9	1280.1	1344.7	1421.3	1606.1	1787.9	1947.1	1954.6
50°	930.0	964.6	1006.6	1078.7	1191.4	1253.0	1332.6	1505.4	1682.7	1792.4	1718.8
52.5°	848.9	880.4	924.0	987.1	1092.3	1164.4	1233.5	1406.3	1555.0	1628.6	1493.4
55°	769.2	796.3	841.4	912.0	1003.6	1059.2	1129.8	1290.6	1421.3	1422.8	1275.5
57.5°	691.1	715.1	752.7	815.8	901.4	966.1	1030.7	1170.4	1259.0	1233.5	1069.7
60°	622.0	637.0	671.6	733.2	812.8	859.4	928.5	1045.7	1104.3	1057.7	881.9
62.5°	549.9	564.9	592.0	641.5	716.7	766.2	809.8	906.0	946.5	875.9	731.7
65°	477.8	495.8	515.3	554.4	625.0	658.1	697.1	767.7	806.8	724.2	599.5
67.5°	414.7	423.7	443.2	483.8	533.4	563.4	590.4	638.5	646.0	579.9	477.8
70°	356.1	359.1	377.1	401.1	438.7	456.7	479.3	507.8	507.8	453.7	372.6
72.5°	290.0	294.5	308.0	333.5	356.1	365.1	372.6	390.6	387.6	338.0	282.5
75°	232.9	235.9	246.4	258.4	267.4	284.0	290.0	287.0	285.5	243.4	211.8
77.5°	180.3	181.8	189.3	199.8	201.3	207.3	202.8	202.8	189.3	165.3	148.7
80°	132.2	133.7	136.7	139.7	139.7	139.7	139.7	132.2	123.2	108.2	103.7
82.5°	88.6	88.6	90.1	93.1	91.6	88.6	85.6	78.1	72.1	67.6	64.6
85°	52.6	52.6	54.1	52.6	46.6	45.1	42.1	40.6	39.1	37.6	37.6
87.5°	25.5	24.0	21.0	18.0	18.0	18.0	18.0	18.0	18.0	16.5	16.5
90°	1.1	2.2	4.5	6.7	8.9	10.0	11.2	12.3	14.5	15.6	17.9
92.5°	16.7	20.1	31.3	48.0	71.5	91.6	111.7	187.6	314.9	453.3	445.5
95°	36.8	38.0	46.9	59.2	83.7	108.8	134.0	253.5	499.1	807.3	989.3
97.5°	56.9	58.1	64.8	77.0	99.4	117.8	136.2	218.9	407.6	740.3	1068.6
100°	78.2	80.4	84.9	97.1	118.4	135.2	151.9	216.6	361.8	643.2	1008.3
102.5°	101.6	102.7	106.1	119.5	138.5	154.6	170.8	226.7	342.8	569.5	902.2
105°	126.2	126.2	131.8	142.9	160.8	176.4	192.1	241.2	340.6	527.0	809.5
107.5°	149.6	151.9	157.4	166.4	185.4	199.4	213.3	261.3	348.4	504.7	740.3
110°	175.3	177.5	182.0	192.1	208.8	223.3	237.8	283.6	360.7	495.8	694.5

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	201.0	203.2	206.6	216.6	233.4	247.4	261.3	304.8	376.3	495.8	667.7
115°	225.6	227.8	231.1	241.2	257.9	271.8	285.8	327.2	391.9	499.1	649.9
117.5°	247.9	251.2	254.6	264.6	283.6	297.0	310.4	349.5	409.8	504.7	639.8
120°	270.2	273.6	278.0	288.1	307.1	321.0	335.0	374.1	427.7	513.6	633.1
122.5°	293.7	295.9	299.2	309.3	330.5	344.4	358.4	397.5	447.8	521.4	627.5
125°	312.6	314.9	320.5	330.5	351.7	366.2	380.8	417.6	465.6	530.4	623.1
127.5°	328.3	331.6	338.3	350.6	372.9	387.4	402.0	437.7	482.4	540.4	620.8
130°	342.8	346.1	355.1	369.6	393.0	407.6	422.1	456.7	499.1	549.4	618.6
132.5°	354.0	358.4	369.6	386.3	410.9	425.4	439.9	474.6	513.6	559.4	618.6
135°	366.2	370.7	384.1	402.0	425.4	440.5	455.6	490.2	527.0	568.3	618.6
137.5°	381.9	385.2	397.5	415.4	438.8	454.4	470.1	501.3	537.1	577.3	619.7
140°	395.3	398.6	412.0	429.9	451.1	466.2	481.3	513.6	547.1	582.9	620.8
142.5°	410.9	413.1	425.4	443.3	463.4	477.4	491.3	521.4	552.7	586.2	621.9
145°	426.5	428.8	439.9	455.6	475.7	488.5	501.3	530.4	558.3	588.4	620.8
147.5°	443.3	444.4	454.5	469.0	486.8	498.6	510.3	536.0	561.6	589.6	618.6
150°	457.8	460.0	467.9	482.4	498.0	507.5	517.0	541.5	565.0	589.6	615.2
152.5°	473.4	474.6	481.3	493.5	508.0	516.4	524.8	547.1	567.2	588.4	610.8
155°	486.8	486.8	493.5	504.7	515.9	523.7	531.5	550.5	568.3	586.2	605.2
157.5°	499.1	499.1	504.7	514.7	524.8	531.0	537.1	553.8	569.5	584.0	599.6
160°	511.4	510.3	514.7	522.6	531.5	536.5	541.5	556.1	569.5	580.6	594.0
162.5°	521.4	520.3	524.8	531.5	538.2	542.1	546.0	558.3	568.3	577.3	587.3
165°	531.5	529.3	532.6	538.2	542.7	546.0	549.4	558.3	567.2	573.9	580.6
167.5°	538.2	537.1	539.3	542.7	546.0	548.2	550.5	558.3	565.0	568.3	573.9
170°	544.9	543.8	544.9	547.1	549.4	551.0	552.7	558.3	562.8	565.0	568.3
172.5°	549.4	547.1	548.2	550.5	551.6	552.2	552.7	557.2	560.5	560.5	561.6
175°	552.7	550.5	551.6	552.7	552.7	552.7	552.7	556.1	558.3	557.2	557.2
177.5°	554.9	552.7	552.7	553.8	552.7	552.7	552.7	554.9	556.1	553.8	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1909.6	1920.1	1929.1	1924.6	1942.6	1941.1	1944.1	1950.1	1951.6	1948.6	1942.6
5°	2013.2	2028.3	2053.8	2067.3	2064.3	2076.3	2082.3	2091.4	2100.4	2097.4	2097.4
7.5°	2128.9	2150.0	2175.5	2210.1	2214.6	2225.1	2243.1	2243.1	2253.6	2249.1	2247.6
10°	2229.6	2255.1	2295.7	2322.7	2334.8	2340.8	2358.8	2364.8	2376.8	2378.3	2378.3
12.5°	2312.2	2357.3	2384.3	2411.4	2417.4	2426.4	2439.9	2448.9	2453.4	2453.4	2448.9
15°	2355.8	2391.8	2423.4	2451.9	2468.5	2476.0	2489.5	2500.0	2506.0	2519.5	2522.6
17.5°	2373.8	2417.4	2468.5	2509.0	2537.6	2545.1	2572.1	2581.1	2593.2	2599.2	2606.7
20°	2399.4	2462.5	2524.1	2573.6	2600.7	2620.2	2648.8	2690.8	2702.8	2702.8	2698.3
22.5°	2421.9	2503.0	2587.2	2666.8	2689.3	2728.4	2781.0	2826.0	2844.1	2851.6	2845.6
25°	2448.9	2560.1	2669.8	2768.9	2830.5	2859.1	2929.7	2983.8	3004.8	3016.8	3019.9
27.5°	2495.5	2635.2	2775.0	2901.2	2964.3	2997.3	3070.9	3117.5	3143.1	3153.6	3146.1
30°	2548.1	2719.4	2881.6	2994.3	3036.4	3076.9	3125.0	3143.1	3137.0	3137.0	3159.6
32.5°	2602.2	2779.5	2923.7	2997.3	3012.3	3006.3	2986.8	2932.7	2901.2	2901.2	2920.7
35°	2632.2	2785.5	2859.1	2835.1	2776.5	2741.9	2635.2	2575.1	2507.5	2503.0	2525.6
37.5°	2615.7	2681.8	2651.8	2494.0	2414.4	2348.3	2181.5	2115.4	2065.8	1996.7	2103.4
40°	2500.0	2477.5	2321.2	2094.4	2005.7	1912.6	1780.4	1714.3	1645.1	1634.6	1660.2
42.5°	2304.7	2171.0	1942.6	1723.3	1633.1	1567.0	1466.4	1401.8	1358.2	1340.2	1370.2
45°	2061.3	1851.0	1622.6	1448.3	1349.2	1314.6	1223.0	1165.9	1132.8	1119.3	1140.3
47.5°	1763.8	1552.0	1335.6	1188.4	1129.8	1095.3	1033.7	984.1	955.5	946.5	955.5
50°	1497.9	1280.1	1098.3	1003.6	951.0	922.5	871.4	839.8	817.3	811.3	826.3
52.5°	1268.0	1069.7	931.5	847.4	812.8	788.8	752.7	725.7	712.1	706.1	716.7
55°	1062.2	901.4	790.3	718.2	692.6	677.6	646.0	631.0	616.0	614.5	625.0
57.5°	880.4	769.2	667.1	616.0	608.5	585.9	558.9	545.4	537.9	536.4	540.9
60°	733.2	634.0	572.4	527.3	516.8	498.8	483.8	474.8	465.7	462.7	465.7
62.5°	610.0	531.9	482.3	452.2	437.2	432.7	416.2	405.7	404.1	404.1	407.2
65°	503.3	437.2	405.7	381.6	371.1	366.6	354.6	347.1	348.6	348.6	350.1
67.5°	410.2	362.1	333.5	321.5	312.5	311.0	299.0	296.0	293.0	293.0	296.0
70°	326.0	296.0	274.9	268.9	267.4	256.9	252.4	250.9	246.4	247.9	247.9
72.5°	255.4	235.9	223.9	214.8	216.3	210.3	204.3	204.3	201.3	205.8	205.8
75°	189.3	180.3	171.3	168.3	171.3	168.3	163.8	162.3	163.8	162.3	162.3
77.5°	139.7	135.2	132.2	130.7	130.7	124.7	121.7	124.7	118.7	121.7	121.7
80°	97.7	91.6	90.1	87.1	88.6	84.1	85.6	82.6	82.6	82.6	82.6
82.5°	61.6	60.1	60.1	60.1	58.6	58.6	58.6	58.6	58.6	58.6	57.1
85°	37.6	36.1	36.1	36.1	34.6	34.6	34.6	34.6	34.6	34.6	34.6
87.5°	15.0	16.5	16.5	18.0	16.5	15.0	15.0	15.0	16.5	16.5	15.0
90°	19.0	20.1	21.2	22.3	23.5	24.6	24.6	24.6	25.7	25.7	25.7
92.5°	359.5	242.3	174.2	129.5	118.9	108.3	90.4	87.1	84.9	82.6	84.9
95°	968.1	802.8	633.1	495.8	448.9	402.0	322.7	289.2	280.3	262.4	280.3
97.5°	1209.3	1151.2	1016.1	877.6	810.6	743.6	676.7	618.6	588.4	575.0	588.4
100°	1287.4	1373.4	1318.7	1203.7	1145.6	1087.6	1010.5	930.1	888.8	870.9	888.8
102.5°	1240.5	1448.2	1504.0	1463.9	1429.2	1394.6	1310.9	1259.5	1213.7	1201.5	1213.7
105°	1130.0	1398.0	1550.9	1600.1	1593.9	1587.8	1552.1	1515.2	1492.9	1479.5	1492.9
107.5°	1025.0	1295.2	1497.3	1615.7	1640.2	1664.8	1674.9	1669.3	1658.1	1647.0	1658.1
110°	937.9	1179.1	1391.3	1548.7	1596.2	1643.6	1693.9	1715.1	1722.9	1722.9	1722.9

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	873.2	1087.6	1286.3	1446.0	1504.0	1562.1	1641.4	1681.6	1703.9	1714.0	1703.9
115°	829.6	1013.9	1186.9	1339.9	1400.8	1461.6	1548.7	1602.3	1633.6	1648.1	1633.6
117.5°	800.6	962.5	1115.5	1249.5	1307.0	1364.5	1452.7	1508.5	1539.8	1548.7	1539.8
120°	777.1	922.3	1056.3	1179.1	1228.2	1277.4	1360.0	1413.6	1443.8	1452.7	1443.8
122.5°	757.0	892.2	1013.9	1119.9	1165.2	1210.4	1281.8	1329.9	1360.0	1367.8	1360.0
125°	739.2	863.1	977.0	1074.2	1114.4	1154.6	1217.1	1262.9	1287.4	1298.6	1287.4
127.5°	722.4	833.0	941.3	1032.8	1070.8	1108.8	1165.7	1207.0	1230.5	1234.9	1230.5
130°	705.7	805.1	903.3	990.4	1026.7	1063.0	1118.8	1155.7	1178.0	1184.7	1178.0
132.5°	692.3	777.1	867.6	944.6	979.2	1013.9	1069.7	1106.5	1126.6	1134.5	1126.6
135°	682.2	753.7	830.7	902.2	934.0	965.9	1015.0	1051.8	1071.9	1078.6	1071.9
137.5°	672.2	732.5	797.2	858.7	886.6	914.5	959.2	993.8	1012.7	1020.6	1012.7
140°	665.5	715.7	768.2	819.6	843.0	866.5	907.8	936.8	953.6	959.2	953.6
142.5°	659.9	701.2	743.6	786.1	805.7	825.2	858.7	882.1	897.7	902.2	897.7
145°	654.3	688.9	723.6	758.2	773.2	788.3	815.1	834.1	846.4	850.8	846.4
147.5°	648.7	676.7	705.7	733.6	745.3	757.0	779.4	795.0	802.8	805.1	802.8
150°	642.0	666.6	691.2	712.4	722.4	732.5	749.2	762.6	767.1	768.2	767.1
152.5°	634.2	655.4	676.7	695.6	702.9	710.2	723.6	733.6	738.1	739.2	738.1
155°	625.3	644.3	662.1	677.8	684.0	690.1	701.2	709.0	712.4	713.5	712.4
157.5°	617.5	633.1	648.7	661.0	666.0	671.1	680.0	686.7	690.1	690.1	690.1
160°	607.4	621.9	633.1	644.3	648.2	652.1	659.9	665.5	667.7	666.6	667.7
162.5°	598.5	609.7	619.7	628.6	632.0	635.3	640.9	645.4	645.4	645.4	645.4
165°	589.6	598.5	606.3	613.0	615.8	618.6	623.1	625.3	625.3	625.3	625.3
167.5°	580.6	587.3	592.9	598.5	600.8	603.0	605.2	607.4	606.3	606.3	606.3
170°	572.8	578.4	581.7	585.1	586.2	587.3	589.6	590.7	590.7	589.6	590.7
172.5°	565.0	568.3	571.7	573.9	574.4	575.0	575.0	577.3	575.0	573.9	575.0
175°	558.3	561.6	561.6	563.9	563.9	563.9	563.9	565.0	562.8	561.6	562.8
177.5°	554.9	556.1	557.2	557.2	557.2	557.2	556.1	557.2	553.8	553.8	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1950.1	1939.6	1944.1	1939.6	1935.1	1930.6	1920.1	1905.1	1893.0	1884.0	1882.5
5°	2100.4	2086.9	2077.8	2073.3	2064.3	2052.3	2032.8	2010.2	1983.2	1972.7	1951.6
7.5°	2238.6	2234.1	2213.1	2210.1	2204.0	2181.5	2148.5	2118.4	2083.8	2055.3	2028.3
10°	2369.3	2358.8	2343.8	2322.7	2319.7	2291.2	2259.6	2217.6	2172.5	2145.4	2097.4
12.5°	2450.4	2438.4	2421.9	2408.4	2400.9	2382.8	2339.3	2297.2	2256.6	2207.0	2165.0
15°	2509.0	2494.0	2464.0	2453.4	2444.4	2420.4	2388.8	2345.3	2291.2	2256.6	2196.5
17.5°	2588.7	2570.6	2540.6	2521.1	2504.5	2467.0	2421.9	2363.3	2312.2	2273.2	2219.1
20°	2680.3	2653.3	2614.2	2588.7	2564.6	2521.1	2458.0	2388.8	2315.2	2267.1	2211.6
22.5°	2832.1	2781.0	2719.4	2683.3	2650.3	2575.1	2500.0	2414.4	2331.7	2259.6	2192.0
25°	2979.3	2928.2	2851.6	2802.0	2750.9	2663.8	2564.6	2445.9	2340.8	2256.6	2168.0
27.5°	3116.0	3063.4	2992.8	2932.7	2883.1	2752.4	2621.7	2488.0	2354.3	2238.6	2148.5
30°	3147.6	3125.0	3070.9	3018.4	2973.3	2853.1	2701.3	2531.6	2370.8	2222.1	2121.4
32.5°	2956.8	3012.3	3025.9	3018.4	2989.8	2904.2	2764.4	2585.7	2394.8	2214.6	2076.3
35°	2560.1	2660.8	2764.4	2820.0	2847.1	2859.1	2776.5	2612.7	2411.4	2202.5	2046.3
37.5°	2122.9	2220.6	2384.3	2467.0	2558.6	2678.8	2711.9	2606.7	2403.9	2193.5	1998.2
40°	1744.3	1869.0	2004.2	2079.3	2159.0	2375.3	2539.1	2527.1	2379.8	2160.5	1960.7
42.5°	1419.8	1497.9	1616.6	1699.2	1796.9	2038.8	2258.1	2366.3	2307.7	2119.9	1912.6
45°	1183.9	1244.0	1328.1	1412.3	1472.4	1691.7	1951.6	2128.9	2184.5	2047.8	1839.0
47.5°	997.6	1042.7	1116.3	1168.9	1233.5	1406.3	1631.6	1881.0	1998.2	1945.6	1760.8
50°	854.9	890.9	949.5	982.6	1039.7	1188.4	1359.7	1621.1	1798.4	1804.4	1657.2
52.5°	730.2	766.2	815.8	844.4	878.9	979.6	1152.4	1373.2	1577.5	1652.7	1538.5
55°	635.5	656.6	697.1	719.7	751.2	848.9	958.5	1146.3	1359.7	1482.9	1410.8
57.5°	548.4	570.9	596.5	614.5	637.0	715.1	814.3	955.5	1167.4	1301.1	1277.1
60°	477.8	491.3	515.3	528.8	549.9	601.0	670.1	811.3	979.6	1105.8	1119.3
62.5°	411.7	423.7	440.2	452.2	465.7	506.3	557.4	658.1	805.3	942.0	960.0
65°	354.6	365.1	374.1	384.6	395.1	420.7	464.2	542.4	656.6	784.3	823.3
67.5°	303.5	306.5	320.0	321.5	327.5	347.1	378.6	441.7	524.3	626.5	677.6
70°	253.9	259.9	262.9	267.4	273.4	287.0	312.5	345.6	407.2	489.8	537.9
72.5°	205.8	207.3	211.8	214.8	220.9	231.4	243.4	268.9	308.0	368.1	411.7
75°	163.8	165.3	168.3	169.8	174.3	177.3	183.3	201.3	228.4	264.4	296.0
77.5°	123.2	126.2	129.2	129.2	130.7	133.7	136.7	142.7	156.3	180.3	207.3
80°	84.1	85.6	85.6	87.1	85.6	90.1	94.7	102.2	108.2	115.7	129.2
82.5°	58.6	58.6	58.6	60.1	60.1	61.6	61.6	63.1	64.6	69.1	75.1
85°	36.1	36.1	37.6	34.6	36.1	37.6	37.6	36.1	37.6	39.1	40.6
87.5°	15.0	15.0	16.5	16.5	16.5	16.5	15.0	16.5	15.0	16.5	16.5
90°	24.6	24.6	24.6	23.5	22.3	21.2	20.1	19.0	17.9	15.6	14.5
92.5°	87.1	90.4	108.3	118.9	129.5	174.2	242.3	359.5	445.5	453.3	314.9
95°	289.2	322.7	402.0	448.9	495.8	633.1	802.8	968.1	989.3	807.3	499.1
97.5°	618.6	676.7	743.6	810.6	877.6	1016.1	1151.2	1209.3	1068.6	740.3	407.6
100°	930.1	1010.5	1087.6	1145.6	1203.7	1318.7	1373.4	1287.4	1008.3	643.2	361.8
102.5°	1259.5	1310.9	1394.6	1429.2	1463.9	1504.0	1448.2	1240.5	902.2	569.5	342.8
105°	1515.2	1552.1	1587.8	1593.9	1600.1	1550.9	1398.0	1130.0	809.5	527.0	340.6
107.5°	1669.3	1674.9	1664.8	1640.2	1615.7	1497.3	1295.2	1025.0	740.3	504.7	348.4
110°	1715.1	1693.9	1643.6	1596.2	1548.7	1391.3	1179.1	937.9	694.5	495.8	360.7

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	1681.6	1641.4	1562.1	1504.0	1446.0	1286.3	1087.6	873.2	667.7	495.8	376.3
115°	1602.3	1548.7	1461.6	1400.8	1339.9	1186.9	1013.9	829.6	649.9	499.1	391.9
117.5°	1508.5	1452.7	1364.5	1307.0	1249.5	1115.5	962.5	800.6	639.8	504.7	409.8
120°	1413.6	1360.0	1277.4	1228.2	1179.1	1056.3	922.3	777.1	633.1	513.6	427.7
122.5°	1329.9	1281.8	1210.4	1165.2	1119.9	1013.9	892.2	757.0	627.5	521.4	447.8
125°	1262.9	1217.1	1154.6	1114.4	1074.2	977.0	863.1	739.2	623.1	530.4	465.6
127.5°	1207.0	1165.7	1108.8	1070.8	1032.8	941.3	833.0	722.4	620.8	540.4	482.4
130°	1155.7	1118.8	1063.0	1026.7	990.4	903.3	805.1	705.7	618.6	549.4	499.1
132.5°	1106.5	1069.7	1013.9	979.2	944.6	867.6	777.1	692.3	618.6	559.4	513.6
135°	1051.8	1015.0	965.9	934.0	902.2	830.7	753.7	682.2	618.6	568.3	527.0
137.5°	993.8	959.2	914.5	886.6	858.7	797.2	732.5	672.2	619.7	577.3	537.1
140°	936.8	907.8	866.5	843.0	819.6	768.2	715.7	665.5	620.8	582.9	547.1
142.5°	882.1	858.7	825.2	805.7	786.1	743.6	701.2	659.9	621.9	586.2	552.7
145°	834.1	815.1	788.3	773.2	758.2	723.6	688.9	654.3	620.8	588.4	558.3
147.5°	795.0	779.4	757.0	745.3	733.6	705.7	676.7	648.7	618.6	589.6	561.6
150°	762.6	749.2	732.5	722.4	712.4	691.2	666.6	642.0	615.2	589.6	565.0
152.5°	733.6	723.6	710.2	702.9	695.6	676.7	655.4	634.2	610.8	588.4	567.2
155°	709.0	701.2	690.1	684.0	677.8	662.1	644.3	625.3	605.2	586.2	568.3
157.5°	686.7	680.0	671.1	666.0	661.0	648.7	633.1	617.5	599.6	584.0	569.5
160°	665.5	659.9	652.1	648.2	644.3	633.1	621.9	607.4	594.0	580.6	569.5
162.5°	645.4	640.9	635.3	632.0	628.6	619.7	609.7	598.5	587.3	577.3	568.3
165°	625.3	623.1	618.6	615.8	613.0	606.3	598.5	589.6	580.6	573.9	567.2
167.5°	607.4	605.2	603.0	600.8	598.5	592.9	587.3	580.6	573.9	568.3	565.0
170°	590.7	589.6	587.3	586.2	585.1	581.7	578.4	572.8	568.3	565.0	562.8
172.5°	577.3	575.0	575.0	574.4	573.9	571.7	568.3	565.0	561.6	560.5	560.5
175°	565.0	563.9	563.9	563.9	563.9	561.6	561.6	558.3	557.2	557.2	558.3
177.5°	557.2	556.1	557.2	557.2	557.2	557.2	556.1	554.9	553.8	553.8	556.1
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1878.0	1869.0	1863.0	1861.5	1852.5	1845.0	1836.0	1834.4	1829.9	1817.9	1810.4
5°	1936.6	1915.6	1911.1	1897.5	1875.0	1858.5	1837.5	1825.4	1811.9	1789.4	1771.3
7.5°	1996.7	1968.2	1947.1	1927.6	1896.0	1866.0	1836.0	1811.9	1787.9	1754.8	1727.8
10°	2055.3	2011.7	1986.2	1957.6	1914.1	1869.0	1826.9	1792.4	1753.3	1714.3	1675.2
12.5°	2109.4	2053.8	2016.2	1975.7	1921.6	1866.0	1811.9	1763.8	1723.3	1670.7	1627.1
15°	2142.4	2080.8	2043.3	2004.2	1923.1	1861.5	1798.4	1736.8	1682.7	1627.1	1586.5
17.5°	2162.0	2092.9	2050.8	2014.7	1932.1	1848.0	1766.8	1700.7	1642.1	1576.0	1521.9
20°	2153.0	2085.4	2046.3	2011.7	1915.6	1831.4	1744.3	1667.7	1594.1	1526.5	1469.4
22.5°	2133.4	2062.8	2019.2	1987.7	1902.1	1802.9	1706.7	1624.1	1547.5	1479.9	1415.3
25°	2091.4	2022.2	1984.7	1945.6	1861.5	1766.8	1669.2	1580.5	1499.4	1427.3	1355.2
27.5°	2053.8	1969.7	1930.6	1896.0	1807.4	1723.3	1627.1	1529.5	1446.8	1371.7	1299.6
30°	2010.2	1915.6	1873.5	1826.9	1747.3	1667.7	1571.5	1481.4	1395.7	1316.1	1247.0
32.5°	1963.7	1854.0	1805.9	1753.3	1672.2	1597.1	1515.9	1427.3	1341.7	1263.5	1191.4
35°	1903.6	1786.4	1730.8	1681.2	1597.1	1521.9	1446.8	1373.2	1287.6	1204.9	1135.8
37.5°	1846.5	1717.3	1658.7	1601.6	1512.9	1440.8	1379.2	1310.1	1227.5	1147.8	1081.7
40°	1781.9	1633.1	1573.0	1520.4	1428.8	1349.2	1293.6	1239.5	1167.4	1090.8	1018.6
42.5°	1723.3	1555.0	1491.9	1437.8	1341.7	1266.5	1214.0	1168.9	1105.8	1035.2	961.5
45°	1642.1	1470.9	1406.3	1349.2	1251.5	1180.9	1126.8	1087.7	1038.2	972.1	906.0
47.5°	1567.0	1389.7	1319.1	1250.0	1161.4	1089.3	1039.7	1009.6	976.6	918.0	850.4
50°	1475.4	1296.6	1224.5	1167.4	1066.7	1005.1	955.5	934.5	904.5	848.9	794.8
52.5°	1376.2	1206.4	1138.8	1069.7	976.6	916.5	872.9	848.9	824.8	784.3	733.2
55°	1260.5	1105.8	1042.7	981.1	887.9	832.3	793.3	767.7	754.2	716.7	679.1
57.5°	1149.3	1003.6	945.0	887.9	806.8	743.7	718.2	695.6	676.1	649.0	617.5
60°	1036.7	904.5	841.4	790.3	719.7	662.6	641.5	619.0	604.0	582.9	560.4
62.5°	907.5	794.8	746.7	698.6	638.5	593.5	569.4	551.4	531.9	518.3	498.8
65°	770.7	691.1	644.5	608.5	551.4	510.8	492.8	480.8	464.2	450.7	435.7
67.5°	643.0	579.9	560.4	521.3	477.8	441.7	428.2	413.2	399.6	392.1	378.6
70°	519.8	474.8	455.2	444.7	396.6	372.6	360.6	354.6	338.0	330.5	321.5
72.5°	402.6	386.1	372.6	359.1	327.5	312.5	299.0	293.0	281.0	274.9	271.9
75°	297.5	287.0	279.4	277.9	264.4	249.4	235.9	232.9	223.9	217.9	214.8
77.5°	208.8	205.8	204.3	205.8	196.8	187.8	184.8	181.8	171.3	169.8	169.8
80°	136.7	144.2	144.2	142.7	139.7	138.2	133.7	130.7	124.7	123.2	124.7
82.5°	84.1	88.6	90.1	93.1	91.6	90.1	87.1	85.6	87.1	84.1	85.6
85°	42.1	45.1	51.1	51.1	52.6	52.6	52.6	51.1	48.1	49.6	48.1
87.5°	16.5	18.0	18.0	18.0	16.5	21.0	22.5	22.5	22.5	19.5	19.5
90°	12.3	11.2	10.0	8.9	6.7	4.5	2.2	1.1	2.2	4.5	6.7
92.5°	187.6	111.7	91.6	71.5	48.0	31.3	20.1	16.7	20.1	31.3	48.0
95°	253.5	134.0	108.8	83.7	59.2	46.9	38.0	36.8	38.0	46.9	59.2
97.5°	218.9	136.2	117.8	99.4	77.0	64.8	58.1	56.9	58.1	64.8	77.0
100°	216.6	151.9	135.2	118.4	97.1	84.9	80.4	78.2	80.4	84.9	97.1
102.5°	226.7	170.8	154.6	138.5	119.5	106.1	102.7	101.6	102.7	106.1	119.5
105°	241.2	192.1	176.4	160.8	142.9	131.8	126.2	126.2	126.2	131.8	142.9
107.5°	261.3	213.3	199.4	185.4	166.4	157.4	151.9	149.6	151.9	157.4	166.4
110°	283.6	237.8	223.3	208.8	192.1	182.0	177.5	175.3	177.5	182.0	192.1

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	304.8	261.3	247.4	233.4	216.6	206.6	203.2	201.0	203.2	206.6	216.6
115°	327.2	285.8	271.8	257.9	241.2	231.1	227.8	225.6	227.8	231.1	241.2
117.5°	349.5	310.4	297.0	283.6	264.6	254.6	251.2	247.9	251.2	254.6	264.6
120°	374.1	335.0	321.0	307.1	288.1	278.0	273.6	270.2	273.6	278.0	288.1
122.5°	397.5	358.4	344.4	330.5	309.3	299.2	295.9	293.7	295.9	299.2	309.3
125°	417.6	380.8	366.2	351.7	330.5	320.5	314.9	312.6	314.9	320.5	330.5
127.5°	437.7	402.0	387.4	372.9	350.6	338.3	331.6	328.3	331.6	338.3	350.6
130°	456.7	422.1	407.6	393.0	369.6	355.1	346.1	342.8	346.1	355.1	369.6
132.5°	474.6	439.9	425.4	410.9	386.3	369.6	358.4	354.0	358.4	369.6	386.3
135°	490.2	455.6	440.5	425.4	402.0	384.1	370.7	366.2	370.7	384.1	402.0
137.5°	501.3	470.1	454.4	438.8	415.4	397.5	385.2	381.9	385.2	397.5	415.4
140°	513.6	481.3	466.2	451.1	429.9	412.0	398.6	395.3	398.6	412.0	429.9
142.5°	521.4	491.3	477.4	463.4	443.3	425.4	413.1	410.9	413.1	425.4	443.3
145°	530.4	501.3	488.5	475.7	455.6	439.9	428.8	426.5	428.8	439.9	455.6
147.5°	536.0	510.3	498.6	486.8	469.0	454.5	444.4	443.3	444.4	454.5	469.0
150°	541.5	517.0	507.5	498.0	482.4	467.9	460.0	457.8	460.0	467.9	482.4
152.5°	547.1	524.8	516.4	508.0	493.5	481.3	474.6	473.4	474.6	481.3	493.5
155°	550.5	531.5	523.7	515.9	504.7	493.5	486.8	486.8	486.8	493.5	504.7
157.5°	553.8	537.1	531.0	524.8	514.7	504.7	499.1	499.1	499.1	504.7	514.7
160°	556.1	541.5	536.5	531.5	522.6	514.7	510.3	511.4	510.3	514.7	522.6
162.5°	558.3	546.0	542.1	538.2	531.5	524.8	520.3	521.4	520.3	524.8	531.5
165°	558.3	549.4	546.0	542.7	538.2	532.6	529.3	531.5	529.3	532.6	538.2
167.5°	558.3	550.5	548.2	546.0	542.7	539.3	537.1	538.2	537.1	539.3	542.7
170°	558.3	552.7	551.0	549.4	547.1	544.9	543.8	544.9	543.8	544.9	547.1
172.5°	557.2	552.7	552.2	551.6	550.5	548.2	547.1	549.4	547.1	548.2	550.5
175°	556.1	552.7	552.7	552.7	552.7	551.6	550.5	552.7	550.5	551.6	552.7
177.5°	554.9	552.7	552.7	552.7	553.8	552.7	552.7	554.9	552.7	552.7	553.8
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1805.9	1799.9	1795.4	1790.9	1771.3	1750.3	1747.3	1742.8	1733.8	1744.3	1739.8
5°	1759.3	1745.8	1738.3	1718.8	1694.7	1676.7	1661.7	1643.6	1636.1	1630.1	1628.6
7.5°	1702.2	1690.2	1676.7	1657.2	1627.1	1597.1	1574.5	1556.5	1541.5	1534.0	1534.0
10°	1646.6	1631.6	1613.6	1580.5	1552.0	1514.4	1490.4	1472.4	1451.3	1439.3	1428.8
12.5°	1589.6	1573.0	1556.5	1514.4	1481.4	1442.3	1407.8	1385.2	1374.7	1361.2	1343.2
15°	1532.5	1506.9	1490.4	1448.3	1406.3	1367.2	1344.7	1320.6	1296.6	1283.1	1277.1
17.5°	1472.4	1454.3	1427.3	1382.2	1335.6	1301.1	1268.0	1245.5	1217.0	1203.4	1189.9
20°	1418.3	1391.2	1364.2	1319.1	1274.0	1227.5	1194.4	1167.4	1149.3	1138.8	1126.8
22.5°	1353.7	1328.1	1305.6	1257.5	1207.9	1164.4	1128.3	1111.8	1093.8	1077.2	1065.2
25°	1298.1	1272.5	1250.0	1197.4	1143.3	1102.8	1075.7	1054.7	1035.2	1027.7	1015.6
27.5°	1239.5	1215.5	1185.4	1132.8	1084.7	1050.2	1021.6	1002.1	987.1	972.1	963.0
30°	1183.9	1156.9	1129.8	1072.7	1033.7	999.1	972.1	948.0	936.0	928.5	913.5
32.5°	1129.8	1095.3	1072.7	1020.1	982.6	949.5	927.0	906.0	890.9	877.4	865.4
35°	1071.2	1033.7	1011.1	967.6	928.5	895.4	875.9	860.9	842.9	830.8	824.8
37.5°	1015.6	984.1	961.5	916.5	877.4	850.4	829.3	809.8	802.3	785.8	782.8
40°	955.5	928.5	907.5	863.9	827.8	806.8	784.3	766.2	752.7	745.2	734.7
42.5°	901.4	878.9	856.4	815.8	781.3	755.7	739.2	722.7	710.6	698.6	691.1
45°	851.9	827.8	806.8	767.7	733.2	710.6	694.1	674.6	671.6	655.1	647.5
47.5°	799.3	778.3	760.2	719.7	688.1	665.6	646.0	632.5	619.0	613.0	602.5
50°	748.2	727.2	706.1	670.1	641.5	619.0	599.5	584.4	576.9	567.9	558.9
52.5°	692.6	676.1	659.6	622.0	593.5	573.9	557.4	537.9	530.4	522.8	516.8
55°	646.0	622.0	604.0	572.4	546.9	525.8	507.8	492.8	485.3	479.3	471.8
57.5°	582.9	567.9	552.9	524.3	500.3	479.3	461.2	449.2	440.2	435.7	437.2
60°	528.8	512.3	503.3	473.3	449.2	432.7	416.2	404.1	395.1	390.6	389.1
62.5°	471.8	459.7	443.2	422.2	398.1	383.1	371.1	362.1	347.1	345.6	341.0
65°	416.2	407.2	392.1	372.6	353.1	339.5	326.0	314.0	308.0	300.5	296.0
67.5°	362.1	353.1	339.5	323.0	309.5	296.0	284.0	271.9	261.4	255.4	252.4
70°	309.5	302.0	293.0	273.4	256.9	246.4	237.4	229.9	219.4	216.3	214.8
72.5°	258.4	250.9	246.4	229.9	214.8	205.8	196.8	189.3	184.8	183.3	178.8
75°	211.8	204.3	198.3	183.3	174.3	168.3	159.3	156.3	151.7	150.2	148.7
77.5°	165.3	157.8	156.3	145.7	135.2	132.2	129.2	123.2	123.2	123.2	120.2
80°	118.7	117.2	115.7	105.2	100.7	97.7	96.2	91.6	88.6	85.6	84.1
82.5°	79.6	78.1	76.6	72.1	67.6	66.1	64.6	61.6	61.6	63.1	60.1
85°	48.1	45.1	43.6	42.1	39.1	39.1	40.6	39.1	39.1	39.1	37.6
87.5°	18.0	18.0	18.0	18.0	19.5	16.5	18.0	18.0	16.5	16.5	15.0
90°	8.9	10.0	11.2	12.3	14.5	15.6	17.9	19.0	20.1	21.2	22.3
92.5°	71.5	91.6	111.7	187.6	314.9	453.3	445.5	359.5	242.3	174.2	129.5
95°	83.7	108.8	134.0	253.5	499.1	807.3	989.3	968.1	802.8	633.1	495.8
97.5°	99.4	117.8	136.2	218.9	407.6	740.3	1068.6	1209.3	1151.2	1016.1	877.6
100°	118.4	135.2	151.9	216.6	361.8	643.2	1008.3	1287.4	1373.4	1318.7	1203.7
102.5°	138.5	154.6	170.8	226.7	342.8	569.5	902.2	1240.5	1448.2	1504.0	1463.9
105°	160.8	176.4	192.1	241.2	340.6	527.0	809.5	1130.0	1398.0	1550.9	1600.1
107.5°	185.4	199.4	213.3	261.3	348.4	504.7	740.3	1025.0	1295.2	1497.3	1615.7
110°	208.8	223.3	237.8	283.6	360.7	495.8	694.5	937.9	1179.1	1391.3	1548.7

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	233.4	247.4	261.3	304.8	376.3	495.8	667.7	873.2	1087.6	1286.3	1446.0
115°	257.9	271.8	285.8	327.2	391.9	499.1	649.9	829.6	1013.9	1186.9	1339.9
117.5°	283.6	297.0	310.4	349.5	409.8	504.7	639.8	800.6	962.5	1115.5	1249.5
120°	307.1	321.0	335.0	374.1	427.7	513.6	633.1	777.1	922.3	1056.3	1179.1
122.5°	330.5	344.4	358.4	397.5	447.8	521.4	627.5	757.0	892.2	1013.9	1119.9
125°	351.7	366.2	380.8	417.6	465.6	530.4	623.1	739.2	863.1	977.0	1074.2
127.5°	372.9	387.4	402.0	437.7	482.4	540.4	620.8	722.4	833.0	941.3	1032.8
130°	393.0	407.6	422.1	456.7	499.1	549.4	618.6	705.7	805.1	903.3	990.4
132.5°	410.9	425.4	439.9	474.6	513.6	559.4	618.6	692.3	777.1	867.6	944.6
135°	425.4	440.5	455.6	490.2	527.0	568.3	618.6	682.2	753.7	830.7	902.2
137.5°	438.8	454.4	470.1	501.3	537.1	577.3	619.7	672.2	732.5	797.2	858.7
140°	451.1	466.2	481.3	513.6	547.1	582.9	620.8	665.5	715.7	768.2	819.6
142.5°	463.4	477.4	491.3	521.4	552.7	586.2	621.9	659.9	701.2	743.6	786.1
145°	475.7	488.5	501.3	530.4	558.3	588.4	620.8	654.3	688.9	723.6	758.2
147.5°	486.8	498.6	510.3	536.0	561.6	589.6	618.6	648.7	676.7	705.7	733.6
150°	498.0	507.5	517.0	541.5	565.0	589.6	615.2	642.0	666.6	691.2	712.4
152.5°	508.0	516.4	524.8	547.1	567.2	588.4	610.8	634.2	655.4	676.7	695.6
155°	515.9	523.7	531.5	550.5	568.3	586.2	605.2	625.3	644.3	662.1	677.8
157.5°	524.8	531.0	537.1	553.8	569.5	584.0	599.6	617.5	633.1	648.7	661.0
160°	531.5	536.5	541.5	556.1	569.5	580.6	594.0	607.4	621.9	633.1	644.3
162.5°	538.2	542.1	546.0	558.3	568.3	577.3	587.3	598.5	609.7	619.7	628.6
165°	542.7	546.0	549.4	558.3	567.2	573.9	580.6	589.6	598.5	606.3	613.0
167.5°	546.0	548.2	550.5	558.3	565.0	568.3	573.9	580.6	587.3	592.9	598.5
170°	549.4	551.0	552.7	558.3	562.8	565.0	568.3	572.8	578.4	581.7	585.1
172.5°	551.6	552.2	552.7	557.2	560.5	560.5	561.6	565.0	568.3	571.7	573.9
175°	552.7	552.7	552.7	556.1	558.3	557.2	557.2	558.3	561.6	561.6	563.9
177.5°	552.7	552.7	552.7	554.9	556.1	553.8	553.8	554.9	556.1	557.2	557.2
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1732.3	1735.3	1727.8	1724.8	1718.8	1726.3	1727.8	1726.3	1739.8	1733.8	1736.8
5°	1631.6	1625.6	1621.1	1610.6	1610.6	1612.1	1616.6	1609.1	1613.6	1624.1	1622.6
7.5°	1520.4	1517.4	1518.9	1506.9	1497.9	1500.9	1497.9	1511.4	1518.9	1515.9	1521.9
10°	1419.8	1425.8	1412.3	1406.3	1400.3	1406.3	1404.8	1407.8	1416.8	1422.8	1433.3
12.5°	1338.7	1337.1	1329.6	1323.6	1313.1	1316.1	1325.1	1322.1	1323.6	1337.1	1335.6
15°	1262.0	1253.0	1247.0	1233.5	1236.5	1226.0	1235.0	1245.5	1250.0	1262.0	1269.5
17.5°	1185.4	1183.9	1176.4	1174.9	1158.4	1153.9	1162.9	1165.9	1170.4	1176.4	1186.9
20°	1120.8	1119.3	1108.8	1105.8	1092.3	1101.3	1098.3	1104.3	1107.3	1119.3	1123.8
22.5°	1062.2	1054.7	1051.7	1047.2	1042.7	1041.2	1047.2	1045.7	1056.2	1060.7	1062.2
25°	1008.1	1002.1	1000.6	993.1	990.1	985.6	990.1	994.6	1006.6	1011.1	1017.1
27.5°	958.5	954.0	951.0	945.0	940.5	940.5	943.5	949.5	954.0	957.0	960.0
30°	913.5	910.5	901.4	898.4	893.9	893.9	893.9	896.9	904.5	913.5	918.0
32.5°	866.9	860.9	854.9	854.9	850.4	850.4	851.9	854.9	862.4	863.9	871.4
35°	821.8	815.8	811.3	808.3	809.8	803.8	806.8	811.3	820.3	823.3	827.8
37.5°	778.3	776.7	767.7	763.2	766.2	766.2	764.7	767.7	773.7	779.8	782.8
40°	730.2	727.2	727.2	722.7	724.2	718.2	722.7	725.7	728.7	734.7	739.2
42.5°	688.1	685.1	679.1	680.6	676.1	676.1	679.1	680.6	685.1	692.6	695.6
45°	643.0	643.0	640.0	635.5	637.0	632.5	635.5	637.0	643.0	650.5	647.5
47.5°	599.5	598.0	598.0	592.0	595.0	590.4	595.0	596.5	599.5	604.0	602.5
50°	557.4	552.9	554.4	552.9	551.4	551.4	554.4	554.4	557.4	557.4	561.9
52.5°	513.8	513.8	510.8	512.3	515.3	512.3	516.8	512.3	515.3	516.8	519.8
55°	474.8	471.8	473.3	471.8	477.8	473.3	477.8	474.8	477.8	476.3	479.3
57.5°	432.7	428.2	429.7	428.2	432.7	431.2	435.7	431.2	432.7	434.2	438.7
60°	384.6	384.6	384.6	381.6	386.1	386.1	384.6	384.6	390.6	393.6	392.1
62.5°	339.5	338.0	333.5	332.0	333.5	330.5	336.5	335.0	338.0	341.0	344.1
65°	290.0	287.0	285.5	282.5	282.5	281.0	282.5	288.5	290.0	291.5	299.0
67.5°	249.4	247.9	246.4	241.9	241.9	244.9	244.9	244.9	253.9	249.4	255.4
70°	213.3	210.3	207.3	205.8	205.8	207.3	208.8	210.3	208.8	214.8	216.3
72.5°	178.8	180.3	177.3	177.3	177.3	175.8	175.8	178.8	180.3	178.8	180.3
75°	148.7	148.7	147.2	148.7	148.7	147.2	147.2	150.2	150.2	148.7	153.2
77.5°	120.2	118.7	115.7	112.7	114.2	112.7	114.2	112.7	117.2	121.7	118.7
80°	84.1	82.6	82.6	82.6	84.1	82.6	85.6	82.6	84.1	84.1	85.6
82.5°	60.1	61.6	61.6	60.1	61.6	60.1	61.6	61.6	61.6	60.1	61.6
85°	39.1	39.1	39.1	39.1	37.6	39.1	39.1	39.1	40.6	39.1	40.6
87.5°	16.5	16.5	16.5	16.5	16.5	16.5	16.5	16.5	18.0	16.5	18.0
90°	23.5	24.6	24.6	24.6	25.7	25.7	25.7	24.6	24.6	24.6	23.5
92.5°	118.9	108.3	90.4	87.1	84.9	82.6	84.9	87.1	90.4	108.3	118.9
95°	448.9	402.0	322.7	289.2	280.3	262.4	280.3	289.2	322.7	402.0	448.9
97.5°	810.6	743.6	676.7	618.6	588.4	575.0	588.4	618.6	676.7	743.6	810.6
100°	1145.6	1087.6	1010.5	930.1	888.8	870.9	888.8	930.1	1010.5	1087.6	1145.6
102.5°	1429.2	1394.6	1310.9	1259.5	1213.7	1201.5	1213.7	1259.5	1310.9	1394.6	1429.2
105°	1593.9	1587.8	1552.1	1515.2	1492.9	1479.5	1492.9	1515.2	1552.1	1587.8	1593.9
107.5°	1640.2	1664.8	1674.9	1669.3	1658.1	1647.0	1658.1	1669.3	1674.9	1664.8	1640.2
110°	1596.2	1643.6	1693.9	1715.1	1722.9	1722.9	1722.9	1715.1	1693.9	1643.6	1596.2

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	1504.0	1562.1	1641.4	1681.6	1703.9	1714.0	1703.9	1681.6	1641.4	1562.1	1504.0
115°	1400.8	1461.6	1548.7	1602.3	1633.6	1648.1	1633.6	1602.3	1548.7	1461.6	1400.8
117.5°	1307.0	1364.5	1452.7	1508.5	1539.8	1548.7	1539.8	1508.5	1452.7	1364.5	1307.0
120°	1228.2	1277.4	1360.0	1413.6	1443.8	1452.7	1443.8	1413.6	1360.0	1277.4	1228.2
122.5°	1165.2	1210.4	1281.8	1329.9	1360.0	1367.8	1360.0	1329.9	1281.8	1210.4	1165.2
125°	1114.4	1154.6	1217.1	1262.9	1287.4	1298.6	1287.4	1262.9	1217.1	1154.6	1114.4
127.5°	1070.8	1108.8	1165.7	1207.0	1230.5	1234.9	1230.5	1207.0	1165.7	1108.8	1070.8
130°	1026.7	1063.0	1118.8	1155.7	1178.0	1184.7	1178.0	1155.7	1118.8	1063.0	1026.7
132.5°	979.2	1013.9	1069.7	1106.5	1126.6	1134.5	1126.6	1106.5	1069.7	1013.9	979.2
135°	934.0	965.9	1015.0	1051.8	1071.9	1078.6	1071.9	1051.8	1015.0	965.9	934.0
137.5°	886.6	914.5	959.2	993.8	1012.7	1020.6	1012.7	993.8	959.2	914.5	886.6
140°	843.0	866.5	907.8	936.8	953.6	959.2	953.6	936.8	907.8	866.5	843.0
142.5°	805.7	825.2	858.7	882.1	897.7	902.2	897.7	882.1	858.7	825.2	805.7
145°	773.2	788.3	815.1	834.1	846.4	850.8	846.4	834.1	815.1	788.3	773.2
147.5°	745.3	757.0	779.4	795.0	802.8	805.1	802.8	795.0	779.4	757.0	745.3
150°	722.4	732.5	749.2	762.6	767.1	768.2	767.1	762.6	749.2	732.5	722.4
152.5°	702.9	710.2	723.6	733.6	738.1	739.2	738.1	733.6	723.6	710.2	702.9
155°	684.0	690.1	701.2	709.0	712.4	713.5	712.4	709.0	701.2	690.1	684.0
157.5°	666.0	671.1	680.0	686.7	690.1	690.1	690.1	686.7	680.0	671.1	666.0
160°	648.2	652.1	659.9	665.5	667.7	666.6	667.7	665.5	659.9	652.1	648.2
162.5°	632.0	635.3	640.9	645.4	645.4	645.4	645.4	645.4	640.9	635.3	632.0
165°	615.8	618.6	623.1	625.3	625.3	625.3	625.3	625.3	623.1	618.6	615.8
167.5°	600.8	603.0	605.2	607.4	606.3	606.3	606.3	607.4	605.2	603.0	600.8
170°	586.2	587.3	589.6	590.7	590.7	589.6	590.7	590.7	589.6	587.3	586.2
172.5°	574.4	575.0	575.0	577.3	575.0	573.9	575.0	577.3	575.0	575.0	574.4
175°	563.9	563.9	563.9	565.0	562.8	561.6	562.8	565.0	563.9	563.9	563.9
177.5°	557.2	557.2	556.1	557.2	553.8	553.8	553.8	557.2	556.1	557.2	557.2
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9	1829.9
2.5°	1730.8	1738.3	1732.3	1727.8	1739.8	1745.8	1745.8	1756.3	1766.8	1775.9	1777.4
5°	1624.1	1636.1	1639.1	1637.6	1655.7	1664.7	1684.2	1694.7	1709.7	1720.3	1732.3
7.5°	1526.5	1543.0	1544.5	1547.5	1574.5	1589.6	1606.1	1633.1	1654.2	1669.2	1682.7
10°	1428.8	1439.3	1449.8	1463.4	1490.4	1515.9	1540.0	1568.5	1595.6	1610.6	1630.1
12.5°	1355.2	1362.7	1374.7	1383.7	1412.3	1434.8	1466.4	1505.4	1544.5	1556.5	1580.5
15°	1278.6	1283.1	1307.1	1316.1	1340.2	1377.7	1397.2	1434.8	1476.9	1499.4	1526.5
17.5°	1189.9	1217.0	1232.0	1242.5	1272.5	1302.6	1334.1	1373.2	1427.3	1448.3	1467.9
20°	1126.8	1146.3	1162.9	1176.4	1203.4	1248.5	1277.1	1308.6	1359.7	1383.7	1412.3
22.5°	1071.2	1087.7	1102.8	1117.8	1135.8	1176.4	1209.4	1253.0	1304.1	1326.6	1359.7
25°	1018.6	1035.2	1044.2	1062.2	1086.2	1114.8	1153.9	1192.9	1244.0	1269.5	1301.1
27.5°	967.6	984.1	1000.6	1015.6	1032.2	1059.2	1086.2	1135.8	1188.4	1218.5	1245.5
30°	924.0	931.5	946.5	963.0	979.6	1005.1	1036.7	1071.2	1131.3	1158.4	1191.4
32.5°	875.9	889.4	899.9	912.0	933.0	954.0	982.6	1026.1	1074.2	1099.8	1135.8
35°	830.8	842.9	850.4	871.4	884.9	907.5	936.0	975.1	1015.6	1044.2	1075.7
37.5°	787.3	799.3	808.3	820.3	838.3	857.9	887.9	916.5	964.6	988.6	1024.6
40°	742.2	752.7	763.2	776.7	793.3	817.3	835.3	871.4	910.5	937.5	964.6
42.5°	698.6	704.6	716.7	731.7	748.2	769.2	794.8	823.3	862.4	886.4	910.5
45°	652.0	662.6	676.1	686.6	701.6	722.7	745.2	770.7	809.8	833.8	859.4
47.5°	608.5	616.0	625.0	641.5	661.1	676.1	700.1	724.2	760.2	782.8	806.8
50°	563.4	570.9	584.4	595.0	610.0	629.5	652.0	677.6	712.1	727.2	751.2
52.5°	521.3	524.3	537.9	548.4	563.4	585.9	604.0	626.5	659.6	676.1	700.1
55°	479.3	482.3	489.8	500.3	516.8	534.9	554.4	579.9	608.5	623.5	646.0
57.5°	435.7	438.7	446.2	453.7	470.3	486.8	509.3	530.4	558.9	572.4	593.5
60°	392.1	392.1	399.6	410.2	422.2	437.2	456.7	482.3	503.3	519.8	534.9
62.5°	345.6	350.1	354.6	362.1	375.6	393.6	410.2	428.2	453.7	465.7	479.3
65°	299.0	303.5	312.5	320.0	330.5	342.6	363.6	378.6	398.1	411.7	423.7
67.5°	258.4	262.9	268.9	277.9	285.5	299.0	314.0	329.0	350.1	359.1	368.1
70°	216.3	220.9	225.4	237.4	244.9	255.4	265.9	281.0	299.0	305.0	312.5
72.5°	183.3	184.8	190.8	193.8	204.3	213.3	225.4	234.4	247.9	255.4	261.4
75°	154.7	154.7	156.3	159.3	165.3	171.3	180.3	189.3	201.3	205.8	213.3
77.5°	121.7	126.2	124.7	127.7	130.7	133.7	141.2	147.2	159.3	162.3	165.3
80°	87.1	88.6	93.1	97.7	97.7	102.2	106.7	108.2	115.7	120.2	120.2
82.5°	63.1	64.6	63.1	64.6	66.1	67.6	72.1	78.1	78.1	79.6	82.6
85°	39.1	39.1	40.6	42.1	42.1	40.6	43.6	42.1	43.6	46.6	46.6
87.5°	19.5	18.0	18.0	18.0	18.0	18.0	19.5	18.0	19.5	19.5	19.5
90°	22.3	21.2	20.1	19.0	17.9	15.6	14.5	12.3	11.2	10.0	8.9
92.5°	129.5	174.2	242.3	359.5	445.5	453.3	314.9	187.6	111.7	91.6	71.5
95°	495.8	633.1	802.8	968.1	989.3	807.3	499.1	253.5	134.0	108.8	83.7
97.5°	877.6	1016.1	1151.2	1209.3	1068.6	740.3	407.6	218.9	136.2	117.8	99.4
100°	1203.7	1318.7	1373.4	1287.4	1008.3	643.2	361.8	216.6	151.9	135.2	118.4
102.5°	1463.9	1504.0	1448.2	1240.5	902.2	569.5	342.8	226.7	170.8	154.6	138.5
105°	1600.1	1550.9	1398.0	1130.0	809.5	527.0	340.6	241.2	192.1	176.4	160.8
107.5°	1615.7	1497.3	1295.2	1025.0	740.3	504.7	348.4	261.3	213.3	199.4	185.4
110°	1548.7	1391.3	1179.1	937.9	694.5	495.8	360.7	283.6	237.8	223.3	208.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	1446.0	1286.3	1087.6	873.2	667.7	495.8	376.3	304.8	261.3	247.4	233.4
115°	1339.9	1186.9	1013.9	829.6	649.9	499.1	391.9	327.2	285.8	271.8	257.9
117.5°	1249.5	1115.5	962.5	800.6	639.8	504.7	409.8	349.5	310.4	297.0	283.6
120°	1179.1	1056.3	922.3	777.1	633.1	513.6	427.7	374.1	335.0	321.0	307.1
122.5°	1119.9	1013.9	892.2	757.0	627.5	521.4	447.8	397.5	358.4	344.4	330.5
125°	1074.2	977.0	863.1	739.2	623.1	530.4	465.6	417.6	380.8	366.2	351.7
127.5°	1032.8	941.3	833.0	722.4	620.8	540.4	482.4	437.7	402.0	387.4	372.9
130°	990.4	903.3	805.1	705.7	618.6	549.4	499.1	456.7	422.1	407.6	393.0
132.5°	944.6	867.6	777.1	692.3	618.6	559.4	513.6	474.6	439.9	425.4	410.9
135°	902.2	830.7	753.7	682.2	618.6	568.3	527.0	490.2	455.6	440.5	425.4
137.5°	858.7	797.2	732.5	672.2	619.7	577.3	537.1	501.3	470.1	454.4	438.8
140°	819.6	768.2	715.7	665.5	620.8	582.9	547.1	513.6	481.3	466.2	451.1
142.5°	786.1	743.6	701.2	659.9	621.9	586.2	552.7	521.4	491.3	477.4	463.4
145°	758.2	723.6	688.9	654.3	620.8	588.4	558.3	530.4	501.3	488.5	475.7
147.5°	733.6	705.7	676.7	648.7	618.6	589.6	561.6	536.0	510.3	498.6	486.8
150°	712.4	691.2	666.6	642.0	615.2	589.6	565.0	541.5	517.0	507.5	498.0
152.5°	695.6	676.7	655.4	634.2	610.8	588.4	567.2	547.1	524.8	516.4	508.0
155°	677.8	662.1	644.3	625.3	605.2	586.2	568.3	550.5	531.5	523.7	515.9
157.5°	661.0	648.7	633.1	617.5	599.6	584.0	569.5	553.8	537.1	531.0	524.8
160°	644.3	633.1	621.9	607.4	594.0	580.6	569.5	556.1	541.5	536.5	531.5
162.5°	628.6	619.7	609.7	598.5	587.3	577.3	568.3	558.3	546.0	542.1	538.2
165°	613.0	606.3	598.5	589.6	580.6	573.9	567.2	558.3	549.4	546.0	542.7
167.5°	598.5	592.9	587.3	580.6	573.9	568.3	565.0	558.3	550.5	548.2	546.0
170°	585.1	581.7	578.4	572.8	568.3	565.0	562.8	558.3	552.7	551.0	549.4
172.5°	573.9	571.7	568.3	565.0	561.6	560.5	560.5	557.2	552.7	552.2	551.6
175°	563.9	561.6	561.6	558.3	557.2	557.2	558.3	556.1	552.7	552.7	552.7
177.5°	557.2	557.2	556.1	554.9	553.8	553.8	556.1	554.9	552.7	552.7	552.7
180°	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8	553.8

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1829.9	1829.9	1829.9	1829.9
2.5°	1787.9	1801.4	1814.9	1831.4
5°	1751.8	1775.9	1801.4	1825.4
7.5°	1712.8	1747.3	1780.4	1814.9
10°	1669.2	1712.8	1750.3	1798.4
12.5°	1621.1	1667.7	1720.3	1774.4
15°	1573.0	1631.6	1687.2	1748.8
17.5°	1528.0	1583.5	1645.1	1718.8
20°	1473.9	1535.5	1604.6	1682.7
22.5°	1416.8	1484.4	1559.5	1643.6
25°	1368.7	1437.8	1509.9	1598.6
27.5°	1316.1	1388.2	1458.8	1553.5
30°	1256.0	1334.1	1406.3	1503.9
32.5°	1198.9	1277.1	1356.7	1448.3
35°	1143.3	1220.0	1299.6	1392.7
37.5°	1090.8	1159.9	1238.0	1322.1
40°	1041.2	1104.3	1173.4	1250.0
42.5°	978.1	1051.7	1116.3	1171.9
45°	924.0	984.1	1044.2	1089.3
47.5°	860.9	921.0	972.1	1008.1
50°	808.3	856.4	898.4	930.0
52.5°	745.2	790.3	824.8	848.9
55°	683.6	722.7	752.7	769.2
57.5°	628.0	653.6	676.1	691.1
60°	566.4	585.9	605.5	622.0
62.5°	500.3	521.3	531.9	549.9
65°	441.7	455.2	471.8	477.8
67.5°	384.6	392.1	402.6	414.7
70°	324.5	329.0	339.5	356.1
72.5°	271.9	276.4	284.0	290.0
75°	216.3	220.9	226.9	232.9
77.5°	169.8	171.3	174.3	180.3
80°	123.2	127.7	130.7	132.2
82.5°	85.6	87.1	87.1	88.6
85°	54.1	51.1	51.1	52.6
87.5°	19.5	22.5	22.5	25.5
90°	6.7	4.5	2.2	1.1
92.5°	48.0	31.3	20.1	16.7
95°	59.2	46.9	38.0	36.8
97.5°	77.0	64.8	58.1	56.9
100°	97.1	84.9	80.4	78.2
102.5°	119.5	106.1	102.7	101.6
105°	142.9	131.8	126.2	126.2
107.5°	166.4	157.4	151.9	149.6
110°	192.1	182.0	177.5	175.3

TEST NUMBER: P1028618

CATALOG NUMBER: S125RDIP-B1270D1270UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	216.6	206.6	203.2	201.0
115°	241.2	231.1	227.8	225.6
117.5°	264.6	254.6	251.2	247.9
120°	288.1	278.0	273.6	270.2
122.5°	309.3	299.2	295.9	293.7
125°	330.5	320.5	314.9	312.6
127.5°	350.6	338.3	331.6	328.3
130°	369.6	355.1	346.1	342.8
132.5°	386.3	369.6	358.4	354.0
135°	402.0	384.1	370.7	366.2
137.5°	415.4	397.5	385.2	381.9
140°	429.9	412.0	398.6	395.3
142.5°	443.3	425.4	413.1	410.9
145°	455.6	439.9	428.8	426.5
147.5°	469.0	454.5	444.4	443.3
150°	482.4	467.9	460.0	457.8
152.5°	493.5	481.3	474.6	473.4
155°	504.7	493.5	486.8	486.8
157.5°	514.7	504.7	499.1	499.1
160°	522.6	514.7	510.3	511.4
162.5°	531.5	524.8	520.3	521.4
165°	538.2	532.6	529.3	531.5
167.5°	542.7	539.3	537.1	538.2
170°	547.1	544.9	543.8	544.9
172.5°	550.5	548.2	547.1	549.4
175°	552.7	551.6	550.5	552.7
177.5°	553.8	552.7	552.7	554.9
180°	553.8	553.8	553.8	553.8

(END OF REPORT)