

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1028635

Luminaire Tested: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1028635
REPORT IS A COMBINATION OF REPORTS P1005222 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1
Description: Define 5 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6233.0 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.4 / 1.47
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot





TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	114	114	114	114	109	109	109	109	100	100	100	91	91	91	83	83	83	79						
1	105	101	97	94	100	97	93	90	89	86	84	81	79	78	75	73	72	68						
2	96	89	83	78	92	85	80	75	79	74	70	72	69	66	67	64	61	58						
3	88	79	71	65	84	76	69	64	70	64	60	64	60	56	59	56	53	50						
4	81	70	62	56	77	67	60	54	62	56	52	58	53	49	53	49	46	43						
5	75	63	55	48	71	61	53	47	56	50	45	52	47	43	48	44	40	38						
6	69	57	48	42	66	55	47	42	51	44	40	47	42	38	44	39	36	33						
7	64	51	43	38	61	50	42	37	46	40	35	43	38	34	40	36	32	30						
8	60	47	39	34	57	45	38	33	42	36	31	40	34	30	37	32	29	27						
9	56	43	35	30	53	42	34	30	39	33	28	37	31	27	34	30	26	24						
10	52	40	32	27	50	38	31	27	36	30	26	34	29	25	32	27	24	22						

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	12247	12247	12247	12247
5°	12236	13802	12236	10608
10°	12167	15511	12127	9171
15°	12035	16409	11953	7984
20°	11876	17714	11770	7218
25°	11668	20050	11536	6550
30°	11456	21312	11284	6073
35°	11182	17527	11026	5629
40°	10695	11903	10606	5229
45°	10057	8556	10044	4835
50°	9402	6580	9448	4472
55°	8666	5350	8649	4120
60°	7980	4385	7941	3659
65°	7180	3654	7226	2946
70°	6519	2932	6493	2453
75°	5507	2222	5507	2016
80°	4463	1355	4411	1355
85°	3139	713	3053	806

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 135°

Vertical Angle: 45°

Luminance: 17432 cd/sqm

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	2.9
10°-20°	537.4	8.6
20°-30°	852.0	13.7
30°-40°	1029.6	16.5
40°-50°	916.7	14.7
50°-60°	702.9	11.3
60°-70°	456.5	7.3
70°-80°	221.6	3.6
80°-90°	52.8	0.8
90°-100°	30.5	0.5
100°-110°	90.6	1.5
110°-120°	153.7	2.5
120°-130°	202.3	3.2
130°-140°	226.7	3.6
140°-150°	222.2	3.6
150°-160°	186.7	3.0
160°-170°	124.1	2.0
170°-180°	43.4	0.7
0°-30°	1572.7	25.2
0°-40°	2602.3	41.7
0°-60°	4221.8	67.7
0°-90°	4952.7	79.5
90°-120°	274.8	4.4
90°-150°	926.1	14.9
90°-180°	1280.0	20.5
0°-180°	6233.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1911	1911	1911	1911	1911	
5°	1907	2191	1907	1684	1907	181
15°	1827	2632	1814	1280	1827	515
25°	1670	3151	1651	1029	1670	770
35°	1455	2614	1434	840	1455	906
45°	1138	1169	1136	661	1138	878
55°	804	642	802	494	804	720
65°	499	364	502	294	499	499
75°	243	170	243	154	243	261
85°	55	36	53	41	55	63
90°	0	9	0	9	0	5
95°	23	31	23	31	23	24
105°	81	88	81	88	81	87
115°	154	155	154	155	154	152
125°	224	226	224	226	224	201
135°	292	293	292	293	292	225
145°	354	355	354	355	354	221
155°	405	405	405	405	405	186
165°	440	439	440	439	440	124
175°	458	456	458	456	458	43
180°	459	459	459	459	459	

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1913.0	1928.6	1933.4	1945.9	1960.0	1963.2	1971.0	1982.0	1988.3	1986.7	1986.7
5°	1906.7	1933.4	1952.2	1974.2	2000.8	2011.8	2021.2	2044.8	2063.6	2074.6	2093.4
7.5°	1895.7	1934.9	1966.3	1999.3	2040.1	2058.9	2079.3	2112.3	2146.8	2168.7	2189.1
10°	1878.4	1928.6	1972.6	2021.2	2076.2	2104.4	2129.5	2179.7	2222.1	2250.3	2297.4
12.5°	1853.3	1916.1	1977.3	2041.6	2110.7	2140.5	2175.0	2229.9	2289.6	2330.4	2369.6
15°	1826.6	1902.0	1967.9	2044.8	2127.9	2173.5	2217.4	2275.5	2328.8	2374.3	2419.8
17.5°	1795.3	1875.3	1956.9	2044.8	2138.9	2184.4	2222.1	2291.1	2347.6	2393.2	2434.0
20°	1757.6	1847.0	1939.6	2036.9	2132.7	2175.0	2211.1	2286.4	2336.7	2385.3	2443.4
22.5°	1716.8	1814.1	1913.0	2008.7	2102.8	2148.3	2190.7	2256.6	2311.5	2377.5	2452.8
25°	1669.7	1776.4	1876.9	1972.6	2062.0	2104.4	2142.1	2214.3	2291.1	2374.3	2459.1
27.5°	1622.6	1726.2	1823.5	1911.4	2008.7	2047.9	2085.6	2176.6	2267.6	2355.5	2471.6
30°	1570.8	1676.0	1760.7	1842.3	1936.5	1977.3	2024.4	2127.9	2231.5	2350.8	2492.0
32.5°	1512.8	1608.5	1687.0	1771.7	1856.5	1906.7	1966.3	2079.3	2198.6	2341.4	2521.8
35°	1454.7	1531.6	1603.8	1683.8	1785.8	1839.2	1897.3	2016.5	2165.6	2336.7	2546.9
37.5°	1381.0	1454.7	1511.2	1592.8	1698.0	1760.7	1818.8	1956.9	2126.4	2325.7	2545.4
40°	1305.6	1368.4	1421.8	1506.5	1621.1	1679.1	1741.9	1892.6	2085.6	2294.3	2507.7
42.5°	1224.0	1277.4	1335.5	1417.1	1528.5	1585.0	1657.2	1832.9	2029.1	2250.3	2410.4
45°	1137.7	1189.5	1238.2	1322.9	1434.3	1495.5	1574.0	1754.5	1960.0	2157.8	2253.5
47.5°	1053.0	1098.5	1150.3	1224.0	1337.0	1404.5	1484.5	1677.6	1867.4	2033.8	2041.6
50°	971.4	1007.5	1051.4	1126.7	1244.4	1308.8	1392.0	1572.4	1757.6	1872.2	1795.3
52.5°	886.6	919.6	965.1	1031.0	1140.9	1216.2	1288.4	1468.8	1624.2	1701.1	1559.9
55°	803.5	831.7	878.8	952.6	1048.3	1106.3	1180.1	1348.0	1484.5	1486.1	1332.3
57.5°	721.9	747.0	786.2	852.1	941.6	1009.0	1076.5	1222.5	1315.1	1288.4	1117.3
60°	649.7	665.4	701.5	765.8	849.0	897.6	969.8	1092.2	1153.4	1104.8	921.2
62.5°	574.4	590.0	618.3	670.1	748.5	800.3	845.8	946.3	988.6	914.9	764.2
65°	499.0	517.9	538.3	579.1	652.8	687.3	728.1	801.9	842.7	756.4	626.1
67.5°	433.1	442.5	462.9	505.3	557.1	588.5	616.7	666.9	674.8	605.7	499.0
70°	371.9	375.1	393.9	419.0	458.2	477.1	500.6	530.4	530.4	473.9	389.2
72.5°	302.9	307.6	321.7	348.4	371.9	381.3	389.2	408.0	404.9	353.1	295.0
75°	243.2	246.4	257.4	269.9	279.3	296.6	302.9	299.7	298.2	254.2	221.3
77.5°	188.3	189.9	197.7	208.7	210.3	216.6	211.9	211.9	197.7	172.6	155.4
80°	138.1	139.7	142.8	145.9	145.9	145.9	145.9	138.1	128.7	113.0	108.3
82.5°	92.6	92.6	94.2	97.3	95.7	92.6	89.4	81.6	75.3	70.6	67.5
85°	54.9	54.9	56.5	54.9	48.6	47.1	43.9	42.4	40.8	39.2	39.2
87.5°	26.7	25.1	22.0	18.8	18.8	18.8	18.8	18.8	18.8	17.3	17.3
90°	0.4	1.0	1.6	2.3	2.9	3.2	3.5	4.0	4.6	5.1	5.7
92.5°	10.7	11.1	11.5	11.9	12.3	12.5	12.9	13.6	14.3	15.0	15.7
95°	23.2	23.4	23.5	23.7	23.8	23.9	24.3	25.1	25.9	26.7	27.5
97.5°	35.7	35.8	35.9	36.0	36.1	36.1	36.7	37.8	38.9	40.0	41.1
100°	50.0	50.0	50.0	50.0	50.0	50.0	50.5	51.5	52.6	53.6	54.6
102.5°	65.3	65.7	66.1	66.5	66.9	67.1	67.3	67.7	68.1	68.5	68.9
105°	81.4	81.8	82.2	82.6	83.0	83.2	83.4	83.9	84.4	84.8	85.3
107.5°	98.9	99.3	99.7	100.1	100.5	100.7	100.9	101.3	101.7	102.1	102.5
110°	117.1	117.5	117.9	118.3	118.7	118.9	119.0	119.2	119.5	119.7	119.9

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	135.7	135.9	136.0	136.2	136.3	136.4	136.6	136.9	137.2	137.5	137.8
115°	153.9	154.2	154.5	154.8	155.1	155.3	155.4	155.5	155.7	155.8	156.0
117.5°	172.4	172.5	172.6	172.7	172.8	172.8	172.9	173.0	173.2	173.3	173.5
120°	189.6	190.0	190.4	190.7	191.1	191.3	191.3	191.4	191.5	191.6	191.7
122.5°	208.1	208.2	208.3	208.4	208.5	208.5	208.6	208.9	209.1	209.4	209.6
125°	224.5	225.0	225.5	226.0	226.5	226.7	226.7	226.8	226.9	226.9	227.0
127.5°	242.8	243.0	243.2	243.5	243.7	243.8	243.8	243.9	244.0	244.1	244.2
130°	258.8	259.2	259.6	260.0	260.4	260.6	260.7	260.8	261.0	261.1	261.3
132.5°	274.9	275.6	276.3	277.0	277.7	278.1	278.1	278.0	277.9	277.8	277.7
135°	292.0	292.5	293.0	293.5	294.0	294.2	294.2	294.3	294.4	294.4	294.5
137.5°	308.1	308.6	309.0	309.5	310.0	310.2	310.3	310.4	310.6	310.7	310.9
140°	323.4	323.8	324.2	324.6	325.0	325.2	325.3	325.6	325.8	326.1	326.3
142.5°	338.8	339.1	339.4	339.7	340.0	340.2	340.4	340.7	341.0	341.3	341.6
145°	353.8	354.1	354.4	354.7	355.0	355.2	355.3	355.6	355.8	356.1	356.3
147.5°	367.7	367.9	368.2	368.4	368.7	368.8	368.9	369.0	369.2	369.3	369.5
150°	381.6	381.5	381.5	381.4	381.3	381.3	381.5	381.8	382.1	382.4	382.7
152.5°	393.0	393.2	393.4	393.5	393.7	393.8	393.8	393.9	394.0	394.0	394.1
155°	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.9	405.0	405.1	405.2
157.5°	415.5	415.3	415.2	415.0	414.9	414.8	414.8	414.9	415.0	415.1	415.2
160°	424.8	424.6	424.3	424.1	423.8	423.7	423.7	423.8	423.9	424.0	424.1
162.5°	433.0	432.8	432.7	432.5	432.4	432.3	432.3	432.3	432.3	432.3	432.3
165°	440.2	440.0	439.9	439.7	439.6	439.5	439.5	439.6	439.7	439.7	439.8
167.5°	446.6	446.3	446.0	445.7	445.4	445.2	445.2	445.2	445.2	445.2	445.2
170°	451.6	451.3	451.0	450.7	450.4	450.2	450.2	450.2	450.2	450.2	450.2
172.5°	455.2	454.9	454.5	454.2	453.9	453.7	453.7	453.7	453.7	453.7	453.7
175°	457.7	457.4	457.0	456.7	456.4	456.2	456.2	456.2	456.2	456.2	456.2
177.5°	459.4	459.1	458.8	458.5	458.2	458.0	458.0	457.9	457.8	457.8	457.7
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1994.6	2005.5	2015.0	2010.2	2029.1	2027.5	2030.6	2036.9	2038.5	2035.4	2029.1
5°	2102.8	2118.5	2145.2	2159.3	2156.2	2168.7	2175.0	2184.4	2193.9	2190.7	2190.7
7.5°	2223.7	2245.6	2272.3	2308.4	2313.1	2324.1	2342.9	2342.9	2353.9	2349.2	2347.6
10°	2328.8	2355.5	2397.9	2426.1	2438.7	2444.9	2463.8	2470.0	2482.6	2484.2	2484.2
12.5°	2415.1	2462.2	2490.4	2518.7	2525.0	2534.4	2548.5	2557.9	2562.6	2562.6	2557.9
15°	2460.6	2498.3	2531.2	2561.1	2578.3	2586.2	2600.3	2611.3	2617.6	2631.7	2634.8
17.5°	2479.5	2525.0	2578.3	2620.7	2650.5	2658.4	2686.6	2696.0	2708.6	2714.9	2722.7
20°	2506.1	2572.0	2636.4	2688.2	2716.4	2736.8	2766.6	2810.6	2823.1	2823.1	2818.4
22.5°	2529.7	2614.4	2702.3	2785.5	2809.0	2849.8	2904.7	2951.8	2970.6	2978.5	2972.2
25°	2557.9	2674.1	2788.6	2892.2	2956.5	2986.3	3060.1	3116.6	3138.6	3151.1	3154.3
27.5°	2606.6	2752.5	2898.5	3030.3	3096.2	3130.7	3207.6	3256.3	3282.9	3293.9	3286.1
30°	2661.5	2840.4	3009.9	3127.6	3171.5	3213.9	3264.1	3282.9	3276.7	3276.7	3300.2
32.5°	2718.0	2903.2	3053.8	3130.7	3146.4	3140.1	3119.7	3063.2	3030.3	3030.3	3050.7
35°	2749.4	2909.4	2986.3	2961.2	2900.0	2863.9	2752.5	2689.7	2619.1	2614.4	2638.0
37.5°	2732.1	2801.2	2769.8	2605.0	2521.8	2452.8	2278.6	2209.5	2157.8	2085.6	2197.0
40°	2611.3	2587.7	2424.5	2187.6	2095.0	1997.7	1859.6	1790.5	1718.4	1707.4	1734.1
42.5°	2407.3	2267.6	2029.1	1800.0	1705.8	1636.8	1531.6	1464.1	1418.6	1399.8	1431.2
45°	2153.1	1933.4	1694.8	1512.8	1409.2	1373.1	1277.4	1217.8	1183.2	1169.1	1191.1
47.5°	1842.3	1621.1	1395.1	1241.3	1180.1	1144.0	1079.7	1027.9	998.1	988.6	998.1
50°	1564.6	1337.0	1147.1	1048.3	993.4	963.5	910.2	877.2	853.7	847.4	863.1
52.5°	1324.5	1117.3	973.0	885.1	849.0	823.9	786.2	758.0	743.8	737.6	748.5
55°	1109.5	941.6	825.4	750.1	723.4	707.7	674.8	659.1	643.4	641.8	652.8
57.5°	919.6	803.5	696.8	643.4	635.6	612.0	583.8	569.6	561.8	560.2	564.9
60°	765.8	662.2	597.9	550.8	539.8	521.0	505.3	495.9	486.5	483.3	486.5
62.5°	637.1	555.5	503.7	472.4	456.7	452.0	434.7	423.7	422.1	422.1	425.3
65°	525.7	456.7	423.7	398.6	387.6	382.9	370.4	362.5	364.1	364.1	365.6
67.5°	428.4	378.2	348.4	335.8	326.4	324.8	312.3	309.1	306.0	306.0	309.1
70°	340.5	309.1	287.2	280.9	279.3	268.3	263.6	262.1	257.4	258.9	258.9
72.5°	266.8	246.4	233.8	224.4	226.0	219.7	213.4	213.4	210.3	215.0	215.0
75°	197.7	188.3	178.9	175.8	178.9	175.8	171.1	169.5	171.1	169.5	169.5
77.5°	145.9	141.2	138.1	136.5	136.5	130.3	127.1	130.3	124.0	127.1	127.1
80°	102.0	95.7	94.2	91.0	92.6	87.9	89.4	86.3	86.3	86.3	86.3
82.5°	64.3	62.8	62.8	62.8	61.2	61.2	61.2	61.2	61.2	61.2	59.6
85°	39.2	37.7	37.7	37.7	36.1	36.1	36.1	36.1	36.1	36.1	36.1
87.5°	15.7	17.3	17.3	18.8	17.3	15.7	15.7	15.7	17.3	17.3	15.7
90°	6.1	6.5	6.9	7.3	7.5	7.6	7.9	8.1	8.4	8.6	8.4
92.5°	16.3	16.8	17.4	17.9	18.2	18.3	18.4	18.6	18.7	18.9	18.7
95°	28.1	28.6	29.2	29.7	30.0	30.1	30.2	30.4	30.5	30.7	30.5
97.5°	41.6	42.0	42.5	43.0	43.2	43.2	43.3	43.4	43.5	43.6	43.5
100°	55.3	56.0	56.7	57.4	57.8	57.9	58.0	58.2	58.3	58.5	58.3
102.5°	69.7	70.5	71.3	72.1	72.5	72.6	72.8	73.1	73.3	73.5	73.3
105°	85.8	86.3	86.8	87.3	87.5	87.6	87.8	88.1	88.3	88.5	88.3
107.5°	102.7	102.9	103.2	103.4	103.5	103.5	103.5	103.5	103.5	103.5	103.5
110°	120.1	120.4	120.6	120.9	121.0	121.0	120.9	120.8	120.8	120.7	120.8

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	137.9	138.0	138.1	138.2	138.2	138.1	137.9	137.8	137.6	137.4	137.6
115°	155.9	155.8	155.7	155.6	155.6	155.6	155.5	155.4	155.4	155.3	155.4
117.5°	173.6	173.7	173.8	173.9	173.9	173.7	173.4	173.1	172.7	172.4	172.7
120°	191.7	191.7	191.7	191.7	191.7	191.5	191.2	190.9	190.6	190.3	190.6
122.5°	209.5	209.4	209.3	209.2	209.2	209.1	208.8	208.6	208.3	208.1	208.3
125°	226.8	226.7	226.5	226.4	226.3	226.3	226.2	226.1	226.1	226.0	226.1
127.5°	244.1	244.0	243.9	243.8	243.8	243.7	243.6	243.4	243.3	243.1	243.3
130°	261.2	261.2	261.1	261.0	261.0	260.9	260.7	260.6	260.4	260.2	260.4
132.5°	277.6	277.6	277.5	277.4	277.4	277.3	277.0	276.8	276.5	276.3	276.5
135°	294.5	294.5	294.5	294.5	294.5	294.3	294.0	293.7	293.4	293.1	293.4
137.5°	311.0	311.1	311.2	311.3	311.3	311.1	310.7	310.3	309.9	309.5	309.9
140°	326.5	326.6	326.8	326.9	327.0	326.8	326.4	326.0	325.6	325.2	325.6
142.5°	341.7	341.8	341.9	342.0	342.0	341.8	341.4	341.0	340.6	340.2	340.6
145°	356.3	356.3	356.3	356.3	356.3	356.2	355.9	355.7	355.4	355.2	355.4
147.5°	369.7	370.0	370.2	370.5	370.6	370.3	369.6	369.0	368.3	367.7	368.3
150°	382.7	382.7	382.7	382.7	382.7	382.6	382.5	382.3	382.2	382.0	382.2
152.5°	394.3	394.6	394.8	395.1	395.2	395.0	394.7	394.4	394.1	393.8	394.1
155°	405.5	405.8	406.1	406.4	406.6	406.4	406.0	405.6	405.2	404.8	405.2
157.5°	415.5	415.8	416.1	416.4	416.6	416.3	415.8	415.2	414.7	414.1	414.7
160°	424.4	424.7	425.0	425.3	425.5	425.3	424.9	424.5	424.1	423.7	424.1
162.5°	432.7	433.1	433.5	433.9	434.1	433.9	433.4	432.9	432.5	432.0	432.5
165°	440.1	440.4	440.7	441.0	441.2	441.0	440.5	440.0	439.6	439.1	439.6
167.5°	445.7	446.1	446.6	447.1	447.3	447.1	446.6	446.1	445.7	445.2	445.7
170°	450.7	451.1	451.6	452.1	452.3	452.0	451.5	450.9	450.4	449.8	450.4
172.5°	454.2	454.7	455.2	455.7	455.9	455.7	455.2	454.7	454.2	453.7	454.2
175°	456.7	457.2	457.7	458.2	458.4	458.1	457.6	457.0	456.5	455.9	456.5
177.5°	458.2	458.6	459.1	459.6	459.8	459.5	459.0	458.4	457.9	457.3	457.9
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	2036.9	2025.9	2030.6	2025.9	2021.2	2016.5	2005.5	1989.8	1977.3	1967.9	1966.3
5°	2193.9	2179.7	2170.3	2165.6	2156.2	2143.6	2123.2	2099.7	2071.4	2060.5	2038.5
7.5°	2338.2	2333.5	2311.5	2308.4	2302.1	2278.6	2244.1	2212.7	2176.6	2146.8	2118.5
10°	2474.8	2463.8	2448.1	2426.1	2423.0	2393.2	2360.2	2316.3	2269.2	2240.9	2190.7
12.5°	2559.5	2546.9	2529.7	2515.6	2507.7	2488.9	2443.4	2399.4	2357.1	2305.3	2261.3
15°	2620.7	2605.0	2573.6	2562.6	2553.2	2528.1	2495.2	2449.6	2393.2	2357.1	2294.3
17.5°	2703.9	2685.0	2653.7	2633.3	2616.0	2576.8	2529.7	2468.5	2415.1	2374.3	2317.8
20°	2799.6	2771.3	2730.5	2703.9	2678.8	2633.3	2567.3	2495.2	2418.3	2368.0	2310.0
22.5°	2958.1	2904.7	2840.4	2802.7	2768.2	2689.7	2611.3	2521.8	2435.5	2360.2	2289.6
25°	3111.9	3058.5	2978.5	2926.7	2873.4	2782.3	2678.8	2554.8	2444.9	2357.1	2264.5
27.5°	3254.7	3199.8	3126.0	3063.2	3011.4	2874.9	2738.4	2598.7	2459.1	2338.2	2244.1
30°	3287.6	3264.1	3207.6	3152.7	3105.6	2980.1	2821.6	2644.2	2476.3	2321.0	2215.8
32.5°	3088.3	3146.4	3160.5	3152.7	3122.9	3033.4	2887.5	2700.7	2501.4	2313.1	2168.7
35°	2674.1	2779.2	2887.5	2945.5	2973.8	2986.3	2900.0	2729.0	2518.7	2300.6	2137.4
37.5°	2217.4	2319.4	2490.4	2576.8	2672.5	2798.0	2832.6	2722.7	2510.8	2291.1	2087.1
40°	1821.9	1952.2	2093.4	2171.9	2255.1	2481.0	2652.1	2639.5	2485.7	2256.6	2047.9
42.5°	1483.0	1564.6	1688.5	1774.9	1876.9	2129.5	2358.6	2471.6	2410.4	2214.3	1997.7
45°	1236.6	1299.4	1387.2	1475.1	1537.9	1767.0	2038.5	2223.7	2281.7	2138.9	1920.8
47.5°	1042.0	1089.1	1166.0	1220.9	1288.4	1468.8	1704.2	1964.7	2087.1	2032.2	1839.2
50°	892.9	930.6	991.8	1026.3	1085.9	1241.3	1420.2	1693.3	1878.4	1884.7	1730.9
52.5°	762.7	800.3	852.1	881.9	918.0	1023.2	1203.6	1434.3	1647.7	1726.2	1606.9
55°	663.8	685.8	728.1	751.7	784.6	886.6	1001.2	1197.4	1420.2	1548.9	1473.6
57.5°	572.8	596.3	623.0	641.8	665.4	747.0	850.5	998.1	1219.3	1359.0	1333.9
60°	499.0	513.2	538.3	552.4	574.4	627.7	699.9	847.4	1023.2	1155.0	1169.1
62.5°	430.0	442.5	459.8	472.4	486.5	528.8	582.2	687.3	841.1	983.9	1002.8
65°	370.4	381.3	390.8	401.7	412.7	439.4	484.9	566.5	685.8	819.2	860.0
67.5°	317.0	320.1	334.3	335.8	342.1	362.5	395.5	461.4	547.7	654.4	707.7
70°	265.2	271.5	274.6	279.3	285.6	299.7	326.4	360.9	425.3	511.6	561.8
72.5°	215.0	216.6	221.3	224.4	230.7	241.7	254.2	280.9	321.7	384.5	430.0
75°	171.1	172.6	175.8	177.3	182.0	185.2	191.5	210.3	238.5	276.2	309.1
77.5°	128.7	131.8	135.0	135.0	136.5	139.7	142.8	149.1	163.2	188.3	216.6
80°	87.9	89.4	89.4	91.0	89.4	94.2	98.9	106.7	113.0	120.8	135.0
82.5°	61.2	61.2	61.2	62.8	62.8	64.3	64.3	65.9	67.5	72.2	78.5
85°	37.7	37.7	39.2	36.1	37.7	39.2	39.2	37.7	39.2	40.8	42.4
87.5°	15.7	15.7	17.3	17.3	17.3	17.3	15.7	17.3	15.7	17.3	17.3
90°	8.1	7.9	7.6	7.5	7.3	6.9	6.5	6.1	5.7	5.1	4.6
92.5°	18.6	18.4	18.3	18.2	17.9	17.4	16.8	16.3	15.7	15.0	14.3
95°	30.4	30.2	30.1	30.0	29.7	29.2	28.6	28.1	27.5	26.7	25.9
97.5°	43.4	43.3	43.2	43.2	43.0	42.5	42.0	41.6	41.1	40.0	38.9
100°	58.2	58.0	57.9	57.8	57.4	56.7	56.0	55.3	54.6	53.6	52.6
102.5°	73.1	72.8	72.6	72.5	72.1	71.3	70.5	69.7	68.9	68.5	68.1
105°	88.1	87.8	87.6	87.5	87.3	86.8	86.3	85.8	85.3	84.8	84.4
107.5°	103.5	103.5	103.5	103.5	103.4	103.2	102.9	102.7	102.5	102.1	101.7
110°	120.8	120.9	121.0	121.0	120.9	120.6	120.4	120.1	119.9	119.7	119.5

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	137.8	137.9	138.1	138.2	138.2	138.1	138.0	137.9	137.8	137.5	137.2
115°	155.4	155.5	155.6	155.6	155.6	155.7	155.8	155.9	156.0	155.8	155.7
117.5°	173.1	173.4	173.7	173.9	173.9	173.8	173.7	173.6	173.5	173.3	173.2
120°	190.9	191.2	191.5	191.7	191.7	191.7	191.7	191.7	191.7	191.6	191.5
122.5°	208.6	208.8	209.1	209.2	209.2	209.3	209.4	209.5	209.6	209.4	209.1
125°	226.1	226.2	226.3	226.3	226.4	226.5	226.7	226.8	227.0	226.9	226.9
127.5°	243.4	243.6	243.7	243.8	243.8	243.9	244.0	244.1	244.2	244.1	244.0
130°	260.6	260.7	260.9	261.0	261.0	261.1	261.2	261.2	261.3	261.1	261.0
132.5°	276.8	277.0	277.3	277.4	277.4	277.5	277.6	277.6	277.7	277.8	277.9
135°	293.7	294.0	294.3	294.5	294.5	294.5	294.5	294.5	294.5	294.4	294.4
137.5°	310.3	310.7	311.1	311.3	311.3	311.2	311.1	311.0	310.9	310.7	310.6
140°	326.0	326.4	326.8	327.0	326.9	326.8	326.6	326.5	326.3	326.1	325.8
142.5°	341.0	341.4	341.8	342.0	342.0	341.9	341.8	341.7	341.6	341.3	341.0
145°	355.7	355.9	356.2	356.3	356.3	356.3	356.3	356.3	356.3	356.1	355.8
147.5°	369.0	369.6	370.3	370.6	370.5	370.2	370.0	369.7	369.5	369.3	369.2
150°	382.3	382.5	382.6	382.7	382.7	382.7	382.7	382.7	382.7	382.4	382.1
152.5°	394.4	394.7	395.0	395.2	395.1	394.8	394.6	394.3	394.1	394.0	394.0
155°	405.6	406.0	406.4	406.6	406.4	406.1	405.8	405.5	405.2	405.1	405.0
157.5°	415.2	415.8	416.3	416.6	416.4	416.1	415.8	415.5	415.2	415.1	415.0
160°	424.5	424.9	425.3	425.5	425.3	425.0	424.7	424.4	424.1	424.0	423.9
162.5°	432.9	433.4	433.9	434.1	433.9	433.5	433.1	432.7	432.3	432.3	432.3
165°	440.0	440.5	441.0	441.2	441.0	440.7	440.4	440.1	439.8	439.7	439.7
167.5°	446.1	446.6	447.1	447.3	447.1	446.6	446.1	445.7	445.2	445.2	445.2
170°	450.9	451.5	452.0	452.3	452.1	451.6	451.1	450.7	450.2	450.2	450.2
172.5°	454.7	455.2	455.7	455.9	455.7	455.2	454.7	454.2	453.7	453.7	453.7
175°	457.0	457.6	458.1	458.4	458.2	457.7	457.2	456.7	456.2	456.2	456.2
177.5°	458.4	459.0	459.5	459.8	459.6	459.1	458.6	458.2	457.7	457.8	457.8
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1961.6	1952.2	1945.9	1944.3	1934.9	1927.1	1917.7	1916.1	1911.4	1898.8	1891.0
5°	2022.8	2000.8	1996.1	1982.0	1958.5	1941.2	1919.2	1906.7	1892.6	1869.0	1850.2
7.5°	2085.6	2055.8	2033.8	2013.4	1980.4	1949.0	1917.7	1892.6	1867.4	1832.9	1804.7
10°	2146.8	2101.3	2074.6	2044.8	1999.3	1952.2	1908.2	1872.2	1831.3	1790.5	1749.7
12.5°	2203.3	2145.2	2106.0	2063.6	2007.1	1949.0	1892.6	1842.3	1800.0	1745.0	1699.5
15°	2237.8	2173.5	2134.2	2093.4	2008.7	1944.3	1878.4	1814.1	1757.6	1699.5	1657.2
17.5°	2258.2	2186.0	2142.1	2104.4	2018.1	1930.2	1845.5	1776.4	1715.2	1646.2	1589.7
20°	2248.8	2178.2	2137.4	2101.3	2000.8	1913.0	1821.9	1741.9	1665.0	1594.4	1534.8
22.5°	2228.4	2154.6	2109.1	2076.2	1986.7	1883.1	1782.7	1696.4	1616.4	1545.7	1478.3
25°	2184.4	2112.3	2073.0	2032.2	1944.3	1845.5	1743.5	1650.9	1566.1	1490.8	1415.5
27.5°	2145.2	2057.3	2016.5	1980.4	1887.8	1800.0	1699.5	1597.5	1511.2	1432.8	1357.4
30°	2099.7	2000.8	1956.9	1908.2	1825.1	1741.9	1641.5	1547.3	1457.9	1374.7	1302.5
32.5°	2051.0	1936.5	1886.3	1831.3	1746.6	1668.1	1583.4	1490.8	1401.4	1319.8	1244.4
35°	1988.3	1865.9	1807.8	1756.0	1668.1	1589.7	1511.2	1434.3	1344.9	1258.6	1186.4
37.5°	1928.6	1793.7	1732.5	1672.9	1580.3	1504.9	1440.6	1368.4	1282.1	1198.9	1129.9
40°	1861.2	1705.8	1643.0	1588.1	1492.4	1409.2	1351.2	1294.7	1219.3	1139.3	1064.0
42.5°	1800.0	1624.2	1558.3	1501.8	1401.4	1322.9	1268.0	1220.9	1155.0	1081.2	1004.3
45°	1715.2	1536.3	1468.8	1409.2	1307.2	1233.5	1177.0	1136.2	1084.4	1015.3	946.3
47.5°	1636.8	1451.6	1377.8	1305.6	1213.1	1137.7	1085.9	1054.6	1020.0	958.8	888.2
50°	1541.0	1354.3	1279.0	1219.3	1114.2	1049.8	998.1	976.1	944.7	886.6	830.1
52.5°	1437.5	1260.1	1189.5	1117.3	1020.0	957.3	911.8	886.6	861.5	819.2	765.8
55°	1316.6	1155.0	1089.1	1024.7	927.4	869.4	828.6	801.9	787.8	748.5	709.3
57.5°	1200.5	1048.3	987.1	927.4	842.7	776.8	750.1	726.6	706.2	677.9	645.0
60°	1082.8	944.7	878.8	825.4	751.7	692.1	670.1	646.5	630.9	608.9	585.3
62.5°	947.8	830.1	779.9	729.7	666.9	619.9	594.8	575.9	555.5	541.4	521.0
65°	805.0	721.9	673.2	635.6	575.9	533.6	514.7	502.2	484.9	470.8	455.1
67.5°	671.7	605.7	585.3	544.5	499.0	461.4	447.2	431.6	417.4	409.6	395.5
70°	543.0	495.9	475.5	464.5	414.3	389.2	376.6	370.4	353.1	345.2	335.8
72.5°	420.6	403.3	389.2	375.1	342.1	326.4	312.3	306.0	293.5	287.2	284.0
75°	310.7	299.7	291.9	290.3	276.2	260.5	246.4	243.2	233.8	227.5	224.4
77.5°	218.1	215.0	213.4	215.0	205.6	196.2	193.0	189.9	178.9	177.3	177.3
80°	142.8	150.7	150.7	149.1	145.9	144.4	139.7	136.5	130.3	128.7	130.3
82.5°	87.9	92.6	94.2	97.3	95.7	94.2	91.0	89.4	91.0	87.9	89.4
85°	43.9	47.1	53.4	53.4	54.9	54.9	54.9	53.4	50.2	51.8	50.2
87.5°	17.3	18.8	18.8	18.8	17.3	22.0	23.5	23.5	23.5	20.4	20.4
90°	4.0	3.5	3.2	2.9	2.3	1.6	1.0	0.4	1.0	1.6	2.3
92.5°	13.6	12.9	12.5	12.3	11.9	11.5	11.1	10.7	11.1	11.5	11.9
95°	25.1	24.3	23.9	23.8	23.7	23.5	23.4	23.2	23.4	23.5	23.7
97.5°	37.8	36.7	36.1	36.1	36.0	35.9	35.8	35.7	35.8	35.9	36.0
100°	51.5	50.5	50.0	50.0	50.0	50.0	50.0	50.0	50.0	50.0	50.0
102.5°	67.7	67.3	67.1	66.9	66.5	66.1	65.7	65.3	65.7	66.1	66.5
105°	83.9	83.4	83.2	83.0	82.6	82.2	81.8	81.4	81.8	82.2	82.6
107.5°	101.3	100.9	100.7	100.5	100.1	99.7	99.3	98.9	99.3	99.7	100.1
110°	119.2	119.0	118.9	118.7	118.3	117.9	117.5	117.1	117.5	117.9	118.3

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	136.9	136.6	136.4	136.3	136.2	136.0	135.9	135.7	135.9	136.0	136.2
115°	155.5	155.4	155.3	155.1	154.8	154.5	154.2	153.9	154.2	154.5	154.8
117.5°	173.0	172.9	172.8	172.8	172.7	172.6	172.5	172.4	172.5	172.6	172.7
120°	191.4	191.3	191.3	191.1	190.7	190.4	190.0	189.6	190.0	190.4	190.7
122.5°	208.9	208.6	208.5	208.5	208.4	208.3	208.2	208.1	208.2	208.3	208.4
125°	226.8	226.7	226.7	226.5	226.0	225.5	225.0	224.5	225.0	225.5	226.0
127.5°	243.9	243.8	243.8	243.7	243.5	243.2	243.0	242.8	243.0	243.2	243.5
130°	260.8	260.7	260.6	260.4	260.0	259.6	259.2	258.8	259.2	259.6	260.0
132.5°	278.0	278.1	278.1	277.7	277.0	276.3	275.6	274.9	275.6	276.3	277.0
135°	294.3	294.2	294.2	294.0	293.5	293.0	292.5	292.0	292.5	293.0	293.5
137.5°	310.4	310.3	310.2	310.0	309.5	309.0	308.6	308.1	308.6	309.0	309.5
140°	325.6	325.3	325.2	325.0	324.6	324.2	323.8	323.4	323.8	324.2	324.6
142.5°	340.7	340.4	340.2	340.0	339.7	339.4	339.1	338.8	339.1	339.4	339.7
145°	355.6	355.3	355.2	355.0	354.7	354.4	354.1	353.8	354.1	354.4	354.7
147.5°	369.0	368.9	368.8	368.7	368.4	368.2	367.9	367.7	367.9	368.2	368.4
150°	381.8	381.5	381.3	381.3	381.4	381.5	381.5	381.6	381.5	381.5	381.4
152.5°	393.9	393.8	393.8	393.7	393.5	393.4	393.2	393.0	393.2	393.4	393.5
155°	404.9	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8	404.8
157.5°	414.9	414.8	414.8	414.9	415.0	415.2	415.3	415.5	415.3	415.2	415.0
160°	423.8	423.7	423.7	423.8	424.1	424.3	424.6	424.8	424.6	424.3	424.1
162.5°	432.3	432.3	432.3	432.4	432.5	432.7	432.8	433.0	432.8	432.7	432.5
165°	439.6	439.5	439.5	439.6	439.7	439.9	440.0	440.2	440.0	439.9	439.7
167.5°	445.2	445.2	445.2	445.4	445.7	446.0	446.3	446.6	446.3	446.0	445.7
170°	450.2	450.2	450.2	450.4	450.7	451.0	451.3	451.6	451.3	451.0	450.7
172.5°	453.7	453.7	453.7	453.9	454.2	454.5	454.9	455.2	454.9	454.5	454.2
175°	456.2	456.2	456.2	456.4	456.7	457.0	457.4	457.7	457.4	457.0	456.7
177.5°	457.9	458.0	458.0	458.2	458.5	458.8	459.1	459.4	459.1	458.8	458.5
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1886.3	1880.0	1875.3	1870.6	1850.2	1828.2	1825.1	1820.4	1810.9	1821.9	1817.2
5°	1837.6	1823.5	1815.7	1795.3	1770.1	1751.3	1735.6	1716.8	1708.9	1702.7	1701.1
7.5°	1778.0	1765.4	1751.3	1730.9	1699.5	1668.1	1644.6	1625.8	1610.1	1602.2	1602.2
10°	1719.9	1704.2	1685.4	1650.9	1621.1	1581.8	1556.7	1537.9	1515.9	1503.4	1492.4
12.5°	1660.3	1643.0	1625.8	1581.8	1547.3	1506.5	1470.4	1446.9	1435.9	1421.8	1402.9
15°	1600.7	1574.0	1556.7	1512.8	1468.8	1428.0	1404.5	1379.4	1354.3	1340.2	1333.9
17.5°	1537.9	1519.1	1490.8	1443.7	1395.1	1359.0	1324.5	1300.9	1271.1	1257.0	1242.9
20°	1481.4	1453.2	1424.9	1377.8	1330.7	1282.1	1247.6	1219.3	1200.5	1189.5	1177.0
22.5°	1413.9	1387.2	1363.7	1313.5	1261.7	1216.2	1178.5	1161.3	1142.4	1125.2	1112.6
25°	1355.9	1329.2	1305.6	1250.7	1194.2	1151.9	1123.6	1101.6	1081.2	1073.4	1060.8
27.5°	1294.7	1269.5	1238.2	1183.2	1133.0	1096.9	1067.1	1046.7	1031.0	1015.3	1005.9
30°	1236.6	1208.3	1180.1	1120.5	1079.7	1043.6	1015.3	990.2	977.7	969.8	954.1
32.5°	1180.1	1144.0	1120.5	1065.5	1026.3	991.8	968.2	946.3	930.6	916.5	903.9
35°	1118.9	1079.7	1056.1	1010.6	969.8	935.3	914.9	899.2	880.4	867.8	861.5
37.5°	1060.8	1027.9	1004.3	957.3	916.5	888.2	866.2	845.8	838.0	820.7	817.6
40°	998.1	969.8	947.8	902.3	864.7	842.7	819.2	800.3	786.2	778.4	767.4
42.5°	941.6	918.0	894.5	852.1	816.0	789.3	772.1	754.8	742.3	729.7	721.9
45°	889.8	864.7	842.7	801.9	765.8	742.3	725.0	704.6	701.5	684.2	676.4
47.5°	834.9	812.9	794.1	751.7	718.7	695.2	674.8	660.7	646.5	640.3	629.3
50°	781.5	759.5	737.6	699.9	670.1	646.5	626.1	610.4	602.6	593.2	583.8
52.5°	723.4	706.2	688.9	649.7	619.9	599.5	582.2	561.8	554.0	546.1	539.8
55°	674.8	649.7	630.9	597.9	571.2	549.2	530.4	514.7	506.9	500.6	492.8
57.5°	608.9	593.2	577.5	547.7	522.6	500.6	481.8	469.2	459.8	455.1	456.7
60°	552.4	535.1	525.7	494.3	469.2	452.0	434.7	422.1	412.7	408.0	406.4
62.5°	492.8	480.2	462.9	441.0	415.9	400.2	387.6	378.2	362.5	360.9	356.2
65°	434.7	425.3	409.6	389.2	368.8	354.7	340.5	328.0	321.7	313.9	309.1
67.5°	378.2	368.8	354.7	337.4	323.3	309.1	296.6	284.0	273.1	266.8	263.6
70°	323.3	315.4	306.0	285.6	268.3	257.4	247.9	240.1	229.1	226.0	224.4
72.5°	269.9	262.1	257.4	240.1	224.4	215.0	205.6	197.7	193.0	191.5	186.7
75°	221.3	213.4	207.1	191.5	182.0	175.8	166.3	163.2	158.5	156.9	155.4
77.5°	172.6	164.8	163.2	152.2	141.2	138.1	135.0	128.7	128.7	128.7	125.5
80°	124.0	122.4	120.8	109.8	105.1	102.0	100.4	95.7	92.6	89.4	87.9
82.5°	83.2	81.6	80.0	75.3	70.6	69.0	67.5	64.3	64.3	65.9	62.8
85°	50.2	47.1	45.5	43.9	40.8	40.8	42.4	40.8	40.8	40.8	39.2
87.5°	18.8	18.8	18.8	18.8	20.4	17.3	18.8	18.8	17.3	17.3	15.7
90°	2.9	3.2	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.9	7.3
92.5°	12.3	12.5	12.9	13.6	14.3	15.0	15.7	16.3	16.8	17.4	17.9
95°	23.8	23.9	24.3	25.1	25.9	26.7	27.5	28.1	28.6	29.2	29.7
97.5°	36.1	36.1	36.7	37.8	38.9	40.0	41.1	41.6	42.0	42.5	43.0
100°	50.0	50.0	50.5	51.5	52.6	53.6	54.6	55.3	56.0	56.7	57.4
102.5°	66.9	67.1	67.3	67.7	68.1	68.5	68.9	69.7	70.5	71.3	72.1
105°	83.0	83.2	83.4	83.9	84.4	84.8	85.3	85.8	86.3	86.8	87.3
107.5°	100.5	100.7	100.9	101.3	101.7	102.1	102.5	102.7	102.9	103.2	103.4
110°	118.7	118.9	119.0	119.2	119.5	119.7	119.9	120.1	120.4	120.6	120.9

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	136.3	136.4	136.6	136.9	137.2	137.5	137.8	137.9	138.0	138.1	138.2
115°	155.1	155.3	155.4	155.5	155.7	155.8	156.0	155.9	155.8	155.7	155.6
117.5°	172.8	172.8	172.9	173.0	173.2	173.3	173.5	173.6	173.7	173.8	173.9
120°	191.1	191.3	191.3	191.4	191.5	191.6	191.7	191.7	191.7	191.7	191.7
122.5°	208.5	208.5	208.6	208.9	209.1	209.4	209.6	209.5	209.4	209.3	209.2
125°	226.5	226.7	226.7	226.8	226.9	226.9	227.0	226.8	226.7	226.5	226.4
127.5°	243.7	243.8	243.8	243.9	244.0	244.1	244.2	244.1	244.0	243.9	243.8
130°	260.4	260.6	260.7	260.8	261.0	261.1	261.3	261.2	261.2	261.1	261.0
132.5°	277.7	278.1	278.1	278.0	277.9	277.8	277.7	277.6	277.6	277.5	277.4
135°	294.0	294.2	294.2	294.3	294.4	294.4	294.5	294.5	294.5	294.5	294.5
137.5°	310.0	310.2	310.3	310.4	310.6	310.7	310.9	311.0	311.1	311.2	311.3
140°	325.0	325.2	325.3	325.6	325.8	326.1	326.3	326.5	326.6	326.8	326.9
142.5°	340.0	340.2	340.4	340.7	341.0	341.3	341.6	341.7	341.8	341.9	342.0
145°	355.0	355.2	355.3	355.6	355.8	356.1	356.3	356.3	356.3	356.3	356.3
147.5°	368.7	368.8	368.9	369.0	369.2	369.3	369.5	369.7	370.0	370.2	370.5
150°	381.3	381.3	381.5	381.8	382.1	382.4	382.7	382.7	382.7	382.7	382.7
152.5°	393.7	393.8	393.8	393.9	394.0	394.0	394.1	394.3	394.6	394.8	395.1
155°	404.8	404.8	404.8	404.9	405.0	405.1	405.2	405.5	405.8	406.1	406.4
157.5°	414.9	414.8	414.8	414.9	415.0	415.1	415.2	415.5	415.8	416.1	416.4
160°	423.8	423.7	423.7	423.8	423.9	424.0	424.1	424.4	424.7	425.0	425.3
162.5°	432.4	432.3	432.3	432.3	432.3	432.3	432.3	432.7	433.1	433.5	433.9
165°	439.6	439.5	439.5	439.6	439.7	439.7	439.8	440.1	440.4	440.7	441.0
167.5°	445.4	445.2	445.2	445.2	445.2	445.2	445.2	445.7	446.1	446.6	447.1
170°	450.4	450.2	450.2	450.2	450.2	450.2	450.2	450.7	451.1	451.6	452.1
172.5°	453.9	453.7	453.7	453.7	453.7	453.7	453.7	454.2	454.7	455.2	455.7
175°	456.4	456.2	456.2	456.2	456.2	456.2	456.2	456.7	457.2	457.7	458.2
177.5°	458.2	458.0	458.0	457.9	457.8	457.8	457.7	458.2	458.6	459.1	459.6
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1809.4	1812.5	1804.7	1801.5	1795.3	1803.1	1804.7	1803.1	1817.2	1810.9	1814.1
5°	1704.2	1698.0	1693.3	1682.3	1682.3	1683.8	1688.5	1680.7	1685.4	1696.4	1694.8
7.5°	1588.1	1585.0	1586.5	1574.0	1564.6	1567.7	1564.6	1578.7	1586.5	1583.4	1589.7
10°	1483.0	1489.2	1475.1	1468.8	1462.6	1468.8	1467.3	1470.4	1479.8	1486.1	1497.1
12.5°	1398.2	1396.7	1388.8	1382.5	1371.6	1374.7	1384.1	1381.0	1382.5	1396.7	1395.1
15°	1318.2	1308.8	1302.5	1288.4	1291.5	1280.5	1289.9	1300.9	1305.6	1318.2	1326.0
17.5°	1238.2	1236.6	1228.7	1227.2	1209.9	1205.2	1214.6	1217.8	1222.5	1228.7	1239.7
20°	1170.7	1169.1	1158.1	1155.0	1140.9	1150.3	1147.1	1153.4	1156.6	1169.1	1173.8
22.5°	1109.5	1101.6	1098.5	1093.8	1089.1	1087.5	1093.8	1092.2	1103.2	1107.9	1109.5
25°	1053.0	1046.7	1045.1	1037.3	1034.2	1029.4	1034.2	1038.9	1051.4	1056.1	1062.4
27.5°	1001.2	996.5	993.4	987.1	982.4	982.4	985.5	991.8	996.5	999.6	1002.8
30°	954.1	951.0	941.6	938.4	933.7	933.7	933.7	936.9	944.7	954.1	958.8
32.5°	905.5	899.2	892.9	892.9	888.2	888.2	889.8	892.9	900.8	902.3	910.2
35°	858.4	852.1	847.4	844.3	845.8	839.6	842.7	847.4	856.8	860.0	864.7
37.5°	812.9	811.3	801.9	797.2	800.3	800.3	798.8	801.9	808.2	814.5	817.6
40°	762.7	759.5	759.5	754.8	756.4	750.1	754.8	758.0	761.1	767.4	772.1
42.5°	718.7	715.6	709.3	710.9	706.2	706.2	709.3	710.9	715.6	723.4	726.6
45°	671.7	671.7	668.5	663.8	665.4	660.7	663.8	665.4	671.7	679.5	676.4
47.5°	626.1	624.6	624.6	618.3	621.4	616.7	621.4	623.0	626.1	630.9	629.3
50°	582.2	577.5	579.1	577.5	575.9	575.9	579.1	579.1	582.2	582.2	586.9
52.5°	536.7	536.7	533.6	535.1	538.3	535.1	539.8	535.1	538.3	539.8	543.0
55°	495.9	492.8	494.3	492.8	499.0	494.3	499.0	495.9	499.0	497.5	500.6
57.5°	452.0	447.2	448.8	447.2	452.0	450.4	455.1	450.4	452.0	453.5	458.2
60°	401.7	401.7	401.7	398.6	403.3	403.3	401.7	401.7	408.0	411.2	409.6
62.5°	354.7	353.1	348.4	346.8	348.4	345.2	351.5	349.9	353.1	356.2	359.4
65°	302.9	299.7	298.2	295.0	295.0	293.5	295.0	301.3	302.9	304.4	312.3
67.5°	260.5	258.9	257.4	252.7	252.7	255.8	255.8	255.8	265.2	260.5	266.8
70°	222.8	219.7	216.6	215.0	215.0	216.6	218.1	219.7	218.1	224.4	226.0
72.5°	186.7	188.3	185.2	185.2	185.2	183.6	183.6	186.7	188.3	186.7	188.3
75°	155.4	155.4	153.8	155.4	155.4	153.8	153.8	156.9	156.9	155.4	160.1
77.5°	125.5	124.0	120.8	117.7	119.3	117.7	119.3	117.7	122.4	127.1	124.0
80°	87.9	86.3	86.3	86.3	87.9	86.3	89.4	86.3	87.9	87.9	89.4
82.5°	62.8	64.3	64.3	62.8	64.3	62.8	64.3	64.3	64.3	62.8	64.3
85°	40.8	40.8	40.8	40.8	39.2	40.8	40.8	40.8	42.4	40.8	42.4
87.5°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	18.8	17.3	18.8
90°	7.5	7.6	7.9	8.1	8.4	8.6	8.4	8.1	7.9	7.6	7.5
92.5°	18.2	18.3	18.4	18.6	18.7	18.9	18.7	18.6	18.4	18.3	18.2
95°	30.0	30.1	30.2	30.4	30.5	30.7	30.5	30.4	30.2	30.1	30.0
97.5°	43.2	43.2	43.3	43.4	43.5	43.6	43.5	43.4	43.3	43.2	43.2
100°	57.8	57.9	58.0	58.2	58.3	58.5	58.3	58.2	58.0	57.9	57.8
102.5°	72.5	72.6	72.8	73.1	73.3	73.5	73.3	73.1	72.8	72.6	72.5
105°	87.5	87.6	87.8	88.1	88.3	88.5	88.3	88.1	87.8	87.6	87.5
107.5°	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.5	103.5
110°	121.0	121.0	120.9	120.8	120.8	120.7	120.8	120.8	120.9	121.0	121.0

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	138.2	138.1	137.9	137.8	137.6	137.4	137.6	137.8	137.9	138.1	138.2
115°	155.6	155.6	155.5	155.4	155.4	155.3	155.4	155.4	155.5	155.6	155.6
117.5°	173.9	173.7	173.4	173.1	172.7	172.4	172.7	173.1	173.4	173.7	173.9
120°	191.7	191.5	191.2	190.9	190.6	190.3	190.6	190.9	191.2	191.5	191.7
122.5°	209.2	209.1	208.8	208.6	208.3	208.1	208.3	208.6	208.8	209.1	209.2
125°	226.3	226.3	226.2	226.1	226.1	226.0	226.1	226.1	226.2	226.3	226.3
127.5°	243.8	243.7	243.6	243.4	243.3	243.1	243.3	243.4	243.6	243.7	243.8
130°	261.0	260.9	260.7	260.6	260.4	260.2	260.4	260.6	260.7	260.9	261.0
132.5°	277.4	277.3	277.0	276.8	276.5	276.3	276.5	276.8	277.0	277.3	277.4
135°	294.5	294.3	294.0	293.7	293.4	293.1	293.4	293.7	294.0	294.3	294.5
137.5°	311.3	311.1	310.7	310.3	309.9	309.5	309.9	310.3	310.7	311.1	311.3
140°	327.0	326.8	326.4	326.0	325.6	325.2	325.6	326.0	326.4	326.8	327.0
142.5°	342.0	341.8	341.4	341.0	340.6	340.2	340.6	341.0	341.4	341.8	342.0
145°	356.3	356.2	355.9	355.7	355.4	355.2	355.4	355.7	355.9	356.2	356.3
147.5°	370.6	370.3	369.6	369.0	368.3	367.7	368.3	369.0	369.6	370.3	370.6
150°	382.7	382.6	382.5	382.3	382.2	382.0	382.2	382.3	382.5	382.6	382.7
152.5°	395.2	395.0	394.7	394.4	394.1	393.8	394.1	394.4	394.7	395.0	395.2
155°	406.6	406.4	406.0	405.6	405.2	404.8	405.2	405.6	406.0	406.4	406.6
157.5°	416.6	416.3	415.8	415.2	414.7	414.1	414.7	415.2	415.8	416.3	416.6
160°	425.5	425.3	424.9	424.5	424.1	423.7	424.1	424.5	424.9	425.3	425.5
162.5°	434.1	433.9	433.4	432.9	432.5	432.0	432.5	432.9	433.4	433.9	434.1
165°	441.2	441.0	440.5	440.0	439.6	439.1	439.6	440.0	440.5	441.0	441.2
167.5°	447.3	447.1	446.6	446.1	445.7	445.2	445.7	446.1	446.6	447.1	447.3
170°	452.3	452.0	451.5	450.9	450.4	449.8	450.4	450.9	451.5	452.0	452.3
172.5°	455.9	455.7	455.2	454.7	454.2	453.7	454.2	454.7	455.2	455.7	455.9
175°	458.4	458.1	457.6	457.0	456.5	455.9	456.5	457.0	457.6	458.1	458.4
177.5°	459.8	459.5	459.0	458.4	457.9	457.3	457.9	458.4	459.0	459.5	459.8
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4	1911.4
2.5°	1807.8	1815.7	1809.4	1804.7	1817.2	1823.5	1823.5	1834.5	1845.5	1854.9	1856.5
5°	1696.4	1708.9	1712.1	1710.5	1729.3	1738.8	1759.2	1770.1	1785.8	1796.8	1809.4
7.5°	1594.4	1611.7	1613.2	1616.4	1644.6	1660.3	1677.6	1705.8	1727.8	1743.5	1757.6
10°	1492.4	1503.4	1514.4	1528.5	1556.7	1583.4	1608.5	1638.3	1666.6	1682.3	1702.7
12.5°	1415.5	1423.3	1435.9	1445.3	1475.1	1498.7	1531.6	1572.4	1613.2	1625.8	1650.9
15°	1335.5	1340.2	1365.3	1374.7	1399.8	1439.0	1459.4	1498.7	1542.6	1566.1	1594.4
17.5°	1242.9	1271.1	1286.8	1297.8	1329.2	1360.6	1393.5	1434.3	1490.8	1512.8	1533.2
20°	1177.0	1197.4	1214.6	1228.7	1257.0	1304.1	1333.9	1366.8	1420.2	1445.3	1475.1
22.5°	1118.9	1136.2	1151.9	1167.5	1186.4	1228.7	1263.3	1308.8	1362.1	1385.7	1420.2
25°	1064.0	1081.2	1090.6	1109.5	1134.6	1164.4	1205.2	1246.0	1299.4	1326.0	1359.0
27.5°	1010.6	1027.9	1045.1	1060.8	1078.1	1106.3	1134.6	1186.4	1241.3	1272.7	1300.9
30°	965.1	973.0	988.6	1005.9	1023.2	1049.8	1082.8	1118.9	1181.7	1209.9	1244.4
32.5°	914.9	929.0	940.0	952.6	974.5	996.5	1026.3	1071.8	1122.0	1148.7	1186.4
35°	867.8	880.4	888.2	910.2	924.3	947.8	977.7	1018.5	1060.8	1090.6	1123.6
37.5°	822.3	834.9	844.3	856.8	875.7	896.1	927.4	957.3	1007.5	1032.6	1070.2
40°	775.2	786.2	797.2	811.3	828.6	853.7	872.5	910.2	951.0	979.2	1007.5
42.5°	729.7	736.0	748.5	764.2	781.5	803.5	830.1	860.0	900.8	925.9	951.0
45°	681.1	692.1	706.2	717.2	732.9	754.8	778.4	805.0	845.8	871.0	897.6
47.5°	635.6	643.4	652.8	670.1	690.5	706.2	731.3	756.4	794.1	817.6	842.7
50°	588.5	596.3	610.4	621.4	637.1	657.5	681.1	707.7	743.8	759.5	784.6
52.5°	544.5	547.7	561.8	572.8	588.5	612.0	630.9	654.4	688.9	706.2	731.3
55°	500.6	503.7	511.6	522.6	539.8	558.7	579.1	605.7	635.6	651.3	674.8
57.5°	455.1	458.2	466.1	473.9	491.2	508.4	532.0	554.0	583.8	597.9	619.9
60°	409.6	409.6	417.4	428.4	441.0	456.7	477.1	503.7	525.7	543.0	558.7
62.5°	360.9	365.6	370.4	378.2	392.3	411.2	428.4	447.2	473.9	486.5	500.6
65°	312.3	317.0	326.4	334.3	345.2	357.8	379.8	395.5	415.9	430.0	442.5
67.5°	269.9	274.6	280.9	290.3	298.2	312.3	328.0	343.7	365.6	375.1	384.5
70°	226.0	230.7	235.4	247.9	255.8	266.8	277.8	293.5	312.3	318.6	326.4
72.5°	191.5	193.0	199.3	202.4	213.4	222.8	235.4	244.8	258.9	266.8	273.1
75°	161.6	161.6	163.2	166.3	172.6	178.9	188.3	197.7	210.3	215.0	222.8
77.5°	127.1	131.8	130.3	133.4	136.5	139.7	147.5	153.8	166.3	169.5	172.6
80°	91.0	92.6	97.3	102.0	102.0	106.7	111.4	113.0	120.8	125.5	125.5
82.5°	65.9	67.5	65.9	67.5	69.0	70.6	75.3	81.6	81.6	83.2	86.3
85°	40.8	40.8	42.4	43.9	43.9	42.4	45.5	43.9	45.5	48.6	48.6
87.5°	20.4	18.8	18.8	18.8	18.8	18.8	20.4	18.8	20.4	20.4	20.4
90°	7.3	6.9	6.5	6.1	5.7	5.1	4.6	4.0	3.5	3.2	2.9
92.5°	17.9	17.4	16.8	16.3	15.7	15.0	14.3	13.6	12.9	12.5	12.3
95°	29.7	29.2	28.6	28.1	27.5	26.7	25.9	25.1	24.3	23.9	23.8
97.5°	43.0	42.5	42.0	41.6	41.1	40.0	38.9	37.8	36.7	36.1	36.1
100°	57.4	56.7	56.0	55.3	54.6	53.6	52.6	51.5	50.5	50.0	50.0
102.5°	72.1	71.3	70.5	69.7	68.9	68.5	68.1	67.7	67.3	67.1	66.9
105°	87.3	86.8	86.3	85.8	85.3	84.8	84.4	83.9	83.4	83.2	83.0
107.5°	103.4	103.2	102.9	102.7	102.5	102.1	101.7	101.3	100.9	100.7	100.5
110°	120.9	120.6	120.4	120.1	119.9	119.7	119.5	119.2	119.0	118.9	118.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	138.2	138.1	138.0	137.9	137.8	137.5	137.2	136.9	136.6	136.4	136.3
115°	155.6	155.7	155.8	155.9	156.0	155.8	155.7	155.5	155.4	155.3	155.1
117.5°	173.9	173.8	173.7	173.6	173.5	173.3	173.2	173.0	172.9	172.8	172.8
120°	191.7	191.7	191.7	191.7	191.7	191.6	191.5	191.4	191.3	191.3	191.1
122.5°	209.2	209.3	209.4	209.5	209.6	209.4	209.1	208.9	208.6	208.5	208.5
125°	226.4	226.5	226.7	226.8	227.0	226.9	226.9	226.8	226.7	226.7	226.5
127.5°	243.8	243.9	244.0	244.1	244.2	244.1	244.0	243.9	243.8	243.8	243.7
130°	261.0	261.1	261.2	261.2	261.3	261.1	261.0	260.8	260.7	260.6	260.4
132.5°	277.4	277.5	277.6	277.6	277.7	277.8	277.9	278.0	278.1	278.1	277.7
135°	294.5	294.5	294.5	294.5	294.5	294.4	294.4	294.3	294.2	294.2	294.0
137.5°	311.3	311.2	311.1	311.0	310.9	310.7	310.6	310.4	310.3	310.2	310.0
140°	326.9	326.8	326.6	326.5	326.3	326.1	325.8	325.6	325.3	325.2	325.0
142.5°	342.0	341.9	341.8	341.7	341.6	341.3	341.0	340.7	340.4	340.2	340.0
145°	356.3	356.3	356.3	356.3	356.3	356.1	355.8	355.6	355.3	355.2	355.0
147.5°	370.5	370.2	370.0	369.7	369.5	369.3	369.2	369.0	368.9	368.8	368.7
150°	382.7	382.7	382.7	382.7	382.7	382.4	382.1	381.8	381.5	381.3	381.3
152.5°	395.1	394.8	394.6	394.3	394.1	394.0	394.0	393.9	393.8	393.8	393.7
155°	406.4	406.1	405.8	405.5	405.2	405.1	405.0	404.9	404.8	404.8	404.8
157.5°	416.4	416.1	415.8	415.5	415.2	415.1	415.0	414.9	414.8	414.8	414.9
160°	425.3	425.0	424.7	424.4	424.1	424.0	423.9	423.8	423.7	423.7	423.8
162.5°	433.9	433.5	433.1	432.7	432.3	432.3	432.3	432.3	432.3	432.3	432.4
165°	441.0	440.7	440.4	440.1	439.8	439.7	439.7	439.6	439.5	439.5	439.6
167.5°	447.1	446.6	446.1	445.7	445.2	445.2	445.2	445.2	445.2	445.2	445.4
170°	452.1	451.6	451.1	450.7	450.2	450.2	450.2	450.2	450.2	450.2	450.4
172.5°	455.7	455.2	454.7	454.2	453.7	453.7	453.7	453.7	453.7	453.7	453.9
175°	458.2	457.7	457.2	456.7	456.2	456.2	456.2	456.2	456.2	456.2	456.4
177.5°	459.6	459.1	458.6	458.2	457.7	457.8	457.8	457.9	458.0	458.0	458.2
180°	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7	458.7

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1911.4	1911.4	1911.4	1911.4
2.5°	1867.4	1881.6	1895.7	1913.0
5°	1829.8	1854.9	1881.6	1906.7
7.5°	1789.0	1825.1	1859.6	1895.7
10°	1743.5	1789.0	1828.2	1878.4
12.5°	1693.3	1741.9	1796.8	1853.3
15°	1643.0	1704.2	1762.3	1826.6
17.5°	1596.0	1654.0	1718.4	1795.3
20°	1539.5	1603.8	1676.0	1757.6
22.5°	1479.8	1550.4	1628.9	1716.8
25°	1429.6	1501.8	1577.1	1669.7
27.5°	1374.7	1450.0	1523.8	1622.6
30°	1311.9	1393.5	1468.8	1570.8
32.5°	1252.3	1333.9	1417.1	1512.8
35°	1194.2	1274.3	1357.4	1454.7
37.5°	1139.3	1211.5	1293.1	1381.0
40°	1087.5	1153.4	1225.6	1305.6
42.5°	1021.6	1098.5	1166.0	1224.0
45°	965.1	1027.9	1090.6	1137.7
47.5°	899.2	962.0	1015.3	1053.0
50°	844.3	894.5	938.4	971.4
52.5°	778.4	825.4	861.5	886.6
55°	714.0	754.8	786.2	803.5
57.5°	656.0	682.6	706.2	721.9
60°	591.6	612.0	632.4	649.7
62.5°	522.6	544.5	555.5	574.4
65°	461.4	475.5	492.8	499.0
67.5°	401.7	409.6	420.6	433.1
70°	339.0	343.7	354.7	371.9
72.5°	284.0	288.7	296.6	302.9
75°	226.0	230.7	237.0	243.2
77.5°	177.3	178.9	182.0	188.3
80°	128.7	133.4	136.5	138.1
82.5°	89.4	91.0	91.0	92.6
85°	56.5	53.4	53.4	54.9
87.5°	20.4	23.5	23.5	26.7
90°	2.3	1.6	1.0	0.4
92.5°	11.9	11.5	11.1	10.7
95°	23.7	23.5	23.4	23.2
97.5°	36.0	35.9	35.8	35.7
100°	50.0	50.0	50.0	50.0
102.5°	66.5	66.1	65.7	65.3
105°	82.6	82.2	81.8	81.4
107.5°	100.1	99.7	99.3	98.9
110°	118.3	117.9	117.5	117.1

TEST NUMBER: P1028635

CATALOG NUMBER: S125RDIP-B1270D375UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	136.2	136.0	135.9	135.7
115°	154.8	154.5	154.2	153.9
117.5°	172.7	172.6	172.5	172.4
120°	190.7	190.4	190.0	189.6
122.5°	208.4	208.3	208.2	208.1
125°	226.0	225.5	225.0	224.5
127.5°	243.5	243.2	243.0	242.8
130°	260.0	259.6	259.2	258.8
132.5°	277.0	276.3	275.6	274.9
135°	293.5	293.0	292.5	292.0
137.5°	309.5	309.0	308.6	308.1
140°	324.6	324.2	323.8	323.4
142.5°	339.7	339.4	339.1	338.8
145°	354.7	354.4	354.1	353.8
147.5°	368.4	368.2	367.9	367.7
150°	381.4	381.5	381.5	381.6
152.5°	393.5	393.4	393.2	393.0
155°	404.8	404.8	404.8	404.8
157.5°	415.0	415.2	415.3	415.5
160°	424.1	424.3	424.6	424.8
162.5°	432.5	432.7	432.8	433.0
165°	439.7	439.9	440.0	440.2
167.5°	445.7	446.0	446.3	446.6
170°	450.7	451.0	451.3	451.6
172.5°	454.2	454.5	454.9	455.2
175°	456.7	457.0	457.4	457.7
177.5°	458.5	458.8	459.1	459.4
180°	458.7	458.7	458.7	458.7

(END OF REPORT)