

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029304

Luminaire Tested: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029304
REPORT IS A COMBINATION OF REPORTS P985480 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K
Description: Define 2 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5540.0 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27
2	84	77	71	66	74	68	64	60	53	50	47	38	36	34	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	31	29	22	21	20
4	70	60	53	47	62	54	47	42	41	37	34	30	28	25	20	18	17
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13
7	55	43	35	30	48	39	32	28	30	26	22	22	19	17	15	13	12
8	51	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	11
9	47	35	28	24	42	32	26	22	25	21	17	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.0
10°-20°	158.6	2.9
20°-30°	230.1	4.2
30°-40°	242.6	4.4
40°-50°	214.7	3.9
50°-60°	171.4	3.1
60°-70°	116.4	2.1
70°-80°	59.6	1.1
80°-90°	18.4	0.3
90°-100°	94.6	1.7
100°-110°	300.6	5.4
110°-120°	514.4	9.3
120°-130°	676.5	12.2
130°-140°	759.3	13.7
140°-150°	744.6	13.4
150°-160°	624.6	11.3
160°-170°	414.3	7.5
170°-180°	144.8	2.6
0°-30°	443.2	8.0
0°-40°	685.8	12.4
0°-60°	1071.9	19.3
0°-90°	1266.4	22.9
90°-120°	909.5	16.4
90°-150°	3090.0	55.8
90°-180°	4274.0	77.1
0°-180°	5540.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	44	1	44	1	5
95°	67	80	67	80	67	75
105°	277	286	277	286	277	293
115°	516	516	516	516	516	510
125°	751	753	751	753	751	671
135°	971	983	971	983	971	751
145°	1179	1192	1179	1192	1179	737
155°	1348	1358	1348	1358	1348	621
165°	1467	1468	1467	1468	1467	414
175°	1526	1521	1526	1521	1526	145
180°	1529	1529	1529	1529	1529	

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	1.3	4.7	8.2	11.6	15.1	16.8	19.9	26.2	32.5	38.8	45.1
92.5°	28.4	30.7	33.0	35.3	37.6	38.7	38.8	39.1	39.4	39.7	40.0
95°	67.1	70.0	72.8	75.7	78.6	80.0	80.3	80.9	81.4	82.0	82.6
97.5°	112.2	114.8	117.4	119.9	122.5	123.8	124.4	125.5	126.7	127.8	129.0
100°	163.8	166.1	168.4	170.7	173.0	174.1	174.5	175.4	176.3	177.1	178.0
102.5°	218.0	219.7	221.4	223.1	224.8	225.7	226.3	227.4	228.6	229.7	230.9
105°	277.3	278.2	279.0	279.9	280.8	281.2	281.5	282.1	282.6	283.2	283.8
107.5°	336.7	337.8	339.0	340.1	341.2	341.8	341.8	341.8	341.8	341.8	341.8
110°	393.4	395.1	396.9	398.6	400.3	401.2	401.2	401.2	401.2	401.2	401.2

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	455.4	457.1	458.8	460.5	462.2	463.1	463.0	462.7	462.4	462.1	461.8
115°	516.0	517.7	519.4	521.1	522.8	523.7	523.4	522.8	522.3	521.7	521.1
117.5°	576.6	578.9	581.2	583.5	585.8	586.9	586.2	584.8	583.3	581.9	580.5
120°	637.2	639.5	641.8	644.1	646.4	647.6	646.4	644.1	641.8	639.5	637.2
122.5°	692.7	695.6	698.4	701.3	704.2	705.6	704.9	703.5	702.0	700.6	699.2
125°	750.8	753.4	756.0	758.5	761.1	762.4	762.0	761.1	760.2	759.4	758.5
127.5°	807.5	810.7	813.8	817.0	820.1	821.7	821.1	820.0	818.8	817.7	816.5
130°	860.4	864.1	867.9	871.6	875.3	877.2	876.9	876.3	875.8	875.2	874.6
132.5°	919.7	922.6	925.4	928.3	931.2	932.6	932.7	933.0	933.3	933.6	933.9
135°	971.3	974.5	977.6	980.8	983.9	985.5	985.8	986.4	986.9	987.5	988.1
137.5°	1028.1	1030.7	1033.3	1035.8	1038.4	1039.7	1040.0	1040.6	1041.1	1041.7	1042.3
140°	1078.4	1081.0	1083.6	1086.1	1088.7	1090.0	1090.7	1092.2	1093.6	1095.1	1096.5
142.5°	1130.0	1132.6	1135.2	1137.7	1140.3	1141.6	1142.0	1142.9	1143.8	1144.6	1145.5
145°	1179.0	1181.0	1183.0	1185.0	1187.0	1188.0	1188.9	1190.6	1192.3	1194.1	1195.8
147.5°	1222.9	1225.5	1228.1	1230.6	1233.2	1234.5	1235.1	1236.2	1237.3	1238.5	1239.6
150°	1268.0	1269.7	1271.5	1273.2	1274.9	1275.8	1276.4	1277.5	1278.6	1279.8	1280.9
152.5°	1308.0	1309.7	1311.4	1313.1	1314.8	1315.7	1316.4	1317.9	1319.3	1320.8	1322.2
155°	1348.0	1348.9	1349.7	1350.6	1351.5	1351.9	1352.3	1353.2	1354.0	1354.9	1355.7
157.5°	1382.8	1383.4	1384.0	1384.5	1385.1	1385.4	1385.7	1386.3	1386.8	1387.4	1388.0
160°	1413.8	1414.4	1415.0	1415.5	1416.1	1416.4	1416.5	1416.8	1417.1	1417.4	1417.7
162.5°	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.3	1442.6	1442.9	1443.2	1443.5
165°	1466.7	1466.4	1466.1	1465.8	1465.5	1465.4	1465.4	1465.4	1465.4	1465.4	1465.4
167.5°	1488.6	1487.7	1486.9	1486.0	1485.1	1484.7	1484.7	1484.7	1484.7	1484.7	1484.7
170°	1505.4	1504.5	1503.7	1502.8	1501.9	1501.5	1501.4	1501.1	1500.8	1500.5	1500.2
172.5°	1517.0	1516.1	1515.3	1514.4	1513.5	1513.1	1513.0	1512.7	1512.4	1512.1	1511.8
175°	1526.0	1525.1	1524.3	1523.4	1522.5	1522.1	1521.8	1521.3	1520.7	1520.2	1519.6
177.5°	1531.2	1530.3	1529.5	1528.6	1527.7	1527.3	1527.0	1526.4	1525.9	1525.3	1524.7
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	44.5	44.0	43.4	42.9	42.6	42.7	43.0	43.3	43.6	43.9	43.6
92.5°	40.3	40.6	40.9	41.2	41.3	41.3	41.3	41.3	41.3	41.3	41.3
95°	82.6	82.6	82.6	82.6	82.6	82.3	81.7	81.2	80.6	80.0	80.6
97.5°	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0
100°	178.0	178.0	178.0	178.0	178.0	177.9	177.6	177.3	177.0	176.7	177.0
102.5°	231.2	231.5	231.8	232.1	232.2	232.1	231.8	231.5	231.2	230.9	231.2
105°	284.4	285.0	285.5	286.1	286.4	286.4	286.4	286.4	286.4	286.4	286.4
107.5°	342.1	342.4	342.7	343.0	343.1	342.4	341.0	339.5	338.1	336.7	338.1
110°	401.2	401.2	401.2	401.2	401.2	400.8	399.9	399.0	398.2	397.3	398.2

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	460.9	460.1	459.2	458.3	457.9	457.6	457.1	456.5	456.0	455.4	456.0
115°	520.8	520.5	520.2	519.9	519.8	519.4	518.5	517.7	516.8	516.0	516.8
117.5°	579.6	578.8	577.9	577.0	576.6	576.2	575.3	574.4	573.6	572.7	573.6
120°	637.2	637.2	637.2	637.2	637.2	636.8	635.9	635.1	634.2	633.4	634.2
122.5°	698.3	697.5	696.6	695.7	695.3	695.0	694.4	693.9	693.3	692.7	693.3
125°	757.6	756.8	755.9	755.0	754.6	754.5	754.2	753.9	753.6	753.3	753.6
127.5°	815.4	814.2	813.1	812.0	811.4	811.0	810.1	809.2	808.4	807.5	808.4
130°	874.0	873.4	872.9	872.3	872.0	871.4	870.3	869.1	868.0	866.8	868.0
132.5°	932.5	931.1	929.6	928.2	927.5	927.1	926.2	925.3	924.5	923.6	924.5
135°	987.8	987.5	987.2	986.9	986.8	986.4	985.5	984.6	983.8	982.9	983.8
137.5°	1042.0	1041.7	1041.4	1041.1	1041.0	1040.4	1039.3	1038.1	1037.0	1035.8	1037.0
140°	1096.5	1096.5	1096.5	1096.5	1096.5	1095.9	1094.8	1093.6	1092.5	1091.3	1092.5
142.5°	1145.8	1146.1	1146.4	1146.7	1146.8	1146.2	1145.1	1143.9	1142.8	1141.6	1142.8
145°	1196.1	1196.4	1196.7	1197.0	1197.1	1196.5	1195.4	1194.2	1193.1	1191.9	1193.1
147.5°	1240.2	1240.8	1241.3	1241.9	1242.2	1241.6	1240.5	1239.4	1238.2	1237.1	1238.2
150°	1281.8	1282.6	1283.5	1284.4	1284.8	1284.4	1283.5	1282.6	1281.8	1280.9	1281.8
152.5°	1323.4	1324.5	1325.7	1326.8	1327.4	1326.8	1325.7	1324.5	1323.4	1322.2	1323.4
155°	1357.1	1358.6	1360.0	1361.5	1362.2	1361.8	1360.9	1360.0	1359.2	1358.3	1359.2
157.5°	1390.0	1392.0	1394.0	1396.0	1397.0	1396.3	1394.9	1393.4	1392.0	1390.6	1392.0
160°	1419.4	1421.1	1422.8	1424.5	1425.4	1424.8	1423.7	1422.5	1421.4	1420.2	1421.4
162.5°	1445.5	1447.5	1449.5	1451.5	1452.5	1451.8	1450.3	1448.9	1447.4	1446.0	1447.4
165°	1467.4	1469.4	1471.4	1473.4	1474.4	1473.7	1472.3	1470.8	1469.4	1468.0	1469.4
167.5°	1486.7	1488.7	1490.8	1492.8	1493.8	1493.1	1491.6	1490.2	1488.7	1487.3	1488.7
170°	1502.2	1504.2	1506.2	1508.2	1509.2	1508.3	1506.6	1504.9	1503.2	1501.5	1503.2
172.5°	1513.8	1515.8	1517.9	1519.9	1520.9	1520.0	1518.3	1516.6	1514.8	1513.1	1514.8
175°	1521.6	1523.6	1525.6	1527.6	1528.6	1527.7	1526.0	1524.3	1522.6	1520.9	1522.6
177.5°	1526.4	1528.2	1529.9	1531.6	1532.5	1531.6	1529.9	1528.2	1526.4	1524.7	1526.4
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	43.3	43.0	42.7	42.6	42.9	43.4	44.0	44.5	45.1	38.8	32.5
92.5°	41.3	41.3	41.3	41.3	41.2	40.9	40.6	40.3	40.0	39.7	39.4
95°	81.2	81.7	82.3	82.6	82.6	82.6	82.6	82.6	82.6	82.0	81.4
97.5°	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	127.8	126.7
100°	177.3	177.6	177.9	178.0	178.0	178.0	178.0	178.0	178.0	177.1	176.3
102.5°	231.5	231.8	232.1	232.2	232.1	231.8	231.5	231.2	230.9	229.7	228.6
105°	286.4	286.4	286.4	286.4	286.1	285.5	285.0	284.4	283.8	283.2	282.6
107.5°	339.5	341.0	342.4	343.1	343.0	342.7	342.4	342.1	341.8	341.8	341.8
110°	399.0	399.9	400.8	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	456.5	457.1	457.6	457.9	458.3	459.2	460.1	460.9	461.8	462.1	462.4
115°	517.7	518.5	519.4	519.8	519.9	520.2	520.5	520.8	521.1	521.7	522.3
117.5°	574.4	575.3	576.2	576.6	577.0	577.9	578.8	579.6	580.5	581.9	583.3
120°	635.1	635.9	636.8	637.2	637.2	637.2	637.2	637.2	637.2	639.5	641.8
122.5°	693.9	694.4	695.0	695.3	695.7	696.6	697.5	698.3	699.2	700.6	702.0
125°	753.9	754.2	754.5	754.6	755.0	755.9	756.8	757.6	758.5	759.4	760.2
127.5°	809.2	810.1	811.0	811.4	812.0	813.1	814.2	815.4	816.5	817.7	818.8
130°	869.1	870.3	871.4	872.0	872.3	872.9	873.4	874.0	874.6	875.2	875.8
132.5°	925.3	926.2	927.1	927.5	928.2	929.6	931.1	932.5	933.9	933.6	933.3
135°	984.6	985.5	986.4	986.8	986.9	987.2	987.5	987.8	988.1	987.5	986.9
137.5°	1038.1	1039.3	1040.4	1041.0	1041.1	1041.4	1041.7	1042.0	1042.3	1041.7	1041.1
140°	1093.6	1094.8	1095.9	1096.5	1096.5	1096.5	1096.5	1096.5	1096.5	1095.1	1093.6
142.5°	1143.9	1145.1	1146.2	1146.8	1146.7	1146.4	1146.1	1145.8	1145.5	1144.6	1143.8
145°	1194.2	1195.4	1196.5	1197.1	1197.0	1196.7	1196.4	1196.1	1195.8	1194.1	1192.3
147.5°	1239.4	1240.5	1241.6	1242.2	1241.9	1241.3	1240.8	1240.2	1239.6	1238.5	1237.3
150°	1282.6	1283.5	1284.4	1284.8	1284.4	1283.5	1282.6	1281.8	1280.9	1279.8	1278.6
152.5°	1324.5	1325.7	1326.8	1327.4	1326.8	1325.7	1324.5	1323.4	1322.2	1320.8	1319.3
155°	1360.0	1360.9	1361.8	1362.2	1361.5	1360.0	1358.6	1357.1	1355.7	1354.9	1354.0
157.5°	1393.4	1394.9	1396.3	1397.0	1396.0	1394.0	1392.0	1390.0	1388.0	1387.4	1386.8
160°	1422.5	1423.7	1424.8	1425.4	1424.5	1422.8	1421.1	1419.4	1417.7	1417.4	1417.1
162.5°	1448.9	1450.3	1451.8	1452.5	1451.5	1449.5	1447.5	1445.5	1443.5	1443.2	1442.9
165°	1470.8	1472.3	1473.7	1474.4	1473.4	1471.4	1469.4	1467.4	1465.4	1465.4	1465.4
167.5°	1490.2	1491.6	1493.1	1493.8	1492.8	1490.8	1488.7	1486.7	1484.7	1484.7	1484.7
170°	1504.9	1506.6	1508.3	1509.2	1508.2	1506.2	1504.2	1502.2	1500.2	1500.5	1500.8
172.5°	1516.6	1518.3	1520.0	1520.9	1519.9	1517.9	1515.8	1513.8	1511.8	1512.1	1512.4
175°	1524.3	1526.0	1527.7	1528.6	1527.6	1525.6	1523.6	1521.6	1519.6	1520.2	1520.7
177.5°	1528.2	1529.9	1531.6	1532.5	1531.6	1529.9	1528.2	1526.4	1524.7	1525.3	1525.9
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	26.2	19.9	16.8	15.1	11.6	8.2	4.7	1.3	4.7	8.2	11.6
92.5°	39.1	38.8	38.7	37.6	35.3	33.0	30.7	28.4	30.7	33.0	35.3
95°	80.9	80.3	80.0	78.6	75.7	72.8	70.0	67.1	70.0	72.8	75.7
97.5°	125.5	124.4	123.8	122.5	119.9	117.4	114.8	112.2	114.8	117.4	119.9
100°	175.4	174.5	174.1	173.0	170.7	168.4	166.1	163.8	166.1	168.4	170.7
102.5°	227.4	226.3	225.7	224.8	223.1	221.4	219.7	218.0	219.7	221.4	223.1
105°	282.1	281.5	281.2	280.8	279.9	279.0	278.2	277.3	278.2	279.0	279.9
107.5°	341.8	341.8	341.8	341.2	340.1	339.0	337.8	336.7	337.8	339.0	340.1
110°	401.2	401.2	401.2	400.3	398.6	396.9	395.1	393.4	395.1	396.9	398.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	462.7	463.0	463.1	462.2	460.5	458.8	457.1	455.4	457.1	458.8	460.5
115°	522.8	523.4	523.7	522.8	521.1	519.4	517.7	516.0	517.7	519.4	521.1
117.5°	584.8	586.2	586.9	585.8	583.5	581.2	578.9	576.6	578.9	581.2	583.5
120°	644.1	646.4	647.6	646.4	644.1	641.8	639.5	637.2	639.5	641.8	644.1
122.5°	703.5	704.9	705.6	704.2	701.3	698.4	695.6	692.7	695.6	698.4	701.3
125°	761.1	762.0	762.4	761.1	758.5	756.0	753.4	750.8	753.4	756.0	758.5
127.5°	820.0	821.1	821.7	820.1	817.0	813.8	810.7	807.5	810.7	813.8	817.0
130°	876.3	876.9	877.2	875.3	871.6	867.9	864.1	860.4	864.1	867.9	871.6
132.5°	933.0	932.7	932.6	931.2	928.3	925.4	922.6	919.7	922.6	925.4	928.3
135°	986.4	985.8	985.5	983.9	980.8	977.6	974.5	971.3	974.5	977.6	980.8
137.5°	1040.6	1040.0	1039.7	1038.4	1035.8	1033.3	1030.7	1028.1	1030.7	1033.3	1035.8
140°	1092.2	1090.7	1090.0	1088.7	1086.1	1083.6	1081.0	1078.4	1081.0	1083.6	1086.1
142.5°	1142.9	1142.0	1141.6	1140.3	1137.7	1135.2	1132.6	1130.0	1132.6	1135.2	1137.7
145°	1190.6	1188.9	1188.0	1187.0	1185.0	1183.0	1181.0	1179.0	1181.0	1183.0	1185.0
147.5°	1236.2	1235.1	1234.5	1233.2	1230.6	1228.1	1225.5	1222.9	1225.5	1228.1	1230.6
150°	1277.5	1276.4	1275.8	1274.9	1273.2	1271.5	1269.7	1268.0	1269.7	1271.5	1273.2
152.5°	1317.9	1316.4	1315.7	1314.8	1313.1	1311.4	1309.7	1308.0	1309.7	1311.4	1313.1
155°	1353.2	1352.3	1351.9	1351.5	1350.6	1349.7	1348.9	1348.0	1348.9	1349.7	1350.6
157.5°	1386.3	1385.7	1385.4	1385.1	1384.5	1384.0	1383.4	1382.8	1383.4	1384.0	1384.5
160°	1416.8	1416.5	1416.4	1416.1	1415.5	1415.0	1414.4	1413.8	1414.4	1415.0	1415.5
162.5°	1442.6	1442.3	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2	1442.2
165°	1465.4	1465.4	1465.4	1465.5	1465.8	1466.1	1466.4	1466.7	1466.4	1466.1	1465.8
167.5°	1484.7	1484.7	1484.7	1485.1	1486.0	1486.9	1487.7	1488.6	1487.7	1486.9	1486.0
170°	1501.1	1501.4	1501.5	1501.9	1502.8	1503.7	1504.5	1505.4	1504.5	1503.7	1502.8
172.5°	1512.7	1513.0	1513.1	1513.5	1514.4	1515.3	1516.1	1517.0	1516.1	1515.3	1514.4
175°	1521.3	1521.8	1522.1	1522.5	1523.4	1524.3	1525.1	1526.0	1525.1	1524.3	1523.4
177.5°	1526.4	1527.0	1527.3	1527.7	1528.6	1529.5	1530.3	1531.2	1530.3	1529.5	1528.6
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	15.1	16.8	19.9	26.2	32.5	38.8	45.1	44.5	44.0	43.4	42.9
92.5°	37.6	38.7	38.8	39.1	39.4	39.7	40.0	40.3	40.6	40.9	41.2
95°	78.6	80.0	80.3	80.9	81.4	82.0	82.6	82.6	82.6	82.6	82.6
97.5°	122.5	123.8	124.4	125.5	126.7	127.8	129.0	129.0	129.0	129.0	129.0
100°	173.0	174.1	174.5	175.4	176.3	177.1	178.0	178.0	178.0	178.0	178.0
102.5°	224.8	225.7	226.3	227.4	228.6	229.7	230.9	231.2	231.5	231.8	232.1
105°	280.8	281.2	281.5	282.1	282.6	283.2	283.8	284.4	285.0	285.5	286.1
107.5°	341.2	341.8	341.8	341.8	341.8	341.8	341.8	342.1	342.4	342.7	343.0
110°	400.3	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	462.2	463.1	463.0	462.7	462.4	462.1	461.8	460.9	460.1	459.2	458.3
115°	522.8	523.7	523.4	522.8	522.3	521.7	521.1	520.8	520.5	520.2	519.9
117.5°	585.8	586.9	586.2	584.8	583.3	581.9	580.5	579.6	578.8	577.9	577.0
120°	646.4	647.6	646.4	644.1	641.8	639.5	637.2	637.2	637.2	637.2	637.2
122.5°	704.2	705.6	704.9	703.5	702.0	700.6	699.2	698.3	697.5	696.6	695.7
125°	761.1	762.4	762.0	761.1	760.2	759.4	758.5	757.6	756.8	755.9	755.0
127.5°	820.1	821.7	821.1	820.0	818.8	817.7	816.5	815.4	814.2	813.1	812.0
130°	875.3	877.2	876.9	876.3	875.8	875.2	874.6	874.0	873.4	872.9	872.3
132.5°	931.2	932.6	932.7	933.0	933.3	933.6	933.9	932.5	931.1	929.6	928.2
135°	983.9	985.5	985.8	986.4	986.9	987.5	988.1	987.8	987.5	987.2	986.9
137.5°	1038.4	1039.7	1040.0	1040.6	1041.1	1041.7	1042.3	1042.0	1041.7	1041.4	1041.1
140°	1088.7	1090.0	1090.7	1092.2	1093.6	1095.1	1096.5	1096.5	1096.5	1096.5	1096.5
142.5°	1140.3	1141.6	1142.0	1142.9	1143.8	1144.6	1145.5	1145.8	1146.1	1146.4	1146.7
145°	1187.0	1188.0	1188.9	1190.6	1192.3	1194.1	1195.8	1196.1	1196.4	1196.7	1197.0
147.5°	1233.2	1234.5	1235.1	1236.2	1237.3	1238.5	1239.6	1240.2	1240.8	1241.3	1241.9
150°	1274.9	1275.8	1276.4	1277.5	1278.6	1279.8	1280.9	1281.8	1282.6	1283.5	1284.4
152.5°	1314.8	1315.7	1316.4	1317.9	1319.3	1320.8	1322.2	1323.4	1324.5	1325.7	1326.8
155°	1351.5	1351.9	1352.3	1353.2	1354.0	1354.9	1355.7	1357.1	1358.6	1360.0	1361.5
157.5°	1385.1	1385.4	1385.7	1386.3	1386.8	1387.4	1388.0	1390.0	1392.0	1394.0	1396.0
160°	1416.1	1416.4	1416.5	1416.8	1417.1	1417.4	1417.7	1419.4	1421.1	1422.8	1424.5
162.5°	1442.2	1442.2	1442.3	1442.6	1442.9	1443.2	1443.5	1445.5	1447.5	1449.5	1451.5
165°	1465.5	1465.4	1465.4	1465.4	1465.4	1465.4	1465.4	1467.4	1469.4	1471.4	1473.4
167.5°	1485.1	1484.7	1484.7	1484.7	1484.7	1484.7	1484.7	1486.7	1488.7	1490.8	1492.8
170°	1501.9	1501.5	1501.4	1501.1	1500.8	1500.5	1500.2	1502.2	1504.2	1506.2	1508.2
172.5°	1513.5	1513.1	1513.0	1512.7	1512.4	1512.1	1511.8	1513.8	1515.8	1517.9	1519.9
175°	1522.5	1522.1	1521.8	1521.3	1520.7	1520.2	1519.6	1521.6	1523.6	1525.6	1527.6
177.5°	1527.7	1527.3	1527.0	1526.4	1525.9	1525.3	1524.7	1526.4	1528.2	1529.9	1531.6
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	42.6	42.7	43.0	43.3	43.6	43.9	43.6	43.3	43.0	42.7	42.6
92.5°	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3	41.3
95°	82.6	82.3	81.7	81.2	80.6	80.0	80.6	81.2	81.7	82.3	82.6
97.5°	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0	129.0
100°	178.0	177.9	177.6	177.3	177.0	176.7	177.0	177.3	177.6	177.9	178.0
102.5°	232.2	232.1	231.8	231.5	231.2	230.9	231.2	231.5	231.8	232.1	232.2
105°	286.4	286.4	286.4	286.4	286.4	286.4	286.4	286.4	286.4	286.4	286.4
107.5°	343.1	342.4	341.0	339.5	338.1	336.7	338.1	339.5	341.0	342.4	343.1
110°	401.2	400.8	399.9	399.0	398.2	397.3	398.2	399.0	399.9	400.8	401.2

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	457.9	457.6	457.1	456.5	456.0	455.4	456.0	456.5	457.1	457.6	457.9
115°	519.8	519.4	518.5	517.7	516.8	516.0	516.8	517.7	518.5	519.4	519.8
117.5°	576.6	576.2	575.3	574.4	573.6	572.7	573.6	574.4	575.3	576.2	576.6
120°	637.2	636.8	635.9	635.1	634.2	633.4	634.2	635.1	635.9	636.8	637.2
122.5°	695.3	695.0	694.4	693.9	693.3	692.7	693.3	693.9	694.4	695.0	695.3
125°	754.6	754.5	754.2	753.9	753.6	753.3	753.6	753.9	754.2	754.5	754.6
127.5°	811.4	811.0	810.1	809.2	808.4	807.5	808.4	809.2	810.1	811.0	811.4
130°	872.0	871.4	870.3	869.1	868.0	866.8	868.0	869.1	870.3	871.4	872.0
132.5°	927.5	927.1	926.2	925.3	924.5	923.6	924.5	925.3	926.2	927.1	927.5
135°	986.8	986.4	985.5	984.6	983.8	982.9	983.8	984.6	985.5	986.4	986.8
137.5°	1041.0	1040.4	1039.3	1038.1	1037.0	1035.8	1037.0	1038.1	1039.3	1040.4	1041.0
140°	1096.5	1095.9	1094.8	1093.6	1092.5	1091.3	1092.5	1093.6	1094.8	1095.9	1096.5
142.5°	1146.8	1146.2	1145.1	1143.9	1142.8	1141.6	1142.8	1143.9	1145.1	1146.2	1146.8
145°	1197.1	1196.5	1195.4	1194.2	1193.1	1191.9	1193.1	1194.2	1195.4	1196.5	1197.1
147.5°	1242.2	1241.6	1240.5	1239.4	1238.2	1237.1	1238.2	1239.4	1240.5	1241.6	1242.2
150°	1284.8	1284.4	1283.5	1282.6	1281.8	1280.9	1281.8	1282.6	1283.5	1284.4	1284.8
152.5°	1327.4	1326.8	1325.7	1324.5	1323.4	1322.2	1323.4	1324.5	1325.7	1326.8	1327.4
155°	1362.2	1361.8	1360.9	1360.0	1359.2	1358.3	1359.2	1360.0	1360.9	1361.8	1362.2
157.5°	1397.0	1396.3	1394.9	1393.4	1392.0	1390.6	1392.0	1393.4	1394.9	1396.3	1397.0
160°	1425.4	1424.8	1423.7	1422.5	1421.4	1420.2	1421.4	1422.5	1423.7	1424.8	1425.4
162.5°	1452.5	1451.8	1450.3	1448.9	1447.4	1446.0	1447.4	1448.9	1450.3	1451.8	1452.5
165°	1474.4	1473.7	1472.3	1470.8	1469.4	1468.0	1469.4	1470.8	1472.3	1473.7	1474.4
167.5°	1493.8	1493.1	1491.6	1490.2	1488.7	1487.3	1488.7	1490.2	1491.6	1493.1	1493.8
170°	1509.2	1508.3	1506.6	1504.9	1503.2	1501.5	1503.2	1504.9	1506.6	1508.3	1509.2
172.5°	1520.9	1520.0	1518.3	1516.6	1514.8	1513.1	1514.8	1516.6	1518.3	1520.0	1520.9
175°	1528.6	1527.7	1526.0	1524.3	1522.6	1520.9	1522.6	1524.3	1526.0	1527.7	1528.6
177.5°	1532.5	1531.6	1529.9	1528.2	1526.4	1524.7	1526.4	1528.2	1529.9	1531.6	1532.5
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	42.9	43.4	44.0	44.5	45.1	38.8	32.5	26.2	19.9	16.8	15.1
92.5°	41.2	40.9	40.6	40.3	40.0	39.7	39.4	39.1	38.8	38.7	37.6
95°	82.6	82.6	82.6	82.6	82.6	82.0	81.4	80.9	80.3	80.0	78.6
97.5°	129.0	129.0	129.0	129.0	129.0	127.8	126.7	125.5	124.4	123.8	122.5
100°	178.0	178.0	178.0	178.0	178.0	177.1	176.3	175.4	174.5	174.1	173.0
102.5°	232.1	231.8	231.5	231.2	230.9	229.7	228.6	227.4	226.3	225.7	224.8
105°	286.1	285.5	285.0	284.4	283.8	283.2	282.6	282.1	281.5	281.2	280.8
107.5°	343.0	342.7	342.4	342.1	341.8	341.8	341.8	341.8	341.8	341.8	341.2
110°	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	401.2	400.3

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	458.3	459.2	460.1	460.9	461.8	462.1	462.4	462.7	463.0	463.1	462.2
115°	519.9	520.2	520.5	520.8	521.1	521.7	522.3	522.8	523.4	523.7	522.8
117.5°	577.0	577.9	578.8	579.6	580.5	581.9	583.3	584.8	586.2	586.9	585.8
120°	637.2	637.2	637.2	637.2	637.2	639.5	641.8	644.1	646.4	647.6	646.4
122.5°	695.7	696.6	697.5	698.3	699.2	700.6	702.0	703.5	704.9	705.6	704.2
125°	755.0	755.9	756.8	757.6	758.5	759.4	760.2	761.1	762.0	762.4	761.1
127.5°	812.0	813.1	814.2	815.4	816.5	817.7	818.8	820.0	821.1	821.7	820.1
130°	872.3	872.9	873.4	874.0	874.6	875.2	875.8	876.3	876.9	877.2	875.3
132.5°	928.2	929.6	931.1	932.5	933.9	933.6	933.3	933.0	932.7	932.6	931.2
135°	986.9	987.2	987.5	987.8	988.1	987.5	986.9	986.4	985.8	985.5	983.9
137.5°	1041.1	1041.4	1041.7	1042.0	1042.3	1041.7	1041.1	1040.6	1040.0	1039.7	1038.4
140°	1096.5	1096.5	1096.5	1096.5	1096.5	1095.1	1093.6	1092.2	1090.7	1090.0	1088.7
142.5°	1146.7	1146.4	1146.1	1145.8	1145.5	1144.6	1143.8	1142.9	1142.0	1141.6	1140.3
145°	1197.0	1196.7	1196.4	1196.1	1195.8	1194.1	1192.3	1190.6	1188.9	1188.0	1187.0
147.5°	1241.9	1241.3	1240.8	1240.2	1239.6	1238.5	1237.3	1236.2	1235.1	1234.5	1233.2
150°	1284.4	1283.5	1282.6	1281.8	1280.9	1279.8	1278.6	1277.5	1276.4	1275.8	1274.9
152.5°	1326.8	1325.7	1324.5	1323.4	1322.2	1320.8	1319.3	1317.9	1316.4	1315.7	1314.8
155°	1361.5	1360.0	1358.6	1357.1	1355.7	1354.9	1354.0	1353.2	1352.3	1351.9	1351.5
157.5°	1396.0	1394.0	1392.0	1390.0	1388.0	1387.4	1386.8	1386.3	1385.7	1385.4	1385.1
160°	1424.5	1422.8	1421.1	1419.4	1417.7	1417.4	1417.1	1416.8	1416.5	1416.4	1416.1
162.5°	1451.5	1449.5	1447.5	1445.5	1443.5	1443.2	1442.9	1442.6	1442.3	1442.2	1442.2
165°	1473.4	1471.4	1469.4	1467.4	1465.4	1465.4	1465.4	1465.4	1465.4	1465.4	1465.5
167.5°	1492.8	1490.8	1488.7	1486.7	1484.7	1484.7	1484.7	1484.7	1484.7	1484.7	1485.1
170°	1508.2	1506.2	1504.2	1502.2	1500.2	1500.5	1500.8	1501.1	1501.4	1501.5	1501.9
172.5°	1519.9	1517.9	1515.8	1513.8	1511.8	1512.1	1512.4	1512.7	1513.0	1513.1	1513.5
175°	1527.6	1525.6	1523.6	1521.6	1519.6	1520.2	1520.7	1521.3	1521.8	1522.1	1522.5
177.5°	1531.6	1529.9	1528.2	1526.4	1524.7	1525.3	1525.9	1526.4	1527.0	1527.3	1527.7
180°	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6	1528.6

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	11.6	8.2	4.7	1.3
92.5°	35.3	33.0	30.7	28.4
95°	75.7	72.8	70.0	67.1
97.5°	119.9	117.4	114.8	112.2
100°	170.7	168.4	166.1	163.8
102.5°	223.1	221.4	219.7	218.0
105°	279.9	279.0	278.2	277.3
107.5°	340.1	339.0	337.8	336.7
110°	398.6	396.9	395.1	393.4

TEST NUMBER: P1029304

CATALOG NUMBER: S122DIW-B290D1240UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	460.5	458.8	457.1	455.4
115°	521.1	519.4	517.7	516.0
117.5°	583.5	581.2	578.9	576.6
120°	644.1	641.8	639.5	637.2
122.5°	701.3	698.4	695.6	692.7
125°	758.5	756.0	753.4	750.8
127.5°	817.0	813.8	810.7	807.5
130°	871.6	867.9	864.1	860.4
132.5°	928.3	925.4	922.6	919.7
135°	980.8	977.6	974.5	971.3
137.5°	1035.8	1033.3	1030.7	1028.1
140°	1086.1	1083.6	1081.0	1078.4
142.5°	1137.7	1135.2	1132.6	1130.0
145°	1185.0	1183.0	1181.0	1179.0
147.5°	1230.6	1228.1	1225.5	1222.9
150°	1273.2	1271.5	1269.7	1268.0
152.5°	1313.1	1311.4	1309.7	1308.0
155°	1350.6	1349.7	1348.9	1348.0
157.5°	1384.5	1384.0	1383.4	1382.8
160°	1415.5	1415.0	1414.4	1413.8
162.5°	1442.2	1442.2	1442.2	1442.2
165°	1465.8	1466.1	1466.4	1466.7
167.5°	1486.0	1486.9	1487.7	1488.6
170°	1502.8	1503.7	1504.5	1505.4
172.5°	1514.4	1515.3	1516.1	1517.0
175°	1523.4	1524.3	1525.1	1526.0
177.5°	1528.6	1529.5	1530.3	1531.2
180°	1528.6	1528.6	1528.6	1528.6

(END OF REPORT)