

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029331

Luminaire Tested: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029331
REPORT IS A COMBINATION OF REPORTS P985567 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K
Description: Define 2 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6287.0 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	41	40	39	26	25	24	24	24	17
2	83	76	71	66	73	68	63	59	51	48	46	37	35	33	23	22	21	21	21	15
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18	18	18	13
4	69	59	52	46	61	53	47	42	40	36	33	29	26	24	18	17	16	16	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	16	15	14	14	14	10
6	59	47	40	34	52	42	36	31	32	28	25	23	20	18	15	13	12	12	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10	10	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	0.9
10°-20°	158.1	2.5
20°-30°	229.4	3.6
30°-40°	241.8	3.8
40°-50°	214.0	3.4
50°-60°	170.9	2.7
60°-70°	116.1	1.8
70°-80°	59.4	0.9
80°-90°	19.1	0.3
90°-100°	111.1	1.8
100°-110°	353.4	5.6
110°-120°	604.7	9.6
120°-130°	795.2	12.6
130°-140°	892.6	14.2
140°-150°	875.4	13.9
150°-160°	734.3	11.7
160°-170°	487.0	7.7
170°-180°	170.2	2.7
0°-30°	441.8	7.0
0°-40°	683.6	10.9
0°-60°	1068.5	17.0
0°-90°	1263.1	20.1
90°-120°	1069.2	17.0
90°-150°	3632.4	57.8
90°-180°	5024.0	79.9
0°-180°	6287.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	2	52	2	52	2	6
95°	79	94	79	94	79	88
105°	326	337	326	337	326	344
115°	607	607	607	607	607	600
125°	882	886	882	886	882	789
135°	1142	1156	1142	1156	1142	882
145°	1386	1401	1386	1401	1386	866
155°	1585	1597	1585	1597	1585	729
165°	1724	1726	1724	1726	1724	486
175°	1794	1788	1794	1788	1794	170
180°	1797	1797	1797	1797	1797	

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	1.5	5.5	9.6	13.6	17.7	19.7	23.4	30.8	38.3	45.7	53.1
92.5°	33.4	36.1	38.8	41.5	44.2	45.5	45.7	46.0	46.3	46.7	47.0
95°	78.9	82.3	85.6	89.0	92.3	94.0	94.3	95.0	95.7	96.3	97.0
97.5°	131.9	134.9	138.0	141.0	144.1	145.6	146.3	147.6	148.9	150.3	151.6
100°	192.6	195.3	198.0	200.7	203.4	204.7	205.2	206.2	207.3	208.3	209.3
102.5°	256.3	258.3	260.3	262.4	264.4	265.4	266.1	267.4	268.7	270.1	271.4
105°	326.0	327.0	328.0	329.1	330.1	330.6	330.9	331.6	332.3	332.9	333.6
107.5°	395.8	397.1	398.5	399.8	401.1	401.8	401.8	401.8	401.8	401.8	401.8
110°	462.5	464.5	466.5	468.6	470.6	471.6	471.6	471.6	471.6	471.6	471.6



TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	535.3	537.3	539.3	541.4	543.4	544.4	544.2	543.9	543.6	543.2	542.9
115°	606.6	608.6	610.6	612.7	614.7	615.7	615.4	614.7	614.0	613.3	612.6
117.5°	677.8	680.5	683.2	685.9	688.6	690.0	689.2	687.5	685.8	684.1	682.4
120°	749.1	751.8	754.5	757.2	759.9	761.2	759.9	757.2	754.5	751.8	749.1
122.5°	814.3	817.7	821.1	824.4	827.8	829.5	828.7	827.0	825.3	823.6	821.9
125°	882.5	885.5	888.6	891.6	894.7	896.2	895.7	894.7	893.6	892.6	891.6
127.5°	949.3	953.0	956.7	960.4	964.1	965.9	965.2	963.9	962.6	961.2	959.9
130°	1011.4	1015.8	1020.2	1024.6	1029.0	1031.2	1030.9	1030.2	1029.5	1028.8	1028.1
132.5°	1081.2	1084.6	1088.0	1091.3	1094.7	1096.4	1096.6	1096.9	1097.2	1097.6	1097.9
135°	1141.8	1145.5	1149.2	1152.9	1156.6	1158.5	1158.8	1159.5	1160.2	1160.9	1161.6
137.5°	1208.6	1211.6	1214.6	1217.7	1220.7	1222.2	1222.5	1223.2	1223.9	1224.6	1225.3
140°	1267.7	1270.7	1273.8	1276.8	1279.9	1281.4	1282.2	1283.9	1285.6	1287.2	1288.9
142.5°	1328.4	1331.4	1334.4	1337.5	1340.5	1342.0	1342.5	1343.5	1344.6	1345.6	1346.6
145°	1386.0	1388.4	1390.7	1393.1	1395.4	1396.6	1397.6	1399.6	1401.7	1403.7	1405.7
147.5°	1437.5	1440.5	1443.6	1446.6	1449.7	1451.2	1451.9	1453.2	1454.6	1455.9	1457.3
150°	1490.6	1492.6	1494.6	1496.7	1498.7	1499.7	1500.4	1501.7	1503.1	1504.4	1505.8
152.5°	1537.6	1539.6	1541.6	1543.7	1545.7	1546.7	1547.5	1549.2	1550.9	1552.6	1554.3
155°	1584.6	1585.6	1586.6	1587.7	1588.7	1589.2	1589.7	1590.7	1591.7	1592.7	1593.7
157.5°	1625.6	1626.3	1626.9	1627.6	1628.3	1628.6	1628.9	1629.6	1630.3	1630.9	1631.6
160°	1662.0	1662.7	1663.3	1664.0	1664.7	1665.0	1665.2	1665.5	1665.8	1666.2	1666.5
162.5°	1695.3	1695.3	1695.3	1695.3	1695.3	1695.3	1695.5	1695.8	1696.2	1696.5	1696.9
165°	1724.1	1723.8	1723.4	1723.1	1722.8	1722.6	1722.6	1722.6	1722.6	1722.6	1722.6
167.5°	1749.9	1748.9	1747.9	1746.9	1745.9	1745.4	1745.4	1745.4	1745.4	1745.4	1745.4
170°	1769.6	1768.6	1767.6	1766.6	1765.6	1765.1	1764.9	1764.6	1764.3	1763.9	1763.6
172.5°	1783.3	1782.3	1781.3	1780.2	1779.2	1778.7	1778.5	1778.2	1777.9	1777.5	1777.2
175°	1793.9	1792.9	1791.9	1790.9	1789.9	1789.4	1789.1	1788.4	1787.7	1787.0	1786.3
177.5°	1800.0	1799.0	1798.0	1796.9	1795.9	1795.4	1795.1	1794.4	1793.7	1793.1	1792.4
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	52.4	51.7	51.0	50.3	50.0	50.2	50.5	50.9	51.2	51.6	51.2
92.5°	47.3	47.7	48.0	48.3	48.5	48.5	48.5	48.5	48.5	48.5	48.5
95°	97.0	97.0	97.0	97.0	97.0	96.7	96.0	95.3	94.7	94.0	94.7
97.5°	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6
100°	209.3	209.3	209.3	209.3	209.3	209.1	208.8	208.4	208.1	207.7	208.1
102.5°	271.8	272.1	272.5	272.8	273.0	272.8	272.5	272.1	271.8	271.4	271.8
105°	334.3	334.9	335.6	336.3	336.6	336.6	336.6	336.6	336.6	336.6	336.6
107.5°	402.2	402.5	402.9	403.2	403.4	402.6	400.9	399.2	397.5	395.8	397.5
110°	471.6	471.6	471.6	471.6	471.6	471.1	470.1	469.1	468.1	467.1	468.1

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	541.9	540.9	539.8	538.8	538.3	538.0	537.3	536.6	536.0	535.3	536.0
115°	612.3	611.9	611.6	611.3	611.1	610.6	609.6	608.6	607.6	606.6	607.6
117.5°	681.4	680.4	679.3	678.3	677.8	677.3	676.3	675.3	674.3	673.3	674.3
120°	749.1	749.1	749.1	749.1	749.1	748.6	747.6	746.6	745.6	744.6	745.6
122.5°	820.9	819.9	818.8	817.8	817.3	817.0	816.3	815.6	815.0	814.3	815.0
125°	890.6	889.6	888.6	887.6	887.1	886.9	886.6	886.3	885.9	885.6	885.9
127.5°	958.5	957.2	955.8	954.5	953.8	953.3	952.3	951.3	950.3	949.3	950.3
130°	1027.4	1026.8	1026.1	1025.4	1025.1	1024.4	1023.1	1021.7	1020.4	1019.0	1020.4
132.5°	1096.2	1094.5	1092.8	1091.1	1090.3	1089.8	1088.8	1087.7	1086.7	1085.7	1086.7
135°	1161.2	1160.9	1160.5	1160.2	1160.0	1159.5	1158.5	1157.5	1156.5	1155.5	1156.5
137.5°	1224.9	1224.6	1224.2	1223.9	1223.7	1223.0	1221.7	1220.4	1219.0	1217.7	1219.0
140°	1288.9	1288.9	1288.9	1288.9	1288.9	1288.2	1286.9	1285.6	1284.2	1282.9	1284.2
142.5°	1346.9	1347.3	1347.6	1347.9	1348.1	1347.4	1346.1	1344.7	1343.4	1342.0	1343.4
145°	1406.0	1406.4	1406.7	1407.0	1407.2	1406.5	1405.2	1403.9	1402.5	1401.2	1402.5
147.5°	1458.0	1458.6	1459.3	1460.0	1460.3	1459.6	1458.3	1456.9	1455.6	1454.2	1455.6
150°	1506.8	1507.8	1508.8	1509.8	1510.3	1509.8	1508.8	1507.8	1506.8	1505.8	1506.8
152.5°	1555.7	1557.0	1558.4	1559.7	1560.4	1559.7	1558.4	1557.0	1555.7	1554.3	1555.7
155°	1595.4	1597.1	1598.8	1600.5	1601.3	1600.8	1599.8	1598.8	1597.8	1596.8	1597.8
157.5°	1634.0	1636.4	1638.7	1641.1	1642.3	1641.5	1639.8	1638.1	1636.4	1634.7	1636.4
160°	1668.5	1670.5	1672.6	1674.6	1675.6	1674.9	1673.6	1672.3	1670.9	1669.6	1670.9
162.5°	1699.3	1701.6	1704.0	1706.3	1707.5	1706.7	1705.0	1703.3	1701.6	1699.9	1701.6
165°	1725.0	1727.3	1729.7	1732.0	1733.2	1732.4	1730.7	1729.0	1727.4	1725.7	1727.4
167.5°	1747.8	1750.1	1752.5	1754.8	1756.0	1755.2	1753.5	1751.8	1750.1	1748.4	1750.1
170°	1766.0	1768.3	1770.7	1773.0	1774.2	1773.2	1771.2	1769.1	1767.1	1765.1	1767.1
172.5°	1779.6	1781.9	1784.3	1786.6	1787.8	1786.8	1784.8	1782.7	1780.7	1778.7	1780.7
175°	1788.7	1791.0	1793.4	1795.7	1796.9	1795.9	1793.9	1791.8	1789.8	1787.8	1789.8
177.5°	1794.4	1796.4	1798.5	1800.5	1801.5	1800.5	1798.5	1796.4	1794.4	1792.4	1794.4
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	50.9	50.5	50.2	50.0	50.3	51.0	51.7	52.4	53.1	45.7	38.3
92.5°	48.5	48.5	48.5	48.5	48.3	48.0	47.7	47.3	47.0	46.7	46.3
95°	95.3	96.0	96.7	97.0	97.0	97.0	97.0	97.0	97.0	96.3	95.7
97.5°	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	150.3	148.9
100°	208.4	208.8	209.1	209.3	209.3	209.3	209.3	209.3	209.3	208.3	207.3
102.5°	272.1	272.5	272.8	273.0	272.8	272.5	272.1	271.8	271.4	270.1	268.7
105°	336.6	336.6	336.6	336.6	336.3	335.6	334.9	334.3	333.6	332.9	332.3
107.5°	399.2	400.9	402.6	403.4	403.2	402.9	402.5	402.2	401.8	401.8	401.8
110°	469.1	470.1	471.1	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	536.6	537.3	538.0	538.3	538.8	539.8	540.9	541.9	542.9	543.2	543.6
115°	608.6	609.6	610.6	611.1	611.3	611.6	611.9	612.3	612.6	613.3	614.0
117.5°	675.3	676.3	677.3	677.8	678.3	679.3	680.4	681.4	682.4	684.1	685.8
120°	746.6	747.6	748.6	749.1	749.1	749.1	749.1	749.1	749.1	751.8	754.5
122.5°	815.6	816.3	817.0	817.3	817.8	818.8	819.9	820.9	821.9	823.6	825.3
125°	886.3	886.6	886.9	887.1	887.6	888.6	889.6	890.6	891.6	892.6	893.6
127.5°	951.3	952.3	953.3	953.8	954.5	955.8	957.2	958.5	959.9	961.2	962.6
130°	1021.7	1023.1	1024.4	1025.1	1025.4	1026.1	1026.8	1027.4	1028.1	1028.8	1029.5
132.5°	1087.7	1088.8	1089.8	1090.3	1091.1	1092.8	1094.5	1096.2	1097.9	1097.6	1097.2
135°	1157.5	1158.5	1159.5	1160.0	1160.2	1160.5	1160.9	1161.2	1161.6	1160.9	1160.2
137.5°	1220.4	1221.7	1223.0	1223.7	1223.9	1224.2	1224.6	1224.9	1225.3	1224.6	1223.9
140°	1285.6	1286.9	1288.2	1288.9	1288.9	1288.9	1288.9	1288.9	1288.9	1287.2	1285.6
142.5°	1344.7	1346.1	1347.4	1348.1	1347.9	1347.6	1347.3	1346.9	1346.6	1345.6	1344.6
145°	1403.9	1405.2	1406.5	1407.2	1407.0	1406.7	1406.4	1406.0	1405.7	1403.7	1401.7
147.5°	1456.9	1458.3	1459.6	1460.3	1460.0	1459.3	1458.6	1458.0	1457.3	1455.9	1454.6
150°	1507.8	1508.8	1509.8	1510.3	1509.8	1508.8	1507.8	1506.8	1505.8	1504.4	1503.1
152.5°	1557.0	1558.4	1559.7	1560.4	1559.7	1558.4	1557.0	1555.7	1554.3	1552.6	1550.9
155°	1598.8	1599.8	1600.8	1601.3	1600.5	1598.8	1597.1	1595.4	1593.7	1592.7	1591.7
157.5°	1638.1	1639.8	1641.5	1642.3	1641.1	1638.7	1636.4	1634.0	1631.6	1630.9	1630.3
160°	1672.3	1673.6	1674.9	1675.6	1674.6	1672.6	1670.5	1668.5	1666.5	1666.2	1665.8
162.5°	1703.3	1705.0	1706.7	1707.5	1706.3	1704.0	1701.6	1699.3	1696.9	1696.5	1696.2
165°	1729.0	1730.7	1732.4	1733.2	1732.0	1729.7	1727.3	1725.0	1722.6	1722.6	1722.6
167.5°	1751.8	1753.5	1755.2	1756.0	1754.8	1752.5	1750.1	1747.8	1745.4	1745.4	1745.4
170°	1769.1	1771.2	1773.2	1774.2	1773.0	1770.7	1768.3	1766.0	1763.6	1763.9	1764.3
172.5°	1782.7	1784.8	1786.8	1787.8	1786.6	1784.3	1781.9	1779.6	1777.2	1777.5	1777.9
175°	1791.8	1793.9	1795.9	1796.9	1795.7	1793.4	1791.0	1788.7	1786.3	1787.0	1787.7
177.5°	1796.4	1798.5	1800.5	1801.5	1800.5	1798.5	1796.4	1794.4	1792.4	1793.1	1793.7
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	30.8	23.4	19.7	17.7	13.6	9.6	5.5	1.5	5.5	9.6	13.6
92.5°	46.0	45.7	45.5	44.2	41.5	38.8	36.1	33.4	36.1	38.8	41.5
95°	95.0	94.3	94.0	92.3	89.0	85.6	82.3	78.9	82.3	85.6	89.0
97.5°	147.6	146.3	145.6	144.1	141.0	138.0	134.9	131.9	134.9	138.0	141.0
100°	206.2	205.2	204.7	203.4	200.7	198.0	195.3	192.6	195.3	198.0	200.7
102.5°	267.4	266.1	265.4	264.4	262.4	260.3	258.3	256.3	258.3	260.3	262.4
105°	331.6	330.9	330.6	330.1	329.1	328.0	327.0	326.0	327.0	328.0	329.1
107.5°	401.8	401.8	401.8	401.1	399.8	398.5	397.1	395.8	397.1	398.5	399.8
110°	471.6	471.6	471.6	470.6	468.6	466.5	464.5	462.5	464.5	466.5	468.6

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	543.9	544.2	544.4	543.4	541.4	539.3	537.3	535.3	537.3	539.3	541.4
115°	614.7	615.4	615.7	614.7	612.7	610.6	608.6	606.6	608.6	610.6	612.7
117.5°	687.5	689.2	690.0	688.6	685.9	683.2	680.5	677.8	680.5	683.2	685.9
120°	757.2	759.9	761.2	759.9	757.2	754.5	751.8	749.1	751.8	754.5	757.2
122.5°	827.0	828.7	829.5	827.8	824.4	821.1	817.7	814.3	817.7	821.1	824.4
125°	894.7	895.7	896.2	894.7	891.6	888.6	885.5	882.5	885.5	888.6	891.6
127.5°	963.9	965.2	965.9	964.1	960.4	956.7	953.0	949.3	953.0	956.7	960.4
130°	1030.2	1030.9	1031.2	1029.0	1024.6	1020.2	1015.8	1011.4	1015.8	1020.2	1024.6
132.5°	1096.9	1096.6	1096.4	1094.7	1091.3	1088.0	1084.6	1081.2	1084.6	1088.0	1091.3
135°	1159.5	1158.8	1158.5	1156.6	1152.9	1149.2	1145.5	1141.8	1145.5	1149.2	1152.9
137.5°	1223.2	1222.5	1222.2	1220.7	1217.7	1214.6	1211.6	1208.6	1211.6	1214.6	1217.7
140°	1283.9	1282.2	1281.4	1279.9	1276.8	1273.8	1270.7	1267.7	1270.7	1273.8	1276.8
142.5°	1343.5	1342.5	1342.0	1340.5	1337.5	1334.4	1331.4	1328.4	1331.4	1334.4	1337.5
145°	1399.6	1397.6	1396.6	1395.4	1393.1	1390.7	1388.4	1386.0	1388.4	1390.7	1393.1
147.5°	1453.2	1451.9	1451.2	1449.7	1446.6	1443.6	1440.5	1437.5	1440.5	1443.6	1446.6
150°	1501.7	1500.4	1499.7	1498.7	1496.7	1494.6	1492.6	1490.6	1492.6	1494.6	1496.7
152.5°	1549.2	1547.5	1546.7	1545.7	1543.7	1541.6	1539.6	1537.6	1539.6	1541.6	1543.7
155°	1590.7	1589.7	1589.2	1588.7	1587.7	1586.6	1585.6	1584.6	1585.6	1586.6	1587.7
157.5°	1629.6	1628.9	1628.6	1628.3	1627.6	1626.9	1626.3	1625.6	1626.3	1626.9	1627.6
160°	1665.5	1665.2	1665.0	1664.7	1664.0	1663.3	1662.7	1662.0	1662.7	1663.3	1664.0
162.5°	1695.8	1695.5	1695.3	1695.3	1695.3	1695.3	1695.3	1695.3	1695.3	1695.3	1695.3
165°	1722.6	1722.6	1722.6	1722.8	1723.1	1723.4	1723.8	1724.1	1723.8	1723.4	1723.1
167.5°	1745.4	1745.4	1745.4	1745.9	1746.9	1747.9	1748.9	1749.9	1748.9	1747.9	1746.9
170°	1764.6	1764.9	1765.1	1765.6	1766.6	1767.6	1768.6	1769.6	1768.6	1767.6	1766.6
172.5°	1778.2	1778.5	1778.7	1779.2	1780.2	1781.3	1782.3	1783.3	1782.3	1781.3	1780.2
175°	1788.4	1789.1	1789.4	1789.9	1790.9	1791.9	1792.9	1793.9	1792.9	1791.9	1790.9
177.5°	1794.4	1795.1	1795.4	1795.9	1796.9	1798.0	1799.0	1800.0	1799.0	1798.0	1796.9
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	17.7	19.7	23.4	30.8	38.3	45.7	53.1	52.4	51.7	51.0	50.3
92.5°	44.2	45.5	45.7	46.0	46.3	46.7	47.0	47.3	47.7	48.0	48.3
95°	92.3	94.0	94.3	95.0	95.7	96.3	97.0	97.0	97.0	97.0	97.0
97.5°	144.1	145.6	146.3	147.6	148.9	150.3	151.6	151.6	151.6	151.6	151.6
100°	203.4	204.7	205.2	206.2	207.3	208.3	209.3	209.3	209.3	209.3	209.3
102.5°	264.4	265.4	266.1	267.4	268.7	270.1	271.4	271.8	272.1	272.5	272.8
105°	330.1	330.6	330.9	331.6	332.3	332.9	333.6	334.3	334.9	335.6	336.3
107.5°	401.1	401.8	401.8	401.8	401.8	401.8	401.8	402.2	402.5	402.9	403.2
110°	470.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	543.4	544.4	544.2	543.9	543.6	543.2	542.9	541.9	540.9	539.8	538.8
115°	614.7	615.7	615.4	614.7	614.0	613.3	612.6	612.3	611.9	611.6	611.3
117.5°	688.6	690.0	689.2	687.5	685.8	684.1	682.4	681.4	680.4	679.3	678.3
120°	759.9	761.2	759.9	757.2	754.5	751.8	749.1	749.1	749.1	749.1	749.1
122.5°	827.8	829.5	828.7	827.0	825.3	823.6	821.9	820.9	819.9	818.8	817.8
125°	894.7	896.2	895.7	894.7	893.6	892.6	891.6	890.6	889.6	888.6	887.6
127.5°	964.1	965.9	965.2	963.9	962.6	961.2	959.9	958.5	957.2	955.8	954.5
130°	1029.0	1031.2	1030.9	1030.2	1029.5	1028.8	1028.1	1027.4	1026.8	1026.1	1025.4
132.5°	1094.7	1096.4	1096.6	1096.9	1097.2	1097.6	1097.9	1096.2	1094.5	1092.8	1091.1
135°	1156.6	1158.5	1158.8	1159.5	1160.2	1160.9	1161.6	1161.2	1160.9	1160.5	1160.2
137.5°	1220.7	1222.2	1222.5	1223.2	1223.9	1224.6	1225.3	1224.9	1224.6	1224.2	1223.9
140°	1279.9	1281.4	1282.2	1283.9	1285.6	1287.2	1288.9	1288.9	1288.9	1288.9	1288.9
142.5°	1340.5	1342.0	1342.5	1343.5	1344.6	1345.6	1346.6	1346.9	1347.3	1347.6	1347.9
145°	1395.4	1396.6	1397.6	1399.6	1401.7	1403.7	1405.7	1406.0	1406.4	1406.7	1407.0
147.5°	1449.7	1451.2	1451.9	1453.2	1454.6	1455.9	1457.3	1458.0	1458.6	1459.3	1460.0
150°	1498.7	1499.7	1500.4	1501.7	1503.1	1504.4	1505.8	1506.8	1507.8	1508.8	1509.8
152.5°	1545.7	1546.7	1547.5	1549.2	1550.9	1552.6	1554.3	1555.7	1557.0	1558.4	1559.7
155°	1588.7	1589.2	1589.7	1590.7	1591.7	1592.7	1593.7	1595.4	1597.1	1598.8	1600.5
157.5°	1628.3	1628.6	1628.9	1629.6	1630.3	1630.9	1631.6	1634.0	1636.4	1638.7	1641.1
160°	1664.7	1665.0	1665.2	1665.5	1665.8	1666.2	1666.5	1668.5	1670.5	1672.6	1674.6
162.5°	1695.3	1695.3	1695.5	1695.8	1696.2	1696.5	1696.9	1699.3	1701.6	1704.0	1706.3
165°	1722.8	1722.6	1722.6	1722.6	1722.6	1722.6	1722.6	1725.0	1727.3	1729.7	1732.0
167.5°	1745.9	1745.4	1745.4	1745.4	1745.4	1745.4	1745.4	1747.8	1750.1	1752.5	1754.8
170°	1765.6	1765.1	1764.9	1764.6	1764.3	1763.9	1763.6	1766.0	1768.3	1770.7	1773.0
172.5°	1779.2	1778.7	1778.5	1778.2	1777.9	1777.5	1777.2	1779.6	1781.9	1784.3	1786.6
175°	1789.9	1789.4	1789.1	1788.4	1787.7	1787.0	1786.3	1788.7	1791.0	1793.4	1795.7
177.5°	1795.9	1795.4	1795.1	1794.4	1793.7	1793.1	1792.4	1794.4	1796.4	1798.5	1800.5
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	50.0	50.2	50.5	50.9	51.2	51.6	51.2	50.9	50.5	50.2	50.0
92.5°	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
95°	97.0	96.7	96.0	95.3	94.7	94.0	94.7	95.3	96.0	96.7	97.0
97.5°	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6	151.6
100°	209.3	209.1	208.8	208.4	208.1	207.7	208.1	208.4	208.8	209.1	209.3
102.5°	273.0	272.8	272.5	272.1	271.8	271.4	271.8	272.1	272.5	272.8	273.0
105°	336.6	336.6	336.6	336.6	336.6	336.6	336.6	336.6	336.6	336.6	336.6
107.5°	403.4	402.6	400.9	399.2	397.5	395.8	397.5	399.2	400.9	402.6	403.4
110°	471.6	471.1	470.1	469.1	468.1	467.1	468.1	469.1	470.1	471.1	471.6

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	538.3	538.0	537.3	536.6	536.0	535.3	536.0	536.6	537.3	538.0	538.3
115°	611.1	610.6	609.6	608.6	607.6	606.6	607.6	608.6	609.6	610.6	611.1
117.5°	677.8	677.3	676.3	675.3	674.3	673.3	674.3	675.3	676.3	677.3	677.8
120°	749.1	748.6	747.6	746.6	745.6	744.6	745.6	746.6	747.6	748.6	749.1
122.5°	817.3	817.0	816.3	815.6	815.0	814.3	815.0	815.6	816.3	817.0	817.3
125°	887.1	886.9	886.6	886.3	885.9	885.6	885.9	886.3	886.6	886.9	887.1
127.5°	953.8	953.3	952.3	951.3	950.3	949.3	950.3	951.3	952.3	953.3	953.8
130°	1025.1	1024.4	1023.1	1021.7	1020.4	1019.0	1020.4	1021.7	1023.1	1024.4	1025.1
132.5°	1090.3	1089.8	1088.8	1087.7	1086.7	1085.7	1086.7	1087.7	1088.8	1089.8	1090.3
135°	1160.0	1159.5	1158.5	1157.5	1156.5	1155.5	1156.5	1157.5	1158.5	1159.5	1160.0
137.5°	1223.7	1223.0	1221.7	1220.4	1219.0	1217.7	1219.0	1220.4	1221.7	1223.0	1223.7
140°	1288.9	1288.2	1286.9	1285.6	1284.2	1282.9	1284.2	1285.6	1286.9	1288.2	1288.9
142.5°	1348.1	1347.4	1346.1	1344.7	1343.4	1342.0	1343.4	1344.7	1346.1	1347.4	1348.1
145°	1407.2	1406.5	1405.2	1403.9	1402.5	1401.2	1402.5	1403.9	1405.2	1406.5	1407.2
147.5°	1460.3	1459.6	1458.3	1456.9	1455.6	1454.2	1455.6	1456.9	1458.3	1459.6	1460.3
150°	1510.3	1509.8	1508.8	1507.8	1506.8	1505.8	1506.8	1507.8	1508.8	1509.8	1510.3
152.5°	1560.4	1559.7	1558.4	1557.0	1555.7	1554.3	1555.7	1557.0	1558.4	1559.7	1560.4
155°	1601.3	1600.8	1599.8	1598.8	1597.8	1596.8	1597.8	1598.8	1599.8	1600.8	1601.3
157.5°	1642.3	1641.5	1639.8	1638.1	1636.4	1634.7	1636.4	1638.1	1639.8	1641.5	1642.3
160°	1675.6	1674.9	1673.6	1672.3	1670.9	1669.6	1670.9	1672.3	1673.6	1674.9	1675.6
162.5°	1707.5	1706.7	1705.0	1703.3	1701.6	1699.9	1701.6	1703.3	1705.0	1706.7	1707.5
165°	1733.2	1732.4	1730.7	1729.0	1727.4	1725.7	1727.4	1729.0	1730.7	1732.4	1733.2
167.5°	1756.0	1755.2	1753.5	1751.8	1750.1	1748.4	1750.1	1751.8	1753.5	1755.2	1756.0
170°	1774.2	1773.2	1771.2	1769.1	1767.1	1765.1	1767.1	1769.1	1771.2	1773.2	1774.2
172.5°	1787.8	1786.8	1784.8	1782.7	1780.7	1778.7	1780.7	1782.7	1784.8	1786.8	1787.8
175°	1796.9	1795.9	1793.9	1791.8	1789.8	1787.8	1789.8	1791.8	1793.9	1795.9	1796.9
177.5°	1801.5	1800.5	1798.5	1796.4	1794.4	1792.4	1794.4	1796.4	1798.5	1800.5	1801.5
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	50.3	51.0	51.7	52.4	53.1	45.7	38.3	30.8	23.4	19.7	17.7
92.5°	48.3	48.0	47.7	47.3	47.0	46.7	46.3	46.0	45.7	45.5	44.2
95°	97.0	97.0	97.0	97.0	97.0	96.3	95.7	95.0	94.3	94.0	92.3
97.5°	151.6	151.6	151.6	151.6	151.6	150.3	148.9	147.6	146.3	145.6	144.1
100°	209.3	209.3	209.3	209.3	209.3	208.3	207.3	206.2	205.2	204.7	203.4
102.5°	272.8	272.5	272.1	271.8	271.4	270.1	268.7	267.4	266.1	265.4	264.4
105°	336.3	335.6	334.9	334.3	333.6	332.9	332.3	331.6	330.9	330.6	330.1
107.5°	403.2	402.9	402.5	402.2	401.8	401.8	401.8	401.8	401.8	401.8	401.1
110°	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	471.6	470.6



TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	538.8	539.8	540.9	541.9	542.9	543.2	543.6	543.9	544.2	544.4	543.4
115°	611.3	611.6	611.9	612.3	612.6	613.3	614.0	614.7	615.4	615.7	614.7
117.5°	678.3	679.3	680.4	681.4	682.4	684.1	685.8	687.5	689.2	690.0	688.6
120°	749.1	749.1	749.1	749.1	749.1	751.8	754.5	757.2	759.9	761.2	759.9
122.5°	817.8	818.8	819.9	820.9	821.9	823.6	825.3	827.0	828.7	829.5	827.8
125°	887.6	888.6	889.6	890.6	891.6	892.6	893.6	894.7	895.7	896.2	894.7
127.5°	954.5	955.8	957.2	958.5	959.9	961.2	962.6	963.9	965.2	965.9	964.1
130°	1025.4	1026.1	1026.8	1027.4	1028.1	1028.8	1029.5	1030.2	1030.9	1031.2	1029.0
132.5°	1091.1	1092.8	1094.5	1096.2	1097.9	1097.6	1097.2	1096.9	1096.6	1096.4	1094.7
135°	1160.2	1160.5	1160.9	1161.2	1161.6	1160.9	1160.2	1159.5	1158.8	1158.5	1156.6
137.5°	1223.9	1224.2	1224.6	1224.9	1225.3	1224.6	1223.9	1223.2	1222.5	1222.2	1220.7
140°	1288.9	1288.9	1288.9	1288.9	1288.9	1287.2	1285.6	1283.9	1282.2	1281.4	1279.9
142.5°	1347.9	1347.6	1347.3	1346.9	1346.6	1345.6	1344.6	1343.5	1342.5	1342.0	1340.5
145°	1407.0	1406.7	1406.4	1406.0	1405.7	1403.7	1401.7	1399.6	1397.6	1396.6	1395.4
147.5°	1460.0	1459.3	1458.6	1458.0	1457.3	1455.9	1454.6	1453.2	1451.9	1451.2	1449.7
150°	1509.8	1508.8	1507.8	1506.8	1505.8	1504.4	1503.1	1501.7	1500.4	1499.7	1498.7
152.5°	1559.7	1558.4	1557.0	1555.7	1554.3	1552.6	1550.9	1549.2	1547.5	1546.7	1545.7
155°	1600.5	1598.8	1597.1	1595.4	1593.7	1592.7	1591.7	1590.7	1589.7	1589.2	1588.7
157.5°	1641.1	1638.7	1636.4	1634.0	1631.6	1630.9	1630.3	1629.6	1628.9	1628.6	1628.3
160°	1674.6	1672.6	1670.5	1668.5	1666.5	1666.2	1665.8	1665.5	1665.2	1665.0	1664.7
162.5°	1706.3	1704.0	1701.6	1699.3	1696.9	1696.5	1696.2	1695.8	1695.5	1695.3	1695.3
165°	1732.0	1729.7	1727.3	1725.0	1722.6	1722.6	1722.6	1722.6	1722.6	1722.6	1722.8
167.5°	1754.8	1752.5	1750.1	1747.8	1745.4	1745.4	1745.4	1745.4	1745.4	1745.4	1745.9
170°	1773.0	1770.7	1768.3	1766.0	1763.6	1763.9	1764.3	1764.6	1764.9	1765.1	1765.6
172.5°	1786.6	1784.3	1781.9	1779.6	1777.2	1777.5	1777.9	1778.2	1778.5	1778.7	1779.2
175°	1795.7	1793.4	1791.0	1788.7	1786.3	1787.0	1787.7	1788.4	1789.1	1789.4	1789.9
177.5°	1800.5	1798.5	1796.4	1794.4	1792.4	1793.1	1793.7	1794.4	1795.1	1795.4	1795.9
180°	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9	1796.9

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	13.6	9.6	5.5	1.5
92.5°	41.5	38.8	36.1	33.4
95°	89.0	85.6	82.3	78.9
97.5°	141.0	138.0	134.9	131.9
100°	200.7	198.0	195.3	192.6
102.5°	262.4	260.3	258.3	256.3
105°	329.1	328.0	327.0	326.0
107.5°	399.8	398.5	397.1	395.8
110°	468.6	466.5	464.5	462.5

TEST NUMBER: P1029331

CATALOG NUMBER: S122DIW-B290D1440UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	541.4	539.3	537.3	535.3
115°	612.7	610.6	608.6	606.6
117.5°	685.9	683.2	680.5	677.8
120°	757.2	754.5	751.8	749.1
122.5°	824.4	821.1	817.7	814.3
125°	891.6	888.6	885.5	882.5
127.5°	960.4	956.7	953.0	949.3
130°	1024.6	1020.2	1015.8	1011.4
132.5°	1091.3	1088.0	1084.6	1081.2
135°	1152.9	1149.2	1145.5	1141.8
137.5°	1217.7	1214.6	1211.6	1208.6
140°	1276.8	1273.8	1270.7	1267.7
142.5°	1337.5	1334.4	1331.4	1328.4
145°	1393.1	1390.7	1388.4	1386.0
147.5°	1446.6	1443.6	1440.5	1437.5
150°	1496.7	1494.6	1492.6	1490.6
152.5°	1543.7	1541.6	1539.6	1537.6
155°	1587.7	1586.6	1585.6	1584.6
157.5°	1627.6	1626.9	1626.3	1625.6
160°	1664.0	1663.3	1662.7	1662.0
162.5°	1695.3	1695.3	1695.3	1695.3
165°	1723.1	1723.4	1723.8	1724.1
167.5°	1746.9	1747.9	1748.9	1749.9
170°	1766.6	1767.6	1768.6	1769.6
172.5°	1780.2	1781.3	1782.3	1783.3
175°	1790.9	1791.9	1792.9	1793.9
177.5°	1796.9	1798.0	1799.0	1800.0
180°	1796.9	1796.9	1796.9	1796.9

(END OF REPORT)