

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029392

Luminaire Tested: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029392
REPORT IS A COMBINATION OF REPORTS P985748 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K
Description: Define 2 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3772.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			34
1	94	90	87	83	85	82	79	76	65	63	61	51	49	48	37	36	35			29
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	31	30			25
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26			21
4	72	62	54	49	65	56	50	45	46	41	37	36	32	30	26	24	23			19
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20			16
6	61	50	42	36	55	45	38	34	37	32	28	29	26	23	22	20	18			15
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16			13
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14			12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13			11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9105	9105	9105	9105
5°	9126	9708	9161	7724
10°	9021	10597	9077	6367
15°	8802	11178	8924	5364
20°	8664	10495	8664	4662
25°	8389	9016	8427	4169
30°	7933	7088	8085	3777
35°	7532	4901	7657	3455
40°	7070	3701	7148	3199
45°	6497	3040	6604	2922
50°	6005	2670	6017	2675
55°	5441	2274	5478	2407
60°	4843	1899	4910	2101
65°	4305	1545	4383	1794
70°	3772	1212	3867	1447
75°	3166	880	3289	1049
80°	2467	557	2651	622
85°	1624	280	1752	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9412 cd/sqm

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	1.5
10°-20°	159.5	4.2
20°-30°	231.4	6.1
30°-40°	244.0	6.5
40°-50°	215.9	5.7
50°-60°	172.4	4.6
60°-70°	117.1	3.1
70°-80°	59.9	1.6
80°-90°	16.7	0.4
90°-100°	55.3	1.5
100°-110°	175.9	4.7
110°-120°	300.9	8.0
120°-130°	395.8	10.5
130°-140°	444.3	11.8
140°-150°	435.7	11.6
150°-160°	365.5	9.7
160°-170°	242.4	6.4
170°-180°	84.7	2.2
0°-30°	445.7	11.8
0°-40°	689.6	18.3
0°-60°	1077.9	28.6
0°-90°	1271.6	33.7
90°-120°	532.2	14.1
90°-150°	1807.9	47.9
90°-180°	2500.0	66.3
0°-180°	3772.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	575	575	575	575	575	
5°	576	642	578	511	576	55
15°	541	790	548	379	541	153
25°	486	658	488	304	486	222
35°	397	358	403	252	397	248
45°	298	216	302	207	298	231
55°	204	152	206	160	204	182
65°	121	93	123	108	121	120
75°	57	46	59	55	57	61
85°	12	12	12	9	12	13
90°	1	26	1	26	1	3
95°	39	47	39	47	39	44
105°	162	168	162	168	162	171
115°	302	302	302	302	302	299
125°	439	441	439	441	439	393
135°	568	575	568	575	568	439
145°	690	697	690	697	690	431
155°	789	795	789	795	789	363
165°	858	859	858	859	858	242
175°	893	890	893	890	893	85
180°	894	894	894	894	894	

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	578.3	579.6	581.8	582.2	586.7	590.2	594.2	594.2	595.5	595.1	591.5
5°	575.6	579.6	585.3	590.2	598.2	601.7	607.0	611.0	614.5	617.2	616.7
7.5°	571.2	578.3	586.7	595.9	606.6	612.7	620.3	627.3	632.2	636.6	639.7
10°	563.7	575.6	587.1	599.5	613.2	621.6	630.4	639.7	647.2	655.6	663.6
12.5°	553.5	570.7	584.9	601.3	618.1	627.3	641.5	648.6	663.1	684.4	690.1
15°	540.7	564.1	577.4	598.2	620.3	627.8	647.2	658.7	688.8	702.1	718.0
17.5°	528.7	554.8	572.5	596.4	618.1	632.6	651.7	675.1	700.3	719.3	737.0
20°	519.0	544.2	565.4	592.0	619.4	637.9	657.8	686.1	713.5	733.0	746.7
22.5°	496.9	529.2	553.9	583.6	616.7	642.4	661.4	692.3	721.9	733.9	745.8
25°	485.9	513.7	542.5	576.1	615.0	645.5	661.8	696.3	722.4	726.8	729.5
27.5°	465.5	496.9	530.5	569.0	614.5	640.2	660.9	692.3	713.1	710.0	702.1
30°	440.3	478.8	515.9	557.5	608.3	636.2	655.6	684.4	695.0	679.1	664.9
32.5°	421.8	458.0	499.1	547.3	601.3	627.8	646.8	669.3	671.5	642.8	618.9
35°	396.6	436.8	483.2	534.1	589.3	613.2	630.9	644.6	634.0	593.7	565.4
37.5°	374.0	413.8	463.3	515.0	573.0	596.4	610.5	612.7	586.7	551.3	509.7
40°	349.3	390.4	442.1	496.5	554.8	575.2	584.0	577.4	539.8	498.7	450.5
42.5°	324.5	365.2	420.9	476.6	531.8	549.1	552.6	534.5	488.5	440.3	384.6
45°	297.5	340.0	395.7	451.8	505.3	515.0	515.5	489.4	435.0	384.6	332.9
47.5°	275.4	314.8	370.0	426.2	471.3	477.9	475.3	445.2	386.0	329.4	284.3
50°	251.1	288.7	343.5	398.8	437.2	439.0	432.4	389.5	331.6	279.8	244.0
52.5°	225.0	263.0	313.4	366.5	401.0	398.3	385.5	339.5	285.2	242.3	214.9
55°	204.2	237.8	285.2	336.9	361.2	353.7	339.5	292.7	249.8	213.5	189.7
57.5°	181.3	210.9	257.3	302.4	316.5	309.5	295.3	251.6	211.8	184.4	168.4
60°	159.6	186.6	227.2	264.8	275.9	268.4	252.0	212.6	183.9	160.9	149.0
62.5°	139.7	163.1	197.2	231.7	236.1	228.6	214.4	182.6	157.8	139.7	130.9
65°	121.1	143.2	170.6	196.7	200.7	192.8	178.2	155.2	134.4	122.9	114.5
67.5°	103.0	120.7	145.0	164.0	166.2	158.7	146.8	128.2	115.4	103.0	96.8
70°	87.1	100.4	119.4	134.8	135.7	128.7	122.5	105.7	95.9	87.1	82.2
72.5°	71.6	80.9	95.5	107.0	107.4	103.0	97.3	86.7	78.3	72.1	67.2
75°	56.6	64.5	73.4	83.6	83.1	79.6	75.2	68.5	61.5	57.5	55.3
77.5°	43.3	48.2	55.3	61.9	61.9	60.1	57.5	52.6	48.2	44.2	42.0
80°	30.9	34.0	39.8	42.0	42.9	42.4	40.2	36.7	34.9	31.8	30.9
82.5°	19.9	22.1	24.8	27.0	28.3	27.4	27.0	25.2	22.5	21.7	20.8
85°	11.5	12.4	13.7	15.0	15.5	15.0	15.9	14.6	13.3	13.3	12.8
87.5°	4.9	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	0.8	2.8	4.8	6.8	8.8	9.8	11.6	15.3	19.0	22.7	26.4
92.5°	16.6	17.9	19.3	20.6	21.9	22.6	22.7	22.9	23.0	23.2	23.4
95°	39.2	40.9	42.6	44.3	46.0	46.8	47.0	47.3	47.6	48.0	48.3
97.5°	65.7	67.2	68.7	70.2	71.7	72.5	72.8	73.5	74.2	74.8	75.5
100°	95.9	97.2	98.6	99.9	101.2	101.9	102.2	102.7	103.2	103.7	104.2
102.5°	127.5	128.5	129.5	130.6	131.6	132.1	132.4	133.1	133.8	134.4	135.1
105°	162.3	162.8	163.3	163.8	164.3	164.5	164.7	165.0	165.3	165.7	166.0
107.5°	197.0	197.7	198.3	199.0	199.7	200.0	200.0	200.0	200.0	200.0	200.0
110°	230.2	231.2	232.2	233.2	234.2	234.7	234.7	234.7	234.7	234.7	234.7

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	266.4	267.4	268.4	269.4	270.4	270.9	270.8	270.7	270.5	270.4	270.2
115°	301.9	302.9	303.9	304.9	305.9	306.4	306.2	305.9	305.6	305.2	304.9
117.5°	337.4	338.7	340.1	341.4	342.7	343.4	343.0	342.1	341.3	340.4	339.6
120°	372.8	374.2	375.5	376.9	378.2	378.9	378.2	376.9	375.5	374.2	372.8
122.5°	405.3	407.0	408.6	410.3	412.0	412.8	412.4	411.6	410.7	409.9	409.1
125°	439.3	440.8	442.3	443.8	445.3	446.0	445.8	445.3	444.8	444.3	443.8
127.5°	472.5	474.3	476.2	478.0	479.9	480.8	480.5	479.8	479.1	478.4	477.7
130°	503.4	505.6	507.8	509.9	512.1	513.2	513.0	512.7	512.4	512.0	511.7
132.5°	538.1	539.8	541.5	543.2	544.9	545.7	545.8	545.9	546.1	546.2	546.4
135°	568.3	570.1	572.0	573.8	575.7	576.6	576.8	577.1	577.4	577.8	578.1
137.5°	601.5	603.0	604.5	606.0	607.5	608.3	608.5	608.8	609.1	609.5	609.8
140°	631.0	632.5	634.0	635.5	637.0	637.7	638.1	639.0	639.8	640.7	641.5
142.5°	661.1	662.6	664.1	665.6	667.1	667.9	668.2	668.7	669.2	669.7	670.2
145°	689.8	691.0	692.2	693.3	694.5	695.1	695.6	696.6	697.6	698.6	699.6
147.5°	715.5	717.0	718.5	720.0	721.5	722.3	722.6	723.3	724.0	724.6	725.3
150°	741.9	742.9	743.9	744.9	745.9	746.4	746.7	747.4	748.1	748.7	749.4
152.5°	765.3	766.3	767.3	768.3	769.3	769.8	770.2	771.1	771.9	772.8	773.6
155°	788.7	789.2	789.7	790.2	790.7	791.0	791.2	791.7	792.2	792.7	793.2
157.5°	809.1	809.4	809.8	810.1	810.4	810.6	810.8	811.1	811.4	811.8	812.1
160°	827.2	827.5	827.9	828.2	828.5	828.7	828.8	829.0	829.1	829.3	829.5
162.5°	843.8	843.8	843.8	843.8	843.8	843.8	843.9	844.0	844.2	844.3	844.5
165°	858.1	857.9	857.8	857.6	857.5	857.4	857.4	857.4	857.4	857.4	857.4
167.5°	871.0	870.5	870.0	869.5	869.0	868.7	868.7	868.7	868.7	868.7	868.7
170°	880.8	880.3	879.8	879.3	878.8	878.5	878.4	878.3	878.1	878.0	877.8
172.5°	887.6	887.1	886.6	886.1	885.6	885.3	885.2	885.0	884.9	884.7	884.5
175°	892.8	892.3	891.8	891.3	890.8	890.6	890.4	890.1	889.8	889.4	889.1
177.5°	895.9	895.4	894.9	894.4	893.9	893.6	893.4	893.1	892.8	892.4	892.1
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	597.7	598.2	599.0	603.5	605.7	606.1	604.3	608.3	609.7	608.3	607.4
5°	626.0	628.7	634.0	639.7	639.3	639.7	642.4	645.0	645.9	642.4	643.7
7.5°	650.8	656.1	661.8	670.7	670.7	675.1	676.9	679.1	684.4	681.7	680.8
10°	679.1	686.1	696.7	710.9	711.3	715.8	720.2	727.3	729.5	727.7	728.6
12.5°	714.4	728.1	729.0	744.5	751.6	752.5	759.5	758.2	762.6	762.6	770.1
15°	729.9	751.1	763.1	778.1	782.5	777.2	783.0	789.1	789.6	789.6	789.1
17.5°	757.8	766.2	778.1	786.1	787.8	787.8	788.3	790.9	789.1	785.6	788.3
20°	763.5	767.0	771.5	770.6	771.5	767.0	762.6	758.2	758.6	756.4	763.1
22.5°	752.9	752.0	741.8	735.2	735.2	726.4	718.0	714.0	710.0	711.3	713.5
25°	726.4	712.7	700.3	690.6	688.3	674.2	662.7	659.2	652.5	657.8	658.7
27.5°	683.9	668.5	648.6	640.2	628.7	622.9	615.0	604.3	590.6	598.6	597.3
30°	638.4	615.4	599.0	578.7	560.6	559.3	544.2	526.5	519.5	519.5	523.4
32.5°	587.5	557.0	533.2	504.4	486.8	479.2	461.1	443.4	447.4	434.1	439.0
35°	528.3	488.1	458.0	430.2	416.9	408.1	384.6	374.9	364.3	358.1	369.6
37.5°	471.7	425.3	386.8	356.3	351.5	335.6	319.6	313.4	307.3	309.9	309.5
40°	402.8	361.6	327.2	303.3	294.9	287.4	276.8	269.2	265.3	267.5	267.9
42.5°	340.4	305.9	280.3	263.5	256.4	251.1	245.8	239.6	238.3	238.3	240.1
45°	292.2	263.9	246.7	233.0	229.0	225.0	221.0	218.4	217.5	215.7	217.1
47.5°	253.8	231.2	220.6	210.4	206.0	205.1	201.6	200.3	198.5	198.1	198.5
50°	221.5	207.3	197.6	191.9	188.8	187.4	185.7	183.0	182.1	184.4	183.5
52.5°	198.9	185.7	180.4	174.6	172.9	171.1	168.4	168.9	168.4	167.6	167.6
55°	176.4	168.0	162.7	158.3	157.8	156.1	153.9	153.0	152.5	151.6	153.0
57.5°	158.3	151.6	146.8	142.8	141.0	141.0	138.8	137.1	137.1	136.6	137.1
60°	140.1	133.5	130.4	126.4	125.1	124.7	123.3	122.5	121.1	121.1	121.1
62.5°	123.3	118.0	114.5	111.0	111.4	109.2	107.4	106.5	106.5	107.0	107.0
65°	107.4	103.9	99.5	96.4	95.5	95.1	94.2	93.7	92.4	93.3	93.3
67.5°	92.8	88.0	85.3	84.0	82.7	82.2	81.3	80.5	80.0	79.6	80.5
70°	78.3	74.3	72.1	71.2	69.9	69.4	69.0	67.6	68.1	68.5	69.0
72.5°	65.0	61.5	61.0	58.4	58.4	58.4	56.6	57.5	57.0	56.1	57.0
75°	51.3	49.5	48.6	47.3	47.7	47.3	46.9	45.5	45.5	46.0	46.4
77.5°	40.7	38.9	38.5	37.1	36.3	37.1	36.3	35.8	35.8	36.3	36.3
80°	30.1	29.2	27.9	27.9	27.9	27.4	27.4	27.4	27.0	26.5	27.0
82.5°	19.9	19.9	19.5	19.0	19.5	18.6	19.0	19.0	19.0	19.0	19.0
85°	12.8	12.4	12.4	11.9	11.9	11.9	12.4	11.5	11.5	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	26.1	25.7	25.4	25.1	24.9	25.0	25.2	25.3	25.5	25.7	25.5
92.5°	23.6	23.8	23.9	24.1	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.3	48.3	48.3	48.3	48.3	48.1	47.8	47.5	47.1	46.8	47.1
97.5°	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5
100°	104.2	104.2	104.2	104.2	104.2	104.1	103.9	103.8	103.6	103.4	103.6
102.5°	135.3	135.5	135.6	135.8	135.9	135.8	135.6	135.5	135.3	135.1	135.3
105°	166.4	166.7	167.1	167.4	167.6	167.6	167.6	167.6	167.6	167.6	167.6
107.5°	200.2	200.4	200.5	200.7	200.8	200.4	199.5	198.7	197.8	197.0	197.8
110°	234.7	234.7	234.7	234.7	234.7	234.5	234.0	233.5	233.0	232.5	233.0



TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	269.7	269.2	268.7	268.2	267.9	267.7	267.4	267.1	266.7	266.4	266.7
115°	304.7	304.6	304.4	304.3	304.2	303.9	303.4	302.9	302.4	301.9	302.4
117.5°	339.1	338.6	338.1	337.6	337.4	337.1	336.6	336.1	335.6	335.1	335.6
120°	372.8	372.8	372.8	372.8	372.8	372.6	372.1	371.6	371.1	370.6	371.1
122.5°	408.6	408.1	407.6	407.1	406.8	406.6	406.3	406.0	405.6	405.3	405.6
125°	443.3	442.8	442.3	441.8	441.5	441.4	441.3	441.1	441.0	440.8	441.0
127.5°	477.0	476.4	475.7	475.0	474.7	474.5	474.0	473.5	473.0	472.5	473.0
130°	511.4	511.0	510.7	510.4	510.2	509.9	509.2	508.5	507.9	507.2	507.9
132.5°	545.6	544.8	543.9	543.1	542.7	542.4	541.9	541.4	540.9	540.4	540.9
135°	577.9	577.8	577.6	577.5	577.4	577.1	576.6	576.1	575.6	575.1	575.6
137.5°	609.6	609.5	609.3	609.2	609.1	608.8	608.1	607.4	606.8	606.1	606.8
140°	641.5	641.5	641.5	641.5	641.5	641.2	640.5	639.8	639.2	638.5	639.2
142.5°	670.4	670.6	670.7	670.9	671.0	670.7	670.0	669.3	668.6	667.9	668.6
145°	699.8	700.0	700.1	700.3	700.4	700.1	699.4	698.7	698.1	697.4	698.1
147.5°	725.6	726.0	726.3	726.6	726.8	726.5	725.8	725.1	724.5	723.8	724.5
150°	749.9	750.4	750.9	751.4	751.7	751.4	750.9	750.4	749.9	749.4	749.9
152.5°	774.3	774.9	775.6	776.3	776.6	776.3	775.6	774.9	774.3	773.6	774.3
155°	794.0	794.9	795.7	796.6	797.0	796.7	796.2	795.7	795.2	794.7	795.2
157.5°	813.3	814.5	815.6	816.8	817.4	817.0	816.1	815.3	814.4	813.6	814.4
160°	830.5	831.5	832.5	833.5	834.0	833.7	833.0	832.3	831.7	831.0	831.7
162.5°	845.7	846.9	848.0	849.2	849.8	849.4	848.6	847.7	846.9	846.1	846.9
165°	858.6	859.8	860.9	862.1	862.7	862.3	861.4	860.6	859.7	858.9	859.7
167.5°	869.9	871.1	872.2	873.4	874.0	873.6	872.7	871.9	871.0	870.2	871.0
170°	879.0	880.1	881.3	882.4	883.0	882.5	881.5	880.5	879.5	878.5	879.5
172.5°	885.7	886.9	888.0	889.2	889.8	889.3	888.3	887.3	886.3	885.3	886.3
175°	890.3	891.5	892.6	893.8	894.4	893.9	892.9	891.8	890.8	889.8	890.8
177.5°	893.1	894.1	895.1	896.1	896.6	896.1	895.1	894.1	893.1	892.1	893.1
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	609.7	606.6	603.9	604.3	606.6	604.8	600.4	594.6	592.4	589.8	592.4
5°	646.3	643.7	638.4	638.8	637.5	635.7	628.7	619.8	619.8	612.7	611.9
7.5°	682.6	678.6	675.1	674.2	669.3	665.8	659.6	647.2	642.4	634.0	629.1
10°	723.3	720.2	716.2	711.3	708.7	702.5	692.3	674.2	665.4	653.9	645.5
12.5°	764.4	763.9	755.1	745.4	744.9	735.2	728.1	703.8	691.9	676.4	656.5
15°	790.5	788.3	783.4	778.5	779.9	769.3	753.3	724.6	716.6	698.1	676.9
17.5°	790.0	790.0	788.7	787.8	786.5	783.4	774.6	755.5	742.7	719.3	699.4
20°	764.8	770.6	771.9	771.5	775.9	778.1	777.7	765.7	755.5	734.8	714.4
22.5°	714.4	727.7	733.4	737.0	746.3	751.1	762.6	758.2	755.5	740.1	722.8
25°	667.6	672.0	689.2	690.1	702.9	714.9	726.4	733.9	743.6	737.9	723.3
27.5°	607.0	617.2	629.5	638.8	641.5	665.8	684.8	699.0	721.1	722.8	718.0
30°	538.5	543.3	563.7	576.1	590.2	607.9	635.3	659.6	679.5	697.6	703.8
32.5°	454.9	474.8	486.8	501.8	514.2	545.5	579.1	610.5	633.5	664.0	677.3
35°	378.4	393.9	414.2	420.4	443.0	469.5	513.3	553.5	588.4	619.4	646.3
37.5°	315.2	327.6	349.3	359.0	372.2	406.3	443.0	492.9	534.9	573.0	606.6
40°	271.9	281.2	297.5	300.6	311.7	342.6	372.2	419.1	474.8	526.1	562.8
42.5°	242.3	246.7	257.7	261.7	268.8	289.6	316.1	360.3	412.0	465.1	516.8
45°	221.0	224.1	230.8	234.3	243.2	252.4	274.1	309.5	350.1	403.6	459.3
47.5°	202.0	206.0	208.7	210.9	215.7	225.9	240.1	266.1	305.0	354.1	408.1
50°	186.1	187.4	192.3	192.8	195.8	202.5	215.7	231.7	262.6	302.4	354.6
52.5°	170.2	171.5	174.6	177.7	179.0	184.4	193.2	206.5	229.4	260.8	307.3
55°	154.3	156.1	159.2	161.4	162.7	167.1	172.4	185.2	203.4	225.5	263.5
57.5°	138.4	142.4	143.2	144.6	146.8	151.6	156.5	164.0	178.2	198.5	226.4
60°	123.3	124.7	127.8	129.1	131.3	134.0	140.1	145.9	156.1	172.0	197.2
62.5°	107.9	111.0	112.3	113.6	115.4	118.5	122.5	128.7	137.5	150.3	170.2
65°	94.6	95.1	97.7	99.5	101.2	103.5	107.4	113.2	118.5	130.4	145.0
67.5°	81.8	82.7	83.6	85.3	87.5	89.7	93.3	96.4	103.0	111.0	122.5
70°	69.4	69.4	71.6	72.9	72.5	75.2	77.8	81.3	86.2	93.7	103.0
72.5°	58.4	57.9	59.7	60.1	61.0	62.8	64.5	68.1	70.7	76.5	83.6
75°	46.4	47.3	48.2	48.2	49.5	50.8	52.6	54.4	57.5	61.0	66.3
77.5°	36.7	36.7	37.6	38.0	39.3	38.9	40.7	42.4	44.7	47.7	51.7
80°	27.0	27.9	27.9	27.9	28.3	28.7	30.5	31.8	33.2	35.4	37.1
82.5°	19.0	19.0	19.9	19.9	19.9	20.8	20.8	21.2	22.1	23.4	24.8
85°	11.9	11.9	11.9	12.4	11.9	12.4	13.3	12.8	13.3	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	25.3	25.2	25.0	24.9	25.1	25.4	25.7	26.1	26.4	22.7	19.0
92.5°	24.2	24.2	24.2	24.2	24.1	23.9	23.8	23.6	23.4	23.2	23.0
95°	47.5	47.8	48.1	48.3	48.3	48.3	48.3	48.3	48.3	48.0	47.6
97.5°	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	74.8	74.2
100°	103.8	103.9	104.1	104.2	104.2	104.2	104.2	104.2	104.2	103.7	103.2
102.5°	135.5	135.6	135.8	135.9	135.8	135.6	135.5	135.3	135.1	134.4	133.8
105°	167.6	167.6	167.6	167.6	167.4	167.1	166.7	166.4	166.0	165.7	165.3
107.5°	198.7	199.5	200.4	200.8	200.7	200.5	200.4	200.2	200.0	200.0	200.0
110°	233.5	234.0	234.5	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7



TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	267.1	267.4	267.7	267.9	268.2	268.7	269.2	269.7	270.2	270.4	270.5
115°	302.9	303.4	303.9	304.2	304.3	304.4	304.6	304.7	304.9	305.2	305.6
117.5°	336.1	336.6	337.1	337.4	337.6	338.1	338.6	339.1	339.6	340.4	341.3
120°	371.6	372.1	372.6	372.8	372.8	372.8	372.8	372.8	372.8	374.2	375.5
122.5°	406.0	406.3	406.6	406.8	407.1	407.6	408.1	408.6	409.1	409.9	410.7
125°	441.1	441.3	441.4	441.5	441.8	442.3	442.8	443.3	443.8	444.3	444.8
127.5°	473.5	474.0	474.5	474.7	475.0	475.7	476.4	477.0	477.7	478.4	479.1
130°	508.5	509.2	509.9	510.2	510.4	510.7	511.0	511.4	511.7	512.0	512.4
132.5°	541.4	541.9	542.4	542.7	543.1	543.9	544.8	545.6	546.4	546.2	546.1
135°	576.1	576.6	577.1	577.4	577.5	577.6	577.8	577.9	578.1	577.8	577.4
137.5°	607.4	608.1	608.8	609.1	609.2	609.3	609.5	609.6	609.8	609.5	609.1
140°	639.8	640.5	641.2	641.5	641.5	641.5	641.5	641.5	641.5	640.7	639.8
142.5°	669.3	670.0	670.7	671.0	670.9	670.7	670.6	670.4	670.2	669.7	669.2
145°	698.7	699.4	700.1	700.4	700.3	700.1	700.0	699.8	699.6	698.6	697.6
147.5°	725.1	725.8	726.5	726.8	726.6	726.3	726.0	725.6	725.3	724.6	724.0
150°	750.4	750.9	751.4	751.7	751.4	750.9	750.4	749.9	749.4	748.7	748.1
152.5°	774.9	775.6	776.3	776.6	776.3	775.6	774.9	774.3	773.6	772.8	771.9
155°	795.7	796.2	796.7	797.0	796.6	795.7	794.9	794.0	793.2	792.7	792.2
157.5°	815.3	816.1	817.0	817.4	816.8	815.6	814.5	813.3	812.1	811.8	811.4
160°	832.3	833.0	833.7	834.0	833.5	832.5	831.5	830.5	829.5	829.3	829.1
162.5°	847.7	848.6	849.4	849.8	849.2	848.0	846.9	845.7	844.5	844.3	844.2
165°	860.6	861.4	862.3	862.7	862.1	860.9	859.8	858.6	857.4	857.4	857.4
167.5°	871.9	872.7	873.6	874.0	873.4	872.2	871.1	869.9	868.7	868.7	868.7
170°	880.5	881.5	882.5	883.0	882.4	881.3	880.1	879.0	877.8	878.0	878.1
172.5°	887.3	888.3	889.3	889.8	889.2	888.0	886.9	885.7	884.5	884.7	884.9
175°	891.8	892.9	893.9	894.4	893.8	892.6	891.5	890.3	889.1	889.4	889.8
177.5°	894.1	895.1	896.1	896.6	896.1	895.1	894.1	893.1	892.1	892.4	892.8
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	590.2	588.0	586.7	587.5	584.9	578.3	578.3	580.5	577.8	575.2	571.2
5°	606.6	602.1	599.5	599.0	592.9	582.2	580.0	577.8	572.1	565.9	559.3
7.5°	622.5	614.5	610.1	607.0	598.2	584.5	578.7	573.8	564.6	555.3	546.9
10°	635.7	624.2	618.9	614.1	602.6	585.3	576.1	567.2	555.3	543.3	532.7
12.5°	646.3	633.1	626.5	619.4	605.2	582.7	571.2	557.0	545.1	529.2	518.6
15°	664.0	636.6	630.4	623.8	609.2	578.3	564.1	548.2	531.8	510.6	499.1
17.5°	678.2	641.5	641.0	626.9	607.9	576.5	554.8	534.1	516.4	495.2	477.0
20°	686.6	649.0	641.9	627.3	603.5	564.6	542.0	519.0	500.0	474.4	456.2
22.5°	693.7	659.6	641.0	623.4	594.2	560.6	527.4	505.8	479.7	451.8	434.6
25°	696.3	661.8	642.4	622.0	587.5	549.1	511.5	488.1	458.9	433.7	410.3
27.5°	696.7	661.4	637.5	616.3	578.3	534.1	495.6	470.8	438.6	409.4	386.0
30°	692.3	656.5	634.9	611.9	569.4	520.3	476.1	448.7	414.2	385.1	360.8
32.5°	679.1	646.8	629.1	603.9	557.9	501.3	457.6	427.1	390.8	362.1	338.6
35°	657.0	634.9	615.4	592.0	542.9	483.7	439.0	403.2	366.5	339.1	317.0
37.5°	629.5	617.6	599.5	576.5	525.7	467.7	418.2	378.4	341.7	315.2	293.6
40°	592.4	595.5	577.8	557.0	505.3	446.1	391.3	353.2	318.8	294.0	272.8
42.5°	552.2	565.0	554.8	534.9	482.8	422.2	371.4	329.4	295.8	270.1	252.4
45°	508.9	531.0	524.8	510.2	459.3	397.0	343.1	302.4	272.8	248.0	232.5
47.5°	461.6	492.9	492.9	482.3	433.3	371.8	318.8	277.2	248.0	230.3	215.3
50°	413.4	448.7	454.5	447.4	404.1	343.1	289.1	251.6	226.4	209.1	198.1
52.5°	363.0	404.1	414.7	411.2	373.1	315.7	264.8	228.1	205.1	190.1	180.4
55°	314.8	362.5	374.0	375.3	340.0	285.6	237.8	205.6	183.5	173.3	164.9
57.5°	269.2	315.2	328.0	330.2	306.4	258.2	212.6	184.4	164.5	156.1	149.4
60°	230.3	268.8	285.6	290.5	269.7	226.4	189.2	161.8	146.8	138.8	132.6
62.5°	198.5	229.4	247.1	248.5	239.2	198.5	164.9	141.9	129.1	122.0	118.9
65°	167.6	195.4	206.0	211.3	203.8	172.0	142.4	123.3	113.2	107.0	103.9
67.5°	142.8	160.5	169.3	176.4	168.9	145.0	121.1	105.7	98.1	92.0	90.2
70°	117.2	131.7	138.4	145.5	138.8	120.7	103.5	89.3	82.7	77.8	75.6
72.5°	93.7	105.2	111.4	115.8	111.9	96.8	82.7	72.9	68.1	64.5	63.2
75°	74.3	82.2	85.8	88.9	87.1	75.6	66.8	58.8	54.4	51.3	50.4
77.5°	56.6	62.3	66.3	67.2	65.0	57.5	50.0	45.1	41.6	39.8	38.9
80°	40.2	43.8	46.0	47.3	45.1	42.0	36.7	33.2	30.1	27.9	27.4
82.5°	27.0	28.7	30.5	30.1	29.2	26.5	23.4	21.7	20.3	18.6	18.6
85°	15.5	15.9	16.8	17.2	16.8	15.0	13.3	12.4	11.5	10.2	10.2
87.5°	6.6	7.1	7.1	7.5	6.6	6.6	5.7	4.9	4.9	4.4	4.0
90°	15.3	11.6	9.8	8.8	6.8	4.8	2.8	0.8	2.8	4.8	6.8
92.5°	22.9	22.7	22.6	21.9	20.6	19.3	17.9	16.6	17.9	19.3	20.6
95°	47.3	47.0	46.8	46.0	44.3	42.6	40.9	39.2	40.9	42.6	44.3
97.5°	73.5	72.8	72.5	71.7	70.2	68.7	67.2	65.7	67.2	68.7	70.2
100°	102.7	102.2	101.9	101.2	99.9	98.6	97.2	95.9	97.2	98.6	99.9
102.5°	133.1	132.4	132.1	131.6	130.6	129.5	128.5	127.5	128.5	129.5	130.6
105°	165.0	164.7	164.5	164.3	163.8	163.3	162.8	162.3	162.8	163.3	163.8
107.5°	200.0	200.0	200.0	199.7	199.0	198.3	197.7	197.0	197.7	198.3	199.0
110°	234.7	234.7	234.7	234.2	233.2	232.2	231.2	230.2	231.2	232.2	233.2

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	270.7	270.8	270.9	270.4	269.4	268.4	267.4	266.4	267.4	268.4	269.4
115°	305.9	306.2	306.4	305.9	304.9	303.9	302.9	301.9	302.9	303.9	304.9
117.5°	342.1	343.0	343.4	342.7	341.4	340.1	338.7	337.4	338.7	340.1	341.4
120°	376.9	378.2	378.9	378.2	376.9	375.5	374.2	372.8	374.2	375.5	376.9
122.5°	411.6	412.4	412.8	412.0	410.3	408.6	407.0	405.3	407.0	408.6	410.3
125°	445.3	445.8	446.0	445.3	443.8	442.3	440.8	439.3	440.8	442.3	443.8
127.5°	479.8	480.5	480.8	479.9	478.0	476.2	474.3	472.5	474.3	476.2	478.0
130°	512.7	513.0	513.2	512.1	509.9	507.8	505.6	503.4	505.6	507.8	509.9
132.5°	545.9	545.8	545.7	544.9	543.2	541.5	539.8	538.1	539.8	541.5	543.2
135°	577.1	576.8	576.6	575.7	573.8	572.0	570.1	568.3	570.1	572.0	573.8
137.5°	608.8	608.5	608.3	607.5	606.0	604.5	603.0	601.5	603.0	604.5	606.0
140°	639.0	638.1	637.7	637.0	635.5	634.0	632.5	631.0	632.5	634.0	635.5
142.5°	668.7	668.2	667.9	667.1	665.6	664.1	662.6	661.1	662.6	664.1	665.6
145°	696.6	695.6	695.1	694.5	693.3	692.2	691.0	689.8	691.0	692.2	693.3
147.5°	723.3	722.6	722.3	721.5	720.0	718.5	717.0	715.5	717.0	718.5	720.0
150°	747.4	746.7	746.4	745.9	744.9	743.9	742.9	741.9	742.9	743.9	744.9
152.5°	771.1	770.2	769.8	769.3	768.3	767.3	766.3	765.3	766.3	767.3	768.3
155°	791.7	791.2	791.0	790.7	790.2	789.7	789.2	788.7	789.2	789.7	790.2
157.5°	811.1	810.8	810.6	810.4	810.1	809.8	809.4	809.1	809.4	809.8	810.1
160°	829.0	828.8	828.7	828.5	828.2	827.9	827.5	827.2	827.5	827.9	828.2
162.5°	844.0	843.9	843.8	843.8	843.8	843.8	843.8	843.8	843.8	843.8	843.8
165°	857.4	857.4	857.4	857.5	857.6	857.8	857.9	858.1	857.9	857.8	857.6
167.5°	868.7	868.7	868.7	869.0	869.5	870.0	870.5	871.0	870.5	870.0	869.5
170°	878.3	878.4	878.5	878.8	879.3	879.8	880.3	880.8	880.3	879.8	879.3
172.5°	885.0	885.2	885.3	885.6	886.1	886.6	887.1	887.6	887.1	886.6	886.1
175°	890.1	890.4	890.6	890.8	891.3	891.8	892.3	892.8	892.3	891.8	891.3
177.5°	893.1	893.4	893.6	893.9	894.4	894.9	895.4	895.9	895.4	894.9	894.4
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	569.0	571.2	570.7	566.3	561.5	557.5	550.0	550.9	548.2	548.6	551.3
5°	554.8	554.8	553.1	546.9	538.9	534.5	526.1	523.9	518.6	518.1	517.7
7.5°	539.8	537.6	535.4	526.5	516.8	509.7	498.2	495.6	490.3	486.8	485.0
10°	522.1	519.0	514.6	504.4	492.5	483.7	471.7	468.2	458.0	453.6	450.9
12.5°	502.7	500.9	493.8	485.4	466.0	456.2	439.0	442.5	432.4	423.5	422.2
15°	483.2	476.6	472.6	458.9	435.5	431.0	417.3	410.3	401.0	393.9	393.9
17.5°	464.2	454.0	445.2	430.6	413.4	401.0	390.8	387.3	375.8	368.7	367.4
20°	439.0	427.5	425.3	404.5	392.6	378.9	369.2	360.3	351.9	348.8	346.6
22.5°	415.1	401.9	398.3	380.6	368.7	355.0	345.3	339.1	332.9	330.7	326.7
25°	389.5	381.5	376.2	357.2	344.0	331.1	324.5	320.1	314.3	313.9	311.2
27.5°	364.7	357.2	351.9	333.8	324.1	312.1	306.8	302.0	298.9	297.5	296.2
30°	343.5	335.1	328.9	315.7	303.7	294.0	289.6	286.5	284.7	282.5	282.1
32.5°	320.1	315.2	306.8	296.6	287.4	278.1	275.4	273.2	270.6	269.7	269.2
35°	300.2	293.6	288.2	276.8	272.8	264.8	261.7	260.0	256.4	255.5	254.6
37.5°	280.7	274.5	268.8	261.7	254.2	249.8	248.0	245.4	243.6	244.0	243.2
40°	261.3	256.4	252.0	244.5	240.1	237.8	234.3	231.7	230.8	231.2	230.8
42.5°	242.3	237.8	235.2	229.4	225.0	222.8	220.6	218.0	219.3	219.3	220.6
45°	225.0	221.0	219.3	214.9	212.2	208.7	206.5	206.0	207.8	207.3	207.3
47.5°	207.3	206.0	203.8	199.8	196.3	194.1	193.6	193.6	195.4	196.3	195.8
50°	193.6	191.0	188.3	185.2	182.6	181.7	180.4	181.3	183.0	183.0	183.9
52.5°	176.4	174.6	173.7	171.1	169.3	169.3	169.3	169.8	171.1	172.4	172.0
55°	161.4	160.0	159.2	157.8	155.6	156.1	155.6	156.5	157.8	159.2	160.0
57.5°	145.5	145.0	144.1	141.9	141.9	141.5	142.8	143.2	145.5	146.3	147.7
60°	131.3	130.0	130.0	128.2	128.2	128.2	129.5	130.9	132.6	133.1	134.0
62.5°	116.3	116.3	115.8	114.5	114.5	115.8	116.3	118.0	118.9	118.9	120.3
65°	102.1	101.7	101.2	101.7	102.1	102.1	103.5	104.3	105.2	105.7	106.1
67.5°	88.0	87.5	88.4	88.0	88.9	90.6	90.2	91.5	92.8	92.8	93.3
70°	74.7	75.6	75.2	76.0	75.6	76.5	77.8	78.3	78.3	78.7	80.0
72.5°	62.3	62.3	62.3	61.9	62.3	63.2	64.1	64.5	65.4	65.9	67.2
75°	50.4	50.4	49.5	50.4	50.4	51.3	52.2	52.2	52.2	53.1	54.4
77.5°	38.0	38.5	38.0	38.9	38.9	39.3	40.2	39.8	40.7	41.1	41.6
80°	27.9	27.4	27.4	27.4	27.9	27.9	28.7	29.2	29.2	30.5	29.6
82.5°	17.7	18.1	17.7	18.1	18.1	18.6	18.1	18.6	19.0	19.9	19.5
85°	10.2	9.7	9.7	10.2	9.7	9.7	10.2	9.7	10.2	9.7	10.2
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.7	2.7	2.7	2.2
90°	8.8	9.8	11.6	15.3	19.0	22.7	26.4	26.1	25.7	25.4	25.1
92.5°	21.9	22.6	22.7	22.9	23.0	23.2	23.4	23.6	23.8	23.9	24.1
95°	46.0	46.8	47.0	47.3	47.6	48.0	48.3	48.3	48.3	48.3	48.3
97.5°	71.7	72.5	72.8	73.5	74.2	74.8	75.5	75.5	75.5	75.5	75.5
100°	101.2	101.9	102.2	102.7	103.2	103.7	104.2	104.2	104.2	104.2	104.2
102.5°	131.6	132.1	132.4	133.1	133.8	134.4	135.1	135.3	135.5	135.6	135.8
105°	164.3	164.5	164.7	165.0	165.3	165.7	166.0	166.4	166.7	167.1	167.4
107.5°	199.7	200.0	200.0	200.0	200.0	200.0	200.0	200.2	200.4	200.5	200.7
110°	234.2	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	270.4	270.9	270.8	270.7	270.5	270.4	270.2	269.7	269.2	268.7	268.2
115°	305.9	306.4	306.2	305.9	305.6	305.2	304.9	304.7	304.6	304.4	304.3
117.5°	342.7	343.4	343.0	342.1	341.3	340.4	339.6	339.1	338.6	338.1	337.6
120°	378.2	378.9	378.2	376.9	375.5	374.2	372.8	372.8	372.8	372.8	372.8
122.5°	412.0	412.8	412.4	411.6	410.7	409.9	409.1	408.6	408.1	407.6	407.1
125°	445.3	446.0	445.8	445.3	444.8	444.3	443.8	443.3	442.8	442.3	441.8
127.5°	479.9	480.8	480.5	479.8	479.1	478.4	477.7	477.0	476.4	475.7	475.0
130°	512.1	513.2	513.0	512.7	512.4	512.0	511.7	511.4	511.0	510.7	510.4
132.5°	544.9	545.7	545.8	545.9	546.1	546.2	546.4	545.6	544.8	543.9	543.1
135°	575.7	576.6	576.8	577.1	577.4	577.8	578.1	577.9	577.8	577.6	577.5
137.5°	607.5	608.3	608.5	608.8	609.1	609.5	609.8	609.6	609.5	609.3	609.2
140°	637.0	637.7	638.1	639.0	639.8	640.7	641.5	641.5	641.5	641.5	641.5
142.5°	667.1	667.9	668.2	668.7	669.2	669.7	670.2	670.4	670.6	670.7	670.9
145°	694.5	695.1	695.6	696.6	697.6	698.6	699.6	699.8	700.0	700.1	700.3
147.5°	721.5	722.3	722.6	723.3	724.0	724.6	725.3	725.6	726.0	726.3	726.6
150°	745.9	746.4	746.7	747.4	748.1	748.7	749.4	749.9	750.4	750.9	751.4
152.5°	769.3	769.8	770.2	771.1	771.9	772.8	773.6	774.3	774.9	775.6	776.3
155°	790.7	791.0	791.2	791.7	792.2	792.7	793.2	794.0	794.9	795.7	796.6
157.5°	810.4	810.6	810.8	811.1	811.4	811.8	812.1	813.3	814.5	815.6	816.8
160°	828.5	828.7	828.8	829.0	829.1	829.3	829.5	830.5	831.5	832.5	833.5
162.5°	843.8	843.8	843.9	844.0	844.2	844.3	844.5	845.7	846.9	848.0	849.2
165°	857.5	857.4	857.4	857.4	857.4	857.4	857.4	858.6	859.8	860.9	862.1
167.5°	869.0	868.7	868.7	868.7	868.7	868.7	868.7	869.9	871.1	872.2	873.4
170°	878.8	878.5	878.4	878.3	878.1	878.0	877.8	879.0	880.1	881.3	882.4
172.5°	885.6	885.3	885.2	885.0	884.9	884.7	884.5	885.7	886.9	888.0	889.2
175°	890.8	890.6	890.4	890.1	889.8	889.4	889.1	890.3	891.5	892.6	893.8
177.5°	893.9	893.6	893.4	893.1	892.8	892.4	892.1	893.1	894.1	895.1	896.1
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	548.2	549.5	546.4	545.5	546.4	543.3	544.2	545.1	545.1	546.4	547.3
5°	516.4	514.6	511.5	510.6	509.7	511.1	510.2	511.5	511.9	515.0	515.5
7.5°	485.0	482.3	479.7	477.0	476.1	473.9	476.1	476.1	479.2	478.4	480.6
10°	447.8	447.4	443.9	442.5	440.8	437.2	442.1	440.8	443.0	447.0	447.8
12.5°	420.4	415.6	417.8	411.6	413.8	410.3	410.7	410.7	414.2	414.7	413.8
15°	394.4	390.4	384.6	382.0	380.6	378.9	384.6	385.1	382.4	388.6	386.4
17.5°	367.8	367.8	362.5	361.2	357.7	359.4	358.5	359.0	358.1	362.5	364.7
20°	344.8	342.6	340.9	341.3	336.9	336.0	335.1	336.0	339.1	342.2	343.1
22.5°	326.3	324.9	320.5	321.4	317.9	319.2	318.3	320.5	321.0	321.0	324.1
25°	308.6	306.8	307.3	305.5	304.2	304.2	302.8	304.2	305.9	306.8	307.3
27.5°	295.3	294.0	291.8	290.5	291.3	289.1	290.9	292.2	292.2	291.3	292.2
30°	279.4	280.3	280.3	275.9	277.6	276.8	278.1	279.0	279.0	279.4	278.5
32.5°	268.8	266.1	265.7	265.3	265.3	263.5	263.5	264.8	265.3	265.7	267.0
35°	254.6	254.6	252.4	253.8	252.0	252.4	252.0	252.4	253.3	252.0	253.3
37.5°	241.8	242.3	241.4	242.3	242.7	241.8	240.9	242.7	241.8	241.8	240.9
40°	230.8	230.3	230.8	230.8	230.8	231.2	230.3	230.3	230.3	229.4	228.6
42.5°	221.5	218.8	219.7	220.2	218.8	218.8	219.3	218.8	220.2	217.5	217.5
45°	208.2	207.3	207.8	207.8	208.7	207.3	208.2	208.7	207.3	206.9	206.0
47.5°	196.3	197.2	196.3	197.2	197.2	198.1	196.3	196.7	197.2	195.4	194.1
50°	184.4	184.4	185.7	185.2	185.7	184.8	184.8	184.4	184.8	183.9	182.6
52.5°	173.3	172.0	174.2	173.7	173.3	172.9	172.4	172.9	172.0	171.1	171.1
55°	159.6	159.6	160.9	161.4	161.4	160.5	159.6	160.0	159.6	159.2	158.7
57.5°	148.5	146.8	147.7	148.1	148.1	146.8	147.7	146.8	146.8	147.2	145.9
60°	134.4	134.4	133.5	134.8	134.8	134.0	134.0	134.4	133.5	133.1	132.6
62.5°	119.4	119.8	121.1	121.6	122.0	121.1	120.3	120.7	120.7	119.4	119.8
65°	106.5	107.4	109.2	108.8	107.9	108.3	107.4	107.9	106.5	107.0	105.7
67.5°	94.2	93.7	94.2	94.2	95.1	94.6	93.7	93.7	93.3	94.6	93.3
70°	80.9	80.9	80.9	80.9	81.3	81.8	80.9	80.0	80.5	79.6	79.1
72.5°	67.2	67.6	67.2	68.1	66.8	67.6	67.6	67.2	66.8	66.8	66.8
75°	54.4	55.3	53.9	54.4	53.9	54.8	54.4	54.4	53.5	53.1	53.5
77.5°	41.6	42.0	41.1	41.6	41.1	41.6	41.6	41.1	41.1	41.1	41.1
80°	29.6	30.1	29.6	29.2	28.7	29.6	28.7	29.2	29.6	29.2	30.1
82.5°	19.0	19.0	18.6	19.0	18.1	18.1	18.6	18.6	18.1	19.0	18.1
85°	9.3	9.3	10.2	9.3	8.8	8.8	8.8	9.3	8.8	9.7	9.3
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.7	1.8
90°	24.9	25.0	25.2	25.3	25.5	25.7	25.5	25.3	25.2	25.0	24.9
92.5°	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2	24.2
95°	48.3	48.1	47.8	47.5	47.1	46.8	47.1	47.5	47.8	48.1	48.3
97.5°	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5	75.5
100°	104.2	104.1	103.9	103.8	103.6	103.4	103.6	103.8	103.9	104.1	104.2
102.5°	135.9	135.8	135.6	135.5	135.3	135.1	135.3	135.5	135.6	135.8	135.9
105°	167.6	167.6	167.6	167.6	167.6	167.6	167.6	167.6	167.6	167.6	167.6
107.5°	200.8	200.4	199.5	198.7	197.8	197.0	197.8	198.7	199.5	200.4	200.8
110°	234.7	234.5	234.0	233.5	233.0	232.5	233.0	233.5	234.0	234.5	234.7

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	267.9	267.7	267.4	267.1	266.7	266.4	266.7	267.1	267.4	267.7	267.9
115°	304.2	303.9	303.4	302.9	302.4	301.9	302.4	302.9	303.4	303.9	304.2
117.5°	337.4	337.1	336.6	336.1	335.6	335.1	335.6	336.1	336.6	337.1	337.4
120°	372.8	372.6	372.1	371.6	371.1	370.6	371.1	371.6	372.1	372.6	372.8
122.5°	406.8	406.6	406.3	406.0	405.6	405.3	405.6	406.0	406.3	406.6	406.8
125°	441.5	441.4	441.3	441.1	441.0	440.8	441.0	441.1	441.3	441.4	441.5
127.5°	474.7	474.5	474.0	473.5	473.0	472.5	473.0	473.5	474.0	474.5	474.7
130°	510.2	509.9	509.2	508.5	507.9	507.2	507.9	508.5	509.2	509.9	510.2
132.5°	542.7	542.4	541.9	541.4	540.9	540.4	540.9	541.4	541.9	542.4	542.7
135°	577.4	577.1	576.6	576.1	575.6	575.1	575.6	576.1	576.6	577.1	577.4
137.5°	609.1	608.8	608.1	607.4	606.8	606.1	606.8	607.4	608.1	608.8	609.1
140°	641.5	641.2	640.5	639.8	639.2	638.5	639.2	639.8	640.5	641.2	641.5
142.5°	671.0	670.7	670.0	669.3	668.6	667.9	668.6	669.3	670.0	670.7	671.0
145°	700.4	700.1	699.4	698.7	698.1	697.4	698.1	698.7	699.4	700.1	700.4
147.5°	726.8	726.5	725.8	725.1	724.5	723.8	724.5	725.1	725.8	726.5	726.8
150°	751.7	751.4	750.9	750.4	749.9	749.4	749.9	750.4	750.9	751.4	751.7
152.5°	776.6	776.3	775.6	774.9	774.3	773.6	774.3	774.9	775.6	776.3	776.6
155°	797.0	796.7	796.2	795.7	795.2	794.7	795.2	795.7	796.2	796.7	797.0
157.5°	817.4	817.0	816.1	815.3	814.4	813.6	814.4	815.3	816.1	817.0	817.4
160°	834.0	833.7	833.0	832.3	831.7	831.0	831.7	832.3	833.0	833.7	834.0
162.5°	849.8	849.4	848.6	847.7	846.9	846.1	846.9	847.7	848.6	849.4	849.8
165°	862.7	862.3	861.4	860.6	859.7	858.9	859.7	860.6	861.4	862.3	862.7
167.5°	874.0	873.6	872.7	871.9	871.0	870.2	871.0	871.9	872.7	873.6	874.0
170°	883.0	882.5	881.5	880.5	879.5	878.5	879.5	880.5	881.5	882.5	883.0
172.5°	889.8	889.3	888.3	887.3	886.3	885.3	886.3	887.3	888.3	889.3	889.8
175°	894.4	893.9	892.9	891.8	890.8	889.8	890.8	891.8	892.9	893.9	894.4
177.5°	896.6	896.1	895.1	894.1	893.1	892.1	893.1	894.1	895.1	896.1	896.6
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2
2.5°	546.0	549.5	548.2	543.3	549.1	549.1	553.1	553.1	557.9	559.7	562.3
5°	515.0	517.7	519.9	517.7	521.7	527.9	531.4	534.5	541.1	543.8	547.8
7.5°	481.9	486.8	489.0	489.0	495.6	502.7	509.7	514.2	523.4	527.0	531.0
10°	449.6	455.4	459.8	459.3	470.4	474.8	483.7	493.8	503.1	508.4	514.2
12.5°	415.6	418.7	424.9	433.7	436.4	444.3	454.5	467.3	484.1	489.0	497.4
15°	387.3	395.7	400.5	404.5	410.7	418.2	429.3	441.7	458.5	469.1	477.9
17.5°	363.4	374.5	377.6	376.7	384.6	396.1	408.9	418.2	433.3	446.1	454.5
20°	344.0	348.4	353.7	355.9	362.1	374.5	386.8	397.4	409.8	420.0	429.7
22.5°	324.5	328.0	332.5	336.4	341.3	348.4	360.3	373.6	385.5	395.2	406.3
25°	308.6	310.8	314.8	317.9	323.2	328.0	336.4	351.0	365.2	370.9	380.6
27.5°	293.1	294.9	297.5	301.1	303.7	308.6	316.1	328.0	342.6	348.4	361.6
30°	279.4	280.7	283.4	285.2	286.5	292.2	298.0	307.3	318.3	326.3	336.0
32.5°	266.6	267.9	270.6	271.0	272.8	275.9	281.2	289.6	299.3	305.9	314.3
35°	252.4	253.3	256.0	256.9	258.2	260.8	264.8	271.0	279.8	284.7	292.2
37.5°	241.4	240.9	242.7	244.0	245.8	247.1	248.5	254.6	261.3	265.7	271.4
40°	229.4	228.6	229.0	230.8	231.7	233.4	233.4	239.6	244.0	247.6	252.0
42.5°	217.5	217.1	216.2	217.1	218.0	218.4	218.8	223.3	227.7	230.8	235.6
45°	205.6	205.1	204.2	204.7	204.7	205.6	206.9	208.7	211.8	214.4	217.1
47.5°	194.5	193.6	192.3	191.9	192.8	192.8	192.8	194.5	197.6	198.5	201.2
50°	183.0	181.7	179.9	179.0	179.0	178.6	179.5	179.9	182.6	183.5	185.7
52.5°	170.6	169.8	168.0	166.2	166.7	165.8	166.2	166.7	167.6	168.9	170.2
55°	158.3	156.5	155.2	154.7	153.4	153.4	152.1	153.9	153.4	153.9	155.6
57.5°	146.3	144.6	142.4	141.5	140.1	139.7	138.8	138.4	138.8	140.1	141.5
60°	132.2	131.3	130.0	128.7	127.8	126.4	125.6	125.6	125.1	125.1	125.6
62.5°	118.5	118.0	116.3	115.8	114.9	114.1	112.7	111.9	111.9	112.7	113.2
65°	105.2	104.8	103.5	103.0	100.8	99.9	99.5	99.0	98.1	98.1	98.1
67.5°	92.8	91.5	91.5	89.3	87.5	86.7	85.8	85.3	85.3	85.3	85.8
70°	79.1	79.1	77.8	76.5	74.7	75.2	73.8	72.5	72.5	71.6	72.1
72.5°	65.9	65.4	64.1	63.7	62.3	61.0	60.1	61.0	59.7	59.2	59.7
75°	53.1	52.6	51.7	50.8	51.3	50.0	48.6	48.2	48.2	47.3	47.3
77.5°	40.7	41.6	39.8	39.3	38.5	37.6	37.1	36.7	36.7	36.7	37.6
80°	28.3	28.7	28.7	27.9	28.3	27.0	27.0	27.0	25.6	26.1	26.5
82.5°	18.1	18.1	17.7	18.1	17.7	17.7	17.2	17.2	16.8	16.8	17.2
85°	10.2	9.7	9.3	10.2	9.7	9.7	9.3	9.3	9.3	9.3	9.3
87.5°	2.2	2.7	2.7	2.7	2.7	3.1	3.1	3.1	3.5	3.5	3.5
90°	25.1	25.4	25.7	26.1	26.4	22.7	19.0	15.3	11.6	9.8	8.8
92.5°	24.1	23.9	23.8	23.6	23.4	23.2	23.0	22.9	22.7	22.6	21.9
95°	48.3	48.3	48.3	48.3	48.3	48.0	47.6	47.3	47.0	46.8	46.0
97.5°	75.5	75.5	75.5	75.5	75.5	74.8	74.2	73.5	72.8	72.5	71.7
100°	104.2	104.2	104.2	104.2	104.2	103.7	103.2	102.7	102.2	101.9	101.2
102.5°	135.8	135.6	135.5	135.3	135.1	134.4	133.8	133.1	132.4	132.1	131.6
105°	167.4	167.1	166.7	166.4	166.0	165.7	165.3	165.0	164.7	164.5	164.3
107.5°	200.7	200.5	200.4	200.2	200.0	200.0	200.0	200.0	200.0	200.0	199.7
110°	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.7	234.2

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	268.2	268.7	269.2	269.7	270.2	270.4	270.5	270.7	270.8	270.9	270.4
115°	304.3	304.4	304.6	304.7	304.9	305.2	305.6	305.9	306.2	306.4	305.9
117.5°	337.6	338.1	338.6	339.1	339.6	340.4	341.3	342.1	343.0	343.4	342.7
120°	372.8	372.8	372.8	372.8	372.8	374.2	375.5	376.9	378.2	378.9	378.2
122.5°	407.1	407.6	408.1	408.6	409.1	409.9	410.7	411.6	412.4	412.8	412.0
125°	441.8	442.3	442.8	443.3	443.8	444.3	444.8	445.3	445.8	446.0	445.3
127.5°	475.0	475.7	476.4	477.0	477.7	478.4	479.1	479.8	480.5	480.8	479.9
130°	510.4	510.7	511.0	511.4	511.7	512.0	512.4	512.7	513.0	513.2	512.1
132.5°	543.1	543.9	544.8	545.6	546.4	546.2	546.1	545.9	545.8	545.7	544.9
135°	577.5	577.6	577.8	577.9	578.1	577.8	577.4	577.1	576.8	576.6	575.7
137.5°	609.2	609.3	609.5	609.6	609.8	609.5	609.1	608.8	608.5	608.3	607.5
140°	641.5	641.5	641.5	641.5	641.5	640.7	639.8	639.0	638.1	637.7	637.0
142.5°	670.9	670.7	670.6	670.4	670.2	669.7	669.2	668.7	668.2	667.9	667.1
145°	700.3	700.1	700.0	699.8	699.6	698.6	697.6	696.6	695.6	695.1	694.5
147.5°	726.6	726.3	726.0	725.6	725.3	724.6	724.0	723.3	722.6	722.3	721.5
150°	751.4	750.9	750.4	749.9	749.4	748.7	748.1	747.4	746.7	746.4	745.9
152.5°	776.3	775.6	774.9	774.3	773.6	772.8	771.9	771.1	770.2	769.8	769.3
155°	796.6	795.7	794.9	794.0	793.2	792.7	792.2	791.7	791.2	791.0	790.7
157.5°	816.8	815.6	814.5	813.3	812.1	811.8	811.4	811.1	810.8	810.6	810.4
160°	833.5	832.5	831.5	830.5	829.5	829.3	829.1	829.0	828.8	828.7	828.5
162.5°	849.2	848.0	846.9	845.7	844.5	844.3	844.2	844.0	843.9	843.8	843.8
165°	862.1	860.9	859.8	858.6	857.4	857.4	857.4	857.4	857.4	857.4	857.5
167.5°	873.4	872.2	871.1	869.9	868.7	868.7	868.7	868.7	868.7	868.7	869.0
170°	882.4	881.3	880.1	879.0	877.8	878.0	878.1	878.3	878.4	878.5	878.8
172.5°	889.2	888.0	886.9	885.7	884.5	884.7	884.9	885.0	885.2	885.3	885.6
175°	893.8	892.6	891.5	890.3	889.1	889.4	889.8	890.1	890.4	890.6	890.8
177.5°	896.1	895.1	894.1	893.1	892.1	892.4	892.8	893.1	893.4	893.6	893.9
180°	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4	894.4

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	575.2	575.2	575.2	575.2
2.5°	564.6	564.6	571.2	578.3
5°	552.2	555.3	565.9	575.6
7.5°	540.2	545.5	558.8	571.2
10°	525.7	532.7	549.1	563.7
12.5°	511.5	518.1	537.1	553.5
15°	491.6	500.0	520.3	540.7
17.5°	471.7	480.1	504.9	528.7
20°	448.3	459.3	487.2	519.0
22.5°	426.6	440.3	471.3	496.9
25°	402.8	424.0	452.7	485.9
27.5°	381.5	402.8	431.9	465.5
30°	357.7	379.3	409.4	440.3
32.5°	334.7	354.6	383.7	421.8
35°	310.8	329.8	358.1	396.6
37.5°	289.1	307.7	338.6	374.0
40°	267.9	287.4	313.9	349.3
42.5°	248.0	265.3	289.1	324.5
45°	229.9	242.3	264.4	297.5
47.5°	210.9	221.9	242.3	275.4
50°	193.2	202.5	220.2	251.1
52.5°	176.0	183.9	200.3	225.0
55°	160.5	168.0	179.9	204.2
57.5°	144.6	150.3	161.8	181.3
60°	129.1	134.4	143.7	159.6
62.5°	113.6	118.0	126.9	139.7
65°	99.9	103.5	110.1	121.1
67.5°	86.7	88.9	94.2	103.0
70°	73.8	75.6	80.0	87.1
72.5°	60.1	61.9	66.8	71.6
75°	48.6	49.1	52.6	56.6
77.5°	38.0	37.6	40.2	43.3
80°	26.1	27.4	29.6	30.9
82.5°	17.7	18.1	19.0	19.9
85°	9.7	10.2	10.2	11.5
87.5°	4.0	4.4	4.4	4.9
90°	6.8	4.8	2.8	0.8
92.5°	20.6	19.3	17.9	16.6
95°	44.3	42.6	40.9	39.2
97.5°	70.2	68.7	67.2	65.7
100°	99.9	98.6	97.2	95.9
102.5°	130.6	129.5	128.5	127.5
105°	163.8	163.3	162.8	162.3
107.5°	199.0	198.3	197.7	197.0
110°	233.2	232.2	231.2	230.2

TEST NUMBER: P1029392

CATALOG NUMBER: S122DIW-B290D710UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	269.4	268.4	267.4	266.4
115°	304.9	303.9	302.9	301.9
117.5°	341.4	340.1	338.7	337.4
120°	376.9	375.5	374.2	372.8
122.5°	410.3	408.6	407.0	405.3
125°	443.8	442.3	440.8	439.3
127.5°	478.0	476.2	474.3	472.5
130°	509.9	507.8	505.6	503.4
132.5°	543.2	541.5	539.8	538.1
135°	573.8	572.0	570.1	568.3
137.5°	606.0	604.5	603.0	601.5
140°	635.5	634.0	632.5	631.0
142.5°	665.6	664.1	662.6	661.1
145°	693.3	692.2	691.0	689.8
147.5°	720.0	718.5	717.0	715.5
150°	744.9	743.9	742.9	741.9
152.5°	768.3	767.3	766.3	765.3
155°	790.2	789.7	789.2	788.7
157.5°	810.1	809.8	809.4	809.1
160°	828.2	827.9	827.5	827.2
162.5°	843.8	843.8	843.8	843.8
165°	857.6	857.8	857.9	858.1
167.5°	869.5	870.0	870.5	871.0
170°	879.3	879.8	880.3	880.8
172.5°	886.1	886.6	887.1	887.6
175°	891.3	891.8	892.3	892.8
177.5°	894.4	894.9	895.4	895.9
180°	894.4	894.4	894.4	894.4

(END OF REPORT)