

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029421

Luminaire Tested: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029421
REPORT IS A COMBINATION OF REPORTS P985837 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K
Description: Define 2 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4635.0 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35			27
1	93	89	85	82	83	80	77	74	62	60	58	46	45	44	31	31	30			23
2	85	78	72	67	76	70	65	61	55	51	49	41	39	37	28	27	26			20
3	77	69	62	56	69	62	56	51	48	44	41	36	34	31	25	23	22			17
4	71	61	53	48	63	55	48	43	43	39	35	32	30	27	22	21	19			15
5	65	54	46	41	58	49	42	37	39	34	30	29	26	24	20	18	17			13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	19	17	15			12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	13			11
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12			10
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11			9
10	44	33	26	22	40	30	24	20	24	20	17	19	15	13	13	11	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9026	9026	9026	9026
5°	9047	9623	9082	7656
10°	8942	10506	8998	6312
15°	8725	11080	8846	5317
20°	8589	10405	8589	4622
25°	8316	8938	8353	4132
30°	7865	7027	8014	3744
35°	7466	4859	7591	3424
40°	7007	3669	7088	3171
45°	6443	3015	6548	2896
50°	5952	2646	5964	2652
55°	5396	2254	5430	2386
60°	4801	1883	4867	2082
65°	4269	1532	4348	1779
70°	3737	1201	3833	1435
75°	3138	873	3261	1039
80°	2451	553	2627	618
85°	1610	277	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9330 cd/sqm

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	1.2
10°-20°	158.1	3.4
20°-30°	229.4	4.9
30°-40°	241.8	5.2
40°-50°	214.0	4.6
50°-60°	170.9	3.7
60°-70°	116.1	2.5
70°-80°	59.4	1.3
80°-90°	17.5	0.4
90°-100°	74.6	1.6
100°-110°	237.3	5.1
110°-120°	406.0	8.8
120°-130°	534.0	11.5
130°-140°	599.4	12.9
140°-150°	587.8	12.7
150°-160°	493.1	10.6
160°-170°	327.0	7.1
170°-180°	114.3	2.5
0°-30°	441.8	9.5
0°-40°	683.6	14.7
0°-60°	1068.5	23.1
0°-90°	1261.4	27.2
90°-120°	718.0	15.5
90°-150°	2439.2	52.6
90°-180°	3374.0	72.8
0°-180°	4635.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	570	570	570	570	570	
5°	571	637	573	507	571	54
15°	536	783	543	376	536	151
25°	482	652	484	302	482	220
35°	393	355	400	250	393	246
45°	295	214	300	206	295	229
55°	202	150	204	159	202	181
65°	120	92	122	107	120	119
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	35	1	35	1	4
95°	53	63	53	63	53	59
105°	219	226	219	226	219	231
115°	407	407	407	407	407	403
125°	593	595	593	595	593	530
135°	767	776	767	776	767	593
145°	931	941	931	941	931	581
155°	1064	1072	1064	1072	1064	490
165°	1158	1159	1158	1159	1158	327
175°	1205	1200	1205	1200	1205	114
180°	1207	1207	1207	1207	1207	

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	573.3	574.6	576.8	577.2	581.6	585.1	589.0	589.0	590.3	589.9	586.4
5°	570.6	574.6	580.3	585.1	593.0	596.5	601.7	605.7	609.2	611.8	611.4
7.5°	566.2	573.3	581.6	590.8	601.3	607.4	614.9	621.9	626.7	631.1	634.2
10°	558.8	570.6	582.0	594.3	607.9	616.2	625.0	634.2	641.6	649.9	657.8
12.5°	548.7	565.8	579.8	596.0	612.7	621.9	635.9	642.9	657.4	678.4	684.1
15°	536.0	559.2	572.4	593.0	614.9	622.3	641.6	653.0	682.8	696.0	711.7
17.5°	524.2	550.0	567.6	591.2	612.7	627.2	646.0	669.2	694.2	713.1	730.6
20°	514.5	539.5	560.5	586.8	614.0	632.4	652.1	680.2	707.4	726.6	740.2
22.5°	492.6	524.6	549.1	578.5	611.4	636.8	655.6	686.3	715.7	727.5	739.4
25°	481.7	509.3	537.8	571.1	609.6	639.9	656.1	690.3	716.1	720.5	723.1
27.5°	461.5	492.6	525.9	564.0	609.2	634.6	655.2	686.3	706.9	703.9	696.0
30°	436.5	474.6	511.5	552.7	603.1	630.7	649.9	678.4	689.0	673.2	659.2
32.5°	418.1	454.0	494.8	542.6	596.0	622.3	641.2	663.5	665.7	637.2	613.6
35°	393.1	433.0	479.0	529.4	584.2	607.9	625.4	639.0	628.5	588.6	560.5
37.5°	370.8	410.2	459.3	510.6	568.0	591.2	605.2	607.4	581.6	546.5	505.3
40°	346.2	387.0	438.3	492.2	550.0	570.2	578.9	572.4	535.1	494.4	446.6
42.5°	321.7	362.0	417.2	472.5	527.2	544.3	547.8	529.9	484.3	436.5	381.3
45°	295.0	337.0	392.2	447.9	500.9	510.6	511.0	485.2	431.3	381.3	330.0
47.5°	273.0	312.0	366.8	422.5	467.2	473.8	471.1	441.3	382.6	326.5	281.8
50°	248.9	286.2	340.5	395.3	433.4	435.2	428.6	386.1	328.7	277.4	241.9
52.5°	223.1	260.8	310.7	363.3	397.5	394.9	382.2	336.6	282.7	240.2	213.0
55°	202.5	235.8	282.7	334.0	358.1	350.6	336.6	290.1	247.6	211.7	188.0
57.5°	179.7	209.1	255.1	299.8	313.8	306.8	292.8	249.4	209.9	182.8	167.0
60°	158.2	184.9	225.3	262.5	273.5	266.0	249.8	210.8	182.3	159.5	147.7
62.5°	138.5	161.7	195.5	229.7	234.0	226.6	212.6	181.0	156.5	138.5	129.7
65°	120.1	142.0	169.2	195.0	199.0	191.1	176.6	153.8	133.2	121.8	113.5
67.5°	102.1	119.6	143.8	162.6	164.8	157.3	145.5	127.1	114.4	102.1	96.0
70°	86.3	99.5	118.3	133.7	134.5	127.5	121.4	104.7	95.1	86.3	81.5
72.5°	71.0	80.2	94.7	106.1	106.5	102.1	96.4	85.9	77.6	71.4	66.6
75°	56.1	64.0	72.8	82.8	82.4	78.9	74.5	67.9	60.9	57.0	54.8
77.5°	43.0	47.8	54.8	61.4	61.4	59.6	57.0	52.2	47.8	43.8	41.6
80°	30.7	33.7	39.4	41.6	42.5	42.1	39.9	36.4	34.6	31.6	30.7
82.5°	19.7	21.9	24.5	26.7	28.0	27.2	26.7	25.0	22.4	21.5	20.6
85°	11.4	12.3	13.6	14.9	15.3	14.9	15.8	14.5	13.1	13.1	12.7
87.5°	4.8	5.3	6.1	6.1	6.6	6.6	6.1	6.6	6.6	6.1	5.7
90°	1.0	3.7	6.4	9.1	11.8	13.2	15.7	20.7	25.6	30.6	35.6
92.5°	22.4	24.2	26.0	27.8	29.6	30.5	30.6	30.9	31.1	31.4	31.6
95°	53.0	55.2	57.5	59.7	62.0	63.1	63.3	63.8	64.3	64.7	65.2
97.5°	88.6	90.6	92.7	94.7	96.8	97.8	98.2	99.1	100.0	100.9	101.8
100°	129.3	131.1	132.9	134.8	136.6	137.5	137.8	138.5	139.2	139.8	140.5
102.5°	172.1	173.5	174.8	176.2	177.5	178.2	178.7	179.6	180.5	181.4	182.3
105°	218.9	219.6	220.3	221.0	221.7	222.0	222.2	222.7	223.1	223.6	224.0
107.5°	265.8	266.7	267.6	268.5	269.4	269.8	269.8	269.8	269.8	269.8	269.8
110°	310.6	312.0	313.3	314.7	316.0	316.7	316.7	316.7	316.7	316.7	316.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	359.4	360.8	362.2	363.5	364.9	365.6	365.5	365.2	365.0	364.7	364.5
115°	407.3	408.7	410.0	411.4	412.7	413.4	413.2	412.7	412.3	411.8	411.4
117.5°	455.2	457.0	458.8	460.6	462.4	463.3	462.7	461.6	460.5	459.3	458.2
120°	503.0	504.8	506.6	508.5	510.3	511.2	510.3	508.5	506.6	504.8	503.0
122.5°	546.8	549.1	551.3	553.6	555.9	557.0	556.4	555.3	554.2	553.0	551.9
125°	592.6	594.6	596.7	598.7	600.8	601.8	601.5	600.8	600.1	599.4	598.7
127.5°	637.4	639.9	642.4	644.9	647.4	648.6	648.2	647.3	646.4	645.5	644.6
130°	679.2	682.1	685.1	688.0	690.9	692.4	692.2	691.7	691.3	690.8	690.4
132.5°	726.0	728.3	730.5	732.8	735.1	736.2	736.3	736.5	736.8	737.0	737.2
135°	766.8	769.3	771.8	774.3	776.8	778.0	778.2	778.7	779.1	779.6	780.0
137.5°	811.6	813.6	815.6	817.7	819.7	820.7	820.9	821.4	821.9	822.3	822.8
140°	851.3	853.3	855.3	857.4	859.4	860.4	861.0	862.1	863.2	864.4	865.5
142.5°	892.0	894.0	896.1	898.1	900.2	901.2	901.5	902.2	902.9	903.5	904.2
145°	930.7	932.3	933.9	935.4	937.0	937.8	938.5	939.8	941.2	942.5	943.9
147.5°	965.3	967.3	969.4	971.4	973.5	974.5	975.0	975.9	976.8	977.7	978.6
150°	1001.0	1002.4	1003.7	1005.1	1006.4	1007.1	1007.5	1008.4	1009.3	1010.2	1011.1
152.5°	1032.5	1033.9	1035.2	1036.6	1037.9	1038.6	1039.2	1040.3	1041.4	1042.6	1043.7
155°	1064.1	1064.8	1065.4	1066.1	1066.8	1067.1	1067.4	1068.1	1068.8	1069.5	1070.2
157.5°	1091.6	1092.0	1092.5	1092.9	1093.4	1093.6	1093.8	1094.3	1094.8	1095.2	1095.7
160°	1116.0	1116.5	1116.9	1117.4	1117.9	1118.1	1118.2	1118.4	1118.7	1118.9	1119.1
162.5°	1138.4	1138.4	1138.4	1138.4	1138.4	1138.4	1138.5	1138.7	1139.0	1139.2	1139.4
165°	1157.8	1157.6	1157.4	1157.1	1156.9	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8
167.5°	1175.1	1174.4	1173.7	1173.0	1172.3	1172.0	1172.0	1172.0	1172.0	1172.0	1172.0
170°	1188.3	1187.6	1187.0	1186.3	1185.6	1185.3	1185.2	1184.9	1184.7	1184.4	1184.2
172.5°	1197.5	1196.8	1196.1	1195.4	1194.7	1194.4	1194.3	1194.1	1193.8	1193.6	1193.4
175°	1204.6	1203.9	1203.3	1202.6	1201.9	1201.6	1201.4	1200.9	1200.4	1200.0	1199.5
177.5°	1208.7	1208.0	1207.3	1206.6	1205.9	1205.6	1205.4	1204.9	1204.5	1204.0	1203.6
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	592.5	593.0	593.9	598.2	600.4	600.9	599.1	603.1	604.4	603.1	602.2
5°	620.6	623.2	628.5	634.2	633.7	634.2	636.8	639.4	640.3	636.8	638.1
7.5°	645.1	650.4	656.1	664.8	664.8	669.2	671.0	673.2	678.4	675.8	674.9
10°	673.2	680.2	690.7	704.7	705.2	709.6	713.9	720.9	723.1	721.4	722.3
12.5°	708.2	721.8	722.7	738.0	745.1	745.9	752.9	751.6	756.0	756.0	763.5
15°	723.6	744.6	756.4	771.3	775.7	770.5	776.2	782.3	782.7	782.7	782.3
17.5°	751.2	759.5	771.3	779.2	781.0	781.0	781.4	784.1	782.3	778.8	781.4
20°	756.9	760.4	764.8	763.9	764.8	760.4	756.0	751.6	752.1	749.9	756.4
22.5°	746.4	745.5	735.4	728.8	728.8	720.1	711.7	707.8	703.9	705.2	707.4
25°	720.1	706.5	694.2	684.6	682.4	668.4	657.0	653.5	646.9	652.1	653.0
27.5°	678.0	662.7	642.9	634.6	623.2	617.5	609.6	599.1	585.5	593.4	592.1
30°	632.9	610.1	593.9	573.7	555.7	554.4	539.5	522.0	515.0	515.0	518.9
32.5°	582.5	552.2	528.5	500.1	482.5	475.1	457.1	439.6	443.5	430.4	435.2
35°	523.7	483.8	454.0	426.4	413.3	404.5	381.3	371.6	361.1	355.0	366.4
37.5°	467.6	421.6	383.5	353.2	348.4	332.6	316.9	310.7	304.6	307.2	306.8
40°	399.3	358.5	324.3	300.7	292.3	284.9	274.4	266.9	263.0	265.2	265.6
42.5°	337.5	303.3	277.9	261.2	254.2	248.9	243.7	237.5	236.2	236.2	238.0
45°	289.7	261.6	244.6	231.0	227.0	223.1	219.1	216.5	215.6	213.9	215.2
47.5°	251.6	229.2	218.7	208.6	204.2	203.4	199.8	198.5	196.8	196.3	196.8
50°	219.6	205.5	195.9	190.2	187.1	185.8	184.1	181.4	180.6	182.8	181.9
52.5°	197.2	184.1	178.8	173.1	171.4	169.6	167.0	167.4	167.0	166.1	166.1
55°	174.9	166.5	161.3	156.9	156.5	154.7	152.5	151.6	151.2	150.3	151.6
57.5°	156.9	150.3	145.5	141.6	139.8	139.8	137.6	135.9	135.9	135.4	135.9
60°	138.9	132.4	129.3	125.3	124.0	123.6	122.3	121.4	120.1	120.1	120.1
62.5°	122.3	117.0	113.5	110.0	110.4	108.3	106.5	105.6	105.6	106.1	106.1
65°	106.5	103.0	98.6	95.5	94.7	94.2	93.4	92.9	91.6	92.5	92.5
67.5°	92.0	87.2	84.6	83.3	82.0	81.5	80.6	79.8	79.3	78.9	79.8
70°	77.6	73.6	71.4	70.6	69.2	68.8	68.4	67.1	67.5	67.9	68.4
72.5°	64.4	60.9	60.5	57.9	57.9	57.9	56.1	57.0	56.5	55.7	56.5
75°	50.8	49.1	48.2	46.9	47.3	46.9	46.5	45.1	45.1	45.6	46.0
77.5°	40.3	38.6	38.1	36.8	35.9	36.8	35.9	35.5	35.5	35.9	35.9
80°	29.8	28.9	27.6	27.6	27.6	27.2	27.2	27.2	26.7	26.3	26.7
82.5°	19.7	19.7	19.3	18.8	19.3	18.4	18.8	18.8	18.8	18.8	18.8
85°	12.7	12.3	12.3	11.8	11.8	11.8	12.3	11.4	11.4	11.8	11.8
87.5°	5.7	5.7	5.7	6.1	5.7	5.7	5.7	6.1	5.7	5.7	5.7
90°	35.2	34.7	34.3	33.8	33.6	33.7	33.9	34.2	34.4	34.6	34.4
92.5°	31.8	32.0	32.3	32.5	32.6	32.6	32.6	32.6	32.6	32.6	32.6
95°	65.2	65.2	65.2	65.2	65.2	65.0	64.5	64.0	63.6	63.1	63.6
97.5°	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8
100°	140.5	140.5	140.5	140.5	140.5	140.4	140.2	139.9	139.7	139.5	139.7
102.5°	182.5	182.7	183.0	183.2	183.3	183.2	183.0	182.7	182.5	182.3	182.5
105°	224.5	224.9	225.4	225.9	226.1	226.1	226.1	226.1	226.1	226.1	226.1
107.5°	270.0	270.3	270.5	270.8	270.9	270.3	269.2	268.1	266.9	265.8	266.9
110°	316.7	316.7	316.7	316.7	316.7	316.4	315.7	315.0	314.3	313.6	314.3

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	363.8	363.2	362.5	361.8	361.5	361.3	360.8	360.3	359.9	359.4	359.9
115°	411.2	411.0	410.7	410.5	410.4	410.1	409.4	408.7	408.0	407.3	408.0
117.5°	457.5	456.9	456.2	455.5	455.2	454.9	454.2	453.5	452.8	452.1	452.8
120°	503.0	503.0	503.0	503.0	503.0	502.7	502.0	501.3	500.7	500.0	500.7
122.5°	551.2	550.5	549.8	549.1	548.8	548.6	548.1	547.7	547.2	546.8	547.2
125°	598.0	597.4	596.7	596.0	595.7	595.6	595.4	595.1	594.9	594.7	594.9
127.5°	643.7	642.8	641.9	641.0	640.5	640.2	639.5	638.8	638.1	637.4	638.1
130°	690.0	689.5	689.1	688.6	688.4	687.9	687.0	686.1	685.2	684.3	685.2
132.5°	736.1	734.9	733.8	732.7	732.1	731.8	731.1	730.4	729.8	729.1	729.8
135°	779.8	779.6	779.3	779.1	779.0	778.7	778.0	777.3	776.6	775.9	776.6
137.5°	822.6	822.3	822.1	821.8	821.7	821.3	820.4	819.5	818.6	817.7	818.6
140°	865.5	865.5	865.5	865.5	865.5	865.1	864.2	863.3	862.4	861.5	862.4
142.5°	904.4	904.6	904.9	905.1	905.2	904.8	903.9	903.0	902.1	901.2	902.1
145°	944.1	944.4	944.6	944.9	945.0	944.5	943.6	942.7	941.8	940.9	941.8
147.5°	979.0	979.5	979.9	980.4	980.6	980.1	979.2	978.3	977.4	976.5	977.4
150°	1011.8	1012.5	1013.2	1013.9	1014.2	1013.9	1013.2	1012.5	1011.8	1011.1	1011.8
152.5°	1044.6	1045.5	1046.4	1047.3	1047.8	1047.3	1046.4	1045.5	1044.6	1043.7	1044.6
155°	1071.3	1072.5	1073.6	1074.7	1075.3	1075.0	1074.3	1073.6	1072.9	1072.2	1072.9
157.5°	1097.3	1098.9	1100.4	1102.0	1102.8	1102.2	1101.1	1100.0	1098.8	1097.7	1098.8
160°	1120.5	1121.8	1123.2	1124.5	1125.2	1124.7	1123.8	1122.9	1122.0	1121.1	1122.0
162.5°	1141.0	1142.6	1144.2	1145.8	1146.6	1146.0	1144.9	1143.8	1142.6	1141.5	1142.6
165°	1158.4	1160.0	1161.5	1163.1	1163.9	1163.3	1162.2	1161.1	1159.9	1158.8	1159.9
167.5°	1173.6	1175.2	1176.8	1178.4	1179.2	1178.6	1177.5	1176.4	1175.2	1174.1	1175.2
170°	1185.8	1187.4	1189.0	1190.6	1191.4	1190.7	1189.4	1188.0	1186.7	1185.3	1186.7
172.5°	1195.0	1196.6	1198.1	1199.7	1200.5	1199.8	1198.5	1197.1	1195.8	1194.4	1195.8
175°	1201.1	1202.7	1204.3	1205.9	1206.7	1206.0	1204.6	1203.3	1201.9	1200.5	1201.9
177.5°	1205.0	1206.3	1207.7	1209.0	1209.7	1209.0	1207.7	1206.3	1205.0	1203.6	1205.0
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	604.4	601.3	598.7	599.1	601.3	599.5	595.2	589.5	587.3	584.6	587.3
5°	640.7	638.1	632.9	633.3	632.0	630.2	623.2	614.4	614.4	607.4	606.6
7.5°	676.7	672.7	669.2	668.4	663.5	660.0	653.9	641.6	636.8	628.5	623.7
10°	717.0	713.9	710.0	705.2	702.5	696.4	686.3	668.4	659.6	648.2	639.9
12.5°	757.8	757.3	748.6	738.9	738.5	728.8	721.8	697.7	685.9	670.5	650.8
15°	783.6	781.4	776.6	771.8	773.1	762.6	746.8	718.3	710.4	692.0	671.0
17.5°	783.2	783.2	781.9	781.0	779.7	776.6	767.8	749.0	736.3	713.1	693.3
20°	758.2	763.9	765.2	764.8	769.2	771.3	770.9	759.1	749.0	728.4	708.2
22.5°	708.2	721.4	727.1	730.6	739.8	744.6	756.0	751.6	749.0	733.7	716.6
25°	661.8	666.2	683.3	684.1	696.8	708.7	720.1	727.5	737.2	731.5	717.0
27.5°	601.7	611.8	624.1	633.3	635.9	660.0	678.9	692.9	714.8	716.6	711.7
30°	533.8	538.6	558.8	571.1	585.1	602.6	629.8	653.9	673.6	691.6	697.7
32.5°	451.0	470.7	482.5	497.4	509.7	540.8	574.1	605.2	628.0	658.3	671.4
35°	375.2	390.5	410.7	416.8	439.1	465.4	508.8	548.7	583.3	614.0	640.7
37.5°	312.5	324.8	346.2	355.9	369.0	402.8	439.1	488.7	530.3	568.0	601.3
40°	269.5	278.7	295.0	298.0	309.0	339.7	369.0	415.5	470.7	521.5	557.9
42.5°	240.2	244.6	255.5	259.5	266.5	287.1	313.4	357.2	408.5	461.1	512.3
45°	219.1	222.2	228.8	232.3	241.0	250.2	271.7	306.8	347.1	400.1	455.4
47.5°	200.3	204.2	206.9	209.1	213.9	224.0	238.0	263.8	302.4	351.1	404.5
50°	184.5	185.8	190.6	191.1	194.2	200.7	213.9	229.7	260.3	299.8	351.5
52.5°	168.7	170.0	173.1	176.2	177.5	182.8	191.5	204.7	227.5	258.6	304.6
55°	153.0	154.7	157.8	160.0	161.3	165.7	170.9	183.6	201.6	223.5	261.2
57.5°	137.2	141.1	142.0	143.3	145.5	150.3	155.1	162.6	176.6	196.8	224.4
60°	122.3	123.6	126.7	128.0	130.2	132.8	138.9	144.6	154.7	170.5	195.5
62.5°	106.9	110.0	111.3	112.6	114.4	117.5	121.4	127.5	136.3	149.0	168.7
65°	93.8	94.2	96.9	98.6	100.4	102.6	106.5	112.2	117.5	129.3	143.8
67.5°	81.1	82.0	82.8	84.6	86.8	89.0	92.5	95.5	102.1	110.0	121.4
70°	68.8	68.8	71.0	72.3	71.9	74.5	77.1	80.6	85.5	92.9	102.1
72.5°	57.9	57.4	59.2	59.6	60.5	62.2	64.0	67.5	70.1	75.8	82.8
75°	46.0	46.9	47.8	47.8	49.1	50.4	52.2	53.9	57.0	60.5	65.7
77.5°	36.4	36.4	37.3	37.7	39.0	38.6	40.3	42.1	44.3	47.3	51.3
80°	26.7	27.6	27.6	27.6	28.0	28.5	30.2	31.6	32.9	35.1	36.8
82.5°	18.8	18.8	19.7	19.7	19.7	20.6	20.6	21.0	21.9	23.2	24.5
85°	11.8	11.8	11.8	12.3	11.8	12.3	13.1	12.7	13.1	14.0	14.0
87.5°	5.7	5.7	5.7	5.7	5.7	6.1	5.7	6.1	6.6	6.6	6.6
90°	34.2	33.9	33.7	33.6	33.8	34.3	34.7	35.2	35.6	30.6	25.6
92.5°	32.6	32.6	32.6	32.6	32.5	32.3	32.0	31.8	31.6	31.4	31.1
95°	64.0	64.5	65.0	65.2	65.2	65.2	65.2	65.2	65.2	64.7	64.3
97.5°	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	100.9	100.0
100°	139.9	140.2	140.4	140.5	140.5	140.5	140.5	140.5	140.5	139.8	139.2
102.5°	182.7	183.0	183.2	183.3	183.2	183.0	182.7	182.5	182.3	181.4	180.5
105°	226.1	226.1	226.1	226.1	225.9	225.4	224.9	224.5	224.0	223.6	223.1
107.5°	268.1	269.2	270.3	270.9	270.8	270.5	270.3	270.0	269.8	269.8	269.8
110°	315.0	315.7	316.4	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	360.3	360.8	361.3	361.5	361.8	362.5	363.2	363.8	364.5	364.7	365.0
115°	408.7	409.4	410.1	410.4	410.5	410.7	411.0	411.2	411.4	411.8	412.3
117.5°	453.5	454.2	454.9	455.2	455.5	456.2	456.9	457.5	458.2	459.3	460.5
120°	501.3	502.0	502.7	503.0	503.0	503.0	503.0	503.0	503.0	504.8	506.6
122.5°	547.7	548.1	548.6	548.8	549.1	549.8	550.5	551.2	551.9	553.0	554.2
125°	595.1	595.4	595.6	595.7	596.0	596.7	597.4	598.0	598.7	599.4	600.1
127.5°	638.8	639.5	640.2	640.5	641.0	641.9	642.8	643.7	644.6	645.5	646.4
130°	686.1	687.0	687.9	688.4	688.6	689.1	689.5	690.0	690.4	690.8	691.3
132.5°	730.4	731.1	731.8	732.1	732.7	733.8	734.9	736.1	737.2	737.0	736.8
135°	777.3	778.0	778.7	779.0	779.1	779.3	779.6	779.8	780.0	779.6	779.1
137.5°	819.5	820.4	821.3	821.7	821.8	822.1	822.3	822.6	822.8	822.3	821.9
140°	863.3	864.2	865.1	865.5	865.5	865.5	865.5	865.5	865.5	864.4	863.2
142.5°	903.0	903.9	904.8	905.2	905.1	904.9	904.6	904.4	904.2	903.5	902.9
145°	942.7	943.6	944.5	945.0	944.9	944.6	944.4	944.1	943.9	942.5	941.2
147.5°	978.3	979.2	980.1	980.6	980.4	979.9	979.5	979.0	978.6	977.7	976.8
150°	1012.5	1013.2	1013.9	1014.2	1013.9	1013.2	1012.5	1011.8	1011.1	1010.2	1009.3
152.5°	1045.5	1046.4	1047.3	1047.8	1047.3	1046.4	1045.5	1044.6	1043.7	1042.6	1041.4
155°	1073.6	1074.3	1075.0	1075.3	1074.7	1073.6	1072.5	1071.3	1070.2	1069.5	1068.8
157.5°	1100.0	1101.1	1102.2	1102.8	1102.0	1100.4	1098.9	1097.3	1095.7	1095.2	1094.8
160°	1122.9	1123.8	1124.7	1125.2	1124.5	1123.2	1121.8	1120.5	1119.1	1118.9	1118.7
162.5°	1143.8	1144.9	1146.0	1146.6	1145.8	1144.2	1142.6	1141.0	1139.4	1139.2	1139.0
165°	1161.1	1162.2	1163.3	1163.9	1163.1	1161.5	1160.0	1158.4	1156.8	1156.8	1156.8
167.5°	1176.4	1177.5	1178.6	1179.2	1178.4	1176.8	1175.2	1173.6	1172.0	1172.0	1172.0
170°	1188.0	1189.4	1190.7	1191.4	1190.6	1189.0	1187.4	1185.8	1184.2	1184.4	1184.7
172.5°	1197.1	1198.5	1199.8	1200.5	1199.7	1198.1	1196.6	1195.0	1193.4	1193.6	1193.8
175°	1203.3	1204.6	1206.0	1206.7	1205.9	1204.3	1202.7	1201.1	1199.5	1200.0	1200.4
177.5°	1206.3	1207.7	1209.0	1209.7	1209.0	1207.7	1206.3	1205.0	1203.6	1204.0	1204.5
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	585.1	582.9	581.6	582.5	579.8	573.3	573.3	575.4	572.8	570.2	566.2
5°	601.3	596.9	594.3	593.9	587.7	577.2	575.0	572.8	567.1	561.0	554.4
7.5°	617.1	609.2	604.8	601.7	593.0	579.4	573.7	568.9	559.7	550.5	542.1
10°	630.2	618.8	613.6	608.8	597.4	580.3	571.1	562.3	550.5	538.6	528.1
12.5°	640.7	627.6	621.0	614.0	600.0	577.6	566.2	552.2	540.4	524.6	514.1
15°	658.3	631.1	625.0	618.4	603.9	573.3	559.2	543.4	527.2	506.2	494.8
17.5°	672.3	635.9	635.5	621.5	602.6	571.5	550.0	529.4	511.9	490.9	472.9
20°	680.6	643.4	636.4	621.9	598.2	559.7	537.3	514.5	495.7	470.3	452.3
22.5°	687.6	653.9	635.5	618.0	589.0	555.7	522.9	501.4	475.5	447.9	430.8
25°	690.3	656.1	636.8	616.6	582.5	544.3	507.1	483.8	454.9	429.9	406.7
27.5°	690.7	655.6	632.0	610.9	573.3	529.4	491.3	466.8	434.8	405.8	382.6
30°	686.3	650.8	629.4	606.6	564.5	515.8	472.0	444.8	410.7	381.7	357.6
32.5°	673.2	641.2	623.7	598.7	553.1	497.0	453.6	423.4	387.4	358.9	335.7
35°	651.3	629.4	610.1	586.8	538.2	479.5	435.2	399.7	363.3	336.2	314.2
37.5°	624.1	612.3	594.3	571.5	521.1	463.7	414.6	375.2	338.8	312.5	291.0
40°	587.3	590.3	572.8	552.2	500.9	442.2	387.9	350.2	316.0	291.4	270.4
42.5°	547.4	560.1	550.0	530.3	478.6	418.5	368.1	326.5	293.2	267.8	250.2
45°	504.4	526.4	520.2	505.8	455.4	393.6	340.1	299.8	270.4	245.9	230.5
47.5°	457.5	488.7	488.7	478.1	429.5	368.6	316.0	274.8	245.9	228.3	213.4
50°	409.8	444.8	450.5	443.5	400.6	340.1	286.6	249.4	224.4	207.3	196.3
52.5°	359.8	400.6	411.1	407.6	369.9	312.9	262.5	226.1	203.4	188.5	178.8
55°	312.0	359.4	370.8	372.1	337.0	283.1	235.8	203.8	181.9	171.8	163.5
57.5°	266.9	312.5	325.2	327.4	303.7	255.9	210.8	182.8	163.0	154.7	148.1
60°	228.3	266.5	283.1	287.9	267.3	224.4	187.6	160.4	145.5	137.6	131.5
62.5°	196.8	227.5	245.0	246.3	237.1	196.8	163.5	140.7	128.0	121.0	117.9
65°	166.1	193.7	204.2	209.5	202.0	170.5	141.1	122.3	112.2	106.1	103.0
67.5°	141.6	159.1	167.9	174.9	167.4	143.8	120.1	104.7	97.3	91.2	89.4
70°	116.1	130.6	137.2	144.2	137.6	119.6	102.6	88.5	82.0	77.1	74.9
72.5°	92.9	104.3	110.4	114.8	110.9	96.0	82.0	72.3	67.5	64.0	62.7
75°	73.6	81.5	85.0	88.1	86.3	74.9	66.2	58.3	53.9	50.8	50.0
77.5°	56.1	61.8	65.7	66.6	64.4	57.0	49.5	44.7	41.2	39.4	38.6
80°	39.9	43.4	45.6	46.9	44.7	41.6	36.4	32.9	29.8	27.6	27.2
82.5°	26.7	28.5	30.2	29.8	28.9	26.3	23.2	21.5	20.2	18.4	18.4
85°	15.3	15.8	16.7	17.1	16.7	14.9	13.1	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	3.9
90°	20.7	15.7	13.2	11.8	9.1	6.4	3.7	1.0	3.7	6.4	9.1
92.5°	30.9	30.6	30.5	29.6	27.8	26.0	24.2	22.4	24.2	26.0	27.8
95°	63.8	63.3	63.1	62.0	59.7	57.5	55.2	53.0	55.2	57.5	59.7
97.5°	99.1	98.2	97.8	96.8	94.7	92.7	90.6	88.6	90.6	92.7	94.7
100°	138.5	137.8	137.5	136.6	134.8	132.9	131.1	129.3	131.1	132.9	134.8
102.5°	179.6	178.7	178.2	177.5	176.2	174.8	173.5	172.1	173.5	174.8	176.2
105°	222.7	222.2	222.0	221.7	221.0	220.3	219.6	218.9	219.6	220.3	221.0
107.5°	269.8	269.8	269.8	269.4	268.5	267.6	266.7	265.8	266.7	267.6	268.5
110°	316.7	316.7	316.7	316.0	314.7	313.3	312.0	310.6	312.0	313.3	314.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	365.2	365.5	365.6	364.9	363.5	362.2	360.8	359.4	360.8	362.2	363.5
115°	412.7	413.2	413.4	412.7	411.4	410.0	408.7	407.3	408.7	410.0	411.4
117.5°	461.6	462.7	463.3	462.4	460.6	458.8	457.0	455.2	457.0	458.8	460.6
120°	508.5	510.3	511.2	510.3	508.5	506.6	504.8	503.0	504.8	506.6	508.5
122.5°	555.3	556.4	557.0	555.9	553.6	551.3	549.1	546.8	549.1	551.3	553.6
125°	600.8	601.5	601.8	600.8	598.7	596.7	594.6	592.6	594.6	596.7	598.7
127.5°	647.3	648.2	648.6	647.4	644.9	642.4	639.9	637.4	639.9	642.4	644.9
130°	691.7	692.2	692.4	690.9	688.0	685.1	682.1	679.2	682.1	685.1	688.0
132.5°	736.5	736.3	736.2	735.1	732.8	730.5	728.3	726.0	728.3	730.5	732.8
135°	778.7	778.2	778.0	776.8	774.3	771.8	769.3	766.8	769.3	771.8	774.3
137.5°	821.4	820.9	820.7	819.7	817.7	815.6	813.6	811.6	813.6	815.6	817.7
140°	862.1	861.0	860.4	859.4	857.4	855.3	853.3	851.3	853.3	855.3	857.4
142.5°	902.2	901.5	901.2	900.2	898.1	896.1	894.0	892.0	894.0	896.1	898.1
145°	939.8	938.5	937.8	937.0	935.4	933.9	932.3	930.7	932.3	933.9	935.4
147.5°	975.9	975.0	974.5	973.5	971.4	969.4	967.3	965.3	967.3	969.4	971.4
150°	1008.4	1007.5	1007.1	1006.4	1005.1	1003.7	1002.4	1001.0	1002.4	1003.7	1005.1
152.5°	1040.3	1039.2	1038.6	1037.9	1036.6	1035.2	1033.9	1032.5	1033.9	1035.2	1036.6
155°	1068.1	1067.4	1067.1	1066.8	1066.1	1065.4	1064.8	1064.1	1064.8	1065.4	1066.1
157.5°	1094.3	1093.8	1093.6	1093.4	1092.9	1092.5	1092.0	1091.6	1092.0	1092.5	1092.9
160°	1118.4	1118.2	1118.1	1117.9	1117.4	1116.9	1116.5	1116.0	1116.5	1116.9	1117.4
162.5°	1138.7	1138.5	1138.4	1138.4	1138.4	1138.4	1138.4	1138.4	1138.4	1138.4	1138.4
165°	1156.8	1156.8	1156.8	1156.9	1157.1	1157.4	1157.6	1157.8	1157.6	1157.4	1157.1
167.5°	1172.0	1172.0	1172.0	1172.3	1173.0	1173.7	1174.4	1175.1	1174.4	1173.7	1173.0
170°	1184.9	1185.2	1185.3	1185.6	1186.3	1187.0	1187.6	1188.3	1187.6	1187.0	1186.3
172.5°	1194.1	1194.3	1194.4	1194.7	1195.4	1196.1	1196.8	1197.5	1196.8	1196.1	1195.4
175°	1200.9	1201.4	1201.6	1201.9	1202.6	1203.3	1203.9	1204.6	1203.9	1203.3	1202.6
177.5°	1204.9	1205.4	1205.6	1205.9	1206.6	1207.3	1208.0	1208.7	1208.0	1207.3	1206.6
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	564.0	566.2	565.8	561.4	556.6	552.7	545.2	546.1	543.4	543.9	546.5
5°	550.0	550.0	548.3	542.1	534.2	529.9	521.5	519.3	514.1	513.6	513.2
7.5°	535.1	532.9	530.7	522.0	512.3	505.3	493.9	491.3	486.0	482.5	480.8
10°	517.6	514.5	510.1	500.1	488.2	479.5	467.6	464.1	454.0	449.7	447.0
12.5°	498.3	496.6	489.5	481.2	461.9	452.3	435.2	438.7	428.6	419.9	418.5
15°	479.0	472.5	468.5	454.9	431.7	427.3	413.7	406.7	397.5	390.5	390.5
17.5°	460.2	450.1	441.3	426.9	409.8	397.5	387.4	383.9	372.5	365.5	364.2
20°	435.2	423.8	421.6	401.0	389.2	375.6	366.0	357.2	348.9	345.8	343.6
22.5°	411.5	398.4	394.9	377.3	365.5	351.9	342.3	336.2	330.0	327.8	323.9
25°	386.1	378.2	373.0	354.1	341.0	328.3	321.7	317.3	311.6	311.2	308.5
27.5°	361.6	354.1	348.9	330.9	321.2	309.4	304.2	299.3	296.3	295.0	293.6
30°	340.5	332.2	326.1	312.9	301.1	291.4	287.1	284.0	282.2	280.1	279.6
32.5°	317.3	312.5	304.2	294.1	284.9	275.7	273.0	270.8	268.2	267.3	266.9
35°	297.6	291.0	285.7	274.4	270.4	262.5	259.5	257.7	254.2	253.3	252.4
37.5°	278.3	272.2	266.5	259.5	252.0	247.6	245.9	243.2	241.5	241.9	241.0
40°	259.0	254.2	249.8	242.4	238.0	235.8	232.3	229.7	228.8	229.2	228.8
42.5°	240.2	235.8	233.2	227.5	223.1	220.9	218.7	216.1	217.4	217.4	218.7
45°	223.1	219.1	217.4	213.0	210.4	206.9	204.7	204.2	206.0	205.5	205.5
47.5°	205.5	204.2	202.0	198.1	194.6	192.4	192.0	192.0	193.7	194.6	194.2
50°	192.0	189.3	186.7	183.6	181.0	180.1	178.8	179.7	181.4	181.4	182.3
52.5°	174.9	173.1	172.2	169.6	167.9	167.9	167.9	168.3	169.6	170.9	170.5
55°	160.0	158.7	157.8	156.5	154.3	154.7	154.3	155.1	156.5	157.8	158.7
57.5°	144.2	143.8	142.9	140.7	140.7	140.2	141.6	142.0	144.2	145.1	146.4
60°	130.2	128.9	128.9	127.1	127.1	127.1	128.4	129.7	131.5	131.9	132.8
62.5°	115.3	115.3	114.8	113.5	113.5	114.8	115.3	117.0	117.9	117.9	119.2
65°	101.2	100.8	100.4	100.8	101.2	101.2	102.6	103.4	104.3	104.7	105.2
67.5°	87.2	86.8	87.7	87.2	88.1	89.8	89.4	90.7	92.0	92.0	92.5
70°	74.1	74.9	74.5	75.4	74.9	75.8	77.1	77.6	77.6	78.0	79.3
72.5°	61.8	61.8	61.8	61.4	61.8	62.7	63.5	64.0	64.9	65.3	66.6
75°	50.0	50.0	49.1	50.0	50.0	50.8	51.7	51.7	51.7	52.6	53.9
77.5°	37.7	38.1	37.7	38.6	38.6	39.0	39.9	39.4	40.3	40.8	41.2
80°	27.6	27.2	27.2	27.2	27.6	27.6	28.5	28.9	28.9	30.2	29.4
82.5°	17.5	18.0	17.5	18.0	18.0	18.4	18.0	18.4	18.8	19.7	19.3
85°	10.1	9.6	9.6	10.1	9.6	9.6	10.1	9.6	10.1	9.6	10.1
87.5°	3.9	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	11.8	13.2	15.7	20.7	25.6	30.6	35.6	35.2	34.7	34.3	33.8
92.5°	29.6	30.5	30.6	30.9	31.1	31.4	31.6	31.8	32.0	32.3	32.5
95°	62.0	63.1	63.3	63.8	64.3	64.7	65.2	65.2	65.2	65.2	65.2
97.5°	96.8	97.8	98.2	99.1	100.0	100.9	101.8	101.8	101.8	101.8	101.8
100°	136.6	137.5	137.8	138.5	139.2	139.8	140.5	140.5	140.5	140.5	140.5
102.5°	177.5	178.2	178.7	179.6	180.5	181.4	182.3	182.5	182.7	183.0	183.2
105°	221.7	222.0	222.2	222.7	223.1	223.6	224.0	224.5	224.9	225.4	225.9
107.5°	269.4	269.8	269.8	269.8	269.8	269.8	269.8	270.0	270.3	270.5	270.8
110°	316.0	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	364.9	365.6	365.5	365.2	365.0	364.7	364.5	363.8	363.2	362.5	361.8
115°	412.7	413.4	413.2	412.7	412.3	411.8	411.4	411.2	411.0	410.7	410.5
117.5°	462.4	463.3	462.7	461.6	460.5	459.3	458.2	457.5	456.9	456.2	455.5
120°	510.3	511.2	510.3	508.5	506.6	504.8	503.0	503.0	503.0	503.0	503.0
122.5°	555.9	557.0	556.4	555.3	554.2	553.0	551.9	551.2	550.5	549.8	549.1
125°	600.8	601.8	601.5	600.8	600.1	599.4	598.7	598.0	597.4	596.7	596.0
127.5°	647.4	648.6	648.2	647.3	646.4	645.5	644.6	643.7	642.8	641.9	641.0
130°	690.9	692.4	692.2	691.7	691.3	690.8	690.4	690.0	689.5	689.1	688.6
132.5°	735.1	736.2	736.3	736.5	736.8	737.0	737.2	736.1	734.9	733.8	732.7
135°	776.8	778.0	778.2	778.7	779.1	779.6	780.0	779.8	779.6	779.3	779.1
137.5°	819.7	820.7	820.9	821.4	821.9	822.3	822.8	822.6	822.3	822.1	821.8
140°	859.4	860.4	861.0	862.1	863.2	864.4	865.5	865.5	865.5	865.5	865.5
142.5°	900.2	901.2	901.5	902.2	902.9	903.5	904.2	904.4	904.6	904.9	905.1
145°	937.0	937.8	938.5	939.8	941.2	942.5	943.9	944.1	944.4	944.6	944.9
147.5°	973.5	974.5	975.0	975.9	976.8	977.7	978.6	979.0	979.5	979.9	980.4
150°	1006.4	1007.1	1007.5	1008.4	1009.3	1010.2	1011.1	1011.8	1012.5	1013.2	1013.9
152.5°	1037.9	1038.6	1039.2	1040.3	1041.4	1042.6	1043.7	1044.6	1045.5	1046.4	1047.3
155°	1066.8	1067.1	1067.4	1068.1	1068.8	1069.5	1070.2	1071.3	1072.5	1073.6	1074.7
157.5°	1093.4	1093.6	1093.8	1094.3	1094.8	1095.2	1095.7	1097.3	1098.9	1100.4	1102.0
160°	1117.9	1118.1	1118.2	1118.4	1118.7	1118.9	1119.1	1120.5	1121.8	1123.2	1124.5
162.5°	1138.4	1138.4	1138.5	1138.7	1139.0	1139.2	1139.4	1141.0	1142.6	1144.2	1145.8
165°	1156.9	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1158.4	1160.0	1161.5	1163.1
167.5°	1172.3	1172.0	1172.0	1172.0	1172.0	1172.0	1172.0	1173.6	1175.2	1176.8	1178.4
170°	1185.6	1185.3	1185.2	1184.9	1184.7	1184.4	1184.2	1185.8	1187.4	1189.0	1190.6
172.5°	1194.7	1194.4	1194.3	1194.1	1193.8	1193.6	1193.4	1195.0	1196.6	1198.1	1199.7
175°	1201.9	1201.6	1201.4	1200.9	1200.4	1200.0	1199.5	1201.1	1202.7	1204.3	1205.9
177.5°	1205.9	1205.6	1205.4	1204.9	1204.5	1204.0	1203.6	1205.0	1206.3	1207.7	1209.0
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	543.4	544.8	541.7	540.8	541.7	538.6	539.5	540.4	540.4	541.7	542.6
5°	511.9	510.1	507.1	506.2	505.3	506.6	505.8	507.1	507.5	510.6	511.0
7.5°	480.8	478.1	475.5	472.9	472.0	469.8	472.0	472.0	475.1	474.2	476.4
10°	444.0	443.5	440.0	438.7	437.0	433.4	438.3	437.0	439.1	443.1	444.0
12.5°	416.8	412.0	414.2	408.0	410.2	406.7	407.1	407.1	410.7	411.1	410.2
15°	390.9	387.0	381.3	378.7	377.3	375.6	381.3	381.7	379.1	385.2	383.0
17.5°	364.6	364.6	359.4	358.1	354.6	356.3	355.4	355.9	355.0	359.4	361.6
20°	341.8	339.7	337.9	338.3	334.0	333.1	332.2	333.1	336.2	339.2	340.1
22.5°	323.4	322.1	317.7	318.6	315.1	316.4	315.6	317.7	318.2	318.2	321.2
25°	305.9	304.2	304.6	302.8	301.5	301.5	300.2	301.5	303.3	304.2	304.6
27.5°	292.8	291.4	289.3	287.9	288.8	286.6	288.4	289.7	289.7	288.8	289.7
30°	277.0	277.9	277.9	273.5	275.2	274.4	275.7	276.5	276.5	277.0	276.1
32.5°	266.5	263.8	263.4	263.0	263.0	261.2	261.2	262.5	263.0	263.4	264.7
35°	252.4	252.4	250.2	251.6	249.8	250.2	249.8	250.2	251.1	249.8	251.1
37.5°	239.7	240.2	239.3	240.2	240.6	239.7	238.9	240.6	239.7	239.7	238.9
40°	228.8	228.3	228.8	228.8	228.8	229.2	228.3	228.3	228.3	227.5	226.6
42.5°	219.6	216.9	217.8	218.3	216.9	216.9	217.4	216.9	218.3	215.6	215.6
45°	206.4	205.5	206.0	206.0	206.9	205.5	206.4	206.9	205.5	205.1	204.2
47.5°	194.6	195.5	194.6	195.5	195.5	196.3	194.6	195.0	195.5	193.7	192.4
50°	182.8	182.8	184.1	183.6	184.1	183.2	183.2	182.8	183.2	182.3	181.0
52.5°	171.8	170.5	172.7	172.2	171.8	171.4	170.9	171.4	170.5	169.6	169.6
55°	158.2	158.2	159.5	160.0	160.0	159.1	158.2	158.7	158.2	157.8	157.3
57.5°	147.3	145.5	146.4	146.8	146.8	145.5	146.4	145.5	145.5	145.9	144.6
60°	133.2	133.2	132.4	133.7	133.7	132.8	132.8	133.2	132.4	131.9	131.5
62.5°	118.3	118.8	120.1	120.5	121.0	120.1	119.2	119.6	119.6	118.3	118.8
65°	105.6	106.5	108.3	107.8	106.9	107.4	106.5	106.9	105.6	106.1	104.7
67.5°	93.4	92.9	93.4	93.4	94.2	93.8	92.9	92.9	92.5	93.8	92.5
70°	80.2	80.2	80.2	80.2	80.6	81.1	80.2	79.3	79.8	78.9	78.4
72.5°	66.6	67.1	66.6	67.5	66.2	67.1	67.1	66.6	66.2	66.2	66.2
75°	53.9	54.8	53.5	53.9	53.5	54.3	53.9	53.9	53.0	52.6	53.0
77.5°	41.2	41.6	40.8	41.2	40.8	41.2	41.2	40.8	40.8	40.8	40.8
80°	29.4	29.8	29.4	28.9	28.5	29.4	28.5	28.9	29.4	28.9	29.8
82.5°	18.8	18.8	18.4	18.8	18.0	18.0	18.4	18.4	18.0	18.8	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.6	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	33.6	33.7	33.9	34.2	34.4	34.6	34.4	34.2	33.9	33.7	33.6
92.5°	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6
95°	65.2	65.0	64.5	64.0	63.6	63.1	63.6	64.0	64.5	65.0	65.2
97.5°	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8	101.8
100°	140.5	140.4	140.2	139.9	139.7	139.5	139.7	139.9	140.2	140.4	140.5
102.5°	183.3	183.2	183.0	182.7	182.5	182.3	182.5	182.7	183.0	183.2	183.3
105°	226.1	226.1	226.1	226.1	226.1	226.1	226.1	226.1	226.1	226.1	226.1
107.5°	270.9	270.3	269.2	268.1	266.9	265.8	266.9	268.1	269.2	270.3	270.9
110°	316.7	316.4	315.7	315.0	314.3	313.6	314.3	315.0	315.7	316.4	316.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	361.5	361.3	360.8	360.3	359.9	359.4	359.9	360.3	360.8	361.3	361.5
115°	410.4	410.1	409.4	408.7	408.0	407.3	408.0	408.7	409.4	410.1	410.4
117.5°	455.2	454.9	454.2	453.5	452.8	452.1	452.8	453.5	454.2	454.9	455.2
120°	503.0	502.7	502.0	501.3	500.7	500.0	500.7	501.3	502.0	502.7	503.0
122.5°	548.8	548.6	548.1	547.7	547.2	546.8	547.2	547.7	548.1	548.6	548.8
125°	595.7	595.6	595.4	595.1	594.9	594.7	594.9	595.1	595.4	595.6	595.7
127.5°	640.5	640.2	639.5	638.8	638.1	637.4	638.1	638.8	639.5	640.2	640.5
130°	688.4	687.9	687.0	686.1	685.2	684.3	685.2	686.1	687.0	687.9	688.4
132.5°	732.1	731.8	731.1	730.4	729.8	729.1	729.8	730.4	731.1	731.8	732.1
135°	779.0	778.7	778.0	777.3	776.6	775.9	776.6	777.3	778.0	778.7	779.0
137.5°	821.7	821.3	820.4	819.5	818.6	817.7	818.6	819.5	820.4	821.3	821.7
140°	865.5	865.1	864.2	863.3	862.4	861.5	862.4	863.3	864.2	865.1	865.5
142.5°	905.2	904.8	903.9	903.0	902.1	901.2	902.1	903.0	903.9	904.8	905.2
145°	945.0	944.5	943.6	942.7	941.8	940.9	941.8	942.7	943.6	944.5	945.0
147.5°	980.6	980.1	979.2	978.3	977.4	976.5	977.4	978.3	979.2	980.1	980.6
150°	1014.2	1013.9	1013.2	1012.5	1011.8	1011.1	1011.8	1012.5	1013.2	1013.9	1014.2
152.5°	1047.8	1047.3	1046.4	1045.5	1044.6	1043.7	1044.6	1045.5	1046.4	1047.3	1047.8
155°	1075.3	1075.0	1074.3	1073.6	1072.9	1072.2	1072.9	1073.6	1074.3	1075.0	1075.3
157.5°	1102.8	1102.2	1101.1	1100.0	1098.8	1097.7	1098.8	1100.0	1101.1	1102.2	1102.8
160°	1125.2	1124.7	1123.8	1122.9	1122.0	1121.1	1122.0	1122.9	1123.8	1124.7	1125.2
162.5°	1146.6	1146.0	1144.9	1143.8	1142.6	1141.5	1142.6	1143.8	1144.9	1146.0	1146.6
165°	1163.9	1163.3	1162.2	1161.1	1159.9	1158.8	1159.9	1161.1	1162.2	1163.3	1163.9
167.5°	1179.2	1178.6	1177.5	1176.4	1175.2	1174.1	1175.2	1176.4	1177.5	1178.6	1179.2
170°	1191.4	1190.7	1189.4	1188.0	1186.7	1185.3	1186.7	1188.0	1189.4	1190.7	1191.4
172.5°	1200.5	1199.8	1198.5	1197.1	1195.8	1194.4	1195.8	1197.1	1198.5	1199.8	1200.5
175°	1206.7	1206.0	1204.6	1203.3	1201.9	1200.5	1201.9	1203.3	1204.6	1206.0	1206.7
177.5°	1209.7	1209.0	1207.7	1206.3	1205.0	1203.6	1205.0	1206.3	1207.7	1209.0	1209.7
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2	570.2
2.5°	541.3	544.8	543.4	538.6	544.3	544.3	548.3	548.3	553.1	554.8	557.5
5°	510.6	513.2	515.4	513.2	517.2	523.3	526.8	529.9	536.4	539.1	543.0
7.5°	477.7	482.5	484.7	484.7	491.3	498.3	505.3	509.7	518.9	522.4	526.4
10°	445.7	451.4	455.8	455.4	466.3	470.7	479.5	489.5	498.7	504.0	509.7
12.5°	412.0	415.0	421.2	429.9	432.6	440.5	450.5	463.2	479.9	484.7	493.0
15°	383.9	392.2	397.1	401.0	407.1	414.6	425.6	437.8	454.5	465.0	473.8
17.5°	360.3	371.2	374.3	373.4	381.3	392.7	405.4	414.6	429.5	442.2	450.5
20°	341.0	345.4	350.6	352.8	358.9	371.2	383.5	394.0	406.3	416.4	426.0
22.5°	321.7	325.2	329.6	333.5	338.3	345.4	357.2	370.3	382.2	391.8	402.8
25°	305.9	308.1	312.0	315.1	320.4	325.2	333.5	348.0	362.0	367.7	377.3
27.5°	290.6	292.3	295.0	298.5	301.1	305.9	313.4	325.2	339.7	345.4	358.5
30°	277.0	278.3	280.9	282.7	284.0	289.7	295.4	304.6	315.6	323.4	333.1
32.5°	264.3	265.6	268.2	268.7	270.4	273.5	278.7	287.1	296.7	303.3	311.6
35°	250.2	251.1	253.8	254.6	255.9	258.6	262.5	268.7	277.4	282.2	289.7
37.5°	239.3	238.9	240.6	241.9	243.7	245.0	246.3	252.4	259.0	263.4	269.1
40°	227.5	226.6	227.0	228.8	229.7	231.4	231.4	237.5	241.9	245.4	249.8
42.5°	215.6	215.2	214.3	215.2	216.1	216.5	216.9	221.3	225.7	228.8	233.6
45°	203.8	203.4	202.5	202.9	202.9	203.8	205.1	206.9	209.9	212.6	215.2
47.5°	192.8	192.0	190.6	190.2	191.1	191.1	191.1	192.8	195.9	196.8	199.4
50°	181.4	180.1	178.4	177.5	177.5	177.1	177.9	178.4	181.0	181.9	184.1
52.5°	169.2	168.3	166.5	164.8	165.2	164.3	164.8	165.2	166.1	167.4	168.7
55°	156.9	155.1	153.8	153.4	152.1	152.1	150.8	152.5	152.1	152.5	154.3
57.5°	145.1	143.3	141.1	140.2	138.9	138.5	137.6	137.2	137.6	138.9	140.2
60°	131.0	130.2	128.9	127.5	126.7	125.3	124.5	124.5	124.0	124.0	124.5
62.5°	117.5	117.0	115.3	114.8	113.9	113.1	111.8	110.9	110.9	111.8	112.2
65°	104.3	103.9	102.6	102.1	99.9	99.0	98.6	98.2	97.3	97.3	97.3
67.5°	92.0	90.7	90.7	88.5	86.8	85.9	85.0	84.6	84.6	84.6	85.0
70°	78.4	78.4	77.1	75.8	74.1	74.5	73.2	71.9	71.9	71.0	71.4
72.5°	65.3	64.9	63.5	63.1	61.8	60.5	59.6	60.5	59.2	58.7	59.2
75°	52.6	52.2	51.3	50.4	50.8	49.5	48.2	47.8	47.8	46.9	46.9
77.5°	40.3	41.2	39.4	39.0	38.1	37.3	36.8	36.4	36.4	36.4	37.3
80°	28.0	28.5	28.5	27.6	28.0	26.7	26.7	26.7	25.4	25.9	26.3
82.5°	18.0	18.0	17.5	18.0	17.5	17.5	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.6	9.2	10.1	9.6	9.6	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	33.8	34.3	34.7	35.2	35.6	30.6	25.6	20.7	15.7	13.2	11.8
92.5°	32.5	32.3	32.0	31.8	31.6	31.4	31.1	30.9	30.6	30.5	29.6
95°	65.2	65.2	65.2	65.2	65.2	64.7	64.3	63.8	63.3	63.1	62.0
97.5°	101.8	101.8	101.8	101.8	101.8	100.9	100.0	99.1	98.2	97.8	96.8
100°	140.5	140.5	140.5	140.5	140.5	139.8	139.2	138.5	137.8	137.5	136.6
102.5°	183.2	183.0	182.7	182.5	182.3	181.4	180.5	179.6	178.7	178.2	177.5
105°	225.9	225.4	224.9	224.5	224.0	223.6	223.1	222.7	222.2	222.0	221.7
107.5°	270.8	270.5	270.3	270.0	269.8	269.8	269.8	269.8	269.8	269.8	269.4
110°	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.7	316.0

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	361.8	362.5	363.2	363.8	364.5	364.7	365.0	365.2	365.5	365.6	364.9
115°	410.5	410.7	411.0	411.2	411.4	411.8	412.3	412.7	413.2	413.4	412.7
117.5°	455.5	456.2	456.9	457.5	458.2	459.3	460.5	461.6	462.7	463.3	462.4
120°	503.0	503.0	503.0	503.0	503.0	504.8	506.6	508.5	510.3	511.2	510.3
122.5°	549.1	549.8	550.5	551.2	551.9	553.0	554.2	555.3	556.4	557.0	555.9
125°	596.0	596.7	597.4	598.0	598.7	599.4	600.1	600.8	601.5	601.8	600.8
127.5°	641.0	641.9	642.8	643.7	644.6	645.5	646.4	647.3	648.2	648.6	647.4
130°	688.6	689.1	689.5	690.0	690.4	690.8	691.3	691.7	692.2	692.4	690.9
132.5°	732.7	733.8	734.9	736.1	737.2	737.0	736.8	736.5	736.3	736.2	735.1
135°	779.1	779.3	779.6	779.8	780.0	779.6	779.1	778.7	778.2	778.0	776.8
137.5°	821.8	822.1	822.3	822.6	822.8	822.3	821.9	821.4	820.9	820.7	819.7
140°	865.5	865.5	865.5	865.5	865.5	864.4	863.2	862.1	861.0	860.4	859.4
142.5°	905.1	904.9	904.6	904.4	904.2	903.5	902.9	902.2	901.5	901.2	900.2
145°	944.9	944.6	944.4	944.1	943.9	942.5	941.2	939.8	938.5	937.8	937.0
147.5°	980.4	979.9	979.5	979.0	978.6	977.7	976.8	975.9	975.0	974.5	973.5
150°	1013.9	1013.2	1012.5	1011.8	1011.1	1010.2	1009.3	1008.4	1007.5	1007.1	1006.4
152.5°	1047.3	1046.4	1045.5	1044.6	1043.7	1042.6	1041.4	1040.3	1039.2	1038.6	1037.9
155°	1074.7	1073.6	1072.5	1071.3	1070.2	1069.5	1068.8	1068.1	1067.4	1067.1	1066.8
157.5°	1102.0	1100.4	1098.9	1097.3	1095.7	1095.2	1094.8	1094.3	1093.8	1093.6	1093.4
160°	1124.5	1123.2	1121.8	1120.5	1119.1	1118.9	1118.7	1118.4	1118.2	1118.1	1117.9
162.5°	1145.8	1144.2	1142.6	1141.0	1139.4	1139.2	1139.0	1138.7	1138.5	1138.4	1138.4
165°	1163.1	1161.5	1160.0	1158.4	1156.8	1156.8	1156.8	1156.8	1156.8	1156.8	1156.9
167.5°	1178.4	1176.8	1175.2	1173.6	1172.0	1172.0	1172.0	1172.0	1172.0	1172.0	1172.3
170°	1190.6	1189.0	1187.4	1185.8	1184.2	1184.4	1184.7	1184.9	1185.2	1185.3	1185.6
172.5°	1199.7	1198.1	1196.6	1195.0	1193.4	1193.6	1193.8	1194.1	1194.3	1194.4	1194.7
175°	1205.9	1204.3	1202.7	1201.1	1199.5	1200.0	1200.4	1200.9	1201.4	1201.6	1201.9
177.5°	1209.0	1207.7	1206.3	1205.0	1203.6	1204.0	1204.5	1204.9	1205.4	1205.6	1205.9
180°	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7	1206.7

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	570.2	570.2	570.2	570.2
2.5°	559.7	559.7	566.2	573.3
5°	547.4	550.5	561.0	570.6
7.5°	535.6	540.8	554.0	566.2
10°	521.1	528.1	544.3	558.8
12.5°	507.1	513.6	532.5	548.7
15°	487.4	495.7	515.8	536.0
17.5°	467.6	476.0	500.5	524.2
20°	444.4	455.4	483.0	514.5
22.5°	422.9	436.5	467.2	492.6
25°	399.3	420.3	448.8	481.7
27.5°	378.2	399.3	428.2	461.5
30°	354.6	376.0	405.8	436.5
32.5°	331.8	351.5	380.4	418.1
35°	308.1	326.9	355.0	393.1
37.5°	286.6	305.0	335.7	370.8
40°	265.6	284.9	311.2	346.2
42.5°	245.9	263.0	286.6	321.7
45°	227.9	240.2	262.1	295.0
47.5°	209.1	220.0	240.2	273.0
50°	191.5	200.7	218.3	248.9
52.5°	174.4	182.3	198.5	223.1
55°	159.1	166.5	178.4	202.5
57.5°	143.3	149.0	160.4	179.7
60°	128.0	133.2	142.4	158.2
62.5°	112.6	117.0	125.8	138.5
65°	99.0	102.6	109.1	120.1
67.5°	85.9	88.1	93.4	102.1
70°	73.2	74.9	79.3	86.3
72.5°	59.6	61.4	66.2	71.0
75°	48.2	48.6	52.2	56.1
77.5°	37.7	37.3	39.9	43.0
80°	25.9	27.2	29.4	30.7
82.5°	17.5	18.0	18.8	19.7
85°	9.6	10.1	10.1	11.4
87.5°	3.9	4.4	4.4	4.8
90°	9.1	6.4	3.7	1.0
92.5°	27.8	26.0	24.2	22.4
95°	59.7	57.5	55.2	53.0
97.5°	94.7	92.7	90.6	88.6
100°	134.8	132.9	131.1	129.3
102.5°	176.2	174.8	173.5	172.1
105°	221.0	220.3	219.6	218.9
107.5°	268.5	267.6	266.7	265.8
110°	314.7	313.3	312.0	310.6

TEST NUMBER: P1029421

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	363.5	362.2	360.8	359.4
115°	411.4	410.0	408.7	407.3
117.5°	460.6	458.8	457.0	455.2
120°	508.5	506.6	504.8	503.0
122.5°	553.6	551.3	549.1	546.8
125°	598.7	596.7	594.6	592.6
127.5°	644.9	642.4	639.9	637.4
130°	688.0	685.1	682.1	679.2
132.5°	732.8	730.5	728.3	726.0
135°	774.3	771.8	769.3	766.8
137.5°	817.7	815.6	813.6	811.6
140°	857.4	855.3	853.3	851.3
142.5°	898.1	896.1	894.0	892.0
145°	935.4	933.9	932.3	930.7
147.5°	971.4	969.4	967.3	965.3
150°	1005.1	1003.7	1002.4	1001.0
152.5°	1036.6	1035.2	1033.9	1032.5
155°	1066.1	1065.4	1064.8	1064.1
157.5°	1092.9	1092.5	1092.0	1091.6
160°	1117.4	1116.9	1116.5	1116.0
162.5°	1138.4	1138.4	1138.4	1138.4
165°	1157.1	1157.4	1157.6	1157.8
167.5°	1173.0	1173.7	1174.4	1175.1
170°	1186.3	1187.0	1187.6	1188.3
172.5°	1195.4	1196.1	1196.8	1197.5
175°	1202.6	1203.3	1203.9	1204.6
177.5°	1206.6	1207.3	1208.0	1208.7
180°	1206.7	1206.7	1206.7	1206.7

(END OF REPORT)