

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029424

Luminaire Tested: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029424
REPORT IS A COMBINATION OF REPORTS P985840 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K
Description: Define 2 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4649.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	102	102	102	102		91	91	91	91		71	71	71		52	52	52		35	35	35
1	93	89	85	82		83	80	77	74		62	60	58		46	45	44		31	31	30
2	85	78	72	67		76	70	65	61		55	51	49		41	39	37		28	27	26
3	77	69	62	56		69	62	56	51		48	44	41		36	34	31		25	24	22
4	71	61	53	48		63	55	48	43		43	39	35		32	30	27		23	21	19
5	65	54	46	41		58	49	42	37		39	34	30		29	26	24		20	18	17
6	60	48	41	35		53	44	37	32		35	30	26		26	23	21		19	17	15
7	55	44	36	31		49	40	33	28		32	27	23		24	21	18		17	15	13
8	51	40	32	27		46	36	29	25		29	24	21		22	19	16		16	14	12
9	48	36	29	24		43	33	26	22		26	22	18		20	17	15		14	12	11
10	44	33	26	22		40	30	24	20		24	20	17		19	15	13		13	11	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9054	9054	9054	9054
5°	9075	9654	9110	7680
10°	8971	10539	9027	6332
15°	8753	11116	8875	5334
20°	8617	10438	8617	4636
25°	8342	8967	8380	4146
30°	7890	7049	8041	3755
35°	7490	4874	7616	3435
40°	7029	3680	7110	3181
45°	6462	3025	6567	2906
50°	5971	2654	5983	2661
55°	5412	2262	5446	2394
60°	4816	1890	4882	2089
65°	4284	1537	4362	1784
70°	3750	1205	3846	1438
75°	3149	875	3273	1043
80°	2459	555	2635	620
85°	1610	280	1737	207

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 9360 cd/sqm

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	1.2
10°-20°	158.6	3.4
20°-30°	230.1	5.0
30°-40°	242.6	5.2
40°-50°	214.7	4.6
50°-60°	171.4	3.7
60°-70°	116.4	2.5
70°-80°	59.6	1.3
80°-90°	17.5	0.4
90°-100°	74.9	1.6
100°-110°	238.0	5.1
110°-120°	407.2	8.8
120°-130°	535.6	11.5
130°-140°	601.2	12.9
140°-150°	589.5	12.7
150°-160°	494.5	10.6
160°-170°	328.0	7.1
170°-180°	114.6	2.5
0°-30°	443.2	9.5
0°-40°	685.8	14.8
0°-60°	1071.9	23.1
0°-90°	1265.5	27.2
90°-120°	720.1	15.5
90°-150°	2446.4	52.6
90°-180°	3384.0	72.8
0°-180°	4649.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	572	572	572	572	572	
5°	572	639	575	508	572	54
15°	538	785	545	377	538	152
25°	483	654	485	302	483	221
35°	394	356	401	251	394	247
45°	296	215	301	206	296	230
55°	203	151	204	160	203	181
65°	120	93	123	108	120	120
75°	56	46	58	54	56	60
85°	11	12	12	9	11	13
90°	1	35	1	35	1	4
95°	53	63	53	63	53	59
105°	220	227	220	227	220	232
115°	408	408	408	408	408	404
125°	594	596	594	596	594	531
135°	769	778	769	778	769	594
145°	934	944	934	944	934	583
155°	1067	1075	1067	1075	1067	491
165°	1161	1162	1161	1162	1161	328
175°	1208	1204	1208	1204	1208	115
180°	1210	1210	1210	1210	1210	

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	575.1	576.4	578.6	579.0	583.4	586.9	590.9	590.9	592.2	591.8	588.3
5°	572.4	576.4	582.1	586.9	594.9	598.4	603.7	607.6	611.1	613.8	613.3
7.5°	568.0	575.1	583.4	592.7	603.2	609.4	616.8	623.9	628.7	633.1	636.2
10°	560.6	572.4	583.9	596.2	609.8	618.2	627.0	636.2	643.7	652.0	659.9
12.5°	550.5	567.6	581.7	597.9	614.6	623.9	637.9	645.0	659.5	680.6	686.3
15°	537.7	561.0	574.2	594.9	616.8	624.3	643.7	655.1	685.0	698.2	714.0
17.5°	525.8	551.8	569.4	593.1	614.6	629.2	648.1	671.4	696.4	715.3	732.9
20°	516.2	541.2	562.3	588.7	616.0	634.4	654.2	682.4	709.6	729.0	742.6
22.5°	494.2	526.3	550.9	580.4	613.3	638.8	657.7	688.5	718.0	729.8	741.7
25°	483.2	510.9	539.5	572.9	611.6	641.9	658.2	692.5	718.4	722.8	725.4
27.5°	463.0	494.2	527.6	565.8	611.1	636.6	657.3	688.5	709.2	706.1	698.2
30°	437.9	476.2	513.1	554.4	605.0	632.7	652.0	680.6	691.1	675.3	661.2
32.5°	419.4	455.5	496.4	544.3	597.9	624.3	643.2	665.6	667.8	639.3	615.5
35°	394.4	434.4	480.5	531.1	586.1	609.8	627.4	641.0	630.5	590.5	562.3
37.5°	372.0	411.5	460.8	512.2	569.8	593.1	607.2	609.4	583.4	548.3	506.9
40°	347.3	388.2	439.7	493.7	551.8	572.0	580.8	574.2	536.8	495.9	448.0
42.5°	322.7	363.2	418.6	474.0	528.9	546.1	549.6	531.5	485.8	437.9	382.5
45°	295.9	338.1	393.5	449.3	502.5	512.2	512.6	486.7	432.6	382.5	331.1
47.5°	273.9	313.0	368.0	423.8	468.7	475.3	472.6	442.7	383.8	327.5	282.7
50°	249.7	287.1	341.6	396.6	434.8	436.6	430.0	387.3	329.7	278.3	242.7
52.5°	223.8	261.6	311.7	364.5	398.8	396.1	383.4	337.7	283.6	240.9	213.7
55°	203.1	236.5	283.6	335.0	359.2	351.7	337.7	291.1	248.4	212.4	188.6
57.5°	180.3	209.7	255.9	300.7	314.8	307.8	293.7	250.2	210.6	183.3	167.5
60°	158.7	185.5	226.0	263.4	274.3	266.9	250.6	211.5	182.9	160.0	148.2
62.5°	138.9	162.2	196.1	230.4	234.8	227.3	213.2	181.6	157.0	138.9	130.1
65°	120.5	142.4	169.7	195.6	199.6	191.7	177.2	154.3	133.7	122.2	113.9
67.5°	102.4	120.0	144.2	163.1	165.3	157.8	146.0	127.5	114.8	102.4	96.3
70°	86.6	99.8	118.7	134.1	135.0	127.9	121.8	105.1	95.4	86.6	81.8
72.5°	71.2	80.5	95.0	106.4	106.8	102.4	96.7	86.2	77.8	71.7	66.8
75°	56.3	64.2	73.0	83.1	82.7	79.1	74.7	68.1	61.1	57.2	55.0
77.5°	43.1	47.9	55.0	61.6	61.6	59.8	57.2	52.3	47.9	44.0	41.8
80°	30.8	33.9	39.6	41.8	42.6	42.2	40.0	36.5	34.7	31.7	30.8
82.5°	19.8	22.0	24.6	26.8	28.1	27.3	26.8	25.1	22.4	21.5	20.7
85°	11.4	12.3	13.6	14.9	15.4	14.9	15.8	14.5	13.2	13.2	12.8
87.5°	4.8	5.3	6.2	6.2	6.6	6.6	6.2	6.6	6.6	6.2	5.7
90°	1.0	3.7	6.5	9.2	11.9	13.3	15.8	20.8	25.7	30.7	35.7
92.5°	22.5	24.3	26.1	27.9	29.7	30.6	30.7	31.0	31.2	31.5	31.7
95°	53.1	55.4	57.6	59.9	62.2	63.3	63.5	64.0	64.5	64.9	65.4
97.5°	88.9	90.9	92.9	95.0	97.0	98.0	98.5	99.4	100.3	101.2	102.1
100°	129.7	131.5	133.3	135.2	137.0	137.9	138.2	138.9	139.6	140.2	140.9
102.5°	172.6	174.0	175.3	176.7	178.0	178.7	179.2	180.1	181.0	181.9	182.8
105°	219.6	220.3	220.9	221.6	222.3	222.6	222.8	223.3	223.8	224.2	224.7
107.5°	266.6	267.5	268.4	269.3	270.2	270.6	270.6	270.6	270.6	270.6	270.6
110°	311.5	312.9	314.2	315.6	316.9	317.6	317.6	317.6	317.6	317.6	317.6

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	360.5	361.9	363.2	364.6	365.9	366.6	366.5	366.3	366.0	365.8	365.6
115°	408.5	409.9	411.2	412.6	413.9	414.6	414.4	413.9	413.5	413.0	412.6
117.5°	456.5	458.3	460.1	462.0	463.8	464.7	464.1	463.0	461.9	460.7	459.6
120°	504.5	506.3	508.1	510.0	511.8	512.7	511.8	510.0	508.1	506.3	504.5
122.5°	548.4	550.7	552.9	555.2	557.5	558.6	558.0	556.9	555.8	554.6	553.5
125°	594.4	596.4	598.5	600.5	602.6	603.6	603.3	602.6	601.9	601.2	600.5
127.5°	639.3	641.8	644.3	646.8	649.3	650.6	650.1	649.2	648.3	647.4	646.5
130°	681.2	684.2	687.1	690.1	693.0	694.5	694.3	693.8	693.3	692.9	692.4
132.5°	728.2	730.5	732.7	735.0	737.3	738.4	738.5	738.7	739.0	739.2	739.4
135°	769.0	771.5	774.0	776.5	779.0	780.3	780.5	781.0	781.4	781.9	782.3
137.5°	814.0	816.0	818.1	820.1	822.2	823.2	823.4	823.9	824.3	824.8	825.2
140°	853.8	855.8	857.9	859.9	862.0	863.0	863.6	864.7	865.8	867.0	868.1
142.5°	894.6	896.6	898.7	900.7	902.8	903.8	904.1	904.8	905.5	906.2	906.9
145°	933.5	935.1	936.7	938.2	939.8	940.6	941.3	942.6	944.0	945.3	946.7
147.5°	968.2	970.2	972.3	974.3	976.4	977.4	977.9	978.8	979.7	980.6	981.5
150°	1003.9	1005.3	1006.7	1008.0	1009.4	1010.1	1010.5	1011.4	1012.3	1013.2	1014.1
152.5°	1035.6	1037.0	1038.3	1039.7	1041.0	1041.7	1042.3	1043.4	1044.5	1045.7	1046.8
155°	1067.2	1067.9	1068.6	1069.3	1070.0	1070.3	1070.6	1071.3	1072.0	1072.7	1073.4
157.5°	1094.8	1095.3	1095.7	1096.2	1096.7	1096.9	1097.1	1097.6	1098.0	1098.5	1098.9
160°	1119.3	1119.8	1120.2	1120.7	1121.2	1121.4	1121.5	1121.7	1122.0	1122.2	1122.4
162.5°	1141.8	1141.8	1141.8	1141.8	1141.8	1141.8	1141.9	1142.1	1142.4	1142.6	1142.8
165°	1161.2	1161.0	1160.8	1160.5	1160.3	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2
167.5°	1178.6	1177.9	1177.2	1176.5	1175.8	1175.5	1175.5	1175.5	1175.5	1175.5	1175.5
170°	1191.8	1191.1	1190.5	1189.8	1189.1	1188.8	1188.7	1188.5	1188.2	1188.0	1187.8
172.5°	1201.0	1200.3	1199.7	1199.0	1198.3	1198.0	1197.9	1197.6	1197.4	1197.1	1196.9
175°	1208.2	1207.5	1206.8	1206.1	1205.4	1205.1	1204.9	1204.4	1204.0	1203.5	1203.1
177.5°	1212.3	1211.6	1210.9	1210.2	1209.5	1209.2	1209.0	1208.5	1208.1	1207.6	1207.2
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	594.4	594.9	595.7	600.1	602.3	602.8	601.0	605.0	606.3	605.0	604.1
5°	622.6	625.2	630.5	636.2	635.7	636.2	638.8	641.5	642.3	638.8	640.1
7.5°	647.2	652.5	658.2	667.0	667.0	671.4	673.1	675.3	680.6	678.0	677.1
10°	675.3	682.4	692.9	707.0	707.4	711.8	716.2	723.2	725.4	723.7	724.6
12.5°	710.5	724.1	725.0	740.4	747.4	748.3	755.3	754.0	758.4	758.4	765.9
15°	725.9	747.0	758.9	773.8	778.2	772.9	778.6	784.8	785.2	785.2	784.8
17.5°	753.6	761.9	773.8	781.7	783.5	783.5	783.9	786.6	784.8	781.3	783.9
20°	759.3	762.8	767.2	766.3	767.2	762.8	758.4	754.0	754.5	752.3	758.9
22.5°	748.7	747.9	737.7	731.2	731.2	722.4	714.0	710.1	706.1	707.4	709.6
25°	722.4	708.7	696.4	686.7	684.6	670.5	659.0	655.5	648.9	654.2	655.1
27.5°	680.2	664.8	645.0	636.6	625.2	619.5	611.6	601.0	587.4	595.3	594.0
30°	634.9	612.0	595.7	575.5	557.5	556.2	541.2	523.6	516.6	516.6	520.6
32.5°	584.3	554.0	530.2	501.7	484.1	476.6	458.6	441.0	444.9	431.7	436.6
35°	525.4	485.4	455.5	427.8	414.6	405.8	382.5	372.8	362.3	356.1	367.6
37.5°	469.1	423.0	384.7	354.4	349.5	333.7	317.9	311.7	305.6	308.2	307.8
40°	400.5	359.6	325.3	301.6	293.3	285.8	275.2	267.8	263.8	266.0	266.4
42.5°	338.5	304.2	278.7	262.0	255.0	249.7	244.5	238.3	237.0	237.0	238.7
45°	290.6	262.5	245.3	231.7	227.7	223.8	219.8	217.2	216.3	214.6	215.9
47.5°	252.4	229.9	219.4	209.3	204.9	204.0	200.5	199.2	197.4	197.0	197.4
50°	220.3	206.2	196.5	190.8	187.7	186.4	184.7	182.0	181.1	183.3	182.5
52.5°	197.8	184.7	179.4	173.7	171.9	170.1	167.5	167.9	167.5	166.6	166.6
55°	175.4	167.1	161.8	157.4	157.0	155.2	153.0	152.1	151.7	150.8	152.1
57.5°	157.4	150.8	146.0	142.0	140.3	140.3	138.1	136.3	136.3	135.9	136.3
60°	139.4	132.8	129.7	125.7	124.4	124.0	122.7	121.8	120.5	120.5	120.5
62.5°	122.7	117.4	113.9	110.4	110.8	108.6	106.8	106.0	106.0	106.4	106.4
65°	106.8	103.3	98.9	95.8	95.0	94.5	93.6	93.2	91.9	92.8	92.8
67.5°	92.3	87.5	84.9	83.5	82.2	81.8	80.9	80.0	79.6	79.1	80.0
70°	77.8	73.9	71.7	70.8	69.5	69.0	68.6	67.3	67.7	68.1	68.6
72.5°	64.6	61.1	60.7	58.0	58.0	58.0	56.3	57.2	56.7	55.8	56.7
75°	51.0	49.2	48.4	47.0	47.5	47.0	46.6	45.3	45.3	45.7	46.2
77.5°	40.4	38.7	38.3	36.9	36.1	36.9	36.1	35.6	35.6	36.1	36.1
80°	29.9	29.0	27.7	27.7	27.7	27.3	27.3	27.3	26.8	26.4	26.8
82.5°	19.8	19.8	19.3	18.9	19.3	18.5	18.9	18.9	18.9	18.9	18.9
85°	12.8	12.3	12.3	11.9	11.9	11.9	12.3	11.4	11.4	11.9	11.9
87.5°	5.7	5.7	5.7	6.2	5.7	5.7	5.7	6.2	5.7	5.7	5.7
90°	35.3	34.8	34.4	33.9	33.7	33.8	34.0	34.3	34.5	34.7	34.5
92.5°	31.9	32.1	32.4	32.6	32.7	32.7	32.7	32.7	32.7	32.7	32.7
95°	65.4	65.4	65.4	65.4	65.4	65.2	64.7	64.2	63.8	63.3	63.8
97.5°	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1
100°	140.9	140.9	140.9	140.9	140.9	140.8	140.6	140.3	140.1	139.9	140.1
102.5°	183.0	183.2	183.5	183.7	183.8	183.7	183.5	183.2	183.0	182.8	183.0
105°	225.1	225.6	226.0	226.5	226.7	226.7	226.7	226.7	226.7	226.7	226.7
107.5°	270.8	271.1	271.3	271.6	271.7	271.1	270.0	268.9	267.7	266.6	267.7
110°	317.6	317.6	317.6	317.6	317.6	317.3	316.6	315.9	315.3	314.6	315.3

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	364.9	364.3	363.6	362.9	362.6	362.4	361.9	361.4	361.0	360.5	361.0
115°	412.4	412.2	411.9	411.7	411.6	411.3	410.6	409.9	409.2	408.5	409.2
117.5°	458.9	458.2	457.5	456.8	456.5	456.2	455.5	454.8	454.2	453.5	454.2
120°	504.5	504.5	504.5	504.5	504.5	504.2	503.5	502.8	502.2	501.5	502.2
122.5°	552.8	552.2	551.5	550.8	550.5	550.3	549.8	549.3	548.9	548.4	548.9
125°	599.8	599.2	598.5	597.8	597.5	597.4	597.1	596.9	596.6	596.4	596.6
127.5°	645.6	644.7	643.8	642.9	642.4	642.1	641.4	640.7	640.0	639.3	640.0
130°	692.0	691.5	691.1	690.6	690.4	689.9	689.0	688.1	687.2	686.3	687.2
132.5°	738.3	737.1	736.0	734.9	734.3	734.0	733.3	732.6	731.9	731.2	731.9
135°	782.1	781.9	781.6	781.4	781.3	781.0	780.3	779.6	778.9	778.2	778.9
137.5°	825.0	824.8	824.5	824.3	824.2	823.7	822.8	821.9	821.0	820.1	821.0
140°	868.1	868.1	868.1	868.1	868.1	867.6	866.7	865.8	864.9	864.0	864.9
142.5°	907.1	907.3	907.6	907.8	907.9	907.4	906.5	905.6	904.7	903.8	904.7
145°	946.9	947.2	947.4	947.7	947.8	947.3	946.4	945.5	944.6	943.7	944.6
147.5°	981.9	982.4	982.8	983.3	983.5	983.0	982.1	981.2	980.3	979.4	980.3
150°	1014.8	1015.5	1016.2	1016.9	1017.2	1016.9	1016.2	1015.5	1014.8	1014.1	1014.8
152.5°	1047.7	1048.6	1049.5	1050.4	1050.9	1050.4	1049.5	1048.6	1047.7	1046.8	1047.7
155°	1074.5	1075.7	1076.8	1077.9	1078.5	1078.2	1077.5	1076.8	1076.1	1075.4	1076.1
157.5°	1100.5	1102.1	1103.7	1105.3	1106.1	1105.5	1104.4	1103.2	1102.1	1100.9	1102.1
160°	1123.8	1125.1	1126.5	1127.8	1128.5	1128.0	1127.1	1126.2	1125.3	1124.4	1125.3
162.5°	1144.4	1146.0	1147.6	1149.2	1150.0	1149.4	1148.3	1147.2	1146.0	1144.9	1146.0
165°	1161.8	1163.4	1164.9	1166.5	1167.3	1166.7	1165.6	1164.5	1163.3	1162.2	1163.3
167.5°	1177.1	1178.7	1180.2	1181.8	1182.6	1182.0	1180.9	1179.8	1178.6	1177.5	1178.6
170°	1189.4	1191.0	1192.5	1194.1	1194.9	1194.2	1192.9	1191.5	1190.2	1188.8	1190.2
172.5°	1198.5	1200.1	1201.7	1203.3	1204.1	1203.4	1202.1	1200.7	1199.4	1198.0	1199.4
175°	1204.7	1206.3	1207.8	1209.4	1210.2	1209.5	1208.2	1206.8	1205.5	1204.1	1205.5
177.5°	1208.6	1209.9	1211.3	1212.6	1213.3	1212.6	1211.3	1209.9	1208.6	1207.2	1208.6
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	606.3	603.2	600.6	601.0	603.2	601.5	597.1	591.3	589.1	586.5	589.1
5°	642.8	640.1	634.9	635.3	634.0	632.2	625.2	616.4	616.4	609.4	608.5
7.5°	678.8	674.9	671.4	670.5	665.6	662.1	656.0	643.7	638.8	630.5	625.6
10°	719.3	716.2	712.2	707.4	704.8	698.6	688.5	670.5	661.7	650.3	641.9
12.5°	760.2	759.7	750.9	741.3	740.8	731.2	724.1	699.9	688.1	672.7	652.9
15°	786.1	783.9	779.1	774.2	775.6	765.0	749.2	720.6	712.7	694.2	673.1
17.5°	785.7	785.7	784.4	783.5	782.2	779.1	770.3	751.4	738.6	715.3	695.5
20°	760.6	766.3	767.6	767.2	771.6	773.8	773.4	761.5	751.4	730.7	710.5
22.5°	710.5	723.7	729.4	732.9	742.1	747.0	758.4	754.0	751.4	736.0	718.8
25°	663.9	668.3	685.4	686.3	699.1	710.9	722.4	729.8	739.5	733.8	719.3
27.5°	603.7	613.8	626.1	635.3	637.9	662.1	681.0	695.1	717.1	718.8	714.0
30°	535.5	540.3	560.6	572.9	586.9	604.5	631.8	656.0	675.8	693.8	699.9
32.5°	452.4	472.2	484.1	499.0	511.3	542.5	576.0	607.2	630.0	660.4	673.6
35°	376.3	391.7	412.0	418.1	440.5	466.9	510.4	550.5	585.2	616.0	642.8
37.5°	313.5	325.8	347.3	357.0	370.2	404.0	440.5	490.2	532.0	569.8	603.2
40°	270.4	279.6	295.9	299.0	310.0	340.7	370.2	416.8	472.2	523.2	559.7
42.5°	240.9	245.3	256.3	260.3	267.3	288.0	314.4	358.3	409.8	462.5	514.0
45°	219.8	222.9	229.5	233.0	241.8	251.0	272.6	307.8	348.2	401.4	456.8
47.5°	200.9	204.9	207.5	209.7	214.6	224.7	238.7	264.7	303.4	352.2	405.8
50°	185.1	186.4	191.3	191.7	194.8	201.4	214.6	230.4	261.2	300.7	352.6
52.5°	169.3	170.6	173.7	176.7	178.1	183.3	192.1	205.3	228.2	259.4	305.6
55°	153.4	155.2	158.3	160.5	161.8	166.2	171.5	184.2	202.2	224.2	262.0
57.5°	137.6	141.6	142.4	143.8	146.0	150.8	155.6	163.1	177.2	197.4	225.1
60°	122.7	124.0	127.1	128.4	130.6	133.2	139.4	145.1	155.2	171.0	196.1
62.5°	107.3	110.4	111.7	113.0	114.8	117.8	121.8	127.9	136.7	149.5	169.3
65°	94.1	94.5	97.2	98.9	100.7	102.9	106.8	112.6	117.8	129.7	144.2
67.5°	81.3	82.2	83.1	84.9	87.1	89.3	92.8	95.8	102.4	110.4	121.8
70°	69.0	69.0	71.2	72.5	72.1	74.7	77.4	80.9	85.7	93.2	102.4
72.5°	58.0	57.6	59.4	59.8	60.7	62.4	64.2	67.7	70.3	76.1	83.1
75°	46.2	47.0	47.9	47.9	49.2	50.6	52.3	54.1	57.2	60.7	65.9
77.5°	36.5	36.5	37.4	37.8	39.1	38.7	40.4	42.2	44.4	47.5	51.4
80°	26.8	27.7	27.7	27.7	28.1	28.6	30.3	31.7	33.0	35.2	36.9
82.5°	18.9	18.9	19.8	19.8	19.8	20.7	20.7	21.1	22.0	23.3	24.6
85°	11.9	11.9	11.9	12.3	11.9	12.3	13.2	12.8	13.2	14.1	14.1
87.5°	5.7	5.7	5.7	5.7	5.7	6.2	5.7	6.2	6.6	6.6	6.6
90°	34.3	34.0	33.8	33.7	33.9	34.4	34.8	35.3	35.7	30.7	25.7
92.5°	32.7	32.7	32.7	32.7	32.6	32.4	32.1	31.9	31.7	31.5	31.2
95°	64.2	64.7	65.2	65.4	65.4	65.4	65.4	65.4	65.4	64.9	64.5
97.5°	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	101.2	100.3
100°	140.3	140.6	140.8	140.9	140.9	140.9	140.9	140.9	140.9	140.2	139.6
102.5°	183.2	183.5	183.7	183.8	183.7	183.5	183.2	183.0	182.8	181.9	181.0
105°	226.7	226.7	226.7	226.7	226.5	226.0	225.6	225.1	224.7	224.2	223.8
107.5°	268.9	270.0	271.1	271.7	271.6	271.3	271.1	270.8	270.6	270.6	270.6
110°	315.9	316.6	317.3	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	361.4	361.9	362.4	362.6	362.9	363.6	364.3	364.9	365.6	365.8	366.0
115°	409.9	410.6	411.3	411.6	411.7	411.9	412.2	412.4	412.6	413.0	413.5
117.5°	454.8	455.5	456.2	456.5	456.8	457.5	458.2	458.9	459.6	460.7	461.9
120°	502.8	503.5	504.2	504.5	504.5	504.5	504.5	504.5	504.5	506.3	508.1
122.5°	549.3	549.8	550.3	550.5	550.8	551.5	552.2	552.8	553.5	554.6	555.8
125°	596.9	597.1	597.4	597.5	597.8	598.5	599.2	599.8	600.5	601.2	601.9
127.5°	640.7	641.4	642.1	642.4	642.9	643.8	644.7	645.6	646.5	647.4	648.3
130°	688.1	689.0	689.9	690.4	690.6	691.1	691.5	692.0	692.4	692.9	693.3
132.5°	732.6	733.3	734.0	734.3	734.9	736.0	737.1	738.3	739.4	739.2	739.0
135°	779.6	780.3	781.0	781.3	781.4	781.6	781.9	782.1	782.3	781.9	781.4
137.5°	821.9	822.8	823.7	824.2	824.3	824.5	824.8	825.0	825.2	824.8	824.3
140°	865.8	866.7	867.6	868.1	868.1	868.1	868.1	868.1	868.1	867.0	865.8
142.5°	905.6	906.5	907.4	907.9	907.8	907.6	907.3	907.1	906.9	906.2	905.5
145°	945.5	946.4	947.3	947.8	947.7	947.4	947.2	946.9	946.7	945.3	944.0
147.5°	981.2	982.1	983.0	983.5	983.3	982.8	982.4	981.9	981.5	980.6	979.7
150°	1015.5	1016.2	1016.9	1017.2	1016.9	1016.2	1015.5	1014.8	1014.1	1013.2	1012.3
152.5°	1048.6	1049.5	1050.4	1050.9	1050.4	1049.5	1048.6	1047.7	1046.8	1045.7	1044.5
155°	1076.8	1077.5	1078.2	1078.5	1077.9	1076.8	1075.7	1074.5	1073.4	1072.7	1072.0
157.5°	1103.2	1104.4	1105.5	1106.1	1105.3	1103.7	1102.1	1100.5	1098.9	1098.5	1098.0
160°	1126.2	1127.1	1128.0	1128.5	1127.8	1126.5	1125.1	1123.8	1122.4	1122.2	1122.0
162.5°	1147.2	1148.3	1149.4	1150.0	1149.2	1147.6	1146.0	1144.4	1142.8	1142.6	1142.4
165°	1164.5	1165.6	1166.7	1167.3	1166.5	1164.9	1163.4	1161.8	1160.2	1160.2	1160.2
167.5°	1179.8	1180.9	1182.0	1182.6	1181.8	1180.2	1178.7	1177.1	1175.5	1175.5	1175.5
170°	1191.5	1192.9	1194.2	1194.9	1194.1	1192.5	1191.0	1189.4	1187.8	1188.0	1188.2
172.5°	1200.7	1202.1	1203.4	1204.1	1203.3	1201.7	1200.1	1198.5	1196.9	1197.1	1197.4
175°	1206.8	1208.2	1209.5	1210.2	1209.4	1207.8	1206.3	1204.7	1203.1	1203.5	1204.0
177.5°	1209.9	1211.3	1212.6	1213.3	1212.6	1211.3	1209.9	1208.6	1207.2	1207.6	1208.1
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	586.9	584.7	583.4	584.3	581.7	575.1	575.1	577.3	574.6	572.0	568.0
5°	603.2	598.8	596.2	595.7	589.6	579.0	576.8	574.6	568.9	562.8	556.2
7.5°	619.0	611.1	606.7	603.7	594.9	581.2	575.5	570.7	561.4	552.2	543.9
10°	632.2	620.8	615.5	610.7	599.3	582.1	572.9	564.1	552.2	540.3	529.8
12.5°	642.8	629.6	623.0	616.0	601.9	579.5	568.0	554.0	542.1	526.3	515.7
15°	660.4	633.1	627.0	620.4	605.9	575.1	561.0	545.2	528.9	507.8	496.4
17.5°	674.4	637.9	637.5	623.4	604.5	573.3	551.8	531.1	513.5	492.4	474.4
20°	682.8	645.4	638.4	623.9	600.1	561.4	539.0	516.2	497.3	471.8	453.7
22.5°	689.8	656.0	637.5	619.9	590.9	557.5	524.5	503.0	477.0	449.3	432.2
25°	692.5	658.2	638.8	618.6	584.3	546.1	508.7	485.4	456.4	431.3	408.0
27.5°	692.9	657.7	634.0	612.9	575.1	531.1	492.9	468.2	436.1	407.1	383.8
30°	688.5	652.9	631.4	608.5	566.3	517.5	473.5	446.3	412.0	382.9	358.8
32.5°	675.3	643.2	625.6	600.6	554.9	498.6	455.0	424.7	388.7	360.1	336.8
35°	653.3	631.4	612.0	588.7	539.9	481.0	436.6	401.0	364.5	337.2	315.2
37.5°	626.1	614.2	596.2	573.3	522.8	465.2	415.9	376.3	339.9	313.5	291.9
40°	589.1	592.2	574.6	554.0	502.5	443.6	389.1	351.3	317.0	292.4	271.3
42.5°	549.1	561.9	551.8	532.0	480.1	419.9	369.3	327.5	294.1	268.6	251.0
45°	506.0	528.0	521.9	507.4	456.8	394.8	341.2	300.7	271.3	246.6	231.3
47.5°	459.0	490.2	490.2	479.7	430.9	369.8	317.0	275.7	246.6	229.1	214.1
50°	411.1	446.3	452.0	444.9	401.8	341.2	287.5	250.2	225.1	208.0	197.0
52.5°	361.0	401.8	412.4	408.9	371.1	313.9	263.4	226.9	204.0	189.1	179.4
55°	313.0	360.5	372.0	373.3	338.1	284.0	236.5	204.4	182.5	172.3	164.0
57.5°	267.8	313.5	326.2	328.4	304.7	256.8	211.5	183.3	163.6	155.2	148.6
60°	229.1	267.3	284.0	288.9	268.2	225.1	188.2	160.9	146.0	138.1	131.9
62.5°	197.4	228.2	245.8	247.1	237.9	197.4	164.0	141.1	128.4	121.3	118.3
65°	166.6	194.3	204.9	210.2	202.7	171.0	141.6	122.7	112.6	106.4	103.3
67.5°	142.0	159.6	168.4	175.4	167.9	144.2	120.5	105.1	97.6	91.4	89.7
70°	116.5	131.0	137.6	144.6	138.1	120.0	102.9	88.8	82.2	77.4	75.2
72.5°	93.2	104.6	110.8	115.2	111.2	96.3	82.2	72.5	67.7	64.2	62.9
75°	73.9	81.8	85.3	88.4	86.6	75.2	66.4	58.5	54.1	51.0	50.1
77.5°	56.3	62.0	65.9	66.8	64.6	57.2	49.7	44.8	41.3	39.6	38.7
80°	40.0	43.5	45.7	47.0	44.8	41.8	36.5	33.0	29.9	27.7	27.3
82.5°	26.8	28.6	30.3	29.9	29.0	26.4	23.3	21.5	20.2	18.5	18.5
85°	15.4	15.8	16.7	17.1	16.7	14.9	13.2	12.3	11.4	10.1	10.1
87.5°	6.6	7.0	7.0	7.5	6.6	6.6	5.7	4.8	4.8	4.4	4.0
90°	20.8	15.8	13.3	11.9	9.2	6.5	3.7	1.0	3.7	6.5	9.2
92.5°	31.0	30.7	30.6	29.7	27.9	26.1	24.3	22.5	24.3	26.1	27.9
95°	64.0	63.5	63.3	62.2	59.9	57.6	55.4	53.1	55.4	57.6	59.9
97.5°	99.4	98.5	98.0	97.0	95.0	92.9	90.9	88.9	90.9	92.9	95.0
100°	138.9	138.2	137.9	137.0	135.2	133.3	131.5	129.7	131.5	133.3	135.2
102.5°	180.1	179.2	178.7	178.0	176.7	175.3	174.0	172.6	174.0	175.3	176.7
105°	223.3	222.8	222.6	222.3	221.6	220.9	220.3	219.6	220.3	220.9	221.6
107.5°	270.6	270.6	270.6	270.2	269.3	268.4	267.5	266.6	267.5	268.4	269.3
110°	317.6	317.6	317.6	316.9	315.6	314.2	312.9	311.5	312.9	314.2	315.6

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	366.3	366.5	366.6	365.9	364.6	363.2	361.9	360.5	361.9	363.2	364.6
115°	413.9	414.4	414.6	413.9	412.6	411.2	409.9	408.5	409.9	411.2	412.6
117.5°	463.0	464.1	464.7	463.8	462.0	460.1	458.3	456.5	458.3	460.1	462.0
120°	510.0	511.8	512.7	511.8	510.0	508.1	506.3	504.5	506.3	508.1	510.0
122.5°	556.9	558.0	558.6	557.5	555.2	552.9	550.7	548.4	550.7	552.9	555.2
125°	602.6	603.3	603.6	602.6	600.5	598.5	596.4	594.4	596.4	598.5	600.5
127.5°	649.2	650.1	650.6	649.3	646.8	644.3	641.8	639.3	641.8	644.3	646.8
130°	693.8	694.3	694.5	693.0	690.1	687.1	684.2	681.2	684.2	687.1	690.1
132.5°	738.7	738.5	738.4	737.3	735.0	732.7	730.5	728.2	730.5	732.7	735.0
135°	781.0	780.5	780.3	779.0	776.5	774.0	771.5	769.0	771.5	774.0	776.5
137.5°	823.9	823.4	823.2	822.2	820.1	818.1	816.0	814.0	816.0	818.1	820.1
140°	864.7	863.6	863.0	862.0	859.9	857.9	855.8	853.8	855.8	857.9	859.9
142.5°	904.8	904.1	903.8	902.8	900.7	898.7	896.6	894.6	896.6	898.7	900.7
145°	942.6	941.3	940.6	939.8	938.2	936.7	935.1	933.5	935.1	936.7	938.2
147.5°	978.8	977.9	977.4	976.4	974.3	972.3	970.2	968.2	970.2	972.3	974.3
150°	1011.4	1010.5	1010.1	1009.4	1008.0	1006.7	1005.3	1003.9	1005.3	1006.7	1008.0
152.5°	1043.4	1042.3	1041.7	1041.0	1039.7	1038.3	1037.0	1035.6	1037.0	1038.3	1039.7
155°	1071.3	1070.6	1070.3	1070.0	1069.3	1068.6	1067.9	1067.2	1067.9	1068.6	1069.3
157.5°	1097.6	1097.1	1096.9	1096.7	1096.2	1095.7	1095.3	1094.8	1095.3	1095.7	1096.2
160°	1121.7	1121.5	1121.4	1121.2	1120.7	1120.2	1119.8	1119.3	1119.8	1120.2	1120.7
162.5°	1142.1	1141.9	1141.8	1141.8	1141.8	1141.8	1141.8	1141.8	1141.8	1141.8	1141.8
165°	1160.2	1160.2	1160.2	1160.3	1160.5	1160.8	1161.0	1161.2	1161.0	1160.8	1160.5
167.5°	1175.5	1175.5	1175.5	1175.8	1176.5	1177.2	1177.9	1178.6	1177.9	1177.2	1176.5
170°	1188.5	1188.7	1188.8	1189.1	1189.8	1190.5	1191.1	1191.8	1191.1	1190.5	1189.8
172.5°	1197.6	1197.9	1198.0	1198.3	1199.0	1199.7	1200.3	1201.0	1200.3	1199.7	1199.0
175°	1204.4	1204.9	1205.1	1205.4	1206.1	1206.8	1207.5	1208.2	1207.5	1206.8	1206.1
177.5°	1208.5	1209.0	1209.2	1209.5	1210.2	1210.9	1211.6	1212.3	1211.6	1210.9	1210.2
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	565.8	568.0	567.6	563.2	558.4	554.4	546.9	547.8	545.2	545.6	548.3
5°	551.8	551.8	550.0	543.9	535.9	531.5	523.2	521.0	515.7	515.3	514.8
7.5°	536.8	534.6	532.4	523.6	514.0	506.9	495.5	492.9	487.6	484.1	482.3
10°	519.2	516.2	511.8	501.7	489.8	481.0	469.1	465.6	455.5	451.1	448.5
12.5°	499.9	498.1	491.1	482.7	463.4	453.7	436.6	440.1	430.0	421.2	419.9
15°	480.5	474.0	470.0	456.4	433.1	428.7	415.0	408.0	398.8	391.7	391.7
17.5°	461.6	451.5	442.7	428.2	411.1	398.8	388.7	385.1	373.7	366.7	365.4
20°	436.6	425.2	423.0	402.3	390.4	376.8	367.1	358.3	350.0	346.9	344.7
22.5°	412.8	399.7	396.1	378.5	366.7	353.0	343.4	337.2	331.1	328.9	324.9
25°	387.3	379.4	374.2	355.2	342.1	329.3	322.7	318.3	312.6	312.2	309.5
27.5°	362.7	355.2	350.0	331.9	322.3	310.4	305.1	300.3	297.2	295.9	294.6
30°	341.6	333.3	327.1	313.9	302.0	292.4	288.0	284.9	283.1	280.9	280.5
32.5°	318.3	313.5	305.1	295.0	285.8	276.5	273.9	271.7	269.1	268.2	267.8
35°	298.5	291.9	286.7	275.2	271.3	263.4	260.3	258.5	255.0	254.1	253.2
37.5°	279.2	273.0	267.3	260.3	252.8	248.4	246.6	244.0	242.3	242.7	241.8
40°	259.8	255.0	250.6	243.1	238.7	236.5	233.0	230.4	229.5	229.9	229.5
42.5°	240.9	236.5	233.9	228.2	223.8	221.6	219.4	216.8	218.1	218.1	219.4
45°	223.8	219.8	218.1	213.7	211.0	207.5	205.3	204.9	206.6	206.2	206.2
47.5°	206.2	204.9	202.7	198.7	195.2	193.0	192.6	192.6	194.3	195.2	194.8
50°	192.6	189.9	187.3	184.2	181.6	180.7	179.4	180.3	182.0	182.0	182.9
52.5°	175.4	173.7	172.8	170.1	168.4	168.4	168.4	168.8	170.1	171.5	171.0
55°	160.5	159.2	158.3	157.0	154.8	155.2	154.8	155.6	157.0	158.3	159.2
57.5°	144.6	144.2	143.3	141.1	141.1	140.7	142.0	142.4	144.6	145.5	146.8
60°	130.6	129.3	129.3	127.5	127.5	127.5	128.8	130.1	131.9	132.3	133.2
62.5°	115.6	115.6	115.2	113.9	113.9	115.2	115.6	117.4	118.3	118.3	119.6
65°	101.6	101.1	100.7	101.1	101.6	101.6	102.9	103.8	104.6	105.1	105.5
67.5°	87.5	87.1	87.9	87.5	88.4	90.1	89.7	91.0	92.3	92.3	92.8
70°	74.3	75.2	74.7	75.6	75.2	76.1	77.4	77.8	77.8	78.3	79.6
72.5°	62.0	62.0	62.0	61.6	62.0	62.9	63.8	64.2	65.1	65.5	66.8
75°	50.1	50.1	49.2	50.1	50.1	51.0	51.9	51.9	51.9	52.8	54.1
77.5°	37.8	38.3	37.8	38.7	38.7	39.1	40.0	39.6	40.4	40.9	41.3
80°	27.7	27.3	27.3	27.3	27.7	27.7	28.6	29.0	29.0	30.3	29.5
82.5°	17.6	18.0	17.6	18.0	18.0	18.5	18.0	18.5	18.9	19.8	19.3
85°	10.1	9.7	9.7	10.1	9.7	9.7	10.1	9.7	10.1	9.7	10.1
87.5°	4.0	3.5	3.5	3.5	3.5	3.1	3.1	2.6	2.6	2.6	2.2
90°	11.9	13.3	15.8	20.8	25.7	30.7	35.7	35.3	34.8	34.4	33.9
92.5°	29.7	30.6	30.7	31.0	31.2	31.5	31.7	31.9	32.1	32.4	32.6
95°	62.2	63.3	63.5	64.0	64.5	64.9	65.4	65.4	65.4	65.4	65.4
97.5°	97.0	98.0	98.5	99.4	100.3	101.2	102.1	102.1	102.1	102.1	102.1
100°	137.0	137.9	138.2	138.9	139.6	140.2	140.9	140.9	140.9	140.9	140.9
102.5°	178.0	178.7	179.2	180.1	181.0	181.9	182.8	183.0	183.2	183.5	183.7
105°	222.3	222.6	222.8	223.3	223.8	224.2	224.7	225.1	225.6	226.0	226.5
107.5°	270.2	270.6	270.6	270.6	270.6	270.6	270.6	270.8	271.1	271.3	271.6
110°	316.9	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	365.9	366.6	366.5	366.3	366.0	365.8	365.6	364.9	364.3	363.6	362.9
115°	413.9	414.6	414.4	413.9	413.5	413.0	412.6	412.4	412.2	411.9	411.7
117.5°	463.8	464.7	464.1	463.0	461.9	460.7	459.6	458.9	458.2	457.5	456.8
120°	511.8	512.7	511.8	510.0	508.1	506.3	504.5	504.5	504.5	504.5	504.5
122.5°	557.5	558.6	558.0	556.9	555.8	554.6	553.5	552.8	552.2	551.5	550.8
125°	602.6	603.6	603.3	602.6	601.9	601.2	600.5	599.8	599.2	598.5	597.8
127.5°	649.3	650.6	650.1	649.2	648.3	647.4	646.5	645.6	644.7	643.8	642.9
130°	693.0	694.5	694.3	693.8	693.3	692.9	692.4	692.0	691.5	691.1	690.6
132.5°	737.3	738.4	738.5	738.7	739.0	739.2	739.4	738.3	737.1	736.0	734.9
135°	779.0	780.3	780.5	781.0	781.4	781.9	782.3	782.1	781.9	781.6	781.4
137.5°	822.2	823.2	823.4	823.9	824.3	824.8	825.2	825.0	824.8	824.5	824.3
140°	862.0	863.0	863.6	864.7	865.8	867.0	868.1	868.1	868.1	868.1	868.1
142.5°	902.8	903.8	904.1	904.8	905.5	906.2	906.9	907.1	907.3	907.6	907.8
145°	939.8	940.6	941.3	942.6	944.0	945.3	946.7	946.9	947.2	947.4	947.7
147.5°	976.4	977.4	977.9	978.8	979.7	980.6	981.5	981.9	982.4	982.8	983.3
150°	1009.4	1010.1	1010.5	1011.4	1012.3	1013.2	1014.1	1014.8	1015.5	1016.2	1016.9
152.5°	1041.0	1041.7	1042.3	1043.4	1044.5	1045.7	1046.8	1047.7	1048.6	1049.5	1050.4
155°	1070.0	1070.3	1070.6	1071.3	1072.0	1072.7	1073.4	1074.5	1075.7	1076.8	1077.9
157.5°	1096.7	1096.9	1097.1	1097.6	1098.0	1098.5	1098.9	1100.5	1102.1	1103.7	1105.3
160°	1121.2	1121.4	1121.5	1121.7	1122.0	1122.2	1122.4	1123.8	1125.1	1126.5	1127.8
162.5°	1141.8	1141.8	1141.9	1142.1	1142.4	1142.6	1142.8	1144.4	1146.0	1147.6	1149.2
165°	1160.3	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1161.8	1163.4	1164.9	1166.5
167.5°	1175.8	1175.5	1175.5	1175.5	1175.5	1175.5	1175.5	1177.1	1178.7	1180.2	1181.8
170°	1189.1	1188.8	1188.7	1188.5	1188.2	1188.0	1187.8	1189.4	1191.0	1192.5	1194.1
172.5°	1198.3	1198.0	1197.9	1197.6	1197.4	1197.1	1196.9	1198.5	1200.1	1201.7	1203.3
175°	1205.4	1205.1	1204.9	1204.4	1204.0	1203.5	1203.1	1204.7	1206.3	1207.8	1209.4
177.5°	1209.5	1209.2	1209.0	1208.5	1208.1	1207.6	1207.2	1208.6	1209.9	1211.3	1212.6
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	545.2	546.5	543.4	542.5	543.4	540.3	541.2	542.1	542.1	543.4	544.3
5°	513.5	511.8	508.7	507.8	506.9	508.2	507.4	508.7	509.1	512.2	512.6
7.5°	482.3	479.7	477.0	474.4	473.5	471.3	473.5	473.5	476.6	475.7	477.9
10°	445.4	444.9	441.4	440.1	438.3	434.8	439.7	438.3	440.5	444.5	445.4
12.5°	418.1	413.3	415.5	409.3	411.5	408.0	408.4	408.4	412.0	412.4	411.5
15°	392.2	388.2	382.5	379.9	378.5	376.8	382.5	382.9	380.3	386.5	384.3
17.5°	365.8	365.8	360.5	359.2	355.7	357.4	356.6	357.0	356.1	360.5	362.7
20°	342.9	340.7	339.0	339.4	335.0	334.1	333.3	334.1	337.2	340.3	341.2
22.5°	324.5	323.1	318.8	319.6	316.1	317.4	316.6	318.8	319.2	319.2	322.3
25°	306.9	305.1	305.6	303.8	302.5	302.5	301.2	302.5	304.2	305.1	305.6
27.5°	293.7	292.4	290.2	288.9	289.7	287.5	289.3	290.6	290.6	289.7	290.6
30°	277.9	278.7	278.7	274.3	276.1	275.2	276.5	277.4	277.4	277.9	277.0
32.5°	267.3	264.7	264.2	263.8	263.8	262.0	262.0	263.4	263.8	264.2	265.6
35°	253.2	253.2	251.0	252.4	250.6	251.0	250.6	251.0	251.9	250.6	251.9
37.5°	240.5	240.9	240.1	240.9	241.4	240.5	239.6	241.4	240.5	240.5	239.6
40°	229.5	229.1	229.5	229.5	229.5	229.9	229.1	229.1	229.1	228.2	227.3
42.5°	220.3	217.6	218.5	219.0	217.6	217.6	218.1	217.6	219.0	216.3	216.3
45°	207.1	206.2	206.6	206.6	207.5	206.2	207.1	207.5	206.2	205.8	204.9
47.5°	195.2	196.1	195.2	196.1	196.1	197.0	195.2	195.6	196.1	194.3	193.0
50°	183.3	183.3	184.7	184.2	184.7	183.8	183.8	183.3	183.8	182.9	181.6
52.5°	172.3	171.0	173.2	172.8	172.3	171.9	171.5	171.9	171.0	170.1	170.1
55°	158.7	158.7	160.0	160.5	160.5	159.6	158.7	159.2	158.7	158.3	157.8
57.5°	147.7	146.0	146.8	147.3	147.3	146.0	146.8	146.0	146.0	146.4	145.1
60°	133.7	133.7	132.8	134.1	134.1	133.2	133.2	133.7	132.8	132.3	131.9
62.5°	118.7	119.1	120.5	120.9	121.3	120.5	119.6	120.0	120.0	118.7	119.1
65°	106.0	106.8	108.6	108.2	107.3	107.7	106.8	107.3	106.0	106.4	105.1
67.5°	93.6	93.2	93.6	93.6	94.5	94.1	93.2	93.2	92.8	94.1	92.8
70°	80.5	80.5	80.5	80.5	80.9	81.3	80.5	79.6	80.0	79.1	78.7
72.5°	66.8	67.3	66.8	67.7	66.4	67.3	67.3	66.8	66.4	66.4	66.4
75°	54.1	55.0	53.6	54.1	53.6	54.5	54.1	54.1	53.2	52.8	53.2
77.5°	41.3	41.8	40.9	41.3	40.9	41.3	41.3	40.9	40.9	40.9	40.9
80°	29.5	29.9	29.5	29.0	28.6	29.5	28.6	29.0	29.5	29.0	29.9
82.5°	18.9	18.9	18.5	18.9	18.0	18.0	18.5	18.5	18.0	18.9	18.0
85°	9.2	9.2	10.1	9.2	8.8	8.8	8.8	9.2	8.8	9.7	9.2
87.5°	2.2	1.8	2.2	2.2	1.8	1.8	2.2	1.8	2.2	2.6	1.8
90°	33.7	33.8	34.0	34.3	34.5	34.7	34.5	34.3	34.0	33.8	33.7
92.5°	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7	32.7
95°	65.4	65.2	64.7	64.2	63.8	63.3	63.8	64.2	64.7	65.2	65.4
97.5°	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1	102.1
100°	140.9	140.8	140.6	140.3	140.1	139.9	140.1	140.3	140.6	140.8	140.9
102.5°	183.8	183.7	183.5	183.2	183.0	182.8	183.0	183.2	183.5	183.7	183.8
105°	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7
107.5°	271.7	271.1	270.0	268.9	267.7	266.6	267.7	268.9	270.0	271.1	271.7
110°	317.6	317.3	316.6	315.9	315.3	314.6	315.3	315.9	316.6	317.3	317.6

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	362.6	362.4	361.9	361.4	361.0	360.5	361.0	361.4	361.9	362.4	362.6
115°	411.6	411.3	410.6	409.9	409.2	408.5	409.2	409.9	410.6	411.3	411.6
117.5°	456.5	456.2	455.5	454.8	454.2	453.5	454.2	454.8	455.5	456.2	456.5
120°	504.5	504.2	503.5	502.8	502.2	501.5	502.2	502.8	503.5	504.2	504.5
122.5°	550.5	550.3	549.8	549.3	548.9	548.4	548.9	549.3	549.8	550.3	550.5
125°	597.5	597.4	597.1	596.9	596.6	596.4	596.6	596.9	597.1	597.4	597.5
127.5°	642.4	642.1	641.4	640.7	640.0	639.3	640.0	640.7	641.4	642.1	642.4
130°	690.4	689.9	689.0	688.1	687.2	686.3	687.2	688.1	689.0	689.9	690.4
132.5°	734.3	734.0	733.3	732.6	731.9	731.2	731.9	732.6	733.3	734.0	734.3
135°	781.3	781.0	780.3	779.6	778.9	778.2	778.9	779.6	780.3	781.0	781.3
137.5°	824.2	823.7	822.8	821.9	821.0	820.1	821.0	821.9	822.8	823.7	824.2
140°	868.1	867.6	866.7	865.8	864.9	864.0	864.9	865.8	866.7	867.6	868.1
142.5°	907.9	907.4	906.5	905.6	904.7	903.8	904.7	905.6	906.5	907.4	907.9
145°	947.8	947.3	946.4	945.5	944.6	943.7	944.6	945.5	946.4	947.3	947.8
147.5°	983.5	983.0	982.1	981.2	980.3	979.4	980.3	981.2	982.1	983.0	983.5
150°	1017.2	1016.9	1016.2	1015.5	1014.8	1014.1	1014.8	1015.5	1016.2	1016.9	1017.2
152.5°	1050.9	1050.4	1049.5	1048.6	1047.7	1046.8	1047.7	1048.6	1049.5	1050.4	1050.9
155°	1078.5	1078.2	1077.5	1076.8	1076.1	1075.4	1076.1	1076.8	1077.5	1078.2	1078.5
157.5°	1106.1	1105.5	1104.4	1103.2	1102.1	1100.9	1102.1	1103.2	1104.4	1105.5	1106.1
160°	1128.5	1128.0	1127.1	1126.2	1125.3	1124.4	1125.3	1126.2	1127.1	1128.0	1128.5
162.5°	1150.0	1149.4	1148.3	1147.2	1146.0	1144.9	1146.0	1147.2	1148.3	1149.4	1150.0
165°	1167.3	1166.7	1165.6	1164.5	1163.3	1162.2	1163.3	1164.5	1165.6	1166.7	1167.3
167.5°	1182.6	1182.0	1180.9	1179.8	1178.6	1177.5	1178.6	1179.8	1180.9	1182.0	1182.6
170°	1194.9	1194.2	1192.9	1191.5	1190.2	1188.8	1190.2	1191.5	1192.9	1194.2	1194.9
172.5°	1204.1	1203.4	1202.1	1200.7	1199.4	1198.0	1199.4	1200.7	1202.1	1203.4	1204.1
175°	1210.2	1209.5	1208.2	1206.8	1205.5	1204.1	1205.5	1206.8	1208.2	1209.5	1210.2
177.5°	1213.3	1212.6	1211.3	1209.9	1208.6	1207.2	1208.6	1209.9	1211.3	1212.6	1213.3
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0	572.0
2.5°	543.0	546.5	545.2	540.3	546.1	546.1	550.0	550.0	554.9	556.6	559.2
5°	512.2	514.8	517.0	514.8	518.8	525.0	528.5	531.5	538.1	540.8	544.7
7.5°	479.2	484.1	486.3	486.3	492.9	499.9	506.9	511.3	520.6	524.1	528.0
10°	447.1	452.8	457.2	456.8	467.8	472.2	481.0	491.1	500.3	505.6	511.3
12.5°	413.3	416.4	422.5	431.3	433.9	441.9	452.0	464.7	481.4	486.3	494.6
15°	385.1	393.5	398.3	402.3	408.4	415.9	426.9	439.2	455.9	466.5	475.3
17.5°	361.4	372.4	375.5	374.6	382.5	393.9	406.7	415.9	430.9	443.6	452.0
20°	342.1	346.5	351.7	353.9	360.1	372.4	384.7	395.3	407.6	417.7	427.3
22.5°	322.7	326.2	330.6	334.6	339.4	346.5	358.3	371.5	383.4	393.1	404.0
25°	306.9	309.1	313.0	316.1	321.4	326.2	334.6	349.1	363.2	368.9	378.5
27.5°	291.5	293.3	295.9	299.4	302.0	306.9	314.4	326.2	340.7	346.5	359.6
30°	277.9	279.2	281.8	283.6	284.9	290.6	296.3	305.6	316.6	324.5	334.1
32.5°	265.1	266.4	269.1	269.5	271.3	274.3	279.6	288.0	297.6	304.2	312.6
35°	251.0	251.9	254.6	255.4	256.8	259.4	263.4	269.5	278.3	283.1	290.6
37.5°	240.1	239.6	241.4	242.7	244.5	245.8	247.1	253.2	259.8	264.2	270.0
40°	228.2	227.3	227.7	229.5	230.4	232.1	232.1	238.3	242.7	246.2	250.6
42.5°	216.3	215.9	215.0	215.9	216.8	217.2	217.6	222.0	226.4	229.5	234.3
45°	204.4	204.0	203.1	203.6	203.6	204.4	205.8	207.5	210.6	213.2	215.9
47.5°	193.5	192.6	191.3	190.8	191.7	191.7	191.7	193.5	196.5	197.4	200.0
50°	182.0	180.7	178.9	178.1	178.1	177.6	178.5	178.9	181.6	182.5	184.7
52.5°	169.7	168.8	167.1	165.3	165.8	164.9	165.3	165.8	166.6	167.9	169.3
55°	157.4	155.6	154.3	153.9	152.6	152.6	151.2	153.0	152.6	153.0	154.8
57.5°	145.5	143.8	141.6	140.7	139.4	138.9	138.1	137.6	138.1	139.4	140.7
60°	131.5	130.6	129.3	127.9	127.1	125.7	124.9	124.9	124.4	124.4	124.9
62.5°	117.8	117.4	115.6	115.2	114.3	113.4	112.1	111.2	111.2	112.1	112.6
65°	104.6	104.2	102.9	102.4	100.2	99.4	98.9	98.5	97.6	97.6	97.6
67.5°	92.3	91.0	91.0	88.8	87.1	86.2	85.3	84.9	84.9	84.9	85.3
70°	78.7	78.7	77.4	76.1	74.3	74.7	73.4	72.1	72.1	71.2	71.7
72.5°	65.5	65.1	63.8	63.3	62.0	60.7	59.8	60.7	59.4	58.9	59.4
75°	52.8	52.3	51.4	50.6	51.0	49.7	48.4	47.9	47.9	47.0	47.0
77.5°	40.4	41.3	39.6	39.1	38.3	37.4	36.9	36.5	36.5	36.5	37.4
80°	28.1	28.6	28.6	27.7	28.1	26.8	26.8	26.8	25.5	25.9	26.4
82.5°	18.0	18.0	17.6	18.0	17.6	17.6	17.1	17.1	16.7	16.7	17.1
85°	10.1	9.7	9.2	10.1	9.7	9.7	9.2	9.2	9.2	9.2	9.2
87.5°	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.1	3.5	3.5	3.5
90°	33.9	34.4	34.8	35.3	35.7	30.7	25.7	20.8	15.8	13.3	11.9
92.5°	32.6	32.4	32.1	31.9	31.7	31.5	31.2	31.0	30.7	30.6	29.7
95°	65.4	65.4	65.4	65.4	65.4	64.9	64.5	64.0	63.5	63.3	62.2
97.5°	102.1	102.1	102.1	102.1	102.1	101.2	100.3	99.4	98.5	98.0	97.0
100°	140.9	140.9	140.9	140.9	140.9	140.2	139.6	138.9	138.2	137.9	137.0
102.5°	183.7	183.5	183.2	183.0	182.8	181.9	181.0	180.1	179.2	178.7	178.0
105°	226.5	226.0	225.6	225.1	224.7	224.2	223.8	223.3	222.8	222.6	222.3
107.5°	271.6	271.3	271.1	270.8	270.6	270.6	270.6	270.6	270.6	270.6	270.2
110°	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6	317.6	316.9

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	362.9	363.6	364.3	364.9	365.6	365.8	366.0	366.3	366.5	366.6	365.9
115°	411.7	411.9	412.2	412.4	412.6	413.0	413.5	413.9	414.4	414.6	413.9
117.5°	456.8	457.5	458.2	458.9	459.6	460.7	461.9	463.0	464.1	464.7	463.8
120°	504.5	504.5	504.5	504.5	504.5	506.3	508.1	510.0	511.8	512.7	511.8
122.5°	550.8	551.5	552.2	552.8	553.5	554.6	555.8	556.9	558.0	558.6	557.5
125°	597.8	598.5	599.2	599.8	600.5	601.2	601.9	602.6	603.3	603.6	602.6
127.5°	642.9	643.8	644.7	645.6	646.5	647.4	648.3	649.2	650.1	650.6	649.3
130°	690.6	691.1	691.5	692.0	692.4	692.9	693.3	693.8	694.3	694.5	693.0
132.5°	734.9	736.0	737.1	738.3	739.4	739.2	739.0	738.7	738.5	738.4	737.3
135°	781.4	781.6	781.9	782.1	782.3	781.9	781.4	781.0	780.5	780.3	779.0
137.5°	824.3	824.5	824.8	825.0	825.2	824.8	824.3	823.9	823.4	823.2	822.2
140°	868.1	868.1	868.1	868.1	868.1	867.0	865.8	864.7	863.6	863.0	862.0
142.5°	907.8	907.6	907.3	907.1	906.9	906.2	905.5	904.8	904.1	903.8	902.8
145°	947.7	947.4	947.2	946.9	946.7	945.3	944.0	942.6	941.3	940.6	939.8
147.5°	983.3	982.8	982.4	981.9	981.5	980.6	979.7	978.8	977.9	977.4	976.4
150°	1016.9	1016.2	1015.5	1014.8	1014.1	1013.2	1012.3	1011.4	1010.5	1010.1	1009.4
152.5°	1050.4	1049.5	1048.6	1047.7	1046.8	1045.7	1044.5	1043.4	1042.3	1041.7	1041.0
155°	1077.9	1076.8	1075.7	1074.5	1073.4	1072.7	1072.0	1071.3	1070.6	1070.3	1070.0
157.5°	1105.3	1103.7	1102.1	1100.5	1098.9	1098.5	1098.0	1097.6	1097.1	1096.9	1096.7
160°	1127.8	1126.5	1125.1	1123.8	1122.4	1122.2	1122.0	1121.7	1121.5	1121.4	1121.2
162.5°	1149.2	1147.6	1146.0	1144.4	1142.8	1142.6	1142.4	1142.1	1141.9	1141.8	1141.8
165°	1166.5	1164.9	1163.4	1161.8	1160.2	1160.2	1160.2	1160.2	1160.2	1160.2	1160.3
167.5°	1181.8	1180.2	1178.7	1177.1	1175.5	1175.5	1175.5	1175.5	1175.5	1175.5	1175.8
170°	1194.1	1192.5	1191.0	1189.4	1187.8	1188.0	1188.2	1188.5	1188.7	1188.8	1189.1
172.5°	1203.3	1201.7	1200.1	1198.5	1196.9	1197.1	1197.4	1197.6	1197.9	1198.0	1198.3
175°	1209.4	1207.8	1206.3	1204.7	1203.1	1203.5	1204.0	1204.4	1204.9	1205.1	1205.4
177.5°	1212.6	1211.3	1209.9	1208.6	1207.2	1207.6	1208.1	1208.5	1209.0	1209.2	1209.5
180°	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2	1210.2

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	572.0	572.0	572.0	572.0
2.5°	561.4	561.4	568.0	575.1
5°	549.1	552.2	562.8	572.4
7.5°	537.3	542.5	555.7	568.0
10°	522.8	529.8	546.1	560.6
12.5°	508.7	515.3	534.2	550.5
15°	488.9	497.3	517.5	537.7
17.5°	469.1	477.5	502.1	525.8
20°	445.8	456.8	484.5	516.2
22.5°	424.3	437.9	468.7	494.2
25°	400.5	421.6	450.2	483.2
27.5°	379.4	400.5	429.5	463.0
30°	355.7	377.2	407.1	437.9
32.5°	332.8	352.6	381.6	419.4
35°	309.1	328.0	356.1	394.4
37.5°	287.5	306.0	336.8	372.0
40°	266.4	285.8	312.2	347.3
42.5°	246.6	263.8	287.5	322.7
45°	228.6	240.9	262.9	295.9
47.5°	209.7	220.7	240.9	273.9
50°	192.1	201.4	219.0	249.7
52.5°	175.0	182.9	199.2	223.8
55°	159.6	167.1	178.9	203.1
57.5°	143.8	149.5	160.9	180.3
60°	128.4	133.7	142.9	158.7
62.5°	113.0	117.4	126.2	138.9
65°	99.4	102.9	109.5	120.5
67.5°	86.2	88.4	93.6	102.4
70°	73.4	75.2	79.6	86.6
72.5°	59.8	61.6	66.4	71.2
75°	48.4	48.8	52.3	56.3
77.5°	37.8	37.4	40.0	43.1
80°	25.9	27.3	29.5	30.8
82.5°	17.6	18.0	18.9	19.8
85°	9.7	10.1	10.1	11.4
87.5°	4.0	4.4	4.4	4.8
90°	9.2	6.5	3.7	1.0
92.5°	27.9	26.1	24.3	22.5
95°	59.9	57.6	55.4	53.1
97.5°	95.0	92.9	90.9	88.9
100°	135.2	133.3	131.5	129.7
102.5°	176.7	175.3	174.0	172.6
105°	221.6	220.9	220.3	219.6
107.5°	269.3	268.4	267.5	266.6
110°	315.6	314.2	312.9	311.5

TEST NUMBER: P1029424

CATALOG NUMBER: S122DIW-B290D970UB2750-4F0-XX-W2A-A1_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	364.6	363.2	361.9	360.5
115°	412.6	411.2	409.9	408.5
117.5°	462.0	460.1	458.3	456.5
120°	510.0	508.1	506.3	504.5
122.5°	555.2	552.9	550.7	548.4
125°	600.5	598.5	596.4	594.4
127.5°	646.8	644.3	641.8	639.3
130°	690.1	687.1	684.2	681.2
132.5°	735.0	732.7	730.5	728.2
135°	776.5	774.0	771.5	769.0
137.5°	820.1	818.1	816.0	814.0
140°	859.9	857.9	855.8	853.8
142.5°	900.7	898.7	896.6	894.6
145°	938.2	936.7	935.1	933.5
147.5°	974.3	972.3	970.2	968.2
150°	1008.0	1006.7	1005.3	1003.9
152.5°	1039.7	1038.3	1037.0	1035.6
155°	1069.3	1068.6	1067.9	1067.2
157.5°	1096.2	1095.7	1095.3	1094.8
160°	1120.7	1120.2	1119.8	1119.3
162.5°	1141.8	1141.8	1141.8	1141.8
165°	1160.5	1160.8	1161.0	1161.2
167.5°	1176.5	1177.2	1177.9	1178.6
170°	1189.8	1190.5	1191.1	1191.8
172.5°	1199.0	1199.7	1200.3	1201.0
175°	1206.1	1206.8	1207.5	1208.2
177.5°	1210.2	1210.9	1211.6	1212.3
180°	1210.2	1210.2	1210.2	1210.2

(END OF REPORT)