

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029449

Luminaire Tested: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029449
REPORT IS A COMBINATION OF REPORTS P985928 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K
Description: Define 2 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6437.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35
2	86	79	73	68	77	72	67	63	57	54	51	44	42	40	32	31	30
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15318	15318	15318	15318
5°	15354	16332	15413	12993
10°	15176	17829	15272	10713
15°	14809	18805	15014	9023
20°	14577	17657	14577	7843
25°	14112	15170	14178	7013
30°	13348	11925	13604	6353
35°	12671	8246	12882	5813
40°	11892	6226	12028	5382
45°	10933	5116	11112	4916
50°	10103	4491	10120	4501
55°	9156	3826	9217	4049
60°	8148	3196	8260	3535
65°	7245	2599	7376	3018
70°	6344	2040	6505	2434
75°	5326	1481	5533	1765
80°	4160	938	4455	1047
85°	2726	473	2938	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15834 cd/sqm

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	1.4
10°-20°	268.3	4.2
20°-30°	389.3	6.0
30°-40°	410.4	6.4
40°-50°	363.2	5.6
50°-60°	290.0	4.5
60°-70°	197.0	3.1
70°-80°	100.8	1.6
80°-90°	28.2	0.4
90°-100°	95.1	1.5
100°-110°	302.3	4.7
110°-120°	517.3	8.0
120°-130°	680.3	10.6
130°-140°	763.6	11.9
140°-150°	748.8	11.6
150°-160°	628.1	9.8
160°-170°	416.6	6.5
170°-180°	145.6	2.3
0°-30°	749.8	11.6
0°-40°	1160.2	18.0
0°-60°	1813.4	28.2
0°-90°	2139.4	33.2
90°-120°	914.6	14.2
90°-150°	3107.3	48.3
90°-180°	4298.0	66.8
0°-180°	6437.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	968	968	968	968	968	
5°	968	1081	972	860	968	92
15°	910	1328	922	637	910	257
25°	817	1107	821	512	817	374
35°	667	602	678	425	667	417
45°	501	363	509	349	501	388
55°	344	255	346	270	344	307
65°	204	157	208	182	204	203
75°	95	77	99	92	95	102
85°	19	20	21	15	19	23
90°	1	44	1	44	1	5
95°	68	80	68	80	68	75
105°	279	288	279	288	279	294
115°	519	519	519	519	519	513
125°	755	758	755	758	755	675
135°	977	988	977	988	977	755
145°	1186	1199	1186	1199	1186	741
155°	1356	1366	1356	1366	1356	624
165°	1475	1476	1475	1476	1475	416
175°	1535	1529	1535	1529	1535	146
180°	1537	1537	1537	1537	1537	

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	972.9	975.1	978.8	979.6	987.0	993.0	999.7	999.7	1001.9	1001.2	995.2
5°	968.4	975.1	984.8	993.0	1006.4	1012.3	1021.2	1027.9	1033.9	1038.3	1037.6
7.5°	961.0	972.9	987.0	1002.6	1020.5	1030.9	1043.5	1055.4	1063.6	1071.1	1076.3
10°	948.3	968.4	987.8	1008.6	1031.6	1045.8	1060.7	1076.3	1088.9	1103.1	1116.4
12.5°	931.2	960.2	984.0	1011.6	1039.8	1055.4	1079.3	1091.2	1115.7	1151.4	1161.1
15°	909.7	949.1	971.4	1006.4	1043.5	1056.2	1088.9	1108.3	1158.8	1181.2	1207.9
17.5°	889.6	933.5	963.2	1003.4	1039.8	1064.4	1096.4	1135.8	1178.2	1210.2	1239.9
20°	873.2	915.6	951.3	995.9	1042.1	1073.3	1106.8	1154.4	1200.5	1233.2	1256.3
22.5°	836.0	890.3	932.0	981.8	1037.6	1080.7	1112.7	1164.8	1214.6	1234.7	1254.8
25°	817.4	864.3	912.6	969.2	1034.6	1085.9	1113.5	1171.5	1215.4	1222.8	1227.3
27.5°	783.2	836.0	892.6	957.3	1033.9	1077.0	1112.0	1164.8	1199.7	1194.5	1181.2
30°	740.8	805.5	868.0	937.9	1023.5	1070.3	1103.1	1151.4	1169.3	1142.5	1118.7
32.5°	709.6	770.6	839.7	920.8	1011.6	1056.2	1088.2	1126.1	1129.8	1081.5	1041.3
35°	667.2	734.9	813.0	898.5	991.5	1031.6	1061.4	1084.5	1066.6	998.9	951.3
37.5°	629.3	696.2	779.5	866.5	964.0	1003.4	1027.2	1030.9	987.0	927.5	857.6
40°	587.6	656.8	743.8	835.3	933.5	967.7	982.6	971.4	908.2	839.0	757.9
42.5°	545.9	614.4	708.1	801.8	894.8	923.8	929.7	899.3	821.9	740.8	647.1
45°	500.6	572.0	665.7	760.2	850.2	866.5	867.3	823.4	731.9	647.1	560.1
47.5°	463.4	529.6	622.6	717.0	792.9	804.0	799.6	749.0	649.3	554.1	478.3
50°	422.5	485.7	577.9	670.9	735.6	738.6	727.4	655.3	557.8	470.8	410.6
52.5°	378.6	442.6	527.4	616.6	674.6	670.2	648.6	571.2	479.7	407.6	361.5
55°	343.6	400.2	479.7	566.8	607.7	595.0	571.2	492.4	420.2	359.3	319.1
57.5°	305.0	354.8	432.9	508.8	532.6	520.7	496.9	423.2	356.3	310.2	283.4
60°	268.5	313.9	382.3	445.5	464.1	451.5	424.0	357.8	309.4	270.7	250.7
62.5°	235.0	274.5	331.7	389.8	397.2	384.5	360.7	307.2	265.5	235.0	220.2
65°	203.8	241.0	287.1	331.0	337.7	324.3	299.8	261.1	226.1	206.8	192.6
67.5°	173.3	203.1	244.0	275.9	279.7	267.0	246.9	215.7	194.1	173.3	162.9
70°	146.5	168.8	200.8	226.9	228.3	216.4	206.0	177.8	161.4	146.5	138.3
72.5°	120.5	136.1	160.7	180.0	180.7	173.3	163.6	145.8	131.7	121.2	113.1
75°	95.2	108.6	123.5	140.6	139.8	133.9	126.4	115.3	103.4	96.7	93.0
77.5°	72.9	81.1	93.0	104.1	104.1	101.2	96.7	88.5	81.1	74.4	70.7
80°	52.1	57.3	66.9	70.7	72.1	71.4	67.7	61.7	58.8	53.6	52.1
82.5°	33.5	37.2	41.7	45.4	47.6	46.1	45.4	42.4	37.9	36.4	35.0
85°	19.3	20.8	23.1	25.3	26.0	25.3	26.8	24.5	22.3	22.3	21.6
87.5°	8.2	8.9	10.4	10.4	11.2	11.2	10.4	11.2	11.2	10.4	9.7
90°	1.3	4.8	8.2	11.7	15.2	16.9	20.1	26.4	32.7	39.1	45.4
92.5°	28.5	30.8	33.1	35.4	37.7	38.9	39.0	39.3	39.6	39.9	40.2
95°	67.5	70.4	73.2	76.1	79.0	80.4	80.7	81.3	81.8	82.4	83.0
97.5°	112.9	115.5	118.1	120.6	123.2	124.5	125.1	126.2	127.4	128.5	129.7
100°	164.7	167.0	169.3	171.6	173.9	175.1	175.5	176.4	177.3	178.1	179.0
102.5°	219.2	220.9	222.7	224.4	226.1	227.0	227.6	228.7	229.9	231.0	232.2
105°	278.9	279.8	280.6	281.5	282.4	282.8	283.1	283.7	284.2	284.8	285.4
107.5°	338.6	339.8	340.9	342.1	343.2	343.8	343.8	343.8	343.8	343.8	343.8
110°	395.6	397.3	399.1	400.8	402.5	403.4	403.4	403.4	403.4	403.4	403.4

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	457.9	459.6	461.4	463.1	464.8	465.7	465.6	465.3	465.0	464.7	464.4
115°	518.9	520.6	522.4	524.1	525.8	526.7	526.4	525.8	525.3	524.7	524.1
117.5°	579.8	582.1	584.4	586.7	589.0	590.2	589.5	588.0	586.6	585.1	583.7
120°	640.8	643.1	645.4	647.7	650.0	651.2	650.0	647.7	645.4	643.1	640.8
122.5°	696.6	699.5	702.4	705.3	708.2	709.6	708.9	707.4	706.0	704.5	703.1
125°	755.0	757.6	760.2	762.7	765.3	766.6	766.2	765.3	764.4	763.6	762.7
127.5°	812.0	815.2	818.4	821.5	824.7	826.3	825.7	824.6	823.4	822.3	821.1
130°	865.2	869.0	872.7	876.5	880.2	882.1	881.8	881.2	880.7	880.1	879.5
132.5°	924.9	927.8	930.7	933.6	936.5	937.9	938.0	938.3	938.6	938.9	939.2
135°	976.8	980.0	983.2	986.3	989.5	991.1	991.4	991.9	992.5	993.0	993.6
137.5°	1033.9	1036.5	1039.1	1041.6	1044.2	1045.5	1045.8	1046.4	1046.9	1047.5	1048.1
140°	1084.4	1087.0	1089.6	1092.2	1094.8	1096.1	1096.8	1098.3	1099.7	1101.2	1102.6
142.5°	1136.3	1138.9	1141.5	1144.1	1146.7	1148.0	1148.4	1149.3	1150.2	1151.0	1151.9
145°	1185.6	1187.6	1189.6	1191.7	1193.7	1194.7	1195.6	1197.3	1199.0	1200.8	1202.5
147.5°	1229.7	1232.3	1234.9	1237.5	1240.1	1241.4	1242.0	1243.1	1244.3	1245.4	1246.6
150°	1275.1	1276.8	1278.6	1280.3	1282.0	1282.9	1283.5	1284.6	1285.8	1286.9	1288.1
152.5°	1315.3	1317.0	1318.8	1320.5	1322.2	1323.1	1323.8	1325.3	1326.7	1328.2	1329.6
155°	1355.6	1356.5	1357.3	1358.2	1359.1	1359.5	1359.9	1360.8	1361.6	1362.5	1363.3
157.5°	1390.6	1391.2	1391.8	1392.3	1392.9	1393.2	1393.5	1394.1	1394.6	1395.2	1395.8
160°	1421.7	1422.3	1422.9	1423.4	1424.0	1424.3	1424.4	1424.7	1425.0	1425.3	1425.6
162.5°	1450.3	1450.3	1450.3	1450.3	1450.3	1450.3	1450.4	1450.7	1451.0	1451.3	1451.6
165°	1474.9	1474.6	1474.3	1474.0	1473.7	1473.6	1473.6	1473.6	1473.6	1473.6	1473.6
167.5°	1497.0	1496.1	1495.3	1494.4	1493.5	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1
170°	1513.8	1512.9	1512.1	1511.2	1510.3	1509.9	1509.8	1509.5	1509.2	1508.9	1508.6
172.5°	1525.5	1524.6	1523.8	1522.9	1522.0	1521.6	1521.5	1521.2	1520.9	1520.6	1520.3
175°	1534.6	1533.7	1532.9	1532.0	1531.1	1530.7	1530.4	1529.8	1529.3	1528.7	1528.1
177.5°	1539.8	1538.9	1538.1	1537.2	1536.3	1535.9	1535.6	1535.0	1534.5	1533.9	1533.3
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1005.6	1006.4	1007.8	1015.3	1019.0	1019.7	1016.8	1023.5	1025.7	1023.5	1022.0
5°	1053.2	1057.7	1066.6	1076.3	1075.5	1076.3	1080.7	1085.2	1086.7	1080.7	1083.0
7.5°	1094.9	1103.8	1113.5	1128.3	1128.3	1135.8	1138.8	1142.5	1151.4	1146.9	1145.4
10°	1142.5	1154.4	1172.2	1196.0	1196.8	1204.2	1211.6	1223.5	1227.3	1224.3	1225.8
12.5°	1202.0	1225.0	1226.5	1252.6	1264.5	1265.9	1277.8	1275.6	1283.1	1283.1	1295.7
15°	1228.0	1263.7	1283.8	1309.1	1316.5	1307.6	1317.3	1327.7	1328.4	1328.4	1327.7
17.5°	1274.9	1289.0	1309.1	1322.5	1325.4	1325.4	1326.2	1330.7	1327.7	1321.7	1326.2
20°	1284.5	1290.5	1297.9	1296.4	1297.9	1290.5	1283.1	1275.6	1276.4	1272.6	1283.8
22.5°	1266.7	1265.2	1248.1	1236.9	1236.9	1222.1	1207.9	1201.2	1194.5	1196.8	1200.5
25°	1222.1	1199.0	1178.2	1161.8	1158.1	1134.3	1115.0	1109.0	1097.8	1106.8	1108.3
27.5°	1150.7	1124.6	1091.2	1077.0	1057.7	1048.0	1034.6	1016.8	993.7	1007.1	1004.9
30°	1074.0	1035.4	1007.8	973.6	943.1	940.9	915.6	885.9	874.0	874.0	880.7
32.5°	988.5	937.2	897.0	848.7	818.9	806.3	775.8	746.0	752.7	730.4	738.6
35°	888.8	821.2	770.6	723.7	701.4	686.5	647.1	630.7	612.9	602.5	621.8
37.5°	793.6	715.5	650.8	599.5	591.3	564.5	537.8	527.4	516.9	521.4	520.7
40°	677.6	608.4	550.4	510.2	496.1	483.5	465.6	453.0	446.3	450.0	450.7
42.5°	572.7	514.7	471.6	443.3	431.4	422.5	413.6	403.1	400.9	400.9	403.9
45°	491.7	444.0	415.0	392.0	385.3	378.6	371.9	367.4	365.9	363.0	365.2
47.5°	426.9	389.0	371.2	354.0	346.6	345.1	339.2	336.9	334.0	333.2	334.0
50°	372.6	348.8	332.5	322.8	317.6	315.4	312.4	307.9	306.4	310.2	308.7
52.5°	334.7	312.4	303.5	293.8	290.8	287.8	283.4	284.1	283.4	281.9	281.9
55°	296.8	282.6	273.7	266.3	265.5	262.6	258.8	257.4	256.6	255.1	257.4
57.5°	266.3	255.1	246.9	240.2	237.3	237.3	233.6	230.6	230.6	229.8	230.6
60°	235.8	224.6	219.4	212.7	210.5	209.8	207.5	206.0	203.8	203.8	203.8
62.5°	207.5	198.6	192.6	186.7	187.4	183.7	180.7	179.3	179.3	180.0	180.0
65°	180.7	174.8	167.4	162.1	160.7	159.9	158.4	157.7	155.5	156.9	156.9
67.5°	156.2	148.0	143.6	141.3	139.1	138.3	136.9	135.4	134.6	133.9	135.4
70°	131.7	125.0	121.2	119.8	117.5	116.8	116.0	113.8	114.5	115.3	116.0
72.5°	109.3	103.4	102.6	98.2	98.2	98.2	95.2	96.7	95.9	94.5	95.9
75°	86.3	83.3	81.8	79.6	80.3	79.6	78.8	76.6	76.6	77.4	78.1
77.5°	68.4	65.5	64.7	62.5	61.0	62.5	61.0	60.2	60.2	61.0	61.0
80°	50.6	49.1	46.9	46.9	46.9	46.1	46.1	46.1	45.4	44.6	45.4
82.5°	33.5	33.5	32.7	32.0	32.7	31.2	32.0	32.0	32.0	32.0	32.0
85°	21.6	20.8	20.8	20.1	20.1	20.1	20.8	19.3	19.3	20.1	20.1
87.5°	9.7	9.7	9.7	10.4	9.7	9.7	9.7	10.4	9.7	9.7	9.7
90°	44.8	44.2	43.7	43.1	42.8	42.9	43.2	43.5	43.8	44.1	43.8
92.5°	40.5	40.8	41.1	41.4	41.5	41.5	41.5	41.5	41.5	41.5	41.5
95°	83.0	83.0	83.0	83.0	83.0	82.7	82.1	81.6	81.0	80.4	81.0
97.5°	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7
100°	179.0	179.0	179.0	179.0	179.0	178.9	178.6	178.3	178.0	177.7	178.0
102.5°	232.5	232.8	233.1	233.4	233.5	233.4	233.1	232.8	232.5	232.2	232.5
105°	286.0	286.6	287.1	287.7	288.0	288.0	288.0	288.0	288.0	288.0	288.0
107.5°	344.1	344.4	344.7	345.0	345.1	344.4	342.9	341.5	340.0	338.6	340.0
110°	403.4	403.4	403.4	403.4	403.4	403.0	402.1	401.2	400.4	399.5	400.4

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	463.5	462.7	461.8	460.9	460.5	460.2	459.6	459.1	458.5	457.9	458.5
115°	523.8	523.5	523.2	522.9	522.8	522.4	521.5	520.6	519.8	518.9	519.8
117.5°	582.8	582.0	581.1	580.2	579.8	579.4	578.5	577.7	576.8	576.0	576.8
120°	640.8	640.8	640.8	640.8	640.8	640.4	639.5	638.6	637.8	636.9	637.8
122.5°	702.2	701.4	700.5	699.6	699.2	698.9	698.3	697.8	697.2	696.6	697.2
125°	761.9	761.0	760.2	759.3	758.9	758.8	758.5	758.2	757.9	757.6	757.9
127.5°	819.9	818.8	817.6	816.5	815.9	815.5	814.6	813.7	812.9	812.0	812.9
130°	878.9	878.3	877.8	877.2	876.9	876.3	875.2	874.0	872.9	871.7	872.9
132.5°	937.8	936.3	934.9	933.4	932.7	932.3	931.4	930.5	929.7	928.8	929.7
135°	993.3	993.0	992.7	992.4	992.3	991.9	991.0	990.2	989.3	988.5	989.3
137.5°	1047.8	1047.5	1047.2	1046.9	1046.8	1046.2	1045.1	1043.9	1042.8	1041.6	1042.8
140°	1102.6	1102.6	1102.6	1102.6	1102.6	1102.0	1100.9	1099.7	1098.6	1097.4	1098.6
142.5°	1152.2	1152.5	1152.8	1153.1	1153.2	1152.6	1151.5	1150.3	1149.2	1148.0	1149.2
145°	1202.8	1203.1	1203.4	1203.7	1203.8	1203.2	1202.1	1200.9	1199.8	1198.6	1199.8
147.5°	1247.2	1247.8	1248.3	1248.9	1249.2	1248.6	1247.5	1246.3	1245.2	1244.0	1245.2
150°	1289.0	1289.8	1290.7	1291.6	1292.0	1291.6	1290.7	1289.8	1289.0	1288.1	1289.0
152.5°	1330.8	1331.9	1333.1	1334.2	1334.8	1334.2	1333.1	1331.9	1330.8	1329.6	1330.8
155°	1364.7	1366.2	1367.6	1369.1	1369.8	1369.4	1368.5	1367.6	1366.8	1365.9	1366.8
157.5°	1397.8	1399.8	1401.9	1403.9	1404.9	1404.2	1402.7	1401.3	1399.8	1398.4	1399.8
160°	1427.3	1429.1	1430.8	1432.5	1433.4	1432.8	1431.7	1430.5	1429.4	1428.2	1429.4
162.5°	1453.6	1455.6	1457.6	1459.6	1460.6	1459.9	1458.4	1457.0	1455.5	1454.1	1455.5
165°	1475.6	1477.6	1479.7	1481.7	1482.7	1482.0	1480.5	1479.1	1477.6	1476.2	1477.6
167.5°	1495.1	1497.1	1499.1	1501.1	1502.1	1501.4	1500.0	1498.5	1497.1	1495.7	1497.1
170°	1510.6	1512.6	1514.7	1516.7	1517.7	1516.8	1515.1	1513.4	1511.6	1509.9	1511.6
172.5°	1522.3	1524.3	1526.4	1528.4	1529.4	1528.5	1526.8	1525.1	1523.3	1521.6	1523.3
175°	1530.1	1532.1	1534.2	1536.2	1537.2	1536.3	1534.6	1532.9	1531.1	1529.4	1531.1
177.5°	1535.0	1536.8	1538.5	1540.2	1541.1	1540.2	1538.5	1536.8	1535.0	1533.3	1535.0
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	1025.7	1020.5	1016.0	1016.8	1020.5	1017.5	1010.1	1000.4	996.7	992.2	996.7
5°	1087.4	1083.0	1074.0	1074.8	1072.6	1069.6	1057.7	1042.8	1042.8	1030.9	1029.4
7.5°	1148.4	1141.7	1135.8	1134.3	1126.1	1120.2	1109.7	1088.9	1080.7	1066.6	1058.4
10°	1216.9	1211.6	1205.0	1196.8	1192.3	1181.9	1164.8	1134.3	1119.4	1100.1	1085.9
12.5°	1286.0	1285.3	1270.4	1254.0	1253.3	1236.9	1225.0	1184.1	1164.0	1138.0	1104.5
15°	1329.9	1326.2	1318.0	1309.8	1312.1	1294.2	1267.4	1219.1	1205.7	1174.5	1138.8
17.5°	1329.2	1329.2	1326.9	1325.4	1323.2	1318.0	1303.1	1271.2	1249.6	1210.2	1176.7
20°	1286.8	1296.4	1298.7	1297.9	1305.4	1309.1	1308.3	1288.3	1271.2	1236.2	1202.0
22.5°	1202.0	1224.3	1234.0	1239.9	1255.5	1263.7	1283.1	1275.6	1271.2	1245.1	1216.1
25°	1123.1	1130.6	1159.6	1161.1	1182.6	1202.7	1222.1	1234.7	1251.1	1241.4	1216.9
27.5°	1021.2	1038.3	1059.2	1074.8	1079.3	1120.2	1152.1	1175.9	1213.1	1216.1	1207.9
30°	905.9	914.1	948.3	969.2	993.0	1022.7	1068.8	1109.7	1143.2	1173.7	1184.1
32.5°	765.4	798.8	818.9	844.2	865.0	917.8	974.4	1027.2	1065.9	1117.2	1139.5
35°	636.7	662.7	696.9	707.4	745.3	789.9	863.5	931.2	990.0	1042.1	1087.4
37.5°	530.3	551.2	587.6	604.0	626.3	683.6	745.3	829.3	900.0	964.0	1020.5
40°	457.4	473.1	500.6	505.8	524.4	576.4	626.3	705.1	798.8	885.1	946.9
42.5°	407.6	415.0	433.6	440.3	452.2	487.2	531.8	606.2	693.2	782.5	869.5
45°	371.9	377.1	388.3	394.2	409.1	424.7	461.2	520.7	589.1	679.1	772.8
47.5°	339.9	346.6	351.1	354.8	363.0	380.1	403.9	447.8	513.2	595.8	686.5
50°	313.1	315.4	323.6	324.3	329.5	340.7	363.0	389.8	441.8	508.8	596.5
52.5°	286.4	288.6	293.8	299.0	301.2	310.2	325.0	347.4	386.0	438.8	516.9
55°	259.6	262.6	267.8	271.5	273.7	281.2	290.1	311.7	342.1	379.3	443.3
57.5°	232.8	239.5	241.0	243.2	246.9	255.1	263.3	275.9	299.8	334.0	380.8
60°	207.5	209.8	215.0	217.2	220.9	225.4	235.8	245.5	262.6	289.3	331.7
62.5°	181.5	186.7	188.9	191.2	194.1	199.3	206.0	216.4	231.3	252.9	286.4
65°	159.2	159.9	164.4	167.4	170.3	174.0	180.7	190.4	199.3	219.4	244.0
67.5°	137.6	139.1	140.6	143.6	147.3	151.0	156.9	162.1	173.3	186.7	206.0
70°	116.8	116.8	120.5	122.7	122.0	126.4	130.9	136.9	145.0	157.7	173.3
72.5°	98.2	97.4	100.4	101.2	102.6	105.6	108.6	114.5	119.0	128.7	140.6
75°	78.1	79.6	81.1	81.1	83.3	85.5	88.5	91.5	96.7	102.6	111.6
77.5°	61.7	61.7	63.2	64.0	66.2	65.5	68.4	71.4	75.1	80.3	87.0
80°	45.4	46.9	46.9	46.9	47.6	48.3	51.3	53.6	55.8	59.5	62.5
82.5°	32.0	32.0	33.5	33.5	33.5	35.0	35.0	35.7	37.2	39.4	41.7
85°	20.1	20.1	20.1	20.8	20.1	20.8	22.3	21.6	22.3	23.8	23.8
87.5°	9.7	9.7	9.7	9.7	9.7	10.4	9.7	10.4	11.2	11.2	11.2
90°	43.5	43.2	42.9	42.8	43.1	43.7	44.2	44.8	45.4	39.1	32.7
92.5°	41.5	41.5	41.5	41.5	41.4	41.1	40.8	40.5	40.2	39.9	39.6
95°	81.6	82.1	82.7	83.0	83.0	83.0	83.0	83.0	83.0	82.4	81.8
97.5°	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	128.5	127.4
100°	178.3	178.6	178.9	179.0	179.0	179.0	179.0	179.0	179.0	178.1	177.3
102.5°	232.8	233.1	233.4	233.5	233.4	233.1	232.8	232.5	232.2	231.0	229.9
105°	288.0	288.0	288.0	288.0	287.7	287.1	286.6	286.0	285.4	284.8	284.2
107.5°	341.5	342.9	344.4	345.1	345.0	344.7	344.4	344.1	343.8	343.8	343.8
110°	401.2	402.1	403.0	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	459.1	459.6	460.2	460.5	460.9	461.8	462.7	463.5	464.4	464.7	465.0
115°	520.6	521.5	522.4	522.8	522.9	523.2	523.5	523.8	524.1	524.7	525.3
117.5°	577.7	578.5	579.4	579.8	580.2	581.1	582.0	582.8	583.7	585.1	586.6
120°	638.6	639.5	640.4	640.8	640.8	640.8	640.8	640.8	640.8	643.1	645.4
122.5°	697.8	698.3	698.9	699.2	699.6	700.5	701.4	702.2	703.1	704.5	706.0
125°	758.2	758.5	758.8	758.9	759.3	760.2	761.0	761.9	762.7	763.6	764.4
127.5°	813.7	814.6	815.5	815.9	816.5	817.6	818.8	819.9	821.1	822.3	823.4
130°	874.0	875.2	876.3	876.9	877.2	877.8	878.3	878.9	879.5	880.1	880.7
132.5°	930.5	931.4	932.3	932.7	933.4	934.9	936.3	937.8	939.2	938.9	938.6
135°	990.2	991.0	991.9	992.3	992.4	992.7	993.0	993.3	993.6	993.0	992.5
137.5°	1043.9	1045.1	1046.2	1046.8	1046.9	1047.2	1047.5	1047.8	1048.1	1047.5	1046.9
140°	1099.7	1100.9	1102.0	1102.6	1102.6	1102.6	1102.6	1102.6	1102.6	1101.2	1099.7
142.5°	1150.3	1151.5	1152.6	1153.2	1153.1	1152.8	1152.5	1152.2	1151.9	1151.0	1150.2
145°	1200.9	1202.1	1203.2	1203.8	1203.7	1203.4	1203.1	1202.8	1202.5	1200.8	1199.0
147.5°	1246.3	1247.5	1248.6	1249.2	1248.9	1248.3	1247.8	1247.2	1246.6	1245.4	1244.3
150°	1289.8	1290.7	1291.6	1292.0	1291.6	1290.7	1289.8	1289.0	1288.1	1286.9	1285.8
152.5°	1331.9	1333.1	1334.2	1334.8	1334.2	1333.1	1331.9	1330.8	1329.6	1328.2	1326.7
155°	1367.6	1368.5	1369.4	1369.8	1369.1	1367.6	1366.2	1364.7	1363.3	1362.5	1361.6
157.5°	1401.3	1402.7	1404.2	1404.9	1403.9	1401.9	1399.8	1397.8	1395.8	1395.2	1394.6
160°	1430.5	1431.7	1432.8	1433.4	1432.5	1430.8	1429.1	1427.3	1425.6	1425.3	1425.0
162.5°	1457.0	1458.4	1459.9	1460.6	1459.6	1457.6	1455.6	1453.6	1451.6	1451.3	1451.0
165°	1479.1	1480.5	1482.0	1482.7	1481.7	1479.7	1477.6	1475.6	1473.6	1473.6	1473.6
167.5°	1498.5	1500.0	1501.4	1502.1	1501.1	1499.1	1497.1	1495.1	1493.1	1493.1	1493.1
170°	1513.4	1515.1	1516.8	1517.7	1516.7	1514.7	1512.6	1510.6	1508.6	1508.9	1509.2
172.5°	1525.1	1526.8	1528.5	1529.4	1528.4	1526.4	1524.3	1522.3	1520.3	1520.6	1520.9
175°	1532.9	1534.6	1536.3	1537.2	1536.2	1534.2	1532.1	1530.1	1528.1	1528.7	1529.3
177.5°	1536.8	1538.5	1540.2	1541.1	1540.2	1538.5	1536.8	1535.0	1533.3	1533.9	1534.5
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	993.0	989.3	987.0	988.5	984.0	972.9	972.9	976.6	972.1	967.7	961.0
5°	1020.5	1013.1	1008.6	1007.8	997.4	979.6	975.9	972.1	962.5	952.1	940.9
7.5°	1047.3	1033.9	1026.4	1021.2	1006.4	983.3	973.6	965.5	949.8	934.2	920.1
10°	1069.6	1050.2	1041.3	1033.1	1013.8	984.8	969.2	954.3	934.2	914.1	896.3
12.5°	1087.4	1065.1	1054.0	1042.1	1018.3	980.3	961.0	937.2	917.1	890.3	872.5
15°	1117.2	1071.1	1060.7	1049.5	1025.0	972.9	949.1	922.3	894.8	859.1	839.7
17.5°	1141.0	1079.3	1078.5	1054.7	1022.7	969.9	933.5	898.5	868.8	833.1	802.6
20°	1155.1	1091.9	1080.0	1055.4	1015.3	949.8	911.9	873.2	841.2	798.1	767.6
22.5°	1167.0	1109.7	1078.5	1048.8	999.7	943.1	887.4	850.9	807.0	760.2	731.2
25°	1171.5	1113.5	1080.7	1046.5	988.5	923.8	860.6	821.2	772.1	729.7	690.2
27.5°	1172.2	1112.7	1072.6	1036.9	972.9	898.5	833.8	792.1	737.8	688.8	649.3
30°	1164.8	1104.5	1068.1	1029.4	958.0	875.5	801.1	755.0	696.9	647.8	606.9
32.5°	1142.5	1088.2	1058.4	1016.0	938.7	843.5	769.8	718.5	657.5	609.2	569.7
35°	1105.3	1068.1	1035.4	995.9	913.4	813.7	738.6	678.3	616.6	570.5	533.3
37.5°	1059.2	1039.1	1008.6	969.9	884.4	786.9	703.6	636.7	575.0	530.3	493.9
40°	996.7	1001.9	972.1	937.2	850.2	750.5	658.3	594.3	536.3	494.6	458.9
42.5°	929.0	950.6	933.5	900.0	812.2	710.3	624.8	554.1	497.6	454.5	424.7
45°	856.1	893.3	882.9	858.3	772.8	667.9	577.2	508.8	458.9	417.3	391.2
47.5°	776.5	829.3	829.3	811.5	728.9	625.5	536.3	466.4	417.3	387.5	362.2
50°	695.5	755.0	764.6	752.7	679.8	577.2	486.4	423.2	380.8	351.8	333.2
52.5°	610.7	679.8	697.7	691.7	627.8	531.1	445.5	383.8	345.1	319.8	303.5
55°	529.6	609.9	629.3	631.5	572.0	480.5	400.2	345.9	308.7	291.6	277.4
57.5°	453.0	530.3	551.9	555.6	515.5	434.4	357.8	310.2	276.7	262.6	251.4
60°	387.5	452.2	480.5	488.7	453.7	380.8	318.3	272.2	246.9	233.6	223.1
62.5°	334.0	386.0	415.8	418.0	402.4	334.0	277.4	238.8	217.2	205.3	200.1
65°	281.9	328.8	346.6	355.5	342.9	289.3	239.5	207.5	190.4	180.0	174.8
67.5°	240.2	270.0	284.9	296.8	284.1	244.0	203.8	177.8	165.1	154.7	151.7
70°	197.1	221.7	232.8	244.7	233.6	203.1	174.0	150.2	139.1	130.9	127.2
72.5°	157.7	177.0	187.4	194.9	188.2	162.9	139.1	122.7	114.5	108.6	106.4
75°	125.0	138.3	144.3	149.5	146.5	127.2	112.3	98.9	91.5	86.3	84.8
77.5°	95.2	104.9	111.6	113.1	109.3	96.7	84.0	75.9	69.9	66.9	65.5
80°	67.7	73.6	77.4	79.6	75.9	70.7	61.7	55.8	50.6	46.9	46.1
82.5°	45.4	48.3	51.3	50.6	49.1	44.6	39.4	36.4	34.2	31.2	31.2
85°	26.0	26.8	28.3	29.0	28.3	25.3	22.3	20.8	19.3	17.1	17.1
87.5°	11.2	11.9	11.9	12.6	11.2	11.2	9.7	8.2	8.2	7.4	6.7
90°	26.4	20.1	16.9	15.2	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	39.3	39.0	38.9	37.7	35.4	33.1	30.8	28.5	30.8	33.1	35.4
95°	81.3	80.7	80.4	79.0	76.1	73.2	70.4	67.5	70.4	73.2	76.1
97.5°	126.2	125.1	124.5	123.2	120.6	118.1	115.5	112.9	115.5	118.1	120.6
100°	176.4	175.5	175.1	173.9	171.6	169.3	167.0	164.7	167.0	169.3	171.6
102.5°	228.7	227.6	227.0	226.1	224.4	222.7	220.9	219.2	220.9	222.7	224.4
105°	283.7	283.1	282.8	282.4	281.5	280.6	279.8	278.9	279.8	280.6	281.5
107.5°	343.8	343.8	343.8	343.2	342.1	340.9	339.8	338.6	339.8	340.9	342.1
110°	403.4	403.4	403.4	402.5	400.8	399.1	397.3	395.6	397.3	399.1	400.8

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	465.3	465.6	465.7	464.8	463.1	461.4	459.6	457.9	459.6	461.4	463.1
115°	525.8	526.4	526.7	525.8	524.1	522.4	520.6	518.9	520.6	522.4	524.1
117.5°	588.0	589.5	590.2	589.0	586.7	584.4	582.1	579.8	582.1	584.4	586.7
120°	647.7	650.0	651.2	650.0	647.7	645.4	643.1	640.8	643.1	645.4	647.7
122.5°	707.4	708.9	709.6	708.2	705.3	702.4	699.5	696.6	699.5	702.4	705.3
125°	765.3	766.2	766.6	765.3	762.7	760.2	757.6	755.0	757.6	760.2	762.7
127.5°	824.6	825.7	826.3	824.7	821.5	818.4	815.2	812.0	815.2	818.4	821.5
130°	881.2	881.8	882.1	880.2	876.5	872.7	869.0	865.2	869.0	872.7	876.5
132.5°	938.3	938.0	937.9	936.5	933.6	930.7	927.8	924.9	927.8	930.7	933.6
135°	991.9	991.4	991.1	989.5	986.3	983.2	980.0	976.8	980.0	983.2	986.3
137.5°	1046.4	1045.8	1045.5	1044.2	1041.6	1039.1	1036.5	1033.9	1036.5	1039.1	1041.6
140°	1098.3	1096.8	1096.1	1094.8	1092.2	1089.6	1087.0	1084.4	1087.0	1089.6	1092.2
142.5°	1149.3	1148.4	1148.0	1146.7	1144.1	1141.5	1138.9	1136.3	1138.9	1141.5	1144.1
145°	1197.3	1195.6	1194.7	1193.7	1191.7	1189.6	1187.6	1185.6	1187.6	1189.6	1191.7
147.5°	1243.1	1242.0	1241.4	1240.1	1237.5	1234.9	1232.3	1229.7	1232.3	1234.9	1237.5
150°	1284.6	1283.5	1282.9	1282.0	1280.3	1278.6	1276.8	1275.1	1276.8	1278.6	1280.3
152.5°	1325.3	1323.8	1323.1	1322.2	1320.5	1318.8	1317.0	1315.3	1317.0	1318.8	1320.5
155°	1360.8	1359.9	1359.5	1359.1	1358.2	1357.3	1356.5	1355.6	1356.5	1357.3	1358.2
157.5°	1394.1	1393.5	1393.2	1392.9	1392.3	1391.8	1391.2	1390.6	1391.2	1391.8	1392.3
160°	1424.7	1424.4	1424.3	1424.0	1423.4	1422.9	1422.3	1421.7	1422.3	1422.9	1423.4
162.5°	1450.7	1450.4	1450.3	1450.3	1450.3	1450.3	1450.3	1450.3	1450.3	1450.3	1450.3
165°	1473.6	1473.6	1473.6	1473.7	1474.0	1474.3	1474.6	1474.9	1474.6	1474.3	1474.0
167.5°	1493.1	1493.1	1493.1	1493.5	1494.4	1495.3	1496.1	1497.0	1496.1	1495.3	1494.4
170°	1509.5	1509.8	1509.9	1510.3	1511.2	1512.1	1512.9	1513.8	1512.9	1512.1	1511.2
172.5°	1521.2	1521.5	1521.6	1522.0	1522.9	1523.8	1524.6	1525.5	1524.6	1523.8	1522.9
175°	1529.8	1530.4	1530.7	1531.1	1532.0	1532.9	1533.7	1534.6	1533.7	1532.9	1532.0
177.5°	1535.0	1535.6	1535.9	1536.3	1537.2	1538.1	1538.9	1539.8	1538.9	1538.1	1537.2
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	957.3	961.0	960.2	952.8	944.6	937.9	925.3	926.8	922.3	923.1	927.5
5°	933.5	933.5	930.5	920.1	906.7	899.3	885.1	881.4	872.5	871.7	871.0
7.5°	908.2	904.5	900.7	885.9	869.5	857.6	838.3	833.8	824.9	818.9	815.9
10°	878.4	873.2	865.8	848.7	828.6	813.7	793.6	787.7	770.6	763.1	758.7
12.5°	845.7	842.7	830.8	816.7	784.0	767.6	738.6	744.5	727.4	712.6	710.3
15°	813.0	801.8	795.1	772.1	732.6	725.2	702.1	690.2	674.6	662.7	662.7
17.5°	781.0	763.9	749.0	724.5	695.5	674.6	657.5	651.6	632.2	620.3	618.1
20°	738.6	719.3	715.5	680.6	660.5	637.4	621.1	606.2	592.1	586.9	583.1
22.5°	698.4	676.1	670.2	640.4	620.3	597.3	580.9	570.5	560.1	556.4	549.7
25°	655.3	641.9	633.0	601.0	578.7	557.1	545.9	538.5	528.8	528.1	523.6
27.5°	613.6	601.0	592.1	561.6	545.2	525.1	516.2	508.0	502.8	500.6	498.3
30°	577.9	563.8	553.4	531.1	511.0	494.6	487.2	482.0	479.0	475.3	474.5
32.5°	538.5	530.3	516.2	499.1	483.5	467.8	463.4	459.7	455.2	453.7	453.0
35°	505.0	493.9	485.0	465.6	458.9	445.5	440.3	437.4	431.4	429.9	428.4
37.5°	472.3	461.9	452.2	440.3	427.7	420.2	417.3	412.8	409.8	410.6	409.1
40°	439.6	431.4	424.0	411.3	403.9	400.2	394.2	389.8	388.3	389.0	388.3
42.5°	407.6	400.2	395.7	386.0	378.6	374.9	371.2	366.7	368.9	368.9	371.2
45°	378.6	371.9	368.9	361.5	357.0	351.1	347.4	346.6	349.6	348.8	348.8
47.5°	348.8	346.6	342.9	336.2	330.2	326.5	325.8	325.8	328.8	330.2	329.5
50°	325.8	321.3	316.9	311.7	307.2	305.7	303.5	305.0	307.9	307.9	309.4
52.5°	296.8	293.8	292.3	287.8	284.9	284.9	284.9	285.6	287.8	290.1	289.3
55°	271.5	269.3	267.8	265.5	261.8	262.6	261.8	263.3	265.5	267.8	269.3
57.5°	244.7	244.0	242.5	238.8	238.8	238.0	240.2	241.0	244.7	246.2	248.4
60°	220.9	218.7	218.7	215.7	215.7	215.7	217.9	220.2	223.1	223.9	225.4
62.5°	195.6	195.6	194.9	192.6	192.6	194.9	195.6	198.6	200.1	200.1	202.3
65°	171.8	171.1	170.3	171.1	171.8	171.8	174.0	175.5	177.0	177.8	178.5
67.5°	148.0	147.3	148.8	148.0	149.5	152.5	151.7	154.0	156.2	156.2	156.9
70°	125.7	127.2	126.4	127.9	127.2	128.7	130.9	131.7	131.7	132.4	134.6
72.5°	104.9	104.9	104.9	104.1	104.9	106.4	107.9	108.6	110.1	110.8	113.1
75°	84.8	84.8	83.3	84.8	84.8	86.3	87.8	87.8	87.8	89.3	91.5
77.5°	64.0	64.7	64.0	65.5	65.5	66.2	67.7	66.9	68.4	69.2	69.9
80°	46.9	46.1	46.1	46.1	46.9	46.9	48.3	49.1	49.1	51.3	49.8
82.5°	29.8	30.5	29.8	30.5	30.5	31.2	30.5	31.2	32.0	33.5	32.7
85°	17.1	16.4	16.4	17.1	16.4	16.4	17.1	16.4	17.1	16.4	17.1
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	15.2	16.9	20.1	26.4	32.7	39.1	45.4	44.8	44.2	43.7	43.1
92.5°	37.7	38.9	39.0	39.3	39.6	39.9	40.2	40.5	40.8	41.1	41.4
95°	79.0	80.4	80.7	81.3	81.8	82.4	83.0	83.0	83.0	83.0	83.0
97.5°	123.2	124.5	125.1	126.2	127.4	128.5	129.7	129.7	129.7	129.7	129.7
100°	173.9	175.1	175.5	176.4	177.3	178.1	179.0	179.0	179.0	179.0	179.0
102.5°	226.1	227.0	227.6	228.7	229.9	231.0	232.2	232.5	232.8	233.1	233.4
105°	282.4	282.8	283.1	283.7	284.2	284.8	285.4	286.0	286.6	287.1	287.7
107.5°	343.2	343.8	343.8	343.8	343.8	343.8	343.8	344.1	344.4	344.7	345.0
110°	402.5	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	464.8	465.7	465.6	465.3	465.0	464.7	464.4	463.5	462.7	461.8	460.9
115°	525.8	526.7	526.4	525.8	525.3	524.7	524.1	523.8	523.5	523.2	522.9
117.5°	589.0	590.2	589.5	588.0	586.6	585.1	583.7	582.8	582.0	581.1	580.2
120°	650.0	651.2	650.0	647.7	645.4	643.1	640.8	640.8	640.8	640.8	640.8
122.5°	708.2	709.6	708.9	707.4	706.0	704.5	703.1	702.2	701.4	700.5	699.6
125°	765.3	766.6	766.2	765.3	764.4	763.6	762.7	761.9	761.0	760.2	759.3
127.5°	824.7	826.3	825.7	824.6	823.4	822.3	821.1	819.9	818.8	817.6	816.5
130°	880.2	882.1	881.8	881.2	880.7	880.1	879.5	878.9	878.3	877.8	877.2
132.5°	936.5	937.9	938.0	938.3	938.6	938.9	939.2	937.8	936.3	934.9	933.4
135°	989.5	991.1	991.4	991.9	992.5	993.0	993.6	993.3	993.0	992.7	992.4
137.5°	1044.2	1045.5	1045.8	1046.4	1046.9	1047.5	1048.1	1047.8	1047.5	1047.2	1046.9
140°	1094.8	1096.1	1096.8	1098.3	1099.7	1101.2	1102.6	1102.6	1102.6	1102.6	1102.6
142.5°	1146.7	1148.0	1148.4	1149.3	1150.2	1151.0	1151.9	1152.2	1152.5	1152.8	1153.1
145°	1193.7	1194.7	1195.6	1197.3	1199.0	1200.8	1202.5	1202.8	1203.1	1203.4	1203.7
147.5°	1240.1	1241.4	1242.0	1243.1	1244.3	1245.4	1246.6	1247.2	1247.8	1248.3	1248.9
150°	1282.0	1282.9	1283.5	1284.6	1285.8	1286.9	1288.1	1289.0	1289.8	1290.7	1291.6
152.5°	1322.2	1323.1	1323.8	1325.3	1326.7	1328.2	1329.6	1330.8	1331.9	1333.1	1334.2
155°	1359.1	1359.5	1359.9	1360.8	1361.6	1362.5	1363.3	1364.7	1366.2	1367.6	1369.1
157.5°	1392.9	1393.2	1393.5	1394.1	1394.6	1395.2	1395.8	1397.8	1399.8	1401.9	1403.9
160°	1424.0	1424.3	1424.4	1424.7	1425.0	1425.3	1425.6	1427.3	1429.1	1430.8	1432.5
162.5°	1450.3	1450.3	1450.4	1450.7	1451.0	1451.3	1451.6	1453.6	1455.6	1457.6	1459.6
165°	1473.7	1473.6	1473.6	1473.6	1473.6	1473.6	1473.6	1475.6	1477.6	1479.7	1481.7
167.5°	1493.5	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1495.1	1497.1	1499.1	1501.1
170°	1510.3	1509.9	1509.8	1509.5	1509.2	1508.9	1508.6	1510.6	1512.6	1514.7	1516.7
172.5°	1522.0	1521.6	1521.5	1521.2	1520.9	1520.6	1520.3	1522.3	1524.3	1526.4	1528.4
175°	1531.1	1530.7	1530.4	1529.8	1529.3	1528.7	1528.1	1530.1	1532.1	1534.2	1536.2
177.5°	1536.3	1535.9	1535.6	1535.0	1534.5	1533.9	1533.3	1535.0	1536.8	1538.5	1540.2
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	922.3	924.5	919.3	917.8	919.3	914.1	915.6	917.1	917.1	919.3	920.8
5°	868.8	865.8	860.6	859.1	857.6	859.8	858.3	860.6	861.3	866.5	867.3
7.5°	815.9	811.5	807.0	802.6	801.1	797.4	801.1	801.1	806.3	804.8	808.5
10°	753.5	752.7	746.8	744.5	741.6	735.6	743.8	741.6	745.3	752.0	753.5
12.5°	707.4	699.2	702.9	692.5	696.2	690.2	691.0	691.0	696.9	697.7	696.2
15°	663.5	656.8	647.1	642.6	640.4	637.4	647.1	647.8	643.4	653.8	650.1
17.5°	618.8	618.8	609.9	607.7	601.7	604.7	603.2	604.0	602.5	609.9	613.6
20°	580.2	576.4	573.5	574.2	566.8	565.3	563.8	565.3	570.5	575.7	577.2
22.5°	548.9	546.7	539.3	540.7	534.8	537.0	535.5	539.3	540.0	540.0	545.2
25°	519.2	516.2	516.9	514.0	511.7	511.7	509.5	511.7	514.7	516.2	516.9
27.5°	496.9	494.6	490.9	488.7	490.2	486.4	489.4	491.7	491.7	490.2	491.7
30°	470.1	471.6	471.6	464.1	467.1	465.6	467.8	469.3	469.3	470.1	468.6
32.5°	452.2	447.8	447.0	446.3	446.3	443.3	443.3	445.5	446.3	447.0	449.3
35°	428.4	428.4	424.7	426.9	424.0	424.7	424.0	424.7	426.2	424.0	426.2
37.5°	406.9	407.6	406.1	407.6	408.3	406.9	405.4	408.3	406.9	406.9	405.4
40°	388.3	387.5	388.3	388.3	388.3	389.0	387.5	387.5	387.5	386.0	384.5
42.5°	372.6	368.2	369.7	370.4	368.2	368.2	368.9	368.2	370.4	365.9	365.9
45°	350.3	348.8	349.6	349.6	351.1	348.8	350.3	351.1	348.8	348.1	346.6
47.5°	330.2	331.7	330.2	331.7	331.7	333.2	330.2	331.0	331.7	328.8	326.5
50°	310.2	310.2	312.4	311.7	312.4	310.9	310.9	310.2	310.9	309.4	307.2
52.5°	291.6	289.3	293.1	292.3	291.6	290.8	290.1	290.8	289.3	287.8	287.8
55°	268.5	268.5	270.7	271.5	271.5	270.0	268.5	269.3	268.5	267.8	267.0
57.5°	249.9	246.9	248.4	249.2	249.2	246.9	248.4	246.9	246.9	247.7	245.5
60°	226.1	226.1	224.6	226.9	226.9	225.4	225.4	226.1	224.6	223.9	223.1
62.5°	200.8	201.6	203.8	204.5	205.3	203.8	202.3	203.1	203.1	200.8	201.6
65°	179.3	180.7	183.7	183.0	181.5	182.2	180.7	181.5	179.3	180.0	177.8
67.5°	158.4	157.7	158.4	158.4	159.9	159.2	157.7	157.7	156.9	159.2	156.9
70°	136.1	136.1	136.1	136.1	136.9	137.6	136.1	134.6	135.4	133.9	133.1
72.5°	113.1	113.8	113.1	114.5	112.3	113.8	113.8	113.1	112.3	112.3	112.3
75°	91.5	93.0	90.7	91.5	90.7	92.2	91.5	91.5	90.0	89.3	90.0
77.5°	69.9	70.7	69.2	69.9	69.2	69.9	69.9	69.2	69.2	69.2	69.2
80°	49.8	50.6	49.8	49.1	48.3	49.8	48.3	49.1	49.8	49.1	50.6
82.5°	32.0	32.0	31.2	32.0	30.5	30.5	31.2	31.2	30.5	32.0	30.5
85°	15.6	15.6	17.1	15.6	14.9	14.9	14.9	15.6	14.9	16.4	15.6
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	42.8	42.9	43.2	43.5	43.8	44.1	43.8	43.5	43.2	42.9	42.8
92.5°	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5	41.5
95°	83.0	82.7	82.1	81.6	81.0	80.4	81.0	81.6	82.1	82.7	83.0
97.5°	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7	129.7
100°	179.0	178.9	178.6	178.3	178.0	177.7	178.0	178.3	178.6	178.9	179.0
102.5°	233.5	233.4	233.1	232.8	232.5	232.2	232.5	232.8	233.1	233.4	233.5
105°	288.0	288.0	288.0	288.0	288.0	288.0	288.0	288.0	288.0	288.0	288.0
107.5°	345.1	344.4	342.9	341.5	340.0	338.6	340.0	341.5	342.9	344.4	345.1
110°	403.4	403.0	402.1	401.2	400.4	399.5	400.4	401.2	402.1	403.0	403.4

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	460.5	460.2	459.6	459.1	458.5	457.9	458.5	459.1	459.6	460.2	460.5
115°	522.8	522.4	521.5	520.6	519.8	518.9	519.8	520.6	521.5	522.4	522.8
117.5°	579.8	579.4	578.5	577.7	576.8	576.0	576.8	577.7	578.5	579.4	579.8
120°	640.8	640.4	639.5	638.6	637.8	636.9	637.8	638.6	639.5	640.4	640.8
122.5°	699.2	698.9	698.3	697.8	697.2	696.6	697.2	697.8	698.3	698.9	699.2
125°	758.9	758.8	758.5	758.2	757.9	757.6	757.9	758.2	758.5	758.8	758.9
127.5°	815.9	815.5	814.6	813.7	812.9	812.0	812.9	813.7	814.6	815.5	815.9
130°	876.9	876.3	875.2	874.0	872.9	871.7	872.9	874.0	875.2	876.3	876.9
132.5°	932.7	932.3	931.4	930.5	929.7	928.8	929.7	930.5	931.4	932.3	932.7
135°	992.3	991.9	991.0	990.2	989.3	988.5	989.3	990.2	991.0	991.9	992.3
137.5°	1046.8	1046.2	1045.1	1043.9	1042.8	1041.6	1042.8	1043.9	1045.1	1046.2	1046.8
140°	1102.6	1102.0	1100.9	1099.7	1098.6	1097.4	1098.6	1099.7	1100.9	1102.0	1102.6
142.5°	1153.2	1152.6	1151.5	1150.3	1149.2	1148.0	1149.2	1150.3	1151.5	1152.6	1153.2
145°	1203.8	1203.2	1202.1	1200.9	1199.8	1198.6	1199.8	1200.9	1202.1	1203.2	1203.8
147.5°	1249.2	1248.6	1247.5	1246.3	1245.2	1244.0	1245.2	1246.3	1247.5	1248.6	1249.2
150°	1292.0	1291.6	1290.7	1289.8	1289.0	1288.1	1289.0	1289.8	1290.7	1291.6	1292.0
152.5°	1334.8	1334.2	1333.1	1331.9	1330.8	1329.6	1330.8	1331.9	1333.1	1334.2	1334.8
155°	1369.8	1369.4	1368.5	1367.6	1366.8	1365.9	1366.8	1367.6	1368.5	1369.4	1369.8
157.5°	1404.9	1404.2	1402.7	1401.3	1399.8	1398.4	1399.8	1401.3	1402.7	1404.2	1404.9
160°	1433.4	1432.8	1431.7	1430.5	1429.4	1428.2	1429.4	1430.5	1431.7	1432.8	1433.4
162.5°	1460.6	1459.9	1458.4	1457.0	1455.5	1454.1	1455.5	1457.0	1458.4	1459.9	1460.6
165°	1482.7	1482.0	1480.5	1479.1	1477.6	1476.2	1477.6	1479.1	1480.5	1482.0	1482.7
167.5°	1502.1	1501.4	1500.0	1498.5	1497.1	1495.7	1497.1	1498.5	1500.0	1501.4	1502.1
170°	1517.7	1516.8	1515.1	1513.4	1511.6	1509.9	1511.6	1513.4	1515.1	1516.8	1517.7
172.5°	1529.4	1528.5	1526.8	1525.1	1523.3	1521.6	1523.3	1525.1	1526.8	1528.5	1529.4
175°	1537.2	1536.3	1534.6	1532.9	1531.1	1529.4	1531.1	1532.9	1534.6	1536.3	1537.2
177.5°	1541.1	1540.2	1538.5	1536.8	1535.0	1533.3	1535.0	1536.8	1538.5	1540.2	1541.1
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7	967.7
2.5°	918.6	924.5	922.3	914.1	923.8	923.8	930.5	930.5	938.7	941.6	946.1
5°	866.5	871.0	874.7	871.0	877.7	888.1	894.0	899.3	910.4	914.9	921.6
7.5°	810.7	818.9	822.6	822.6	833.8	845.7	857.6	865.0	880.7	886.6	893.3
10°	756.4	766.1	773.6	772.8	791.4	798.8	813.7	830.8	846.4	855.4	865.0
12.5°	699.2	704.4	714.8	729.7	734.1	747.5	764.6	786.2	814.5	822.6	836.8
15°	651.6	665.7	673.9	680.6	691.0	703.6	722.2	743.1	771.3	789.2	804.0
17.5°	611.4	630.0	635.2	633.7	647.1	666.4	688.0	703.6	728.9	750.5	764.6
20°	578.7	586.1	595.0	598.8	609.2	630.0	650.8	668.7	689.5	706.6	723.0
22.5°	545.9	551.9	559.3	566.0	574.2	586.1	606.2	628.5	648.6	665.0	683.6
25°	519.2	522.9	529.6	534.8	543.7	551.9	566.0	590.6	614.4	624.0	640.4
27.5°	493.1	496.1	500.6	506.5	511.0	519.2	531.8	551.9	576.4	586.1	608.4
30°	470.1	472.3	476.8	479.7	482.0	491.7	501.3	516.9	535.5	548.9	565.3
32.5°	448.5	450.7	455.2	455.9	458.9	464.1	473.1	487.2	503.6	514.7	528.8
35°	424.7	426.2	430.7	432.1	434.4	438.8	445.5	455.9	470.8	479.0	491.7
37.5°	406.1	405.4	408.3	410.6	413.6	415.8	418.0	428.4	439.6	447.0	456.7
40°	386.0	384.5	385.3	388.3	389.8	392.7	392.7	403.1	410.6	416.5	424.0
42.5°	365.9	365.2	363.7	365.2	366.7	367.4	368.2	375.6	383.1	388.3	396.4
45°	345.9	345.1	343.6	344.4	344.4	345.9	348.1	351.1	356.3	360.7	365.2
47.5°	327.3	325.8	323.6	322.8	324.3	324.3	324.3	327.3	332.5	334.0	338.4
50°	307.9	305.7	302.7	301.2	301.2	300.5	302.0	302.7	307.2	308.7	312.4
52.5°	287.1	285.6	282.6	279.7	280.4	278.9	279.7	280.4	281.9	284.1	286.4
55°	266.3	263.3	261.1	260.3	258.1	258.1	255.9	258.8	258.1	258.8	261.8
57.5°	246.2	243.2	239.5	238.0	235.8	235.0	233.6	232.8	233.6	235.8	238.0
60°	222.4	220.9	218.7	216.4	215.0	212.7	211.2	211.2	210.5	210.5	211.2
62.5°	199.3	198.6	195.6	194.9	193.4	191.9	189.7	188.2	188.2	189.7	190.4
65°	177.0	176.3	174.0	173.3	169.6	168.1	167.4	166.6	165.1	165.1	165.1
67.5°	156.2	154.0	154.0	150.2	147.3	145.8	144.3	143.6	143.6	143.6	144.3
70°	133.1	133.1	130.9	128.7	125.7	126.4	124.2	122.0	122.0	120.5	121.2
72.5°	110.8	110.1	107.9	107.1	104.9	102.6	101.2	102.6	100.4	99.7	100.4
75°	89.3	88.5	87.0	85.5	86.3	84.0	81.8	81.1	81.1	79.6	79.6
77.5°	68.4	69.9	66.9	66.2	64.7	63.2	62.5	61.7	61.7	61.7	63.2
80°	47.6	48.3	48.3	46.9	47.6	45.4	45.4	45.4	43.1	43.9	44.6
82.5°	30.5	30.5	29.8	30.5	29.8	29.8	29.0	29.0	28.3	28.3	29.0
85°	17.1	16.4	15.6	17.1	16.4	16.4	15.6	15.6	15.6	15.6	15.6
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	43.1	43.7	44.2	44.8	45.4	39.1	32.7	26.4	20.1	16.9	15.2
92.5°	41.4	41.1	40.8	40.5	40.2	39.9	39.6	39.3	39.0	38.9	37.7
95°	83.0	83.0	83.0	83.0	83.0	82.4	81.8	81.3	80.7	80.4	79.0
97.5°	129.7	129.7	129.7	129.7	129.7	128.5	127.4	126.2	125.1	124.5	123.2
100°	179.0	179.0	179.0	179.0	179.0	178.1	177.3	176.4	175.5	175.1	173.9
102.5°	233.4	233.1	232.8	232.5	232.2	231.0	229.9	228.7	227.6	227.0	226.1
105°	287.7	287.1	286.6	286.0	285.4	284.8	284.2	283.7	283.1	282.8	282.4
107.5°	345.0	344.7	344.4	344.1	343.8	343.8	343.8	343.8	343.8	343.8	343.2
110°	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	403.4	402.5

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	460.9	461.8	462.7	463.5	464.4	464.7	465.0	465.3	465.6	465.7	464.8
115°	522.9	523.2	523.5	523.8	524.1	524.7	525.3	525.8	526.4	526.7	525.8
117.5°	580.2	581.1	582.0	582.8	583.7	585.1	586.6	588.0	589.5	590.2	589.0
120°	640.8	640.8	640.8	640.8	640.8	643.1	645.4	647.7	650.0	651.2	650.0
122.5°	699.6	700.5	701.4	702.2	703.1	704.5	706.0	707.4	708.9	709.6	708.2
125°	759.3	760.2	761.0	761.9	762.7	763.6	764.4	765.3	766.2	766.6	765.3
127.5°	816.5	817.6	818.8	819.9	821.1	822.3	823.4	824.6	825.7	826.3	824.7
130°	877.2	877.8	878.3	878.9	879.5	880.1	880.7	881.2	881.8	882.1	880.2
132.5°	933.4	934.9	936.3	937.8	939.2	938.9	938.6	938.3	938.0	937.9	936.5
135°	992.4	992.7	993.0	993.3	993.6	993.0	992.5	991.9	991.4	991.1	989.5
137.5°	1046.9	1047.2	1047.5	1047.8	1048.1	1047.5	1046.9	1046.4	1045.8	1045.5	1044.2
140°	1102.6	1102.6	1102.6	1102.6	1102.6	1101.2	1099.7	1098.3	1096.8	1096.1	1094.8
142.5°	1153.1	1152.8	1152.5	1152.2	1151.9	1151.0	1150.2	1149.3	1148.4	1148.0	1146.7
145°	1203.7	1203.4	1203.1	1202.8	1202.5	1200.8	1199.0	1197.3	1195.6	1194.7	1193.7
147.5°	1248.9	1248.3	1247.8	1247.2	1246.6	1245.4	1244.3	1243.1	1242.0	1241.4	1240.1
150°	1291.6	1290.7	1289.8	1289.0	1288.1	1286.9	1285.8	1284.6	1283.5	1282.9	1282.0
152.5°	1334.2	1333.1	1331.9	1330.8	1329.6	1328.2	1326.7	1325.3	1323.8	1323.1	1322.2
155°	1369.1	1367.6	1366.2	1364.7	1363.3	1362.5	1361.6	1360.8	1359.9	1359.5	1359.1
157.5°	1403.9	1401.9	1399.8	1397.8	1395.8	1395.2	1394.6	1394.1	1393.5	1393.2	1392.9
160°	1432.5	1430.8	1429.1	1427.3	1425.6	1425.3	1425.0	1424.7	1424.4	1424.3	1424.0
162.5°	1459.6	1457.6	1455.6	1453.6	1451.6	1451.3	1451.0	1450.7	1450.4	1450.3	1450.3
165°	1481.7	1479.7	1477.6	1475.6	1473.6	1473.6	1473.6	1473.6	1473.6	1473.6	1473.7
167.5°	1501.1	1499.1	1497.1	1495.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.1	1493.5
170°	1516.7	1514.7	1512.6	1510.6	1508.6	1508.9	1509.2	1509.5	1509.8	1509.9	1510.3
172.5°	1528.4	1526.4	1524.3	1522.3	1520.3	1520.6	1520.9	1521.2	1521.5	1521.6	1522.0
175°	1536.2	1534.2	1532.1	1530.1	1528.1	1528.7	1529.3	1529.8	1530.4	1530.7	1531.1
177.5°	1540.2	1538.5	1536.8	1535.0	1533.3	1533.9	1534.5	1535.0	1535.6	1535.9	1536.3
180°	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2	1537.2

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	967.7	967.7	967.7	967.7
2.5°	949.8	949.8	961.0	972.9
5°	929.0	934.2	952.1	968.4
7.5°	908.9	917.8	940.2	961.0
10°	884.4	896.3	923.8	948.3
12.5°	860.6	871.7	903.7	931.2
15°	827.1	841.2	875.5	909.7
17.5°	793.6	807.8	849.4	889.6
20°	754.2	772.8	819.7	873.2
22.5°	717.8	740.8	792.9	836.0
25°	677.6	713.3	761.6	817.4
27.5°	641.9	677.6	726.7	783.2
30°	601.7	638.2	688.8	740.8
32.5°	563.1	596.5	645.6	709.6
35°	522.9	554.9	602.5	667.2
37.5°	486.4	517.7	569.7	629.3
40°	450.7	483.5	528.1	587.6
42.5°	417.3	446.3	486.4	545.9
45°	386.8	407.6	444.8	500.6
47.5°	354.8	373.4	407.6	463.4
50°	325.0	340.7	370.4	422.5
52.5°	296.0	309.4	336.9	378.6
55°	270.0	282.6	302.7	343.6
57.5°	243.2	252.9	272.2	305.0
60°	217.2	226.1	241.7	268.5
62.5°	191.2	198.6	213.5	235.0
65°	168.1	174.0	185.2	203.8
67.5°	145.8	149.5	158.4	173.3
70°	124.2	127.2	134.6	146.5
72.5°	101.2	104.1	112.3	120.5
75°	81.8	82.6	88.5	95.2
77.5°	64.0	63.2	67.7	72.9
80°	43.9	46.1	49.8	52.1
82.5°	29.8	30.5	32.0	33.5
85°	16.4	17.1	17.1	19.3
87.5°	6.7	7.4	7.4	8.2
90°	11.7	8.2	4.8	1.3
92.5°	35.4	33.1	30.8	28.5
95°	76.1	73.2	70.4	67.5
97.5°	120.6	118.1	115.5	112.9
100°	171.6	169.3	167.0	164.7
102.5°	224.4	222.7	220.9	219.2
105°	281.5	280.6	279.8	278.9
107.5°	342.1	340.9	339.8	338.6
110°	400.8	399.1	397.3	395.6

TEST NUMBER: P1029449

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	463.1	461.4	459.6	457.9
115°	524.1	522.4	520.6	518.9
117.5°	586.7	584.4	582.1	579.8
120°	647.7	645.4	643.1	640.8
122.5°	705.3	702.4	699.5	696.6
125°	762.7	760.2	757.6	755.0
127.5°	821.5	818.4	815.2	812.0
130°	876.5	872.7	869.0	865.2
132.5°	933.6	930.7	927.8	924.9
135°	986.3	983.2	980.0	976.8
137.5°	1041.6	1039.1	1036.5	1033.9
140°	1092.2	1089.6	1087.0	1084.4
142.5°	1144.1	1141.5	1138.9	1136.3
145°	1191.7	1189.6	1187.6	1185.6
147.5°	1237.5	1234.9	1232.3	1229.7
150°	1280.3	1278.6	1276.8	1275.1
152.5°	1320.5	1318.8	1317.0	1315.3
155°	1358.2	1357.3	1356.5	1355.6
157.5°	1392.3	1391.8	1391.2	1390.6
160°	1423.4	1422.9	1422.3	1421.7
162.5°	1450.3	1450.3	1450.3	1450.3
165°	1474.0	1474.3	1474.6	1474.9
167.5°	1494.4	1495.3	1496.1	1497.0
170°	1511.2	1512.1	1512.9	1513.8
172.5°	1522.9	1523.8	1524.6	1525.5
175°	1532.0	1532.9	1533.7	1534.6
177.5°	1537.2	1538.1	1538.9	1539.8
180°	1537.2	1537.2	1537.2	1537.2

(END OF REPORT)