

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029450

Luminaire Tested: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029450
REPORT IS A COMBINATION OF REPORTS P985929 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K
Description: Define 2 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6465.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41			33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	36	36	35			29
2	86	79	73	68	77	72	67	63	57	54	51	44	42	40	32	31	30			24
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26			21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22			18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20			16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18			14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16			13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14			12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13			11
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15383	15383	15383	15383
5°	15419	16401	15478	13049
10°	15240	17905	15336	10758
15°	14871	18885	15077	9062
20°	14638	17732	14638	7877
25°	14172	15233	14236	7044
30°	13404	11974	13659	6380
35°	12724	8280	12937	5837
40°	11943	6252	12079	5404
45°	10979	5138	11158	4937
50°	10147	4510	10163	4520
55°	9196	3842	9254	4066
60°	8181	3210	8296	3549
65°	7277	2610	7408	3031
70°	6370	2049	6535	2445
75°	5348	1487	5555	1772
80°	4176	942	4471	1051
85°	2740	475	2952	350

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15901 cd/sqm

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	1.4
10°-20°	269.4	4.2
20°-30°	391.0	6.0
30°-40°	412.2	6.4
40°-50°	364.7	5.6
50°-60°	291.2	4.5
60°-70°	197.8	3.1
70°-80°	101.2	1.6
80°-90°	28.3	0.4
90°-100°	95.5	1.5
100°-110°	303.6	4.7
110°-120°	519.5	8.0
120°-130°	683.3	10.6
130°-140°	767.0	11.9
140°-150°	752.1	11.6
150°-160°	630.9	9.8
160°-170°	418.4	6.5
170°-180°	146.2	2.3
0°-30°	752.9	11.6
0°-40°	1165.1	18.0
0°-60°	1821.1	28.2
0°-90°	2148.4	33.2
90°-120°	918.7	14.2
90°-150°	3121.1	48.3
90°-180°	4317.0	66.8
0°-180°	6465.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	972	1085	976	864	972	92
15°	914	1334	926	640	914	258
25°	821	1111	825	514	821	375
35°	670	605	681	426	670	419
45°	503	364	511	350	503	390
55°	345	256	347	271	345	308
65°	205	158	208	183	205	203
75°	96	78	99	93	96	103
85°	19	20	21	15	19	23
90°	1	44	1	44	1	5
95°	68	81	68	81	68	76
105°	280	289	280	289	280	296
115°	521	521	521	521	521	516
125°	758	761	758	761	758	678
135°	981	993	981	993	981	758
145°	1191	1204	1191	1204	1191	744
155°	1362	1372	1362	1372	1362	627
165°	1481	1483	1481	1483	1481	418
175°	1541	1536	1541	1536	1541	146
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	977.0	979.2	983.0	983.7	991.2	997.2	1003.9	1003.9	1006.1	1005.4	999.4
5°	972.5	979.2	988.9	997.2	1010.6	1016.6	1025.5	1032.3	1038.2	1042.7	1042.0
7.5°	965.0	977.0	991.2	1006.9	1024.8	1035.3	1047.9	1059.9	1068.1	1075.6	1080.8
10°	952.3	972.5	991.9	1012.8	1036.0	1050.2	1065.1	1080.8	1093.5	1107.7	1121.1
12.5°	935.2	964.3	988.2	1015.8	1044.2	1059.9	1083.8	1095.8	1120.4	1156.3	1166.0
15°	913.5	953.1	975.5	1010.6	1047.9	1060.6	1093.5	1112.9	1163.7	1186.1	1213.0
17.5°	893.3	937.4	967.3	1007.6	1044.2	1068.9	1101.0	1140.6	1183.1	1215.3	1245.1
20°	876.9	919.5	955.3	1000.1	1046.5	1077.8	1111.4	1159.2	1205.6	1238.4	1261.6
22.5°	839.6	894.1	935.9	986.0	1042.0	1085.3	1117.4	1169.7	1219.7	1239.9	1260.1
25°	820.9	867.9	916.5	973.3	1039.0	1090.5	1118.2	1176.4	1220.5	1228.0	1232.4
27.5°	786.5	839.6	896.3	961.3	1038.2	1081.6	1116.7	1169.7	1204.8	1199.6	1186.1
30°	743.9	808.9	871.7	941.9	1027.8	1074.8	1107.7	1156.3	1174.2	1147.3	1123.4
32.5°	712.6	773.8	843.3	924.7	1015.8	1060.6	1092.8	1130.9	1134.6	1086.0	1045.7
35°	670.0	738.0	816.4	902.3	995.7	1036.0	1065.9	1089.0	1071.1	1003.1	955.3
37.5°	631.9	699.1	782.8	870.2	968.0	1007.6	1031.5	1035.3	991.2	931.4	861.2
40°	590.1	659.5	746.9	838.8	937.4	971.8	986.7	975.5	912.0	842.5	761.1
42.5°	548.2	617.0	711.1	805.2	898.6	927.7	933.7	903.0	825.4	743.9	649.8
45°	502.7	574.4	668.5	763.4	853.7	870.2	870.9	826.9	735.0	649.8	562.4
47.5°	465.3	531.8	625.2	720.0	796.2	807.4	803.0	752.2	652.1	556.5	480.3
50°	424.3	487.7	580.4	673.7	738.7	741.7	730.5	658.0	560.2	472.8	412.3
52.5°	380.2	444.4	529.6	619.2	677.5	673.0	651.3	573.6	481.8	409.3	363.0
55°	345.1	401.9	481.8	569.2	610.2	597.5	573.6	494.5	422.0	360.8	320.4
57.5°	306.2	356.3	434.7	510.9	534.8	522.9	499.0	425.0	357.8	311.5	284.6
60°	269.6	315.2	383.9	447.4	466.1	453.4	425.8	359.3	310.7	271.9	251.7
62.5°	236.0	275.6	333.1	391.4	398.9	386.2	362.3	308.5	266.7	236.0	221.1
65°	204.7	242.0	288.3	332.4	339.1	325.7	301.0	262.2	227.1	207.6	193.5
67.5°	174.0	203.9	245.0	277.1	280.8	268.1	248.0	216.6	194.9	174.0	163.6
70°	147.1	169.6	201.7	227.8	229.3	217.4	206.9	178.5	162.1	147.1	138.9
72.5°	121.0	136.7	161.3	180.8	181.5	174.0	164.3	146.4	132.2	121.8	113.5
75°	95.6	109.1	124.0	141.2	140.4	134.4	127.0	115.8	103.8	97.1	93.4
77.5°	73.2	81.4	93.4	104.6	104.6	101.6	97.1	88.9	81.4	74.7	71.0
80°	52.3	57.5	67.2	71.0	72.5	71.7	68.0	62.0	59.0	53.8	52.3
82.5°	33.6	37.3	41.8	45.6	47.8	46.3	45.6	42.6	38.1	36.6	35.1
85°	19.4	20.9	23.2	25.4	26.1	25.4	26.9	24.6	22.4	22.4	21.7
87.5°	8.2	9.0	10.5	10.5	11.2	11.2	10.5	11.2	11.2	10.5	9.7
90°	1.3	4.8	8.2	11.7	15.2	16.9	20.1	26.5	32.8	39.2	45.6
92.5°	28.7	31.0	33.3	35.6	37.9	39.1	39.2	39.5	39.8	40.1	40.4
95°	67.8	70.7	73.6	76.5	79.4	80.8	81.1	81.7	82.2	82.8	83.4
97.5°	113.4	116.0	118.6	121.2	123.8	125.1	125.7	126.8	128.0	129.1	130.3
100°	165.5	167.8	170.1	172.4	174.7	175.9	176.3	177.2	178.1	178.9	179.8
102.5°	220.2	221.9	223.7	225.4	227.1	228.0	228.6	229.7	230.9	232.0	233.2
105°	280.1	281.0	281.8	282.7	283.6	284.0	284.3	284.9	285.4	286.0	286.6
107.5°	340.1	341.3	342.4	343.6	344.7	345.3	345.3	345.3	345.3	345.3	345.3
110°	397.4	399.1	400.9	402.6	404.3	405.2	405.2	405.2	405.2	405.2	405.2

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	459.9	461.6	463.4	465.1	466.8	467.7	467.6	467.3	467.0	466.7	466.4
115°	521.2	522.9	524.7	526.4	528.1	529.0	528.7	528.1	527.6	527.0	526.4
117.5°	582.4	584.7	587.0	589.3	591.6	592.8	592.1	590.6	589.2	587.7	586.3
120°	643.6	645.9	648.3	650.6	652.9	654.1	652.9	650.6	648.3	645.9	643.6
122.5°	699.7	702.6	705.5	708.4	711.3	712.7	712.0	710.5	709.1	707.6	706.2
125°	758.3	760.9	763.5	766.1	768.7	770.0	769.6	768.7	767.8	767.0	766.1
127.5°	815.6	818.8	822.0	825.2	828.4	830.0	829.4	828.2	827.1	825.9	824.7
130°	869.0	872.8	876.6	880.3	884.1	886.0	885.7	885.1	884.6	884.0	883.4
132.5°	929.0	931.9	934.8	937.7	940.6	942.0	942.1	942.4	942.7	943.0	943.3
135°	981.1	984.3	987.5	990.6	993.8	995.4	995.7	996.3	996.8	997.4	998.0
137.5°	1038.4	1041.0	1043.6	1046.3	1048.9	1050.2	1050.5	1051.1	1051.6	1052.2	1052.8
140°	1089.2	1091.8	1094.4	1097.1	1099.7	1101.0	1101.7	1103.2	1104.6	1106.1	1107.5
142.5°	1141.4	1144.0	1146.6	1149.2	1151.8	1153.1	1153.5	1154.4	1155.3	1156.1	1157.0
145°	1190.9	1192.9	1194.9	1197.0	1199.0	1200.0	1200.9	1202.6	1204.3	1206.1	1207.8
147.5°	1235.2	1237.8	1240.4	1243.0	1245.6	1246.9	1247.5	1248.6	1249.8	1250.9	1252.1
150°	1280.8	1282.5	1284.3	1286.0	1287.7	1288.6	1289.2	1290.3	1291.5	1292.6	1293.8
152.5°	1321.2	1322.9	1324.7	1326.4	1328.1	1329.0	1329.7	1331.2	1332.6	1334.1	1335.5
155°	1361.5	1362.4	1363.3	1364.2	1365.1	1365.5	1365.9	1366.8	1367.7	1368.5	1369.4
157.5°	1396.7	1397.3	1397.9	1398.4	1399.0	1399.3	1399.6	1400.2	1400.7	1401.3	1401.9
160°	1428.0	1428.6	1429.2	1429.7	1430.3	1430.6	1430.7	1431.0	1431.3	1431.6	1431.9
162.5°	1456.7	1456.7	1456.7	1456.7	1456.7	1456.7	1456.8	1457.1	1457.4	1457.7	1458.0
165°	1481.4	1481.1	1480.8	1480.5	1480.2	1480.1	1480.1	1480.1	1480.1	1480.1	1480.1
167.5°	1503.6	1502.7	1501.9	1501.0	1500.1	1499.7	1499.7	1499.7	1499.7	1499.7	1499.7
170°	1520.5	1519.6	1518.8	1517.9	1517.0	1516.6	1516.5	1516.2	1515.9	1515.6	1515.3
172.5°	1532.2	1531.3	1530.5	1529.6	1528.7	1528.3	1528.2	1527.9	1527.6	1527.3	1527.0
175°	1541.3	1540.4	1539.6	1538.7	1537.8	1537.4	1537.1	1536.5	1536.0	1535.4	1534.8
177.5°	1546.6	1545.7	1544.9	1544.0	1543.1	1542.7	1542.4	1541.8	1541.2	1540.6	1540.0
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1009.9	1010.6	1012.1	1019.6	1023.3	1024.0	1021.1	1027.8	1030.0	1027.8	1026.3
5°	1057.7	1062.1	1071.1	1080.8	1080.1	1080.8	1085.3	1089.8	1091.3	1085.3	1087.5
7.5°	1099.5	1108.4	1118.2	1133.1	1133.1	1140.6	1143.6	1147.3	1156.3	1151.8	1150.3
10°	1147.3	1159.2	1177.2	1201.1	1201.8	1209.3	1216.8	1228.7	1232.4	1229.5	1230.9
12.5°	1207.0	1230.2	1231.7	1257.8	1269.8	1271.3	1283.2	1281.0	1288.5	1288.5	1301.2
15°	1233.2	1269.0	1289.2	1314.6	1322.1	1313.1	1322.8	1333.3	1334.0	1334.0	1333.3
17.5°	1280.2	1294.4	1314.6	1328.0	1331.0	1331.0	1331.8	1336.3	1333.3	1327.3	1331.8
20°	1290.0	1295.9	1303.4	1301.9	1303.4	1295.9	1288.5	1281.0	1281.7	1278.0	1289.2
22.5°	1272.0	1270.5	1253.4	1242.2	1242.2	1227.2	1213.0	1206.3	1199.6	1201.8	1205.6
25°	1227.2	1204.1	1183.1	1166.7	1163.0	1139.1	1119.7	1113.7	1102.5	1111.4	1112.9
27.5°	1155.5	1129.4	1095.8	1081.6	1062.1	1052.4	1039.0	1021.1	997.9	1011.3	1009.1
30°	1078.6	1039.7	1012.1	977.7	947.1	944.9	919.5	889.6	877.6	877.6	884.4
32.5°	992.7	941.1	900.8	852.3	822.4	809.7	779.1	749.2	755.9	733.5	741.7
35°	892.6	824.6	773.8	726.8	704.4	689.4	649.8	633.4	615.5	605.0	624.4
37.5°	797.0	718.6	653.6	602.0	593.8	566.9	540.0	529.6	519.1	523.6	522.9
40°	680.5	611.0	552.7	512.4	498.2	485.5	467.6	454.9	448.2	451.9	452.6
42.5°	575.1	516.9	473.6	445.2	433.2	424.3	415.3	404.8	402.6	402.6	405.6
45°	493.7	445.9	416.8	393.6	386.9	380.2	373.5	369.0	367.5	364.5	366.7
47.5°	428.7	390.6	372.7	355.5	348.1	346.6	340.6	338.4	335.4	334.6	335.4
50°	374.2	350.3	333.9	324.2	318.9	316.7	313.7	309.2	307.7	311.5	310.0
52.5°	336.1	313.7	304.7	295.0	292.1	289.1	284.6	285.3	284.6	283.1	283.1
55°	298.0	283.8	274.9	267.4	266.7	263.7	259.9	258.4	257.7	256.2	258.4
57.5°	267.4	256.2	248.0	241.3	238.3	238.3	234.5	231.5	231.5	230.8	231.5
60°	236.8	225.6	220.3	213.6	211.4	210.6	208.4	206.9	204.7	204.7	204.7
62.5°	208.4	199.4	193.5	187.5	188.2	184.5	181.5	180.0	180.0	180.8	180.8
65°	181.5	175.5	168.1	162.8	161.3	160.6	159.1	158.3	156.1	157.6	157.6
67.5°	156.9	148.6	144.2	141.9	139.7	138.9	137.4	135.9	135.2	134.4	135.9
70°	132.2	125.5	121.8	120.3	118.0	117.3	116.5	114.3	115.0	115.8	116.5
72.5°	109.8	103.8	103.1	98.6	98.6	98.6	95.6	97.1	96.4	94.9	96.4
75°	86.6	83.7	82.2	79.9	80.7	79.9	79.2	76.9	76.9	77.7	78.4
77.5°	68.7	65.7	65.0	62.7	61.2	62.7	61.2	60.5	60.5	61.2	61.2
80°	50.8	49.3	47.1	47.1	47.1	46.3	46.3	46.3	45.6	44.8	45.6
82.5°	33.6	33.6	32.9	32.1	32.9	31.4	32.1	32.1	32.1	32.1	32.1
85°	21.7	20.9	20.9	20.2	20.2	20.2	20.9	19.4	19.4	20.2	20.2
87.5°	9.7	9.7	9.7	10.5	9.7	9.7	9.7	10.5	9.7	9.7	9.7
90°	45.0	44.4	43.9	43.3	43.0	43.1	43.4	43.7	44.0	44.3	44.0
92.5°	40.7	41.0	41.3	41.6	41.7	41.7	41.7	41.7	41.7	41.7	41.7
95°	83.4	83.4	83.4	83.4	83.4	83.1	82.5	82.0	81.4	80.8	81.4
97.5°	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3
100°	179.8	179.8	179.8	179.8	179.8	179.7	179.4	179.1	178.8	178.5	178.8
102.5°	233.5	233.8	234.1	234.4	234.5	234.4	234.1	233.8	233.5	233.2	233.5
105°	287.2	287.8	288.3	288.9	289.2	289.2	289.2	289.2	289.2	289.2	289.2
107.5°	345.6	345.9	346.2	346.5	346.6	345.9	344.4	343.0	341.5	340.1	341.5
110°	405.2	405.2	405.2	405.2	405.2	404.8	403.9	403.0	402.2	401.3	402.2

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	465.5	464.7	463.8	462.9	462.5	462.2	461.6	461.1	460.5	459.9	460.5
115°	526.1	525.8	525.5	525.2	525.1	524.7	523.8	522.9	522.1	521.2	522.1
117.5°	585.4	584.6	583.7	582.8	582.4	582.0	581.1	580.2	579.4	578.5	579.4
120°	643.6	643.6	643.6	643.6	643.6	643.2	642.3	641.4	640.6	639.7	640.6
122.5°	705.3	704.5	703.6	702.7	702.3	702.0	701.4	700.9	700.3	699.7	700.3
125°	765.2	764.4	763.5	762.6	762.2	762.1	761.8	761.5	761.2	760.9	761.2
127.5°	823.5	822.4	821.2	820.1	819.5	819.1	818.2	817.3	816.5	815.6	816.5
130°	882.8	882.2	881.7	881.1	880.8	880.2	879.1	877.9	876.8	875.6	876.8
132.5°	941.9	940.4	939.0	937.5	936.8	936.4	935.5	934.6	933.8	932.9	933.8
135°	997.7	997.4	997.1	996.8	996.7	996.3	995.4	994.5	993.7	992.8	993.7
137.5°	1052.5	1052.2	1051.9	1051.6	1051.5	1050.9	1049.7	1048.6	1047.4	1046.2	1047.4
140°	1107.5	1107.5	1107.5	1107.5	1107.5	1106.9	1105.8	1104.6	1103.5	1102.3	1103.5
142.5°	1157.3	1157.6	1157.9	1158.2	1158.3	1157.7	1156.6	1155.4	1154.3	1153.1	1154.3
145°	1208.1	1208.4	1208.7	1209.0	1209.1	1208.5	1207.4	1206.2	1205.1	1203.9	1205.1
147.5°	1252.7	1253.3	1253.8	1254.4	1254.7	1254.1	1253.0	1251.8	1250.7	1249.5	1250.7
150°	1294.7	1295.5	1296.4	1297.3	1297.7	1297.3	1296.4	1295.5	1294.7	1293.8	1294.7
152.5°	1336.7	1337.8	1339.0	1340.1	1340.7	1340.1	1339.0	1337.8	1336.7	1335.5	1336.7
155°	1370.8	1372.3	1373.7	1375.2	1375.9	1375.5	1374.6	1373.7	1372.9	1372.0	1372.9
157.5°	1403.9	1406.0	1408.0	1410.1	1411.1	1410.4	1408.9	1407.4	1406.0	1404.5	1406.0
160°	1433.6	1435.4	1437.1	1438.8	1439.7	1439.1	1438.0	1436.8	1435.7	1434.5	1435.7
162.5°	1460.0	1462.0	1464.1	1466.1	1467.1	1466.4	1464.9	1463.5	1462.0	1460.6	1462.0
165°	1482.1	1484.1	1486.2	1488.2	1489.2	1488.5	1487.0	1485.6	1484.1	1482.7	1484.1
167.5°	1501.7	1503.7	1505.8	1507.8	1508.8	1508.1	1506.6	1505.2	1503.7	1502.3	1503.7
170°	1517.3	1519.3	1521.4	1523.4	1524.4	1523.5	1521.8	1520.1	1518.3	1516.6	1518.3
172.5°	1529.0	1531.0	1533.1	1535.1	1536.1	1535.2	1533.5	1531.8	1530.0	1528.3	1530.0
175°	1536.8	1538.9	1540.9	1543.0	1544.0	1543.1	1541.4	1539.6	1537.9	1536.1	1537.9
177.5°	1541.8	1543.5	1545.3	1547.0	1547.9	1547.0	1545.3	1543.5	1541.8	1540.0	1541.8
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	1030.0	1024.8	1020.3	1021.1	1024.8	1021.8	1014.3	1004.6	1000.9	996.4	1000.9
5°	1092.0	1087.5	1078.6	1079.3	1077.1	1074.1	1062.1	1047.2	1047.2	1035.3	1033.8
7.5°	1153.3	1146.5	1140.6	1139.1	1130.9	1124.9	1114.4	1093.5	1085.3	1071.1	1062.9
10°	1222.0	1216.8	1210.0	1201.8	1197.3	1186.9	1169.7	1139.1	1124.1	1104.7	1090.5
12.5°	1291.4	1290.7	1275.8	1259.3	1258.6	1242.2	1230.2	1189.1	1169.0	1142.8	1109.2
15°	1335.5	1331.8	1323.6	1315.4	1317.6	1299.7	1272.8	1224.2	1210.8	1179.4	1143.6
17.5°	1334.8	1334.8	1332.5	1331.0	1328.8	1323.6	1308.6	1276.5	1254.8	1215.3	1181.6
20°	1292.2	1301.9	1304.1	1303.4	1310.9	1314.6	1313.9	1293.7	1276.5	1241.4	1207.0
22.5°	1207.0	1229.5	1239.2	1245.1	1260.8	1269.0	1288.5	1281.0	1276.5	1250.4	1221.2
25°	1127.9	1135.3	1164.5	1166.0	1187.6	1207.8	1227.2	1239.9	1256.3	1246.6	1222.0
27.5°	1025.5	1042.7	1063.6	1079.3	1083.8	1124.9	1157.0	1180.9	1218.2	1221.2	1213.0
30°	909.8	918.0	952.3	973.3	997.2	1027.0	1073.3	1114.4	1148.0	1178.7	1189.1
32.5°	768.6	802.2	822.4	847.8	868.7	921.7	978.5	1031.5	1070.4	1121.9	1144.3
35°	639.4	665.5	699.9	710.3	748.4	793.2	867.2	935.2	994.2	1046.5	1092.0
37.5°	532.6	553.5	590.1	606.5	628.9	686.4	748.4	832.8	903.8	968.0	1024.8
40°	459.4	475.0	502.7	507.9	526.6	578.9	628.9	708.1	802.2	888.9	950.8
42.5°	409.3	416.8	435.5	442.2	454.1	489.2	534.1	608.8	696.1	785.8	873.2
45°	373.5	378.7	389.9	395.9	410.8	426.5	463.1	522.9	591.6	682.0	776.1
47.5°	341.3	348.1	352.6	356.3	364.5	381.7	405.6	449.7	515.4	598.3	689.4
50°	314.5	316.7	324.9	325.7	330.9	342.1	364.5	391.4	443.7	510.9	599.0
52.5°	287.6	289.8	295.0	300.3	302.5	311.5	326.4	348.8	387.7	440.7	519.1
55°	260.7	263.7	268.9	272.6	274.9	282.3	291.3	313.0	343.6	380.9	445.2
57.5°	233.8	240.5	242.0	244.2	248.0	256.2	264.4	277.1	301.0	335.4	382.4
60°	208.4	210.6	215.9	218.1	221.8	226.3	236.8	246.5	263.7	290.6	333.1
62.5°	182.3	187.5	189.7	192.0	194.9	200.2	206.9	217.4	232.3	254.0	287.6
65°	159.8	160.6	165.1	168.1	171.0	174.8	181.5	191.2	200.2	220.3	245.0
67.5°	138.2	139.7	141.2	144.2	147.9	151.6	157.6	162.8	174.0	187.5	206.9
70°	117.3	117.3	121.0	123.2	122.5	127.0	131.5	137.4	145.7	158.3	174.0
72.5°	98.6	97.8	100.8	101.6	103.1	106.1	109.1	115.0	119.5	129.2	141.2
75°	78.4	79.9	81.4	81.4	83.7	85.9	88.9	91.9	97.1	103.1	112.0
77.5°	62.0	62.0	63.5	64.2	66.5	65.7	68.7	71.7	75.4	80.7	87.4
80°	45.6	47.1	47.1	47.1	47.8	48.6	51.5	53.8	56.0	59.8	62.7
82.5°	32.1	32.1	33.6	33.6	33.6	35.1	35.1	35.9	37.3	39.6	41.8
85°	20.2	20.2	20.2	20.9	20.2	20.9	22.4	21.7	22.4	23.9	23.9
87.5°	9.7	9.7	9.7	9.7	9.7	10.5	9.7	10.5	11.2	11.2	11.2
90°	43.7	43.4	43.1	43.0	43.3	43.9	44.4	45.0	45.6	39.2	32.8
92.5°	41.7	41.7	41.7	41.7	41.6	41.3	41.0	40.7	40.4	40.1	39.8
95°	82.0	82.5	83.1	83.4	83.4	83.4	83.4	83.4	83.4	82.8	82.2
97.5°	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	129.1	128.0
100°	179.1	179.4	179.7	179.8	179.8	179.8	179.8	179.8	179.8	178.9	178.1
102.5°	233.8	234.1	234.4	234.5	234.4	234.1	233.8	233.5	233.2	232.0	230.9
105°	289.2	289.2	289.2	289.2	288.9	288.3	287.8	287.2	286.6	286.0	285.4
107.5°	343.0	344.4	345.9	346.6	346.5	346.2	345.9	345.6	345.3	345.3	345.3
110°	403.0	403.9	404.8	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	461.1	461.6	462.2	462.5	462.9	463.8	464.7	465.5	466.4	466.7	467.0
115°	522.9	523.8	524.7	525.1	525.2	525.5	525.8	526.1	526.4	527.0	527.6
117.5°	580.2	581.1	582.0	582.4	582.8	583.7	584.6	585.4	586.3	587.7	589.2
120°	641.4	642.3	643.2	643.6	643.6	643.6	643.6	643.6	643.6	645.9	648.3
122.5°	700.9	701.4	702.0	702.3	702.7	703.6	704.5	705.3	706.2	707.6	709.1
125°	761.5	761.8	762.1	762.2	762.6	763.5	764.4	765.2	766.1	767.0	767.8
127.5°	817.3	818.2	819.1	819.5	820.1	821.2	822.4	823.5	824.7	825.9	827.1
130°	877.9	879.1	880.2	880.8	881.1	881.7	882.2	882.8	883.4	884.0	884.6
132.5°	934.6	935.5	936.4	936.8	937.5	939.0	940.4	941.9	943.3	943.0	942.7
135°	994.5	995.4	996.3	996.7	996.8	997.1	997.4	997.7	998.0	997.4	996.8
137.5°	1048.6	1049.7	1050.9	1051.5	1051.6	1051.9	1052.2	1052.5	1052.8	1052.2	1051.6
140°	1104.6	1105.8	1106.9	1107.5	1107.5	1107.5	1107.5	1107.5	1107.5	1106.1	1104.6
142.5°	1155.4	1156.6	1157.7	1158.3	1158.2	1157.9	1157.6	1157.3	1157.0	1156.1	1155.3
145°	1206.2	1207.4	1208.5	1209.1	1209.0	1208.7	1208.4	1208.1	1207.8	1206.1	1204.3
147.5°	1251.8	1253.0	1254.1	1254.7	1254.4	1253.8	1253.3	1252.7	1252.1	1250.9	1249.8
150°	1295.5	1296.4	1297.3	1297.7	1297.3	1296.4	1295.5	1294.7	1293.8	1292.6	1291.5
152.5°	1337.8	1339.0	1340.1	1340.7	1340.1	1339.0	1337.8	1336.7	1335.5	1334.1	1332.6
155°	1373.7	1374.6	1375.5	1375.9	1375.2	1373.7	1372.3	1370.8	1369.4	1368.5	1367.7
157.5°	1407.4	1408.9	1410.4	1411.1	1410.1	1408.0	1406.0	1403.9	1401.9	1401.3	1400.7
160°	1436.8	1438.0	1439.1	1439.7	1438.8	1437.1	1435.4	1433.6	1431.9	1431.6	1431.3
162.5°	1463.5	1464.9	1466.4	1467.1	1466.1	1464.1	1462.0	1460.0	1458.0	1457.7	1457.4
165°	1485.6	1487.0	1488.5	1489.2	1488.2	1486.2	1484.1	1482.1	1480.1	1480.1	1480.1
167.5°	1505.2	1506.6	1508.1	1508.8	1507.8	1505.8	1503.7	1501.7	1499.7	1499.7	1499.7
170°	1520.1	1521.8	1523.5	1524.4	1523.4	1521.4	1519.3	1517.3	1515.3	1515.6	1515.9
172.5°	1531.8	1533.5	1535.2	1536.1	1535.1	1533.1	1531.0	1529.0	1527.0	1527.3	1527.6
175°	1539.6	1541.4	1543.1	1544.0	1543.0	1540.9	1538.9	1536.8	1534.8	1535.4	1536.0
177.5°	1543.5	1545.3	1547.0	1547.9	1547.0	1545.3	1543.5	1541.8	1540.0	1540.6	1541.2
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	997.2	993.4	991.2	992.7	988.2	977.0	977.0	980.7	976.2	971.8	965.0
5°	1024.8	1017.3	1012.8	1012.1	1001.6	983.7	980.0	976.2	966.5	956.1	944.9
7.5°	1051.7	1038.2	1030.8	1025.5	1010.6	987.4	977.7	969.5	953.8	938.1	924.0
10°	1074.1	1054.7	1045.7	1037.5	1018.1	988.9	973.3	958.3	938.1	918.0	900.1
12.5°	1092.0	1069.6	1058.4	1046.5	1022.6	984.5	965.0	941.1	921.0	894.1	876.2
15°	1121.9	1075.6	1065.1	1053.9	1029.3	977.0	953.1	926.2	898.6	862.7	843.3
17.5°	1145.8	1083.8	1083.1	1059.2	1027.0	974.0	937.4	902.3	872.4	836.6	805.9
20°	1160.0	1096.5	1084.5	1059.9	1019.6	953.8	915.7	876.9	844.8	801.5	770.8
22.5°	1171.9	1114.4	1083.1	1053.2	1003.9	947.1	891.1	854.5	810.4	763.4	734.2
25°	1176.4	1118.2	1085.3	1050.9	992.7	927.7	864.2	824.6	775.3	732.7	693.2
27.5°	1177.2	1117.4	1077.1	1041.2	977.0	902.3	837.3	795.5	741.0	691.7	652.1
30°	1169.7	1109.2	1072.6	1033.8	962.1	879.1	804.4	758.1	699.9	650.6	609.5
32.5°	1147.3	1092.8	1062.9	1020.3	942.6	847.0	773.1	721.5	660.3	611.7	572.2
35°	1109.9	1072.6	1039.7	1000.1	917.2	817.1	741.7	681.2	619.2	572.9	535.6
37.5°	1063.6	1043.5	1012.8	974.0	888.1	790.3	706.6	639.4	577.4	532.6	496.0
40°	1000.9	1006.1	976.2	941.1	853.7	753.7	661.0	596.8	538.5	496.7	460.9
42.5°	932.9	954.6	937.4	903.8	815.7	713.3	627.4	556.5	499.7	456.4	426.5
45°	859.7	897.1	886.6	862.0	776.1	670.7	579.6	510.9	460.9	419.0	392.9
47.5°	779.8	832.8	832.8	814.9	732.0	628.2	538.5	468.3	419.0	389.2	363.8
50°	698.4	758.1	767.8	755.9	682.7	579.6	488.5	425.0	382.4	353.3	334.6
52.5°	613.2	682.7	700.6	694.6	630.4	533.3	447.4	385.4	346.6	321.2	304.7
55°	531.8	612.5	631.9	634.1	574.4	482.5	401.9	347.3	310.0	292.8	278.6
57.5°	454.9	532.6	554.2	558.0	517.6	436.2	359.3	311.5	277.9	263.7	252.5
60°	389.2	454.1	482.5	490.7	455.6	382.4	319.7	273.4	248.0	234.5	224.1
62.5°	335.4	387.7	417.5	419.8	404.1	335.4	278.6	239.8	218.1	206.2	200.9
65°	283.1	330.1	348.1	357.0	344.3	290.6	240.5	208.4	191.2	180.8	175.5
67.5°	241.3	271.1	286.1	298.0	285.3	245.0	204.7	178.5	165.8	155.4	152.4
70°	197.9	222.6	233.8	245.7	234.5	203.9	174.8	150.9	139.7	131.5	127.7
72.5°	158.3	177.8	188.2	195.7	189.0	163.6	139.7	123.2	115.0	109.1	106.8
75°	125.5	138.9	144.9	150.1	147.1	127.7	112.8	99.3	91.9	86.6	85.2
77.5°	95.6	105.3	112.0	113.5	109.8	97.1	84.4	76.2	70.2	67.2	65.7
80°	68.0	73.9	77.7	79.9	76.2	71.0	62.0	56.0	50.8	47.1	46.3
82.5°	45.6	48.6	51.5	50.8	49.3	44.8	39.6	36.6	34.4	31.4	31.4
85°	26.1	26.9	28.4	29.1	28.4	25.4	22.4	20.9	19.4	17.2	17.2
87.5°	11.2	12.0	12.0	12.7	11.2	11.2	9.7	8.2	8.2	7.5	6.7
90°	26.5	20.1	16.9	15.2	11.7	8.2	4.8	1.3	4.8	8.2	11.7
92.5°	39.5	39.2	39.1	37.9	35.6	33.3	31.0	28.7	31.0	33.3	35.6
95°	81.7	81.1	80.8	79.4	76.5	73.6	70.7	67.8	70.7	73.6	76.5
97.5°	126.8	125.7	125.1	123.8	121.2	118.6	116.0	113.4	116.0	118.6	121.2
100°	177.2	176.3	175.9	174.7	172.4	170.1	167.8	165.5	167.8	170.1	172.4
102.5°	229.7	228.6	228.0	227.1	225.4	223.7	221.9	220.2	221.9	223.7	225.4
105°	284.9	284.3	284.0	283.6	282.7	281.8	281.0	280.1	281.0	281.8	282.7
107.5°	345.3	345.3	345.3	344.7	343.6	342.4	341.3	340.1	341.3	342.4	343.6
110°	405.2	405.2	405.2	404.3	402.6	400.9	399.1	397.4	399.1	400.9	402.6

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	467.3	467.6	467.7	466.8	465.1	463.4	461.6	459.9	461.6	463.4	465.1
115°	528.1	528.7	529.0	528.1	526.4	524.7	522.9	521.2	522.9	524.7	526.4
117.5°	590.6	592.1	592.8	591.6	589.3	587.0	584.7	582.4	584.7	587.0	589.3
120°	650.6	652.9	654.1	652.9	650.6	648.3	645.9	643.6	645.9	648.3	650.6
122.5°	710.5	712.0	712.7	711.3	708.4	705.5	702.6	699.7	702.6	705.5	708.4
125°	768.7	769.6	770.0	768.7	766.1	763.5	760.9	758.3	760.9	763.5	766.1
127.5°	828.2	829.4	830.0	828.4	825.2	822.0	818.8	815.6	818.8	822.0	825.2
130°	885.1	885.7	886.0	884.1	880.3	876.6	872.8	869.0	872.8	876.6	880.3
132.5°	942.4	942.1	942.0	940.6	937.7	934.8	931.9	929.0	931.9	934.8	937.7
135°	996.3	995.7	995.4	993.8	990.6	987.5	984.3	981.1	984.3	987.5	990.6
137.5°	1051.1	1050.5	1050.2	1048.9	1046.3	1043.6	1041.0	1038.4	1041.0	1043.6	1046.3
140°	1103.2	1101.7	1101.0	1099.7	1097.1	1094.4	1091.8	1089.2	1091.8	1094.4	1097.1
142.5°	1154.4	1153.5	1153.1	1151.8	1149.2	1146.6	1144.0	1141.4	1144.0	1146.6	1149.2
145°	1202.6	1200.9	1200.0	1199.0	1197.0	1194.9	1192.9	1190.9	1192.9	1194.9	1197.0
147.5°	1248.6	1247.5	1246.9	1245.6	1243.0	1240.4	1237.8	1235.2	1237.8	1240.4	1243.0
150°	1290.3	1289.2	1288.6	1287.7	1286.0	1284.3	1282.5	1280.8	1282.5	1284.3	1286.0
152.5°	1331.2	1329.7	1329.0	1328.1	1326.4	1324.7	1322.9	1321.2	1322.9	1324.7	1326.4
155°	1366.8	1365.9	1365.5	1365.1	1364.2	1363.3	1362.4	1361.5	1362.4	1363.3	1364.2
157.5°	1400.2	1399.6	1399.3	1399.0	1398.4	1397.9	1397.3	1396.7	1397.3	1397.9	1398.4
160°	1431.0	1430.7	1430.6	1430.3	1429.7	1429.2	1428.6	1428.0	1428.6	1429.2	1429.7
162.5°	1457.1	1456.8	1456.7	1456.7	1456.7	1456.7	1456.7	1456.7	1456.7	1456.7	1456.7
165°	1480.1	1480.1	1480.1	1480.2	1480.5	1480.8	1481.1	1481.4	1481.1	1480.8	1480.5
167.5°	1499.7	1499.7	1499.7	1500.1	1501.0	1501.9	1502.7	1503.6	1502.7	1501.9	1501.0
170°	1516.2	1516.5	1516.6	1517.0	1517.9	1518.8	1519.6	1520.5	1519.6	1518.8	1517.9
172.5°	1527.9	1528.2	1528.3	1528.7	1529.6	1530.5	1531.3	1532.2	1531.3	1530.5	1529.6
175°	1536.5	1537.1	1537.4	1537.8	1538.7	1539.6	1540.4	1541.3	1540.4	1539.6	1538.7
177.5°	1541.8	1542.4	1542.7	1543.1	1544.0	1544.9	1545.7	1546.6	1545.7	1544.9	1544.0
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	961.3	965.0	964.3	956.8	948.6	941.9	929.2	930.7	926.2	926.9	931.4
5°	937.4	937.4	934.4	924.0	910.5	903.0	888.9	885.1	876.2	875.4	874.7
7.5°	912.0	908.3	904.5	889.6	873.2	861.2	841.8	837.3	828.3	822.4	819.4
10°	882.1	876.9	869.4	852.3	832.1	817.1	797.0	791.0	773.8	766.4	761.9
12.5°	849.3	846.3	834.3	820.1	787.3	770.8	741.7	747.7	730.5	715.6	713.3
15°	816.4	805.2	798.5	775.3	735.7	728.3	705.1	693.2	677.5	665.5	665.5
17.5°	784.3	767.1	752.2	727.5	698.4	677.5	660.3	654.3	634.9	622.9	620.7
20°	741.7	722.3	718.6	683.4	663.3	640.1	623.7	608.8	594.6	589.3	585.6
22.5°	701.4	679.0	673.0	643.1	622.9	599.8	583.4	572.9	562.4	558.7	552.0
25°	658.0	644.6	635.6	603.5	581.1	559.5	548.2	540.8	531.1	530.3	525.8
27.5°	616.2	603.5	594.6	563.9	547.5	527.3	518.4	510.2	504.9	502.7	500.4
30°	580.4	566.2	555.7	533.3	513.1	496.7	489.2	484.0	481.0	477.3	476.5
32.5°	540.8	532.6	518.4	501.2	485.5	469.8	465.3	461.6	457.1	455.6	454.9
35°	507.2	496.0	487.0	467.6	460.9	447.4	442.2	439.2	433.2	431.7	430.2
37.5°	474.3	463.8	454.1	442.2	429.5	422.0	419.0	414.5	411.6	412.3	410.8
40°	441.4	433.2	425.8	413.1	405.6	401.9	395.9	391.4	389.9	390.6	389.9
42.5°	409.3	401.9	397.4	387.7	380.2	376.5	372.7	368.2	370.5	370.5	372.7
45°	380.2	373.5	370.5	363.0	358.5	352.6	348.8	348.1	351.1	350.3	350.3
47.5°	350.3	348.1	344.3	337.6	331.6	327.9	327.2	327.2	330.1	331.6	330.9
50°	327.2	322.7	318.2	313.0	308.5	307.0	304.7	306.2	309.2	309.2	310.7
52.5°	298.0	295.0	293.5	289.1	286.1	286.1	286.1	286.8	289.1	291.3	290.6
55°	272.6	270.4	268.9	266.7	262.9	263.7	262.9	264.4	266.7	268.9	270.4
57.5°	245.7	245.0	243.5	239.8	239.8	239.0	241.3	242.0	245.7	247.2	249.5
60°	221.8	219.6	219.6	216.6	216.6	216.6	218.9	221.1	224.1	224.8	226.3
62.5°	196.4	196.4	195.7	193.5	193.5	195.7	196.4	199.4	200.9	200.9	203.2
65°	172.5	171.8	171.0	171.8	172.5	172.5	174.8	176.3	177.8	178.5	179.3
67.5°	148.6	147.9	149.4	148.6	150.1	153.1	152.4	154.6	156.9	156.9	157.6
70°	126.2	127.7	127.0	128.5	127.7	129.2	131.5	132.2	132.2	133.0	135.2
72.5°	105.3	105.3	105.3	104.6	105.3	106.8	108.3	109.1	110.5	111.3	113.5
75°	85.2	85.2	83.7	85.2	85.2	86.6	88.1	88.1	88.1	89.6	91.9
77.5°	64.2	65.0	64.2	65.7	65.7	66.5	68.0	67.2	68.7	69.5	70.2
80°	47.1	46.3	46.3	46.3	47.1	47.1	48.6	49.3	49.3	51.5	50.0
82.5°	29.9	30.6	29.9	30.6	30.6	31.4	30.6	31.4	32.1	33.6	32.9
85°	17.2	16.4	16.4	17.2	16.4	16.4	17.2	16.4	17.2	16.4	17.2
87.5°	6.7	6.0	6.0	6.0	6.0	5.2	5.2	4.5	4.5	4.5	3.7
90°	15.2	16.9	20.1	26.5	32.8	39.2	45.6	45.0	44.4	43.9	43.3
92.5°	37.9	39.1	39.2	39.5	39.8	40.1	40.4	40.7	41.0	41.3	41.6
95°	79.4	80.8	81.1	81.7	82.2	82.8	83.4	83.4	83.4	83.4	83.4
97.5°	123.8	125.1	125.7	126.8	128.0	129.1	130.3	130.3	130.3	130.3	130.3
100°	174.7	175.9	176.3	177.2	178.1	178.9	179.8	179.8	179.8	179.8	179.8
102.5°	227.1	228.0	228.6	229.7	230.9	232.0	233.2	233.5	233.8	234.1	234.4
105°	283.6	284.0	284.3	284.9	285.4	286.0	286.6	287.2	287.8	288.3	288.9
107.5°	344.7	345.3	345.3	345.3	345.3	345.3	345.3	345.6	345.9	346.2	346.5
110°	404.3	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	466.8	467.7	467.6	467.3	467.0	466.7	466.4	465.5	464.7	463.8	462.9
115°	528.1	529.0	528.7	528.1	527.6	527.0	526.4	526.1	525.8	525.5	525.2
117.5°	591.6	592.8	592.1	590.6	589.2	587.7	586.3	585.4	584.6	583.7	582.8
120°	652.9	654.1	652.9	650.6	648.3	645.9	643.6	643.6	643.6	643.6	643.6
122.5°	711.3	712.7	712.0	710.5	709.1	707.6	706.2	705.3	704.5	703.6	702.7
125°	768.7	770.0	769.6	768.7	767.8	767.0	766.1	765.2	764.4	763.5	762.6
127.5°	828.4	830.0	829.4	828.2	827.1	825.9	824.7	823.5	822.4	821.2	820.1
130°	884.1	886.0	885.7	885.1	884.6	884.0	883.4	882.8	882.2	881.7	881.1
132.5°	940.6	942.0	942.1	942.4	942.7	943.0	943.3	941.9	940.4	939.0	937.5
135°	993.8	995.4	995.7	996.3	996.8	997.4	998.0	997.7	997.4	997.1	996.8
137.5°	1048.9	1050.2	1050.5	1051.1	1051.6	1052.2	1052.8	1052.5	1052.2	1051.9	1051.6
140°	1099.7	1101.0	1101.7	1103.2	1104.6	1106.1	1107.5	1107.5	1107.5	1107.5	1107.5
142.5°	1151.8	1153.1	1153.5	1154.4	1155.3	1156.1	1157.0	1157.3	1157.6	1157.9	1158.2
145°	1199.0	1200.0	1200.9	1202.6	1204.3	1206.1	1207.8	1208.1	1208.4	1208.7	1209.0
147.5°	1245.6	1246.9	1247.5	1248.6	1249.8	1250.9	1252.1	1252.7	1253.3	1253.8	1254.4
150°	1287.7	1288.6	1289.2	1290.3	1291.5	1292.6	1293.8	1294.7	1295.5	1296.4	1297.3
152.5°	1328.1	1329.0	1329.7	1331.2	1332.6	1334.1	1335.5	1336.7	1337.8	1339.0	1340.1
155°	1365.1	1365.5	1365.9	1366.8	1367.7	1368.5	1369.4	1370.8	1372.3	1373.7	1375.2
157.5°	1399.0	1399.3	1399.6	1400.2	1400.7	1401.3	1401.9	1403.9	1406.0	1408.0	1410.1
160°	1430.3	1430.6	1430.7	1431.0	1431.3	1431.6	1431.9	1433.6	1435.4	1437.1	1438.8
162.5°	1456.7	1456.7	1456.8	1457.1	1457.4	1457.7	1458.0	1460.0	1462.0	1464.1	1466.1
165°	1480.2	1480.1	1480.1	1480.1	1480.1	1480.1	1480.1	1482.1	1484.1	1486.2	1488.2
167.5°	1500.1	1499.7	1499.7	1499.7	1499.7	1499.7	1499.7	1501.7	1503.7	1505.8	1507.8
170°	1517.0	1516.6	1516.5	1516.2	1515.9	1515.6	1515.3	1517.3	1519.3	1521.4	1523.4
172.5°	1528.7	1528.3	1528.2	1527.9	1527.6	1527.3	1527.0	1529.0	1531.0	1533.1	1535.1
175°	1537.8	1537.4	1537.1	1536.5	1536.0	1535.4	1534.8	1536.8	1538.9	1540.9	1543.0
177.5°	1543.1	1542.7	1542.4	1541.8	1541.2	1540.6	1540.0	1541.8	1543.5	1545.3	1547.0
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	926.2	928.4	923.2	921.7	923.2	918.0	919.5	921.0	921.0	923.2	924.7
5°	872.4	869.4	864.2	862.7	861.2	863.5	862.0	864.2	864.9	870.2	870.9
7.5°	819.4	814.9	810.4	805.9	804.4	800.7	804.4	804.4	809.7	808.2	811.9
10°	756.6	755.9	749.9	747.7	744.7	738.7	746.9	744.7	748.4	755.1	756.6
12.5°	710.3	702.1	705.9	695.4	699.1	693.2	693.9	693.9	699.9	700.6	699.1
15°	666.3	659.5	649.8	645.4	643.1	640.1	649.8	650.6	646.1	656.6	652.8
17.5°	621.4	621.4	612.5	610.2	604.3	607.3	605.8	606.5	605.0	612.5	616.2
20°	582.6	578.9	575.9	576.6	569.2	567.7	566.2	567.7	572.9	578.1	579.6
22.5°	551.2	549.0	541.5	543.0	537.0	539.3	537.8	541.5	542.3	542.3	547.5
25°	521.4	518.4	519.1	516.1	513.9	513.9	511.6	513.9	516.9	518.4	519.1
27.5°	499.0	496.7	493.0	490.7	492.2	488.5	491.5	493.7	493.7	492.2	493.7
30°	472.1	473.6	473.6	466.1	469.1	467.6	469.8	471.3	471.3	472.1	470.6
32.5°	454.1	449.7	448.9	448.2	448.2	445.2	445.2	447.4	448.2	448.9	451.1
35°	430.2	430.2	426.5	428.7	425.8	426.5	425.8	426.5	428.0	425.8	428.0
37.5°	408.6	409.3	407.8	409.3	410.1	408.6	407.1	410.1	408.6	408.6	407.1
40°	389.9	389.2	389.9	389.9	389.9	390.6	389.2	389.2	389.2	387.7	386.2
42.5°	374.2	369.7	371.2	372.0	369.7	369.7	370.5	369.7	372.0	367.5	367.5
45°	351.8	350.3	351.1	351.1	352.6	350.3	351.8	352.6	350.3	349.6	348.1
47.5°	331.6	333.1	331.6	333.1	333.1	334.6	331.6	332.4	333.1	330.1	327.9
50°	311.5	311.5	313.7	313.0	313.7	312.2	312.2	311.5	312.2	310.7	308.5
52.5°	292.8	290.6	294.3	293.5	292.8	292.1	291.3	292.1	290.6	289.1	289.1
55°	269.6	269.6	271.9	272.6	272.6	271.1	269.6	270.4	269.6	268.9	268.1
57.5°	251.0	248.0	249.5	250.2	250.2	248.0	249.5	248.0	248.0	248.7	246.5
60°	227.1	227.1	225.6	227.8	227.8	226.3	226.3	227.1	225.6	224.8	224.1
62.5°	201.7	202.4	204.7	205.4	206.2	204.7	203.2	203.9	203.9	201.7	202.4
65°	180.0	181.5	184.5	183.7	182.3	183.0	181.5	182.3	180.0	180.8	178.5
67.5°	159.1	158.3	159.1	159.1	160.6	159.8	158.3	158.3	157.6	159.8	157.6
70°	136.7	136.7	136.7	136.7	137.4	138.2	136.7	135.2	135.9	134.4	133.7
72.5°	113.5	114.3	113.5	115.0	112.8	114.3	114.3	113.5	112.8	112.8	112.8
75°	91.9	93.4	91.1	91.9	91.1	92.6	91.9	91.9	90.4	89.6	90.4
77.5°	70.2	71.0	69.5	70.2	69.5	70.2	70.2	69.5	69.5	69.5	69.5
80°	50.0	50.8	50.0	49.3	48.6	50.0	48.6	49.3	50.0	49.3	50.8
82.5°	32.1	32.1	31.4	32.1	30.6	30.6	31.4	31.4	30.6	32.1	30.6
85°	15.7	15.7	17.2	15.7	14.9	14.9	14.9	15.7	14.9	16.4	15.7
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.5	3.0
90°	43.0	43.1	43.4	43.7	44.0	44.3	44.0	43.7	43.4	43.1	43.0
92.5°	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7	41.7
95°	83.4	83.1	82.5	82.0	81.4	80.8	81.4	82.0	82.5	83.1	83.4
97.5°	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3	130.3
100°	179.8	179.7	179.4	179.1	178.8	178.5	178.8	179.1	179.4	179.7	179.8
102.5°	234.5	234.4	234.1	233.8	233.5	233.2	233.5	233.8	234.1	234.4	234.5
105°	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2	289.2
107.5°	346.6	345.9	344.4	343.0	341.5	340.1	341.5	343.0	344.4	345.9	346.6
110°	405.2	404.8	403.9	403.0	402.2	401.3	402.2	403.0	403.9	404.8	405.2

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	462.5	462.2	461.6	461.1	460.5	459.9	460.5	461.1	461.6	462.2	462.5
115°	525.1	524.7	523.8	522.9	522.1	521.2	522.1	522.9	523.8	524.7	525.1
117.5°	582.4	582.0	581.1	580.2	579.4	578.5	579.4	580.2	581.1	582.0	582.4
120°	643.6	643.2	642.3	641.4	640.6	639.7	640.6	641.4	642.3	643.2	643.6
122.5°	702.3	702.0	701.4	700.9	700.3	699.7	700.3	700.9	701.4	702.0	702.3
125°	762.2	762.1	761.8	761.5	761.2	760.9	761.2	761.5	761.8	762.1	762.2
127.5°	819.5	819.1	818.2	817.3	816.5	815.6	816.5	817.3	818.2	819.1	819.5
130°	880.8	880.2	879.1	877.9	876.8	875.6	876.8	877.9	879.1	880.2	880.8
132.5°	936.8	936.4	935.5	934.6	933.8	932.9	933.8	934.6	935.5	936.4	936.8
135°	996.7	996.3	995.4	994.5	993.7	992.8	993.7	994.5	995.4	996.3	996.7
137.5°	1051.5	1050.9	1049.7	1048.6	1047.4	1046.2	1047.4	1048.6	1049.7	1050.9	1051.5
140°	1107.5	1106.9	1105.8	1104.6	1103.5	1102.3	1103.5	1104.6	1105.8	1106.9	1107.5
142.5°	1158.3	1157.7	1156.6	1155.4	1154.3	1153.1	1154.3	1155.4	1156.6	1157.7	1158.3
145°	1209.1	1208.5	1207.4	1206.2	1205.1	1203.9	1205.1	1206.2	1207.4	1208.5	1209.1
147.5°	1254.7	1254.1	1253.0	1251.8	1250.7	1249.5	1250.7	1251.8	1253.0	1254.1	1254.7
150°	1297.7	1297.3	1296.4	1295.5	1294.7	1293.8	1294.7	1295.5	1296.4	1297.3	1297.7
152.5°	1340.7	1340.1	1339.0	1337.8	1336.7	1335.5	1336.7	1337.8	1339.0	1340.1	1340.7
155°	1375.9	1375.5	1374.6	1373.7	1372.9	1372.0	1372.9	1373.7	1374.6	1375.5	1375.9
157.5°	1411.1	1410.4	1408.9	1407.4	1406.0	1404.5	1406.0	1407.4	1408.9	1410.4	1411.1
160°	1439.7	1439.1	1438.0	1436.8	1435.7	1434.5	1435.7	1436.8	1438.0	1439.1	1439.7
162.5°	1467.1	1466.4	1464.9	1463.5	1462.0	1460.6	1462.0	1463.5	1464.9	1466.4	1467.1
165°	1489.2	1488.5	1487.0	1485.6	1484.1	1482.7	1484.1	1485.6	1487.0	1488.5	1489.2
167.5°	1508.8	1508.1	1506.6	1505.2	1503.7	1502.3	1503.7	1505.2	1506.6	1508.1	1508.8
170°	1524.4	1523.5	1521.8	1520.1	1518.3	1516.6	1518.3	1520.1	1521.8	1523.5	1524.4
172.5°	1536.1	1535.2	1533.5	1531.8	1530.0	1528.3	1530.0	1531.8	1533.5	1535.2	1536.1
175°	1544.0	1543.1	1541.4	1539.6	1537.9	1536.1	1537.9	1539.6	1541.4	1543.1	1544.0
177.5°	1547.9	1547.0	1545.3	1543.5	1541.8	1540.0	1541.8	1543.5	1545.3	1547.0	1547.9
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8	971.8
2.5°	922.5	928.4	926.2	918.0	927.7	927.7	934.4	934.4	942.6	945.6	950.1
5°	870.2	874.7	878.4	874.7	881.4	891.8	897.8	903.0	914.2	918.7	925.5
7.5°	814.2	822.4	826.1	826.1	837.3	849.3	861.2	868.7	884.4	890.3	897.1
10°	759.6	769.3	776.8	776.1	794.7	802.2	817.1	834.3	850.0	859.0	868.7
12.5°	702.1	707.3	717.8	732.7	737.2	750.7	767.8	789.5	817.9	826.1	840.3
15°	654.3	668.5	676.7	683.4	693.9	706.6	725.3	746.2	774.6	792.5	807.4
17.5°	614.0	632.7	637.9	636.4	649.8	669.3	690.9	706.6	732.0	753.7	767.8
20°	581.1	588.6	597.5	601.3	611.7	632.7	653.6	671.5	692.4	709.6	726.0
22.5°	548.2	554.2	561.7	568.4	576.6	588.6	608.8	631.2	651.3	667.8	686.4
25°	521.4	525.1	531.8	537.0	546.0	554.2	568.4	593.1	617.0	626.7	643.1
27.5°	495.2	498.2	502.7	508.7	513.1	521.4	534.1	554.2	578.9	588.6	611.0
30°	472.1	474.3	478.8	481.8	484.0	493.7	503.4	519.1	537.8	551.2	567.7
32.5°	450.4	452.6	457.1	457.9	460.9	466.1	475.0	489.2	505.7	516.9	531.1
35°	426.5	428.0	432.5	434.0	436.2	440.7	447.4	457.9	472.8	481.0	493.7
37.5°	407.8	407.1	410.1	412.3	415.3	417.5	419.8	430.2	441.4	448.9	458.6
40°	387.7	386.2	386.9	389.9	391.4	394.4	394.4	404.8	412.3	418.3	425.8
42.5°	367.5	366.7	365.3	366.7	368.2	369.0	369.7	377.2	384.7	389.9	398.1
45°	347.3	346.6	345.1	345.8	345.8	347.3	349.6	352.6	357.8	362.3	366.7
47.5°	328.7	327.2	324.9	324.2	325.7	325.7	325.7	328.7	333.9	335.4	339.9
50°	309.2	307.0	304.0	302.5	302.5	301.8	303.3	304.0	308.5	310.0	313.7
52.5°	288.3	286.8	283.8	280.8	281.6	280.1	280.8	281.6	283.1	285.3	287.6
55°	267.4	264.4	262.2	261.4	259.2	259.2	256.9	259.9	259.2	259.9	262.9
57.5°	247.2	244.2	240.5	239.0	236.8	236.0	234.5	233.8	234.5	236.8	239.0
60°	223.3	221.8	219.6	217.4	215.9	213.6	212.1	212.1	211.4	211.4	212.1
62.5°	200.2	199.4	196.4	195.7	194.2	192.7	190.5	189.0	189.0	190.5	191.2
65°	177.8	177.0	174.8	174.0	170.3	168.8	168.1	167.3	165.8	165.8	165.8
67.5°	156.9	154.6	154.6	150.9	147.9	146.4	144.9	144.2	144.2	144.2	144.9
70°	133.7	133.7	131.5	129.2	126.2	127.0	124.7	122.5	122.5	121.0	121.8
72.5°	111.3	110.5	108.3	107.6	105.3	103.1	101.6	103.1	100.8	100.1	100.8
75°	89.6	88.9	87.4	85.9	86.6	84.4	82.2	81.4	81.4	79.9	79.9
77.5°	68.7	70.2	67.2	66.5	65.0	63.5	62.7	62.0	62.0	62.0	63.5
80°	47.8	48.6	48.6	47.1	47.8	45.6	45.6	45.6	43.3	44.1	44.8
82.5°	30.6	30.6	29.9	30.6	29.9	29.9	29.1	29.1	28.4	28.4	29.1
85°	17.2	16.4	15.7	17.2	16.4	16.4	15.7	15.7	15.7	15.7	15.7
87.5°	3.7	4.5	4.5	4.5	4.5	5.2	5.2	5.2	6.0	6.0	6.0
90°	43.3	43.9	44.4	45.0	45.6	39.2	32.8	26.5	20.1	16.9	15.2
92.5°	41.6	41.3	41.0	40.7	40.4	40.1	39.8	39.5	39.2	39.1	37.9
95°	83.4	83.4	83.4	83.4	83.4	82.8	82.2	81.7	81.1	80.8	79.4
97.5°	130.3	130.3	130.3	130.3	130.3	129.1	128.0	126.8	125.7	125.1	123.8
100°	179.8	179.8	179.8	179.8	179.8	178.9	178.1	177.2	176.3	175.9	174.7
102.5°	234.4	234.1	233.8	233.5	233.2	232.0	230.9	229.7	228.6	228.0	227.1
105°	288.9	288.3	287.8	287.2	286.6	286.0	285.4	284.9	284.3	284.0	283.6
107.5°	346.5	346.2	345.9	345.6	345.3	345.3	345.3	345.3	345.3	345.3	344.7
110°	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	405.2	404.3

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	462.9	463.8	464.7	465.5	466.4	466.7	467.0	467.3	467.6	467.7	466.8
115°	525.2	525.5	525.8	526.1	526.4	527.0	527.6	528.1	528.7	529.0	528.1
117.5°	582.8	583.7	584.6	585.4	586.3	587.7	589.2	590.6	592.1	592.8	591.6
120°	643.6	643.6	643.6	643.6	643.6	645.9	648.3	650.6	652.9	654.1	652.9
122.5°	702.7	703.6	704.5	705.3	706.2	707.6	709.1	710.5	712.0	712.7	711.3
125°	762.6	763.5	764.4	765.2	766.1	767.0	767.8	768.7	769.6	770.0	768.7
127.5°	820.1	821.2	822.4	823.5	824.7	825.9	827.1	828.2	829.4	830.0	828.4
130°	881.1	881.7	882.2	882.8	883.4	884.0	884.6	885.1	885.7	886.0	884.1
132.5°	937.5	939.0	940.4	941.9	943.3	943.0	942.7	942.4	942.1	942.0	940.6
135°	996.8	997.1	997.4	997.7	998.0	997.4	996.8	996.3	995.7	995.4	993.8
137.5°	1051.6	1051.9	1052.2	1052.5	1052.8	1052.2	1051.6	1051.1	1050.5	1050.2	1048.9
140°	1107.5	1107.5	1107.5	1107.5	1107.5	1106.1	1104.6	1103.2	1101.7	1101.0	1099.7
142.5°	1158.2	1157.9	1157.6	1157.3	1157.0	1156.1	1155.3	1154.4	1153.5	1153.1	1151.8
145°	1209.0	1208.7	1208.4	1208.1	1207.8	1206.1	1204.3	1202.6	1200.9	1200.0	1199.0
147.5°	1254.4	1253.8	1253.3	1252.7	1252.1	1250.9	1249.8	1248.6	1247.5	1246.9	1245.6
150°	1297.3	1296.4	1295.5	1294.7	1293.8	1292.6	1291.5	1290.3	1289.2	1288.6	1287.7
152.5°	1340.1	1339.0	1337.8	1336.7	1335.5	1334.1	1332.6	1331.2	1329.7	1329.0	1328.1
155°	1375.2	1373.7	1372.3	1370.8	1369.4	1368.5	1367.7	1366.8	1365.9	1365.5	1365.1
157.5°	1410.1	1408.0	1406.0	1403.9	1401.9	1401.3	1400.7	1400.2	1399.6	1399.3	1399.0
160°	1438.8	1437.1	1435.4	1433.6	1431.9	1431.6	1431.3	1431.0	1430.7	1430.6	1430.3
162.5°	1466.1	1464.1	1462.0	1460.0	1458.0	1457.7	1457.4	1457.1	1456.8	1456.7	1456.7
165°	1488.2	1486.2	1484.1	1482.1	1480.1	1480.1	1480.1	1480.1	1480.1	1480.1	1480.2
167.5°	1507.8	1505.8	1503.7	1501.7	1499.7	1499.7	1499.7	1499.7	1499.7	1499.7	1500.1
170°	1523.4	1521.4	1519.3	1517.3	1515.3	1515.6	1515.9	1516.2	1516.5	1516.6	1517.0
172.5°	1535.1	1533.1	1531.0	1529.0	1527.0	1527.3	1527.6	1527.9	1528.2	1528.3	1528.7
175°	1543.0	1540.9	1538.9	1536.8	1534.8	1535.4	1536.0	1536.5	1537.1	1537.4	1537.8
177.5°	1547.0	1545.3	1543.5	1541.8	1540.0	1540.6	1541.2	1541.8	1542.4	1542.7	1543.1
180°	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0	1544.0

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	971.8	971.8	971.8	971.8
2.5°	953.8	953.8	965.0	977.0
5°	932.9	938.1	956.1	972.5
7.5°	912.8	921.7	944.1	965.0
10°	888.1	900.1	927.7	952.3
12.5°	864.2	875.4	907.5	935.2
15°	830.6	844.8	879.1	913.5
17.5°	797.0	811.2	853.0	893.3
20°	757.4	776.1	823.1	876.9
22.5°	720.8	743.9	796.2	839.6
25°	680.5	716.3	764.9	820.9
27.5°	644.6	680.5	729.8	786.5
30°	604.3	640.9	691.7	743.9
32.5°	565.4	599.0	648.3	712.6
35°	525.1	557.2	605.0	670.0
37.5°	488.5	519.9	572.2	631.9
40°	452.6	485.5	530.3	590.1
42.5°	419.0	448.2	488.5	548.2
45°	388.4	409.3	446.7	502.7
47.5°	356.3	375.0	409.3	465.3
50°	326.4	342.1	372.0	424.3
52.5°	297.3	310.7	338.4	380.2
55°	271.1	283.8	304.0	345.1
57.5°	244.2	254.0	273.4	306.2
60°	218.1	227.1	242.8	269.6
62.5°	192.0	199.4	214.4	236.0
65°	168.8	174.8	186.0	204.7
67.5°	146.4	150.1	159.1	174.0
70°	124.7	127.7	135.2	147.1
72.5°	101.6	104.6	112.8	121.0
75°	82.2	82.9	88.9	95.6
77.5°	64.2	63.5	68.0	73.2
80°	44.1	46.3	50.0	52.3
82.5°	29.9	30.6	32.1	33.6
85°	16.4	17.2	17.2	19.4
87.5°	6.7	7.5	7.5	8.2
90°	11.7	8.2	4.8	1.3
92.5°	35.6	33.3	31.0	28.7
95°	76.5	73.6	70.7	67.8
97.5°	121.2	118.6	116.0	113.4
100°	172.4	170.1	167.8	165.5
102.5°	225.4	223.7	221.9	220.2
105°	282.7	281.8	281.0	280.1
107.5°	343.6	342.4	341.3	340.1
110°	402.6	400.9	399.1	397.4

TEST NUMBER: P1029450

CATALOG NUMBER: S122DIW-B485D1240UB2750-4F0-XX-W2A-A1_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	465.1	463.4	461.6	459.9
115°	526.4	524.7	522.9	521.2
117.5°	589.3	587.0	584.7	582.4
120°	650.6	648.3	645.9	643.6
122.5°	708.4	705.5	702.6	699.7
125°	766.1	763.5	760.9	758.3
127.5°	825.2	822.0	818.8	815.6
130°	880.3	876.6	872.8	869.0
132.5°	937.7	934.8	931.9	929.0
135°	990.6	987.5	984.3	981.1
137.5°	1046.3	1043.6	1041.0	1038.4
140°	1097.1	1094.4	1091.8	1089.2
142.5°	1149.2	1146.6	1144.0	1141.4
145°	1197.0	1194.9	1192.9	1190.9
147.5°	1243.0	1240.4	1237.8	1235.2
150°	1286.0	1284.3	1282.5	1280.8
152.5°	1326.4	1324.7	1322.9	1321.2
155°	1364.2	1363.3	1362.4	1361.5
157.5°	1398.4	1397.9	1397.3	1396.7
160°	1429.7	1429.2	1428.6	1428.0
162.5°	1456.7	1456.7	1456.7	1456.7
165°	1480.5	1480.8	1481.1	1481.4
167.5°	1501.0	1501.9	1502.7	1503.6
170°	1517.9	1518.8	1519.6	1520.5
172.5°	1529.6	1530.5	1531.3	1532.2
175°	1538.7	1539.6	1540.4	1541.3
177.5°	1544.0	1544.9	1545.7	1546.6
180°	1544.0	1544.0	1544.0	1544.0

(END OF REPORT)