

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029546

Luminaire Tested: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029546
REPORT IS A COMBINATION OF REPORTS P986210 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K
Description: Define 2 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4993.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	44	43	42
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	81	72	65	59	74	66	60	55	55	50	47	45	42	39	35	33	31
4	74	64	56	50	67	59	52	47	49	44	40	40	37	34	32	29	27
5	68	57	49	43	62	52	46	40	44	39	35	36	32	29	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	21
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	27	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16
10	47	35	28	24	43	33	26	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15231	15231	15231	15231
5°	15268	16241	15327	12921
10°	15091	17729	15185	10653
15°	14726	18701	14929	8974
20°	14495	17558	14495	7799
25°	14033	15085	14096	6975
30°	13274	11858	13526	6317
35°	12599	8200	12810	5780
40°	11826	6191	11961	5351
45°	10872	5087	11049	4890
50°	10046	4465	10063	4476
55°	9105	3805	9164	4027
60°	8102	3179	8214	3514
65°	7206	2585	7337	3001
70°	6310	2027	6470	2420
75°	5298	1472	5505	1755
80°	4136	933	4431	1043
85°	2712	470	2924	348

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 15745 cd/sqm

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.7	1.8
10°-20°	266.8	5.3
20°-30°	387.2	7.8
30°-40°	408.1	8.2
40°-50°	361.2	7.2
50°-60°	288.4	5.8
60°-70°	195.9	3.9
70°-80°	100.2	2.0
80°-90°	25.4	0.5
90°-100°	32.3	0.6
100°-110°	120.3	2.4
110°-120°	319.0	6.4
120°-130°	529.0	10.6
130°-140°	561.9	11.3
140°-150°	522.3	10.5
150°-160°	419.9	8.4
160°-170°	270.6	5.4
170°-180°	93.1	1.9
0°-30°	745.6	14.9
0°-40°	1153.7	23.1
0°-60°	1803.2	36.1
0°-90°	2124.7	42.6
90°-120°	471.5	9.4
90°-150°	2084.7	41.8
90°-180°	2868.0	57.4
0°-180°	4993.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	963	1075	967	855	963	91
15°	905	1321	917	634	905	255
25°	813	1101	816	509	813	372
35°	663	599	674	422	663	415
45°	498	361	506	347	498	386
55°	342	254	344	268	342	305
65°	203	156	206	181	203	201
75°	95	77	98	92	95	102
85°	19	20	21	15	19	22
90°	1	19	1	19	1	4
95°	46	30	46	30	46	54
105°	215	54	215	54	215	230
115°	407	58	407	58	407	401
125°	576	605	576	605	576	513
135°	712	736	712	736	712	550
145°	826	839	826	839	826	517
155°	910	910	910	910	910	419
165°	959	956	959	956	959	271
175°	980	975	980	975	980	93
180°	978	978	978	978	978	

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	967.4	969.6	973.3	974.1	981.5	987.4	994.0	994.0	996.3	995.5	989.6
5°	963.0	969.6	979.3	987.4	1000.7	1006.6	1015.5	1022.2	1028.1	1032.5	1031.8
7.5°	955.6	967.4	981.5	997.0	1014.8	1025.1	1037.7	1049.5	1057.7	1065.0	1070.2
10°	943.0	963.0	982.2	1002.9	1025.8	1039.9	1054.7	1070.2	1082.8	1096.9	1110.2
12.5°	926.0	954.8	978.5	1005.9	1034.0	1049.5	1073.2	1085.0	1109.4	1144.9	1154.5
15°	904.6	943.8	965.9	1000.7	1037.7	1050.3	1082.8	1102.0	1152.3	1174.5	1201.1
17.5°	884.6	928.2	957.8	997.7	1034.0	1058.4	1090.2	1129.4	1171.6	1203.4	1232.9
20°	868.3	910.5	946.0	990.3	1036.2	1067.3	1100.6	1147.9	1193.7	1226.3	1249.2
22.5°	831.3	885.3	926.7	976.3	1031.8	1074.7	1106.5	1158.2	1207.8	1227.8	1247.7
25°	812.8	859.4	907.5	963.7	1028.8	1079.8	1107.2	1164.9	1208.5	1215.9	1220.4
27.5°	778.8	831.3	887.5	951.9	1028.1	1071.0	1105.7	1158.2	1193.0	1187.8	1174.5
30°	736.7	801.0	863.1	932.7	1017.7	1064.3	1096.9	1144.9	1162.7	1136.1	1112.4
32.5°	705.6	766.2	835.0	915.6	1005.9	1050.3	1082.1	1119.8	1123.5	1075.4	1035.5
35°	663.4	730.7	808.4	893.5	985.9	1025.8	1055.4	1078.4	1060.6	993.3	946.0
37.5°	625.7	692.3	775.1	861.7	958.5	997.7	1021.4	1025.1	981.5	922.3	852.8
40°	584.3	653.1	739.6	830.6	928.2	962.2	977.0	965.9	903.1	834.3	753.7
42.5°	542.9	610.9	704.1	797.3	889.8	918.6	924.5	894.2	817.3	736.7	643.5
45°	497.8	568.8	662.0	755.9	845.4	861.7	862.4	818.8	727.8	643.5	556.9
47.5°	460.8	526.6	619.1	713.0	788.4	799.5	795.1	744.8	645.7	551.0	475.6
50°	420.1	483.0	574.7	667.1	731.5	734.4	723.3	651.6	554.7	468.2	408.3
52.5°	376.5	440.1	524.4	613.1	670.8	666.4	644.9	568.0	477.1	405.3	359.5
55°	341.7	397.9	477.1	563.6	604.3	591.7	568.0	489.6	417.9	357.2	317.3
57.5°	303.2	352.8	430.5	505.9	529.6	517.7	494.1	420.8	354.3	308.4	281.8
60°	267.0	312.1	380.2	443.0	461.5	448.9	421.6	355.8	307.7	269.2	249.3
62.5°	233.7	272.9	329.9	387.6	395.0	382.4	358.7	305.5	264.0	233.7	218.9
65°	202.7	239.6	285.5	329.1	335.8	322.5	298.1	259.6	224.8	205.6	191.6
67.5°	172.3	201.9	242.6	274.4	278.1	265.5	245.6	214.5	193.0	172.3	162.0
70°	145.7	167.9	199.7	225.6	227.1	215.2	204.9	176.8	160.5	145.7	137.6
72.5°	119.8	135.4	159.8	179.0	179.7	172.3	162.7	145.0	130.9	120.6	112.4
75°	94.7	108.0	122.8	139.8	139.0	133.1	125.7	114.6	102.8	96.2	92.5
77.5°	72.5	80.6	92.5	103.5	103.5	100.6	96.2	88.0	80.6	74.0	70.3
80°	51.8	57.0	66.6	70.3	71.7	71.0	67.3	61.4	58.4	53.3	51.8
82.5°	33.3	37.0	41.4	45.1	47.3	45.9	45.1	42.2	37.7	36.2	34.8
85°	19.2	20.7	22.9	25.1	25.9	25.1	26.6	24.4	22.2	22.2	21.4
87.5°	8.1	8.9	10.4	10.4	11.1	11.1	10.4	11.1	11.1	10.4	9.6
90°	0.7	2.4	4.2	5.9	7.6	8.5	9.1	10.4	11.7	12.9	14.2
92.5°	17.7	17.1	16.5	15.8	15.2	14.9	15.1	15.6	16.1	16.5	17.0
95°	46.0	40.8	35.6	30.5	25.3	22.7	23.2	24.3	25.4	26.5	27.6
97.5°	82.8	69.9	57.0	44.1	31.2	24.8	26.1	28.6	31.1	33.6	36.1
100°	125.3	103.7	82.2	60.6	39.1	28.3	29.6	32.3	35.0	37.7	40.4
102.5°	172.0	171.7	171.4	171.1	170.8	170.6	156.3	127.7	99.0	70.4	41.8
105°	215.2	219.9	224.7	229.4	234.1	236.5	215.0	172.1	129.1	86.2	43.2
107.5°	265.5	269.4	273.4	277.3	281.2	283.2	256.7	203.7	150.6	97.6	44.6
110°	313.6	316.9	320.2	323.5	326.8	328.5	305.8	260.3	214.8	169.4	123.9



TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	358.9	361.7	364.6	367.4	370.3	371.7	370.4	367.7	365.0	362.3	359.6
115°	407.1	409.8	412.4	415.1	417.8	419.1	421.1	425.0	428.9	432.9	436.8
117.5°	448.8	452.0	455.1	458.3	461.4	463.0	464.3	467.0	469.7	472.3	475.0
120°	495.6	498.0	500.3	502.7	505.0	506.2	507.6	510.4	513.3	516.1	518.9
122.5°	535.2	537.7	540.2	542.7	545.2	546.5	548.1	551.2	554.4	557.5	560.7
125°	575.6	577.6	579.7	581.7	583.8	584.8	586.3	589.3	592.2	595.2	598.2
127.5°	612.4	614.6	616.8	619.0	621.2	622.3	623.5	625.8	628.2	630.5	632.9
130°	647.1	649.6	652.1	654.6	657.1	658.4	659.3	661.0	662.7	664.5	666.2
132.5°	682.5	684.5	686.6	688.6	690.7	691.7	692.6	694.3	696.0	697.8	699.5
135°	712.2	714.7	717.2	719.7	722.2	723.5	724.2	725.6	727.1	728.5	729.9
137.5°	743.3	745.2	747.1	749.0	750.9	751.8	752.6	754.2	755.7	757.3	758.9
140°	773.8	775.1	776.3	777.6	778.9	779.5	780.4	782.1	783.8	785.5	787.2
142.5°	799.3	800.4	801.5	802.6	803.7	804.2	805.2	807.3	809.3	811.4	813.4
145°	826.2	826.0	825.9	825.7	825.6	825.5	826.8	829.5	832.2	834.8	837.5
147.5°	849.5	849.0	848.6	848.1	847.6	847.4	848.7	851.4	854.1	856.7	859.4
150°	872.2	871.1	870.0	868.9	867.8	867.2	868.5	871.0	873.5	876.1	878.6
152.5°	891.3	890.0	888.8	887.5	886.2	885.6	886.8	889.2	891.5	893.9	896.3
155°	909.7	908.3	906.9	905.4	904.0	903.3	904.2	906.1	908.0	909.9	911.8
157.5°	924.6	923.3	922.1	920.8	919.5	918.9	919.6	921.0	922.5	923.9	925.3
160°	937.3	936.4	935.4	934.5	933.6	933.1	933.6	934.5	935.4	936.4	937.3
162.5°	948.7	947.7	946.8	945.8	944.9	944.4	944.8	945.6	946.3	947.1	947.9
165°	958.6	957.6	956.7	955.7	954.8	954.3	954.5	955.0	955.5	955.9	956.4
167.5°	966.3	965.4	964.4	963.5	962.6	962.1	962.3	962.8	963.3	963.7	964.2
170°	972.7	971.8	970.8	969.9	969.0	968.5	968.7	969.0	969.3	969.6	969.9
172.5°	977.0	976.0	975.1	974.1	973.2	972.7	972.9	973.2	973.5	973.8	974.1
175°	980.5	979.4	978.3	977.2	976.1	975.6	975.8	976.1	976.4	976.7	977.0
177.5°	981.9	980.8	979.7	978.6	977.5	977.0	977.1	977.2	977.4	977.5	977.7
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1000.0	1000.7	1002.2	1009.6	1013.3	1014.0	1011.1	1017.7	1019.9	1017.7	1016.2
5°	1047.3	1051.7	1060.6	1070.2	1069.5	1070.2	1074.7	1079.1	1080.6	1074.7	1076.9
7.5°	1088.7	1097.6	1107.2	1122.0	1122.0	1129.4	1132.4	1136.1	1144.9	1140.5	1139.0
10°	1136.1	1147.9	1165.6	1189.3	1190.0	1197.4	1204.8	1216.7	1220.4	1217.4	1218.9
12.5°	1195.2	1218.2	1219.6	1245.5	1257.3	1258.8	1270.7	1268.4	1275.8	1275.8	1288.4
15°	1221.1	1256.6	1276.6	1301.7	1309.1	1300.2	1309.9	1320.2	1321.0	1321.0	1320.2
17.5°	1267.7	1281.8	1301.7	1315.0	1318.0	1318.0	1318.7	1323.2	1320.2	1314.3	1318.7
20°	1277.3	1283.2	1290.6	1289.2	1290.6	1283.2	1275.8	1268.4	1269.2	1265.5	1276.6
22.5°	1259.6	1258.1	1241.1	1230.0	1230.0	1215.2	1201.1	1194.5	1187.8	1190.0	1193.7
25°	1215.2	1192.3	1171.6	1155.3	1151.6	1127.9	1108.7	1102.8	1091.7	1100.6	1102.0
27.5°	1144.2	1118.3	1085.0	1071.0	1051.7	1042.1	1028.8	1011.1	988.1	1001.4	999.2
30°	1068.0	1029.5	1002.2	968.2	937.8	935.6	910.5	880.9	869.1	869.1	875.7
32.5°	983.0	931.9	892.0	843.9	814.3	801.7	771.4	741.8	748.5	726.3	734.4
35°	883.8	816.5	766.2	719.6	697.5	682.7	643.5	627.2	609.4	599.1	618.3
37.5°	789.2	711.5	647.2	596.1	588.0	561.4	534.7	524.4	514.0	518.5	517.7
40°	673.8	605.0	547.3	507.4	493.3	480.8	463.0	450.4	443.8	447.5	448.2
42.5°	569.5	511.8	468.9	440.8	429.0	420.1	411.2	400.9	398.7	398.7	401.6
45°	488.9	441.6	412.7	389.8	383.1	376.5	369.8	365.4	363.9	360.9	363.2
47.5°	424.5	386.8	369.1	352.1	344.7	343.2	337.3	335.0	332.1	331.3	332.1
50°	370.5	346.9	330.6	321.0	315.8	313.6	310.6	306.2	304.7	308.4	306.9
52.5°	332.8	310.6	301.8	292.1	289.2	286.2	281.8	282.5	281.8	280.3	280.3
55°	295.1	281.1	272.2	264.8	264.0	261.1	257.4	255.9	255.2	253.7	255.9
57.5°	264.8	253.7	245.6	238.9	235.9	235.9	232.2	229.3	229.3	228.5	229.3
60°	234.5	223.4	218.2	211.5	209.3	208.6	206.4	204.9	202.7	202.7	202.7
62.5°	206.4	197.5	191.6	185.6	186.4	182.7	179.7	178.2	178.2	179.0	179.0
65°	179.7	173.8	166.4	161.2	159.8	159.0	157.5	156.8	154.6	156.1	156.1
67.5°	155.3	147.2	142.7	140.5	138.3	137.6	136.1	134.6	133.9	133.1	134.6
70°	130.9	124.3	120.6	119.1	116.9	116.1	115.4	113.2	113.9	114.6	115.4
72.5°	108.7	102.8	102.1	97.6	97.6	97.6	94.7	96.2	95.4	93.9	95.4
75°	85.8	82.8	81.4	79.1	79.9	79.1	78.4	76.2	76.2	76.9	77.7
77.5°	68.0	65.1	64.3	62.1	60.6	62.1	60.6	59.9	59.9	60.6	60.6
80°	50.3	48.8	46.6	46.6	46.6	45.9	45.9	45.9	45.1	44.4	45.1
82.5°	33.3	33.3	32.5	31.8	32.5	31.1	31.8	31.8	31.8	31.8	31.8
85°	21.4	20.7	20.7	20.0	20.0	20.0	20.7	19.2	19.2	20.0	20.0
87.5°	9.6	9.6	9.6	10.4	9.6	9.6	9.6	10.4	9.6	9.6	9.6
90°	15.0	15.8	16.5	17.3	17.7	17.9	18.2	18.5	18.8	19.1	18.8
92.5°	17.3	17.6	17.9	18.2	18.4	18.5	18.6	18.8	18.9	19.1	18.9
95°	28.4	29.2	29.9	30.7	31.1	31.0	30.9	30.7	30.6	30.4	30.6
97.5°	36.6	37.0	37.5	38.0	38.2	38.3	38.4	38.6	38.7	38.9	38.7
100°	41.6	42.9	44.1	45.4	46.0	46.2	46.5	46.8	47.1	47.4	47.1
102.5°	43.5	45.3	47.0	48.7	49.6	49.8	50.3	50.8	51.2	51.7	51.2
105°	44.9	46.7	48.4	50.1	51.0	51.3	51.9	52.6	53.2	53.8	53.2
107.5°	46.3	48.1	49.8	51.5	52.4	52.7	53.3	54.0	54.6	55.2	54.6
110°	108.2	92.4	76.7	61.0	53.1	53.4	54.0	54.7	55.3	55.9	55.3

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.8	224.0	156.2	88.4	54.5	54.7	55.2	55.7	56.1	56.6	56.1
115°	364.0	291.1	218.3	145.4	109.0	103.3	92.0	80.7	69.4	58.1	69.4
117.5°	452.5	430.0	407.5	385.0	373.8	353.2	312.0	270.7	229.5	188.3	229.5
120°	520.8	522.7	524.6	526.5	527.4	516.8	495.5	474.3	453.0	431.8	453.0
122.5°	561.6	562.6	563.5	564.4	564.9	565.0	565.2	565.3	565.5	565.7	565.5
125°	599.3	600.4	601.5	602.6	603.2	603.4	603.9	604.4	604.8	605.3	604.8
127.5°	634.5	636.1	637.6	639.2	640.0	640.1	640.2	640.4	640.5	640.7	640.5
130°	667.9	669.7	671.4	673.1	674.0	673.9	673.8	673.6	673.5	673.3	673.5
132.5°	700.9	702.3	703.7	705.1	705.8	705.7	705.6	705.4	705.3	705.1	705.3
135°	731.5	733.1	734.6	736.2	737.0	736.8	736.5	736.2	735.9	735.6	735.9
137.5°	760.5	762.1	763.6	765.2	766.0	765.8	765.3	764.8	764.4	763.9	764.4
140°	788.6	790.0	791.5	792.9	793.6	793.2	792.4	791.7	790.9	790.1	790.9
142.5°	814.7	815.9	817.2	818.5	819.1	818.7	817.9	817.2	816.4	815.6	816.4
145°	838.6	839.7	840.8	841.9	842.5	842.1	841.3	840.5	839.7	838.9	839.7
147.5°	860.2	861.0	861.8	862.6	863.0	862.7	862.1	861.4	860.8	860.2	860.8
150°	879.5	880.5	881.4	882.3	882.8	882.4	881.6	880.9	880.1	879.3	880.1
152.5°	897.2	898.2	899.1	900.0	900.5	900.0	898.9	897.8	896.7	895.6	896.7
155°	912.8	913.7	914.7	915.6	916.1	915.5	914.2	912.9	911.7	910.4	911.7
157.5°	926.4	927.5	928.6	929.7	930.2	929.6	928.3	927.1	925.8	924.6	925.8
160°	938.3	939.2	940.2	941.1	941.6	941.0	939.9	938.8	937.7	936.6	937.7
162.5°	949.0	950.1	951.2	952.3	952.9	952.2	950.8	949.3	947.9	946.5	947.9
165°	957.5	958.6	959.7	960.8	961.4	960.8	959.7	958.6	957.5	956.4	957.5
167.5°	965.3	966.4	967.5	968.6	969.2	968.5	967.1	965.6	964.2	962.8	964.2
170°	971.0	972.1	973.2	974.3	974.8	974.1	972.7	971.3	969.9	968.5	969.9
172.5°	975.2	976.3	977.4	978.5	979.1	978.4	977.0	975.5	974.1	972.7	974.1
175°	978.1	979.2	980.3	981.4	981.9	981.1	979.5	978.0	976.4	974.8	976.4
177.5°	978.8	979.9	981.0	982.1	982.6	981.9	980.5	979.1	977.7	976.3	977.7
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	1019.9	1014.8	1010.3	1011.1	1014.8	1011.8	1004.4	994.8	991.1	986.6	991.1
5°	1081.3	1076.9	1068.0	1068.7	1066.5	1063.6	1051.7	1036.9	1036.9	1025.1	1023.6
7.5°	1142.0	1135.3	1129.4	1127.9	1119.8	1113.9	1103.5	1082.8	1074.7	1060.6	1052.5
10°	1210.0	1204.8	1198.2	1190.0	1185.6	1175.3	1158.2	1127.9	1113.1	1093.9	1079.8
12.5°	1278.8	1278.1	1263.3	1247.0	1246.3	1230.0	1218.2	1177.5	1157.5	1131.6	1098.3
15°	1322.4	1318.7	1310.6	1302.5	1304.7	1286.9	1260.3	1212.2	1198.9	1167.9	1132.4
17.5°	1321.7	1321.7	1319.5	1318.0	1315.8	1310.6	1295.8	1264.0	1242.6	1203.4	1170.1
20°	1279.5	1289.2	1291.4	1290.6	1298.0	1301.7	1301.0	1281.0	1264.0	1229.2	1195.2
22.5°	1195.2	1217.4	1227.0	1232.9	1248.5	1256.6	1275.8	1268.4	1264.0	1238.1	1209.3
25°	1116.8	1124.2	1153.1	1154.5	1176.0	1196.0	1215.2	1227.8	1244.0	1234.4	1210.0
27.5°	1015.5	1032.5	1053.2	1068.7	1073.2	1113.9	1145.7	1169.3	1206.3	1209.3	1201.1
30°	900.9	909.0	943.0	963.7	987.4	1017.0	1062.8	1103.5	1136.8	1167.1	1177.5
32.5°	761.1	794.3	814.3	839.5	860.2	912.7	968.9	1021.4	1059.9	1110.9	1133.1
35°	633.1	659.0	693.0	703.4	741.1	785.5	858.7	926.0	984.4	1036.2	1081.3
37.5°	527.3	548.1	584.3	600.6	622.8	679.7	741.1	824.7	894.9	958.5	1014.8
40°	454.9	470.4	497.8	502.9	521.4	573.2	622.8	701.2	794.3	880.1	941.5
42.5°	405.3	412.7	431.2	437.9	449.7	484.4	528.8	602.8	689.3	778.1	864.6
45°	369.8	375.0	386.1	392.0	406.8	422.3	458.6	517.7	585.8	675.3	768.5
47.5°	338.0	344.7	349.1	352.8	360.9	377.9	401.6	445.2	510.3	592.4	682.7
50°	311.4	313.6	321.7	322.5	327.7	338.7	360.9	387.6	439.3	505.9	593.2
52.5°	284.8	287.0	292.1	297.3	299.5	308.4	323.2	345.4	383.9	436.4	514.0
55°	258.1	261.1	266.3	270.0	272.2	279.6	288.5	309.9	340.2	377.2	440.8
57.5°	231.5	238.2	239.6	241.9	245.6	253.7	261.8	274.4	298.1	332.1	378.7
60°	206.4	208.6	213.7	216.0	219.7	224.1	234.5	244.1	261.1	287.7	329.9
62.5°	180.5	185.6	187.9	190.1	193.0	198.2	204.9	215.2	230.0	251.5	284.8
65°	158.3	159.0	163.5	166.4	169.4	173.1	179.7	189.3	198.2	218.2	242.6
67.5°	136.8	138.3	139.8	142.7	146.4	150.1	156.1	161.2	172.3	185.6	204.9
70°	116.1	116.1	119.8	122.0	121.3	125.7	130.2	136.1	144.2	156.8	172.3
72.5°	97.6	96.9	99.8	100.6	102.1	105.0	108.0	113.9	118.3	128.0	139.8
75°	77.7	79.1	80.6	80.6	82.8	85.1	88.0	91.0	96.2	102.1	110.9
77.5°	61.4	61.4	62.9	63.6	65.8	65.1	68.0	71.0	74.7	79.9	86.5
80°	45.1	46.6	46.6	46.6	47.3	48.1	51.0	53.3	55.5	59.2	62.1
82.5°	31.8	31.8	33.3	33.3	33.3	34.8	34.8	35.5	37.0	39.2	41.4
85°	20.0	20.0	20.0	20.7	20.0	20.7	22.2	21.4	22.2	23.7	23.7
87.5°	9.6	9.6	9.6	9.6	9.6	10.4	9.6	10.4	11.1	11.1	11.1
90°	18.5	18.2	17.9	17.7	17.3	16.5	15.8	15.0	14.2	12.9	11.7
92.5°	18.8	18.6	18.5	18.4	18.2	17.9	17.6	17.3	17.0	16.5	16.1
95°	30.7	30.9	31.0	31.1	30.7	29.9	29.2	28.4	27.6	26.5	25.4
97.5°	38.6	38.4	38.3	38.2	38.0	37.5	37.0	36.6	36.1	33.6	31.1
100°	46.8	46.5	46.2	46.0	45.4	44.1	42.9	41.6	40.4	37.7	35.0
102.5°	50.8	50.3	49.8	49.6	48.7	47.0	45.3	43.5	41.8	70.4	99.0
105°	52.6	51.9	51.3	51.0	50.1	48.4	46.7	44.9	43.2	86.2	129.1
107.5°	54.0	53.3	52.7	52.4	51.5	49.8	48.1	46.3	44.6	97.6	150.6
110°	54.7	54.0	53.4	53.1	61.0	76.7	92.4	108.2	123.9	169.4	214.8

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.7	55.2	54.7	54.5	88.4	156.2	224.0	291.8	359.6	362.3	365.0
115°	80.7	92.0	103.3	109.0	145.4	218.3	291.1	364.0	436.8	432.9	428.9
117.5°	270.7	312.0	353.2	373.8	385.0	407.5	430.0	452.5	475.0	472.3	469.7
120°	474.3	495.5	516.8	527.4	526.5	524.6	522.7	520.8	518.9	516.1	513.3
122.5°	565.3	565.2	565.0	564.9	564.4	563.5	562.6	561.6	560.7	557.5	554.4
125°	604.4	603.9	603.4	603.2	602.6	601.5	600.4	599.3	598.2	595.2	592.2
127.5°	640.4	640.2	640.1	640.0	639.2	637.6	636.1	634.5	632.9	630.5	628.2
130°	673.6	673.8	673.9	674.0	673.1	671.4	669.7	667.9	666.2	664.5	662.7
132.5°	705.4	705.6	705.7	705.8	705.1	703.7	702.3	700.9	699.5	697.8	696.0
135°	736.2	736.5	736.8	737.0	736.2	734.6	733.1	731.5	729.9	728.5	727.1
137.5°	764.8	765.3	765.8	766.0	765.2	763.6	762.1	760.5	758.9	757.3	755.7
140°	791.7	792.4	793.2	793.6	792.9	791.5	790.0	788.6	787.2	785.5	783.8
142.5°	817.2	817.9	818.7	819.1	818.5	817.2	815.9	814.7	813.4	811.4	809.3
145°	840.5	841.3	842.1	842.5	841.9	840.8	839.7	838.6	837.5	834.8	832.2
147.5°	861.4	862.1	862.7	863.0	862.6	861.8	861.0	860.2	859.4	856.7	854.1
150°	880.9	881.6	882.4	882.8	882.3	881.4	880.5	879.5	878.6	876.1	873.5
152.5°	897.8	898.9	900.0	900.5	900.0	899.1	898.2	897.2	896.3	893.9	891.5
155°	912.9	914.2	915.5	916.1	915.6	914.7	913.7	912.8	911.8	909.9	908.0
157.5°	927.1	928.3	929.6	930.2	929.7	928.6	927.5	926.4	925.3	923.9	922.5
160°	938.8	939.9	941.0	941.6	941.1	940.2	939.2	938.3	937.3	936.4	935.4
162.5°	949.3	950.8	952.2	952.9	952.3	951.2	950.1	949.0	947.9	947.1	946.3
165°	958.6	959.7	960.8	961.4	960.8	959.7	958.6	957.5	956.4	955.9	955.5
167.5°	965.6	967.1	968.5	969.2	968.6	967.5	966.4	965.3	964.2	963.7	963.3
170°	971.3	972.7	974.1	974.8	974.3	973.2	972.1	971.0	969.9	969.6	969.3
172.5°	975.5	977.0	978.4	979.1	978.5	977.4	976.3	975.2	974.1	973.8	973.5
175°	978.0	979.5	981.1	981.9	981.4	980.3	979.2	978.1	977.0	976.7	976.4
177.5°	979.1	980.5	981.9	982.6	982.1	981.0	979.9	978.8	977.7	977.5	977.4
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	987.4	983.7	981.5	983.0	978.5	967.4	967.4	971.1	966.7	962.2	955.6
5°	1014.8	1007.4	1002.9	1002.2	991.8	974.1	970.4	966.7	957.1	946.7	935.6
7.5°	1041.4	1028.1	1020.7	1015.5	1000.7	977.8	968.2	960.0	944.5	929.0	914.9
10°	1063.6	1044.3	1035.5	1027.3	1008.1	979.3	963.7	948.9	929.0	909.0	891.2
12.5°	1081.3	1059.1	1048.0	1036.2	1012.5	974.8	955.6	931.9	911.9	885.3	867.6
15°	1110.9	1065.0	1054.7	1043.6	1019.2	967.4	943.8	917.1	889.8	854.3	835.0
17.5°	1134.6	1073.2	1072.4	1048.8	1017.0	964.5	928.2	893.5	863.9	828.4	798.0
20°	1148.6	1085.8	1073.9	1049.5	1009.6	944.5	906.8	868.3	836.5	793.6	763.3
22.5°	1160.5	1103.5	1072.4	1042.9	994.0	937.8	882.4	846.1	802.5	755.9	727.0
25°	1164.9	1107.2	1074.7	1040.6	983.0	918.6	855.7	816.5	767.7	725.6	686.4
27.5°	1165.6	1106.5	1066.5	1031.0	967.4	893.5	829.1	787.7	733.7	684.9	645.7
30°	1158.2	1098.3	1062.1	1023.6	952.6	870.5	796.6	750.7	693.0	644.2	603.5
32.5°	1136.1	1082.1	1052.5	1010.3	933.4	838.7	765.5	714.5	653.8	605.7	566.5
35°	1099.1	1062.1	1029.5	990.3	908.3	809.1	734.4	674.5	613.1	567.3	530.3
37.5°	1053.2	1033.2	1002.9	964.5	879.4	782.5	699.7	633.1	571.7	527.3	491.1
40°	991.1	996.3	966.7	931.9	845.4	746.3	654.6	591.0	533.3	491.8	456.3
42.5°	923.8	945.2	928.2	894.9	807.7	706.3	621.3	551.0	494.8	451.9	422.3
45°	851.3	888.3	877.9	853.5	768.5	664.2	573.9	505.9	456.3	414.9	389.0
47.5°	772.2	824.7	824.7	806.9	724.8	622.0	533.3	463.7	414.9	385.3	360.2
50°	691.5	750.7	760.3	748.5	676.0	573.9	483.7	420.8	378.7	349.8	331.3
52.5°	607.2	676.0	693.8	687.8	624.2	528.1	443.0	381.6	343.2	318.0	301.8
55°	526.6	606.5	625.7	627.9	568.8	477.8	397.9	343.9	306.9	289.9	275.9
57.5°	450.4	527.3	548.8	552.5	512.6	431.9	355.8	308.4	275.1	261.1	250.0
60°	385.3	449.7	477.8	485.9	451.2	378.7	316.6	270.7	245.6	232.2	221.9
62.5°	332.1	383.9	413.4	415.7	400.1	332.1	275.9	237.4	216.0	204.1	199.0
65°	280.3	326.9	344.7	353.5	341.0	287.7	238.2	206.4	189.3	179.0	173.8
67.5°	238.9	268.5	283.3	295.1	282.5	242.6	202.7	176.8	164.2	153.8	150.9
70°	196.0	220.4	231.5	243.3	232.2	201.9	173.1	149.4	138.3	130.2	126.5
72.5°	156.8	176.0	186.4	193.8	187.1	162.0	138.3	122.0	113.9	108.0	105.8
75°	124.3	137.6	143.5	148.7	145.7	126.5	111.7	98.4	91.0	85.8	84.3
77.5°	94.7	104.3	110.9	112.4	108.7	96.2	83.6	75.4	69.5	66.6	65.1
80°	67.3	73.2	76.9	79.1	75.4	70.3	61.4	55.5	50.3	46.6	45.9
82.5°	45.1	48.1	51.0	50.3	48.8	44.4	39.2	36.2	34.0	31.1	31.1
85°	25.9	26.6	28.1	28.8	28.1	25.1	22.2	20.7	19.2	17.0	17.0
87.5°	11.1	11.8	11.8	12.6	11.1	11.1	9.6	8.1	8.1	7.4	6.7
90°	10.4	9.1	8.5	7.6	5.9	4.2	2.4	0.7	2.4	4.2	5.9
92.5°	15.6	15.1	14.9	15.2	15.8	16.5	17.1	17.7	17.1	16.5	15.8
95°	24.3	23.2	22.7	25.3	30.5	35.6	40.8	46.0	40.8	35.6	30.5
97.5°	28.6	26.1	24.8	31.2	44.1	57.0	69.9	82.8	69.9	57.0	44.1
100°	32.3	29.6	28.3	39.1	60.6	82.2	103.7	125.3	103.7	82.2	60.6
102.5°	127.7	156.3	170.6	170.8	171.1	171.4	171.7	172.0	171.7	171.4	171.1
105°	172.1	215.0	236.5	234.1	229.4	224.7	219.9	215.2	219.9	224.7	229.4
107.5°	203.7	256.7	283.2	281.2	277.3	273.4	269.4	265.5	269.4	273.4	277.3
110°	260.3	305.8	328.5	326.8	323.5	320.2	316.9	313.6	316.9	320.2	323.5

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	367.7	370.4	371.7	370.3	367.4	364.6	361.7	358.9	361.7	364.6	367.4
115°	425.0	421.1	419.1	417.8	415.1	412.4	409.8	407.1	409.8	412.4	415.1
117.5°	467.0	464.3	463.0	461.4	458.3	455.1	452.0	448.8	452.0	455.1	458.3
120°	510.4	507.6	506.2	505.0	502.7	500.3	498.0	495.6	498.0	500.3	502.7
122.5°	551.2	548.1	546.5	545.2	542.7	540.2	537.7	535.2	537.7	540.2	542.7
125°	589.3	586.3	584.8	583.8	581.7	579.7	577.6	575.6	577.6	579.7	581.7
127.5°	625.8	623.5	622.3	621.2	619.0	616.8	614.6	612.4	614.6	616.8	619.0
130°	661.0	659.3	658.4	657.1	654.6	652.1	649.6	647.1	649.6	652.1	654.6
132.5°	694.3	692.6	691.7	690.7	688.6	686.6	684.5	682.5	684.5	686.6	688.6
135°	725.6	724.2	723.5	722.2	719.7	717.2	714.7	712.2	714.7	717.2	719.7
137.5°	754.2	752.6	751.8	750.9	749.0	747.1	745.2	743.3	745.2	747.1	749.0
140°	782.1	780.4	779.5	778.9	777.6	776.3	775.1	773.8	775.1	776.3	777.6
142.5°	807.3	805.2	804.2	803.7	802.6	801.5	800.4	799.3	800.4	801.5	802.6
145°	829.5	826.8	825.5	825.6	825.7	825.9	826.0	826.2	826.0	825.9	825.7
147.5°	851.4	848.7	847.4	847.6	848.1	848.6	849.0	849.5	849.0	848.6	848.1
150°	871.0	868.5	867.2	867.8	868.9	870.0	871.1	872.2	871.1	870.0	868.9
152.5°	889.2	886.8	885.6	886.2	887.5	888.8	890.0	891.3	890.0	888.8	887.5
155°	906.1	904.2	903.3	904.0	905.4	906.9	908.3	909.7	908.3	906.9	905.4
157.5°	921.0	919.6	918.9	919.5	920.8	922.1	923.3	924.6	923.3	922.1	920.8
160°	934.5	933.6	933.1	933.6	934.5	935.4	936.4	937.3	936.4	935.4	934.5
162.5°	945.6	944.8	944.4	944.9	945.8	946.8	947.7	948.7	947.7	946.8	945.8
165°	955.0	954.5	954.3	954.8	955.7	956.7	957.6	958.6	957.6	956.7	955.7
167.5°	962.8	962.3	962.1	962.6	963.5	964.4	965.4	966.3	965.4	964.4	963.5
170°	969.0	968.7	968.5	969.0	969.9	970.8	971.8	972.7	971.8	970.8	969.9
172.5°	973.2	972.9	972.7	973.2	974.1	975.1	976.0	977.0	976.0	975.1	974.1
175°	976.1	975.8	975.6	976.1	977.2	978.3	979.4	980.5	979.4	978.3	977.2
177.5°	977.2	977.1	977.0	977.5	978.6	979.7	980.8	981.9	980.8	979.7	978.6
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	951.9	955.6	954.8	947.5	939.3	932.7	920.1	921.6	917.1	917.9	922.3
5°	928.2	928.2	925.3	914.9	901.6	894.2	880.1	876.4	867.6	866.8	866.1
7.5°	903.1	899.4	895.7	880.9	864.6	852.8	833.5	829.1	820.2	814.3	811.4
10°	873.5	868.3	860.9	843.9	823.9	809.1	789.2	783.3	766.2	758.8	754.4
12.5°	840.9	838.0	826.2	812.1	779.6	763.3	734.4	740.4	723.3	708.6	706.3
15°	808.4	797.3	790.7	767.7	728.5	721.1	698.2	686.4	670.8	659.0	659.0
17.5°	776.6	759.6	744.8	720.4	691.5	670.8	653.8	647.9	628.7	616.8	614.6
20°	734.4	715.2	711.5	676.8	656.8	633.9	617.6	602.8	588.7	583.6	579.9
22.5°	694.5	672.3	666.4	636.8	616.8	593.9	577.6	567.3	556.9	553.2	546.6
25°	651.6	638.3	629.4	597.6	575.4	554.0	542.9	535.5	525.9	525.1	520.7
27.5°	610.2	597.6	588.7	558.4	542.1	522.2	513.3	505.2	500.0	497.8	495.5
30°	574.7	560.6	550.3	528.1	508.1	491.8	484.4	479.3	476.3	472.6	471.9
32.5°	535.5	527.3	513.3	496.3	480.8	465.2	460.8	457.1	452.6	451.2	450.4
35°	502.2	491.1	482.2	463.0	456.3	443.0	437.9	434.9	429.0	427.5	426.0
37.5°	469.7	459.3	449.7	437.9	425.3	417.9	414.9	410.5	407.5	408.3	406.8
40°	437.1	429.0	421.6	409.0	401.6	397.9	392.0	387.6	386.1	386.8	386.1
42.5°	405.3	397.9	393.5	383.9	376.5	372.8	369.1	364.6	366.9	366.9	369.1
45°	376.5	369.8	366.9	359.5	355.0	349.1	345.4	344.7	347.6	346.9	346.9
47.5°	346.9	344.7	341.0	334.3	328.4	324.7	324.0	324.0	326.9	328.4	327.7
50°	324.0	319.5	315.1	309.9	305.5	304.0	301.8	303.2	306.2	306.2	307.7
52.5°	295.1	292.1	290.7	286.2	283.3	283.3	283.3	284.0	286.2	288.5	287.7
55°	270.0	267.7	266.3	264.0	260.3	261.1	260.3	261.8	264.0	266.3	267.7
57.5°	243.3	242.6	241.1	237.4	237.4	236.7	238.9	239.6	243.3	244.8	247.0
60°	219.7	217.4	217.4	214.5	214.5	214.5	216.7	218.9	221.9	222.6	224.1
62.5°	194.5	194.5	193.8	191.6	191.6	193.8	194.5	197.5	199.0	199.0	201.2
65°	170.9	170.1	169.4	170.1	170.9	170.9	173.1	174.5	176.0	176.8	177.5
67.5°	147.2	146.4	147.9	147.2	148.7	151.6	150.9	153.1	155.3	155.3	156.1
70°	125.0	126.5	125.7	127.2	126.5	128.0	130.2	130.9	130.9	131.7	133.9
72.5°	104.3	104.3	104.3	103.5	104.3	105.8	107.2	108.0	109.5	110.2	112.4
75°	84.3	84.3	82.8	84.3	84.3	85.8	87.3	87.3	87.3	88.8	91.0
77.5°	63.6	64.3	63.6	65.1	65.1	65.8	67.3	66.6	68.0	68.8	69.5
80°	46.6	45.9	45.9	45.9	46.6	46.6	48.1	48.8	48.8	51.0	49.6
82.5°	29.6	30.3	29.6	30.3	30.3	31.1	30.3	31.1	31.8	33.3	32.5
85°	17.0	16.3	16.3	17.0	16.3	16.3	17.0	16.3	17.0	16.3	17.0
87.5°	6.7	5.9	5.9	5.9	5.9	5.2	5.2	4.4	4.4	4.4	3.7
90°	7.6	8.5	9.1	10.4	11.7	12.9	14.2	15.0	15.8	16.5	17.3
92.5°	15.2	14.9	15.1	15.6	16.1	16.5	17.0	17.3	17.6	17.9	18.2
95°	25.3	22.7	23.2	24.3	25.4	26.5	27.6	28.4	29.2	29.9	30.7
97.5°	31.2	24.8	26.1	28.6	31.1	33.6	36.1	36.6	37.0	37.5	38.0
100°	39.1	28.3	29.6	32.3	35.0	37.7	40.4	41.6	42.9	44.1	45.4
102.5°	170.8	170.6	156.3	127.7	99.0	70.4	41.8	43.5	45.3	47.0	48.7
105°	234.1	236.5	215.0	172.1	129.1	86.2	43.2	44.9	46.7	48.4	50.1
107.5°	281.2	283.2	256.7	203.7	150.6	97.6	44.6	46.3	48.1	49.8	51.5
110°	326.8	328.5	305.8	260.3	214.8	169.4	123.9	108.2	92.4	76.7	61.0

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	370.3	371.7	370.4	367.7	365.0	362.3	359.6	291.8	224.0	156.2	88.4
115°	417.8	419.1	421.1	425.0	428.9	432.9	436.8	364.0	291.1	218.3	145.4
117.5°	461.4	463.0	464.3	467.0	469.7	472.3	475.0	452.5	430.0	407.5	385.0
120°	505.0	506.2	507.6	510.4	513.3	516.1	518.9	520.8	522.7	524.6	526.5
122.5°	545.2	546.5	548.1	551.2	554.4	557.5	560.7	561.6	562.6	563.5	564.4
125°	583.8	584.8	586.3	589.3	592.2	595.2	598.2	599.3	600.4	601.5	602.6
127.5°	621.2	622.3	623.5	625.8	628.2	630.5	632.9	634.5	636.1	637.6	639.2
130°	657.1	658.4	659.3	661.0	662.7	664.5	666.2	667.9	669.7	671.4	673.1
132.5°	690.7	691.7	692.6	694.3	696.0	697.8	699.5	700.9	702.3	703.7	705.1
135°	722.2	723.5	724.2	725.6	727.1	728.5	729.9	731.5	733.1	734.6	736.2
137.5°	750.9	751.8	752.6	754.2	755.7	757.3	758.9	760.5	762.1	763.6	765.2
140°	778.9	779.5	780.4	782.1	783.8	785.5	787.2	788.6	790.0	791.5	792.9
142.5°	803.7	804.2	805.2	807.3	809.3	811.4	813.4	814.7	815.9	817.2	818.5
145°	825.6	825.5	826.8	829.5	832.2	834.8	837.5	838.6	839.7	840.8	841.9
147.5°	847.6	847.4	848.7	851.4	854.1	856.7	859.4	860.2	861.0	861.8	862.6
150°	867.8	867.2	868.5	871.0	873.5	876.1	878.6	879.5	880.5	881.4	882.3
152.5°	886.2	885.6	886.8	889.2	891.5	893.9	896.3	897.2	898.2	899.1	900.0
155°	904.0	903.3	904.2	906.1	908.0	909.9	911.8	912.8	913.7	914.7	915.6
157.5°	919.5	918.9	919.6	921.0	922.5	923.9	925.3	926.4	927.5	928.6	929.7
160°	933.6	933.1	933.6	934.5	935.4	936.4	937.3	938.3	939.2	940.2	941.1
162.5°	944.9	944.4	944.8	945.6	946.3	947.1	947.9	949.0	950.1	951.2	952.3
165°	954.8	954.3	954.5	955.0	955.5	955.9	956.4	957.5	958.6	959.7	960.8
167.5°	962.6	962.1	962.3	962.8	963.3	963.7	964.2	965.3	966.4	967.5	968.6
170°	969.0	968.5	968.7	969.0	969.3	969.6	969.9	971.0	972.1	973.2	974.3
172.5°	973.2	972.7	972.9	973.2	973.5	973.8	974.1	975.2	976.3	977.4	978.5
175°	976.1	975.6	975.8	976.1	976.4	976.7	977.0	978.1	979.2	980.3	981.4
177.5°	977.5	977.0	977.1	977.2	977.4	977.5	977.7	978.8	979.9	981.0	982.1
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	917.1	919.3	914.2	912.7	914.2	909.0	910.5	911.9	911.9	914.2	915.6
5°	863.9	860.9	855.7	854.3	852.8	855.0	853.5	855.7	856.5	861.7	862.4
7.5°	811.4	806.9	802.5	798.0	796.6	792.9	796.6	796.6	801.7	800.3	804.0
10°	749.2	748.5	742.6	740.4	737.4	731.5	739.6	737.4	741.1	747.8	749.2
12.5°	703.4	695.2	698.9	688.6	692.3	686.4	687.1	687.1	693.0	693.8	692.3
15°	659.7	653.1	643.5	639.0	636.8	633.9	643.5	644.2	639.8	650.1	646.4
17.5°	615.4	615.4	606.5	604.3	598.4	601.3	599.8	600.6	599.1	606.5	610.2
20°	576.9	573.2	570.2	571.0	563.6	562.1	560.6	562.1	567.3	572.5	573.9
22.5°	545.8	543.6	536.2	537.7	531.8	534.0	532.5	536.2	537.0	537.0	542.1
25°	516.3	513.3	514.0	511.1	508.9	508.9	506.6	508.9	511.8	513.3	514.0
27.5°	494.1	491.8	488.1	485.9	487.4	483.7	486.7	488.9	488.9	487.4	488.9
30°	467.4	468.9	468.9	461.5	464.5	463.0	465.2	466.7	466.7	467.4	466.0
32.5°	449.7	445.2	444.5	443.8	443.8	440.8	440.8	443.0	443.8	444.5	446.7
35°	426.0	426.0	422.3	424.5	421.6	422.3	421.6	422.3	423.8	421.6	423.8
37.5°	404.6	405.3	403.8	405.3	406.1	404.6	403.1	406.1	404.6	404.6	403.1
40°	386.1	385.3	386.1	386.1	386.1	386.8	385.3	385.3	385.3	383.9	382.4
42.5°	370.5	366.1	367.6	368.3	366.1	366.1	366.9	366.1	368.3	363.9	363.9
45°	348.4	346.9	347.6	347.6	349.1	346.9	348.4	349.1	346.9	346.1	344.7
47.5°	328.4	329.9	328.4	329.9	329.9	331.3	328.4	329.1	329.9	326.9	324.7
50°	308.4	308.4	310.6	309.9	310.6	309.2	309.2	308.4	309.2	307.7	305.5
52.5°	289.9	287.7	291.4	290.7	289.9	289.2	288.5	289.2	287.7	286.2	286.2
55°	267.0	267.0	269.2	270.0	270.0	268.5	267.0	267.7	267.0	266.3	265.5
57.5°	248.5	245.6	247.0	247.8	247.8	245.6	247.0	245.6	245.6	246.3	244.1
60°	224.8	224.8	223.4	225.6	225.6	224.1	224.1	224.8	223.4	222.6	221.9
62.5°	199.7	200.4	202.7	203.4	204.1	202.7	201.2	201.9	201.9	199.7	200.4
65°	178.2	179.7	182.7	181.9	180.5	181.2	179.7	180.5	178.2	179.0	176.8
67.5°	157.5	156.8	157.5	157.5	159.0	158.3	156.8	156.8	156.1	158.3	156.1
70°	135.4	135.4	135.4	135.4	136.1	136.8	135.4	133.9	134.6	133.1	132.4
72.5°	112.4	113.2	112.4	113.9	111.7	113.2	113.2	112.4	111.7	111.7	111.7
75°	91.0	92.5	90.2	91.0	90.2	91.7	91.0	91.0	89.5	88.8	89.5
77.5°	69.5	70.3	68.8	69.5	68.8	69.5	69.5	68.8	68.8	68.8	68.8
80°	49.6	50.3	49.6	48.8	48.1	49.6	48.1	48.8	49.6	48.8	50.3
82.5°	31.8	31.8	31.1	31.8	30.3	30.3	31.1	31.1	30.3	31.8	30.3
85°	15.5	15.5	17.0	15.5	14.8	14.8	14.8	15.5	14.8	16.3	15.5
87.5°	3.7	3.0	3.7	3.7	3.0	3.0	3.7	3.0	3.7	4.4	3.0
90°	17.7	17.9	18.2	18.5	18.8	19.1	18.8	18.5	18.2	17.9	17.7
92.5°	18.4	18.5	18.6	18.8	18.9	19.1	18.9	18.8	18.6	18.5	18.4
95°	31.1	31.0	30.9	30.7	30.6	30.4	30.6	30.7	30.9	31.0	31.1
97.5°	38.2	38.3	38.4	38.6	38.7	38.9	38.7	38.6	38.4	38.3	38.2
100°	46.0	46.2	46.5	46.8	47.1	47.4	47.1	46.8	46.5	46.2	46.0
102.5°	49.6	49.8	50.3	50.8	51.2	51.7	51.2	50.8	50.3	49.8	49.6
105°	51.0	51.3	51.9	52.6	53.2	53.8	53.2	52.6	51.9	51.3	51.0
107.5°	52.4	52.7	53.3	54.0	54.6	55.2	54.6	54.0	53.3	52.7	52.4
110°	53.1	53.4	54.0	54.7	55.3	55.9	55.3	54.7	54.0	53.4	53.1

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.5	54.7	55.2	55.7	56.1	56.6	56.1	55.7	55.2	54.7	54.5
115°	109.0	103.3	92.0	80.7	69.4	58.1	69.4	80.7	92.0	103.3	109.0
117.5°	373.8	353.2	312.0	270.7	229.5	188.3	229.5	270.7	312.0	353.2	373.8
120°	527.4	516.8	495.5	474.3	453.0	431.8	453.0	474.3	495.5	516.8	527.4
122.5°	564.9	565.0	565.2	565.3	565.5	565.7	565.5	565.3	565.2	565.0	564.9
125°	603.2	603.4	603.9	604.4	604.8	605.3	604.8	604.4	603.9	603.4	603.2
127.5°	640.0	640.1	640.2	640.4	640.5	640.7	640.5	640.4	640.2	640.1	640.0
130°	674.0	673.9	673.8	673.6	673.5	673.3	673.5	673.6	673.8	673.9	674.0
132.5°	705.8	705.7	705.6	705.4	705.3	705.1	705.3	705.4	705.6	705.7	705.8
135°	737.0	736.8	736.5	736.2	735.9	735.6	735.9	736.2	736.5	736.8	737.0
137.5°	766.0	765.8	765.3	764.8	764.4	763.9	764.4	764.8	765.3	765.8	766.0
140°	793.6	793.2	792.4	791.7	790.9	790.1	790.9	791.7	792.4	793.2	793.6
142.5°	819.1	818.7	817.9	817.2	816.4	815.6	816.4	817.2	817.9	818.7	819.1
145°	842.5	842.1	841.3	840.5	839.7	838.9	839.7	840.5	841.3	842.1	842.5
147.5°	863.0	862.7	862.1	861.4	860.8	860.2	860.8	861.4	862.1	862.7	863.0
150°	882.8	882.4	881.6	880.9	880.1	879.3	880.1	880.9	881.6	882.4	882.8
152.5°	900.5	900.0	898.9	897.8	896.7	895.6	896.7	897.8	898.9	900.0	900.5
155°	916.1	915.5	914.2	912.9	911.7	910.4	911.7	912.9	914.2	915.5	916.1
157.5°	930.2	929.6	928.3	927.1	925.8	924.6	925.8	927.1	928.3	929.6	930.2
160°	941.6	941.0	939.9	938.8	937.7	936.6	937.7	938.8	939.9	941.0	941.6
162.5°	952.9	952.2	950.8	949.3	947.9	946.5	947.9	949.3	950.8	952.2	952.9
165°	961.4	960.8	959.7	958.6	957.5	956.4	957.5	958.6	959.7	960.8	961.4
167.5°	969.2	968.5	967.1	965.6	964.2	962.8	964.2	965.6	967.1	968.5	969.2
170°	974.8	974.1	972.7	971.3	969.9	968.5	969.9	971.3	972.7	974.1	974.8
172.5°	979.1	978.4	977.0	975.5	974.1	972.7	974.1	975.5	977.0	978.4	979.1
175°	981.9	981.1	979.5	978.0	976.4	974.8	976.4	978.0	979.5	981.1	981.9
177.5°	982.6	981.9	980.5	979.1	977.7	976.3	977.7	979.1	980.5	981.9	982.6
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2	962.2
2.5°	913.4	919.3	917.1	909.0	918.6	918.6	925.3	925.3	933.4	936.4	940.8
5°	861.7	866.1	869.8	866.1	872.7	883.1	889.0	894.2	905.3	909.7	916.4
7.5°	806.2	814.3	818.0	818.0	829.1	840.9	852.8	860.2	875.7	881.6	888.3
10°	752.2	761.8	769.2	768.5	787.0	794.3	809.1	826.2	841.7	850.6	860.2
12.5°	695.2	700.4	710.8	725.6	730.0	743.3	760.3	781.8	809.9	818.0	832.1
15°	647.9	662.0	670.1	676.8	687.1	699.7	718.2	738.9	767.0	784.7	799.5
17.5°	608.0	626.5	631.6	630.2	643.5	662.7	684.1	699.7	724.8	746.3	760.3
20°	575.4	582.8	591.7	595.4	605.7	626.5	647.2	664.9	685.6	702.6	718.9
22.5°	542.9	548.8	556.2	562.8	571.0	582.8	602.8	625.0	644.9	661.2	679.7
25°	516.3	520.0	526.6	531.8	540.7	548.8	562.8	587.3	610.9	620.5	636.8
27.5°	490.4	493.3	497.8	503.7	508.1	516.3	528.8	548.8	573.2	582.8	605.0
30°	467.4	469.7	474.1	477.1	479.3	488.9	498.5	514.0	532.5	545.8	562.1
32.5°	446.0	448.2	452.6	453.4	456.3	461.5	470.4	484.4	500.7	511.8	525.9
35°	422.3	423.8	428.2	429.7	431.9	436.4	443.0	453.4	468.2	476.3	488.9
37.5°	403.8	403.1	406.1	408.3	411.2	413.4	415.7	426.0	437.1	444.5	454.1
40°	383.9	382.4	383.1	386.1	387.6	390.5	390.5	400.9	408.3	414.2	421.6
42.5°	363.9	363.2	361.7	363.2	364.6	365.4	366.1	373.5	380.9	386.1	394.2
45°	343.9	343.2	341.7	342.4	342.4	343.9	346.1	349.1	354.3	358.7	363.2
47.5°	325.4	324.0	321.7	321.0	322.5	322.5	322.5	325.4	330.6	332.1	336.5
50°	306.2	304.0	301.0	299.5	299.5	298.8	300.3	301.0	305.5	306.9	310.6
52.5°	285.5	284.0	281.1	278.1	278.8	277.4	278.1	278.8	280.3	282.5	284.8
55°	264.8	261.8	259.6	258.9	256.6	256.6	254.4	257.4	256.6	257.4	260.3
57.5°	244.8	241.9	238.2	236.7	234.5	233.7	232.2	231.5	232.2	234.5	236.7
60°	221.1	219.7	217.4	215.2	213.7	211.5	210.1	210.1	209.3	209.3	210.1
62.5°	198.2	197.5	194.5	193.8	192.3	190.8	188.6	187.1	187.1	188.6	189.3
65°	176.0	175.3	173.1	172.3	168.6	167.2	166.4	165.7	164.2	164.2	164.2
67.5°	155.3	153.1	153.1	149.4	146.4	145.0	143.5	142.7	142.7	142.7	143.5
70°	132.4	132.4	130.2	128.0	125.0	125.7	123.5	121.3	121.3	119.8	120.6
72.5°	110.2	109.5	107.2	106.5	104.3	102.1	100.6	102.1	99.8	99.1	99.8
75°	88.8	88.0	86.5	85.1	85.8	83.6	81.4	80.6	80.6	79.1	79.1
77.5°	68.0	69.5	66.6	65.8	64.3	62.9	62.1	61.4	61.4	61.4	62.9
80°	47.3	48.1	48.1	46.6	47.3	45.1	45.1	45.1	42.9	43.6	44.4
82.5°	30.3	30.3	29.6	30.3	29.6	29.6	28.8	28.8	28.1	28.1	28.8
85°	17.0	16.3	15.5	17.0	16.3	16.3	15.5	15.5	15.5	15.5	15.5
87.5°	3.7	4.4	4.4	4.4	4.4	5.2	5.2	5.2	5.9	5.9	5.9
90°	17.3	16.5	15.8	15.0	14.2	12.9	11.7	10.4	9.1	8.5	7.6
92.5°	18.2	17.9	17.6	17.3	17.0	16.5	16.1	15.6	15.1	14.9	15.2
95°	30.7	29.9	29.2	28.4	27.6	26.5	25.4	24.3	23.2	22.7	25.3
97.5°	38.0	37.5	37.0	36.6	36.1	33.6	31.1	28.6	26.1	24.8	31.2
100°	45.4	44.1	42.9	41.6	40.4	37.7	35.0	32.3	29.6	28.3	39.1
102.5°	48.7	47.0	45.3	43.5	41.8	70.4	99.0	127.7	156.3	170.6	170.8
105°	50.1	48.4	46.7	44.9	43.2	86.2	129.1	172.1	215.0	236.5	234.1
107.5°	51.5	49.8	48.1	46.3	44.6	97.6	150.6	203.7	256.7	283.2	281.2
110°	61.0	76.7	92.4	108.2	123.9	169.4	214.8	260.3	305.8	328.5	326.8

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	88.4	156.2	224.0	291.8	359.6	362.3	365.0	367.7	370.4	371.7	370.3
115°	145.4	218.3	291.1	364.0	436.8	432.9	428.9	425.0	421.1	419.1	417.8
117.5°	385.0	407.5	430.0	452.5	475.0	472.3	469.7	467.0	464.3	463.0	461.4
120°	526.5	524.6	522.7	520.8	518.9	516.1	513.3	510.4	507.6	506.2	505.0
122.5°	564.4	563.5	562.6	561.6	560.7	557.5	554.4	551.2	548.1	546.5	545.2
125°	602.6	601.5	600.4	599.3	598.2	595.2	592.2	589.3	586.3	584.8	583.8
127.5°	639.2	637.6	636.1	634.5	632.9	630.5	628.2	625.8	623.5	622.3	621.2
130°	673.1	671.4	669.7	667.9	666.2	664.5	662.7	661.0	659.3	658.4	657.1
132.5°	705.1	703.7	702.3	700.9	699.5	697.8	696.0	694.3	692.6	691.7	690.7
135°	736.2	734.6	733.1	731.5	729.9	728.5	727.1	725.6	724.2	723.5	722.2
137.5°	765.2	763.6	762.1	760.5	758.9	757.3	755.7	754.2	752.6	751.8	750.9
140°	792.9	791.5	790.0	788.6	787.2	785.5	783.8	782.1	780.4	779.5	778.9
142.5°	818.5	817.2	815.9	814.7	813.4	811.4	809.3	807.3	805.2	804.2	803.7
145°	841.9	840.8	839.7	838.6	837.5	834.8	832.2	829.5	826.8	825.5	825.6
147.5°	862.6	861.8	861.0	860.2	859.4	856.7	854.1	851.4	848.7	847.4	847.6
150°	882.3	881.4	880.5	879.5	878.6	876.1	873.5	871.0	868.5	867.2	867.8
152.5°	900.0	899.1	898.2	897.2	896.3	893.9	891.5	889.2	886.8	885.6	886.2
155°	915.6	914.7	913.7	912.8	911.8	909.9	908.0	906.1	904.2	903.3	904.0
157.5°	929.7	928.6	927.5	926.4	925.3	923.9	922.5	921.0	919.6	918.9	919.5
160°	941.1	940.2	939.2	938.3	937.3	936.4	935.4	934.5	933.6	933.1	933.6
162.5°	952.3	951.2	950.1	949.0	947.9	947.1	946.3	945.6	944.8	944.4	944.9
165°	960.8	959.7	958.6	957.5	956.4	955.9	955.5	955.0	954.5	954.3	954.8
167.5°	968.6	967.5	966.4	965.3	964.2	963.7	963.3	962.8	962.3	962.1	962.6
170°	974.3	973.2	972.1	971.0	969.9	969.6	969.3	969.0	968.7	968.5	969.0
172.5°	978.5	977.4	976.3	975.2	974.1	973.8	973.5	973.2	972.9	972.7	973.2
175°	981.4	980.3	979.2	978.1	977.0	976.7	976.4	976.1	975.8	975.6	976.1
177.5°	982.1	981.0	979.9	978.8	977.7	977.5	977.4	977.2	977.1	977.0	977.5
180°	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4	978.4

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	962.2	962.2	962.2	962.2
2.5°	944.5	944.5	955.6	967.4
5°	923.8	929.0	946.7	963.0
7.5°	903.8	912.7	934.9	955.6
10°	879.4	891.2	918.6	943.0
12.5°	855.7	866.8	898.6	926.0
15°	822.5	836.5	870.5	904.6
17.5°	789.2	803.2	844.6	884.6
20°	750.0	768.5	815.1	868.3
22.5°	713.7	736.7	788.4	831.3
25°	673.8	709.3	757.4	812.8
27.5°	638.3	673.8	722.6	778.8
30°	598.4	634.6	684.9	736.7
32.5°	559.9	593.2	642.0	705.6
35°	520.0	551.8	599.1	663.4
37.5°	483.7	514.8	566.5	625.7
40°	448.2	480.8	525.1	584.3
42.5°	414.9	443.8	483.7	542.9
45°	384.6	405.3	442.3	497.8
47.5°	352.8	371.3	405.3	460.8
50°	323.2	338.7	368.3	420.1
52.5°	294.4	307.7	335.0	376.5
55°	268.5	281.1	301.0	341.7
57.5°	241.9	251.5	270.7	303.2
60°	216.0	224.8	240.4	267.0
62.5°	190.1	197.5	212.3	233.7
65°	167.2	173.1	184.2	202.7
67.5°	145.0	148.7	157.5	172.3
70°	123.5	126.5	133.9	145.7
72.5°	100.6	103.5	111.7	119.8
75°	81.4	82.1	88.0	94.7
77.5°	63.6	62.9	67.3	72.5
80°	43.6	45.9	49.6	51.8
82.5°	29.6	30.3	31.8	33.3
85°	16.3	17.0	17.0	19.2
87.5°	6.7	7.4	7.4	8.1
90°	5.9	4.2	2.4	0.7
92.5°	15.8	16.5	17.1	17.7
95°	30.5	35.6	40.8	46.0
97.5°	44.1	57.0	69.9	82.8
100°	60.6	82.2	103.7	125.3
102.5°	171.1	171.4	171.7	172.0
105°	229.4	224.7	219.9	215.2
107.5°	277.3	273.4	269.4	265.5
110°	323.5	320.2	316.9	313.6

TEST NUMBER: P1029546

CATALOG NUMBER: S122DIW-B485D710UB2750-4F0-XX-W2A-A_4000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	367.4	364.6	361.7	358.9
115°	415.1	412.4	409.8	407.1
117.5°	458.3	455.1	452.0	448.8
120°	502.7	500.3	498.0	495.6
122.5°	542.7	540.2	537.7	535.2
125°	581.7	579.7	577.6	575.6
127.5°	619.0	616.8	614.6	612.4
130°	654.6	652.1	649.6	647.1
132.5°	688.6	686.6	684.5	682.5
135°	719.7	717.2	714.7	712.2
137.5°	749.0	747.1	745.2	743.3
140°	777.6	776.3	775.1	773.8
142.5°	802.6	801.5	800.4	799.3
145°	825.7	825.9	826.0	826.2
147.5°	848.1	848.6	849.0	849.5
150°	868.9	870.0	871.1	872.2
152.5°	887.5	888.8	890.0	891.3
155°	905.4	906.9	908.3	909.7
157.5°	920.8	922.1	923.3	924.6
160°	934.5	935.4	936.4	937.3
162.5°	945.8	946.8	947.7	948.7
165°	955.7	956.7	957.6	958.6
167.5°	963.5	964.4	965.4	966.3
170°	969.9	970.8	971.8	972.7
172.5°	974.1	975.1	976.0	977.0
175°	977.2	978.3	979.4	980.5
177.5°	978.6	979.7	980.8	981.9
180°	978.4	978.4	978.4	978.4

(END OF REPORT)