

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029629

Luminaire Tested: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029629
REPORT IS A COMBINATION OF REPORTS P986471 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K
Description: Define 2 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7710.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	104	104	104	104		94	94	94	94		76	76	76		59	59	59		44	44	44
1	95	91	87	84		86	83	80	77		67	65	63		53	51	50		39	39	38
2	87	80	74	69		79	73	68	64		59	56	53		47	44	42		35	34	32
3	79	71	64	58		72	64	58	53		52	48	45		42	39	36		31	30	28
4	73	63	55	49		66	57	51	46		47	42	38		37	34	31		28	26	24
5	67	56	48	42		61	51	44	39		42	37	33		34	30	27		26	23	21
6	62	50	42	37		56	46	39	34		38	33	29		30	27	24		23	21	19
7	57	45	38	32		52	42	35	30		34	29	26		28	24	21		21	19	17
8	53	41	34	29		48	38	31	27		31	26	23		25	22	19		20	17	15
9	49	38	30	25		45	35	28	24		29	24	20		23	20	17		18	16	14
10	46	34	27	23		42	32	26	21		27	22	18		22	18	16		17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20318	20318	20318	20318
5°	20367	21665	20445	17235
10°	20130	23650	20257	14211
15°	19642	24945	19915	11969
20°	19336	23422	19336	10403
25°	18720	20122	18804	9304
30°	17706	15818	18043	8427
35°	16808	10938	17089	7711
40°	15774	8258	15954	7139
45°	14502	6787	14738	6522
50°	13401	5956	13425	5970
55°	12145	5075	12225	5371
60°	10809	4239	10957	4687
65°	9609	3448	9787	4003
70°	8419	2705	8631	3229
75°	7065	1964	7339	2341
80°	5517	1245	5908	1390
85°	3630	626	3899	463

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21003 cd/sqm

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.3	1.6
10°-20°	355.8	4.6
20°-30°	516.4	6.7
30°-40°	544.4	7.1
40°-50°	481.8	6.2
50°-60°	384.7	5.0
60°-70°	261.3	3.4
70°-80°	133.7	1.7
80°-90°	36.5	0.5
90°-100°	107.8	1.4
100°-110°	342.8	4.4
110°-120°	586.5	7.6
120°-130°	771.4	10.0
130°-140°	865.8	11.2
140°-150°	849.1	11.0
150°-160°	712.2	9.2
160°-170°	472.4	6.1
170°-180°	165.1	2.1
0°-30°	994.6	12.9
0°-40°	1539.0	20.0
0°-60°	2405.4	31.2
0°-90°	2837.0	36.8
90°-120°	1037.1	13.5
90°-150°	3523.4	45.7
90°-180°	4873.0	63.2
0°-180°	7710.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1284	1284	1284	1284	1284	
5°	1285	1434	1290	1140	1285	122
15°	1207	1762	1223	846	1207	341
25°	1084	1468	1089	679	1084	496
35°	885	799	900	563	885	554
45°	664	482	675	463	664	515
55°	456	338	459	358	456	407
65°	270	208	275	242	270	269
75°	126	103	131	122	126	136
85°	26	27	28	20	26	30
90°	2	50	2	50	2	6
95°	76	91	76	91	76	85
105°	316	326	316	326	316	334
115°	588	588	588	588	588	582
125°	856	859	856	859	856	765
135°	1108	1121	1108	1121	1108	856
145°	1344	1359	1344	1359	1344	840
155°	1537	1549	1537	1549	1537	708
165°	1672	1674	1672	1674	1672	472
175°	1740	1734	1740	1734	1740	165
180°	1743	1743	1743	1743	1743	

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1290.5	1293.5	1298.4	1299.4	1309.2	1317.1	1326.0	1326.0	1329.0	1328.0	1320.1
5°	1284.6	1293.5	1306.3	1317.1	1334.9	1342.8	1354.6	1363.5	1371.4	1377.3	1376.3
7.5°	1274.7	1290.5	1309.2	1330.0	1353.6	1367.5	1384.2	1400.0	1410.9	1420.7	1427.6
10°	1257.9	1284.6	1310.2	1337.9	1368.4	1387.2	1406.9	1427.6	1444.4	1463.2	1480.9
12.5°	1235.2	1273.7	1305.3	1341.8	1379.3	1400.0	1431.6	1447.4	1479.9	1527.3	1540.1
15°	1206.6	1258.9	1288.5	1334.9	1384.2	1401.0	1444.4	1470.1	1537.2	1566.8	1602.3
17.5°	1180.0	1238.2	1277.7	1331.0	1379.3	1411.9	1454.3	1506.6	1562.8	1605.2	1644.7
20°	1158.3	1214.5	1261.9	1321.1	1382.3	1423.7	1468.1	1531.2	1592.4	1635.8	1666.4
22.5°	1109.0	1181.0	1236.2	1302.3	1376.3	1433.6	1476.0	1545.0	1611.2	1637.8	1664.4
25°	1084.3	1146.5	1210.6	1285.6	1372.4	1440.5	1477.0	1553.9	1612.1	1622.0	1627.9
27.5°	1038.9	1109.0	1183.9	1269.8	1371.4	1428.6	1475.0	1545.0	1591.4	1584.5	1566.8
30°	982.7	1068.5	1151.4	1244.1	1357.6	1419.7	1463.2	1527.3	1551.0	1515.5	1483.9
32.5°	941.2	1022.1	1113.9	1221.4	1341.8	1401.0	1443.4	1493.7	1498.7	1434.5	1381.3
35°	885.0	974.8	1078.4	1191.8	1315.2	1368.4	1407.9	1438.5	1414.8	1325.0	1261.9
37.5°	834.7	923.5	1034.0	1149.4	1278.7	1331.0	1362.5	1367.5	1309.2	1230.3	1137.6
40°	779.4	871.2	986.6	1108.0	1238.2	1283.6	1303.3	1288.5	1204.7	1112.9	1005.4
42.5°	724.2	814.9	939.3	1063.6	1186.9	1225.4	1233.3	1192.8	1090.2	982.7	858.4
45°	664.0	758.7	883.0	1008.3	1127.7	1149.4	1150.4	1092.2	970.8	858.4	742.9
47.5°	614.7	702.5	825.8	951.1	1051.7	1066.5	1060.6	993.5	861.3	735.0	634.4
50°	560.4	644.3	766.6	889.9	975.8	979.7	964.9	869.2	740.0	624.5	544.6
52.5°	502.2	587.0	699.5	817.9	894.9	888.9	860.3	757.7	636.4	540.7	479.5
55°	455.8	530.8	636.4	751.8	806.1	789.3	757.7	653.1	557.4	476.5	423.3
57.5°	404.5	470.6	574.2	674.8	706.4	690.6	659.1	561.4	472.6	411.4	375.9
60°	356.2	416.4	507.1	591.0	615.7	598.9	562.4	474.6	410.4	359.1	332.5
62.5°	311.8	364.1	440.0	517.0	526.9	510.1	478.5	407.5	352.2	311.8	292.0
65°	270.3	319.7	380.8	439.0	447.9	430.2	397.6	346.3	299.9	274.3	255.5
67.5°	229.9	269.3	323.6	366.0	371.0	354.2	327.6	286.1	257.5	229.9	216.1
70°	194.4	224.0	266.4	300.9	302.9	287.1	273.3	235.8	214.1	194.4	183.5
72.5°	159.8	180.6	213.1	238.8	239.7	229.9	217.1	193.4	174.6	160.8	150.0
75°	126.3	144.0	163.8	186.5	185.5	177.6	167.7	152.9	137.1	128.3	123.3
77.5°	96.7	107.5	123.3	138.1	138.1	134.2	128.3	117.4	107.5	98.7	93.7
80°	69.1	76.0	88.8	93.7	95.7	94.7	89.8	81.9	77.9	71.0	69.1
82.5°	44.4	49.3	55.3	60.2	63.1	61.2	60.2	56.2	50.3	48.3	46.4
85°	25.7	27.6	30.6	33.5	34.5	33.5	35.5	32.6	29.6	29.6	28.6
87.5°	10.9	11.8	13.8	13.8	14.8	14.8	13.8	14.8	14.8	13.8	12.8
90°	1.5	5.4	9.3	13.2	17.1	19.1	22.7	29.9	37.1	44.3	51.5
92.5°	32.4	35.0	37.6	40.2	42.8	44.1	44.3	44.6	44.9	45.3	45.6
95°	76.5	79.8	83.0	86.3	89.6	91.2	91.5	92.2	92.8	93.5	94.1
97.5°	128.0	130.9	133.9	136.8	139.7	141.2	141.9	143.2	144.5	145.8	147.1
100°	186.8	189.4	192.0	194.7	197.3	198.6	199.1	200.1	201.0	202.0	203.0
102.5°	248.6	250.6	252.5	254.5	256.4	257.4	258.1	259.4	260.7	262.0	263.3
105°	316.2	317.2	318.2	319.1	320.1	320.6	320.9	321.6	322.3	322.9	323.6
107.5°	383.9	385.2	386.5	387.8	389.1	389.8	389.8	389.8	389.8	389.8	389.8
110°	448.6	450.6	452.5	454.5	456.4	457.4	457.4	457.4	457.4	457.4	457.4

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	519.2	521.2	523.1	525.1	527.0	528.0	527.8	527.5	527.2	526.9	526.6
115°	588.3	590.3	592.3	594.2	596.2	597.2	596.9	596.2	595.5	594.9	594.2
117.5°	657.5	660.1	662.7	665.3	667.9	669.2	668.4	666.8	665.1	663.5	661.9
120°	726.6	729.2	731.8	734.5	737.1	738.4	737.1	734.5	731.8	729.2	726.6
122.5°	789.9	793.2	796.4	799.7	803.0	804.6	803.8	802.1	800.5	798.8	797.2
125°	856.0	859.0	861.9	864.9	867.8	869.3	868.8	867.8	866.9	865.9	864.9
127.5°	920.8	924.4	928.0	931.5	935.1	936.9	936.3	935.0	933.7	932.4	931.1
130°	981.1	985.3	989.6	993.8	998.1	1000.2	999.9	999.2	998.5	997.9	997.2
132.5°	1048.7	1052.0	1055.2	1058.5	1061.8	1063.4	1063.6	1063.9	1064.2	1064.6	1064.9
135°	1107.6	1111.2	1114.8	1118.3	1121.9	1123.7	1124.0	1124.7	1125.4	1126.0	1126.7
137.5°	1172.3	1175.2	1178.2	1181.1	1184.0	1185.5	1185.8	1186.5	1187.2	1187.8	1188.5
140°	1229.6	1232.6	1235.5	1238.5	1241.4	1242.9	1243.7	1245.3	1247.0	1248.6	1250.2
142.5°	1288.5	1291.4	1294.4	1297.3	1300.2	1301.7	1302.2	1303.2	1304.1	1305.1	1306.1
145°	1344.4	1346.7	1349.0	1351.3	1353.6	1354.7	1355.7	1357.6	1359.6	1361.5	1363.5
147.5°	1394.4	1397.3	1400.3	1403.2	1406.1	1407.6	1408.3	1409.6	1410.9	1412.2	1413.5
150°	1445.9	1447.9	1449.8	1451.8	1453.7	1454.7	1455.4	1456.7	1458.0	1459.3	1460.6
152.5°	1491.5	1493.5	1495.4	1497.4	1499.3	1500.3	1501.1	1502.7	1504.4	1506.0	1507.6
155°	1537.1	1538.1	1539.1	1540.0	1541.0	1541.5	1542.0	1543.0	1543.9	1544.9	1545.9
157.5°	1576.8	1577.4	1578.1	1578.7	1579.4	1579.7	1580.0	1580.7	1581.4	1582.0	1582.7
160°	1612.1	1612.7	1613.4	1614.0	1614.7	1615.0	1615.2	1615.5	1615.8	1616.2	1616.5
162.5°	1644.4	1644.4	1644.4	1644.4	1644.4	1644.4	1644.6	1644.9	1645.2	1645.6	1645.9
165°	1672.4	1672.1	1671.7	1671.4	1671.1	1670.9	1670.9	1670.9	1670.9	1670.9	1670.9
167.5°	1697.4	1696.4	1695.4	1694.5	1693.5	1693.0	1693.0	1693.0	1693.0	1693.0	1693.0
170°	1716.5	1715.5	1714.5	1713.6	1712.6	1712.1	1711.9	1711.6	1711.3	1710.9	1710.6
172.5°	1729.7	1728.7	1727.7	1726.8	1725.8	1725.3	1725.1	1724.8	1724.5	1724.2	1723.9
175°	1740.0	1739.0	1738.0	1737.1	1736.1	1735.6	1735.3	1734.6	1734.0	1733.3	1732.7
177.5°	1745.9	1744.9	1743.9	1743.0	1742.0	1741.5	1741.2	1740.5	1739.9	1739.2	1738.6
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1333.9	1334.9	1336.9	1346.7	1351.7	1352.7	1348.7	1357.6	1360.6	1357.6	1355.6
5°	1397.1	1403.0	1414.8	1427.6	1426.7	1427.6	1433.6	1439.5	1441.5	1433.6	1436.5
7.5°	1452.3	1464.1	1477.0	1496.7	1496.7	1506.6	1510.5	1515.5	1527.3	1521.4	1519.4
10°	1515.5	1531.2	1554.9	1586.5	1587.5	1597.3	1607.2	1623.0	1627.9	1624.0	1626.0
12.5°	1594.4	1625.0	1626.9	1661.5	1677.3	1679.2	1695.0	1692.1	1701.9	1701.9	1718.7
15°	1628.9	1676.3	1702.9	1736.5	1746.3	1734.5	1747.3	1761.1	1762.1	1762.1	1761.1
17.5°	1691.1	1709.8	1736.5	1754.2	1758.2	1758.2	1759.1	1765.1	1761.1	1753.2	1759.1
20°	1703.9	1711.8	1721.7	1719.7	1721.7	1711.8	1701.9	1692.1	1693.0	1688.1	1702.9
22.5°	1680.2	1678.2	1655.6	1640.8	1640.8	1621.0	1602.3	1593.4	1584.5	1587.5	1592.4
25°	1621.0	1590.4	1562.8	1541.1	1536.2	1504.6	1478.9	1471.1	1456.3	1468.1	1470.1
27.5°	1526.3	1491.8	1447.4	1428.6	1403.0	1390.1	1372.4	1348.7	1318.1	1335.9	1332.9
30°	1424.7	1373.4	1336.9	1291.5	1251.0	1248.1	1214.5	1175.1	1159.3	1159.3	1168.2
32.5°	1311.2	1243.1	1189.9	1125.7	1086.3	1069.5	1029.0	989.6	998.5	968.9	979.7
35°	1179.0	1089.2	1022.1	960.0	930.4	910.7	858.4	836.7	813.0	799.2	824.8
37.5°	1052.7	949.1	863.3	795.2	784.4	748.8	713.3	699.5	685.7	691.6	690.6
40°	898.8	807.1	730.1	676.8	658.1	641.3	617.6	600.9	592.0	596.9	597.9
42.5°	759.7	682.7	625.5	588.0	572.2	560.4	548.6	534.7	531.8	531.8	535.7
45°	652.2	589.0	550.5	519.9	511.1	502.2	493.3	487.4	485.4	481.5	484.4
47.5°	566.3	516.0	492.3	469.6	459.8	457.8	449.9	446.9	443.0	442.0	443.0
50°	494.3	462.7	441.0	428.2	421.3	418.3	414.4	408.5	406.5	411.4	409.4
52.5°	444.0	414.4	402.5	389.7	385.8	381.8	375.9	376.9	375.9	373.9	373.9
55°	393.7	374.9	363.1	353.2	352.2	348.3	343.3	341.4	340.4	338.4	341.4
57.5°	353.2	338.4	327.6	318.7	314.7	314.7	309.8	305.9	305.9	304.9	305.9
60°	312.8	298.0	291.1	282.2	279.2	278.2	275.3	273.3	270.3	270.3	270.3
62.5°	275.3	263.4	255.5	247.6	248.6	243.7	239.7	237.8	237.8	238.8	238.8
65°	239.7	231.9	222.0	215.1	213.1	212.1	210.2	209.2	206.2	208.2	208.2
67.5°	207.2	196.3	190.4	187.5	184.5	183.5	181.5	179.6	178.6	177.6	179.6
70°	174.6	165.8	160.8	158.8	155.9	154.9	153.9	151.0	151.9	152.9	153.9
72.5°	145.0	137.1	136.2	130.2	130.2	130.2	126.3	128.3	127.3	125.3	127.3
75°	114.4	110.5	108.5	105.6	106.6	105.6	104.6	101.6	101.6	102.6	103.6
77.5°	90.8	86.8	85.8	82.9	80.9	82.9	80.9	79.9	79.9	80.9	80.9
80°	67.1	65.1	62.2	62.2	62.2	61.2	61.2	61.2	60.2	59.2	60.2
82.5°	44.4	44.4	43.4	42.4	43.4	41.4	42.4	42.4	42.4	42.4	42.4
85°	28.6	27.6	27.6	26.6	26.6	26.6	27.6	25.7	25.7	26.6	26.6
87.5°	12.8	12.8	12.8	13.8	12.8	12.8	12.8	13.8	12.8	12.8	12.8
90°	50.8	50.2	49.5	48.8	48.5	48.7	49.0	49.3	49.7	50.0	49.7
92.5°	45.9	46.3	46.6	46.9	47.1	47.1	47.1	47.1	47.1	47.1	47.1
95°	94.1	94.1	94.1	94.1	94.1	93.8	93.1	92.5	91.8	91.2	91.8
97.5°	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1
100°	203.0	203.0	203.0	203.0	203.0	202.8	202.5	202.2	201.8	201.5	201.8
102.5°	263.6	264.0	264.3	264.6	264.8	264.6	264.3	264.0	263.6	263.3	263.6
105°	324.2	324.9	325.5	326.2	326.5	326.5	326.5	326.5	326.5	326.5	326.5
107.5°	390.1	390.5	390.8	391.1	391.3	390.5	388.8	387.2	385.5	383.9	385.5
110°	457.4	457.4	457.4	457.4	457.4	456.9	455.9	455.0	454.0	453.0	454.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	525.6	524.6	523.7	522.7	522.2	521.9	521.2	520.5	519.9	519.2	519.9
115°	593.9	593.6	593.3	593.0	592.8	592.3	591.3	590.3	589.3	588.3	589.3
117.5°	660.9	659.9	659.0	658.0	657.5	657.0	656.0	655.1	654.1	653.1	654.1
120°	726.6	726.6	726.6	726.6	726.6	726.1	725.1	724.2	723.2	722.2	723.2
122.5°	796.2	795.2	794.3	793.3	792.8	792.5	791.8	791.2	790.5	789.9	790.5
125°	863.9	862.9	862.0	861.0	860.5	860.3	860.0	859.7	859.3	859.0	859.3
127.5°	929.8	928.5	927.2	925.9	925.2	924.7	923.7	922.8	921.8	920.8	921.8
130°	996.6	995.9	995.3	994.6	994.3	993.6	992.3	991.0	989.7	988.4	989.7
132.5°	1063.3	1061.7	1060.0	1058.4	1057.6	1057.1	1056.1	1055.1	1054.1	1053.1	1054.1
135°	1126.4	1126.0	1125.7	1125.4	1125.2	1124.7	1123.7	1122.8	1121.8	1120.8	1121.8
137.5°	1188.2	1187.8	1187.5	1187.2	1187.0	1186.3	1185.0	1183.7	1182.4	1181.1	1182.4
140°	1250.2	1250.2	1250.2	1250.2	1250.2	1249.6	1248.3	1247.0	1245.7	1244.4	1245.7
142.5°	1306.4	1306.8	1307.1	1307.4	1307.6	1306.9	1305.6	1304.3	1303.0	1301.7	1303.0
145°	1363.8	1364.2	1364.5	1364.8	1365.0	1364.3	1363.0	1361.7	1360.4	1359.1	1360.4
147.5°	1414.1	1414.8	1415.4	1416.1	1416.4	1415.8	1414.5	1413.2	1411.9	1410.6	1411.9
150°	1461.6	1462.6	1463.5	1464.5	1465.0	1464.5	1463.5	1462.6	1461.6	1460.6	1461.6
152.5°	1508.9	1510.2	1511.5	1512.8	1513.5	1512.8	1511.5	1510.2	1508.9	1507.6	1508.9
155°	1547.5	1549.1	1550.8	1552.4	1553.2	1552.7	1551.7	1550.8	1549.8	1548.8	1549.8
157.5°	1585.0	1587.3	1589.6	1591.9	1593.0	1592.2	1590.5	1588.9	1587.2	1585.6	1587.2
160°	1618.5	1620.4	1622.4	1624.3	1625.3	1624.6	1623.3	1622.0	1620.7	1619.4	1620.7
162.5°	1648.2	1650.5	1652.8	1655.1	1656.2	1655.4	1653.7	1652.1	1650.4	1648.8	1650.4
165°	1673.2	1675.5	1677.8	1680.1	1681.2	1680.4	1678.7	1677.1	1675.4	1673.8	1675.4
167.5°	1695.3	1697.6	1699.9	1702.2	1703.3	1702.5	1700.8	1699.2	1697.5	1695.9	1697.5
170°	1712.9	1715.2	1717.5	1719.8	1720.9	1719.9	1718.0	1716.0	1714.1	1712.1	1714.1
172.5°	1726.2	1728.5	1730.8	1733.1	1734.2	1733.2	1731.2	1729.3	1727.3	1725.3	1727.3
175°	1735.0	1737.3	1739.6	1741.9	1743.0	1742.0	1740.1	1738.1	1736.2	1734.2	1736.2
177.5°	1740.6	1742.5	1744.5	1746.4	1747.4	1746.4	1744.5	1742.5	1740.6	1738.6	1740.6
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1360.6	1353.6	1347.7	1348.7	1353.6	1349.7	1339.8	1327.0	1322.1	1316.2	1322.1
5°	1442.4	1436.5	1424.7	1425.7	1422.7	1418.8	1403.0	1383.2	1383.2	1367.5	1365.5
7.5°	1523.3	1514.5	1506.6	1504.6	1493.7	1485.9	1472.0	1444.4	1433.6	1414.8	1404.0
10°	1614.1	1607.2	1598.3	1587.5	1581.6	1567.7	1545.0	1504.6	1484.9	1459.2	1440.5
12.5°	1705.9	1704.9	1685.1	1663.4	1662.5	1640.8	1625.0	1570.7	1544.1	1509.5	1465.1
15°	1764.1	1759.1	1748.3	1737.4	1740.4	1716.7	1681.2	1617.1	1599.3	1557.9	1510.5
17.5°	1763.1	1763.1	1760.1	1758.2	1755.2	1748.3	1728.6	1686.1	1657.5	1605.2	1560.8
20°	1706.9	1719.7	1722.6	1721.7	1731.5	1736.5	1735.5	1708.8	1686.1	1639.8	1594.4
22.5°	1594.4	1624.0	1636.8	1644.7	1665.4	1676.3	1701.9	1692.1	1686.1	1651.6	1613.1
25°	1489.8	1499.7	1538.1	1540.1	1568.7	1595.4	1621.0	1637.8	1659.5	1646.7	1614.1
27.5°	1354.6	1377.3	1404.9	1425.7	1431.6	1485.9	1528.3	1559.8	1609.2	1613.1	1602.3
30°	1201.7	1212.6	1257.9	1285.6	1317.1	1356.6	1417.8	1472.0	1516.4	1556.9	1570.7
32.5°	1015.2	1059.6	1086.3	1119.8	1147.4	1217.5	1292.5	1362.5	1413.8	1481.9	1511.5
35°	844.5	879.1	924.5	938.3	988.6	1047.8	1145.5	1235.2	1313.2	1382.3	1442.4
37.5°	703.5	731.1	779.4	801.1	830.7	906.7	988.6	1100.1	1193.8	1278.7	1353.6
40°	606.8	627.5	664.0	670.9	695.6	764.6	830.7	935.3	1059.6	1174.1	1256.0
42.5°	540.7	550.5	575.2	584.1	599.9	646.2	705.4	804.1	919.5	1037.9	1153.4
45°	493.3	500.2	515.0	522.9	542.6	563.4	611.7	690.6	781.4	900.8	1025.1
47.5°	450.9	459.8	465.7	470.6	481.5	504.2	535.7	593.9	680.8	790.3	910.7
50°	415.4	418.3	429.2	430.2	437.1	451.9	481.5	517.0	586.1	674.8	791.3
52.5°	379.8	382.8	389.7	396.6	399.6	411.4	431.2	460.8	512.1	582.1	685.7
55°	344.3	348.3	355.2	360.1	363.1	372.9	384.8	413.4	453.8	503.2	588.0
57.5°	308.8	317.7	319.7	322.6	327.6	338.4	349.3	366.0	397.6	443.0	505.2
60°	275.3	278.2	285.1	288.1	293.0	298.9	312.8	325.6	348.3	383.8	440.0
62.5°	240.7	247.6	250.6	253.6	257.5	264.4	273.3	287.1	306.8	335.5	379.8
65°	211.1	212.1	218.0	222.0	225.9	230.9	239.7	252.6	264.4	291.1	323.6
67.5°	182.5	184.5	186.5	190.4	195.4	200.3	208.2	215.1	229.9	247.6	273.3
70°	154.9	154.9	159.8	162.8	161.8	167.7	173.6	181.5	192.4	209.2	229.9
72.5°	130.2	129.2	133.2	134.2	136.2	140.1	144.0	151.9	157.9	170.7	186.5
75°	103.6	105.6	107.5	107.5	110.5	113.5	117.4	121.4	128.3	136.2	148.0
77.5°	81.9	81.9	83.9	84.8	87.8	86.8	90.8	94.7	99.6	106.6	115.4
80°	60.2	62.2	62.2	62.2	63.1	64.1	68.1	71.0	74.0	78.9	82.9
82.5°	42.4	42.4	44.4	44.4	44.4	46.4	46.4	47.4	49.3	52.3	55.3
85°	26.6	26.6	26.6	27.6	26.6	27.6	29.6	28.6	29.6	31.6	31.6
87.5°	12.8	12.8	12.8	12.8	12.8	13.8	12.8	13.8	14.8	14.8	14.8
90°	49.3	49.0	48.7	48.5	48.8	49.5	50.2	50.8	51.5	44.3	37.1
92.5°	47.1	47.1	47.1	47.1	46.9	46.6	46.3	45.9	45.6	45.3	44.9
95°	92.5	93.1	93.8	94.1	94.1	94.1	94.1	94.1	94.1	93.5	92.8
97.5°	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	145.8	144.5
100°	202.2	202.5	202.8	203.0	203.0	203.0	203.0	203.0	203.0	202.0	201.0
102.5°	264.0	264.3	264.6	264.8	264.6	264.3	264.0	263.6	263.3	262.0	260.7
105°	326.5	326.5	326.5	326.5	326.2	325.5	324.9	324.2	323.6	322.9	322.3
107.5°	387.2	388.8	390.5	391.3	391.1	390.8	390.5	390.1	389.8	389.8	389.8
110°	455.0	455.9	456.9	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	520.5	521.2	521.9	522.2	522.7	523.7	524.6	525.6	526.6	526.9	527.2
115°	590.3	591.3	592.3	592.8	593.0	593.3	593.6	593.9	594.2	594.9	595.5
117.5°	655.1	656.0	657.0	657.5	658.0	659.0	659.9	660.9	661.9	663.5	665.1
120°	724.2	725.1	726.1	726.6	726.6	726.6	726.6	726.6	726.6	729.2	731.8
122.5°	791.2	791.8	792.5	792.8	793.3	794.3	795.2	796.2	797.2	798.8	800.5
125°	859.7	860.0	860.3	860.5	861.0	862.0	862.9	863.9	864.9	865.9	866.9
127.5°	922.8	923.7	924.7	925.2	925.9	927.2	928.5	929.8	931.1	932.4	933.7
130°	991.0	992.3	993.6	994.3	994.6	995.3	995.9	996.6	997.2	997.9	998.5
132.5°	1055.1	1056.1	1057.1	1057.6	1058.4	1060.0	1061.7	1063.3	1064.9	1064.6	1064.2
135°	1122.8	1123.7	1124.7	1125.2	1125.4	1125.7	1126.0	1126.4	1126.7	1126.0	1125.4
137.5°	1183.7	1185.0	1186.3	1187.0	1187.2	1187.5	1187.8	1188.2	1188.5	1187.8	1187.2
140°	1247.0	1248.3	1249.6	1250.2	1250.2	1250.2	1250.2	1250.2	1250.2	1248.6	1247.0
142.5°	1304.3	1305.6	1306.9	1307.6	1307.4	1307.1	1306.8	1306.4	1306.1	1305.1	1304.1
145°	1361.7	1363.0	1364.3	1365.0	1364.8	1364.5	1364.2	1363.8	1363.5	1361.5	1359.6
147.5°	1413.2	1414.5	1415.8	1416.4	1416.1	1415.4	1414.8	1414.1	1413.5	1412.2	1410.9
150°	1462.6	1463.5	1464.5	1465.0	1464.5	1463.5	1462.6	1461.6	1460.6	1459.3	1458.0
152.5°	1510.2	1511.5	1512.8	1513.5	1512.8	1511.5	1510.2	1508.9	1507.6	1506.0	1504.4
155°	1550.8	1551.7	1552.7	1553.2	1552.4	1550.8	1549.1	1547.5	1545.9	1544.9	1543.9
157.5°	1588.9	1590.5	1592.2	1593.0	1591.9	1589.6	1587.3	1585.0	1582.7	1582.0	1581.4
160°	1622.0	1623.3	1624.6	1625.3	1624.3	1622.4	1620.4	1618.5	1616.5	1616.2	1615.8
162.5°	1652.1	1653.7	1655.4	1656.2	1655.1	1652.8	1650.5	1648.2	1645.9	1645.6	1645.2
165°	1677.1	1678.7	1680.4	1681.2	1680.1	1677.8	1675.5	1673.2	1670.9	1670.9	1670.9
167.5°	1699.2	1700.8	1702.5	1703.3	1702.2	1699.9	1697.6	1695.3	1693.0	1693.0	1693.0
170°	1716.0	1718.0	1719.9	1720.9	1719.8	1717.5	1715.2	1712.9	1710.6	1710.9	1711.3
172.5°	1729.3	1731.2	1733.2	1734.2	1733.1	1730.8	1728.5	1726.2	1723.9	1724.2	1724.5
175°	1738.1	1740.1	1742.0	1743.0	1741.9	1739.6	1737.3	1735.0	1732.7	1733.3	1734.0
177.5°	1742.5	1744.5	1746.4	1747.4	1746.4	1744.5	1742.5	1740.6	1738.6	1739.2	1739.9
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1317.1	1312.2	1309.2	1311.2	1305.3	1290.5	1290.5	1295.4	1289.5	1283.6	1274.7
5°	1353.6	1343.8	1337.9	1336.9	1323.1	1299.4	1294.4	1289.5	1276.7	1262.9	1248.1
7.5°	1389.2	1371.4	1361.5	1354.6	1334.9	1304.3	1291.5	1280.6	1259.9	1239.2	1220.5
10°	1418.8	1393.1	1381.3	1370.4	1344.8	1306.3	1285.6	1265.8	1239.2	1212.6	1188.9
12.5°	1442.4	1412.8	1398.0	1382.3	1350.7	1300.4	1274.7	1243.1	1216.5	1181.0	1157.3
15°	1481.9	1420.7	1406.9	1392.1	1359.6	1290.5	1258.9	1223.4	1186.9	1139.5	1113.9
17.5°	1513.5	1431.6	1430.6	1399.0	1356.6	1286.6	1238.2	1191.8	1152.4	1105.0	1064.6
20°	1532.2	1448.4	1432.6	1400.0	1346.7	1259.9	1209.6	1158.3	1115.9	1058.6	1018.2
22.5°	1548.0	1472.0	1430.6	1391.1	1326.0	1251.0	1177.0	1128.7	1070.5	1008.3	969.8
25°	1553.9	1477.0	1433.6	1388.2	1311.2	1225.4	1141.5	1089.2	1024.1	967.9	915.6
27.5°	1554.9	1476.0	1422.7	1375.4	1290.5	1191.8	1106.0	1050.8	978.7	913.6	861.3
30°	1545.0	1465.1	1416.8	1365.5	1270.8	1161.3	1062.6	1001.4	924.5	859.3	805.1
32.5°	1515.5	1443.4	1404.0	1347.7	1245.1	1118.8	1021.2	953.1	872.2	808.0	755.8
35°	1466.1	1416.8	1373.4	1321.1	1211.6	1079.4	979.7	899.8	817.9	756.7	707.4
37.5°	1404.9	1378.3	1337.9	1286.6	1173.1	1043.8	933.3	844.5	762.7	703.5	655.1
40°	1322.1	1329.0	1289.5	1243.1	1127.7	995.5	873.2	788.3	711.4	656.1	608.7
42.5°	1232.3	1260.9	1238.2	1193.8	1077.4	942.2	828.8	735.0	660.0	602.8	563.4
45°	1135.6	1184.9	1171.1	1138.6	1025.1	886.0	765.6	674.8	608.7	553.5	519.0
47.5°	1030.0	1100.1	1100.1	1076.4	966.9	829.7	711.4	618.6	553.5	514.0	480.5
50°	922.5	1001.4	1014.2	998.5	901.8	765.6	645.3	561.4	505.2	466.7	442.0
52.5°	810.0	901.8	925.5	917.6	832.7	704.4	591.0	509.1	457.8	424.2	402.5
55°	702.5	809.0	834.7	837.6	758.7	637.4	530.8	458.8	409.4	386.8	368.0
57.5°	600.9	703.5	732.1	737.0	683.7	576.2	474.6	411.4	367.0	348.3	333.5
60°	514.0	599.9	637.4	648.2	601.8	505.2	422.3	361.1	327.6	309.8	296.0
62.5°	443.0	512.1	551.5	554.5	533.8	443.0	368.0	316.7	288.1	272.3	265.4
65°	373.9	436.1	459.8	471.6	454.8	383.8	317.7	275.3	252.6	238.8	231.9
67.5°	318.7	358.1	377.9	393.7	376.9	323.6	270.3	235.8	219.0	205.2	201.3
70°	261.5	294.0	308.8	324.6	309.8	269.3	230.9	199.3	184.5	173.6	168.7
72.5°	209.2	234.8	248.6	258.5	249.6	216.1	184.5	162.8	151.9	144.0	141.1
75°	165.8	183.5	191.4	198.3	194.4	168.7	149.0	131.2	121.4	114.4	112.5
77.5°	126.3	139.1	148.0	150.0	145.0	128.3	111.5	100.6	92.7	88.8	86.8
80°	89.8	97.7	102.6	105.6	100.6	93.7	81.9	74.0	67.1	62.2	61.2
82.5°	60.2	64.1	68.1	67.1	65.1	59.2	52.3	48.3	45.4	41.4	41.4
85°	34.5	35.5	37.5	38.5	37.5	33.5	29.6	27.6	25.7	22.7	22.7
87.5°	14.8	15.8	15.8	16.8	14.8	14.8	12.8	10.9	10.9	9.9	8.9
90°	29.9	22.7	19.1	17.1	13.2	9.3	5.4	1.5	5.4	9.3	13.2
92.5°	44.6	44.3	44.1	42.8	40.2	37.6	35.0	32.4	35.0	37.6	40.2
95°	92.2	91.5	91.2	89.6	86.3	83.0	79.8	76.5	79.8	83.0	86.3
97.5°	143.2	141.9	141.2	139.7	136.8	133.9	130.9	128.0	130.9	133.9	136.8
100°	200.1	199.1	198.6	197.3	194.7	192.0	189.4	186.8	189.4	192.0	194.7
102.5°	259.4	258.1	257.4	256.4	254.5	252.5	250.6	248.6	250.6	252.5	254.5
105°	321.6	320.9	320.6	320.1	319.1	318.2	317.2	316.2	317.2	318.2	319.1
107.5°	389.8	389.8	389.8	389.1	387.8	386.5	385.2	383.9	385.2	386.5	387.8
110°	457.4	457.4	457.4	456.4	454.5	452.5	450.6	448.6	450.6	452.5	454.5

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	527.5	527.8	528.0	527.0	525.1	523.1	521.2	519.2	521.2	523.1	525.1
115°	596.2	596.9	597.2	596.2	594.2	592.3	590.3	588.3	590.3	592.3	594.2
117.5°	666.8	668.4	669.2	667.9	665.3	662.7	660.1	657.5	660.1	662.7	665.3
120°	734.5	737.1	738.4	737.1	734.5	731.8	729.2	726.6	729.2	731.8	734.5
122.5°	802.1	803.8	804.6	803.0	799.7	796.4	793.2	789.9	793.2	796.4	799.7
125°	867.8	868.8	869.3	867.8	864.9	861.9	859.0	856.0	859.0	861.9	864.9
127.5°	935.0	936.3	936.9	935.1	931.5	928.0	924.4	920.8	924.4	928.0	931.5
130°	999.2	999.9	1000.2	998.1	993.8	989.6	985.3	981.1	985.3	989.6	993.8
132.5°	1063.9	1063.6	1063.4	1061.8	1058.5	1055.2	1052.0	1048.7	1052.0	1055.2	1058.5
135°	1124.7	1124.0	1123.7	1121.9	1118.3	1114.8	1111.2	1107.6	1111.2	1114.8	1118.3
137.5°	1186.5	1185.8	1185.5	1184.0	1181.1	1178.2	1175.2	1172.3	1175.2	1178.2	1181.1
140°	1245.3	1243.7	1242.9	1241.4	1238.5	1235.5	1232.6	1229.6	1232.6	1235.5	1238.5
142.5°	1303.2	1302.2	1301.7	1300.2	1297.3	1294.4	1291.4	1288.5	1291.4	1294.4	1297.3
145°	1357.6	1355.7	1354.7	1353.6	1351.3	1349.0	1346.7	1344.4	1346.7	1349.0	1351.3
147.5°	1409.6	1408.3	1407.6	1406.1	1403.2	1400.3	1397.3	1394.4	1397.3	1400.3	1403.2
150°	1456.7	1455.4	1454.7	1453.7	1451.8	1449.8	1447.9	1445.9	1447.9	1449.8	1451.8
152.5°	1502.7	1501.1	1500.3	1499.3	1497.4	1495.4	1493.5	1491.5	1493.5	1495.4	1497.4
155°	1543.0	1542.0	1541.5	1541.0	1540.0	1539.1	1538.1	1537.1	1538.1	1539.1	1540.0
157.5°	1580.7	1580.0	1579.7	1579.4	1578.7	1578.1	1577.4	1576.8	1577.4	1578.1	1578.7
160°	1615.5	1615.2	1615.0	1614.7	1614.0	1613.4	1612.7	1612.1	1612.7	1613.4	1614.0
162.5°	1644.9	1644.6	1644.4	1644.4	1644.4	1644.4	1644.4	1644.4	1644.4	1644.4	1644.4
165°	1670.9	1670.9	1670.9	1671.1	1671.4	1671.7	1672.1	1672.4	1672.1	1671.7	1671.4
167.5°	1693.0	1693.0	1693.0	1693.5	1694.5	1695.4	1696.4	1697.4	1696.4	1695.4	1694.5
170°	1711.6	1711.9	1712.1	1712.6	1713.6	1714.5	1715.5	1716.5	1715.5	1714.5	1713.6
172.5°	1724.8	1725.1	1725.3	1725.8	1726.8	1727.7	1728.7	1729.7	1728.7	1727.7	1726.8
175°	1734.6	1735.3	1735.6	1736.1	1737.1	1738.0	1739.0	1740.0	1739.0	1738.0	1737.1
177.5°	1740.5	1741.2	1741.5	1742.0	1743.0	1743.9	1744.9	1745.9	1744.9	1743.9	1743.0
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1269.8	1274.7	1273.7	1263.9	1253.0	1244.1	1227.4	1229.3	1223.4	1224.4	1230.3
5°	1238.2	1238.2	1234.3	1220.5	1202.7	1192.8	1174.1	1169.1	1157.3	1156.3	1155.3
7.5°	1204.7	1199.7	1194.8	1175.1	1153.4	1137.6	1111.9	1106.0	1094.2	1086.3	1082.3
10°	1165.2	1158.3	1148.4	1125.7	1099.1	1079.4	1052.7	1044.8	1022.1	1012.3	1006.4
12.5°	1121.8	1117.8	1102.1	1083.3	1039.9	1018.2	979.7	987.6	964.9	945.2	942.2
15°	1078.4	1063.6	1054.7	1024.1	971.8	962.0	931.4	915.6	894.9	879.1	879.1
17.5°	1036.0	1013.3	993.5	961.0	922.5	894.9	872.2	864.3	838.6	822.8	819.9
20°	979.7	954.1	949.1	902.8	876.1	845.5	823.8	804.1	785.4	778.4	773.5
22.5°	926.4	896.8	888.9	849.5	822.8	792.3	770.6	756.7	742.9	738.0	729.1
25°	869.2	851.5	839.6	797.2	767.6	739.0	724.2	714.3	701.5	700.5	694.6
27.5°	814.0	797.2	785.4	744.9	723.2	696.6	684.7	673.9	667.0	664.0	661.0
30°	766.6	747.9	734.0	704.4	677.8	656.1	646.2	639.3	635.4	630.5	629.5
32.5°	714.3	703.5	684.7	662.0	641.3	620.6	614.7	609.7	603.8	601.8	600.9
35°	669.9	655.1	643.3	617.6	608.7	591.0	584.1	580.1	572.2	570.3	568.3
37.5°	626.5	612.7	599.9	584.1	567.3	557.4	553.5	547.6	543.6	544.6	542.6
40°	583.1	572.2	562.4	545.6	535.7	530.8	522.9	517.0	515.0	516.0	515.0
42.5°	540.7	530.8	524.9	512.1	502.2	497.3	492.3	486.4	489.4	489.4	492.3
45°	502.2	493.3	489.4	479.5	473.6	465.7	460.8	459.8	463.7	462.7	462.7
47.5°	462.7	459.8	454.8	446.0	438.1	433.1	432.1	432.1	436.1	438.1	437.1
50°	432.1	426.2	420.3	413.4	407.5	405.5	402.5	404.5	408.5	408.5	410.4
52.5°	393.7	389.7	387.7	381.8	377.9	377.9	377.9	378.9	381.8	384.8	383.8
55°	360.1	357.2	355.2	352.2	347.3	348.3	347.3	349.3	352.2	355.2	357.2
57.5°	324.6	323.6	321.6	316.7	316.7	315.7	318.7	319.7	324.6	326.6	329.5
60°	293.0	290.1	290.1	286.1	286.1	286.1	289.1	292.0	296.0	297.0	298.9
62.5°	259.5	259.5	258.5	255.5	255.5	258.5	259.5	263.4	265.4	265.4	268.4
65°	227.9	226.9	225.9	226.9	227.9	227.9	230.9	232.8	234.8	235.8	236.8
67.5°	196.3	195.4	197.3	196.3	198.3	202.3	201.3	204.2	207.2	207.2	208.2
70°	166.7	168.7	167.7	169.7	168.7	170.7	173.6	174.6	174.6	175.6	178.6
72.5°	139.1	139.1	139.1	138.1	139.1	141.1	143.1	144.0	146.0	147.0	150.0
75°	112.5	112.5	110.5	112.5	112.5	114.4	116.4	116.4	116.4	118.4	121.4
77.5°	84.8	85.8	84.8	86.8	86.8	87.8	89.8	88.8	90.8	91.8	92.7
80°	62.2	61.2	61.2	61.2	62.2	62.2	64.1	65.1	65.1	68.1	66.1
82.5°	39.5	40.5	39.5	40.5	40.5	41.4	40.5	41.4	42.4	44.4	43.4
85°	22.7	21.7	21.7	22.7	21.7	21.7	22.7	21.7	22.7	21.7	22.7
87.5°	8.9	7.9	7.9	7.9	7.9	6.9	6.9	5.9	5.9	5.9	4.9
90°	17.1	19.1	22.7	29.9	37.1	44.3	51.5	50.8	50.2	49.5	48.8
92.5°	42.8	44.1	44.3	44.6	44.9	45.3	45.6	45.9	46.3	46.6	46.9
95°	89.6	91.2	91.5	92.2	92.8	93.5	94.1	94.1	94.1	94.1	94.1
97.5°	139.7	141.2	141.9	143.2	144.5	145.8	147.1	147.1	147.1	147.1	147.1
100°	197.3	198.6	199.1	200.1	201.0	202.0	203.0	203.0	203.0	203.0	203.0
102.5°	256.4	257.4	258.1	259.4	260.7	262.0	263.3	263.6	264.0	264.3	264.6
105°	320.1	320.6	320.9	321.6	322.3	322.9	323.6	324.2	324.9	325.5	326.2
107.5°	389.1	389.8	389.8	389.8	389.8	389.8	389.8	390.1	390.5	390.8	391.1
110°	456.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	527.0	528.0	527.8	527.5	527.2	526.9	526.6	525.6	524.6	523.7	522.7
115°	596.2	597.2	596.9	596.2	595.5	594.9	594.2	593.9	593.6	593.3	593.0
117.5°	667.9	669.2	668.4	666.8	665.1	663.5	661.9	660.9	659.9	659.0	658.0
120°	737.1	738.4	737.1	734.5	731.8	729.2	726.6	726.6	726.6	726.6	726.6
122.5°	803.0	804.6	803.8	802.1	800.5	798.8	797.2	796.2	795.2	794.3	793.3
125°	867.8	869.3	868.8	867.8	866.9	865.9	864.9	863.9	862.9	862.0	861.0
127.5°	935.1	936.9	936.3	935.0	933.7	932.4	931.1	929.8	928.5	927.2	925.9
130°	998.1	1000.2	999.9	999.2	998.5	997.9	997.2	996.6	995.9	995.3	994.6
132.5°	1061.8	1063.4	1063.6	1063.9	1064.2	1064.6	1064.9	1063.3	1061.7	1060.0	1058.4
135°	1121.9	1123.7	1124.0	1124.7	1125.4	1126.0	1126.7	1126.4	1126.0	1125.7	1125.4
137.5°	1184.0	1185.5	1185.8	1186.5	1187.2	1187.8	1188.5	1188.2	1187.8	1187.5	1187.2
140°	1241.4	1242.9	1243.7	1245.3	1247.0	1248.6	1250.2	1250.2	1250.2	1250.2	1250.2
142.5°	1300.2	1301.7	1302.2	1303.2	1304.1	1305.1	1306.1	1306.4	1306.8	1307.1	1307.4
145°	1353.6	1354.7	1355.7	1357.6	1359.6	1361.5	1363.5	1363.8	1364.2	1364.5	1364.8
147.5°	1406.1	1407.6	1408.3	1409.6	1410.9	1412.2	1413.5	1414.1	1414.8	1415.4	1416.1
150°	1453.7	1454.7	1455.4	1456.7	1458.0	1459.3	1460.6	1461.6	1462.6	1463.5	1464.5
152.5°	1499.3	1500.3	1501.1	1502.7	1504.4	1506.0	1507.6	1508.9	1510.2	1511.5	1512.8
155°	1541.0	1541.5	1542.0	1543.0	1543.9	1544.9	1545.9	1547.5	1549.1	1550.8	1552.4
157.5°	1579.4	1579.7	1580.0	1580.7	1581.4	1582.0	1582.7	1585.0	1587.3	1589.6	1591.9
160°	1614.7	1615.0	1615.2	1615.5	1615.8	1616.2	1616.5	1618.5	1620.4	1622.4	1624.3
162.5°	1644.4	1644.4	1644.6	1644.9	1645.2	1645.6	1645.9	1648.2	1650.5	1652.8	1655.1
165°	1671.1	1670.9	1670.9	1670.9	1670.9	1670.9	1670.9	1673.2	1675.5	1677.8	1680.1
167.5°	1693.5	1693.0	1693.0	1693.0	1693.0	1693.0	1693.0	1695.3	1697.6	1699.9	1702.2
170°	1712.6	1712.1	1711.9	1711.6	1711.3	1710.9	1710.6	1712.9	1715.2	1717.5	1719.8
172.5°	1725.8	1725.3	1725.1	1724.8	1724.5	1724.2	1723.9	1726.2	1728.5	1730.8	1733.1
175°	1736.1	1735.6	1735.3	1734.6	1734.0	1733.3	1732.7	1735.0	1737.3	1739.6	1741.9
177.5°	1742.0	1741.5	1741.2	1740.5	1739.9	1739.2	1738.6	1740.6	1742.5	1744.5	1746.4
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1223.4	1226.4	1219.5	1217.5	1219.5	1212.6	1214.5	1216.5	1216.5	1219.5	1221.4
5°	1152.4	1148.4	1141.5	1139.5	1137.6	1140.5	1138.6	1141.5	1142.5	1149.4	1150.4
7.5°	1082.3	1076.4	1070.5	1064.6	1062.6	1057.7	1062.6	1062.6	1069.5	1067.5	1072.5
10°	999.4	998.5	990.6	987.6	983.7	975.8	986.6	983.7	988.6	997.5	999.4
12.5°	938.3	927.4	932.4	918.5	923.5	915.6	916.6	916.6	924.5	925.5	923.5
15°	880.1	871.2	858.4	852.4	849.5	845.5	858.4	859.3	853.4	867.2	862.3
17.5°	820.9	820.9	809.0	806.1	798.2	802.1	800.1	801.1	799.2	809.0	814.0
20°	769.6	764.6	760.7	761.7	751.8	749.8	747.9	749.8	756.7	763.6	765.6
22.5°	728.1	725.2	715.3	717.3	709.4	712.3	710.4	715.3	716.3	716.3	723.2
25°	688.7	684.7	685.7	681.8	678.8	678.8	675.8	678.8	682.7	684.7	685.7
27.5°	659.1	656.1	651.2	648.2	650.2	645.3	649.2	652.2	652.2	650.2	652.2
30°	623.5	625.5	625.5	615.7	619.6	617.6	620.6	622.6	622.6	623.5	621.6
32.5°	599.9	593.9	593.0	592.0	592.0	588.0	588.0	591.0	592.0	593.0	595.9
35°	568.3	568.3	563.4	566.3	562.4	563.4	562.4	563.4	565.3	562.4	565.3
37.5°	539.7	540.7	538.7	540.7	541.7	539.7	537.7	541.7	539.7	539.7	537.7
40°	515.0	514.0	515.0	515.0	515.0	516.0	514.0	514.0	514.0	512.1	510.1
42.5°	494.3	488.4	490.4	491.3	488.4	488.4	489.4	488.4	491.3	485.4	485.4
45°	464.7	462.7	463.7	463.7	465.7	462.7	464.7	465.7	462.7	461.7	459.8
47.5°	438.1	440.0	438.1	440.0	440.0	442.0	438.1	439.0	440.0	436.1	433.1
50°	411.4	411.4	414.4	413.4	414.4	412.4	412.4	411.4	412.4	410.4	407.5
52.5°	386.8	383.8	388.7	387.7	386.8	385.8	384.8	385.8	383.8	381.8	381.8
55°	356.2	356.2	359.1	360.1	360.1	358.1	356.2	357.2	356.2	355.2	354.2
57.5°	331.5	327.6	329.5	330.5	330.5	327.6	329.5	327.6	327.6	328.5	325.6
60°	299.9	299.9	298.0	300.9	300.9	298.9	298.9	299.9	298.0	297.0	296.0
62.5°	266.4	267.4	270.3	271.3	272.3	270.3	268.4	269.3	269.3	266.4	267.4
65°	237.8	239.7	243.7	242.7	240.7	241.7	239.7	240.7	237.8	238.8	235.8
67.5°	210.2	209.2	210.2	210.2	212.1	211.1	209.2	209.2	208.2	211.1	208.2
70°	180.6	180.6	180.6	180.6	181.5	182.5	180.6	178.6	179.6	177.6	176.6
72.5°	150.0	151.0	150.0	151.9	149.0	151.0	151.0	150.0	149.0	149.0	149.0
75°	121.4	123.3	120.4	121.4	120.4	122.3	121.4	121.4	119.4	118.4	119.4
77.5°	92.7	93.7	91.8	92.7	91.8	92.7	92.7	91.8	91.8	91.8	91.8
80°	66.1	67.1	66.1	65.1	64.1	66.1	64.1	65.1	66.1	65.1	67.1
82.5°	42.4	42.4	41.4	42.4	40.5	40.5	41.4	41.4	40.5	42.4	40.5
85°	20.7	20.7	22.7	20.7	19.7	19.7	19.7	20.7	19.7	21.7	20.7
87.5°	4.9	3.9	4.9	4.9	3.9	3.9	4.9	3.9	4.9	5.9	3.9
90°	48.5	48.7	49.0	49.3	49.7	50.0	49.7	49.3	49.0	48.7	48.5
92.5°	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1	47.1
95°	94.1	93.8	93.1	92.5	91.8	91.2	91.8	92.5	93.1	93.8	94.1
97.5°	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1	147.1
100°	203.0	202.8	202.5	202.2	201.8	201.5	201.8	202.2	202.5	202.8	203.0
102.5°	264.8	264.6	264.3	264.0	263.6	263.3	263.6	264.0	264.3	264.6	264.8
105°	326.5	326.5	326.5	326.5	326.5	326.5	326.5	326.5	326.5	326.5	326.5
107.5°	391.3	390.5	388.8	387.2	385.5	383.9	385.5	387.2	388.8	390.5	391.3
110°	457.4	456.9	455.9	455.0	454.0	453.0	454.0	455.0	455.9	456.9	457.4

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	522.2	521.9	521.2	520.5	519.9	519.2	519.9	520.5	521.2	521.9	522.2
115°	592.8	592.3	591.3	590.3	589.3	588.3	589.3	590.3	591.3	592.3	592.8
117.5°	657.5	657.0	656.0	655.1	654.1	653.1	654.1	655.1	656.0	657.0	657.5
120°	726.6	726.1	725.1	724.2	723.2	722.2	723.2	724.2	725.1	726.1	726.6
122.5°	792.8	792.5	791.8	791.2	790.5	789.9	790.5	791.2	791.8	792.5	792.8
125°	860.5	860.3	860.0	859.7	859.3	859.0	859.3	859.7	860.0	860.3	860.5
127.5°	925.2	924.7	923.7	922.8	921.8	920.8	921.8	922.8	923.7	924.7	925.2
130°	994.3	993.6	992.3	991.0	989.7	988.4	989.7	991.0	992.3	993.6	994.3
132.5°	1057.6	1057.1	1056.1	1055.1	1054.1	1053.1	1054.1	1055.1	1056.1	1057.1	1057.6
135°	1125.2	1124.7	1123.7	1122.8	1121.8	1120.8	1121.8	1122.8	1123.7	1124.7	1125.2
137.5°	1187.0	1186.3	1185.0	1183.7	1182.4	1181.1	1182.4	1183.7	1185.0	1186.3	1187.0
140°	1250.2	1249.6	1248.3	1247.0	1245.7	1244.4	1245.7	1247.0	1248.3	1249.6	1250.2
142.5°	1307.6	1306.9	1305.6	1304.3	1303.0	1301.7	1303.0	1304.3	1305.6	1306.9	1307.6
145°	1365.0	1364.3	1363.0	1361.7	1360.4	1359.1	1360.4	1361.7	1363.0	1364.3	1365.0
147.5°	1416.4	1415.8	1414.5	1413.2	1411.9	1410.6	1411.9	1413.2	1414.5	1415.8	1416.4
150°	1465.0	1464.5	1463.5	1462.6	1461.6	1460.6	1461.6	1462.6	1463.5	1464.5	1465.0
152.5°	1513.5	1512.8	1511.5	1510.2	1508.9	1507.6	1508.9	1510.2	1511.5	1512.8	1513.5
155°	1553.2	1552.7	1551.7	1550.8	1549.8	1548.8	1549.8	1550.8	1551.7	1552.7	1553.2
157.5°	1593.0	1592.2	1590.5	1588.9	1587.2	1585.6	1587.2	1588.9	1590.5	1592.2	1593.0
160°	1625.3	1624.6	1623.3	1622.0	1620.7	1619.4	1620.7	1622.0	1623.3	1624.6	1625.3
162.5°	1656.2	1655.4	1653.7	1652.1	1650.4	1648.8	1650.4	1652.1	1653.7	1655.4	1656.2
165°	1681.2	1680.4	1678.7	1677.1	1675.4	1673.8	1675.4	1677.1	1678.7	1680.4	1681.2
167.5°	1703.3	1702.5	1700.8	1699.2	1697.5	1695.9	1697.5	1699.2	1700.8	1702.5	1703.3
170°	1720.9	1719.9	1718.0	1716.0	1714.1	1712.1	1714.1	1716.0	1718.0	1719.9	1720.9
172.5°	1734.2	1733.2	1731.2	1729.3	1727.3	1725.3	1727.3	1729.3	1731.2	1733.2	1734.2
175°	1743.0	1742.0	1740.1	1738.1	1736.2	1734.2	1736.2	1738.1	1740.1	1742.0	1743.0
177.5°	1747.4	1746.4	1744.5	1742.5	1740.6	1738.6	1740.6	1742.5	1744.5	1746.4	1747.4
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6	1283.6
2.5°	1218.5	1226.4	1223.4	1212.6	1225.4	1225.4	1234.3	1234.3	1245.1	1249.1	1255.0
5°	1149.4	1155.3	1160.3	1155.3	1164.2	1178.0	1185.9	1192.8	1207.6	1213.5	1222.4
7.5°	1075.4	1086.3	1091.2	1091.2	1106.0	1121.8	1137.6	1147.4	1168.2	1176.1	1184.9
10°	1003.4	1016.2	1026.1	1025.1	1049.8	1059.6	1079.4	1102.1	1122.8	1134.6	1147.4
12.5°	927.4	934.3	948.1	967.9	973.8	991.6	1014.2	1042.9	1080.4	1091.2	1109.9
15°	864.3	883.0	893.9	902.8	916.6	933.3	958.0	985.6	1023.1	1046.8	1066.5
17.5°	811.0	835.7	842.6	840.6	858.4	884.0	912.6	933.3	966.9	995.5	1014.2
20°	767.6	777.5	789.3	794.2	808.0	835.7	863.3	887.0	914.6	937.3	959.0
22.5°	724.2	732.1	741.9	750.8	761.7	777.5	804.1	833.7	860.3	882.0	906.7
25°	688.7	693.6	702.5	709.4	721.2	732.1	750.8	783.4	814.9	827.8	849.5
27.5°	654.1	658.1	664.0	671.9	677.8	688.7	705.4	732.1	764.6	777.5	807.1
30°	623.5	626.5	632.4	636.4	639.3	652.2	665.0	685.7	710.4	728.1	749.8
32.5°	594.9	597.9	603.8	604.8	608.7	615.7	627.5	646.2	667.9	682.7	701.5
35°	563.4	565.3	571.3	573.2	576.2	582.1	591.0	604.8	624.5	635.4	652.2
37.5°	538.7	537.7	541.7	544.6	548.6	551.5	554.5	568.3	583.1	593.0	605.8
40°	512.1	510.1	511.1	515.0	517.0	520.9	520.9	534.7	544.6	552.5	562.4
42.5°	485.4	484.4	482.5	484.4	486.4	487.4	488.4	498.2	508.1	515.0	525.9
45°	458.8	457.8	455.8	456.8	456.8	458.8	461.7	465.7	472.6	478.5	484.4
47.5°	434.1	432.1	429.2	428.2	430.2	430.2	430.2	434.1	441.0	443.0	448.9
50°	408.5	405.5	401.6	399.6	399.6	398.6	400.6	401.6	407.5	409.4	414.4
52.5°	380.8	378.9	374.9	371.0	372.0	370.0	371.0	372.0	373.9	376.9	379.8
55°	353.2	349.3	346.3	345.3	342.4	342.4	339.4	343.3	342.4	343.3	347.3
57.5°	326.6	322.6	317.7	315.7	312.8	311.8	309.8	308.8	309.8	312.8	315.7
60°	295.0	293.0	290.1	287.1	285.1	282.2	280.2	280.2	279.2	279.2	280.2
62.5°	264.4	263.4	259.5	258.5	256.5	254.5	251.6	249.6	249.6	251.6	252.6
65°	234.8	233.8	230.9	229.9	224.9	223.0	222.0	221.0	219.0	219.0	219.0
67.5°	207.2	204.2	204.2	199.3	195.4	193.4	191.4	190.4	190.4	190.4	191.4
70°	176.6	176.6	173.6	170.7	166.7	167.7	164.8	161.8	161.8	159.8	160.8
72.5°	147.0	146.0	143.1	142.1	139.1	136.2	134.2	136.2	133.2	132.2	133.2
75°	118.4	117.4	115.4	113.5	114.4	111.5	108.5	107.5	107.5	105.6	105.6
77.5°	90.8	92.7	88.8	87.8	85.8	83.9	82.9	81.9	81.9	81.9	83.9
80°	63.1	64.1	64.1	62.2	63.1	60.2	60.2	60.2	57.2	58.2	59.2
82.5°	40.5	40.5	39.5	40.5	39.5	39.5	38.5	38.5	37.5	37.5	38.5
85°	22.7	21.7	20.7	22.7	21.7	21.7	20.7	20.7	20.7	20.7	20.7
87.5°	4.9	5.9	5.9	5.9	5.9	6.9	6.9	6.9	7.9	7.9	7.9
90°	48.8	49.5	50.2	50.8	51.5	44.3	37.1	29.9	22.7	19.1	17.1
92.5°	46.9	46.6	46.3	45.9	45.6	45.3	44.9	44.6	44.3	44.1	42.8
95°	94.1	94.1	94.1	94.1	94.1	93.5	92.8	92.2	91.5	91.2	89.6
97.5°	147.1	147.1	147.1	147.1	147.1	145.8	144.5	143.2	141.9	141.2	139.7
100°	203.0	203.0	203.0	203.0	203.0	202.0	201.0	200.1	199.1	198.6	197.3
102.5°	264.6	264.3	264.0	263.6	263.3	262.0	260.7	259.4	258.1	257.4	256.4
105°	326.2	325.5	324.9	324.2	323.6	322.9	322.3	321.6	320.9	320.6	320.1
107.5°	391.1	390.8	390.5	390.1	389.8	389.8	389.8	389.8	389.8	389.8	389.1
110°	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	457.4	456.4

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	522.7	523.7	524.6	525.6	526.6	526.9	527.2	527.5	527.8	528.0	527.0
115°	593.0	593.3	593.6	593.9	594.2	594.9	595.5	596.2	596.9	597.2	596.2
117.5°	658.0	659.0	659.9	660.9	661.9	663.5	665.1	666.8	668.4	669.2	667.9
120°	726.6	726.6	726.6	726.6	726.6	729.2	731.8	734.5	737.1	738.4	737.1
122.5°	793.3	794.3	795.2	796.2	797.2	798.8	800.5	802.1	803.8	804.6	803.0
125°	861.0	862.0	862.9	863.9	864.9	865.9	866.9	867.8	868.8	869.3	867.8
127.5°	925.9	927.2	928.5	929.8	931.1	932.4	933.7	935.0	936.3	936.9	935.1
130°	994.6	995.3	995.9	996.6	997.2	997.9	998.5	999.2	999.9	1000.2	998.1
132.5°	1058.4	1060.0	1061.7	1063.3	1064.9	1064.6	1064.2	1063.9	1063.6	1063.4	1061.8
135°	1125.4	1125.7	1126.0	1126.4	1126.7	1126.0	1125.4	1124.7	1124.0	1123.7	1121.9
137.5°	1187.2	1187.5	1187.8	1188.2	1188.5	1187.8	1187.2	1186.5	1185.8	1185.5	1184.0
140°	1250.2	1250.2	1250.2	1250.2	1250.2	1248.6	1247.0	1245.3	1243.7	1242.9	1241.4
142.5°	1307.4	1307.1	1306.8	1306.4	1306.1	1305.1	1304.1	1303.2	1302.2	1301.7	1300.2
145°	1364.8	1364.5	1364.2	1363.8	1363.5	1361.5	1359.6	1357.6	1355.7	1354.7	1353.6
147.5°	1416.1	1415.4	1414.8	1414.1	1413.5	1412.2	1410.9	1409.6	1408.3	1407.6	1406.1
150°	1464.5	1463.5	1462.6	1461.6	1460.6	1459.3	1458.0	1456.7	1455.4	1454.7	1453.7
152.5°	1512.8	1511.5	1510.2	1508.9	1507.6	1506.0	1504.4	1502.7	1501.1	1500.3	1499.3
155°	1552.4	1550.8	1549.1	1547.5	1545.9	1544.9	1543.9	1543.0	1542.0	1541.5	1541.0
157.5°	1591.9	1589.6	1587.3	1585.0	1582.7	1582.0	1581.4	1580.7	1580.0	1579.7	1579.4
160°	1624.3	1622.4	1620.4	1618.5	1616.5	1616.2	1615.8	1615.5	1615.2	1615.0	1614.7
162.5°	1655.1	1652.8	1650.5	1648.2	1645.9	1645.6	1645.2	1644.9	1644.6	1644.4	1644.4
165°	1680.1	1677.8	1675.5	1673.2	1670.9	1670.9	1670.9	1670.9	1670.9	1670.9	1671.1
167.5°	1702.2	1699.9	1697.6	1695.3	1693.0	1693.0	1693.0	1693.0	1693.0	1693.0	1693.5
170°	1719.8	1717.5	1715.2	1712.9	1710.6	1710.9	1711.3	1711.6	1711.9	1712.1	1712.6
172.5°	1733.1	1730.8	1728.5	1726.2	1723.9	1724.2	1724.5	1724.8	1725.1	1725.3	1725.8
175°	1741.9	1739.6	1737.3	1735.0	1732.7	1733.3	1734.0	1734.6	1735.3	1735.6	1736.1
177.5°	1746.4	1744.5	1742.5	1740.6	1738.6	1739.2	1739.9	1740.5	1741.2	1741.5	1742.0
180°	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0	1743.0

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1283.6	1283.6	1283.6	1283.6
2.5°	1259.9	1259.9	1274.7	1290.5
5°	1232.3	1239.2	1262.9	1284.6
7.5°	1205.7	1217.5	1247.1	1274.7
10°	1173.1	1188.9	1225.4	1257.9
12.5°	1141.5	1156.3	1198.7	1235.2
15°	1097.1	1115.9	1161.3	1206.6
17.5°	1052.7	1071.5	1126.7	1180.0
20°	1000.4	1025.1	1087.3	1158.3
22.5°	952.1	982.7	1051.7	1109.0
25°	898.8	946.2	1010.3	1084.3
27.5°	851.5	898.8	963.9	1038.9
30°	798.2	846.5	913.6	982.7
32.5°	746.9	791.3	856.4	941.2
35°	693.6	736.0	799.2	885.0
37.5°	645.3	686.7	755.8	834.7
40°	597.9	641.3	700.5	779.4
42.5°	553.5	592.0	645.3	724.2
45°	513.0	540.7	590.0	664.0
47.5°	470.6	495.3	540.7	614.7
50°	431.2	451.9	491.3	560.4
52.5°	392.7	410.4	446.9	502.2
55°	358.1	374.9	401.6	455.8
57.5°	322.6	335.5	361.1	404.5
60°	288.1	299.9	320.7	356.2
62.5°	253.6	263.4	283.2	311.8
65°	223.0	230.9	245.7	270.3
67.5°	193.4	198.3	210.2	229.9
70°	164.8	168.7	178.6	194.4
72.5°	134.2	138.1	149.0	159.8
75°	108.5	109.5	117.4	126.3
77.5°	84.8	83.9	89.8	96.7
80°	58.2	61.2	66.1	69.1
82.5°	39.5	40.5	42.4	44.4
85°	21.7	22.7	22.7	25.7
87.5°	8.9	9.9	9.9	10.9
90°	13.2	9.3	5.4	1.5
92.5°	40.2	37.6	35.0	32.4
95°	86.3	83.0	79.8	76.5
97.5°	136.8	133.9	130.9	128.0
100°	194.7	192.0	189.4	186.8
102.5°	254.5	252.5	250.6	248.6
105°	319.1	318.2	317.2	316.2
107.5°	387.8	386.5	385.2	383.9
110°	454.5	452.5	450.6	448.6

TEST NUMBER: P1029629

CATALOG NUMBER: S122DIW-B675D1440UB2750-4F0-XX-W2A-A1_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	525.1	523.1	521.2	519.2
115°	594.2	592.3	590.3	588.3
117.5°	665.3	662.7	660.1	657.5
120°	734.5	731.8	729.2	726.6
122.5°	799.7	796.4	793.2	789.9
125°	864.9	861.9	859.0	856.0
127.5°	931.5	928.0	924.4	920.8
130°	993.8	989.6	985.3	981.1
132.5°	1058.5	1055.2	1052.0	1048.7
135°	1118.3	1114.8	1111.2	1107.6
137.5°	1181.1	1178.2	1175.2	1172.3
140°	1238.5	1235.5	1232.6	1229.6
142.5°	1297.3	1294.4	1291.4	1288.5
145°	1351.3	1349.0	1346.7	1344.4
147.5°	1403.2	1400.3	1397.3	1394.4
150°	1451.8	1449.8	1447.9	1445.9
152.5°	1497.4	1495.4	1493.5	1491.5
155°	1540.0	1539.1	1538.1	1537.1
157.5°	1578.7	1578.1	1577.4	1576.8
160°	1614.0	1613.4	1612.7	1612.1
162.5°	1644.4	1644.4	1644.4	1644.4
165°	1671.4	1671.7	1672.1	1672.4
167.5°	1694.5	1695.4	1696.4	1697.4
170°	1713.6	1714.5	1715.5	1716.5
172.5°	1726.8	1727.7	1728.7	1729.7
175°	1737.1	1738.0	1739.0	1740.0
177.5°	1743.0	1743.9	1744.9	1745.9
180°	1743.0	1743.0	1743.0	1743.0

(END OF REPORT)