

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1029690

Luminaire Tested: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1029690
REPORT IS A COMBINATION OF REPORTS P986657 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K
Description: Define 2 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5782.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44	44	44
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	37	37	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32	32	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28	28	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	32	33	30	28	25	25	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22	22	22
7	60	48	40	34	55	44	38	33	39	33	29	33	29	26	28	25	22	20	20	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	22	20	18	18	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16	16	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	20950	20950	20950	20950
5°	21000	22337	21081	17772
10°	20756	24384	20887	14652
15°	20252	25721	20534	12342
20°	19937	24150	19937	10726
25°	19302	20747	19390	9593
30°	18256	16309	18604	8689
35°	17330	11278	17620	7951
40°	16266	8515	16450	7360
45°	14952	6997	15196	6725
50°	13817	6141	13841	6156
55°	12524	5233	12604	5539
60°	11143	4370	11297	4833
65°	9908	3554	10089	4127
70°	8679	2790	8900	3329
75°	7283	2025	7569	2414
80°	5684	1282	6092	1434
85°	3729	647	4026	477

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 21656 cd/sqm

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.1	2.2
10°-20°	366.9	6.3
20°-30°	532.5	9.2
30°-40°	561.3	9.7
40°-50°	496.7	8.6
50°-60°	396.6	6.9
60°-70°	269.4	4.7
70°-80°	137.8	2.4
80°-90°	34.3	0.6
90°-100°	32.2	0.6
100°-110°	119.9	2.1
110°-120°	318.1	5.5
120°-130°	527.5	9.1
130°-140°	560.4	9.7
140°-150°	520.8	9.0
150°-160°	418.7	7.2
160°-170°	269.8	4.7
170°-180°	92.9	1.6
0°-30°	1025.5	17.7
0°-40°	1586.8	27.4
0°-60°	2480.2	42.9
0°-90°	2921.7	50.5
90°-120°	470.2	8.1
90°-150°	2078.9	36.0
90°-180°	2860.0	49.5
0°-180°	5782.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1324	1324	1324	1324	1324	
5°	1324	1478	1330	1176	1324	126
15°	1244	1817	1261	872	1244	351
25°	1118	1514	1123	700	1118	511
35°	912	824	928	581	912	571
45°	685	496	696	477	685	531
55°	470	349	473	369	470	419
65°	279	215	284	249	279	277
75°	130	106	135	126	130	140
85°	26	28	28	20	26	31
90°	1	19	1	19	1	4
95°	46	30	46	30	46	54
105°	215	54	215	54	215	229
115°	406	58	406	58	406	400
125°	574	604	574	604	574	512
135°	710	734	710	734	710	549
145°	824	837	824	837	824	515
155°	907	908	907	908	907	418
165°	956	954	956	954	956	270
175°	978	972	978	972	978	93
180°	976	976	976	976	976	

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1330.6	1333.7	1338.7	1339.8	1349.9	1358.1	1367.2	1367.2	1370.3	1369.3	1361.1
5°	1324.5	1333.7	1346.9	1358.1	1376.4	1384.5	1396.7	1405.9	1414.0	1420.1	1419.1
7.5°	1314.3	1330.6	1349.9	1371.3	1395.7	1409.9	1427.2	1443.5	1454.7	1464.9	1472.0
10°	1297.0	1324.5	1350.9	1379.4	1411.0	1430.3	1450.6	1472.0	1489.3	1508.6	1526.9
12.5°	1273.6	1313.3	1345.9	1383.5	1422.2	1443.5	1476.1	1492.3	1525.9	1574.7	1588.0
15°	1244.1	1298.0	1328.6	1376.4	1427.2	1444.5	1489.3	1515.7	1584.9	1615.4	1652.1
17.5°	1216.7	1276.7	1317.4	1372.3	1422.2	1455.7	1499.5	1553.4	1611.4	1655.1	1695.8
20°	1194.3	1252.3	1301.1	1362.1	1425.2	1467.9	1513.7	1578.8	1641.9	1686.6	1718.2
22.5°	1143.4	1217.7	1274.7	1342.8	1419.1	1478.1	1521.8	1593.1	1661.2	1688.7	1716.1
25°	1118.0	1182.1	1248.2	1325.5	1415.0	1485.2	1522.9	1602.2	1662.2	1672.4	1678.5
27.5°	1071.2	1143.4	1220.7	1309.2	1414.0	1473.0	1520.8	1593.1	1640.9	1633.8	1615.4
30°	1013.2	1101.7	1187.2	1282.8	1399.8	1463.9	1508.6	1574.7	1599.2	1562.5	1530.0
32.5°	970.5	1053.9	1148.5	1259.4	1383.5	1444.5	1488.3	1540.2	1545.2	1479.1	1424.2
35°	912.5	1005.1	1111.9	1228.9	1356.0	1411.0	1451.7	1483.2	1458.8	1366.2	1301.1
37.5°	860.6	952.2	1066.1	1185.1	1318.4	1372.3	1404.9	1409.9	1349.9	1268.5	1172.9
40°	803.7	898.3	1017.3	1142.4	1276.7	1323.5	1343.8	1328.6	1242.1	1147.5	1036.6
42.5°	746.7	840.3	968.4	1096.6	1223.8	1263.5	1271.6	1229.9	1124.1	1013.2	885.0
45°	684.6	782.3	910.5	1039.7	1162.7	1185.1	1186.1	1126.1	1001.0	885.0	766.0
47.5°	633.8	724.3	851.5	980.7	1084.4	1099.7	1093.6	1024.4	888.1	757.9	654.1
50°	577.8	664.3	790.4	917.6	1006.1	1010.2	994.9	896.2	763.0	643.9	561.5
52.5°	517.8	605.3	721.3	843.3	922.7	916.6	887.1	781.3	656.1	557.5	494.4
55°	470.0	547.3	656.1	775.2	831.1	813.8	781.3	673.4	574.8	491.3	436.4
57.5°	417.1	485.2	592.1	695.8	728.4	712.1	679.5	578.8	487.3	424.2	387.6
60°	367.2	429.3	522.9	609.4	634.8	617.5	579.8	489.3	423.2	370.3	342.8
62.5°	321.5	375.4	453.7	533.1	543.2	525.9	493.4	420.1	363.2	321.5	301.1
65°	278.7	329.6	392.7	452.7	461.8	443.5	410.0	357.1	309.3	282.8	263.5
67.5°	237.0	277.7	333.7	377.4	382.5	365.2	337.7	295.0	265.5	237.0	222.8
70°	200.4	230.9	274.7	310.3	312.3	296.0	281.8	243.1	220.7	200.4	189.2
72.5°	164.8	186.2	219.7	246.2	247.2	237.0	223.8	199.4	180.1	165.8	154.6
75°	130.2	148.5	168.9	192.3	191.2	183.1	172.9	157.7	141.4	132.2	127.2
77.5°	99.7	110.9	127.2	142.4	142.4	138.3	132.2	121.1	110.9	101.7	96.6
80°	71.2	78.3	91.6	96.6	98.7	97.7	92.6	84.4	80.4	73.2	71.2
82.5°	45.8	50.9	57.0	62.1	65.1	63.1	62.1	58.0	51.9	49.8	47.8
85°	26.4	28.5	31.5	34.6	35.6	34.6	36.6	33.6	30.5	30.5	29.5
87.5°	11.2	12.2	14.2	14.2	15.3	15.3	14.2	15.3	15.3	14.2	13.2
90°	0.7	2.4	4.2	5.9	7.6	8.5	9.1	10.4	11.6	12.9	14.1
92.5°	17.6	17.0	16.4	15.7	15.1	14.8	15.0	15.5	16.0	16.4	16.9
95°	45.9	40.7	35.5	30.4	25.2	22.6	23.1	24.2	25.3	26.4	27.5
97.5°	82.6	69.7	56.9	44.0	31.1	24.7	26.0	28.5	31.0	33.5	36.0
100°	125.0	103.5	82.0	60.5	39.0	28.2	29.5	32.2	34.9	37.5	40.2
102.5°	171.6	171.3	170.9	170.6	170.3	170.1	155.8	127.3	98.8	70.2	41.7
105°	214.6	219.3	224.0	228.7	233.4	235.8	214.4	171.6	128.7	85.9	43.1
107.5°	264.7	268.6	272.6	276.5	280.4	282.4	256.0	203.1	150.2	97.4	44.5
110°	312.7	316.0	319.3	322.6	325.9	327.6	304.9	259.6	214.2	168.9	123.5

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	357.9	360.7	363.5	366.4	369.2	370.6	369.3	366.6	363.9	361.3	358.6
115°	405.9	408.6	411.2	413.9	416.6	417.9	419.9	423.8	427.7	431.7	435.6
117.5°	447.6	450.7	453.9	457.0	460.1	461.7	463.0	465.7	468.4	471.0	473.7
120°	494.2	496.6	498.9	501.3	503.6	504.8	506.2	509.0	511.9	514.7	517.5
122.5°	533.7	536.2	538.7	541.2	543.7	545.0	546.6	549.7	552.8	556.0	559.1
125°	574.0	576.0	578.0	580.1	582.1	583.1	584.6	587.6	590.5	593.5	596.5
127.5°	610.7	612.9	615.1	617.3	619.5	620.6	621.8	624.1	626.4	628.8	631.1
130°	645.3	647.8	650.3	652.8	655.3	656.6	657.5	659.2	660.9	662.6	664.3
132.5°	680.6	682.6	684.6	686.7	688.7	689.7	690.6	692.3	694.0	695.8	697.5
135°	710.2	712.7	715.2	717.7	720.2	721.5	722.2	723.6	725.1	726.5	727.9
137.5°	741.3	743.2	745.0	746.9	748.8	749.7	750.5	752.1	753.6	755.2	756.8
140°	771.6	772.9	774.1	775.4	776.7	777.3	778.2	779.9	781.6	783.3	785.0
142.5°	797.0	798.1	799.2	800.3	801.4	802.0	803.0	805.1	807.1	809.2	811.2
145°	823.9	823.7	823.6	823.4	823.3	823.2	824.5	827.2	829.9	832.5	835.2
147.5°	847.2	846.7	846.3	845.8	845.3	845.1	846.4	849.1	851.8	854.4	857.1
150°	869.8	868.7	867.6	866.5	865.4	864.8	866.1	868.6	871.1	873.6	876.1
152.5°	888.8	887.6	886.3	885.1	883.8	883.2	884.4	886.7	889.1	891.4	893.8
155°	907.2	905.8	904.4	902.9	901.5	900.8	901.7	903.6	905.5	907.4	909.3
157.5°	922.0	920.8	919.5	918.3	917.0	916.4	917.1	918.5	919.9	921.3	922.7
160°	934.7	933.8	932.8	931.9	931.0	930.5	931.0	931.9	932.8	933.8	934.7
162.5°	946.0	945.1	944.1	943.2	942.3	941.8	942.2	943.0	943.7	944.5	945.3
165°	955.9	955.0	954.0	953.1	952.2	951.7	951.9	952.4	952.9	953.3	953.8
167.5°	963.7	962.7	961.8	960.8	959.9	959.4	959.6	960.1	960.6	961.0	961.5
170°	970.0	969.1	968.1	967.2	966.3	965.8	966.0	966.3	966.6	966.9	967.2
172.5°	974.2	973.3	972.3	971.4	970.5	970.0	970.2	970.5	970.8	971.1	971.4
175°	977.8	976.7	975.6	974.5	973.4	972.8	973.0	973.3	973.6	973.9	974.2
177.5°	979.2	978.1	977.0	975.9	974.8	974.2	974.3	974.5	974.6	974.8	975.0
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1375.4	1376.4	1378.4	1388.6	1393.7	1394.7	1390.6	1399.8	1402.8	1399.8	1397.7
5°	1440.5	1446.6	1458.8	1472.0	1471.0	1472.0	1478.1	1484.2	1486.2	1478.1	1481.2
7.5°	1497.4	1509.6	1522.9	1543.2	1543.2	1553.4	1557.5	1562.5	1574.7	1568.6	1566.6
10°	1562.5	1578.8	1603.2	1635.8	1636.8	1647.0	1657.1	1673.4	1678.5	1674.4	1676.5
12.5°	1643.9	1675.5	1677.5	1713.1	1729.4	1731.4	1747.7	1744.6	1754.8	1754.8	1772.1
15°	1679.5	1728.4	1755.8	1790.4	1800.6	1788.4	1801.6	1815.8	1816.9	1816.9	1815.8
17.5°	1743.6	1762.9	1790.4	1808.7	1812.8	1812.8	1813.8	1819.9	1815.8	1807.7	1813.8
20°	1756.8	1765.0	1775.2	1773.1	1775.2	1765.0	1754.8	1744.6	1745.7	1740.6	1755.8
22.5°	1732.4	1730.4	1707.0	1691.7	1691.7	1671.4	1652.1	1642.9	1633.8	1636.8	1641.9
25°	1671.4	1639.9	1611.4	1589.0	1583.9	1551.4	1524.9	1516.8	1501.5	1513.7	1515.7
27.5°	1573.7	1538.1	1492.3	1473.0	1446.6	1433.3	1415.0	1390.6	1359.1	1377.4	1374.3
30°	1469.0	1416.1	1378.4	1331.6	1289.9	1286.9	1252.3	1211.6	1195.3	1195.3	1204.5
32.5°	1352.0	1281.8	1226.8	1160.7	1120.0	1102.7	1061.0	1020.3	1029.5	999.0	1010.2
35°	1215.6	1123.1	1053.9	989.8	959.3	938.9	885.0	862.7	838.2	824.0	850.4
37.5°	1085.4	978.6	890.1	819.9	808.7	772.1	735.5	721.3	707.0	713.1	712.1
40°	926.7	832.1	752.8	697.9	678.5	661.2	636.8	619.5	610.4	615.5	616.5
42.5°	783.3	704.0	645.0	606.3	590.0	577.8	565.6	551.4	548.3	548.3	552.4
45°	672.4	607.3	567.6	536.1	527.0	517.8	508.6	502.5	500.5	496.4	499.5
47.5°	583.9	532.0	507.6	484.2	474.1	472.0	463.9	460.8	456.8	455.7	456.8
50°	509.7	477.1	454.7	441.5	434.4	431.3	427.3	421.2	419.1	424.2	422.2
52.5°	457.8	427.3	415.0	401.8	397.8	393.7	387.6	388.6	387.6	385.5	385.5
55°	405.9	386.6	374.4	364.2	363.2	359.1	354.0	352.0	351.0	348.9	352.0
57.5°	364.2	348.9	337.7	328.6	324.5	324.5	319.4	315.4	315.4	314.3	315.4
60°	322.5	307.2	300.1	290.9	287.9	286.9	283.8	281.8	278.7	278.7	278.7
62.5°	283.8	271.6	263.5	255.3	256.4	251.3	247.2	245.2	245.2	246.2	246.2
65°	247.2	239.1	228.9	221.8	219.7	218.7	216.7	215.7	212.6	214.6	214.6
67.5°	213.6	202.4	196.3	193.3	190.2	189.2	187.2	185.1	184.1	183.1	185.1
70°	180.1	170.9	165.8	163.8	160.7	159.7	158.7	155.6	156.7	157.7	158.7
72.5°	149.5	141.4	140.4	134.3	134.3	134.3	130.2	132.2	131.2	129.2	131.2
75°	118.0	113.9	111.9	108.8	109.9	108.8	107.8	104.8	104.8	105.8	106.8
77.5°	93.6	89.5	88.5	85.5	83.4	85.5	83.4	82.4	82.4	83.4	83.4
80°	69.2	67.1	64.1	64.1	64.1	63.1	63.1	63.1	62.1	61.0	62.1
82.5°	45.8	45.8	44.8	43.7	44.8	42.7	43.7	43.7	43.7	43.7	43.7
85°	29.5	28.5	28.5	27.5	27.5	27.5	28.5	26.4	26.4	27.5	27.5
87.5°	13.2	13.2	13.2	14.2	13.2	13.2	13.2	14.2	13.2	13.2	13.2
90°	14.9	15.7	16.4	17.2	17.6	17.8	18.1	18.4	18.8	19.1	18.8
92.5°	17.2	17.6	17.9	18.2	18.4	18.5	18.6	18.8	18.9	19.1	18.9
95°	28.3	29.1	29.9	30.7	31.1	31.0	30.9	30.7	30.6	30.4	30.6
97.5°	36.5	36.9	37.4	37.9	38.1	38.2	38.3	38.5	38.6	38.8	38.6
100°	41.5	42.7	44.0	45.3	45.9	46.1	46.4	46.7	47.0	47.3	47.0
102.5°	43.4	45.1	46.8	48.5	49.4	49.6	50.1	50.6	51.0	51.5	51.0
105°	44.8	46.5	48.2	49.9	50.8	51.1	51.8	52.4	53.1	53.7	53.1
107.5°	46.2	47.9	49.6	51.3	52.2	52.5	53.2	53.8	54.5	55.1	54.5
110°	107.8	92.1	76.4	60.7	52.9	53.2	53.9	54.5	55.2	55.8	55.2

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.0	223.4	155.8	88.2	54.4	54.6	55.1	55.6	56.0	56.5	56.0
115°	363.0	290.3	217.7	145.0	108.7	103.1	91.8	80.5	69.2	57.9	69.2
117.5°	451.3	428.9	406.4	384.0	372.8	352.2	311.1	270.0	228.9	187.8	228.9
120°	519.4	521.3	523.2	525.1	526.0	515.4	494.2	473.0	451.8	430.6	451.8
122.5°	560.1	561.0	562.0	562.9	563.4	563.5	563.6	563.8	563.9	564.1	563.9
125°	597.6	598.7	599.8	600.9	601.5	601.7	602.2	602.7	603.1	603.6	603.1
127.5°	632.7	634.3	635.8	637.4	638.2	638.3	638.4	638.6	638.7	638.9	638.7
130°	666.0	667.8	669.5	671.2	672.1	672.0	671.9	671.7	671.6	671.4	671.6
132.5°	698.9	700.3	701.8	703.2	703.9	703.8	703.7	703.5	703.4	703.2	703.4
135°	729.5	731.0	732.6	734.1	734.9	734.7	734.4	734.1	733.8	733.5	733.8
137.5°	758.4	760.0	761.5	763.1	763.9	763.7	763.2	762.7	762.2	761.7	762.2
140°	786.4	787.8	789.3	790.7	791.4	791.0	790.2	789.5	788.7	787.9	788.7
142.5°	812.4	813.7	814.9	816.2	816.8	816.4	815.6	814.9	814.1	813.3	814.1
145°	836.3	837.4	838.5	839.6	840.1	839.7	838.9	838.2	837.4	836.6	837.4
147.5°	857.9	858.7	859.4	860.2	860.6	860.3	859.7	859.0	858.4	857.8	858.4
150°	877.1	878.0	879.0	879.9	880.4	880.0	879.2	878.4	877.6	876.8	877.6
152.5°	894.7	895.7	896.6	897.5	898.0	897.5	896.4	895.3	894.2	893.1	894.2
155°	910.2	911.2	912.1	913.0	913.5	912.9	911.6	910.4	909.1	907.9	909.1
157.5°	923.8	924.9	926.0	927.1	927.7	927.1	925.8	924.5	923.3	922.0	923.3
160°	935.6	936.6	937.5	938.4	938.9	938.4	937.3	936.2	935.1	934.0	935.1
162.5°	946.4	947.5	948.6	949.7	950.2	949.5	948.1	946.7	945.3	943.9	945.3
165°	954.9	956.0	957.1	958.2	958.7	958.2	957.1	956.0	954.9	953.8	954.9
167.5°	962.6	963.7	964.8	965.9	966.5	965.8	964.4	962.9	961.5	960.1	961.5
170°	968.3	969.4	970.5	971.6	972.1	971.4	970.0	968.6	967.2	965.8	967.2
172.5°	972.5	973.6	974.7	975.8	976.4	975.7	974.3	972.8	971.4	970.0	971.4
175°	975.3	976.4	977.5	978.6	979.2	978.4	976.8	975.3	973.7	972.1	973.7
177.5°	976.1	977.2	978.3	979.4	979.9	979.2	977.8	976.3	974.9	973.5	974.9
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1402.8	1395.7	1389.6	1390.6	1395.7	1391.6	1381.5	1368.2	1363.2	1357.1	1363.2
5°	1487.3	1481.2	1469.0	1470.0	1466.9	1462.8	1446.6	1426.2	1426.2	1409.9	1407.9
7.5°	1570.7	1561.5	1553.4	1551.4	1540.2	1532.0	1517.8	1489.3	1478.1	1458.8	1447.6
10°	1664.3	1657.1	1648.0	1636.8	1630.7	1616.5	1593.1	1551.4	1531.0	1504.6	1485.2
12.5°	1758.9	1757.9	1737.5	1715.1	1714.1	1691.7	1675.5	1619.5	1592.0	1556.4	1510.7
15°	1818.9	1813.8	1802.6	1791.4	1794.5	1770.1	1733.4	1667.3	1649.0	1606.3	1557.5
17.5°	1817.9	1817.9	1814.8	1812.8	1809.7	1802.6	1782.3	1738.5	1709.0	1655.1	1609.3
20°	1759.9	1773.1	1776.2	1775.2	1785.3	1790.4	1789.4	1761.9	1738.5	1690.7	1643.9
22.5°	1643.9	1674.4	1687.7	1695.8	1717.2	1728.4	1754.8	1744.6	1738.5	1702.9	1663.3
25°	1536.1	1546.3	1585.9	1588.0	1617.5	1644.9	1671.4	1688.7	1711.1	1697.8	1664.3
27.5°	1396.7	1420.1	1448.6	1470.0	1476.1	1532.0	1575.8	1608.3	1659.2	1663.3	1652.1
30°	1239.0	1250.2	1297.0	1325.5	1358.1	1398.8	1461.8	1517.8	1563.6	1605.3	1619.5
32.5°	1046.8	1092.6	1120.0	1154.6	1183.1	1255.3	1332.6	1404.9	1457.8	1528.0	1558.5
35°	870.8	906.4	953.2	967.4	1019.3	1080.4	1181.1	1273.6	1354.0	1425.2	1487.3
37.5°	725.3	753.8	803.7	826.0	856.5	934.9	1019.3	1134.3	1230.9	1318.4	1395.7
40°	625.6	647.0	684.6	691.7	717.2	788.4	856.5	964.4	1092.6	1210.6	1295.0
42.5°	557.5	567.6	593.1	602.2	618.5	666.3	727.4	829.1	948.1	1070.2	1189.2
45°	508.6	515.8	531.0	539.2	559.5	580.9	630.7	712.1	805.7	928.8	1057.0
47.5°	464.9	474.1	480.2	485.2	496.4	519.8	552.4	612.4	701.9	814.8	938.9
50°	428.3	431.3	442.5	443.5	450.7	465.9	496.4	533.1	604.3	695.8	815.9
52.5°	391.7	394.7	401.8	408.9	412.0	424.2	444.6	475.1	528.0	600.2	707.0
55°	355.0	359.1	366.2	371.3	374.4	384.5	396.7	426.2	467.9	518.8	606.3
57.5°	318.4	327.6	329.6	332.7	337.7	348.9	360.1	377.4	410.0	456.8	520.8
60°	283.8	286.9	294.0	297.0	302.1	308.2	322.5	335.7	359.1	395.7	453.7
62.5°	248.2	255.3	258.4	261.4	265.5	272.6	281.8	296.0	316.4	345.9	391.7
65°	217.7	218.7	224.8	228.9	233.0	238.0	247.2	260.4	272.6	300.1	333.7
67.5°	188.2	190.2	192.3	196.3	201.4	206.5	214.6	221.8	237.0	255.3	281.8
70°	159.7	159.7	164.8	167.9	166.8	172.9	179.0	187.2	198.4	215.7	237.0
72.5°	134.3	133.3	137.3	138.3	140.4	144.5	148.5	156.7	162.8	176.0	192.3
75°	106.8	108.8	110.9	110.9	113.9	117.0	121.1	125.1	132.2	140.4	152.6
77.5°	84.4	84.4	86.5	87.5	90.5	89.5	93.6	97.7	102.7	109.9	119.0
80°	62.1	64.1	64.1	64.1	65.1	66.1	70.2	73.2	76.3	81.4	85.5
82.5°	43.7	43.7	45.8	45.8	45.8	47.8	47.8	48.8	50.9	53.9	57.0
85°	27.5	27.5	27.5	28.5	27.5	28.5	30.5	29.5	30.5	32.6	32.6
87.5°	13.2	13.2	13.2	13.2	13.2	14.2	13.2	14.2	15.3	15.3	15.3
90°	18.4	18.1	17.8	17.6	17.2	16.4	15.7	14.9	14.1	12.9	11.6
92.5°	18.8	18.6	18.5	18.4	18.2	17.9	17.6	17.2	16.9	16.4	16.0
95°	30.7	30.9	31.0	31.1	30.7	29.9	29.1	28.3	27.5	26.4	25.3
97.5°	38.5	38.3	38.2	38.1	37.9	37.4	36.9	36.5	36.0	33.5	31.0
100°	46.7	46.4	46.1	45.9	45.3	44.0	42.7	41.5	40.2	37.5	34.9
102.5°	50.6	50.1	49.6	49.4	48.5	46.8	45.1	43.4	41.7	70.2	98.8
105°	52.4	51.8	51.1	50.8	49.9	48.2	46.5	44.8	43.1	85.9	128.7
107.5°	53.8	53.2	52.5	52.2	51.3	49.6	47.9	46.2	44.5	97.4	150.2
110°	54.5	53.9	53.2	52.9	60.7	76.4	92.1	107.8	123.5	168.9	214.2

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	55.6	55.1	54.6	54.4	88.2	155.8	223.4	291.0	358.6	361.3	363.9
115°	80.5	91.8	103.1	108.7	145.0	217.7	290.3	363.0	435.6	431.7	427.7
117.5°	270.0	311.1	352.2	372.8	384.0	406.4	428.9	451.3	473.7	471.0	468.4
120°	473.0	494.2	515.4	526.0	525.1	523.2	521.3	519.4	517.5	514.7	511.9
122.5°	563.8	563.6	563.5	563.4	562.9	562.0	561.0	560.1	559.1	556.0	552.8
125°	602.7	602.2	601.7	601.5	600.9	599.8	598.7	597.6	596.5	593.5	590.5
127.5°	638.6	638.4	638.3	638.2	637.4	635.8	634.3	632.7	631.1	628.8	626.4
130°	671.7	671.9	672.0	672.1	671.2	669.5	667.8	666.0	664.3	662.6	660.9
132.5°	703.5	703.7	703.8	703.9	703.2	701.8	700.3	698.9	697.5	695.8	694.0
135°	734.1	734.4	734.7	734.9	734.1	732.6	731.0	729.5	727.9	726.5	725.1
137.5°	762.7	763.2	763.7	763.9	763.1	761.5	760.0	758.4	756.8	755.2	753.6
140°	789.5	790.2	791.0	791.4	790.7	789.3	787.8	786.4	785.0	783.3	781.6
142.5°	814.9	815.6	816.4	816.8	816.2	814.9	813.7	812.4	811.2	809.2	807.1
145°	838.2	838.9	839.7	840.1	839.6	838.5	837.4	836.3	835.2	832.5	829.9
147.5°	859.0	859.7	860.3	860.6	860.2	859.4	858.7	857.9	857.1	854.4	851.8
150°	878.4	879.2	880.0	880.4	879.9	879.0	878.0	877.1	876.1	873.6	871.1
152.5°	895.3	896.4	897.5	898.0	897.5	896.6	895.7	894.7	893.8	891.4	889.1
155°	910.4	911.6	912.9	913.5	913.0	912.1	911.2	910.2	909.3	907.4	905.5
157.5°	924.5	925.8	927.1	927.7	927.1	926.0	924.9	923.8	922.7	921.3	919.9
160°	936.2	937.3	938.4	938.9	938.4	937.5	936.6	935.6	934.7	933.8	932.8
162.5°	946.7	948.1	949.5	950.2	949.7	948.6	947.5	946.4	945.3	944.5	943.7
165°	956.0	957.1	958.2	958.7	958.2	957.1	956.0	954.9	953.8	953.3	952.9
167.5°	962.9	964.4	965.8	966.5	965.9	964.8	963.7	962.6	961.5	961.0	960.6
170°	968.6	970.0	971.4	972.1	971.6	970.5	969.4	968.3	967.2	966.9	966.6
172.5°	972.8	974.3	975.7	976.4	975.8	974.7	973.6	972.5	971.4	971.1	970.8
175°	975.3	976.8	978.4	979.2	978.6	977.5	976.4	975.3	974.2	973.9	973.6
177.5°	976.3	977.8	979.2	979.9	979.4	978.3	977.2	976.1	975.0	974.8	974.6
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1358.1	1353.0	1349.9	1352.0	1345.9	1330.6	1330.6	1335.7	1329.6	1323.5	1314.3
5°	1395.7	1385.5	1379.4	1378.4	1364.2	1339.8	1334.7	1329.6	1316.4	1302.1	1286.9
7.5°	1432.3	1414.0	1403.8	1396.7	1376.4	1344.8	1331.6	1320.4	1299.1	1277.7	1258.4
10°	1462.8	1436.4	1424.2	1413.0	1386.6	1346.9	1325.5	1305.2	1277.7	1250.2	1225.8
12.5°	1487.3	1456.7	1441.5	1425.2	1392.7	1340.8	1314.3	1281.8	1254.3	1217.7	1193.3
15°	1528.0	1464.9	1450.6	1435.4	1401.8	1330.6	1298.0	1261.4	1223.8	1175.0	1148.5
17.5°	1560.5	1476.1	1475.1	1442.5	1398.8	1326.5	1276.7	1228.9	1188.2	1139.4	1097.6
20°	1579.8	1493.4	1477.1	1443.5	1388.6	1299.1	1247.2	1194.3	1150.5	1091.5	1049.8
22.5°	1596.1	1517.8	1475.1	1434.4	1367.2	1289.9	1213.6	1163.8	1103.7	1039.7	1000.0
25°	1602.2	1522.9	1478.1	1431.3	1352.0	1263.5	1177.0	1123.1	1055.9	998.0	944.0
27.5°	1603.2	1521.8	1466.9	1418.1	1330.6	1228.9	1140.4	1083.4	1009.1	942.0	888.1
30°	1593.1	1510.7	1460.8	1407.9	1310.3	1197.3	1095.6	1032.5	953.2	886.1	830.1
32.5°	1562.5	1488.3	1447.6	1389.6	1283.8	1153.6	1052.9	982.7	899.3	833.2	779.2
35°	1511.7	1460.8	1416.1	1362.1	1249.2	1112.9	1010.2	927.8	843.3	780.3	729.4
37.5°	1448.6	1421.1	1379.4	1326.5	1209.5	1076.3	962.3	870.8	786.4	725.3	675.5
40°	1363.2	1370.3	1329.6	1281.8	1162.7	1026.4	900.3	812.8	733.5	676.5	627.7
42.5°	1270.6	1300.1	1276.7	1230.9	1110.9	971.5	854.5	757.9	680.6	621.6	580.9
45°	1170.9	1221.8	1207.5	1173.9	1057.0	913.5	789.4	695.8	627.7	570.7	535.1
47.5°	1062.0	1134.3	1134.3	1109.9	996.9	855.5	733.5	637.8	570.7	530.0	495.4
50°	951.2	1032.5	1045.8	1029.5	929.8	789.4	665.3	578.8	520.8	481.2	455.7
52.5°	835.2	929.8	954.2	946.1	858.6	726.3	609.4	524.9	472.0	437.4	415.0
55°	724.3	834.2	860.6	863.7	782.3	657.2	547.3	473.0	422.2	398.8	379.4
57.5°	619.5	725.3	754.8	759.9	705.0	594.1	489.3	424.2	378.4	359.1	343.8
60°	530.0	618.5	657.2	668.4	620.5	520.8	435.4	372.3	337.7	319.4	305.2
62.5°	456.8	528.0	568.7	571.7	550.3	456.8	379.4	326.5	297.0	280.8	273.6
65°	385.5	449.6	474.1	486.3	469.0	395.7	327.6	283.8	260.4	246.2	239.1
67.5°	328.6	369.3	389.6	405.9	388.6	333.7	278.7	243.1	225.8	211.6	207.5
70°	269.6	303.1	318.4	334.7	319.4	277.7	238.0	205.5	190.2	179.0	174.0
72.5°	215.7	242.1	256.4	266.5	257.4	222.8	190.2	167.9	156.7	148.5	145.5
75°	170.9	189.2	197.4	204.5	200.4	174.0	153.6	135.3	125.1	118.0	116.0
77.5°	130.2	143.4	152.6	154.6	149.5	132.2	115.0	103.8	95.6	91.6	89.5
80°	92.6	100.7	105.8	108.8	103.8	96.6	84.4	76.3	69.2	64.1	63.1
82.5°	62.1	66.1	70.2	69.2	67.1	61.0	53.9	49.8	46.8	42.7	42.7
85°	35.6	36.6	38.7	39.7	38.7	34.6	30.5	28.5	26.4	23.4	23.4
87.5°	15.3	16.3	16.3	17.3	15.3	15.3	13.2	11.2	11.2	10.2	9.2
90°	10.4	9.1	8.5	7.6	5.9	4.2	2.4	0.7	2.4	4.2	5.9
92.5°	15.5	15.0	14.8	15.1	15.7	16.4	17.0	17.6	17.0	16.4	15.7
95°	24.2	23.1	22.6	25.2	30.4	35.5	40.7	45.9	40.7	35.5	30.4
97.5°	28.5	26.0	24.7	31.1	44.0	56.9	69.7	82.6	69.7	56.9	44.0
100°	32.2	29.5	28.2	39.0	60.5	82.0	103.5	125.0	103.5	82.0	60.5
102.5°	127.3	155.8	170.1	170.3	170.6	170.9	171.3	171.6	171.3	170.9	170.6
105°	171.6	214.4	235.8	233.4	228.7	224.0	219.3	214.6	219.3	224.0	228.7
107.5°	203.1	256.0	282.4	280.4	276.5	272.6	268.6	264.7	268.6	272.6	276.5
110°	259.6	304.9	327.6	325.9	322.6	319.3	316.0	312.7	316.0	319.3	322.6

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	366.6	369.3	370.6	369.2	366.4	363.5	360.7	357.9	360.7	363.5	366.4
115°	423.8	419.9	417.9	416.6	413.9	411.2	408.6	405.9	408.6	411.2	413.9
117.5°	465.7	463.0	461.7	460.1	457.0	453.9	450.7	447.6	450.7	453.9	457.0
120°	509.0	506.2	504.8	503.6	501.3	498.9	496.6	494.2	496.6	498.9	501.3
122.5°	549.7	546.6	545.0	543.7	541.2	538.7	536.2	533.7	536.2	538.7	541.2
125°	587.6	584.6	583.1	582.1	580.1	578.0	576.0	574.0	576.0	578.0	580.1
127.5°	624.1	621.8	620.6	619.5	617.3	615.1	612.9	610.7	612.9	615.1	617.3
130°	659.2	657.5	656.6	655.3	652.8	650.3	647.8	645.3	647.8	650.3	652.8
132.5°	692.3	690.6	689.7	688.7	686.7	684.6	682.6	680.6	682.6	684.6	686.7
135°	723.6	722.2	721.5	720.2	717.7	715.2	712.7	710.2	712.7	715.2	717.7
137.5°	752.1	750.5	749.7	748.8	746.9	745.0	743.2	741.3	743.2	745.0	746.9
140°	779.9	778.2	777.3	776.7	775.4	774.1	772.9	771.6	772.9	774.1	775.4
142.5°	805.1	803.0	802.0	801.4	800.3	799.2	798.1	797.0	798.1	799.2	800.3
145°	827.2	824.5	823.2	823.3	823.4	823.6	823.7	823.9	823.7	823.6	823.4
147.5°	849.1	846.4	845.1	845.3	845.8	846.3	846.7	847.2	846.7	846.3	845.8
150°	868.6	866.1	864.8	865.4	866.5	867.6	868.7	869.8	868.7	867.6	866.5
152.5°	886.7	884.4	883.2	883.8	885.1	886.3	887.6	888.8	887.6	886.3	885.1
155°	903.6	901.7	900.8	901.5	902.9	904.4	905.8	907.2	905.8	904.4	902.9
157.5°	918.5	917.1	916.4	917.0	918.3	919.5	920.8	922.0	920.8	919.5	918.3
160°	931.9	931.0	930.5	931.0	931.9	932.8	933.8	934.7	933.8	932.8	931.9
162.5°	943.0	942.2	941.8	942.3	943.2	944.1	945.1	946.0	945.1	944.1	943.2
165°	952.4	951.9	951.7	952.2	953.1	954.0	955.0	955.9	955.0	954.0	953.1
167.5°	960.1	959.6	959.4	959.9	960.8	961.8	962.7	963.7	962.7	961.8	960.8
170°	966.3	966.0	965.8	966.3	967.2	968.1	969.1	970.0	969.1	968.1	967.2
172.5°	970.5	970.2	970.0	970.5	971.4	972.3	973.3	974.2	973.3	972.3	971.4
175°	973.3	973.0	972.8	973.4	974.5	975.6	976.7	977.8	976.7	975.6	974.5
177.5°	974.5	974.3	974.2	974.8	975.9	977.0	978.1	979.2	978.1	977.0	975.9
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1309.2	1314.3	1313.3	1303.1	1291.9	1282.8	1265.5	1267.5	1261.4	1262.4	1268.5
5°	1276.7	1276.7	1272.6	1258.4	1240.1	1229.9	1210.6	1205.5	1193.3	1192.3	1191.2
7.5°	1242.1	1237.0	1231.9	1211.6	1189.2	1172.9	1146.5	1140.4	1128.2	1120.0	1116.0
10°	1201.4	1194.3	1184.1	1160.7	1133.2	1112.9	1085.4	1077.3	1053.9	1043.7	1037.6
12.5°	1156.6	1152.6	1136.3	1117.0	1072.2	1049.8	1010.2	1018.3	994.9	974.6	971.5
15°	1111.9	1096.6	1087.5	1055.9	1002.0	991.8	960.3	944.0	922.7	906.4	906.4
17.5°	1068.1	1044.7	1024.4	990.8	951.2	922.7	899.3	891.1	864.7	848.4	845.4
20°	1010.2	983.7	978.6	930.8	903.3	871.8	849.4	829.1	809.8	802.6	797.5
22.5°	955.2	924.7	916.6	875.9	848.4	816.9	794.5	780.3	766.0	760.9	751.8
25°	896.2	877.9	865.7	822.0	791.4	761.9	746.7	736.5	723.3	722.3	716.2
27.5°	839.3	822.0	809.8	768.0	745.7	718.2	706.0	694.8	687.7	684.6	681.6
30°	790.4	771.1	756.9	726.3	698.9	676.5	666.3	659.2	655.1	650.0	649.0
32.5°	736.5	725.3	706.0	682.6	661.2	639.9	633.8	628.7	622.6	620.5	619.5
35°	690.7	675.5	663.3	636.8	627.7	609.4	602.2	598.2	590.0	588.0	586.0
37.5°	646.0	631.7	618.5	602.2	584.9	574.8	570.7	564.6	560.5	561.5	559.5
40°	601.2	590.0	579.8	562.6	552.4	547.3	539.2	533.1	531.0	532.0	531.0
42.5°	557.5	547.3	541.2	528.0	517.8	512.7	507.6	501.5	504.6	504.6	507.6
45°	517.8	508.6	504.6	494.4	488.3	480.2	475.1	474.1	478.1	477.1	477.1
47.5°	477.1	474.1	469.0	459.8	451.7	446.6	445.6	445.6	449.6	451.7	450.7
50°	445.6	439.5	433.4	426.2	420.1	418.1	415.0	417.1	421.2	421.2	423.2
52.5°	405.9	401.8	399.8	393.7	389.6	389.6	389.6	390.6	393.7	396.7	395.7
55°	371.3	368.3	366.2	363.2	358.1	359.1	358.1	360.1	363.2	366.2	368.3
57.5°	334.7	333.7	331.6	326.5	326.5	325.5	328.6	329.6	334.7	336.7	339.8
60°	302.1	299.1	299.1	295.0	295.0	295.0	298.1	301.1	305.2	306.2	308.2
62.5°	267.5	267.5	266.5	263.5	263.5	266.5	267.5	271.6	273.6	273.6	276.7
65°	235.0	234.0	233.0	234.0	235.0	235.0	238.0	240.1	242.1	243.1	244.1
67.5°	202.4	201.4	203.5	202.4	204.5	208.5	207.5	210.6	213.6	213.6	214.6
70°	171.9	174.0	172.9	175.0	174.0	176.0	179.0	180.1	180.1	181.1	184.1
72.5°	143.4	143.4	143.4	142.4	143.4	145.5	147.5	148.5	150.6	151.6	154.6
75°	116.0	116.0	113.9	116.0	116.0	118.0	120.0	120.0	120.0	122.1	125.1
77.5°	87.5	88.5	87.5	89.5	89.5	90.5	92.6	91.6	93.6	94.6	95.6
80°	64.1	63.1	63.1	63.1	64.1	64.1	66.1	67.1	67.1	70.2	68.2
82.5°	40.7	41.7	40.7	41.7	41.7	42.7	41.7	42.7	43.7	45.8	44.8
85°	23.4	22.4	22.4	23.4	22.4	22.4	23.4	22.4	23.4	22.4	23.4
87.5°	9.2	8.1	8.1	8.1	8.1	7.1	7.1	6.1	6.1	6.1	5.1
90°	7.6	8.5	9.1	10.4	11.6	12.9	14.1	14.9	15.7	16.4	17.2
92.5°	15.1	14.8	15.0	15.5	16.0	16.4	16.9	17.2	17.6	17.9	18.2
95°	25.2	22.6	23.1	24.2	25.3	26.4	27.5	28.3	29.1	29.9	30.7
97.5°	31.1	24.7	26.0	28.5	31.0	33.5	36.0	36.5	36.9	37.4	37.9
100°	39.0	28.2	29.5	32.2	34.9	37.5	40.2	41.5	42.7	44.0	45.3
102.5°	170.3	170.1	155.8	127.3	98.8	70.2	41.7	43.4	45.1	46.8	48.5
105°	233.4	235.8	214.4	171.6	128.7	85.9	43.1	44.8	46.5	48.2	49.9
107.5°	280.4	282.4	256.0	203.1	150.2	97.4	44.5	46.2	47.9	49.6	51.3
110°	325.9	327.6	304.9	259.6	214.2	168.9	123.5	107.8	92.1	76.4	60.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	369.2	370.6	369.3	366.6	363.9	361.3	358.6	291.0	223.4	155.8	88.2
115°	416.6	417.9	419.9	423.8	427.7	431.7	435.6	363.0	290.3	217.7	145.0
117.5°	460.1	461.7	463.0	465.7	468.4	471.0	473.7	451.3	428.9	406.4	384.0
120°	503.6	504.8	506.2	509.0	511.9	514.7	517.5	519.4	521.3	523.2	525.1
122.5°	543.7	545.0	546.6	549.7	552.8	556.0	559.1	560.1	561.0	562.0	562.9
125°	582.1	583.1	584.6	587.6	590.5	593.5	596.5	597.6	598.7	599.8	600.9
127.5°	619.5	620.6	621.8	624.1	626.4	628.8	631.1	632.7	634.3	635.8	637.4
130°	655.3	656.6	657.5	659.2	660.9	662.6	664.3	666.0	667.8	669.5	671.2
132.5°	688.7	689.7	690.6	692.3	694.0	695.8	697.5	698.9	700.3	701.8	703.2
135°	720.2	721.5	722.2	723.6	725.1	726.5	727.9	729.5	731.0	732.6	734.1
137.5°	748.8	749.7	750.5	752.1	753.6	755.2	756.8	758.4	760.0	761.5	763.1
140°	776.7	777.3	778.2	779.9	781.6	783.3	785.0	786.4	787.8	789.3	790.7
142.5°	801.4	802.0	803.0	805.1	807.1	809.2	811.2	812.4	813.7	814.9	816.2
145°	823.3	823.2	824.5	827.2	829.9	832.5	835.2	836.3	837.4	838.5	839.6
147.5°	845.3	845.1	846.4	849.1	851.8	854.4	857.1	857.9	858.7	859.4	860.2
150°	865.4	864.8	866.1	868.6	871.1	873.6	876.1	877.1	878.0	879.0	879.9
152.5°	883.8	883.2	884.4	886.7	889.1	891.4	893.8	894.7	895.7	896.6	897.5
155°	901.5	900.8	901.7	903.6	905.5	907.4	909.3	910.2	911.2	912.1	913.0
157.5°	917.0	916.4	917.1	918.5	919.9	921.3	922.7	923.8	924.9	926.0	927.1
160°	931.0	930.5	931.0	931.9	932.8	933.8	934.7	935.6	936.6	937.5	938.4
162.5°	942.3	941.8	942.2	943.0	943.7	944.5	945.3	946.4	947.5	948.6	949.7
165°	952.2	951.7	951.9	952.4	952.9	953.3	953.8	954.9	956.0	957.1	958.2
167.5°	959.9	959.4	959.6	960.1	960.6	961.0	961.5	962.6	963.7	964.8	965.9
170°	966.3	965.8	966.0	966.3	966.6	966.9	967.2	968.3	969.4	970.5	971.6
172.5°	970.5	970.0	970.2	970.5	970.8	971.1	971.4	972.5	973.6	974.7	975.8
175°	973.4	972.8	973.0	973.3	973.6	973.9	974.2	975.3	976.4	977.5	978.6
177.5°	974.8	974.2	974.3	974.5	974.6	974.8	975.0	976.1	977.2	978.3	979.4
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1261.4	1264.5	1257.4	1255.3	1257.4	1250.2	1252.3	1254.3	1254.3	1257.4	1259.4
5°	1188.2	1184.1	1177.0	1175.0	1172.9	1176.0	1173.9	1177.0	1178.0	1185.1	1186.1
7.5°	1116.0	1109.9	1103.7	1097.6	1095.6	1090.5	1095.6	1095.6	1102.7	1100.7	1105.8
10°	1030.5	1029.5	1021.3	1018.3	1014.2	1006.1	1017.3	1014.2	1019.3	1028.5	1030.5
12.5°	967.4	956.2	961.3	947.1	952.2	944.0	945.1	945.1	953.2	954.2	952.2
15°	907.4	898.3	885.0	878.9	875.9	871.8	885.0	886.1	879.9	894.2	889.1
17.5°	846.4	846.4	834.2	831.1	823.0	827.0	825.0	826.0	824.0	834.2	839.3
20°	793.5	788.4	784.3	785.3	775.2	773.1	771.1	773.1	780.3	787.4	789.4
22.5°	750.8	747.7	737.5	739.6	731.4	734.5	732.4	737.5	738.5	738.5	745.7
25°	710.1	706.0	707.0	702.9	699.9	699.9	696.8	699.9	704.0	706.0	707.0
27.5°	679.5	676.5	671.4	668.4	670.4	665.3	669.4	672.4	672.4	670.4	672.4
30°	642.9	645.0	645.0	634.8	638.9	636.8	639.9	641.9	641.9	642.9	640.9
32.5°	618.5	612.4	611.4	610.4	610.4	606.3	606.3	609.4	610.4	611.4	614.4
35°	586.0	586.0	580.9	583.9	579.8	580.9	579.8	580.9	582.9	579.8	582.9
37.5°	556.5	557.5	555.4	557.5	558.5	556.5	554.4	558.5	556.5	556.5	554.4
40°	531.0	530.0	531.0	531.0	531.0	532.0	530.0	530.0	530.0	528.0	525.9
42.5°	509.7	503.6	505.6	506.6	503.6	503.6	504.6	503.6	506.6	500.5	500.5
45°	479.1	477.1	478.1	478.1	480.2	477.1	479.1	480.2	477.1	476.1	474.1
47.5°	451.7	453.7	451.7	453.7	453.7	455.7	451.7	452.7	453.7	449.6	446.6
50°	424.2	424.2	427.3	426.2	427.3	425.2	425.2	424.2	425.2	423.2	420.1
52.5°	398.8	395.7	400.8	399.8	398.8	397.8	396.7	397.8	395.7	393.7	393.7
55°	367.2	367.2	370.3	371.3	371.3	369.3	367.2	368.3	367.2	366.2	365.2
57.5°	341.8	337.7	339.8	340.8	340.8	337.7	339.8	337.7	337.7	338.8	335.7
60°	309.3	309.3	307.2	310.3	310.3	308.2	308.2	309.3	307.2	306.2	305.2
62.5°	274.7	275.7	278.7	279.8	280.8	278.7	276.7	277.7	277.7	274.7	275.7
65°	245.2	247.2	251.3	250.3	248.2	249.2	247.2	248.2	245.2	246.2	243.1
67.5°	216.7	215.7	216.7	216.7	218.7	217.7	215.7	215.7	214.6	217.7	214.6
70°	186.2	186.2	186.2	186.2	187.2	188.2	186.2	184.1	185.1	183.1	182.1
72.5°	154.6	155.6	154.6	156.7	153.6	155.6	155.6	154.6	153.6	153.6	153.6
75°	125.1	127.2	124.1	125.1	124.1	126.1	125.1	125.1	123.1	122.1	123.1
77.5°	95.6	96.6	94.6	95.6	94.6	95.6	95.6	94.6	94.6	94.6	94.6
80°	68.2	69.2	68.2	67.1	66.1	68.2	66.1	67.1	68.2	67.1	69.2
82.5°	43.7	43.7	42.7	43.7	41.7	41.7	42.7	42.7	41.7	43.7	41.7
85°	21.4	21.4	23.4	21.4	20.3	20.3	20.3	21.4	20.3	22.4	21.4
87.5°	5.1	4.1	5.1	5.1	4.1	4.1	5.1	4.1	5.1	6.1	4.1
90°	17.6	17.8	18.1	18.4	18.8	19.1	18.8	18.4	18.1	17.8	17.6
92.5°	18.4	18.5	18.6	18.8	18.9	19.1	18.9	18.8	18.6	18.5	18.4
95°	31.1	31.0	30.9	30.7	30.6	30.4	30.6	30.7	30.9	31.0	31.1
97.5°	38.1	38.2	38.3	38.5	38.6	38.8	38.6	38.5	38.3	38.2	38.1
100°	45.9	46.1	46.4	46.7	47.0	47.3	47.0	46.7	46.4	46.1	45.9
102.5°	49.4	49.6	50.1	50.6	51.0	51.5	51.0	50.6	50.1	49.6	49.4
105°	50.8	51.1	51.8	52.4	53.1	53.7	53.1	52.4	51.8	51.1	50.8
107.5°	52.2	52.5	53.2	53.8	54.5	55.1	54.5	53.8	53.2	52.5	52.2
110°	52.9	53.2	53.9	54.5	55.2	55.8	55.2	54.5	53.9	53.2	52.9

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	54.4	54.6	55.1	55.6	56.0	56.5	56.0	55.6	55.1	54.6	54.4
115°	108.7	103.1	91.8	80.5	69.2	57.9	69.2	80.5	91.8	103.1	108.7
117.5°	372.8	352.2	311.1	270.0	228.9	187.8	228.9	270.0	311.1	352.2	372.8
120°	526.0	515.4	494.2	473.0	451.8	430.6	451.8	473.0	494.2	515.4	526.0
122.5°	563.4	563.5	563.6	563.8	563.9	564.1	563.9	563.8	563.6	563.5	563.4
125°	601.5	601.7	602.2	602.7	603.1	603.6	603.1	602.7	602.2	601.7	601.5
127.5°	638.2	638.3	638.4	638.6	638.7	638.9	638.7	638.6	638.4	638.3	638.2
130°	672.1	672.0	671.9	671.7	671.6	671.4	671.6	671.7	671.9	672.0	672.1
132.5°	703.9	703.8	703.7	703.5	703.4	703.2	703.4	703.5	703.7	703.8	703.9
135°	734.9	734.7	734.4	734.1	733.8	733.5	733.8	734.1	734.4	734.7	734.9
137.5°	763.9	763.7	763.2	762.7	762.2	761.7	762.2	762.7	763.2	763.7	763.9
140°	791.4	791.0	790.2	789.5	788.7	787.9	788.7	789.5	790.2	791.0	791.4
142.5°	816.8	816.4	815.6	814.9	814.1	813.3	814.1	814.9	815.6	816.4	816.8
145°	840.1	839.7	838.9	838.2	837.4	836.6	837.4	838.2	838.9	839.7	840.1
147.5°	860.6	860.3	859.7	859.0	858.4	857.8	858.4	859.0	859.7	860.3	860.6
150°	880.4	880.0	879.2	878.4	877.6	876.8	877.6	878.4	879.2	880.0	880.4
152.5°	898.0	897.5	896.4	895.3	894.2	893.1	894.2	895.3	896.4	897.5	898.0
155°	913.5	912.9	911.6	910.4	909.1	907.9	909.1	910.4	911.6	912.9	913.5
157.5°	927.7	927.1	925.8	924.5	923.3	922.0	923.3	924.5	925.8	927.1	927.7
160°	938.9	938.4	937.3	936.2	935.1	934.0	935.1	936.2	937.3	938.4	938.9
162.5°	950.2	949.5	948.1	946.7	945.3	943.9	945.3	946.7	948.1	949.5	950.2
165°	958.7	958.2	957.1	956.0	954.9	953.8	954.9	956.0	957.1	958.2	958.7
167.5°	966.5	965.8	964.4	962.9	961.5	960.1	961.5	962.9	964.4	965.8	966.5
170°	972.1	971.4	970.0	968.6	967.2	965.8	967.2	968.6	970.0	971.4	972.1
172.5°	976.4	975.7	974.3	972.8	971.4	970.0	971.4	972.8	974.3	975.7	976.4
175°	979.2	978.4	976.8	975.3	973.7	972.1	973.7	975.3	976.8	978.4	979.2
177.5°	979.9	979.2	977.8	976.3	974.9	973.5	974.9	976.3	977.8	979.2	979.9
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5	1323.5
2.5°	1256.3	1264.5	1261.4	1250.2	1263.5	1263.5	1272.6	1272.6	1283.8	1287.9	1294.0
5°	1185.1	1191.2	1196.3	1191.2	1200.4	1214.6	1222.8	1229.9	1245.1	1251.3	1260.4
7.5°	1108.8	1120.0	1125.1	1125.1	1140.4	1156.6	1172.9	1183.1	1204.5	1212.6	1221.8
10°	1034.6	1047.8	1058.0	1057.0	1082.4	1092.6	1112.9	1136.3	1157.7	1169.9	1183.1
12.5°	956.2	963.4	977.6	998.0	1004.1	1022.4	1045.8	1075.3	1113.9	1125.1	1144.4
15°	891.1	910.5	921.7	930.8	945.1	962.3	987.8	1016.3	1054.9	1079.3	1099.7
17.5°	836.2	861.6	868.8	866.7	885.0	911.5	941.0	962.3	996.9	1026.4	1045.8
20°	791.4	801.6	813.8	818.9	833.2	861.6	890.1	914.5	943.0	966.4	988.8
22.5°	746.7	754.8	765.0	774.1	785.3	801.6	829.1	859.6	887.1	909.4	934.9
25°	710.1	715.1	724.3	731.4	743.6	754.8	774.1	807.7	840.3	853.5	875.9
27.5°	674.5	678.5	684.6	692.8	698.9	710.1	727.4	754.8	788.4	801.6	832.1
30°	642.9	646.0	652.1	656.1	659.2	672.4	685.6	707.0	732.4	750.8	773.1
32.5°	613.4	616.5	622.6	623.6	627.7	634.8	647.0	666.3	688.7	704.0	723.3
35°	580.9	582.9	589.0	591.0	594.1	600.2	609.4	623.6	643.9	655.1	672.4
37.5°	555.4	554.4	558.5	561.5	565.6	568.7	571.7	586.0	601.2	611.4	624.6
40°	528.0	525.9	527.0	531.0	533.1	537.1	537.1	551.4	561.5	569.7	579.8
42.5°	500.5	499.5	497.4	499.5	501.5	502.5	503.6	513.7	523.9	531.0	542.2
45°	473.0	472.0	470.0	471.0	471.0	473.0	476.1	480.2	487.3	493.4	499.5
47.5°	447.6	445.6	442.5	441.5	443.5	443.5	443.5	447.6	454.7	456.8	462.9
50°	421.2	418.1	414.0	412.0	412.0	411.0	413.0	414.0	420.1	422.2	427.3
52.5°	392.7	390.6	386.6	382.5	383.5	381.5	382.5	383.5	385.5	388.6	391.7
55°	364.2	360.1	357.1	356.0	353.0	353.0	349.9	354.0	353.0	354.0	358.1
57.5°	336.7	332.7	327.6	325.5	322.5	321.5	319.4	318.4	319.4	322.5	325.5
60°	304.2	302.1	299.1	296.0	294.0	290.9	288.9	288.9	287.9	287.9	288.9
62.5°	272.6	271.6	267.5	266.5	264.5	262.5	259.4	257.4	257.4	259.4	260.4
65°	242.1	241.1	238.0	237.0	231.9	229.9	228.9	227.9	225.8	225.8	225.8
67.5°	213.6	210.6	210.6	205.5	201.4	199.4	197.4	196.3	196.3	196.3	197.4
70°	182.1	182.1	179.0	176.0	171.9	172.9	169.9	166.8	166.8	164.8	165.8
72.5°	151.6	150.6	147.5	146.5	143.4	140.4	138.3	140.4	137.3	136.3	137.3
75°	122.1	121.1	119.0	117.0	118.0	115.0	111.9	110.9	110.9	108.8	108.8
77.5°	93.6	95.6	91.6	90.5	88.5	86.5	85.5	84.4	84.4	84.4	86.5
80°	65.1	66.1	66.1	64.1	65.1	62.1	62.1	62.1	59.0	60.0	61.0
82.5°	41.7	41.7	40.7	41.7	40.7	40.7	39.7	39.7	38.7	38.7	39.7
85°	23.4	22.4	21.4	23.4	22.4	22.4	21.4	21.4	21.4	21.4	21.4
87.5°	5.1	6.1	6.1	6.1	6.1	7.1	7.1	7.1	8.1	8.1	8.1
90°	17.2	16.4	15.7	14.9	14.1	12.9	11.6	10.4	9.1	8.5	7.6
92.5°	18.2	17.9	17.6	17.2	16.9	16.4	16.0	15.5	15.0	14.8	15.1
95°	30.7	29.9	29.1	28.3	27.5	26.4	25.3	24.2	23.1	22.6	25.2
97.5°	37.9	37.4	36.9	36.5	36.0	33.5	31.0	28.5	26.0	24.7	31.1
100°	45.3	44.0	42.7	41.5	40.2	37.5	34.9	32.2	29.5	28.2	39.0
102.5°	48.5	46.8	45.1	43.4	41.7	70.2	98.8	127.3	155.8	170.1	170.3
105°	49.9	48.2	46.5	44.8	43.1	85.9	128.7	171.6	214.4	235.8	233.4
107.5°	51.3	49.6	47.9	46.2	44.5	97.4	150.2	203.1	256.0	282.4	280.4
110°	60.7	76.4	92.1	107.8	123.5	168.9	214.2	259.6	304.9	327.6	325.9

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	88.2	155.8	223.4	291.0	358.6	361.3	363.9	366.6	369.3	370.6	369.2
115°	145.0	217.7	290.3	363.0	435.6	431.7	427.7	423.8	419.9	417.9	416.6
117.5°	384.0	406.4	428.9	451.3	473.7	471.0	468.4	465.7	463.0	461.7	460.1
120°	525.1	523.2	521.3	519.4	517.5	514.7	511.9	509.0	506.2	504.8	503.6
122.5°	562.9	562.0	561.0	560.1	559.1	556.0	552.8	549.7	546.6	545.0	543.7
125°	600.9	599.8	598.7	597.6	596.5	593.5	590.5	587.6	584.6	583.1	582.1
127.5°	637.4	635.8	634.3	632.7	631.1	628.8	626.4	624.1	621.8	620.6	619.5
130°	671.2	669.5	667.8	666.0	664.3	662.6	660.9	659.2	657.5	656.6	655.3
132.5°	703.2	701.8	700.3	698.9	697.5	695.8	694.0	692.3	690.6	689.7	688.7
135°	734.1	732.6	731.0	729.5	727.9	726.5	725.1	723.6	722.2	721.5	720.2
137.5°	763.1	761.5	760.0	758.4	756.8	755.2	753.6	752.1	750.5	749.7	748.8
140°	790.7	789.3	787.8	786.4	785.0	783.3	781.6	779.9	778.2	777.3	776.7
142.5°	816.2	814.9	813.7	812.4	811.2	809.2	807.1	805.1	803.0	802.0	801.4
145°	839.6	838.5	837.4	836.3	835.2	832.5	829.9	827.2	824.5	823.2	823.3
147.5°	860.2	859.4	858.7	857.9	857.1	854.4	851.8	849.1	846.4	845.1	845.3
150°	879.9	879.0	878.0	877.1	876.1	873.6	871.1	868.6	866.1	864.8	865.4
152.5°	897.5	896.6	895.7	894.7	893.8	891.4	889.1	886.7	884.4	883.2	883.8
155°	913.0	912.1	911.2	910.2	909.3	907.4	905.5	903.6	901.7	900.8	901.5
157.5°	927.1	926.0	924.9	923.8	922.7	921.3	919.9	918.5	917.1	916.4	917.0
160°	938.4	937.5	936.6	935.6	934.7	933.8	932.8	931.9	931.0	930.5	931.0
162.5°	949.7	948.6	947.5	946.4	945.3	944.5	943.7	943.0	942.2	941.8	942.3
165°	958.2	957.1	956.0	954.9	953.8	953.3	952.9	952.4	951.9	951.7	952.2
167.5°	965.9	964.8	963.7	962.6	961.5	961.0	960.6	960.1	959.6	959.4	959.9
170°	971.6	970.5	969.4	968.3	967.2	966.9	966.6	966.3	966.0	965.8	966.3
172.5°	975.8	974.7	973.6	972.5	971.4	971.1	970.8	970.5	970.2	970.0	970.5
175°	978.6	977.5	976.4	975.3	974.2	973.9	973.6	973.3	973.0	972.8	973.4
177.5°	979.4	978.3	977.2	976.1	975.0	974.8	974.6	974.5	974.3	974.2	974.8
180°	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1323.5	1323.5	1323.5	1323.5
2.5°	1299.1	1299.1	1314.3	1330.6
5°	1270.6	1277.7	1302.1	1324.5
7.5°	1243.1	1255.3	1285.8	1314.3
10°	1209.5	1225.8	1263.5	1297.0
12.5°	1177.0	1192.3	1236.0	1273.6
15°	1131.2	1150.5	1197.3	1244.1
17.5°	1085.4	1104.8	1161.7	1216.7
20°	1031.5	1057.0	1121.0	1194.3
22.5°	981.7	1013.2	1084.4	1143.4
25°	926.7	975.6	1041.7	1118.0
27.5°	877.9	926.7	993.9	1071.2
30°	823.0	872.8	942.0	1013.2
32.5°	770.1	815.9	883.0	970.5
35°	715.1	758.9	824.0	912.5
37.5°	665.3	708.0	779.2	860.6
40°	616.5	661.2	722.3	803.7
42.5°	570.7	610.4	665.3	746.7
45°	529.0	557.5	608.3	684.6
47.5°	485.2	510.7	557.5	633.8
50°	444.6	465.9	506.6	577.8
52.5°	404.9	423.2	460.8	517.8
55°	369.3	386.6	414.0	470.0
57.5°	332.7	345.9	372.3	417.1
60°	297.0	309.3	330.6	367.2
62.5°	261.4	271.6	292.0	321.5
65°	229.9	238.0	253.3	278.7
67.5°	199.4	204.5	216.7	237.0
70°	169.9	174.0	184.1	200.4
72.5°	138.3	142.4	153.6	164.8
75°	111.9	112.9	121.1	130.2
77.5°	87.5	86.5	92.6	99.7
80°	60.0	63.1	68.2	71.2
82.5°	40.7	41.7	43.7	45.8
85°	22.4	23.4	23.4	26.4
87.5°	9.2	10.2	10.2	11.2
90°	5.9	4.2	2.4	0.7
92.5°	15.7	16.4	17.0	17.6
95°	30.4	35.5	40.7	45.9
97.5°	44.0	56.9	69.7	82.6
100°	60.5	82.0	103.5	125.0
102.5°	170.6	170.9	171.3	171.6
105°	228.7	224.0	219.3	214.6
107.5°	276.5	272.6	268.6	264.7
110°	322.6	319.3	316.0	312.7

TEST NUMBER: P1029690

CATALOG NUMBER: S122DIW-B675D710UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	366.4	363.5	360.7	357.9
115°	413.9	411.2	408.6	405.9
117.5°	457.0	453.9	450.7	447.6
120°	501.3	498.9	496.6	494.2
122.5°	541.2	538.7	536.2	533.7
125°	580.1	578.0	576.0	574.0
127.5°	617.3	615.1	612.9	610.7
130°	652.8	650.3	647.8	645.3
132.5°	686.7	684.6	682.6	680.6
135°	717.7	715.2	712.7	710.2
137.5°	746.9	745.0	743.2	741.3
140°	775.4	774.1	772.9	771.6
142.5°	800.3	799.2	798.1	797.0
145°	823.4	823.6	823.7	823.9
147.5°	845.8	846.3	846.7	847.2
150°	866.5	867.6	868.7	869.8
152.5°	885.1	886.3	887.6	888.8
155°	902.9	904.4	905.8	907.2
157.5°	918.3	919.5	920.8	922.0
160°	931.9	932.8	933.8	934.7
162.5°	943.2	944.1	945.1	946.0
165°	953.1	954.0	955.0	955.9
167.5°	960.8	961.8	962.7	963.7
170°	967.2	968.1	969.1	970.0
172.5°	971.4	972.3	973.3	974.2
175°	974.5	975.6	976.7	977.8
177.5°	975.9	977.0	978.1	979.2
180°	975.7	975.7	975.7	975.7

(END OF REPORT)