

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030762

Luminaire Tested: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030762
REPORT IS A COMBINATION OF REPORTS P991060 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6801.0 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	69	67	66
2	94	87	81	75	89	83	77	72	75	70	67	68	64	61	61	58	56
3	86	77	69	63	82	73	66	61	66	61	57	60	56	52	54	51	48
4	79	68	60	54	75	65	58	52	59	53	49	54	49	45	49	45	42
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36
6	67	55	47	41	64	53	45	39	48	42	37	44	39	35	40	36	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	37	32	29
8	58	45	37	32	55	44	36	31	40	34	29	37	31	28	34	29	26
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17575	17575	17575	17575
5°	17587	20250	17637	15114
10°	17475	24505	17493	13197
15°	17233	29061	17374	11880
20°	17026	33460	17061	10932
25°	16716	34302	16754	10436
30°	16496	28340	16496	10112
35°	16223	18954	16121	9826
40°	15896	13682	15699	9387
45°	15484	10838	15038	8842
50°	14485	9203	13970	8306
55°	13388	8088	12843	7710
60°	12275	7043	11621	7082
65°	11052	6029	10518	6247
70°	9786	5005	9132	5266
75°	8365	3774	7825	4066
80°	6612	2520	6097	2670
85°	4563	1157	3650	1053

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 28344 cd/sqm

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.6	2.4
10°-20°	515.8	7.6
20°-30°	867.8	12.8
30°-40°	980.7	14.4
40°-50°	878.4	12.9
50°-60°	709.1	10.4
60°-70°	494.1	7.3
70°-80°	259.3	3.8
80°-90°	63.4	0.9
90°-100°	21.7	0.3
100°-110°	104.7	1.5
110°-120°	256.5	3.8
120°-130°	325.6	4.8
130°-140°	347.9	5.1
140°-150°	325.3	4.8
150°-160°	262.4	3.9
160°-170°	169.3	2.5
170°-180°	58.4	0.9
0°-30°	1544.2	22.7
0°-40°	2524.9	37.1
0°-60°	4112.4	60.5
0°-90°	4929.2	72.5
90°-120°	382.9	5.6
90°-150°	1381.7	20.3
90°-180°	1872.0	27.5
0°-180°	6801.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1633	1633	1633	1633	1633	
5°	1631	1940	1636	1448	1631	155
15°	1557	2887	1570	1180	1557	440
25°	1424	3427	1427	1043	1424	657
35°	1256	1846	1248	957	1256	786
45°	1043	997	1013	813	1043	797
55°	739	677	709	646	739	662
65°	457	440	435	456	457	455
75°	220	226	206	244	220	236
85°	48	52	38	48	48	55
90°	0	14	0	14	0	5
95°	28	17	28	17	28	33
105°	136	20	136	20	136	144
115°	255	268	255	268	255	252
125°	359	367	359	367	359	321
135°	448	452	448	452	448	345
145°	516	521	516	521	516	323
155°	569	568	569	568	569	262
165°	600	598	600	598	600	169
175°	614	612	614	612	614	58
180°	614	614	614	614	614	

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1637.5	1650.2	1656.5	1666.0	1675.5	1689.7	1694.5	1702.4	1699.2	1705.6	1708.7
5°	1631.2	1653.4	1672.3	1696.1	1718.2	1734.0	1749.9	1775.2	1794.2	1797.3	1811.6
7.5°	1620.1	1651.8	1685.0	1718.2	1760.9	1786.3	1814.7	1849.5	1878.0	1923.9	1941.3
10°	1605.9	1650.2	1697.7	1743.5	1802.1	1841.6	1876.4	1935.0	1993.5	2041.0	2085.3
12.5°	1583.7	1639.1	1700.8	1768.8	1844.8	1890.7	1938.1	2015.7	2104.3	2177.0	2224.5
15°	1556.8	1626.5	1705.6	1778.3	1862.2	1947.6	1998.3	2085.3	2211.9	2279.9	2401.7
17.5°	1534.7	1605.9	1685.0	1798.9	1912.8	1998.3	2034.6	2194.4	2281.5	2395.4	2533.0
20°	1499.9	1590.1	1691.3	1805.2	1952.4	2004.6	2078.9	2240.3	2347.9	2496.6	2665.9
22.5°	1463.5	1560.0	1681.8	1800.5	1965.0	2020.4	2121.7	2249.8	2420.7	2567.8	2754.5
25°	1423.9	1528.4	1651.8	1792.6	1954.0	2034.6	2129.6	2287.8	2472.9	2658.0	2830.5
27.5°	1384.4	1498.3	1626.5	1767.3	1923.9	2018.8	2113.8	2278.3	2515.6	2716.6	2936.5
30°	1346.4	1460.3	1588.5	1732.5	1897.0	1988.8	2078.9	2284.6	2548.8	2775.1	2996.6
32.5°	1305.3	1422.4	1556.8	1677.1	1843.2	1941.3	2042.6	2284.6	2569.4	2809.9	3012.4
35°	1256.2	1376.5	1492.0	1612.2	1776.8	1885.9	1999.8	2268.8	2588.4	2821.0	2946.0
37.5°	1208.8	1314.8	1414.4	1531.5	1704.0	1821.1	1952.4	2249.8	2578.9	2773.5	2808.3
40°	1155.0	1261.0	1341.7	1450.8	1632.8	1768.8	1901.7	2224.5	2537.8	2661.2	2559.9
42.5°	1102.8	1186.6	1256.2	1362.2	1560.0	1692.9	1836.9	2178.6	2457.1	2482.4	2254.6
45°	1042.6	1102.8	1164.5	1284.7	1480.9	1617.0	1776.8	2112.2	2327.3	2254.6	1966.6
47.5°	965.1	1018.9	1086.9	1197.7	1397.0	1537.9	1689.7	2026.7	2139.1	1987.2	1672.3
50°	890.8	936.6	999.9	1107.5	1308.4	1446.1	1607.5	1892.3	1947.6	1708.7	1441.3
52.5°	816.4	851.2	912.9	1020.5	1221.4	1354.3	1501.5	1754.6	1723.0	1466.7	1229.3
55°	738.9	768.9	827.5	933.5	1120.2	1246.7	1387.5	1585.3	1503.0	1259.4	1069.5
57.5°	662.9	694.6	754.7	843.3	1018.9	1142.3	1254.6	1409.7	1286.3	1091.7	924.0
60°	594.9	621.8	667.7	754.7	914.5	1014.2	1117.0	1223.0	1120.2	931.9	803.7
62.5°	523.7	549.0	591.7	670.8	808.5	897.1	979.4	1066.4	952.5	814.8	700.9
65°	457.2	477.8	517.4	590.1	702.5	775.3	841.7	901.8	810.1	683.5	598.1
67.5°	397.1	414.5	447.7	512.6	607.5	659.8	713.6	764.2	686.7	585.4	512.6
70°	332.3	346.5	376.6	424.0	500.0	553.8	593.3	631.3	561.7	481.0	431.9
72.5°	275.3	289.5	308.5	357.6	409.8	443.0	485.7	506.3	466.7	400.3	351.2
75°	219.9	231.0	248.4	280.0	329.1	351.2	378.1	394.0	357.6	313.3	283.2
77.5°	172.5	177.2	189.9	212.0	245.2	270.5	291.1	300.6	275.3	246.8	221.5
80°	121.8	128.2	137.6	156.6	181.9	189.9	202.5	213.6	197.8	172.5	156.6
82.5°	80.7	88.6	93.3	101.3	117.1	126.6	129.7	139.2	125.0	115.5	109.2
85°	47.5	50.6	52.2	57.0	64.9	69.6	74.4	75.9	72.8	71.2	64.9
87.5°	23.7	23.7	23.7	26.9	28.5	31.6	33.2	33.2	33.2	31.6	30.1
90°	0.5	1.5	2.5	3.5	4.5	5.0	5.7	7.0	8.3	9.6	10.9
92.5°	10.5	9.9	9.3	8.7	8.1	7.8	8.3	9.2	10.1	11.0	11.9
95°	27.8	23.6	19.5	15.3	11.2	9.1	9.7	10.8	11.9	13.0	14.1
97.5°	50.6	47.8	45.0	42.1	39.3	37.9	35.3	30.1	25.0	19.8	14.6
100°	77.1	79.1	81.1	83.2	85.2	86.2	78.3	62.5	46.7	30.9	15.1
102.5°	107.2	108.5	109.8	111.1	112.4	113.1	104.3	86.7	69.0	51.4	33.8
105°	135.9	137.0	138.2	139.3	140.4	141.0	136.4	127.3	118.2	109.0	99.9
107.5°	166.5	167.4	168.3	169.2	170.1	170.6	171.4	172.9	174.4	175.9	177.4
110°	197.1	197.9	198.7	199.5	200.3	200.7	201.3	202.4	203.5	204.6	205.7



TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	226.3	227.0	227.7	228.4	229.1	229.4	230.0	231.1	232.2	233.4	234.5
115°	255.0	255.6	256.2	256.8	257.4	257.7	258.2	259.1	260.0	260.9	261.8
117.5°	283.3	284.0	284.7	285.4	286.1	286.5	286.7	287.2	287.7	288.2	288.7
120°	309.3	310.2	311.1	312.0	312.9	313.4	313.5	313.8	314.1	314.4	314.7
122.5°	335.7	336.4	337.1	337.8	338.5	338.9	339.1	339.5	339.9	340.3	340.7
125°	359.4	360.2	361.0	361.9	362.7	363.1	363.3	363.7	364.1	364.5	364.9
127.5°	383.2	384.0	384.8	385.6	386.4	386.8	387.1	387.6	388.1	388.6	389.1
130°	405.1	405.9	406.7	407.5	408.3	408.7	408.9	409.3	409.7	410.1	410.5
132.5°	426.0	426.8	427.6	428.5	429.3	429.7	429.9	430.2	430.5	430.8	431.1
135°	447.5	448.1	448.7	449.3	449.9	450.2	450.4	450.8	451.2	451.6	452.0
137.5°	465.7	466.5	467.3	468.2	469.0	469.4	469.5	469.7	469.9	470.1	470.3
140°	484.0	484.6	485.2	485.8	486.4	486.7	486.9	487.2	487.5	487.8	488.1
142.5°	500.9	501.5	502.1	502.7	503.3	503.6	503.8	504.1	504.4	504.7	505.0
145°	516.4	517.1	517.8	518.5	519.2	519.6	519.7	519.9	520.1	520.3	520.5
147.5°	531.4	531.9	532.4	532.9	533.4	533.7	533.8	534.0	534.2	534.4	534.6
150°	545.1	545.4	545.7	546.0	546.3	546.5	546.6	546.8	547.0	547.2	547.4
152.5°	557.4	557.5	557.6	557.7	557.8	557.9	557.9	558.0	558.1	558.2	558.3
155°	568.8	568.6	568.4	568.2	568.0	567.9	568.0	568.1	568.2	568.3	568.4
157.5°	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.8	577.7	577.6	577.5
160°	586.2	586.1	586.0	585.9	585.8	585.7	585.6	585.5	585.4	585.3	585.2
162.5°	593.9	593.6	593.3	593.0	592.7	592.5	592.5	592.4	592.3	592.2	592.1
165°	599.8	599.5	599.2	598.9	598.6	598.5	598.4	598.3	598.2	598.1	598.0
167.5°	604.9	604.5	604.1	603.6	603.2	603.0	603.0	603.0	603.0	603.0	603.0
170°	609.0	608.6	608.2	607.7	607.3	607.1	607.1	607.1	607.1	607.1	607.1
172.5°	611.7	611.2	610.7	610.2	609.7	609.4	609.5	609.6	609.7	609.8	609.9
175°	614.0	613.5	613.0	612.5	612.0	611.7	611.8	611.9	612.0	612.1	612.2
177.5°	614.9	614.4	613.9	613.4	612.9	612.6	612.7	612.8	612.9	613.0	613.1
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1719.8	1723.0	1734.0	1742.0	1757.8	1756.2	1756.2	1754.6	1749.9	1757.8	1762.5
5°	1840.0	1866.9	1870.1	1904.9	1906.5	1920.7	1930.2	1922.3	1941.3	1939.7	1925.5
7.5°	1988.8	2025.2	2042.6	2075.8	2113.8	2104.3	2140.7	2147.0	2143.8	2159.6	2170.7
10°	2151.7	2215.0	2259.3	2321.0	2336.8	2346.3	2370.1	2390.6	2431.8	2400.1	2420.7
12.5°	2338.4	2384.3	2442.8	2540.9	2590.0	2621.6	2632.7	2646.9	2675.4	2658.0	2659.6
15°	2495.1	2556.8	2656.4	2778.3	2792.5	2832.1	2822.6	2908.0	2949.1	2887.4	2922.2
17.5°	2658.0	2740.3	2859.0	2965.0	3025.1	3052.0	3077.3	3159.6	3156.4	3146.9	3154.8
20°	2762.4	2896.9	3044.1	3184.9	3202.3	3222.8	3290.9	3325.7	3319.4	3346.3	3363.7
22.5°	2909.6	3052.0	3208.6	3302.0	3341.5	3365.2	3419.0	3441.2	3450.7	3457.0	3445.9
25°	3033.0	3184.9	3300.4	3382.6	3406.4	3419.0	3436.4	3442.8	3438.0	3426.9	3436.4
27.5°	3116.8	3238.7	3317.8	3355.7	3343.1	3322.5	3289.3	3267.1	3218.1	3194.4	3222.8
30°	3151.7	3205.4	3229.2	3165.9	3102.6	3052.0	2988.7	2871.6	2779.8	2806.7	2770.4
32.5°	3096.3	3061.5	2947.6	2784.6	2735.5	2653.3	2474.5	2336.8	2341.6	2268.8	2298.9
35°	2933.3	2775.1	2559.9	2313.1	2248.2	2203.9	2007.8	1977.7	1914.4	1846.4	1865.4
37.5°	2645.4	2414.4	2153.3	1971.4	1874.9	1778.3	1667.6	1601.1	1563.2	1534.7	1556.8
40°	2294.1	2012.5	1797.3	1634.4	1552.1	1490.4	1414.4	1348.0	1305.3	1300.5	1308.4
42.5°	1949.2	1711.9	1514.1	1359.1	1332.2	1259.4	1210.3	1158.1	1145.5	1124.9	1136.0
45°	1650.2	1457.2	1294.2	1167.6	1136.0	1117.0	1056.9	1023.7	1009.4	996.8	1015.7
47.5°	1433.4	1230.9	1112.3	1036.3	1004.7	973.0	939.8	917.6	906.6	908.2	906.6
50°	1224.6	1075.9	971.4	912.9	893.9	871.8	844.9	830.6	825.9	811.6	822.7
52.5°	1053.7	946.1	873.3	818.0	803.7	787.9	765.8	757.9	746.8	743.6	743.6
55°	916.1	832.2	773.7	737.3	719.9	707.2	694.6	685.1	677.2	677.2	677.2
57.5°	808.5	735.7	693.0	661.3	655.0	642.4	628.1	628.1	617.0	615.5	620.2
60°	716.7	651.8	618.6	591.7	582.2	579.1	564.8	564.8	561.7	553.8	560.1
62.5°	623.4	575.9	547.4	526.9	517.4	517.4	506.3	498.4	498.4	500.0	496.8
65°	537.9	503.1	477.8	462.0	457.2	450.9	449.3	443.0	438.3	439.8	438.3
67.5°	462.0	435.1	417.7	405.0	397.1	394.0	389.2	389.2	386.0	387.6	379.7
70°	394.0	367.1	352.8	340.2	337.0	337.0	330.7	332.3	329.1	333.8	330.7
72.5°	324.3	303.8	292.7	288.0	284.8	283.2	280.0	276.9	275.3	278.5	276.9
75°	262.6	245.2	237.3	234.2	231.0	231.0	229.4	227.8	226.2	226.2	226.2
77.5°	204.1	193.0	183.5	186.7	181.9	183.5	178.8	178.8	180.4	178.8	178.8
80°	150.3	142.4	142.4	139.2	132.9	136.1	136.1	131.3	129.7	132.9	128.2
82.5°	99.7	98.1	94.9	93.3	90.2	91.8	90.2	88.6	87.0	90.2	87.0
85°	58.5	58.5	57.0	53.8	57.0	55.4	53.8	53.8	52.2	52.2	52.2
87.5°	30.1	26.9	26.9	25.3	26.9	23.7	25.3	23.7	22.2	23.7	22.2
90°	11.3	11.7	12.2	12.6	12.8	12.9	13.1	13.3	13.5	13.7	13.5
92.5°	12.6	13.3	14.0	14.7	15.1	15.1	15.2	15.3	15.4	15.5	15.4
95°	14.8	15.5	16.2	16.9	17.3	17.3	17.3	17.3	17.3	17.3	17.3
97.5°	15.4	16.2	17.0	17.8	18.2	18.3	18.4	18.5	18.6	18.7	18.6
100°	15.9	16.7	17.5	18.3	18.7	18.8	18.9	19.0	19.1	19.2	19.1
102.5°	30.4	27.1	23.7	20.4	18.7	18.8	19.0	19.2	19.4	19.6	19.4
105°	82.0	64.0	46.1	28.2	19.2	19.3	19.5	19.7	19.9	20.1	19.9
107.5°	161.8	146.2	130.6	115.0	107.2	100.6	87.3	74.0	60.7	47.4	60.7
110°	202.4	199.0	195.7	192.4	190.7	183.4	168.9	154.4	139.9	125.4	139.9

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	235.4	236.3	237.2	238.1	238.6	238.5	238.3	238.1	237.9	237.7	237.9
115°	262.8	263.8	264.9	265.9	266.4	266.6	267.0	267.4	267.8	268.2	267.8
117.5°	289.5	290.3	291.2	292.0	292.4	292.4	292.5	292.6	292.7	292.8	292.7
120°	315.5	316.3	317.2	318.0	318.4	318.4	318.4	318.4	318.4	318.4	318.4
122.5°	341.2	341.7	342.2	342.7	343.0	343.1	343.2	343.3	343.4	343.5	343.4
125°	365.1	365.3	365.5	365.7	365.8	365.9	366.1	366.3	366.5	366.7	366.5
127.5°	389.4	389.7	390.0	390.3	390.5	390.4	390.2	390.0	389.8	389.6	389.8
130°	410.9	411.3	411.8	412.2	412.4	412.3	412.1	411.8	411.6	411.4	411.6
132.5°	431.5	431.9	432.3	432.7	432.9	432.7	432.4	432.1	431.8	431.5	431.8
135°	452.3	452.6	452.9	453.2	453.4	453.2	452.9	452.6	452.3	452.0	452.3
137.5°	470.8	471.3	471.8	472.3	472.6	472.5	472.3	472.1	471.9	471.7	471.9
140°	488.5	488.9	489.3	489.7	489.9	489.8	489.6	489.4	489.2	489.0	489.2
142.5°	505.3	505.6	505.9	506.2	506.3	506.2	505.9	505.6	505.3	505.0	505.3
145°	520.7	520.9	521.1	521.3	521.4	521.4	521.4	521.4	521.4	521.4	521.4
147.5°	534.8	535.0	535.2	535.4	535.5	535.2	534.7	534.2	533.7	533.2	533.7
150°	547.6	547.8	548.0	548.2	548.3	548.1	547.8	547.5	547.2	546.9	547.2
152.5°	558.7	559.1	559.6	560.0	560.2	559.9	559.4	558.9	558.4	557.9	558.4
155°	568.9	569.4	569.9	570.4	570.6	570.3	569.7	569.1	568.5	567.9	568.5
157.5°	578.1	578.7	579.3	579.9	580.2	579.8	579.0	578.2	577.4	576.6	577.4
160°	585.8	586.4	587.1	587.7	588.0	587.6	586.9	586.2	585.5	584.8	585.5
162.5°	592.8	593.5	594.2	594.9	595.3	595.0	594.4	593.7	593.1	592.5	593.1
165°	598.8	599.6	600.5	601.3	601.7	601.3	600.6	599.9	599.2	598.5	599.2
167.5°	603.8	604.6	605.5	606.3	606.7	606.3	605.5	604.6	603.8	603.0	603.8
170°	607.9	608.7	609.6	610.4	610.8	610.4	609.6	608.7	607.9	607.1	607.9
172.5°	610.7	611.5	612.3	613.1	613.5	613.0	612.1	611.2	610.3	609.4	610.3
175°	612.9	613.6	614.3	615.0	615.3	614.9	614.1	613.3	612.5	611.7	612.5
177.5°	613.9	614.7	615.5	616.3	616.7	616.2	615.2	614.2	613.2	612.2	613.2
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1749.9	1754.6	1742.0	1738.8	1738.8	1745.1	1740.4	1697.7	1705.6	1696.1	1692.9
5°	1942.9	1933.4	1920.7	1914.4	1906.5	1884.3	1882.8	1833.7	1824.2	1792.6	1778.3
7.5°	2154.9	2147.0	2109.0	2104.3	2101.1	2080.5	2028.3	1976.1	1938.1	1901.7	1866.9
10°	2397.0	2373.2	2355.8	2321.0	2303.6	2275.1	2207.1	2158.1	2093.2	2037.8	1965.0
12.5°	2688.1	2661.2	2602.6	2577.3	2555.2	2476.1	2408.0	2352.7	2226.1	2188.1	2097.9
15°	2901.7	2844.7	2838.4	2783.0	2779.8	2692.8	2563.1	2503.0	2404.9	2265.6	2172.3
17.5°	3132.7	3082.0	3042.5	2976.0	2966.5	2884.3	2789.3	2642.2	2534.6	2401.7	2283.0
20°	3302.0	3275.1	3207.0	3180.1	3124.8	3055.1	2957.0	2775.1	2643.8	2510.9	2365.3
22.5°	3436.4	3409.5	3355.7	3319.4	3287.7	3197.5	3080.5	2925.4	2745.0	2571.0	2420.7
25°	3434.9	3426.9	3404.8	3387.4	3363.7	3297.2	3199.1	3050.4	2849.5	2658.0	2449.2
27.5°	3240.3	3262.4	3300.4	3319.4	3314.6	3305.1	3249.7	3124.8	2944.4	2716.6	2482.4
30°	2835.2	2915.9	2987.1	3082.0	3110.5	3180.1	3211.8	3140.6	2996.6	2784.6	2525.1
32.5°	2351.1	2468.2	2623.2	2675.4	2765.6	2900.1	3050.4	3077.3	2987.1	2824.1	2552.0
35°	1928.6	2025.2	2145.4	2227.7	2308.4	2526.7	2716.6	2881.1	2911.2	2803.6	2545.7
37.5°	1596.4	1664.4	1770.4	1840.0	1914.4	2101.1	2366.9	2580.5	2730.8	2734.0	2528.3
40°	1355.9	1386.0	1477.7	1528.4	1599.6	1760.9	1998.3	2276.7	2496.6	2597.9	2482.4
42.5°	1148.6	1188.2	1264.1	1302.1	1348.0	1488.8	1645.4	1909.7	2181.8	2398.5	2397.0
45°	1025.2	1053.7	1088.5	1120.2	1172.4	1256.2	1435.0	1632.8	1893.8	2139.1	2235.6
47.5°	916.1	943.0	977.8	987.3	1022.1	1101.2	1210.3	1382.8	1626.5	1870.1	2052.1
50°	824.3	846.5	870.2	887.6	903.4	968.3	1050.6	1196.1	1390.7	1626.5	1852.7
52.5°	753.1	768.9	789.5	799.0	813.2	860.7	924.0	1031.6	1191.4	1406.5	1626.5
55°	686.7	697.7	710.4	726.2	732.5	767.3	816.4	908.2	1026.8	1219.8	1428.7
57.5°	625.0	629.7	637.6	647.1	655.0	685.1	727.8	789.5	893.9	1042.6	1240.4
60°	555.3	568.0	572.7	582.2	587.0	610.7	643.9	696.1	776.8	905.0	1053.7
62.5°	496.8	504.7	512.6	517.4	528.4	536.4	563.2	610.7	677.2	772.1	906.6
65°	444.6	447.7	452.5	457.2	460.4	469.9	495.2	526.9	577.5	661.3	765.8
67.5°	384.5	387.6	394.0	395.5	398.7	411.4	425.6	452.5	495.2	558.5	643.9
70°	325.9	330.7	333.8	337.0	341.7	346.5	362.3	384.5	417.7	462.0	528.4
72.5°	275.3	280.0	280.0	283.2	281.6	288.0	303.8	319.6	341.7	378.1	436.7
75°	224.7	224.7	227.8	229.4	231.0	237.3	243.7	256.3	273.7	302.2	338.6
77.5°	177.2	175.6	178.8	178.8	178.8	183.5	189.9	196.2	207.3	227.8	256.3
80°	129.7	129.7	132.9	134.5	131.3	132.9	136.1	142.4	150.3	164.5	180.4
82.5°	85.4	91.8	90.2	91.8	90.2	93.3	94.9	96.5	99.7	106.0	117.1
85°	52.2	52.2	52.2	53.8	52.2	53.8	53.8	53.8	55.4	58.5	63.3
87.5°	22.2	22.2	22.2	23.7	22.2	22.2	23.7	22.2	23.7	23.7	25.3
90°	13.3	13.1	12.9	12.8	12.6	12.2	11.7	11.3	10.9	9.6	8.3
92.5°	15.3	15.2	15.1	15.1	14.7	14.0	13.3	12.6	11.9	11.0	10.1
95°	17.3	17.3	17.3	17.3	16.9	16.2	15.5	14.8	14.1	13.0	11.9
97.5°	18.5	18.4	18.3	18.2	17.8	17.0	16.2	15.4	14.6	19.8	25.0
100°	19.0	18.9	18.8	18.7	18.3	17.5	16.7	15.9	15.1	30.9	46.7
102.5°	19.2	19.0	18.8	18.7	20.4	23.7	27.1	30.4	33.8	51.4	69.0
105°	19.7	19.5	19.3	19.2	28.2	46.1	64.0	82.0	99.9	109.0	118.2
107.5°	74.0	87.3	100.6	107.2	115.0	130.6	146.2	161.8	177.4	175.9	174.4
110°	154.4	168.9	183.4	190.7	192.4	195.7	199.0	202.4	205.7	204.6	203.5

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	238.1	238.3	238.5	238.6	238.1	237.2	236.3	235.4	234.5	233.4	232.2
115°	267.4	267.0	266.6	266.4	265.9	264.9	263.8	262.8	261.8	260.9	260.0
117.5°	292.6	292.5	292.4	292.4	292.0	291.2	290.3	289.5	288.7	288.2	287.7
120°	318.4	318.4	318.4	318.4	318.0	317.2	316.3	315.5	314.7	314.4	314.1
122.5°	343.3	343.2	343.1	343.0	342.7	342.2	341.7	341.2	340.7	340.3	339.9
125°	366.3	366.1	365.9	365.8	365.7	365.5	365.3	365.1	364.9	364.5	364.1
127.5°	390.0	390.2	390.4	390.5	390.3	390.0	389.7	389.4	389.1	388.6	388.1
130°	411.8	412.1	412.3	412.4	412.2	411.8	411.3	410.9	410.5	410.1	409.7
132.5°	432.1	432.4	432.7	432.9	432.7	432.3	431.9	431.5	431.1	430.8	430.5
135°	452.6	452.9	453.2	453.4	453.2	452.9	452.6	452.3	452.0	451.6	451.2
137.5°	472.1	472.3	472.5	472.6	472.3	471.8	471.3	470.8	470.3	470.1	469.9
140°	489.4	489.6	489.8	489.9	489.7	489.3	488.9	488.5	488.1	487.8	487.5
142.5°	505.6	505.9	506.2	506.3	506.2	505.9	505.6	505.3	505.0	504.7	504.4
145°	521.4	521.4	521.4	521.4	521.3	521.1	520.9	520.7	520.5	520.3	520.1
147.5°	534.2	534.7	535.2	535.5	535.4	535.2	535.0	534.8	534.6	534.4	534.2
150°	547.5	547.8	548.1	548.3	548.2	548.0	547.8	547.6	547.4	547.2	547.0
152.5°	558.9	559.4	559.9	560.2	560.0	559.6	559.1	558.7	558.3	558.2	558.1
155°	569.1	569.7	570.3	570.6	570.4	569.9	569.4	568.9	568.4	568.3	568.2
157.5°	578.2	579.0	579.8	580.2	579.9	579.3	578.7	578.1	577.5	577.6	577.7
160°	586.2	586.9	587.6	588.0	587.7	587.1	586.4	585.8	585.2	585.3	585.4
162.5°	593.7	594.4	595.0	595.3	594.9	594.2	593.5	592.8	592.1	592.2	592.3
165°	599.9	600.6	601.3	601.7	601.3	600.5	599.6	598.8	598.0	598.1	598.2
167.5°	604.6	605.5	606.3	606.7	606.3	605.5	604.6	603.8	603.0	603.0	603.0
170°	608.7	609.6	610.4	610.8	610.4	609.6	608.7	607.9	607.1	607.1	607.1
172.5°	611.2	612.1	613.0	613.5	613.1	612.3	611.5	610.7	609.9	609.8	609.7
175°	613.3	614.1	614.9	615.3	615.0	614.3	613.6	612.9	612.2	612.1	612.0
177.5°	614.2	615.2	616.2	616.7	616.3	615.5	614.7	613.9	613.1	613.0	612.9
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1677.1	1672.3	1672.3	1669.2	1659.7	1642.3	1640.7	1643.9	1634.4	1624.9	1610.6
5°	1759.4	1729.3	1719.8	1710.3	1691.3	1659.7	1647.0	1635.9	1618.5	1598.0	1575.8
7.5°	1829.0	1786.3	1773.6	1756.2	1718.2	1673.9	1645.4	1621.7	1598.0	1569.5	1542.6
10°	1916.0	1854.3	1824.2	1798.9	1746.7	1685.0	1642.3	1607.5	1569.5	1534.7	1499.9
12.5°	2014.1	1914.4	1904.9	1843.2	1783.1	1691.3	1639.1	1588.5	1537.9	1495.1	1458.7
15°	2096.4	1987.2	1947.6	1906.5	1791.0	1677.1	1626.5	1569.5	1511.0	1465.1	1411.3
17.5°	2148.6	2058.4	1974.5	1919.2	1798.9	1697.7	1599.6	1534.7	1473.0	1409.7	1365.4
20°	2211.9	2080.5	2007.8	1933.4	1814.7	1681.8	1583.7	1503.0	1427.1	1370.1	1316.4
22.5°	2275.1	2097.9	2037.8	1957.1	1817.9	1666.0	1555.3	1474.6	1387.5	1330.6	1272.1
25°	2268.8	2123.3	2023.6	1955.5	1786.3	1651.8	1522.0	1427.1	1346.4	1273.6	1215.1
27.5°	2273.6	2094.8	1993.5	1914.4	1764.1	1631.2	1487.2	1387.5	1303.7	1227.8	1166.0
30°	2275.1	2052.1	1963.5	1868.5	1723.0	1582.2	1447.7	1346.4	1257.8	1175.5	1120.2
32.5°	2270.4	2017.2	1906.5	1821.1	1658.1	1534.7	1401.8	1294.2	1204.0	1128.1	1075.9
35°	2259.3	1976.1	1848.0	1740.4	1591.6	1466.7	1359.1	1248.3	1151.8	1082.2	1022.1
37.5°	2229.3	1931.8	1786.3	1680.2	1514.1	1387.5	1292.6	1200.9	1107.5	1025.2	974.6
40°	2207.1	1871.7	1724.5	1609.1	1430.3	1306.9	1227.8	1140.7	1049.0	974.6	925.6
42.5°	2156.5	1814.7	1661.3	1523.6	1348.0	1221.4	1147.1	1077.4	998.3	925.6	881.3
45°	2074.2	1753.0	1583.7	1444.5	1257.8	1137.6	1069.5	1012.6	943.0	873.3	829.0
47.5°	1958.7	1664.4	1501.5	1362.2	1169.2	1047.4	979.4	936.6	881.3	822.7	784.7
50°	1833.7	1567.9	1417.6	1280.0	1083.8	965.1	898.7	859.1	822.7	768.9	732.5
52.5°	1670.8	1465.1	1321.1	1189.8	992.0	878.1	819.6	791.1	753.1	715.1	683.5
55°	1512.5	1332.2	1213.5	1088.5	901.8	795.8	738.9	708.8	686.7	655.0	629.7
57.5°	1329.0	1208.8	1099.6	985.7	818.0	721.5	667.7	631.3	617.0	602.8	579.1
60°	1159.7	1068.0	979.4	884.4	731.0	643.9	591.7	563.2	549.0	539.5	523.7
62.5°	1004.7	933.5	857.5	781.6	642.4	563.2	523.7	495.2	482.6	481.0	466.7
65°	855.9	805.3	743.6	669.3	560.1	490.5	452.5	435.1	420.9	420.9	409.8
67.5°	707.2	672.4	623.4	571.2	485.7	420.9	386.0	370.2	362.3	362.3	354.4
70°	588.6	564.8	520.5	474.6	400.3	351.2	324.3	310.1	305.4	306.9	300.6
72.5°	477.8	452.5	416.1	382.9	327.5	291.1	272.1	256.3	248.4	250.0	248.4
75°	370.2	357.6	325.9	300.6	256.3	231.0	213.6	205.7	199.4	200.9	197.8
77.5°	278.5	259.5	242.1	224.7	197.8	177.2	163.0	155.1	150.3	150.3	150.3
80°	189.9	186.7	172.5	163.0	140.8	125.0	113.9	112.3	107.6	107.6	107.6
82.5°	123.4	115.5	107.6	101.3	88.6	79.1	74.4	71.2	69.6	68.0	71.2
85°	68.0	63.3	60.1	53.8	49.0	44.3	39.6	38.0	36.4	38.0	36.4
87.5°	26.9	22.2	22.2	20.6	19.0	17.4	17.4	14.2	14.2	12.7	12.7
90°	7.0	5.7	5.0	4.5	3.5	2.5	1.5	0.5	1.5	2.5	3.5
92.5°	9.2	8.3	7.8	8.1	8.7	9.3	9.9	10.5	9.9	9.3	8.7
95°	10.8	9.7	9.1	11.2	15.3	19.5	23.6	27.8	23.6	19.5	15.3
97.5°	30.1	35.3	37.9	39.3	42.1	45.0	47.8	50.6	47.8	45.0	42.1
100°	62.5	78.3	86.2	85.2	83.2	81.1	79.1	77.1	79.1	81.1	83.2
102.5°	86.7	104.3	113.1	112.4	111.1	109.8	108.5	107.2	108.5	109.8	111.1
105°	127.3	136.4	141.0	140.4	139.3	138.2	137.0	135.9	137.0	138.2	139.3
107.5°	172.9	171.4	170.6	170.1	169.2	168.3	167.4	166.5	167.4	168.3	169.2
110°	202.4	201.3	200.7	200.3	199.5	198.7	197.9	197.1	197.9	198.7	199.5

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	231.1	230.0	229.4	229.1	228.4	227.7	227.0	226.3	227.0	227.7	228.4
115°	259.1	258.2	257.7	257.4	256.8	256.2	255.6	255.0	255.6	256.2	256.8
117.5°	287.2	286.7	286.5	286.1	285.4	284.7	284.0	283.3	284.0	284.7	285.4
120°	313.8	313.5	313.4	312.9	312.0	311.1	310.2	309.3	310.2	311.1	312.0
122.5°	339.5	339.1	338.9	338.5	337.8	337.1	336.4	335.7	336.4	337.1	337.8
125°	363.7	363.3	363.1	362.7	361.9	361.0	360.2	359.4	360.2	361.0	361.9
127.5°	387.6	387.1	386.8	386.4	385.6	384.8	384.0	383.2	384.0	384.8	385.6
130°	409.3	408.9	408.7	408.3	407.5	406.7	405.9	405.1	405.9	406.7	407.5
132.5°	430.2	429.9	429.7	429.3	428.5	427.6	426.8	426.0	426.8	427.6	428.5
135°	450.8	450.4	450.2	449.9	449.3	448.7	448.1	447.5	448.1	448.7	449.3
137.5°	469.7	469.5	469.4	469.0	468.2	467.3	466.5	465.7	466.5	467.3	468.2
140°	487.2	486.9	486.7	486.4	485.8	485.2	484.6	484.0	484.6	485.2	485.8
142.5°	504.1	503.8	503.6	503.3	502.7	502.1	501.5	500.9	501.5	502.1	502.7
145°	519.9	519.7	519.6	519.2	518.5	517.8	517.1	516.4	517.1	517.8	518.5
147.5°	534.0	533.8	533.7	533.4	532.9	532.4	531.9	531.4	531.9	532.4	532.9
150°	546.8	546.6	546.5	546.3	546.0	545.7	545.4	545.1	545.4	545.7	546.0
152.5°	558.0	557.9	557.9	557.8	557.7	557.6	557.5	557.4	557.5	557.6	557.7
155°	568.1	568.0	567.9	568.0	568.2	568.4	568.6	568.8	568.6	568.4	568.2
157.5°	577.8	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9	577.9
160°	585.5	585.6	585.7	585.8	585.9	586.0	586.1	586.2	586.1	586.0	585.9
162.5°	592.4	592.5	592.5	592.7	593.0	593.3	593.6	593.9	593.6	593.3	593.0
165°	598.3	598.4	598.5	598.6	598.9	599.2	599.5	599.8	599.5	599.2	598.9
167.5°	603.0	603.0	603.0	603.2	603.6	604.1	604.5	604.9	604.5	604.1	603.6
170°	607.1	607.1	607.1	607.3	607.7	608.2	608.6	609.0	608.6	608.2	607.7
172.5°	609.6	609.5	609.4	609.7	610.2	610.7	611.2	611.7	611.2	610.7	610.2
175°	611.9	611.8	611.7	612.0	612.5	613.0	613.5	614.0	613.5	613.0	612.5
177.5°	612.8	612.7	612.6	612.9	613.4	613.9	614.4	614.9	614.4	613.9	613.4
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1607.5	1605.9	1609.1	1599.6	1583.7	1575.8	1553.7	1548.9	1547.3	1548.9	1550.5
5°	1563.2	1561.6	1556.8	1541.0	1522.0	1507.8	1480.9	1479.3	1469.8	1460.3	1465.1
7.5°	1520.4	1514.1	1504.6	1484.1	1458.7	1442.9	1420.8	1405.0	1392.3	1384.4	1378.1
10°	1477.7	1468.2	1458.7	1431.8	1400.2	1376.5	1349.6	1336.9	1322.7	1316.4	1310.0
12.5°	1422.4	1412.9	1395.5	1363.8	1344.8	1314.8	1287.9	1275.2	1267.3	1254.6	1246.7
15°	1378.1	1359.1	1349.6	1316.4	1276.8	1273.6	1224.6	1221.4	1205.6	1205.6	1192.9
17.5°	1327.4	1313.2	1295.8	1262.6	1234.1	1205.6	1180.3	1170.8	1156.6	1153.4	1147.1
20°	1278.4	1259.4	1253.1	1219.8	1189.8	1155.0	1128.1	1118.6	1112.3	1105.9	1110.7
22.5°	1227.8	1211.9	1196.1	1166.0	1143.9	1109.1	1093.3	1083.8	1074.3	1071.1	1072.7
25°	1178.7	1164.5	1148.6	1118.6	1094.9	1066.4	1052.1	1047.4	1042.6	1042.6	1041.1
27.5°	1131.2	1117.0	1102.8	1075.9	1052.1	1031.6	1020.5	1015.7	1011.0	1014.2	1017.3
30°	1082.2	1069.5	1056.9	1033.1	1014.2	995.2	988.8	985.7	984.1	992.0	992.0
32.5°	1037.9	1026.8	1017.3	995.2	976.2	960.4	955.6	957.2	958.8	963.5	966.7
35°	992.0	984.1	974.6	955.6	939.8	925.6	927.1	927.1	930.3	938.2	944.5
37.5°	950.9	939.8	931.9	916.1	903.4	890.8	895.5	900.2	903.4	912.9	916.1
40°	901.8	897.1	890.8	874.9	863.9	862.3	863.9	867.0	873.3	878.1	882.8
42.5°	862.3	855.9	848.0	835.4	825.9	827.5	829.0	832.2	835.4	843.3	848.0
45°	818.0	813.2	806.9	795.8	787.9	789.5	791.1	791.1	794.2	803.7	806.9
47.5°	768.9	770.5	762.6	751.5	746.8	746.8	746.8	749.9	757.9	761.0	762.6
50°	721.5	718.3	716.7	705.6	702.5	700.9	702.5	704.1	715.1	713.6	718.3
52.5°	670.8	670.8	669.3	662.9	658.2	658.2	655.0	662.9	666.1	669.3	674.0
55°	621.8	617.0	615.5	612.3	606.0	604.4	607.5	617.0	620.2	623.4	628.1
57.5°	568.0	568.0	564.8	560.1	560.1	560.1	560.1	566.4	571.2	574.3	583.8
60°	518.9	512.6	507.9	507.9	507.9	506.3	515.8	515.8	525.3	526.9	530.0
62.5°	460.4	457.2	454.1	455.7	454.1	457.2	460.4	466.7	468.3	473.1	477.8
65°	405.0	405.0	401.9	411.4	405.0	405.0	412.9	412.9	416.1	420.9	427.2
67.5°	351.2	352.8	349.7	349.7	352.8	354.4	356.0	362.3	363.9	370.2	378.1
70°	295.9	299.0	300.6	297.4	300.6	303.8	306.9	308.5	314.8	318.0	322.8
72.5°	246.8	250.0	245.2	246.8	248.4	251.6	253.1	256.3	259.5	269.0	272.1
75°	197.8	196.2	194.6	200.9	197.8	204.1	205.7	205.7	208.8	216.8	219.9
77.5°	151.9	151.9	153.5	150.3	155.1	153.5	155.1	159.8	164.5	164.5	177.2
80°	106.0	109.2	109.2	109.2	110.8	112.3	109.2	117.1	118.7	118.7	123.4
82.5°	68.0	69.6	68.0	71.2	71.2	74.4	72.8	74.4	77.5	80.7	82.3
85°	36.4	36.4	39.6	39.6	38.0	39.6	38.0	39.6	42.7	42.7	44.3
87.5°	12.7	12.7	12.7	12.7	14.2	12.7	14.2	14.2	12.7	12.7	17.4
90°	4.5	5.0	5.7	7.0	8.3	9.6	10.9	11.3	11.7	12.2	12.6
92.5°	8.1	7.8	8.3	9.2	10.1	11.0	11.9	12.6	13.3	14.0	14.7
95°	11.2	9.1	9.7	10.8	11.9	13.0	14.1	14.8	15.5	16.2	16.9
97.5°	39.3	37.9	35.3	30.1	25.0	19.8	14.6	15.4	16.2	17.0	17.8
100°	85.2	86.2	78.3	62.5	46.7	30.9	15.1	15.9	16.7	17.5	18.3
102.5°	112.4	113.1	104.3	86.7	69.0	51.4	33.8	30.4	27.1	23.7	20.4
105°	140.4	141.0	136.4	127.3	118.2	109.0	99.9	82.0	64.0	46.1	28.2
107.5°	170.1	170.6	171.4	172.9	174.4	175.9	177.4	161.8	146.2	130.6	115.0
110°	200.3	200.7	201.3	202.4	203.5	204.6	205.7	202.4	199.0	195.7	192.4

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	229.1	229.4	230.0	231.1	232.2	233.4	234.5	235.4	236.3	237.2	238.1
115°	257.4	257.7	258.2	259.1	260.0	260.9	261.8	262.8	263.8	264.9	265.9
117.5°	286.1	286.5	286.7	287.2	287.7	288.2	288.7	289.5	290.3	291.2	292.0
120°	312.9	313.4	313.5	313.8	314.1	314.4	314.7	315.5	316.3	317.2	318.0
122.5°	338.5	338.9	339.1	339.5	339.9	340.3	340.7	341.2	341.7	342.2	342.7
125°	362.7	363.1	363.3	363.7	364.1	364.5	364.9	365.1	365.3	365.5	365.7
127.5°	386.4	386.8	387.1	387.6	388.1	388.6	389.1	389.4	389.7	390.0	390.3
130°	408.3	408.7	408.9	409.3	409.7	410.1	410.5	410.9	411.3	411.8	412.2
132.5°	429.3	429.7	429.9	430.2	430.5	430.8	431.1	431.5	431.9	432.3	432.7
135°	449.9	450.2	450.4	450.8	451.2	451.6	452.0	452.3	452.6	452.9	453.2
137.5°	469.0	469.4	469.5	469.7	469.9	470.1	470.3	470.8	471.3	471.8	472.3
140°	486.4	486.7	486.9	487.2	487.5	487.8	488.1	488.5	488.9	489.3	489.7
142.5°	503.3	503.6	503.8	504.1	504.4	504.7	505.0	505.3	505.6	505.9	506.2
145°	519.2	519.6	519.7	519.9	520.1	520.3	520.5	520.7	520.9	521.1	521.3
147.5°	533.4	533.7	533.8	534.0	534.2	534.4	534.6	534.8	535.0	535.2	535.4
150°	546.3	546.5	546.6	546.8	547.0	547.2	547.4	547.6	547.8	548.0	548.2
152.5°	557.8	557.9	557.9	558.0	558.1	558.2	558.3	558.7	559.1	559.6	560.0
155°	568.0	567.9	568.0	568.1	568.2	568.3	568.4	568.9	569.4	569.9	570.4
157.5°	577.9	577.9	577.9	577.8	577.7	577.6	577.5	578.1	578.7	579.3	579.9
160°	585.8	585.7	585.6	585.5	585.4	585.3	585.2	585.8	586.4	587.1	587.7
162.5°	592.7	592.5	592.5	592.4	592.3	592.2	592.1	592.8	593.5	594.2	594.9
165°	598.6	598.5	598.4	598.3	598.2	598.1	598.0	598.8	599.6	600.5	601.3
167.5°	603.2	603.0	603.0	603.0	603.0	603.0	603.0	603.8	604.6	605.5	606.3
170°	607.3	607.1	607.1	607.1	607.1	607.1	607.1	607.9	608.7	609.6	610.4
172.5°	609.7	609.4	609.5	609.6	609.7	609.8	609.9	610.7	611.5	612.3	613.1
175°	612.0	611.7	611.8	611.9	612.0	612.1	612.2	612.9	613.6	614.3	615.0
177.5°	612.9	612.6	612.7	612.8	612.9	613.0	613.1	613.9	614.7	615.5	616.3
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1548.9	1550.5	1544.2	1539.4	1552.1	1544.2	1544.2	1545.8	1542.6	1547.3	1545.8
5°	1461.9	1463.5	1452.4	1455.6	1449.3	1447.7	1446.1	1455.6	1454.0	1452.4	1455.6
7.5°	1376.5	1376.5	1371.7	1368.6	1368.6	1363.8	1370.1	1368.6	1371.7	1371.7	1376.5
10°	1305.3	1308.4	1300.5	1292.6	1291.0	1292.6	1292.6	1294.2	1295.8	1306.9	1305.3
12.5°	1246.7	1242.0	1240.4	1235.7	1227.8	1224.6	1221.4	1238.8	1234.1	1234.1	1234.1
15°	1181.9	1192.9	1191.4	1177.1	1174.0	1180.3	1177.1	1177.1	1192.9	1191.4	1189.8
17.5°	1147.1	1143.9	1140.7	1132.8	1134.4	1132.8	1134.4	1134.4	1143.9	1143.9	1143.9
20°	1107.5	1101.2	1101.2	1098.0	1098.0	1093.3	1099.6	1101.2	1107.5	1107.5	1109.1
22.5°	1072.7	1068.0	1068.0	1066.4	1069.5	1063.2	1069.5	1071.1	1071.1	1075.9	1075.9
25°	1042.6	1039.5	1039.5	1042.6	1042.6	1042.6	1042.6	1049.0	1044.2	1045.8	1044.2
27.5°	1015.7	1017.3	1018.9	1020.5	1018.9	1020.5	1022.1	1025.2	1026.8	1025.2	1022.1
30°	990.4	995.2	996.8	996.8	999.9	1001.5	1003.1	1003.1	1004.7	999.9	1003.1
32.5°	971.4	971.4	974.6	976.2	979.4	980.9	980.9	984.1	982.5	977.8	979.4
35°	944.5	944.5	950.9	954.0	958.8	957.2	958.8	958.8	960.4	957.2	952.5
37.5°	917.6	920.8	920.8	927.1	928.7	930.3	928.7	931.9	930.3	927.1	925.6
40°	886.0	884.4	886.0	890.8	892.3	892.3	892.3	895.5	895.5	895.5	893.9
42.5°	846.5	851.2	849.6	854.4	852.8	852.8	855.9	859.1	860.7	855.9	857.5
45°	808.5	808.5	811.6	811.6	813.2	813.2	819.6	816.4	819.6	816.4	818.0
47.5°	767.3	768.9	768.9	770.5	773.7	776.8	773.7	775.3	775.3	776.8	773.7
50°	721.5	721.5	724.6	729.4	735.7	732.5	731.0	737.3	732.5	732.5	729.4
52.5°	674.0	678.7	680.3	685.1	689.8	691.4	693.0	689.8	691.4	686.7	688.2
55°	628.1	629.7	636.0	640.8	645.5	645.5	643.9	645.5	647.1	640.8	640.8
57.5°	582.2	587.0	593.3	593.3	599.6	599.6	598.1	598.1	599.6	594.9	593.3
60°	533.2	537.9	545.8	545.8	555.3	556.9	553.8	550.6	550.6	545.8	547.4
62.5°	481.0	485.7	490.5	498.4	504.7	501.5	507.9	501.5	503.1	493.6	493.6
65°	435.1	436.7	444.6	452.5	452.5	455.7	452.5	454.1	449.3	449.3	443.0
67.5°	381.3	381.3	389.2	397.1	405.0	405.0	405.0	400.3	400.3	395.5	395.5
70°	333.8	332.3	340.2	344.9	349.7	351.2	348.1	346.5	343.3	338.6	337.0
72.5°	275.3	278.5	286.4	289.5	297.4	295.9	303.8	294.3	294.3	286.4	284.8
75°	223.1	226.2	234.2	238.9	243.7	243.7	248.4	243.7	237.3	234.2	232.6
77.5°	177.2	175.6	181.9	189.9	191.4	189.9	193.0	191.4	185.1	185.1	181.9
80°	126.6	131.3	137.6	136.1	142.4	140.8	140.8	137.6	137.6	132.9	136.1
82.5°	83.9	88.6	90.2	88.6	90.2	93.3	94.9	93.3	93.3	90.2	91.8
85°	44.3	44.3	47.5	49.0	47.5	47.5	49.0	53.8	50.6	47.5	50.6
87.5°	14.2	12.7	12.7	14.2	12.7	12.7	14.2	14.2	15.8	15.8	15.8
90°	12.8	12.9	13.1	13.3	13.5	13.7	13.5	13.3	13.1	12.9	12.8
92.5°	15.1	15.1	15.2	15.3	15.4	15.5	15.4	15.3	15.2	15.1	15.1
95°	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3	17.3
97.5°	18.2	18.3	18.4	18.5	18.6	18.7	18.6	18.5	18.4	18.3	18.2
100°	18.7	18.8	18.9	19.0	19.1	19.2	19.1	19.0	18.9	18.8	18.7
102.5°	18.7	18.8	19.0	19.2	19.4	19.6	19.4	19.2	19.0	18.8	18.7
105°	19.2	19.3	19.5	19.7	19.9	20.1	19.9	19.7	19.5	19.3	19.2
107.5°	107.2	100.6	87.3	74.0	60.7	47.4	60.7	74.0	87.3	100.6	107.2
110°	190.7	183.4	168.9	154.4	139.9	125.4	139.9	154.4	168.9	183.4	190.7

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	238.6	238.5	238.3	238.1	237.9	237.7	237.9	238.1	238.3	238.5	238.6
115°	266.4	266.6	267.0	267.4	267.8	268.2	267.8	267.4	267.0	266.6	266.4
117.5°	292.4	292.4	292.5	292.6	292.7	292.8	292.7	292.6	292.5	292.4	292.4
120°	318.4	318.4	318.4	318.4	318.4	318.4	318.4	318.4	318.4	318.4	318.4
122.5°	343.0	343.1	343.2	343.3	343.4	343.5	343.4	343.3	343.2	343.1	343.0
125°	365.8	365.9	366.1	366.3	366.5	366.7	366.5	366.3	366.1	365.9	365.8
127.5°	390.5	390.4	390.2	390.0	389.8	389.6	389.8	390.0	390.2	390.4	390.5
130°	412.4	412.3	412.1	411.8	411.6	411.4	411.6	411.8	412.1	412.3	412.4
132.5°	432.9	432.7	432.4	432.1	431.8	431.5	431.8	432.1	432.4	432.7	432.9
135°	453.4	453.2	452.9	452.6	452.3	452.0	452.3	452.6	452.9	453.2	453.4
137.5°	472.6	472.5	472.3	472.1	471.9	471.7	471.9	472.1	472.3	472.5	472.6
140°	489.9	489.8	489.6	489.4	489.2	489.0	489.2	489.4	489.6	489.8	489.9
142.5°	506.3	506.2	505.9	505.6	505.3	505.0	505.3	505.6	505.9	506.2	506.3
145°	521.4	521.4	521.4	521.4	521.4	521.4	521.4	521.4	521.4	521.4	521.4
147.5°	535.5	535.2	534.7	534.2	533.7	533.2	533.7	534.2	534.7	535.2	535.5
150°	548.3	548.1	547.8	547.5	547.2	546.9	547.2	547.5	547.8	548.1	548.3
152.5°	560.2	559.9	559.4	558.9	558.4	557.9	558.4	558.9	559.4	559.9	560.2
155°	570.6	570.3	569.7	569.1	568.5	567.9	568.5	569.1	569.7	570.3	570.6
157.5°	580.2	579.8	579.0	578.2	577.4	576.6	577.4	578.2	579.0	579.8	580.2
160°	588.0	587.6	586.9	586.2	585.5	584.8	585.5	586.2	586.9	587.6	588.0
162.5°	595.3	595.0	594.4	593.7	593.1	592.5	593.1	593.7	594.4	595.0	595.3
165°	601.7	601.3	600.6	599.9	599.2	598.5	599.2	599.9	600.6	601.3	601.7
167.5°	606.7	606.3	605.5	604.6	603.8	603.0	603.8	604.6	605.5	606.3	606.7
170°	610.8	610.4	609.6	608.7	607.9	607.1	607.9	608.7	609.6	610.4	610.8
172.5°	613.5	613.0	612.1	611.2	610.3	609.4	610.3	611.2	612.1	613.0	613.5
175°	615.3	614.9	614.1	613.3	612.5	611.7	612.5	613.3	614.1	614.9	615.3
177.5°	616.7	616.2	615.2	614.2	613.2	612.2	613.2	614.2	615.2	616.2	616.7
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8	1632.8
2.5°	1550.5	1553.7	1555.3	1548.9	1544.2	1552.1	1563.2	1571.1	1577.4	1585.3	1590.1
5°	1458.7	1469.8	1469.8	1473.0	1477.7	1485.6	1506.2	1520.4	1533.1	1542.6	1550.5
7.5°	1381.2	1389.1	1393.9	1401.8	1409.7	1420.8	1444.5	1465.1	1484.1	1495.1	1507.8
10°	1311.6	1317.9	1325.8	1330.6	1344.8	1360.7	1390.7	1408.1	1430.3	1447.7	1463.5
12.5°	1245.2	1267.3	1272.1	1270.5	1283.1	1300.5	1330.6	1357.5	1381.2	1398.6	1416.0
15°	1197.7	1205.6	1215.1	1213.5	1240.4	1245.2	1270.5	1302.1	1333.8	1344.8	1360.7
17.5°	1145.5	1158.1	1167.6	1172.4	1180.3	1197.7	1221.4	1245.2	1286.3	1287.9	1329.0
20°	1104.3	1117.0	1123.3	1129.7	1134.4	1155.0	1175.5	1202.4	1235.7	1253.1	1275.2
22.5°	1077.4	1083.8	1088.5	1093.3	1099.6	1110.7	1136.0	1166.0	1188.2	1207.2	1221.4
25°	1045.8	1052.1	1058.5	1061.6	1066.4	1072.7	1091.7	1115.4	1147.1	1159.7	1174.0
27.5°	1023.7	1023.7	1026.8	1026.8	1033.1	1039.5	1053.7	1075.9	1101.2	1117.0	1136.0
30°	999.9	998.3	999.9	998.3	996.8	1006.2	1018.9	1037.9	1055.3	1074.3	1086.9
32.5°	976.2	974.6	974.6	976.2	969.9	974.6	980.9	998.3	1017.3	1026.8	1041.1
35°	950.9	947.7	947.7	947.7	944.5	941.4	947.7	963.5	976.2	988.8	999.9
37.5°	925.6	920.8	920.8	917.6	914.5	909.7	909.7	922.4	939.8	944.5	958.8
40°	890.8	890.8	887.6	886.0	882.8	879.7	874.9	886.0	901.8	906.6	917.6
42.5°	855.9	851.2	849.6	849.6	849.6	844.9	841.7	849.6	859.1	867.0	873.3
45°	816.4	813.2	814.8	813.2	810.1	808.5	806.9	810.1	821.1	824.3	832.2
47.5°	773.7	772.1	772.1	770.5	768.9	770.5	764.2	772.1	775.3	778.4	784.7
50°	729.4	727.8	726.2	724.6	724.6	726.2	724.6	724.6	731.0	734.1	740.4
52.5°	685.1	680.3	680.3	678.7	678.7	675.6	678.7	680.3	683.5	686.7	689.8
55°	637.6	637.6	632.9	632.9	629.7	629.7	631.3	629.7	636.0	639.2	639.2
57.5°	591.7	585.4	587.0	583.8	580.7	579.1	579.1	582.2	585.4	585.4	588.6
60°	542.7	536.4	534.8	528.4	531.6	526.9	528.4	528.4	534.8	531.6	534.8
62.5°	493.6	485.7	481.0	477.8	477.8	479.4	476.2	474.6	477.8	481.0	487.3
65°	441.4	436.7	431.9	427.2	427.2	425.6	428.8	424.0	422.4	424.0	427.2
67.5°	387.6	382.9	378.1	373.4	375.0	370.2	367.1	371.8	368.6	370.2	373.4
70°	335.4	332.3	322.8	319.6	318.0	319.6	318.0	314.8	319.6	318.0	319.6
72.5°	283.2	280.0	275.3	267.4	267.4	265.8	264.2	264.2	262.6	262.6	262.6
75°	232.6	226.2	221.5	219.9	216.8	215.2	213.6	210.4	212.0	213.6	210.4
77.5°	180.4	172.5	170.9	170.9	166.1	166.1	167.7	166.1	164.5	164.5	164.5
80°	132.9	126.6	126.6	123.4	120.2	120.2	120.2	120.2	118.7	117.1	118.7
82.5°	85.4	83.9	82.3	82.3	85.4	79.1	82.3	80.7	79.1	79.1	77.5
85°	47.5	49.0	47.5	49.0	45.9	47.5	47.5	47.5	45.9	47.5	44.3
87.5°	17.4	17.4	17.4	19.0	19.0	19.0	19.0	19.0	20.6	19.0	19.0
90°	12.6	12.2	11.7	11.3	10.9	9.6	8.3	7.0	5.7	5.0	4.5
92.5°	14.7	14.0	13.3	12.6	11.9	11.0	10.1	9.2	8.3	7.8	8.1
95°	16.9	16.2	15.5	14.8	14.1	13.0	11.9	10.8	9.7	9.1	11.2
97.5°	17.8	17.0	16.2	15.4	14.6	19.8	25.0	30.1	35.3	37.9	39.3
100°	18.3	17.5	16.7	15.9	15.1	30.9	46.7	62.5	78.3	86.2	85.2
102.5°	20.4	23.7	27.1	30.4	33.8	51.4	69.0	86.7	104.3	113.1	112.4
105°	28.2	46.1	64.0	82.0	99.9	109.0	118.2	127.3	136.4	141.0	140.4
107.5°	115.0	130.6	146.2	161.8	177.4	175.9	174.4	172.9	171.4	170.6	170.1
110°	192.4	195.7	199.0	202.4	205.7	204.6	203.5	202.4	201.3	200.7	200.3

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	238.1	237.2	236.3	235.4	234.5	233.4	232.2	231.1	230.0	229.4	229.1
115°	265.9	264.9	263.8	262.8	261.8	260.9	260.0	259.1	258.2	257.7	257.4
117.5°	292.0	291.2	290.3	289.5	288.7	288.2	287.7	287.2	286.7	286.5	286.1
120°	318.0	317.2	316.3	315.5	314.7	314.4	314.1	313.8	313.5	313.4	312.9
122.5°	342.7	342.2	341.7	341.2	340.7	340.3	339.9	339.5	339.1	338.9	338.5
125°	365.7	365.5	365.3	365.1	364.9	364.5	364.1	363.7	363.3	363.1	362.7
127.5°	390.3	390.0	389.7	389.4	389.1	388.6	388.1	387.6	387.1	386.8	386.4
130°	412.2	411.8	411.3	410.9	410.5	410.1	409.7	409.3	408.9	408.7	408.3
132.5°	432.7	432.3	431.9	431.5	431.1	430.8	430.5	430.2	429.9	429.7	429.3
135°	453.2	452.9	452.6	452.3	452.0	451.6	451.2	450.8	450.4	450.2	449.9
137.5°	472.3	471.8	471.3	470.8	470.3	470.1	469.9	469.7	469.5	469.4	469.0
140°	489.7	489.3	488.9	488.5	488.1	487.8	487.5	487.2	486.9	486.7	486.4
142.5°	506.2	505.9	505.6	505.3	505.0	504.7	504.4	504.1	503.8	503.6	503.3
145°	521.3	521.1	520.9	520.7	520.5	520.3	520.1	519.9	519.7	519.6	519.2
147.5°	535.4	535.2	535.0	534.8	534.6	534.4	534.2	534.0	533.8	533.7	533.4
150°	548.2	548.0	547.8	547.6	547.4	547.2	547.0	546.8	546.6	546.5	546.3
152.5°	560.0	559.6	559.1	558.7	558.3	558.2	558.1	558.0	557.9	557.9	557.8
155°	570.4	569.9	569.4	568.9	568.4	568.3	568.2	568.1	568.0	567.9	568.0
157.5°	579.9	579.3	578.7	578.1	577.5	577.6	577.7	577.8	577.9	577.9	577.9
160°	587.7	587.1	586.4	585.8	585.2	585.3	585.4	585.5	585.6	585.7	585.8
162.5°	594.9	594.2	593.5	592.8	592.1	592.2	592.3	592.4	592.5	592.5	592.7
165°	601.3	600.5	599.6	598.8	598.0	598.1	598.2	598.3	598.4	598.5	598.6
167.5°	606.3	605.5	604.6	603.8	603.0	603.0	603.0	603.0	603.0	603.0	603.2
170°	610.4	609.6	608.7	607.9	607.1	607.1	607.1	607.1	607.1	607.1	607.3
172.5°	613.1	612.3	611.5	610.7	609.9	609.8	609.7	609.6	609.5	609.4	609.7
175°	615.0	614.3	613.6	612.9	612.2	612.1	612.0	611.9	611.8	611.7	612.0
177.5°	616.3	615.5	614.7	613.9	613.1	613.0	612.9	612.8	612.7	612.6	612.9
180°	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0	614.0

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1632.8	1632.8	1632.8	1632.8
2.5°	1598.0	1602.7	1618.5	1637.5
5°	1566.3	1579.0	1601.1	1631.2
7.5°	1531.5	1550.5	1582.2	1620.1
10°	1492.0	1518.9	1558.4	1605.9
12.5°	1449.3	1484.1	1534.7	1583.7
15°	1422.4	1457.2	1503.0	1556.8
17.5°	1370.1	1411.3	1458.7	1534.7
20°	1316.4	1362.2	1423.9	1499.9
22.5°	1275.2	1324.3	1382.8	1463.5
25°	1226.2	1276.8	1340.1	1423.9
27.5°	1174.0	1224.6	1295.8	1384.4
30°	1134.4	1183.5	1251.5	1346.4
32.5°	1086.9	1134.4	1205.6	1305.3
35°	1033.1	1086.9	1155.0	1256.2
37.5°	992.0	1041.1	1112.3	1208.8
40°	947.7	990.4	1060.0	1155.0
42.5°	900.2	947.7	1007.8	1102.8
45°	855.9	890.8	952.5	1042.6
47.5°	808.5	848.0	895.5	965.1
50°	757.9	791.1	843.3	890.8
52.5°	708.8	735.7	780.0	816.4
55°	656.6	683.5	716.7	738.9
57.5°	607.5	626.5	648.7	662.9
60°	547.4	566.4	580.7	594.9
62.5°	493.6	507.9	515.8	523.7
65°	438.3	446.2	450.9	457.2
67.5°	378.1	386.0	387.6	397.1
70°	322.8	324.3	327.5	332.3
72.5°	270.5	273.7	272.1	275.3
75°	216.8	219.9	216.8	219.9
77.5°	164.5	167.7	167.7	172.5
80°	118.7	120.2	121.8	121.8
82.5°	77.5	82.3	79.1	80.7
85°	44.3	45.9	45.9	47.5
87.5°	20.6	22.2	20.6	23.7
90°	3.5	2.5	1.5	0.5
92.5°	8.7	9.3	9.9	10.5
95°	15.3	19.5	23.6	27.8
97.5°	42.1	45.0	47.8	50.6
100°	83.2	81.1	79.1	77.1
102.5°	111.1	109.8	108.5	107.2
105°	139.3	138.2	137.0	135.9
107.5°	169.2	168.3	167.4	166.5
110°	199.5	198.7	197.9	197.1

TEST NUMBER: P1030762

CATALOG NUMBER: S123DIW-B1165D460UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	228.4	227.7	227.0	226.3
115°	256.8	256.2	255.6	255.0
117.5°	285.4	284.7	284.0	283.3
120°	312.0	311.1	310.2	309.3
122.5°	337.8	337.1	336.4	335.7
125°	361.9	361.0	360.2	359.4
127.5°	385.6	384.8	384.0	383.2
130°	407.5	406.7	405.9	405.1
132.5°	428.5	427.6	426.8	426.0
135°	449.3	448.7	448.1	447.5
137.5°	468.2	467.3	466.5	465.7
140°	485.8	485.2	484.6	484.0
142.5°	502.7	502.1	501.5	500.9
145°	518.5	517.8	517.1	516.4
147.5°	532.9	532.4	531.9	531.4
150°	546.0	545.7	545.4	545.1
152.5°	557.7	557.6	557.5	557.4
155°	568.2	568.4	568.6	568.8
157.5°	577.9	577.9	577.9	577.9
160°	585.9	586.0	586.1	586.2
162.5°	593.0	593.3	593.6	593.9
165°	598.9	599.2	599.5	599.8
167.5°	603.6	604.1	604.5	604.9
170°	607.7	608.2	608.6	609.0
172.5°	610.2	610.7	611.2	611.7
175°	612.5	613.0	613.5	614.0
177.5°	613.4	613.9	614.4	614.9
180°	614.0	614.0	614.0	614.0

(END OF REPORT)