

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030866

Luminaire Tested: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030866
REPORT IS A COMBINATION OF REPORTS P991521 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6559.0 lumens
Efficiency: N/A
Efficacy: 118.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36		
1	95	91	87	84	86	82	79	76	67	64	62	52	51	49	39	38	37	31		
2	87	79	74	69	78	72	67	63	59	55	52	46	44	42	34	33	32	26		
3	79	70	63	57	71	64	58	53	52	47	44	41	38	35	31	29	27	22		
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23	19		
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17		
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15		
7	56	45	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16	13		
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14	12		
9	49	37	29	25	44	34	27	23	28	23	19	22	19	16	17	15	13	11		
10	45	34	27	22	41	31	25	20	26	21	17	21	17	15	16	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8473	8473	8473	8473
5°	8480	9763	8504	7287
10°	8426	11815	8434	6363
15°	8309	14012	8376	5728
20°	8209	16132	8226	5270
25°	8059	16539	8078	5032
30°	7954	13664	7954	4876
35°	7822	9138	7773	4737
40°	7664	6596	7569	4526
45°	7466	5226	7250	4263
50°	6984	4437	6735	4005
55°	6454	3900	6191	3717
60°	5918	3395	5604	3415
65°	5330	2908	5072	3012
70°	4718	2414	4403	2538
75°	4032	1820	3774	1960
80°	3187	1216	2942	1288
85°	2200	559	1758	508

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13666 cd/sqm

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	1.2
10°-20°	248.7	3.8
20°-30°	418.4	6.4
30°-40°	472.9	7.2
40°-50°	423.5	6.5
50°-60°	341.9	5.2
60°-70°	238.2	3.6
70°-80°	125.0	1.9
80°-90°	32.7	0.5
90°-100°	48.4	0.7
100°-110°	233.8	3.6
110°-120°	572.9	8.7
120°-130°	727.3	11.1
130°-140°	776.9	11.8
140°-150°	726.5	11.1
150°-160°	586.0	8.9
160°-170°	378.2	5.8
170°-180°	130.3	2.0
0°-30°	744.5	11.4
0°-40°	1217.4	18.6
0°-60°	1982.7	30.2
0°-90°	2378.7	36.3
90°-120°	855.0	13.0
90°-150°	3085.8	47.0
90°-180°	4180.0	63.7
0°-180°	6559.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	787	787	787	787	787	
5°	786	935	789	698	786	75
15°	751	1392	757	569	751	212
25°	686	1652	688	503	686	317
35°	606	890	602	462	606	379
45°	503	481	488	392	503	384
55°	356	326	342	311	356	319
65°	220	212	210	220	220	220
75°	106	109	99	118	106	114
85°	23	25	18	23	23	26
90°	1	31	1	31	1	5
95°	62	39	62	39	62	74
105°	304	45	304	45	304	322
115°	570	599	570	599	570	562
125°	803	819	803	819	803	717
135°	999	1010	999	1010	999	769
145°	1153	1164	1153	1164	1153	722
155°	1270	1268	1270	1268	1270	585
165°	1340	1337	1340	1337	1340	379
175°	1371	1366	1371	1366	1371	130
180°	1371	1371	1371	1371	1371	

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	789.5	795.6	798.7	803.3	807.8	814.7	817.0	820.8	819.3	822.3	823.9
5°	786.5	797.2	806.3	817.7	828.4	836.1	843.7	855.9	865.0	866.6	873.4
7.5°	781.1	796.4	812.4	828.4	849.0	861.2	875.0	891.7	905.5	927.6	936.0
10°	774.3	795.6	818.5	840.6	868.9	887.9	904.7	932.9	961.2	984.0	1005.4
12.5°	763.6	790.3	820.0	852.8	889.5	911.6	934.5	971.8	1014.6	1049.6	1072.5
15°	750.6	784.2	822.3	857.4	897.8	939.0	963.4	1005.4	1066.4	1099.2	1158.0
17.5°	739.9	774.3	812.4	867.3	922.3	963.4	981.0	1058.0	1100.0	1154.9	1221.3
20°	723.2	766.6	815.5	870.4	941.3	966.5	1002.4	1080.2	1132.0	1203.7	1285.4
22.5°	705.6	752.1	810.9	868.1	947.4	974.1	1022.9	1084.7	1167.1	1238.1	1328.1
25°	686.5	736.9	796.4	864.3	942.1	981.0	1026.8	1103.0	1192.3	1281.5	1364.7
27.5°	667.5	722.4	784.2	852.1	927.6	973.4	1019.1	1098.5	1212.9	1309.8	1415.8
30°	649.2	704.1	765.9	835.3	914.6	958.9	1002.4	1101.5	1228.9	1338.0	1444.8
32.5°	629.3	685.8	750.6	808.6	888.7	936.0	984.8	1101.5	1238.8	1354.8	1452.4
35°	605.7	663.7	719.3	777.3	856.7	909.3	964.2	1093.9	1248.0	1360.1	1420.4
37.5°	582.8	633.9	682.0	738.4	821.6	878.0	941.3	1084.7	1243.4	1337.2	1354.0
40°	556.9	608.0	646.9	699.5	787.2	852.8	916.9	1072.5	1223.6	1283.1	1234.2
42.5°	531.7	572.1	605.7	656.8	752.1	816.2	885.6	1050.4	1184.7	1196.9	1087.0
45°	502.7	531.7	561.4	619.4	714.0	779.6	856.7	1018.4	1122.1	1087.0	948.2
47.5°	465.3	491.3	524.1	577.5	673.6	741.5	814.7	977.2	1031.3	958.1	806.3
50°	429.5	451.6	482.1	534.0	630.9	697.2	775.0	912.3	939.0	823.9	694.9
52.5°	393.6	410.4	440.1	492.0	588.9	653.0	723.9	846.0	830.7	707.1	592.7
55°	356.2	370.7	399.0	450.1	540.1	601.1	669.0	764.3	724.7	607.2	515.7
57.5°	319.6	334.9	363.9	406.6	491.3	550.8	604.9	679.7	620.2	526.3	445.5
60°	286.8	299.8	321.9	363.9	440.9	489.0	538.6	589.7	540.1	449.3	387.5
62.5°	252.5	264.7	285.3	323.4	389.8	432.5	472.2	514.1	459.2	392.9	337.9
65°	220.5	230.4	249.4	284.5	338.7	373.8	405.8	434.8	390.6	329.5	288.3
67.5°	191.5	199.9	215.9	247.2	292.9	318.1	344.0	368.4	331.1	282.2	247.2
70°	160.2	167.1	181.6	204.4	241.1	267.0	286.1	304.4	270.8	231.9	208.3
72.5°	132.7	139.6	148.8	172.4	197.6	213.6	234.2	244.1	225.0	193.0	169.3
75°	106.0	111.4	119.8	135.0	158.7	169.3	182.3	189.9	172.4	151.0	136.5
77.5°	83.1	85.4	91.5	102.2	118.2	130.4	140.4	144.9	132.7	119.0	106.8
80°	58.7	61.8	66.4	75.5	87.7	91.5	97.6	103.0	95.4	83.1	75.5
82.5°	38.9	42.7	45.0	48.8	56.4	61.0	62.6	67.1	60.3	55.7	52.6
85°	22.9	24.4	25.2	27.5	31.3	33.6	35.9	36.6	35.1	34.3	31.3
87.5°	11.4	11.4	11.4	13.0	13.7	15.3	16.0	16.0	16.0	15.3	14.5
90°	1.0	3.3	5.5	7.8	10.1	11.2	12.7	15.6	18.5	21.5	24.4
92.5°	23.4	22.0	20.7	19.3	18.0	17.3	18.3	20.4	22.4	24.5	26.5
95°	62.1	52.8	43.6	34.3	25.0	20.4	21.6	24.1	26.6	29.1	31.6
97.5°	113.1	106.8	100.4	94.1	87.8	84.6	78.8	67.3	55.7	44.2	32.6
100°	172.2	176.7	181.2	185.7	190.2	192.5	174.8	139.5	104.2	68.9	33.6
102.5°	239.4	242.3	245.3	248.2	251.1	252.6	232.9	193.5	154.2	114.8	75.4
105°	303.6	306.1	308.6	311.1	313.6	314.8	304.6	284.2	263.9	243.5	223.1
107.5°	371.8	373.8	375.9	377.9	380.0	381.0	382.7	386.1	389.5	392.9	396.3
110°	440.1	441.9	443.7	445.5	447.3	448.2	449.4	451.9	454.4	456.9	459.4

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	505.3	506.9	508.5	510.0	511.6	512.4	513.6	516.1	518.6	521.1	523.6
115°	569.5	570.9	572.2	573.6	574.9	575.6	576.6	578.7	580.7	582.8	584.8
117.5°	632.6	634.2	635.8	637.4	639.0	639.8	640.4	641.5	642.6	643.8	644.9
120°	690.7	692.7	694.8	696.8	698.9	699.9	700.2	700.9	701.6	702.2	702.9
122.5°	749.8	751.4	753.0	754.5	756.1	756.9	757.4	758.3	759.2	760.1	761.0
125°	802.8	804.6	806.4	808.2	810.0	810.9	811.4	812.3	813.2	814.1	815.0
127.5°	855.7	857.5	859.3	861.2	863.0	863.9	864.5	865.6	866.7	867.9	869.0
130°	904.6	906.4	908.2	910.1	911.9	912.8	913.3	914.2	915.1	916.0	916.9
132.5°	951.5	953.3	955.1	956.9	958.7	959.6	959.9	960.6	961.3	962.0	962.7
135°	999.4	1000.8	1002.1	1003.5	1004.8	1005.5	1006.0	1006.9	1007.8	1008.7	1009.6
137.5°	1040.1	1041.9	1043.7	1045.6	1047.4	1048.3	1048.5	1049.0	1049.4	1049.9	1050.3
140°	1080.9	1082.3	1083.6	1085.0	1086.3	1087.0	1087.3	1088.0	1088.7	1089.3	1090.0
142.5°	1118.6	1120.0	1121.3	1122.7	1124.0	1124.7	1125.0	1125.7	1126.4	1127.0	1127.7
145°	1153.2	1154.8	1156.4	1157.9	1159.5	1160.3	1160.5	1161.0	1161.5	1161.9	1162.4
147.5°	1186.8	1187.9	1189.1	1190.2	1191.3	1191.9	1192.1	1192.6	1193.1	1193.5	1194.0
150°	1217.4	1218.1	1218.7	1219.4	1220.1	1220.4	1220.6	1221.1	1221.6	1222.0	1222.5
152.5°	1244.9	1245.1	1245.3	1245.6	1245.8	1245.9	1246.0	1246.2	1246.5	1246.7	1246.9
155°	1270.4	1269.9	1269.5	1269.0	1268.5	1268.3	1268.4	1268.6	1268.9	1269.1	1269.3
157.5°	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.6	1290.4	1290.1	1289.9	1289.7
160°	1309.1	1308.9	1308.7	1308.4	1308.2	1308.1	1308.0	1307.7	1307.5	1307.2	1307.0
162.5°	1326.4	1325.7	1325.0	1324.3	1323.6	1323.3	1323.2	1323.0	1322.7	1322.5	1322.3
165°	1339.6	1338.9	1338.3	1337.6	1336.9	1336.6	1336.5	1336.3	1336.0	1335.8	1335.6
167.5°	1350.8	1349.9	1349.0	1348.1	1347.2	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8
170°	1360.0	1359.1	1358.2	1357.3	1356.4	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9
172.5°	1366.1	1365.0	1363.8	1362.7	1361.6	1361.0	1361.1	1361.3	1361.6	1361.8	1362.0
175°	1371.2	1370.1	1368.9	1367.8	1366.7	1366.1	1366.2	1366.4	1366.7	1366.9	1367.1
177.5°	1373.3	1372.2	1371.0	1369.9	1368.8	1368.2	1368.3	1368.5	1368.8	1369.0	1369.2
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	829.2	830.7	836.1	839.9	847.5	846.7	846.7	846.0	843.7	847.5	849.8
5°	887.2	900.1	901.7	918.4	919.2	926.1	930.6	926.8	936.0	935.2	928.4
7.5°	958.9	976.4	984.8	1000.8	1019.1	1014.6	1032.1	1035.2	1033.6	1041.3	1046.6
10°	1037.4	1068.0	1089.3	1119.1	1126.7	1131.3	1142.7	1152.6	1172.5	1157.2	1167.1
12.5°	1127.5	1149.6	1177.8	1225.1	1248.7	1264.0	1269.3	1276.2	1289.9	1281.5	1282.3
15°	1203.0	1232.7	1280.8	1339.5	1346.4	1365.5	1360.9	1402.1	1421.9	1392.2	1408.9
17.5°	1281.5	1321.2	1378.4	1429.5	1458.5	1471.5	1483.7	1523.4	1521.8	1517.3	1521.1
20°	1331.9	1396.7	1467.7	1535.6	1544.0	1553.9	1586.7	1603.5	1600.4	1613.4	1621.8
22.5°	1402.8	1471.5	1547.0	1592.0	1611.1	1622.5	1648.5	1659.1	1663.7	1666.8	1661.4
25°	1462.3	1535.6	1591.3	1630.9	1642.4	1648.5	1656.9	1659.9	1657.6	1652.3	1656.9
27.5°	1502.8	1561.5	1599.6	1617.9	1611.8	1601.9	1585.9	1575.2	1551.6	1540.1	1553.9
30°	1519.5	1545.5	1556.9	1526.4	1495.9	1471.5	1441.0	1384.5	1340.3	1353.2	1335.7
32.5°	1492.8	1476.1	1421.1	1342.6	1318.9	1279.3	1193.1	1126.7	1129.0	1093.9	1108.4
35°	1414.3	1338.0	1234.2	1115.2	1084.0	1062.6	968.0	953.5	923.0	890.2	899.4
37.5°	1275.4	1164.1	1038.2	950.5	903.9	857.4	804.0	772.0	753.7	739.9	750.6
40°	1106.1	970.3	866.6	788.0	748.3	718.6	682.0	649.9	629.3	627.0	630.9
42.5°	939.8	825.4	730.0	655.3	642.3	607.2	583.6	558.4	552.3	542.4	547.7
45°	795.6	702.6	624.0	563.0	547.7	538.6	509.6	493.5	486.7	480.6	489.7
47.5°	691.1	593.5	536.3	499.6	484.4	469.1	453.1	442.4	437.1	437.9	437.1
50°	590.4	518.7	468.4	440.1	431.0	420.3	407.3	400.5	398.2	391.3	396.7
52.5°	508.0	456.2	421.1	394.4	387.5	379.9	369.2	365.4	360.1	358.5	358.5
55°	441.7	401.2	373.0	355.5	347.1	341.0	334.9	330.3	326.5	326.5	326.5
57.5°	389.8	354.7	334.1	318.9	315.8	309.7	302.8	302.8	297.5	296.7	299.0
60°	345.6	314.3	298.3	285.3	280.7	279.2	272.3	272.3	270.8	267.0	270.0
62.5°	300.6	277.7	263.9	254.0	249.4	249.4	244.1	240.3	240.3	241.1	239.5
65°	259.4	242.6	230.4	222.7	220.5	217.4	216.6	213.6	211.3	212.1	211.3
67.5°	222.7	209.8	201.4	195.3	191.5	189.9	187.7	187.7	186.1	186.9	183.1
70°	189.9	177.0	170.1	164.0	162.5	162.5	159.4	160.2	158.7	161.0	159.4
72.5°	156.4	146.5	141.1	138.8	137.3	136.5	135.0	133.5	132.7	134.3	133.5
75°	126.6	118.2	114.4	112.9	111.4	111.4	110.6	109.8	109.1	109.1	109.1
77.5°	98.4	93.1	88.5	90.0	87.7	88.5	86.2	86.2	87.0	86.2	86.2
80°	72.5	68.7	68.7	67.1	64.1	65.6	65.6	63.3	62.6	64.1	61.8
82.5°	48.1	47.3	45.8	45.0	43.5	44.2	43.5	42.7	42.0	43.5	42.0
85°	28.2	28.2	27.5	25.9	27.5	26.7	25.9	25.9	25.2	25.2	25.2
87.5°	14.5	13.0	13.0	12.2	13.0	11.4	12.2	11.4	10.7	11.4	10.7
90°	25.3	26.2	27.1	28.0	28.5	28.7	29.2	29.7	30.1	30.6	30.1
92.5°	28.1	29.7	31.2	32.8	33.6	33.7	33.9	34.2	34.4	34.6	34.4
95°	33.2	34.8	36.3	37.9	38.7	38.7	38.7	38.7	38.7	38.7	38.7
97.5°	34.4	36.2	38.0	39.8	40.7	40.8	41.1	41.3	41.6	41.8	41.6
100°	35.4	37.2	39.1	40.9	41.8	41.9	42.1	42.4	42.6	42.8	42.6
102.5°	67.9	60.5	53.0	45.5	41.8	42.0	42.5	42.9	43.4	43.8	43.4
105°	183.0	143.0	102.9	62.8	42.8	43.0	43.5	43.9	44.4	44.8	44.4
107.5°	361.4	326.6	291.7	256.8	239.4	224.6	194.9	165.2	135.6	105.9	135.6
110°	451.9	444.5	437.0	429.5	425.8	409.6	377.3	344.9	312.6	280.2	312.6

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	525.6	527.7	529.7	531.8	532.8	532.6	532.1	531.7	531.2	530.8	531.2
115°	587.0	589.3	591.5	593.8	594.9	595.4	596.3	597.2	598.1	599.0	598.1
117.5°	646.7	648.5	650.3	652.1	653.0	653.1	653.3	653.6	653.8	654.0	653.8
120°	704.7	706.5	708.4	710.2	711.1	711.1	711.1	711.1	711.1	711.1	711.1
122.5°	762.1	763.3	764.4	765.5	766.1	766.2	766.4	766.7	766.9	767.1	766.9
125°	815.4	815.9	816.3	816.8	817.0	817.2	817.7	818.2	818.6	819.1	818.6
127.5°	869.7	870.3	871.0	871.7	872.0	871.8	871.3	870.9	870.4	870.0	870.4
130°	917.8	918.7	919.6	920.5	920.9	920.7	920.2	919.8	919.3	918.9	919.3
132.5°	963.6	964.5	965.4	966.3	966.8	966.5	965.8	965.1	964.4	963.7	964.4
135°	1010.3	1010.9	1011.6	1012.3	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1010.3
137.5°	1051.4	1052.6	1053.7	1054.8	1055.4	1055.2	1054.7	1054.3	1053.8	1053.4	1053.8
140°	1090.9	1091.8	1092.7	1093.6	1094.1	1093.9	1093.4	1093.0	1092.5	1092.1	1092.5
142.5°	1128.4	1129.1	1129.8	1130.5	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1128.4
145°	1162.8	1163.3	1163.7	1164.2	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4
147.5°	1194.4	1194.9	1195.3	1195.8	1196.0	1195.4	1194.3	1193.2	1192.0	1190.9	1192.0
150°	1222.9	1223.4	1223.8	1224.3	1224.5	1224.2	1223.5	1222.8	1222.2	1221.5	1222.2
152.5°	1247.8	1248.7	1249.6	1250.5	1251.0	1250.4	1249.3	1248.2	1247.0	1245.9	1247.0
155°	1270.4	1271.6	1272.7	1273.8	1274.4	1273.7	1272.4	1271.0	1269.7	1268.3	1269.7
157.5°	1291.1	1292.4	1293.8	1295.1	1295.8	1294.9	1293.1	1291.3	1289.5	1287.7	1289.5
160°	1308.4	1309.7	1311.1	1312.4	1313.1	1312.3	1310.7	1309.2	1307.6	1306.0	1307.6
162.5°	1323.9	1325.5	1327.0	1328.6	1329.4	1328.7	1327.4	1326.0	1324.7	1323.3	1324.7
165°	1337.4	1339.2	1341.0	1342.8	1343.7	1342.9	1341.3	1339.8	1338.2	1336.6	1338.2
167.5°	1348.6	1350.4	1352.2	1354.0	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1348.6
170°	1357.7	1359.5	1361.4	1363.2	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1357.7
172.5°	1363.8	1365.6	1367.5	1369.3	1370.2	1369.2	1367.1	1365.1	1363.0	1361.0	1363.0
175°	1368.7	1370.3	1371.9	1373.5	1374.3	1373.4	1371.6	1369.7	1367.9	1366.1	1367.9
177.5°	1371.0	1372.8	1374.6	1376.4	1377.3	1376.2	1373.9	1371.6	1369.4	1367.1	1369.4
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	843.7	846.0	839.9	838.3	838.3	841.4	839.1	818.5	822.3	817.7	816.2
5°	936.7	932.2	926.1	923.0	919.2	908.5	907.8	884.1	879.5	864.3	857.4
7.5°	1039.0	1035.2	1016.8	1014.6	1013.0	1003.1	977.9	952.8	934.5	916.9	900.1
10°	1155.7	1144.2	1135.8	1119.1	1110.7	1096.9	1064.1	1040.5	1009.2	982.5	947.4
12.5°	1296.0	1283.1	1254.8	1242.6	1232.0	1193.8	1161.0	1134.3	1073.3	1055.0	1011.5
15°	1399.0	1371.6	1368.5	1341.8	1340.3	1298.3	1235.8	1206.8	1159.5	1092.4	1047.4
17.5°	1510.4	1486.0	1466.9	1434.9	1430.3	1390.6	1344.9	1273.9	1222.0	1158.0	1100.8
20°	1592.0	1579.0	1546.2	1533.3	1506.6	1473.0	1425.7	1338.0	1274.7	1210.6	1140.4
22.5°	1656.9	1643.9	1617.9	1600.4	1585.1	1541.7	1485.2	1410.5	1323.5	1239.6	1167.1
25°	1656.1	1652.3	1641.6	1633.2	1621.8	1589.7	1542.4	1470.7	1373.8	1281.5	1180.9
27.5°	1562.3	1572.9	1591.3	1600.4	1598.1	1593.5	1566.8	1506.6	1419.6	1309.8	1196.9
30°	1367.0	1405.9	1440.2	1486.0	1499.7	1533.3	1548.5	1514.2	1444.8	1342.6	1217.5
32.5°	1133.6	1190.0	1264.8	1289.9	1333.4	1398.3	1470.7	1483.7	1440.2	1361.6	1230.4
35°	929.9	976.4	1034.4	1074.1	1113.0	1218.2	1309.8	1389.1	1403.6	1351.7	1227.4
37.5°	769.7	802.5	853.6	887.2	923.0	1013.0	1141.2	1244.2	1316.6	1318.2	1219.0
40°	653.7	668.2	712.5	736.9	771.2	849.0	963.4	1097.7	1203.7	1252.6	1196.9
42.5°	553.8	572.9	609.5	627.8	649.9	717.8	793.3	920.7	1051.9	1156.4	1155.7
45°	494.3	508.0	524.8	540.1	565.3	605.7	691.9	787.2	913.1	1031.3	1077.9
47.5°	441.7	454.6	471.4	476.0	492.8	530.9	583.6	666.7	784.2	901.7	989.4
50°	397.4	408.1	419.6	427.9	435.6	466.8	506.5	576.7	670.5	784.2	893.3
52.5°	363.1	370.7	380.6	385.2	392.1	415.0	445.5	497.4	574.4	678.2	784.2
55°	331.1	336.4	342.5	350.1	353.2	370.0	393.6	437.9	495.1	588.1	688.8
57.5°	301.3	303.6	307.4	312.0	315.8	330.3	350.9	380.6	431.0	502.7	598.1
60°	267.8	273.9	276.1	280.7	283.0	294.5	310.5	335.6	374.5	436.3	508.0
62.5°	239.5	243.3	247.2	249.4	254.8	258.6	271.6	294.5	326.5	372.3	437.1
65°	214.4	215.9	218.2	220.5	222.0	226.6	238.8	254.0	278.4	318.9	369.2
67.5°	185.4	186.9	189.9	190.7	192.2	198.3	205.2	218.2	238.8	269.3	310.5
70°	157.1	159.4	161.0	162.5	164.8	167.1	174.7	185.4	201.4	222.7	254.8
72.5°	132.7	135.0	135.0	136.5	135.8	138.8	146.5	154.1	164.8	182.3	210.5
75°	108.3	108.3	109.8	110.6	111.4	114.4	117.5	123.6	132.0	145.7	163.2
77.5°	85.4	84.7	86.2	86.2	86.2	88.5	91.5	94.6	99.9	109.8	123.6
80°	62.6	62.6	64.1	64.8	63.3	64.1	65.6	68.7	72.5	79.3	87.0
82.5°	41.2	44.2	43.5	44.2	43.5	45.0	45.8	46.5	48.1	51.1	56.4
85°	25.2	25.2	25.2	25.9	25.2	25.9	25.9	25.9	26.7	28.2	30.5
87.5°	10.7	10.7	10.7	11.4	10.7	10.7	11.4	10.7	11.4	11.4	12.2
90°	29.7	29.2	28.7	28.5	28.0	27.1	26.2	25.3	24.4	21.5	18.5
92.5°	34.2	33.9	33.7	33.6	32.8	31.2	29.7	28.1	26.5	24.5	22.4
95°	38.7	38.7	38.7	38.7	37.9	36.3	34.8	33.2	31.6	29.1	26.6
97.5°	41.3	41.1	40.8	40.7	39.8	38.0	36.2	34.4	32.6	44.2	55.7
100°	42.4	42.1	41.9	41.8	40.9	39.1	37.2	35.4	33.6	68.9	104.2
102.5°	42.9	42.5	42.0	41.8	45.5	53.0	60.5	67.9	75.4	114.8	154.2
105°	43.9	43.5	43.0	42.8	62.8	102.9	143.0	183.0	223.1	243.5	263.9
107.5°	165.2	194.9	224.6	239.4	256.8	291.7	326.6	361.4	396.3	392.9	389.5
110°	344.9	377.3	409.6	425.8	429.5	437.0	444.5	451.9	459.4	456.9	454.4

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	531.7	532.1	532.6	532.8	531.8	529.7	527.7	525.6	523.6	521.1	518.6
115°	597.2	596.3	595.4	594.9	593.8	591.5	589.3	587.0	584.8	582.8	580.7
117.5°	653.6	653.3	653.1	653.0	652.1	650.3	648.5	646.7	644.9	643.8	642.6
120°	711.1	711.1	711.1	711.1	710.2	708.4	706.5	704.7	702.9	702.2	701.6
122.5°	766.7	766.4	766.2	766.1	765.5	764.4	763.3	762.1	761.0	760.1	759.2
125°	818.2	817.7	817.2	817.0	816.8	816.3	815.9	815.4	815.0	814.1	813.2
127.5°	870.9	871.3	871.8	872.0	871.7	871.0	870.3	869.7	869.0	867.9	866.7
130°	919.8	920.2	920.7	920.9	920.5	919.6	918.7	917.8	916.9	916.0	915.1
132.5°	965.1	965.8	966.5	966.8	966.3	965.4	964.5	963.6	962.7	962.0	961.3
135°	1010.9	1011.6	1012.3	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1008.7	1007.8
137.5°	1054.3	1054.7	1055.2	1055.4	1054.8	1053.7	1052.6	1051.4	1050.3	1049.9	1049.4
140°	1093.0	1093.4	1093.9	1094.1	1093.6	1092.7	1091.8	1090.9	1090.0	1089.3	1088.7
142.5°	1129.1	1129.8	1130.5	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1127.0	1126.4
145°	1164.4	1164.4	1164.4	1164.4	1164.2	1163.7	1163.3	1162.8	1162.4	1161.9	1161.5
147.5°	1193.2	1194.3	1195.4	1196.0	1195.8	1195.3	1194.9	1194.4	1194.0	1193.5	1193.1
150°	1222.8	1223.5	1224.2	1224.5	1224.3	1223.8	1223.4	1222.9	1222.5	1222.0	1221.6
152.5°	1248.2	1249.3	1250.4	1251.0	1250.5	1249.6	1248.7	1247.8	1246.9	1246.7	1246.5
155°	1271.0	1272.4	1273.7	1274.4	1273.8	1272.7	1271.6	1270.4	1269.3	1269.1	1268.9
157.5°	1291.3	1293.1	1294.9	1295.8	1295.1	1293.8	1292.4	1291.1	1289.7	1289.9	1290.1
160°	1309.2	1310.7	1312.3	1313.1	1312.4	1311.1	1309.7	1308.4	1307.0	1307.2	1307.5
162.5°	1326.0	1327.4	1328.7	1329.4	1328.6	1327.0	1325.5	1323.9	1322.3	1322.5	1322.7
165°	1339.8	1341.3	1342.9	1343.7	1342.8	1341.0	1339.2	1337.4	1335.6	1335.8	1336.0
167.5°	1350.4	1352.2	1354.0	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1346.8	1346.8
170°	1359.5	1361.4	1363.2	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1355.9	1355.9
172.5°	1365.1	1367.1	1369.2	1370.2	1369.3	1367.5	1365.6	1363.8	1362.0	1361.8	1361.6
175°	1369.7	1371.6	1373.4	1374.3	1373.5	1371.9	1370.3	1368.7	1367.1	1366.9	1366.7
177.5°	1371.6	1373.9	1376.2	1377.3	1376.4	1374.6	1372.8	1371.0	1369.2	1369.0	1368.8
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	808.6	806.3	806.3	804.8	800.2	791.8	791.0	792.6	788.0	783.4	776.6
5°	848.3	833.8	829.2	824.6	815.5	800.2	794.1	788.8	780.4	770.5	759.8
7.5°	881.8	861.2	855.1	846.7	828.4	807.1	793.3	781.9	770.5	756.7	743.8
10°	923.8	894.0	879.5	867.3	842.2	812.4	791.8	775.0	756.7	739.9	723.2
12.5°	971.1	923.0	918.4	888.7	859.7	815.5	790.3	765.9	741.5	720.9	703.3
15°	1010.7	958.1	939.0	919.2	863.5	808.6	784.2	756.7	728.5	706.4	680.4
17.5°	1035.9	992.4	952.0	925.3	867.3	818.5	771.2	739.9	710.2	679.7	658.3
20°	1066.4	1003.1	968.0	932.2	875.0	810.9	763.6	724.7	688.1	660.6	634.7
22.5°	1096.9	1011.5	982.5	943.6	876.5	803.3	749.9	711.0	669.0	641.5	613.3
25°	1093.9	1023.7	975.7	942.9	861.2	796.4	733.8	688.1	649.2	614.1	585.8
27.5°	1096.2	1010.0	961.2	923.0	850.5	786.5	717.1	669.0	628.6	592.0	562.2
30°	1096.9	989.4	946.7	900.9	830.7	762.8	698.0	649.2	606.4	566.8	540.1
32.5°	1094.7	972.6	919.2	878.0	799.4	739.9	675.9	624.0	580.5	543.9	518.7
35°	1089.3	952.8	891.0	839.1	767.4	707.1	655.3	601.9	555.3	521.8	492.8
37.5°	1074.8	931.4	861.2	810.1	730.0	669.0	623.2	579.0	534.0	494.3	469.9
40°	1064.1	902.4	831.5	775.8	689.6	630.1	592.0	550.0	505.8	469.9	446.3
42.5°	1039.7	875.0	801.0	734.6	649.9	588.9	553.0	519.5	481.3	446.3	424.9
45°	1000.1	845.2	763.6	696.5	606.4	548.5	515.7	488.2	454.6	421.1	399.7
47.5°	944.4	802.5	723.9	656.8	563.7	505.0	472.2	451.6	424.9	396.7	378.4
50°	884.1	756.0	683.5	617.1	522.5	465.3	433.3	414.2	396.7	370.7	353.2
52.5°	805.5	706.4	637.0	573.6	478.3	423.4	395.1	381.4	363.1	344.8	329.5
55°	729.3	642.3	585.1	524.8	434.8	383.7	356.2	341.7	331.1	315.8	303.6
57.5°	640.8	582.8	530.2	475.2	394.4	347.8	321.9	304.4	297.5	290.6	279.2
60°	559.2	514.9	472.2	426.4	352.4	310.5	285.3	271.6	264.7	260.1	252.5
62.5°	484.4	450.1	413.5	376.8	309.7	271.6	252.5	238.8	232.7	231.9	225.0
65°	412.7	388.3	358.5	322.7	270.0	236.5	218.2	209.8	202.9	202.9	197.6
67.5°	341.0	324.2	300.6	275.4	234.2	202.9	186.1	178.5	174.7	174.7	170.9
70°	283.8	272.3	251.0	228.8	193.0	169.3	156.4	149.5	147.2	148.0	144.9
72.5°	230.4	218.2	200.6	184.6	157.9	140.4	131.2	123.6	119.8	120.5	119.8
75°	178.5	172.4	157.1	144.9	123.6	111.4	103.0	99.2	96.1	96.9	95.4
77.5°	134.3	125.1	116.7	108.3	95.4	85.4	78.6	74.8	72.5	72.5	72.5
80°	91.5	90.0	83.1	78.6	67.9	60.3	54.9	54.2	51.9	51.9	51.9
82.5°	59.5	55.7	51.9	48.8	42.7	38.1	35.9	34.3	33.6	32.8	34.3
85°	32.8	30.5	29.0	25.9	23.6	21.4	19.1	18.3	17.5	18.3	17.5
87.5°	13.0	10.7	10.7	9.9	9.2	8.4	8.4	6.9	6.9	6.1	6.1
90°	15.6	12.7	11.2	10.1	7.8	5.5	3.3	1.0	3.3	5.5	7.8
92.5°	20.4	18.3	17.3	18.0	19.3	20.7	22.0	23.4	22.0	20.7	19.3
95°	24.1	21.6	20.4	25.0	34.3	43.6	52.8	62.1	52.8	43.6	34.3
97.5°	67.3	78.8	84.6	87.8	94.1	100.4	106.8	113.1	106.8	100.4	94.1
100°	139.5	174.8	192.5	190.2	185.7	181.2	176.7	172.2	176.7	181.2	185.7
102.5°	193.5	232.9	252.6	251.1	248.2	245.3	242.3	239.4	242.3	245.3	248.2
105°	284.2	304.6	314.8	313.6	311.1	308.6	306.1	303.6	306.1	308.6	311.1
107.5°	386.1	382.7	381.0	380.0	377.9	375.9	373.8	371.8	373.8	375.9	377.9
110°	451.9	449.4	448.2	447.3	445.5	443.7	441.9	440.1	441.9	443.7	445.5

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	516.1	513.6	512.4	511.6	510.0	508.5	506.9	505.3	506.9	508.5	510.0
115°	578.7	576.6	575.6	574.9	573.6	572.2	570.9	569.5	570.9	572.2	573.6
117.5°	641.5	640.4	639.8	639.0	637.4	635.8	634.2	632.6	634.2	635.8	637.4
120°	700.9	700.2	699.9	698.9	696.8	694.8	692.7	690.7	692.7	694.8	696.8
122.5°	758.3	757.4	756.9	756.1	754.5	753.0	751.4	749.8	751.4	753.0	754.5
125°	812.3	811.4	810.9	810.0	808.2	806.4	804.6	802.8	804.6	806.4	808.2
127.5°	865.6	864.5	863.9	863.0	861.2	859.3	857.5	855.7	857.5	859.3	861.2
130°	914.2	913.3	912.8	911.9	910.1	908.2	906.4	904.6	906.4	908.2	910.1
132.5°	960.6	959.9	959.6	958.7	956.9	955.1	953.3	951.5	953.3	955.1	956.9
135°	1006.9	1006.0	1005.5	1004.8	1003.5	1002.1	1000.8	999.4	1000.8	1002.1	1003.5
137.5°	1049.0	1048.5	1048.3	1047.4	1045.6	1043.7	1041.9	1040.1	1041.9	1043.7	1045.6
140°	1088.0	1087.3	1087.0	1086.3	1085.0	1083.6	1082.3	1080.9	1082.3	1083.6	1085.0
142.5°	1125.7	1125.0	1124.7	1124.0	1122.7	1121.3	1120.0	1118.6	1120.0	1121.3	1122.7
145°	1161.0	1160.5	1160.3	1159.5	1157.9	1156.4	1154.8	1153.2	1154.8	1156.4	1157.9
147.5°	1192.6	1192.1	1191.9	1191.3	1190.2	1189.1	1187.9	1186.8	1187.9	1189.1	1190.2
150°	1221.1	1220.6	1220.4	1220.1	1219.4	1218.7	1218.1	1217.4	1218.1	1218.7	1219.4
152.5°	1246.2	1246.0	1245.9	1245.8	1245.6	1245.3	1245.1	1244.9	1245.1	1245.3	1245.6
155°	1268.6	1268.4	1268.3	1268.5	1269.0	1269.5	1269.9	1270.4	1269.9	1269.5	1269.0
157.5°	1290.4	1290.6	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7	1290.7
160°	1307.7	1308.0	1308.1	1308.2	1308.4	1308.7	1308.9	1309.1	1308.9	1308.7	1308.4
162.5°	1323.0	1323.2	1323.3	1323.6	1324.3	1325.0	1325.7	1326.4	1325.7	1325.0	1324.3
165°	1336.3	1336.5	1336.6	1336.9	1337.6	1338.3	1338.9	1339.6	1338.9	1338.3	1337.6
167.5°	1346.8	1346.8	1346.8	1347.2	1348.1	1349.0	1349.9	1350.8	1349.9	1349.0	1348.1
170°	1355.9	1355.9	1355.9	1356.4	1357.3	1358.2	1359.1	1360.0	1359.1	1358.2	1357.3
172.5°	1361.3	1361.1	1361.0	1361.6	1362.7	1363.8	1365.0	1366.1	1365.0	1363.8	1362.7
175°	1366.4	1366.2	1366.1	1366.7	1367.8	1368.9	1370.1	1371.2	1370.1	1368.9	1367.8
177.5°	1368.5	1368.3	1368.2	1368.8	1369.9	1371.0	1372.2	1373.3	1372.2	1371.0	1369.9
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	775.0	774.3	775.8	771.2	763.6	759.8	749.1	746.8	746.0	746.8	747.6
5°	753.7	752.9	750.6	743.0	733.8	727.0	714.0	713.2	708.7	704.1	706.4
7.5°	733.1	730.0	725.4	715.5	703.3	695.7	685.0	677.4	671.3	667.5	664.4
10°	712.5	707.9	703.3	690.4	675.1	663.7	650.7	644.6	637.7	634.7	631.6
12.5°	685.8	681.2	672.8	657.6	648.4	633.9	620.9	614.8	611.0	604.9	601.1
15°	664.4	655.3	650.7	634.7	615.6	614.1	590.4	588.9	581.3	581.3	575.2
17.5°	640.0	633.1	624.8	608.7	595.0	581.3	569.1	564.5	557.6	556.1	553.0
20°	616.4	607.2	604.2	588.1	573.6	556.9	543.9	539.3	536.3	533.2	535.5
22.5°	592.0	584.3	576.7	562.2	551.5	534.7	527.1	522.5	518.0	516.4	517.2
25°	568.3	561.4	553.8	539.3	527.9	514.1	507.3	505.0	502.7	502.7	501.9
27.5°	545.4	538.6	531.7	518.7	507.3	497.4	492.0	489.7	487.4	489.0	490.5
30°	521.8	515.7	509.6	498.1	489.0	479.8	476.8	475.2	474.5	478.3	478.3
32.5°	500.4	495.1	490.5	479.8	470.7	463.0	460.7	461.5	462.3	464.6	466.1
35°	478.3	474.5	469.9	460.7	453.1	446.3	447.0	447.0	448.5	452.4	455.4
37.5°	458.5	453.1	449.3	441.7	435.6	429.5	431.8	434.0	435.6	440.1	441.7
40°	434.8	432.5	429.5	421.8	416.5	415.7	416.5	418.0	421.1	423.4	425.7
42.5°	415.7	412.7	408.9	402.8	398.2	399.0	399.7	401.2	402.8	406.6	408.9
45°	394.4	392.1	389.0	383.7	379.9	380.6	381.4	381.4	382.9	387.5	389.0
47.5°	370.7	371.5	367.7	362.3	360.1	360.1	360.1	361.6	365.4	366.9	367.7
50°	347.8	346.3	345.6	340.2	338.7	337.9	338.7	339.5	344.8	344.0	346.3
52.5°	323.4	323.4	322.7	319.6	317.3	317.3	315.8	319.6	321.1	322.7	325.0
55°	299.8	297.5	296.7	295.2	292.2	291.4	292.9	297.5	299.0	300.6	302.8
57.5°	273.9	273.9	272.3	270.0	270.0	270.0	270.0	273.1	275.4	276.9	281.5
60°	250.2	247.2	244.9	244.9	244.9	244.1	248.7	248.7	253.3	254.0	255.5
62.5°	222.0	220.5	218.9	219.7	218.9	220.5	222.0	225.0	225.8	228.1	230.4
65°	195.3	195.3	193.8	198.3	195.3	195.3	199.1	199.1	200.6	202.9	206.0
67.5°	169.3	170.1	168.6	168.6	170.1	170.9	171.6	174.7	175.4	178.5	182.3
70°	142.6	144.2	144.9	143.4	144.9	146.5	148.0	148.8	151.8	153.3	155.6
72.5°	119.0	120.5	118.2	119.0	119.8	121.3	122.1	123.6	125.1	129.7	131.2
75°	95.4	94.6	93.8	96.9	95.4	98.4	99.2	99.2	100.7	104.5	106.0
77.5°	73.2	73.2	74.0	72.5	74.8	74.0	74.8	77.0	79.3	79.3	85.4
80°	51.1	52.6	52.6	52.6	53.4	54.2	52.6	56.4	57.2	57.2	59.5
82.5°	32.8	33.6	32.8	34.3	34.3	35.9	35.1	35.9	37.4	38.9	39.7
85°	17.5	17.5	19.1	19.1	18.3	19.1	18.3	19.1	20.6	20.6	21.4
87.5°	6.1	6.1	6.1	6.1	6.9	6.1	6.9	6.9	6.1	6.1	8.4
90°	10.1	11.2	12.7	15.6	18.5	21.5	24.4	25.3	26.2	27.1	28.0
92.5°	18.0	17.3	18.3	20.4	22.4	24.5	26.5	28.1	29.7	31.2	32.8
95°	25.0	20.4	21.6	24.1	26.6	29.1	31.6	33.2	34.8	36.3	37.9
97.5°	87.8	84.6	78.8	67.3	55.7	44.2	32.6	34.4	36.2	38.0	39.8
100°	190.2	192.5	174.8	139.5	104.2	68.9	33.6	35.4	37.2	39.1	40.9
102.5°	251.1	252.6	232.9	193.5	154.2	114.8	75.4	67.9	60.5	53.0	45.5
105°	313.6	314.8	304.6	284.2	263.9	243.5	223.1	183.0	143.0	102.9	62.8
107.5°	380.0	381.0	382.7	386.1	389.5	392.9	396.3	361.4	326.6	291.7	256.8
110°	447.3	448.2	449.4	451.9	454.4	456.9	459.4	451.9	444.5	437.0	429.5

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	511.6	512.4	513.6	516.1	518.6	521.1	523.6	525.6	527.7	529.7	531.8
115°	574.9	575.6	576.6	578.7	580.7	582.8	584.8	587.0	589.3	591.5	593.8
117.5°	639.0	639.8	640.4	641.5	642.6	643.8	644.9	646.7	648.5	650.3	652.1
120°	698.9	699.9	700.2	700.9	701.6	702.2	702.9	704.7	706.5	708.4	710.2
122.5°	756.1	756.9	757.4	758.3	759.2	760.1	761.0	762.1	763.3	764.4	765.5
125°	810.0	810.9	811.4	812.3	813.2	814.1	815.0	815.4	815.9	816.3	816.8
127.5°	863.0	863.9	864.5	865.6	866.7	867.9	869.0	869.7	870.3	871.0	871.7
130°	911.9	912.8	913.3	914.2	915.1	916.0	916.9	917.8	918.7	919.6	920.5
132.5°	958.7	959.6	959.9	960.6	961.3	962.0	962.7	963.6	964.5	965.4	966.3
135°	1004.8	1005.5	1006.0	1006.9	1007.8	1008.7	1009.6	1010.3	1010.9	1011.6	1012.3
137.5°	1047.4	1048.3	1048.5	1049.0	1049.4	1049.9	1050.3	1051.4	1052.6	1053.7	1054.8
140°	1086.3	1087.0	1087.3	1088.0	1088.7	1089.3	1090.0	1090.9	1091.8	1092.7	1093.6
142.5°	1124.0	1124.7	1125.0	1125.7	1126.4	1127.0	1127.7	1128.4	1129.1	1129.8	1130.5
145°	1159.5	1160.3	1160.5	1161.0	1161.5	1161.9	1162.4	1162.8	1163.3	1163.7	1164.2
147.5°	1191.3	1191.9	1192.1	1192.6	1193.1	1193.5	1194.0	1194.4	1194.9	1195.3	1195.8
150°	1220.1	1220.4	1220.6	1221.1	1221.6	1222.0	1222.5	1222.9	1223.4	1223.8	1224.3
152.5°	1245.8	1245.9	1246.0	1246.2	1246.5	1246.7	1246.9	1247.8	1248.7	1249.6	1250.5
155°	1268.5	1268.3	1268.4	1268.6	1268.9	1269.1	1269.3	1270.4	1271.6	1272.7	1273.8
157.5°	1290.7	1290.7	1290.6	1290.4	1290.1	1289.9	1289.7	1291.1	1292.4	1293.8	1295.1
160°	1308.2	1308.1	1308.0	1307.7	1307.5	1307.2	1307.0	1308.4	1309.7	1311.1	1312.4
162.5°	1323.6	1323.3	1323.2	1323.0	1322.7	1322.5	1322.3	1323.9	1325.5	1327.0	1328.6
165°	1336.9	1336.6	1336.5	1336.3	1336.0	1335.8	1335.6	1337.4	1339.2	1341.0	1342.8
167.5°	1347.2	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8	1348.6	1350.4	1352.2	1354.0
170°	1356.4	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9	1357.7	1359.5	1361.4	1363.2
172.5°	1361.6	1361.0	1361.1	1361.3	1361.6	1361.8	1362.0	1363.8	1365.6	1367.5	1369.3
175°	1366.7	1366.1	1366.2	1366.4	1366.7	1366.9	1367.1	1368.7	1370.3	1371.9	1373.5
177.5°	1368.8	1368.2	1368.3	1368.5	1368.8	1369.0	1369.2	1371.0	1372.8	1374.6	1376.4
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	746.8	747.6	744.5	742.2	748.3	744.5	744.5	745.3	743.8	746.0	745.3
5°	704.8	705.6	700.3	701.8	698.7	698.0	697.2	701.8	701.0	700.3	701.8
7.5°	663.7	663.7	661.4	659.8	659.8	657.6	660.6	659.8	661.4	661.4	663.7
10°	629.3	630.9	627.0	623.2	622.5	623.2	623.2	624.0	624.8	630.1	629.3
12.5°	601.1	598.8	598.1	595.8	592.0	590.4	588.9	597.3	595.0	595.0	595.0
15°	569.8	575.2	574.4	567.5	566.0	569.1	567.5	567.5	575.2	574.4	573.6
17.5°	553.0	551.5	550.0	546.2	546.9	546.2	546.9	546.9	551.5	551.5	551.5
20°	534.0	530.9	530.9	529.4	529.4	527.1	530.2	530.9	534.0	534.0	534.7
22.5°	517.2	514.9	514.9	514.1	515.7	512.6	515.7	516.4	516.4	518.7	518.7
25°	502.7	501.2	501.2	502.7	502.7	502.7	502.7	505.8	503.5	504.2	503.5
27.5°	489.7	490.5	491.3	492.0	491.3	492.0	492.8	494.3	495.1	494.3	492.8
30°	477.5	479.8	480.6	480.6	482.1	482.9	483.6	483.6	484.4	482.1	483.6
32.5°	468.4	468.4	469.9	470.7	472.2	473.0	473.0	474.5	473.7	471.4	472.2
35°	455.4	455.4	458.5	460.0	462.3	461.5	462.3	462.3	463.0	461.5	459.2
37.5°	442.4	444.0	444.0	447.0	447.8	448.5	447.8	449.3	448.5	447.0	446.3
40°	427.2	426.4	427.2	429.5	430.2	430.2	430.2	431.8	431.8	431.8	431.0
42.5°	408.1	410.4	409.6	411.9	411.2	411.2	412.7	414.2	415.0	412.7	413.5
45°	389.8	389.8	391.3	391.3	392.1	392.1	395.1	393.6	395.1	393.6	394.4
47.5°	370.0	370.7	370.7	371.5	373.0	374.5	373.0	373.8	373.8	374.5	373.0
50°	347.8	347.8	349.4	351.7	354.7	353.2	352.4	355.5	353.2	353.2	351.7
52.5°	325.0	327.3	328.0	330.3	332.6	333.4	334.1	332.6	333.4	331.1	331.8
55°	302.8	303.6	306.7	308.9	311.2	311.2	310.5	311.2	312.0	308.9	308.9
57.5°	280.7	283.0	286.1	286.1	289.1	289.1	288.3	288.3	289.1	286.8	286.1
60°	257.1	259.4	263.2	263.2	267.8	268.5	267.0	265.5	265.5	263.2	263.9
62.5°	231.9	234.2	236.5	240.3	243.3	241.8	244.9	241.8	242.6	238.0	238.0
65°	209.8	210.5	214.4	218.2	218.2	219.7	218.2	218.9	216.6	216.6	213.6
67.5°	183.8	183.8	187.7	191.5	195.3	195.3	195.3	193.0	193.0	190.7	190.7
70°	161.0	160.2	164.0	166.3	168.6	169.3	167.8	167.1	165.5	163.2	162.5
72.5°	132.7	134.3	138.1	139.6	143.4	142.6	146.5	141.9	141.9	138.1	137.3
75°	107.6	109.1	112.9	115.2	117.5	117.5	119.8	117.5	114.4	112.9	112.1
77.5°	85.4	84.7	87.7	91.5	92.3	91.5	93.1	92.3	89.3	89.3	87.7
80°	61.0	63.3	66.4	65.6	68.7	67.9	67.9	66.4	66.4	64.1	65.6
82.5°	40.4	42.7	43.5	42.7	43.5	45.0	45.8	45.0	45.0	43.5	44.2
85°	21.4	21.4	22.9	23.6	22.9	22.9	23.6	25.9	24.4	22.9	24.4
87.5°	6.9	6.1	6.1	6.9	6.1	6.1	6.9	6.9	7.6	7.6	7.6
90°	28.5	28.7	29.2	29.7	30.1	30.6	30.1	29.7	29.2	28.7	28.5
92.5°	33.6	33.7	33.9	34.2	34.4	34.6	34.4	34.2	33.9	33.7	33.6
95°	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7	38.7
97.5°	40.7	40.8	41.1	41.3	41.6	41.8	41.6	41.3	41.1	40.8	40.7
100°	41.8	41.9	42.1	42.4	42.6	42.8	42.6	42.4	42.1	41.9	41.8
102.5°	41.8	42.0	42.5	42.9	43.4	43.8	43.4	42.9	42.5	42.0	41.8
105°	42.8	43.0	43.5	43.9	44.4	44.8	44.4	43.9	43.5	43.0	42.8
107.5°	239.4	224.6	194.9	165.2	135.6	105.9	135.6	165.2	194.9	224.6	239.4
110°	425.8	409.6	377.3	344.9	312.6	280.2	312.6	344.9	377.3	409.6	425.8

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	532.8	532.6	532.1	531.7	531.2	530.8	531.2	531.7	532.1	532.6	532.8
115°	594.9	595.4	596.3	597.2	598.1	599.0	598.1	597.2	596.3	595.4	594.9
117.5°	653.0	653.1	653.3	653.6	653.8	654.0	653.8	653.6	653.3	653.1	653.0
120°	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1	711.1
122.5°	766.1	766.2	766.4	766.7	766.9	767.1	766.9	766.7	766.4	766.2	766.1
125°	817.0	817.2	817.7	818.2	818.6	819.1	818.6	818.2	817.7	817.2	817.0
127.5°	872.0	871.8	871.3	870.9	870.4	870.0	870.4	870.9	871.3	871.8	872.0
130°	920.9	920.7	920.2	919.8	919.3	918.9	919.3	919.8	920.2	920.7	920.9
132.5°	966.8	966.5	965.8	965.1	964.4	963.7	964.4	965.1	965.8	966.5	966.8
135°	1012.6	1012.3	1011.6	1010.9	1010.3	1009.6	1010.3	1010.9	1011.6	1012.3	1012.6
137.5°	1055.4	1055.2	1054.7	1054.3	1053.8	1053.4	1053.8	1054.3	1054.7	1055.2	1055.4
140°	1094.1	1093.9	1093.4	1093.0	1092.5	1092.1	1092.5	1093.0	1093.4	1093.9	1094.1
142.5°	1130.8	1130.5	1129.8	1129.1	1128.4	1127.7	1128.4	1129.1	1129.8	1130.5	1130.8
145°	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4	1164.4
147.5°	1196.0	1195.4	1194.3	1193.2	1192.0	1190.9	1192.0	1193.2	1194.3	1195.4	1196.0
150°	1224.5	1224.2	1223.5	1222.8	1222.2	1221.5	1222.2	1222.8	1223.5	1224.2	1224.5
152.5°	1251.0	1250.4	1249.3	1248.2	1247.0	1245.9	1247.0	1248.2	1249.3	1250.4	1251.0
155°	1274.4	1273.7	1272.4	1271.0	1269.7	1268.3	1269.7	1271.0	1272.4	1273.7	1274.4
157.5°	1295.8	1294.9	1293.1	1291.3	1289.5	1287.7	1289.5	1291.3	1293.1	1294.9	1295.8
160°	1313.1	1312.3	1310.7	1309.2	1307.6	1306.0	1307.6	1309.2	1310.7	1312.3	1313.1
162.5°	1329.4	1328.7	1327.4	1326.0	1324.7	1323.3	1324.7	1326.0	1327.4	1328.7	1329.4
165°	1343.7	1342.9	1341.3	1339.8	1338.2	1336.6	1338.2	1339.8	1341.3	1342.9	1343.7
167.5°	1354.9	1354.0	1352.2	1350.4	1348.6	1346.8	1348.6	1350.4	1352.2	1354.0	1354.9
170°	1364.1	1363.2	1361.4	1359.5	1357.7	1355.9	1357.7	1359.5	1361.4	1363.2	1364.1
172.5°	1370.2	1369.2	1367.1	1365.1	1363.0	1361.0	1363.0	1365.1	1367.1	1369.2	1370.2
175°	1374.3	1373.4	1371.6	1369.7	1367.9	1366.1	1367.9	1369.7	1371.6	1373.4	1374.3
177.5°	1377.3	1376.2	1373.9	1371.6	1369.4	1367.1	1369.4	1371.6	1373.9	1376.2	1377.3
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2	787.2
2.5°	747.6	749.1	749.9	746.8	744.5	748.3	753.7	757.5	760.5	764.3	766.6
5°	703.3	708.7	708.7	710.2	712.5	716.3	726.2	733.1	739.2	743.8	747.6
7.5°	665.9	669.8	672.0	675.9	679.7	685.0	696.5	706.4	715.5	720.9	727.0
10°	632.4	635.4	639.2	641.5	648.4	656.0	670.5	678.9	689.6	698.0	705.6
12.5°	600.3	611.0	613.3	612.5	618.7	627.0	641.5	654.5	665.9	674.3	682.7
15°	577.5	581.3	585.8	585.1	598.1	600.3	612.5	627.8	643.1	648.4	656.0
17.5°	552.3	558.4	563.0	565.3	569.1	577.5	588.9	600.3	620.2	620.9	640.8
20°	532.5	538.6	541.6	544.7	546.9	556.9	566.8	579.7	595.8	604.2	614.8
22.5°	519.5	522.5	524.8	527.1	530.2	535.5	547.7	562.2	572.9	582.0	588.9
25°	504.2	507.3	510.3	511.9	514.1	517.2	526.3	537.8	553.0	559.2	566.0
27.5°	493.5	493.5	495.1	495.1	498.1	501.2	508.0	518.7	530.9	538.6	547.7
30°	482.1	481.3	482.1	481.3	480.6	485.2	491.3	500.4	508.8	518.0	524.1
32.5°	470.7	469.9	469.9	470.7	467.6	469.9	473.0	481.3	490.5	495.1	501.9
35°	458.5	456.9	456.9	456.9	455.4	453.9	456.9	464.6	470.7	476.8	482.1
37.5°	446.3	444.0	444.0	442.4	440.9	438.6	438.6	444.7	453.1	455.4	462.3
40°	429.5	429.5	427.9	427.2	425.7	424.1	421.8	427.2	434.8	437.1	442.4
42.5°	412.7	410.4	409.6	409.6	409.6	407.3	405.8	409.6	414.2	418.0	421.1
45°	393.6	392.1	392.9	392.1	390.6	389.8	389.0	390.6	395.9	397.4	401.2
47.5°	373.0	372.3	372.3	371.5	370.7	371.5	368.4	372.3	373.8	375.3	378.4
50°	351.7	350.9	350.1	349.4	349.4	350.1	349.4	349.4	352.4	354.0	357.0
52.5°	330.3	328.0	328.0	327.3	327.3	325.7	327.3	328.0	329.5	331.1	332.6
55°	307.4	307.4	305.1	305.1	303.6	303.6	304.4	303.6	306.7	308.2	308.2
57.5°	285.3	282.2	283.0	281.5	280.0	279.2	279.2	280.7	282.2	282.2	283.8
60°	261.6	258.6	257.8	254.8	256.3	254.0	254.8	254.8	257.8	256.3	257.8
62.5°	238.0	234.2	231.9	230.4	230.4	231.1	229.6	228.8	230.4	231.9	234.9
65°	212.8	210.5	208.3	206.0	206.0	205.2	206.7	204.4	203.7	204.4	206.0
67.5°	186.9	184.6	182.3	180.0	180.8	178.5	177.0	179.3	177.7	178.5	180.0
70°	161.7	160.2	155.6	154.1	153.3	154.1	153.3	151.8	154.1	153.3	154.1
72.5°	136.5	135.0	132.7	128.9	128.9	128.2	127.4	127.4	126.6	126.6	126.6
75°	112.1	109.1	106.8	106.0	104.5	103.7	103.0	101.5	102.2	103.0	101.5
77.5°	87.0	83.1	82.4	82.4	80.1	80.1	80.9	80.1	79.3	79.3	79.3
80°	64.1	61.0	61.0	59.5	58.0	58.0	58.0	58.0	57.2	56.4	57.2
82.5°	41.2	40.4	39.7	39.7	41.2	38.1	39.7	38.9	38.1	38.1	37.4
85°	22.9	23.6	22.9	23.6	22.1	22.9	22.9	22.9	22.1	22.9	21.4
87.5°	8.4	8.4	8.4	9.2	9.2	9.2	9.2	9.2	9.9	9.2	9.2
90°	28.0	27.1	26.2	25.3	24.4	21.5	18.5	15.6	12.7	11.2	10.1
92.5°	32.8	31.2	29.7	28.1	26.5	24.5	22.4	20.4	18.3	17.3	18.0
95°	37.9	36.3	34.8	33.2	31.6	29.1	26.6	24.1	21.6	20.4	25.0
97.5°	39.8	38.0	36.2	34.4	32.6	44.2	55.7	67.3	78.8	84.6	87.8
100°	40.9	39.1	37.2	35.4	33.6	68.9	104.2	139.5	174.8	192.5	190.2
102.5°	45.5	53.0	60.5	67.9	75.4	114.8	154.2	193.5	232.9	252.6	251.1
105°	62.8	102.9	143.0	183.0	223.1	243.5	263.9	284.2	304.6	314.8	313.6
107.5°	256.8	291.7	326.6	361.4	396.3	392.9	389.5	386.1	382.7	381.0	380.0
110°	429.5	437.0	444.5	451.9	459.4	456.9	454.4	451.9	449.4	448.2	447.3

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	531.8	529.7	527.7	525.6	523.6	521.1	518.6	516.1	513.6	512.4	511.6
115°	593.8	591.5	589.3	587.0	584.8	582.8	580.7	578.7	576.6	575.6	574.9
117.5°	652.1	650.3	648.5	646.7	644.9	643.8	642.6	641.5	640.4	639.8	639.0
120°	710.2	708.4	706.5	704.7	702.9	702.2	701.6	700.9	700.2	699.9	698.9
122.5°	765.5	764.4	763.3	762.1	761.0	760.1	759.2	758.3	757.4	756.9	756.1
125°	816.8	816.3	815.9	815.4	815.0	814.1	813.2	812.3	811.4	810.9	810.0
127.5°	871.7	871.0	870.3	869.7	869.0	867.9	866.7	865.6	864.5	863.9	863.0
130°	920.5	919.6	918.7	917.8	916.9	916.0	915.1	914.2	913.3	912.8	911.9
132.5°	966.3	965.4	964.5	963.6	962.7	962.0	961.3	960.6	959.9	959.6	958.7
135°	1012.3	1011.6	1010.9	1010.3	1009.6	1008.7	1007.8	1006.9	1006.0	1005.5	1004.8
137.5°	1054.8	1053.7	1052.6	1051.4	1050.3	1049.9	1049.4	1049.0	1048.5	1048.3	1047.4
140°	1093.6	1092.7	1091.8	1090.9	1090.0	1089.3	1088.7	1088.0	1087.3	1087.0	1086.3
142.5°	1130.5	1129.8	1129.1	1128.4	1127.7	1127.0	1126.4	1125.7	1125.0	1124.7	1124.0
145°	1164.2	1163.7	1163.3	1162.8	1162.4	1161.9	1161.5	1161.0	1160.5	1160.3	1159.5
147.5°	1195.8	1195.3	1194.9	1194.4	1194.0	1193.5	1193.1	1192.6	1192.1	1191.9	1191.3
150°	1224.3	1223.8	1223.4	1222.9	1222.5	1222.0	1221.6	1221.1	1220.6	1220.4	1220.1
152.5°	1250.5	1249.6	1248.7	1247.8	1246.9	1246.7	1246.5	1246.2	1246.0	1245.9	1245.8
155°	1273.8	1272.7	1271.6	1270.4	1269.3	1269.1	1268.9	1268.6	1268.4	1268.3	1268.5
157.5°	1295.1	1293.8	1292.4	1291.1	1289.7	1289.9	1290.1	1290.4	1290.6	1290.7	1290.7
160°	1312.4	1311.1	1309.7	1308.4	1307.0	1307.2	1307.5	1307.7	1308.0	1308.1	1308.2
162.5°	1328.6	1327.0	1325.5	1323.9	1322.3	1322.5	1322.7	1323.0	1323.2	1323.3	1323.6
165°	1342.8	1341.0	1339.2	1337.4	1335.6	1335.8	1336.0	1336.3	1336.5	1336.6	1336.9
167.5°	1354.0	1352.2	1350.4	1348.6	1346.8	1346.8	1346.8	1346.8	1346.8	1346.8	1347.2
170°	1363.2	1361.4	1359.5	1357.7	1355.9	1355.9	1355.9	1355.9	1355.9	1355.9	1356.4
172.5°	1369.3	1367.5	1365.6	1363.8	1362.0	1361.8	1361.6	1361.3	1361.1	1361.0	1361.6
175°	1373.5	1371.9	1370.3	1368.7	1367.1	1366.9	1366.7	1366.4	1366.2	1366.1	1366.7
177.5°	1376.4	1374.6	1372.8	1371.0	1369.2	1369.0	1368.8	1368.5	1368.3	1368.2	1368.8
180°	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2	1371.2

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	787.2	787.2	787.2	787.2
2.5°	770.5	772.7	780.4	789.5
5°	755.2	761.3	772.0	786.5
7.5°	738.4	747.6	762.8	781.1
10°	719.3	732.3	751.4	774.3
12.5°	698.7	715.5	739.9	763.6
15°	685.8	702.6	724.7	750.6
17.5°	660.6	680.4	703.3	739.9
20°	634.7	656.8	686.5	723.2
22.5°	614.8	638.5	666.7	705.6
25°	591.2	615.6	646.1	686.5
27.5°	566.0	590.4	624.8	667.5
30°	546.9	570.6	603.4	649.2
32.5°	524.1	546.9	581.3	629.3
35°	498.1	524.1	556.9	605.7
37.5°	478.3	501.9	536.3	582.8
40°	456.9	477.5	511.1	556.9
42.5°	434.0	456.9	485.9	531.7
45°	412.7	429.5	459.2	502.7
47.5°	389.8	408.9	431.8	465.3
50°	365.4	381.4	406.6	429.5
52.5°	341.7	354.7	376.1	393.6
55°	316.6	329.5	345.6	356.2
57.5°	292.9	302.1	312.8	319.6
60°	263.9	273.1	280.0	286.8
62.5°	238.0	244.9	248.7	252.5
65°	211.3	215.1	217.4	220.5
67.5°	182.3	186.1	186.9	191.5
70°	155.6	156.4	157.9	160.2
72.5°	130.4	132.0	131.2	132.7
75°	104.5	106.0	104.5	106.0
77.5°	79.3	80.9	80.9	83.1
80°	57.2	58.0	58.7	58.7
82.5°	37.4	39.7	38.1	38.9
85°	21.4	22.1	22.1	22.9
87.5°	9.9	10.7	9.9	11.4
90°	7.8	5.5	3.3	1.0
92.5°	19.3	20.7	22.0	23.4
95°	34.3	43.6	52.8	62.1
97.5°	94.1	100.4	106.8	113.1
100°	185.7	181.2	176.7	172.2
102.5°	248.2	245.3	242.3	239.4
105°	311.1	308.6	306.1	303.6
107.5°	377.9	375.9	373.8	371.8
110°	445.5	443.7	441.9	440.1

TEST NUMBER: P1030866

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	510.0	508.5	506.9	505.3
115°	573.6	572.2	570.9	569.5
117.5°	637.4	635.8	634.2	632.6
120°	696.8	694.8	692.7	690.7
122.5°	754.5	753.0	751.4	749.8
125°	808.2	806.4	804.6	802.8
127.5°	861.2	859.3	857.5	855.7
130°	910.1	908.2	906.4	904.6
132.5°	956.9	955.1	953.3	951.5
135°	1003.5	1002.1	1000.8	999.4
137.5°	1045.6	1043.7	1041.9	1040.1
140°	1085.0	1083.6	1082.3	1080.9
142.5°	1122.7	1121.3	1120.0	1118.6
145°	1157.9	1156.4	1154.8	1153.2
147.5°	1190.2	1189.1	1187.9	1186.8
150°	1219.4	1218.7	1218.1	1217.4
152.5°	1245.6	1245.3	1245.1	1244.9
155°	1269.0	1269.5	1269.9	1270.4
157.5°	1290.7	1290.7	1290.7	1290.7
160°	1308.4	1308.7	1308.9	1309.1
162.5°	1324.3	1325.0	1325.7	1326.4
165°	1337.6	1338.3	1338.9	1339.6
167.5°	1348.1	1349.0	1349.9	1350.8
170°	1357.3	1358.2	1359.1	1360.0
172.5°	1362.7	1363.8	1365.0	1366.1
175°	1367.8	1368.9	1370.1	1371.2
177.5°	1369.9	1371.0	1372.2	1373.3
180°	1371.2	1371.2	1371.2	1371.2

(END OF REPORT)