

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030940

Luminaire Tested: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030940
REPORT IS A COMBINATION OF REPORTS P991850 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7397.0 lumens
Efficiency: N/A
Efficacy: 109.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			44
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43			38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37			32
3	81	71	64	59	74	66	59	54	55	50	47	45	42	39	36	33	31			27
4	74	63	56	50	67	58	52	46	49	44	40	40	36	33	32	29	27			23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24			20
6	62	51	43	37	57	47	40	35	39	34	30	33	29	25	26	23	21			18
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19			16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17			14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15			13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11591	11591	11591	11591
5°	11599	13354	11632	9967
10°	11525	16161	11536	8704
15°	11365	19167	11458	7834
20°	11229	22066	11253	7209
25°	11025	22623	11050	6883
30°	10880	18690	10880	6669
35°	10699	12500	10632	6480
40°	10483	9023	10354	6191
45°	10212	7148	9918	5831
50°	9552	6070	9214	5478
55°	8830	5334	8471	5084
60°	8095	4644	7666	4671
65°	7288	3977	6935	4120
70°	6452	3302	6022	3473
75°	5516	2489	5158	2681
80°	4359	1661	4023	1762
85°	3007	762	2401	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18693 cd/sqm

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	1.4
10°-20°	340.1	4.6
20°-30°	572.3	7.7
30°-40°	646.8	8.7
40°-50°	579.3	7.8
50°-60°	467.6	6.3
60°-70°	325.9	4.4
70°-80°	171.0	2.3
80°-90°	43.7	0.6
90°-100°	47.9	0.6
100°-110°	231.8	3.1
110°-120°	568.0	7.7
120°-130°	721.0	9.7
130°-140°	770.3	10.4
140°-150°	720.3	9.7
150°-160°	581.0	7.9
160°-170°	374.9	5.1
170°-180°	129.2	1.7
0°-30°	1018.4	13.8
0°-40°	1665.2	22.5
0°-60°	2712.1	36.7
0°-90°	3252.7	44.0
90°-120°	847.7	11.5
90°-150°	3059.2	41.4
90°-180°	4144.0	56.0
0°-180°	7397.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1077	1077	1077	1077	1077	
5°	1076	1279	1079	955	1076	102
15°	1027	1904	1035	778	1027	290
25°	939	2260	941	688	939	433
35°	828	1218	823	631	828	518
45°	688	657	668	536	688	526
55°	487	447	468	426	487	436
65°	302	290	287	300	302	300
75°	145	149	136	161	145	156
85°	31	34	25	31	31	36
90°	1	30	1	30	1	6
95°	62	38	62	38	62	74
105°	301	44	301	44	301	319
115°	565	594	565	594	565	558
125°	796	812	796	812	796	711
135°	991	1001	991	1001	991	763
145°	1143	1154	1143	1154	1143	716
155°	1259	1257	1259	1257	1259	580
165°	1328	1325	1328	1325	1328	375
175°	1359	1354	1359	1354	1359	129
180°	1359	1359	1359	1359	1359	

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1079.9	1088.3	1092.5	1098.7	1105.0	1114.4	1117.5	1122.7	1120.6	1124.8	1126.9
5°	1075.8	1090.4	1102.9	1118.6	1133.2	1143.6	1154.0	1170.7	1183.2	1185.3	1194.7
7.5°	1068.5	1089.3	1111.2	1133.2	1161.3	1178.0	1196.8	1219.8	1238.5	1268.8	1280.3
10°	1059.1	1088.3	1119.6	1149.9	1188.5	1214.5	1237.5	1276.1	1314.7	1346.0	1375.2
12.5°	1044.5	1081.0	1121.7	1166.5	1216.6	1246.9	1278.2	1329.3	1387.8	1435.8	1467.1
15°	1026.7	1072.6	1124.8	1172.8	1228.1	1284.5	1317.8	1375.2	1458.7	1503.6	1583.9
17.5°	1012.1	1059.1	1111.2	1186.4	1261.5	1317.8	1341.8	1447.2	1504.6	1579.7	1670.5
20°	989.2	1048.6	1115.4	1190.5	1287.6	1322.0	1371.1	1477.5	1548.4	1646.5	1758.2
22.5°	965.2	1028.8	1109.2	1187.4	1295.9	1332.5	1399.2	1483.8	1596.4	1693.5	1816.6
25°	939.1	1007.9	1089.3	1182.2	1288.6	1341.8	1404.5	1508.8	1630.9	1753.0	1866.7
27.5°	913.0	988.1	1072.6	1165.5	1268.8	1331.4	1394.0	1502.5	1659.0	1791.6	1936.6
30°	888.0	963.1	1047.6	1142.6	1251.1	1311.6	1371.1	1506.7	1681.0	1830.2	1976.2
32.5°	860.8	938.0	1026.7	1106.0	1215.6	1280.3	1347.1	1506.7	1694.5	1853.1	1986.7
35°	828.5	907.8	983.9	1063.3	1171.8	1243.8	1318.9	1496.3	1707.0	1860.4	1942.9
37.5°	797.2	867.1	932.8	1010.0	1123.8	1201.0	1287.6	1483.8	1700.8	1829.1	1852.1
40°	761.7	831.6	884.8	956.8	1076.8	1166.5	1254.2	1467.1	1673.7	1755.0	1688.3
42.5°	727.3	782.6	828.5	898.4	1028.8	1116.5	1211.4	1436.8	1620.4	1637.1	1486.9
45°	687.6	727.3	768.0	847.3	976.6	1066.4	1171.8	1393.0	1534.9	1486.9	1297.0
47.5°	636.5	672.0	716.8	789.9	921.3	1014.2	1114.4	1336.6	1410.7	1310.5	1102.9
50°	587.4	617.7	659.4	730.4	862.9	953.7	1060.1	1247.9	1284.5	1126.9	950.6
52.5°	538.4	561.4	602.1	673.0	805.5	893.2	990.2	1157.2	1136.3	967.3	810.7
55°	487.3	507.1	545.7	615.6	738.7	822.2	915.1	1045.5	991.3	830.6	705.4
57.5°	437.2	458.1	497.7	556.1	672.0	753.4	827.4	929.7	848.3	720.0	609.4
60°	392.3	410.1	440.3	497.7	603.1	668.8	736.7	806.6	738.7	614.6	530.1
62.5°	345.4	362.1	390.2	442.4	533.2	591.6	645.9	703.3	628.1	537.4	462.2
65°	301.5	315.1	341.2	389.2	463.3	511.3	555.1	594.8	534.2	450.8	394.4
67.5°	261.9	273.4	295.3	338.1	400.7	435.1	470.6	504.0	452.8	386.1	338.1
70°	219.1	228.5	248.3	279.6	329.7	365.2	391.3	416.3	370.4	317.2	284.9
72.5°	181.6	190.9	203.5	235.8	270.2	292.2	320.3	333.9	307.8	264.0	231.6
75°	145.0	152.3	163.8	184.7	217.0	231.6	249.4	259.8	235.8	206.6	186.8
77.5°	113.7	116.9	125.2	139.8	161.7	178.4	192.0	198.3	181.6	162.8	146.1
80°	80.3	84.5	90.8	103.3	120.0	125.2	133.6	140.9	130.4	113.7	103.3
82.5°	53.2	58.4	61.6	66.8	77.2	83.5	85.6	91.8	82.4	76.2	72.0
85°	31.3	33.4	34.4	37.6	42.8	45.9	49.0	50.1	48.0	47.0	42.8
87.5°	15.7	15.7	15.7	17.7	18.8	20.9	21.9	21.9	21.9	20.9	19.8
90°	1.0	3.2	5.5	7.7	10.0	11.1	12.6	15.5	18.4	21.3	24.2
92.5°	23.2	21.9	20.5	19.2	17.9	17.2	18.2	20.2	22.3	24.3	26.3
95°	61.6	52.4	43.2	34.0	24.8	20.2	21.4	23.9	26.4	28.8	31.3
97.5°	112.1	105.8	99.5	93.2	86.9	83.8	78.1	66.6	55.2	43.7	32.3
100°	170.7	175.2	179.7	184.2	188.7	190.9	173.4	138.4	103.3	68.3	33.3
102.5°	237.3	240.2	243.2	246.1	249.0	250.5	231.0	191.9	152.8	113.8	74.7
105°	301.0	303.5	305.9	308.4	310.9	312.1	302.0	281.8	261.6	241.4	221.2
107.5°	368.6	370.6	372.6	374.7	376.7	377.7	379.4	382.8	386.1	389.5	392.9
110°	436.3	438.1	439.9	441.7	443.5	444.4	445.6	448.1	450.6	453.0	455.5

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	500.9	502.5	504.1	505.6	507.2	508.0	509.2	511.7	514.2	516.6	519.1
115°	564.6	565.9	567.3	568.6	569.9	570.6	571.6	573.6	575.7	577.7	579.7
117.5°	627.2	628.8	630.4	631.9	633.5	634.3	634.9	636.0	637.1	638.2	639.3
120°	684.8	686.8	688.8	690.8	692.8	693.8	694.1	694.8	695.5	696.2	696.9
122.5°	743.3	744.9	746.5	748.0	749.6	750.4	750.8	751.7	752.6	753.5	754.4
125°	795.9	797.7	799.5	801.2	803.0	803.9	804.4	805.3	806.2	807.1	808.0
127.5°	848.4	850.2	852.0	853.8	855.6	856.5	857.1	858.2	859.3	860.4	861.5
130°	896.8	898.6	900.4	902.2	904.0	904.9	905.4	906.3	907.2	908.1	909.0
132.5°	943.3	945.1	946.9	948.7	950.5	951.4	951.7	952.4	953.1	953.7	954.4
135°	990.8	992.1	993.5	994.8	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9
137.5°	1031.2	1033.0	1034.8	1036.6	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3
140°	1071.6	1072.9	1074.3	1075.6	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7
142.5°	1108.9	1110.3	1111.6	1113.0	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0
145°	1143.3	1144.9	1146.5	1148.0	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4
147.5°	1176.6	1177.7	1178.9	1180.0	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7
150°	1206.9	1207.6	1208.2	1208.9	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0
152.5°	1234.2	1234.4	1234.6	1234.9	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2
155°	1259.4	1259.0	1258.5	1258.1	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4
157.5°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6
160°	1297.8	1297.6	1297.4	1297.1	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8
162.5°	1315.0	1314.3	1313.6	1312.9	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9
165°	1328.1	1327.4	1326.8	1326.1	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1
167.5°	1339.2	1338.3	1337.4	1336.5	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2
170°	1348.3	1347.4	1346.5	1345.6	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3
172.5°	1354.4	1353.3	1352.1	1351.0	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3
175°	1359.4	1358.3	1357.2	1356.1	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4
177.5°	1361.4	1360.3	1359.2	1358.1	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1134.2	1136.3	1143.6	1148.8	1159.2	1158.2	1158.2	1157.2	1154.0	1159.2	1162.4
5°	1213.5	1231.2	1233.3	1256.3	1257.3	1266.7	1273.0	1267.8	1280.3	1279.2	1269.8
7.5°	1311.6	1335.6	1347.1	1369.0	1394.0	1387.8	1411.8	1415.9	1413.8	1424.3	1431.6
10°	1419.1	1460.8	1490.0	1530.7	1541.1	1547.4	1563.1	1576.6	1603.7	1582.9	1596.4
12.5°	1542.2	1572.4	1611.0	1675.7	1708.1	1729.0	1736.3	1745.7	1764.4	1753.0	1754.0
15°	1645.5	1686.2	1751.9	1832.3	1841.6	1867.7	1861.5	1917.8	1944.9	1904.3	1927.2
17.5°	1753.0	1807.2	1885.5	1955.4	1995.0	2012.8	2029.5	2083.7	2081.6	2075.4	2080.6
20°	1821.8	1910.5	2007.6	2100.4	2111.9	2125.5	2170.3	2193.3	2189.1	2206.8	2218.3
22.5°	1918.9	2012.8	2116.1	2177.6	2203.7	2219.4	2254.8	2269.4	2275.7	2279.9	2272.6
25°	2000.2	2100.4	2176.6	2230.8	2246.5	2254.8	2266.3	2270.5	2267.4	2260.1	2266.3
27.5°	2055.5	2135.9	2188.1	2213.1	2204.8	2191.2	2169.3	2154.7	2122.3	2106.7	2125.5
30°	2078.5	2114.0	2129.6	2087.9	2046.2	2012.8	1971.0	1893.8	1833.3	1851.0	1827.0
32.5°	2042.0	2019.0	1943.9	1836.4	1804.1	1749.8	1631.9	1541.1	1544.3	1496.3	1516.1
35°	1934.5	1830.2	1688.3	1525.5	1482.7	1453.5	1324.1	1304.3	1262.5	1217.7	1230.2
37.5°	1744.6	1592.3	1420.1	1300.1	1236.5	1172.8	1099.8	1055.9	1030.9	1012.1	1026.7
40°	1513.0	1327.2	1185.3	1077.9	1023.6	982.9	932.8	889.0	860.8	857.7	862.9
42.5°	1285.5	1129.0	998.6	896.3	878.6	830.6	798.2	763.8	755.4	741.9	749.2
45°	1088.3	961.0	853.5	770.0	749.2	736.7	697.0	675.1	665.7	657.4	669.9
47.5°	945.3	811.8	733.5	683.4	662.6	641.7	619.8	605.2	597.9	598.9	597.9
50°	807.6	709.5	640.7	602.1	589.5	574.9	557.2	547.8	544.7	535.3	542.6
52.5°	694.9	624.0	576.0	539.5	530.1	519.6	505.0	499.8	492.5	490.4	490.4
55°	604.1	548.8	510.2	486.2	474.8	466.4	458.1	451.8	446.6	446.6	446.6
57.5°	533.2	485.2	457.0	436.2	432.0	423.6	414.2	414.2	406.9	405.9	409.0
60°	472.7	429.9	408.0	390.2	384.0	381.9	372.5	372.5	370.4	365.2	369.4
62.5°	411.1	379.8	361.0	347.5	341.2	341.2	333.9	328.7	328.7	329.7	327.6
65°	354.8	331.8	315.1	304.7	301.5	297.4	296.3	292.2	289.0	290.1	289.0
67.5°	304.7	286.9	275.5	267.1	261.9	259.8	256.7	256.7	254.6	255.6	250.4
70°	259.8	242.1	232.7	224.3	222.2	222.2	218.1	219.1	217.0	220.2	218.1
72.5°	213.9	200.3	193.0	189.9	187.8	186.8	184.7	182.6	181.6	183.6	182.6
75°	173.2	161.7	156.5	154.4	152.3	152.3	151.3	150.3	149.2	149.2	149.2
77.5°	134.6	127.3	121.0	123.1	120.0	121.0	117.9	117.9	119.0	117.9	117.9
80°	99.1	93.9	93.9	91.8	87.6	89.7	89.7	86.6	85.6	87.6	84.5
82.5°	65.7	64.7	62.6	61.6	59.5	60.5	59.5	58.4	57.4	59.5	57.4
85°	38.6	38.6	37.6	35.5	37.6	36.5	35.5	35.5	34.4	34.4	34.4
87.5°	19.8	17.7	17.7	16.7	17.7	15.7	16.7	15.7	14.6	15.7	14.6
90°	25.1	26.0	26.9	27.8	28.3	28.5	29.0	29.4	29.9	30.3	29.9
92.5°	27.9	29.4	31.0	32.5	33.3	33.4	33.6	33.9	34.1	34.3	34.1
95°	32.9	34.5	36.0	37.6	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	34.1	35.9	37.7	39.5	40.4	40.5	40.7	41.0	41.2	41.4	41.2
100°	35.1	36.9	38.7	40.5	41.4	41.5	41.7	42.0	42.2	42.4	42.2
102.5°	67.3	59.9	52.5	45.1	41.4	41.6	42.1	42.5	43.0	43.4	43.0
105°	181.5	141.7	102.0	62.3	42.4	42.6	43.1	43.5	44.0	44.4	44.0
107.5°	358.3	323.7	289.2	254.6	237.3	222.6	193.2	163.8	134.4	105.0	134.4
110°	448.1	440.7	433.3	425.9	422.2	406.1	374.0	341.9	309.8	277.7	309.8

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	521.1	523.1	525.2	527.2	528.2	528.0	527.5	527.1	526.6	526.2	526.6
115°	581.9	584.2	586.4	588.7	589.8	590.3	591.2	592.1	593.0	593.9	593.0
117.5°	641.1	642.9	644.7	646.5	647.4	647.5	647.7	648.0	648.2	648.4	648.2
120°	698.7	700.5	702.3	704.1	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	755.5	756.7	757.8	758.9	759.5	759.6	759.8	760.1	760.3	760.5	760.3
125°	808.4	808.9	809.3	809.8	810.0	810.2	810.7	811.1	811.6	812.0	811.6
127.5°	862.2	862.8	863.5	864.2	864.5	864.3	863.8	863.4	862.9	862.5	862.9
130°	909.9	910.8	911.7	912.6	913.0	912.8	912.3	911.9	911.4	911.0	911.4
132.5°	955.3	956.2	957.1	958.0	958.5	958.2	957.5	956.8	956.1	955.4	956.1
135°	1001.6	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6
137.5°	1042.4	1043.5	1044.6	1045.7	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7
140°	1081.6	1082.5	1083.4	1084.3	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1
142.5°	1118.7	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7
145°	1152.8	1153.3	1153.7	1154.2	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1184.1	1184.6	1185.0	1185.5	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7
150°	1212.4	1212.9	1213.3	1213.8	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6
152.5°	1237.1	1238.0	1238.9	1239.8	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3
155°	1259.5	1260.7	1261.8	1262.9	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8
157.5°	1280.0	1281.3	1282.7	1284.0	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4
160°	1297.1	1298.5	1299.8	1301.1	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4
162.5°	1312.5	1314.1	1315.6	1317.2	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3
165°	1325.9	1327.7	1329.4	1331.2	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7
167.5°	1337.0	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0
170°	1346.1	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1
172.5°	1352.1	1353.9	1355.7	1357.5	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3
175°	1357.0	1358.5	1360.1	1361.6	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2
177.5°	1359.2	1361.0	1362.8	1364.6	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1154.0	1157.2	1148.8	1146.7	1146.7	1150.9	1147.8	1119.6	1124.8	1118.6	1116.5
5°	1281.3	1275.1	1266.7	1262.5	1257.3	1242.7	1241.7	1209.3	1203.1	1182.2	1172.8
7.5°	1421.1	1415.9	1390.9	1387.8	1385.7	1372.1	1337.7	1303.2	1278.2	1254.2	1231.2
10°	1580.8	1565.1	1553.7	1530.7	1519.2	1500.4	1455.6	1423.2	1380.5	1343.9	1295.9
12.5°	1772.8	1755.0	1716.4	1699.7	1685.1	1633.0	1588.1	1551.6	1468.1	1443.1	1383.6
15°	1913.6	1876.1	1871.9	1835.4	1833.3	1775.9	1690.3	1650.7	1586.0	1494.2	1432.6
17.5°	2066.0	2032.6	2006.5	1962.7	1956.4	1902.2	1839.6	1742.5	1671.6	1583.9	1505.7
20°	2177.6	2159.9	2115.0	2097.3	2060.8	2014.9	1950.2	1830.2	1743.6	1655.9	1559.9
22.5°	2266.3	2248.6	2213.1	2189.1	2168.2	2108.8	2031.5	1929.3	1810.3	1695.6	1596.4
25°	2265.3	2260.1	2245.5	2234.0	2218.3	2174.5	2109.8	2011.7	1879.2	1753.0	1615.2
27.5°	2136.9	2151.5	2176.6	2189.1	2186.0	2179.7	2143.2	2060.8	1941.8	1791.6	1637.1
30°	1869.8	1923.0	1970.0	2032.6	2051.4	2097.3	2118.2	2071.2	1976.2	1836.4	1665.3
32.5°	1550.5	1627.7	1730.0	1764.4	1823.9	1912.6	2011.7	2029.5	1970.0	1862.5	1683.0
35°	1271.9	1335.6	1414.9	1469.1	1522.4	1666.4	1791.6	1900.1	1919.9	1848.9	1678.9
37.5°	1052.8	1097.7	1167.6	1213.5	1262.5	1385.7	1561.0	1701.8	1801.0	1803.0	1667.4
40°	894.2	914.0	974.6	1007.9	1054.9	1161.3	1317.8	1501.5	1646.5	1713.3	1637.1
42.5°	757.5	783.6	833.7	858.7	889.0	981.9	1085.2	1259.4	1438.9	1581.8	1580.8
45°	676.1	694.9	717.9	738.7	773.2	828.5	946.4	1076.8	1249.0	1410.7	1474.4
47.5°	604.1	621.9	644.8	651.1	674.1	726.2	798.2	912.0	1072.6	1233.3	1353.3
50°	543.6	558.2	573.9	585.4	595.8	638.6	692.8	788.8	917.2	1072.6	1221.9
52.5°	496.7	507.1	520.7	526.9	536.3	567.6	609.4	680.3	785.7	927.6	1072.6
55°	452.8	460.2	468.5	478.9	483.1	506.1	538.4	598.9	677.2	804.5	942.2
57.5°	412.2	415.3	420.5	426.8	432.0	451.8	480.0	520.7	589.5	687.6	818.0
60°	366.2	374.6	377.7	384.0	387.1	402.8	424.7	459.1	512.3	596.8	694.9
62.5°	327.6	332.9	338.1	341.2	348.5	353.7	371.5	402.8	446.6	509.2	597.9
65°	293.2	295.3	298.4	301.5	303.6	309.9	326.6	347.5	380.9	436.2	505.0
67.5°	253.6	255.6	259.8	260.9	262.9	271.3	280.7	298.4	326.6	368.3	424.7
70°	214.9	218.1	220.2	222.2	225.4	228.5	238.9	253.6	275.5	304.7	348.5
72.5°	181.6	184.7	184.7	186.8	185.7	189.9	200.3	210.8	225.4	249.4	288.0
75°	148.2	148.2	150.3	151.3	152.3	156.5	160.7	169.0	180.5	199.3	223.3
77.5°	116.9	115.8	117.9	117.9	117.9	121.0	125.2	129.4	136.7	150.3	169.0
80°	85.6	85.6	87.6	88.7	86.6	87.6	89.7	93.9	99.1	108.5	119.0
82.5°	56.3	60.5	59.5	60.5	59.5	61.6	62.6	63.6	65.7	69.9	77.2
85°	34.4	34.4	34.4	35.5	34.4	35.5	35.5	35.5	36.5	38.6	41.7
87.5°	14.6	14.6	14.6	15.7	14.6	14.6	15.7	14.6	15.7	15.7	16.7
90°	29.4	29.0	28.5	28.3	27.8	26.9	26.0	25.1	24.2	21.3	18.4
92.5°	33.9	33.6	33.4	33.3	32.5	31.0	29.4	27.9	26.3	24.3	22.3
95°	38.4	38.4	38.4	38.4	37.6	36.0	34.5	32.9	31.3	28.8	26.4
97.5°	41.0	40.7	40.5	40.4	39.5	37.7	35.9	34.1	32.3	43.7	55.2
100°	42.0	41.7	41.5	41.4	40.5	38.7	36.9	35.1	33.3	68.3	103.3
102.5°	42.5	42.1	41.6	41.4	45.1	52.5	59.9	67.3	74.7	113.8	152.8
105°	43.5	43.1	42.6	42.4	62.3	102.0	141.7	181.5	221.2	241.4	261.6
107.5°	163.8	193.2	222.6	237.3	254.6	289.2	323.7	358.3	392.9	389.5	386.1
110°	341.9	374.0	406.1	422.2	425.9	433.3	440.7	448.1	455.5	453.0	450.6

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	527.1	527.5	528.0	528.2	527.2	525.2	523.1	521.1	519.1	516.6	514.2
115°	592.1	591.2	590.3	589.8	588.7	586.4	584.2	581.9	579.7	577.7	575.7
117.5°	648.0	647.7	647.5	647.4	646.5	644.7	642.9	641.1	639.3	638.2	637.1
120°	705.0	705.0	705.0	705.0	704.1	702.3	700.5	698.7	696.9	696.2	695.5
122.5°	760.1	759.8	759.6	759.5	758.9	757.8	756.7	755.5	754.4	753.5	752.6
125°	811.1	810.7	810.2	810.0	809.8	809.3	808.9	808.4	808.0	807.1	806.2
127.5°	863.4	863.8	864.3	864.5	864.2	863.5	862.8	862.2	861.5	860.4	859.3
130°	911.9	912.3	912.8	913.0	912.6	911.7	910.8	909.9	909.0	908.1	907.2
132.5°	956.8	957.5	958.2	958.5	958.0	957.1	956.2	955.3	954.4	953.7	953.1
135°	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1
137.5°	1045.2	1045.6	1046.1	1046.3	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4
140°	1083.6	1084.0	1084.5	1084.7	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3
142.5°	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7
145°	1154.4	1154.4	1154.4	1154.4	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5
147.5°	1182.9	1184.0	1185.1	1185.7	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8
150°	1212.3	1213.0	1213.7	1214.0	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1
152.5°	1237.4	1238.5	1239.6	1240.2	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8
155°	1260.1	1261.5	1262.8	1263.5	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0
157.5°	1280.2	1282.0	1283.8	1284.7	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0
160°	1297.9	1299.5	1301.0	1301.8	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2
162.5°	1314.6	1316.0	1317.3	1318.0	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3
165°	1328.2	1329.8	1331.3	1332.1	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5
167.5°	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2
170°	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3
172.5°	1353.3	1355.4	1357.4	1358.4	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9
175°	1358.0	1359.7	1361.5	1362.4	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0
177.5°	1359.9	1362.1	1364.4	1365.5	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1106.0	1102.9	1102.9	1100.8	1094.6	1083.1	1082.0	1084.1	1077.9	1071.6	1062.2
5°	1160.3	1140.5	1134.2	1127.9	1115.4	1094.6	1086.2	1078.9	1067.4	1053.9	1039.3
7.5°	1206.2	1178.0	1169.7	1158.2	1133.2	1103.9	1085.2	1069.5	1053.9	1035.1	1017.3
10°	1263.6	1222.9	1203.1	1186.4	1151.9	1111.2	1083.1	1060.1	1035.1	1012.1	989.2
12.5°	1328.3	1262.5	1256.3	1215.6	1175.9	1115.4	1081.0	1047.6	1014.2	986.0	962.0
15°	1382.5	1310.5	1284.5	1257.3	1181.2	1106.0	1072.6	1035.1	996.5	966.2	930.7
17.5°	1417.0	1357.5	1302.2	1265.7	1186.4	1119.6	1054.9	1012.1	971.4	929.7	900.5
20°	1458.7	1372.1	1324.1	1275.1	1196.8	1109.2	1044.5	991.3	941.2	903.6	868.1
22.5°	1500.4	1383.6	1343.9	1290.7	1198.9	1098.7	1025.7	972.5	915.1	877.5	838.9
25°	1496.3	1400.3	1334.5	1289.7	1178.0	1089.3	1003.8	941.2	888.0	840.0	801.4
27.5°	1499.4	1381.5	1314.7	1262.5	1163.4	1075.8	980.8	915.1	859.8	809.7	769.0
30°	1500.4	1353.3	1294.9	1232.3	1136.3	1043.4	954.7	888.0	829.5	775.3	738.7
32.5°	1497.3	1330.4	1257.3	1201.0	1093.5	1012.1	924.5	853.5	794.0	744.0	709.5
35°	1490.0	1303.2	1218.7	1147.8	1049.7	967.3	896.3	823.3	759.6	713.7	674.1
37.5°	1470.2	1274.0	1178.0	1108.1	998.6	915.1	852.5	792.0	730.4	676.1	642.7
40°	1455.6	1234.4	1137.3	1061.2	943.3	861.9	809.7	752.3	691.8	642.7	610.4
42.5°	1422.2	1196.8	1095.6	1004.8	889.0	805.5	756.5	710.6	658.4	610.4	581.2
45°	1367.9	1156.1	1044.5	952.6	829.5	750.2	705.4	667.8	621.9	576.0	546.8
47.5°	1291.8	1097.7	990.2	898.4	771.1	690.7	645.9	617.7	581.2	542.6	517.5
50°	1209.3	1034.0	934.9	844.1	714.7	636.5	592.7	566.6	542.6	507.1	483.1
52.5°	1101.9	966.2	871.3	784.7	654.2	579.1	540.5	521.7	496.7	471.6	450.8
55°	997.5	878.6	800.3	717.9	594.8	524.8	487.3	467.5	452.8	432.0	415.3
57.5°	876.5	797.2	725.2	650.1	539.5	475.8	440.3	416.3	406.9	397.5	381.9
60°	764.8	704.3	645.9	583.3	482.1	424.7	390.2	371.5	362.1	355.8	345.4
62.5°	662.6	615.6	565.5	515.5	423.6	371.5	345.4	326.6	318.2	317.2	307.8
65°	564.5	531.1	490.4	441.4	369.4	323.5	298.4	286.9	277.6	277.6	270.2
67.5°	466.4	443.5	411.1	376.7	320.3	277.6	254.6	244.2	238.9	238.9	233.7
70°	388.2	372.5	343.3	313.0	264.0	231.6	213.9	204.5	201.4	202.4	198.3
72.5°	315.1	298.4	274.4	252.5	216.0	192.0	179.5	169.0	163.8	164.9	163.8
75°	244.2	235.8	214.9	198.3	169.0	152.3	140.9	135.6	131.5	132.5	130.4
77.5°	183.6	171.1	159.6	148.2	130.4	116.9	107.5	102.3	99.1	99.1	99.1
80°	125.2	123.1	113.7	107.5	92.9	82.4	75.1	74.1	71.0	71.0	71.0
82.5°	81.4	76.2	71.0	66.8	58.4	52.2	49.0	47.0	45.9	44.9	47.0
85°	44.9	41.7	39.7	35.5	32.3	29.2	26.1	25.0	24.0	25.0	24.0
87.5°	17.7	14.6	14.6	13.6	12.5	11.5	11.5	9.4	9.4	8.3	8.3
90°	15.5	12.6	11.1	10.0	7.7	5.5	3.2	1.0	3.2	5.5	7.7
92.5°	20.2	18.2	17.2	17.9	19.2	20.5	21.9	23.2	21.9	20.5	19.2
95°	23.9	21.4	20.2	24.8	34.0	43.2	52.4	61.6	52.4	43.2	34.0
97.5°	66.6	78.1	83.8	86.9	93.2	99.5	105.8	112.1	105.8	99.5	93.2
100°	138.4	173.4	190.9	188.7	184.2	179.7	175.2	170.7	175.2	179.7	184.2
102.5°	191.9	231.0	250.5	249.0	246.1	243.2	240.2	237.3	240.2	243.2	246.1
105°	281.8	302.0	312.1	310.9	308.4	305.9	303.5	301.0	303.5	305.9	308.4
107.5°	382.8	379.4	377.7	376.7	374.7	372.6	370.6	368.6	370.6	372.6	374.7
110°	448.1	445.6	444.4	443.5	441.7	439.9	438.1	436.3	438.1	439.9	441.7

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	511.7	509.2	508.0	507.2	505.6	504.1	502.5	500.9	502.5	504.1	505.6
115°	573.6	571.6	570.6	569.9	568.6	567.3	565.9	564.6	565.9	567.3	568.6
117.5°	636.0	634.9	634.3	633.5	631.9	630.4	628.8	627.2	628.8	630.4	631.9
120°	694.8	694.1	693.8	692.8	690.8	688.8	686.8	684.8	686.8	688.8	690.8
122.5°	751.7	750.8	750.4	749.6	748.0	746.5	744.9	743.3	744.9	746.5	748.0
125°	805.3	804.4	803.9	803.0	801.2	799.5	797.7	795.9	797.7	799.5	801.2
127.5°	858.2	857.1	856.5	855.6	853.8	852.0	850.2	848.4	850.2	852.0	853.8
130°	906.3	905.4	904.9	904.0	902.2	900.4	898.6	896.8	898.6	900.4	902.2
132.5°	952.4	951.7	951.4	950.5	948.7	946.9	945.1	943.3	945.1	946.9	948.7
135°	998.2	997.3	996.8	996.1	994.8	993.5	992.1	990.8	992.1	993.5	994.8
137.5°	1040.0	1039.5	1039.3	1038.4	1036.6	1034.8	1033.0	1031.2	1033.0	1034.8	1036.6
140°	1078.6	1077.9	1077.6	1076.9	1075.6	1074.3	1072.9	1071.6	1072.9	1074.3	1075.6
142.5°	1116.0	1115.3	1115.0	1114.3	1113.0	1111.6	1110.3	1108.9	1110.3	1111.6	1113.0
145°	1151.1	1150.6	1150.4	1149.6	1148.0	1146.5	1144.9	1143.3	1144.9	1146.5	1148.0
147.5°	1182.4	1181.9	1181.7	1181.1	1180.0	1178.9	1177.7	1176.6	1177.7	1178.9	1180.0
150°	1210.6	1210.1	1209.9	1209.6	1208.9	1208.2	1207.6	1206.9	1207.6	1208.2	1208.9
152.5°	1235.5	1235.3	1235.2	1235.1	1234.9	1234.6	1234.4	1234.2	1234.4	1234.6	1234.9
155°	1257.7	1257.5	1257.4	1257.6	1258.1	1258.5	1259.0	1259.4	1259.0	1258.5	1258.1
157.5°	1279.3	1279.5	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
160°	1296.5	1296.7	1296.8	1296.9	1297.1	1297.4	1297.6	1297.8	1297.6	1297.4	1297.1
162.5°	1311.6	1311.8	1311.9	1312.2	1312.9	1313.6	1314.3	1315.0	1314.3	1313.6	1312.9
165°	1324.8	1325.0	1325.1	1325.4	1326.1	1326.8	1327.4	1328.1	1327.4	1326.8	1326.1
167.5°	1335.2	1335.2	1335.2	1335.6	1336.5	1337.4	1338.3	1339.2	1338.3	1337.4	1336.5
170°	1344.3	1344.3	1344.3	1344.7	1345.6	1346.5	1347.4	1348.3	1347.4	1346.5	1345.6
172.5°	1349.6	1349.4	1349.3	1349.9	1351.0	1352.1	1353.3	1354.4	1353.3	1352.1	1351.0
175°	1354.7	1354.5	1354.4	1355.0	1356.1	1357.2	1358.3	1359.4	1358.3	1357.2	1356.1
177.5°	1356.7	1356.5	1356.4	1357.0	1358.1	1359.2	1360.3	1361.4	1360.3	1359.2	1358.1
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1060.1	1059.1	1061.2	1054.9	1044.5	1039.3	1024.6	1021.5	1020.5	1021.5	1022.6
5°	1030.9	1029.9	1026.7	1016.3	1003.8	994.4	976.6	975.6	969.3	963.1	966.2
7.5°	1002.7	998.6	992.3	978.7	962.0	951.6	937.0	926.6	918.2	913.0	908.8
10°	974.6	968.3	962.0	944.3	923.4	907.8	890.0	881.7	872.3	868.1	864.0
12.5°	938.0	931.8	920.3	899.4	886.9	867.1	849.3	841.0	835.8	827.4	822.2
15°	908.8	896.3	890.0	868.1	842.0	840.0	807.6	805.5	795.1	795.1	786.7
17.5°	875.4	866.0	854.6	832.7	813.9	795.1	778.4	772.1	762.7	760.7	756.5
20°	843.1	830.6	826.4	804.5	784.7	761.7	744.0	737.7	733.5	729.4	732.5
22.5°	809.7	799.3	788.8	769.0	754.4	731.4	721.0	714.7	708.5	706.4	707.4
25°	777.4	768.0	757.5	737.7	722.1	703.3	693.9	690.7	687.6	687.6	686.6
27.5°	746.0	736.7	727.3	709.5	693.9	680.3	673.0	669.9	666.7	668.8	670.9
30°	713.7	705.4	697.0	681.4	668.8	656.3	652.1	650.1	649.0	654.2	654.2
32.5°	684.5	677.2	670.9	656.3	643.8	633.4	630.2	631.3	632.3	635.4	637.5
35°	654.2	649.0	642.7	630.2	619.8	610.4	611.4	611.4	613.5	618.8	622.9
37.5°	627.1	619.8	614.6	604.1	595.8	587.4	590.6	593.7	595.8	602.1	604.1
40°	594.8	591.6	587.4	577.0	569.7	568.7	569.7	571.8	576.0	579.1	582.2
42.5°	568.7	564.5	559.3	550.9	544.7	545.7	546.8	548.8	550.9	556.1	559.3
45°	539.5	536.3	532.1	524.8	519.6	520.7	521.7	521.7	523.8	530.1	532.1
47.5°	507.1	508.1	502.9	495.6	492.5	492.5	492.5	494.6	499.8	501.9	502.9
50°	475.8	473.7	472.7	465.4	463.3	462.2	463.3	464.3	471.6	470.6	473.7
52.5°	442.4	442.4	441.4	437.2	434.1	434.1	432.0	437.2	439.3	441.4	444.5
55°	410.1	406.9	405.9	403.8	399.6	398.6	400.7	406.9	409.0	411.1	414.2
57.5°	374.6	374.6	372.5	369.4	369.4	369.4	369.4	373.5	376.7	378.8	385.0
60°	342.2	338.1	334.9	334.9	334.9	333.9	340.2	340.2	346.4	347.5	349.5
62.5°	303.6	301.5	299.5	300.5	299.5	301.5	303.6	307.8	308.9	312.0	315.1
65°	267.1	267.1	265.0	271.3	267.1	267.1	272.3	272.3	274.4	277.6	281.7
67.5°	231.6	232.7	230.6	230.6	232.7	233.7	234.8	238.9	240.0	244.2	249.4
70°	195.1	197.2	198.3	196.2	198.3	200.3	202.4	203.5	207.6	209.7	212.9
72.5°	162.8	164.9	161.7	162.8	163.8	165.9	166.9	169.0	171.1	177.4	179.5
75°	130.4	129.4	128.3	132.5	130.4	134.6	135.6	135.6	137.7	142.9	145.0
77.5°	100.2	100.2	101.2	99.1	102.3	101.2	102.3	105.4	108.5	108.5	116.9
80°	69.9	72.0	72.0	72.0	73.0	74.1	72.0	77.2	78.3	78.3	81.4
82.5°	44.9	45.9	44.9	47.0	47.0	49.0	48.0	49.0	51.1	53.2	54.3
85°	24.0	24.0	26.1	26.1	25.0	26.1	25.0	26.1	28.2	28.2	29.2
87.5°	8.3	8.3	8.3	8.3	9.4	8.3	9.4	9.4	8.3	8.3	11.5
90°	10.0	11.1	12.6	15.5	18.4	21.3	24.2	25.1	26.0	26.9	27.8
92.5°	17.9	17.2	18.2	20.2	22.3	24.3	26.3	27.9	29.4	31.0	32.5
95°	24.8	20.2	21.4	23.9	26.4	28.8	31.3	32.9	34.5	36.0	37.6
97.5°	86.9	83.8	78.1	66.6	55.2	43.7	32.3	34.1	35.9	37.7	39.5
100°	188.7	190.9	173.4	138.4	103.3	68.3	33.3	35.1	36.9	38.7	40.5
102.5°	249.0	250.5	231.0	191.9	152.8	113.8	74.7	67.3	59.9	52.5	45.1
105°	310.9	312.1	302.0	281.8	261.6	241.4	221.2	181.5	141.7	102.0	62.3
107.5°	376.7	377.7	379.4	382.8	386.1	389.5	392.9	358.3	323.7	289.2	254.6
110°	443.5	444.4	445.6	448.1	450.6	453.0	455.5	448.1	440.7	433.3	425.9

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	507.2	508.0	509.2	511.7	514.2	516.6	519.1	521.1	523.1	525.2	527.2
115°	569.9	570.6	571.6	573.6	575.7	577.7	579.7	581.9	584.2	586.4	588.7
117.5°	633.5	634.3	634.9	636.0	637.1	638.2	639.3	641.1	642.9	644.7	646.5
120°	692.8	693.8	694.1	694.8	695.5	696.2	696.9	698.7	700.5	702.3	704.1
122.5°	749.6	750.4	750.8	751.7	752.6	753.5	754.4	755.5	756.7	757.8	758.9
125°	803.0	803.9	804.4	805.3	806.2	807.1	808.0	808.4	808.9	809.3	809.8
127.5°	855.6	856.5	857.1	858.2	859.3	860.4	861.5	862.2	862.8	863.5	864.2
130°	904.0	904.9	905.4	906.3	907.2	908.1	909.0	909.9	910.8	911.7	912.6
132.5°	950.5	951.4	951.7	952.4	953.1	953.7	954.4	955.3	956.2	957.1	958.0
135°	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9	1001.6	1002.2	1002.9	1003.6
137.5°	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3	1042.4	1043.5	1044.6	1045.7
140°	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7	1081.6	1082.5	1083.4	1084.3
142.5°	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4	1152.8	1153.3	1153.7	1154.2
147.5°	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7	1184.1	1184.6	1185.0	1185.5
150°	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0	1212.4	1212.9	1213.3	1213.8
152.5°	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2	1237.1	1238.0	1238.9	1239.8
155°	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4	1259.5	1260.7	1261.8	1262.9
157.5°	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6	1280.0	1281.3	1282.7	1284.0
160°	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8	1297.1	1298.5	1299.8	1301.1
162.5°	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9	1312.5	1314.1	1315.6	1317.2
165°	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1	1325.9	1327.7	1329.4	1331.2
167.5°	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1337.0	1338.8	1340.6	1342.4
170°	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1346.1	1347.9	1349.6	1351.4
172.5°	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3	1352.1	1353.9	1355.7	1357.5
175°	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4	1357.0	1358.5	1360.1	1361.6
177.5°	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4	1359.2	1361.0	1362.8	1364.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1021.5	1022.6	1018.4	1015.3	1023.6	1018.4	1018.4	1019.4	1017.3	1020.5	1019.4
5°	964.1	965.2	957.9	960.0	955.8	954.7	953.7	960.0	958.9	957.9	960.0
7.5°	907.8	907.8	904.6	902.6	902.6	899.4	903.6	902.6	904.6	904.6	907.8
10°	860.8	862.9	857.7	852.5	851.4	852.5	852.5	853.5	854.6	861.9	860.8
12.5°	822.2	819.1	818.0	814.9	809.7	807.6	805.5	817.0	813.9	813.9	813.9
15°	779.4	786.7	785.7	776.3	774.2	778.4	776.3	776.3	786.7	785.7	784.7
17.5°	756.5	754.4	752.3	747.1	748.1	747.1	748.1	748.1	754.4	754.4	754.4
20°	730.4	726.2	726.2	724.1	724.1	721.0	725.2	726.2	730.4	730.4	731.4
22.5°	707.4	704.3	704.3	703.3	705.4	701.2	705.4	706.4	706.4	709.5	709.5
25°	687.6	685.5	685.5	687.6	687.6	687.6	687.6	691.8	688.7	689.7	688.7
27.5°	669.9	670.9	672.0	673.0	672.0	673.0	674.1	676.1	677.2	676.1	674.1
30°	653.2	656.3	657.4	657.4	659.4	660.5	661.5	661.5	662.6	659.4	661.5
32.5°	640.7	640.7	642.7	643.8	645.9	646.9	646.9	649.0	648.0	644.8	645.9
35°	622.9	622.9	627.1	629.2	632.3	631.3	632.3	632.3	633.4	631.3	628.1
37.5°	605.2	607.3	607.3	611.4	612.5	613.5	612.5	614.6	613.5	611.4	610.4
40°	584.3	583.3	584.3	587.4	588.5	588.5	588.5	590.6	590.6	590.6	589.5
42.5°	558.2	561.4	560.3	563.4	562.4	562.4	564.5	566.6	567.6	564.5	565.5
45°	533.2	533.2	535.3	535.3	536.3	536.3	540.5	538.4	540.5	538.4	539.5
47.5°	506.1	507.1	507.1	508.1	510.2	512.3	510.2	511.3	511.3	512.3	510.2
50°	475.8	475.8	477.9	481.0	485.2	483.1	482.1	486.2	483.1	483.1	481.0
52.5°	444.5	447.6	448.7	451.8	454.9	456.0	457.0	454.9	456.0	452.8	453.9
55°	414.2	415.3	419.5	422.6	425.7	425.7	424.7	425.7	426.8	422.6	422.6
57.5°	384.0	387.1	391.3	391.3	395.5	395.5	394.4	394.4	395.5	392.3	391.3
60°	351.6	354.8	360.0	360.0	366.2	367.3	365.2	363.1	363.1	360.0	361.0
62.5°	317.2	320.3	323.5	328.7	332.9	330.8	334.9	330.8	331.8	325.5	325.5
65°	286.9	288.0	293.2	298.4	298.4	300.5	298.4	299.5	296.3	296.3	292.2
67.5°	251.5	251.5	256.7	261.9	267.1	267.1	267.1	264.0	264.0	260.9	260.9
70°	220.2	219.1	224.3	227.5	230.6	231.6	229.6	228.5	226.4	223.3	222.2
72.5°	181.6	183.6	188.9	190.9	196.2	195.1	200.3	194.1	194.1	188.9	187.8
75°	147.1	149.2	154.4	157.6	160.7	160.7	163.8	160.7	156.5	154.4	153.4
77.5°	116.9	115.8	120.0	125.2	126.3	125.2	127.3	126.3	122.1	122.1	120.0
80°	83.5	86.6	90.8	89.7	93.9	92.9	92.9	90.8	90.8	87.6	89.7
82.5°	55.3	58.4	59.5	58.4	59.5	61.6	62.6	61.6	61.6	59.5	60.5
85°	29.2	29.2	31.3	32.3	31.3	31.3	32.3	35.5	33.4	31.3	33.4
87.5°	9.4	8.3	8.3	9.4	8.3	8.3	9.4	9.4	10.4	10.4	10.4
90°	28.3	28.5	29.0	29.4	29.9	30.3	29.9	29.4	29.0	28.5	28.3
92.5°	33.3	33.4	33.6	33.9	34.1	34.3	34.1	33.9	33.6	33.4	33.3
95°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	40.4	40.5	40.7	41.0	41.2	41.4	41.2	41.0	40.7	40.5	40.4
100°	41.4	41.5	41.7	42.0	42.2	42.4	42.2	42.0	41.7	41.5	41.4
102.5°	41.4	41.6	42.1	42.5	43.0	43.4	43.0	42.5	42.1	41.6	41.4
105°	42.4	42.6	43.1	43.5	44.0	44.4	44.0	43.5	43.1	42.6	42.4
107.5°	237.3	222.6	193.2	163.8	134.4	105.0	134.4	163.8	193.2	222.6	237.3
110°	422.2	406.1	374.0	341.9	309.8	277.7	309.8	341.9	374.0	406.1	422.2

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	528.2	528.0	527.5	527.1	526.6	526.2	526.6	527.1	527.5	528.0	528.2
115°	589.8	590.3	591.2	592.1	593.0	593.9	593.0	592.1	591.2	590.3	589.8
117.5°	647.4	647.5	647.7	648.0	648.2	648.4	648.2	648.0	647.7	647.5	647.4
120°	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	759.5	759.6	759.8	760.1	760.3	760.5	760.3	760.1	759.8	759.6	759.5
125°	810.0	810.2	810.7	811.1	811.6	812.0	811.6	811.1	810.7	810.2	810.0
127.5°	864.5	864.3	863.8	863.4	862.9	862.5	862.9	863.4	863.8	864.3	864.5
130°	913.0	912.8	912.3	911.9	911.4	911.0	911.4	911.9	912.3	912.8	913.0
132.5°	958.5	958.2	957.5	956.8	956.1	955.4	956.1	956.8	957.5	958.2	958.5
135°	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6	1002.2	1002.9	1003.6	1003.9
137.5°	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7	1045.2	1045.6	1046.1	1046.3
140°	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1	1083.6	1084.0	1084.5	1084.7
142.5°	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7	1119.4	1120.1	1120.8	1121.1
145°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7	1182.9	1184.0	1185.1	1185.7
150°	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6	1212.3	1213.0	1213.7	1214.0
152.5°	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3	1237.4	1238.5	1239.6	1240.2
155°	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8	1260.1	1261.5	1262.8	1263.5
157.5°	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4	1280.2	1282.0	1283.8	1284.7
160°	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4	1297.9	1299.5	1301.0	1301.8
162.5°	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3	1314.6	1316.0	1317.3	1318.0
165°	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7	1328.2	1329.8	1331.3	1332.1
167.5°	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0	1338.8	1340.6	1342.4	1343.3
170°	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1	1347.9	1349.6	1351.4	1352.3
172.5°	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3	1353.3	1355.4	1357.4	1358.4
175°	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2	1358.0	1359.7	1361.5	1362.4
177.5°	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6	1359.9	1362.1	1364.4	1365.5
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8	1076.8
2.5°	1022.6	1024.6	1025.7	1021.5	1018.4	1023.6	1030.9	1036.1	1040.3	1045.5	1048.6
5°	962.0	969.3	969.3	971.4	974.6	979.8	993.3	1002.7	1011.1	1017.3	1022.6
7.5°	910.9	916.1	919.3	924.5	929.7	937.0	952.6	966.2	978.7	986.0	994.4
10°	865.0	869.2	874.4	877.5	886.9	897.3	917.2	928.6	943.3	954.7	965.2
12.5°	821.2	835.8	838.9	837.9	846.2	857.7	877.5	895.3	910.9	922.4	933.9
15°	789.9	795.1	801.4	800.3	818.0	821.2	837.9	858.7	879.6	886.9	897.3
17.5°	755.4	763.8	770.0	773.2	778.4	789.9	805.5	821.2	848.3	849.3	876.5
20°	728.3	736.7	740.8	745.0	748.1	761.7	775.3	793.0	814.9	826.4	841.0
22.5°	710.6	714.7	717.9	721.0	725.2	732.5	749.2	769.0	783.6	796.1	805.5
25°	689.7	693.9	698.1	700.1	703.3	707.4	720.0	735.6	756.5	764.8	774.2
27.5°	675.1	675.1	677.2	677.2	681.4	685.5	694.9	709.5	726.2	736.7	749.2
30°	659.4	658.4	659.4	658.4	657.4	663.6	672.0	684.5	696.0	708.5	716.8
32.5°	643.8	642.7	642.7	643.8	639.6	642.7	646.9	658.4	670.9	677.2	686.6
35°	627.1	625.0	625.0	625.0	622.9	620.8	625.0	635.4	643.8	652.1	659.4
37.5°	610.4	607.3	607.3	605.2	603.1	600.0	600.0	608.3	619.8	622.9	632.3
40°	587.4	587.4	585.4	584.3	582.2	580.1	577.0	584.3	594.8	597.9	605.2
42.5°	564.5	561.4	560.3	560.3	560.3	557.2	555.1	560.3	566.6	571.8	576.0
45°	538.4	536.3	537.4	536.3	534.2	533.2	532.1	534.2	541.5	543.6	548.8
47.5°	510.2	509.2	509.2	508.1	507.1	508.1	504.0	509.2	511.3	513.4	517.5
50°	481.0	480.0	478.9	477.9	477.9	478.9	477.9	477.9	482.1	484.1	488.3
52.5°	451.8	448.7	448.7	447.6	447.6	445.5	447.6	448.7	450.8	452.8	454.9
55°	420.5	420.5	417.4	417.4	415.3	415.3	416.3	415.3	419.5	421.5	421.5
57.5°	390.2	386.1	387.1	385.0	382.9	381.9	381.9	384.0	386.1	386.1	388.2
60°	357.9	353.7	352.7	348.5	350.6	347.5	348.5	348.5	352.7	350.6	352.7
62.5°	325.5	320.3	317.2	315.1	315.1	316.2	314.1	313.0	315.1	317.2	321.4
65°	291.1	288.0	284.9	281.7	281.7	280.7	282.8	279.6	278.6	279.6	281.7
67.5°	255.6	252.5	249.4	246.2	247.3	244.2	242.1	245.2	243.1	244.2	246.2
70°	221.2	219.1	212.9	210.8	209.7	210.8	209.7	207.6	210.8	209.7	210.8
72.5°	186.8	184.7	181.6	176.3	176.3	175.3	174.3	174.3	173.2	173.2	173.2
75°	153.4	149.2	146.1	145.0	142.9	141.9	140.9	138.8	139.8	140.9	138.8
77.5°	119.0	113.7	112.7	112.7	109.6	109.6	110.6	109.6	108.5	108.5	108.5
80°	87.6	83.5	83.5	81.4	79.3	79.3	79.3	79.3	78.3	77.2	78.3
82.5°	56.3	55.3	54.3	54.3	56.3	52.2	54.3	53.2	52.2	52.2	51.1
85°	31.3	32.3	31.3	32.3	30.3	31.3	31.3	31.3	30.3	31.3	29.2
87.5°	11.5	11.5	11.5	12.5	12.5	12.5	12.5	12.5	13.6	12.5	12.5
90°	27.8	26.9	26.0	25.1	24.2	21.3	18.4	15.5	12.6	11.1	10.0
92.5°	32.5	31.0	29.4	27.9	26.3	24.3	22.3	20.2	18.2	17.2	17.9
95°	37.6	36.0	34.5	32.9	31.3	28.8	26.4	23.9	21.4	20.2	24.8
97.5°	39.5	37.7	35.9	34.1	32.3	43.7	55.2	66.6	78.1	83.8	86.9
100°	40.5	38.7	36.9	35.1	33.3	68.3	103.3	138.4	173.4	190.9	188.7
102.5°	45.1	52.5	59.9	67.3	74.7	113.8	152.8	191.9	231.0	250.5	249.0
105°	62.3	102.0	141.7	181.5	221.2	241.4	261.6	281.8	302.0	312.1	310.9
107.5°	254.6	289.2	323.7	358.3	392.9	389.5	386.1	382.8	379.4	377.7	376.7
110°	425.9	433.3	440.7	448.1	455.5	453.0	450.6	448.1	445.6	444.4	443.5

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	527.2	525.2	523.1	521.1	519.1	516.6	514.2	511.7	509.2	508.0	507.2
115°	588.7	586.4	584.2	581.9	579.7	577.7	575.7	573.6	571.6	570.6	569.9
117.5°	646.5	644.7	642.9	641.1	639.3	638.2	637.1	636.0	634.9	634.3	633.5
120°	704.1	702.3	700.5	698.7	696.9	696.2	695.5	694.8	694.1	693.8	692.8
122.5°	758.9	757.8	756.7	755.5	754.4	753.5	752.6	751.7	750.8	750.4	749.6
125°	809.8	809.3	808.9	808.4	808.0	807.1	806.2	805.3	804.4	803.9	803.0
127.5°	864.2	863.5	862.8	862.2	861.5	860.4	859.3	858.2	857.1	856.5	855.6
130°	912.6	911.7	910.8	909.9	909.0	908.1	907.2	906.3	905.4	904.9	904.0
132.5°	958.0	957.1	956.2	955.3	954.4	953.7	953.1	952.4	951.7	951.4	950.5
135°	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1	998.2	997.3	996.8	996.1
137.5°	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4	1040.0	1039.5	1039.3	1038.4
140°	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3	1078.6	1077.9	1077.6	1076.9
142.5°	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7	1116.0	1115.3	1115.0	1114.3
145°	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5	1151.1	1150.6	1150.4	1149.6
147.5°	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8	1182.4	1181.9	1181.7	1181.1
150°	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1	1210.6	1210.1	1209.9	1209.6
152.5°	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8	1235.5	1235.3	1235.2	1235.1
155°	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0	1257.7	1257.5	1257.4	1257.6
157.5°	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0	1279.3	1279.5	1279.6	1279.6
160°	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2	1296.5	1296.7	1296.8	1296.9
162.5°	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3	1311.6	1311.8	1311.9	1312.2
165°	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5	1324.8	1325.0	1325.1	1325.4
167.5°	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1335.6
170°	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1344.7
172.5°	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9	1349.6	1349.4	1349.3	1349.9
175°	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0	1354.7	1354.5	1354.4	1355.0
177.5°	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0	1356.7	1356.5	1356.4	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1076.8	1076.8	1076.8	1076.8
2.5°	1053.9	1057.0	1067.4	1079.9
5°	1033.0	1041.3	1055.9	1075.8
7.5°	1010.0	1022.6	1043.4	1068.5
10°	983.9	1001.7	1027.8	1059.1
12.5°	955.8	978.7	1012.1	1044.5
15°	938.0	961.0	991.3	1026.7
17.5°	903.6	930.7	962.0	1012.1
20°	868.1	898.4	939.1	989.2
22.5°	841.0	873.3	912.0	965.2
25°	808.7	842.0	883.8	939.1
27.5°	774.2	807.6	854.6	913.0
30°	748.1	780.5	825.3	888.0
32.5°	716.8	748.1	795.1	860.8
35°	681.4	716.8	761.7	828.5
37.5°	654.2	686.6	733.5	797.2
40°	625.0	653.2	699.1	761.7
42.5°	593.7	625.0	664.7	727.3
45°	564.5	587.4	628.1	687.6
47.5°	533.2	559.3	590.6	636.5
50°	499.8	521.7	556.1	587.4
52.5°	467.5	485.2	514.4	538.4
55°	433.0	450.8	472.7	487.3
57.5°	400.7	413.2	427.8	437.2
60°	361.0	373.5	382.9	392.3
62.5°	325.5	334.9	340.2	345.4
65°	289.0	294.2	297.4	301.5
67.5°	249.4	254.6	255.6	261.9
70°	212.9	213.9	216.0	219.1
72.5°	178.4	180.5	179.5	181.6
75°	142.9	145.0	142.9	145.0
77.5°	108.5	110.6	110.6	113.7
80°	78.3	79.3	80.3	80.3
82.5°	51.1	54.3	52.2	53.2
85°	29.2	30.3	30.3	31.3
87.5°	13.6	14.6	13.6	15.7
90°	7.7	5.5	3.2	1.0
92.5°	19.2	20.5	21.9	23.2
95°	34.0	43.2	52.4	61.6
97.5°	93.2	99.5	105.8	112.1
100°	184.2	179.7	175.2	170.7
102.5°	246.1	243.2	240.2	237.3
105°	308.4	305.9	303.5	301.0
107.5°	374.7	372.6	370.6	368.6
110°	441.7	439.9	438.1	436.3



TEST NUMBER: P1030940

CATALOG NUMBER: S123DIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	505.6	504.1	502.5	500.9
115°	568.6	567.3	565.9	564.6
117.5°	631.9	630.4	628.8	627.2
120°	690.8	688.8	686.8	684.8
122.5°	748.0	746.5	744.9	743.3
125°	801.2	799.5	797.7	795.9
127.5°	853.8	852.0	850.2	848.4
130°	902.2	900.4	898.6	896.8
132.5°	948.7	946.9	945.1	943.3
135°	994.8	993.5	992.1	990.8
137.5°	1036.6	1034.8	1033.0	1031.2
140°	1075.6	1074.3	1072.9	1071.6
142.5°	1113.0	1111.6	1110.3	1108.9
145°	1148.0	1146.5	1144.9	1143.3
147.5°	1180.0	1178.9	1177.7	1176.6
150°	1208.9	1208.2	1207.6	1206.9
152.5°	1234.9	1234.6	1234.4	1234.2
155°	1258.1	1258.5	1259.0	1259.4
157.5°	1279.6	1279.6	1279.6	1279.6
160°	1297.1	1297.4	1297.6	1297.8
162.5°	1312.9	1313.6	1314.3	1315.0
165°	1326.1	1326.8	1327.4	1328.1
167.5°	1336.5	1337.4	1338.3	1339.2
170°	1345.6	1346.5	1347.4	1348.3
172.5°	1351.0	1352.1	1353.3	1354.4
175°	1356.1	1357.2	1358.3	1359.4
177.5°	1358.1	1359.2	1360.3	1361.4
180°	1359.4	1359.4	1359.4	1359.4

(END OF REPORT)