

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030958

Luminaire Tested: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030958
REPORT IS A COMBINATION OF REPORTS P991920 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8231.0 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45			38
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	40	40	39			33
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33			28
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28			24
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24			20
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21			18
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	23	21	19			16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	21	19	17			14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15			13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14			11
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.2
10°-20°	329.9	4.0
20°-30°	555.1	6.7
30°-40°	627.3	7.6
40°-50°	561.8	6.8
50°-60°	453.5	5.5
60°-70°	316.0	3.8
70°-80°	165.9	2.0
80°-90°	43.1	0.5
90°-100°	58.7	0.7
100°-110°	283.9	3.4
110°-120°	695.6	8.5
120°-130°	883.1	10.7
130°-140°	943.4	11.5
140°-150°	882.1	10.7
150°-160°	711.5	8.6
160°-170°	459.2	5.6
170°-180°	158.2	1.9
0°-30°	987.7	12.0
0°-40°	1615.0	19.6
0°-60°	2630.3	32.0
0°-90°	3155.3	38.3
90°-120°	1038.2	12.6
90°-150°	3746.7	45.5
90°-180°	5076.0	61.7
0°-180°	8231.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	1	37	1	37	1	6
95°	76	47	76	47	76	90
105°	369	54	369	54	369	391
115°	692	727	692	727	692	683
125°	975	994	975	994	975	871
135°	1213	1226	1213	1226	1213	934
145°	1400	1414	1400	1414	1400	877
155°	1542	1540	1542	1540	1542	711
165°	1627	1623	1627	1623	1627	460
175°	1665	1659	1665	1659	1665	158
180°	1665	1665	1665	1665	1665	

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	1.2	4.0	6.7	9.5	12.2	13.6	15.4	19.0	22.5	26.1	29.7
92.5°	28.4	26.8	25.1	23.5	21.8	21.0	22.2	24.7	27.2	29.7	32.2
95°	75.5	64.2	52.9	41.6	30.3	24.7	26.2	29.2	32.3	35.3	38.3
97.5°	137.3	129.6	121.9	114.2	106.5	102.7	95.7	81.7	67.6	53.6	39.6
100°	209.0	214.5	220.0	225.5	231.0	233.8	212.4	169.5	126.6	83.7	40.8
102.5°	290.7	294.3	297.9	301.4	305.0	306.8	282.9	235.0	187.2	139.3	91.5
105°	368.6	371.6	374.6	377.7	380.7	382.2	369.8	345.1	320.4	295.6	270.9
107.5°	451.5	454.0	456.4	458.9	461.4	462.6	464.7	468.8	472.9	477.1	481.2
110°	534.4	536.6	538.8	541.0	543.2	544.3	545.8	548.8	551.9	554.9	557.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	613.5	615.4	617.4	619.3	621.2	622.2	623.7	626.7	629.8	632.8	635.8
115°	691.5	693.1	694.8	696.4	698.1	698.9	700.1	702.6	705.1	707.5	710.0
117.5°	768.1	770.0	772.0	773.9	775.8	776.8	777.5	778.9	780.2	781.6	783.0
120°	838.6	841.1	843.6	846.1	848.6	849.8	850.2	851.0	851.9	852.7	853.5
122.5°	910.4	912.3	914.3	916.2	918.1	919.1	919.6	920.7	921.8	922.9	924.0
125°	974.7	976.9	979.1	981.3	983.5	984.6	985.2	986.3	987.4	988.5	989.6
127.5°	1039.0	1041.2	1043.4	1045.6	1047.8	1048.9	1049.6	1051.0	1052.3	1053.7	1055.1
130°	1098.4	1100.6	1102.8	1105.0	1107.2	1108.3	1108.9	1110.0	1111.1	1112.2	1113.3
132.5°	1155.3	1157.5	1159.7	1161.9	1164.1	1165.2	1165.6	1166.4	1167.3	1168.1	1168.9
135°	1213.4	1215.1	1216.7	1218.4	1220.1	1220.9	1221.4	1222.5	1223.6	1224.7	1225.8
137.5°	1262.9	1265.1	1267.3	1269.5	1271.7	1272.8	1273.1	1273.6	1274.2	1274.7	1275.3
140°	1312.4	1314.0	1315.7	1317.3	1319.0	1319.8	1320.2	1321.0	1321.9	1322.7	1323.5
142.5°	1358.2	1359.8	1361.5	1363.1	1364.8	1365.6	1366.0	1366.8	1367.7	1368.5	1369.3
145°	1400.2	1402.1	1404.1	1406.0	1407.9	1408.9	1409.2	1409.7	1410.3	1410.8	1411.4
147.5°	1441.0	1442.4	1443.8	1445.1	1446.5	1447.2	1447.5	1448.0	1448.6	1449.1	1449.7
150°	1478.1	1478.9	1479.8	1480.6	1481.5	1481.9	1482.2	1482.7	1483.2	1483.8	1484.3
152.5°	1511.5	1511.8	1512.1	1512.4	1512.7	1512.8	1512.9	1513.2	1513.5	1513.7	1514.0
155°	1542.5	1541.9	1541.4	1540.8	1540.3	1540.0	1540.1	1540.4	1540.7	1540.9	1541.2
157.5°	1567.2	1567.2	1567.2	1567.2	1567.2	1567.2	1567.1	1566.8	1566.5	1566.3	1566.0
160°	1589.5	1589.2	1588.9	1588.6	1588.3	1588.2	1588.1	1587.8	1587.5	1587.3	1587.0
162.5°	1610.5	1609.7	1608.9	1608.0	1607.2	1606.8	1606.7	1606.4	1606.1	1605.9	1605.6
165°	1626.6	1625.8	1625.0	1624.1	1623.3	1622.9	1622.8	1622.5	1622.2	1621.9	1621.6
167.5°	1640.2	1639.1	1638.0	1636.9	1635.8	1635.2	1635.2	1635.2	1635.2	1635.2	1635.2
170°	1651.3	1650.2	1649.1	1648.0	1646.9	1646.4	1646.4	1646.4	1646.4	1646.4	1646.4
172.5°	1658.7	1657.3	1656.0	1654.6	1653.3	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8
175°	1664.9	1663.5	1662.1	1660.8	1659.4	1658.7	1658.8	1659.1	1659.4	1659.7	1660.0
177.5°	1667.4	1666.0	1664.6	1663.3	1661.9	1661.2	1661.3	1661.6	1661.9	1662.2	1662.5
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	30.8	31.9	33.0	34.1	34.6	34.9	35.4	36.0	36.5	37.1	36.5
92.5°	34.1	36.0	37.9	39.8	40.8	40.9	41.2	41.5	41.8	42.1	41.8
95°	40.2	42.2	44.1	46.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
97.5°	41.8	44.0	46.2	48.4	49.5	49.6	49.9	50.2	50.4	50.7	50.4
100°	43.0	45.2	47.4	49.6	50.7	50.8	51.1	51.4	51.7	52.0	51.7
102.5°	82.4	73.4	64.3	55.2	50.7	51.0	51.5	52.1	52.6	53.2	52.6
105°	222.3	173.6	125.0	76.3	52.0	52.3	52.8	53.3	53.9	54.4	53.9
107.5°	438.9	396.5	354.2	311.9	290.7	272.7	236.7	200.6	164.6	128.6	164.6
110°	548.8	539.7	530.6	521.5	517.0	497.4	458.1	418.8	379.5	340.2	379.5

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	638.3	640.7	643.2	645.7	646.9	646.6	646.1	645.5	645.0	644.4	645.0
115°	712.8	715.5	718.3	721.0	722.4	722.9	724.0	725.1	726.2	727.3	726.2
117.5°	785.2	787.4	789.6	791.8	792.9	793.0	793.3	793.6	793.8	794.1	793.8
120°	855.7	857.9	860.1	862.3	863.4	863.4	863.4	863.4	863.4	863.4	863.4
122.5°	925.4	926.8	928.1	929.5	930.2	930.3	930.6	930.9	931.1	931.4	931.1
125°	990.1	990.7	991.2	991.7	992.0	992.3	992.8	993.4	993.9	994.5	993.9
127.5°	1055.9	1056.7	1057.6	1058.4	1058.8	1058.5	1058.0	1057.5	1056.9	1056.4	1056.9
130°	1114.4	1115.5	1116.6	1117.7	1118.2	1117.9	1117.4	1116.8	1116.3	1115.7	1116.3
132.5°	1170.0	1171.1	1172.2	1173.3	1173.9	1173.5	1172.7	1171.8	1171.0	1170.2	1171.0
135°	1226.6	1227.4	1228.3	1229.1	1229.5	1229.1	1228.3	1227.4	1226.6	1225.8	1226.6
137.5°	1276.7	1278.1	1279.4	1280.8	1281.5	1281.2	1280.7	1280.1	1279.6	1279.0	1279.6
140°	1324.6	1325.7	1326.8	1327.9	1328.5	1328.2	1327.7	1327.1	1326.6	1326.0	1326.6
142.5°	1370.1	1370.9	1371.8	1372.6	1373.0	1372.6	1371.8	1370.9	1370.1	1369.3	1370.1
145°	1411.9	1412.5	1413.0	1413.5	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8
147.5°	1450.3	1450.8	1451.4	1451.9	1452.2	1451.5	1450.1	1448.8	1447.4	1446.0	1447.4
150°	1484.9	1485.4	1486.0	1486.5	1486.8	1486.4	1485.6	1484.7	1483.9	1483.1	1483.9
152.5°	1515.1	1516.2	1517.3	1518.4	1519.0	1518.3	1516.9	1515.6	1514.2	1512.8	1514.2
155°	1542.6	1544.0	1545.3	1546.7	1547.4	1546.6	1544.9	1543.3	1541.6	1540.0	1541.6
157.5°	1567.6	1569.3	1570.9	1572.6	1573.4	1572.3	1570.1	1567.9	1565.7	1563.5	1565.7
160°	1588.6	1590.3	1591.9	1593.6	1594.4	1593.4	1591.5	1589.6	1587.7	1585.8	1587.7
162.5°	1607.5	1609.4	1611.3	1613.2	1614.2	1613.4	1611.7	1610.1	1608.4	1606.8	1608.4
165°	1623.8	1626.0	1628.2	1630.4	1631.5	1630.5	1628.6	1626.7	1624.8	1622.9	1624.8
167.5°	1637.4	1639.6	1641.8	1644.0	1645.1	1644.0	1641.8	1639.6	1637.4	1635.2	1637.4
170°	1648.6	1650.8	1653.0	1655.2	1656.3	1655.2	1653.0	1650.8	1648.6	1646.4	1648.6
172.5°	1656.0	1658.2	1660.4	1662.6	1663.7	1662.5	1660.0	1657.5	1655.1	1652.6	1655.1
175°	1661.9	1663.8	1665.7	1667.6	1668.6	1667.5	1665.3	1663.1	1660.9	1658.7	1660.9
177.5°	1664.7	1666.9	1669.0	1671.2	1672.3	1670.9	1668.2	1665.5	1662.7	1660.0	1662.7
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	36.0	35.4	34.9	34.6	34.1	33.0	31.9	30.8	29.7	26.1	22.5
92.5°	41.5	41.2	40.9	40.8	39.8	37.9	36.0	34.1	32.2	29.7	27.2
95°	47.0	47.0	47.0	47.0	46.0	44.1	42.2	40.2	38.3	35.3	32.3
97.5°	50.2	49.9	49.6	49.5	48.4	46.2	44.0	41.8	39.6	53.6	67.6
100°	51.4	51.1	50.8	50.7	49.6	47.4	45.2	43.0	40.8	83.7	126.6
102.5°	52.1	51.5	51.0	50.7	55.2	64.3	73.4	82.4	91.5	139.3	187.2
105°	53.3	52.8	52.3	52.0	76.3	125.0	173.6	222.3	270.9	295.6	320.4
107.5°	200.6	236.7	272.7	290.7	311.9	354.2	396.5	438.9	481.2	477.1	472.9
110°	418.8	458.1	497.4	517.0	521.5	530.6	539.7	548.8	557.9	554.9	551.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	645.5	646.1	646.6	646.9	645.7	643.2	640.7	638.3	635.8	632.8	629.8
115°	725.1	724.0	722.9	722.4	721.0	718.3	715.5	712.8	710.0	707.5	705.1
117.5°	793.6	793.3	793.0	792.9	791.8	789.6	787.4	785.2	783.0	781.6	780.2
120°	863.4	863.4	863.4	863.4	862.3	860.1	857.9	855.7	853.5	852.7	851.9
122.5°	930.9	930.6	930.3	930.2	929.5	928.1	926.8	925.4	924.0	922.9	921.8
125°	993.4	992.8	992.3	992.0	991.7	991.2	990.7	990.1	989.6	988.5	987.4
127.5°	1057.5	1058.0	1058.5	1058.8	1058.4	1057.6	1056.7	1055.9	1055.1	1053.7	1052.3
130°	1116.8	1117.4	1117.9	1118.2	1117.7	1116.6	1115.5	1114.4	1113.3	1112.2	1111.1
132.5°	1171.8	1172.7	1173.5	1173.9	1173.3	1172.2	1171.1	1170.0	1168.9	1168.1	1167.3
135°	1227.4	1228.3	1229.1	1229.5	1229.1	1228.3	1227.4	1226.6	1225.8	1224.7	1223.6
137.5°	1280.1	1280.7	1281.2	1281.5	1280.8	1279.4	1278.1	1276.7	1275.3	1274.7	1274.2
140°	1327.1	1327.7	1328.2	1328.5	1327.9	1326.8	1325.7	1324.6	1323.5	1322.7	1321.9
142.5°	1370.9	1371.8	1372.6	1373.0	1372.6	1371.8	1370.9	1370.1	1369.3	1368.5	1367.7
145°	1413.8	1413.8	1413.8	1413.8	1413.5	1413.0	1412.5	1411.9	1411.4	1410.8	1410.3
147.5°	1448.8	1450.1	1451.5	1452.2	1451.9	1451.4	1450.8	1450.3	1449.7	1449.1	1448.6
150°	1484.7	1485.6	1486.4	1486.8	1486.5	1486.0	1485.4	1484.9	1484.3	1483.8	1483.2
152.5°	1515.6	1516.9	1518.3	1519.0	1518.4	1517.3	1516.2	1515.1	1514.0	1513.7	1513.5
155°	1543.3	1544.9	1546.6	1547.4	1546.7	1545.3	1544.0	1542.6	1541.2	1540.9	1540.7
157.5°	1567.9	1570.1	1572.3	1573.4	1572.6	1570.9	1569.3	1567.6	1566.0	1566.3	1566.5
160°	1589.6	1591.5	1593.4	1594.4	1593.6	1591.9	1590.3	1588.6	1587.0	1587.3	1587.5
162.5°	1610.1	1611.7	1613.4	1614.2	1613.2	1611.3	1609.4	1607.5	1605.6	1605.9	1606.1
165°	1626.7	1628.6	1630.5	1631.5	1630.4	1628.2	1626.0	1623.8	1621.6	1621.9	1622.2
167.5°	1639.6	1641.8	1644.0	1645.1	1644.0	1641.8	1639.6	1637.4	1635.2	1635.2	1635.2
170°	1650.8	1653.0	1655.2	1656.3	1655.2	1653.0	1650.8	1648.6	1646.4	1646.4	1646.4
172.5°	1657.5	1660.0	1662.5	1663.7	1662.6	1660.4	1658.2	1656.0	1653.8	1653.5	1653.3
175°	1663.1	1665.3	1667.5	1668.6	1667.6	1665.7	1663.8	1661.9	1660.0	1659.7	1659.4
177.5°	1665.5	1668.2	1670.9	1672.3	1671.2	1669.0	1666.9	1664.7	1662.5	1662.2	1661.9
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	19.0	15.4	13.6	12.2	9.5	6.7	4.0	1.2	4.0	6.7	9.5
92.5°	24.7	22.2	21.0	21.8	23.5	25.1	26.8	28.4	26.8	25.1	23.5
95°	29.2	26.2	24.7	30.3	41.6	52.9	64.2	75.5	64.2	52.9	41.6
97.5°	81.7	95.7	102.7	106.5	114.2	121.9	129.6	137.3	129.6	121.9	114.2
100°	169.5	212.4	233.8	231.0	225.5	220.0	214.5	209.0	214.5	220.0	225.5
102.5°	235.0	282.9	306.8	305.0	301.4	297.9	294.3	290.7	294.3	297.9	301.4
105°	345.1	369.8	382.2	380.7	377.7	374.6	371.6	368.6	371.6	374.6	377.7
107.5°	468.8	464.7	462.6	461.4	458.9	456.4	454.0	451.5	454.0	456.4	458.9
110°	548.8	545.8	544.3	543.2	541.0	538.8	536.6	534.4	536.6	538.8	541.0

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	626.7	623.7	622.2	621.2	619.3	617.4	615.4	613.5	615.4	617.4	619.3
115°	702.6	700.1	698.9	698.1	696.4	694.8	693.1	691.5	693.1	694.8	696.4
117.5°	778.9	777.5	776.8	775.8	773.9	772.0	770.0	768.1	770.0	772.0	773.9
120°	851.0	850.2	849.8	848.6	846.1	843.6	841.1	838.6	841.1	843.6	846.1
122.5°	920.7	919.6	919.1	918.1	916.2	914.3	912.3	910.4	912.3	914.3	916.2
125°	986.3	985.2	984.6	983.5	981.3	979.1	976.9	974.7	976.9	979.1	981.3
127.5°	1051.0	1049.6	1048.9	1047.8	1045.6	1043.4	1041.2	1039.0	1041.2	1043.4	1045.6
130°	1110.0	1108.9	1108.3	1107.2	1105.0	1102.8	1100.6	1098.4	1100.6	1102.8	1105.0
132.5°	1166.4	1165.6	1165.2	1164.1	1161.9	1159.7	1157.5	1155.3	1157.5	1159.7	1161.9
135°	1222.5	1221.4	1220.9	1220.1	1218.4	1216.7	1215.1	1213.4	1215.1	1216.7	1218.4
137.5°	1273.6	1273.1	1272.8	1271.7	1269.5	1267.3	1265.1	1262.9	1265.1	1267.3	1269.5
140°	1321.0	1320.2	1319.8	1319.0	1317.3	1315.7	1314.0	1312.4	1314.0	1315.7	1317.3
142.5°	1366.8	1366.0	1365.6	1364.8	1363.1	1361.5	1359.8	1358.2	1359.8	1361.5	1363.1
145°	1409.7	1409.2	1408.9	1407.9	1406.0	1404.1	1402.1	1400.2	1402.1	1404.1	1406.0
147.5°	1448.0	1447.5	1447.2	1446.5	1445.1	1443.8	1442.4	1441.0	1442.4	1443.8	1445.1
150°	1482.7	1482.2	1481.9	1481.5	1480.6	1479.8	1478.9	1478.1	1478.9	1479.8	1480.6
152.5°	1513.2	1512.9	1512.8	1512.7	1512.4	1512.1	1511.8	1511.5	1511.8	1512.1	1512.4
155°	1540.4	1540.1	1540.0	1540.3	1540.8	1541.4	1541.9	1542.5	1541.9	1541.4	1540.8
157.5°	1566.8	1567.1	1567.2	1567.2	1567.2	1567.2	1567.2	1567.2	1567.2	1567.2	1567.2
160°	1587.8	1588.1	1588.2	1588.3	1588.6	1588.9	1589.2	1589.5	1589.2	1588.9	1588.6
162.5°	1606.4	1606.7	1606.8	1607.2	1608.0	1608.9	1609.7	1610.5	1609.7	1608.9	1608.0
165°	1622.5	1622.8	1622.9	1623.3	1624.1	1625.0	1625.8	1626.6	1625.8	1625.0	1624.1
167.5°	1635.2	1635.2	1635.2	1635.8	1636.9	1638.0	1639.1	1640.2	1639.1	1638.0	1636.9
170°	1646.4	1646.4	1646.4	1646.9	1648.0	1649.1	1650.2	1651.3	1650.2	1649.1	1648.0
172.5°	1653.0	1652.7	1652.6	1653.3	1654.6	1656.0	1657.3	1658.7	1657.3	1656.0	1654.6
175°	1659.1	1658.8	1658.7	1659.4	1660.8	1662.1	1663.5	1664.9	1663.5	1662.1	1660.8
177.5°	1661.6	1661.3	1661.2	1661.9	1663.3	1664.6	1666.0	1667.4	1666.0	1664.6	1663.3
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	12.2	13.6	15.4	19.0	22.5	26.1	29.7	30.8	31.9	33.0	34.1
92.5°	21.8	21.0	22.2	24.7	27.2	29.7	32.2	34.1	36.0	37.9	39.8
95°	30.3	24.7	26.2	29.2	32.3	35.3	38.3	40.2	42.2	44.1	46.0
97.5°	106.5	102.7	95.7	81.7	67.6	53.6	39.6	41.8	44.0	46.2	48.4
100°	231.0	233.8	212.4	169.5	126.6	83.7	40.8	43.0	45.2	47.4	49.6
102.5°	305.0	306.8	282.9	235.0	187.2	139.3	91.5	82.4	73.4	64.3	55.2
105°	380.7	382.2	369.8	345.1	320.4	295.6	270.9	222.3	173.6	125.0	76.3
107.5°	461.4	462.6	464.7	468.8	472.9	477.1	481.2	438.9	396.5	354.2	311.9
110°	543.2	544.3	545.8	548.8	551.9	554.9	557.9	548.8	539.7	530.6	521.5

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	621.2	622.2	623.7	626.7	629.8	632.8	635.8	638.3	640.7	643.2	645.7
115°	698.1	698.9	700.1	702.6	705.1	707.5	710.0	712.8	715.5	718.3	721.0
117.5°	775.8	776.8	777.5	778.9	780.2	781.6	783.0	785.2	787.4	789.6	791.8
120°	848.6	849.8	850.2	851.0	851.9	852.7	853.5	855.7	857.9	860.1	862.3
122.5°	918.1	919.1	919.6	920.7	921.8	922.9	924.0	925.4	926.8	928.1	929.5
125°	983.5	984.6	985.2	986.3	987.4	988.5	989.6	990.1	990.7	991.2	991.7
127.5°	1047.8	1048.9	1049.6	1051.0	1052.3	1053.7	1055.1	1055.9	1056.7	1057.6	1058.4
130°	1107.2	1108.3	1108.9	1110.0	1111.1	1112.2	1113.3	1114.4	1115.5	1116.6	1117.7
132.5°	1164.1	1165.2	1165.6	1166.4	1167.3	1168.1	1168.9	1170.0	1171.1	1172.2	1173.3
135°	1220.1	1220.9	1221.4	1222.5	1223.6	1224.7	1225.8	1226.6	1227.4	1228.3	1229.1
137.5°	1271.7	1272.8	1273.1	1273.6	1274.2	1274.7	1275.3	1276.7	1278.1	1279.4	1280.8
140°	1319.0	1319.8	1320.2	1321.0	1321.9	1322.7	1323.5	1324.6	1325.7	1326.8	1327.9
142.5°	1364.8	1365.6	1366.0	1366.8	1367.7	1368.5	1369.3	1370.1	1370.9	1371.8	1372.6
145°	1407.9	1408.9	1409.2	1409.7	1410.3	1410.8	1411.4	1411.9	1412.5	1413.0	1413.5
147.5°	1446.5	1447.2	1447.5	1448.0	1448.6	1449.1	1449.7	1450.3	1450.8	1451.4	1451.9
150°	1481.5	1481.9	1482.2	1482.7	1483.2	1483.8	1484.3	1484.9	1485.4	1486.0	1486.5
152.5°	1512.7	1512.8	1512.9	1513.2	1513.5	1513.7	1514.0	1515.1	1516.2	1517.3	1518.4
155°	1540.3	1540.0	1540.1	1540.4	1540.7	1540.9	1541.2	1542.6	1544.0	1545.3	1546.7
157.5°	1567.2	1567.2	1567.1	1566.8	1566.5	1566.3	1566.0	1567.6	1569.3	1570.9	1572.6
160°	1588.3	1588.2	1588.1	1587.8	1587.5	1587.3	1587.0	1588.6	1590.3	1591.9	1593.6
162.5°	1607.2	1606.8	1606.7	1606.4	1606.1	1605.9	1605.6	1607.5	1609.4	1611.3	1613.2
165°	1623.3	1622.9	1622.8	1622.5	1622.2	1621.9	1621.6	1623.8	1626.0	1628.2	1630.4
167.5°	1635.8	1635.2	1635.2	1635.2	1635.2	1635.2	1635.2	1637.4	1639.6	1641.8	1644.0
170°	1646.9	1646.4	1646.4	1646.4	1646.4	1646.4	1646.4	1648.6	1650.8	1653.0	1655.2
172.5°	1653.3	1652.6	1652.7	1653.0	1653.3	1653.5	1653.8	1656.0	1658.2	1660.4	1662.6
175°	1659.4	1658.7	1658.8	1659.1	1659.4	1659.7	1660.0	1661.9	1663.8	1665.7	1667.6
177.5°	1661.9	1661.2	1661.3	1661.6	1661.9	1662.2	1662.5	1664.7	1666.9	1669.0	1671.2
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	34.6	34.9	35.4	36.0	36.5	37.1	36.5	36.0	35.4	34.9	34.6
92.5°	40.8	40.9	41.2	41.5	41.8	42.1	41.8	41.5	41.2	40.9	40.8
95°	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0	47.0
97.5°	49.5	49.6	49.9	50.2	50.4	50.7	50.4	50.2	49.9	49.6	49.5
100°	50.7	50.8	51.1	51.4	51.7	52.0	51.7	51.4	51.1	50.8	50.7
102.5°	50.7	51.0	51.5	52.1	52.6	53.2	52.6	52.1	51.5	51.0	50.7
105°	52.0	52.3	52.8	53.3	53.9	54.4	53.9	53.3	52.8	52.3	52.0
107.5°	290.7	272.7	236.7	200.6	164.6	128.6	164.6	200.6	236.7	272.7	290.7
110°	517.0	497.4	458.1	418.8	379.5	340.2	379.5	418.8	458.1	497.4	517.0

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	646.9	646.6	646.1	645.5	645.0	644.4	645.0	645.5	646.1	646.6	646.9
115°	722.4	722.9	724.0	725.1	726.2	727.3	726.2	725.1	724.0	722.9	722.4
117.5°	792.9	793.0	793.3	793.6	793.8	794.1	793.8	793.6	793.3	793.0	792.9
120°	863.4	863.4	863.4	863.4	863.4	863.4	863.4	863.4	863.4	863.4	863.4
122.5°	930.2	930.3	930.6	930.9	931.1	931.4	931.1	930.9	930.6	930.3	930.2
125°	992.0	992.3	992.8	993.4	993.9	994.5	993.9	993.4	992.8	992.3	992.0
127.5°	1058.8	1058.5	1058.0	1057.5	1056.9	1056.4	1056.9	1057.5	1058.0	1058.5	1058.8
130°	1118.2	1117.9	1117.4	1116.8	1116.3	1115.7	1116.3	1116.8	1117.4	1117.9	1118.2
132.5°	1173.9	1173.5	1172.7	1171.8	1171.0	1170.2	1171.0	1171.8	1172.7	1173.5	1173.9
135°	1229.5	1229.1	1228.3	1227.4	1226.6	1225.8	1226.6	1227.4	1228.3	1229.1	1229.5
137.5°	1281.5	1281.2	1280.7	1280.1	1279.6	1279.0	1279.6	1280.1	1280.7	1281.2	1281.5
140°	1328.5	1328.2	1327.7	1327.1	1326.6	1326.0	1326.6	1327.1	1327.7	1328.2	1328.5
142.5°	1373.0	1372.6	1371.8	1370.9	1370.1	1369.3	1370.1	1370.9	1371.8	1372.6	1373.0
145°	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8	1413.8
147.5°	1452.2	1451.5	1450.1	1448.8	1447.4	1446.0	1447.4	1448.8	1450.1	1451.5	1452.2
150°	1486.8	1486.4	1485.6	1484.7	1483.9	1483.1	1483.9	1484.7	1485.6	1486.4	1486.8
152.5°	1519.0	1518.3	1516.9	1515.6	1514.2	1512.8	1514.2	1515.6	1516.9	1518.3	1519.0
155°	1547.4	1546.6	1544.9	1543.3	1541.6	1540.0	1541.6	1543.3	1544.9	1546.6	1547.4
157.5°	1573.4	1572.3	1570.1	1567.9	1565.7	1563.5	1565.7	1567.9	1570.1	1572.3	1573.4
160°	1594.4	1593.4	1591.5	1589.6	1587.7	1585.8	1587.7	1589.6	1591.5	1593.4	1594.4
162.5°	1614.2	1613.4	1611.7	1610.1	1608.4	1606.8	1608.4	1610.1	1611.7	1613.4	1614.2
165°	1631.5	1630.5	1628.6	1626.7	1624.8	1622.9	1624.8	1626.7	1628.6	1630.5	1631.5
167.5°	1645.1	1644.0	1641.8	1639.6	1637.4	1635.2	1637.4	1639.6	1641.8	1644.0	1645.1
170°	1656.3	1655.2	1653.0	1650.8	1648.6	1646.4	1648.6	1650.8	1653.0	1655.2	1656.3
172.5°	1663.7	1662.5	1660.0	1657.5	1655.1	1652.6	1655.1	1657.5	1660.0	1662.5	1663.7
175°	1668.6	1667.5	1665.3	1663.1	1660.9	1658.7	1660.9	1663.1	1665.3	1667.5	1668.6
177.5°	1672.3	1670.9	1668.2	1665.5	1662.7	1660.0	1662.7	1665.5	1668.2	1670.9	1672.3
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	34.1	33.0	31.9	30.8	29.7	26.1	22.5	19.0	15.4	13.6	12.2
92.5°	39.8	37.9	36.0	34.1	32.2	29.7	27.2	24.7	22.2	21.0	21.8
95°	46.0	44.1	42.2	40.2	38.3	35.3	32.3	29.2	26.2	24.7	30.3
97.5°	48.4	46.2	44.0	41.8	39.6	53.6	67.6	81.7	95.7	102.7	106.5
100°	49.6	47.4	45.2	43.0	40.8	83.7	126.6	169.5	212.4	233.8	231.0
102.5°	55.2	64.3	73.4	82.4	91.5	139.3	187.2	235.0	282.9	306.8	305.0
105°	76.3	125.0	173.6	222.3	270.9	295.6	320.4	345.1	369.8	382.2	380.7
107.5°	311.9	354.2	396.5	438.9	481.2	477.1	472.9	468.8	464.7	462.6	461.4
110°	521.5	530.6	539.7	548.8	557.9	554.9	551.9	548.8	545.8	544.3	543.2

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	645.7	643.2	640.7	638.3	635.8	632.8	629.8	626.7	623.7	622.2	621.2
115°	721.0	718.3	715.5	712.8	710.0	707.5	705.1	702.6	700.1	698.9	698.1
117.5°	791.8	789.6	787.4	785.2	783.0	781.6	780.2	778.9	777.5	776.8	775.8
120°	862.3	860.1	857.9	855.7	853.5	852.7	851.9	851.0	850.2	849.8	848.6
122.5°	929.5	928.1	926.8	925.4	924.0	922.9	921.8	920.7	919.6	919.1	918.1
125°	991.7	991.2	990.7	990.1	989.6	988.5	987.4	986.3	985.2	984.6	983.5
127.5°	1058.4	1057.6	1056.7	1055.9	1055.1	1053.7	1052.3	1051.0	1049.6	1048.9	1047.8
130°	1117.7	1116.6	1115.5	1114.4	1113.3	1112.2	1111.1	1110.0	1108.9	1108.3	1107.2
132.5°	1173.3	1172.2	1171.1	1170.0	1168.9	1168.1	1167.3	1166.4	1165.6	1165.2	1164.1
135°	1229.1	1228.3	1227.4	1226.6	1225.8	1224.7	1223.6	1222.5	1221.4	1220.9	1220.1
137.5°	1280.8	1279.4	1278.1	1276.7	1275.3	1274.7	1274.2	1273.6	1273.1	1272.8	1271.7
140°	1327.9	1326.8	1325.7	1324.6	1323.5	1322.7	1321.9	1321.0	1320.2	1319.8	1319.0
142.5°	1372.6	1371.8	1370.9	1370.1	1369.3	1368.5	1367.7	1366.8	1366.0	1365.6	1364.8
145°	1413.5	1413.0	1412.5	1411.9	1411.4	1410.8	1410.3	1409.7	1409.2	1408.9	1407.9
147.5°	1451.9	1451.4	1450.8	1450.3	1449.7	1449.1	1448.6	1448.0	1447.5	1447.2	1446.5
150°	1486.5	1486.0	1485.4	1484.9	1484.3	1483.8	1483.2	1482.7	1482.2	1481.9	1481.5
152.5°	1518.4	1517.3	1516.2	1515.1	1514.0	1513.7	1513.5	1513.2	1512.9	1512.8	1512.7
155°	1546.7	1545.3	1544.0	1542.6	1541.2	1540.9	1540.7	1540.4	1540.1	1540.0	1540.3
157.5°	1572.6	1570.9	1569.3	1567.6	1566.0	1566.3	1566.5	1566.8	1567.1	1567.2	1567.2
160°	1593.6	1591.9	1590.3	1588.6	1587.0	1587.3	1587.5	1587.8	1588.1	1588.2	1588.3
162.5°	1613.2	1611.3	1609.4	1607.5	1605.6	1605.9	1606.1	1606.4	1606.7	1606.8	1607.2
165°	1630.4	1628.2	1626.0	1623.8	1621.6	1621.9	1622.2	1622.5	1622.8	1622.9	1623.3
167.5°	1644.0	1641.8	1639.6	1637.4	1635.2	1635.2	1635.2	1635.2	1635.2	1635.2	1635.8
170°	1655.2	1653.0	1650.8	1648.6	1646.4	1646.4	1646.4	1646.4	1646.4	1646.4	1646.9
172.5°	1662.6	1660.4	1658.2	1656.0	1653.8	1653.5	1653.3	1653.0	1652.7	1652.6	1653.3
175°	1667.6	1665.7	1663.8	1661.9	1660.0	1659.7	1659.4	1659.1	1658.8	1658.7	1659.4
177.5°	1671.2	1669.0	1666.9	1664.7	1662.5	1662.2	1661.9	1661.6	1661.3	1661.2	1661.9
180°	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9	1664.9

TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	9.5	6.7	4.0	1.2
92.5°	23.5	25.1	26.8	28.4
95°	41.6	52.9	64.2	75.5
97.5°	114.2	121.9	129.6	137.3
100°	225.5	220.0	214.5	209.0
102.5°	301.4	297.9	294.3	290.7
105°	377.7	374.6	371.6	368.6
107.5°	458.9	456.4	454.0	451.5
110°	541.0	538.8	536.6	534.4



TEST NUMBER: P1030958

CATALOG NUMBER: S123DIW-B775D1320UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	619.3	617.4	615.4	613.5
115°	696.4	694.8	693.1	691.5
117.5°	773.9	772.0	770.0	768.1
120°	846.1	843.6	841.1	838.6
122.5°	916.2	914.3	912.3	910.4
125°	981.3	979.1	976.9	974.7
127.5°	1045.6	1043.4	1041.2	1039.0
130°	1105.0	1102.8	1100.6	1098.4
132.5°	1161.9	1159.7	1157.5	1155.3
135°	1218.4	1216.7	1215.1	1213.4
137.5°	1269.5	1267.3	1265.1	1262.9
140°	1317.3	1315.7	1314.0	1312.4
142.5°	1363.1	1361.5	1359.8	1358.2
145°	1406.0	1404.1	1402.1	1400.2
147.5°	1445.1	1443.8	1442.4	1441.0
150°	1480.6	1479.8	1478.9	1478.1
152.5°	1512.4	1512.1	1511.8	1511.5
155°	1540.8	1541.4	1541.9	1542.5
157.5°	1567.2	1567.2	1567.2	1567.2
160°	1588.6	1588.9	1589.2	1589.5
162.5°	1608.0	1608.9	1609.7	1610.5
165°	1624.1	1625.0	1625.8	1626.6
167.5°	1636.9	1638.0	1639.1	1640.2
170°	1648.0	1649.1	1650.2	1651.3
172.5°	1654.6	1656.0	1657.3	1658.7
175°	1660.8	1662.1	1663.5	1664.9
177.5°	1663.3	1664.6	1666.0	1667.4
180°	1664.9	1664.9	1664.9	1664.9

(END OF REPORT)