

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031127

Luminaire Tested: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031127
REPORT IS A COMBINATION OF REPORTS P994213 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6630.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	41	40	39	26	25	25	25	25	17
2	83	76	71	66	73	68	63	59	52	48	46	37	35	33	23	22	21	21	21	15
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	20	19	18	18	18	13
4	70	60	52	47	61	53	47	42	41	36	33	29	26	24	18	17	16	16	16	11
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	13	12	12	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	11	11	8
8	50	39	31	26	44	34	28	24	27	22	19	19	17	14	13	11	10	10	10	7
9	47	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	21	38	29	23	19	22	18	15	16	14	12	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5727	5727	5727	5727
5°	5732	6597	5747	4894
10°	5681	7964	5707	4275
15°	5623	9037	5623	3769
20°	5508	9748	5538	3344
25°	5424	9262	5412	3051
30°	5325	6417	5314	2765
35°	5207	4120	5184	2549
40°	5061	2909	5034	2334
45°	4804	2328	4797	2125
50°	4490	1948	4475	1880
55°	4135	1605	4102	1594
60°	3788	1326	3751	1356
65°	3382	1061	3404	1149
70°	3004	738	3086	930
75°	2549	547	2651	714
80°	2030	362	2199	535
85°	1441	171	1575	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7647 cd/sqm

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	0.8
10°-20°	163.6	2.5
20°-30°	257.6	3.9
30°-40°	267.9	4.0
40°-50°	229.2	3.5
50°-60°	174.7	2.6
60°-70°	111.9	1.7
70°-80°	53.6	0.8
80°-90°	17.6	0.3
90°-100°	61.3	0.9
100°-110°	296.5	4.5
110°-120°	726.6	11.0
120°-130°	922.4	13.9
130°-140°	985.3	14.9
140°-150°	921.4	13.9
150°-160°	743.2	11.2
160°-170°	479.6	7.2
170°-180°	165.3	2.5
0°-30°	473.5	7.1
0°-40°	741.4	11.2
0°-60°	1145.3	17.3
0°-90°	1328.5	20.0
90°-120°	1084.4	16.4
90°-150°	3913.4	59.0
90°-180°	5302.0	80.0
0°-180°	6630.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	532	532	532	532	532	
5°	532	632	533	469	532	50
15°	508	898	508	374	508	143
25°	462	925	461	305	462	213
35°	403	401	401	248	403	252
45°	324	214	323	195	324	249
55°	228	134	226	134	228	205
65°	140	77	141	84	140	140
75°	67	33	70	43	67	72
85°	15	8	16	15	15	17
90°	1	39	1	39	1	5
95°	79	49	79	49	79	94
105°	385	57	385	57	385	408
115°	722	760	722	760	722	713
125°	1018	1039	1018	1039	1018	910
135°	1267	1280	1267	1280	1267	976
145°	1462	1477	1462	1477	1462	916
155°	1611	1608	1611	1608	1611	742
165°	1699	1695	1699	1695	1699	480
175°	1739	1733	1739	1733	1739	166
180°	1739	1739	1739	1739	1739	

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4FO-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	533.5	537.1	539.9	541.7	546.2	549.0	551.3	555.4	555.4	556.3	558.1
5°	531.7	539.4	544.9	552.2	561.7	566.3	572.7	578.1	585.9	590.0	594.1
7.5°	527.6	538.5	549.9	560.8	574.9	584.1	590.4	604.6	614.6	626.9	636.4
10°	522.1	537.1	551.7	568.6	587.7	601.4	610.9	629.6	648.7	666.1	680.6
12.5°	515.3	533.5	554.4	574.9	601.8	615.5	631.0	654.2	681.5	703.4	723.0
15°	508.0	528.9	552.6	577.7	611.4	630.5	652.8	681.1	711.6	743.0	769.9
17.5°	496.6	523.0	549.4	585.9	625.5	636.9	656.0	694.8	732.6	760.8	793.6
20°	485.2	514.8	548.1	580.9	623.7	650.1	667.9	708.9	749.4	783.6	815.0
22.5°	474.7	505.7	540.3	581.8	621.9	648.3	670.6	713.4	760.4	798.6	837.4
25°	462.0	495.7	533.9	573.1	621.9	641.9	666.5	716.2	765.8	810.0	857.9
27.5°	448.3	482.5	520.3	560.4	605.0	634.6	658.8	712.1	772.7	820.0	869.2
30°	434.6	469.7	506.1	542.1	592.3	620.5	648.3	707.1	776.3	830.5	868.3
32.5°	421.4	451.0	487.0	522.1	571.8	602.7	634.2	702.0	777.7	823.2	841.5
35°	403.2	434.2	463.3	500.7	550.8	581.3	618.2	701.6	771.8	800.0	790.9
37.5°	386.3	412.3	440.1	473.3	524.8	564.5	602.7	689.7	752.2	754.0	702.5
40°	367.7	389.1	412.3	447.4	503.0	542.1	583.6	671.5	716.6	689.7	599.1
42.5°	346.2	365.4	383.6	417.8	478.4	522.1	566.7	648.7	665.1	603.2	508.9
45°	323.5	339.0	355.8	391.8	452.4	495.7	540.3	613.7	596.8	509.3	419.6
47.5°	299.8	313.0	329.4	362.2	424.6	468.8	511.2	563.6	520.7	426.9	351.7
50°	276.1	286.6	302.5	336.2	396.4	436.4	475.6	509.8	449.7	366.3	290.7
52.5°	252.8	261.0	277.4	306.1	364.5	402.7	431.0	444.2	383.1	302.5	252.4
55°	228.2	237.4	248.3	277.4	335.3	363.6	382.2	381.8	318.9	256.5	208.7
57.5°	204.6	212.8	222.3	251.5	298.4	317.5	333.5	325.7	266.1	210.0	179.0
60°	183.6	188.2	198.6	223.2	258.8	275.2	284.3	271.1	217.3	177.2	148.1
62.5°	160.8	165.4	174.0	197.3	219.1	227.8	235.5	218.7	179.5	144.4	126.7
65°	139.9	145.8	151.3	169.9	181.8	192.3	191.3	177.2	140.3	117.5	103.0
67.5°	121.6	123.9	128.5	139.9	145.3	153.1	153.5	137.6	113.0	95.7	87.0
70°	102.0	104.3	107.5	113.0	116.6	118.5	117.5	103.4	85.2	74.7	67.0
72.5°	85.2	84.7	87.0	87.0	90.7	90.2	87.5	76.5	64.7	56.0	51.5
75°	67.0	67.4	67.9	67.0	65.6	63.8	61.5	53.3	45.6	41.5	37.4
77.5°	52.4	51.5	51.9	48.7	46.9	45.1	41.9	37.8	31.4	30.5	28.7
80°	37.4	36.9	36.4	35.1	31.0	29.2	26.9	24.6	23.2	22.3	21.9
82.5°	25.1	25.1	24.1	21.4	19.1	17.8	17.3	16.4	15.0	15.0	14.6
85°	15.0	14.6	13.7	10.9	9.6	9.6	9.6	9.6	8.7	8.7	8.2
87.5°	5.9	5.5	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.3	4.2	7.0	9.9	12.8	14.2	16.1	19.8	23.5	27.3	31.0
92.5°	29.7	28.0	26.3	24.6	22.9	22.0	23.3	25.9	28.4	31.0	33.6
95°	78.8	67.0	55.2	43.5	31.7	25.8	27.4	30.6	33.7	36.9	40.1
97.5°	143.4	135.4	127.3	119.3	111.2	107.2	99.9	85.2	70.6	55.9	41.3
100°	218.3	224.1	229.8	235.6	241.3	244.2	221.8	177.0	132.2	87.4	42.6
102.5°	303.6	307.3	311.1	314.8	318.5	320.4	295.4	245.5	195.5	145.6	95.6
105°	385.0	388.2	391.3	394.5	397.6	399.2	386.3	360.4	334.6	308.7	282.9
107.5°	471.6	474.2	476.8	479.3	481.9	483.2	485.4	489.7	494.0	498.3	502.6
110°	558.1	560.4	562.7	565.0	567.3	568.5	570.1	573.2	576.4	579.5	582.7

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	640.8	642.8	644.8	646.9	648.9	649.9	651.5	654.6	657.8	660.9	664.1
115°	722.2	723.9	725.7	727.4	729.1	730.0	731.3	733.9	736.4	739.0	741.6
117.5°	802.3	804.3	806.3	808.4	810.4	811.4	812.1	813.5	815.0	816.4	817.8
120°	876.0	878.6	881.2	883.7	886.3	887.6	888.0	888.9	889.8	890.6	891.5
122.5°	950.9	952.9	954.9	956.9	958.9	959.9	960.5	961.6	962.8	963.9	965.1
125°	1018.1	1020.4	1022.7	1025.0	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6
127.5°	1085.3	1087.6	1089.9	1092.2	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1
130°	1147.3	1149.6	1151.9	1154.2	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8
132.5°	1206.7	1209.0	1211.3	1213.6	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9
135°	1267.4	1269.1	1270.9	1272.6	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4
137.5°	1319.1	1321.4	1323.7	1326.0	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0
140°	1370.8	1372.5	1374.2	1375.9	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4
142.5°	1418.6	1420.3	1422.1	1423.8	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2
145°	1462.5	1464.5	1466.5	1468.6	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2
147.5°	1505.2	1506.6	1508.0	1509.5	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2
150°	1543.9	1544.8	1545.6	1546.5	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4
152.5°	1578.8	1579.1	1579.4	1579.7	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4
155°	1611.1	1610.5	1609.9	1609.4	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8
157.5°	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7
160°	1660.2	1659.9	1659.6	1659.3	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6
162.5°	1682.2	1681.3	1680.5	1679.6	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0
165°	1699.0	1698.1	1697.3	1696.4	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8
167.5°	1713.2	1712.0	1710.9	1709.7	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0
170°	1724.8	1723.6	1722.5	1721.3	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6
172.5°	1732.6	1731.2	1729.7	1728.3	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4
175°	1739.0	1737.6	1736.2	1734.7	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8
177.5°	1741.6	1740.2	1738.7	1737.3	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4FO-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	561.7	561.7	565.8	569.9	567.7	569.0	574.0	572.2	575.9	575.4	576.8
5°	604.1	609.1	613.2	621.9	623.2	621.9	630.5	632.8	636.9	631.9	634.2
7.5°	651.9	662.4	672.4	685.2	689.3	690.2	694.8	701.1	706.6	696.6	701.6
10°	698.4	714.3	734.8	746.2	756.3	759.9	763.6	767.7	774.0	780.0	775.4
12.5°	748.5	771.8	791.3	811.8	824.1	822.8	833.3	836.0	841.0	842.4	844.2
15°	789.5	822.3	834.6	865.1	867.9	877.0	888.8	899.3	900.7	897.9	897.9
17.5°	828.7	856.9	878.8	903.4	908.4	916.2	931.2	936.2	938.0	937.6	937.6
20°	860.6	879.3	916.2	936.7	944.9	954.9	965.4	971.8	973.1	974.9	972.2
22.5°	881.5	909.8	939.9	956.7	963.6	967.2	974.0	975.9	973.6	974.0	974.5
25°	897.9	925.7	944.0	948.5	948.1	943.5	938.5	929.8	928.9	925.3	918.0
27.5°	902.5	913.0	910.7	892.0	873.3	871.5	841.5	825.1	806.4	809.1	798.6
30°	877.9	864.2	831.9	784.5	764.9	733.0	699.3	664.2	650.6	635.5	663.3
32.5°	817.8	769.0	711.6	650.1	617.3	589.1	553.1	527.6	513.0	500.7	524.4
35°	727.1	651.0	574.9	516.6	489.7	464.2	430.5	417.8	399.5	401.4	403.6
37.5°	610.5	526.6	469.2	411.8	394.1	383.6	359.0	339.4	333.0	331.2	331.2
40°	501.1	432.3	381.3	336.2	322.6	313.9	294.3	285.2	278.4	276.5	278.8
42.5°	414.6	355.8	316.2	286.1	276.5	265.6	257.4	246.0	244.6	241.5	245.6
45°	348.1	297.0	267.4	245.6	237.4	233.3	224.1	217.3	214.6	214.1	217.3
47.5°	295.2	255.6	229.6	215.9	209.6	205.5	197.7	195.0	192.3	193.2	191.8
50°	247.8	218.2	201.4	189.1	185.0	180.9	175.9	173.1	171.8	171.8	171.3
52.5°	212.8	188.2	177.2	165.8	164.0	161.7	156.3	154.4	152.2	151.7	153.5
55°	182.2	165.4	154.4	147.6	145.8	141.2	139.0	136.7	135.3	134.4	134.9
57.5°	155.8	143.1	135.8	129.8	126.7	124.8	120.7	120.3	119.4	119.4	118.9
60°	133.9	124.8	116.2	112.5	110.3	108.0	107.5	104.8	103.4	104.3	103.9
62.5°	113.4	106.1	101.1	97.0	95.7	93.8	92.5	91.6	90.2	90.7	90.7
65°	94.8	88.8	85.2	81.5	81.1	79.3	78.8	77.9	77.9	77.4	78.4
67.5°	77.9	73.8	70.6	68.3	67.0	67.4	65.6	64.2	64.2	63.8	65.1
70°	62.0	59.7	56.5	53.8	51.9	51.9	49.7	49.2	49.2	49.2	48.7
72.5°	47.8	43.7	42.4	41.5	41.5	41.5	40.5	40.5	40.1	40.5	40.1
75°	35.5	35.1	34.2	33.7	33.7	33.3	32.8	32.8	32.8	32.8	32.8
77.5°	27.8	27.8	26.9	26.4	26.4	26.4	26.0	26.0	25.5	25.5	25.5
80°	20.5	20.5	19.6	19.6	19.6	19.1	19.1	19.1	19.6	19.1	19.1
82.5°	14.1	14.1	13.7	14.1	13.7	13.2	13.2	13.2	12.8	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	32.2	33.3	34.5	35.6	36.2	36.5	37.1	37.6	38.2	38.8	38.2
92.5°	35.6	37.6	39.6	41.6	42.6	42.7	43.0	43.3	43.6	43.9	43.6
95°	42.1	44.1	46.1	48.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	43.6	45.9	48.2	50.5	51.7	51.8	52.1	52.4	52.7	53.0	52.7
100°	44.9	47.2	49.5	51.8	53.0	53.1	53.4	53.7	54.0	54.3	54.0
102.5°	86.1	76.7	67.2	57.7	53.0	53.3	53.9	54.4	55.0	55.6	55.0
105°	232.1	181.3	130.5	79.7	54.3	54.6	55.1	55.7	56.2	56.8	56.2
107.5°	458.4	414.2	369.9	325.7	303.6	284.8	247.2	209.6	172.0	134.4	172.0
110°	573.2	563.7	554.2	544.7	540.0	519.5	478.4	437.4	396.3	355.3	396.3

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	666.7	669.3	671.8	674.4	675.7	675.4	674.8	674.3	673.7	673.1	673.7
115°	744.5	747.3	750.2	753.1	754.5	755.1	756.2	757.4	758.5	759.7	758.5
117.5°	820.1	822.4	824.7	827.0	828.2	828.3	828.6	828.9	829.2	829.5	829.2
120°	893.8	896.1	898.4	900.7	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	966.5	968.0	969.4	970.9	971.6	971.7	972.0	972.3	972.6	972.9	972.6
125°	1034.2	1034.8	1035.3	1035.9	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2
127.5°	1102.9	1103.8	1104.6	1105.5	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0
130°	1164.0	1165.1	1166.3	1167.4	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0
132.5°	1222.1	1223.2	1224.4	1225.5	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1
135°	1281.2	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2
137.5°	1333.4	1334.9	1336.3	1337.8	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5
140°	1383.6	1384.7	1385.9	1387.0	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6
142.5°	1431.1	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1
145°	1474.8	1475.3	1475.9	1476.4	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1514.8	1515.4	1515.9	1516.5	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7
150°	1551.0	1551.6	1552.1	1552.7	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0
152.5°	1582.6	1583.7	1584.9	1586.0	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5
155°	1611.2	1612.7	1614.1	1615.6	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2
157.5°	1637.4	1639.1	1640.8	1642.5	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4
160°	1659.3	1661.1	1662.8	1664.5	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3
162.5°	1679.0	1681.0	1683.0	1685.0	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0
165°	1696.1	1698.4	1700.7	1703.0	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1
167.5°	1710.3	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3
170°	1721.9	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9
172.5°	1729.7	1732.0	1734.3	1736.6	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7
175°	1735.8	1737.8	1739.9	1741.9	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9
177.5°	1738.7	1741.0	1743.3	1745.6	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	574.5	571.8	569.9	568.6	567.2	571.3	565.8	559.9	555.8	553.1	552.2
5°	634.6	628.7	623.7	619.6	620.5	620.5	610.9	600.5	591.3	586.3	580.9
7.5°	704.3	697.9	687.9	685.6	683.8	672.4	662.9	643.7	632.3	621.0	610.9
10°	773.6	765.4	755.8	752.6	748.1	733.9	719.4	694.8	680.6	659.7	646.5
12.5°	838.3	828.2	818.7	816.4	809.6	797.3	772.2	746.7	722.5	700.2	677.0
15°	892.5	889.7	875.2	866.1	851.0	834.2	828.7	794.1	763.6	740.3	698.4
17.5°	938.0	925.3	911.6	905.7	899.8	880.2	860.6	825.1	792.3	758.1	731.2
20°	974.5	960.4	950.8	942.1	939.4	917.1	886.1	854.7	818.7	780.4	745.3
22.5°	976.3	974.5	968.1	963.1	957.6	943.0	918.4	879.3	841.0	799.1	753.1
25°	938.5	935.8	954.0	949.4	953.1	947.6	934.4	901.6	856.9	807.7	761.3
27.5°	824.6	852.4	881.1	891.1	897.9	917.5	923.9	905.7	869.7	817.3	765.4
30°	669.7	706.6	753.1	778.1	797.3	833.7	881.1	887.0	870.2	828.2	764.5
32.5°	525.7	559.5	596.8	626.4	651.9	726.6	790.4	836.4	844.6	822.8	766.7
35°	423.7	438.3	473.8	502.0	536.7	600.5	675.6	749.9	800.0	802.7	759.9
37.5°	349.4	357.2	388.2	404.1	424.6	480.6	550.8	647.8	725.7	762.6	740.8
40°	289.3	307.1	324.8	333.9	348.5	387.2	454.7	530.7	627.3	695.7	711.2
42.5°	251.0	258.8	270.2	282.9	292.0	325.7	370.8	440.5	527.6	622.8	665.6
45°	221.4	224.1	236.0	244.2	253.8	277.4	309.3	367.7	444.2	538.0	610.9
47.5°	196.8	202.3	208.7	213.7	220.0	238.3	265.6	308.0	375.4	459.2	537.6
50°	174.9	178.1	186.3	188.6	193.2	205.9	226.9	259.2	314.8	381.8	462.9
52.5°	154.4	160.4	163.6	166.7	170.8	181.3	195.0	221.4	263.3	326.2	395.0
55°	138.5	140.3	144.9	147.6	150.8	158.1	169.9	189.5	222.3	272.4	337.6
57.5°	123.0	123.0	127.6	129.8	133.0	138.5	149.0	164.0	187.7	225.1	284.7
60°	106.6	107.1	110.7	113.4	114.4	119.8	128.5	140.3	158.5	185.9	234.6
62.5°	92.0	94.3	96.1	97.0	100.2	103.4	110.7	118.9	131.7	155.8	190.4
65°	79.7	80.2	81.5	82.5	83.8	87.5	92.9	98.4	109.3	127.1	155.4
67.5°	65.6	67.4	69.2	69.2	70.6	72.4	77.9	82.5	90.7	101.1	120.3
70°	49.2	50.1	52.8	54.2	56.0	59.2	62.0	64.7	71.1	78.8	93.4
72.5°	41.0	41.0	41.9	42.4	42.4	44.6	48.7	51.5	54.7	60.1	70.2
75°	32.8	32.8	34.2	33.7	34.6	35.5	36.0	37.8	39.6	43.7	49.7
77.5°	26.0	26.4	26.4	26.9	26.9	27.3	27.8	28.7	29.6	31.9	34.6
80°	19.1	19.6	19.6	20.0	20.0	20.5	21.0	21.4	22.3	23.2	24.6
82.5°	13.2	13.7	13.7	14.1	13.7	14.1	14.6	14.6	15.0	15.9	16.4
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.7	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	37.6	37.1	36.5	36.2	35.6	34.5	33.3	32.2	31.0	27.3	23.5
92.5°	43.3	43.0	42.7	42.6	41.6	39.6	37.6	35.6	33.6	31.0	28.4
95°	49.1	49.1	49.1	49.1	48.1	46.1	44.1	42.1	40.1	36.9	33.7
97.5°	52.4	52.1	51.8	51.7	50.5	48.2	45.9	43.6	41.3	55.9	70.6
100°	53.7	53.4	53.1	53.0	51.8	49.5	47.2	44.9	42.6	87.4	132.2
102.5°	54.4	53.9	53.3	53.0	57.7	67.2	76.7	86.1	95.6	145.6	195.5
105°	55.7	55.1	54.6	54.3	79.7	130.5	181.3	232.1	282.9	308.7	334.6
107.5°	209.6	247.2	284.8	303.6	325.7	369.9	414.2	458.4	502.6	498.3	494.0
110°	437.4	478.4	519.5	540.0	544.7	554.2	563.7	573.2	582.7	579.5	576.4

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	674.3	674.8	675.4	675.7	674.4	671.8	669.3	666.7	664.1	660.9	657.8
115°	757.4	756.2	755.1	754.5	753.1	750.2	747.3	744.5	741.6	739.0	736.4
117.5°	828.9	828.6	828.3	828.2	827.0	824.7	822.4	820.1	817.8	816.4	815.0
120°	901.8	901.8	901.8	901.8	900.7	898.4	896.1	893.8	891.5	890.6	889.8
122.5°	972.3	972.0	971.7	971.6	970.9	969.4	968.0	966.5	965.1	963.9	962.8
125°	1037.6	1037.1	1036.5	1036.2	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3
127.5°	1104.5	1105.1	1105.6	1105.9	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2
130°	1166.6	1167.1	1167.7	1168.0	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5
132.5°	1223.9	1224.8	1225.7	1226.1	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2
135°	1282.1	1282.9	1283.8	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1
137.5°	1337.1	1337.6	1338.2	1338.5	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9
140°	1386.2	1386.7	1387.3	1387.6	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7
142.5°	1431.9	1432.8	1433.7	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5
145°	1476.7	1476.7	1476.7	1476.7	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0
147.5°	1513.2	1514.6	1516.1	1516.8	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0
150°	1550.8	1551.7	1552.6	1553.0	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2
152.5°	1583.0	1584.4	1585.9	1586.6	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8
155°	1612.0	1613.7	1615.4	1616.3	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2
157.5°	1637.7	1640.0	1642.3	1643.4	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2
160°	1660.3	1662.4	1664.4	1665.4	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2
162.5°	1681.7	1683.4	1685.1	1686.0	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6
165°	1699.1	1701.1	1703.1	1704.1	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4
167.5°	1712.6	1714.9	1717.2	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0
170°	1724.2	1726.5	1728.8	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6
172.5°	1731.3	1733.8	1736.4	1737.7	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8
175°	1737.2	1739.5	1741.8	1742.9	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3
177.5°	1739.6	1742.5	1745.4	1746.8	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	550.8	548.5	546.2	546.2	541.2	536.7	534.4	535.3	532.6	528.9	525.3
5°	574.9	565.8	564.0	559.0	552.2	542.6	537.6	533.0	527.6	520.3	513.4
7.5°	597.3	585.4	579.0	574.0	560.8	547.6	536.7	529.4	519.8	508.9	500.7
10°	626.4	604.6	597.7	586.3	567.7	549.0	536.2	524.4	511.2	498.4	487.5
12.5°	649.7	624.6	611.8	600.5	576.3	552.6	531.2	516.6	500.7	486.6	472.4
15°	676.1	647.8	625.5	611.8	581.3	552.6	528.5	508.0	490.2	472.9	460.6
17.5°	688.8	653.3	643.3	623.7	579.5	550.8	521.2	499.3	477.9	457.9	443.3
20°	708.9	667.4	642.4	629.2	590.0	547.6	513.0	487.9	465.6	444.2	428.7
22.5°	710.2	665.1	648.7	623.7	575.4	538.0	505.7	475.2	449.2	429.2	413.2
25°	707.1	661.0	638.3	618.2	578.1	532.6	491.1	461.0	435.5	412.3	393.6
27.5°	705.7	649.2	627.8	607.7	562.6	516.6	482.5	448.3	419.1	398.6	379.5
30°	703.9	636.4	610.5	587.2	545.8	504.3	463.3	433.7	405.9	380.0	360.8
32.5°	692.0	619.1	592.7	568.1	523.5	482.0	449.7	418.2	388.2	364.0	346.7
35°	688.4	603.2	568.6	542.1	498.4	461.5	427.3	401.4	373.1	349.0	328.5
37.5°	677.9	586.8	549.4	515.7	470.2	435.1	410.0	384.1	356.7	330.8	314.3
40°	659.7	567.7	525.3	490.7	443.7	408.2	385.0	365.8	339.0	315.7	295.7
42.5°	632.8	548.1	502.5	466.1	414.1	380.9	361.7	343.5	320.7	296.6	280.2
45°	601.8	522.1	479.7	439.2	386.3	354.0	333.9	323.0	302.0	281.5	262.4
47.5°	559.5	495.2	453.3	411.4	357.6	326.2	310.2	299.3	284.7	262.4	246.9
50°	506.1	460.6	421.0	383.6	329.4	299.3	283.4	275.2	262.9	246.9	231.9
52.5°	446.9	420.5	387.7	353.1	300.7	272.4	257.9	251.5	242.4	227.3	214.6
55°	387.2	375.9	353.5	319.4	270.6	247.4	234.6	226.4	219.6	208.7	197.7
57.5°	333.9	328.5	313.0	286.6	245.6	221.4	210.5	205.0	199.5	191.3	180.4
60°	278.8	284.7	268.8	255.6	218.2	197.3	187.7	181.8	179.0	171.8	164.9
62.5°	231.0	236.4	227.3	217.3	190.9	172.2	166.3	160.8	159.0	152.6	145.8
65°	187.7	194.5	187.7	182.2	166.3	150.8	143.5	140.8	139.0	134.9	129.4
67.5°	149.4	156.3	153.1	146.2	141.2	128.5	124.4	121.6	120.7	117.5	113.0
70°	112.5	122.1	123.0	118.9	114.4	108.4	105.7	104.8	102.5	99.8	97.0
72.5°	81.1	92.0	92.5	92.5	89.7	89.7	87.0	85.6	85.6	82.9	79.7
75°	59.7	67.0	67.9	68.8	70.2	71.5	69.7	69.7	69.2	66.5	65.1
77.5°	39.6	46.0	48.3	51.5	53.3	53.3	54.2	55.1	54.2	52.8	51.9
80°	25.5	30.1	32.8	34.6	37.4	38.7	40.1	40.5	39.6	39.2	37.8
82.5°	16.9	18.2	19.6	21.9	25.1	27.3	27.3	26.9	27.8	27.3	26.9
85°	9.6	10.5	10.9	11.4	13.2	15.5	15.9	16.4	17.3	16.4	15.5
87.5°	3.6	4.1	4.1	4.1	5.0	5.5	6.8	8.7	8.2	7.3	7.3
90°	19.8	16.1	14.2	12.8	9.9	7.0	4.2	1.3	4.2	7.0	9.9
92.5°	25.9	23.3	22.0	22.9	24.6	26.3	28.0	29.7	28.0	26.3	24.6
95°	30.6	27.4	25.8	31.7	43.5	55.2	67.0	78.8	67.0	55.2	43.5
97.5°	85.2	99.9	107.2	111.2	119.3	127.3	135.4	143.4	135.4	127.3	119.3
100°	177.0	221.8	244.2	241.3	235.6	229.8	224.1	218.3	224.1	229.8	235.6
102.5°	245.5	295.4	320.4	318.5	314.8	311.1	307.3	303.6	307.3	311.1	314.8
105°	360.4	386.3	399.2	397.6	394.5	391.3	388.2	385.0	388.2	391.3	394.5
107.5°	489.7	485.4	483.2	481.9	479.3	476.8	474.2	471.6	474.2	476.8	479.3
110°	573.2	570.1	568.5	567.3	565.0	562.7	560.4	558.1	560.4	562.7	565.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	654.6	651.5	649.9	648.9	646.9	644.8	642.8	640.8	642.8	644.8	646.9
115°	733.9	731.3	730.0	729.1	727.4	725.7	723.9	722.2	723.9	725.7	727.4
117.5°	813.5	812.1	811.4	810.4	808.4	806.3	804.3	802.3	804.3	806.3	808.4
120°	888.9	888.0	887.6	886.3	883.7	881.2	878.6	876.0	878.6	881.2	883.7
122.5°	961.6	960.5	959.9	958.9	956.9	954.9	952.9	950.9	952.9	954.9	956.9
125°	1030.1	1029.0	1028.4	1027.3	1025.0	1022.7	1020.4	1018.1	1020.4	1022.7	1025.0
127.5°	1097.8	1096.3	1095.6	1094.5	1092.2	1089.9	1087.6	1085.3	1087.6	1089.9	1092.2
130°	1159.3	1158.2	1157.6	1156.5	1154.2	1151.9	1149.6	1147.3	1149.6	1151.9	1154.2
132.5°	1218.4	1217.5	1217.1	1215.9	1213.6	1211.3	1209.0	1206.7	1209.0	1211.3	1213.6
135°	1276.9	1275.8	1275.2	1274.3	1272.6	1270.9	1269.1	1267.4	1269.1	1270.9	1272.6
137.5°	1330.3	1329.8	1329.5	1328.3	1326.0	1323.7	1321.4	1319.1	1321.4	1323.7	1326.0
140°	1379.8	1378.9	1378.5	1377.6	1375.9	1374.2	1372.5	1370.8	1372.5	1374.2	1375.9
142.5°	1427.7	1426.8	1426.4	1425.5	1423.8	1422.1	1420.3	1418.6	1420.3	1422.1	1423.8
145°	1472.5	1471.9	1471.6	1470.6	1468.6	1466.5	1464.5	1462.5	1464.5	1466.5	1468.6
147.5°	1512.5	1511.9	1511.6	1510.9	1509.5	1508.0	1506.6	1505.2	1506.6	1508.0	1509.5
150°	1548.7	1548.1	1547.8	1547.4	1546.5	1545.6	1544.8	1543.9	1544.8	1545.6	1546.5
152.5°	1580.5	1580.2	1580.1	1580.0	1579.7	1579.4	1579.1	1578.8	1579.1	1579.4	1579.7
155°	1608.9	1608.6	1608.5	1608.8	1609.4	1609.9	1610.5	1611.1	1610.5	1609.9	1609.4
157.5°	1636.5	1636.8	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9	1636.9
160°	1658.5	1658.8	1658.9	1659.0	1659.3	1659.6	1659.9	1660.2	1659.9	1659.6	1659.3
162.5°	1677.9	1678.2	1678.3	1678.7	1679.6	1680.5	1681.3	1682.2	1681.3	1680.5	1679.6
165°	1694.7	1695.0	1695.1	1695.5	1696.4	1697.3	1698.1	1699.0	1698.1	1697.3	1696.4
167.5°	1708.0	1708.0	1708.0	1708.6	1709.7	1710.9	1712.0	1713.2	1712.0	1710.9	1709.7
170°	1719.6	1719.6	1719.6	1720.2	1721.3	1722.5	1723.6	1724.8	1723.6	1722.5	1721.3
172.5°	1726.5	1726.2	1726.1	1726.8	1728.3	1729.7	1731.2	1732.6	1731.2	1729.7	1728.3
175°	1733.0	1732.7	1732.6	1733.3	1734.7	1736.2	1737.6	1739.0	1737.6	1736.2	1734.7
177.5°	1735.5	1735.2	1735.1	1735.8	1737.3	1738.7	1740.2	1741.6	1740.2	1738.7	1737.3
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4FO-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	525.3	523.0	522.1	519.8	514.3	510.7	506.6	503.9	504.3	502.0	503.4
5°	508.9	508.4	505.2	500.7	492.9	488.8	481.5	477.9	476.1	476.5	473.8
7.5°	495.2	491.1	488.8	481.5	474.3	465.6	459.7	456.5	453.8	451.0	449.2
10°	479.7	476.1	472.4	464.7	454.7	446.5	438.3	435.1	431.0	429.2	427.8
12.5°	463.3	461.0	456.5	447.4	436.0	428.2	418.7	416.9	411.4	407.7	406.8
15°	448.3	446.9	438.7	428.2	416.9	409.1	400.9	395.4	386.3	388.2	385.0
17.5°	432.3	426.4	421.4	407.3	401.8	390.0	380.4	377.7	371.3	367.2	363.1
20°	414.6	410.9	404.6	395.4	382.2	368.6	361.3	356.7	353.1	346.7	344.9
22.5°	397.7	393.2	387.7	375.9	364.5	353.1	343.1	339.0	334.4	329.8	327.1
25°	384.5	377.7	371.8	357.2	345.8	336.2	329.8	323.0	316.6	313.9	313.0
27.5°	364.0	359.9	354.0	340.3	329.8	319.4	313.4	308.9	302.0	298.9	296.1
30°	350.8	342.6	335.8	324.8	314.3	303.0	297.5	292.0	287.9	283.8	280.6
32.5°	333.0	326.7	321.2	310.2	299.8	289.3	283.4	275.2	272.9	269.7	266.1
35°	315.7	311.6	305.7	293.8	282.5	275.2	268.8	261.0	258.3	256.0	252.8
37.5°	299.3	293.4	289.3	277.9	267.9	259.2	254.2	247.8	246.0	243.3	241.0
40°	285.2	279.3	275.2	263.8	253.3	244.2	241.0	234.6	231.9	228.7	227.3
42.5°	269.2	264.2	258.8	250.6	239.6	230.5	224.1	220.5	216.9	215.5	212.8
45°	252.4	247.8	243.7	234.6	223.2	216.9	211.4	206.4	203.6	201.4	199.5
47.5°	237.8	233.7	228.2	218.2	209.1	203.2	197.7	192.7	190.0	187.2	185.0
50°	221.0	218.7	212.8	203.2	194.5	187.7	182.7	178.1	176.3	173.1	169.5
52.5°	205.9	201.8	196.8	189.1	181.3	173.1	166.3	163.6	160.4	158.5	155.4
55°	188.2	185.4	180.0	173.1	164.9	158.1	153.1	149.4	145.3	143.5	139.4
57.5°	173.1	168.1	165.4	156.7	149.0	142.1	138.5	134.9	130.3	127.6	125.7
60°	156.7	152.2	148.1	140.8	135.3	128.0	122.6	119.4	116.2	112.5	110.7
62.5°	140.8	137.1	132.1	126.2	119.4	113.4	109.3	104.8	103.0	99.3	97.9
65°	123.5	120.7	116.6	109.8	104.3	99.3	95.2	91.6	89.7	88.4	87.5
67.5°	108.0	104.3	101.6	95.7	89.7	85.6	83.4	81.1	78.8	77.4	76.1
70°	92.0	89.3	86.6	81.1	77.0	73.3	71.5	69.7	68.3	67.0	65.6
72.5°	75.6	74.3	71.5	67.9	64.7	62.0	60.6	58.3	56.9	54.7	53.8
75°	62.4	60.1	58.8	55.6	52.8	50.6	48.7	46.0	44.2	43.3	42.8
77.5°	49.2	48.3	46.5	43.7	42.4	40.1	37.4	36.4	35.5	35.5	35.1
80°	36.9	35.5	34.2	31.9	30.5	28.7	28.7	28.7	28.2	28.7	28.2
82.5°	25.1	24.1	23.2	21.9	21.4	21.4	21.9	21.9	21.9	21.9	21.9
85°	14.6	14.6	14.6	15.0	14.6	14.6	15.0	15.5	15.0	15.0	14.6
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	12.8	14.2	16.1	19.8	23.5	27.3	31.0	32.2	33.3	34.5	35.6
92.5°	22.9	22.0	23.3	25.9	28.4	31.0	33.6	35.6	37.6	39.6	41.6
95°	31.7	25.8	27.4	30.6	33.7	36.9	40.1	42.1	44.1	46.1	48.1
97.5°	111.2	107.2	99.9	85.2	70.6	55.9	41.3	43.6	45.9	48.2	50.5
100°	241.3	244.2	221.8	177.0	132.2	87.4	42.6	44.9	47.2	49.5	51.8
102.5°	318.5	320.4	295.4	245.5	195.5	145.6	95.6	86.1	76.7	67.2	57.7
105°	397.6	399.2	386.3	360.4	334.6	308.7	282.9	232.1	181.3	130.5	79.7
107.5°	481.9	483.2	485.4	489.7	494.0	498.3	502.6	458.4	414.2	369.9	325.7
110°	567.3	568.5	570.1	573.2	576.4	579.5	582.7	573.2	563.7	554.2	544.7

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	648.9	649.9	651.5	654.6	657.8	660.9	664.1	666.7	669.3	671.8	674.4
115°	729.1	730.0	731.3	733.9	736.4	739.0	741.6	744.5	747.3	750.2	753.1
117.5°	810.4	811.4	812.1	813.5	815.0	816.4	817.8	820.1	822.4	824.7	827.0
120°	886.3	887.6	888.0	888.9	889.8	890.6	891.5	893.8	896.1	898.4	900.7
122.5°	958.9	959.9	960.5	961.6	962.8	963.9	965.1	966.5	968.0	969.4	970.9
125°	1027.3	1028.4	1029.0	1030.1	1031.3	1032.4	1033.6	1034.2	1034.8	1035.3	1035.9
127.5°	1094.5	1095.6	1096.3	1097.8	1099.2	1100.7	1102.1	1102.9	1103.8	1104.6	1105.5
130°	1156.5	1157.6	1158.2	1159.3	1160.5	1161.6	1162.8	1164.0	1165.1	1166.3	1167.4
132.5°	1215.9	1217.1	1217.5	1218.4	1219.2	1220.1	1220.9	1222.1	1223.2	1224.4	1225.5
135°	1274.3	1275.2	1275.8	1276.9	1278.1	1279.2	1280.4	1281.2	1282.1	1282.9	1283.8
137.5°	1328.3	1329.5	1329.8	1330.3	1330.9	1331.4	1332.0	1333.4	1334.9	1336.3	1337.8
140°	1377.6	1378.5	1378.9	1379.8	1380.7	1381.5	1382.4	1383.6	1384.7	1385.9	1387.0
142.5°	1425.5	1426.4	1426.8	1427.7	1428.5	1429.4	1430.2	1431.1	1431.9	1432.8	1433.7
145°	1470.6	1471.6	1471.9	1472.5	1473.0	1473.6	1474.2	1474.8	1475.3	1475.9	1476.4
147.5°	1510.9	1511.6	1511.9	1512.5	1513.0	1513.6	1514.2	1514.8	1515.4	1515.9	1516.5
150°	1547.4	1547.8	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.6	1552.1	1552.7
152.5°	1580.0	1580.1	1580.2	1580.5	1580.8	1581.1	1581.4	1582.6	1583.7	1584.9	1586.0
155°	1608.8	1608.5	1608.6	1608.9	1609.2	1609.5	1609.8	1611.2	1612.7	1614.1	1615.6
157.5°	1636.9	1636.9	1636.8	1636.5	1636.2	1636.0	1635.7	1637.4	1639.1	1640.8	1642.5
160°	1659.0	1658.9	1658.8	1658.5	1658.2	1657.9	1657.6	1659.3	1661.1	1662.8	1664.5
162.5°	1678.7	1678.3	1678.2	1677.9	1677.6	1677.3	1677.0	1679.0	1681.0	1683.0	1685.0
165°	1695.5	1695.1	1695.0	1694.7	1694.4	1694.1	1693.8	1696.1	1698.4	1700.7	1703.0
167.5°	1708.6	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1710.3	1712.6	1714.9	1717.2
170°	1720.2	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1721.9	1724.2	1726.5	1728.8
172.5°	1726.8	1726.1	1726.2	1726.5	1726.8	1727.1	1727.4	1729.7	1732.0	1734.3	1736.6
175°	1733.3	1732.6	1732.7	1733.0	1733.3	1733.5	1733.8	1735.8	1737.8	1739.9	1741.9
177.5°	1735.8	1735.1	1735.2	1735.5	1735.8	1736.1	1736.4	1738.7	1741.0	1743.3	1745.6
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.0	503.4	502.0	499.3	498.9	499.8	502.5	501.6	499.3	503.4	499.8
5°	475.2	472.9	472.0	472.9	470.2	468.8	471.5	470.2	471.5	472.0	473.3
7.5°	448.3	448.7	446.0	446.5	442.8	443.7	443.7	443.7	445.1	446.0	447.8
10°	425.1	426.0	422.8	423.2	420.5	418.7	420.0	422.8	422.8	422.8	423.7
12.5°	406.4	402.3	400.0	399.5	396.4	395.4	398.2	399.1	401.4	401.4	402.7
15°	383.1	382.2	380.4	380.4	372.7	374.5	375.4	378.6	383.1	379.5	380.4
17.5°	362.2	359.9	357.6	356.7	355.8	353.1	356.7	356.3	359.0	359.5	360.8
20°	343.5	341.7	337.1	337.6	338.5	334.4	336.7	336.7	339.4	342.1	345.3
22.5°	325.3	323.5	321.2	322.1	319.4	318.4	318.4	320.7	323.9	326.2	325.7
25°	311.2	308.0	306.6	305.2	303.9	304.8	303.4	305.7	308.0	309.3	308.0
27.5°	295.2	293.8	291.1	289.7	287.5	288.4	289.3	291.1	292.5	292.5	293.8
30°	279.7	277.9	277.0	275.6	275.6	273.8	274.3	276.1	277.4	278.8	280.6
32.5°	264.7	263.3	262.0	262.0	261.0	260.6	260.1	262.9	262.9	265.6	265.6
35°	252.4	250.1	250.1	247.8	248.7	248.3	247.4	249.2	249.7	251.5	251.0
37.5°	238.7	238.7	237.8	235.5	233.7	234.2	236.4	236.4	237.8	237.4	238.7
40°	225.1	224.1	224.1	222.8	222.3	221.9	222.3	222.8	225.1	224.6	225.1
42.5°	211.4	211.8	209.6	209.6	209.6	208.2	208.7	209.1	210.0	210.9	212.3
45°	198.2	197.3	196.8	195.9	195.0	195.4	195.0	196.8	196.4	197.3	198.6
47.5°	184.1	182.7	182.2	180.4	180.4	181.3	180.9	182.2	182.7	184.1	183.1
50°	170.4	168.6	167.2	167.7	164.9	165.8	165.8	167.2	168.6	169.0	169.9
52.5°	154.4	154.0	153.5	151.3	150.8	150.3	150.8	151.3	153.1	154.4	154.9
55°	139.0	138.5	135.8	134.9	133.5	133.5	134.4	134.9	138.0	138.5	140.3
57.5°	124.8	123.5	120.3	119.8	119.8	119.8	118.5	120.3	121.2	123.5	123.5
60°	109.3	109.3	106.6	106.6	107.1	106.6	106.6	107.1	107.1	108.9	109.8
62.5°	97.0	96.6	96.6	95.7	95.2	95.7	95.2	95.2	95.7	97.0	98.4
65°	86.1	85.6	85.2	84.7	83.8	83.8	84.3	85.2	85.2	86.1	86.6
67.5°	75.6	75.6	74.7	74.7	74.3	73.8	74.3	73.8	75.6	75.6	76.1
70°	65.1	64.7	63.3	62.9	61.5	62.0	62.0	63.3	63.8	64.7	65.6
72.5°	52.4	52.4	51.5	50.6	51.0	50.1	50.1	50.6	50.6	51.9	52.4
75°	43.3	42.4	41.9	42.4	41.9	42.8	41.9	41.9	42.8	42.8	42.8
77.5°	35.5	35.5	35.1	35.1	35.5	35.1	35.5	35.5	35.5	35.1	35.5
80°	29.2	28.7	28.7	28.7	28.2	28.2	28.2	28.2	28.2	28.2	28.2
82.5°	21.9	21.9	21.4	21.9	21.9	21.4	21.9	21.4	21.4	21.9	21.9
85°	14.6	15.5	14.6	14.6	15.0	15.0	15.5	15.0	15.5	14.6	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.7	7.7	8.2
90°	36.2	36.5	37.1	37.6	38.2	38.8	38.2	37.6	37.1	36.5	36.2
92.5°	42.6	42.7	43.0	43.3	43.6	43.9	43.6	43.3	43.0	42.7	42.6
95°	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1	49.1
97.5°	51.7	51.8	52.1	52.4	52.7	53.0	52.7	52.4	52.1	51.8	51.7
100°	53.0	53.1	53.4	53.7	54.0	54.3	54.0	53.7	53.4	53.1	53.0
102.5°	53.0	53.3	53.9	54.4	55.0	55.6	55.0	54.4	53.9	53.3	53.0
105°	54.3	54.6	55.1	55.7	56.2	56.8	56.2	55.7	55.1	54.6	54.3
107.5°	303.6	284.8	247.2	209.6	172.0	134.4	172.0	209.6	247.2	284.8	303.6
110°	540.0	519.5	478.4	437.4	396.3	355.3	396.3	437.4	478.4	519.5	540.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	675.7	675.4	674.8	674.3	673.7	673.1	673.7	674.3	674.8	675.4	675.7
115°	754.5	755.1	756.2	757.4	758.5	759.7	758.5	757.4	756.2	755.1	754.5
117.5°	828.2	828.3	828.6	828.9	829.2	829.5	829.2	828.9	828.6	828.3	828.2
120°	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8	901.8
122.5°	971.6	971.7	972.0	972.3	972.6	972.9	972.6	972.3	972.0	971.7	971.6
125°	1036.2	1036.5	1037.1	1037.6	1038.2	1038.8	1038.2	1037.6	1037.1	1036.5	1036.2
127.5°	1105.9	1105.6	1105.1	1104.5	1104.0	1103.4	1104.0	1104.5	1105.1	1105.6	1105.9
130°	1168.0	1167.7	1167.1	1166.6	1166.0	1165.4	1166.0	1166.6	1167.1	1167.7	1168.0
132.5°	1226.1	1225.7	1224.8	1223.9	1223.1	1222.2	1223.1	1223.9	1224.8	1225.7	1226.1
135°	1284.2	1283.8	1282.9	1282.1	1281.2	1280.4	1281.2	1282.1	1282.9	1283.8	1284.2
137.5°	1338.5	1338.2	1337.6	1337.1	1336.5	1335.9	1336.5	1337.1	1337.6	1338.2	1338.5
140°	1387.6	1387.3	1386.7	1386.2	1385.6	1385.0	1385.6	1386.2	1386.7	1387.3	1387.6
142.5°	1434.1	1433.7	1432.8	1431.9	1431.1	1430.2	1431.1	1431.9	1432.8	1433.7	1434.1
145°	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7	1476.7
147.5°	1516.8	1516.1	1514.6	1513.2	1511.7	1510.3	1511.7	1513.2	1514.6	1516.1	1516.8
150°	1553.0	1552.6	1551.7	1550.8	1550.0	1549.1	1550.0	1550.8	1551.7	1552.6	1553.0
152.5°	1586.6	1585.9	1584.4	1583.0	1581.5	1580.1	1581.5	1583.0	1584.4	1585.9	1586.6
155°	1616.3	1615.4	1613.7	1612.0	1610.2	1608.5	1610.2	1612.0	1613.7	1615.4	1616.3
157.5°	1643.4	1642.3	1640.0	1637.7	1635.4	1633.1	1635.4	1637.7	1640.0	1642.3	1643.4
160°	1665.4	1664.4	1662.4	1660.3	1658.3	1656.3	1658.3	1660.3	1662.4	1664.4	1665.4
162.5°	1686.0	1685.1	1683.4	1681.7	1680.0	1678.3	1680.0	1681.7	1683.4	1685.1	1686.0
165°	1704.1	1703.1	1701.1	1699.1	1697.1	1695.1	1697.1	1699.1	1701.1	1703.1	1704.1
167.5°	1718.3	1717.2	1714.9	1712.6	1710.3	1708.0	1710.3	1712.6	1714.9	1717.2	1718.3
170°	1730.0	1728.8	1726.5	1724.2	1721.9	1719.6	1721.9	1724.2	1726.5	1728.8	1730.0
172.5°	1737.7	1736.4	1733.8	1731.3	1728.7	1726.1	1728.7	1731.3	1733.8	1736.4	1737.7
175°	1742.9	1741.8	1739.5	1737.2	1734.9	1732.6	1734.9	1737.2	1739.5	1741.8	1742.9
177.5°	1746.8	1745.4	1742.5	1739.6	1736.7	1733.8	1736.7	1739.6	1742.5	1745.4	1746.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1	532.1
2.5°	503.4	505.2	503.4	499.8	503.4	505.7	508.0	511.6	513.4	513.4	516.2
5°	474.7	478.4	477.0	476.1	479.7	482.0	485.6	490.2	495.2	498.4	502.0
7.5°	449.2	451.5	453.8	453.8	457.4	462.4	467.9	473.3	479.7	484.3	487.0
10°	426.9	428.7	430.1	431.9	437.4	442.8	450.1	456.9	462.4	467.4	472.0
12.5°	405.5	408.2	411.4	412.8	416.9	423.7	430.5	438.7	447.4	452.4	456.9
15°	385.0	386.3	390.0	394.1	397.7	405.0	413.7	422.3	429.6	437.4	441.5
17.5°	364.0	364.5	374.0	371.8	383.6	390.4	395.0	403.2	415.0	421.4	427.8
20°	343.5	348.1	352.2	354.4	360.8	368.6	381.8	388.2	397.7	403.6	409.1
22.5°	327.6	334.4	334.4	339.9	343.1	350.3	359.9	372.2	382.7	386.8	394.5
25°	313.4	316.6	322.1	323.9	329.8	336.2	342.6	355.8	367.2	372.7	378.1
27.5°	295.2	299.3	306.6	306.6	314.3	321.2	328.9	337.6	349.0	356.7	362.6
30°	281.1	285.2	288.4	293.4	296.6	303.0	316.6	323.0	333.0	339.9	347.2
32.5°	267.9	271.1	273.8	279.3	282.9	290.2	297.5	308.9	317.5	323.9	331.7
35°	253.3	256.5	260.1	264.2	269.7	276.5	283.4	292.9	301.6	307.5	313.9
37.5°	239.6	241.9	247.4	250.1	254.7	261.0	269.7	279.7	287.5	292.0	298.4
40°	226.4	228.2	232.3	237.4	240.5	245.6	254.7	263.3	272.9	278.4	283.4
42.5°	212.3	214.6	218.2	223.2	228.2	233.7	238.7	248.7	257.4	262.0	267.4
45°	200.0	201.4	204.1	209.1	214.1	218.2	226.0	235.1	243.3	246.9	252.8
47.5°	185.4	186.8	190.9	193.2	198.6	204.1	211.8	221.0	228.2	231.9	237.4
50°	170.4	171.8	174.5	179.5	183.1	189.1	195.9	203.6	212.8	217.8	221.0
52.5°	155.8	158.5	160.8	164.9	169.5	175.4	181.8	189.1	196.8	201.8	205.5
55°	141.2	143.5	146.2	148.5	154.0	159.5	166.7	173.6	180.4	185.0	189.1
57.5°	124.8	128.0	130.8	135.3	139.4	144.0	152.2	157.6	165.8	169.0	172.7
60°	110.7	113.9	116.2	119.8	123.5	129.4	134.9	141.7	148.5	152.6	157.2
62.5°	98.9	100.2	101.6	105.2	108.9	114.4	119.8	126.7	133.9	136.2	139.9
65°	87.0	88.4	90.7	93.8	96.6	99.8	105.7	111.2	118.0	121.6	123.0
67.5°	77.0	78.4	78.8	81.1	83.4	87.0	90.2	95.7	102.0	104.3	107.1
70°	65.6	67.9	68.3	70.2	71.1	73.3	77.0	81.1	86.1	90.2	92.5
72.5°	52.4	55.6	56.5	59.2	60.6	62.9	65.6	68.8	72.0	73.8	75.6
75°	42.8	43.7	44.2	46.5	48.7	51.9	53.3	55.1	57.9	60.1	62.0
77.5°	35.5	36.0	36.4	36.4	36.9	38.7	41.5	43.7	45.6	46.5	47.8
80°	28.7	28.2	28.2	28.7	28.7	28.7	29.6	32.8	33.7	36.0	35.5
82.5°	22.3	21.4	21.9	21.4	21.4	21.4	21.4	21.9	21.9	23.2	24.1
85°	14.6	15.0	14.6	14.6	14.1	14.6	14.1	14.1	13.7	13.7	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	35.6	34.5	33.3	32.2	31.0	27.3	23.5	19.8	16.1	14.2	12.8
92.5°	41.6	39.6	37.6	35.6	33.6	31.0	28.4	25.9	23.3	22.0	22.9
95°	48.1	46.1	44.1	42.1	40.1	36.9	33.7	30.6	27.4	25.8	31.7
97.5°	50.5	48.2	45.9	43.6	41.3	55.9	70.6	85.2	99.9	107.2	111.2
100°	51.8	49.5	47.2	44.9	42.6	87.4	132.2	177.0	221.8	244.2	241.3
102.5°	57.7	67.2	76.7	86.1	95.6	145.6	195.5	245.5	295.4	320.4	318.5
105°	79.7	130.5	181.3	232.1	282.9	308.7	334.6	360.4	386.3	399.2	397.6
107.5°	325.7	369.9	414.2	458.4	502.6	498.3	494.0	489.7	485.4	483.2	481.9
110°	544.7	554.2	563.7	573.2	582.7	579.5	576.4	573.2	570.1	568.5	567.3

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	674.4	671.8	669.3	666.7	664.1	660.9	657.8	654.6	651.5	649.9	648.9
115°	753.1	750.2	747.3	744.5	741.6	739.0	736.4	733.9	731.3	730.0	729.1
117.5°	827.0	824.7	822.4	820.1	817.8	816.4	815.0	813.5	812.1	811.4	810.4
120°	900.7	898.4	896.1	893.8	891.5	890.6	889.8	888.9	888.0	887.6	886.3
122.5°	970.9	969.4	968.0	966.5	965.1	963.9	962.8	961.6	960.5	959.9	958.9
125°	1035.9	1035.3	1034.8	1034.2	1033.6	1032.4	1031.3	1030.1	1029.0	1028.4	1027.3
127.5°	1105.5	1104.6	1103.8	1102.9	1102.1	1100.7	1099.2	1097.8	1096.3	1095.6	1094.5
130°	1167.4	1166.3	1165.1	1164.0	1162.8	1161.6	1160.5	1159.3	1158.2	1157.6	1156.5
132.5°	1225.5	1224.4	1223.2	1222.1	1220.9	1220.1	1219.2	1218.4	1217.5	1217.1	1215.9
135°	1283.8	1282.9	1282.1	1281.2	1280.4	1279.2	1278.1	1276.9	1275.8	1275.2	1274.3
137.5°	1337.8	1336.3	1334.9	1333.4	1332.0	1331.4	1330.9	1330.3	1329.8	1329.5	1328.3
140°	1387.0	1385.9	1384.7	1383.6	1382.4	1381.5	1380.7	1379.8	1378.9	1378.5	1377.6
142.5°	1433.7	1432.8	1431.9	1431.1	1430.2	1429.4	1428.5	1427.7	1426.8	1426.4	1425.5
145°	1476.4	1475.9	1475.3	1474.8	1474.2	1473.6	1473.0	1472.5	1471.9	1471.6	1470.6
147.5°	1516.5	1515.9	1515.4	1514.8	1514.2	1513.6	1513.0	1512.5	1511.9	1511.6	1510.9
150°	1552.7	1552.1	1551.6	1551.0	1550.4	1549.8	1549.2	1548.7	1548.1	1547.8	1547.4
152.5°	1586.0	1584.9	1583.7	1582.6	1581.4	1581.1	1580.8	1580.5	1580.2	1580.1	1580.0
155°	1615.6	1614.1	1612.7	1611.2	1609.8	1609.5	1609.2	1608.9	1608.6	1608.5	1608.8
157.5°	1642.5	1640.8	1639.1	1637.4	1635.7	1636.0	1636.2	1636.5	1636.8	1636.9	1636.9
160°	1664.5	1662.8	1661.1	1659.3	1657.6	1657.9	1658.2	1658.5	1658.8	1658.9	1659.0
162.5°	1685.0	1683.0	1681.0	1679.0	1677.0	1677.3	1677.6	1677.9	1678.2	1678.3	1678.7
165°	1703.0	1700.7	1698.4	1696.1	1693.8	1694.1	1694.4	1694.7	1695.0	1695.1	1695.5
167.5°	1717.2	1714.9	1712.6	1710.3	1708.0	1708.0	1708.0	1708.0	1708.0	1708.0	1708.6
170°	1728.8	1726.5	1724.2	1721.9	1719.6	1719.6	1719.6	1719.6	1719.6	1719.6	1720.2
172.5°	1736.6	1734.3	1732.0	1729.7	1727.4	1727.1	1726.8	1726.5	1726.2	1726.1	1726.8
175°	1741.9	1739.9	1737.8	1735.8	1733.8	1733.5	1733.3	1733.0	1732.7	1732.6	1733.3
177.5°	1745.6	1743.3	1741.0	1738.7	1736.4	1736.1	1735.8	1735.5	1735.2	1735.1	1735.8
180°	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0	1739.0

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	532.1	532.1	532.1	532.1
2.5°	518.4	521.6	528.0	533.5
5°	507.5	512.5	522.1	531.7
7.5°	494.3	502.0	514.3	527.6
10°	481.5	491.6	506.6	522.1
12.5°	468.8	479.3	495.2	515.3
15°	453.8	464.7	483.8	508.0
17.5°	440.5	455.1	472.4	496.6
20°	426.4	437.4	459.7	485.2
22.5°	408.7	426.9	447.8	474.7
25°	394.5	410.5	431.4	462.0
27.5°	377.2	395.9	421.4	448.3
30°	363.1	378.6	402.3	434.6
32.5°	346.7	364.9	389.5	421.4
35°	332.1	347.6	370.8	403.2
37.5°	314.8	331.7	357.6	386.3
40°	299.8	316.2	340.8	367.7
42.5°	281.5	298.9	323.5	346.2
45°	267.0	282.9	302.5	323.5
47.5°	249.2	266.1	285.2	299.8
50°	233.3	248.7	263.8	276.1
52.5°	215.9	230.1	243.7	252.8
55°	200.0	210.9	221.9	228.2
57.5°	181.3	191.8	200.9	204.6
60°	164.9	173.6	179.5	183.6
62.5°	147.6	154.0	158.5	160.8
65°	130.8	135.3	137.6	139.9
67.5°	113.4	117.5	118.9	121.6
70°	95.2	99.8	100.7	102.0
72.5°	81.5	81.5	83.4	85.2
75°	65.1	66.1	67.0	67.0
77.5°	51.0	51.0	51.9	52.4
80°	37.4	37.8	37.8	37.4
82.5°	25.5	26.4	25.5	25.1
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	9.9	7.0	4.2	1.3
92.5°	24.6	26.3	28.0	29.7
95°	43.5	55.2	67.0	78.8
97.5°	119.3	127.3	135.4	143.4
100°	235.6	229.8	224.1	218.3
102.5°	314.8	311.1	307.3	303.6
105°	394.5	391.3	388.2	385.0
107.5°	479.3	476.8	474.2	471.6
110°	565.0	562.7	560.4	558.1

TEST NUMBER: P1031127

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	646.9	644.8	642.8	640.8
115°	727.4	725.7	723.9	722.2
117.5°	808.4	806.3	804.3	802.3
120°	883.7	881.2	878.6	876.0
122.5°	956.9	954.9	952.9	950.9
125°	1025.0	1022.7	1020.4	1018.1
127.5°	1092.2	1089.9	1087.6	1085.3
130°	1154.2	1151.9	1149.6	1147.3
132.5°	1213.6	1211.3	1209.0	1206.7
135°	1272.6	1270.9	1269.1	1267.4
137.5°	1326.0	1323.7	1321.4	1319.1
140°	1375.9	1374.2	1372.5	1370.8
142.5°	1423.8	1422.1	1420.3	1418.6
145°	1468.6	1466.5	1464.5	1462.5
147.5°	1509.5	1508.0	1506.6	1505.2
150°	1546.5	1545.6	1544.8	1543.9
152.5°	1579.7	1579.4	1579.1	1578.8
155°	1609.4	1609.9	1610.5	1611.1
157.5°	1636.9	1636.9	1636.9	1636.9
160°	1659.3	1659.6	1659.9	1660.2
162.5°	1679.6	1680.5	1681.3	1682.2
165°	1696.4	1697.3	1698.1	1699.0
167.5°	1709.7	1710.9	1712.0	1713.2
170°	1721.3	1722.5	1723.6	1724.8
172.5°	1728.3	1729.7	1731.2	1732.6
175°	1734.7	1736.2	1737.6	1739.0
177.5°	1737.3	1738.7	1740.2	1741.6
180°	1739.0	1739.0	1739.0	1739.0

(END OF REPORT)