

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031158

Luminaire Tested: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031158
REPORT IS A COMBINATION OF REPORTS P994347 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4223.0 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	38	38	30
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	33	33	33	33	26
2	86	79	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	22
3	78	69	62	57	70	63	57	52	50	46	42	38	35	33	27	26	24	24	24	19
4	72	61	54	48	64	56	49	44	44	40	36	34	31	29	24	23	21	21	21	17
5	66	55	47	41	59	50	43	38	40	35	31	31	27	25	22	20	19	19	19	15
6	61	49	41	36	54	45	38	33	36	31	27	28	24	22	20	18	16	16	16	13
7	56	44	37	31	50	40	34	29	33	28	24	25	22	19	18	16	15	15	15	12
8	52	40	33	28	47	37	30	26	30	25	21	23	20	17	17	15	13	13	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	16	16	14	12	12	12	10
10	45	34	27	22	40	31	25	20	25	20	17	20	16	14	15	12	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5481	5481	5481	5481
5°	5486	6313	5500	4683
10°	5437	7621	5461	4091
15°	5381	8649	5381	3607
20°	5270	9329	5300	3200
25°	5190	8864	5180	2920
30°	5096	6141	5086	2645
35°	4982	3943	4960	2439
40°	4842	2784	4818	2233
45°	4596	2228	4591	2033
50°	4296	1864	4282	1800
55°	3957	1536	3926	1525
60°	3625	1269	3590	1297
65°	3234	1016	3256	1100
70°	2877	706	2954	889
75°	2438	524	2537	684
80°	1944	347	2106	512
85°	1383	164	1508	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7318 cd/sqm

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	1.2
10°-20°	156.5	3.7
20°-30°	246.6	5.8
30°-40°	256.4	6.1
40°-50°	219.3	5.2
50°-60°	167.2	4.0
60°-70°	107.1	2.5
70°-80°	51.3	1.2
80°-90°	15.4	0.4
90°-100°	34.1	0.8
100°-110°	165.2	3.9
110°-120°	404.7	9.6
120°-130°	513.8	12.2
130°-140°	548.9	13.0
140°-150°	513.2	12.2
150°-160°	414.0	9.8
160°-170°	267.2	6.3
170°-180°	92.1	2.2
0°-30°	453.1	10.7
0°-40°	709.5	16.8
0°-60°	1096.0	26.0
0°-90°	1269.9	30.1
90°-120°	604.0	14.3
90°-150°	2179.9	51.6
90°-180°	2953.0	69.9
0°-180°	4223.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	509	605	510	449	509	48
15°	486	859	486	358	486	137
25°	442	886	441	292	442	204
35°	386	384	384	238	386	241
45°	310	205	309	187	310	238
55°	218	129	217	128	218	196
65°	134	74	135	80	134	134
75°	64	31	67	41	64	69
85°	14	7	16	14	14	16
90°	1	22	1	22	1	3
95°	44	27	44	27	44	52
105°	214	32	214	32	214	227
115°	402	423	402	423	402	397
125°	567	579	567	579	567	507
135°	706	713	706	713	706	544
145°	815	823	815	823	815	510
155°	897	896	897	896	897	414
165°	946	944	946	944	946	267
175°	969	965	969	965	969	92
180°	969	969	969	969	969	

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	510.5	514.0	516.6	518.4	522.7	525.4	527.5	531.5	531.5	532.3	534.1
5°	508.8	516.2	521.4	528.4	537.6	541.9	548.0	553.3	560.7	564.6	568.5
7.5°	504.9	515.3	526.2	536.7	550.2	558.9	565.0	578.5	588.1	599.9	609.1
10°	499.6	514.0	528.0	544.1	562.4	575.5	584.7	602.5	620.8	637.4	651.4
12.5°	493.1	510.5	530.6	550.2	575.9	589.0	603.8	626.1	652.2	673.2	691.9
15°	486.1	506.2	528.8	552.8	585.1	603.4	624.8	651.8	681.0	711.1	736.8
17.5°	475.2	500.5	525.8	560.7	598.6	609.5	627.8	664.9	701.1	728.1	759.5
20°	464.3	492.7	524.5	555.9	596.9	622.1	639.1	678.4	717.2	749.9	780.0
22.5°	454.3	483.9	517.1	556.7	595.1	620.4	641.8	682.7	727.7	764.3	801.3
25°	442.1	474.3	511.0	548.5	595.1	614.3	637.8	685.4	732.9	775.2	821.0
27.5°	429.0	461.7	497.9	536.3	579.0	607.3	630.4	681.4	739.4	784.8	831.9
30°	415.9	449.5	484.4	518.8	566.8	593.8	620.4	676.6	742.9	794.8	831.0
32.5°	403.3	431.6	466.1	499.6	547.2	576.8	606.9	671.8	744.2	787.8	805.3
35°	385.8	415.5	443.4	479.1	527.1	556.3	591.6	671.4	738.6	765.6	756.9
37.5°	369.7	394.6	421.2	453.0	502.2	540.2	576.8	660.1	719.8	721.5	672.3
40°	351.8	372.3	394.6	428.1	481.3	518.8	558.5	642.6	685.8	660.1	573.3
42.5°	331.3	349.7	367.1	399.8	457.8	499.6	542.4	620.8	636.5	577.2	487.0
45°	309.5	324.4	340.5	374.9	432.9	474.3	517.1	587.3	571.1	487.4	401.5
47.5°	286.9	299.5	315.2	346.6	406.3	448.6	489.2	539.3	498.3	408.5	336.6
50°	264.2	274.2	289.5	321.8	379.3	417.7	455.2	487.9	430.3	350.5	278.2
52.5°	242.0	249.8	265.5	293.0	348.8	385.4	412.4	425.1	366.7	289.5	241.5
55°	218.4	227.1	237.6	265.5	320.9	347.9	365.8	365.4	305.2	245.5	199.7
57.5°	195.8	203.6	212.8	240.7	285.6	303.9	319.1	311.7	254.6	201.0	171.3
60°	175.7	180.1	190.1	213.6	247.6	263.3	272.1	259.4	208.0	169.6	141.7
62.5°	153.9	158.3	166.5	188.8	209.7	218.0	225.4	209.3	171.8	138.2	121.2
65°	133.8	139.5	144.7	162.6	174.0	184.0	183.1	169.6	134.3	112.5	98.5
67.5°	116.4	118.6	122.9	133.8	139.1	146.5	146.9	131.7	108.1	91.6	83.3
70°	97.7	99.8	102.9	108.1	111.6	113.4	112.5	99.0	81.5	71.5	64.1
72.5°	81.5	81.1	83.3	83.3	86.8	86.3	83.7	73.2	61.9	53.6	49.3
75°	64.1	64.5	65.0	64.1	62.8	61.0	58.9	51.0	43.6	39.7	35.8
77.5°	50.1	49.3	49.7	46.6	44.9	43.2	40.1	36.2	30.1	29.2	27.5
80°	35.8	35.3	34.9	33.6	29.6	27.9	25.7	23.5	22.2	21.4	20.9
82.5°	24.0	24.0	23.1	20.5	18.3	17.0	16.6	15.7	14.4	14.4	14.0
85°	14.4	14.0	13.1	10.5	9.2	9.2	9.2	9.2	8.3	8.3	7.8
87.5°	5.7	5.2	3.9	3.9	3.5	3.5	3.5	3.1	3.1	2.6	2.6
90°	0.7	2.3	3.9	5.5	7.1	7.9	8.9	11.0	13.1	15.2	17.3
92.5°	16.6	15.6	14.6	13.7	12.7	12.2	12.9	14.4	15.8	17.3	18.7
95°	43.9	37.3	30.8	24.2	17.7	14.4	15.3	17.0	18.8	20.5	22.3
97.5°	79.9	75.4	70.9	66.4	61.9	59.7	55.6	47.5	39.3	31.2	23.0
100°	121.6	124.8	128.0	131.2	134.4	136.0	123.5	98.6	73.6	48.7	23.7
102.5°	169.1	171.2	173.3	175.4	177.5	178.5	164.6	136.8	108.9	81.1	53.3
105°	214.5	216.3	218.0	219.8	221.5	222.4	215.2	200.8	186.4	172.0	157.6
107.5°	262.7	264.1	265.6	267.0	268.5	269.2	270.4	272.8	275.1	277.5	279.9
110°	310.9	312.2	313.5	314.8	316.1	316.7	317.6	319.3	321.1	322.8	324.6



TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	357.0	358.1	359.2	360.3	361.4	362.0	362.9	364.6	366.4	368.1	369.9
115°	402.3	403.3	404.2	405.2	406.1	406.6	407.3	408.8	410.2	411.7	413.1
117.5°	446.9	448.0	449.1	450.2	451.3	451.9	452.3	453.1	453.9	454.7	455.5
120°	487.9	489.3	490.8	492.2	493.7	494.4	494.6	495.1	495.6	496.1	496.6
122.5°	529.7	530.8	531.9	533.0	534.1	534.7	535.0	535.7	536.3	537.0	537.6
125°	567.1	568.4	569.7	571.0	572.3	572.9	573.2	573.8	574.5	575.1	575.7
127.5°	604.5	605.8	607.1	608.4	609.7	610.3	610.7	611.5	612.3	613.1	613.9
130°	639.1	640.4	641.6	642.9	644.2	644.8	645.1	645.8	646.4	647.1	647.7
132.5°	672.2	673.5	674.7	676.0	677.3	677.9	678.1	678.6	679.1	679.6	680.1
135°	706.0	707.0	707.9	708.9	709.8	710.3	710.6	711.3	711.9	712.6	713.2
137.5°	734.8	736.1	737.3	738.6	739.9	740.5	740.7	741.0	741.3	741.7	742.0
140°	763.6	764.6	765.5	766.5	767.4	767.9	768.1	768.6	769.1	769.5	770.0
142.5°	790.2	791.2	792.1	793.1	794.0	794.5	794.7	795.2	795.7	796.2	796.7
145°	814.7	815.8	816.9	818.0	819.1	819.7	819.9	820.2	820.5	820.8	821.1
147.5°	838.4	839.2	840.0	840.8	841.6	842.0	842.2	842.5	842.8	843.1	843.4
150°	860.0	860.5	861.0	861.5	862.0	862.2	862.4	862.7	863.0	863.3	863.6
152.5°	879.4	879.6	879.7	879.9	880.0	880.1	880.2	880.4	880.5	880.7	880.9
155°	897.4	897.1	896.8	896.5	896.2	896.0	896.1	896.2	896.4	896.5	896.7
157.5°	911.8	911.8	911.8	911.8	911.8	911.8	911.7	911.6	911.4	911.3	911.1
160°	924.8	924.6	924.4	924.3	924.1	924.0	923.9	923.8	923.6	923.5	923.3
162.5°	937.0	936.5	936.0	935.5	935.0	934.8	934.7	934.6	934.4	934.3	934.1
165°	946.4	945.9	945.4	944.9	944.4	944.2	944.1	944.0	943.8	943.7	943.5
167.5°	954.3	953.7	953.0	952.4	951.7	951.4	951.4	951.4	951.4	951.4	951.4
170°	960.8	960.2	959.5	958.9	958.2	957.9	957.9	957.9	957.9	957.9	957.9
172.5°	965.1	964.3	963.5	962.7	961.9	961.5	961.6	961.7	961.9	962.0	962.2
175°	968.7	967.9	967.1	966.3	965.5	965.1	965.2	965.3	965.5	965.6	965.8
177.5°	970.1	969.3	968.5	967.7	966.9	966.5	966.6	966.7	966.9	967.0	967.2
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	537.6	537.6	541.5	545.4	543.2	544.5	549.3	547.6	551.1	550.6	552.0
5°	578.1	582.9	586.8	595.1	596.4	595.1	603.4	605.6	609.5	604.7	606.9
7.5°	623.9	633.9	643.5	655.7	659.6	660.5	664.9	671.0	676.2	666.6	671.4
10°	668.4	683.6	703.2	714.1	723.7	727.2	730.7	734.6	740.7	746.4	742.0
12.5°	716.3	738.6	757.3	776.9	788.7	787.4	797.4	800.0	804.8	806.1	807.9
15°	755.6	786.9	798.7	827.9	830.5	839.3	850.6	860.6	861.9	859.3	859.3
17.5°	793.0	820.1	841.0	864.6	869.3	876.8	891.1	895.9	897.7	897.2	897.2
20°	823.6	841.4	876.8	896.4	904.2	913.8	923.8	929.9	931.3	933.0	930.4
22.5°	843.6	870.7	899.4	915.6	922.1	925.6	932.1	933.9	931.7	932.1	932.6
25°	859.3	885.9	903.4	907.7	907.3	902.9	898.1	889.8	889.0	885.5	878.5
27.5°	863.7	873.7	871.5	853.7	835.8	834.0	805.3	789.6	771.7	774.3	764.3
30°	840.1	827.1	796.1	750.8	732.0	701.5	669.2	635.7	622.6	608.2	634.8
32.5°	782.6	735.9	681.0	622.1	590.8	563.7	529.3	504.9	490.9	479.1	501.8
35°	695.8	623.0	550.2	494.4	468.7	444.3	412.0	399.8	382.4	384.1	386.3
37.5°	584.2	504.0	449.1	394.1	377.1	367.1	343.6	324.8	318.7	317.0	317.0
40°	479.6	413.7	364.9	321.8	308.7	300.4	281.6	272.9	266.4	264.6	266.8
42.5°	396.7	340.5	302.6	273.8	264.6	254.2	246.3	235.4	234.1	231.1	235.0
45°	333.1	284.3	255.9	235.0	227.1	223.2	214.5	208.0	205.3	204.9	208.0
47.5°	282.5	244.6	219.7	206.7	200.6	196.6	189.2	186.6	184.0	184.9	183.5
50°	237.2	208.8	192.7	180.9	177.0	173.1	168.3	165.7	164.4	164.4	163.9
52.5°	203.6	180.1	169.6	158.7	157.0	154.8	149.5	147.8	145.6	145.2	146.9
55°	174.4	158.3	147.8	141.3	139.5	135.2	133.0	130.8	129.5	128.6	129.1
57.5°	149.1	136.9	129.9	124.3	121.2	119.5	115.5	115.1	114.2	114.2	113.8
60°	128.2	119.5	111.2	107.7	105.5	103.3	102.9	100.3	99.0	99.8	99.4
62.5°	108.6	101.6	96.8	92.9	91.6	89.8	88.5	87.6	86.3	86.8	86.8
65°	90.7	85.0	81.5	78.0	77.6	75.9	75.4	74.6	74.6	74.1	75.0
67.5°	74.6	70.6	67.6	65.4	64.1	64.5	62.8	61.5	61.5	61.0	62.3
70°	59.3	57.1	54.1	51.4	49.7	49.7	47.5	47.1	47.1	47.1	46.6
72.5°	45.8	41.9	40.5	39.7	39.7	39.7	38.8	38.8	38.4	38.8	38.4
75°	34.0	33.6	32.7	32.3	32.3	31.8	31.4	31.4	31.4	31.4	31.4
77.5°	26.6	26.6	25.7	25.3	25.3	25.3	24.9	24.9	24.4	24.4	24.4
80°	19.6	19.6	18.7	18.7	18.7	18.3	18.3	18.3	18.7	18.3	18.3
82.5°	13.5	13.5	13.1	13.5	13.1	12.6	12.6	12.6	12.2	12.6	12.6
85°	7.8	7.8	7.4	7.0	7.4	7.4	7.0	7.4	7.0	7.4	7.0
87.5°	3.1	2.6	2.6	2.6	2.2	2.6	2.2	2.2	2.6	2.2	2.6
90°	17.9	18.6	19.2	19.9	20.2	20.4	20.7	21.0	21.3	21.6	21.3
92.5°	19.8	20.9	22.0	23.1	23.7	23.8	24.0	24.1	24.3	24.5	24.3
95°	23.4	24.5	25.6	26.7	27.3	27.3	27.3	27.3	27.3	27.3	27.3
97.5°	24.3	25.6	26.9	28.2	28.8	28.9	29.0	29.2	29.3	29.5	29.3
100°	25.0	26.3	27.6	28.9	29.5	29.6	29.7	29.9	30.0	30.2	30.0
102.5°	48.0	42.7	37.4	32.1	29.5	29.7	30.0	30.3	30.6	30.9	30.6
105°	129.3	101.0	72.7	44.4	30.2	30.4	30.7	31.0	31.4	31.7	31.4
107.5°	255.3	230.7	206.0	181.4	169.1	158.6	137.7	116.7	95.8	74.8	95.8
110°	319.3	314.0	308.7	303.4	300.8	289.4	266.5	243.6	220.8	197.9	220.8

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	371.3	372.8	374.2	375.7	376.4	376.2	375.9	375.6	375.2	374.9	375.2
115°	414.7	416.3	417.9	419.5	420.3	420.6	421.3	421.9	422.6	423.2	422.6
117.5°	456.8	458.1	459.4	460.7	461.3	461.4	461.5	461.7	461.8	462.0	461.8
120°	497.9	499.1	500.4	501.7	502.3	502.3	502.3	502.3	502.3	502.3	502.3
122.5°	538.4	539.2	540.0	540.8	541.2	541.3	541.4	541.6	541.7	541.9	541.7
125°	576.0	576.4	576.7	577.0	577.2	577.4	577.7	578.0	578.3	578.6	578.3
127.5°	614.4	614.8	615.3	615.8	616.0	615.8	615.5	615.2	614.9	614.6	614.9
130°	648.3	649.0	649.6	650.3	650.6	650.4	650.1	649.8	649.4	649.1	649.4
132.5°	680.7	681.4	682.0	682.7	683.0	682.8	682.3	681.8	681.3	680.8	681.3
135°	713.7	714.1	714.6	715.1	715.3	715.1	714.6	714.1	713.7	713.2	713.7
137.5°	742.8	743.6	744.4	745.2	745.6	745.4	745.1	744.8	744.4	744.1	744.4
140°	770.6	771.3	771.9	772.6	772.9	772.7	772.4	772.1	771.8	771.5	771.8
142.5°	797.2	797.6	798.1	798.6	798.8	798.6	798.1	797.6	797.2	796.7	797.2
145°	821.4	821.8	822.1	822.4	822.6	822.6	822.6	822.6	822.6	822.6	822.6
147.5°	843.7	844.1	844.4	844.7	844.9	844.5	843.7	842.9	842.1	841.3	842.1
150°	863.9	864.2	864.5	864.8	865.0	864.8	864.3	863.8	863.4	862.9	863.4
152.5°	881.5	882.1	882.8	883.4	883.7	883.3	882.5	881.7	880.9	880.1	880.9
155°	897.5	898.3	899.1	899.9	900.3	899.8	898.9	897.9	897.0	896.0	897.0
157.5°	912.1	913.0	914.0	914.9	915.4	914.8	913.5	912.2	911.0	909.7	911.0
160°	924.3	925.2	926.2	927.1	927.6	927.0	925.9	924.8	923.7	922.6	923.7
162.5°	935.2	936.4	937.5	938.6	939.2	938.7	937.7	936.8	935.8	934.8	935.8
165°	944.8	946.0	947.3	948.6	949.2	948.6	947.5	946.4	945.3	944.2	945.3
167.5°	952.7	954.0	955.3	956.6	957.2	956.6	955.3	954.0	952.7	951.4	952.7
170°	959.2	960.4	961.7	963.0	963.6	963.0	961.7	960.4	959.2	957.9	959.2
172.5°	963.5	964.7	966.0	967.3	967.9	967.2	965.8	964.3	962.9	961.5	962.9
175°	966.9	968.0	969.1	970.2	970.8	970.2	968.9	967.6	966.4	965.1	966.4
177.5°	968.5	969.8	971.1	972.4	973.0	972.2	970.6	969.0	967.4	965.8	967.4
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	549.8	547.2	545.4	544.1	542.8	546.7	541.5	535.8	531.9	529.3	528.4
5°	607.3	601.7	596.9	592.9	593.8	593.8	584.7	574.6	565.9	561.1	555.9
7.5°	674.0	667.9	658.3	656.2	654.4	643.5	634.4	616.0	605.1	594.2	584.7
10°	740.3	732.4	723.3	720.2	715.9	702.4	688.4	664.9	651.4	631.3	618.7
12.5°	802.2	792.6	783.5	781.3	774.7	763.0	739.0	714.6	691.5	670.1	647.9
15°	854.1	851.5	837.5	828.8	814.4	798.3	793.0	759.9	730.7	708.5	668.4
17.5°	897.7	885.5	872.4	866.7	861.1	842.3	823.6	789.6	758.2	725.5	699.7
20°	932.6	919.0	909.9	901.6	899.0	877.6	848.0	817.9	783.5	746.8	713.3
22.5°	934.3	932.6	926.5	921.7	916.4	902.5	878.9	841.4	804.8	764.7	720.7
25°	898.1	895.5	912.9	908.6	912.1	906.8	894.2	862.8	820.1	773.0	728.5
27.5°	789.1	815.7	843.2	852.8	859.3	878.1	884.2	866.7	832.3	782.1	732.4
30°	640.9	676.2	720.7	744.7	763.0	797.8	843.2	848.9	832.7	792.6	731.6
32.5°	503.1	535.4	571.1	599.5	623.9	695.4	756.4	800.5	808.3	787.4	733.8
35°	405.5	419.4	453.4	480.5	513.6	574.6	646.6	717.6	765.6	768.2	727.2
37.5°	334.4	341.8	371.5	386.7	406.3	460.0	527.1	620.0	694.5	729.8	708.9
40°	276.8	293.9	310.9	319.6	333.5	370.6	435.1	507.9	600.3	665.7	680.6
42.5°	240.2	247.6	258.5	270.7	279.5	311.7	354.9	421.6	504.9	596.0	637.0
45°	211.9	214.5	225.8	233.7	242.8	265.5	296.0	351.8	425.1	514.9	584.7
47.5°	188.3	193.6	199.7	204.5	210.6	228.0	254.2	294.7	359.2	439.5	514.5
50°	167.4	170.5	178.3	180.5	184.9	197.1	217.1	248.1	301.3	365.4	443.0
52.5°	147.8	153.5	156.5	159.6	163.5	173.5	186.6	211.9	252.0	312.2	378.0
55°	132.5	134.3	138.6	141.3	144.3	151.3	162.6	181.4	212.8	260.7	323.1
57.5°	117.7	117.7	122.1	124.3	127.3	132.5	142.6	157.0	179.6	215.4	272.5
60°	102.0	102.5	105.9	108.6	109.4	114.7	122.9	134.3	151.7	177.9	224.5
62.5°	88.1	90.2	92.0	92.9	95.9	99.0	105.9	113.8	126.0	149.1	182.2
65°	76.3	76.7	78.0	78.9	80.2	83.7	88.9	94.2	104.6	121.6	148.7
67.5°	62.8	64.5	66.3	66.3	67.6	69.3	74.6	78.9	86.8	96.8	115.1
70°	47.1	48.0	50.6	51.9	53.6	56.7	59.3	61.9	68.0	75.4	89.4
72.5°	39.2	39.2	40.1	40.5	40.5	42.7	46.6	49.3	52.3	57.5	67.1
75°	31.4	31.4	32.7	32.3	33.1	34.0	34.4	36.2	37.9	41.9	47.5
77.5°	24.9	25.3	25.3	25.7	25.7	26.2	26.6	27.5	28.3	30.5	33.1
80°	18.3	18.7	18.7	19.2	19.2	19.6	20.1	20.5	21.4	22.2	23.5
82.5°	12.6	13.1	13.1	13.5	13.1	13.5	14.0	14.0	14.4	15.3	15.7
85°	7.4	7.4	7.8	7.4	7.4	7.4	7.8	7.8	8.3	9.6	9.6
87.5°	2.2	2.6	2.2	2.6	2.6	2.6	2.6	3.1	3.1	3.5	3.9
90°	21.0	20.7	20.4	20.2	19.9	19.2	18.6	17.9	17.3	15.2	13.1
92.5°	24.1	24.0	23.8	23.7	23.1	22.0	20.9	19.8	18.7	17.3	15.8
95°	27.3	27.3	27.3	27.3	26.7	25.6	24.5	23.4	22.3	20.5	18.8
97.5°	29.2	29.0	28.9	28.8	28.2	26.9	25.6	24.3	23.0	31.2	39.3
100°	29.9	29.7	29.6	29.5	28.9	27.6	26.3	25.0	23.7	48.7	73.6
102.5°	30.3	30.0	29.7	29.5	32.1	37.4	42.7	48.0	53.3	81.1	108.9
105°	31.0	30.7	30.4	30.2	44.4	72.7	101.0	129.3	157.6	172.0	186.4
107.5°	116.7	137.7	158.6	169.1	181.4	206.0	230.7	255.3	279.9	277.5	275.1
110°	243.6	266.5	289.4	300.8	303.4	308.7	314.0	319.3	324.6	322.8	321.1

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	375.6	375.9	376.2	376.4	375.7	374.2	372.8	371.3	369.9	368.1	366.4
115°	421.9	421.3	420.6	420.3	419.5	417.9	416.3	414.7	413.1	411.7	410.2
117.5°	461.7	461.5	461.4	461.3	460.7	459.4	458.1	456.8	455.5	454.7	453.9
120°	502.3	502.3	502.3	502.3	501.7	500.4	499.1	497.9	496.6	496.1	495.6
122.5°	541.6	541.4	541.3	541.2	540.8	540.0	539.2	538.4	537.6	537.0	536.3
125°	578.0	577.7	577.4	577.2	577.0	576.7	576.4	576.0	575.7	575.1	574.5
127.5°	615.2	615.5	615.8	616.0	615.8	615.3	614.8	614.4	613.9	613.1	612.3
130°	649.8	650.1	650.4	650.6	650.3	649.6	649.0	648.3	647.7	647.1	646.4
132.5°	681.8	682.3	682.8	683.0	682.7	682.0	681.4	680.7	680.1	679.6	679.1
135°	714.1	714.6	715.1	715.3	715.1	714.6	714.1	713.7	713.2	712.6	711.9
137.5°	744.8	745.1	745.4	745.6	745.2	744.4	743.6	742.8	742.0	741.7	741.3
140°	772.1	772.4	772.7	772.9	772.6	771.9	771.3	770.6	770.0	769.5	769.1
142.5°	797.6	798.1	798.6	798.8	798.6	798.1	797.6	797.2	796.7	796.2	795.7
145°	822.6	822.6	822.6	822.6	822.4	822.1	821.8	821.4	821.1	820.8	820.5
147.5°	842.9	843.7	844.5	844.9	844.7	844.4	844.1	843.7	843.4	843.1	842.8
150°	863.8	864.3	864.8	865.0	864.8	864.5	864.2	863.9	863.6	863.3	863.0
152.5°	881.7	882.5	883.3	883.7	883.4	882.8	882.1	881.5	880.9	880.7	880.5
155°	897.9	898.9	899.8	900.3	899.9	899.1	898.3	897.5	896.7	896.5	896.4
157.5°	912.2	913.5	914.8	915.4	914.9	914.0	913.0	912.1	911.1	911.3	911.4
160°	924.8	925.9	927.0	927.6	927.1	926.2	925.2	924.3	923.3	923.5	923.6
162.5°	936.8	937.7	938.7	939.2	938.6	937.5	936.4	935.2	934.1	934.3	934.4
165°	946.4	947.5	948.6	949.2	948.6	947.3	946.0	944.8	943.5	943.7	943.8
167.5°	954.0	955.3	956.6	957.2	956.6	955.3	954.0	952.7	951.4	951.4	951.4
170°	960.4	961.7	963.0	963.6	963.0	961.7	960.4	959.2	957.9	957.9	957.9
172.5°	964.3	965.8	967.2	967.9	967.3	966.0	964.7	963.5	962.2	962.0	961.9
175°	967.6	968.9	970.2	970.8	970.2	969.1	968.0	966.9	965.8	965.6	965.5
177.5°	969.0	970.6	972.2	973.0	972.4	971.1	969.8	968.5	967.2	967.0	966.9
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	527.1	524.9	522.7	522.7	517.9	513.6	511.4	512.3	509.7	506.2	502.7
5°	550.2	541.5	539.7	534.9	528.4	519.3	514.5	510.1	504.9	497.9	491.4
7.5°	571.6	560.2	554.1	549.3	536.7	524.0	513.6	506.6	497.5	487.0	479.1
10°	599.5	578.5	572.0	561.1	543.2	525.4	513.1	501.8	489.2	477.0	466.5
12.5°	621.7	597.7	585.5	574.6	551.5	528.8	508.4	494.4	479.1	465.6	452.1
15°	647.0	620.0	598.6	585.5	556.3	528.8	505.7	486.1	469.1	452.5	440.8
17.5°	659.2	625.2	615.6	596.9	554.6	527.1	498.8	477.8	457.3	438.2	424.2
20°	678.4	638.7	614.7	602.1	564.6	524.0	490.9	466.9	445.6	425.1	410.3
22.5°	679.7	636.5	620.8	596.9	550.6	514.9	483.9	454.7	429.9	410.7	395.4
25°	676.6	632.6	610.8	591.6	553.3	509.7	470.0	441.2	416.8	394.6	376.7
27.5°	675.3	621.3	600.8	581.6	538.4	494.4	461.7	429.0	401.1	381.5	363.2
30°	673.6	609.1	584.2	562.0	522.3	482.6	443.4	415.1	388.5	363.6	345.3
32.5°	662.3	592.5	567.2	543.7	500.9	461.3	430.3	400.2	371.5	348.3	331.8
35°	658.8	577.2	544.1	518.8	477.0	441.6	409.0	384.1	357.1	334.0	314.3
37.5°	648.7	561.5	525.8	493.5	449.9	416.4	392.4	367.5	341.4	316.5	300.8
40°	631.3	543.2	502.7	469.6	424.6	390.6	368.4	350.1	324.4	302.1	283.0
42.5°	605.6	524.5	480.9	446.0	396.3	364.5	346.2	328.7	306.9	283.8	268.1
45°	575.9	499.6	459.1	420.3	369.7	338.8	319.6	309.1	289.1	269.4	251.1
47.5°	535.4	473.9	433.8	393.7	342.2	312.2	296.9	286.4	272.5	251.1	236.3
50°	484.4	440.8	402.8	367.1	315.2	286.4	271.2	263.3	251.6	236.3	221.9
52.5°	427.7	402.4	371.0	337.9	287.7	260.7	246.8	240.7	231.9	217.6	205.3
55°	370.6	359.7	338.3	305.6	259.0	236.7	224.5	216.7	210.1	199.7	189.2
57.5°	319.6	314.3	299.5	274.2	235.0	211.9	201.4	196.2	191.0	183.1	172.6
60°	266.8	272.5	257.2	244.6	208.8	188.8	179.6	174.0	171.3	164.4	157.8
62.5°	221.0	226.3	217.6	208.0	182.7	164.8	159.1	153.9	152.2	146.1	139.5
65°	179.6	186.2	179.6	174.4	159.1	144.3	137.3	134.7	133.0	129.1	123.8
67.5°	143.0	149.5	146.5	139.9	135.2	122.9	119.0	116.4	115.5	112.5	108.1
70°	107.7	116.8	117.7	113.8	109.4	103.8	101.1	100.3	98.1	95.5	92.9
72.5°	77.6	88.1	88.5	88.5	85.9	85.9	83.3	82.0	82.0	79.3	76.3
75°	57.1	64.1	65.0	65.8	67.1	68.4	66.7	66.7	66.3	63.7	62.3
77.5°	37.9	44.0	46.2	49.3	51.0	51.0	51.9	52.8	51.9	50.6	49.7
80°	24.4	28.8	31.4	33.1	35.8	37.1	38.4	38.8	37.9	37.5	36.2
82.5°	16.1	17.4	18.7	20.9	24.0	26.2	26.2	25.7	26.6	26.2	25.7
85°	9.2	10.0	10.5	10.9	12.6	14.8	15.3	15.7	16.6	15.7	14.8
87.5°	3.5	3.9	3.9	3.9	4.8	5.2	6.5	8.3	7.8	7.0	7.0
90°	11.0	8.9	7.9	7.1	5.5	3.9	2.3	0.7	2.3	3.9	5.5
92.5°	14.4	12.9	12.2	12.7	13.7	14.6	15.6	16.6	15.6	14.6	13.7
95°	17.0	15.3	14.4	17.7	24.2	30.8	37.3	43.9	37.3	30.8	24.2
97.5°	47.5	55.6	59.7	61.9	66.4	70.9	75.4	79.9	75.4	70.9	66.4
100°	98.6	123.5	136.0	134.4	131.2	128.0	124.8	121.6	124.8	128.0	131.2
102.5°	136.8	164.6	178.5	177.5	175.4	173.3	171.2	169.1	171.2	173.3	175.4
105°	200.8	215.2	222.4	221.5	219.8	218.0	216.3	214.5	216.3	218.0	219.8
107.5°	272.8	270.4	269.2	268.5	267.0	265.6	264.1	262.7	264.1	265.6	267.0
110°	319.3	317.6	316.7	316.1	314.8	313.5	312.2	310.9	312.2	313.5	314.8

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	364.6	362.9	362.0	361.4	360.3	359.2	358.1	357.0	358.1	359.2	360.3
115°	408.8	407.3	406.6	406.1	405.2	404.2	403.3	402.3	403.3	404.2	405.2
117.5°	453.1	452.3	451.9	451.3	450.2	449.1	448.0	446.9	448.0	449.1	450.2
120°	495.1	494.6	494.4	493.7	492.2	490.8	489.3	487.9	489.3	490.8	492.2
122.5°	535.7	535.0	534.7	534.1	533.0	531.9	530.8	529.7	530.8	531.9	533.0
125°	573.8	573.2	572.9	572.3	571.0	569.7	568.4	567.1	568.4	569.7	571.0
127.5°	611.5	610.7	610.3	609.7	608.4	607.1	605.8	604.5	605.8	607.1	608.4
130°	645.8	645.1	644.8	644.2	642.9	641.6	640.4	639.1	640.4	641.6	642.9
132.5°	678.6	678.1	677.9	677.3	676.0	674.7	673.5	672.2	673.5	674.7	676.0
135°	711.3	710.6	710.3	709.8	708.9	707.9	707.0	706.0	707.0	707.9	708.9
137.5°	741.0	740.7	740.5	739.9	738.6	737.3	736.1	734.8	736.1	737.3	738.6
140°	768.6	768.1	767.9	767.4	766.5	765.5	764.6	763.6	764.6	765.5	766.5
142.5°	795.2	794.7	794.5	794.0	793.1	792.1	791.2	790.2	791.2	792.1	793.1
145°	820.2	819.9	819.7	819.1	818.0	816.9	815.8	814.7	815.8	816.9	818.0
147.5°	842.5	842.2	842.0	841.6	840.8	840.0	839.2	838.4	839.2	840.0	840.8
150°	862.7	862.4	862.2	862.0	861.5	861.0	860.5	860.0	860.5	861.0	861.5
152.5°	880.4	880.2	880.1	880.0	879.9	879.7	879.6	879.4	879.6	879.7	879.9
155°	896.2	896.1	896.0	896.2	896.5	896.8	897.1	897.4	897.1	896.8	896.5
157.5°	911.6	911.7	911.8	911.8	911.8	911.8	911.8	911.8	911.8	911.8	911.8
160°	923.8	923.9	924.0	924.1	924.3	924.4	924.6	924.8	924.6	924.4	924.3
162.5°	934.6	934.7	934.8	935.0	935.5	936.0	936.5	937.0	936.5	936.0	935.5
165°	944.0	944.1	944.2	944.4	944.9	945.4	945.9	946.4	945.9	945.4	944.9
167.5°	951.4	951.4	951.4	951.7	952.4	953.0	953.7	954.3	953.7	953.0	952.4
170°	957.9	957.9	957.9	958.2	958.9	959.5	960.2	960.8	960.2	959.5	958.9
172.5°	961.7	961.6	961.5	961.9	962.7	963.5	964.3	965.1	964.3	963.5	962.7
175°	965.3	965.2	965.1	965.5	966.3	967.1	967.9	968.7	967.9	967.1	966.3
177.5°	966.7	966.6	966.5	966.9	967.7	968.5	969.3	970.1	969.3	968.5	967.7
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	502.7	500.5	499.6	497.5	492.2	488.7	484.8	482.2	482.6	480.5	481.8
5°	487.0	486.6	483.5	479.1	471.7	467.8	460.8	457.3	455.6	456.0	453.4
7.5°	473.9	470.0	467.8	460.8	453.9	445.6	439.9	436.9	434.2	431.6	429.9
10°	459.1	455.6	452.1	444.7	435.1	427.3	419.4	416.4	412.4	410.7	409.4
12.5°	443.4	441.2	436.9	428.1	417.2	409.8	400.7	398.9	393.7	390.2	389.3
15°	429.0	427.7	419.8	409.8	398.9	391.5	383.7	378.4	369.7	371.5	368.4
17.5°	413.7	408.1	403.3	389.8	384.5	373.2	364.0	361.4	355.3	351.4	347.5
20°	396.7	393.3	387.2	378.4	365.8	352.7	345.7	341.4	337.9	331.8	330.0
22.5°	380.6	376.3	371.0	359.7	348.8	337.9	328.3	324.4	320.0	315.7	313.0
25°	368.0	361.4	355.8	341.8	330.9	321.8	315.7	309.1	303.0	300.4	299.5
27.5°	348.3	344.4	338.8	325.7	315.7	305.6	300.0	295.6	289.1	286.0	283.4
30°	335.7	327.9	321.3	310.9	300.8	289.9	284.7	279.5	275.5	271.6	268.6
32.5°	318.7	312.6	307.4	296.9	286.9	276.8	271.2	263.3	261.2	258.1	254.6
35°	302.1	298.2	292.5	281.2	270.3	263.3	257.2	249.8	247.2	245.0	242.0
37.5°	286.4	280.8	276.8	265.9	256.4	248.1	243.3	237.2	235.4	232.8	230.6
40°	272.9	267.3	263.3	252.4	242.4	233.7	230.6	224.5	221.9	218.9	217.6
42.5°	257.7	252.9	247.6	239.8	229.3	220.6	214.5	211.0	207.5	206.2	203.6
45°	241.5	237.2	233.2	224.5	213.6	207.5	202.3	197.5	194.9	192.7	191.0
47.5°	227.6	223.7	218.4	208.8	200.1	194.4	189.2	184.4	181.8	179.2	177.0
50°	211.5	209.3	203.6	194.4	186.2	179.6	174.8	170.5	168.7	165.7	162.2
52.5°	197.1	193.1	188.3	180.9	173.5	165.7	159.1	156.5	153.5	151.7	148.7
55°	180.1	177.4	172.2	165.7	157.8	151.3	146.5	143.0	139.1	137.3	133.4
57.5°	165.7	160.9	158.3	150.0	142.6	136.0	132.5	129.1	124.7	122.1	120.3
60°	150.0	145.6	141.7	134.7	129.5	122.5	117.3	114.2	111.2	107.7	105.9
62.5°	134.7	131.2	126.4	120.8	114.2	108.6	104.6	100.3	98.5	95.0	93.7
65°	118.2	115.5	111.6	105.1	99.8	95.0	91.1	87.6	85.9	84.6	83.7
67.5°	103.3	99.8	97.2	91.6	85.9	82.0	79.8	77.6	75.4	74.1	72.8
70°	88.1	85.5	82.8	77.6	73.7	70.2	68.4	66.7	65.4	64.1	62.8
72.5°	72.4	71.1	68.4	65.0	61.9	59.3	58.0	55.8	54.5	52.3	51.4
75°	59.7	57.5	56.2	53.2	50.6	48.4	46.6	44.0	42.3	41.4	41.0
77.5°	47.1	46.2	44.5	41.9	40.5	38.4	35.8	34.9	34.0	34.0	33.6
80°	35.3	34.0	32.7	30.5	29.2	27.5	27.5	27.5	27.0	27.5	27.0
82.5°	24.0	23.1	22.2	20.9	20.5	20.5	20.9	20.9	20.9	20.9	20.9
85°	14.0	14.0	14.0	14.4	14.0	14.0	14.4	14.8	14.4	14.4	14.0
87.5°	6.5	6.5	7.0	7.0	7.4	7.4	7.4	7.4	7.4	7.4	7.8
90°	7.1	7.9	8.9	11.0	13.1	15.2	17.3	17.9	18.6	19.2	19.9
92.5°	12.7	12.2	12.9	14.4	15.8	17.3	18.7	19.8	20.9	22.0	23.1
95°	17.7	14.4	15.3	17.0	18.8	20.5	22.3	23.4	24.5	25.6	26.7
97.5°	61.9	59.7	55.6	47.5	39.3	31.2	23.0	24.3	25.6	26.9	28.2
100°	134.4	136.0	123.5	98.6	73.6	48.7	23.7	25.0	26.3	27.6	28.9
102.5°	177.5	178.5	164.6	136.8	108.9	81.1	53.3	48.0	42.7	37.4	32.1
105°	221.5	222.4	215.2	200.8	186.4	172.0	157.6	129.3	101.0	72.7	44.4
107.5°	268.5	269.2	270.4	272.8	275.1	277.5	279.9	255.3	230.7	206.0	181.4
110°	316.1	316.7	317.6	319.3	321.1	322.8	324.6	319.3	314.0	308.7	303.4

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	361.4	362.0	362.9	364.6	366.4	368.1	369.9	371.3	372.8	374.2	375.7
115°	406.1	406.6	407.3	408.8	410.2	411.7	413.1	414.7	416.3	417.9	419.5
117.5°	451.3	451.9	452.3	453.1	453.9	454.7	455.5	456.8	458.1	459.4	460.7
120°	493.7	494.4	494.6	495.1	495.6	496.1	496.6	497.9	499.1	500.4	501.7
122.5°	534.1	534.7	535.0	535.7	536.3	537.0	537.6	538.4	539.2	540.0	540.8
125°	572.3	572.9	573.2	573.8	574.5	575.1	575.7	576.0	576.4	576.7	577.0
127.5°	609.7	610.3	610.7	611.5	612.3	613.1	613.9	614.4	614.8	615.3	615.8
130°	644.2	644.8	645.1	645.8	646.4	647.1	647.7	648.3	649.0	649.6	650.3
132.5°	677.3	677.9	678.1	678.6	679.1	679.6	680.1	680.7	681.4	682.0	682.7
135°	709.8	710.3	710.6	711.3	711.9	712.6	713.2	713.7	714.1	714.6	715.1
137.5°	739.9	740.5	740.7	741.0	741.3	741.7	742.0	742.8	743.6	744.4	745.2
140°	767.4	767.9	768.1	768.6	769.1	769.5	770.0	770.6	771.3	771.9	772.6
142.5°	794.0	794.5	794.7	795.2	795.7	796.2	796.7	797.2	797.6	798.1	798.6
145°	819.1	819.7	819.9	820.2	820.5	820.8	821.1	821.4	821.8	822.1	822.4
147.5°	841.6	842.0	842.2	842.5	842.8	843.1	843.4	843.7	844.1	844.4	844.7
150°	862.0	862.2	862.4	862.7	863.0	863.3	863.6	863.9	864.2	864.5	864.8
152.5°	880.0	880.1	880.2	880.4	880.5	880.7	880.9	881.5	882.1	882.8	883.4
155°	896.2	896.0	896.1	896.2	896.4	896.5	896.7	897.5	898.3	899.1	899.9
157.5°	911.8	911.8	911.7	911.6	911.4	911.3	911.1	912.1	913.0	914.0	914.9
160°	924.1	924.0	923.9	923.8	923.6	923.5	923.3	924.3	925.2	926.2	927.1
162.5°	935.0	934.8	934.7	934.6	934.4	934.3	934.1	935.2	936.4	937.5	938.6
165°	944.4	944.2	944.1	944.0	943.8	943.7	943.5	944.8	946.0	947.3	948.6
167.5°	951.7	951.4	951.4	951.4	951.4	951.4	951.4	952.7	954.0	955.3	956.6
170°	958.2	957.9	957.9	957.9	957.9	957.9	957.9	959.2	960.4	961.7	963.0
172.5°	961.9	961.5	961.6	961.7	961.9	962.0	962.2	963.5	964.7	966.0	967.3
175°	965.5	965.1	965.2	965.3	965.5	965.6	965.8	966.9	968.0	969.1	970.2
177.5°	966.9	966.5	966.6	966.7	966.9	967.0	967.2	968.5	969.8	971.1	972.4
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.3	481.8	480.5	477.8	477.4	478.3	480.9	480.0	477.8	481.8	478.3
5°	454.7	452.5	451.7	452.5	449.9	448.6	451.2	449.9	451.2	451.7	453.0
7.5°	429.0	429.4	426.8	427.3	423.8	424.6	424.6	424.6	426.0	426.8	428.6
10°	406.8	407.6	404.6	405.0	402.4	400.7	402.0	404.6	404.6	404.6	405.5
12.5°	388.9	385.0	382.8	382.4	379.3	378.4	381.0	381.9	384.1	384.1	385.4
15°	366.7	365.8	364.0	364.0	356.6	358.4	359.2	362.3	366.7	363.2	364.0
17.5°	346.6	344.4	342.2	341.4	340.5	337.9	341.4	340.9	343.6	344.0	345.3
20°	328.7	327.0	322.6	323.1	323.9	320.0	322.2	322.2	324.8	327.4	330.5
22.5°	311.3	309.5	307.4	308.2	305.6	304.8	304.8	306.9	310.0	312.2	311.7
25°	297.8	294.7	293.4	292.1	290.8	291.7	290.4	292.5	294.7	296.0	294.7
27.5°	282.5	281.2	278.6	277.3	275.1	276.0	276.8	278.6	279.9	279.9	281.2
30°	267.7	265.9	265.1	263.8	263.8	262.0	262.5	264.2	265.5	266.8	268.6
32.5°	253.3	252.0	250.7	250.7	249.8	249.4	248.9	251.6	251.6	254.2	254.2
35°	241.5	239.4	239.4	237.2	238.0	237.6	236.7	238.5	238.9	240.7	240.2
37.5°	228.5	228.5	227.6	225.4	223.7	224.1	226.3	226.3	227.6	227.1	228.5
40°	215.4	214.5	214.5	213.2	212.8	212.3	212.8	213.2	215.4	214.9	215.4
42.5°	202.3	202.7	200.6	200.6	200.6	199.2	199.7	200.1	201.0	201.9	203.2
45°	189.7	188.8	188.3	187.5	186.6	187.0	186.6	188.3	187.9	188.8	190.1
47.5°	176.1	174.8	174.4	172.6	172.6	173.5	173.1	174.4	174.8	176.1	175.3
50°	163.1	161.3	160.0	160.4	157.8	158.7	158.7	160.0	161.3	161.7	162.6
52.5°	147.8	147.4	146.9	144.7	144.3	143.9	144.3	144.7	146.5	147.8	148.2
55°	133.0	132.5	129.9	129.1	127.7	127.7	128.6	129.1	132.1	132.5	134.3
57.5°	119.5	118.2	115.1	114.7	114.7	114.7	113.4	115.1	116.0	118.2	118.2
60°	104.6	104.6	102.0	102.0	102.5	102.0	102.0	102.5	102.5	104.2	105.1
62.5°	92.9	92.4	92.4	91.6	91.1	91.6	91.1	91.1	91.6	92.9	94.2
65°	82.4	82.0	81.5	81.1	80.2	80.2	80.7	81.5	81.5	82.4	82.8
67.5°	72.4	72.4	71.5	71.5	71.1	70.6	71.1	70.6	72.4	72.4	72.8
70°	62.3	61.9	60.6	60.2	58.9	59.3	59.3	60.6	61.0	61.9	62.8
72.5°	50.1	50.1	49.3	48.4	48.8	48.0	48.0	48.4	48.4	49.7	50.1
75°	41.4	40.5	40.1	40.5	40.1	41.0	40.1	40.1	41.0	41.0	41.0
77.5°	34.0	34.0	33.6	33.6	34.0	33.6	34.0	34.0	34.0	33.6	34.0
80°	27.9	27.5	27.5	27.5	27.0	27.0	27.0	27.0	27.0	27.0	27.0
82.5°	20.9	20.9	20.5	20.9	20.9	20.5	20.9	20.5	20.5	20.9	20.9
85°	14.0	14.8	14.0	14.0	14.4	14.4	14.8	14.4	14.8	14.0	14.4
87.5°	7.4	7.8	7.8	7.4	7.4	7.8	7.8	7.8	8.3	7.4	7.8
90°	20.2	20.4	20.7	21.0	21.3	21.6	21.3	21.0	20.7	20.4	20.2
92.5°	23.7	23.8	24.0	24.1	24.3	24.5	24.3	24.1	24.0	23.8	23.7
95°	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3	27.3
97.5°	28.8	28.9	29.0	29.2	29.3	29.5	29.3	29.2	29.0	28.9	28.8
100°	29.5	29.6	29.7	29.9	30.0	30.2	30.0	29.9	29.7	29.6	29.5
102.5°	29.5	29.7	30.0	30.3	30.6	30.9	30.6	30.3	30.0	29.7	29.5
105°	30.2	30.4	30.7	31.0	31.4	31.7	31.4	31.0	30.7	30.4	30.2
107.5°	169.1	158.6	137.7	116.7	95.8	74.8	95.8	116.7	137.7	158.6	169.1
110°	300.8	289.4	266.5	243.6	220.8	197.9	220.8	243.6	266.5	289.4	300.8

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	376.4	376.2	375.9	375.6	375.2	374.9	375.2	375.6	375.9	376.2	376.4
115°	420.3	420.6	421.3	421.9	422.6	423.2	422.6	421.9	421.3	420.6	420.3
117.5°	461.3	461.4	461.5	461.7	461.8	462.0	461.8	461.7	461.5	461.4	461.3
120°	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3	502.3
122.5°	541.2	541.3	541.4	541.6	541.7	541.9	541.7	541.6	541.4	541.3	541.2
125°	577.2	577.4	577.7	578.0	578.3	578.6	578.3	578.0	577.7	577.4	577.2
127.5°	616.0	615.8	615.5	615.2	614.9	614.6	614.9	615.2	615.5	615.8	616.0
130°	650.6	650.4	650.1	649.8	649.4	649.1	649.4	649.8	650.1	650.4	650.6
132.5°	683.0	682.8	682.3	681.8	681.3	680.8	681.3	681.8	682.3	682.8	683.0
135°	715.3	715.1	714.6	714.1	713.7	713.2	713.7	714.1	714.6	715.1	715.3
137.5°	745.6	745.4	745.1	744.8	744.4	744.1	744.4	744.8	745.1	745.4	745.6
140°	772.9	772.7	772.4	772.1	771.8	771.5	771.8	772.1	772.4	772.7	772.9
142.5°	798.8	798.6	798.1	797.6	797.2	796.7	797.2	797.6	798.1	798.6	798.8
145°	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6	822.6
147.5°	844.9	844.5	843.7	842.9	842.1	841.3	842.1	842.9	843.7	844.5	844.9
150°	865.0	864.8	864.3	863.8	863.4	862.9	863.4	863.8	864.3	864.8	865.0
152.5°	883.7	883.3	882.5	881.7	880.9	880.1	880.9	881.7	882.5	883.3	883.7
155°	900.3	899.8	898.9	897.9	897.0	896.0	897.0	897.9	898.9	899.8	900.3
157.5°	915.4	914.8	913.5	912.2	911.0	909.7	911.0	912.2	913.5	914.8	915.4
160°	927.6	927.0	925.9	924.8	923.7	922.6	923.7	924.8	925.9	927.0	927.6
162.5°	939.2	938.7	937.7	936.8	935.8	934.8	935.8	936.8	937.7	938.7	939.2
165°	949.2	948.6	947.5	946.4	945.3	944.2	945.3	946.4	947.5	948.6	949.2
167.5°	957.2	956.6	955.3	954.0	952.7	951.4	952.7	954.0	955.3	956.6	957.2
170°	963.6	963.0	961.7	960.4	959.2	957.9	959.2	960.4	961.7	963.0	963.6
172.5°	967.9	967.2	965.8	964.3	962.9	961.5	962.9	964.3	965.8	967.2	967.9
175°	970.8	970.2	968.9	967.6	966.4	965.1	966.4	967.6	968.9	970.2	970.8
177.5°	973.0	972.2	970.6	969.0	967.4	965.8	967.4	969.0	970.6	972.2	973.0
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2	509.2
2.5°	481.8	483.5	481.8	478.3	481.8	483.9	486.1	489.6	491.4	491.4	494.0
5°	454.3	457.8	456.5	455.6	459.1	461.3	464.8	469.1	473.9	477.0	480.5
7.5°	429.9	432.1	434.2	434.2	437.7	442.5	447.8	453.0	459.1	463.4	466.1
10°	408.5	410.3	411.6	413.3	418.5	423.8	430.7	437.3	442.5	447.3	451.7
12.5°	388.0	390.6	393.7	395.0	398.9	405.5	412.0	419.8	428.1	432.9	437.3
15°	368.4	369.7	373.2	377.1	380.6	387.6	395.9	404.2	411.1	418.5	422.5
17.5°	348.3	348.8	357.9	355.8	367.1	373.6	378.0	385.8	397.2	403.3	409.4
20°	328.7	333.1	337.0	339.2	345.3	352.7	365.4	371.5	380.6	386.3	391.5
22.5°	313.5	320.0	320.0	325.2	328.3	335.3	344.4	356.2	366.2	370.1	377.6
25°	300.0	303.0	308.2	310.0	315.7	321.8	327.9	340.5	351.4	356.6	361.9
27.5°	282.5	286.4	293.4	293.4	300.8	307.4	314.8	323.1	334.0	341.4	347.0
30°	269.0	272.9	276.0	280.8	283.8	289.9	303.0	309.1	318.7	325.2	332.2
32.5°	256.4	259.4	262.0	267.3	270.7	277.7	284.7	295.6	303.9	310.0	317.4
35°	242.4	245.5	248.9	252.9	258.1	264.6	271.2	280.3	288.6	294.3	300.4
37.5°	229.3	231.5	236.7	239.4	243.7	249.8	258.1	267.7	275.1	279.5	285.6
40°	216.7	218.4	222.4	227.1	230.2	235.0	243.7	252.0	261.2	266.4	271.2
42.5°	203.2	205.3	208.8	213.6	218.4	223.7	228.5	238.0	246.3	250.7	255.9
45°	191.4	192.7	195.3	200.1	204.9	208.8	216.2	225.0	232.8	236.3	242.0
47.5°	177.4	178.8	182.7	184.9	190.1	195.3	202.7	211.5	218.4	221.9	227.1
50°	163.1	164.4	167.0	171.8	175.3	180.9	187.5	194.9	203.6	208.4	211.5
52.5°	149.1	151.7	153.9	157.8	162.2	167.9	174.0	180.9	188.3	193.1	196.6
55°	135.2	137.3	139.9	142.1	147.4	152.6	159.6	166.1	172.6	177.0	180.9
57.5°	119.5	122.5	125.1	129.5	133.4	137.8	145.6	150.8	158.7	161.7	165.2
60°	105.9	109.0	111.2	114.7	118.2	123.8	129.1	135.6	142.1	146.1	150.4
62.5°	94.6	95.9	97.2	100.7	104.2	109.4	114.7	121.2	128.2	130.4	133.8
65°	83.3	84.6	86.8	89.8	92.4	95.5	101.1	106.4	112.9	116.4	117.7
67.5°	73.7	75.0	75.4	77.6	79.8	83.3	86.3	91.6	97.7	99.8	102.5
70°	62.8	65.0	65.4	67.1	68.0	70.2	73.7	77.6	82.4	86.3	88.5
72.5°	50.1	53.2	54.1	56.7	58.0	60.2	62.8	65.8	68.9	70.6	72.4
75°	41.0	41.9	42.3	44.5	46.6	49.7	51.0	52.8	55.4	57.5	59.3
77.5°	34.0	34.4	34.9	34.9	35.3	37.1	39.7	41.9	43.6	44.5	45.8
80°	27.5	27.0	27.0	27.5	27.5	27.5	28.3	31.4	32.3	34.4	34.0
82.5°	21.4	20.5	20.9	20.5	20.5	20.5	20.5	20.9	20.9	22.2	23.1
85°	14.0	14.4	14.0	14.0	13.5	14.0	13.5	13.5	13.1	13.1	12.6
87.5°	7.4	7.8	7.4	7.4	7.0	7.4	7.0	7.0	6.5	6.5	5.7
90°	19.9	19.2	18.6	17.9	17.3	15.2	13.1	11.0	8.9	7.9	7.1
92.5°	23.1	22.0	20.9	19.8	18.7	17.3	15.8	14.4	12.9	12.2	12.7
95°	26.7	25.6	24.5	23.4	22.3	20.5	18.8	17.0	15.3	14.4	17.7
97.5°	28.2	26.9	25.6	24.3	23.0	31.2	39.3	47.5	55.6	59.7	61.9
100°	28.9	27.6	26.3	25.0	23.7	48.7	73.6	98.6	123.5	136.0	134.4
102.5°	32.1	37.4	42.7	48.0	53.3	81.1	108.9	136.8	164.6	178.5	177.5
105°	44.4	72.7	101.0	129.3	157.6	172.0	186.4	200.8	215.2	222.4	221.5
107.5°	181.4	206.0	230.7	255.3	279.9	277.5	275.1	272.8	270.4	269.2	268.5
110°	303.4	308.7	314.0	319.3	324.6	322.8	321.1	319.3	317.6	316.7	316.1

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	375.7	374.2	372.8	371.3	369.9	368.1	366.4	364.6	362.9	362.0	361.4
115°	419.5	417.9	416.3	414.7	413.1	411.7	410.2	408.8	407.3	406.6	406.1
117.5°	460.7	459.4	458.1	456.8	455.5	454.7	453.9	453.1	452.3	451.9	451.3
120°	501.7	500.4	499.1	497.9	496.6	496.1	495.6	495.1	494.6	494.4	493.7
122.5°	540.8	540.0	539.2	538.4	537.6	537.0	536.3	535.7	535.0	534.7	534.1
125°	577.0	576.7	576.4	576.0	575.7	575.1	574.5	573.8	573.2	572.9	572.3
127.5°	615.8	615.3	614.8	614.4	613.9	613.1	612.3	611.5	610.7	610.3	609.7
130°	650.3	649.6	649.0	648.3	647.7	647.1	646.4	645.8	645.1	644.8	644.2
132.5°	682.7	682.0	681.4	680.7	680.1	679.6	679.1	678.6	678.1	677.9	677.3
135°	715.1	714.6	714.1	713.7	713.2	712.6	711.9	711.3	710.6	710.3	709.8
137.5°	745.2	744.4	743.6	742.8	742.0	741.7	741.3	741.0	740.7	740.5	739.9
140°	772.6	771.9	771.3	770.6	770.0	769.5	769.1	768.6	768.1	767.9	767.4
142.5°	798.6	798.1	797.6	797.2	796.7	796.2	795.7	795.2	794.7	794.5	794.0
145°	822.4	822.1	821.8	821.4	821.1	820.8	820.5	820.2	819.9	819.7	819.1
147.5°	844.7	844.4	844.1	843.7	843.4	843.1	842.8	842.5	842.2	842.0	841.6
150°	864.8	864.5	864.2	863.9	863.6	863.3	863.0	862.7	862.4	862.2	862.0
152.5°	883.4	882.8	882.1	881.5	880.9	880.7	880.5	880.4	880.2	880.1	880.0
155°	899.9	899.1	898.3	897.5	896.7	896.5	896.4	896.2	896.1	896.0	896.2
157.5°	914.9	914.0	913.0	912.1	911.1	911.3	911.4	911.6	911.7	911.8	911.8
160°	927.1	926.2	925.2	924.3	923.3	923.5	923.6	923.8	923.9	924.0	924.1
162.5°	938.6	937.5	936.4	935.2	934.1	934.3	934.4	934.6	934.7	934.8	935.0
165°	948.6	947.3	946.0	944.8	943.5	943.7	943.8	944.0	944.1	944.2	944.4
167.5°	956.6	955.3	954.0	952.7	951.4	951.4	951.4	951.4	951.4	951.4	951.7
170°	963.0	961.7	960.4	959.2	957.9	957.9	957.9	957.9	957.9	957.9	958.2
172.5°	967.3	966.0	964.7	963.5	962.2	962.0	961.9	961.7	961.6	961.5	961.9
175°	970.2	969.1	968.0	966.9	965.8	965.6	965.5	965.3	965.2	965.1	965.5
177.5°	972.4	971.1	969.8	968.5	967.2	967.0	966.9	966.7	966.6	966.5	966.9
180°	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7	968.7

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	509.2	509.2	509.2	509.2
2.5°	496.1	499.2	505.3	510.5
5°	485.7	490.5	499.6	508.8
7.5°	473.0	480.5	492.2	504.9
10°	460.8	470.4	484.8	499.6
12.5°	448.6	458.7	473.9	493.1
15°	434.2	444.7	463.0	486.1
17.5°	421.6	435.5	452.1	475.2
20°	408.1	418.5	439.9	464.3
22.5°	391.1	408.5	428.6	454.3
25°	377.6	392.8	412.9	442.1
27.5°	361.0	378.9	403.3	429.0
30°	347.5	362.3	385.0	415.9
32.5°	331.8	349.2	372.8	403.3
35°	317.8	332.7	354.9	385.8
37.5°	301.3	317.4	342.2	369.7
40°	286.9	302.6	326.1	351.8
42.5°	269.4	286.0	309.5	331.3
45°	255.5	270.7	289.5	309.5
47.5°	238.5	254.6	272.9	286.9
50°	223.2	238.0	252.4	264.2
52.5°	206.7	220.2	233.2	242.0
55°	191.4	201.9	212.3	218.4
57.5°	173.5	183.5	192.3	195.8
60°	157.8	166.1	171.8	175.7
62.5°	141.3	147.4	151.7	153.9
65°	125.1	129.5	131.7	133.8
67.5°	108.6	112.5	113.8	116.4
70°	91.1	95.5	96.4	97.7
72.5°	78.0	78.0	79.8	81.5
75°	62.3	63.2	64.1	64.1
77.5°	48.8	48.8	49.7	50.1
80°	35.8	36.2	36.2	35.8
82.5°	24.4	25.3	24.4	24.0
85°	13.5	15.3	14.4	14.4
87.5°	5.7	5.7	6.5	5.7
90°	5.5	3.9	2.3	0.7
92.5°	13.7	14.6	15.6	16.6
95°	24.2	30.8	37.3	43.9
97.5°	66.4	70.9	75.4	79.9
100°	131.2	128.0	124.8	121.6
102.5°	175.4	173.3	171.2	169.1
105°	219.8	218.0	216.3	214.5
107.5°	267.0	265.6	264.1	262.7
110°	314.8	313.5	312.2	310.9

TEST NUMBER: P1031158

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	360.3	359.2	358.1	357.0
115°	405.2	404.2	403.3	402.3
117.5°	450.2	449.1	448.0	446.9
120°	492.2	490.8	489.3	487.9
122.5°	533.0	531.9	530.8	529.7
125°	571.0	569.7	568.4	567.1
127.5°	608.4	607.1	605.8	604.5
130°	642.9	641.6	640.4	639.1
132.5°	676.0	674.7	673.5	672.2
135°	708.9	707.9	707.0	706.0
137.5°	738.6	737.3	736.1	734.8
140°	766.5	765.5	764.6	763.6
142.5°	793.1	792.1	791.2	790.2
145°	818.0	816.9	815.8	814.7
147.5°	840.8	840.0	839.2	838.4
150°	861.5	861.0	860.5	860.0
152.5°	879.9	879.7	879.6	879.4
155°	896.5	896.8	897.1	897.4
157.5°	911.8	911.8	911.8	911.8
160°	924.3	924.4	924.6	924.8
162.5°	935.5	936.0	936.5	937.0
165°	944.9	945.4	945.9	946.4
167.5°	952.4	953.0	953.7	954.3
170°	958.9	959.5	960.2	960.8
172.5°	962.7	963.5	964.3	965.1
175°	966.3	967.1	967.9	968.7
177.5°	967.7	968.5	969.3	970.1
180°	968.7	968.7	968.7	968.7

(END OF REPORT)