

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031175

Luminaire Tested: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031175
REPORT IS A COMBINATION OF REPORTS P994431 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7437.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	94	90	86	83	84	80	77	75	63	61	60	48	47	45	34	33	32
2	85	79	73	68	76	71	66	62	56	53	50	42	40	38	30	29	28
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21
5	66	55	47	41	59	50	43	38	40	35	31	30	27	25	22	20	18
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15
8	52	40	33	28	46	36	30	26	29	25	21	23	20	17	17	15	13
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12
10	45	33	27	22	40	30	24	20	25	20	17	19	16	14	14	12	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9510	9510	9510	9510
5°	9518	10953	9542	8126
10°	9434	13222	9475	7098
15°	9336	15006	9336	6258
20°	9145	16186	9196	5551
25°	9004	15378	8987	5066
30°	8841	10655	8823	4590
35°	8645	6841	8606	4232
40°	8401	4831	8359	3876
45°	7977	3865	7965	3528
50°	7454	3234	7430	3122
55°	6867	2665	6811	2647
60°	6289	2203	6227	2251
65°	5613	1763	5649	1908
70°	4989	1225	5124	1543
75°	4230	909	4401	1186
80°	3366	603	3654	889
85°	2401	286	2613	554

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 12696 cd/sqm

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.2
10°-20°	271.6	3.7
20°-30°	427.8	5.8
30°-40°	444.8	6.0
40°-50°	380.6	5.1
50°-60°	290.1	3.9
60°-70°	185.9	2.5
70°-80°	89.1	1.2
80°-90°	26.9	0.4
90°-100°	60.5	0.8
100°-110°	292.7	3.9
110°-120°	717.2	9.6
120°-130°	910.5	12.2
130°-140°	972.7	13.1
140°-150°	909.6	12.2
150°-160°	733.7	9.9
160°-170°	473.5	6.4
170°-180°	163.2	2.2
0°-30°	786.1	10.6
0°-40°	1231.0	16.6
0°-60°	1901.6	25.6
0°-90°	2203.4	29.6
90°-120°	1070.5	14.4
90°-150°	3863.3	51.9
90°-180°	5234.0	70.4
0°-180°	7437.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	884	884	884	884	884	
5°	883	1049	885	778	883	84
15°	843	1491	843	622	843	237
25°	767	1536	766	506	767	353
35°	669	666	666	412	669	419
45°	537	356	536	324	537	414
55°	379	223	376	222	379	340
65°	232	129	234	139	232	232
75°	111	54	116	71	111	120
85°	25	13	27	25	25	28
90°	1	38	1	38	1	6
95°	78	48	78	48	78	93
105°	380	56	380	56	380	403
115°	713	750	713	750	713	704
125°	1005	1025	1005	1025	1005	898
135°	1251	1264	1251	1264	1251	963
145°	1444	1458	1444	1458	1444	904
155°	1590	1588	1590	1588	1590	733
165°	1677	1673	1677	1673	1677	474
175°	1717	1710	1717	1710	1717	163
180°	1717	1717	1717	1717	1717	

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	885.8	891.8	896.4	899.4	907.0	911.5	915.3	922.1	922.1	923.6	926.6
5°	882.8	895.6	904.7	916.8	932.7	940.2	950.8	959.9	972.8	979.6	986.4
7.5°	876.0	894.1	913.0	931.2	954.6	969.7	980.3	1003.8	1020.4	1040.9	1056.7
10°	866.9	891.8	916.0	944.0	975.8	998.5	1014.4	1045.4	1077.2	1105.9	1130.1
12.5°	855.5	885.8	920.6	954.6	999.2	1021.9	1047.7	1086.2	1131.6	1167.9	1200.5
15°	843.4	878.2	917.6	959.2	1015.1	1046.9	1084.0	1130.9	1181.5	1233.7	1278.4
17.5°	824.5	868.4	912.3	972.8	1038.6	1057.5	1089.3	1153.6	1216.3	1263.2	1317.7
20°	805.6	854.8	910.0	964.5	1035.6	1079.4	1108.9	1177.0	1244.3	1301.1	1353.3
22.5°	788.2	839.6	897.1	966.0	1032.5	1076.4	1113.5	1184.6	1262.5	1326.0	1390.3
25°	767.0	823.0	886.5	951.6	1032.5	1065.8	1106.7	1189.1	1271.6	1344.9	1424.4
27.5°	744.3	801.1	863.8	930.4	1004.5	1053.7	1093.8	1182.3	1282.9	1361.6	1443.3
30°	721.6	779.9	840.4	900.2	983.4	1030.3	1076.4	1174.0	1289.0	1379.0	1441.8
32.5°	699.7	748.9	808.6	866.9	949.3	1000.8	1053.0	1165.7	1291.2	1366.9	1397.1
35°	669.4	720.9	769.3	831.3	914.5	965.2	1026.5	1164.9	1281.4	1328.3	1313.2
37.5°	641.5	684.6	730.7	785.9	871.4	937.2	1000.8	1145.2	1248.9	1251.9	1166.4
40°	610.4	646.0	684.6	742.8	835.1	900.2	969.0	1115.0	1189.9	1145.2	994.7
42.5°	574.9	606.7	636.9	693.6	794.3	866.9	941.0	1077.2	1104.4	1001.5	844.9
45°	537.1	562.8	590.8	650.5	751.1	823.0	897.1	1018.9	990.9	845.7	696.7
47.5°	497.7	519.7	546.9	601.4	705.0	778.4	848.7	935.7	864.6	708.8	584.0
50°	458.4	475.8	502.3	558.2	658.1	724.7	789.7	846.4	746.6	608.2	482.6
52.5°	419.8	433.4	460.7	508.3	605.1	668.7	715.6	737.5	636.2	502.3	419.1
55°	379.0	394.1	412.3	460.7	556.7	603.6	634.6	633.9	529.5	425.9	346.4
57.5°	339.6	353.3	369.1	417.6	495.5	527.2	553.7	540.9	441.8	348.7	297.3
60°	304.8	312.4	329.8	370.7	429.7	456.9	472.0	450.1	360.8	294.3	245.8
62.5°	267.0	274.6	289.0	327.5	363.8	378.2	391.1	363.1	298.0	239.8	210.3
65°	232.2	242.1	251.1	282.1	301.8	319.2	317.7	294.3	233.0	195.2	171.0
67.5°	202.0	205.7	213.3	232.2	241.3	254.2	254.9	228.4	187.6	158.9	144.5
70°	169.4	173.2	178.5	187.6	193.6	196.7	195.2	171.7	141.5	124.1	111.2
72.5°	141.5	140.7	144.5	144.5	150.5	149.8	145.2	127.1	107.4	93.0	85.5
75°	111.2	112.0	112.7	111.2	108.9	105.9	102.1	88.5	75.6	68.8	62.0
77.5°	87.0	85.5	86.2	80.9	77.9	74.9	69.6	62.8	52.2	50.7	47.7
80°	62.0	61.3	60.5	58.2	51.4	48.4	44.6	40.8	38.6	37.1	36.3
82.5°	41.6	41.6	40.1	35.6	31.8	29.5	28.7	27.2	25.0	25.0	24.2
85°	25.0	24.2	22.7	18.2	15.9	15.9	15.9	15.9	14.4	14.4	13.6
87.5°	9.8	9.1	6.8	6.8	6.1	6.1	6.1	5.3	5.3	4.5	4.5
90°	1.3	4.1	6.9	9.8	12.6	14.0	15.8	19.5	23.2	26.9	30.6
92.5°	29.3	27.6	25.9	24.2	22.5	21.7	23.0	25.5	28.1	30.6	33.2
95°	77.8	66.2	54.6	42.9	31.3	25.5	27.1	30.2	33.3	36.4	39.5
97.5°	141.6	133.7	125.7	117.8	109.9	105.9	98.7	84.2	69.7	55.3	40.8
100°	215.5	221.2	226.9	232.6	238.3	241.1	219.0	174.8	130.5	86.3	42.1
102.5°	299.7	303.4	307.1	310.8	314.5	316.3	291.6	242.3	193.0	143.7	94.4
105°	380.1	383.2	386.3	389.4	392.5	394.1	381.3	355.8	330.3	304.8	279.3
107.5°	465.5	468.1	470.6	473.2	475.7	477.0	479.1	483.4	487.6	491.9	496.1
110°	551.0	553.3	555.5	557.8	560.1	561.2	562.8	565.9	569.0	572.1	575.2

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	632.6	634.6	636.6	638.5	640.5	641.5	643.1	646.2	649.3	652.5	655.6
115°	713.0	714.7	716.4	718.1	719.8	720.6	721.9	724.4	727.0	729.5	732.1
117.5°	792.0	794.0	796.0	798.0	800.0	801.0	801.7	803.1	804.5	805.9	807.3
120°	864.7	867.3	869.8	872.4	874.9	876.2	876.6	877.5	878.3	879.2	880.0
122.5°	938.7	940.7	942.7	944.6	946.6	947.6	948.2	949.3	950.4	951.6	952.7
125°	1005.0	1007.3	1009.5	1011.8	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3
127.5°	1071.4	1073.7	1075.9	1078.2	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9
130°	1132.6	1134.9	1137.1	1139.4	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9
132.5°	1191.2	1193.5	1195.8	1198.1	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3
135°	1251.2	1252.9	1254.6	1256.3	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9
137.5°	1302.2	1304.5	1306.7	1309.0	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0
140°	1353.2	1354.9	1356.6	1358.3	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7
142.5°	1400.4	1402.1	1403.8	1405.5	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9
145°	1443.8	1445.8	1447.8	1449.7	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3
147.5°	1485.9	1487.3	1488.7	1490.1	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8
150°	1524.1	1525.0	1525.8	1526.7	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5
152.5°	1558.6	1558.9	1559.1	1559.4	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1
155°	1590.5	1589.9	1589.3	1588.8	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2
157.5°	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7
160°	1638.9	1638.6	1638.3	1638.0	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4
162.5°	1660.6	1659.8	1658.9	1658.1	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5
165°	1677.2	1676.4	1675.5	1674.7	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1
167.5°	1691.2	1690.1	1688.9	1687.8	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1
170°	1702.7	1701.6	1700.4	1699.3	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6
172.5°	1710.3	1708.9	1707.5	1706.1	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2
175°	1716.7	1715.3	1713.9	1712.4	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6
177.5°	1719.3	1717.9	1716.5	1715.0	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	932.7	932.7	939.5	946.3	942.5	944.8	953.1	950.1	956.1	955.4	957.6
5°	1003.0	1011.4	1018.2	1032.5	1034.8	1032.5	1046.9	1050.7	1057.5	1049.2	1053.0
7.5°	1082.5	1099.9	1116.5	1137.7	1144.5	1146.0	1153.6	1164.2	1173.2	1156.6	1164.9
10°	1159.6	1186.1	1220.1	1239.0	1255.7	1261.7	1267.8	1274.6	1285.2	1295.0	1287.5
12.5°	1242.8	1281.4	1313.9	1348.0	1368.4	1366.1	1383.5	1388.1	1396.4	1398.6	1401.7
15°	1310.9	1365.4	1385.8	1436.5	1441.0	1456.1	1475.8	1493.2	1495.5	1490.9	1490.9
17.5°	1376.0	1422.9	1459.2	1500.0	1508.3	1521.2	1546.2	1554.5	1557.5	1556.7	1556.7
20°	1428.9	1459.9	1521.2	1555.2	1568.8	1585.5	1602.9	1613.5	1615.7	1618.8	1614.2
22.5°	1463.7	1510.6	1560.5	1588.5	1599.9	1605.9	1617.3	1620.3	1616.5	1617.3	1618.0
25°	1490.9	1537.1	1567.3	1574.9	1574.1	1566.6	1558.3	1543.9	1542.4	1536.3	1524.2
27.5°	1498.5	1515.9	1512.1	1481.1	1450.1	1447.1	1397.1	1369.9	1338.9	1343.4	1326.0
30°	1457.6	1435.0	1381.2	1302.6	1270.1	1217.1	1161.1	1102.9	1080.2	1055.2	1101.4
32.5°	1357.8	1276.9	1181.5	1079.4	1025.0	978.1	918.3	876.0	851.7	831.3	870.7
35°	1207.3	1080.9	954.6	857.8	813.2	770.8	714.8	693.6	663.4	666.4	670.2
37.5°	1013.6	874.4	779.1	683.8	654.3	636.9	596.1	563.5	553.0	549.9	549.9
40°	832.1	717.9	633.1	558.2	535.6	521.2	488.7	473.5	462.2	459.2	462.9
42.5°	688.4	590.8	525.0	475.0	459.2	441.0	427.4	408.5	406.2	400.9	407.7
45°	577.9	493.2	444.0	407.7	394.1	387.3	372.2	360.8	356.3	355.5	360.8
47.5°	490.2	424.4	381.2	358.5	348.0	341.2	328.3	323.8	319.2	320.7	318.5
50°	411.5	362.3	334.3	313.9	307.1	300.3	292.0	287.4	285.2	285.2	284.4
52.5°	353.3	312.4	294.3	275.3	272.3	268.5	259.5	256.4	252.6	251.9	254.9
55°	302.6	274.6	256.4	245.1	242.1	234.5	230.7	226.9	224.7	223.1	223.9
57.5°	258.7	237.5	225.4	215.6	210.3	207.3	200.5	199.7	198.2	198.2	197.4
60°	222.4	207.3	192.9	186.8	183.1	179.3	178.5	174.0	171.7	173.2	172.5
62.5°	188.4	176.2	167.9	161.1	158.9	155.8	153.6	152.0	149.8	150.5	150.5
65°	157.3	147.5	141.5	135.4	134.6	131.6	130.9	129.4	129.4	128.6	130.1
67.5°	129.4	122.5	117.2	113.5	111.2	112.0	108.9	106.7	106.7	105.9	108.2
70°	102.9	99.1	93.8	89.3	86.2	86.2	82.5	81.7	81.7	81.7	80.9
72.5°	79.4	72.6	70.3	68.8	68.8	68.8	67.3	67.3	66.6	67.3	66.6
75°	59.0	58.2	56.7	56.0	56.0	55.2	54.5	54.5	54.5	54.5	54.5
77.5°	46.1	46.1	44.6	43.9	43.9	43.9	43.1	43.1	42.4	42.4	42.4
80°	34.0	34.0	32.5	32.5	32.5	31.8	31.8	31.8	32.5	31.8	31.8
82.5°	23.4	23.4	22.7	23.4	22.7	21.9	21.9	21.9	21.2	21.9	21.9
85°	13.6	13.6	12.9	12.1	12.9	12.9	12.1	12.9	12.1	12.9	12.1
87.5°	5.3	4.5	4.5	4.5	3.8	4.5	3.8	3.8	4.5	3.8	4.5
90°	31.7	32.9	34.0	35.1	35.7	36.0	36.6	37.1	37.7	38.3	37.7
92.5°	35.2	37.2	39.1	41.1	42.1	42.2	42.5	42.8	43.1	43.4	43.1
95°	41.5	43.5	45.5	47.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	43.1	45.3	47.6	49.9	51.0	51.1	51.4	51.7	52.0	52.3	52.0
100°	44.4	46.6	48.9	51.2	52.3	52.4	52.7	53.0	53.3	53.6	53.3
102.5°	85.0	75.7	66.3	57.0	52.3	52.6	53.1	53.7	54.2	54.8	54.2
105°	229.1	179.0	128.8	78.7	53.6	53.9	54.4	55.0	55.5	56.1	55.5
107.5°	452.5	408.8	365.2	321.5	299.7	281.1	244.0	206.9	169.7	132.6	169.7
110°	565.8	556.5	547.1	537.8	533.1	512.8	472.3	431.8	391.2	350.7	391.2

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	658.1	660.7	663.2	665.7	667.0	666.7	666.2	665.6	665.1	664.5	665.1
115°	734.9	737.7	740.6	743.4	744.8	745.4	746.5	747.6	748.8	749.9	748.8
117.5°	809.6	811.8	814.1	816.4	817.5	817.6	817.9	818.2	818.5	818.8	818.5
120°	882.3	884.5	886.8	889.1	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	954.1	955.5	957.0	958.4	959.1	959.2	959.5	959.8	960.1	960.4	960.1
125°	1020.9	1021.5	1022.0	1022.6	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8
127.5°	1088.8	1089.6	1090.5	1091.4	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8
130°	1149.0	1150.2	1151.3	1152.4	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0
132.5°	1206.4	1207.6	1208.7	1209.8	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4
135°	1264.8	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8
137.5°	1316.4	1317.8	1319.2	1320.6	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4
140°	1365.8	1367.0	1368.1	1369.2	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9
142.5°	1412.7	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7
145°	1455.9	1456.4	1457.0	1457.5	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1495.4	1495.9	1496.5	1497.0	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4
150°	1531.1	1531.7	1532.2	1532.8	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1
152.5°	1562.2	1563.4	1564.5	1565.6	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2
155°	1590.6	1592.0	1593.5	1594.9	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6
157.5°	1616.4	1618.1	1619.8	1621.5	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4
160°	1638.1	1639.8	1641.5	1643.2	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1
162.5°	1657.5	1659.5	1661.4	1663.4	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5
165°	1674.4	1676.6	1678.9	1681.2	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4
167.5°	1688.4	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4
170°	1699.9	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9
172.5°	1707.5	1709.7	1712.0	1714.3	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5
175°	1713.6	1715.6	1717.5	1719.5	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6
177.5°	1716.5	1718.7	1721.0	1723.3	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	953.9	949.3	946.3	944.0	941.8	948.6	939.5	929.7	922.8	918.3	916.8
5°	1053.7	1043.9	1035.6	1028.7	1030.3	1030.3	1014.4	997.0	981.9	973.5	964.5
7.5°	1169.4	1158.9	1142.2	1138.4	1135.4	1116.5	1100.6	1068.8	1049.9	1031.0	1014.4
10°	1284.4	1270.8	1254.9	1249.6	1242.1	1218.6	1194.4	1153.6	1130.1	1095.3	1073.4
12.5°	1391.8	1375.2	1359.3	1355.5	1344.2	1323.8	1282.2	1239.8	1199.7	1162.6	1124.1
15°	1481.9	1477.3	1453.1	1438.0	1413.0	1385.0	1376.0	1318.5	1267.8	1229.2	1159.6
17.5°	1557.5	1536.3	1513.6	1503.8	1494.0	1461.4	1428.9	1369.9	1315.4	1258.7	1214.1
20°	1618.0	1594.6	1578.7	1564.3	1559.8	1522.7	1471.3	1419.1	1359.3	1295.8	1237.5
22.5°	1621.0	1618.0	1607.4	1599.1	1590.0	1565.8	1525.0	1459.9	1396.4	1326.8	1250.4
25°	1558.3	1553.7	1584.0	1576.4	1582.5	1573.4	1551.4	1497.0	1422.9	1341.2	1264.0
27.5°	1369.1	1415.3	1462.9	1479.6	1490.9	1523.5	1534.0	1503.8	1444.0	1357.0	1270.8
30°	1112.0	1173.2	1250.4	1292.0	1323.8	1384.3	1462.9	1472.8	1444.8	1375.2	1269.3
32.5°	872.9	928.9	990.9	1040.1	1082.5	1206.5	1312.4	1388.8	1402.4	1366.1	1273.1
35°	703.5	727.7	786.7	833.6	891.1	997.0	1121.8	1245.1	1328.3	1332.8	1261.7
37.5°	580.2	593.0	644.5	671.0	705.0	798.0	914.5	1075.6	1205.0	1266.3	1230.0
40°	480.3	509.8	539.3	554.5	578.7	643.0	754.9	881.2	1041.6	1155.1	1180.8
42.5°	416.8	429.7	448.6	469.7	484.9	540.9	615.7	731.5	876.0	1034.0	1105.1
45°	367.6	372.2	391.8	405.4	421.3	460.7	513.6	610.4	737.5	893.3	1014.4
47.5°	326.8	335.9	346.4	354.8	365.4	395.6	441.0	511.3	623.3	762.5	892.6
50°	290.5	295.8	309.4	313.2	320.7	341.9	376.7	430.4	522.7	633.9	768.5
52.5°	256.4	266.3	271.6	276.9	283.7	301.1	323.8	367.6	437.2	541.6	655.8
55°	230.0	233.0	240.5	245.1	250.4	262.5	282.1	314.7	369.1	452.3	560.5
57.5°	204.2	204.2	211.8	215.6	220.9	230.0	247.4	272.3	311.7	373.7	472.8
60°	177.0	177.8	183.8	188.4	189.9	198.9	213.3	233.0	263.2	308.6	389.6
62.5°	152.8	156.6	159.6	161.1	166.4	171.7	183.8	197.4	218.6	258.7	316.2
65°	132.4	133.1	135.4	136.9	139.2	145.2	154.3	163.4	181.5	211.0	257.9
67.5°	108.9	112.0	115.0	115.0	117.2	120.3	129.4	136.9	150.5	167.9	199.7
70°	81.7	83.2	87.7	90.0	93.0	98.3	102.9	107.4	118.0	130.9	155.1
72.5°	68.1	68.1	69.6	70.3	70.3	74.1	80.9	85.5	90.8	99.8	116.5
75°	54.5	54.5	56.7	56.0	57.5	59.0	59.8	62.8	65.8	72.6	82.5
77.5°	43.1	43.9	43.9	44.6	44.6	45.4	46.1	47.7	49.2	53.0	57.5
80°	31.8	32.5	32.5	33.3	33.3	34.0	34.8	35.6	37.1	38.6	40.8
82.5°	21.9	22.7	22.7	23.4	22.7	23.4	24.2	24.2	25.0	26.5	27.2
85°	12.9	12.9	13.6	12.9	12.9	12.9	13.6	13.6	14.4	16.6	16.6
87.5°	3.8	4.5	3.8	4.5	4.5	4.5	4.5	5.3	5.3	6.1	6.8
90°	37.1	36.6	36.0	35.7	35.1	34.0	32.9	31.7	30.6	26.9	23.2
92.5°	42.8	42.5	42.2	42.1	41.1	39.1	37.2	35.2	33.2	30.6	28.1
95°	48.5	48.5	48.5	48.5	47.5	45.5	43.5	41.5	39.5	36.4	33.3
97.5°	51.7	51.4	51.1	51.0	49.9	47.6	45.3	43.1	40.8	55.3	69.7
100°	53.0	52.7	52.4	52.3	51.2	48.9	46.6	44.4	42.1	86.3	130.5
102.5°	53.7	53.1	52.6	52.3	57.0	66.3	75.7	85.0	94.4	143.7	193.0
105°	55.0	54.4	53.9	53.6	78.7	128.8	179.0	229.1	279.3	304.8	330.3
107.5°	206.9	244.0	281.1	299.7	321.5	365.2	408.8	452.5	496.1	491.9	487.6
110°	431.8	472.3	512.8	533.1	537.8	547.1	556.5	565.8	575.2	572.1	569.0

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	665.6	666.2	666.7	667.0	665.7	663.2	660.7	658.1	655.6	652.5	649.3
115°	747.6	746.5	745.4	744.8	743.4	740.6	737.7	734.9	732.1	729.5	727.0
117.5°	818.2	817.9	817.6	817.5	816.4	814.1	811.8	809.6	807.3	805.9	804.5
120°	890.2	890.2	890.2	890.2	889.1	886.8	884.5	882.3	880.0	879.2	878.3
122.5°	959.8	959.5	959.2	959.1	958.4	957.0	955.5	954.1	952.7	951.6	950.4
125°	1024.3	1023.7	1023.2	1022.9	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0
127.5°	1090.4	1090.9	1091.5	1091.8	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1
130°	1151.6	1152.1	1152.7	1153.0	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6
132.5°	1208.3	1209.1	1210.0	1210.4	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6
135°	1265.6	1266.5	1267.4	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6
137.5°	1319.9	1320.5	1321.0	1321.3	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8
140°	1368.4	1369.0	1369.5	1369.8	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0
142.5°	1413.6	1414.4	1415.3	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2
145°	1457.8	1457.8	1457.8	1457.8	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1
147.5°	1493.8	1495.2	1496.6	1497.3	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6
150°	1530.9	1531.8	1532.7	1533.1	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4
152.5°	1562.6	1564.1	1565.5	1566.2	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5
155°	1591.3	1593.0	1594.7	1595.6	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6
157.5°	1616.6	1618.9	1621.2	1622.3	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3
160°	1639.1	1641.0	1643.0	1644.0	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9
162.5°	1660.2	1661.9	1663.6	1664.4	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1
165°	1677.4	1679.3	1681.3	1682.3	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7
167.5°	1690.6	1692.9	1695.2	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1
170°	1702.1	1704.4	1706.7	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6
172.5°	1709.1	1711.6	1714.1	1715.4	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7
175°	1714.8	1717.1	1719.4	1720.5	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0
177.5°	1717.3	1720.1	1723.0	1724.4	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	914.5	910.7	907.0	907.0	898.6	891.1	887.3	888.8	884.3	878.2	872.2
5°	954.6	939.5	936.5	928.1	916.8	900.9	892.6	885.0	876.0	863.8	852.5
7.5°	991.7	972.0	961.4	953.1	931.2	909.2	891.1	879.0	863.1	844.9	831.3
10°	1040.1	1003.8	992.4	973.5	942.5	911.5	890.3	870.7	848.7	827.5	809.4
12.5°	1078.7	1037.1	1015.9	997.0	956.9	917.6	882.0	857.8	831.3	807.9	784.4
15°	1122.5	1075.6	1038.6	1015.9	965.2	917.6	877.5	843.4	813.9	785.2	764.8
17.5°	1143.7	1084.7	1068.1	1035.6	962.2	914.5	865.4	829.1	793.5	760.2	736.0
20°	1177.0	1108.2	1066.6	1044.6	979.6	909.2	851.7	810.1	773.1	737.5	711.8
22.5°	1179.3	1104.4	1077.2	1035.6	955.4	893.3	839.6	789.0	745.8	712.6	686.1
25°	1174.0	1097.6	1059.8	1026.5	959.9	884.3	815.4	765.5	723.2	684.6	653.6
27.5°	1171.7	1077.9	1042.4	1009.1	934.2	857.8	801.1	744.3	695.9	661.9	630.1
30°	1168.7	1056.7	1013.6	975.0	906.2	837.4	769.3	720.1	674.0	630.9	599.1
32.5°	1149.0	1028.0	984.1	943.3	869.1	800.3	746.6	694.4	644.5	604.4	575.6
35°	1143.0	1001.5	944.0	900.2	827.5	766.3	709.5	666.4	619.5	579.4	545.4
37.5°	1125.6	974.3	912.3	856.3	780.6	722.4	680.8	637.7	592.3	549.2	521.9
40°	1095.3	942.5	872.2	814.7	736.8	677.8	639.2	607.4	562.8	524.2	490.9
42.5°	1050.7	910.0	834.3	773.8	687.6	632.4	600.6	570.4	532.5	492.4	465.2
45°	999.2	866.9	796.5	729.2	641.5	587.7	554.5	536.3	501.5	467.5	435.7
47.5°	928.9	822.2	752.7	683.1	593.8	541.6	515.1	497.0	472.8	435.7	410.0
50°	840.4	764.8	698.9	636.9	546.9	497.0	470.5	456.9	436.5	410.0	385.0
52.5°	742.1	698.2	643.7	586.2	499.2	452.3	428.1	417.6	402.4	377.5	356.3
55°	643.0	624.1	587.0	530.3	449.3	410.7	389.6	375.9	364.6	346.4	328.3
57.5°	554.5	545.4	519.7	475.8	407.7	367.6	349.5	340.4	331.3	317.7	299.5
60°	462.9	472.8	446.3	424.4	362.3	327.5	311.7	301.8	297.3	285.2	273.8
62.5°	383.5	392.6	377.5	360.8	316.9	285.9	276.1	267.0	264.0	253.4	242.1
65°	311.7	323.0	311.7	302.6	276.1	250.4	238.3	233.7	230.7	223.9	214.8
67.5°	248.1	259.5	254.2	242.8	234.5	213.3	206.5	202.0	200.5	195.2	187.6
70°	186.8	202.7	204.2	197.4	189.9	180.0	175.5	174.0	170.2	165.7	161.1
72.5°	134.6	152.8	153.6	153.6	149.0	149.0	144.5	142.2	142.2	137.7	132.4
75°	99.1	111.2	112.7	114.2	116.5	118.8	115.7	115.7	115.0	110.4	108.2
77.5°	65.8	76.4	80.2	85.5	88.5	88.5	90.0	91.5	90.0	87.7	86.2
80°	42.4	49.9	54.5	57.5	62.0	64.3	66.6	67.3	65.8	65.1	62.8
82.5°	28.0	30.3	32.5	36.3	41.6	45.4	45.4	44.6	46.1	45.4	44.6
85°	15.9	17.4	18.2	18.9	21.9	25.7	26.5	27.2	28.7	27.2	25.7
87.5°	6.1	6.8	6.8	6.8	8.3	9.1	11.3	14.4	13.6	12.1	12.1
90°	19.5	15.8	14.0	12.6	9.8	6.9	4.1	1.3	4.1	6.9	9.8
92.5°	25.5	23.0	21.7	22.5	24.2	25.9	27.6	29.3	27.6	25.9	24.2
95°	30.2	27.1	25.5	31.3	42.9	54.6	66.2	77.8	66.2	54.6	42.9
97.5°	84.2	98.7	105.9	109.9	117.8	125.7	133.7	141.6	133.7	125.7	117.8
100°	174.8	219.0	241.1	238.3	232.6	226.9	221.2	215.5	221.2	226.9	232.6
102.5°	242.3	291.6	316.3	314.5	310.8	307.1	303.4	299.7	303.4	307.1	310.8
105°	355.8	381.3	394.1	392.5	389.4	386.3	383.2	380.1	383.2	386.3	389.4
107.5°	483.4	479.1	477.0	475.7	473.2	470.6	468.1	465.5	468.1	470.6	473.2
110°	565.9	562.8	561.2	560.1	557.8	555.5	553.3	551.0	553.3	555.5	557.8

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	646.2	643.1	641.5	640.5	638.5	636.6	634.6	632.6	634.6	636.6	638.5
115°	724.4	721.9	720.6	719.8	718.1	716.4	714.7	713.0	714.7	716.4	718.1
117.5°	803.1	801.7	801.0	800.0	798.0	796.0	794.0	792.0	794.0	796.0	798.0
120°	877.5	876.6	876.2	874.9	872.4	869.8	867.3	864.7	867.3	869.8	872.4
122.5°	949.3	948.2	947.6	946.6	944.6	942.7	940.7	938.7	940.7	942.7	944.6
125°	1016.9	1015.8	1015.2	1014.1	1011.8	1009.5	1007.3	1005.0	1007.3	1009.5	1011.8
127.5°	1083.7	1082.3	1081.6	1080.5	1078.2	1075.9	1073.7	1071.4	1073.7	1075.9	1078.2
130°	1144.5	1143.4	1142.8	1141.7	1139.4	1137.1	1134.9	1132.6	1134.9	1137.1	1139.4
132.5°	1202.8	1201.9	1201.5	1200.4	1198.1	1195.8	1193.5	1191.2	1193.5	1195.8	1198.1
135°	1260.5	1259.4	1258.8	1258.0	1256.3	1254.6	1252.9	1251.2	1252.9	1254.6	1256.3
137.5°	1313.3	1312.7	1312.4	1311.3	1309.0	1306.7	1304.5	1302.2	1304.5	1306.7	1309.0
140°	1362.2	1361.3	1360.9	1360.0	1358.3	1356.6	1354.9	1353.2	1354.9	1356.6	1358.3
142.5°	1409.4	1408.5	1408.1	1407.2	1405.5	1403.8	1402.1	1400.4	1402.1	1403.8	1405.5
145°	1453.6	1453.0	1452.7	1451.7	1449.7	1447.8	1445.8	1443.8	1445.8	1447.8	1449.7
147.5°	1493.1	1492.5	1492.2	1491.5	1490.1	1488.7	1487.3	1485.9	1487.3	1488.7	1490.1
150°	1528.8	1528.3	1528.0	1527.6	1526.7	1525.8	1525.0	1524.1	1525.0	1525.8	1526.7
152.5°	1560.2	1559.9	1559.8	1559.7	1559.4	1559.1	1558.9	1558.6	1558.9	1559.1	1559.4
155°	1588.3	1588.0	1587.9	1588.2	1588.8	1589.3	1589.9	1590.5	1589.9	1589.3	1588.8
157.5°	1615.6	1615.9	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0	1616.0
160°	1637.2	1637.5	1637.6	1637.7	1638.0	1638.3	1638.6	1638.9	1638.6	1638.3	1638.0
162.5°	1656.4	1656.7	1656.8	1657.2	1658.1	1658.9	1659.8	1660.6	1659.8	1658.9	1658.1
165°	1673.0	1673.3	1673.4	1673.8	1674.7	1675.5	1676.4	1677.2	1676.4	1675.5	1674.7
167.5°	1686.1	1686.1	1686.1	1686.7	1687.8	1688.9	1690.1	1691.2	1690.1	1688.9	1687.8
170°	1697.6	1697.6	1697.6	1698.2	1699.3	1700.4	1701.6	1702.7	1701.6	1700.4	1699.3
172.5°	1704.4	1704.1	1704.0	1704.7	1706.1	1707.5	1708.9	1710.3	1708.9	1707.5	1706.1
175°	1710.7	1710.4	1710.3	1711.0	1712.4	1713.9	1715.3	1716.7	1715.3	1713.9	1712.4
177.5°	1713.3	1713.0	1712.9	1713.6	1715.0	1716.5	1717.9	1719.3	1717.9	1716.5	1715.0
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	872.2	868.4	866.9	863.1	854.0	848.0	841.2	836.6	837.4	833.6	835.9
5°	844.9	844.2	838.9	831.3	818.5	811.7	799.6	793.5	790.5	791.2	786.7
7.5°	822.2	815.4	811.7	799.6	787.4	773.1	763.2	757.9	753.4	748.9	745.8
10°	796.5	790.5	784.4	771.6	754.9	741.3	727.7	722.4	715.6	712.6	710.3
12.5°	769.3	765.5	757.9	742.8	723.9	711.0	695.2	692.1	683.1	677.0	675.5
15°	744.3	742.1	728.4	711.0	692.1	679.3	665.7	656.6	641.5	644.5	639.2
17.5°	717.9	708.0	699.7	676.3	667.2	647.5	631.6	627.1	616.5	609.7	602.9
20°	688.4	682.3	671.7	656.6	634.6	612.0	599.9	592.3	586.2	575.6	572.6
22.5°	660.4	652.8	643.7	624.1	605.1	586.2	569.6	562.8	555.2	547.7	543.1
25°	638.4	627.1	617.2	593.0	574.1	558.2	547.7	536.3	525.7	521.2	519.7
27.5°	604.4	597.6	587.7	565.1	547.7	530.3	520.4	512.9	501.5	496.2	491.7
30°	582.5	568.8	557.5	539.3	521.9	503.0	494.0	484.9	478.1	471.3	466.0
32.5°	553.0	542.4	533.3	515.1	497.7	480.3	470.5	456.9	453.1	447.8	441.8
35°	524.2	517.4	507.6	487.9	469.0	456.9	446.3	433.4	428.9	425.1	419.8
37.5°	497.0	487.1	480.3	461.4	444.8	430.4	422.1	411.5	408.5	403.9	400.2
40°	473.5	463.7	456.9	438.0	420.6	405.4	400.2	389.6	385.0	379.7	377.5
42.5°	447.1	438.7	429.7	416.0	397.9	382.8	372.2	366.1	360.1	357.8	353.3
45°	419.1	411.5	404.7	389.6	370.7	360.1	351.0	342.7	338.1	334.3	331.3
47.5°	394.9	388.1	379.0	362.3	347.2	337.4	328.3	320.0	315.4	310.9	307.1
50°	366.9	363.1	353.3	337.4	323.0	311.7	303.3	295.8	292.7	287.4	281.4
52.5°	341.9	335.1	326.8	313.9	301.1	287.4	276.1	271.6	266.3	263.2	257.9
55°	312.4	307.9	298.8	287.4	273.8	262.5	254.2	248.1	241.3	238.3	231.5
57.5°	287.4	279.1	274.6	260.2	247.4	236.0	230.0	223.9	216.3	211.8	208.8
60°	260.2	252.6	245.8	233.7	224.7	212.6	203.5	198.2	192.9	186.8	183.8
62.5°	233.7	227.7	219.4	209.5	198.2	188.4	181.5	174.0	171.0	164.9	162.6
65°	205.0	200.5	193.6	182.3	173.2	164.9	158.1	152.0	149.0	146.7	145.2
67.5°	179.3	173.2	168.7	158.9	149.0	142.2	138.4	134.6	130.9	128.6	126.3
70°	152.8	148.3	143.7	134.6	127.8	121.8	118.8	115.7	113.5	111.2	108.9
72.5°	125.6	123.3	118.8	112.7	107.4	102.9	100.6	96.8	94.6	90.8	89.3
75°	103.6	99.8	97.6	92.3	87.7	84.0	80.9	76.4	73.4	71.9	71.1
77.5°	81.7	80.2	77.2	72.6	70.3	66.6	62.0	60.5	59.0	59.0	58.2
80°	61.3	59.0	56.7	53.0	50.7	47.7	47.7	47.7	46.9	47.7	46.9
82.5°	41.6	40.1	38.6	36.3	35.6	35.6	36.3	36.3	36.3	36.3	36.3
85°	24.2	24.2	24.2	25.0	24.2	24.2	25.0	25.7	25.0	25.0	24.2
87.5°	11.3	11.3	12.1	12.1	12.9	12.9	12.9	12.9	12.9	12.9	13.6
90°	12.6	14.0	15.8	19.5	23.2	26.9	30.6	31.7	32.9	34.0	35.1
92.5°	22.5	21.7	23.0	25.5	28.1	30.6	33.2	35.2	37.2	39.1	41.1
95°	31.3	25.5	27.1	30.2	33.3	36.4	39.5	41.5	43.5	45.5	47.5
97.5°	109.9	105.9	98.7	84.2	69.7	55.3	40.8	43.1	45.3	47.6	49.9
100°	238.3	241.1	219.0	174.8	130.5	86.3	42.1	44.4	46.6	48.9	51.2
102.5°	314.5	316.3	291.6	242.3	193.0	143.7	94.4	85.0	75.7	66.3	57.0
105°	392.5	394.1	381.3	355.8	330.3	304.8	279.3	229.1	179.0	128.8	78.7
107.5°	475.7	477.0	479.1	483.4	487.6	491.9	496.1	452.5	408.8	365.2	321.5
110°	560.1	561.2	562.8	565.9	569.0	572.1	575.2	565.8	556.5	547.1	537.8

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	640.5	641.5	643.1	646.2	649.3	652.5	655.6	658.1	660.7	663.2	665.7
115°	719.8	720.6	721.9	724.4	727.0	729.5	732.1	734.9	737.7	740.6	743.4
117.5°	800.0	801.0	801.7	803.1	804.5	805.9	807.3	809.6	811.8	814.1	816.4
120°	874.9	876.2	876.6	877.5	878.3	879.2	880.0	882.3	884.5	886.8	889.1
122.5°	946.6	947.6	948.2	949.3	950.4	951.6	952.7	954.1	955.5	957.0	958.4
125°	1014.1	1015.2	1015.8	1016.9	1018.0	1019.2	1020.3	1020.9	1021.5	1022.0	1022.6
127.5°	1080.5	1081.6	1082.3	1083.7	1085.1	1086.5	1087.9	1088.8	1089.6	1090.5	1091.4
130°	1141.7	1142.8	1143.4	1144.5	1145.6	1146.8	1147.9	1149.0	1150.2	1151.3	1152.4
132.5°	1200.4	1201.5	1201.9	1202.8	1203.6	1204.5	1205.3	1206.4	1207.6	1208.7	1209.8
135°	1258.0	1258.8	1259.4	1260.5	1261.6	1262.8	1263.9	1264.8	1265.6	1266.5	1267.4
137.5°	1311.3	1312.4	1312.7	1313.3	1313.8	1314.4	1315.0	1316.4	1317.8	1319.2	1320.6
140°	1360.0	1360.9	1361.3	1362.2	1363.0	1363.9	1364.7	1365.8	1367.0	1368.1	1369.2
142.5°	1407.2	1408.1	1408.5	1409.4	1410.2	1411.1	1411.9	1412.7	1413.6	1414.4	1415.3
145°	1451.7	1452.7	1453.0	1453.6	1454.1	1454.7	1455.3	1455.9	1456.4	1457.0	1457.5
147.5°	1491.5	1492.2	1492.5	1493.1	1493.6	1494.2	1494.8	1495.4	1495.9	1496.5	1497.0
150°	1527.6	1528.0	1528.3	1528.8	1529.4	1529.9	1530.5	1531.1	1531.7	1532.2	1532.8
152.5°	1559.7	1559.8	1559.9	1560.2	1560.5	1560.8	1561.1	1562.2	1563.4	1564.5	1565.6
155°	1588.2	1587.9	1588.0	1588.3	1588.6	1588.9	1589.2	1590.6	1592.0	1593.5	1594.9
157.5°	1616.0	1616.0	1615.9	1615.6	1615.3	1615.0	1614.7	1616.4	1618.1	1619.8	1621.5
160°	1637.7	1637.6	1637.5	1637.2	1636.9	1636.7	1636.4	1638.1	1639.8	1641.5	1643.2
162.5°	1657.2	1656.8	1656.7	1656.4	1656.1	1655.8	1655.5	1657.5	1659.5	1661.4	1663.4
165°	1673.8	1673.4	1673.3	1673.0	1672.7	1672.4	1672.1	1674.4	1676.6	1678.9	1681.2
167.5°	1686.7	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1688.4	1690.6	1692.9	1695.2
170°	1698.2	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1699.9	1702.1	1704.4	1706.7
172.5°	1704.7	1704.0	1704.1	1704.4	1704.7	1704.9	1705.2	1707.5	1709.7	1712.0	1714.3
175°	1711.0	1710.3	1710.4	1710.7	1711.0	1711.3	1711.6	1713.6	1715.6	1717.5	1719.5
177.5°	1713.6	1712.9	1713.0	1713.3	1713.6	1713.9	1714.2	1716.5	1718.7	1721.0	1723.3
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.1	835.9	833.6	829.1	828.3	829.8	834.3	832.8	829.1	835.9	829.8
5°	789.0	785.2	783.7	785.2	780.6	778.4	782.9	780.6	782.9	783.7	785.9
7.5°	744.3	745.1	740.5	741.3	735.3	736.8	736.8	736.8	739.0	740.5	743.6
10°	705.8	707.3	702.0	702.7	698.2	695.2	697.4	702.0	702.0	702.0	703.5
12.5°	674.7	667.9	664.1	663.4	658.1	656.6	661.1	662.6	666.4	666.4	668.7
15°	636.2	634.6	631.6	631.6	618.8	621.8	623.3	628.6	636.2	630.1	631.6
17.5°	601.4	597.6	593.8	592.3	590.8	586.2	592.3	591.5	596.1	596.8	599.1
20°	570.4	567.3	559.8	560.5	562.0	555.2	559.0	559.0	563.5	568.1	573.4
22.5°	540.1	537.1	533.3	534.8	530.3	528.7	528.7	532.5	537.8	541.6	540.9
25°	516.6	511.3	509.1	506.8	504.5	506.1	503.8	507.6	511.3	513.6	511.3
27.5°	490.2	487.9	483.4	481.1	477.3	478.8	480.3	483.4	485.6	485.6	487.9
30°	464.5	461.4	459.9	457.6	457.6	454.6	455.4	458.4	460.7	462.9	466.0
32.5°	439.5	437.2	434.9	434.9	433.4	432.7	431.9	436.5	436.5	441.0	441.0
35°	419.1	415.3	415.3	411.5	413.0	412.3	410.7	413.8	414.5	417.6	416.8
37.5°	396.4	396.4	394.9	391.1	388.1	388.8	392.6	392.6	394.9	394.1	396.4
40°	373.7	372.2	372.2	369.9	369.1	368.4	369.1	369.9	373.7	372.9	373.7
42.5°	351.0	351.7	348.0	348.0	348.0	345.7	346.4	347.2	348.7	350.2	352.5
45°	329.0	327.5	326.8	325.3	323.8	324.5	323.8	326.8	326.0	327.5	329.8
47.5°	305.6	303.3	302.6	299.5	299.5	301.1	300.3	302.6	303.3	305.6	304.1
50°	282.9	279.9	277.6	278.4	273.8	275.3	275.3	277.6	279.9	280.6	282.1
52.5°	256.4	255.7	254.9	251.1	250.4	249.6	250.4	251.1	254.2	256.4	257.2
55°	230.7	230.0	225.4	223.9	221.6	221.6	223.1	223.9	229.2	230.0	233.0
57.5°	207.3	205.0	199.7	198.9	198.9	198.9	196.7	199.7	201.2	205.0	205.0
60°	181.5	181.5	177.0	177.0	177.8	177.0	177.0	177.8	177.8	180.8	182.3
62.5°	161.1	160.4	160.4	158.9	158.1	158.9	158.1	158.1	158.9	161.1	163.4
65°	143.0	142.2	141.5	140.7	139.2	139.2	139.9	141.5	141.5	143.0	143.7
67.5°	125.6	125.6	124.1	124.1	123.3	122.5	123.3	122.5	125.6	125.6	126.3
70°	108.2	107.4	105.1	104.4	102.1	102.9	102.9	105.1	105.9	107.4	108.9
72.5°	87.0	87.0	85.5	84.0	84.7	83.2	83.2	84.0	84.0	86.2	87.0
75°	71.9	70.3	69.6	70.3	69.6	71.1	69.6	69.6	71.1	71.1	71.1
77.5°	59.0	59.0	58.2	58.2	59.0	58.2	59.0	59.0	59.0	58.2	59.0
80°	48.4	47.7	47.7	47.7	46.9	46.9	46.9	46.9	46.9	46.9	46.9
82.5°	36.3	36.3	35.6	36.3	36.3	35.6	36.3	35.6	35.6	36.3	36.3
85°	24.2	25.7	24.2	24.2	25.0	25.0	25.7	25.0	25.7	24.2	25.0
87.5°	12.9	13.6	13.6	12.9	12.9	13.6	13.6	13.6	14.4	12.9	13.6
90°	35.7	36.0	36.6	37.1	37.7	38.3	37.7	37.1	36.6	36.0	35.7
92.5°	42.1	42.2	42.5	42.8	43.1	43.4	43.1	42.8	42.5	42.2	42.1
95°	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5	48.5
97.5°	51.0	51.1	51.4	51.7	52.0	52.3	52.0	51.7	51.4	51.1	51.0
100°	52.3	52.4	52.7	53.0	53.3	53.6	53.3	53.0	52.7	52.4	52.3
102.5°	52.3	52.6	53.1	53.7	54.2	54.8	54.2	53.7	53.1	52.6	52.3
105°	53.6	53.9	54.4	55.0	55.5	56.1	55.5	55.0	54.4	53.9	53.6
107.5°	299.7	281.1	244.0	206.9	169.7	132.6	169.7	206.9	244.0	281.1	299.7
110°	533.1	512.8	472.3	431.8	391.2	350.7	391.2	431.8	472.3	512.8	533.1

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	667.0	666.7	666.2	665.6	665.1	664.5	665.1	665.6	666.2	666.7	667.0
115°	744.8	745.4	746.5	747.6	748.8	749.9	748.8	747.6	746.5	745.4	744.8
117.5°	817.5	817.6	817.9	818.2	818.5	818.8	818.5	818.2	817.9	817.6	817.5
120°	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2	890.2
122.5°	959.1	959.2	959.5	959.8	960.1	960.4	960.1	959.8	959.5	959.2	959.1
125°	1022.9	1023.2	1023.7	1024.3	1024.8	1025.4	1024.8	1024.3	1023.7	1023.2	1022.9
127.5°	1091.8	1091.5	1090.9	1090.4	1089.8	1089.2	1089.8	1090.4	1090.9	1091.5	1091.8
130°	1153.0	1152.7	1152.1	1151.6	1151.0	1150.4	1151.0	1151.6	1152.1	1152.7	1153.0
132.5°	1210.4	1210.0	1209.1	1208.3	1207.4	1206.6	1207.4	1208.3	1209.1	1210.0	1210.4
135°	1267.8	1267.4	1266.5	1265.6	1264.8	1263.9	1264.8	1265.6	1266.5	1267.4	1267.8
137.5°	1321.3	1321.0	1320.5	1319.9	1319.4	1318.8	1319.4	1319.9	1320.5	1321.0	1321.3
140°	1369.8	1369.5	1369.0	1368.4	1367.9	1367.3	1367.9	1368.4	1369.0	1369.5	1369.8
142.5°	1415.7	1415.3	1414.4	1413.6	1412.7	1411.9	1412.7	1413.6	1414.4	1415.3	1415.7
145°	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8	1457.8
147.5°	1497.3	1496.6	1495.2	1493.8	1492.4	1491.0	1492.4	1493.8	1495.2	1496.6	1497.3
150°	1533.1	1532.7	1531.8	1530.9	1530.1	1529.2	1530.1	1530.9	1531.8	1532.7	1533.1
152.5°	1566.2	1565.5	1564.1	1562.6	1561.2	1559.8	1561.2	1562.6	1564.1	1565.5	1566.2
155°	1595.6	1594.7	1593.0	1591.3	1589.6	1587.9	1589.6	1591.3	1593.0	1594.7	1595.6
157.5°	1622.3	1621.2	1618.9	1616.6	1614.4	1612.1	1614.4	1616.6	1618.9	1621.2	1622.3
160°	1644.0	1643.0	1641.0	1639.1	1637.1	1635.1	1637.1	1639.1	1641.0	1643.0	1644.0
162.5°	1664.4	1663.6	1661.9	1660.2	1658.5	1656.8	1658.5	1660.2	1661.9	1663.6	1664.4
165°	1682.3	1681.3	1679.3	1677.4	1675.4	1673.4	1675.4	1677.4	1679.3	1681.3	1682.3
167.5°	1696.3	1695.2	1692.9	1690.6	1688.4	1686.1	1688.4	1690.6	1692.9	1695.2	1696.3
170°	1707.8	1706.7	1704.4	1702.1	1699.9	1697.6	1699.9	1702.1	1704.4	1706.7	1707.8
172.5°	1715.4	1714.1	1711.6	1709.1	1706.5	1704.0	1706.5	1709.1	1711.6	1714.1	1715.4
175°	1720.5	1719.4	1717.1	1714.8	1712.6	1710.3	1712.6	1714.8	1717.1	1719.4	1720.5
177.5°	1724.4	1723.0	1720.1	1717.3	1714.4	1711.6	1714.4	1717.3	1720.1	1723.0	1724.4
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5	883.5
2.5°	835.9	838.9	835.9	829.8	835.9	839.6	843.4	849.5	852.5	852.5	857.0
5°	788.2	794.3	792.0	790.5	796.5	800.3	806.4	813.9	822.2	827.5	833.6
7.5°	745.8	749.6	753.4	753.4	759.5	767.8	776.9	785.9	796.5	804.1	808.6
10°	708.8	711.8	714.1	717.1	726.2	735.3	747.4	758.7	767.8	776.1	783.7
12.5°	673.2	677.8	683.1	685.3	692.1	703.5	714.8	728.4	742.8	751.1	758.7
15°	639.2	641.5	647.5	654.3	660.4	672.5	686.8	701.2	713.3	726.2	733.0
17.5°	604.4	605.1	621.0	617.2	636.9	648.3	655.8	669.4	689.1	699.7	710.3
20°	570.4	577.9	584.7	588.5	599.1	612.0	633.9	644.5	660.4	670.2	679.3
22.5°	543.9	555.2	555.2	564.3	569.6	581.7	597.6	618.0	635.4	642.2	655.1
25°	520.4	525.7	534.8	537.8	547.7	558.2	568.8	590.8	609.7	618.8	627.8
27.5°	490.2	497.0	509.1	509.1	521.9	533.3	546.1	560.5	579.4	592.3	602.1
30°	466.7	473.5	478.8	487.1	492.4	503.0	525.7	536.3	553.0	564.3	576.4
32.5°	444.8	450.1	454.6	463.7	469.7	481.8	494.0	512.9	527.2	537.8	550.7
35°	420.6	425.9	431.9	438.7	447.8	459.2	470.5	486.4	500.8	510.6	521.2
37.5°	397.9	401.7	410.7	415.3	422.8	433.4	447.8	464.5	477.3	484.9	495.5
40°	375.9	379.0	385.8	394.1	399.4	407.7	422.8	437.2	453.1	462.2	470.5
42.5°	352.5	356.3	362.3	370.7	379.0	388.1	396.4	413.0	427.4	434.9	444.0
45°	332.1	334.3	338.9	347.2	355.5	362.3	375.2	390.3	403.9	410.0	419.8
47.5°	307.9	310.1	316.9	320.7	329.8	338.9	351.7	366.9	379.0	385.0	394.1
50°	282.9	285.2	289.7	298.0	304.1	313.9	325.3	338.1	353.3	361.6	366.9
52.5°	258.7	263.2	267.0	273.8	281.4	291.2	301.8	313.9	326.8	335.1	341.2
55°	234.5	238.3	242.8	246.6	255.7	264.8	276.9	288.2	299.5	307.1	313.9
57.5°	207.3	212.6	217.1	224.7	231.5	239.0	252.6	261.7	275.3	280.6	286.7
60°	183.8	189.1	192.9	198.9	205.0	214.8	223.9	235.3	246.6	253.4	261.0
62.5°	164.1	166.4	168.7	174.7	180.8	189.9	198.9	210.3	222.4	226.2	232.2
65°	144.5	146.7	150.5	155.8	160.4	165.7	175.5	184.6	195.9	202.0	204.2
67.5°	127.8	130.1	130.9	134.6	138.4	144.5	149.8	158.9	169.4	173.2	177.8
70°	108.9	112.7	113.5	116.5	118.0	121.8	127.8	134.6	143.0	149.8	153.6
72.5°	87.0	92.3	93.8	98.3	100.6	104.4	108.9	114.2	119.5	122.5	125.6
75°	71.1	72.6	73.4	77.2	80.9	86.2	88.5	91.5	96.1	99.8	102.9
77.5°	59.0	59.8	60.5	60.5	61.3	64.3	68.8	72.6	75.6	77.2	79.4
80°	47.7	46.9	46.9	47.7	47.7	47.7	49.2	54.5	56.0	59.8	59.0
82.5°	37.1	35.6	36.3	35.6	35.6	35.6	35.6	36.3	36.3	38.6	40.1
85°	24.2	25.0	24.2	24.2	23.4	24.2	23.4	23.4	22.7	22.7	21.9
87.5°	12.9	13.6	12.9	12.9	12.1	12.9	12.1	12.1	11.3	11.3	9.8
90°	35.1	34.0	32.9	31.7	30.6	26.9	23.2	19.5	15.8	14.0	12.6
92.5°	41.1	39.1	37.2	35.2	33.2	30.6	28.1	25.5	23.0	21.7	22.5
95°	47.5	45.5	43.5	41.5	39.5	36.4	33.3	30.2	27.1	25.5	31.3
97.5°	49.9	47.6	45.3	43.1	40.8	55.3	69.7	84.2	98.7	105.9	109.9
100°	51.2	48.9	46.6	44.4	42.1	86.3	130.5	174.8	219.0	241.1	238.3
102.5°	57.0	66.3	75.7	85.0	94.4	143.7	193.0	242.3	291.6	316.3	314.5
105°	78.7	128.8	179.0	229.1	279.3	304.8	330.3	355.8	381.3	394.1	392.5
107.5°	321.5	365.2	408.8	452.5	496.1	491.9	487.6	483.4	479.1	477.0	475.7
110°	537.8	547.1	556.5	565.8	575.2	572.1	569.0	565.9	562.8	561.2	560.1

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	665.7	663.2	660.7	658.1	655.6	652.5	649.3	646.2	643.1	641.5	640.5
115°	743.4	740.6	737.7	734.9	732.1	729.5	727.0	724.4	721.9	720.6	719.8
117.5°	816.4	814.1	811.8	809.6	807.3	805.9	804.5	803.1	801.7	801.0	800.0
120°	889.1	886.8	884.5	882.3	880.0	879.2	878.3	877.5	876.6	876.2	874.9
122.5°	958.4	957.0	955.5	954.1	952.7	951.6	950.4	949.3	948.2	947.6	946.6
125°	1022.6	1022.0	1021.5	1020.9	1020.3	1019.2	1018.0	1016.9	1015.8	1015.2	1014.1
127.5°	1091.4	1090.5	1089.6	1088.8	1087.9	1086.5	1085.1	1083.7	1082.3	1081.6	1080.5
130°	1152.4	1151.3	1150.2	1149.0	1147.9	1146.8	1145.6	1144.5	1143.4	1142.8	1141.7
132.5°	1209.8	1208.7	1207.6	1206.4	1205.3	1204.5	1203.6	1202.8	1201.9	1201.5	1200.4
135°	1267.4	1266.5	1265.6	1264.8	1263.9	1262.8	1261.6	1260.5	1259.4	1258.8	1258.0
137.5°	1320.6	1319.2	1317.8	1316.4	1315.0	1314.4	1313.8	1313.3	1312.7	1312.4	1311.3
140°	1369.2	1368.1	1367.0	1365.8	1364.7	1363.9	1363.0	1362.2	1361.3	1360.9	1360.0
142.5°	1415.3	1414.4	1413.6	1412.7	1411.9	1411.1	1410.2	1409.4	1408.5	1408.1	1407.2
145°	1457.5	1457.0	1456.4	1455.9	1455.3	1454.7	1454.1	1453.6	1453.0	1452.7	1451.7
147.5°	1497.0	1496.5	1495.9	1495.4	1494.8	1494.2	1493.6	1493.1	1492.5	1492.2	1491.5
150°	1532.8	1532.2	1531.7	1531.1	1530.5	1529.9	1529.4	1528.8	1528.3	1528.0	1527.6
152.5°	1565.6	1564.5	1563.4	1562.2	1561.1	1560.8	1560.5	1560.2	1559.9	1559.8	1559.7
155°	1594.9	1593.5	1592.0	1590.6	1589.2	1588.9	1588.6	1588.3	1588.0	1587.9	1588.2
157.5°	1621.5	1619.8	1618.1	1616.4	1614.7	1615.0	1615.3	1615.6	1615.9	1616.0	1616.0
160°	1643.2	1641.5	1639.8	1638.1	1636.4	1636.7	1636.9	1637.2	1637.5	1637.6	1637.7
162.5°	1663.4	1661.4	1659.5	1657.5	1655.5	1655.8	1656.1	1656.4	1656.7	1656.8	1657.2
165°	1681.2	1678.9	1676.6	1674.4	1672.1	1672.4	1672.7	1673.0	1673.3	1673.4	1673.8
167.5°	1695.2	1692.9	1690.6	1688.4	1686.1	1686.1	1686.1	1686.1	1686.1	1686.1	1686.7
170°	1706.7	1704.4	1702.1	1699.9	1697.6	1697.6	1697.6	1697.6	1697.6	1697.6	1698.2
172.5°	1714.3	1712.0	1709.7	1707.5	1705.2	1704.9	1704.7	1704.4	1704.1	1704.0	1704.7
175°	1719.5	1717.5	1715.6	1713.6	1711.6	1711.3	1711.0	1710.7	1710.4	1710.3	1711.0
177.5°	1723.3	1721.0	1718.7	1716.5	1714.2	1713.9	1713.6	1713.3	1713.0	1712.9	1713.6
180°	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7	1716.7

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	883.5	883.5	883.5	883.5
2.5°	860.8	866.1	876.7	885.8
5°	842.7	851.0	866.9	882.8
7.5°	820.7	833.6	854.0	876.0
10°	799.6	816.2	841.2	866.9
12.5°	778.4	795.8	822.2	855.5
15°	753.4	771.6	803.3	843.4
17.5°	731.5	755.7	784.4	824.5
20°	708.0	726.2	763.2	805.6
22.5°	678.5	708.8	743.6	788.2
25°	655.1	681.5	716.3	767.0
27.5°	626.3	657.3	699.7	744.3
30°	602.9	628.6	667.9	721.6
32.5°	575.6	605.9	646.8	699.7
35°	551.4	577.2	615.7	669.4
37.5°	522.7	550.7	593.8	641.5
40°	497.7	525.0	565.8	610.4
42.5°	467.5	496.2	537.1	574.9
45°	443.3	469.7	502.3	537.1
47.5°	413.8	441.8	473.5	497.7
50°	387.3	413.0	438.0	458.4
52.5°	358.5	382.0	404.7	419.8
55°	332.1	350.2	368.4	379.0
57.5°	301.1	318.5	333.6	339.6
60°	273.8	288.2	298.0	304.8
62.5°	245.1	255.7	263.2	267.0
65°	217.1	224.7	228.4	232.2
67.5°	188.4	195.2	197.4	202.0
70°	158.1	165.7	167.2	169.4
72.5°	135.4	135.4	138.4	141.5
75°	108.2	109.7	111.2	111.2
77.5°	84.7	84.7	86.2	87.0
80°	62.0	62.8	62.8	62.0
82.5°	42.4	43.9	42.4	41.6
85°	23.4	26.5	25.0	25.0
87.5°	9.8	9.8	11.3	9.8
90°	9.8	6.9	4.1	1.3
92.5°	24.2	25.9	27.6	29.3
95°	42.9	54.6	66.2	77.8
97.5°	117.8	125.7	133.7	141.6
100°	232.6	226.9	221.2	215.5
102.5°	310.8	307.1	303.4	299.7
105°	389.4	386.3	383.2	380.1
107.5°	473.2	470.6	468.1	465.5
110°	557.8	555.5	553.3	551.0

TEST NUMBER: P1031175

CATALOG NUMBER: S123RDIW-B560D1320UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	638.5	636.6	634.6	632.6
115°	718.1	716.4	714.7	713.0
117.5°	798.0	796.0	794.0	792.0
120°	872.4	869.8	867.3	864.7
122.5°	944.6	942.7	940.7	938.7
125°	1011.8	1009.5	1007.3	1005.0
127.5°	1078.2	1075.9	1073.7	1071.4
130°	1139.4	1137.1	1134.9	1132.6
132.5°	1198.1	1195.8	1193.5	1191.2
135°	1256.3	1254.6	1252.9	1251.2
137.5°	1309.0	1306.7	1304.5	1302.2
140°	1358.3	1356.6	1354.9	1353.2
142.5°	1405.5	1403.8	1402.1	1400.4
145°	1449.7	1447.8	1445.8	1443.8
147.5°	1490.1	1488.7	1487.3	1485.9
150°	1526.7	1525.8	1525.0	1524.1
152.5°	1559.4	1559.1	1558.9	1558.6
155°	1588.8	1589.3	1589.9	1590.5
157.5°	1616.0	1616.0	1616.0	1616.0
160°	1638.0	1638.3	1638.6	1638.9
162.5°	1658.1	1658.9	1659.8	1660.6
165°	1674.7	1675.5	1676.4	1677.2
167.5°	1687.8	1688.9	1690.1	1691.2
170°	1699.3	1700.4	1701.6	1702.7
172.5°	1706.1	1707.5	1708.9	1710.3
175°	1712.4	1713.9	1715.3	1716.7
177.5°	1715.0	1716.5	1717.9	1719.3
180°	1716.7	1716.7	1716.7	1716.7

(END OF REPORT)