

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031215

Luminaire Tested: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031215
REPORT IS A COMBINATION OF REPORTS P994607 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7182.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	97	92	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42
2	88	81	76	71	80	75	70	65	62	58	55	50	48	46	39	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	51	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13119	13119	13119	13119
5°	13130	15110	13163	11210
10°	13014	18240	13070	9791
15°	12879	20701	12879	8634
20°	12616	22330	12686	7659
25°	12422	21214	12398	6988
30°	12197	14699	12171	6333
35°	11926	9438	11873	5838
40°	11589	6664	11533	5346
45°	11003	5333	10988	4868
50°	10284	4461	10249	4307
55°	9473	3676	9397	3652
60°	8677	3039	8592	3106
65°	7745	2432	7796	2632
70°	6885	1690	7068	2128
75°	5835	1253	6075	1637
80°	4647	831	5044	1227
85°	3304	392	3612	762

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 17515 cd/sqm

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.7	1.7
10°-20°	374.7	5.2
20°-30°	590.1	8.2
30°-40°	613.6	8.5
40°-50°	525.0	7.3
50°-60°	400.3	5.6
60°-70°	256.4	3.6
70°-80°	122.9	1.7
80°-90°	35.0	0.5
90°-100°	47.9	0.7
100°-110°	231.8	3.2
110°-120°	568.0	7.9
120°-130°	721.0	10.0
130°-140°	770.3	10.7
140°-150°	720.3	10.0
150°-160°	581.0	8.1
160°-170°	374.9	5.2
170°-180°	129.2	1.8
0°-30°	1084.5	15.1
0°-40°	1698.2	23.6
0°-60°	2623.4	36.5
0°-90°	3037.7	42.3
90°-120°	847.7	11.8
90°-150°	3059.2	42.6
90°-180°	4144.0	57.7
0°-180°	7182.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1219	1219	1219	1219	1219	
5°	1218	1447	1221	1074	1218	116
15°	1164	2057	1164	858	1164	327
25°	1058	2119	1056	698	1058	487
35°	924	919	919	569	924	578
45°	741	490	740	448	741	570
55°	523	308	519	306	523	468
65°	320	177	322	192	320	320
75°	153	75	160	98	153	166
85°	34	18	38	34	34	38
90°	1	30	1	30	1	5
95°	62	38	62	38	62	74
105°	301	44	301	44	301	319
115°	565	594	565	594	565	558
125°	796	812	796	812	796	711
135°	991	1001	991	1001	991	763
145°	1143	1154	1143	1154	1143	716
155°	1259	1257	1259	1257	1259	580
165°	1328	1325	1328	1325	1328	375
175°	1359	1354	1359	1354	1359	129
180°	1359	1359	1359	1359	1359	

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1222.0	1230.3	1236.6	1240.8	1251.2	1257.5	1262.7	1272.1	1272.1	1274.2	1278.3
5°	1217.8	1235.5	1248.1	1264.8	1286.7	1297.1	1311.7	1324.2	1342.0	1351.4	1360.8
7.5°	1208.4	1233.5	1259.5	1284.6	1316.9	1337.8	1352.4	1384.8	1407.7	1435.9	1457.8
10°	1195.9	1230.3	1263.7	1302.3	1346.2	1377.5	1399.4	1442.2	1486.0	1525.6	1559.0
12.5°	1180.2	1222.0	1270.0	1316.9	1378.5	1409.8	1445.3	1498.5	1561.1	1611.2	1656.1
15°	1163.5	1211.5	1265.8	1323.2	1400.4	1444.3	1495.4	1560.1	1630.0	1702.0	1763.6
17.5°	1137.5	1198.0	1258.5	1342.0	1432.8	1458.9	1502.7	1591.4	1678.0	1742.7	1817.8
20°	1111.4	1179.2	1255.4	1330.5	1428.6	1489.1	1529.8	1623.7	1716.6	1794.9	1866.9
22.5°	1087.4	1158.3	1237.6	1332.6	1424.4	1484.9	1536.1	1634.2	1741.7	1829.3	1918.0
25°	1058.1	1135.4	1223.0	1312.8	1424.4	1470.3	1526.7	1640.4	1754.2	1855.4	1965.0
27.5°	1026.8	1105.1	1191.7	1283.5	1385.8	1453.6	1509.0	1631.0	1769.8	1878.4	1991.1
30°	995.5	1075.9	1159.4	1241.8	1356.6	1421.3	1484.9	1619.6	1778.2	1902.4	1989.0
32.5°	965.3	1033.1	1115.5	1195.9	1309.6	1380.6	1452.6	1608.1	1781.3	1885.7	1927.4
35°	923.5	994.5	1061.3	1146.8	1261.6	1331.6	1416.1	1607.0	1767.7	1832.4	1811.6
37.5°	884.9	944.4	1008.1	1084.2	1202.2	1292.9	1380.6	1579.9	1722.9	1727.0	1609.1
40°	842.1	891.2	944.4	1024.8	1152.1	1241.8	1336.8	1538.2	1641.5	1579.9	1372.2
42.5°	793.1	836.9	878.7	956.9	1095.7	1195.9	1298.2	1486.0	1523.6	1381.6	1165.6
45°	740.9	776.4	815.0	897.4	1036.2	1135.4	1237.6	1405.6	1367.0	1166.7	961.1
47.5°	686.6	716.9	754.5	829.6	972.6	1073.8	1170.8	1290.9	1192.8	977.8	805.6
50°	632.4	656.4	692.9	770.1	907.9	999.7	1089.5	1167.7	1030.0	839.0	665.8
52.5°	579.2	597.9	635.5	701.3	834.8	922.5	987.2	1017.4	877.6	692.9	578.1
55°	522.8	543.7	568.7	635.5	768.0	832.7	875.5	874.5	730.5	587.5	477.9
57.5°	468.5	487.3	509.2	576.0	683.5	727.3	763.9	746.1	609.4	481.1	410.1
60°	420.5	431.0	455.0	511.3	592.7	630.3	651.2	620.9	497.8	405.9	339.1
62.5°	368.4	378.8	398.6	451.9	501.9	521.8	539.5	500.9	411.2	330.8	290.1
65°	320.4	333.9	346.5	389.2	416.4	440.4	438.3	405.9	321.4	269.2	235.8
67.5°	278.6	283.8	294.3	320.4	332.9	350.6	351.7	315.1	258.8	219.1	199.3
70°	233.8	239.0	246.3	258.8	267.1	271.3	269.2	236.9	195.1	171.1	153.4
72.5°	195.1	194.1	199.3	199.3	207.7	206.6	200.4	175.3	148.2	128.4	117.9
75°	153.4	154.4	155.5	153.4	150.3	146.1	140.9	122.1	104.4	95.0	85.6
77.5°	120.0	117.9	119.0	111.7	107.5	103.3	96.0	86.6	72.0	69.9	65.7
80°	85.6	84.5	83.5	80.4	71.0	66.8	61.6	56.4	53.2	51.1	50.1
82.5°	57.4	57.4	55.3	49.0	43.8	40.7	39.7	37.6	34.4	34.4	33.4
85°	34.4	33.4	31.3	25.0	21.9	21.9	21.9	21.9	19.8	19.8	18.8
87.5°	13.6	12.5	9.4	9.4	8.3	8.3	8.3	7.3	7.3	6.3	6.3
90°	1.0	3.2	5.5	7.7	10.0	11.1	12.6	15.5	18.4	21.3	24.2
92.5°	23.2	21.9	20.5	19.2	17.9	17.2	18.2	20.2	22.3	24.3	26.3
95°	61.6	52.4	43.2	34.0	24.8	20.2	21.4	23.9	26.4	28.8	31.3
97.5°	112.1	105.8	99.5	93.2	86.9	83.8	78.1	66.6	55.2	43.7	32.3
100°	170.7	175.2	179.7	184.2	188.7	190.9	173.4	138.4	103.3	68.3	33.3
102.5°	237.3	240.2	243.2	246.1	249.0	250.5	231.0	191.9	152.8	113.8	74.7
105°	301.0	303.5	305.9	308.4	310.9	312.1	302.0	281.8	261.6	241.4	221.2
107.5°	368.6	370.6	372.6	374.7	376.7	377.7	379.4	382.8	386.1	389.5	392.9
110°	436.3	438.1	439.9	441.7	443.5	444.4	445.6	448.1	450.6	453.0	455.5

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	500.9	502.5	504.1	505.6	507.2	508.0	509.2	511.7	514.2	516.6	519.1
115°	564.6	565.9	567.3	568.6	569.9	570.6	571.6	573.6	575.7	577.7	579.7
117.5°	627.2	628.8	630.4	631.9	633.5	634.3	634.9	636.0	637.1	638.2	639.3
120°	684.8	686.8	688.8	690.8	692.8	693.8	694.1	694.8	695.5	696.2	696.9
122.5°	743.3	744.9	746.5	748.0	749.6	750.4	750.8	751.7	752.6	753.5	754.4
125°	795.9	797.7	799.5	801.2	803.0	803.9	804.4	805.3	806.2	807.1	808.0
127.5°	848.4	850.2	852.0	853.8	855.6	856.5	857.1	858.2	859.3	860.4	861.5
130°	896.8	898.6	900.4	902.2	904.0	904.9	905.4	906.3	907.2	908.1	909.0
132.5°	943.3	945.1	946.9	948.7	950.5	951.4	951.7	952.4	953.1	953.7	954.4
135°	990.8	992.1	993.5	994.8	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9
137.5°	1031.2	1033.0	1034.8	1036.6	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3
140°	1071.6	1072.9	1074.3	1075.6	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7
142.5°	1108.9	1110.3	1111.6	1113.0	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0
145°	1143.3	1144.9	1146.5	1148.0	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4
147.5°	1176.6	1177.7	1178.9	1180.0	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7
150°	1206.9	1207.6	1208.2	1208.9	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0
152.5°	1234.2	1234.4	1234.6	1234.9	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2
155°	1259.4	1259.0	1258.5	1258.1	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4
157.5°	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6
160°	1297.8	1297.6	1297.4	1297.1	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8
162.5°	1315.0	1314.3	1313.6	1312.9	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9
165°	1328.1	1327.4	1326.8	1326.1	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1
167.5°	1339.2	1338.3	1337.4	1336.5	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2
170°	1348.3	1347.4	1346.5	1345.6	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3
172.5°	1354.4	1353.3	1352.1	1351.0	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3
175°	1359.4	1358.3	1357.2	1356.1	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4
177.5°	1361.4	1360.3	1359.2	1358.1	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4FO-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1286.7	1286.7	1296.1	1305.5	1300.2	1303.4	1314.9	1310.7	1319.0	1318.0	1321.1
5°	1383.7	1395.2	1404.6	1424.4	1427.6	1424.4	1444.3	1449.5	1458.9	1447.4	1452.6
7.5°	1493.3	1517.3	1540.3	1569.5	1578.9	1581.0	1591.4	1606.0	1618.5	1595.6	1607.0
10°	1599.7	1636.3	1683.2	1709.3	1732.3	1740.6	1749.0	1758.4	1773.0	1786.5	1776.1
12.5°	1714.5	1767.7	1812.6	1859.6	1887.8	1884.6	1908.6	1914.9	1926.4	1929.5	1933.7
15°	1808.4	1883.6	1911.8	1981.7	1987.9	2008.8	2035.9	2059.9	2063.1	2056.8	2056.8
17.5°	1898.2	1962.9	2013.0	2069.3	2080.8	2098.5	2133.0	2144.5	2148.6	2147.6	2147.6
20°	1971.2	2014.0	2098.5	2145.5	2164.3	2187.2	2211.2	2225.9	2229.0	2233.2	2226.9
22.5°	2019.2	2083.9	2152.8	2191.4	2207.1	2215.4	2231.1	2235.3	2230.0	2231.1	2232.1
25°	2056.8	2120.5	2162.2	2172.6	2171.6	2161.2	2149.7	2129.9	2127.8	2119.4	2102.7
27.5°	2067.2	2091.2	2086.0	2043.2	2000.5	1996.3	1927.4	1889.8	1847.1	1853.3	1829.3
30°	2010.9	1979.6	1905.5	1797.0	1752.1	1679.0	1601.8	1521.5	1490.2	1455.7	1519.4
32.5°	1873.1	1761.5	1630.0	1489.1	1414.0	1349.3	1266.9	1208.4	1175.0	1146.8	1201.1
35°	1665.5	1491.2	1316.9	1183.4	1121.8	1063.4	986.1	956.9	915.2	919.4	924.6
37.5°	1398.3	1206.3	1074.8	943.4	902.7	878.7	822.3	777.4	762.8	758.6	758.6
40°	1147.9	990.3	873.4	770.1	738.8	719.0	674.1	653.3	637.6	633.4	638.6
42.5°	949.6	815.0	724.2	655.3	633.4	608.4	589.6	563.5	560.4	553.1	562.5
45°	797.3	680.4	612.6	562.5	543.7	534.3	513.4	497.8	491.5	490.5	497.8
47.5°	676.2	585.4	525.9	494.6	480.0	470.6	452.9	446.6	440.4	442.5	439.3
50°	567.7	499.9	461.2	433.1	423.7	414.3	402.8	396.5	393.4	393.4	392.4
52.5°	487.3	431.0	405.9	379.8	375.7	370.5	357.9	353.8	348.5	347.5	351.7
55°	417.4	378.8	353.8	338.1	333.9	323.5	318.3	313.1	309.9	307.8	308.9
57.5°	356.9	327.7	311.0	297.4	290.1	285.9	276.5	275.5	273.4	273.4	272.4
60°	306.8	285.9	266.1	257.8	252.5	247.3	246.3	240.0	236.9	239.0	237.9
62.5°	259.8	243.1	231.7	222.3	219.1	215.0	211.8	209.8	206.6	207.7	207.7
65°	217.1	203.5	195.1	186.8	185.7	181.6	180.5	178.4	178.4	177.4	179.5
67.5°	178.4	169.1	161.7	156.5	153.4	154.4	150.3	147.1	147.1	146.1	149.2
70°	141.9	136.7	129.4	123.1	119.0	119.0	113.7	112.7	112.7	112.7	111.7
72.5°	109.6	100.2	97.0	95.0	95.0	95.0	92.9	92.9	91.8	92.9	91.8
75°	81.4	80.4	78.3	77.2	77.2	76.2	75.1	75.1	75.1	75.1	75.1
77.5°	63.7	63.7	61.6	60.5	60.5	60.5	59.5	59.5	58.4	58.4	58.4
80°	47.0	47.0	44.9	44.9	44.9	43.8	43.8	43.8	44.9	43.8	43.8
82.5°	32.3	32.3	31.3	32.3	31.3	30.3	30.3	30.3	29.2	30.3	30.3
85°	18.8	18.8	17.7	16.7	17.7	17.7	16.7	17.7	16.7	17.7	16.7
87.5°	7.3	6.3	6.3	6.3	5.2	6.3	5.2	5.2	6.3	5.2	6.3
90°	25.1	26.0	26.9	27.8	28.3	28.5	29.0	29.4	29.9	30.3	29.9
92.5°	27.9	29.4	31.0	32.5	33.3	33.4	33.6	33.9	34.1	34.3	34.1
95°	32.9	34.5	36.0	37.6	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	34.1	35.9	37.7	39.5	40.4	40.5	40.7	41.0	41.2	41.4	41.2
100°	35.1	36.9	38.7	40.5	41.4	41.5	41.7	42.0	42.2	42.4	42.2
102.5°	67.3	59.9	52.5	45.1	41.4	41.6	42.1	42.5	43.0	43.4	43.0
105°	181.5	141.7	102.0	62.3	42.4	42.6	43.1	43.5	44.0	44.4	44.0
107.5°	358.3	323.7	289.2	254.6	237.3	222.6	193.2	163.8	134.4	105.0	134.4
110°	448.1	440.7	433.3	425.9	422.2	406.1	374.0	341.9	309.8	277.7	309.8

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	521.1	523.1	525.2	527.2	528.2	528.0	527.5	527.1	526.6	526.2	526.6
115°	581.9	584.2	586.4	588.7	589.8	590.3	591.2	592.1	593.0	593.9	593.0
117.5°	641.1	642.9	644.7	646.5	647.4	647.5	647.7	648.0	648.2	648.4	648.2
120°	698.7	700.5	702.3	704.1	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	755.5	756.7	757.8	758.9	759.5	759.6	759.8	760.1	760.3	760.5	760.3
125°	808.4	808.9	809.3	809.8	810.0	810.2	810.7	811.1	811.6	812.0	811.6
127.5°	862.2	862.8	863.5	864.2	864.5	864.3	863.8	863.4	862.9	862.5	862.9
130°	909.9	910.8	911.7	912.6	913.0	912.8	912.3	911.9	911.4	911.0	911.4
132.5°	955.3	956.2	957.1	958.0	958.5	958.2	957.5	956.8	956.1	955.4	956.1
135°	1001.6	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6
137.5°	1042.4	1043.5	1044.6	1045.7	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7
140°	1081.6	1082.5	1083.4	1084.3	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1
142.5°	1118.7	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7
145°	1152.8	1153.3	1153.7	1154.2	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1184.1	1184.6	1185.0	1185.5	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7
150°	1212.4	1212.9	1213.3	1213.8	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6
152.5°	1237.1	1238.0	1238.9	1239.8	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3
155°	1259.5	1260.7	1261.8	1262.9	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8
157.5°	1280.0	1281.3	1282.7	1284.0	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4
160°	1297.1	1298.5	1299.8	1301.1	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4
162.5°	1312.5	1314.1	1315.6	1317.2	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3
165°	1325.9	1327.7	1329.4	1331.2	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7
167.5°	1337.0	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0
170°	1346.1	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1
172.5°	1352.1	1353.9	1355.7	1357.5	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3
175°	1357.0	1358.5	1360.1	1361.6	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2
177.5°	1359.2	1361.0	1362.8	1364.6	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1315.9	1309.6	1305.5	1302.3	1299.2	1308.6	1296.1	1282.5	1273.1	1266.9	1264.8
5°	1453.6	1440.1	1428.6	1419.2	1421.3	1421.3	1399.4	1375.4	1354.5	1343.0	1330.5
7.5°	1613.3	1598.7	1575.7	1570.5	1566.3	1540.3	1518.3	1474.5	1448.4	1422.3	1399.4
10°	1771.9	1753.1	1731.2	1723.9	1713.5	1681.1	1647.7	1591.4	1559.0	1511.0	1480.8
12.5°	1920.1	1897.1	1875.2	1870.0	1854.4	1826.2	1768.8	1710.4	1655.0	1603.9	1550.7
15°	2044.3	2038.0	2004.6	1983.8	1949.3	1910.7	1898.2	1818.9	1749.0	1695.7	1599.7
17.5°	2148.6	2119.4	2088.1	2074.5	2061.0	2016.1	1971.2	1889.8	1814.7	1736.4	1674.9
20°	2232.1	2199.8	2177.9	2158.0	2151.8	2100.6	2029.7	1957.7	1875.2	1787.6	1707.2
22.5°	2236.3	2232.1	2217.5	2206.0	2193.5	2160.1	2103.8	2014.0	1926.4	1830.4	1725.0
25°	2149.7	2143.4	2185.2	2174.7	2183.1	2170.6	2140.3	2065.2	1962.9	1850.2	1743.7
27.5°	1888.8	1952.5	2018.2	2041.2	2056.8	2101.7	2116.3	2074.5	1992.1	1872.1	1753.1
30°	1534.0	1618.5	1725.0	1782.4	1826.2	1909.7	2018.2	2031.8	1993.2	1897.1	1751.1
32.5°	1204.2	1281.5	1367.0	1434.9	1493.3	1664.4	1810.5	1915.9	1934.7	1884.6	1756.3
35°	970.5	1003.9	1085.3	1150.0	1229.3	1375.4	1547.6	1717.7	1832.4	1838.7	1740.6
37.5°	800.4	818.1	889.1	925.6	972.6	1100.9	1261.6	1483.9	1662.4	1746.9	1696.8
40°	662.6	703.3	744.0	764.9	798.3	887.0	1041.4	1215.7	1436.9	1593.5	1629.0
42.5°	575.0	592.7	618.8	648.0	668.9	746.1	849.4	1009.1	1208.4	1426.5	1524.6
45°	507.2	513.4	540.6	559.3	581.2	635.5	708.6	842.1	1017.4	1232.4	1399.4
47.5°	450.8	463.3	477.9	489.4	504.0	545.8	608.4	705.4	859.9	1051.9	1231.4
50°	400.7	408.0	426.8	432.0	442.5	471.7	519.7	593.8	721.1	874.5	1060.2
52.5°	353.8	367.3	374.6	381.9	391.3	415.3	446.6	507.2	603.2	747.2	904.7
55°	317.2	321.4	331.8	338.1	345.4	362.1	389.2	434.1	509.2	624.0	773.3
57.5°	281.8	281.8	292.2	297.4	304.7	317.2	341.2	375.7	429.9	515.5	652.2
60°	244.2	245.2	253.6	259.8	261.9	274.4	294.3	321.4	363.2	425.8	537.4
62.5°	210.8	216.0	220.2	222.3	229.6	236.9	253.6	272.4	301.6	356.9	436.2
65°	182.6	183.7	186.8	188.9	192.0	200.4	212.9	225.4	250.4	291.1	355.8
67.5°	150.3	154.4	158.6	158.6	161.7	165.9	178.4	188.9	207.7	231.7	275.5
70°	112.7	114.8	121.1	124.2	128.4	135.7	141.9	148.2	162.8	180.5	213.9
72.5°	93.9	93.9	96.0	97.0	97.0	102.3	111.7	117.9	125.2	137.7	160.7
75°	75.1	75.1	78.3	77.2	79.3	81.4	82.4	86.6	90.8	100.2	113.7
77.5°	59.5	60.5	60.5	61.6	61.6	62.6	63.7	65.7	67.8	73.0	79.3
80°	43.8	44.9	44.9	45.9	45.9	47.0	48.0	49.0	51.1	53.2	56.4
82.5°	30.3	31.3	31.3	32.3	31.3	32.3	33.4	33.4	34.4	36.5	37.6
85°	17.7	17.7	18.8	17.7	17.7	17.7	18.8	18.8	19.8	23.0	23.0
87.5°	5.2	6.3	5.2	6.3	6.3	6.3	6.3	7.3	7.3	8.3	9.4
90°	29.4	29.0	28.5	28.3	27.8	26.9	26.0	25.1	24.2	21.3	18.4
92.5°	33.9	33.6	33.4	33.3	32.5	31.0	29.4	27.9	26.3	24.3	22.3
95°	38.4	38.4	38.4	38.4	37.6	36.0	34.5	32.9	31.3	28.8	26.4
97.5°	41.0	40.7	40.5	40.4	39.5	37.7	35.9	34.1	32.3	43.7	55.2
100°	42.0	41.7	41.5	41.4	40.5	38.7	36.9	35.1	33.3	68.3	103.3
102.5°	42.5	42.1	41.6	41.4	45.1	52.5	59.9	67.3	74.7	113.8	152.8
105°	43.5	43.1	42.6	42.4	62.3	102.0	141.7	181.5	221.2	241.4	261.6
107.5°	163.8	193.2	222.6	237.3	254.6	289.2	323.7	358.3	392.9	389.5	386.1
110°	341.9	374.0	406.1	422.2	425.9	433.3	440.7	448.1	455.5	453.0	450.6

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	527.1	527.5	528.0	528.2	527.2	525.2	523.1	521.1	519.1	516.6	514.2
115°	592.1	591.2	590.3	589.8	588.7	586.4	584.2	581.9	579.7	577.7	575.7
117.5°	648.0	647.7	647.5	647.4	646.5	644.7	642.9	641.1	639.3	638.2	637.1
120°	705.0	705.0	705.0	705.0	704.1	702.3	700.5	698.7	696.9	696.2	695.5
122.5°	760.1	759.8	759.6	759.5	758.9	757.8	756.7	755.5	754.4	753.5	752.6
125°	811.1	810.7	810.2	810.0	809.8	809.3	808.9	808.4	808.0	807.1	806.2
127.5°	863.4	863.8	864.3	864.5	864.2	863.5	862.8	862.2	861.5	860.4	859.3
130°	911.9	912.3	912.8	913.0	912.6	911.7	910.8	909.9	909.0	908.1	907.2
132.5°	956.8	957.5	958.2	958.5	958.0	957.1	956.2	955.3	954.4	953.7	953.1
135°	1002.2	1002.9	1003.6	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1
137.5°	1045.2	1045.6	1046.1	1046.3	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4
140°	1083.6	1084.0	1084.5	1084.7	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3
142.5°	1119.4	1120.1	1120.8	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7
145°	1154.4	1154.4	1154.4	1154.4	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5
147.5°	1182.9	1184.0	1185.1	1185.7	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8
150°	1212.3	1213.0	1213.7	1214.0	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1
152.5°	1237.4	1238.5	1239.6	1240.2	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8
155°	1260.1	1261.5	1262.8	1263.5	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0
157.5°	1280.2	1282.0	1283.8	1284.7	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0
160°	1297.9	1299.5	1301.0	1301.8	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2
162.5°	1314.6	1316.0	1317.3	1318.0	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3
165°	1328.2	1329.8	1331.3	1332.1	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5
167.5°	1338.8	1340.6	1342.4	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2
170°	1347.9	1349.6	1351.4	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3
172.5°	1353.3	1355.4	1357.4	1358.4	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9
175°	1358.0	1359.7	1361.5	1362.4	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0
177.5°	1359.9	1362.1	1364.4	1365.5	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1261.6	1256.4	1251.2	1251.2	1239.7	1229.3	1224.1	1226.2	1219.9	1211.5	1203.2
5°	1316.9	1296.1	1291.9	1280.4	1264.8	1242.8	1231.4	1220.9	1208.4	1191.7	1176.1
7.5°	1368.1	1340.9	1326.3	1314.9	1284.6	1254.3	1229.3	1212.6	1190.7	1165.6	1146.8
10°	1434.9	1384.8	1369.1	1343.0	1300.2	1257.5	1228.2	1201.1	1170.8	1141.6	1116.6
12.5°	1488.1	1430.7	1401.5	1375.4	1320.1	1265.8	1216.8	1183.4	1146.8	1114.5	1082.1
15°	1548.6	1483.9	1432.8	1401.5	1331.6	1265.8	1210.5	1163.5	1122.8	1083.2	1055.0
17.5°	1577.8	1496.4	1473.5	1428.6	1327.4	1261.6	1193.8	1143.7	1094.7	1048.8	1015.4
20°	1623.7	1528.8	1471.4	1441.1	1351.4	1254.3	1175.0	1117.6	1066.5	1017.4	982.0
22.5°	1626.9	1523.6	1486.0	1428.6	1318.0	1232.4	1158.3	1088.4	1028.9	983.0	946.5
25°	1619.6	1514.2	1462.0	1416.1	1324.2	1219.9	1124.9	1056.1	997.6	944.4	901.6
27.5°	1616.4	1487.0	1438.0	1392.1	1288.8	1183.4	1105.1	1026.8	960.1	913.1	869.3
30°	1612.3	1457.8	1398.3	1345.1	1250.2	1155.2	1061.3	993.4	929.8	870.3	826.5
32.5°	1585.1	1418.2	1357.6	1301.3	1199.0	1104.1	1030.0	958.0	889.1	833.8	794.1
35°	1576.8	1381.6	1302.3	1241.8	1141.6	1057.1	978.8	919.4	854.7	799.3	752.4
37.5°	1552.8	1344.1	1258.5	1181.3	1076.9	996.6	939.2	879.7	817.1	757.6	720.0
40°	1511.0	1300.2	1203.2	1123.9	1016.4	935.0	881.8	838.0	776.4	723.2	677.3
42.5°	1449.5	1255.4	1151.0	1067.5	948.6	872.4	828.6	786.8	734.6	679.3	641.8
45°	1378.5	1195.9	1098.8	1006.0	884.9	810.8	764.9	739.9	691.9	644.9	601.1
47.5°	1281.5	1134.3	1038.3	942.3	819.2	747.2	710.6	685.6	652.2	601.1	565.6
50°	1159.4	1055.0	964.2	878.7	754.5	685.6	649.1	630.3	602.1	565.6	531.2
52.5°	1023.7	963.2	888.0	808.7	688.7	624.0	590.6	576.0	555.2	520.7	491.5
55°	887.0	860.9	809.8	731.5	619.9	566.6	537.4	518.6	503.0	477.9	452.9
57.5°	764.9	752.4	716.9	656.4	562.5	507.2	482.1	469.6	457.1	438.3	413.2
60°	638.6	652.2	615.7	585.4	499.9	451.9	429.9	416.4	410.1	393.4	377.8
62.5°	529.1	541.6	520.7	497.8	437.2	394.5	380.9	368.4	364.2	349.6	333.9
65°	429.9	445.6	429.9	417.4	380.9	345.4	328.7	322.5	318.3	308.9	296.4
67.5°	342.3	357.9	350.6	335.0	323.5	294.3	284.9	278.6	276.5	269.2	258.8
70°	257.8	279.7	281.8	272.4	261.9	248.4	242.1	240.0	234.8	228.5	222.3
72.5°	185.7	210.8	211.8	211.8	205.6	205.6	199.3	196.2	196.2	189.9	182.6
75°	136.7	153.4	155.5	157.6	160.7	163.8	159.7	159.7	158.6	152.4	149.2
77.5°	90.8	105.4	110.6	117.9	122.1	122.1	124.2	126.3	124.2	121.1	119.0
80°	58.4	68.9	75.1	79.3	85.6	88.7	91.8	92.9	90.8	89.7	86.6
82.5°	38.6	41.7	44.9	50.1	57.4	62.6	62.6	61.6	63.7	62.6	61.6
85°	21.9	24.0	25.0	26.1	30.3	35.5	36.5	37.6	39.7	37.6	35.5
87.5°	8.3	9.4	9.4	9.4	11.5	12.5	15.7	19.8	18.8	16.7	16.7
90°	15.5	12.6	11.1	10.0	7.7	5.5	3.2	1.0	3.2	5.5	7.7
92.5°	20.2	18.2	17.2	17.9	19.2	20.5	21.9	23.2	21.9	20.5	19.2
95°	23.9	21.4	20.2	24.8	34.0	43.2	52.4	61.6	52.4	43.2	34.0
97.5°	66.6	78.1	83.8	86.9	93.2	99.5	105.8	112.1	105.8	99.5	93.2
100°	138.4	173.4	190.9	188.7	184.2	179.7	175.2	170.7	175.2	179.7	184.2
102.5°	191.9	231.0	250.5	249.0	246.1	243.2	240.2	237.3	240.2	243.2	246.1
105°	281.8	302.0	312.1	310.9	308.4	305.9	303.5	301.0	303.5	305.9	308.4
107.5°	382.8	379.4	377.7	376.7	374.7	372.6	370.6	368.6	370.6	372.6	374.7
110°	448.1	445.6	444.4	443.5	441.7	439.9	438.1	436.3	438.1	439.9	441.7

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	511.7	509.2	508.0	507.2	505.6	504.1	502.5	500.9	502.5	504.1	505.6
115°	573.6	571.6	570.6	569.9	568.6	567.3	565.9	564.6	565.9	567.3	568.6
117.5°	636.0	634.9	634.3	633.5	631.9	630.4	628.8	627.2	628.8	630.4	631.9
120°	694.8	694.1	693.8	692.8	690.8	688.8	686.8	684.8	686.8	688.8	690.8
122.5°	751.7	750.8	750.4	749.6	748.0	746.5	744.9	743.3	744.9	746.5	748.0
125°	805.3	804.4	803.9	803.0	801.2	799.5	797.7	795.9	797.7	799.5	801.2
127.5°	858.2	857.1	856.5	855.6	853.8	852.0	850.2	848.4	850.2	852.0	853.8
130°	906.3	905.4	904.9	904.0	902.2	900.4	898.6	896.8	898.6	900.4	902.2
132.5°	952.4	951.7	951.4	950.5	948.7	946.9	945.1	943.3	945.1	946.9	948.7
135°	998.2	997.3	996.8	996.1	994.8	993.5	992.1	990.8	992.1	993.5	994.8
137.5°	1040.0	1039.5	1039.3	1038.4	1036.6	1034.8	1033.0	1031.2	1033.0	1034.8	1036.6
140°	1078.6	1077.9	1077.6	1076.9	1075.6	1074.3	1072.9	1071.6	1072.9	1074.3	1075.6
142.5°	1116.0	1115.3	1115.0	1114.3	1113.0	1111.6	1110.3	1108.9	1110.3	1111.6	1113.0
145°	1151.1	1150.6	1150.4	1149.6	1148.0	1146.5	1144.9	1143.3	1144.9	1146.5	1148.0
147.5°	1182.4	1181.9	1181.7	1181.1	1180.0	1178.9	1177.7	1176.6	1177.7	1178.9	1180.0
150°	1210.6	1210.1	1209.9	1209.6	1208.9	1208.2	1207.6	1206.9	1207.6	1208.2	1208.9
152.5°	1235.5	1235.3	1235.2	1235.1	1234.9	1234.6	1234.4	1234.2	1234.4	1234.6	1234.9
155°	1257.7	1257.5	1257.4	1257.6	1258.1	1258.5	1259.0	1259.4	1259.0	1258.5	1258.1
157.5°	1279.3	1279.5	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6	1279.6
160°	1296.5	1296.7	1296.8	1296.9	1297.1	1297.4	1297.6	1297.8	1297.6	1297.4	1297.1
162.5°	1311.6	1311.8	1311.9	1312.2	1312.9	1313.6	1314.3	1315.0	1314.3	1313.6	1312.9
165°	1324.8	1325.0	1325.1	1325.4	1326.1	1326.8	1327.4	1328.1	1327.4	1326.8	1326.1
167.5°	1335.2	1335.2	1335.2	1335.6	1336.5	1337.4	1338.3	1339.2	1338.3	1337.4	1336.5
170°	1344.3	1344.3	1344.3	1344.7	1345.6	1346.5	1347.4	1348.3	1347.4	1346.5	1345.6
172.5°	1349.6	1349.4	1349.3	1349.9	1351.0	1352.1	1353.3	1354.4	1353.3	1352.1	1351.0
175°	1354.7	1354.5	1354.4	1355.0	1356.1	1357.2	1358.3	1359.4	1358.3	1357.2	1356.1
177.5°	1356.7	1356.5	1356.4	1357.0	1358.1	1359.2	1360.3	1361.4	1360.3	1359.2	1358.1
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1203.2	1198.0	1195.9	1190.7	1178.2	1169.8	1160.4	1154.1	1155.2	1150.0	1153.1
5°	1165.6	1164.6	1157.3	1146.8	1129.1	1119.7	1103.0	1094.7	1090.5	1091.5	1085.3
7.5°	1134.3	1124.9	1119.7	1103.0	1086.3	1066.5	1052.9	1045.6	1039.4	1033.1	1028.9
10°	1098.8	1090.5	1082.1	1064.4	1041.4	1022.7	1003.9	996.6	987.2	983.0	979.9
12.5°	1061.3	1056.1	1045.6	1024.8	998.7	980.9	959.0	954.8	942.3	934.0	931.9
15°	1026.8	1023.7	1004.9	980.9	954.8	937.1	918.3	905.8	884.9	889.1	881.8
17.5°	990.3	976.7	965.3	932.9	920.4	893.3	871.4	865.1	850.5	841.1	831.7
20°	949.6	941.3	926.7	905.8	875.5	844.2	827.5	817.1	808.7	794.1	790.0
22.5°	911.0	900.6	888.0	860.9	834.8	808.7	785.8	776.4	766.0	755.5	749.3
25°	880.7	865.1	851.5	818.1	792.0	770.1	755.5	739.9	725.3	719.0	716.9
27.5°	833.8	824.4	810.8	779.5	755.5	731.5	718.0	707.5	691.9	684.6	678.3
30°	803.5	784.7	769.1	744.0	720.0	694.0	681.4	668.9	659.5	650.1	642.8
32.5°	762.8	748.2	735.7	710.6	686.6	662.6	649.1	630.3	625.1	617.8	609.4
35°	723.2	713.8	700.2	673.1	647.0	630.3	615.7	597.9	591.7	586.5	579.2
37.5°	685.6	672.0	662.6	636.6	613.6	593.8	582.3	567.7	563.5	557.2	552.0
40°	653.3	639.7	630.3	604.2	580.2	559.3	552.0	537.4	531.2	523.9	520.7
42.5°	616.7	605.3	592.7	573.9	548.9	528.0	513.4	505.1	496.7	493.6	487.3
45°	578.1	567.7	558.3	537.4	511.3	496.7	484.2	472.7	466.5	461.2	457.1
47.5°	544.7	535.3	522.8	499.9	479.0	465.4	452.9	441.4	435.2	428.9	423.7
50°	506.1	500.9	487.3	465.4	445.6	429.9	418.5	408.0	403.8	396.5	388.2
52.5°	471.7	462.3	450.8	433.1	415.3	396.5	380.9	374.6	367.3	363.2	355.8
55°	431.0	424.7	412.2	396.5	377.8	362.1	350.6	342.3	332.9	328.7	319.3
57.5°	396.5	385.1	378.8	359.0	341.2	325.6	317.2	308.9	298.5	292.2	288.0
60°	359.0	348.5	339.1	322.5	309.9	293.2	280.7	273.4	266.1	257.8	253.6
62.5°	322.5	314.1	302.6	289.1	273.4	259.8	250.4	240.0	235.8	227.5	224.4
65°	282.8	276.5	267.1	251.5	239.0	227.5	218.1	209.8	205.6	202.4	200.4
67.5°	247.3	239.0	232.7	219.1	205.6	196.2	191.0	185.7	180.5	177.4	174.3
70°	210.8	204.5	198.3	185.7	176.4	168.0	163.8	159.7	156.5	153.4	150.3
72.5°	173.2	170.1	163.8	155.5	148.2	141.9	138.8	133.6	130.4	125.2	123.1
75°	143.0	137.7	134.6	127.3	121.1	115.8	111.7	105.4	101.2	99.1	98.1
77.5°	112.7	110.6	106.4	100.2	97.0	91.8	85.6	83.5	81.4	81.4	80.4
80°	84.5	81.4	78.3	73.0	69.9	65.7	65.7	65.7	64.7	65.7	64.7
82.5°	57.4	55.3	53.2	50.1	49.0	49.0	50.1	50.1	50.1	50.1	50.1
85°	33.4	33.4	33.4	34.4	33.4	33.4	34.4	35.5	34.4	34.4	33.4
87.5°	15.7	15.7	16.7	16.7	17.7	17.7	17.7	17.7	17.7	17.7	18.8
90°	10.0	11.1	12.6	15.5	18.4	21.3	24.2	25.1	26.0	26.9	27.8
92.5°	17.9	17.2	18.2	20.2	22.3	24.3	26.3	27.9	29.4	31.0	32.5
95°	24.8	20.2	21.4	23.9	26.4	28.8	31.3	32.9	34.5	36.0	37.6
97.5°	86.9	83.8	78.1	66.6	55.2	43.7	32.3	34.1	35.9	37.7	39.5
100°	188.7	190.9	173.4	138.4	103.3	68.3	33.3	35.1	36.9	38.7	40.5
102.5°	249.0	250.5	231.0	191.9	152.8	113.8	74.7	67.3	59.9	52.5	45.1
105°	310.9	312.1	302.0	281.8	261.6	241.4	221.2	181.5	141.7	102.0	62.3
107.5°	376.7	377.7	379.4	382.8	386.1	389.5	392.9	358.3	323.7	289.2	254.6
110°	443.5	444.4	445.6	448.1	450.6	453.0	455.5	448.1	440.7	433.3	425.9

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	507.2	508.0	509.2	511.7	514.2	516.6	519.1	521.1	523.1	525.2	527.2
115°	569.9	570.6	571.6	573.6	575.7	577.7	579.7	581.9	584.2	586.4	588.7
117.5°	633.5	634.3	634.9	636.0	637.1	638.2	639.3	641.1	642.9	644.7	646.5
120°	692.8	693.8	694.1	694.8	695.5	696.2	696.9	698.7	700.5	702.3	704.1
122.5°	749.6	750.4	750.8	751.7	752.6	753.5	754.4	755.5	756.7	757.8	758.9
125°	803.0	803.9	804.4	805.3	806.2	807.1	808.0	808.4	808.9	809.3	809.8
127.5°	855.6	856.5	857.1	858.2	859.3	860.4	861.5	862.2	862.8	863.5	864.2
130°	904.0	904.9	905.4	906.3	907.2	908.1	909.0	909.9	910.8	911.7	912.6
132.5°	950.5	951.4	951.7	952.4	953.1	953.7	954.4	955.3	956.2	957.1	958.0
135°	996.1	996.8	997.3	998.2	999.1	1000.0	1000.9	1001.6	1002.2	1002.9	1003.6
137.5°	1038.4	1039.3	1039.5	1040.0	1040.4	1040.9	1041.3	1042.4	1043.5	1044.6	1045.7
140°	1076.9	1077.6	1077.9	1078.6	1079.3	1080.0	1080.7	1081.6	1082.5	1083.4	1084.3
142.5°	1114.3	1115.0	1115.3	1116.0	1116.7	1117.3	1118.0	1118.7	1119.4	1120.1	1120.8
145°	1149.6	1150.4	1150.6	1151.1	1151.5	1152.0	1152.4	1152.8	1153.3	1153.7	1154.2
147.5°	1181.1	1181.7	1181.9	1182.4	1182.8	1183.3	1183.7	1184.1	1184.6	1185.0	1185.5
150°	1209.6	1209.9	1210.1	1210.6	1211.1	1211.5	1212.0	1212.4	1212.9	1213.3	1213.8
152.5°	1235.1	1235.2	1235.3	1235.5	1235.8	1236.0	1236.2	1237.1	1238.0	1238.9	1239.8
155°	1257.6	1257.4	1257.5	1257.7	1258.0	1258.2	1258.4	1259.5	1260.7	1261.8	1262.9
157.5°	1279.6	1279.6	1279.5	1279.3	1279.0	1278.8	1278.6	1280.0	1281.3	1282.7	1284.0
160°	1296.9	1296.8	1296.7	1296.5	1296.2	1296.0	1295.8	1297.1	1298.5	1299.8	1301.1
162.5°	1312.2	1311.9	1311.8	1311.6	1311.3	1311.1	1310.9	1312.5	1314.1	1315.6	1317.2
165°	1325.4	1325.1	1325.0	1324.8	1324.5	1324.3	1324.1	1325.9	1327.7	1329.4	1331.2
167.5°	1335.6	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1337.0	1338.8	1340.6	1342.4
170°	1344.7	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1346.1	1347.9	1349.6	1351.4
172.5°	1349.9	1349.3	1349.4	1349.6	1349.9	1350.1	1350.3	1352.1	1353.9	1355.7	1357.5
175°	1355.0	1354.4	1354.5	1354.7	1355.0	1355.2	1355.4	1357.0	1358.5	1360.1	1361.6
177.5°	1357.0	1356.4	1356.5	1356.7	1357.0	1357.2	1357.4	1359.2	1361.0	1362.8	1364.6
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1152.1	1153.1	1150.0	1143.7	1142.7	1144.8	1151.0	1148.9	1143.7	1153.1	1144.8
5°	1088.4	1083.2	1081.1	1083.2	1076.9	1073.8	1080.1	1076.9	1080.1	1081.1	1084.2
7.5°	1026.8	1027.9	1021.6	1022.7	1014.3	1016.4	1016.4	1016.4	1019.5	1021.6	1025.8
10°	973.6	975.7	968.4	969.4	963.2	959.0	962.1	968.4	968.4	968.4	970.5
12.5°	930.8	921.4	916.2	915.2	907.9	905.8	912.0	914.1	919.4	919.4	922.5
15°	877.6	875.5	871.4	871.4	853.6	857.8	859.9	867.2	877.6	869.3	871.4
17.5°	829.6	824.4	819.2	817.1	815.0	808.7	817.1	816.0	822.3	823.3	826.5
20°	786.8	782.7	772.2	773.3	775.3	766.0	771.2	771.2	777.4	783.7	791.0
22.5°	745.1	740.9	735.7	737.8	731.5	729.4	729.4	734.6	742.0	747.2	746.1
25°	712.7	705.4	702.3	699.2	696.0	698.1	695.0	700.2	705.4	708.6	705.4
27.5°	676.2	673.1	666.8	663.7	658.5	660.6	662.6	666.8	669.9	669.9	673.1
30°	640.7	636.6	634.5	631.3	631.3	627.2	628.2	632.4	635.5	638.6	642.8
32.5°	606.3	603.2	600.0	600.0	597.9	596.9	595.9	602.1	602.1	608.4	608.4
35°	578.1	572.9	572.9	567.7	569.8	568.7	566.6	570.8	571.9	576.0	575.0
37.5°	546.8	546.8	544.7	539.5	535.3	536.4	541.6	541.6	544.7	543.7	546.8
40°	515.5	513.4	513.4	510.3	509.2	508.2	509.2	510.3	515.5	514.5	515.5
42.5°	484.2	485.2	480.0	480.0	480.0	476.9	477.9	479.0	481.1	483.2	486.3
45°	453.9	451.9	450.8	448.7	446.6	447.7	446.6	450.8	449.8	451.9	455.0
47.5°	421.6	418.5	417.4	413.2	413.2	415.3	414.3	417.4	418.5	421.6	419.5
50°	390.3	386.1	383.0	384.0	377.8	379.8	379.8	383.0	386.1	387.2	389.2
52.5°	353.8	352.7	351.7	346.5	345.4	344.4	345.4	346.5	350.6	353.8	354.8
55°	318.3	317.2	311.0	308.9	305.8	305.8	307.8	308.9	316.2	317.2	321.4
57.5°	285.9	282.8	275.5	274.4	274.4	274.4	271.3	275.5	277.6	282.8	282.8
60°	250.4	250.4	244.2	244.2	245.2	244.2	244.2	245.2	245.2	249.4	251.5
62.5°	222.3	221.2	221.2	219.1	218.1	219.1	218.1	218.1	219.1	222.3	225.4
65°	197.2	196.2	195.1	194.1	192.0	192.0	193.1	195.1	195.1	197.2	198.3
67.5°	173.2	173.2	171.1	171.1	170.1	169.1	170.1	169.1	173.2	173.2	174.3
70°	149.2	148.2	145.1	144.0	140.9	141.9	141.9	145.1	146.1	148.2	150.3
72.5°	120.0	120.0	117.9	115.8	116.9	114.8	114.8	115.8	115.8	119.0	120.0
75°	99.1	97.0	96.0	97.0	96.0	98.1	96.0	96.0	98.1	98.1	98.1
77.5°	81.4	81.4	80.4	80.4	81.4	80.4	81.4	81.4	81.4	80.4	81.4
80°	66.8	65.7	65.7	65.7	64.7	64.7	64.7	64.7	64.7	64.7	64.7
82.5°	50.1	50.1	49.0	50.1	50.1	49.0	50.1	49.0	49.0	50.1	50.1
85°	33.4	35.5	33.4	33.4	34.4	34.4	35.5	34.4	35.5	33.4	34.4
87.5°	17.7	18.8	18.8	17.7	17.7	18.8	18.8	18.8	19.8	17.7	18.8
90°	28.3	28.5	29.0	29.4	29.9	30.3	29.9	29.4	29.0	28.5	28.3
92.5°	33.3	33.4	33.6	33.9	34.1	34.3	34.1	33.9	33.6	33.4	33.3
95°	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4	38.4
97.5°	40.4	40.5	40.7	41.0	41.2	41.4	41.2	41.0	40.7	40.5	40.4
100°	41.4	41.5	41.7	42.0	42.2	42.4	42.2	42.0	41.7	41.5	41.4
102.5°	41.4	41.6	42.1	42.5	43.0	43.4	43.0	42.5	42.1	41.6	41.4
105°	42.4	42.6	43.1	43.5	44.0	44.4	44.0	43.5	43.1	42.6	42.4
107.5°	237.3	222.6	193.2	163.8	134.4	105.0	134.4	163.8	193.2	222.6	237.3
110°	422.2	406.1	374.0	341.9	309.8	277.7	309.8	341.9	374.0	406.1	422.2

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	528.2	528.0	527.5	527.1	526.6	526.2	526.6	527.1	527.5	528.0	528.2
115°	589.8	590.3	591.2	592.1	593.0	593.9	593.0	592.1	591.2	590.3	589.8
117.5°	647.4	647.5	647.7	648.0	648.2	648.4	648.2	648.0	647.7	647.5	647.4
120°	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0	705.0
122.5°	759.5	759.6	759.8	760.1	760.3	760.5	760.3	760.1	759.8	759.6	759.5
125°	810.0	810.2	810.7	811.1	811.6	812.0	811.6	811.1	810.7	810.2	810.0
127.5°	864.5	864.3	863.8	863.4	862.9	862.5	862.9	863.4	863.8	864.3	864.5
130°	913.0	912.8	912.3	911.9	911.4	911.0	911.4	911.9	912.3	912.8	913.0
132.5°	958.5	958.2	957.5	956.8	956.1	955.4	956.1	956.8	957.5	958.2	958.5
135°	1003.9	1003.6	1002.9	1002.2	1001.6	1000.9	1001.6	1002.2	1002.9	1003.6	1003.9
137.5°	1046.3	1046.1	1045.6	1045.2	1044.7	1044.3	1044.7	1045.2	1045.6	1046.1	1046.3
140°	1084.7	1084.5	1084.0	1083.6	1083.1	1082.7	1083.1	1083.6	1084.0	1084.5	1084.7
142.5°	1121.1	1120.8	1120.1	1119.4	1118.7	1118.0	1118.7	1119.4	1120.1	1120.8	1121.1
145°	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4	1154.4
147.5°	1185.7	1185.1	1184.0	1182.9	1181.7	1180.6	1181.7	1182.9	1184.0	1185.1	1185.7
150°	1214.0	1213.7	1213.0	1212.3	1211.6	1210.9	1211.6	1212.3	1213.0	1213.7	1214.0
152.5°	1240.2	1239.6	1238.5	1237.4	1236.3	1235.2	1236.3	1237.4	1238.5	1239.6	1240.2
155°	1263.5	1262.8	1261.5	1260.1	1258.8	1257.4	1258.8	1260.1	1261.5	1262.8	1263.5
157.5°	1284.7	1283.8	1282.0	1280.2	1278.4	1276.6	1278.4	1280.2	1282.0	1283.8	1284.7
160°	1301.8	1301.0	1299.5	1297.9	1296.4	1294.8	1296.4	1297.9	1299.5	1301.0	1301.8
162.5°	1318.0	1317.3	1316.0	1314.6	1313.3	1311.9	1313.3	1314.6	1316.0	1317.3	1318.0
165°	1332.1	1331.3	1329.8	1328.2	1326.7	1325.1	1326.7	1328.2	1329.8	1331.3	1332.1
167.5°	1343.3	1342.4	1340.6	1338.8	1337.0	1335.2	1337.0	1338.8	1340.6	1342.4	1343.3
170°	1352.3	1351.4	1349.6	1347.9	1346.1	1344.3	1346.1	1347.9	1349.6	1351.4	1352.3
172.5°	1358.4	1357.4	1355.4	1353.3	1351.3	1349.3	1351.3	1353.3	1355.4	1357.4	1358.4
175°	1362.4	1361.5	1359.7	1358.0	1356.2	1354.4	1356.2	1358.0	1359.7	1361.5	1362.4
177.5°	1365.5	1364.4	1362.1	1359.9	1357.6	1355.4	1357.6	1359.9	1362.1	1364.4	1365.5
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8	1218.8
2.5°	1153.1	1157.3	1153.1	1144.8	1153.1	1158.3	1163.5	1171.9	1176.1	1176.1	1182.3
5°	1087.4	1095.7	1092.6	1090.5	1098.8	1104.1	1112.4	1122.8	1134.3	1141.6	1150.0
7.5°	1028.9	1034.1	1039.4	1039.4	1047.7	1059.2	1071.7	1084.2	1098.8	1109.3	1115.5
10°	977.8	982.0	985.1	989.3	1001.8	1014.3	1031.0	1046.7	1059.2	1070.7	1081.1
12.5°	928.7	935.0	942.3	945.4	954.8	970.5	986.1	1004.9	1024.8	1036.2	1046.7
15°	881.8	884.9	893.3	902.7	911.0	927.7	947.5	967.4	984.1	1001.8	1011.2
17.5°	833.8	834.8	856.7	851.5	878.7	894.3	904.7	923.5	950.7	965.3	979.9
20°	786.8	797.3	806.7	811.9	826.5	844.2	874.5	889.1	911.0	924.6	937.1
22.5°	750.3	766.0	766.0	778.5	785.8	802.5	824.4	852.6	876.6	886.0	903.7
25°	718.0	725.3	737.8	742.0	755.5	770.1	784.7	815.0	841.1	853.6	866.1
27.5°	676.2	685.6	702.3	702.3	720.0	735.7	753.4	773.3	799.3	817.1	830.7
30°	643.9	653.3	660.6	672.0	679.3	694.0	725.3	739.9	762.8	778.5	795.2
32.5°	613.6	620.9	627.2	639.7	648.0	664.7	681.4	707.5	727.3	742.0	759.7
35°	580.2	587.5	595.9	605.3	617.8	633.4	649.1	671.0	690.8	704.4	719.0
37.5°	548.9	554.1	566.6	572.9	583.3	597.9	617.8	640.7	658.5	668.9	683.5
40°	518.6	522.8	532.2	543.7	551.0	562.5	583.3	603.2	625.1	637.6	649.1
42.5°	486.3	491.5	499.9	511.3	522.8	535.3	546.8	569.8	589.6	600.0	612.6
45°	458.1	461.2	467.5	479.0	490.5	499.9	517.6	538.5	557.2	565.6	579.2
47.5°	424.7	427.8	437.2	442.5	455.0	467.5	485.2	506.1	522.8	531.2	543.7
50°	390.3	393.4	399.7	411.2	419.5	433.1	448.7	466.5	487.3	498.8	506.1
52.5°	356.9	363.2	368.4	377.8	388.2	401.8	416.4	433.1	450.8	462.3	470.6
55°	323.5	328.7	335.0	340.2	352.7	365.2	381.9	397.6	413.2	423.7	433.1
57.5°	285.9	293.2	299.5	309.9	319.3	329.8	348.5	361.1	379.8	387.2	395.5
60°	253.6	260.9	266.1	274.4	282.8	296.4	308.9	324.5	340.2	349.6	360.0
62.5°	226.4	229.6	232.7	241.1	249.4	261.9	274.4	290.1	306.8	312.0	320.4
65°	199.3	202.4	207.7	215.0	221.2	228.5	242.1	254.6	270.3	278.6	281.8
67.5°	176.4	179.5	180.5	185.7	191.0	199.3	206.6	219.1	233.8	239.0	245.2
70°	150.3	155.5	156.5	160.7	162.8	168.0	176.4	185.7	197.2	206.6	211.8
72.5°	120.0	127.3	129.4	135.7	138.8	144.0	150.3	157.6	164.9	169.1	173.2
75°	98.1	100.2	101.2	106.4	111.7	119.0	122.1	126.3	132.5	137.7	141.9
77.5°	81.4	82.4	83.5	83.5	84.5	88.7	95.0	100.2	104.4	106.4	109.6
80°	65.7	64.7	64.7	65.7	65.7	65.7	67.8	75.1	77.2	82.4	81.4
82.5°	51.1	49.0	50.1	49.0	49.0	49.0	49.0	50.1	50.1	53.2	55.3
85°	33.4	34.4	33.4	33.4	32.3	33.4	32.3	32.3	31.3	31.3	30.3
87.5°	17.7	18.8	17.7	17.7	16.7	17.7	16.7	16.7	15.7	15.7	13.6
90°	27.8	26.9	26.0	25.1	24.2	21.3	18.4	15.5	12.6	11.1	10.0
92.5°	32.5	31.0	29.4	27.9	26.3	24.3	22.3	20.2	18.2	17.2	17.9
95°	37.6	36.0	34.5	32.9	31.3	28.8	26.4	23.9	21.4	20.2	24.8
97.5°	39.5	37.7	35.9	34.1	32.3	43.7	55.2	66.6	78.1	83.8	86.9
100°	40.5	38.7	36.9	35.1	33.3	68.3	103.3	138.4	173.4	190.9	188.7
102.5°	45.1	52.5	59.9	67.3	74.7	113.8	152.8	191.9	231.0	250.5	249.0
105°	62.3	102.0	141.7	181.5	221.2	241.4	261.6	281.8	302.0	312.1	310.9
107.5°	254.6	289.2	323.7	358.3	392.9	389.5	386.1	382.8	379.4	377.7	376.7
110°	425.9	433.3	440.7	448.1	455.5	453.0	450.6	448.1	445.6	444.4	443.5

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	527.2	525.2	523.1	521.1	519.1	516.6	514.2	511.7	509.2	508.0	507.2
115°	588.7	586.4	584.2	581.9	579.7	577.7	575.7	573.6	571.6	570.6	569.9
117.5°	646.5	644.7	642.9	641.1	639.3	638.2	637.1	636.0	634.9	634.3	633.5
120°	704.1	702.3	700.5	698.7	696.9	696.2	695.5	694.8	694.1	693.8	692.8
122.5°	758.9	757.8	756.7	755.5	754.4	753.5	752.6	751.7	750.8	750.4	749.6
125°	809.8	809.3	808.9	808.4	808.0	807.1	806.2	805.3	804.4	803.9	803.0
127.5°	864.2	863.5	862.8	862.2	861.5	860.4	859.3	858.2	857.1	856.5	855.6
130°	912.6	911.7	910.8	909.9	909.0	908.1	907.2	906.3	905.4	904.9	904.0
132.5°	958.0	957.1	956.2	955.3	954.4	953.7	953.1	952.4	951.7	951.4	950.5
135°	1003.6	1002.9	1002.2	1001.6	1000.9	1000.0	999.1	998.2	997.3	996.8	996.1
137.5°	1045.7	1044.6	1043.5	1042.4	1041.3	1040.9	1040.4	1040.0	1039.5	1039.3	1038.4
140°	1084.3	1083.4	1082.5	1081.6	1080.7	1080.0	1079.3	1078.6	1077.9	1077.6	1076.9
142.5°	1120.8	1120.1	1119.4	1118.7	1118.0	1117.3	1116.7	1116.0	1115.3	1115.0	1114.3
145°	1154.2	1153.7	1153.3	1152.8	1152.4	1152.0	1151.5	1151.1	1150.6	1150.4	1149.6
147.5°	1185.5	1185.0	1184.6	1184.1	1183.7	1183.3	1182.8	1182.4	1181.9	1181.7	1181.1
150°	1213.8	1213.3	1212.9	1212.4	1212.0	1211.5	1211.1	1210.6	1210.1	1209.9	1209.6
152.5°	1239.8	1238.9	1238.0	1237.1	1236.2	1236.0	1235.8	1235.5	1235.3	1235.2	1235.1
155°	1262.9	1261.8	1260.7	1259.5	1258.4	1258.2	1258.0	1257.7	1257.5	1257.4	1257.6
157.5°	1284.0	1282.7	1281.3	1280.0	1278.6	1278.8	1279.0	1279.3	1279.5	1279.6	1279.6
160°	1301.1	1299.8	1298.5	1297.1	1295.8	1296.0	1296.2	1296.5	1296.7	1296.8	1296.9
162.5°	1317.2	1315.6	1314.1	1312.5	1310.9	1311.1	1311.3	1311.6	1311.8	1311.9	1312.2
165°	1331.2	1329.4	1327.7	1325.9	1324.1	1324.3	1324.5	1324.8	1325.0	1325.1	1325.4
167.5°	1342.4	1340.6	1338.8	1337.0	1335.2	1335.2	1335.2	1335.2	1335.2	1335.2	1335.6
170°	1351.4	1349.6	1347.9	1346.1	1344.3	1344.3	1344.3	1344.3	1344.3	1344.3	1344.7
172.5°	1357.5	1355.7	1353.9	1352.1	1350.3	1350.1	1349.9	1349.6	1349.4	1349.3	1349.9
175°	1361.6	1360.1	1358.5	1357.0	1355.4	1355.2	1355.0	1354.7	1354.5	1354.4	1355.0
177.5°	1364.6	1362.8	1361.0	1359.2	1357.4	1357.2	1357.0	1356.7	1356.5	1356.4	1357.0
180°	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4	1359.4

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1218.8	1218.8	1218.8	1218.8
2.5°	1187.5	1194.8	1209.5	1222.0
5°	1162.5	1174.0	1195.9	1217.8
7.5°	1132.2	1150.0	1178.2	1208.4
10°	1103.0	1126.0	1160.4	1195.9
12.5°	1073.8	1097.8	1134.3	1180.2
15°	1039.4	1064.4	1108.2	1163.5
17.5°	1009.1	1042.5	1082.1	1137.5
20°	976.7	1001.8	1052.9	1111.4
22.5°	936.1	977.8	1025.8	1087.4
25°	903.7	940.2	988.2	1058.1
27.5°	864.0	906.8	965.3	1026.8
30°	831.7	867.2	921.4	995.5
32.5°	794.1	835.9	892.2	965.3
35°	760.7	796.2	849.4	923.5
37.5°	721.1	759.7	819.2	884.9
40°	686.6	724.2	780.6	842.1
42.5°	644.9	684.6	740.9	793.1
45°	611.5	648.0	692.9	740.9
47.5°	570.8	609.4	653.3	686.6
50°	534.3	569.8	604.2	632.4
52.5°	494.6	527.0	558.3	579.2
55°	458.1	483.2	508.2	522.8
57.5°	415.3	439.3	460.2	468.5
60°	377.8	397.6	411.2	420.5
62.5°	338.1	352.7	363.2	368.4
65°	299.5	309.9	315.1	320.4
67.5°	259.8	269.2	272.4	278.6
70°	218.1	228.5	230.6	233.8
72.5°	186.8	186.8	191.0	195.1
75°	149.2	151.3	153.4	153.4
77.5°	116.9	116.9	119.0	120.0
80°	85.6	86.6	86.6	85.6
82.5°	58.4	60.5	58.4	57.4
85°	32.3	36.5	34.4	34.4
87.5°	13.6	13.6	15.7	13.6
90°	7.7	5.5	3.2	1.0
92.5°	19.2	20.5	21.9	23.2
95°	34.0	43.2	52.4	61.6
97.5°	93.2	99.5	105.8	112.1
100°	184.2	179.7	175.2	170.7
102.5°	246.1	243.2	240.2	237.3
105°	308.4	305.9	303.5	301.0
107.5°	374.7	372.6	370.6	368.6
110°	441.7	439.9	438.1	436.3

TEST NUMBER: P1031215

CATALOG NUMBER: S123RDIW-B775D1030UB2750-4F0-XX-W2A-A_2700K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	505.6	504.1	502.5	500.9
115°	568.6	567.3	565.9	564.6
117.5°	631.9	630.4	628.8	627.2
120°	690.8	688.8	686.8	684.8
122.5°	748.0	746.5	744.9	743.3
125°	801.2	799.5	797.7	795.9
127.5°	853.8	852.0	850.2	848.4
130°	902.2	900.4	898.6	896.8
132.5°	948.7	946.9	945.1	943.3
135°	994.8	993.5	992.1	990.8
137.5°	1036.6	1034.8	1033.0	1031.2
140°	1075.6	1074.3	1072.9	1071.6
142.5°	1113.0	1111.6	1110.3	1108.9
145°	1148.0	1146.5	1144.9	1143.3
147.5°	1180.0	1178.9	1177.7	1176.6
150°	1208.9	1208.2	1207.6	1206.9
152.5°	1234.9	1234.6	1234.4	1234.2
155°	1258.1	1258.5	1259.0	1259.4
157.5°	1279.6	1279.6	1279.6	1279.6
160°	1297.1	1297.4	1297.6	1297.8
162.5°	1312.9	1313.6	1314.3	1315.0
165°	1326.1	1326.8	1327.4	1328.1
167.5°	1336.5	1337.4	1338.3	1339.2
170°	1345.6	1346.5	1347.4	1348.3
172.5°	1351.0	1352.1	1353.3	1354.4
175°	1356.1	1357.2	1358.3	1359.4
177.5°	1358.1	1359.2	1360.3	1361.4
180°	1359.4	1359.4	1359.4	1359.4

(END OF REPORT)